

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1055039

Luminaire Tested: SQ4R-FA-075D-927-1-UNV-STD-W-4

Issue Date: 7/23/2025

Test Information

Test Method: LM-79-2019
Report Number: P1055039
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-892-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/23/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4R-FA-075D-927-1-UNV-STD-W-4
Description: CORELITE SQ4R RECESSED LED LUMINAIRE WITH ASYMMETRIC FROSTED CONTINUOUS ROLL LENS
750 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2124.6 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular (W 0.29' x L: 3.83' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	89	87
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73
3	91	81	73	66	88	79	72	66	76	70	64	73	68	63	71	66	62
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54
5	77	64	55	49	75	63	54	48	61	53	48	59	52	47	57	51	47
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41
7	66	52	44	38	64	51	43	37	50	42	37	48	42	37	47	41	37
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7887	7887	7887	7887
5°	7955	6449	7955	8202
10°	7911	5948	7911	8319
15°	7833	6999	7833	8381
20°	7679	7226	7679	8409
25°	7352	7295	7352	8332
30°	6928	7177	6928	8314
35°	6186	7023	6186	8226
40°	5163	6974	5163	8075
45°	4622	6891	4622	7852
50°	4922	6825	4922	7522
55°	4644	6972	4644	7142
60°	4806	6835	4806	6493
65°	4378	6533	4378	5843
70°	3054	6131	3054	5213
75°	2712	5420	2712	4527
80°	2234	4214	2234	3870
85°	1370	2916	1370	3424

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 225°

Vertical Angle: 45°

Luminance: 8021 cd/sqm

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.0	3.5
10°-20°	210.0	9.9
20°-30°	324.6	15.3
30°-40°	387.5	18.2
40°-50°	389.8	18.3
50°-60°	339.2	16.0
60°-70°	240.5	11.3
70°-80°	127.3	6.0
80°-90°	31.7	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	608.6	28.6
0°-40°	996.1	46.9
0°-60°	1725.1	81.2
0°-90°	2124.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2124.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	819	819	819	819	819	
5°	823	667	823	849	823	78
15°	786	702	786	841	786	221
25°	692	687	692	784	692	318
35°	526	598	526	700	526	326
45°	340	506	340	577	340	272
55°	277	415	277	426	277	254
65°	192	287	192	256	192	184
75°	73	146	73	122	73	77
85°	12	26	12	31	12	17
90°	0	0	0	0	0	1
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2
2.5°	826.2	824.7	822.3	820.8	818.5	817.7	816.9	816.1	815.4	813.0	811.5
5°	823.1	820.0	816.1	813.0	809.2	806.1	803.7	800.6	797.5	792.9	788.2
7.5°	816.9	811.5	806.1	800.6	795.2	788.2	781.3	774.3	767.3	754.9	740.2
10°	809.2	801.4	792.9	785.1	776.6	760.3	744.1	727.0	710.7	689.0	674.3
12.5°	798.3	785.1	771.2	758.0	744.1	720.8	698.3	675.1	651.8	637.1	628.6
15°	785.9	765.0	743.3	722.4	700.7	680.5	660.4	639.4	619.3	608.4	602.2
17.5°	768.9	741.0	713.8	685.9	658.0	642.5	626.3	610.8	594.5	586.7	582.1
20°	749.5	719.3	688.3	658.0	627.0	614.6	602.2	589.1	576.7	569.7	567.3
22.5°	723.1	693.7	664.2	634.8	605.3	593.7	582.1	569.7	558.0	552.6	554.2
25°	692.1	666.6	640.2	614.6	588.3	577.4	565.8	554.9	543.3	537.1	541.8
27.5°	659.6	637.9	616.2	594.5	572.8	561.1	549.5	537.1	525.5	523.2	534.0
30°	623.2	606.9	589.8	573.6	556.5	544.1	531.7	519.3	506.9	506.1	523.2
32.5°	582.1	570.4	559.6	548.0	536.3	524.7	513.1	500.7	489.1	488.3	509.2
35°	526.3	523.2	520.1	516.2	513.1	501.5	489.8	478.2	466.6	467.4	490.6
37.5°	465.0	470.5	476.7	482.1	487.5	476.7	466.6	455.7	444.9	444.9	469.7
40°	410.8	421.6	432.5	443.3	454.2	447.2	439.5	432.5	424.7	422.4	448.0
42.5°	370.5	380.6	390.6	399.9	410.0	407.7	406.1	403.8	401.5	398.4	423.2
45°	339.5	341.0	343.4	344.9	346.5	354.2	362.0	369.7	377.5	375.1	397.6
47.5°	329.4	319.3	308.5	298.4	287.6	303.8	320.1	335.6	351.9	351.1	371.3
50°	328.6	308.5	287.6	267.4	246.5	265.8	285.2	303.8	323.2	326.3	341.8
52.5°	298.4	279.8	261.2	241.8	223.2	240.3	256.5	273.6	289.9	299.2	313.1
55°	276.7	258.9	241.0	223.2	205.4	217.0	227.9	239.5	250.3	270.5	282.9
57.5°	272.0	250.3	228.6	206.2	184.5	192.2	199.2	206.9	213.9	233.3	248.8
60°	249.6	227.9	206.2	183.7	162.0	167.4	172.1	177.5	182.1	196.9	215.5
62.5°	226.3	206.2	186.8	166.6	146.5	151.9	156.6	162.0	166.6	169.7	189.9
65°	192.2	177.5	162.8	148.0	133.3	138.0	141.8	146.5	150.4	151.1	169.7
67.5°	146.5	140.3	134.1	127.1	120.9	125.6	129.4	134.1	138.0	138.7	154.2
70°	108.5	108.5	108.5	107.7	107.7	111.6	116.3	120.1	124.0	125.6	137.2
72.5°	89.9	91.5	93.8	95.3	96.9	100.0	103.1	106.2	109.3	110.8	119.4
75°	72.9	76.0	79.1	81.4	84.5	86.8	89.1	90.7	93.0	93.8	100.0
77.5°	53.5	57.4	61.2	64.3	68.2	70.5	72.1	74.4	76.0	74.4	79.1
80°	40.3	42.6	45.0	46.5	48.8	50.4	52.7	54.3	55.8	54.3	57.4
82.5°	27.1	27.9	29.5	30.2	31.0	32.6	34.1	35.7	37.2	35.7	38.0
85°	12.4	13.2	14.7	15.5	16.3	17.8	18.6	20.2	20.9	20.2	20.9
87.5°	3.9	4.7	5.4	5.4	6.2	7.0	7.8	8.5	9.3	9.3	10.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2
2.5°	810.7	809.2	806.1	803.7	800.6	797.5	796.0	794.4	792.9	791.3	792.9
5°	782.8	778.2	771.2	764.2	757.2	750.3	741.0	731.7	724.7	717.7	716.2
7.5°	724.7	710.0	697.6	684.4	672.0	658.8	651.8	644.9	638.7	632.5	630.9
10°	658.8	644.1	635.6	627.8	619.3	610.8	606.9	602.2	601.5	599.9	600.7
12.5°	619.3	610.8	606.1	601.5	596.0	591.4	590.6	589.8	592.2	593.7	599.1
15°	596.0	589.8	588.3	586.7	584.4	582.9	587.5	591.4	605.3	618.5	634.0
17.5°	578.2	573.6	577.4	580.5	584.4	587.5	611.5	635.6	654.2	672.0	677.4
20°	565.8	563.5	579.0	595.3	610.8	626.3	644.9	662.7	669.7	675.9	679.0
22.5°	554.9	556.5	579.8	602.2	625.5	648.0	655.7	662.7	667.3	672.0	674.3
25°	547.2	551.8	575.1	599.1	622.4	645.6	650.3	654.2	655.7	656.5	661.9
27.5°	544.9	555.7	575.9	596.0	615.4	635.6	638.7	641.8	643.3	644.1	649.5
30°	539.4	556.5	573.6	589.8	606.9	623.2	622.4	621.6	624.7	627.8	633.2
32.5°	530.1	551.1	564.2	578.2	591.4	604.6	603.8	603.0	607.7	611.5	615.4
35°	514.6	537.9	549.5	560.4	572.0	582.9	583.6	583.6	587.5	591.4	593.7
37.5°	495.3	520.1	530.9	541.8	551.8	562.7	561.9	561.1	562.7	563.5	567.3
40°	472.8	498.4	509.2	520.1	530.1	541.0	538.7	535.6	535.6	534.8	539.4
42.5°	447.2	472.0	482.9	493.7	503.8	514.6	510.0	504.6	506.1	506.9	513.1
45°	420.9	443.3	453.4	464.3	474.3	484.4	481.3	477.4	480.5	483.6	489.8
47.5°	391.4	411.6	422.4	433.3	444.1	455.0	453.4	451.1	454.2	457.3	464.3
50°	358.1	373.6	386.8	399.9	413.1	426.3	426.3	426.3	429.4	431.7	438.7
52.5°	326.3	340.3	355.8	371.3	386.0	401.5	402.3	403.0	406.1	408.5	414.7
55°	295.3	307.7	324.8	341.8	358.9	375.9	377.5	379.0	382.1	384.4	390.6
57.5°	263.5	279.0	296.9	315.5	333.3	351.1	351.9	352.7	355.0	357.3	362.7
60°	234.1	252.7	269.7	287.6	304.6	321.7	324.8	327.1	328.6	330.2	334.8
62.5°	210.8	231.0	246.5	262.7	278.2	293.8	297.6	300.7	302.3	303.1	306.2
65°	189.1	207.7	222.4	236.4	251.1	265.1	268.2	271.3	273.6	275.1	277.5
67.5°	169.7	185.2	196.9	208.5	220.1	231.7	236.4	240.3	241.8	243.4	244.9
70°	149.6	161.2	171.3	181.4	191.4	201.5	205.4	209.3	210.8	211.6	212.4
72.5°	127.9	136.4	144.2	151.9	159.7	167.4	171.3	175.2	176.7	177.5	178.3
75°	105.4	111.6	117.8	124.0	130.2	136.4	139.5	141.8	142.6	143.4	143.4
77.5°	82.9	87.6	92.2	96.9	100.8	105.4	107.7	110.1	110.1	110.1	110.1
80°	59.7	62.8	65.9	69.0	72.1	75.2	76.0	76.7	77.5	78.3	78.3
82.5°	39.5	41.9	43.4	45.7	47.3	48.8	48.8	48.8	48.8	48.8	49.6
85°	22.5	23.3	24.0	24.8	25.6	26.4	27.1	27.1	27.1	27.1	27.1
87.5°	10.1	10.9	10.9	11.6	11.6	11.6	11.6	10.9	10.9	10.9	10.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2
2.5°	793.7	795.2	796.0	794.4	792.1	790.6	788.2	789.0	789.8	790.6	791.3
5°	713.8	712.3	710.0	704.5	699.1	693.7	689.8	686.7	683.6	680.5	677.4
7.5°	628.6	627.0	624.7	623.2	621.6	620.1	617.0	616.2	615.4	614.6	613.9
10°	601.5	601.5	602.2	603.0	603.0	603.8	604.6	606.1	606.9	608.4	609.2
12.5°	604.6	609.2	614.6	624.7	635.6	645.6	652.6	658.8	665.8	672.0	678.2
15°	650.3	665.8	681.3	685.2	689.8	693.7	696.0	697.6	699.1	699.9	701.4
17.5°	682.8	687.5	692.9	694.5	696.8	698.3	699.1	699.9	701.4	702.2	703.0
20°	682.1	684.4	687.5	689.8	692.1	694.5	696.0	698.3	699.9	702.2	703.8
22.5°	677.4	679.7	682.1	685.9	689.0	692.9	696.0	697.6	699.1	700.7	702.2
25°	666.6	672.0	676.6	679.7	682.1	685.2	685.2	685.2	685.9	685.9	685.9
27.5°	654.9	660.4	665.8	666.6	668.1	668.9	670.4	672.0	672.8	674.3	675.1
30°	638.7	644.1	649.5	651.1	652.6	654.2	652.6	651.8	651.1	649.5	648.7
32.5°	620.1	623.9	627.8	628.6	628.6	629.4	625.5	624.7	623.9	622.4	621.6
35°	596.8	599.1	601.5	600.7	600.7	599.9	600.7	600.7	600.7	599.9	599.9
37.5°	570.4	574.3	577.4	578.2	578.2	579.0	580.5	580.5	580.5	579.8	579.8
40°	544.9	549.5	554.2	554.9	556.5	557.3	558.0	558.0	558.0	557.3	557.3
42.5°	519.3	525.5	531.7	533.2	534.8	536.3	535.6	534.8	534.8	534.0	533.2
45°	496.8	503.0	509.2	510.0	511.5	512.3	513.1	512.3	510.8	510.0	508.4
47.5°	471.2	477.4	484.4	486.0	486.7	488.3	488.3	487.5	486.7	485.2	484.4
50°	446.4	453.4	460.4	461.2	461.9	462.7	461.9	460.4	459.6	458.1	456.5
52.5°	421.6	427.8	434.0	434.0	433.3	433.3	433.3	433.3	434.0	434.0	434.0
55°	396.1	402.3	407.7	407.7	407.7	407.7	408.5	410.0	411.6	412.3	413.9
57.5°	368.9	374.4	379.8	380.6	380.6	381.3	381.3	382.1	383.7	384.4	385.2
60°	340.3	344.9	349.6	350.3	350.3	351.1	352.7	353.4	354.2	355.0	355.8
62.5°	309.3	311.6	314.7	316.2	317.8	319.3	320.9	320.9	321.7	321.7	321.7
65°	279.8	281.3	283.7	284.4	285.2	286.0	287.6	287.6	288.3	288.3	288.3
67.5°	246.5	247.2	248.8	249.6	251.1	251.9	251.1	251.1	251.1	250.3	250.3
70°	213.1	213.9	214.7	215.5	216.2	217.0	217.0	217.0	217.0	216.2	216.2
72.5°	178.3	179.0	179.0	179.0	179.8	179.8	179.0	179.8	180.6	181.4	182.1
75°	144.2	144.2	144.2	144.2	143.4	143.4	144.9	144.9	144.2	144.2	143.4
77.5°	110.1	110.1	110.1	110.1	109.3	109.3	110.8	110.8	110.1	110.1	109.3
80°	78.3	77.5	77.5	77.5	77.5	77.5	76.7	76.7	76.7	76.7	76.7
82.5°	49.6	50.4	50.4	50.4	49.6	49.6	48.8	48.8	48.8	48.8	48.8
85°	26.4	26.4	25.6	26.4	26.4	27.1	27.9	27.9	27.1	27.1	26.4
87.5°	10.9	10.9	10.9	10.9	10.1	10.1	9.3	9.3	9.3	9.3	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2
2.5°	789.0	787.5	785.1	782.8	785.1	787.5	789.0	791.3	790.6	789.8	789.0
5°	675.1	672.8	669.7	667.3	669.7	672.8	675.1	677.4	680.5	683.6	686.7
7.5°	612.3	610.8	609.2	607.7	609.2	610.8	612.3	613.9	614.6	615.4	616.2
10°	609.2	609.2	608.4	608.4	608.4	609.2	609.2	609.2	608.4	606.9	606.1
12.5°	678.2	677.4	677.4	676.6	677.4	677.4	678.2	678.2	672.0	665.8	658.8
15°	701.4	702.2	702.2	702.2	702.2	702.2	701.4	701.4	699.9	699.1	697.6
17.5°	703.0	703.0	703.0	703.0	703.0	703.0	703.0	703.0	702.2	701.4	699.9
20°	704.5	704.5	705.3	705.3	705.3	704.5	704.5	703.8	702.2	699.9	698.3
22.5°	702.2	702.2	701.4	701.4	701.4	702.2	702.2	702.2	700.7	699.1	697.6
25°	685.9	686.7	686.7	686.7	686.7	686.7	685.9	685.9	685.9	685.9	685.2
27.5°	675.1	675.1	674.3	674.3	674.3	675.1	675.1	675.1	674.3	672.8	672.0
30°	648.0	647.2	646.4	645.6	646.4	647.2	648.0	648.7	649.5	651.1	651.8
32.5°	620.8	620.8	620.1	619.3	620.1	620.8	620.8	621.6	622.4	623.9	624.7
35°	599.1	599.1	598.4	597.6	598.4	599.1	599.1	599.9	599.9	600.7	600.7
37.5°	579.0	578.2	577.4	576.7	577.4	578.2	579.0	579.8	579.8	580.5	580.5
40°	556.5	556.5	555.7	554.9	555.7	556.5	556.5	557.3	557.3	558.0	558.0
42.5°	533.2	532.5	532.5	531.7	532.5	532.5	533.2	533.2	534.0	534.8	534.8
45°	507.7	507.7	506.9	506.1	506.9	507.7	507.7	508.4	510.0	510.8	512.3
47.5°	483.6	483.6	482.9	482.1	482.9	483.6	483.6	484.4	485.2	486.7	487.5
50°	456.5	456.5	455.7	455.7	455.7	456.5	456.5	456.5	458.1	459.6	460.4
52.5°	434.8	434.8	435.6	435.6	435.6	434.8	434.8	434.0	434.0	434.0	433.3
55°	414.7	414.7	415.4	415.4	415.4	414.7	414.7	413.9	412.3	411.6	410.0
57.5°	385.2	385.2	385.2	385.2	385.2	385.2	385.2	385.2	384.4	383.7	382.1
60°	355.8	355.8	355.0	355.0	355.0	355.8	355.8	355.8	355.0	354.2	353.4
62.5°	321.7	320.9	320.9	320.1	320.9	320.9	321.7	321.7	321.7	321.7	320.9
65°	288.3	287.6	287.6	286.8	287.6	287.6	288.3	288.3	288.3	288.3	287.6
67.5°	251.1	251.9	252.7	253.4	252.7	251.9	251.1	250.3	250.3	251.1	251.1
70°	217.0	217.0	217.8	217.8	217.8	217.0	217.0	216.2	216.2	217.0	217.0
72.5°	181.4	181.4	180.6	179.8	180.6	181.4	181.4	182.1	181.4	180.6	179.8
75°	144.2	144.9	144.9	145.7	144.9	144.9	144.2	143.4	144.2	144.2	144.9
77.5°	109.3	109.3	109.3	109.3	109.3	109.3	109.3	109.3	110.1	110.1	110.8
80°	76.7	76.7	76.0	76.0	76.0	76.7	76.7	76.7	76.7	76.7	76.7
82.5°	49.6	49.6	50.4	50.4	50.4	49.6	49.6	48.8	48.8	48.8	48.8
85°	26.4	26.4	26.4	26.4	26.4	26.4	26.4	26.4	27.1	27.1	27.9
87.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2
2.5°	788.2	790.6	792.1	794.4	796.0	795.2	793.7	792.9	791.3	792.9	794.4
5°	689.8	693.7	699.1	704.5	710.0	712.3	713.8	716.2	717.7	724.7	731.7
7.5°	617.0	620.1	621.6	623.2	624.7	627.0	628.6	630.9	632.5	638.7	644.9
10°	604.6	603.8	603.0	603.0	602.2	601.5	601.5	600.7	599.9	601.5	602.2
12.5°	652.6	645.6	635.6	624.7	614.6	609.2	604.6	599.1	593.7	592.2	589.8
15°	696.0	693.7	689.8	685.2	681.3	665.8	650.3	634.0	618.5	605.3	591.4
17.5°	699.1	698.3	696.8	694.5	692.9	687.5	682.8	677.4	672.0	654.2	635.6
20°	696.0	694.5	692.1	689.8	687.5	684.4	682.1	679.0	675.9	669.7	662.7
22.5°	696.0	692.9	689.0	685.9	682.1	679.7	677.4	674.3	672.0	667.3	662.7
25°	685.2	685.2	682.1	679.7	676.6	672.0	666.6	661.9	656.5	655.7	654.2
27.5°	670.4	668.9	668.1	666.6	665.8	660.4	654.9	649.5	644.1	643.3	641.8
30°	652.6	654.2	652.6	651.1	649.5	644.1	638.7	633.2	627.8	624.7	621.6
32.5°	625.5	629.4	628.6	628.6	627.8	623.9	620.1	615.4	611.5	607.7	603.0
35°	600.7	599.9	600.7	600.7	601.5	599.1	596.8	593.7	591.4	587.5	583.6
37.5°	580.5	579.0	578.2	578.2	577.4	574.3	570.4	567.3	563.5	562.7	561.1
40°	558.0	557.3	556.5	554.9	554.2	549.5	544.9	539.4	534.8	535.6	535.6
42.5°	535.6	536.3	534.8	533.2	531.7	525.5	519.3	513.1	506.9	506.1	504.6
45°	513.1	512.3	511.5	510.0	509.2	503.0	496.8	489.8	483.6	480.5	477.4
47.5°	488.3	488.3	486.7	486.0	484.4	477.4	471.2	464.3	457.3	454.2	451.1
50°	461.9	462.7	461.9	461.2	460.4	453.4	446.4	438.7	431.7	429.4	426.3
52.5°	433.3	433.3	433.3	434.0	434.0	427.8	421.6	414.7	408.5	406.1	403.0
55°	408.5	407.7	407.7	407.7	407.7	402.3	396.1	390.6	384.4	382.1	379.0
57.5°	381.3	381.3	380.6	380.6	379.8	374.4	368.9	362.7	357.3	355.0	352.7
60°	352.7	351.1	350.3	350.3	349.6	344.9	340.3	334.8	330.2	328.6	327.1
62.5°	320.9	319.3	317.8	316.2	314.7	311.6	309.3	306.2	303.1	302.3	300.7
65°	287.6	286.0	285.2	284.4	283.7	281.3	279.8	277.5	275.1	273.6	271.3
67.5°	251.1	251.9	251.1	249.6	248.8	247.2	246.5	244.9	243.4	241.8	240.3
70°	217.0	217.0	216.2	215.5	214.7	213.9	213.1	212.4	211.6	210.8	209.3
72.5°	179.0	179.8	179.8	179.0	179.0	179.0	178.3	178.3	177.5	176.7	175.2
75°	144.9	143.4	143.4	144.2	144.2	144.2	144.2	143.4	143.4	142.6	141.8
77.5°	110.8	109.3	109.3	110.1	110.1	110.1	110.1	110.1	110.1	110.1	110.1
80°	76.7	77.5	77.5	77.5	77.5	77.5	78.3	78.3	78.3	77.5	76.7
82.5°	48.8	49.6	49.6	50.4	50.4	50.4	49.6	49.6	48.8	48.8	48.8
85°	27.9	27.1	26.4	26.4	25.6	26.4	26.4	27.1	27.1	27.1	27.1
87.5°	9.3	10.1	10.1	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2
2.5°	796.0	797.5	800.6	803.7	806.1	809.2	810.7	811.5	813.0	815.4	816.1
5°	741.0	750.3	757.2	764.2	771.2	778.2	782.8	788.2	792.9	797.5	800.6
7.5°	651.8	658.8	672.0	684.4	697.6	710.0	724.7	740.2	754.9	767.3	774.3
10°	606.9	610.8	619.3	627.8	635.6	644.1	658.8	674.3	689.0	710.7	727.0
12.5°	590.6	591.4	596.0	601.5	606.1	610.8	619.3	628.6	637.1	651.8	675.1
15°	587.5	582.9	584.4	586.7	588.3	589.8	596.0	602.2	608.4	619.3	639.4
17.5°	611.5	587.5	584.4	580.5	577.4	573.6	578.2	582.1	586.7	594.5	610.8
20°	644.9	626.3	610.8	595.3	579.0	563.5	565.8	567.3	569.7	576.7	589.1
22.5°	655.7	648.0	625.5	602.2	579.8	556.5	554.9	554.2	552.6	558.0	569.7
25°	650.3	645.6	622.4	599.1	575.1	551.8	547.2	541.8	537.1	543.3	554.9
27.5°	638.7	635.6	615.4	596.0	575.9	555.7	544.9	534.0	523.2	525.5	537.1
30°	622.4	623.2	606.9	589.8	573.6	556.5	539.4	523.2	506.1	506.9	519.3
32.5°	603.8	604.6	591.4	578.2	564.2	551.1	530.1	509.2	488.3	489.1	500.7
35°	583.6	582.9	572.0	560.4	549.5	537.9	514.6	490.6	467.4	466.6	478.2
37.5°	561.9	562.7	551.8	541.8	530.9	520.1	495.3	469.7	444.9	444.9	455.7
40°	538.7	541.0	530.1	520.1	509.2	498.4	472.8	448.0	422.4	424.7	432.5
42.5°	510.0	514.6	503.8	493.7	482.9	472.0	447.2	423.2	398.4	401.5	403.8
45°	481.3	484.4	474.3	464.3	453.4	443.3	420.9	397.6	375.1	377.5	369.7
47.5°	453.4	455.0	444.1	433.3	422.4	411.6	391.4	371.3	351.1	351.9	335.6
50°	426.3	426.3	413.1	399.9	386.8	373.6	358.1	341.8	326.3	323.2	303.8
52.5°	402.3	401.5	386.0	371.3	355.8	340.3	326.3	313.1	299.2	289.9	273.6
55°	377.5	375.9	358.9	341.8	324.8	307.7	295.3	282.9	270.5	250.3	239.5
57.5°	351.9	351.1	333.3	315.5	296.9	279.0	263.5	248.8	233.3	213.9	206.9
60°	324.8	321.7	304.6	287.6	269.7	252.7	234.1	215.5	196.9	182.1	177.5
62.5°	297.6	293.8	278.2	262.7	246.5	231.0	210.8	189.9	169.7	166.6	162.0
65°	268.2	265.1	251.1	236.4	222.4	207.7	189.1	169.7	151.1	150.4	146.5
67.5°	236.4	231.7	220.1	208.5	196.9	185.2	169.7	154.2	138.7	138.0	134.1
70°	205.4	201.5	191.4	181.4	171.3	161.2	149.6	137.2	125.6	124.0	120.1
72.5°	171.3	167.4	159.7	151.9	144.2	136.4	127.9	119.4	110.8	109.3	106.2
75°	139.5	136.4	130.2	124.0	117.8	111.6	105.4	100.0	93.8	93.0	90.7
77.5°	107.7	105.4	100.8	96.9	92.2	87.6	82.9	79.1	74.4	76.0	74.4
80°	76.0	75.2	72.1	69.0	65.9	62.8	59.7	57.4	54.3	55.8	54.3
82.5°	48.8	48.8	47.3	45.7	43.4	41.9	39.5	38.0	35.7	37.2	35.7
85°	27.1	26.4	25.6	24.8	24.0	23.3	22.5	20.9	20.2	20.9	20.2
87.5°	11.6	11.6	11.6	11.6	10.9	10.9	10.1	10.1	9.3	9.3	8.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2
2.5°	816.9	817.7	818.5	820.8	822.3	824.7	826.2	826.2	826.2	826.2	826.2
5°	803.7	806.1	809.2	813.0	816.1	820.0	823.1	824.7	826.2	827.8	829.3
7.5°	781.3	788.2	795.2	800.6	806.1	811.5	816.9	820.0	823.1	825.4	828.5
10°	744.1	760.3	776.6	785.1	792.9	801.4	809.2	813.0	817.7	821.6	825.4
12.5°	698.3	720.8	744.1	758.0	771.2	785.1	798.3	803.7	809.9	815.4	820.8
15°	660.4	680.5	700.7	722.4	743.3	765.0	785.9	792.9	799.1	806.1	812.3
17.5°	626.3	642.5	658.0	685.9	713.8	741.0	768.9	777.4	785.1	793.7	801.4
20°	602.2	614.6	627.0	658.0	688.3	719.3	749.5	758.8	768.1	777.4	786.7
22.5°	582.1	593.7	605.3	634.8	664.2	693.7	723.1	735.5	747.2	759.6	771.2
25°	565.8	577.4	588.3	614.6	640.2	666.6	692.1	707.6	723.1	738.6	754.1
27.5°	549.5	561.1	572.8	594.5	616.2	637.9	659.6	678.2	696.0	714.6	732.4
30°	531.7	544.1	556.5	573.6	589.8	606.9	623.2	643.3	662.7	682.8	702.2
32.5°	513.1	524.7	536.3	548.0	559.6	570.4	582.1	600.7	620.1	638.7	657.3
35°	489.8	501.5	513.1	516.2	520.1	523.2	526.3	550.3	574.3	598.4	622.4
37.5°	466.6	476.7	487.5	482.1	476.7	470.5	465.0	496.8	528.6	560.4	592.2
40°	439.5	447.2	454.2	443.3	432.5	421.6	410.8	444.1	478.2	511.5	544.9
42.5°	406.1	407.7	410.0	399.9	390.6	380.6	370.5	401.5	431.7	462.7	492.9
45°	362.0	354.2	346.5	344.9	343.4	341.0	339.5	374.4	409.2	444.1	479.0
47.5°	320.1	303.8	287.6	298.4	308.5	319.3	329.4	359.6	390.6	420.9	451.1
50°	285.2	265.8	246.5	267.4	287.6	308.5	328.6	351.9	374.4	397.6	420.1
52.5°	256.5	240.3	223.2	241.8	261.2	279.8	298.4	319.3	340.3	361.2	382.1
55°	227.9	217.0	205.4	223.2	241.0	258.9	276.7	293.0	310.0	326.3	342.6
57.5°	199.2	192.2	184.5	206.2	228.6	250.3	272.0	275.1	279.0	282.1	285.2
60°	172.1	167.4	162.0	183.7	206.2	227.9	249.6	238.7	227.9	217.0	206.2
62.5°	156.6	151.9	146.5	166.6	186.8	206.2	226.3	206.9	188.3	169.0	149.6
65°	141.8	138.0	133.3	148.0	162.8	177.5	192.2	175.9	158.9	142.6	125.6
67.5°	129.4	125.6	120.9	127.1	134.1	140.3	146.5	135.6	124.8	113.2	102.3
70°	116.3	111.6	107.7	107.7	108.5	108.5	108.5	98.4	88.4	78.3	68.2
72.5°	103.1	100.0	96.9	95.3	93.8	91.5	89.9	81.4	72.9	63.6	55.0
75°	89.1	86.8	84.5	81.4	79.1	76.0	72.9	69.0	65.9	62.0	58.1
77.5°	72.1	70.5	68.2	64.3	61.2	57.4	53.5	53.5	54.3	54.3	54.3
80°	52.7	50.4	48.8	46.5	45.0	42.6	40.3	41.1	41.9	41.9	42.6
82.5°	34.1	32.6	31.0	30.2	29.5	27.9	27.1	27.1	27.1	27.1	27.1
85°	18.6	17.8	16.3	15.5	14.7	13.2	12.4	13.2	14.0	14.7	15.5
87.5°	7.8	7.0	6.2	5.4	5.4	4.7	3.9	4.7	5.4	6.2	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2
2.5°	827.8	828.5	830.1	830.9	832.4	832.4	832.4	832.4	831.6	831.6	830.9
5°	831.6	834.0	835.5	837.8	839.4	840.2	840.2	840.9	840.9	840.9	840.2
7.5°	831.6	834.0	837.1	839.4	841.7	842.5	843.3	844.0	843.3	843.3	842.5
10°	828.5	831.6	834.7	837.8	839.4	840.2	840.9	841.7	840.9	840.9	840.2
12.5°	823.9	827.0	829.3	832.4	834.0	834.7	836.3	837.1	837.1	837.1	836.3
15°	815.4	817.7	820.8	823.1	824.7	826.2	828.5	830.1	830.1	829.3	829.3
17.5°	804.5	807.6	810.7	813.8	816.1	817.7	818.5	820.0	820.0	820.0	819.2
20°	790.6	794.4	797.5	801.4	803.7	805.3	806.1	807.6	807.6	807.6	807.6
22.5°	775.1	778.9	782.8	786.7	788.2	789.8	791.3	792.9	792.9	792.9	792.9
25°	757.2	761.1	764.2	767.3	772.0	773.5	775.1	776.6	777.4	778.2	778.2
27.5°	737.1	741.0	745.6	749.5	752.6	754.9	756.5	758.8	759.6	760.3	760.3
30°	708.4	715.4	721.6	727.8	730.9	734.0	737.9	741.0	741.7	741.7	742.5
32.5°	669.7	681.3	693.7	705.3	712.3	715.4	718.5	721.6	720.8	719.3	718.5
35°	637.9	653.4	668.9	684.4	690.6	692.9	695.2	697.6	696.0	695.2	693.7
37.5°	610.0	627.8	644.9	662.7	667.3	668.9	671.2	672.8	671.2	669.7	667.3
40°	568.1	591.4	613.9	637.1	640.2	641.8	643.3	644.9	643.3	642.5	641.0
42.5°	522.4	551.8	580.5	610.0	613.9	613.1	611.5	610.8	611.5	613.1	613.9
45°	504.6	530.1	554.9	580.5	585.2	583.6	582.1	580.5	582.1	583.6	585.2
47.5°	475.9	501.5	526.3	551.1	551.1	550.3	549.5	548.7	551.1	552.6	554.9
50°	442.6	465.8	488.3	510.8	507.7	511.5	514.6	518.5	520.8	523.2	525.5
52.5°	401.5	420.9	439.5	458.8	470.5	475.9	482.1	487.5	489.1	490.6	491.4
55°	359.6	377.5	394.5	411.6	434.8	441.0	446.4	452.6	454.2	456.5	458.1
57.5°	306.2	327.1	347.2	368.2	397.6	404.6	412.3	419.3	419.3	419.3	418.5
60°	234.8	264.3	293.0	321.7	356.5	364.3	371.3	379.0	378.2	378.2	377.5
62.5°	179.8	209.3	239.5	268.9	308.5	319.3	329.4	340.3	340.3	340.3	339.5
65°	141.8	158.9	175.2	191.4	256.5	272.0	286.8	302.3	303.1	303.1	303.8
67.5°	109.3	116.3	122.5	129.4	213.9	231.0	248.8	265.8	265.8	265.1	265.1
70°	73.6	79.1	84.5	89.9	173.6	192.2	211.6	230.2	229.4	228.6	227.1
72.5°	58.1	60.5	63.6	65.9	134.9	154.2	174.4	193.8	193.0	191.4	190.7
75°	56.6	54.3	52.7	50.4	100.0	119.4	138.0	157.3	156.6	155.8	155.0
77.5°	51.2	47.3	44.2	40.3	73.6	90.7	107.7	124.8	124.0	122.5	121.7
80°	39.5	36.4	33.3	30.2	50.4	63.6	76.7	89.9	89.9	89.9	89.9
82.5°	26.4	24.8	24.0	22.5	31.8	41.9	51.2	61.2	60.5	60.5	59.7
85°	15.5	14.7	14.7	14.0	19.4	24.0	28.7	33.3	34.1	34.1	34.9
87.5°	7.8	7.8	8.5	8.5	10.9	13.2	14.7	17.1	17.1	17.8	17.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2
2.5°	830.1	829.3	827.8	829.3	830.1	831.6	834.0	835.5	837.1	837.8	838.6
5°	840.2	839.4	838.6	839.4	840.2	842.5	844.0	846.4	847.9	848.7	848.7
7.5°	841.7	841.7	840.9	841.7	842.5	844.8	846.4	848.7	850.2	851.0	851.0
10°	839.4	839.4	839.4	840.9	842.5	844.8	846.4	848.7	850.2	851.0	851.0
12.5°	836.3	836.3	835.5	837.1	838.6	840.9	842.5	844.8	846.4	847.1	847.1
15°	828.5	828.5	828.5	830.1	831.6	834.0	836.3	837.8	840.2	840.9	841.7
17.5°	819.2	820.0	820.0	821.6	823.1	825.4	827.0	829.3	830.9	831.6	831.6
20°	807.6	807.6	807.6	809.9	811.5	813.8	815.4	817.7	819.2	820.0	821.6
22.5°	792.9	793.7	794.4	797.5	799.9	801.4	803.7	805.3	806.8	806.8	807.6
25°	778.9	780.5	781.3	782.8	784.4	785.1	785.9	785.9	786.7	786.7	785.9
27.5°	761.1	762.7	764.2	765.0	765.0	765.0	765.8	765.8	765.8	766.5	767.3
30°	742.5	741.0	739.4	740.2	741.0	741.7	743.3	744.1	744.8	745.6	745.6
32.5°	716.9	716.9	716.2	717.7	718.5	720.0	721.6	723.1	724.7	724.7	724.7
35°	692.1	693.7	695.2	696.0	696.0	696.8	698.3	699.1	699.9	700.7	701.4
37.5°	665.8	668.1	670.4	672.0	672.8	673.5	674.3	675.1	675.9	675.1	675.1
40°	639.4	641.8	644.1	644.9	645.6	646.4	646.4	647.2	647.2	646.4	646.4
42.5°	614.6	615.4	616.2	617.7	619.3	618.5	618.5	617.7	617.0	616.2	614.6
45°	586.7	588.3	589.1	589.1	589.1	587.5	586.0	583.6	582.1	581.3	581.3
47.5°	556.5	558.8	560.4	558.0	554.9	553.4	551.8	549.5	548.0	547.2	546.4
50°	527.8	526.3	523.9	521.6	518.5	517.0	516.2	514.6	513.1	510.0	507.7
52.5°	492.9	489.8	486.7	484.4	481.3	479.0	476.7	474.3	472.0	470.5	469.7
55°	459.6	454.2	448.0	445.7	442.6	439.5	435.6	432.5	428.6	427.8	427.1
57.5°	418.5	415.4	411.6	406.9	401.5	398.4	396.1	393.0	389.9	389.1	388.3
60°	376.7	373.6	370.5	365.8	361.2	358.9	355.8	353.4	350.3	349.6	349.6
62.5°	339.5	337.2	334.1	327.1	320.1	318.6	316.2	314.7	312.4	310.8	310.0
65°	303.8	298.4	292.2	287.6	282.1	279.8	278.2	275.9	273.6	272.0	270.5
67.5°	264.3	257.3	249.6	247.2	244.9	242.6	239.5	237.2	234.1	233.3	232.5
70°	226.3	220.9	214.7	212.4	209.3	206.9	204.6	201.5	199.2	197.6	195.3
72.5°	189.1	184.5	179.0	175.9	172.8	170.5	169.0	166.6	164.3	162.8	161.2
75°	154.2	149.6	144.9	141.8	138.7	137.2	135.6	133.3	131.8	129.4	127.9
77.5°	120.1	117.8	114.7	110.8	107.0	106.2	105.4	104.6	103.9	101.5	100.0
80°	89.9	87.6	85.3	82.9	79.8	78.3	77.5	76.0	74.4	73.6	72.1
82.5°	58.9	57.4	55.8	55.0	54.3	53.5	52.7	51.9	51.2	50.4	50.4
85°	34.9	34.9	34.9	34.1	33.3	33.3	33.3	32.6	32.6	31.8	31.8
87.5°	17.8	18.6	18.6	18.6	18.6	18.6	18.6	18.6	18.6	18.6	19.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2
2.5°	839.4	838.6	839.4	839.4	840.2	840.2	839.4	839.4	838.6	837.8	838.6
5°	849.5	850.2	850.2	850.2	850.2	850.2	850.2	849.5	849.5	848.7	849.5
7.5°	851.8	851.8	852.6	852.6	853.3	853.3	852.6	852.6	851.8	851.0	851.8
10°	851.8	852.6	852.6	853.3	853.3	853.3	852.6	852.6	851.8	851.0	851.8
12.5°	847.9	847.9	848.7	848.7	849.5	849.5	849.5	848.7	848.7	847.9	848.7
15°	842.5	841.7	842.5	842.5	843.3	843.3	842.5	842.5	841.7	840.9	841.7
17.5°	832.4	833.2	833.2	834.0	834.0	834.0	833.2	832.4	831.6	830.9	831.6
20°	822.3	822.3	822.3	823.1	823.1	823.1	822.3	822.3	821.6	820.8	821.6
22.5°	807.6	807.6	807.6	806.8	806.8	806.1	805.3	805.3	804.5	803.7	804.5
25°	785.9	786.7	786.7	786.7	786.7	786.7	785.9	785.9	785.1	784.4	785.1
27.5°	768.1	766.5	767.3	767.3	768.1	768.1	768.1	767.3	767.3	766.5	767.3
30°	746.4	747.9	748.7	748.7	749.5	749.5	749.5	748.7	748.7	747.9	748.7
32.5°	724.7	726.2	726.2	726.2	726.2	726.2	726.2	725.5	725.5	724.7	725.5
35°	702.2	701.4	701.4	702.2	702.2	702.2	701.4	701.4	700.7	699.9	700.7
37.5°	674.3	674.3	674.3	674.3	674.3	674.3	673.5	673.5	672.8	672.0	672.8
40°	645.6	644.9	644.9	645.6	645.6	645.6	644.9	644.1	643.3	642.5	643.3
42.5°	613.9	613.9	613.9	613.9	613.1	613.1	613.1	613.1	612.3	612.3	612.3
45°	580.5	579.8	579.8	579.0	579.0	578.2	578.2	577.4	577.4	576.7	577.4
47.5°	545.6	545.6	544.9	543.3	542.5	541.0	540.2	539.4	537.9	537.1	537.9
50°	504.6	504.6	503.8	503.0	502.2	501.5	501.5	502.2	502.2	502.2	502.2
52.5°	468.1	465.0	464.3	464.3	463.5	462.7	462.7	462.7	461.9	461.9	461.9
55°	426.3	424.7	424.7	424.7	424.0	424.0	424.7	424.7	425.5	425.5	425.5
57.5°	387.5	386.8	386.8	386.0	386.0	385.2	384.4	384.4	383.7	382.9	383.7
60°	348.8	347.2	345.7	344.1	341.8	340.3	339.5	338.7	337.9	337.2	337.9
62.5°	308.5	305.4	304.6	303.1	302.3	300.7	299.2	298.4	296.9	295.3	296.9
65°	268.9	268.2	265.8	263.5	261.2	258.9	258.1	258.1	257.3	256.5	257.3
67.5°	231.7	227.1	225.5	224.0	222.4	220.9	220.9	220.9	220.9	220.9	220.9
70°	193.8	190.7	189.9	188.3	187.6	186.0	186.0	186.0	185.2	185.2	185.2
72.5°	159.7	156.6	155.8	155.0	153.5	152.7	152.7	152.7	151.9	151.9	151.9
75°	125.6	126.3	125.6	124.8	124.0	123.2	123.2	122.5	122.5	121.7	122.5
77.5°	97.7	97.7	96.9	96.1	95.3	94.6	94.6	94.6	94.6	94.6	94.6
80°	71.3	71.3	71.3	71.3	70.5	70.5	70.5	70.5	69.8	69.8	69.8
82.5°	49.6	49.6	49.6	49.6	49.6	49.6	49.6	48.8	48.8	48.1	48.8
85°	31.0	31.8	31.8	31.8	31.0	31.0	31.0	31.0	31.0	31.0	31.0
87.5°	19.4	19.4	19.4	20.2	20.2	20.2	20.2	20.2	19.4	19.4	19.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2
2.5°	839.4	839.4	840.2	840.2	839.4	839.4	838.6	839.4	838.6	837.8	837.1
5°	849.5	850.2	850.2	850.2	850.2	850.2	850.2	849.5	848.7	848.7	847.9
7.5°	852.6	852.6	853.3	853.3	852.6	852.6	851.8	851.8	851.0	851.0	850.2
10°	852.6	852.6	853.3	853.3	853.3	852.6	852.6	851.8	851.0	851.0	850.2
12.5°	848.7	849.5	849.5	849.5	848.7	848.7	847.9	847.9	847.1	847.1	846.4
15°	842.5	842.5	843.3	843.3	842.5	842.5	841.7	842.5	841.7	840.9	840.2
17.5°	832.4	833.2	834.0	834.0	834.0	833.2	833.2	832.4	831.6	831.6	830.9
20°	822.3	822.3	823.1	823.1	823.1	822.3	822.3	822.3	821.6	820.0	819.2
22.5°	805.3	805.3	806.1	806.8	806.8	807.6	807.6	807.6	807.6	806.8	806.8
25°	785.9	785.9	786.7	786.7	786.7	786.7	786.7	785.9	785.9	786.7	786.7
27.5°	767.3	768.1	768.1	768.1	767.3	767.3	766.5	768.1	767.3	766.5	765.8
30°	748.7	749.5	749.5	749.5	748.7	748.7	747.9	746.4	745.6	745.6	744.8
32.5°	725.5	726.2	726.2	726.2	726.2	726.2	726.2	724.7	724.7	724.7	724.7
35°	701.4	701.4	702.2	702.2	702.2	701.4	701.4	702.2	701.4	700.7	699.9
37.5°	673.5	673.5	674.3	674.3	674.3	674.3	674.3	674.3	675.1	675.1	675.9
40°	644.1	644.9	645.6	645.6	645.6	644.9	644.9	645.6	646.4	646.4	647.2
42.5°	613.1	613.1	613.1	613.1	613.9	613.9	613.9	613.9	614.6	616.2	617.0
45°	577.4	578.2	578.2	579.0	579.0	579.8	579.8	580.5	581.3	581.3	582.1
47.5°	539.4	540.2	541.0	542.5	543.3	544.9	545.6	545.6	546.4	547.2	548.0
50°	502.2	501.5	501.5	502.2	503.0	503.8	504.6	504.6	507.7	510.0	513.1
52.5°	462.7	462.7	462.7	463.5	464.3	464.3	465.0	468.1	469.7	470.5	472.0
55°	424.7	424.7	424.0	424.0	424.7	424.7	424.7	426.3	427.1	427.8	428.6
57.5°	384.4	384.4	385.2	386.0	386.0	386.8	386.8	387.5	388.3	389.1	389.9
60°	338.7	339.5	340.3	341.8	344.1	345.7	347.2	348.8	349.6	349.6	350.3
62.5°	298.4	299.2	300.7	302.3	303.1	304.6	305.4	308.5	310.0	310.8	312.4
65°	258.1	258.1	258.9	261.2	263.5	265.8	268.2	268.9	270.5	272.0	273.6
67.5°	220.9	220.9	220.9	222.4	224.0	225.5	227.1	231.7	232.5	233.3	234.1
70°	186.0	186.0	186.0	187.6	188.3	189.9	190.7	193.8	195.3	197.6	199.2
72.5°	152.7	152.7	152.7	153.5	155.0	155.8	156.6	159.7	161.2	162.8	164.3
75°	122.5	123.2	123.2	124.0	124.8	125.6	126.3	125.6	127.9	129.4	131.8
77.5°	94.6	94.6	94.6	95.3	96.1	96.9	97.7	97.7	100.0	101.5	103.9
80°	70.5	70.5	70.5	70.5	71.3	71.3	71.3	71.3	72.1	73.6	74.4
82.5°	48.8	49.6	49.6	49.6	49.6	49.6	49.6	49.6	50.4	50.4	51.2
85°	31.0	31.0	31.0	31.0	31.8	31.8	31.8	31.0	31.8	31.8	32.6
87.5°	20.2	20.2	20.2	20.2	20.2	19.4	19.4	19.4	19.4	18.6	18.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2
2.5°	835.5	834.0	831.6	830.1	829.3	827.8	829.3	830.1	830.9	831.6	831.6
5°	846.4	844.0	842.5	840.2	839.4	838.6	839.4	840.2	840.2	840.9	840.9
7.5°	848.7	846.4	844.8	842.5	841.7	840.9	841.7	841.7	842.5	843.3	843.3
10°	848.7	846.4	844.8	842.5	840.9	839.4	839.4	839.4	840.2	840.9	840.9
12.5°	844.8	842.5	840.9	838.6	837.1	835.5	836.3	836.3	836.3	837.1	837.1
15°	837.8	836.3	834.0	831.6	830.1	828.5	828.5	828.5	829.3	829.3	830.1
17.5°	829.3	827.0	825.4	823.1	821.6	820.0	820.0	819.2	819.2	820.0	820.0
20°	817.7	815.4	813.8	811.5	809.9	807.6	807.6	807.6	807.6	807.6	807.6
22.5°	805.3	803.7	801.4	799.9	796.8	794.4	793.7	792.9	792.9	792.9	792.9
25°	785.9	785.9	785.1	784.4	782.8	781.3	780.5	778.9	778.2	778.2	777.4
27.5°	765.8	765.8	765.0	765.0	765.0	764.2	762.7	761.1	760.3	760.3	759.6
30°	744.1	743.3	741.7	741.0	740.2	739.4	741.0	742.5	742.5	741.7	741.7
32.5°	723.1	721.6	720.0	718.5	717.7	716.2	716.9	716.9	718.5	719.3	720.8
35°	699.1	698.3	696.8	696.0	696.0	695.2	693.7	692.1	693.7	695.2	696.0
37.5°	675.1	674.3	673.5	672.8	672.0	670.4	668.1	665.8	667.3	668.9	671.2
40°	647.2	646.4	646.4	645.6	644.9	644.1	641.8	639.4	641.0	642.5	643.3
42.5°	617.7	618.5	618.5	619.3	617.7	616.2	615.4	614.6	613.9	613.1	611.5
45°	583.6	586.0	587.5	589.1	589.1	589.1	588.3	586.7	585.2	583.6	582.1
47.5°	549.5	551.8	553.4	554.9	558.0	560.4	558.8	556.5	554.9	552.6	551.1
50°	514.6	516.2	517.0	518.5	521.6	523.9	526.3	527.8	525.5	523.2	520.8
52.5°	474.3	476.7	479.0	481.3	484.4	486.7	489.8	492.9	491.4	490.6	489.1
55°	432.5	435.6	439.5	442.6	445.7	448.0	454.2	459.6	458.1	456.5	454.2
57.5°	393.0	395.3	398.4	401.5	406.9	411.6	415.4	418.5	418.5	419.3	419.3
60°	353.4	355.8	358.9	361.2	365.8	370.5	373.6	376.7	377.5	378.2	378.2
62.5°	314.7	316.2	318.6	320.1	327.1	334.1	337.2	339.5	339.5	340.3	340.3
65°	275.9	278.2	279.8	282.1	287.6	292.2	298.4	303.8	303.8	303.1	303.1
67.5°	237.2	239.5	242.6	244.9	247.2	249.6	257.3	264.3	265.1	265.1	265.8
70°	201.5	204.6	206.9	209.3	212.4	214.7	220.9	226.3	227.1	228.6	229.4
72.5°	166.6	169.0	170.5	172.8	175.9	179.0	184.5	189.1	190.7	191.4	193.0
75°	133.3	135.6	137.2	138.7	141.8	144.9	149.6	154.2	155.0	155.8	156.6
77.5°	104.6	105.4	106.2	107.0	110.8	114.7	117.8	120.1	121.7	122.5	124.0
80°	76.0	77.5	78.3	79.8	82.9	85.3	87.6	89.9	89.9	89.9	89.9
82.5°	51.9	52.7	53.5	54.3	55.0	55.8	57.4	58.9	59.7	60.5	60.5
85°	32.6	33.3	33.3	33.3	34.1	34.9	34.9	34.9	34.9	34.1	34.1
87.5°	18.6	18.6	18.6	18.6	18.6	18.6	18.6	17.8	17.8	17.8	17.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2
2.5°	832.4	832.4	832.4	832.4	830.9	830.1	828.5	827.8	826.2	826.2	826.2
5°	840.9	840.2	840.2	839.4	837.8	835.5	833.2	831.6	829.3	827.8	826.2
7.5°	844.0	843.3	842.5	841.7	839.4	837.1	834.0	831.6	828.5	825.4	822.3
10°	841.7	840.9	840.2	839.4	837.8	834.7	831.6	828.5	825.4	821.6	816.9
12.5°	837.1	836.3	834.7	834.0	832.4	829.3	826.2	823.9	820.8	815.4	809.2
15°	830.1	828.5	826.2	824.7	823.1	820.8	817.7	815.4	812.3	806.1	799.1
17.5°	820.0	818.5	817.7	816.1	813.8	810.7	807.6	804.5	801.4	793.7	785.1
20°	807.6	806.1	805.3	803.7	801.4	797.5	793.7	790.6	786.7	777.4	768.1
22.5°	792.9	791.3	789.8	788.2	786.7	782.8	778.9	775.1	771.2	759.6	747.2
25°	776.6	775.1	773.5	772.0	767.3	764.2	760.3	757.2	754.1	738.6	723.1
27.5°	758.8	756.5	754.9	752.6	749.5	745.6	741.0	737.1	732.4	714.6	696.0
30°	741.0	737.9	734.0	730.9	727.8	721.6	714.6	708.4	702.2	682.8	662.7
32.5°	721.6	718.5	715.4	712.3	705.3	693.7	681.3	669.7	657.3	638.7	619.3
35°	697.6	695.2	692.9	690.6	684.4	668.9	653.4	637.9	622.4	598.4	574.3
37.5°	672.8	671.2	668.9	667.3	662.7	644.9	627.0	610.0	592.2	560.4	528.6
40°	644.9	643.3	641.8	640.2	637.1	613.9	590.6	568.1	544.9	511.5	477.4
42.5°	610.8	611.5	613.1	613.9	610.0	580.5	551.1	522.4	492.9	462.7	431.7
45°	580.5	582.1	583.6	585.2	580.5	554.9	529.4	504.6	479.0	444.1	409.2
47.5°	548.7	549.5	550.3	551.1	551.1	526.3	500.7	475.9	451.1	420.9	389.9
50°	518.5	514.6	511.5	507.7	510.8	488.3	465.0	442.6	420.1	397.6	374.4
52.5°	487.5	482.1	475.9	470.5	458.8	439.5	420.1	401.5	382.1	361.2	340.3
55°	452.6	446.4	441.0	434.8	411.6	394.5	376.7	359.6	342.6	326.3	309.3
57.5°	419.3	412.3	404.6	397.6	368.2	347.2	326.3	306.2	285.2	282.1	278.2
60°	379.0	371.3	364.3	356.5	321.7	293.0	263.5	234.8	206.2	217.0	227.9
62.5°	340.3	329.4	319.3	308.5	268.9	239.5	209.3	179.8	149.6	169.0	188.3
65°	302.3	286.8	272.0	256.5	191.4	175.2	158.1	141.8	125.6	142.6	158.9
67.5°	265.8	248.8	231.0	213.9	129.4	122.5	115.5	109.3	102.3	113.2	124.8
70°	230.2	211.6	192.2	173.6	89.9	84.5	79.1	73.6	68.2	78.3	88.4
72.5°	193.8	174.4	154.2	134.9	65.9	63.6	60.5	58.1	55.0	63.6	72.9
75°	157.3	138.0	119.4	100.0	50.4	52.7	54.3	56.6	58.1	62.0	65.9
77.5°	124.8	107.7	90.7	73.6	40.3	44.2	47.3	51.2	54.3	54.3	54.3
80°	89.9	76.7	63.6	50.4	30.2	33.3	36.4	39.5	42.6	41.9	41.9
82.5°	61.2	51.2	41.9	31.8	22.5	24.0	24.8	26.4	27.1	27.1	27.1
85°	33.3	28.7	24.0	19.4	14.0	14.7	14.7	15.5	15.5	14.7	14.0
87.5°	17.1	14.7	13.2	10.9	8.5	8.5	7.8	7.8	7.0	6.2	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	819.2	819.2
2.5°	826.2	826.2
5°	824.7	823.1
7.5°	820.0	816.9
10°	813.0	809.2
12.5°	803.7	798.3
15°	792.9	785.9
17.5°	777.4	768.9
20°	758.8	749.5
22.5°	735.5	723.1
25°	707.6	692.1
27.5°	678.2	659.6
30°	643.3	623.2
32.5°	600.7	582.1
35°	550.3	526.3
37.5°	496.8	465.0
40°	444.1	410.8
42.5°	401.5	370.5
45°	374.4	339.5
47.5°	359.6	329.4
50°	351.9	328.6
52.5°	319.3	298.4
55°	293.0	276.7
57.5°	275.1	272.0
60°	238.7	249.6
62.5°	206.9	226.3
65°	175.9	192.2
67.5°	135.6	146.5
70°	98.4	108.5
72.5°	81.4	89.9
75°	69.0	72.9
77.5°	53.5	53.5
80°	41.1	40.3
82.5°	27.1	27.1
85°	13.2	12.4
87.5°	4.7	3.9
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

TEST NUMBER: P1055039

CATALOG NUMBER: SQ4R-FA-075D-927-1-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.27	18.88	17.63	19.20	19.51	19.18	20.79	19.55	21.11	21.42
	3H	17.93	19.39	18.31	19.71	20.07	20.98	22.43	21.36	22.76	23.12
	4H	18.27	19.63	18.66	19.98	20.36	21.60	22.97	22.00	23.32	23.69
	6H	18.56	19.82	18.97	20.19	20.58	21.99	23.25	22.40	23.62	24.01
	8H	18.63	19.84	19.06	20.23	20.63	22.08	23.29	22.51	23.68	24.08
	12H	18.66	19.82	19.09	20.20	20.63	22.13	23.29	22.56	23.67	24.10
4H	2H	18.40	19.76	18.80	20.11	20.49	19.75	21.12	20.15	21.47	21.85
	3H	19.72	20.86	20.13	21.26	21.66	21.78	22.92	22.19	23.32	23.72
	4H	20.15	21.18	20.58	21.59	22.03	22.52	23.55	22.95	23.97	24.40
	6H	20.44	21.34	20.90	21.78	22.24	23.02	23.92	23.47	24.36	24.81
	8H	20.52	21.36	20.98	21.80	22.27	23.14	23.98	23.61	24.43	24.89
	12H	20.56	21.32	21.04	21.79	22.26	23.22	23.97	23.70	24.45	24.92
8H	4H	20.74	21.58	21.20	22.02	22.49	22.75	23.59	23.21	24.03	24.50
	6H	21.22	21.92	21.72	22.41	22.88	23.35	24.04	23.84	24.53	25.01
	8H	21.35	21.98	21.86	22.48	22.97	23.53	24.15	24.04	24.66	25.14
	12H	21.42	21.98	21.93	22.47	23.03	23.65	24.20	24.16	24.69	25.25
12H	4H	20.79	21.55	21.27	22.02	22.49	22.76	23.51	23.24	23.99	24.46
	6H	21.32	21.95	21.83	22.46	22.94	23.36	23.99	23.87	24.50	24.98
	8H	21.53	22.08	22.03	22.57	23.13	23.59	24.14	24.10	24.63	25.20