

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1055042

Luminaire Tested: SQ4R-FA-075D-940-1-UNV-STD-W-4

Issue Date: 7/23/2025

Test Information

Test Method: LM-79-2019
Report Number: P1055042
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-892-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/23/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4R-FA-075D-940-1-UNV-STD-W-4
Description: CORELITE SQ4R RECESSED LED LUMINAIRE WITH ASYMMETRIC FROSTED CONTINUOUS ROLL LENS
750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2358.5 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular (W 0.29' x L: 3.83' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	89	87
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73
3	91	81	73	66	88	79	72	66	76	70	64	73	68	63	71	66	62
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54
5	77	64	55	49	75	63	54	48	61	53	48	59	52	47	57	51	47
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41
7	66	52	44	38	64	51	43	37	50	42	37	48	42	37	47	41	37
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8756	8756	8756	8756
5°	8831	7159	8831	9105
10°	8782	6603	8782	9235
15°	8696	7769	8696	9304
20°	8524	8022	8524	9335
25°	8161	8098	8161	9249
30°	7691	7967	7691	9230
35°	6866	7797	6866	9132
40°	5731	7743	5731	8964
45°	5132	7649	5132	8715
50°	5464	7577	5464	8350
55°	5156	7741	5156	7929
60°	5335	7588	5335	7207
65°	4861	7253	4861	6488
70°	3392	6806	3392	5787
75°	3009	6019	3009	5025
80°	2478	4674	2478	4291
85°	1524	3237	1524	3800

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 225°

Vertical Angle: 45°

Luminance: 8903 cd/sqm

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.1	3.5
10°-20°	233.1	9.9
20°-30°	360.4	15.3
30°-40°	430.2	18.2
40°-50°	432.7	18.3
50°-60°	376.5	16.0
60°-70°	267.0	11.3
70°-80°	141.3	6.0
80°-90°	35.2	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	675.6	28.6
0°-40°	1105.8	46.9
0°-60°	1915.0	81.2
0°-90°	2358.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2358.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	910	910	910	910	910	
5°	914	741	914	942	914	87
15°	872	780	872	934	872	245
25°	768	762	768	871	768	353
35°	584	663	584	777	584	361
45°	377	562	377	640	377	302
55°	307	461	307	472	307	282
65°	213	318	213	285	213	204
75°	81	162	81	135	81	85
85°	14	29	14	34	14	19
90°	0	0	0	0	0	1
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5
2.5°	917.2	915.5	912.9	911.2	908.6	907.7	906.9	906.0	905.2	902.6	900.8
5°	913.8	910.3	906.0	902.6	898.3	894.8	892.2	888.8	885.4	880.2	875.0
7.5°	906.9	900.8	894.8	888.8	882.8	875.0	867.3	859.5	851.8	838.0	821.7
10°	898.3	889.7	880.2	871.6	862.1	844.1	826.0	807.1	789.0	764.9	748.6
12.5°	886.2	871.6	856.1	841.5	826.0	800.2	775.2	749.4	723.6	707.3	697.8
15°	872.5	849.2	825.1	801.9	777.8	755.4	733.1	709.8	687.5	675.4	668.5
17.5°	853.5	822.6	792.4	761.5	730.5	713.3	695.2	678.0	659.9	651.3	646.2
20°	832.0	798.5	764.0	730.5	696.1	682.3	668.5	653.9	640.1	632.4	629.8
22.5°	802.8	770.1	737.4	704.7	672.0	659.1	646.2	632.4	619.5	613.5	615.2
25°	768.3	740.0	710.7	682.3	653.1	641.0	628.1	616.1	603.1	596.3	601.4
27.5°	732.2	708.1	684.0	659.9	635.8	622.9	610.0	596.3	583.4	580.8	592.8
30°	691.8	673.7	654.8	636.7	617.8	604.0	590.2	576.5	562.7	561.8	580.8
32.5°	646.2	633.3	621.2	608.3	595.4	582.5	569.6	555.8	542.9	542.1	565.3
35°	584.2	580.8	577.3	573.0	569.6	556.7	543.8	530.9	518.0	518.8	544.6
37.5°	516.2	522.3	529.2	535.2	541.2	529.2	518.0	505.9	493.9	493.9	521.4
40°	456.0	468.1	480.1	492.2	504.2	496.5	487.9	480.1	471.5	468.9	497.3
42.5°	411.3	422.5	433.6	444.0	455.2	452.6	450.9	448.3	445.7	442.3	469.8
45°	376.9	378.6	381.2	382.9	384.6	393.2	401.8	410.4	419.0	416.4	441.4
47.5°	365.7	354.5	342.4	331.3	319.2	337.3	355.3	372.6	390.6	389.8	412.1
50°	364.8	342.4	319.2	296.8	273.6	295.1	316.6	337.3	358.8	362.2	379.4
52.5°	331.3	310.6	290.0	268.4	247.8	266.7	284.8	303.7	321.8	332.1	347.6
55°	307.2	287.4	267.6	247.8	228.0	240.9	253.0	265.9	277.9	300.3	314.0
57.5°	302.0	277.9	253.8	228.9	204.8	213.4	221.1	229.7	237.5	259.0	276.2
60°	277.1	253.0	228.9	203.9	179.8	185.8	191.0	197.0	202.2	218.5	239.2
62.5°	251.2	228.9	207.4	185.0	162.6	168.6	173.8	179.8	185.0	188.4	210.8
65°	213.4	197.0	180.7	164.3	148.0	153.2	157.5	162.6	166.9	167.8	188.4
67.5°	162.6	155.7	148.9	141.1	134.2	139.4	143.7	148.9	153.2	154.0	171.2
70°	120.5	120.5	120.5	119.6	119.6	123.9	129.1	133.4	137.7	139.4	152.3
72.5°	99.8	101.5	104.1	105.8	107.6	111.0	114.4	117.9	121.3	123.0	132.5
75°	80.9	84.3	87.8	90.3	93.8	96.4	98.9	100.7	103.2	104.1	111.0
77.5°	59.4	63.7	68.0	71.4	75.7	78.3	80.0	82.6	84.3	82.6	87.8
80°	44.7	47.3	49.9	51.6	54.2	55.9	58.5	60.2	61.9	60.2	63.7
82.5°	30.1	31.0	32.7	33.6	34.4	36.1	37.9	39.6	41.3	39.6	42.2
85°	13.8	14.6	16.3	17.2	18.1	19.8	20.6	22.4	23.2	22.4	23.2
87.5°	4.3	5.2	6.0	6.0	6.9	7.7	8.6	9.5	10.3	10.3	11.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5
2.5°	900.0	898.3	894.8	892.2	888.8	885.4	883.6	881.9	880.2	878.5	880.2
5°	869.0	863.9	856.1	848.4	840.6	832.9	822.6	812.2	804.5	796.7	795.0
7.5°	804.5	788.1	774.4	759.7	746.0	731.3	723.6	715.9	709.0	702.1	700.4
10°	731.3	715.0	705.5	696.9	687.5	678.0	673.7	668.5	667.7	666.0	666.8
12.5°	687.5	678.0	672.8	667.7	661.7	656.5	655.6	654.8	657.4	659.1	665.1
15°	661.7	654.8	653.1	651.3	648.7	647.0	652.2	656.5	672.0	686.6	703.8
17.5°	641.9	636.7	641.0	644.4	648.7	652.2	678.9	705.5	726.2	746.0	752.0
20°	628.1	625.5	642.7	660.8	678.0	695.2	715.9	735.7	743.4	750.3	753.7
22.5°	616.1	617.8	643.6	668.5	694.4	719.3	727.9	735.7	740.8	746.0	748.6
25°	607.4	612.6	638.4	665.1	690.9	716.7	721.9	726.2	727.9	728.8	734.8
27.5°	604.9	616.9	639.3	661.7	683.2	705.5	709.0	712.4	714.1	715.0	721.0
30°	598.8	617.8	636.7	654.8	673.7	691.8	690.9	690.0	693.5	696.9	703.0
32.5°	588.5	611.8	626.4	641.9	656.5	671.1	670.3	669.4	674.6	678.9	683.2
35°	571.3	597.1	610.0	622.1	635.0	647.0	647.9	647.9	652.2	656.5	659.1
37.5°	549.8	577.3	589.4	601.4	612.6	624.7	623.8	622.9	624.7	625.5	629.8
40°	524.8	553.2	565.3	577.3	588.5	600.6	598.0	594.5	594.5	593.7	598.8
42.5°	496.5	524.0	536.0	548.1	559.3	571.3	566.1	560.1	561.8	562.7	569.6
45°	467.2	492.2	503.3	515.4	526.6	537.8	534.3	530.0	533.5	536.9	543.8
47.5°	434.5	456.9	468.9	481.0	493.0	505.1	503.3	500.8	504.2	507.6	515.4
50°	397.5	414.7	429.3	444.0	458.6	473.2	473.2	473.2	476.7	479.2	487.0
52.5°	362.2	377.7	394.9	412.1	428.5	445.7	446.6	447.4	450.9	453.4	460.3
55°	327.8	341.6	360.5	379.4	398.4	417.3	419.0	420.7	424.2	426.8	433.6
57.5°	292.5	309.7	329.5	350.2	370.0	389.8	390.6	391.5	394.1	396.6	402.7
60°	259.8	280.5	299.4	319.2	338.1	357.1	360.5	363.1	364.8	366.5	371.7
62.5°	234.0	256.4	273.6	291.7	308.9	326.1	330.4	333.8	335.6	336.4	339.9
65°	209.9	230.6	246.9	262.4	278.8	294.3	297.7	301.1	303.7	305.4	308.0
67.5°	188.4	205.6	218.5	231.5	244.4	257.3	262.4	266.7	268.4	270.2	271.9
70°	166.1	179.0	190.2	201.3	212.5	223.7	228.0	232.3	234.0	234.9	235.8
72.5°	142.0	151.4	160.0	168.6	177.2	185.8	190.2	194.5	196.2	197.0	197.9
75°	117.0	123.9	130.8	137.7	144.5	151.4	154.9	157.5	158.3	159.2	159.2
77.5°	92.1	97.2	102.4	107.6	111.9	117.0	119.6	122.2	122.2	122.2	122.2
80°	66.3	69.7	73.1	76.6	80.0	83.5	84.3	85.2	86.0	86.9	86.9
82.5°	43.9	46.5	48.2	50.8	52.5	54.2	54.2	54.2	54.2	54.2	55.1
85°	25.0	25.8	26.7	27.5	28.4	29.3	30.1	30.1	30.1	30.1	30.1
87.5°	11.2	12.0	12.0	12.9	12.9	12.9	12.9	12.0	12.0	12.0	12.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5
2.5°	881.1	882.8	883.6	881.9	879.3	877.6	875.0	875.9	876.8	877.6	878.5
5°	792.4	790.7	788.1	782.1	776.1	770.1	765.8	762.3	758.9	755.4	752.0
7.5°	697.8	696.1	693.5	691.8	690.0	688.3	684.9	684.0	683.2	682.3	681.4
10°	667.7	667.7	668.5	669.4	669.4	670.3	671.1	672.8	673.7	675.4	676.3
12.5°	671.1	676.3	682.3	693.5	705.5	716.7	724.5	731.3	739.1	746.0	752.9
15°	721.9	739.1	756.3	760.6	765.8	770.1	772.6	774.4	776.1	777.0	778.7
17.5°	758.0	763.2	769.2	770.9	773.5	775.2	776.1	777.0	778.7	779.5	780.4
20°	757.2	759.7	763.2	765.8	768.3	770.9	772.6	775.2	777.0	779.5	781.3
22.5°	752.0	754.6	757.2	761.5	764.9	769.2	772.6	774.4	776.1	777.8	779.5
25°	740.0	746.0	751.1	754.6	757.2	760.6	760.6	760.6	761.5	761.5	761.5
27.5°	727.0	733.1	739.1	740.0	741.7	742.5	744.3	746.0	746.8	748.6	749.4
30°	709.0	715.0	721.0	722.7	724.5	726.2	724.5	723.6	722.7	721.0	720.2
32.5°	688.3	692.6	696.9	697.8	697.8	698.7	694.4	693.5	692.6	690.9	690.0
35°	662.5	665.1	667.7	666.8	666.8	666.0	666.8	666.8	666.8	666.0	666.0
37.5°	633.3	637.6	641.0	641.9	641.9	642.7	644.4	644.4	644.4	643.6	643.6
40°	604.9	610.0	615.2	616.1	617.8	618.6	619.5	619.5	619.5	618.6	618.6
42.5°	576.5	583.4	590.2	592.0	593.7	595.4	594.5	593.7	593.7	592.8	592.0
45°	551.5	558.4	565.3	566.1	567.9	568.7	569.6	568.7	567.0	566.1	564.4
47.5°	523.1	530.0	537.8	539.5	540.3	542.1	542.1	541.2	540.3	538.6	537.8
50°	495.6	503.3	511.1	511.9	512.8	513.7	512.8	511.1	510.2	508.5	506.8
52.5°	468.1	474.9	481.8	481.8	481.0	481.0	481.0	481.0	481.8	481.8	481.8
55°	439.7	446.6	452.6	452.6	452.6	452.6	453.4	455.2	456.9	457.7	459.5
57.5°	409.6	415.6	421.6	422.5	422.5	423.3	423.3	424.2	425.9	426.8	427.6
60°	377.7	382.9	388.0	388.9	388.9	389.8	391.5	392.3	393.2	394.1	394.9
62.5°	343.3	345.9	349.3	351.0	352.8	354.5	356.2	356.2	357.1	357.1	357.1
65°	310.6	312.3	314.9	315.8	316.6	317.5	319.2	319.2	320.1	320.1	320.1
67.5°	273.6	274.5	276.2	277.1	278.8	279.6	278.8	278.8	278.8	277.9	277.9
70°	236.6	237.5	238.3	239.2	240.1	240.9	240.9	240.9	240.9	240.1	240.1
72.5°	197.9	198.8	198.8	198.8	199.6	199.6	198.8	199.6	200.5	201.3	202.2
75°	160.0	160.0	160.0	160.0	159.2	159.2	160.9	160.9	160.0	160.0	159.2
77.5°	122.2	122.2	122.2	122.2	121.3	121.3	123.0	123.0	122.2	122.2	121.3
80°	86.9	86.0	86.0	86.0	86.0	86.0	85.2	85.2	85.2	85.2	85.2
82.5°	55.1	55.9	55.9	55.9	55.1	55.1	54.2	54.2	54.2	54.2	54.2
85°	29.3	29.3	28.4	29.3	29.3	30.1	31.0	31.0	30.1	30.1	29.3
87.5°	12.0	12.0	12.0	12.0	11.2	11.2	10.3	10.3	10.3	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5
2.5°	875.9	874.2	871.6	869.0	871.6	874.2	875.9	878.5	877.6	876.8	875.9
5°	749.4	746.8	743.4	740.8	743.4	746.8	749.4	752.0	755.4	758.9	762.3
7.5°	679.7	678.0	676.3	674.6	676.3	678.0	679.7	681.4	682.3	683.2	684.0
10°	676.3	676.3	675.4	675.4	675.4	676.3	676.3	676.3	675.4	673.7	672.8
12.5°	752.9	752.0	752.0	751.1	752.0	752.0	752.9	752.9	746.0	739.1	731.3
15°	778.7	779.5	779.5	779.5	779.5	779.5	778.7	778.7	777.0	776.1	774.4
17.5°	780.4	780.4	780.4	780.4	780.4	780.4	780.4	780.4	779.5	778.7	777.0
20°	782.1	782.1	783.0	783.0	783.0	782.1	782.1	781.3	779.5	777.0	775.2
22.5°	779.5	779.5	778.7	778.7	778.7	779.5	779.5	779.5	777.8	776.1	774.4
25°	761.5	762.3	762.3	762.3	762.3	762.3	761.5	761.5	761.5	761.5	760.6
27.5°	749.4	749.4	748.6	748.6	748.6	749.4	749.4	749.4	748.6	746.8	746.0
30°	719.3	718.4	717.6	716.7	717.6	718.4	719.3	720.2	721.0	722.7	723.6
32.5°	689.2	689.2	688.3	687.5	688.3	689.2	689.2	690.0	690.9	692.6	693.5
35°	665.1	665.1	664.2	663.4	664.2	665.1	665.1	666.0	666.0	666.8	666.8
37.5°	642.7	641.9	641.0	640.1	641.0	641.9	642.7	643.6	643.6	644.4	644.4
40°	617.8	617.8	616.9	616.1	616.9	617.8	617.8	618.6	618.6	619.5	619.5
42.5°	592.0	591.1	591.1	590.2	591.1	591.1	592.0	592.0	592.8	593.7	593.7
45°	563.6	563.6	562.7	561.8	562.7	563.6	563.6	564.4	566.1	567.0	568.7
47.5°	536.9	536.9	536.0	535.2	536.0	536.9	536.9	537.8	538.6	540.3	541.2
50°	506.8	506.8	505.9	505.9	505.9	506.8	506.8	506.8	508.5	510.2	511.1
52.5°	482.7	482.7	483.6	483.6	483.6	482.7	482.7	481.8	481.8	481.8	481.0
55°	460.3	460.3	461.2	461.2	461.2	460.3	460.3	459.5	457.7	456.9	455.2
57.5°	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	426.8	425.9	424.2
60°	394.9	394.9	394.1	394.1	394.1	394.9	394.9	394.9	394.1	393.2	392.3
62.5°	357.1	356.2	356.2	355.3	356.2	356.2	357.1	357.1	357.1	357.1	356.2
65°	320.1	319.2	319.2	318.4	319.2	319.2	320.1	320.1	320.1	320.1	319.2
67.5°	278.8	279.6	280.5	281.4	280.5	279.6	278.8	277.9	277.9	278.8	278.8
70°	240.9	240.9	241.8	241.8	241.8	240.9	240.9	240.1	240.1	240.9	240.9
72.5°	201.3	201.3	200.5	199.6	200.5	201.3	201.3	202.2	201.3	200.5	199.6
75°	160.0	160.9	160.9	161.8	160.9	160.9	160.0	159.2	160.0	160.0	160.9
77.5°	121.3	121.3	121.3	121.3	121.3	121.3	121.3	121.3	122.2	122.2	123.0
80°	85.2	85.2	84.3	84.3	84.3	85.2	85.2	85.2	85.2	85.2	85.2
82.5°	55.1	55.1	55.9	55.9	55.9	55.1	55.1	54.2	54.2	54.2	54.2
85°	29.3	29.3	29.3	29.3	29.3	29.3	29.3	29.3	30.1	30.1	31.0
87.5°	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5
2.5°	875.0	877.6	879.3	881.9	883.6	882.8	881.1	880.2	878.5	880.2	881.9
5°	765.8	770.1	776.1	782.1	788.1	790.7	792.4	795.0	796.7	804.5	812.2
7.5°	684.9	688.3	690.0	691.8	693.5	696.1	697.8	700.4	702.1	709.0	715.9
10°	671.1	670.3	669.4	669.4	668.5	667.7	667.7	666.8	666.0	667.7	668.5
12.5°	724.5	716.7	705.5	693.5	682.3	676.3	671.1	665.1	659.1	657.4	654.8
15°	772.6	770.1	765.8	760.6	756.3	739.1	721.9	703.8	686.6	672.0	656.5
17.5°	776.1	775.2	773.5	770.9	769.2	763.2	758.0	752.0	746.0	726.2	705.5
20°	772.6	770.9	768.3	765.8	763.2	759.7	757.2	753.7	750.3	743.4	735.7
22.5°	772.6	769.2	764.9	761.5	757.2	754.6	752.0	748.6	746.0	740.8	735.7
25°	760.6	760.6	757.2	754.6	751.1	746.0	740.0	734.8	728.8	727.9	726.2
27.5°	744.3	742.5	741.7	740.0	739.1	733.1	727.0	721.0	715.0	714.1	712.4
30°	724.5	726.2	724.5	722.7	721.0	715.0	709.0	703.0	696.9	693.5	690.0
32.5°	694.4	698.7	697.8	697.8	696.9	692.6	688.3	683.2	678.9	674.6	669.4
35°	666.8	666.0	666.8	666.8	667.7	665.1	662.5	659.1	656.5	652.2	647.9
37.5°	644.4	642.7	641.9	641.9	641.0	637.6	633.3	629.8	625.5	624.7	622.9
40°	619.5	618.6	617.8	616.1	615.2	610.0	604.9	598.8	593.7	594.5	594.5
42.5°	594.5	595.4	593.7	592.0	590.2	583.4	576.5	569.6	562.7	561.8	560.1
45°	569.6	568.7	567.9	566.1	565.3	558.4	551.5	543.8	536.9	533.5	530.0
47.5°	542.1	542.1	540.3	539.5	537.8	530.0	523.1	515.4	507.6	504.2	500.8
50°	512.8	513.7	512.8	511.9	511.1	503.3	495.6	487.0	479.2	476.7	473.2
52.5°	481.0	481.0	481.0	481.8	481.8	474.9	468.1	460.3	453.4	450.9	447.4
55°	453.4	452.6	452.6	452.6	452.6	446.6	439.7	433.6	426.8	424.2	420.7
57.5°	423.3	423.3	422.5	422.5	421.6	415.6	409.6	402.7	396.6	394.1	391.5
60°	391.5	389.8	388.9	388.9	388.0	382.9	377.7	371.7	366.5	364.8	363.1
62.5°	356.2	354.5	352.8	351.0	349.3	345.9	343.3	339.9	336.4	335.6	333.8
65°	319.2	317.5	316.6	315.8	314.9	312.3	310.6	308.0	305.4	303.7	301.1
67.5°	278.8	279.6	278.8	277.1	276.2	274.5	273.6	271.9	270.2	268.4	266.7
70°	240.9	240.9	240.1	239.2	238.3	237.5	236.6	235.8	234.9	234.0	232.3
72.5°	198.8	199.6	199.6	198.8	198.8	198.8	197.9	197.9	197.0	196.2	194.5
75°	160.9	159.2	159.2	160.0	160.0	160.0	160.0	159.2	159.2	158.3	157.5
77.5°	123.0	121.3	121.3	122.2	122.2	122.2	122.2	122.2	122.2	122.2	122.2
80°	85.2	86.0	86.0	86.0	86.0	86.0	86.9	86.9	86.9	86.0	85.2
82.5°	54.2	55.1	55.1	55.9	55.9	55.9	55.1	55.1	54.2	54.2	54.2
85°	31.0	30.1	29.3	29.3	28.4	29.3	29.3	30.1	30.1	30.1	30.1
87.5°	10.3	11.2	11.2	12.0	12.0	12.0	12.0	12.0	12.0	12.0	12.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5
2.5°	883.6	885.4	888.8	892.2	894.8	898.3	900.0	900.8	902.6	905.2	906.0
5°	822.6	832.9	840.6	848.4	856.1	863.9	869.0	875.0	880.2	885.4	888.8
7.5°	723.6	731.3	746.0	759.7	774.4	788.1	804.5	821.7	838.0	851.8	859.5
10°	673.7	678.0	687.5	696.9	705.5	715.0	731.3	748.6	764.9	789.0	807.1
12.5°	655.6	656.5	661.7	667.7	672.8	678.0	687.5	697.8	707.3	723.6	749.4
15°	652.2	647.0	648.7	651.3	653.1	654.8	661.7	668.5	675.4	687.5	709.8
17.5°	678.9	652.2	648.7	644.4	641.0	636.7	641.9	646.2	651.3	659.9	678.0
20°	715.9	695.2	678.0	660.8	642.7	625.5	628.1	629.8	632.4	640.1	653.9
22.5°	727.9	719.3	694.4	668.5	643.6	617.8	616.1	615.2	613.5	619.5	632.4
25°	721.9	716.7	690.9	665.1	638.4	612.6	607.4	601.4	596.3	603.1	616.1
27.5°	709.0	705.5	683.2	661.7	639.3	616.9	604.9	592.8	580.8	583.4	596.3
30°	690.9	691.8	673.7	654.8	636.7	617.8	598.8	580.8	561.8	562.7	576.5
32.5°	670.3	671.1	656.5	641.9	626.4	611.8	588.5	565.3	542.1	542.9	555.8
35°	647.9	647.0	635.0	622.1	610.0	597.1	571.3	544.6	518.8	518.0	530.9
37.5°	623.8	624.7	612.6	601.4	589.4	577.3	549.8	521.4	493.9	493.9	505.9
40°	598.0	600.6	588.5	577.3	565.3	553.2	524.8	497.3	468.9	471.5	480.1
42.5°	566.1	571.3	559.3	548.1	536.0	524.0	496.5	469.8	442.3	445.7	448.3
45°	534.3	537.8	526.6	515.4	503.3	492.2	467.2	441.4	416.4	419.0	410.4
47.5°	503.3	505.1	493.0	481.0	468.9	456.9	434.5	412.1	389.8	390.6	372.6
50°	473.2	473.2	458.6	444.0	429.3	414.7	397.5	379.4	362.2	358.8	337.3
52.5°	446.6	445.7	428.5	412.1	394.9	377.7	362.2	347.6	332.1	321.8	303.7
55°	419.0	417.3	398.4	379.4	360.5	341.6	327.8	314.0	300.3	277.9	265.9
57.5°	390.6	389.8	370.0	350.2	329.5	309.7	292.5	276.2	259.0	237.5	229.7
60°	360.5	357.1	338.1	319.2	299.4	280.5	259.8	239.2	218.5	202.2	197.0
62.5°	330.4	326.1	308.9	291.7	273.6	256.4	234.0	210.8	188.4	185.0	179.8
65°	297.7	294.3	278.8	262.4	246.9	230.6	209.9	188.4	167.8	166.9	162.6
67.5°	262.4	257.3	244.4	231.5	218.5	205.6	188.4	171.2	154.0	153.2	148.9
70°	228.0	223.7	212.5	201.3	190.2	179.0	166.1	152.3	139.4	137.7	133.4
72.5°	190.2	185.8	177.2	168.6	160.0	151.4	142.0	132.5	123.0	121.3	117.9
75°	154.9	151.4	144.5	137.7	130.8	123.9	117.0	111.0	104.1	103.2	100.7
77.5°	119.6	117.0	111.9	107.6	102.4	97.2	92.1	87.8	82.6	84.3	82.6
80°	84.3	83.5	80.0	76.6	73.1	69.7	66.3	63.7	60.2	61.9	60.2
82.5°	54.2	54.2	52.5	50.8	48.2	46.5	43.9	42.2	39.6	41.3	39.6
85°	30.1	29.3	28.4	27.5	26.7	25.8	25.0	23.2	22.4	23.2	22.4
87.5°	12.9	12.9	12.9	12.9	12.0	12.0	11.2	11.2	10.3	10.3	9.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5
2.5°	906.9	907.7	908.6	911.2	912.9	915.5	917.2	917.2	917.2	917.2	917.2
5°	892.2	894.8	898.3	902.6	906.0	910.3	913.8	915.5	917.2	918.9	920.6
7.5°	867.3	875.0	882.8	888.8	894.8	900.8	906.9	910.3	913.8	916.3	919.8
10°	826.0	844.1	862.1	871.6	880.2	889.7	898.3	902.6	907.7	912.0	916.3
12.5°	775.2	800.2	826.0	841.5	856.1	871.6	886.2	892.2	899.1	905.2	911.2
15°	733.1	755.4	777.8	801.9	825.1	849.2	872.5	880.2	887.1	894.8	901.7
17.5°	695.2	713.3	730.5	761.5	792.4	822.6	853.5	863.0	871.6	881.1	889.7
20°	668.5	682.3	696.1	730.5	764.0	798.5	832.0	842.3	852.7	863.0	873.3
22.5°	646.2	659.1	672.0	704.7	737.4	770.1	802.8	816.5	829.4	843.2	856.1
25°	628.1	641.0	653.1	682.3	710.7	740.0	768.3	785.6	802.8	820.0	837.2
27.5°	610.0	622.9	635.8	659.9	684.0	708.1	732.2	752.9	772.6	793.3	813.1
30°	590.2	604.0	617.8	636.7	654.8	673.7	691.8	714.1	735.7	758.0	779.5
32.5°	569.6	582.5	595.4	608.3	621.2	633.3	646.2	666.8	688.3	709.0	729.6
35°	543.8	556.7	569.6	573.0	577.3	580.8	584.2	610.9	637.6	664.2	690.9
37.5°	518.0	529.2	541.2	535.2	529.2	522.3	516.2	551.5	586.8	622.1	657.4
40°	487.9	496.5	504.2	492.2	480.1	468.1	456.0	493.0	530.9	567.9	604.9
42.5°	450.9	452.6	455.2	444.0	433.6	422.5	411.3	445.7	479.2	513.7	547.2
45°	401.8	393.2	384.6	382.9	381.2	378.6	376.9	415.6	454.3	493.0	531.7
47.5°	355.3	337.3	319.2	331.3	342.4	354.5	365.7	399.2	433.6	467.2	500.8
50°	316.6	295.1	273.6	296.8	319.2	342.4	364.8	390.6	415.6	441.4	466.3
52.5°	284.8	266.7	247.8	268.4	290.0	310.6	331.3	354.5	377.7	401.0	424.2
55°	253.0	240.9	228.0	247.8	267.6	287.4	307.2	325.2	344.2	362.2	380.3
57.5°	221.1	213.4	204.8	228.9	253.8	277.9	302.0	305.4	309.7	313.2	316.6
60°	191.0	185.8	179.8	203.9	228.9	253.0	277.1	265.0	253.0	240.9	228.9
62.5°	173.8	168.6	162.6	185.0	207.4	228.9	251.2	229.7	209.1	187.6	166.1
65°	157.5	153.2	148.0	164.3	180.7	197.0	213.4	195.3	176.4	158.3	139.4
67.5°	143.7	139.4	134.2	141.1	148.9	155.7	162.6	150.6	138.5	125.6	113.6
70°	129.1	123.9	119.6	119.6	120.5	120.5	120.5	109.3	98.1	86.9	75.7
72.5°	114.4	111.0	107.6	105.8	104.1	101.5	99.8	90.3	80.9	70.6	61.1
75°	98.9	96.4	93.8	90.3	87.8	84.3	80.9	76.6	73.1	68.8	64.5
77.5°	80.0	78.3	75.7	71.4	68.0	63.7	59.4	59.4	60.2	60.2	60.2
80°	58.5	55.9	54.2	51.6	49.9	47.3	44.7	45.6	46.5	46.5	47.3
82.5°	37.9	36.1	34.4	33.6	32.7	31.0	30.1	30.1	30.1	30.1	30.1
85°	20.6	19.8	18.1	17.2	16.3	14.6	13.8	14.6	15.5	16.3	17.2
87.5°	8.6	7.7	6.9	6.0	6.0	5.2	4.3	5.2	6.0	6.9	7.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5
2.5°	918.9	919.8	921.5	922.4	924.1	924.1	924.1	924.1	923.2	923.2	922.4
5°	923.2	925.8	927.5	930.1	931.8	932.7	932.7	933.5	933.5	933.5	932.7
7.5°	923.2	925.8	929.2	931.8	934.4	935.3	936.1	937.0	936.1	936.1	935.3
10°	919.8	923.2	926.7	930.1	931.8	932.7	933.5	934.4	933.5	933.5	932.7
12.5°	914.6	918.1	920.6	924.1	925.8	926.7	928.4	929.2	929.2	929.2	928.4
15°	905.2	907.7	911.2	913.8	915.5	917.2	919.8	921.5	921.5	920.6	920.6
17.5°	893.1	896.5	900.0	903.4	906.0	907.7	908.6	910.3	910.3	910.3	909.5
20°	877.6	881.9	885.4	889.7	892.2	894.0	894.8	896.5	896.5	896.5	896.5
22.5°	860.4	864.7	869.0	873.3	875.0	876.8	878.5	880.2	880.2	880.2	880.2
25°	840.6	844.9	848.4	851.8	857.0	858.7	860.4	862.1	863.0	863.9	863.9
27.5°	818.2	822.6	827.7	832.0	835.5	838.0	839.8	842.3	843.2	844.1	844.1
30°	786.4	794.2	801.0	807.9	811.4	814.8	819.1	822.6	823.4	823.4	824.3
32.5°	743.4	756.3	770.1	783.0	790.7	794.2	797.6	801.0	800.2	798.5	797.6
35°	708.1	725.3	742.5	759.7	766.6	769.2	771.8	774.4	772.6	771.8	770.1
37.5°	677.1	696.9	715.9	735.7	740.8	742.5	745.1	746.8	745.1	743.4	740.8
40°	630.7	656.5	681.4	707.3	710.7	712.4	714.1	715.9	714.1	713.3	711.6
42.5°	579.9	612.6	644.4	677.1	681.4	680.6	678.9	678.0	678.9	680.6	681.4
45°	560.1	588.5	616.1	644.4	649.6	647.9	646.2	644.4	646.2	647.9	649.6
47.5°	528.3	556.7	584.2	611.8	611.8	610.9	610.0	609.2	611.8	613.5	616.1
50°	491.3	517.1	542.1	567.0	563.6	567.9	571.3	575.6	578.2	580.8	583.4
52.5°	445.7	467.2	487.9	509.4	522.3	528.3	535.2	541.2	542.9	544.6	545.5
55°	399.2	419.0	437.9	456.9	482.7	489.6	495.6	502.5	504.2	506.8	508.5
57.5°	339.9	363.1	385.5	408.7	441.4	449.1	457.7	465.5	465.5	465.5	464.6
60°	260.7	293.4	325.2	357.1	395.8	404.4	412.1	420.7	419.9	419.9	419.0
62.5°	199.6	232.3	265.9	298.6	342.4	354.5	365.7	377.7	377.7	377.7	376.9
65°	157.5	176.4	194.5	212.5	284.8	302.0	318.4	335.6	336.4	336.4	337.3
67.5°	121.3	129.1	135.9	143.7	237.5	256.4	276.2	295.1	295.1	294.3	294.3
70°	81.7	87.8	93.8	99.8	192.7	213.4	234.9	255.5	254.7	253.8	252.1
72.5°	64.5	67.1	70.6	73.1	149.7	171.2	193.6	215.1	214.2	212.5	211.7
75°	62.8	60.2	58.5	55.9	111.0	132.5	153.2	174.7	173.8	172.9	172.1
77.5°	56.8	52.5	49.0	44.7	81.7	100.7	119.6	138.5	137.7	135.9	135.1
80°	43.9	40.4	37.0	33.6	55.9	70.6	85.2	99.8	99.8	99.8	99.8
82.5°	29.3	27.5	26.7	25.0	35.3	46.5	56.8	68.0	67.1	67.1	66.3
85°	17.2	16.3	16.3	15.5	21.5	26.7	31.8	37.0	37.9	37.9	38.7
87.5°	8.6	8.6	9.5	9.5	12.0	14.6	16.3	18.9	18.9	19.8	19.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5
2.5°	921.5	920.6	918.9	920.6	921.5	923.2	925.8	927.5	929.2	930.1	931.0
5°	932.7	931.8	931.0	931.8	932.7	935.3	937.0	939.6	941.3	942.1	942.1
7.5°	934.4	934.4	933.5	934.4	935.3	937.8	939.6	942.1	943.9	944.7	944.7
10°	931.8	931.8	931.8	933.5	935.3	937.8	939.6	942.1	943.9	944.7	944.7
12.5°	928.4	928.4	927.5	929.2	931.0	933.5	935.3	937.8	939.6	940.4	940.4
15°	919.8	919.8	919.8	921.5	923.2	925.8	928.4	930.1	932.7	933.5	934.4
17.5°	909.5	910.3	910.3	912.0	913.8	916.3	918.1	920.6	922.4	923.2	923.2
20°	896.5	896.5	896.5	899.1	900.8	903.4	905.2	907.7	909.5	910.3	912.0
22.5°	880.2	881.1	881.9	885.4	887.9	889.7	892.2	894.0	895.7	895.7	896.5
25°	864.7	866.4	867.3	869.0	870.7	871.6	872.5	872.5	873.3	873.3	872.5
27.5°	844.9	846.6	848.4	849.2	849.2	849.2	850.1	850.1	850.1	850.9	851.8
30°	824.3	822.6	820.8	821.7	822.6	823.4	825.1	826.0	826.9	827.7	827.7
32.5°	795.9	795.9	795.0	796.7	797.6	799.3	801.0	802.8	804.5	804.5	804.5
35°	768.3	770.1	771.8	772.6	772.6	773.5	775.2	776.1	777.0	777.8	778.7
37.5°	739.1	741.7	744.3	746.0	746.8	747.7	748.6	749.4	750.3	749.4	749.4
40°	709.8	712.4	715.0	715.9	716.7	717.6	717.6	718.4	718.4	717.6	717.6
42.5°	682.3	683.2	684.0	685.7	687.5	686.6	686.6	685.7	684.9	684.0	682.3
45°	651.3	653.1	653.9	653.9	653.9	652.2	650.5	647.9	646.2	645.3	645.3
47.5°	617.8	620.4	622.1	619.5	616.1	614.3	612.6	610.0	608.3	607.4	606.6
50°	585.9	584.2	581.6	579.1	575.6	573.9	573.0	571.3	569.6	566.1	563.6
52.5°	547.2	543.8	540.3	537.8	534.3	531.7	529.2	526.6	524.0	522.3	521.4
55°	510.2	504.2	497.3	494.7	491.3	487.9	483.6	480.1	475.8	474.9	474.1
57.5°	464.6	461.2	456.9	451.7	445.7	442.3	439.7	436.2	432.8	431.9	431.1
60°	418.2	414.7	411.3	406.1	401.0	398.4	394.9	392.3	388.9	388.0	388.0
62.5°	376.9	374.3	370.8	363.1	355.3	353.6	351.0	349.3	346.7	345.0	344.2
65°	337.3	331.3	324.4	319.2	313.2	310.6	308.9	306.3	303.7	302.0	300.3
67.5°	293.4	285.7	277.1	274.5	271.9	269.3	265.9	263.3	259.8	259.0	258.1
70°	251.2	245.2	238.3	235.8	232.3	229.7	227.1	223.7	221.1	219.4	216.8
72.5°	209.9	204.8	198.8	195.3	191.9	189.3	187.6	185.0	182.4	180.7	179.0
75°	171.2	166.1	160.9	157.5	154.0	152.3	150.6	148.0	146.3	143.7	142.0
77.5°	133.4	130.8	127.3	123.0	118.7	117.9	117.0	116.2	115.3	112.7	111.0
80°	99.8	97.2	94.6	92.1	88.6	86.9	86.0	84.3	82.6	81.7	80.0
82.5°	65.4	63.7	61.9	61.1	60.2	59.4	58.5	57.6	56.8	55.9	55.9
85°	38.7	38.7	38.7	37.9	37.0	37.0	37.0	36.1	36.1	35.3	35.3
87.5°	19.8	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	21.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5
2.5°	931.8	931.0	931.8	931.8	932.7	932.7	931.8	931.8	931.0	930.1	931.0
5°	943.0	943.9	943.9	943.9	943.9	943.9	943.9	943.0	943.0	942.1	943.0
7.5°	945.6	945.6	946.5	946.5	947.3	947.3	946.5	946.5	945.6	944.7	945.6
10°	945.6	946.5	946.5	947.3	947.3	947.3	946.5	946.5	945.6	944.7	945.6
12.5°	941.3	941.3	942.1	942.1	943.0	943.0	943.0	942.1	942.1	941.3	942.1
15°	935.3	934.4	935.3	935.3	936.1	936.1	935.3	935.3	934.4	933.5	934.4
17.5°	924.1	924.9	924.9	925.8	925.8	925.8	924.9	924.1	923.2	922.4	923.2
20°	912.9	912.9	912.9	913.8	913.8	913.8	912.9	912.9	912.0	911.2	912.0
22.5°	896.5	896.5	896.5	895.7	895.7	894.8	894.0	894.0	893.1	892.2	893.1
25°	872.5	873.3	873.3	873.3	873.3	873.3	872.5	872.5	871.6	870.7	871.6
27.5°	852.7	850.9	851.8	851.8	852.7	852.7	852.7	851.8	851.8	850.9	851.8
30°	828.6	830.3	831.2	831.2	832.0	832.0	832.0	831.2	831.2	830.3	831.2
32.5°	804.5	806.2	806.2	806.2	806.2	806.2	806.2	805.3	805.3	804.5	805.3
35°	779.5	778.7	778.7	779.5	779.5	779.5	778.7	778.7	777.8	777.0	777.8
37.5°	748.6	748.6	748.6	748.6	748.6	748.6	747.7	747.7	746.8	746.0	746.8
40°	716.7	715.9	715.9	716.7	716.7	716.7	715.9	715.0	714.1	713.3	714.1
42.5°	681.4	681.4	681.4	681.4	680.6	680.6	680.6	680.6	679.7	679.7	679.7
45°	644.4	643.6	643.6	642.7	642.7	641.9	641.9	641.0	641.0	640.1	641.0
47.5°	605.7	605.7	604.9	603.1	602.3	600.6	599.7	598.8	597.1	596.3	597.1
50°	560.1	560.1	559.3	558.4	557.5	556.7	556.7	557.5	557.5	557.5	557.5
52.5°	519.7	516.2	515.4	515.4	514.5	513.7	513.7	513.7	512.8	512.8	512.8
55°	473.2	471.5	471.5	471.5	470.6	470.6	471.5	471.5	472.4	472.4	472.4
57.5°	430.2	429.3	429.3	428.5	428.5	427.6	426.8	426.8	425.9	425.0	425.9
60°	387.2	385.5	383.7	382.0	379.4	377.7	376.9	376.0	375.1	374.3	375.1
62.5°	342.4	339.0	338.1	336.4	335.6	333.8	332.1	331.3	329.5	327.8	329.5
65°	298.6	297.7	295.1	292.5	290.0	287.4	286.5	286.5	285.7	284.8	285.7
67.5°	257.3	252.1	250.4	248.7	246.9	245.2	245.2	245.2	245.2	245.2	245.2
70°	215.1	211.7	210.8	209.1	208.2	206.5	206.5	206.5	205.6	205.6	205.6
72.5°	177.2	173.8	172.9	172.1	170.4	169.5	169.5	169.5	168.6	168.6	168.6
75°	139.4	140.2	139.4	138.5	137.7	136.8	136.8	135.9	135.9	135.1	135.9
77.5°	108.4	108.4	107.6	106.7	105.8	105.0	105.0	105.0	105.0	105.0	105.0
80°	79.2	79.2	79.2	79.2	78.3	78.3	78.3	78.3	77.4	77.4	77.4
82.5°	55.1	55.1	55.1	55.1	55.1	55.1	55.1	54.2	54.2	53.3	54.2
85°	34.4	35.3	35.3	35.3	34.4	34.4	34.4	34.4	34.4	34.4	34.4
87.5°	21.5	21.5	21.5	22.4	22.4	22.4	22.4	22.4	21.5	21.5	21.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5
2.5°	931.8	931.8	932.7	932.7	931.8	931.8	931.0	931.8	931.0	930.1	929.2
5°	943.0	943.9	943.9	943.9	943.9	943.9	943.9	943.0	942.1	942.1	941.3
7.5°	946.5	946.5	947.3	947.3	946.5	946.5	945.6	945.6	944.7	944.7	943.9
10°	946.5	946.5	947.3	947.3	947.3	946.5	946.5	945.6	944.7	944.7	943.9
12.5°	942.1	943.0	943.0	943.0	942.1	942.1	941.3	941.3	940.4	940.4	939.6
15°	935.3	935.3	936.1	936.1	935.3	935.3	934.4	935.3	934.4	933.5	932.7
17.5°	924.1	924.9	925.8	925.8	925.8	924.9	924.9	924.1	923.2	923.2	922.4
20°	912.9	912.9	913.8	913.8	913.8	912.9	912.9	912.9	912.0	910.3	909.5
22.5°	894.0	894.0	894.8	895.7	895.7	896.5	896.5	896.5	896.5	895.7	895.7
25°	872.5	872.5	873.3	873.3	873.3	873.3	873.3	872.5	872.5	873.3	873.3
27.5°	851.8	852.7	852.7	852.7	851.8	851.8	850.9	852.7	851.8	850.9	850.1
30°	831.2	832.0	832.0	832.0	831.2	831.2	830.3	828.6	827.7	827.7	826.9
32.5°	805.3	806.2	806.2	806.2	806.2	806.2	806.2	804.5	804.5	804.5	804.5
35°	778.7	778.7	779.5	779.5	779.5	778.7	778.7	779.5	778.7	777.8	777.0
37.5°	747.7	747.7	748.6	748.6	748.6	748.6	748.6	748.6	749.4	749.4	750.3
40°	715.0	715.9	716.7	716.7	716.7	715.9	715.9	716.7	717.6	717.6	718.4
42.5°	680.6	680.6	680.6	680.6	681.4	681.4	681.4	681.4	682.3	684.0	684.9
45°	641.0	641.9	641.9	642.7	642.7	643.6	643.6	644.4	645.3	645.3	646.2
47.5°	598.8	599.7	600.6	602.3	603.1	604.9	605.7	605.7	606.6	607.4	608.3
50°	557.5	556.7	556.7	557.5	558.4	559.3	560.1	560.1	563.6	566.1	569.6
52.5°	513.7	513.7	513.7	514.5	515.4	515.4	516.2	519.7	521.4	522.3	524.0
55°	471.5	471.5	470.6	470.6	471.5	471.5	471.5	473.2	474.1	474.9	475.8
57.5°	426.8	426.8	427.6	428.5	428.5	429.3	429.3	430.2	431.1	431.9	432.8
60°	376.0	376.9	377.7	379.4	382.0	383.7	385.5	387.2	388.0	388.0	388.9
62.5°	331.3	332.1	333.8	335.6	336.4	338.1	339.0	342.4	344.2	345.0	346.7
65°	286.5	286.5	287.4	290.0	292.5	295.1	297.7	298.6	300.3	302.0	303.7
67.5°	245.2	245.2	245.2	246.9	248.7	250.4	252.1	257.3	258.1	259.0	259.8
70°	206.5	206.5	206.5	208.2	209.1	210.8	211.7	215.1	216.8	219.4	221.1
72.5°	169.5	169.5	169.5	170.4	172.1	172.9	173.8	177.2	179.0	180.7	182.4
75°	135.9	136.8	136.8	137.7	138.5	139.4	140.2	139.4	142.0	143.7	146.3
77.5°	105.0	105.0	105.0	105.8	106.7	107.6	108.4	108.4	111.0	112.7	115.3
80°	78.3	78.3	78.3	78.3	79.2	79.2	79.2	79.2	80.0	81.7	82.6
82.5°	54.2	55.1	55.1	55.1	55.1	55.1	55.1	55.1	55.9	55.9	56.8
85°	34.4	34.4	34.4	34.4	35.3	35.3	35.3	34.4	35.3	35.3	36.1
87.5°	22.4	22.4	22.4	22.4	22.4	21.5	21.5	21.5	21.5	20.6	20.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5
2.5°	927.5	925.8	923.2	921.5	920.6	918.9	920.6	921.5	922.4	923.2	923.2
5°	939.6	937.0	935.3	932.7	931.8	931.0	931.8	932.7	932.7	933.5	933.5
7.5°	942.1	939.6	937.8	935.3	934.4	933.5	934.4	934.4	935.3	936.1	936.1
10°	942.1	939.6	937.8	935.3	933.5	931.8	931.8	931.8	932.7	933.5	933.5
12.5°	937.8	935.3	933.5	931.0	929.2	927.5	928.4	928.4	928.4	929.2	929.2
15°	930.1	928.4	925.8	923.2	921.5	919.8	919.8	919.8	920.6	920.6	921.5
17.5°	920.6	918.1	916.3	913.8	912.0	910.3	910.3	909.5	909.5	910.3	910.3
20°	907.7	905.2	903.4	900.8	899.1	896.5	896.5	896.5	896.5	896.5	896.5
22.5°	894.0	892.2	889.7	887.9	884.5	881.9	881.1	880.2	880.2	880.2	880.2
25°	872.5	872.5	871.6	870.7	869.0	867.3	866.4	864.7	863.9	863.9	863.0
27.5°	850.1	850.1	849.2	849.2	849.2	848.4	846.6	844.9	844.1	844.1	843.2
30°	826.0	825.1	823.4	822.6	821.7	820.8	822.6	824.3	824.3	823.4	823.4
32.5°	802.8	801.0	799.3	797.6	796.7	795.0	795.9	795.9	797.6	798.5	800.2
35°	776.1	775.2	773.5	772.6	772.6	771.8	770.1	768.3	770.1	771.8	772.6
37.5°	749.4	748.6	747.7	746.8	746.0	744.3	741.7	739.1	740.8	742.5	745.1
40°	718.4	717.6	717.6	716.7	715.9	715.0	712.4	709.8	711.6	713.3	714.1
42.5°	685.7	686.6	686.6	687.5	685.7	684.0	683.2	682.3	681.4	680.6	678.9
45°	647.9	650.5	652.2	653.9	653.9	653.9	653.1	651.3	649.6	647.9	646.2
47.5°	610.0	612.6	614.3	616.1	619.5	622.1	620.4	617.8	616.1	613.5	611.8
50°	571.3	573.0	573.9	575.6	579.1	581.6	584.2	585.9	583.4	580.8	578.2
52.5°	526.6	529.2	531.7	534.3	537.8	540.3	543.8	547.2	545.5	544.6	542.9
55°	480.1	483.6	487.9	491.3	494.7	497.3	504.2	510.2	508.5	506.8	504.2
57.5°	436.2	438.8	442.3	445.7	451.7	456.9	461.2	464.6	464.6	465.5	465.5
60°	392.3	394.9	398.4	401.0	406.1	411.3	414.7	418.2	419.0	419.9	419.9
62.5°	349.3	351.0	353.6	355.3	363.1	370.8	374.3	376.9	376.9	377.7	377.7
65°	306.3	308.9	310.6	313.2	319.2	324.4	331.3	337.3	337.3	336.4	336.4
67.5°	263.3	265.9	269.3	271.9	274.5	277.1	285.7	293.4	294.3	294.3	295.1
70°	223.7	227.1	229.7	232.3	235.8	238.3	245.2	251.2	252.1	253.8	254.7
72.5°	185.0	187.6	189.3	191.9	195.3	198.8	204.8	209.9	211.7	212.5	214.2
75°	148.0	150.6	152.3	154.0	157.5	160.9	166.1	171.2	172.1	172.9	173.8
77.5°	116.2	117.0	117.9	118.7	123.0	127.3	130.8	133.4	135.1	135.9	137.7
80°	84.3	86.0	86.9	88.6	92.1	94.6	97.2	99.8	99.8	99.8	99.8
82.5°	57.6	58.5	59.4	60.2	61.1	61.9	63.7	65.4	66.3	67.1	67.1
85°	36.1	37.0	37.0	37.0	37.9	38.7	38.7	38.7	38.7	37.9	37.9
87.5°	20.6	20.6	20.6	20.6	20.6	20.6	20.6	19.8	19.8	19.8	18.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5	909.5
2.5°	924.1	924.1	924.1	924.1	922.4	921.5	919.8	918.9	917.2	917.2	917.2
5°	933.5	932.7	932.7	931.8	930.1	927.5	924.9	923.2	920.6	918.9	917.2
7.5°	937.0	936.1	935.3	934.4	931.8	929.2	925.8	923.2	919.8	916.3	912.9
10°	934.4	933.5	932.7	931.8	930.1	926.7	923.2	919.8	916.3	912.0	906.9
12.5°	929.2	928.4	926.7	925.8	924.1	920.6	917.2	914.6	911.2	905.2	898.3
15°	921.5	919.8	917.2	915.5	913.8	911.2	907.7	905.2	901.7	894.8	887.1
17.5°	910.3	908.6	907.7	906.0	903.4	900.0	896.5	893.1	889.7	881.1	871.6
20°	896.5	894.8	894.0	892.2	889.7	885.4	881.1	877.6	873.3	863.0	852.7
22.5°	880.2	878.5	876.8	875.0	873.3	869.0	864.7	860.4	856.1	843.2	829.4
25°	862.1	860.4	858.7	857.0	851.8	848.4	844.1	840.6	837.2	820.0	802.8
27.5°	842.3	839.8	838.0	835.5	832.0	827.7	822.6	818.2	813.1	793.3	772.6
30°	822.6	819.1	814.8	811.4	807.9	801.0	793.3	786.4	779.5	758.0	735.7
32.5°	801.0	797.6	794.2	790.7	783.0	770.1	756.3	743.4	729.6	709.0	687.5
35°	774.4	771.8	769.2	766.6	759.7	742.5	725.3	708.1	690.9	664.2	637.6
37.5°	746.8	745.1	742.5	740.8	735.7	715.9	696.1	677.1	657.4	622.1	586.8
40°	715.9	714.1	712.4	710.7	707.3	681.4	655.6	630.7	604.9	567.9	530.0
42.5°	678.0	678.9	680.6	681.4	677.1	644.4	611.8	579.9	547.2	513.7	479.2
45°	644.4	646.2	647.9	649.6	644.4	616.1	587.7	560.1	531.7	493.0	454.3
47.5°	609.2	610.0	610.9	611.8	611.8	584.2	555.8	528.3	500.8	467.2	432.8
50°	575.6	571.3	567.9	563.6	567.0	542.1	516.2	491.3	466.3	441.4	415.6
52.5°	541.2	535.2	528.3	522.3	509.4	487.9	466.3	445.7	424.2	401.0	377.7
55°	502.5	495.6	489.6	482.7	456.9	437.9	418.2	399.2	380.3	362.2	343.3
57.5°	465.5	457.7	449.1	441.4	408.7	385.5	362.2	339.9	316.6	313.2	308.9
60°	420.7	412.1	404.4	395.8	357.1	325.2	292.5	260.7	228.9	240.9	253.0
62.5°	377.7	365.7	354.5	342.4	298.6	265.9	232.3	199.6	166.1	187.6	209.1
65°	335.6	318.4	302.0	284.8	212.5	194.5	175.5	157.5	139.4	158.3	176.4
67.5°	295.1	276.2	256.4	237.5	143.7	135.9	128.2	121.3	113.6	125.6	138.5
70°	255.5	234.9	213.4	192.7	99.8	93.8	87.8	81.7	75.7	86.9	98.1
72.5°	215.1	193.6	171.2	149.7	73.1	70.6	67.1	64.5	61.1	70.6	80.9
75°	174.7	153.2	132.5	111.0	55.9	58.5	60.2	62.8	64.5	68.8	73.1
77.5°	138.5	119.6	100.7	81.7	44.7	49.0	52.5	56.8	60.2	60.2	60.2
80°	99.8	85.2	70.6	55.9	33.6	37.0	40.4	43.9	47.3	46.5	46.5
82.5°	68.0	56.8	46.5	35.3	25.0	26.7	27.5	29.3	30.1	30.1	30.1
85°	37.0	31.8	26.7	21.5	15.5	16.3	16.3	17.2	17.2	16.3	15.5
87.5°	18.9	16.3	14.6	12.0	9.5	9.5	8.6	8.6	7.7	6.9	6.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	909.5	909.5
2.5°	917.2	917.2
5°	915.5	913.8
7.5°	910.3	906.9
10°	902.6	898.3
12.5°	892.2	886.2
15°	880.2	872.5
17.5°	863.0	853.5
20°	842.3	832.0
22.5°	816.5	802.8
25°	785.6	768.3
27.5°	752.9	732.2
30°	714.1	691.8
32.5°	666.8	646.2
35°	610.9	584.2
37.5°	551.5	516.2
40°	493.0	456.0
42.5°	445.7	411.3
45°	415.6	376.9
47.5°	399.2	365.7
50°	390.6	364.8
52.5°	354.5	331.3
55°	325.2	307.2
57.5°	305.4	302.0
60°	265.0	277.1
62.5°	229.7	251.2
65°	195.3	213.4
67.5°	150.6	162.6
70°	109.3	120.5
72.5°	90.3	99.8
75°	76.6	80.9
77.5°	59.4	59.4
80°	45.6	44.7
82.5°	30.1	30.1
85°	14.6	13.8
87.5°	5.2	4.3
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

TEST NUMBER: P1055042

CATALOG NUMBER: SQ4R-FA-075D-940-1-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.63	19.24	18.00	19.56	19.87	19.55	21.16	19.91	21.47	21.79
	3H	18.30	19.75	18.67	20.08	20.44	21.34	22.80	21.72	23.12	23.48
	4H	18.63	19.99	19.03	20.34	20.72	21.97	23.33	22.36	23.68	24.06
	6H	18.92	20.18	19.33	20.55	20.94	22.35	23.61	22.76	23.98	24.37
	8H	18.99	20.20	19.42	20.59	20.99	22.44	23.65	22.87	24.04	24.44
	12H	19.02	20.18	19.45	20.56	20.99	22.49	23.65	22.92	24.03	24.46
4H	2H	18.76	20.13	19.16	20.48	20.85	20.12	21.48	20.52	21.83	22.21
	3H	20.08	21.22	20.49	21.62	22.02	22.15	23.29	22.56	23.69	24.09
	4H	20.51	21.54	20.95	21.96	22.39	22.89	23.92	23.32	24.33	24.77
	6H	20.81	21.70	21.26	22.15	22.60	23.38	24.28	23.84	24.72	25.18
	8H	20.88	21.72	21.35	22.17	22.63	23.51	24.35	23.97	24.79	25.26
	12H	20.93	21.68	21.41	22.16	22.62	23.58	24.34	24.06	24.81	25.28
8H	4H	21.10	21.94	21.56	22.39	22.85	23.11	23.96	23.58	24.40	24.86
	6H	21.58	22.28	22.08	22.77	23.25	23.71	24.41	24.20	24.90	25.37
	8H	21.71	22.34	22.22	22.84	23.33	23.89	24.51	24.40	25.02	25.51
	12H	21.79	22.34	22.29	22.83	23.39	24.01	24.57	24.52	25.06	25.62
12H	4H	21.15	21.91	21.63	22.38	22.85	23.12	23.87	23.60	24.35	24.82
	6H	21.68	22.31	22.19	22.82	23.30	23.73	24.35	24.24	24.86	25.35
	8H	21.89	22.44	22.40	22.93	23.49	23.95	24.51	24.46	25.00	25.56