

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P935482

Luminaire Tested: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-2700K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P935482
REPORT IS A COMBINATION OF REPORTS P933754 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-2700K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6814.7 lumens
Efficiency: N/A
Efficacy: 143.2 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 47.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P935482

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-2700K

Luminous Intensity Polar Plot



TEST NUMBER: P935482

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	88	85	81	83	79	76	73	62	60	58	46	44	43	31	30	29
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	48	43	40	35	33	30	24	22	21
4	70	60	52	47	62	54	47	42	42	38	34	31	28	26	21	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14
7	55	43	35	30	49	38	32	27	30	26	22	23	20	17	16	14	12
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	15	12	11
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	13	11	10
10	44	32	25	20	39	29	23	19	23	19	15	18	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6552	6552	6552	6552
5°	6593	6614	6593	5200
10°	6542	6515	6542	4658
15°	6463	6374	6463	5322
20°	6321	6206	6321	5333
25°	6037	5962	6037	5220
30°	5672	5760	5672	4973
35°	5050	5504	5050	4699
40°	4200	5203	4200	4494
45°	3745	4850	3745	4255
50°	3971	4429	3971	4018
55°	3724	3975	3724	3882
60°	3826	3375	3826	3555
65°	3451	2791	3451	3119
70°	2374	2225	2374	2615
75°	2056	1645	2056	1969
80°	1629	1088	1629	1182
85°	886	575	886	489

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 5752 cd/sqm

TEST NUMBER: P935482

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.7	0.9
10°-20°	181.0	2.7
20°-30°	279.7	4.1
30°-40°	333.9	4.9
40°-50°	335.9	4.9
50°-60°	292.3	4.3
60°-70°	207.2	3.0
70°-80°	109.6	1.6
80°-90°	30.2	0.4
90°-100°	374.5	5.5
100°-110°	984.7	14.4
110°-120°	1021.0	15.0
120°-130°	819.0	12.0
130°-140°	642.6	9.4
140°-150°	493.2	7.2
150°-160°	355.2	5.2
160°-170°	217.3	3.2
170°-180°	73.4	1.1
0°-30°	524.4	7.7
0°-40°	858.3	12.6
0°-60°	1486.5	21.8
0°-90°	1833.6	26.9
90°-120°	2380.3	34.9
90°-150°	4335.1	63.6
90°-180°	4981.0	73.1
0°-180°	6814.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	706	706	706	706	706	
5°	709	732	709	575	709	67
15°	677	725	677	605	677	191
25°	596	676	596	592	596	274
35°	454	603	454	515	454	281
45°	292	497	292	436	292	234
55°	238	367	238	358	238	219
65°	166	221	166	247	166	158
75°	63	105	63	126	63	66
85°	11	27	11	23	11	14
90°	5	20	5	20	5	5
95°	50	226	50	226	50	55
105°	177	1542	177	1542	177	188
115°	315	1985	315	1985	315	311
125°	438	1581	438	1581	438	389
135°	522	1227	522	1227	522	404
145°	606	995	606	995	606	380
155°	685	857	685	857	685	315
165°	739	798	739	798	739	209
175°	768	774	768	774	768	73
180°	768	768	768	768	768	

TEST NUMBER: P935482

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1
2.5°	712.0	712.0	716.0	717.4	717.4	715.4	713.4	715.4	721.4	723.4	722.7
5°	709.4	714.7	722.1	723.4	724.8	724.1	722.7	724.1	730.8	732.1	732.8
7.5°	704.1	714.0	723.4	725.4	727.4	725.4	724.8	726.1	732.8	734.1	734.1
10°	697.4	711.3	722.1	723.4	725.4	723.4	723.4	726.1	732.8	734.1	734.7
12.5°	688.0	707.4	717.4	718.7	721.4	720.7	720.1	722.7	729.5	730.8	730.8
15°	677.3	700.0	709.4	710.7	715.4	714.0	714.0	716.7	724.1	726.1	725.4
17.5°	662.6	690.7	701.4	703.4	706.8	706.1	706.8	709.4	716.0	717.4	718.1
20°	645.9	678.0	690.7	692.7	696.0	696.0	696.0	699.4	706.1	708.8	708.8
22.5°	623.2	664.6	678.0	679.4	683.4	683.4	684.7	689.3	695.3	696.0	696.0
25°	596.5	649.9	661.2	665.3	669.3	671.3	673.3	676.0	678.0	677.3	678.0
27.5°	568.4	631.3	645.9	648.6	654.0	656.0	658.7	659.3	659.9	661.9	660.6
30°	537.0	605.2	627.2	629.9	638.5	639.9	637.2	638.5	641.9	643.2	644.6
32.5°	501.7	566.4	607.9	613.8	621.9	617.9	617.2	619.2	624.6	624.6	625.9
35°	453.6	536.3	589.8	595.2	601.2	596.5	599.2	599.8	603.2	605.2	604.5
37.5°	400.8	510.4	571.1	575.1	579.8	573.8	577.8	579.8	582.5	581.2	581.2
40°	354.0	469.6	549.1	551.8	555.8	551.1	555.1	556.5	557.8	556.5	555.8
42.5°	319.3	424.8	525.7	529.1	526.4	529.7	531.1	533.8	531.7	529.1	529.1
45°	292.5	412.8	500.3	504.3	500.3	505.7	507.7	507.7	501.7	500.3	499.6
47.5°	283.9	388.7	474.9	474.9	472.9	479.6	483.0	478.3	472.3	470.2	470.2
50°	283.3	362.0	440.2	437.5	446.9	454.9	451.6	446.9	442.2	434.9	434.9
52.5°	257.2	329.3	395.4	405.5	420.1	424.8	419.5	414.8	406.8	403.5	400.8
55°	238.4	295.2	354.7	374.7	390.1	396.1	386.0	381.4	369.4	367.4	366.0
57.5°	234.5	245.8	317.3	342.6	361.3	360.8	354.7	346.0	336.0	334.0	333.4
60°	215.1	177.7	277.2	307.3	326.6	324.6	319.3	311.2	301.9	300.6	299.3
62.5°	195.0	128.9	231.8	265.8	293.2	292.5	287.9	275.9	269.2	265.8	263.1
65°	165.6	108.2	165.0	221.1	260.6	261.8	251.8	243.1	235.8	231.8	231.1
67.5°	126.3	88.1	111.6	184.4	229.1	227.8	215.1	211.1	201.7	199.7	195.7
70°	93.5	58.8	77.5	149.6	198.4	195.0	185.1	180.4	171.7	167.0	164.3
72.5°	77.5	47.4	56.8	116.2	167.0	162.9	154.3	149.0	141.6	137.6	135.0
75°	62.7	50.1	43.4	86.2	135.6	133.0	124.9	119.5	113.5	108.2	108.9
77.5°	46.1	46.7	34.8	63.4	107.6	103.6	98.9	92.2	89.5	84.2	84.2
80°	34.8	36.8	26.1	43.4	77.5	77.5	73.5	68.8	64.1	61.5	61.5
82.5°	23.4	23.4	19.3	27.4	52.8	50.8	48.1	46.7	44.1	42.7	42.7
85°	10.7	13.3	12.1	16.7	28.7	30.1	30.1	28.7	28.1	26.7	27.4
87.5°	3.4	6.0	7.4	9.4	14.7	15.3	16.0	16.0	16.0	16.7	16.7
90°	5.2	9.3	13.4	14.4	22.7	33.7	39.1	34.8	26.1	19.6	19.6
92.5°	20.6	55.7	90.7	99.5	139.9	193.8	220.7	193.4	138.9	98.0	94.1
95°	49.5	113.6	177.9	193.9	344.3	544.8	645.1	575.7	436.8	332.7	320.8
97.5°	85.6	142.1	198.8	212.9	463.7	798.1	965.3	921.4	833.7	767.8	745.4
100°	113.4	164.8	216.1	229.0	507.3	878.3	1063.8	1067.0	1073.5	1078.3	1051.5
102.5°	137.1	185.1	233.0	244.9	527.2	903.6	1091.7	1147.7	1259.5	1343.4	1320.5
105°	177.4	218.0	258.6	268.7	542.0	906.5	1088.6	1214.0	1464.7	1652.8	1640.4
107.5°	218.6	256.5	294.3	303.8	544.8	866.1	1026.8	1201.7	1551.4	1813.6	1816.6
110°	246.5	280.7	314.7	323.3	540.6	830.4	975.2	1170.7	1561.7	1855.0	1867.8

TEST NUMBER: P935482

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	273.8	306.4	338.8	347.0	540.7	799.1	928.3	1128.4	1528.6	1828.7	1848.4
115°	315.0	345.1	375.2	382.7	545.8	763.2	872.0	1064.7	1450.3	1739.4	1766.7
117.5°	355.9	383.2	410.5	417.2	556.0	740.9	833.4	1007.3	1355.2	1616.1	1646.4
120°	379.6	405.3	431.0	437.3	564.2	733.4	817.9	976.9	1294.7	1533.1	1562.6
122.5°	402.8	428.7	454.6	461.0	576.1	729.4	806.1	949.2	1235.4	1450.1	1479.2
125°	438.3	461.9	485.6	491.4	592.0	726.1	793.1	914.7	1157.8	1340.2	1367.0
127.5°	467.2	491.0	514.8	520.8	608.0	724.2	782.3	886.6	1095.5	1252.1	1274.7
130°	482.7	508.4	534.1	540.4	619.7	725.4	778.2	871.1	1057.0	1196.4	1217.2
132.5°	498.7	524.4	550.1	556.5	629.2	726.1	774.6	857.8	1024.2	1149.0	1167.6
135°	522.4	545.8	569.1	575.0	639.4	725.4	768.4	838.1	977.5	1082.0	1098.1
137.5°	546.6	569.7	592.9	598.7	654.9	729.9	767.3	826.2	944.0	1032.4	1045.5
140°	566.7	588.0	609.4	614.7	664.4	730.7	763.7	814.6	916.4	992.7	1005.1
142.5°	582.2	601.9	621.6	626.6	672.3	733.3	763.7	808.5	897.8	964.8	975.4
145°	606.0	623.1	640.3	644.6	682.6	733.3	758.6	795.1	868.2	923.1	931.2
147.5°	629.7	646.4	663.1	667.3	697.7	738.2	758.6	787.3	844.9	888.0	894.7
150°	645.1	660.2	675.4	679.2	705.7	740.9	758.6	782.9	831.5	867.9	873.3
152.5°	661.1	672.6	684.1	686.9	710.8	742.6	758.6	779.3	820.8	851.9	856.0
155°	684.8	693.3	701.8	703.9	722.1	746.4	758.6	775.1	808.1	832.9	835.5
157.5°	702.4	710.6	718.8	720.9	733.5	750.2	758.6	771.4	797.1	816.3	818.2
160°	714.2	720.6	727.1	728.7	738.6	751.9	758.6	769.5	791.5	808.1	809.2
162.5°	726.1	730.9	735.7	736.9	744.1	753.8	758.6	767.8	786.4	800.4	801.4
165°	738.9	743.3	747.7	748.8	752.1	756.4	758.6	765.2	778.5	788.4	789.5
167.5°	750.9	752.9	755.0	755.5	758.3	761.9	763.7	768.1	776.8	783.4	783.9
170°	758.6	760.6	762.7	763.2	763.4	763.6	763.7	768.1	776.8	783.4	783.4
172.5°	762.7	763.1	763.6	763.7	763.7	763.7	763.7	767.1	774.0	779.2	778.8
175°	768.4	768.4	768.4	768.4	766.8	764.7	763.7	765.9	770.2	773.5	773.5
177.5°	768.4	768.4	768.4	768.4	767.2	765.5	764.7	766.4	769.9	772.5	772.0
180°	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4

TEST NUMBER: P935482

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1
2.5°	724.1	722.1	724.1	722.7	723.4	721.4	715.4	713.4	715.4	717.4	717.4
5°	732.8	731.5	732.8	732.8	732.1	730.8	724.1	722.7	724.1	724.8	723.4
7.5°	735.4	733.5	735.4	734.1	734.1	732.8	726.1	724.8	725.4	727.4	725.4
10°	735.4	733.5	735.4	734.7	734.1	732.8	726.1	723.4	723.4	725.4	723.4
12.5°	732.1	730.8	732.1	730.8	730.8	729.5	722.7	720.1	720.7	721.4	718.7
15°	726.8	724.8	726.8	725.4	726.1	724.1	716.7	714.0	714.0	715.4	710.7
17.5°	718.7	716.0	718.7	718.1	717.4	716.0	709.4	706.8	706.1	706.8	703.4
20°	709.4	707.4	709.4	708.8	708.8	706.1	699.4	696.0	696.0	696.0	692.7
22.5°	694.7	692.7	694.7	696.0	696.0	695.3	689.3	684.7	683.4	683.4	679.4
25°	678.0	676.0	678.0	678.0	677.3	678.0	676.0	673.3	671.3	669.3	665.3
27.5°	661.9	660.6	661.9	660.6	661.9	659.9	659.3	658.7	656.0	654.0	648.6
30°	645.9	644.6	645.9	644.6	643.2	641.9	638.5	637.2	639.9	638.5	629.9
32.5°	625.9	624.6	625.9	625.9	624.6	624.6	619.2	617.2	617.9	621.9	613.8
35°	605.2	603.2	605.2	604.5	605.2	603.2	599.8	599.2	596.5	601.2	595.2
37.5°	581.2	579.2	581.2	581.2	581.2	582.5	579.8	577.8	573.8	579.8	575.1
40°	556.5	553.8	556.5	555.8	556.5	557.8	556.5	555.1	551.1	555.8	551.8
42.5°	528.4	527.7	528.4	529.1	529.1	531.7	533.8	531.1	529.7	526.4	529.1
45°	498.3	497.0	498.3	499.6	500.3	501.7	507.7	507.7	505.7	500.3	504.3
47.5°	466.2	462.9	466.2	470.2	470.2	472.3	478.3	483.0	479.6	472.9	474.9
50°	432.2	432.9	432.2	434.9	434.9	442.2	446.9	451.6	454.9	446.9	437.5
52.5°	398.8	398.1	398.8	400.8	403.5	406.8	414.8	419.5	424.8	420.1	405.5
55°	365.3	366.7	365.3	366.0	367.4	369.4	381.4	386.0	396.1	390.1	374.7
57.5°	332.0	330.0	332.0	333.4	334.0	336.0	346.0	354.7	360.8	361.3	342.6
60°	293.2	290.5	293.2	299.3	300.6	301.9	311.2	319.3	324.6	326.6	307.3
62.5°	259.2	254.5	259.2	263.1	265.8	269.2	275.9	287.9	292.5	293.2	265.8
65°	223.1	221.1	223.1	231.1	231.8	235.8	243.1	251.8	261.8	260.6	221.1
67.5°	190.3	190.3	190.3	195.7	199.7	201.7	211.1	215.1	227.8	229.1	184.4
70°	160.4	159.7	160.4	164.3	167.0	171.7	180.4	185.1	195.0	198.4	149.6
72.5°	131.6	130.9	131.6	135.0	137.6	141.6	149.0	154.3	162.9	167.0	116.2
75°	106.2	104.9	106.2	108.9	108.2	113.5	119.5	124.9	133.0	135.6	86.2
77.5°	81.5	81.5	81.5	84.2	84.2	89.5	92.2	98.9	103.6	107.6	63.4
80°	60.8	60.2	60.8	61.5	61.5	64.1	68.8	73.5	77.5	77.5	43.4
82.5°	42.7	41.4	42.7	42.7	42.7	44.1	46.7	48.1	50.8	52.8	27.4
85°	26.7	26.7	26.7	27.4	26.7	28.1	28.7	30.1	30.1	28.7	16.7
87.5°	17.3	16.7	17.3	16.7	16.7	16.0	16.0	16.0	15.3	14.7	9.4
90°	19.6	19.6	19.6	19.6	19.6	26.1	34.8	39.1	33.7	22.7	14.4
92.5°	78.5	62.9	78.5	94.1	98.0	138.9	193.4	220.7	193.8	139.9	99.5
95°	273.6	226.4	273.6	320.8	332.7	436.8	575.7	645.1	544.8	344.3	193.9
97.5°	655.6	565.7	655.6	745.4	767.8	833.7	921.4	965.3	798.1	463.7	212.9
100°	944.5	837.4	944.5	1051.5	1078.3	1073.5	1067.0	1063.8	878.3	507.3	229.0
102.5°	1228.8	1137.1	1228.8	1320.5	1343.4	1259.5	1147.7	1091.7	903.6	527.2	244.9
105°	1591.2	1541.9	1591.2	1640.4	1652.8	1464.7	1214.0	1088.6	906.5	542.0	268.7
107.5°	1828.6	1840.5	1828.6	1816.6	1813.6	1551.4	1201.7	1026.8	866.1	544.8	303.8
110°	1919.1	1970.4	1919.1	1867.8	1855.0	1561.7	1170.7	975.2	830.4	540.6	323.3

TEST NUMBER: P935482

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1927.2	2006.0	1927.2	1848.4	1828.7	1528.6	1128.4	928.3	799.1	540.7	347.0
115°	1876.1	1985.4	1876.1	1766.7	1739.4	1450.3	1064.7	872.0	763.2	545.8	382.7
117.5°	1767.7	1888.9	1767.7	1646.4	1616.1	1355.2	1007.3	833.4	740.9	556.0	417.2
120°	1680.4	1798.2	1680.4	1562.6	1533.1	1294.7	976.9	817.9	733.4	564.2	437.3
122.5°	1595.3	1711.5	1595.3	1479.2	1450.1	1235.4	949.2	806.1	729.4	576.1	461.0
125°	1474.0	1581.1	1474.0	1367.0	1340.2	1157.8	914.7	793.1	726.1	592.0	491.4
127.5°	1364.9	1455.3	1364.9	1274.7	1252.1	1095.5	886.6	782.3	724.2	608.0	520.8
130°	1300.7	1384.1	1300.7	1217.2	1196.4	1057.0	871.1	778.2	725.4	619.7	540.4
132.5°	1242.3	1317.0	1242.3	1167.6	1149.0	1024.2	857.8	774.6	726.1	629.2	556.5
135°	1162.4	1226.8	1162.4	1098.1	1082.0	977.5	838.1	768.4	725.4	639.4	575.0
137.5°	1098.3	1151.0	1098.3	1045.5	1032.4	944.0	826.2	767.3	729.9	654.9	598.7
140°	1054.3	1103.6	1054.3	1005.1	992.7	916.4	814.6	763.7	730.7	664.4	614.7
142.5°	1017.8	1060.2	1017.8	975.4	964.8	897.8	808.5	763.7	733.3	672.3	626.6
145°	963.2	995.3	963.2	931.2	923.1	868.2	795.1	758.6	733.3	682.6	644.6
147.5°	921.2	947.8	921.2	894.7	888.0	844.9	787.3	758.6	738.2	697.7	667.3
150°	894.9	916.4	894.9	873.3	867.9	831.5	782.9	758.6	740.9	705.7	679.2
152.5°	872.2	888.5	872.2	856.0	851.9	820.8	779.3	758.6	742.6	710.8	686.9
155°	846.3	857.1	846.3	835.5	832.9	808.1	775.1	758.6	746.4	722.1	703.9
157.5°	825.8	833.4	825.8	818.2	816.3	797.1	771.4	758.6	750.2	733.5	720.9
160°	813.5	817.9	813.5	809.2	808.1	791.5	769.5	758.6	751.9	738.6	728.7
162.5°	805.6	809.6	805.6	801.4	800.4	786.4	767.8	758.6	753.8	744.1	736.9
165°	793.9	798.3	793.9	789.5	788.4	778.5	765.2	758.6	756.4	752.1	748.8
167.5°	785.6	787.4	785.6	783.9	783.4	776.8	768.1	763.7	761.9	758.3	755.5
170°	783.4	783.4	783.4	783.4	783.4	776.8	768.1	763.7	763.6	763.4	763.2
172.5°	777.2	775.6	777.2	778.8	779.2	774.0	767.1	763.7	763.7	763.7	763.7
175°	773.5	773.5	773.5	773.5	773.5	770.2	765.9	763.7	764.7	766.8	768.4
177.5°	770.2	768.4	770.2	772.0	772.5	769.9	766.4	764.7	765.5	767.2	768.4
180°	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4

TEST NUMBER: P935482

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1
2.5°	716.0	712.0	712.0	705.4	702.7	700.7	697.4	687.3	684.7	682.0	686.0
5°	722.1	714.7	709.4	697.4	687.3	683.4	670.6	646.6	630.6	618.5	611.8
7.5°	723.4	714.0	704.1	685.3	661.2	650.6	611.8	567.8	555.8	545.1	538.3
10°	722.1	711.3	697.4	669.3	612.5	593.8	555.1	526.4	519.0	517.0	519.0
12.5°	717.4	707.4	688.0	641.2	561.7	549.1	526.4	509.7	508.4	511.6	529.7
15°	709.4	700.0	677.3	603.9	533.8	524.4	508.4	502.3	509.7	533.1	587.1
17.5°	701.4	690.7	662.6	567.1	512.3	505.7	494.3	506.4	547.7	579.2	597.2
20°	690.7	678.0	645.9	540.4	497.0	490.9	485.6	539.7	571.1	582.5	592.5
22.5°	678.0	664.6	623.2	521.7	481.0	476.3	479.6	558.5	571.1	579.2	587.8
25°	661.2	649.9	596.5	507.0	468.2	462.9	475.6	556.5	563.7	565.7	583.2
27.5°	645.9	631.3	568.4	493.6	452.9	450.9	479.0	547.7	553.1	555.1	573.8
30°	627.2	605.2	537.0	479.6	436.8	436.1	479.6	537.0	535.7	541.0	559.8
32.5°	607.9	566.4	501.7	462.2	421.5	420.8	474.9	521.0	519.7	527.0	541.0
35°	589.8	536.3	453.6	442.2	402.1	402.8	463.5	502.3	503.0	509.7	518.3
37.5°	571.1	510.4	400.8	420.1	383.5	383.5	448.2	485.0	483.7	485.6	497.6
40°	549.1	469.6	354.0	391.4	366.0	364.0	429.5	466.2	461.5	460.9	477.6
42.5°	525.7	424.8	319.3	353.4	346.0	343.3	406.8	443.5	434.9	436.8	458.3
45°	500.3	412.8	292.5	298.6	325.3	323.3	382.1	417.5	411.4	416.8	438.8
47.5°	474.9	388.7	283.9	247.8	303.3	302.6	354.7	392.1	388.7	394.1	417.5
50°	440.2	362.0	283.3	212.4	278.6	281.2	322.0	367.4	367.4	372.1	396.8
52.5°	395.4	329.3	257.2	192.3	249.8	257.9	293.2	346.0	347.3	352.0	374.1
55°	354.7	295.2	238.4	177.0	215.7	233.2	265.1	324.0	326.6	331.3	351.4
57.5°	317.3	245.8	234.5	159.0	184.4	201.1	240.4	302.6	303.9	308.0	327.3
60°	277.2	177.7	215.1	139.6	157.0	169.6	217.7	277.2	281.9	284.6	301.3
62.5°	231.8	128.9	195.0	126.3	143.6	146.3	199.1	253.2	259.2	261.2	271.2
65°	165.0	108.2	165.6	114.9	129.6	130.3	179.0	228.5	233.8	237.1	244.5
67.5°	111.6	88.1	126.3	104.2	118.9	119.5	159.7	199.7	207.1	209.8	214.4
70°	77.5	58.8	93.5	92.8	106.9	108.2	138.9	173.7	180.4	182.4	185.1
72.5°	56.8	47.4	77.5	83.5	94.2	95.5	117.5	144.3	151.0	153.0	154.3
75°	43.4	50.1	62.7	72.8	80.2	80.8	96.2	117.5	122.2	123.6	124.2
77.5°	34.8	46.7	46.1	58.8	65.4	64.1	75.5	90.8	94.8	94.8	94.8
80°	26.1	36.8	34.8	42.1	48.1	46.7	54.1	64.8	66.1	67.4	66.8
82.5°	19.3	23.4	23.4	26.7	32.1	30.8	36.1	42.1	42.1	42.1	43.4
85°	12.1	13.3	10.7	14.0	18.0	17.3	20.0	22.7	23.4	23.4	22.0
87.5°	7.4	6.0	3.4	5.4	8.0	8.0	9.4	10.1	9.4	9.4	9.4
90°	13.4	9.3	5.2	9.3	13.4	14.4	22.7	33.7	39.1	34.8	26.1
92.5°	90.7	55.7	20.6	55.7	90.7	99.5	139.9	193.8	220.7	193.4	138.9
95°	177.9	113.6	49.5	113.6	177.9	193.9	344.3	544.8	645.1	575.7	436.8
97.5°	198.8	142.1	85.6	142.1	198.8	212.9	463.7	798.1	965.3	921.4	833.7
100°	216.1	164.8	113.4	164.8	216.1	229.0	507.3	878.3	1063.8	1067.0	1073.5
102.5°	233.0	185.1	137.1	185.1	233.0	244.9	527.2	903.6	1091.7	1147.7	1259.5
105°	258.6	218.0	177.4	218.0	258.6	268.7	542.0	906.5	1088.6	1214.0	1464.7
107.5°	294.3	256.5	218.6	256.5	294.3	303.8	544.8	866.1	1026.8	1201.7	1551.4
110°	314.7	280.7	246.5	280.7	314.7	323.3	540.6	830.4	975.2	1170.7	1561.7

TEST NUMBER: P935482

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	338.8	306.4	273.8	306.4	338.8	347.0	540.7	799.1	928.3	1128.4	1528.6
115°	375.2	345.1	315.0	345.1	375.2	382.7	545.8	763.2	872.0	1064.7	1450.3
117.5°	410.5	383.2	355.9	383.2	410.5	417.2	556.0	740.9	833.4	1007.3	1355.2
120°	431.0	405.3	379.6	405.3	431.0	437.3	564.2	733.4	817.9	976.9	1294.7
122.5°	454.6	428.7	402.8	428.7	454.6	461.0	576.1	729.4	806.1	949.2	1235.4
125°	485.6	461.9	438.3	461.9	485.6	491.4	592.0	726.1	793.1	914.7	1157.8
127.5°	514.8	491.0	467.2	491.0	514.8	520.8	608.0	724.2	782.3	886.6	1095.5
130°	534.1	508.4	482.7	508.4	534.1	540.4	619.7	725.4	778.2	871.1	1057.0
132.5°	550.1	524.4	498.7	524.4	550.1	556.5	629.2	726.1	774.6	857.8	1024.2
135°	569.1	545.8	522.4	545.8	569.1	575.0	639.4	725.4	768.4	838.1	977.5
137.5°	592.9	569.7	546.6	569.7	592.9	598.7	654.9	729.9	767.3	826.2	944.0
140°	609.4	588.0	566.7	588.0	609.4	614.7	664.4	730.7	763.7	814.6	916.4
142.5°	621.6	601.9	582.2	601.9	621.6	626.6	672.3	733.3	763.7	808.5	897.8
145°	640.3	623.1	606.0	623.1	640.3	644.6	682.6	733.3	758.6	795.1	868.2
147.5°	663.1	646.4	629.7	646.4	663.1	667.3	697.7	738.2	758.6	787.3	844.9
150°	675.4	660.2	645.1	660.2	675.4	679.2	705.7	740.9	758.6	782.9	831.5
152.5°	684.1	672.6	661.1	672.6	684.1	686.9	710.8	742.6	758.6	779.3	820.8
155°	701.8	693.3	684.8	693.3	701.8	703.9	722.1	746.4	758.6	775.1	808.1
157.5°	718.8	710.6	702.4	710.6	718.8	720.9	733.5	750.2	758.6	771.4	797.1
160°	727.1	720.6	714.2	720.6	727.1	728.7	738.6	751.9	758.6	769.5	791.5
162.5°	735.7	730.9	726.1	730.9	735.7	736.9	744.1	753.8	758.6	767.8	786.4
165°	747.7	743.3	738.9	743.3	747.7	748.8	752.1	756.4	758.6	765.2	778.5
167.5°	755.0	752.9	750.9	752.9	755.0	755.5	758.3	761.9	763.7	768.1	776.8
170°	762.7	760.6	758.6	760.6	762.7	763.2	763.4	763.6	763.7	768.1	776.8
172.5°	763.6	763.1	762.7	763.1	763.6	763.7	763.7	763.7	763.7	767.1	774.0
175°	768.4	768.4	768.4	768.4	768.4	768.4	766.8	764.7	763.7	765.9	770.2
177.5°	768.4	768.4	768.4	768.4	768.4	768.4	767.2	765.5	764.7	766.4	769.9
180°	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4

TEST NUMBER: P935482

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1	706.1
2.5°	681.4	679.4	682.0	674.7	682.0	679.4	681.4	686.0	682.0	684.7	687.3
5°	597.8	594.5	583.9	575.1	583.9	594.5	597.8	611.8	618.5	630.6	646.6
7.5°	534.4	531.7	529.1	523.7	529.1	531.7	534.4	538.3	545.1	555.8	567.8
10°	520.3	521.0	525.0	524.4	525.0	521.0	520.3	519.0	517.0	519.0	526.4
12.5°	556.5	562.4	584.5	583.2	584.5	562.4	556.5	529.7	511.6	508.4	509.7
15°	597.8	599.8	604.5	605.2	604.5	599.8	597.8	587.1	533.1	509.7	502.3
17.5°	601.9	602.5	605.9	605.9	605.9	602.5	601.9	597.2	579.2	547.7	506.4
20°	598.5	599.8	606.6	607.9	606.6	599.8	598.5	592.5	582.5	571.1	539.7
22.5°	597.2	599.8	605.2	604.5	605.2	599.8	597.2	587.8	579.2	571.1	558.5
25°	590.5	590.5	591.1	591.8	591.1	590.5	590.5	583.2	565.7	563.7	556.5
27.5°	576.5	577.8	581.8	581.2	581.8	577.8	576.5	573.8	555.1	553.1	547.7
30°	563.7	562.4	559.1	556.5	559.1	562.4	563.7	559.8	541.0	535.7	537.0
32.5°	542.4	539.0	535.7	533.8	535.7	539.0	542.4	541.0	527.0	519.7	521.0
35°	517.0	517.7	517.0	515.0	517.0	517.7	517.0	518.3	509.7	503.0	502.3
37.5°	499.0	500.3	499.6	497.0	499.6	500.3	499.0	497.6	485.6	483.7	485.0
40°	480.3	481.0	480.3	478.3	480.3	481.0	480.3	477.6	460.9	461.5	466.2
42.5°	462.2	461.5	459.6	458.3	459.6	461.5	462.2	458.3	436.8	434.9	443.5
45°	441.5	442.2	438.1	436.1	438.1	442.2	441.5	438.8	416.8	411.4	417.5
47.5°	420.8	420.8	417.5	415.4	417.5	420.8	420.8	417.5	394.1	388.7	392.1
50°	398.8	398.1	393.4	392.7	393.4	398.1	398.8	396.8	372.1	367.4	367.4
52.5°	373.4	373.4	374.1	375.4	374.1	373.4	373.4	374.1	352.0	347.3	346.0
55°	351.4	352.0	356.7	358.1	356.7	352.0	351.4	351.4	331.3	326.6	324.0
57.5°	328.7	328.7	332.0	332.0	332.0	328.7	328.7	327.3	308.0	303.9	302.6
60°	302.6	303.9	306.6	306.0	306.6	303.9	302.6	301.3	284.6	281.9	277.2
62.5°	275.2	276.6	277.2	275.9	277.2	276.6	275.2	271.2	261.2	259.2	253.2
65°	246.5	247.8	248.5	247.1	248.5	247.8	246.5	244.5	237.1	233.8	228.5
67.5°	217.1	216.4	215.7	218.4	215.7	216.4	217.1	214.4	209.8	207.1	199.7
70°	187.0	187.0	186.4	187.7	186.4	187.0	187.0	185.1	182.4	180.4	173.7
72.5°	155.0	154.3	157.0	155.0	157.0	154.3	155.0	154.3	153.0	151.0	144.3
75°	123.6	124.9	123.6	125.6	123.6	124.9	123.6	124.2	123.6	122.2	117.5
77.5°	94.2	95.5	94.2	94.2	94.2	95.5	94.2	94.8	94.8	94.8	90.8
80°	66.8	66.1	66.1	65.4	66.1	66.1	66.8	66.8	67.4	66.1	64.8
82.5°	42.7	42.1	42.1	43.4	42.1	42.1	42.7	43.4	42.1	42.1	42.1
85°	23.4	24.0	22.7	22.7	22.7	24.0	23.4	22.0	23.4	23.4	22.7
87.5°	8.7	8.0	8.0	8.0	8.0	8.0	8.7	9.4	9.4	9.4	10.1
90°	19.6	19.6	19.6	19.6	19.6	19.6	19.6	26.1	34.8	39.1	33.7
92.5°	98.0	94.1	78.5	62.9	78.5	94.1	98.0	138.9	193.4	220.7	193.8
95°	332.7	320.8	273.6	226.4	273.6	320.8	332.7	436.8	575.7	645.1	544.8
97.5°	767.8	745.4	655.6	565.7	655.6	745.4	767.8	833.7	921.4	965.3	798.1
100°	1078.3	1051.5	944.5	837.4	944.5	1051.5	1078.3	1073.5	1067.0	1063.8	878.3
102.5°	1343.4	1320.5	1228.8	1137.1	1228.8	1320.5	1343.4	1259.5	1147.7	1091.7	903.6
105°	1652.8	1640.4	1591.2	1541.9	1591.2	1640.4	1652.8	1464.7	1214.0	1088.6	906.5
107.5°	1813.6	1816.6	1828.6	1840.5	1828.6	1816.6	1813.6	1551.4	1201.7	1026.8	866.1
110°	1855.0	1867.8	1919.1	1970.4	1919.1	1867.8	1855.0	1561.7	1170.7	975.2	830.4

TEST NUMBER: P935482

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1828.7	1848.4	1927.2	2006.0	1927.2	1848.4	1828.7	1528.6	1128.4	928.3	799.1
115°	1739.4	1766.7	1876.1	1985.4	1876.1	1766.7	1739.4	1450.3	1064.7	872.0	763.2
117.5°	1616.1	1646.4	1767.7	1888.9	1767.7	1646.4	1616.1	1355.2	1007.3	833.4	740.9
120°	1533.1	1562.6	1680.4	1798.2	1680.4	1562.6	1533.1	1294.7	976.9	817.9	733.4
122.5°	1450.1	1479.2	1595.3	1711.5	1595.3	1479.2	1450.1	1235.4	949.2	806.1	729.4
125°	1340.2	1367.0	1474.0	1581.1	1474.0	1367.0	1340.2	1157.8	914.7	793.1	726.1
127.5°	1252.1	1274.7	1364.9	1455.3	1364.9	1274.7	1252.1	1095.5	886.6	782.3	724.2
130°	1196.4	1217.2	1300.7	1384.1	1300.7	1217.2	1196.4	1057.0	871.1	778.2	725.4
132.5°	1149.0	1167.6	1242.3	1317.0	1242.3	1167.6	1149.0	1024.2	857.8	774.6	726.1
135°	1082.0	1098.1	1162.4	1226.8	1162.4	1098.1	1082.0	977.5	838.1	768.4	725.4
137.5°	1032.4	1045.5	1098.3	1151.0	1098.3	1045.5	1032.4	944.0	826.2	767.3	729.9
140°	992.7	1005.1	1054.3	1103.6	1054.3	1005.1	992.7	916.4	814.6	763.7	730.7
142.5°	964.8	975.4	1017.8	1060.2	1017.8	975.4	964.8	897.8	808.5	763.7	733.3
145°	923.1	931.2	963.2	995.3	963.2	931.2	923.1	868.2	795.1	758.6	733.3
147.5°	888.0	894.7	921.2	947.8	921.2	894.7	888.0	844.9	787.3	758.6	738.2
150°	867.9	873.3	894.9	916.4	894.9	873.3	867.9	831.5	782.9	758.6	740.9
152.5°	851.9	856.0	872.2	888.5	872.2	856.0	851.9	820.8	779.3	758.6	742.6
155°	832.9	835.5	846.3	857.1	846.3	835.5	832.9	808.1	775.1	758.6	746.4
157.5°	816.3	818.2	825.8	833.4	825.8	818.2	816.3	797.1	771.4	758.6	750.2
160°	808.1	809.2	813.5	817.9	813.5	809.2	808.1	791.5	769.5	758.6	751.9
162.5°	800.4	801.4	805.6	809.6	805.6	801.4	800.4	786.4	767.8	758.6	753.8
165°	788.4	789.5	793.9	798.3	793.9	789.5	788.4	778.5	765.2	758.6	756.4
167.5°	783.4	783.9	785.6	787.4	785.6	783.9	783.4	776.8	768.1	763.7	761.9
170°	783.4	783.4	783.4	783.4	783.4	783.4	783.4	776.8	768.1	763.7	763.6
172.5°	779.2	778.8	777.2	775.6	777.2	778.8	779.2	774.0	767.1	763.7	763.7
175°	773.5	773.5	773.5	773.5	773.5	773.5	773.5	770.2	765.9	763.7	764.7
177.5°	772.5	772.0	770.2	768.4	770.2	772.0	772.5	769.9	766.4	764.7	765.5
180°	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4	768.4

TEST NUMBER: P935482

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	706.1	706.1	706.1	706.1	706.1
2.5°	697.4	700.7	702.7	705.4	712.0
5°	670.6	683.4	687.3	697.4	709.4
7.5°	611.8	650.6	661.2	685.3	704.1
10°	555.1	593.8	612.5	669.3	697.4
12.5°	526.4	549.1	561.7	641.2	688.0
15°	508.4	524.4	533.8	603.9	677.3
17.5°	494.3	505.7	512.3	567.1	662.6
20°	485.6	490.9	497.0	540.4	645.9
22.5°	479.6	476.3	481.0	521.7	623.2
25°	475.6	462.9	468.2	507.0	596.5
27.5°	479.0	450.9	452.9	493.6	568.4
30°	479.6	436.1	436.8	479.6	537.0
32.5°	474.9	420.8	421.5	462.2	501.7
35°	463.5	402.8	402.1	442.2	453.6
37.5°	448.2	383.5	383.5	420.1	400.8
40°	429.5	364.0	366.0	391.4	354.0
42.5°	406.8	343.3	346.0	353.4	319.3
45°	382.1	323.3	325.3	298.6	292.5
47.5°	354.7	302.6	303.3	247.8	283.9
50°	322.0	281.2	278.6	212.4	283.3
52.5°	293.2	257.9	249.8	192.3	257.2
55°	265.1	233.2	215.7	177.0	238.4
57.5°	240.4	201.1	184.4	159.0	234.5
60°	217.7	169.6	157.0	139.6	215.1
62.5°	199.1	146.3	143.6	126.3	195.0
65°	179.0	130.3	129.6	114.9	165.6
67.5°	159.7	119.5	118.9	104.2	126.3
70°	138.9	108.2	106.9	92.8	93.5
72.5°	117.5	95.5	94.2	83.5	77.5
75°	96.2	80.8	80.2	72.8	62.7
77.5°	75.5	64.1	65.4	58.8	46.1
80°	54.1	46.7	48.1	42.1	34.8
82.5°	36.1	30.8	32.1	26.7	23.4
85°	20.0	17.3	18.0	14.0	10.7
87.5°	9.4	8.0	8.0	5.4	3.4
90°	22.7	14.4	13.4	9.3	5.2
92.5°	139.9	99.5	90.7	55.7	20.6
95°	344.3	193.9	177.9	113.6	49.5
97.5°	463.7	212.9	198.8	142.1	85.6
100°	507.3	229.0	216.1	164.8	113.4
102.5°	527.2	244.9	233.0	185.1	137.1
105°	542.0	268.7	258.6	218.0	177.4
107.5°	544.8	303.8	294.3	256.5	218.6
110°	540.6	323.3	314.7	280.7	246.5

TEST NUMBER: P935482

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-2700K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	540.7	347.0	338.8	306.4	273.8
115°	545.8	382.7	375.2	345.1	315.0
117.5°	556.0	417.2	410.5	383.2	355.9
120°	564.2	437.3	431.0	405.3	379.6
122.5°	576.1	461.0	454.6	428.7	402.8
125°	592.0	491.4	485.6	461.9	438.3
127.5°	608.0	520.8	514.8	491.0	467.2
130°	619.7	540.4	534.1	508.4	482.7
132.5°	629.2	556.5	550.1	524.4	498.7
135°	639.4	575.0	569.1	545.8	522.4
137.5°	654.9	598.7	592.9	569.7	546.6
140°	664.4	614.7	609.4	588.0	566.7
142.5°	672.3	626.6	621.6	601.9	582.2
145°	682.6	644.6	640.3	623.1	606.0
147.5°	697.7	667.3	663.1	646.4	629.7
150°	705.7	679.2	675.4	660.2	645.1
152.5°	710.8	686.9	684.1	672.6	661.1
155°	722.1	703.9	701.8	693.3	684.8
157.5°	733.5	720.9	718.8	710.6	702.4
160°	738.6	728.7	727.1	720.6	714.2
162.5°	744.1	736.9	735.7	730.9	726.1
165°	752.1	748.8	747.7	743.3	738.9
167.5°	758.3	755.5	755.0	752.9	750.9
170°	763.4	763.2	762.7	760.6	758.6
172.5°	763.7	763.7	763.6	763.1	762.7
175°	766.8	768.4	768.4	768.4	768.4
177.5°	767.2	768.4	768.4	768.4	768.4
180°	768.4	768.4	768.4	768.4	768.4

TEST NUMBER: P935482

CATALOG NUMBER: SQ4-FA-125U-050D-B2750-1D-UNV-W2A-W-4-2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.67	9.36	9.80	10.48	12.05	11.47	12.15	12.60	13.28	14.84
	3H	9.13	9.75	10.27	10.88	12.46	12.79	13.40	13.93	14.54	16.12
	4H	9.32	9.90	10.47	11.03	12.62	13.22	13.80	14.37	14.93	16.52
	6H	9.43	9.96	10.58	11.10	12.70	13.49	14.02	14.64	15.16	16.76
	8H	9.42	9.93	10.58	11.08	12.67	13.55	14.06	14.71	15.21	16.80
	12H	9.39	9.87	10.55	11.02	12.63	13.58	14.06	14.74	15.21	16.82
4H	2H	9.67	10.26	10.83	11.39	12.98	11.86	12.44	13.01	13.57	15.16
	3H	10.68	11.17	11.84	12.33	13.93	13.34	13.82	14.50	14.98	16.58
	4H	10.95	11.40	12.12	12.54	14.16	13.85	14.30	15.01	15.44	17.06
	6H	11.07	11.45	12.24	12.62	14.23	14.20	14.58	15.37	15.75	17.36
	8H	11.07	11.42	12.24	12.59	14.21	14.29	14.65	15.46	15.81	17.44
	12H	11.03	11.35	12.21	12.52	14.15	14.34	14.66	15.52	15.83	17.46
8H	4H	11.38	11.74	12.55	12.90	14.53	13.96	14.32	15.13	15.48	17.10
	6H	11.64	11.93	12.83	13.14	14.76	14.38	14.68	15.57	15.88	17.50
	8H	11.68	11.94	12.87	13.12	14.76	14.53	14.78	15.72	15.96	17.61
	12H	11.66	11.88	12.85	13.06	14.74	14.61	14.84	15.81	16.02	17.69
12H	4H	11.38	11.71	12.57	12.88	14.51	13.92	14.24	15.10	15.41	17.04
	6H	11.70	11.95	12.89	13.14	14.78	14.38	14.63	15.57	15.82	17.46
	8H	11.76	11.98	12.95	13.16	14.83	14.52	14.75	15.72	15.93	17.60

END OF REPORT