

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P935083

Luminaire Tested: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P935083
REPORT IS A COMBINATION OF REPORTS P933738 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5776.0 lumens
Efficiency: N/A
Efficacy: 140.2 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P935083

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-3000K

Luminous Intensity Polar Plot



TEST NUMBER: P935083

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33
2	85	78	72	67	76	70	65	61	56	53	50	43	40	38	30	29	28
3	78	69	62	56	70	62	56	51	49	45	42	38	35	32	27	25	24
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	15
7	55	43	36	30	49	39	33	28	32	27	23	25	21	18	18	15	14
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12
9	47	36	28	23	43	32	26	22	26	21	18	20	17	15	15	13	11
10	44	33	26	21	40	30	23	19	24	19	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6486	6486	6486	6486
5°	6526	6547	6526	5148
10°	6477	6449	6477	4611
15°	6398	6310	6398	5269
20°	6257	6144	6257	5280
25°	5976	5903	5976	5168
30°	5616	5702	5616	4923
35°	4999	5448	4999	4653
40°	4157	5150	4157	4448
45°	3708	4801	3708	4214
50°	3931	4384	3931	3978
55°	3686	3935	3686	3843
60°	3789	3342	3789	3519
65°	3418	2763	3418	3087
70°	2351	2203	2351	2590
75°	2036	1627	2036	1949
80°	1610	1078	1610	1172
85°	878	569	878	485

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 5694 cd/sqm

TEST NUMBER: P935083

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	1.1
10°-20°	179.1	3.1
20°-30°	276.9	4.8
30°-40°	330.6	5.7
40°-50°	332.5	5.8
50°-60°	289.3	5.0
60°-70°	205.1	3.6
70°-80°	108.5	1.9
80°-90°	29.4	0.5
90°-100°	297.9	5.2
100°-110°	783.1	13.6
110°-120°	812.0	14.1
120°-130°	651.3	11.3
130°-140°	511.1	8.8
140°-150°	392.3	6.8
150°-160°	282.5	4.9
160°-170°	172.8	3.0
170°-180°	58.4	1.0
0°-30°	519.1	9.0
0°-40°	849.7	14.7
0°-60°	1471.6	25.5
0°-90°	1814.6	31.4
90°-120°	1893.0	32.8
90°-150°	3447.6	59.7
90°-180°	3961.0	68.6
0°-180°	5776.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	699	699	699	699	699	
5°	702	724	702	569	702	67
15°	670	718	670	599	670	189
25°	590	669	590	586	590	271
35°	449	597	449	510	449	278
45°	290	492	290	432	290	232
55°	236	363	236	354	236	217
65°	164	219	164	245	164	157
75°	62	104	62	124	62	65
85°	11	26	11	22	11	14
90°	4	16	4	16	4	4
95°	39	180	39	180	39	44
105°	141	1226	141	1226	141	150
115°	250	1579	250	1579	250	247
125°	349	1257	349	1257	349	309
135°	416	976	416	976	416	321
145°	482	792	482	792	482	302
155°	545	682	545	682	545	250
165°	588	635	588	635	588	166
175°	611	615	611	615	611	58
180°	611	611	611	611	611	

TEST NUMBER: P935083

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	699.0	699.0	699.0	699.0	699.0	699.0	699.0	699.0	699.0	699.0	699.0
2.5°	704.9	704.9	708.8	710.2	710.2	708.2	706.3	708.2	714.2	716.1	715.4
5°	702.2	707.6	714.8	716.1	717.5	716.8	715.4	716.8	723.4	724.7	725.4
7.5°	697.0	706.9	716.1	718.1	720.1	718.1	717.5	718.8	725.4	726.7	726.7
10°	690.4	704.2	714.8	716.1	718.1	716.1	716.1	718.8	725.4	726.7	727.4
12.5°	681.1	700.3	710.2	711.5	714.2	713.5	712.9	715.4	722.1	723.4	723.4
15°	670.5	693.0	702.2	703.6	708.2	706.9	706.9	709.5	716.8	718.8	718.1
17.5°	656.0	683.8	694.3	696.3	699.7	699.0	699.7	702.2	708.8	710.2	710.9
20°	639.4	671.2	683.8	685.8	689.0	689.0	689.0	692.4	699.0	701.6	701.6
22.5°	616.9	658.0	671.2	672.6	676.5	676.5	677.8	682.4	688.3	689.0	689.0
25°	590.5	643.4	654.6	658.6	662.6	664.6	666.5	669.2	671.2	670.5	671.2
27.5°	562.7	624.9	639.4	642.1	647.4	649.4	652.0	652.6	653.3	655.3	654.0
30°	531.7	599.1	620.9	623.5	632.1	633.5	630.8	632.1	635.5	636.8	638.1
32.5°	496.6	560.7	601.8	607.7	615.7	611.7	611.0	613.0	618.3	618.3	619.6
35°	449.0	531.0	583.9	589.2	595.1	590.5	593.2	593.8	597.1	599.1	598.4
37.5°	396.8	505.2	565.4	569.3	574.0	568.0	572.0	574.0	576.6	575.3	575.3
40°	350.4	464.9	543.6	546.2	550.2	545.6	549.5	550.9	552.2	550.9	550.2
42.5°	316.1	420.5	520.4	523.8	521.1	524.4	525.7	528.4	526.3	523.8	523.8
45°	289.6	408.7	495.3	499.2	495.3	500.6	502.6	502.6	496.6	495.3	494.6
47.5°	281.0	384.8	470.1	470.1	468.2	474.8	478.1	473.5	467.6	465.5	465.5
50°	280.4	358.4	435.8	433.1	442.4	450.3	447.1	442.4	437.8	430.5	430.5
52.5°	254.6	326.0	391.4	401.4	415.9	420.5	415.3	410.7	402.7	399.4	396.8
55°	236.0	292.3	351.1	370.9	386.2	392.1	382.2	377.5	365.7	363.7	362.4
57.5°	232.1	243.3	314.1	339.2	357.7	357.1	351.1	342.5	332.6	330.6	330.0
60°	213.0	175.9	274.4	304.2	323.3	321.3	316.1	308.1	298.9	297.6	296.3
62.5°	193.1	127.6	229.4	263.2	290.3	289.6	285.1	273.1	266.5	263.2	260.5
65°	164.0	107.1	163.4	218.9	257.9	259.2	249.3	240.7	233.4	229.4	228.8
67.5°	125.0	87.3	110.4	182.5	226.8	225.5	213.0	208.9	199.7	197.7	193.7
70°	92.6	58.2	76.7	148.1	196.4	193.1	183.2	178.6	170.0	165.4	162.7
72.5°	76.7	46.9	56.2	115.1	165.4	161.3	152.7	147.5	140.2	136.3	133.6
75°	62.1	49.6	43.0	85.3	134.2	131.6	123.6	118.3	112.4	107.1	107.8
77.5°	45.7	46.2	34.4	62.8	106.5	102.5	97.9	91.3	88.6	83.3	83.3
80°	34.4	36.4	25.8	43.0	76.7	76.7	72.8	68.1	63.5	60.8	60.8
82.5°	23.2	23.2	19.1	27.1	52.3	50.3	47.6	46.2	43.7	42.3	42.3
85°	10.6	13.2	11.9	16.6	28.4	29.8	29.8	28.4	27.8	26.4	27.1
87.5°	3.4	5.9	7.3	9.3	14.6	15.2	15.9	15.9	15.9	16.6	16.6
90°	4.1	7.4	10.6	11.4	18.0	26.8	31.2	27.7	20.8	15.6	15.6
92.5°	16.4	44.3	72.2	79.2	111.3	154.1	175.5	153.8	110.4	77.9	74.8
95°	39.3	90.4	141.5	154.2	273.8	433.2	513.0	457.8	347.4	264.5	255.2
97.5°	68.0	113.1	158.2	169.4	368.9	634.8	767.7	732.8	663.0	610.6	592.8
100°	90.2	131.0	171.9	182.1	403.5	698.6	846.1	848.7	853.7	857.5	836.2
102.5°	109.1	147.2	185.3	194.8	419.3	718.6	868.3	912.7	1001.7	1068.3	1050.1
105°	141.1	173.3	205.6	213.7	431.1	720.9	865.8	965.5	1164.9	1314.4	1304.7
107.5°	173.9	204.0	234.1	241.6	433.2	688.7	816.5	955.6	1233.8	1442.4	1444.8
110°	196.0	223.2	250.3	257.1	429.9	660.3	775.5	931.0	1242.0	1475.2	1485.4



TEST NUMBER: P935083

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	217.8	243.6	269.5	276.0	430.1	635.5	738.2	897.4	1215.5	1454.3	1469.9
115°	250.5	274.4	298.3	304.3	434.0	607.1	693.6	846.9	1153.4	1383.4	1405.0
117.5°	283.0	304.7	326.4	331.8	442.1	589.2	662.8	801.1	1077.8	1285.3	1309.4
120°	301.8	322.2	342.6	347.8	448.6	583.2	650.5	776.9	1029.7	1219.3	1242.8
122.5°	320.4	341.0	361.6	366.7	458.1	580.1	641.0	754.8	982.5	1153.2	1176.3
125°	348.6	367.4	386.1	390.9	470.8	577.4	630.7	727.5	920.8	1065.9	1087.2
127.5°	371.5	390.5	409.5	414.2	483.5	575.9	622.2	705.2	871.2	995.8	1013.7
130°	383.8	404.3	424.7	429.8	492.8	576.9	618.9	692.9	840.7	951.5	968.1
132.5°	396.6	417.0	437.4	442.5	500.3	577.4	616.0	682.1	814.4	913.7	928.6
135°	415.5	434.0	452.7	457.3	508.6	576.9	611.1	666.5	777.3	860.4	873.2
137.5°	434.7	453.2	471.5	476.1	520.8	580.5	610.2	657.1	750.7	821.0	831.5
140°	450.7	467.7	484.6	488.9	528.4	581.0	607.4	647.8	728.8	789.5	799.3
142.5°	463.0	478.7	494.4	498.3	534.7	583.1	607.4	642.9	714.0	767.3	775.8
145°	481.9	495.6	509.2	512.6	542.9	583.2	603.3	632.4	690.5	734.1	740.5
147.5°	500.8	514.1	527.3	530.7	554.9	587.2	603.3	626.2	672.0	706.3	711.6
150°	513.0	525.0	537.1	540.1	561.2	589.3	603.3	622.7	661.2	690.2	694.4
152.5°	525.7	534.8	544.0	546.2	565.3	590.6	603.3	619.8	652.7	677.5	680.7
155°	544.7	551.4	558.2	559.9	574.3	593.7	603.3	616.4	642.7	662.3	664.5
157.5°	558.6	565.2	571.7	573.4	583.3	596.6	603.3	613.5	633.9	649.2	650.7
160°	568.0	573.2	578.2	579.5	587.5	598.0	603.3	612.1	629.6	642.7	643.6
162.5°	577.4	581.2	585.1	586.1	591.8	599.5	603.3	610.7	625.4	636.5	637.3
165°	587.7	591.1	594.6	595.4	598.1	601.6	603.3	608.7	619.2	627.1	628.0
167.5°	597.1	598.8	600.5	600.9	603.0	605.9	607.4	610.8	617.7	623.0	623.3
170°	603.3	604.9	606.6	607.0	607.1	607.3	607.4	610.8	617.7	623.0	623.0
172.5°	606.6	607.0	607.3	607.4	607.4	607.4	607.4	610.1	615.6	619.7	619.4
175°	611.1	611.1	611.1	611.1	609.8	608.2	607.4	609.2	612.6	615.2	615.2
177.5°	611.1	611.1	611.1	611.1	610.1	608.9	608.2	609.5	612.3	614.4	614.0
180°	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1

TEST NUMBER: P935083

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	699.0	699.0	699.0	699.0	699.0	699.0	699.0	699.0	699.0	699.0	699.0
2.5°	716.8	714.8	716.8	715.4	716.1	714.2	708.2	706.3	708.2	710.2	710.2
5°	725.4	724.1	725.4	725.4	724.7	723.4	716.8	715.4	716.8	717.5	716.1
7.5°	728.1	726.1	728.1	726.7	726.7	725.4	718.8	717.5	718.1	720.1	718.1
10°	728.1	726.1	728.1	727.4	726.7	725.4	718.8	716.1	716.1	718.1	716.1
12.5°	724.7	723.4	724.7	723.4	723.4	722.1	715.4	712.9	713.5	714.2	711.5
15°	719.5	717.5	719.5	718.1	718.8	716.8	709.5	706.9	706.9	708.2	703.6
17.5°	711.5	708.8	711.5	710.9	710.2	708.8	702.2	699.7	699.0	699.7	696.3
20°	702.2	700.3	702.2	701.6	701.6	699.0	692.4	689.0	689.0	689.0	685.8
22.5°	687.7	685.8	687.7	689.0	689.0	688.3	682.4	677.8	676.5	676.5	672.6
25°	671.2	669.2	671.2	671.2	670.5	671.2	669.2	666.5	664.6	662.6	658.6
27.5°	655.3	654.0	655.3	654.0	655.3	653.3	652.6	652.0	649.4	647.4	642.1
30°	639.4	638.1	639.4	638.1	636.8	635.5	632.1	630.8	633.5	632.1	623.5
32.5°	619.6	618.3	619.6	619.6	618.3	618.3	613.0	611.0	611.7	615.7	607.7
35°	599.1	597.1	599.1	598.4	599.1	597.1	593.8	593.2	590.5	595.1	589.2
37.5°	575.3	573.4	575.3	575.3	575.3	576.6	574.0	572.0	568.0	574.0	569.3
40°	550.9	548.2	550.9	550.2	550.9	552.2	550.9	549.5	545.6	550.2	546.2
42.5°	523.1	522.4	523.1	523.8	523.8	526.3	528.4	525.7	524.4	521.1	523.8
45°	493.3	492.0	493.3	494.6	495.3	496.6	502.6	502.6	500.6	495.3	499.2
47.5°	461.5	458.3	461.5	465.5	465.5	467.6	473.5	478.1	474.8	468.2	470.1
50°	427.8	428.5	427.8	430.5	430.5	437.8	442.4	447.1	450.3	442.4	433.1
52.5°	394.8	394.1	394.8	396.8	399.4	402.7	410.7	415.3	420.5	415.9	401.4
55°	361.7	363.0	361.7	362.4	363.7	365.7	377.5	382.2	392.1	386.2	370.9
57.5°	328.6	326.7	328.6	330.0	330.6	332.6	342.5	351.1	357.1	357.7	339.2
60°	290.3	287.6	290.3	296.3	297.6	298.9	308.1	316.1	321.3	323.3	304.2
62.5°	256.6	251.9	256.6	260.5	263.2	266.5	273.1	285.1	289.6	290.3	263.2
65°	220.9	218.9	220.9	228.8	229.4	233.4	240.7	249.3	259.2	257.9	218.9
67.5°	188.4	188.4	188.4	193.7	197.7	199.7	208.9	213.0	225.5	226.8	182.5
70°	158.7	158.1	158.7	162.7	165.4	170.0	178.6	183.2	193.1	196.4	148.1
72.5°	130.3	129.6	130.3	133.6	136.3	140.2	147.5	152.7	161.3	165.4	115.1
75°	105.1	103.8	105.1	107.8	107.1	112.4	118.3	123.6	131.6	134.2	85.3
77.5°	80.7	80.7	80.7	83.3	83.3	88.6	91.3	97.9	102.5	106.5	62.8
80°	60.1	59.6	60.1	60.8	60.8	63.5	68.1	72.8	76.7	76.7	43.0
82.5°	42.3	41.0	42.3	42.3	42.3	43.7	46.2	47.6	50.3	52.3	27.1
85°	26.4	26.4	26.4	27.1	26.4	27.8	28.4	29.8	29.8	28.4	16.6
87.5°	17.2	16.6	17.2	16.6	16.6	15.9	15.9	15.9	15.2	14.6	9.3
90°	15.6	15.6	15.6	15.6	15.6	20.8	27.7	31.2	26.8	18.0	11.4
92.5°	62.4	50.0	62.4	74.8	77.9	110.4	153.8	175.5	154.1	111.3	79.2
95°	217.6	180.0	217.6	255.2	264.5	347.4	457.8	513.0	433.2	273.8	154.2
97.5°	521.3	449.9	521.3	592.8	610.6	663.0	732.8	767.7	634.8	368.9	169.4
100°	751.1	666.0	751.1	836.2	857.5	853.7	848.7	846.1	698.6	403.5	182.1
102.5°	977.2	904.4	977.2	1050.1	1068.3	1001.7	912.7	868.3	718.6	419.3	194.8
105°	1265.4	1226.3	1265.4	1304.7	1314.4	1164.9	965.5	865.8	720.9	431.1	213.7
107.5°	1454.3	1463.7	1454.3	1444.8	1442.4	1233.8	955.6	816.5	688.7	433.2	241.6
110°	1526.2	1567.0	1526.2	1485.4	1475.2	1242.0	931.0	775.5	660.3	429.9	257.1

TEST NUMBER: P935083

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1532.6	1595.3	1532.6	1469.9	1454.3	1215.5	897.4	738.2	635.5	430.1	276.0
115°	1492.0	1579.0	1492.0	1405.0	1383.4	1153.4	846.9	693.6	607.1	434.0	304.3
117.5°	1405.8	1502.3	1405.8	1309.4	1285.3	1077.8	801.1	662.8	589.2	442.1	331.8
120°	1336.4	1430.1	1336.4	1242.8	1219.3	1029.7	776.9	650.5	583.2	448.6	347.8
122.5°	1268.8	1361.2	1268.8	1176.3	1153.2	982.5	754.8	641.0	580.1	458.1	366.7
125°	1172.3	1257.4	1172.3	1087.2	1065.9	920.8	727.5	630.7	577.4	470.8	390.9
127.5°	1085.6	1157.4	1085.6	1013.7	995.8	871.2	705.2	622.2	575.9	483.5	414.2
130°	1034.4	1100.8	1034.4	968.1	951.5	840.7	692.9	618.9	576.9	492.8	429.8
132.5°	988.0	1047.4	988.0	928.6	913.7	814.4	682.1	616.0	577.4	500.3	442.5
135°	924.4	975.6	924.4	873.2	860.4	777.3	666.5	611.1	576.9	508.6	457.3
137.5°	873.5	915.4	873.5	831.5	821.0	750.7	657.1	610.2	580.5	520.8	476.1
140°	838.5	877.6	838.5	799.3	789.5	728.8	647.8	607.4	581.0	528.4	488.9
142.5°	809.5	843.2	809.5	775.8	767.3	714.0	642.9	607.4	583.1	534.7	498.3
145°	766.0	791.6	766.0	740.5	734.1	690.5	632.4	603.3	583.2	542.9	512.6
147.5°	732.7	753.8	732.7	711.6	706.3	672.0	626.2	603.3	587.2	554.9	530.7
150°	711.6	728.8	711.6	694.4	690.2	661.2	622.7	603.3	589.3	561.2	540.1
152.5°	693.7	706.7	693.7	680.7	677.5	652.7	619.8	603.3	590.6	565.3	546.2
155°	673.0	681.6	673.0	664.5	662.3	642.7	616.4	603.3	593.7	574.3	559.9
157.5°	656.8	662.8	656.8	650.7	649.2	633.9	613.5	603.3	596.6	583.3	573.4
160°	647.0	650.5	647.0	643.6	642.7	629.6	612.1	603.3	598.0	587.5	579.5
162.5°	640.6	643.9	640.6	637.3	636.5	625.4	610.7	603.3	599.5	591.8	586.1
165°	631.4	634.9	631.4	628.0	627.1	619.2	608.7	603.3	601.6	598.1	595.4
167.5°	624.7	626.2	624.7	623.3	623.0	617.7	610.8	607.4	605.9	603.0	600.9
170°	623.0	623.0	623.0	623.0	623.0	617.7	610.8	607.4	607.3	607.1	607.0
172.5°	618.1	616.8	618.1	619.4	619.7	615.6	610.1	607.4	607.4	607.4	607.4
175°	615.2	615.2	615.2	615.2	615.2	612.6	609.2	607.4	608.2	609.8	611.1
177.5°	612.6	611.1	612.6	614.0	614.4	612.3	609.5	608.2	608.9	610.1	611.1
180°	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1

TEST NUMBER: P935083

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	699.0	699.0	699.0	699.0	699.0	699.0	699.0	699.0	699.0	699.0	699.0
2.5°	708.8	704.9	704.9	698.3	695.6	693.7	690.4	680.4	677.8	675.1	679.2
5°	714.8	707.6	702.2	690.4	680.4	676.5	663.9	640.1	624.2	612.3	605.7
7.5°	716.1	706.9	697.0	678.5	654.6	644.1	605.7	562.1	550.2	539.6	532.9
10°	714.8	704.2	690.4	662.6	606.4	587.9	549.5	521.1	513.8	511.8	513.8
12.5°	710.2	700.3	681.1	634.8	556.1	543.6	521.1	504.5	503.3	506.5	524.4
15°	702.2	693.0	670.5	597.8	528.4	519.1	503.3	497.2	504.5	527.7	581.2
17.5°	694.3	683.8	656.0	561.4	507.2	500.6	489.4	501.3	542.2	573.4	591.2
20°	683.8	671.2	639.4	535.0	492.0	486.0	480.8	534.3	565.4	576.6	586.6
22.5°	671.2	658.0	616.9	516.5	476.1	471.5	474.8	552.9	565.4	573.4	581.9
25°	654.6	643.4	590.5	501.9	463.5	458.3	470.8	550.9	558.1	560.0	577.3
27.5°	639.4	624.9	562.7	488.7	448.3	446.4	474.2	542.2	547.5	549.5	568.0
30°	620.9	599.1	531.7	474.8	432.5	431.8	474.8	531.7	530.4	535.6	554.1
32.5°	601.8	560.7	496.6	457.6	417.3	416.6	470.1	515.8	514.5	521.7	535.6
35°	583.9	531.0	449.0	437.8	398.0	398.7	458.9	497.2	497.9	504.5	513.1
37.5°	565.4	505.2	396.8	415.9	379.6	379.6	443.7	480.1	478.8	480.8	492.6
40°	543.6	464.9	350.4	387.5	362.4	360.4	425.2	461.5	456.9	456.3	472.8
42.5°	520.4	420.5	316.1	349.8	342.5	339.9	402.7	439.1	430.5	432.5	453.7
45°	495.3	408.7	289.6	295.6	322.0	320.1	378.2	413.3	407.3	412.6	434.4
47.5°	470.1	384.8	281.0	245.3	300.2	299.5	351.1	388.2	384.8	390.2	413.3
50°	435.8	358.4	280.4	210.3	275.8	278.3	318.8	363.7	363.7	368.4	392.8
52.5°	391.4	326.0	254.6	190.4	247.3	255.3	290.3	342.5	343.8	348.5	370.3
55°	351.1	292.3	236.0	175.2	213.6	230.8	262.5	320.7	323.3	327.9	347.9
57.5°	314.1	243.3	232.1	157.4	182.5	199.1	238.0	299.5	300.8	304.9	324.0
60°	274.4	175.9	213.0	138.2	155.4	167.9	215.5	274.4	279.0	281.7	298.3
62.5°	229.4	127.6	193.1	125.0	142.2	144.8	197.1	250.6	256.6	258.5	268.5
65°	163.4	107.1	164.0	113.8	128.3	129.0	177.2	226.2	231.4	234.8	242.1
67.5°	110.4	87.3	125.0	103.1	117.7	118.3	158.1	197.7	205.0	207.7	212.3
70°	76.7	58.2	92.6	91.9	105.8	107.1	137.5	172.0	178.6	180.5	183.2
72.5°	56.2	46.9	76.7	82.6	93.3	94.6	116.3	142.9	149.5	151.4	152.7
75°	43.0	49.6	62.1	72.1	79.4	80.0	95.2	116.3	121.0	122.4	123.0
77.5°	34.4	46.2	45.7	58.2	64.8	63.5	74.7	89.9	93.9	93.9	93.9
80°	25.8	36.4	34.4	41.7	47.6	46.2	53.5	64.2	65.5	66.8	66.2
82.5°	19.1	23.2	23.2	26.4	31.7	30.5	35.7	41.7	41.7	41.7	43.0
85°	11.9	13.2	10.6	13.9	17.8	17.2	19.8	22.5	23.2	23.2	21.8
87.5°	7.3	5.9	3.4	5.3	7.9	7.9	9.3	10.0	9.3	9.3	9.3
90°	10.6	7.4	4.1	7.4	10.6	11.4	18.0	26.8	31.2	27.7	20.8
92.5°	72.2	44.3	16.4	44.3	72.2	79.2	111.3	154.1	175.5	153.8	110.4
95°	141.5	90.4	39.3	90.4	141.5	154.2	273.8	433.2	513.0	457.8	347.4
97.5°	158.2	113.1	68.0	113.1	158.2	169.4	368.9	634.8	767.7	732.8	663.0
100°	171.9	131.0	90.2	131.0	171.9	182.1	403.5	698.6	846.1	848.7	853.7
102.5°	185.3	147.2	109.1	147.2	185.3	194.8	419.3	718.6	868.3	912.7	1001.7
105°	205.6	173.3	141.1	173.3	205.6	213.7	431.1	720.9	865.8	965.5	1164.9
107.5°	234.1	204.0	173.9	204.0	234.1	241.6	433.2	688.7	816.5	955.6	1233.8
110°	250.3	223.2	196.0	223.2	250.3	257.1	429.9	660.3	775.5	931.0	1242.0

TEST NUMBER: P935083

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	269.5	243.6	217.8	243.6	269.5	276.0	430.1	635.5	738.2	897.4	1215.5
115°	298.3	274.4	250.5	274.4	298.3	304.3	434.0	607.1	693.6	846.9	1153.4
117.5°	326.4	304.7	283.0	304.7	326.4	331.8	442.1	589.2	662.8	801.1	1077.8
120°	342.6	322.2	301.8	322.2	342.6	347.8	448.6	583.2	650.5	776.9	1029.7
122.5°	361.6	341.0	320.4	341.0	361.6	366.7	458.1	580.1	641.0	754.8	982.5
125°	386.1	367.4	348.6	367.4	386.1	390.9	470.8	577.4	630.7	727.5	920.8
127.5°	409.5	390.5	371.5	390.5	409.5	414.2	483.5	575.9	622.2	705.2	871.2
130°	424.7	404.3	383.8	404.3	424.7	429.8	492.8	576.9	618.9	692.9	840.7
132.5°	437.4	417.0	396.6	417.0	437.4	442.5	500.3	577.4	616.0	682.1	814.4
135°	452.7	434.0	415.5	434.0	452.7	457.3	508.6	576.9	611.1	666.5	777.3
137.5°	471.5	453.2	434.7	453.2	471.5	476.1	520.8	580.5	610.2	657.1	750.7
140°	484.6	467.7	450.7	467.7	484.6	488.9	528.4	581.0	607.4	647.8	728.8
142.5°	494.4	478.7	463.0	478.7	494.4	498.3	534.7	583.1	607.4	642.9	714.0
145°	509.2	495.6	481.9	495.6	509.2	512.6	542.9	583.2	603.3	632.4	690.5
147.5°	527.3	514.1	500.8	514.1	527.3	530.7	554.9	587.2	603.3	626.2	672.0
150°	537.1	525.0	513.0	525.0	537.1	540.1	561.2	589.3	603.3	622.7	661.2
152.5°	544.0	534.8	525.7	534.8	544.0	546.2	565.3	590.6	603.3	619.8	652.7
155°	558.2	551.4	544.7	551.4	558.2	559.9	574.3	593.7	603.3	616.4	642.7
157.5°	571.7	565.2	558.6	565.2	571.7	573.4	583.3	596.6	603.3	613.5	633.9
160°	578.2	573.2	568.0	573.2	578.2	579.5	587.5	598.0	603.3	612.1	629.6
162.5°	585.1	581.2	577.4	581.2	585.1	586.1	591.8	599.5	603.3	610.7	625.4
165°	594.6	591.1	587.7	591.1	594.6	595.4	598.1	601.6	603.3	608.7	619.2
167.5°	600.5	598.8	597.1	598.8	600.5	600.9	603.0	605.9	607.4	610.8	617.7
170°	606.6	604.9	603.3	604.9	606.6	607.0	607.1	607.3	607.4	610.8	617.7
172.5°	607.3	607.0	606.6	607.0	607.3	607.4	607.4	607.4	607.4	610.1	615.6
175°	611.1	611.1	611.1	611.1	611.1	611.1	609.8	608.2	607.4	609.2	612.6
177.5°	611.1	611.1	611.1	611.1	611.1	611.1	610.1	608.9	608.2	609.5	612.3
180°	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1

TEST NUMBER: P935083

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	699.0	699.0	699.0	699.0	699.0	699.0	699.0	699.0	699.0	699.0	699.0
2.5°	674.5	672.6	675.1	667.9	675.1	672.6	674.5	679.2	675.1	677.8	680.4
5°	591.8	588.5	578.0	569.3	578.0	588.5	591.8	605.7	612.3	624.2	640.1
7.5°	529.0	526.3	523.8	518.4	523.8	526.3	529.0	532.9	539.6	550.2	562.1
10°	515.1	515.8	519.7	519.1	519.7	515.8	515.1	513.8	511.8	513.8	521.1
12.5°	550.9	556.8	578.6	577.3	578.6	556.8	550.9	524.4	506.5	503.3	504.5
15°	591.8	593.8	598.4	599.1	598.4	593.8	591.8	581.2	527.7	504.5	497.2
17.5°	595.8	596.4	599.8	599.8	599.8	596.4	595.8	591.2	573.4	542.2	501.3
20°	592.5	593.8	600.5	601.8	600.5	593.8	592.5	586.6	576.6	565.4	534.3
22.5°	591.2	593.8	599.1	598.4	599.1	593.8	591.2	581.9	573.4	565.4	552.9
25°	584.6	584.6	585.2	585.9	585.2	584.6	584.6	577.3	560.0	558.1	550.9
27.5°	570.7	572.0	575.9	575.3	575.9	572.0	570.7	568.0	549.5	547.5	542.2
30°	558.1	556.8	553.4	550.9	553.4	556.8	558.1	554.1	535.6	530.4	531.7
32.5°	537.0	533.6	530.4	528.4	530.4	533.6	537.0	535.6	521.7	514.5	515.8
35°	511.8	512.5	511.8	509.9	511.8	512.5	511.8	513.1	504.5	497.9	497.2
37.5°	494.0	495.3	494.6	492.0	494.6	495.3	494.0	492.6	480.8	478.8	480.1
40°	475.4	476.1	475.4	473.5	475.4	476.1	475.4	472.8	456.3	456.9	461.5
42.5°	457.6	456.9	454.9	453.7	454.9	456.9	457.6	453.7	432.5	430.5	439.1
45°	437.1	437.8	433.7	431.8	433.7	437.8	437.1	434.4	412.6	407.3	413.3
47.5°	416.6	416.6	413.3	411.3	413.3	416.6	416.6	413.3	390.2	384.8	388.2
50°	394.8	394.1	389.5	388.8	389.5	394.1	394.8	392.8	368.4	363.7	363.7
52.5°	369.7	369.7	370.3	371.6	370.3	369.7	369.7	370.3	348.5	343.8	342.5
55°	347.9	348.5	353.1	354.5	353.1	348.5	347.9	347.9	327.9	323.3	320.7
57.5°	325.4	325.4	328.6	328.6	328.6	325.4	325.4	324.0	304.9	300.8	299.5
60°	299.5	300.8	303.5	302.9	303.5	300.8	299.5	298.3	281.7	279.0	274.4
62.5°	272.4	273.8	274.4	273.1	274.4	273.8	272.4	268.5	258.5	256.6	250.6
65°	244.0	245.3	246.0	244.6	246.0	245.3	244.0	242.1	234.8	231.4	226.2
67.5°	214.9	214.3	213.6	216.2	213.6	214.3	214.9	212.3	207.7	205.0	197.7
70°	185.2	185.2	184.5	185.9	184.5	185.2	185.2	183.2	180.5	178.6	172.0
72.5°	153.4	152.7	155.4	153.4	155.4	152.7	153.4	152.7	151.4	149.5	142.9
75°	122.4	123.6	122.4	124.3	122.4	123.6	122.4	123.0	122.4	121.0	116.3
77.5°	93.3	94.6	93.3	93.3	93.3	94.6	93.3	93.9	93.9	93.9	89.9
80°	66.2	65.5	65.5	64.8	65.5	65.5	66.2	66.2	66.8	65.5	64.2
82.5°	42.3	41.7	41.7	43.0	41.7	41.7	42.3	43.0	41.7	41.7	41.7
85°	23.2	23.8	22.5	22.5	22.5	23.8	23.2	21.8	23.2	23.2	22.5
87.5°	8.6	7.9	7.9	7.9	7.9	7.9	8.6	9.3	9.3	9.3	10.0
90°	15.6	15.6	15.6	15.6	15.6	15.6	15.6	20.8	27.7	31.2	26.8
92.5°	77.9	74.8	62.4	50.0	62.4	74.8	77.9	110.4	153.8	175.5	154.1
95°	264.5	255.2	217.6	180.0	217.6	255.2	264.5	347.4	457.8	513.0	433.2
97.5°	610.6	592.8	521.3	449.9	521.3	592.8	610.6	663.0	732.8	767.7	634.8
100°	857.5	836.2	751.1	666.0	751.1	836.2	857.5	853.7	848.7	846.1	698.6
102.5°	1068.3	1050.1	977.2	904.4	977.2	1050.1	1068.3	1001.7	912.7	868.3	718.6
105°	1314.4	1304.7	1265.4	1226.3	1265.4	1304.7	1314.4	1164.9	965.5	865.8	720.9
107.5°	1442.4	1444.8	1454.3	1463.7	1454.3	1444.8	1442.4	1233.8	955.6	816.5	688.7
110°	1475.2	1485.4	1526.2	1567.0	1526.2	1485.4	1475.2	1242.0	931.0	775.5	660.3

TEST NUMBER: P935083

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1454.3	1469.9	1532.6	1595.3	1532.6	1469.9	1454.3	1215.5	897.4	738.2	635.5
115°	1383.4	1405.0	1492.0	1579.0	1492.0	1405.0	1383.4	1153.4	846.9	693.6	607.1
117.5°	1285.3	1309.4	1405.8	1502.3	1405.8	1309.4	1285.3	1077.8	801.1	662.8	589.2
120°	1219.3	1242.8	1336.4	1430.1	1336.4	1242.8	1219.3	1029.7	776.9	650.5	583.2
122.5°	1153.2	1176.3	1268.8	1361.2	1268.8	1176.3	1153.2	982.5	754.8	641.0	580.1
125°	1065.9	1087.2	1172.3	1257.4	1172.3	1087.2	1065.9	920.8	727.5	630.7	577.4
127.5°	995.8	1013.7	1085.6	1157.4	1085.6	1013.7	995.8	871.2	705.2	622.2	575.9
130°	951.5	968.1	1034.4	1100.8	1034.4	968.1	951.5	840.7	692.9	618.9	576.9
132.5°	913.7	928.6	988.0	1047.4	988.0	928.6	913.7	814.4	682.1	616.0	577.4
135°	860.4	873.2	924.4	975.6	924.4	873.2	860.4	777.3	666.5	611.1	576.9
137.5°	821.0	831.5	873.5	915.4	873.5	831.5	821.0	750.7	657.1	610.2	580.5
140°	789.5	799.3	838.5	877.6	838.5	799.3	789.5	728.8	647.8	607.4	581.0
142.5°	767.3	775.8	809.5	843.2	809.5	775.8	767.3	714.0	642.9	607.4	583.1
145°	734.1	740.5	766.0	791.6	766.0	740.5	734.1	690.5	632.4	603.3	583.2
147.5°	706.3	711.6	732.7	753.8	732.7	711.6	706.3	672.0	626.2	603.3	587.2
150°	690.2	694.4	711.6	728.8	711.6	694.4	690.2	661.2	622.7	603.3	589.3
152.5°	677.5	680.7	693.7	706.7	693.7	680.7	677.5	652.7	619.8	603.3	590.6
155°	662.3	664.5	673.0	681.6	673.0	664.5	662.3	642.7	616.4	603.3	593.7
157.5°	649.2	650.7	656.8	662.8	656.8	650.7	649.2	633.9	613.5	603.3	596.6
160°	642.7	643.6	647.0	650.5	647.0	643.6	642.7	629.6	612.1	603.3	598.0
162.5°	636.5	637.3	640.6	643.9	640.6	637.3	636.5	625.4	610.7	603.3	599.5
165°	627.1	628.0	631.4	634.9	631.4	628.0	627.1	619.2	608.7	603.3	601.6
167.5°	623.0	623.3	624.7	626.2	624.7	623.3	623.0	617.7	610.8	607.4	605.9
170°	623.0	623.0	623.0	623.0	623.0	623.0	623.0	617.7	610.8	607.4	607.3
172.5°	619.7	619.4	618.1	616.8	618.1	619.4	619.7	615.6	610.1	607.4	607.4
175°	615.2	615.2	615.2	615.2	615.2	615.2	615.2	612.6	609.2	607.4	608.2
177.5°	614.4	614.0	612.6	611.1	612.6	614.0	614.4	612.3	609.5	608.2	608.9
180°	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1	611.1

TEST NUMBER: P935083

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	699.0	699.0	699.0	699.0	699.0
2.5°	690.4	693.7	695.6	698.3	704.9
5°	663.9	676.5	680.4	690.4	702.2
7.5°	605.7	644.1	654.6	678.5	697.0
10°	549.5	587.9	606.4	662.6	690.4
12.5°	521.1	543.6	556.1	634.8	681.1
15°	503.3	519.1	528.4	597.8	670.5
17.5°	489.4	500.6	507.2	561.4	656.0
20°	480.8	486.0	492.0	535.0	639.4
22.5°	474.8	471.5	476.1	516.5	616.9
25°	470.8	458.3	463.5	501.9	590.5
27.5°	474.2	446.4	448.3	488.7	562.7
30°	474.8	431.8	432.5	474.8	531.7
32.5°	470.1	416.6	417.3	457.6	496.6
35°	458.9	398.7	398.0	437.8	449.0
37.5°	443.7	379.6	379.6	415.9	396.8
40°	425.2	360.4	362.4	387.5	350.4
42.5°	402.7	339.9	342.5	349.8	316.1
45°	378.2	320.1	322.0	295.6	289.6
47.5°	351.1	299.5	300.2	245.3	281.0
50°	318.8	278.3	275.8	210.3	280.4
52.5°	290.3	255.3	247.3	190.4	254.6
55°	262.5	230.8	213.6	175.2	236.0
57.5°	238.0	199.1	182.5	157.4	232.1
60°	215.5	167.9	155.4	138.2	213.0
62.5°	197.1	144.8	142.2	125.0	193.1
65°	177.2	129.0	128.3	113.8	164.0
67.5°	158.1	118.3	117.7	103.1	125.0
70°	137.5	107.1	105.8	91.9	92.6
72.5°	116.3	94.6	93.3	82.6	76.7
75°	95.2	80.0	79.4	72.1	62.1
77.5°	74.7	63.5	64.8	58.2	45.7
80°	53.5	46.2	47.6	41.7	34.4
82.5°	35.7	30.5	31.7	26.4	23.2
85°	19.8	17.2	17.8	13.9	10.6
87.5°	9.3	7.9	7.9	5.3	3.4
90°	18.0	11.4	10.6	7.4	4.1
92.5°	111.3	79.2	72.2	44.3	16.4
95°	273.8	154.2	141.5	90.4	39.3
97.5°	368.9	169.4	158.2	113.1	68.0
100°	403.5	182.1	171.9	131.0	90.2
102.5°	419.3	194.8	185.3	147.2	109.1
105°	431.1	213.7	205.6	173.3	141.1
107.5°	433.2	241.6	234.1	204.0	173.9
110°	429.9	257.1	250.3	223.2	196.0

TEST NUMBER: P935083

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	430.1	276.0	269.5	243.6	217.8
115°	434.0	304.3	298.3	274.4	250.5
117.5°	442.1	331.8	326.4	304.7	283.0
120°	448.6	347.8	342.6	322.2	301.8
122.5°	458.1	366.7	361.6	341.0	320.4
125°	470.8	390.9	386.1	367.4	348.6
127.5°	483.5	414.2	409.5	390.5	371.5
130°	492.8	429.8	424.7	404.3	383.8
132.5°	500.3	442.5	437.4	417.0	396.6
135°	508.6	457.3	452.7	434.0	415.5
137.5°	520.8	476.1	471.5	453.2	434.7
140°	528.4	488.9	484.6	467.7	450.7
142.5°	534.7	498.3	494.4	478.7	463.0
145°	542.9	512.6	509.2	495.6	481.9
147.5°	554.9	530.7	527.3	514.1	500.8
150°	561.2	540.1	537.1	525.0	513.0
152.5°	565.3	546.2	544.0	534.8	525.7
155°	574.3	559.9	558.2	551.4	544.7
157.5°	583.3	573.4	571.7	565.2	558.6
160°	587.5	579.5	578.2	573.2	568.0
162.5°	591.8	586.1	585.1	581.2	577.4
165°	598.1	595.4	594.6	591.1	587.7
167.5°	603.0	600.9	600.5	598.8	597.1
170°	607.1	607.0	606.6	604.9	603.3
172.5°	607.4	607.4	607.3	607.0	606.6
175°	609.8	611.1	611.1	611.1	611.1
177.5°	610.1	611.1	611.1	611.1	611.1
180°	611.1	611.1	611.1	611.1	611.1

TEST NUMBER: P935083

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.26	9.98	10.37	11.08	12.59	12.06	12.78	13.16	13.88	15.39
	3H	9.73	10.37	10.84	11.48	13.01	13.39	14.03	14.50	15.13	16.67
	4H	9.91	10.52	11.04	11.63	13.17	13.82	14.43	14.94	15.53	17.07
	6H	10.03	10.59	11.16	11.70	13.25	14.09	14.65	15.22	15.76	17.31
	8H	10.02	10.56	11.16	11.68	13.22	14.15	14.69	15.29	15.81	17.35
	12H	9.99	10.50	11.13	11.62	13.18	14.18	14.69	15.32	15.81	17.37
4H	2H	10.27	10.88	11.40	11.99	13.52	12.46	13.06	13.58	14.17	15.71
	3H	11.28	11.79	12.42	12.93	14.47	13.94	14.44	15.07	15.58	17.13
	4H	11.55	12.02	12.69	13.14	14.71	14.45	14.92	15.59	16.04	17.61
	6H	11.67	12.07	12.82	13.22	14.78	14.80	15.20	15.95	16.35	17.91
	8H	11.67	12.05	12.82	13.18	14.76	14.90	15.27	16.04	16.41	17.99
	12H	11.63	11.97	12.79	13.12	14.70	14.94	15.28	16.10	16.43	18.01
8H	4H	11.99	12.36	13.13	13.50	15.08	14.57	14.94	15.71	16.08	17.65
	6H	12.25	12.55	13.41	13.73	15.31	14.99	15.30	16.15	16.48	18.05
	8H	12.29	12.56	13.46	13.72	15.31	15.13	15.40	16.30	16.56	18.16
	12H	12.27	12.50	13.44	13.66	15.29	15.22	15.46	16.39	16.61	18.24
12H	4H	11.99	12.33	13.15	13.48	15.06	14.52	14.86	15.68	16.01	17.59
	6H	12.30	12.57	13.47	13.73	15.33	14.98	15.25	16.15	16.41	18.01
	8H	12.36	12.60	13.54	13.76	15.38	15.13	15.37	16.31	16.53	18.15

END OF REPORT