

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P933889

Luminaire Tested: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-6-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P933889
REPORT IS A COMBINATION OF REPORTS P933675 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-6-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4078.5 lumens
Efficiency: N/A
Efficacy: 123.6 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P933889

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-6-3500K

Luminous Intensity Polar Plot



TEST NUMBER: P933889

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-6-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	66		
1	101	97	93	89	95	91	88	85	81	78	76	71	69	68	62	61	60	55		
2	92	85	78	73	87	80	74	70	71	67	63	63	59	56	55	52	50	46		
3	84	75	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43	39		
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	43	40	37	34		
5	71	59	50	44	66	56	48	43	50	44	39	44	39	35	39	35	32	29		
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	35	31	28	26		
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25	23		
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20		
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18		
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6374	6374	6374	6374
5°	6419	6434	6419	5059
10°	6373	6338	6373	4531
15°	6303	6201	6303	5177
20°	6168	6038	6168	5188
25°	5896	5801	5896	5079
30°	5545	5604	5545	4837
35°	4941	5354	4941	4572
40°	4115	5061	4115	4372
45°	3674	4718	3674	4141
50°	3900	4309	3900	3910
55°	3666	3868	3666	3776
60°	3775	3284	3775	3458
65°	3417	2716	3417	3035
70°	2359	2163	2359	2544
75°	2063	1599	2063	1915
80°	1650	1057	1650	1151
85°	930	560	930	475

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 5635 cd/sqm

TEST NUMBER: P933889

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-6-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.0	2.3
10°-20°	264.1	6.5
20°-30°	408.2	10.0
30°-40°	487.3	11.9
40°-50°	490.2	12.0
50°-60°	426.5	10.5
60°-70°	302.4	7.4
70°-80°	160.0	3.9
80°-90°	40.7	1.0
90°-100°	105.7	2.6
100°-110°	278.0	6.8
110°-120°	288.2	7.1
120°-130°	231.2	5.7
130°-140°	181.4	4.4
140°-150°	139.2	3.4
150°-160°	100.3	2.5
160°-170°	61.4	1.5
170°-180°	20.7	0.5
0°-30°	765.3	18.8
0°-40°	1252.6	30.7
0°-60°	2169.3	53.2
0°-90°	2672.4	65.5
90°-120°	671.9	16.5
90°-150°	1223.8	30.0
90°-180°	1406.0	34.5
0°-180°	4078.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1030	1030	1030	1030	1030	
5°	1035	1067	1035	839	1035	98
15°	988	1058	988	883	988	278
25°	870	986	870	864	870	400
35°	662	880	662	752	662	409
45°	427	725	427	636	427	342
55°	348	535	348	522	348	320
65°	242	323	242	361	242	231
75°	92	153	92	183	92	96
85°	16	39	16	33	16	21
90°	2	6	2	6	2	2
95°	14	64	14	64	14	16
105°	50	435	50	435	50	53
115°	89	560	89	560	89	88
125°	124	446	124	446	124	110
135°	148	346	148	346	148	114
145°	171	281	171	281	171	107
155°	193	242	193	242	193	89
165°	209	225	209	225	209	59
175°	217	218	217	218	217	21
180°	217	217	217	217	217	

TEST NUMBER: P933889

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3
2.5°	1039.2	1039.2	1045.0	1046.9	1046.9	1044.0	1041.1	1044.0	1052.8	1055.7	1054.8
5°	1035.2	1043.0	1053.8	1055.7	1057.7	1056.7	1054.8	1056.7	1066.4	1068.4	1069.4
7.5°	1027.4	1042.1	1055.7	1058.6	1061.5	1058.6	1057.7	1059.6	1069.4	1071.3	1071.3
10°	1017.6	1038.2	1053.8	1055.7	1058.6	1055.7	1055.7	1059.6	1069.4	1071.3	1072.3
12.5°	1004.1	1032.3	1046.9	1048.8	1052.8	1051.8	1050.8	1054.8	1064.4	1066.4	1066.4
15°	988.5	1021.6	1035.2	1037.2	1044.0	1042.1	1042.1	1045.9	1056.7	1059.6	1058.6
17.5°	967.0	1008.0	1023.6	1026.5	1031.3	1030.3	1031.3	1035.2	1045.0	1046.9	1047.9
20°	942.6	989.4	1008.0	1010.9	1015.7	1015.7	1015.7	1020.6	1030.3	1034.2	1034.2
22.5°	909.5	969.9	989.4	991.4	997.2	997.2	999.1	1006.0	1014.7	1015.7	1015.7
25°	870.5	948.5	965.0	970.9	976.8	979.7	982.6	986.5	989.4	988.5	989.4
27.5°	829.6	921.1	942.6	946.5	954.4	957.3	961.2	962.1	963.1	966.0	964.1
30°	783.7	883.1	915.3	919.2	931.9	933.8	929.9	931.9	936.7	938.8	940.7
32.5°	732.1	826.7	887.0	895.8	907.6	901.7	900.7	903.6	911.4	911.4	913.4
35°	661.9	782.8	860.8	868.5	877.3	870.5	874.4	875.4	880.2	883.1	882.2
37.5°	584.9	744.8	833.4	839.3	846.1	837.3	843.2	846.1	850.0	848.1	848.1
40°	516.7	685.3	801.3	805.1	811.1	804.2	810.1	812.0	814.0	812.0	811.1
42.5°	466.0	620.0	767.2	772.0	768.1	773.0	775.0	778.9	776.0	772.0	772.0
45°	426.9	602.4	730.1	736.0	730.1	737.9	740.8	740.8	732.1	730.1	729.2
47.5°	414.2	567.3	693.1	693.1	690.1	699.9	704.8	698.0	689.2	686.2	686.2
50°	413.3	528.3	642.4	638.5	652.1	663.9	658.9	652.1	645.4	634.6	634.6
52.5°	375.3	480.5	577.0	591.7	613.2	620.0	612.2	605.3	593.6	588.8	584.9
55°	348.0	430.8	517.6	546.9	569.3	578.0	563.5	556.6	539.1	536.1	534.2
57.5°	342.2	358.7	463.0	500.1	527.3	526.4	517.6	504.9	490.3	487.4	486.4
60°	313.9	259.3	404.6	448.5	476.7	473.7	466.0	454.3	440.6	438.7	436.7
62.5°	284.6	188.2	338.3	388.0	427.9	426.9	420.2	402.6	392.8	388.0	384.1
65°	241.8	157.9	240.8	322.7	380.1	382.1	367.5	354.8	344.1	338.3	337.3
67.5°	184.2	128.7	162.8	269.1	334.4	332.4	313.9	308.0	294.4	291.5	285.7
70°	136.4	85.8	113.1	218.3	289.5	284.6	270.1	263.2	250.5	243.7	239.8
72.5°	113.1	69.2	82.8	169.6	243.7	237.9	225.2	217.3	206.7	200.8	196.9
75°	91.7	73.1	63.4	125.8	197.9	194.0	182.3	174.5	165.7	157.9	158.9
77.5°	67.2	68.2	50.7	92.6	157.0	151.1	144.3	134.5	130.6	122.9	122.9
80°	50.7	53.6	38.0	63.4	113.1	113.1	107.3	100.4	93.6	89.7	89.7
82.5°	34.1	34.1	28.3	39.9	77.0	74.1	70.2	68.2	64.3	62.4	62.4
85°	15.6	19.5	17.5	24.3	42.0	43.9	43.9	42.0	41.0	39.0	39.9
87.5°	4.8	8.8	10.8	13.7	21.4	22.4	23.4	23.4	23.4	24.3	24.3
90°	1.5	2.6	3.8	4.1	6.4	9.5	11.0	9.8	7.4	5.5	5.5
92.5°	5.8	15.7	25.6	28.1	39.5	54.7	62.3	54.6	39.1	27.6	26.6
95°	14.0	32.1	50.2	54.7	97.2	153.8	182.1	162.5	123.3	93.9	90.6
97.5°	24.1	40.1	56.1	60.1	130.9	225.3	272.5	260.1	235.4	216.8	210.5
100°	32.1	46.5	61.0	64.6	143.2	248.0	300.3	301.2	303.0	304.4	296.8
102.5°	38.8	52.3	65.8	69.2	148.8	255.0	308.1	323.9	355.5	379.3	372.8
105°	50.1	61.5	73.0	75.9	153.0	255.8	307.3	342.6	413.5	466.6	463.1
107.5°	61.7	72.4	83.0	85.8	153.8	244.5	289.8	339.2	438.0	512.0	512.9
110°	69.6	79.3	88.9	91.3	152.6	234.4	275.3	330.5	440.9	523.6	527.2

TEST NUMBER: P933889

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	77.3	86.5	95.6	98.0	152.6	225.6	262.0	318.5	431.5	516.2	521.7
115°	89.0	97.5	105.9	108.0	154.1	215.4	246.1	300.6	409.4	491.0	498.7
117.5°	100.5	108.1	115.8	117.7	156.9	209.1	235.3	284.4	382.6	456.2	464.7
120°	107.2	114.4	121.6	123.5	159.3	207.1	230.9	275.8	365.5	432.9	441.2
122.5°	113.7	121.0	128.3	130.1	162.6	205.9	227.5	267.9	348.7	409.4	417.6
125°	123.7	130.4	137.1	138.8	167.2	205.0	223.9	258.2	326.9	378.4	386.0
127.5°	131.9	138.6	145.4	147.0	171.6	204.5	220.8	250.3	309.3	353.5	359.9
130°	136.2	143.5	150.7	152.5	174.9	204.7	219.7	245.9	298.4	337.7	343.6
132.5°	140.8	148.1	155.2	157.1	177.6	205.0	218.7	242.2	289.1	324.3	329.6
135°	147.5	154.1	160.7	162.3	180.5	204.8	217.0	236.6	276.0	305.4	310.0
137.5°	154.4	160.9	167.3	169.0	184.9	206.1	216.7	233.3	266.6	291.5	295.2
140°	160.0	166.0	172.0	173.5	187.6	206.3	215.6	229.9	258.7	280.2	283.7
142.5°	164.3	169.9	175.5	176.8	189.7	207.0	215.6	228.2	253.5	272.4	275.4
145°	171.0	175.9	180.7	182.0	192.7	207.0	214.1	224.4	245.1	260.6	262.8
147.5°	177.7	182.5	187.2	188.4	197.0	208.4	214.1	222.3	238.5	250.7	252.5
150°	182.1	186.3	190.7	191.8	199.2	209.2	214.1	221.0	234.7	245.0	246.5
152.5°	186.6	189.8	193.1	193.9	200.7	209.7	214.1	220.0	231.7	240.5	241.7
155°	193.3	195.7	198.2	198.7	203.9	210.8	214.1	218.8	228.1	235.1	235.9
157.5°	198.3	200.6	202.9	203.5	207.1	211.8	214.1	217.7	225.0	230.4	231.0
160°	201.6	203.5	205.2	205.7	208.5	212.3	214.1	217.2	223.5	228.1	228.4
162.5°	204.9	206.3	207.7	208.0	210.1	212.8	214.1	216.8	222.0	226.0	226.3
165°	208.6	209.8	211.0	211.3	212.3	213.6	214.1	216.0	219.8	222.6	222.9
167.5°	211.9	212.5	213.1	213.3	214.1	215.1	215.6	216.9	219.3	221.1	221.2
170°	214.1	214.7	215.3	215.4	215.5	215.6	215.6	216.9	219.3	221.1	221.1
172.5°	215.3	215.4	215.6	215.6	215.6	215.6	215.6	216.6	218.5	220.0	219.9
175°	217.0	217.0	217.0	217.0	216.5	215.9	215.6	216.2	217.4	218.4	218.4
177.5°	217.0	217.0	217.0	217.0	216.6	216.1	215.9	216.4	217.3	218.1	218.0
180°	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0

TEST NUMBER: P933889

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3
2.5°	1056.7	1053.8	1056.7	1054.8	1055.7	1052.8	1044.0	1041.1	1044.0	1046.9	1046.9
5°	1069.4	1067.4	1069.4	1069.4	1068.4	1066.4	1056.7	1054.8	1056.7	1057.7	1055.7
7.5°	1073.3	1070.4	1073.3	1071.3	1071.3	1069.4	1059.6	1057.7	1058.6	1061.5	1058.6
10°	1073.3	1070.4	1073.3	1072.3	1071.3	1069.4	1059.6	1055.7	1055.7	1058.6	1055.7
12.5°	1068.4	1066.4	1068.4	1066.4	1066.4	1064.4	1054.8	1050.8	1051.8	1052.8	1048.8
15°	1060.6	1057.7	1060.6	1058.6	1059.6	1056.7	1045.9	1042.1	1042.1	1044.0	1037.2
17.5°	1048.8	1045.0	1048.8	1047.9	1046.9	1045.0	1035.2	1031.3	1030.3	1031.3	1026.5
20°	1035.2	1032.3	1035.2	1034.2	1034.2	1030.3	1020.6	1015.7	1015.7	1015.7	1010.9
22.5°	1013.8	1010.9	1013.8	1015.7	1015.7	1014.7	1006.0	999.1	997.2	997.2	991.4
25°	989.4	986.5	989.4	989.4	988.5	989.4	986.5	982.6	979.7	976.8	970.9
27.5°	966.0	964.1	966.0	964.1	966.0	963.1	962.1	961.2	957.3	954.4	946.5
30°	942.6	940.7	942.6	940.7	938.8	936.7	931.9	929.9	933.8	931.9	919.2
32.5°	913.4	911.4	913.4	913.4	911.4	911.4	903.6	900.7	901.7	907.6	895.8
35°	883.1	880.2	883.1	882.2	883.1	880.2	875.4	874.4	870.5	877.3	868.5
37.5°	848.1	845.2	848.1	848.1	848.1	850.0	846.1	843.2	837.3	846.1	839.3
40°	812.0	808.1	812.0	811.1	812.0	814.0	812.0	810.1	804.2	811.1	805.1
42.5°	771.0	770.1	771.0	772.0	772.0	776.0	778.9	775.0	773.0	768.1	772.0
45°	727.2	725.2	727.2	729.2	730.1	732.1	740.8	740.8	737.9	730.1	736.0
47.5°	680.4	675.5	680.4	686.2	686.2	689.2	698.0	704.8	699.9	690.1	693.1
50°	630.7	631.7	630.7	634.6	634.6	645.4	652.1	658.9	663.9	652.1	638.5
52.5°	582.0	581.0	582.0	584.9	588.8	593.6	605.3	612.2	620.0	613.2	591.7
55°	533.2	535.2	533.2	534.2	536.1	539.1	556.6	563.5	578.0	569.3	546.9
57.5°	484.5	481.6	484.5	486.4	487.4	490.3	504.9	517.6	526.4	527.3	500.1
60°	427.9	424.0	427.9	436.7	438.7	440.6	454.3	466.0	473.7	476.7	448.5
62.5°	378.2	371.4	378.2	384.1	388.0	392.8	402.6	420.2	426.9	427.9	388.0
65°	325.6	322.7	325.6	337.3	338.3	344.1	354.8	367.5	382.1	380.1	322.7
67.5°	277.8	277.8	277.8	285.7	291.5	294.4	308.0	313.9	332.4	334.4	269.1
70°	233.9	232.9	233.9	239.8	243.7	250.5	263.2	270.1	284.6	289.5	218.3
72.5°	192.1	191.1	192.1	196.9	200.8	206.7	217.3	225.2	237.9	243.7	169.6
75°	155.0	153.0	155.0	158.9	157.9	165.7	174.5	182.3	194.0	197.9	125.8
77.5°	118.9	118.9	118.9	122.9	122.9	130.6	134.5	144.3	151.1	157.0	92.6
80°	88.7	87.7	88.7	89.7	89.7	93.6	100.4	107.3	113.1	113.1	63.4
82.5°	62.4	60.5	62.4	62.4	62.4	64.3	68.2	70.2	74.1	77.0	39.9
85°	39.0	39.0	39.0	39.9	39.0	41.0	42.0	43.9	43.9	42.0	24.3
87.5°	25.4	24.3	25.4	24.3	24.3	23.4	23.4	23.4	22.4	21.4	13.7
90°	5.5	5.5	5.5	5.5	5.5	7.4	9.8	11.0	9.5	6.4	4.1
92.5°	22.1	17.7	22.1	26.6	27.6	39.1	54.6	62.3	54.7	39.5	28.1
95°	77.2	64.0	77.2	90.6	93.9	123.3	162.5	182.1	153.8	97.2	54.7
97.5°	185.1	159.7	185.1	210.5	216.8	235.4	260.1	272.5	225.3	130.9	60.1
100°	266.7	236.4	266.7	296.8	304.4	303.0	301.2	300.3	248.0	143.2	64.6
102.5°	346.9	321.0	346.9	372.8	379.3	355.5	323.9	308.1	255.0	148.8	69.2
105°	449.2	435.3	449.2	463.1	466.6	413.5	342.6	307.3	255.8	153.0	75.9
107.5°	516.2	519.6	516.2	512.9	512.0	438.0	339.2	289.8	244.5	153.8	85.8
110°	541.8	556.3	541.8	527.2	523.6	440.9	330.5	275.3	234.4	152.6	91.3

TEST NUMBER: P933889

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	544.0	566.3	544.0	521.7	516.2	431.5	318.5	262.0	225.6	152.6	98.0
115°	529.6	560.5	529.6	498.7	491.0	409.4	300.6	246.1	215.4	154.1	108.0
117.5°	499.0	533.2	499.0	464.7	456.2	382.6	284.4	235.3	209.1	156.9	117.7
120°	474.4	507.7	474.4	441.2	432.9	365.5	275.8	230.9	207.1	159.3	123.5
122.5°	450.4	483.1	450.4	417.6	409.4	348.7	267.9	227.5	205.9	162.6	130.1
125°	416.1	446.3	416.1	386.0	378.4	326.9	258.2	223.9	205.0	167.2	138.8
127.5°	385.4	410.9	385.4	359.9	353.5	309.3	250.3	220.8	204.5	171.6	147.0
130°	367.2	390.7	367.2	343.6	337.7	298.4	245.9	219.7	204.7	174.9	152.5
132.5°	350.7	371.8	350.7	329.6	324.3	289.1	242.2	218.7	205.0	177.6	157.1
135°	328.1	346.3	328.1	310.0	305.4	276.0	236.6	217.0	204.8	180.5	162.3
137.5°	310.1	324.9	310.1	295.2	291.5	266.6	233.3	216.7	206.1	184.9	169.0
140°	297.6	311.5	297.6	283.7	280.2	258.7	229.9	215.6	206.3	187.6	173.5
142.5°	287.3	299.3	287.3	275.4	272.4	253.5	228.2	215.6	207.0	189.7	176.8
145°	271.9	281.0	271.9	262.8	260.6	245.1	224.4	214.1	207.0	192.7	182.0
147.5°	260.1	267.5	260.1	252.5	250.7	238.5	222.3	214.1	208.4	197.0	188.4
150°	252.6	258.7	252.6	246.5	245.0	234.7	221.0	214.1	209.2	199.2	191.8
152.5°	246.2	250.9	246.2	241.7	240.5	231.7	220.0	214.1	209.7	200.7	193.9
155°	238.9	242.0	238.9	235.9	235.1	228.1	218.8	214.1	210.8	203.9	198.7
157.5°	233.1	235.3	233.1	231.0	230.4	225.0	217.7	214.1	211.8	207.1	203.5
160°	229.7	230.9	229.7	228.4	228.1	223.5	217.2	214.1	212.3	208.5	205.7
162.5°	227.4	228.6	227.4	226.3	226.0	222.0	216.8	214.1	212.8	210.1	208.0
165°	224.1	225.4	224.1	222.9	222.6	219.8	216.0	214.1	213.6	212.3	211.3
167.5°	221.8	222.3	221.8	221.2	221.1	219.3	216.9	215.6	215.1	214.1	213.3
170°	221.1	221.1	221.1	221.1	221.1	219.3	216.9	215.6	215.6	215.5	215.4
172.5°	219.4	219.0	219.4	219.9	220.0	218.5	216.6	215.6	215.6	215.6	215.6
175°	218.4	218.4	218.4	218.4	218.4	217.4	216.2	215.6	215.9	216.5	217.0
177.5°	217.4	217.0	217.4	218.0	218.1	217.3	216.4	215.9	216.1	216.6	217.0
180°	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0

TEST NUMBER: P933889

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3
2.5°	1045.0	1039.2	1039.2	1029.4	1025.5	1022.6	1017.6	1003.1	999.1	995.3	1001.1
5°	1053.8	1043.0	1035.2	1017.6	1003.1	997.2	978.7	943.6	920.2	902.6	892.9
7.5°	1055.7	1042.1	1027.4	1000.1	965.0	949.4	892.9	828.6	811.1	795.5	785.7
10°	1053.8	1038.2	1017.6	976.8	893.9	866.6	810.1	768.1	757.4	754.5	757.4
12.5°	1046.9	1032.3	1004.1	935.8	819.8	801.3	768.1	743.8	741.8	746.7	773.0
15°	1035.2	1021.6	988.5	881.2	778.9	765.2	741.8	733.0	743.8	777.9	856.9
17.5°	1023.6	1008.0	967.0	827.6	747.7	737.9	721.3	738.9	799.3	845.2	871.4
20°	1008.0	989.4	942.6	788.6	725.2	716.5	708.6	787.6	833.4	850.0	864.6
22.5°	989.4	969.9	909.5	761.3	701.8	695.1	699.9	814.9	833.4	845.2	857.9
25°	965.0	948.5	870.5	739.8	683.3	675.5	694.1	812.0	822.7	825.7	851.0
27.5°	942.6	921.1	829.6	720.4	661.0	658.0	698.9	799.3	807.2	810.1	837.3
30°	915.3	883.1	783.7	699.9	637.5	636.5	699.9	783.7	781.8	789.5	816.9
32.5°	887.0	826.7	732.1	674.5	615.1	614.2	693.1	760.4	758.4	769.1	789.5
35°	860.8	782.8	661.9	645.4	586.8	587.8	676.5	733.0	734.0	743.8	756.4
37.5°	833.4	744.8	584.9	613.2	559.5	559.5	654.1	707.7	705.7	708.6	726.3
40°	801.3	685.3	516.7	571.2	534.2	531.3	626.7	680.4	673.6	672.6	697.0
42.5°	767.2	620.0	466.0	515.7	504.9	501.1	593.6	647.3	634.6	637.5	668.7
45°	730.1	602.4	426.9	435.8	474.7	471.8	557.6	609.2	600.5	608.2	640.4
47.5°	693.1	567.3	414.2	361.6	442.5	441.6	517.6	572.2	567.3	575.1	609.2
50°	642.4	528.3	413.3	310.0	406.5	410.4	469.9	536.1	536.1	542.9	579.1
52.5°	577.0	480.5	375.3	280.7	364.5	376.3	427.9	504.9	506.9	513.8	545.8
55°	517.6	430.8	348.0	258.3	314.8	340.2	387.0	472.8	476.7	483.5	512.7
57.5°	463.0	358.7	342.2	232.0	269.1	293.4	351.0	441.6	443.5	449.4	477.6
60°	404.6	259.3	313.9	203.7	229.1	247.6	317.7	404.6	411.3	415.2	439.6
62.5°	338.3	188.2	284.6	184.2	209.6	213.5	290.5	369.5	378.2	381.1	395.7
65°	240.8	157.9	241.8	167.6	189.1	190.1	261.2	333.3	341.2	346.0	356.8
67.5°	162.8	128.7	184.2	152.0	173.5	174.5	232.9	291.5	302.2	306.1	312.9
70°	113.1	85.8	136.4	135.5	156.0	157.9	202.7	253.5	263.2	266.1	270.1
72.5°	82.8	69.2	113.1	121.8	137.4	139.4	171.6	210.6	220.4	223.3	225.2
75°	63.4	73.1	91.7	106.3	117.0	117.9	140.4	171.6	178.4	180.3	181.3
77.5°	50.7	68.2	67.2	85.8	95.5	93.6	110.2	132.6	138.4	138.4	138.4
80°	38.0	53.6	50.7	61.4	70.2	68.2	79.0	94.6	96.5	98.5	97.5
82.5°	28.3	34.1	34.1	39.0	46.8	44.9	52.6	61.4	61.4	61.4	63.4
85°	17.5	19.5	15.6	20.4	26.4	25.4	29.3	33.1	34.1	34.1	32.2
87.5°	10.8	8.8	4.8	7.8	11.7	11.7	13.7	14.6	13.7	13.7	13.7
90°	3.8	2.6	1.5	2.6	3.8	4.1	6.4	9.5	11.0	9.8	7.4
92.5°	25.6	15.7	5.8	15.7	25.6	28.1	39.5	54.7	62.3	54.6	39.1
95°	50.2	32.1	14.0	32.1	50.2	54.7	97.2	153.8	182.1	162.5	123.3
97.5°	56.1	40.1	24.1	40.1	56.1	60.1	130.9	225.3	272.5	260.1	235.4
100°	61.0	46.5	32.1	46.5	61.0	64.6	143.2	248.0	300.3	301.2	303.0
102.5°	65.8	52.3	38.8	52.3	65.8	69.2	148.8	255.0	308.1	323.9	355.5
105°	73.0	61.5	50.1	61.5	73.0	75.9	153.0	255.8	307.3	342.6	413.5
107.5°	83.0	72.4	61.7	72.4	83.0	85.8	153.8	244.5	289.8	339.2	438.0
110°	88.9	79.3	69.6	79.3	88.9	91.3	152.6	234.4	275.3	330.5	440.9

TEST NUMBER: P933889

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	95.6	86.5	77.3	86.5	95.6	98.0	152.6	225.6	262.0	318.5	431.5
115°	105.9	97.5	89.0	97.5	105.9	108.0	154.1	215.4	246.1	300.6	409.4
117.5°	115.8	108.1	100.5	108.1	115.8	117.7	156.9	209.1	235.3	284.4	382.6
120°	121.6	114.4	107.2	114.4	121.6	123.5	159.3	207.1	230.9	275.8	365.5
122.5°	128.3	121.0	113.7	121.0	128.3	130.1	162.6	205.9	227.5	267.9	348.7
125°	137.1	130.4	123.7	130.4	137.1	138.8	167.2	205.0	223.9	258.2	326.9
127.5°	145.4	138.6	131.9	138.6	145.4	147.0	171.6	204.5	220.8	250.3	309.3
130°	150.7	143.5	136.2	143.5	150.7	152.5	174.9	204.7	219.7	245.9	298.4
132.5°	155.2	148.1	140.8	148.1	155.2	157.1	177.6	205.0	218.7	242.2	289.1
135°	160.7	154.1	147.5	154.1	160.7	162.3	180.5	204.8	217.0	236.6	276.0
137.5°	167.3	160.9	154.4	160.9	167.3	169.0	184.9	206.1	216.7	233.3	266.6
140°	172.0	166.0	160.0	166.0	172.0	173.5	187.6	206.3	215.6	229.9	258.7
142.5°	175.5	169.9	164.3	169.9	175.5	176.8	189.7	207.0	215.6	228.2	253.5
145°	180.7	175.9	171.0	175.9	180.7	182.0	192.7	207.0	214.1	224.4	245.1
147.5°	187.2	182.5	177.7	182.5	187.2	188.4	197.0	208.4	214.1	222.3	238.5
150°	190.7	186.3	182.1	186.3	190.7	191.8	199.2	209.2	214.1	221.0	234.7
152.5°	193.1	189.8	186.6	189.8	193.1	193.9	200.7	209.7	214.1	220.0	231.7
155°	198.2	195.7	193.3	195.7	198.2	198.7	203.9	210.8	214.1	218.8	228.1
157.5°	202.9	200.6	198.3	200.6	202.9	203.5	207.1	211.8	214.1	217.7	225.0
160°	205.2	203.5	201.6	203.5	205.2	205.7	208.5	212.3	214.1	217.2	223.5
162.5°	207.7	206.3	204.9	206.3	207.7	208.0	210.1	212.8	214.1	216.8	222.0
165°	211.0	209.8	208.6	209.8	211.0	211.3	212.3	213.6	214.1	216.0	219.8
167.5°	213.1	212.5	211.9	212.5	213.1	213.3	214.1	215.1	215.6	216.9	219.3
170°	215.3	214.7	214.1	214.7	215.3	215.4	215.5	215.6	215.6	216.9	219.3
172.5°	215.6	215.4	215.3	215.4	215.6	215.6	215.6	215.6	215.6	216.6	218.5
175°	217.0	217.0	217.0	217.0	217.0	217.0	216.5	215.9	215.6	216.2	217.4
177.5°	217.0	217.0	217.0	217.0	217.0	217.0	216.6	216.1	215.9	216.4	217.3
180°	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0

TEST NUMBER: P933889

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3	1030.3
2.5°	994.3	991.4	995.3	984.5	995.3	991.4	994.3	1001.1	995.3	999.1	1003.1
5°	872.5	867.5	851.9	839.3	851.9	867.5	872.5	892.9	902.6	920.2	943.6
7.5°	779.9	776.0	772.0	764.3	772.0	776.0	779.9	785.7	795.5	811.1	828.6
10°	759.4	760.4	766.2	765.2	766.2	760.4	759.4	757.4	754.5	757.4	768.1
12.5°	812.0	820.7	852.9	851.0	852.9	820.7	812.0	773.0	746.7	741.8	743.8
15°	872.5	875.4	882.2	883.1	882.2	875.4	872.5	856.9	777.9	743.8	733.0
17.5°	878.3	879.3	884.1	884.1	884.1	879.3	878.3	871.4	845.2	799.3	738.9
20°	873.5	875.4	885.1	887.0	885.1	875.4	873.5	864.6	850.0	833.4	787.6
22.5°	871.4	875.4	883.1	882.2	883.1	875.4	871.4	857.9	845.2	833.4	814.9
25°	861.7	861.7	862.7	863.7	862.7	861.7	861.7	851.0	825.7	822.7	812.0
27.5°	841.3	843.2	849.0	848.1	849.0	843.2	841.3	837.3	810.1	807.2	799.3
30°	822.7	820.7	815.9	812.0	815.9	820.7	822.7	816.9	789.5	781.8	783.7
32.5°	791.6	786.6	781.8	778.9	781.8	786.6	791.6	789.5	769.1	758.4	760.4
35°	754.5	755.4	754.5	751.6	754.5	755.4	754.5	756.4	743.8	734.0	733.0
37.5°	728.2	730.1	729.2	725.2	729.2	730.1	728.2	726.3	708.6	705.7	707.7
40°	700.9	701.8	700.9	698.0	700.9	701.8	700.9	697.0	672.6	673.6	680.4
42.5°	674.5	673.6	670.6	668.7	670.6	673.6	674.5	668.7	637.5	634.6	647.3
45°	644.4	645.4	639.4	636.5	639.4	645.4	644.4	640.4	608.2	600.5	609.2
47.5°	614.2	614.2	609.2	606.3	609.2	614.2	614.2	609.2	575.1	567.3	572.2
50°	582.0	581.0	574.1	573.2	574.1	581.0	582.0	579.1	542.9	536.1	536.1
52.5°	544.9	544.9	545.8	547.9	545.8	544.9	544.9	545.8	513.8	506.9	504.9
55°	512.7	513.8	520.5	522.5	520.5	513.8	512.7	512.7	483.5	476.7	472.8
57.5°	479.6	479.6	484.5	484.5	484.5	479.6	479.6	477.6	449.4	443.5	441.6
60°	441.6	443.5	447.4	446.4	447.4	443.5	441.6	439.6	415.2	411.3	404.6
62.5°	401.7	403.6	404.6	402.6	404.6	403.6	401.7	395.7	381.1	378.2	369.5
65°	359.7	361.6	362.6	360.7	362.6	361.6	359.7	356.8	346.0	341.2	333.3
67.5°	316.8	315.8	314.8	318.8	314.8	315.8	316.8	312.9	306.1	302.2	291.5
70°	273.0	273.0	272.0	273.9	272.0	273.0	273.0	270.1	266.1	263.2	253.5
72.5°	226.2	225.2	229.1	226.2	229.1	225.2	226.2	225.2	223.3	220.4	210.6
75°	180.3	182.3	180.3	183.2	180.3	182.3	180.3	181.3	180.3	178.4	171.6
77.5°	137.4	139.4	137.4	137.4	137.4	139.4	137.4	138.4	138.4	138.4	132.6
80°	97.5	96.5	96.5	95.5	96.5	96.5	97.5	97.5	98.5	96.5	94.6
82.5°	62.4	61.4	61.4	63.4	61.4	61.4	62.4	63.4	61.4	61.4	61.4
85°	34.1	35.1	33.1	33.1	33.1	35.1	34.1	32.2	34.1	34.1	33.1
87.5°	12.7	11.7	11.7	11.7	11.7	11.7	12.7	13.7	13.7	13.7	14.6
90°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	7.4	9.8	11.0	9.5
92.5°	27.6	26.6	22.1	17.7	22.1	26.6	27.6	39.1	54.6	62.3	54.7
95°	93.9	90.6	77.2	64.0	77.2	90.6	93.9	123.3	162.5	182.1	153.8
97.5°	216.8	210.5	185.1	159.7	185.1	210.5	216.8	235.4	260.1	272.5	225.3
100°	304.4	296.8	266.7	236.4	266.7	296.8	304.4	303.0	301.2	300.3	248.0
102.5°	379.3	372.8	346.9	321.0	346.9	372.8	379.3	355.5	323.9	308.1	255.0
105°	466.6	463.1	449.2	435.3	449.2	463.1	466.6	413.5	342.6	307.3	255.8
107.5°	512.0	512.9	516.2	519.6	516.2	512.9	512.0	438.0	339.2	289.8	244.5
110°	523.6	527.2	541.8	556.3	541.8	527.2	523.6	440.9	330.5	275.3	234.4

TEST NUMBER: P933889

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	516.2	521.7	544.0	566.3	544.0	521.7	516.2	431.5	318.5	262.0	225.6
115°	491.0	498.7	529.6	560.5	529.6	498.7	491.0	409.4	300.6	246.1	215.4
117.5°	456.2	464.7	499.0	533.2	499.0	464.7	456.2	382.6	284.4	235.3	209.1
120°	432.9	441.2	474.4	507.7	474.4	441.2	432.9	365.5	275.8	230.9	207.1
122.5°	409.4	417.6	450.4	483.1	450.4	417.6	409.4	348.7	267.9	227.5	205.9
125°	378.4	386.0	416.1	446.3	416.1	386.0	378.4	326.9	258.2	223.9	205.0
127.5°	353.5	359.9	385.4	410.9	385.4	359.9	353.5	309.3	250.3	220.8	204.5
130°	337.7	343.6	367.2	390.7	367.2	343.6	337.7	298.4	245.9	219.7	204.7
132.5°	324.3	329.6	350.7	371.8	350.7	329.6	324.3	289.1	242.2	218.7	205.0
135°	305.4	310.0	328.1	346.3	328.1	310.0	305.4	276.0	236.6	217.0	204.8
137.5°	291.5	295.2	310.1	324.9	310.1	295.2	291.5	266.6	233.3	216.7	206.1
140°	280.2	283.7	297.6	311.5	297.6	283.7	280.2	258.7	229.9	215.6	206.3
142.5°	272.4	275.4	287.3	299.3	287.3	275.4	272.4	253.5	228.2	215.6	207.0
145°	260.6	262.8	271.9	281.0	271.9	262.8	260.6	245.1	224.4	214.1	207.0
147.5°	250.7	252.5	260.1	267.5	260.1	252.5	250.7	238.5	222.3	214.1	208.4
150°	245.0	246.5	252.6	258.7	252.6	246.5	245.0	234.7	221.0	214.1	209.2
152.5°	240.5	241.7	246.2	250.9	246.2	241.7	240.5	231.7	220.0	214.1	209.7
155°	235.1	235.9	238.9	242.0	238.9	235.9	235.1	228.1	218.8	214.1	210.8
157.5°	230.4	231.0	233.1	235.3	233.1	231.0	230.4	225.0	217.7	214.1	211.8
160°	228.1	228.4	229.7	230.9	229.7	228.4	228.1	223.5	217.2	214.1	212.3
162.5°	226.0	226.3	227.4	228.6	227.4	226.3	226.0	222.0	216.8	214.1	212.8
165°	222.6	222.9	224.1	225.4	224.1	222.9	222.6	219.8	216.0	214.1	213.6
167.5°	221.1	221.2	221.8	222.3	221.8	221.2	221.1	219.3	216.9	215.6	215.1
170°	221.1	221.1	221.1	221.1	221.1	221.1	221.1	219.3	216.9	215.6	215.6
172.5°	220.0	219.9	219.4	219.0	219.4	219.9	220.0	218.5	216.6	215.6	215.6
175°	218.4	218.4	218.4	218.4	218.4	218.4	218.4	217.4	216.2	215.6	215.9
177.5°	218.1	218.0	217.4	217.0	217.4	218.0	218.1	217.3	216.4	215.9	216.1
180°	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0

TEST NUMBER: P933889

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1030.3	1030.3	1030.3	1030.3	1030.3
2.5°	1017.6	1022.6	1025.5	1029.4	1039.2
5°	978.7	997.2	1003.1	1017.6	1035.2
7.5°	892.9	949.4	965.0	1000.1	1027.4
10°	810.1	866.6	893.9	976.8	1017.6
12.5°	768.1	801.3	819.8	935.8	1004.1
15°	741.8	765.2	778.9	881.2	988.5
17.5°	721.3	737.9	747.7	827.6	967.0
20°	708.6	716.5	725.2	788.6	942.6
22.5°	699.9	695.1	701.8	761.3	909.5
25°	694.1	675.5	683.3	739.8	870.5
27.5°	698.9	658.0	661.0	720.4	829.6
30°	699.9	636.5	637.5	699.9	783.7
32.5°	693.1	614.2	615.1	674.5	732.1
35°	676.5	587.8	586.8	645.4	661.9
37.5°	654.1	559.5	559.5	613.2	584.9
40°	626.7	531.3	534.2	571.2	516.7
42.5°	593.6	501.1	504.9	515.7	466.0
45°	557.6	471.8	474.7	435.8	426.9
47.5°	517.6	441.6	442.5	361.6	414.2
50°	469.9	410.4	406.5	310.0	413.3
52.5°	427.9	376.3	364.5	280.7	375.3
55°	387.0	340.2	314.8	258.3	348.0
57.5°	351.0	293.4	269.1	232.0	342.2
60°	317.7	247.6	229.1	203.7	313.9
62.5°	290.5	213.5	209.6	184.2	284.6
65°	261.2	190.1	189.1	167.6	241.8
67.5°	232.9	174.5	173.5	152.0	184.2
70°	202.7	157.9	156.0	135.5	136.4
72.5°	171.6	139.4	137.4	121.8	113.1
75°	140.4	117.9	117.0	106.3	91.7
77.5°	110.2	93.6	95.5	85.8	67.2
80°	79.0	68.2	70.2	61.4	50.7
82.5°	52.6	44.9	46.8	39.0	34.1
85°	29.3	25.4	26.4	20.4	15.6
87.5°	13.7	11.7	11.7	7.8	4.8
90°	6.4	4.1	3.8	2.6	1.5
92.5°	39.5	28.1	25.6	15.7	5.8
95°	97.2	54.7	50.2	32.1	14.0
97.5°	130.9	60.1	56.1	40.1	24.1
100°	143.2	64.6	61.0	46.5	32.1
102.5°	148.8	69.2	65.8	52.3	38.8
105°	153.0	75.9	73.0	61.5	50.1
107.5°	153.8	85.8	83.0	72.4	61.7
110°	152.6	91.3	88.9	79.3	69.6



TEST NUMBER: P933889

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-6-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	152.6	98.0	95.6	86.5	77.3
115°	154.1	108.0	105.9	97.5	89.0
117.5°	156.9	117.7	115.8	108.1	100.5
120°	159.3	123.5	121.6	114.4	107.2
122.5°	162.6	130.1	128.3	121.0	113.7
125°	167.2	138.8	137.1	130.4	123.7
127.5°	171.6	147.0	145.4	138.6	131.9
130°	174.9	152.5	150.7	143.5	136.2
132.5°	177.6	157.1	155.2	148.1	140.8
135°	180.5	162.3	160.7	154.1	147.5
137.5°	184.9	169.0	167.3	160.9	154.4
140°	187.6	173.5	172.0	166.0	160.0
142.5°	189.7	176.8	175.5	169.9	164.3
145°	192.7	182.0	180.7	175.9	171.0
147.5°	197.0	188.4	187.2	182.5	177.7
150°	199.2	191.8	190.7	186.3	182.1
152.5°	200.7	193.9	193.1	189.8	186.6
155°	203.9	198.7	198.2	195.7	193.3
157.5°	207.1	203.5	202.9	200.6	198.3
160°	208.5	205.7	205.2	203.5	201.6
162.5°	210.1	208.0	207.7	206.3	204.9
165°	212.3	211.3	211.0	209.8	208.6
167.5°	214.1	213.3	213.1	212.5	211.9
170°	215.5	215.4	215.3	214.7	214.1
172.5°	215.6	215.6	215.6	215.4	215.3
175°	216.5	217.0	217.0	217.0	217.0
177.5°	216.6	217.0	217.0	217.0	217.0
180°	217.0	217.0	217.0	217.0	217.0

TEST NUMBER: P933889

CATALOG NUMBER: SQ4-FA-025U-050D-B2750-1D-UNV-W2A-W-6-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.56	13.58	13.37	14.41	15.44	15.38	16.40	16.19	17.24	18.27
	3H	13.05	13.96	13.87	14.81	15.87	16.74	17.65	17.56	18.50	19.56
	4H	13.25	14.11	14.09	14.96	16.03	17.19	18.05	18.03	18.91	19.97
	6H	13.37	14.17	14.23	15.03	16.11	17.48	18.28	18.33	19.14	20.22
	8H	13.38	14.14	14.24	15.02	16.10	17.56	18.32	18.42	19.20	20.28
	12H	13.36	14.08	14.22	14.95	16.06	17.60	18.33	18.47	19.20	20.31
4H	2H	13.61	14.47	14.46	15.33	16.40	15.81	16.68	16.66	17.53	18.60
	3H	14.65	15.37	15.51	16.26	17.34	17.33	18.05	18.19	18.94	20.02
	4H	14.93	15.59	15.80	16.47	17.58	17.86	18.52	18.73	19.40	20.51
	6H	15.07	15.64	15.95	16.54	17.66	18.24	18.80	19.12	19.71	20.82
	8H	15.08	15.61	15.97	16.51	17.64	18.35	18.88	19.24	19.78	20.91
	12H	15.05	15.53	15.96	16.45	17.58	18.41	18.89	19.32	19.81	20.94
8H	4H	15.40	15.93	16.29	16.83	17.96	18.00	18.53	18.89	19.43	20.56
	6H	15.67	16.11	16.58	17.05	18.18	18.44	18.88	19.36	19.82	20.95
	8H	15.71	16.10	16.64	17.03	18.18	18.60	18.98	19.52	19.92	21.06
	12H	15.70	16.05	16.63	16.97	18.17	18.70	19.04	19.63	19.97	21.17
12H	4H	15.41	15.89	16.32	16.81	17.94	17.97	18.45	18.88	19.37	20.50
	6H	15.73	16.12	16.66	17.05	18.20	18.44	18.83	19.37	19.76	20.91
	8H	15.80	16.15	16.73	17.07	18.27	18.61	18.95	19.54	19.88	21.08

END OF REPORT