

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P933984

Luminaire Tested: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-4-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P933984
REPORT IS A COMBINATION OF REPORTS P933678 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-4-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3593.9 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 30
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P933984

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-4-3500K

Luminous Intensity Polar Plot



TEST NUMBER: P933984

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-4-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	74		
1	103	99	95	91	98	94	90	87	85	82	80	77	75	73	69	68	66	62		
2	94	86	80	75	89	82	77	72	75	70	66	68	64	61	61	58	56	52		
3	86	76	68	62	81	72	66	60	66	60	56	60	55	52	54	51	48	44		
4	79	67	59	53	74	64	57	51	59	52	48	53	48	44	48	44	41	38		
5	72	60	52	45	68	57	50	44	52	46	41	48	43	38	43	39	36	33		
6	67	54	46	39	63	52	44	38	47	41	36	43	38	34	39	35	31	29		
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	26		
8	57	44	36	31	54	43	35	30	39	33	28	36	31	27	33	28	25	23		
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	23	21		
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9505	9505	9505	9505
5°	9566	9595	9566	7545
10°	9491	9453	9491	6758
15°	9378	9248	9378	7721
20°	9170	9004	9170	7737
25°	8758	8650	8758	7573
30°	8230	8357	8230	7214
35°	7325	7985	7325	6818
40°	6095	7548	6095	6519
45°	5435	7036	5435	6176
50°	5762	6425	5762	5831
55°	5405	5768	5405	5631
60°	5550	4899	5550	5158
65°	5008	4048	5008	4526
70°	3445	3227	3445	3794
75°	2987	2384	2987	2856
80°	2359	1577	2359	1718
85°	1283	836	1283	709

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 8346 cd/sqm

TEST NUMBER: P933984

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-4-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.5	2.6
10°-20°	262.5	7.3
20°-30°	405.8	11.3
30°-40°	484.5	13.5
40°-50°	487.3	13.6
50°-60°	424.0	11.8
60°-70°	300.6	8.4
70°-80°	159.0	4.4
80°-90°	40.2	1.1
90°-100°	70.5	2.0
100°-110°	185.3	5.2
110°-120°	192.2	5.3
120°-130°	154.1	4.3
130°-140°	120.9	3.4
140°-150°	92.8	2.6
150°-160°	66.8	1.9
160°-170°	40.9	1.1
170°-180°	13.8	0.4
0°-30°	760.8	21.2
0°-40°	1245.3	34.7
0°-60°	2156.7	60.0
0°-90°	2656.5	73.9
90°-120°	448.0	12.5
90°-150°	815.9	22.7
90°-180°	937.0	26.1
0°-180°	3593.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1024	1024	1024	1024	1024	
5°	1029	1061	1029	834	1029	98
15°	983	1052	983	878	983	276
25°	865	981	865	859	865	397
35°	658	875	658	747	658	407
45°	424	721	424	633	424	340
55°	346	532	346	520	346	318
65°	240	321	240	359	240	230
75°	91	152	91	182	91	96
85°	16	39	16	33	16	21
90°	1	4	1	4	1	1
95°	9	43	9	43	9	10
105°	33	290	33	290	33	35
115°	59	374	59	374	59	59
125°	82	298	82	298	82	73
135°	98	231	98	231	98	76
145°	114	187	114	187	114	71
155°	129	161	129	161	129	59
165°	139	150	139	150	139	39
175°	145	146	145	146	145	14
180°	145	145	145	145	145	

TEST NUMBER: P933984

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3
2.5°	1033.1	1033.1	1039.0	1040.9	1040.9	1038.0	1035.1	1038.0	1046.7	1049.6	1048.7
5°	1029.2	1037.0	1047.7	1049.6	1051.6	1050.6	1048.7	1050.6	1060.3	1062.2	1063.2
7.5°	1021.4	1036.1	1049.6	1052.5	1055.4	1052.5	1051.6	1053.5	1063.2	1065.1	1065.1
10°	1011.7	1032.1	1047.7	1049.6	1052.5	1049.6	1049.6	1053.5	1063.2	1065.1	1066.1
12.5°	998.2	1026.3	1040.9	1042.8	1046.7	1045.7	1044.8	1048.7	1058.3	1060.3	1060.3
15°	982.7	1015.6	1029.2	1031.1	1038.0	1036.1	1036.1	1039.9	1050.6	1053.5	1052.5
17.5°	961.3	1002.0	1017.5	1020.5	1025.3	1024.3	1025.3	1029.2	1039.0	1040.9	1041.9
20°	937.1	983.6	1002.0	1004.9	1009.8	1009.8	1009.8	1014.6	1024.3	1028.2	1028.2
22.5°	904.2	964.3	983.6	985.6	991.4	991.4	993.3	1000.1	1008.8	1009.8	1009.8
25°	865.4	942.9	959.4	965.2	971.0	973.9	976.8	980.7	983.6	982.7	983.6
27.5°	824.7	915.8	937.1	941.0	948.7	951.7	955.5	956.5	957.5	960.4	958.4
30°	779.2	878.0	910.0	913.9	926.5	928.4	924.5	926.5	931.3	933.2	935.2
32.5°	727.8	821.8	881.9	890.6	902.2	896.4	895.5	898.4	906.1	906.1	908.0
35°	658.0	778.2	855.7	863.5	872.2	865.4	869.3	870.3	875.1	878.0	877.0
37.5°	581.5	740.4	828.6	834.4	841.2	832.5	838.3	841.2	845.1	843.1	843.1
40°	513.7	681.3	796.6	800.5	806.3	799.5	805.3	807.3	809.2	807.3	806.3
42.5°	463.3	616.4	762.7	767.5	763.7	768.5	770.5	774.3	771.4	767.5	767.5
45°	424.5	598.9	725.9	731.7	725.9	733.6	736.5	736.5	727.8	725.9	724.9
47.5°	411.9	564.1	689.1	689.1	686.1	695.8	700.7	693.9	685.2	682.3	682.3
50°	411.0	525.3	638.7	634.8	648.4	660.0	655.1	648.4	641.6	630.9	630.9
52.5°	373.2	477.8	573.7	588.3	609.6	616.4	608.6	601.8	590.2	585.4	581.5
55°	346.0	428.4	514.6	543.7	566.0	574.7	560.2	553.4	536.0	533.0	531.1
57.5°	340.1	356.7	460.4	497.2	524.3	523.4	514.6	502.0	487.5	484.6	483.6
60°	312.0	257.8	402.2	445.8	473.9	471.0	463.3	451.7	438.1	436.1	434.2
62.5°	282.9	187.0	336.2	385.8	425.5	424.5	417.7	400.3	390.6	385.8	381.9
65°	240.3	157.0	239.3	320.7	378.0	379.9	365.4	352.8	342.1	336.2	335.3
67.5°	183.1	127.9	161.8	267.4	332.4	330.4	312.0	306.2	292.6	289.7	283.9
70°	135.7	85.3	112.4	217.1	287.8	282.9	268.4	261.6	249.0	242.2	238.4
72.5°	112.4	68.8	82.4	168.6	242.2	236.4	223.8	216.1	205.4	199.6	195.7
75°	91.1	72.7	63.0	125.0	196.7	192.8	181.2	173.5	164.7	157.0	157.9
77.5°	66.9	67.8	50.4	92.1	156.0	150.2	143.4	133.7	129.8	122.1	122.1
80°	50.4	53.3	37.8	63.0	112.4	112.4	106.6	99.8	93.0	89.1	89.1
82.5°	33.9	33.9	28.1	39.7	76.6	73.6	69.8	67.8	64.0	62.0	62.0
85°	15.5	19.4	17.4	24.2	41.7	43.6	43.6	41.7	40.7	38.8	39.7
87.5°	4.8	8.7	10.7	13.6	21.3	22.3	23.3	23.3	23.3	24.2	24.2
90°	1.0	1.7	2.5	2.7	4.3	6.3	7.4	6.6	4.9	3.7	3.7
92.5°	3.9	10.5	17.1	18.7	26.4	36.5	41.6	36.4	26.2	18.4	17.6
95°	9.3	21.4	33.5	36.5	64.8	102.5	121.4	108.3	82.2	62.6	60.4
97.5°	16.1	26.7	37.4	40.1	87.3	150.2	181.7	173.5	156.9	144.5	140.2
100°	21.3	31.0	40.7	43.1	95.4	165.3	200.2	200.8	202.0	202.9	197.9
102.5°	25.8	34.8	43.9	46.1	99.2	170.1	205.4	216.0	237.0	252.8	248.5
105°	33.4	41.1	48.6	50.6	102.0	170.5	204.8	228.5	275.7	311.0	308.7
107.5°	41.2	48.3	55.4	57.2	102.5	163.0	193.2	226.2	292.0	341.4	342.0
110°	46.4	52.8	59.2	60.9	101.7	156.3	183.5	220.4	293.9	349.1	351.6

TEST NUMBER: P933984

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	51.6	57.7	63.8	65.3	101.7	150.4	174.7	212.4	287.7	344.2	347.9
115°	59.3	64.9	70.5	72.0	102.7	143.7	164.1	200.4	273.0	327.3	332.5
117.5°	67.0	72.1	77.2	78.5	104.7	139.4	156.9	189.6	255.0	304.2	309.9
120°	71.4	76.3	81.1	82.3	106.1	138.0	153.9	183.8	243.7	288.6	294.1
122.5°	75.8	80.6	85.5	86.7	108.3	137.2	151.6	178.6	232.5	272.9	278.3
125°	82.5	86.9	91.4	92.5	111.4	136.6	149.2	172.1	217.9	252.2	257.3
127.5°	87.9	92.4	96.9	98.1	114.4	136.2	147.2	166.9	206.2	235.7	239.9
130°	90.8	95.6	100.5	101.7	116.7	136.5	146.4	164.0	198.9	225.2	229.1
132.5°	93.9	98.7	103.6	104.7	118.4	136.6	145.7	161.4	192.7	216.3	219.8
135°	98.4	102.7	107.2	108.2	120.3	136.5	144.6	157.7	183.9	203.6	206.6
137.5°	102.9	107.3	111.6	112.7	123.3	137.3	144.4	155.4	177.6	194.3	196.8
140°	106.7	110.7	114.7	115.7	125.0	137.5	143.7	153.3	172.5	186.8	189.1
142.5°	109.6	113.3	117.0	117.9	126.6	138.0	143.7	152.1	169.0	181.6	183.6
145°	114.1	117.2	120.5	121.3	128.5	138.0	142.7	149.6	163.4	173.7	175.3
147.5°	118.5	121.6	124.8	125.6	131.3	139.0	142.7	148.2	159.0	167.2	168.4
150°	121.4	124.2	127.1	127.8	132.8	139.4	142.7	147.3	156.5	163.4	164.3
152.5°	124.4	126.6	128.7	129.3	133.7	139.7	142.7	146.6	154.5	160.4	161.1
155°	128.9	130.4	132.1	132.5	135.9	140.4	142.7	145.8	152.1	156.8	157.3
157.5°	132.2	133.7	135.3	135.7	138.0	141.2	142.7	145.2	150.0	153.6	154.0
160°	134.4	135.6	136.8	137.1	139.0	141.5	142.7	144.8	148.9	152.0	152.2
162.5°	136.6	137.5	138.5	138.7	140.0	141.9	142.7	144.5	148.0	150.6	150.8
165°	139.1	139.8	140.7	140.9	141.5	142.3	142.7	144.0	146.5	148.4	148.5
167.5°	141.3	141.7	142.1	142.2	142.6	143.3	143.7	144.5	146.1	147.4	147.5
170°	142.7	143.1	143.5	143.6	143.6	143.7	143.7	144.5	146.1	147.4	147.4
172.5°	143.5	143.6	143.7	143.7	143.7	143.7	143.7	144.4	145.6	146.6	146.5
175°	144.6	144.6	144.6	144.6	144.3	143.9	143.7	144.1	145.0	145.5	145.5
177.5°	144.6	144.6	144.6	144.6	144.4	144.1	143.9	144.2	144.9	145.4	145.3
180°	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6

TEST NUMBER: P933984

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3
2.5°	1050.6	1047.7	1050.6	1048.7	1049.6	1046.7	1038.0	1035.1	1038.0	1040.9	1040.9
5°	1063.2	1061.2	1063.2	1063.2	1062.2	1060.3	1050.6	1048.7	1050.6	1051.6	1049.6
7.5°	1067.1	1064.2	1067.1	1065.1	1065.1	1063.2	1053.5	1051.6	1052.5	1055.4	1052.5
10°	1067.1	1064.2	1067.1	1066.1	1065.1	1063.2	1053.5	1049.6	1049.6	1052.5	1049.6
12.5°	1062.2	1060.3	1062.2	1060.3	1060.3	1058.3	1048.7	1044.8	1045.7	1046.7	1042.8
15°	1054.5	1051.6	1054.5	1052.5	1053.5	1050.6	1039.9	1036.1	1036.1	1038.0	1031.1
17.5°	1042.8	1039.0	1042.8	1041.9	1040.9	1039.0	1029.2	1025.3	1024.3	1025.3	1020.5
20°	1029.2	1026.3	1029.2	1028.2	1028.2	1024.3	1014.6	1009.8	1009.8	1009.8	1004.9
22.5°	1007.9	1004.9	1007.9	1009.8	1009.8	1008.8	1000.1	993.3	991.4	991.4	985.6
25°	983.6	980.7	983.6	983.6	982.7	983.6	980.7	976.8	973.9	971.0	965.2
27.5°	960.4	958.4	960.4	958.4	960.4	957.5	956.5	955.5	951.7	948.7	941.0
30°	937.1	935.2	937.1	935.2	933.2	931.3	926.5	924.5	928.4	926.5	913.9
32.5°	908.0	906.1	908.0	908.0	906.1	906.1	898.4	895.5	896.4	902.2	890.6
35°	878.0	875.1	878.0	877.0	878.0	875.1	870.3	869.3	865.4	872.2	863.5
37.5°	843.1	840.2	843.1	843.1	843.1	845.1	841.2	838.3	832.5	841.2	834.4
40°	807.3	803.4	807.3	806.3	807.3	809.2	807.3	805.3	799.5	806.3	800.5
42.5°	766.6	765.6	766.6	767.5	767.5	771.4	774.3	770.5	768.5	763.7	767.5
45°	723.0	721.0	723.0	724.9	725.9	727.8	736.5	736.5	733.6	725.9	731.7
47.5°	676.5	671.6	676.5	682.3	682.3	685.2	693.9	700.7	695.8	686.1	689.1
50°	627.0	628.0	627.0	630.9	630.9	641.6	648.4	655.1	660.0	648.4	634.8
52.5°	578.6	577.6	578.6	581.5	585.4	590.2	601.8	608.6	616.4	609.6	588.3
55°	530.1	532.1	530.1	531.1	533.0	536.0	553.4	560.2	574.7	566.0	543.7
57.5°	481.7	478.8	481.7	483.6	484.6	487.5	502.0	514.6	523.4	524.3	497.2
60°	425.5	421.6	425.5	434.2	436.1	438.1	451.7	463.3	471.0	473.9	445.8
62.5°	376.1	369.3	376.1	381.9	385.8	390.6	400.3	417.7	424.5	425.5	385.8
65°	323.6	320.7	323.6	335.3	336.2	342.1	352.8	365.4	379.9	378.0	320.7
67.5°	276.2	276.2	276.2	283.9	289.7	292.6	306.2	312.0	330.4	332.4	267.4
70°	232.6	231.6	232.6	238.4	242.2	249.0	261.6	268.4	282.9	287.8	217.1
72.5°	190.9	189.9	190.9	195.7	199.6	205.4	216.1	223.8	236.4	242.2	168.6
75°	154.1	152.1	154.1	157.9	157.0	164.7	173.5	181.2	192.8	196.7	125.0
77.5°	118.2	118.2	118.2	122.1	122.1	129.8	133.7	143.4	150.2	156.0	92.1
80°	88.2	87.2	88.2	89.1	89.1	93.0	99.8	106.6	112.4	112.4	63.0
82.5°	62.0	60.1	62.0	62.0	62.0	64.0	67.8	69.8	73.6	76.6	39.7
85°	38.8	38.8	38.8	39.7	38.8	40.7	41.7	43.6	43.6	41.7	24.2
87.5°	25.2	24.2	25.2	24.2	24.2	23.3	23.3	23.3	22.3	21.3	13.6
90°	3.7	3.7	3.7	3.7	3.7	4.9	6.6	7.4	6.3	4.3	2.7
92.5°	14.7	11.8	14.7	17.6	18.4	26.2	36.4	41.6	36.5	26.4	18.7
95°	51.6	42.6	51.6	60.4	62.6	82.2	108.3	121.4	102.5	64.8	36.5
97.5°	123.4	106.5	123.4	140.2	144.5	156.9	173.5	181.7	150.2	87.3	40.1
100°	177.8	157.7	177.8	197.9	202.9	202.0	200.8	200.2	165.3	95.4	43.1
102.5°	231.2	214.0	231.2	248.5	252.8	237.0	216.0	205.4	170.1	99.2	46.1
105°	299.5	290.2	299.5	308.7	311.0	275.7	228.5	204.8	170.5	102.0	50.6
107.5°	344.2	346.4	344.2	342.0	341.4	292.0	226.2	193.2	163.0	102.5	57.2
110°	361.1	370.8	361.1	351.6	349.1	293.9	220.4	183.5	156.3	101.7	60.9

TEST NUMBER: P933984

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	362.7	377.5	362.7	347.9	344.2	287.7	212.4	174.7	150.4	101.7	65.3
115°	353.1	373.6	353.1	332.5	327.3	273.0	200.4	164.1	143.7	102.7	72.0
117.5°	332.7	355.5	332.7	309.9	304.2	255.0	189.6	156.9	139.4	104.7	78.5
120°	316.3	338.4	316.3	294.1	288.6	243.7	183.8	153.9	138.0	106.1	82.3
122.5°	300.2	322.1	300.2	278.3	272.9	232.5	178.6	151.6	137.2	108.3	86.7
125°	277.4	297.6	277.4	257.3	252.2	217.9	172.1	149.2	136.6	111.4	92.5
127.5°	256.9	273.8	256.9	239.9	235.7	206.2	166.9	147.2	136.2	114.4	98.1
130°	244.8	260.5	244.8	229.1	225.2	198.9	164.0	146.4	136.5	116.7	101.7
132.5°	233.8	247.9	233.8	219.8	216.3	192.7	161.4	145.7	136.6	118.4	104.7
135°	218.8	230.9	218.8	206.6	203.6	183.9	157.7	144.6	136.5	120.3	108.2
137.5°	206.7	216.7	206.7	196.8	194.3	177.6	155.4	144.4	137.3	123.3	112.7
140°	198.4	207.7	198.4	189.1	186.8	172.5	153.3	143.7	137.5	125.0	115.7
142.5°	191.6	199.5	191.6	183.6	181.6	169.0	152.1	143.7	138.0	126.6	117.9
145°	181.3	187.3	181.3	175.3	173.7	163.4	149.6	142.7	138.0	128.5	121.3
147.5°	173.4	178.4	173.4	168.4	167.2	159.0	148.2	142.7	139.0	131.3	125.6
150°	168.4	172.5	168.4	164.3	163.4	156.5	147.3	142.7	139.4	132.8	127.8
152.5°	164.1	167.2	164.1	161.1	160.4	154.5	146.6	142.7	139.7	133.7	129.3
155°	159.3	161.3	159.3	157.3	156.8	152.1	145.8	142.7	140.4	135.9	132.5
157.5°	155.4	156.9	155.4	154.0	153.6	150.0	145.2	142.7	141.2	138.0	135.7
160°	153.1	153.9	153.1	152.2	152.0	148.9	144.8	142.7	141.5	139.0	137.1
162.5°	151.6	152.3	151.6	150.8	150.6	148.0	144.5	142.7	141.9	140.0	138.7
165°	149.4	150.2	149.4	148.5	148.4	146.5	144.0	142.7	142.3	141.5	140.9
167.5°	147.8	148.2	147.8	147.5	147.4	146.1	144.5	143.7	143.3	142.6	142.2
170°	147.4	147.4	147.4	147.4	147.4	146.1	144.5	143.7	143.7	143.6	143.6
172.5°	146.2	145.9	146.2	146.5	146.6	145.6	144.4	143.7	143.7	143.7	143.7
175°	145.5	145.5	145.5	145.5	145.5	145.0	144.1	143.7	143.9	144.3	144.6
177.5°	145.0	144.6	145.0	145.3	145.4	144.9	144.2	143.9	144.1	144.4	144.6
180°	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6

TEST NUMBER: P933984

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3
2.5°	1039.0	1033.1	1033.1	1023.4	1019.5	1016.6	1011.7	997.2	993.3	989.4	995.3
5°	1047.7	1037.0	1029.2	1011.7	997.2	991.4	973.0	938.1	914.8	897.4	887.7
7.5°	1049.6	1036.1	1021.4	994.3	959.4	943.9	887.7	823.7	806.3	790.8	781.1
10°	1047.7	1032.1	1011.7	971.0	888.7	861.5	805.3	763.7	753.0	750.1	753.0
12.5°	1040.9	1026.3	998.2	930.3	815.0	796.6	763.7	739.4	737.5	742.4	768.5
15°	1029.2	1015.6	982.7	876.1	774.3	760.8	737.5	728.8	739.4	773.4	851.8
17.5°	1017.5	1002.0	961.3	822.8	743.3	733.6	717.2	734.6	794.7	840.2	866.4
20°	1002.0	983.6	937.1	784.0	721.0	712.3	704.6	783.0	828.6	845.1	859.6
22.5°	983.6	964.3	904.2	756.9	697.8	691.0	695.8	810.2	828.6	840.2	852.8
25°	959.4	942.9	865.4	735.6	679.4	671.6	690.0	807.3	817.9	820.8	846.0
27.5°	937.1	915.8	824.7	716.2	657.1	654.2	694.9	794.7	802.4	805.3	832.5
30°	910.0	878.0	779.2	695.8	633.8	632.9	695.8	779.2	777.2	785.0	812.1
32.5°	881.9	821.8	727.8	670.6	611.5	610.6	689.1	755.9	754.0	764.6	785.0
35°	855.7	778.2	658.0	641.6	583.4	584.4	672.6	728.8	729.8	739.4	752.0
37.5°	828.6	740.4	581.5	609.6	556.3	556.3	650.3	703.6	701.7	704.6	722.0
40°	796.6	681.3	513.7	567.9	531.1	528.2	623.2	676.5	669.7	668.7	692.9
42.5°	762.7	616.4	463.3	512.7	502.0	498.2	590.2	643.5	630.9	633.8	664.8
45°	725.9	598.9	424.5	433.2	472.0	469.1	554.4	605.7	597.0	604.8	636.7
47.5°	689.1	564.1	411.9	359.6	440.0	439.1	514.6	568.9	564.1	571.8	605.7
50°	638.7	525.3	411.0	308.1	404.2	408.0	467.2	533.0	533.0	539.8	575.7
52.5°	573.7	477.8	373.2	279.1	362.5	374.1	425.5	502.0	504.0	510.8	542.7
55°	514.6	428.4	346.0	256.8	313.0	338.2	384.8	470.1	473.9	480.7	509.8
57.5°	460.4	356.7	340.1	230.6	267.4	291.7	348.9	439.1	441.0	446.8	474.9
60°	402.2	257.8	312.0	202.5	227.7	246.1	315.9	402.2	409.0	412.9	437.1
62.5°	336.2	187.0	282.9	183.1	208.3	212.2	288.8	367.3	376.1	379.0	393.5
65°	239.3	157.0	240.3	166.7	188.0	189.0	259.7	331.4	339.2	344.0	354.8
67.5°	161.8	127.9	183.1	151.2	172.5	173.5	231.6	289.7	300.4	304.3	311.0
70°	112.4	85.3	135.7	134.7	155.0	157.0	201.6	251.9	261.6	264.5	268.4
72.5°	82.4	68.8	112.4	121.1	136.6	138.6	170.5	209.3	219.0	221.9	223.8
75°	63.0	72.7	91.1	105.6	116.3	117.2	139.5	170.5	177.3	179.3	180.2
77.5°	50.4	67.8	66.9	85.3	95.0	93.0	109.5	131.8	137.6	137.6	137.6
80°	37.8	53.3	50.4	61.0	69.8	67.8	78.5	94.0	95.9	97.9	96.9
82.5°	28.1	33.9	33.9	38.8	46.5	44.6	52.3	61.0	61.0	61.0	63.0
85°	17.4	19.4	15.5	20.3	26.2	25.2	29.1	32.9	33.9	33.9	32.0
87.5°	10.7	8.7	4.8	7.8	11.6	11.6	13.6	14.5	13.6	13.6	13.6
90°	2.5	1.7	1.0	1.7	2.5	2.7	4.3	6.3	7.4	6.6	4.9
92.5°	17.1	10.5	3.9	10.5	17.1	18.7	26.4	36.5	41.6	36.4	26.2
95°	33.5	21.4	9.3	21.4	33.5	36.5	64.8	102.5	121.4	108.3	82.2
97.5°	37.4	26.7	16.1	26.7	37.4	40.1	87.3	150.2	181.7	173.5	156.9
100°	40.7	31.0	21.3	31.0	40.7	43.1	95.4	165.3	200.2	200.8	202.0
102.5°	43.9	34.8	25.8	34.8	43.9	46.1	99.2	170.1	205.4	216.0	237.0
105°	48.6	41.1	33.4	41.1	48.6	50.6	102.0	170.5	204.8	228.5	275.7
107.5°	55.4	48.3	41.2	48.3	55.4	57.2	102.5	163.0	193.2	226.2	292.0
110°	59.2	52.8	46.4	52.8	59.2	60.9	101.7	156.3	183.5	220.4	293.9

TEST NUMBER: P933984

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	63.8	57.7	51.6	57.7	63.8	65.3	101.7	150.4	174.7	212.4	287.7
115°	70.5	64.9	59.3	64.9	70.5	72.0	102.7	143.7	164.1	200.4	273.0
117.5°	77.2	72.1	67.0	72.1	77.2	78.5	104.7	139.4	156.9	189.6	255.0
120°	81.1	76.3	71.4	76.3	81.1	82.3	106.1	138.0	153.9	183.8	243.7
122.5°	85.5	80.6	75.8	80.6	85.5	86.7	108.3	137.2	151.6	178.6	232.5
125°	91.4	86.9	82.5	86.9	91.4	92.5	111.4	136.6	149.2	172.1	217.9
127.5°	96.9	92.4	87.9	92.4	96.9	98.1	114.4	136.2	147.2	166.9	206.2
130°	100.5	95.6	90.8	95.6	100.5	101.7	116.7	136.5	146.4	164.0	198.9
132.5°	103.6	98.7	93.9	98.7	103.6	104.7	118.4	136.6	145.7	161.4	192.7
135°	107.2	102.7	98.4	102.7	107.2	108.2	120.3	136.5	144.6	157.7	183.9
137.5°	111.6	107.3	102.9	107.3	111.6	112.7	123.3	137.3	144.4	155.4	177.6
140°	114.7	110.7	106.7	110.7	114.7	115.7	125.0	137.5	143.7	153.3	172.5
142.5°	117.0	113.3	109.6	113.3	117.0	117.9	126.6	138.0	143.7	152.1	169.0
145°	120.5	117.2	114.1	117.2	120.5	121.3	128.5	138.0	142.7	149.6	163.4
147.5°	124.8	121.6	118.5	121.6	124.8	125.6	131.3	139.0	142.7	148.2	159.0
150°	127.1	124.2	121.4	124.2	127.1	127.8	132.8	139.4	142.7	147.3	156.5
152.5°	128.7	126.6	124.4	126.6	128.7	129.3	133.7	139.7	142.7	146.6	154.5
155°	132.1	130.4	128.9	130.4	132.1	132.5	135.9	140.4	142.7	145.8	152.1
157.5°	135.3	133.7	132.2	133.7	135.3	135.7	138.0	141.2	142.7	145.2	150.0
160°	136.8	135.6	134.4	135.6	136.8	137.1	139.0	141.5	142.7	144.8	148.9
162.5°	138.5	137.5	136.6	137.5	138.5	138.7	140.0	141.9	142.7	144.5	148.0
165°	140.7	139.8	139.1	139.8	140.7	140.9	141.5	142.3	142.7	144.0	146.5
167.5°	142.1	141.7	141.3	141.7	142.1	142.2	142.6	143.3	143.7	144.5	146.1
170°	143.5	143.1	142.7	143.1	143.5	143.6	143.6	143.7	143.7	144.5	146.1
172.5°	143.7	143.6	143.5	143.6	143.7	143.7	143.7	143.7	143.7	144.4	145.6
175°	144.6	144.6	144.6	144.6	144.6	144.6	144.3	143.9	143.7	144.1	145.0
177.5°	144.6	144.6	144.6	144.6	144.6	144.6	144.4	144.1	143.9	144.2	144.9
180°	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6

TEST NUMBER: P933984

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3	1024.3
2.5°	988.5	985.6	989.4	978.8	989.4	985.6	988.5	995.3	989.4	993.3	997.2
5°	867.4	862.5	847.0	834.4	847.0	862.5	867.4	887.7	897.4	914.8	938.1
7.5°	775.3	771.4	767.5	759.8	767.5	771.4	775.3	781.1	790.8	806.3	823.7
10°	754.9	755.9	761.7	760.8	761.7	755.9	754.9	753.0	750.1	753.0	763.7
12.5°	807.3	816.0	848.0	846.0	848.0	816.0	807.3	768.5	742.4	737.5	739.4
15°	867.4	870.3	877.0	878.0	877.0	870.3	867.4	851.8	773.4	739.4	728.8
17.5°	873.2	874.1	879.0	879.0	879.0	874.1	873.2	866.4	840.2	794.7	734.6
20°	868.3	870.3	879.9	881.9	879.9	870.3	868.3	859.6	845.1	828.6	783.0
22.5°	866.4	870.3	878.0	877.0	878.0	870.3	866.4	852.8	840.2	828.6	810.2
25°	856.7	856.7	857.7	858.6	857.7	856.7	856.7	846.0	820.8	817.9	807.3
27.5°	836.3	838.3	844.1	843.1	844.1	838.3	836.3	832.5	805.3	802.4	794.7
30°	817.9	816.0	811.1	807.3	811.1	816.0	817.9	812.1	785.0	777.2	779.2
32.5°	786.9	782.1	777.2	774.3	777.2	782.1	786.9	785.0	764.6	754.0	755.9
35°	750.1	751.1	750.1	747.2	750.1	751.1	750.1	752.0	739.4	729.8	728.8
37.5°	723.9	725.9	724.9	721.0	724.9	725.9	723.9	722.0	704.6	701.7	703.6
40°	696.8	697.8	696.8	693.9	696.8	697.8	696.8	692.9	668.7	669.7	676.5
42.5°	670.6	669.7	666.8	664.8	666.8	669.7	670.6	664.8	633.8	630.9	643.5
45°	640.6	641.6	635.8	632.9	635.8	641.6	640.6	636.7	604.8	597.0	605.7
47.5°	610.6	610.6	605.7	602.8	605.7	610.6	610.6	605.7	571.8	564.1	568.9
50°	578.6	577.6	570.8	569.9	570.8	577.6	578.6	575.7	539.8	533.0	533.0
52.5°	541.8	541.8	542.7	544.7	542.7	541.8	541.8	542.7	510.8	504.0	502.0
55°	509.8	510.8	517.5	519.5	517.5	510.8	509.8	509.8	480.7	473.9	470.1
57.5°	476.8	476.8	481.7	481.7	481.7	476.8	476.8	474.9	446.8	441.0	439.1
60°	439.1	441.0	444.9	443.9	444.9	441.0	439.1	437.1	412.9	409.0	402.2
62.5°	399.3	401.3	402.2	400.3	402.2	401.3	399.3	393.5	379.0	376.1	367.3
65°	357.7	359.6	360.6	358.6	360.6	359.6	357.7	354.8	344.0	339.2	331.4
67.5°	314.9	314.0	313.0	316.9	313.0	314.0	314.9	311.0	304.3	300.4	289.7
70°	271.3	271.3	270.4	272.3	270.4	271.3	271.3	268.4	264.5	261.6	251.9
72.5°	224.8	223.8	227.7	224.8	227.7	223.8	224.8	223.8	221.9	219.0	209.3
75°	179.3	181.2	179.3	182.2	179.3	181.2	179.3	180.2	179.3	177.3	170.5
77.5°	136.6	138.6	136.6	136.6	136.6	138.6	136.6	137.6	137.6	137.6	131.8
80°	96.9	95.9	95.9	95.0	95.9	95.9	96.9	96.9	97.9	95.9	94.0
82.5°	62.0	61.0	61.0	63.0	61.0	61.0	62.0	63.0	61.0	61.0	61.0
85°	33.9	34.9	32.9	32.9	32.9	34.9	33.9	32.0	33.9	33.9	32.9
87.5°	12.6	11.6	11.6	11.6	11.6	11.6	12.6	13.6	13.6	13.6	14.5
90°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	4.9	6.6	7.4	6.3
92.5°	18.4	17.6	14.7	11.8	14.7	17.6	18.4	26.2	36.4	41.6	36.5
95°	62.6	60.4	51.6	42.6	51.6	60.4	62.6	82.2	108.3	121.4	102.5
97.5°	144.5	140.2	123.4	106.5	123.4	140.2	144.5	156.9	173.5	181.7	150.2
100°	202.9	197.9	177.8	157.7	177.8	197.9	202.9	202.0	200.8	200.2	165.3
102.5°	252.8	248.5	231.2	214.0	231.2	248.5	252.8	237.0	216.0	205.4	170.1
105°	311.0	308.7	299.5	290.2	299.5	308.7	311.0	275.7	228.5	204.8	170.5
107.5°	341.4	342.0	344.2	346.4	344.2	342.0	341.4	292.0	226.2	193.2	163.0
110°	349.1	351.6	361.1	370.8	361.1	351.6	349.1	293.9	220.4	183.5	156.3

TEST NUMBER: P933984

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	344.2	347.9	362.7	377.5	362.7	347.9	344.2	287.7	212.4	174.7	150.4
115°	327.3	332.5	353.1	373.6	353.1	332.5	327.3	273.0	200.4	164.1	143.7
117.5°	304.2	309.9	332.7	355.5	332.7	309.9	304.2	255.0	189.6	156.9	139.4
120°	288.6	294.1	316.3	338.4	316.3	294.1	288.6	243.7	183.8	153.9	138.0
122.5°	272.9	278.3	300.2	322.1	300.2	278.3	272.9	232.5	178.6	151.6	137.2
125°	252.2	257.3	277.4	297.6	277.4	257.3	252.2	217.9	172.1	149.2	136.6
127.5°	235.7	239.9	256.9	273.8	256.9	239.9	235.7	206.2	166.9	147.2	136.2
130°	225.2	229.1	244.8	260.5	244.8	229.1	225.2	198.9	164.0	146.4	136.5
132.5°	216.3	219.8	233.8	247.9	233.8	219.8	216.3	192.7	161.4	145.7	136.6
135°	203.6	206.6	218.8	230.9	218.8	206.6	203.6	183.9	157.7	144.6	136.5
137.5°	194.3	196.8	206.7	216.7	206.7	196.8	194.3	177.6	155.4	144.4	137.3
140°	186.8	189.1	198.4	207.7	198.4	189.1	186.8	172.5	153.3	143.7	137.5
142.5°	181.6	183.6	191.6	199.5	191.6	183.6	181.6	169.0	152.1	143.7	138.0
145°	173.7	175.3	181.3	187.3	181.3	175.3	173.7	163.4	149.6	142.7	138.0
147.5°	167.2	168.4	173.4	178.4	173.4	168.4	167.2	159.0	148.2	142.7	139.0
150°	163.4	164.3	168.4	172.5	168.4	164.3	163.4	156.5	147.3	142.7	139.4
152.5°	160.4	161.1	164.1	167.2	164.1	161.1	160.4	154.5	146.6	142.7	139.7
155°	156.8	157.3	159.3	161.3	159.3	157.3	156.8	152.1	145.8	142.7	140.4
157.5°	153.6	154.0	155.4	156.9	155.4	154.0	153.6	150.0	145.2	142.7	141.2
160°	152.0	152.2	153.1	153.9	153.1	152.2	152.0	148.9	144.8	142.7	141.5
162.5°	150.6	150.8	151.6	152.3	151.6	150.8	150.6	148.0	144.5	142.7	141.9
165°	148.4	148.5	149.4	150.2	149.4	148.5	148.4	146.5	144.0	142.7	142.3
167.5°	147.4	147.5	147.8	148.2	147.8	147.5	147.4	146.1	144.5	143.7	143.3
170°	147.4	147.4	147.4	147.4	147.4	147.4	147.4	146.1	144.5	143.7	143.7
172.5°	146.6	146.5	146.2	145.9	146.2	146.5	146.6	145.6	144.4	143.7	143.7
175°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.0	144.1	143.7	143.9
177.5°	145.4	145.3	145.0	144.6	145.0	145.3	145.4	144.9	144.2	143.9	144.1
180°	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6

TEST NUMBER: P933984

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1024.3	1024.3	1024.3	1024.3	1024.3
2.5°	1011.7	1016.6	1019.5	1023.4	1033.1
5°	973.0	991.4	997.2	1011.7	1029.2
7.5°	887.7	943.9	959.4	994.3	1021.4
10°	805.3	861.5	888.7	971.0	1011.7
12.5°	763.7	796.6	815.0	930.3	998.2
15°	737.5	760.8	774.3	876.1	982.7
17.5°	717.2	733.6	743.3	822.8	961.3
20°	704.6	712.3	721.0	784.0	937.1
22.5°	695.8	691.0	697.8	756.9	904.2
25°	690.0	671.6	679.4	735.6	865.4
27.5°	694.9	654.2	657.1	716.2	824.7
30°	695.8	632.9	633.8	695.8	779.2
32.5°	689.1	610.6	611.5	670.6	727.8
35°	672.6	584.4	583.4	641.6	658.0
37.5°	650.3	556.3	556.3	609.6	581.5
40°	623.2	528.2	531.1	567.9	513.7
42.5°	590.2	498.2	502.0	512.7	463.3
45°	554.4	469.1	472.0	433.2	424.5
47.5°	514.6	439.1	440.0	359.6	411.9
50°	467.2	408.0	404.2	308.1	411.0
52.5°	425.5	374.1	362.5	279.1	373.2
55°	384.8	338.2	313.0	256.8	346.0
57.5°	348.9	291.7	267.4	230.6	340.1
60°	315.9	246.1	227.7	202.5	312.0
62.5°	288.8	212.2	208.3	183.1	282.9
65°	259.7	189.0	188.0	166.7	240.3
67.5°	231.6	173.5	172.5	151.2	183.1
70°	201.6	157.0	155.0	134.7	135.7
72.5°	170.5	138.6	136.6	121.1	112.4
75°	139.5	117.2	116.3	105.6	91.1
77.5°	109.5	93.0	95.0	85.3	66.9
80°	78.5	67.8	69.8	61.0	50.4
82.5°	52.3	44.6	46.5	38.8	33.9
85°	29.1	25.2	26.2	20.3	15.5
87.5°	13.6	11.6	11.6	7.8	4.8
90°	4.3	2.7	2.5	1.7	1.0
92.5°	26.4	18.7	17.1	10.5	3.9
95°	64.8	36.5	33.5	21.4	9.3
97.5°	87.3	40.1	37.4	26.7	16.1
100°	95.4	43.1	40.7	31.0	21.3
102.5°	99.2	46.1	43.9	34.8	25.8
105°	102.0	50.6	48.6	41.1	33.4
107.5°	102.5	57.2	55.4	48.3	41.2
110°	101.7	60.9	59.2	52.8	46.4

TEST NUMBER: P933984

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	101.7	65.3	63.8	57.7	51.6
115°	102.7	72.0	70.5	64.9	59.3
117.5°	104.7	78.5	77.2	72.1	67.0
120°	106.1	82.3	81.1	76.3	71.4
122.5°	108.3	86.7	85.5	80.6	75.8
125°	111.4	92.5	91.4	86.9	82.5
127.5°	114.4	98.1	96.9	92.4	87.9
130°	116.7	101.7	100.5	95.6	90.8
132.5°	118.4	104.7	103.6	98.7	93.9
135°	120.3	108.2	107.2	102.7	98.4
137.5°	123.3	112.7	111.6	107.3	102.9
140°	125.0	115.7	114.7	110.7	106.7
142.5°	126.6	117.9	117.0	113.3	109.6
145°	128.5	121.3	120.5	117.2	114.1
147.5°	131.3	125.6	124.8	121.6	118.5
150°	132.8	127.8	127.1	124.2	121.4
152.5°	133.7	129.3	128.7	126.6	124.4
155°	135.9	132.5	132.1	130.4	128.9
157.5°	138.0	135.7	135.3	133.7	132.2
160°	139.0	137.1	136.8	135.6	134.4
162.5°	140.0	138.7	138.5	137.5	136.6
165°	141.5	140.9	140.7	139.8	139.1
167.5°	142.6	142.2	142.1	141.7	141.3
170°	143.6	143.6	143.5	143.1	142.7
172.5°	143.7	143.7	143.7	143.6	143.5
175°	144.3	144.6	144.6	144.6	144.6
177.5°	144.4	144.6	144.6	144.6	144.6
180°	144.6	144.6	144.6	144.6	144.6

TEST NUMBER: P933984

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-4-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.58	15.71	15.30	16.45	17.33	17.38	18.51	18.10	19.25	20.13
	3H	15.08	16.09	15.81	16.84	17.76	18.74	19.75	19.47	20.50	21.41
	4H	15.28	16.24	16.04	17.00	17.93	19.19	20.14	19.94	20.90	21.83
	6H	15.42	16.30	16.18	17.07	18.01	19.48	20.36	20.24	21.13	22.07
	8H	15.42	16.26	16.20	17.05	18.00	19.55	20.39	20.33	21.18	22.13
	12H	15.40	16.21	16.19	16.99	17.96	19.60	20.40	20.38	21.18	22.15
4H	2H	15.64	16.59	16.40	17.36	18.28	17.82	18.78	18.58	19.54	20.47
	3H	16.69	17.49	17.46	18.28	19.23	19.34	20.14	20.11	20.94	21.88
	4H	16.98	17.70	17.76	18.50	19.47	19.88	20.60	20.66	21.39	22.37
	6H	17.12	17.74	17.92	18.56	19.54	20.25	20.87	21.05	21.69	22.67
	8H	17.13	17.71	17.94	18.53	19.52	20.36	20.94	21.16	21.76	22.75
	12H	17.11	17.64	17.94	18.47	19.47	20.42	20.95	21.25	21.79	22.78
8H	4H	17.45	18.03	18.25	18.85	19.84	20.02	20.61	20.83	21.42	22.42
	6H	17.72	18.20	18.55	19.06	20.06	20.46	20.95	21.30	21.80	22.80
	8H	17.76	18.20	18.61	19.05	20.06	20.61	21.04	21.46	21.90	22.91
	12H	17.76	18.14	18.61	18.99	20.05	20.72	21.10	21.56	21.94	23.01
12H	4H	17.46	17.99	18.29	18.83	19.83	20.00	20.53	20.83	21.36	22.36
	6H	17.78	18.21	18.63	19.07	20.08	20.46	20.89	21.31	21.75	22.76
	8H	17.86	18.24	18.71	19.09	20.15	20.63	21.01	21.48	21.86	22.92

END OF REPORT