

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934684

Luminaire Tested: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-4-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934684
REPORT IS A COMBINATION OF REPORTS P933706 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-4-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4684.2 lumens
Efficiency: N/A
Efficacy: 136.2 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934684

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-4-3500K

Luminous Intensity Polar Plot



TEST NUMBER: P934684

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-4-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	87	84	86	83	79	77	67	65	63	53	52	50	40	39	38
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32
3	79	70	63	57	71	64	57	52	52	47	44	41	38	35	31	29	27
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	25	24
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	21	18	16
8	52	40	32	27	47	37	30	25	30	25	22	24	21	18	19	16	14
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6374	6374	6374	6374
5°	6414	6434	6414	5059
10°	6365	6338	6365	4532
15°	6288	6201	6288	5178
20°	6149	6038	6149	5189
25°	5873	5801	5873	5079
30°	5519	5604	5519	4838
35°	4913	5354	4913	4572
40°	4086	5062	4086	4371
45°	3644	4718	3644	4140
50°	3863	4308	3863	3909
55°	3624	3868	3624	3777
60°	3723	3285	3723	3459
65°	3357	2715	3357	3034
70°	2310	2164	2310	2545
75°	2000	1599	2000	1916
80°	1582	1058	1582	1152
85°	861	560	861	476

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 5596 cd/sqm

TEST NUMBER: P934684

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-4-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.0	1.3
10°-20°	176.0	3.8
20°-30°	272.1	5.8
30°-40°	324.9	6.9
40°-50°	326.8	7.0
50°-60°	284.3	6.1
60°-70°	201.6	4.3
70°-80°	106.7	2.3
80°-90°	28.3	0.6
90°-100°	218.2	4.7
100°-110°	573.6	12.2
110°-120°	594.7	12.7
120°-130°	477.1	10.2
130°-140°	374.3	8.0
140°-150°	287.3	6.1
150°-160°	206.9	4.4
160°-170°	126.6	2.7
170°-180°	42.8	0.9
0°-30°	510.2	10.9
0°-40°	835.1	17.8
0°-60°	1446.2	30.9
0°-90°	1782.7	38.1
90°-120°	1386.5	29.6
90°-150°	2525.2	53.9
90°-180°	2901.0	61.9
0°-180°	4684.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	687	687	687	687	687	
5°	690	712	690	560	690	65
15°	659	705	659	589	659	185
25°	580	658	580	576	580	266
35°	441	587	441	501	441	273
45°	285	484	285	424	285	228
55°	232	357	232	348	232	213
65°	161	215	161	240	161	154
75°	61	102	61	122	61	64
85°	10	26	10	22	10	14
90°	3	11	3	11	3	3
95°	29	132	29	132	29	32
105°	103	898	103	898	103	110
115°	184	1156	184	1156	184	181
125°	255	921	255	921	255	227
135°	304	715	304	715	304	235
145°	353	580	353	580	353	221
155°	399	499	399	499	399	183
165°	430	465	430	465	430	121
175°	448	451	448	451	448	42
180°	448	448	448	448	448	

TEST NUMBER: P934684

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9
2.5°	692.7	692.7	696.6	698.0	698.0	696.0	694.1	696.0	701.8	703.8	703.1
5°	690.1	695.4	702.5	703.8	705.1	704.5	703.1	704.5	711.0	712.2	712.9
7.5°	685.0	694.7	703.8	705.7	707.7	705.7	705.1	706.4	712.9	714.2	714.2
10°	678.5	692.1	702.5	703.8	705.7	703.8	703.8	706.4	712.9	714.2	714.8
12.5°	669.4	688.2	698.0	699.2	701.8	701.2	700.6	703.1	709.7	711.0	711.0
15°	658.9	681.0	690.1	691.5	696.0	694.7	694.7	697.3	704.5	706.4	705.7
17.5°	644.7	672.0	682.4	684.3	687.6	686.9	687.6	690.1	696.6	698.0	698.6
20°	628.4	659.6	672.0	673.9	677.1	677.1	677.1	680.4	686.9	689.5	689.5
22.5°	606.3	646.6	659.6	661.0	664.8	664.8	666.1	670.6	676.5	677.1	677.1
25°	580.3	632.3	643.3	647.3	651.2	653.1	655.0	657.7	659.6	658.9	659.6
27.5°	553.0	614.2	628.4	631.0	636.2	638.2	640.8	641.4	642.1	644.0	642.7
30°	522.5	588.8	610.2	612.8	621.2	622.6	620.0	621.2	624.5	625.8	627.1
32.5°	488.1	551.1	591.4	597.2	605.0	601.2	600.5	602.4	607.7	607.7	608.9
35°	441.3	521.8	573.8	579.1	584.9	580.3	583.0	583.5	586.8	588.8	588.1
37.5°	389.9	496.5	555.6	559.5	564.1	558.2	562.1	564.1	566.7	565.4	565.4
40°	344.4	456.9	534.2	536.8	540.7	536.1	540.0	541.4	542.6	541.4	540.7
42.5°	310.7	413.3	511.4	514.7	512.1	515.3	516.7	519.3	517.3	514.7	514.7
45°	284.6	401.7	486.7	490.6	486.7	492.0	493.9	493.9	488.1	486.7	486.1
47.5°	276.2	378.2	462.0	462.0	460.1	466.6	469.9	465.3	459.5	457.5	457.5
50°	275.6	352.2	428.3	425.7	434.8	442.5	439.3	434.8	430.2	423.1	423.1
52.5°	250.2	320.4	384.7	394.5	408.7	413.3	408.1	403.6	395.7	392.5	389.9
55°	232.0	287.2	345.1	364.5	379.6	385.4	375.6	371.0	359.4	357.5	356.1
57.5°	228.1	239.1	308.7	333.3	351.6	351.0	345.1	336.6	326.8	324.9	324.3
60°	209.3	172.9	269.7	298.9	317.7	315.8	310.7	302.8	293.7	292.4	291.2
62.5°	189.7	125.4	225.5	258.6	285.3	284.6	280.1	268.4	261.9	258.6	256.0
65°	161.1	105.2	160.6	215.1	253.5	254.8	245.0	236.5	229.4	225.5	224.8
67.5°	122.9	85.8	108.5	179.4	222.9	221.6	209.3	205.3	196.2	194.3	190.4
70°	91.0	57.2	75.4	145.5	193.0	189.7	180.0	175.5	167.1	162.5	159.9
72.5°	75.4	46.1	55.2	113.1	162.5	158.5	150.1	145.0	137.8	133.9	131.3
75°	61.0	48.7	42.2	83.8	131.9	129.4	121.5	116.3	110.5	105.2	105.9
77.5°	44.9	45.4	33.8	61.7	104.7	100.8	96.2	89.7	87.1	81.9	81.9
80°	33.8	35.8	25.4	42.2	75.4	75.4	71.5	67.0	62.4	59.8	59.8
82.5°	22.8	22.8	18.8	26.6	51.4	49.4	46.8	45.4	42.9	41.6	41.6
85°	10.4	13.0	11.7	16.3	27.9	29.3	29.3	27.9	27.3	26.0	26.6
87.5°	3.3	5.8	7.2	9.1	14.3	14.9	15.6	15.6	15.6	16.3	16.3
90°	3.0	5.4	7.8	8.4	13.3	19.7	22.9	20.3	15.2	11.4	11.4
92.5°	12.0	32.5	52.8	57.9	81.5	112.9	128.6	112.7	80.9	57.1	54.8
95°	28.9	66.3	103.7	113.0	200.6	317.3	375.8	335.3	254.4	193.7	186.8
97.5°	49.9	82.8	115.8	124.0	270.2	464.9	562.3	536.7	485.7	447.3	434.2
100°	66.1	95.9	125.9	133.3	295.4	511.6	619.7	621.5	625.3	628.1	612.5
102.5°	79.9	107.8	135.7	142.6	307.1	526.4	636.0	668.5	733.6	782.5	769.1
105°	103.3	126.9	150.6	156.5	315.7	528.0	634.1	707.2	853.2	962.7	955.5
107.5°	127.3	149.4	171.4	176.9	317.3	504.5	598.1	699.9	903.6	1056.4	1058.1
110°	143.6	163.5	183.4	188.4	314.9	483.6	568.0	681.9	909.6	1080.4	1087.9

TEST NUMBER: P934684

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	159.5	178.5	197.4	202.1	315.0	465.5	540.7	657.3	890.3	1065.1	1076.7
115°	183.5	201.0	218.5	222.9	317.9	444.6	507.9	620.3	844.8	1013.2	1029.1
117.5°	207.3	223.2	239.1	243.0	323.8	431.5	485.4	586.7	789.3	941.4	959.0
120°	221.1	236.0	251.0	254.8	328.6	427.1	476.4	569.0	754.2	893.0	910.2
122.5°	234.6	249.7	264.7	268.5	335.5	424.8	469.5	552.8	719.6	844.7	861.6
125°	255.3	269.1	282.9	286.2	344.9	423.0	462.0	532.9	674.5	780.7	796.3
127.5°	272.2	286.0	299.9	303.4	354.2	421.9	455.7	516.6	638.2	729.4	742.5
130°	281.2	296.1	311.0	314.8	361.0	422.5	453.3	507.5	615.7	696.9	709.0
132.5°	290.5	305.4	320.4	324.1	366.5	423.0	451.2	499.6	596.6	669.3	680.1
135°	304.3	317.8	331.5	334.9	372.5	422.6	447.6	488.2	569.4	630.2	639.6
137.5°	318.4	331.9	345.4	348.7	381.5	425.2	447.0	481.3	549.9	601.4	609.0
140°	330.1	342.5	354.9	358.0	387.0	425.6	444.9	474.5	533.7	578.2	585.4
142.5°	339.2	350.6	362.0	364.9	391.6	427.1	444.9	470.9	523.0	562.0	568.2
145°	352.9	363.0	373.0	375.5	397.6	427.1	441.9	463.2	505.7	537.7	542.3
147.5°	366.8	376.5	386.2	388.7	406.4	430.0	441.9	458.6	492.2	517.3	521.1
150°	375.8	384.6	393.4	395.6	411.0	431.6	441.9	456.0	484.3	505.5	508.6
152.5°	385.1	391.8	398.5	400.1	414.1	432.6	441.9	454.0	478.1	496.2	498.6
155°	398.9	403.9	408.7	410.0	420.6	434.8	441.9	451.5	470.6	485.1	486.6
157.5°	409.1	414.0	418.8	420.0	427.2	437.0	441.9	449.3	464.2	475.5	476.6
160°	416.0	419.8	423.5	424.4	430.2	438.0	441.9	448.3	461.1	470.7	471.3
162.5°	423.0	425.8	428.6	429.3	433.4	439.1	441.9	447.3	458.0	466.2	466.8
165°	430.4	432.9	435.5	436.1	438.1	440.6	441.9	445.7	453.5	459.3	460.0
167.5°	437.3	438.5	439.7	440.0	441.7	443.8	444.9	447.4	452.5	456.3	456.6
170°	441.9	443.0	444.3	444.6	444.7	444.8	444.9	447.4	452.5	456.3	456.3
172.5°	444.3	444.6	444.8	444.9	444.9	444.9	444.9	446.9	450.9	453.9	453.7
175°	447.6	447.6	447.6	447.6	446.7	445.4	444.9	446.1	448.6	450.6	450.6
177.5°	447.6	447.6	447.6	447.6	446.9	445.9	445.4	446.4	448.5	450.0	449.7
180°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6

TEST NUMBER: P934684

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9
2.5°	704.5	702.5	704.5	703.1	703.8	701.8	696.0	694.1	696.0	698.0	698.0
5°	712.9	711.6	712.9	712.9	712.2	711.0	704.5	703.1	704.5	705.1	703.8
7.5°	715.5	713.6	715.5	714.2	714.2	712.9	706.4	705.1	705.7	707.7	705.7
10°	715.5	713.6	715.5	714.8	714.2	712.9	706.4	703.8	703.8	705.7	703.8
12.5°	712.2	711.0	712.2	711.0	711.0	709.7	703.1	700.6	701.2	701.8	699.2
15°	707.1	705.1	707.1	705.7	706.4	704.5	697.3	694.7	694.7	696.0	691.5
17.5°	699.2	696.6	699.2	698.6	698.0	696.6	690.1	687.6	686.9	687.6	684.3
20°	690.1	688.2	690.1	689.5	689.5	686.9	680.4	677.1	677.1	677.1	673.9
22.5°	675.9	673.9	675.9	677.1	677.1	676.5	670.6	666.1	664.8	664.8	661.0
25°	659.6	657.7	659.6	659.6	658.9	659.6	657.7	655.0	653.1	651.2	647.3
27.5°	644.0	642.7	644.0	642.7	644.0	642.1	641.4	640.8	638.2	636.2	631.0
30°	628.4	627.1	628.4	627.1	625.8	624.5	621.2	620.0	622.6	621.2	612.8
32.5°	608.9	607.7	608.9	608.9	607.7	607.7	602.4	600.5	601.2	605.0	597.2
35°	588.8	586.8	588.8	588.1	588.8	586.8	583.5	583.0	580.3	584.9	579.1
37.5°	565.4	563.5	565.4	565.4	565.4	566.7	564.1	562.1	558.2	564.1	559.5
40°	541.4	538.8	541.4	540.7	541.4	542.6	541.4	540.0	536.1	540.7	536.8
42.5°	514.1	513.4	514.1	514.7	514.7	517.3	519.3	516.7	515.3	512.1	514.7
45°	484.8	483.5	484.8	486.1	486.7	488.1	493.9	493.9	492.0	486.7	490.6
47.5°	453.6	450.4	453.6	457.5	457.5	459.5	465.3	469.9	466.6	460.1	462.0
50°	420.4	421.1	420.4	423.1	423.1	430.2	434.8	439.3	442.5	434.8	425.7
52.5°	388.0	387.3	388.0	389.9	392.5	395.7	403.6	408.1	413.3	408.7	394.5
55°	355.4	356.8	355.4	356.1	357.5	359.4	371.0	375.6	385.4	379.6	364.5
57.5°	323.0	321.0	323.0	324.3	324.9	326.8	336.6	345.1	351.0	351.6	333.3
60°	285.3	282.7	285.3	291.2	292.4	293.7	302.8	310.7	315.8	317.7	298.9
62.5°	252.1	247.6	252.1	256.0	258.6	261.9	268.4	280.1	284.6	285.3	258.6
65°	217.1	215.1	217.1	224.8	225.5	229.4	236.5	245.0	254.8	253.5	215.1
67.5°	185.2	185.2	185.2	190.4	194.3	196.2	205.3	209.3	221.6	222.9	179.4
70°	156.0	155.3	156.0	159.9	162.5	167.1	175.5	180.0	189.7	193.0	145.5
72.5°	128.0	127.3	128.0	131.3	133.9	137.8	145.0	150.1	158.5	162.5	113.1
75°	103.3	102.0	103.3	105.9	105.2	110.5	116.3	121.5	129.4	131.9	83.8
77.5°	79.3	79.3	79.3	81.9	81.9	87.1	89.7	96.2	100.8	104.7	61.7
80°	59.1	58.5	59.1	59.8	59.8	62.4	67.0	71.5	75.4	75.4	42.2
82.5°	41.6	40.3	41.6	41.6	41.6	42.9	45.4	46.8	49.4	51.4	26.6
85°	26.0	26.0	26.0	26.6	26.0	27.3	27.9	29.3	29.3	27.9	16.3
87.5°	16.9	16.3	16.9	16.3	16.3	15.6	15.6	15.6	14.9	14.3	9.1
90°	11.4	11.4	11.4	11.4	11.4	15.2	20.3	22.9	19.7	13.3	8.4
92.5°	45.7	36.6	45.7	54.8	57.1	80.9	112.7	128.6	112.9	81.5	57.9
95°	159.4	131.9	159.4	186.8	193.7	254.4	335.3	375.8	317.3	200.6	113.0
97.5°	381.9	329.6	381.9	434.2	447.3	485.7	536.7	562.3	464.9	270.2	124.0
100°	550.2	487.8	550.2	612.5	628.1	625.3	621.5	619.7	511.6	295.4	133.3
102.5°	715.7	662.3	715.7	769.1	782.5	733.6	668.5	636.0	526.4	307.1	142.6
105°	926.8	898.2	926.8	955.5	962.7	853.2	707.2	634.1	528.0	315.7	156.5
107.5°	1065.1	1072.1	1065.1	1058.1	1056.4	903.6	699.9	598.1	504.5	317.3	176.9
110°	1117.8	1147.8	1117.8	1087.9	1080.4	909.6	681.9	568.0	483.6	314.9	188.4

TEST NUMBER: P934684

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1122.6	1168.5	1122.6	1076.7	1065.1	890.3	657.3	540.7	465.5	315.0	202.1
115°	1092.8	1156.5	1092.8	1029.1	1013.2	844.8	620.3	507.9	444.6	317.9	222.9
117.5°	1029.7	1100.3	1029.7	959.0	941.4	789.3	586.7	485.4	431.5	323.8	243.0
120°	978.8	1047.4	978.8	910.2	893.0	754.2	569.0	476.4	427.1	328.6	254.8
122.5°	929.3	997.0	929.3	861.6	844.7	719.6	552.8	469.5	424.8	335.5	268.5
125°	858.6	920.9	858.6	796.3	780.7	674.5	532.9	462.0	423.0	344.9	286.2
127.5°	795.1	847.7	795.1	742.5	729.4	638.2	516.6	455.7	421.9	354.2	303.4
130°	757.7	806.2	757.7	709.0	696.9	615.7	507.5	453.3	422.5	361.0	314.8
132.5°	723.6	767.2	723.6	680.1	669.3	596.6	499.6	451.2	423.0	366.5	324.1
135°	677.1	714.6	677.1	639.6	630.2	569.4	488.2	447.6	422.6	372.5	334.9
137.5°	639.7	670.5	639.7	609.0	601.4	549.9	481.3	447.0	425.2	381.5	348.7
140°	614.2	642.8	614.2	585.4	578.2	533.7	474.5	444.9	425.6	387.0	358.0
142.5°	592.8	617.5	592.8	568.2	562.0	523.0	470.9	444.9	427.1	391.6	364.9
145°	561.1	579.8	561.1	542.3	537.7	505.7	463.2	441.9	427.1	397.6	375.5
147.5°	536.6	552.1	536.6	521.1	517.3	492.2	458.6	441.9	430.0	406.4	388.7
150°	521.2	533.8	521.2	508.6	505.5	484.3	456.0	441.9	431.6	411.0	395.6
152.5°	508.0	517.5	508.0	498.6	496.2	478.1	454.0	441.9	432.6	414.1	400.1
155°	492.9	499.2	492.9	486.6	485.1	470.6	451.5	441.9	434.8	420.6	410.0
157.5°	481.0	485.4	481.0	476.6	475.5	464.2	449.3	441.9	437.0	427.2	420.0
160°	473.8	476.4	473.8	471.3	470.7	461.1	448.3	441.9	438.0	430.2	424.4
162.5°	469.2	471.6	469.2	466.8	466.2	458.0	447.3	441.9	439.1	433.4	429.3
165°	462.5	465.0	462.5	460.0	459.3	453.5	445.7	441.9	440.6	438.1	436.1
167.5°	457.7	458.7	457.7	456.6	456.3	452.5	447.4	444.9	443.8	441.7	440.0
170°	456.3	456.3	456.3	456.3	456.3	452.5	447.4	444.9	444.8	444.7	444.6
172.5°	452.7	451.7	452.7	453.7	453.9	450.9	446.9	444.9	444.9	444.9	444.9
175°	450.6	450.6	450.6	450.6	450.6	448.6	446.1	444.9	445.4	446.7	447.6
177.5°	448.6	447.6	448.6	449.7	450.0	448.5	446.4	445.4	445.9	446.9	447.6
180°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6

TEST NUMBER: P934684

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9
2.5°	696.6	692.7	692.7	686.2	683.6	681.7	678.5	668.7	666.1	663.5	667.4
5°	702.5	695.4	690.1	678.5	668.7	664.8	652.4	629.1	613.5	601.7	595.3
7.5°	703.8	694.7	685.0	666.8	643.3	633.0	595.3	552.4	540.7	530.3	523.7
10°	702.5	692.1	678.5	651.2	595.9	577.7	540.0	512.1	504.9	503.0	504.9
12.5°	698.0	688.2	669.4	623.8	546.5	534.2	512.1	495.8	494.6	497.8	515.3
15°	690.1	681.0	658.9	587.5	519.3	510.2	494.6	488.7	495.8	518.6	571.2
17.5°	682.4	672.0	644.7	551.7	498.5	492.0	480.9	492.6	532.9	563.5	581.0
20°	672.0	659.6	628.4	525.8	483.5	477.6	472.5	525.1	555.6	566.7	576.5
22.5°	659.6	646.6	606.3	507.6	467.9	463.4	466.6	543.3	555.6	563.5	571.9
25°	643.3	632.3	580.3	493.2	455.5	450.4	462.7	541.4	548.5	550.4	567.3
27.5°	628.4	614.2	553.0	480.2	440.6	438.7	466.0	532.9	538.1	540.0	558.2
30°	610.2	588.8	522.5	466.6	425.0	424.3	466.6	522.5	521.2	526.4	544.6
32.5°	591.4	551.1	488.1	449.7	410.1	409.4	462.0	506.9	505.6	512.7	526.4
35°	573.8	521.8	441.3	430.2	391.2	391.9	451.0	488.7	489.3	495.8	504.3
37.5°	555.6	496.5	389.9	408.7	373.1	373.1	436.0	471.8	470.5	472.5	484.1
40°	534.2	456.9	344.4	380.8	356.1	354.2	417.8	453.6	449.0	448.5	464.6
42.5°	511.4	413.3	310.7	343.8	336.6	334.0	395.7	431.5	423.1	425.0	445.8
45°	486.7	401.7	284.6	290.5	316.5	314.5	371.7	406.2	400.3	405.5	426.9
47.5°	462.0	378.2	276.2	241.1	295.1	294.4	345.1	381.5	378.2	383.4	406.2
50°	428.3	352.2	275.6	206.7	271.0	273.5	313.3	357.5	357.5	362.0	386.0
52.5°	384.7	320.4	250.2	187.1	243.0	250.9	285.3	336.6	337.9	342.4	364.0
55°	345.1	287.2	232.0	172.2	209.9	226.8	257.9	315.2	317.7	322.3	341.9
57.5°	308.7	239.1	228.1	154.7	179.4	195.6	233.9	294.4	295.6	299.6	318.4
60°	269.7	172.9	209.3	135.9	152.7	165.0	211.8	269.7	274.2	276.8	293.1
62.5°	225.5	125.4	189.7	122.9	139.7	142.3	193.7	246.3	252.1	254.1	263.9
65°	160.6	105.2	161.1	111.8	126.1	126.7	174.1	222.3	227.4	230.7	237.9
67.5°	108.5	85.8	122.9	101.4	115.7	116.3	155.3	194.3	201.5	204.1	208.6
70°	75.4	57.2	91.0	90.3	104.0	105.2	135.2	169.0	175.5	177.4	180.0
72.5°	55.2	46.1	75.4	81.2	91.7	92.9	114.3	140.4	146.9	148.8	150.1
75°	42.2	48.7	61.0	70.8	78.0	78.6	93.6	114.3	118.9	120.3	120.8
77.5°	33.8	45.4	44.9	57.2	63.7	62.4	73.5	88.4	92.2	92.2	92.2
80°	25.4	35.8	33.8	41.0	46.8	45.4	52.6	63.1	64.3	65.6	65.0
82.5°	18.8	22.8	22.8	26.0	31.2	29.9	35.1	41.0	41.0	41.0	42.2
85°	11.7	13.0	10.4	13.7	17.5	16.9	19.5	22.1	22.8	22.8	21.4
87.5°	7.2	5.8	3.3	5.2	7.8	7.8	9.1	9.8	9.1	9.1	9.1
90°	7.8	5.4	3.0	5.4	7.8	8.4	13.3	19.7	22.9	20.3	15.2
92.5°	52.8	32.5	12.0	32.5	52.8	57.9	81.5	112.9	128.6	112.7	80.9
95°	103.7	66.3	28.9	66.3	103.7	113.0	200.6	317.3	375.8	335.3	254.4
97.5°	115.8	82.8	49.9	82.8	115.8	124.0	270.2	464.9	562.3	536.7	485.7
100°	125.9	95.9	66.1	95.9	125.9	133.3	295.4	511.6	619.7	621.5	625.3
102.5°	135.7	107.8	79.9	107.8	135.7	142.6	307.1	526.4	636.0	668.5	733.6
105°	150.6	126.9	103.3	126.9	150.6	156.5	315.7	528.0	634.1	707.2	853.2
107.5°	171.4	149.4	127.3	149.4	171.4	176.9	317.3	504.5	598.1	699.9	903.6
110°	183.4	163.5	143.6	163.5	183.4	188.4	314.9	483.6	568.0	681.9	909.6

TEST NUMBER: P934684

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	197.4	178.5	159.5	178.5	197.4	202.1	315.0	465.5	540.7	657.3	890.3
115°	218.5	201.0	183.5	201.0	218.5	222.9	317.9	444.6	507.9	620.3	844.8
117.5°	239.1	223.2	207.3	223.2	239.1	243.0	323.8	431.5	485.4	586.7	789.3
120°	251.0	236.0	221.1	236.0	251.0	254.8	328.6	427.1	476.4	569.0	754.2
122.5°	264.7	249.7	234.6	249.7	264.7	268.5	335.5	424.8	469.5	552.8	719.6
125°	282.9	269.1	255.3	269.1	282.9	286.2	344.9	423.0	462.0	532.9	674.5
127.5°	299.9	286.0	272.2	286.0	299.9	303.4	354.2	421.9	455.7	516.6	638.2
130°	311.0	296.1	281.2	296.1	311.0	314.8	361.0	422.5	453.3	507.5	615.7
132.5°	320.4	305.4	290.5	305.4	320.4	324.1	366.5	423.0	451.2	499.6	596.6
135°	331.5	317.8	304.3	317.8	331.5	334.9	372.5	422.6	447.6	488.2	569.4
137.5°	345.4	331.9	318.4	331.9	345.4	348.7	381.5	425.2	447.0	481.3	549.9
140°	354.9	342.5	330.1	342.5	354.9	358.0	387.0	425.6	444.9	474.5	533.7
142.5°	362.0	350.6	339.2	350.6	362.0	364.9	391.6	427.1	444.9	470.9	523.0
145°	373.0	363.0	352.9	363.0	373.0	375.5	397.6	427.1	441.9	463.2	505.7
147.5°	386.2	376.5	366.8	376.5	386.2	388.7	406.4	430.0	441.9	458.6	492.2
150°	393.4	384.6	375.8	384.6	393.4	395.6	411.0	431.6	441.9	456.0	484.3
152.5°	398.5	391.8	385.1	391.8	398.5	400.1	414.1	432.6	441.9	454.0	478.1
155°	408.7	403.9	398.9	403.9	408.7	410.0	420.6	434.8	441.9	451.5	470.6
157.5°	418.8	414.0	409.1	414.0	418.8	420.0	427.2	437.0	441.9	449.3	464.2
160°	423.5	419.8	416.0	419.8	423.5	424.4	430.2	438.0	441.9	448.3	461.1
162.5°	428.6	425.8	423.0	425.8	428.6	429.3	433.4	439.1	441.9	447.3	458.0
165°	435.5	432.9	430.4	432.9	435.5	436.1	438.1	440.6	441.9	445.7	453.5
167.5°	439.7	438.5	437.3	438.5	439.7	440.0	441.7	443.8	444.9	447.4	452.5
170°	444.3	443.0	441.9	443.0	444.3	444.6	444.7	444.8	444.9	447.4	452.5
172.5°	444.8	444.6	444.3	444.6	444.8	444.9	444.9	444.9	444.9	446.9	450.9
175°	447.6	447.6	447.6	447.6	447.6	447.6	446.7	445.4	444.9	446.1	448.6
177.5°	447.6	447.6	447.6	447.6	447.6	447.6	446.9	445.9	445.4	446.4	448.5
180°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6

TEST NUMBER: P934684

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9
2.5°	662.9	661.0	663.5	656.4	663.5	661.0	662.9	667.4	663.5	666.1	668.7
5°	581.6	578.4	568.0	559.5	568.0	578.4	581.6	595.3	601.7	613.5	629.1
7.5°	519.9	517.3	514.7	509.5	514.7	517.3	519.9	523.7	530.3	540.7	552.4
10°	506.2	506.9	510.8	510.2	510.8	506.9	506.2	504.9	503.0	504.9	512.1
12.5°	541.4	547.2	568.6	567.3	568.6	547.2	541.4	515.3	497.8	494.6	495.8
15°	581.6	583.5	588.1	588.8	588.1	583.5	581.6	571.2	518.6	495.8	488.7
17.5°	585.6	586.1	589.4	589.4	589.4	586.1	585.6	581.0	563.5	532.9	492.6
20°	582.3	583.5	590.1	591.4	590.1	583.5	582.3	576.5	566.7	555.6	525.1
22.5°	581.0	583.5	588.8	588.1	588.8	583.5	581.0	571.9	563.5	555.6	543.3
25°	574.5	574.5	575.1	575.8	575.1	574.5	574.5	567.3	550.4	548.5	541.4
27.5°	560.9	562.1	566.0	565.4	566.0	562.1	560.9	558.2	540.0	538.1	532.9
30°	548.5	547.2	543.9	541.4	543.9	547.2	548.5	544.6	526.4	521.2	522.5
32.5°	527.7	524.4	521.2	519.3	521.2	524.4	527.7	526.4	512.7	505.6	506.9
35°	503.0	503.7	503.0	501.1	503.0	503.7	503.0	504.3	495.8	489.3	488.7
37.5°	485.5	486.7	486.1	483.5	486.1	486.7	485.5	484.1	472.5	470.5	471.8
40°	467.3	467.9	467.3	465.3	467.3	467.9	467.3	464.6	448.5	449.0	453.6
42.5°	449.7	449.0	447.1	445.8	447.1	449.0	449.7	445.8	425.0	423.1	431.5
45°	429.6	430.2	426.3	424.3	426.3	430.2	429.6	426.9	405.5	400.3	406.2
47.5°	409.4	409.4	406.2	404.2	406.2	409.4	409.4	406.2	383.4	378.2	381.5
50°	388.0	387.3	382.8	382.1	382.8	387.3	388.0	386.0	362.0	357.5	357.5
52.5°	363.3	363.3	364.0	365.2	364.0	363.3	363.3	364.0	342.4	337.9	336.6
55°	341.9	342.4	347.0	348.4	347.0	342.4	341.9	341.9	322.3	317.7	315.2
57.5°	319.8	319.8	323.0	323.0	323.0	319.8	319.8	318.4	299.6	295.6	294.4
60°	294.4	295.6	298.3	297.7	298.3	295.6	294.4	293.1	276.8	274.2	269.7
62.5°	267.7	269.1	269.7	268.4	269.7	269.1	267.7	263.9	254.1	252.1	246.3
65°	239.8	241.1	241.8	240.4	241.8	241.1	239.8	237.9	230.7	227.4	222.3
67.5°	211.2	210.6	209.9	212.5	209.9	210.6	211.2	208.6	204.1	201.5	194.3
70°	182.0	182.0	181.3	182.7	181.3	182.0	182.0	180.0	177.4	175.5	169.0
72.5°	150.8	150.1	152.7	150.8	152.7	150.1	150.8	150.1	148.8	146.9	140.4
75°	120.3	121.5	120.3	122.2	120.3	121.5	120.3	120.8	120.3	118.9	114.3
77.5°	91.7	92.9	91.7	91.7	91.7	92.9	91.7	92.2	92.2	92.2	88.4
80°	65.0	64.3	64.3	63.7	64.3	64.3	65.0	65.0	65.6	64.3	63.1
82.5°	41.6	41.0	41.0	42.2	41.0	41.0	41.6	42.2	41.0	41.0	41.0
85°	22.8	23.4	22.1	22.1	22.1	23.4	22.8	21.4	22.8	22.8	22.1
87.5°	8.4	7.8	7.8	7.8	7.8	7.8	8.4	9.1	9.1	9.1	9.8
90°	11.4	11.4	11.4	11.4	11.4	11.4	11.4	15.2	20.3	22.9	19.7
92.5°	57.1	54.8	45.7	36.6	45.7	54.8	57.1	80.9	112.7	128.6	112.9
95°	193.7	186.8	159.4	131.9	159.4	186.8	193.7	254.4	335.3	375.8	317.3
97.5°	447.3	434.2	381.9	329.6	381.9	434.2	447.3	485.7	536.7	562.3	464.9
100°	628.1	612.5	550.2	487.8	550.2	612.5	628.1	625.3	621.5	619.7	511.6
102.5°	782.5	769.1	715.7	662.3	715.7	769.1	782.5	733.6	668.5	636.0	526.4
105°	962.7	955.5	926.8	898.2	926.8	955.5	962.7	853.2	707.2	634.1	528.0
107.5°	1056.4	1058.1	1065.1	1072.1	1065.1	1058.1	1056.4	903.6	699.9	598.1	504.5
110°	1080.4	1087.9	1117.8	1147.8	1117.8	1087.9	1080.4	909.6	681.9	568.0	483.6

TEST NUMBER: P934684

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1065.1	1076.7	1122.6	1168.5	1122.6	1076.7	1065.1	890.3	657.3	540.7	465.5
115°	1013.2	1029.1	1092.8	1156.5	1092.8	1029.1	1013.2	844.8	620.3	507.9	444.6
117.5°	941.4	959.0	1029.7	1100.3	1029.7	959.0	941.4	789.3	586.7	485.4	431.5
120°	893.0	910.2	978.8	1047.4	978.8	910.2	893.0	754.2	569.0	476.4	427.1
122.5°	844.7	861.6	929.3	997.0	929.3	861.6	844.7	719.6	552.8	469.5	424.8
125°	780.7	796.3	858.6	920.9	858.6	796.3	780.7	674.5	532.9	462.0	423.0
127.5°	729.4	742.5	795.1	847.7	795.1	742.5	729.4	638.2	516.6	455.7	421.9
130°	696.9	709.0	757.7	806.2	757.7	709.0	696.9	615.7	507.5	453.3	422.5
132.5°	669.3	680.1	723.6	767.2	723.6	680.1	669.3	596.6	499.6	451.2	423.0
135°	630.2	639.6	677.1	714.6	677.1	639.6	630.2	569.4	488.2	447.6	422.6
137.5°	601.4	609.0	639.7	670.5	639.7	609.0	601.4	549.9	481.3	447.0	425.2
140°	578.2	585.4	614.2	642.8	614.2	585.4	578.2	533.7	474.5	444.9	425.6
142.5°	562.0	568.2	592.8	617.5	592.8	568.2	562.0	523.0	470.9	444.9	427.1
145°	537.7	542.3	561.1	579.8	561.1	542.3	537.7	505.7	463.2	441.9	427.1
147.5°	517.3	521.1	536.6	552.1	536.6	521.1	517.3	492.2	458.6	441.9	430.0
150°	505.5	508.6	521.2	533.8	521.2	508.6	505.5	484.3	456.0	441.9	431.6
152.5°	496.2	498.6	508.0	517.5	508.0	498.6	496.2	478.1	454.0	441.9	432.6
155°	485.1	486.6	492.9	499.2	492.9	486.6	485.1	470.6	451.5	441.9	434.8
157.5°	475.5	476.6	481.0	485.4	481.0	476.6	475.5	464.2	449.3	441.9	437.0
160°	470.7	471.3	473.8	476.4	473.8	471.3	470.7	461.1	448.3	441.9	438.0
162.5°	466.2	466.8	469.2	471.6	469.2	466.8	466.2	458.0	447.3	441.9	439.1
165°	459.3	460.0	462.5	465.0	462.5	460.0	459.3	453.5	445.7	441.9	440.6
167.5°	456.3	456.6	457.7	458.7	457.7	456.6	456.3	452.5	447.4	444.9	443.8
170°	456.3	456.3	456.3	456.3	456.3	456.3	456.3	452.5	447.4	444.9	444.8
172.5°	453.9	453.7	452.7	451.7	452.7	453.7	453.9	450.9	446.9	444.9	444.9
175°	450.6	450.6	450.6	450.6	450.6	450.6	450.6	448.6	446.1	444.9	445.4
177.5°	450.0	449.7	448.6	447.6	448.6	449.7	450.0	448.5	446.4	445.4	445.9
180°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6

TEST NUMBER: P934684

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	686.9	686.9	686.9	686.9	686.9
2.5°	678.5	681.7	683.6	686.2	692.7
5°	652.4	664.8	668.7	678.5	690.1
7.5°	595.3	633.0	643.3	666.8	685.0
10°	540.0	577.7	595.9	651.2	678.5
12.5°	512.1	534.2	546.5	623.8	669.4
15°	494.6	510.2	519.3	587.5	658.9
17.5°	480.9	492.0	498.5	551.7	644.7
20°	472.5	477.6	483.5	525.8	628.4
22.5°	466.6	463.4	467.9	507.6	606.3
25°	462.7	450.4	455.5	493.2	580.3
27.5°	466.0	438.7	440.6	480.2	553.0
30°	466.6	424.3	425.0	466.6	522.5
32.5°	462.0	409.4	410.1	449.7	488.1
35°	451.0	391.9	391.2	430.2	441.3
37.5°	436.0	373.1	373.1	408.7	389.9
40°	417.8	354.2	356.1	380.8	344.4
42.5°	395.7	334.0	336.6	343.8	310.7
45°	371.7	314.5	316.5	290.5	284.6
47.5°	345.1	294.4	295.1	241.1	276.2
50°	313.3	273.5	271.0	206.7	275.6
52.5°	285.3	250.9	243.0	187.1	250.2
55°	257.9	226.8	209.9	172.2	232.0
57.5°	233.9	195.6	179.4	154.7	228.1
60°	211.8	165.0	152.7	135.9	209.3
62.5°	193.7	142.3	139.7	122.9	189.7
65°	174.1	126.7	126.1	111.8	161.1
67.5°	155.3	116.3	115.7	101.4	122.9
70°	135.2	105.2	104.0	90.3	91.0
72.5°	114.3	92.9	91.7	81.2	75.4
75°	93.6	78.6	78.0	70.8	61.0
77.5°	73.5	62.4	63.7	57.2	44.9
80°	52.6	45.4	46.8	41.0	33.8
82.5°	35.1	29.9	31.2	26.0	22.8
85°	19.5	16.9	17.5	13.7	10.4
87.5°	9.1	7.8	7.8	5.2	3.3
90°	13.3	8.4	7.8	5.4	3.0
92.5°	81.5	57.9	52.8	32.5	12.0
95°	200.6	113.0	103.7	66.3	28.9
97.5°	270.2	124.0	115.8	82.8	49.9
100°	295.4	133.3	125.9	95.9	66.1
102.5°	307.1	142.6	135.7	107.8	79.9
105°	315.7	156.5	150.6	126.9	103.3
107.5°	317.3	176.9	171.4	149.4	127.3
110°	314.9	188.4	183.4	163.5	143.6

TEST NUMBER: P934684

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	315.0	202.1	197.4	178.5	159.5
115°	317.9	222.9	218.5	201.0	183.5
117.5°	323.8	243.0	239.1	223.2	207.3
120°	328.6	254.8	251.0	236.0	221.1
122.5°	335.5	268.5	264.7	249.7	234.6
125°	344.9	286.2	282.9	269.1	255.3
127.5°	354.2	303.4	299.9	286.0	272.2
130°	361.0	314.8	311.0	296.1	281.2
132.5°	366.5	324.1	320.4	305.4	290.5
135°	372.5	334.9	331.5	317.8	304.3
137.5°	381.5	348.7	345.4	331.9	318.4
140°	387.0	358.0	354.9	342.5	330.1
142.5°	391.6	364.9	362.0	350.6	339.2
145°	397.6	375.5	373.0	363.0	352.9
147.5°	406.4	388.7	386.2	376.5	366.8
150°	411.0	395.6	393.4	384.6	375.8
152.5°	414.1	400.1	398.5	391.8	385.1
155°	420.6	410.0	408.7	403.9	398.9
157.5°	427.2	420.0	418.8	414.0	409.1
160°	430.2	424.4	423.5	419.8	416.0
162.5°	433.4	429.3	428.6	425.8	423.0
165°	438.1	436.1	435.5	432.9	430.4
167.5°	441.7	440.0	439.7	438.5	437.3
170°	444.7	444.6	444.3	443.0	441.9
172.5°	444.9	444.9	444.8	444.6	444.3
175°	446.7	447.6	447.6	447.6	447.6
177.5°	446.9	447.6	447.6	447.6	447.6
180°	447.6	447.6	447.6	447.6	447.6

TEST NUMBER: P934684

CATALOG NUMBER: SQ4-FA-075U-050D-B2750-1D-UNV-W2A-W-4-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.01	10.78	11.07	11.83	13.27	12.81	13.57	13.86	14.63	16.06
	3H	10.48	11.17	11.55	12.23	13.68	14.14	14.82	15.20	15.89	17.34
	4H	10.67	11.32	11.74	12.38	13.84	14.57	15.22	15.65	16.29	17.74
	6H	10.78	11.38	11.87	12.45	13.92	14.84	15.44	15.93	16.51	17.98
	8H	10.78	11.35	11.87	12.44	13.90	14.91	15.48	16.00	16.57	18.03
	12H	10.75	11.29	11.84	12.37	13.86	14.94	15.48	16.03	16.56	18.05
4H	2H	11.03	11.67	12.11	12.74	14.20	13.21	13.86	14.29	14.93	16.38
	3H	12.04	12.58	13.13	13.68	15.15	14.70	15.24	15.78	16.33	17.80
	4H	12.31	12.81	13.41	13.90	15.39	15.21	15.71	16.31	16.79	18.29
	6H	12.43	12.86	13.54	13.97	15.45	15.56	15.99	16.67	17.10	18.58
	8H	12.44	12.84	13.54	13.94	15.44	15.66	16.06	16.77	17.16	18.66
	12H	12.40	12.76	13.52	13.87	15.38	15.71	16.07	16.83	17.18	18.69
8H	4H	12.76	13.15	13.86	14.25	15.75	15.33	15.73	16.43	16.83	18.33
	6H	13.01	13.34	14.14	14.48	15.98	15.75	16.08	16.88	17.23	18.72
	8H	13.05	13.34	14.19	14.47	15.98	15.90	16.19	17.03	17.31	18.83
	12H	13.03	13.29	14.17	14.41	15.96	15.99	16.24	17.12	17.36	18.92
12H	4H	12.76	13.11	13.87	14.23	15.73	15.29	15.65	16.41	16.76	18.27
	6H	13.07	13.36	14.20	14.48	16.00	15.75	16.04	16.88	17.16	18.68
	8H	13.13	13.39	14.27	14.51	16.06	15.90	16.16	17.04	17.28	18.83

END OF REPORT