

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P935085

Luminaire Tested: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P935085
REPORT IS A COMBINATION OF REPORTS P933738 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5594.4 lumens
Efficiency: N/A
Efficacy: 135.8 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P935085

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-4000K

Luminous Intensity Polar Plot



TEST NUMBER: P935085

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33
2	85	78	72	67	76	70	65	61	56	53	50	43	40	38	30	29	28
3	78	69	62	56	70	62	56	51	49	45	42	38	35	32	27	25	24
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	15
7	55	43	36	30	49	39	33	28	32	27	23	25	21	18	18	15	14
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12
9	47	36	28	23	43	32	26	22	26	21	18	20	17	15	15	13	11
10	44	33	26	21	40	30	23	19	24	19	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6282	6282	6282	6282
5°	6322	6342	6322	4986
10°	6273	6247	6273	4466
15°	6197	6112	6197	5103
20°	6060	5950	6060	5113
25°	5788	5717	5788	5005
30°	5439	5523	5439	4768
35°	4842	5277	4842	4506
40°	4027	4989	4027	4308
45°	3591	4650	3591	4081
50°	3807	4246	3807	3853
55°	3571	3811	3571	3721
60°	3670	3237	3670	3409
65°	3309	2676	3309	2990
70°	2277	2133	2277	2508
75°	1974	1577	1974	1888
80°	1558	1043	1558	1134
85°	845	552	845	470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 5515 cd/sqm

TEST NUMBER: P935085

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.1	1.1
10°-20°	173.5	3.1
20°-30°	268.2	4.8
30°-40°	320.2	5.7
40°-50°	322.1	5.8
50°-60°	280.2	5.0
60°-70°	198.7	3.6
70°-80°	105.1	1.9
80°-90°	28.4	0.5
90°-100°	288.5	5.2
100°-110°	758.5	13.6
110°-120°	786.5	14.1
120°-130°	630.8	11.3
130°-140°	495.0	8.8
140°-150°	379.9	6.8
150°-160°	273.6	4.9
160°-170°	167.4	3.0
170°-180°	56.6	1.0
0°-30°	502.8	9.0
0°-40°	823.0	14.7
0°-60°	1425.3	25.5
0°-90°	1757.6	31.4
90°-120°	1833.5	32.8
90°-150°	3339.2	59.7
90°-180°	3837.0	68.6
0°-180°	5594.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	677	677	677	677	677	
5°	680	701	680	551	680	65
15°	649	695	649	580	649	183
25°	572	648	572	568	572	263
35°	435	578	435	494	435	269
45°	280	476	280	418	280	225
55°	229	352	229	343	229	210
65°	159	212	159	237	159	152
75°	60	101	60	120	60	63
85°	10	26	10	22	10	14
90°	4	15	4	15	4	4
95°	38	174	38	174	38	42
105°	137	1188	137	1188	137	145
115°	243	1529	243	1529	243	240
125°	338	1218	338	1218	338	300
135°	402	945	402	945	402	311
145°	467	767	467	767	467	292
155°	528	660	528	660	528	242
165°	569	615	569	615	569	161
175°	592	596	592	596	592	56
180°	592	592	592	592	592	

TEST NUMBER: P935085

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0
2.5°	682.7	682.7	686.5	687.9	687.9	686.0	684.1	686.0	691.7	693.6	692.9
5°	680.2	685.3	692.4	693.6	695.0	694.3	692.9	694.3	700.7	701.9	702.6
7.5°	675.1	684.6	693.6	695.5	697.4	695.5	695.0	696.2	702.6	703.8	703.8
10°	668.7	682.1	692.4	693.6	695.5	693.6	693.6	696.2	702.6	703.8	704.5
12.5°	659.7	678.2	687.9	689.1	691.7	691.0	690.5	692.9	699.4	700.7	700.7
15°	649.4	671.2	680.2	681.5	686.0	684.6	684.6	687.2	694.3	696.2	695.5
17.5°	635.4	662.3	672.5	674.4	677.7	677.0	677.7	680.2	686.5	687.9	688.6
20°	619.3	650.1	662.3	664.2	667.4	667.4	667.4	670.6	677.0	679.6	679.6
22.5°	597.5	637.3	650.1	651.4	655.2	655.2	656.5	661.0	666.7	667.4	667.4
25°	571.9	623.1	634.0	637.9	641.8	643.7	645.6	648.2	650.1	649.4	650.1
27.5°	545.0	605.3	619.3	621.9	627.1	629.0	631.5	632.1	632.8	634.7	633.5
30°	514.9	580.3	601.4	603.9	612.3	613.6	611.0	612.3	615.5	616.7	618.1
32.5°	481.0	543.1	582.8	588.6	596.3	592.5	591.8	593.7	598.9	598.9	600.1
35°	434.9	514.3	565.6	570.7	576.4	571.9	574.5	575.1	578.3	580.3	579.6
37.5°	384.3	489.3	547.6	551.4	555.9	550.2	554.0	555.9	558.5	557.2	557.2
40°	339.4	450.3	526.5	529.1	532.9	528.4	532.2	533.6	534.8	533.6	532.9
42.5°	306.2	407.3	504.0	507.3	504.7	507.9	509.2	511.8	509.8	507.3	507.3
45°	280.5	395.8	479.7	483.5	479.7	484.9	486.8	486.8	481.0	479.7	479.0
47.5°	272.2	372.7	455.3	455.3	453.4	459.8	463.1	458.6	452.9	450.9	450.9
50°	271.6	347.1	422.1	419.5	428.5	436.1	433.0	428.5	424.0	417.0	417.0
52.5°	246.6	315.7	379.1	388.8	402.8	407.3	402.2	397.8	390.0	386.9	384.3
55°	228.6	283.1	340.1	359.3	374.1	379.8	370.2	365.7	354.2	352.3	351.0
57.5°	224.8	235.7	304.3	328.5	346.5	345.9	340.1	331.8	322.1	320.2	319.6
60°	206.3	170.4	265.8	294.6	313.1	311.2	306.2	298.4	289.5	288.2	287.0
62.5°	187.0	123.6	222.2	254.9	281.2	280.5	276.1	264.5	258.1	254.9	252.3
65°	158.8	103.7	158.2	212.0	249.8	251.1	241.4	233.1	226.0	222.2	221.6
67.5°	121.1	84.5	107.0	176.8	219.6	218.4	206.3	202.4	193.4	191.5	187.7
70°	89.7	56.3	74.3	143.4	190.2	187.0	177.4	173.0	164.6	160.2	157.6
72.5°	74.3	45.5	54.4	111.4	160.2	156.2	147.9	142.9	135.8	132.0	129.4
75°	60.2	48.0	41.6	82.6	130.0	127.5	119.8	114.6	108.9	103.7	104.4
77.5°	44.2	44.8	33.3	60.8	103.1	99.3	94.8	88.4	85.9	80.7	80.7
80°	33.3	35.2	25.0	41.6	74.3	74.3	70.5	66.0	61.5	58.9	58.9
82.5°	22.4	22.4	18.5	26.3	50.6	48.7	46.1	44.8	42.3	41.0	41.0
85°	10.2	12.8	11.6	16.0	27.5	28.8	28.8	27.5	26.9	25.6	26.3
87.5°	3.2	5.7	7.1	9.0	14.1	14.7	15.4	15.4	15.4	16.0	16.0
90°	4.0	7.2	10.3	11.1	17.5	26.0	30.2	26.8	20.2	15.1	15.1
92.5°	15.9	42.9	69.9	76.7	107.8	149.3	170.0	149.0	107.0	75.4	72.5
95°	38.1	87.6	137.0	149.4	265.2	419.6	496.9	443.4	336.4	256.2	247.2
97.5°	65.9	109.5	153.2	164.1	357.3	614.8	743.6	709.8	642.1	591.4	574.1
100°	87.4	126.9	166.5	176.4	390.8	676.6	819.5	822.0	826.8	830.6	809.9
102.5°	105.6	142.6	179.4	188.7	406.2	696.0	841.0	884.0	970.2	1034.7	1017.1
105°	136.7	167.9	199.1	206.9	417.5	698.2	838.6	935.1	1128.2	1273.1	1263.7
107.5°	168.5	197.6	226.7	234.0	419.6	667.1	790.8	925.6	1195.0	1397.1	1399.4
110°	189.9	216.2	242.5	249.1	416.4	639.6	751.1	901.7	1202.9	1428.8	1438.7

TEST NUMBER: P935085

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	211.0	236.0	261.0	267.3	416.6	615.5	715.0	869.1	1177.3	1408.5	1423.7
115°	242.7	265.8	288.9	294.7	420.4	588.0	671.7	820.2	1117.2	1339.9	1360.9
117.5°	274.1	295.1	316.1	321.4	428.2	570.7	642.0	775.9	1043.9	1244.9	1268.2
120°	292.3	312.1	331.9	336.8	434.5	564.9	630.0	752.4	997.3	1181.0	1203.7
122.5°	310.3	330.2	350.2	355.2	443.7	561.8	620.8	731.1	951.6	1117.0	1139.3
125°	337.7	355.8	374.0	378.6	456.0	559.2	610.9	704.6	891.9	1032.4	1053.0
127.5°	359.8	378.2	396.6	401.2	468.3	557.8	602.6	683.0	843.8	964.5	981.8
130°	371.8	391.6	411.3	416.3	477.3	558.8	599.5	671.1	814.2	921.6	937.6
132.5°	384.1	403.9	423.6	428.6	484.6	559.2	596.6	660.7	788.8	885.0	899.4
135°	402.4	420.4	438.4	442.9	492.6	558.8	591.9	645.6	752.8	833.3	845.7
137.5°	421.1	438.9	456.7	461.2	504.4	562.2	591.0	636.4	727.1	795.2	805.4
140°	436.5	453.0	469.4	473.5	511.8	562.8	588.3	627.4	705.8	764.7	774.1
142.5°	448.5	463.7	478.8	482.7	517.9	564.8	588.3	622.7	691.5	743.2	751.4
145°	466.7	480.0	493.2	496.5	525.8	564.9	584.4	612.5	668.8	711.0	717.2
147.5°	485.0	497.9	510.7	514.0	537.5	568.7	584.4	606.5	650.8	684.1	689.2
150°	496.9	508.5	520.2	523.1	543.6	570.8	584.4	603.1	640.4	668.5	672.6
152.5°	509.2	518.0	526.9	529.1	547.5	572.0	584.4	600.3	632.2	656.2	659.3
155°	527.5	534.0	540.6	542.2	556.3	575.0	584.4	597.1	622.5	641.5	643.6
157.5°	541.0	547.4	553.7	555.3	565.0	577.9	584.4	594.2	614.0	628.8	630.2
160°	550.2	555.1	560.0	561.3	569.0	579.2	584.4	592.9	609.8	622.5	623.3
162.5°	559.2	563.0	566.7	567.7	573.2	580.6	584.4	591.5	605.8	616.5	617.2
165°	569.2	572.5	575.9	576.7	579.3	582.6	584.4	589.5	599.7	607.4	608.2
167.5°	578.3	580.0	581.6	582.0	584.1	586.8	588.3	591.6	598.3	603.4	603.8
170°	584.4	585.9	587.5	587.9	588.0	588.2	588.3	591.6	598.3	603.4	603.4
172.5°	587.5	587.9	588.2	588.3	588.3	588.3	588.3	591.0	596.2	600.2	599.9
175°	591.9	591.9	591.9	591.9	590.7	589.0	588.3	590.0	593.3	595.8	595.8
177.5°	591.9	591.9	591.9	591.9	591.0	589.7	589.0	590.4	593.1	595.1	594.7
180°	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9

TEST NUMBER: P935085

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0
2.5°	694.3	692.4	694.3	692.9	693.6	691.7	686.0	684.1	686.0	687.9	687.9
5°	702.6	701.4	702.6	702.6	701.9	700.7	694.3	692.9	694.3	695.0	693.6
7.5°	705.2	703.3	705.2	703.8	703.8	702.6	696.2	695.0	695.5	697.4	695.5
10°	705.2	703.3	705.2	704.5	703.8	702.6	696.2	693.6	693.6	695.5	693.6
12.5°	701.9	700.7	701.9	700.7	700.7	699.4	692.9	690.5	691.0	691.7	689.1
15°	696.9	695.0	696.9	695.5	696.2	694.3	687.2	684.6	684.6	686.0	681.5
17.5°	689.1	686.5	689.1	688.6	687.9	686.5	680.2	677.7	677.0	677.7	674.4
20°	680.2	678.2	680.2	679.6	679.6	677.0	670.6	667.4	667.4	667.4	664.2
22.5°	666.1	664.2	666.1	667.4	667.4	666.7	661.0	656.5	655.2	655.2	651.4
25°	650.1	648.2	650.1	650.1	649.4	650.1	648.2	645.6	643.7	641.8	637.9
27.5°	634.7	633.5	634.7	633.5	634.7	632.8	632.1	631.5	629.0	627.1	621.9
30°	619.3	618.1	619.3	618.1	616.7	615.5	612.3	611.0	613.6	612.3	603.9
32.5°	600.1	598.9	600.1	600.1	598.9	598.9	593.7	591.8	592.5	596.3	588.6
35°	580.3	578.3	580.3	579.6	580.3	578.3	575.1	574.5	571.9	576.4	570.7
37.5°	557.2	555.3	557.2	557.2	557.2	558.5	555.9	554.0	550.2	555.9	551.4
40°	533.6	531.0	533.6	532.9	533.6	534.8	533.6	532.2	528.4	532.9	529.1
42.5°	506.6	506.0	506.6	507.3	507.3	509.8	511.8	509.2	507.9	504.7	507.3
45°	477.8	476.5	477.8	479.0	479.7	481.0	486.8	486.8	484.9	479.7	483.5
47.5°	447.0	443.9	447.0	450.9	450.9	452.9	458.6	463.1	459.8	453.4	455.3
50°	414.4	415.0	414.4	417.0	417.0	424.0	428.5	433.0	436.1	428.5	419.5
52.5°	382.4	381.7	382.4	384.3	386.9	390.0	397.8	402.2	407.3	402.8	388.8
55°	350.3	351.6	350.3	351.0	352.3	354.2	365.7	370.2	379.8	374.1	359.3
57.5°	318.3	316.4	318.3	319.6	320.2	322.1	331.8	340.1	345.9	346.5	328.5
60°	281.2	278.6	281.2	287.0	288.2	289.5	298.4	306.2	311.2	313.1	294.6
62.5°	248.5	244.0	248.5	252.3	254.9	258.1	264.5	276.1	280.5	281.2	254.9
65°	213.9	212.0	213.9	221.6	222.2	226.0	233.1	241.4	251.1	249.8	212.0
67.5°	182.5	182.5	182.5	187.7	191.5	193.4	202.4	206.3	218.4	219.6	176.8
70°	153.8	153.1	153.8	157.6	160.2	164.6	173.0	177.4	187.0	190.2	143.4
72.5°	126.2	125.5	126.2	129.4	132.0	135.8	142.9	147.9	156.2	160.2	111.4
75°	101.8	100.6	101.8	104.4	103.7	108.9	114.6	119.8	127.5	130.0	82.6
77.5°	78.1	78.1	78.1	80.7	80.7	85.9	88.4	94.8	99.3	103.1	60.8
80°	58.3	57.7	58.3	58.9	58.9	61.5	66.0	70.5	74.3	74.3	41.6
82.5°	41.0	39.7	41.0	41.0	41.0	42.3	44.8	46.1	48.7	50.6	26.3
85°	25.6	25.6	25.6	26.3	25.6	26.9	27.5	28.8	28.8	27.5	16.0
87.5°	16.6	16.0	16.6	16.0	16.0	15.4	15.4	15.4	14.7	14.1	9.0
90°	15.1	15.1	15.1	15.1	15.1	20.2	26.8	30.2	26.0	17.5	11.1
92.5°	60.5	48.4	60.5	72.5	75.4	107.0	149.0	170.0	149.3	107.8	76.7
95°	210.8	174.4	210.8	247.2	256.2	336.4	443.4	496.9	419.6	265.2	149.4
97.5°	504.9	435.8	504.9	574.1	591.4	642.1	709.8	743.6	614.8	357.3	164.1
100°	727.5	645.1	727.5	809.9	830.6	826.8	822.0	819.5	676.6	390.8	176.4
102.5°	946.5	875.9	946.5	1017.1	1034.7	970.2	884.0	841.0	696.0	406.2	188.7
105°	1225.6	1187.7	1225.6	1263.7	1273.1	1128.2	935.1	838.6	698.2	417.5	206.9
107.5°	1408.5	1417.7	1408.5	1399.4	1397.1	1195.0	925.6	790.8	667.1	419.6	234.0
110°	1478.2	1517.8	1478.2	1438.7	1428.8	1202.9	901.7	751.1	639.6	416.4	249.1

TEST NUMBER: P935085

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1484.5	1545.2	1484.5	1423.7	1408.5	1177.3	869.1	715.0	615.5	416.6	267.3
115°	1445.1	1529.3	1445.1	1360.9	1339.9	1117.2	820.2	671.7	588.0	420.4	294.7
117.5°	1361.6	1455.0	1361.6	1268.2	1244.9	1043.9	775.9	642.0	570.7	428.2	321.4
120°	1294.4	1385.1	1294.4	1203.7	1181.0	997.3	752.4	630.0	564.9	434.5	336.8
122.5°	1228.9	1318.4	1228.9	1139.3	1117.0	951.6	731.1	620.8	561.8	443.7	355.2
125°	1135.4	1217.9	1135.4	1053.0	1032.4	891.9	704.6	610.9	559.2	456.0	378.6
127.5°	1051.5	1121.0	1051.5	981.8	964.5	843.8	683.0	602.6	557.8	468.3	401.2
130°	1001.9	1066.2	1001.9	937.6	921.6	814.2	671.1	599.5	558.8	477.3	416.3
132.5°	956.9	1014.5	956.9	899.4	885.0	788.8	660.7	596.6	559.2	484.6	428.6
135°	895.3	945.0	895.3	845.7	833.3	752.8	645.6	591.9	558.8	492.6	442.9
137.5°	846.0	886.6	846.0	805.4	795.2	727.1	636.4	591.0	562.2	504.4	461.2
140°	812.1	850.0	812.1	774.1	764.7	705.8	627.4	588.3	562.8	511.8	473.5
142.5°	784.1	816.7	784.1	751.4	743.2	691.5	622.7	588.3	564.8	517.9	482.7
145°	741.9	766.7	741.9	717.2	711.0	668.8	612.5	584.4	564.9	525.8	496.5
147.5°	709.7	730.1	709.7	689.2	684.1	650.8	606.5	584.4	568.7	537.5	514.0
150°	689.2	705.8	689.2	672.6	668.5	640.4	603.1	584.4	570.8	543.6	523.1
152.5°	671.8	684.4	671.8	659.3	656.2	632.2	600.3	584.4	572.0	547.5	529.1
155°	651.9	660.2	651.9	643.6	641.5	622.5	597.1	584.4	575.0	556.3	542.2
157.5°	636.1	642.0	636.1	630.2	628.8	614.0	594.2	584.4	577.9	565.0	555.3
160°	626.7	630.0	626.7	623.3	622.5	609.8	592.9	584.4	579.2	569.0	561.3
162.5°	620.5	623.6	620.5	617.2	616.5	605.8	591.5	584.4	580.6	573.2	567.7
165°	611.6	614.9	611.6	608.2	607.4	599.7	589.5	584.4	582.6	579.3	576.7
167.5°	605.1	606.5	605.1	603.8	603.4	598.3	591.6	588.3	586.8	584.1	582.0
170°	603.4	603.4	603.4	603.4	603.4	598.3	591.6	588.3	588.2	588.0	587.9
172.5°	598.7	597.4	598.7	599.9	600.2	596.2	591.0	588.3	588.3	588.3	588.3
175°	595.8	595.8	595.8	595.8	595.8	593.3	590.0	588.3	589.0	590.7	591.9
177.5°	593.3	591.9	593.3	594.7	595.1	593.1	590.4	589.0	589.7	591.0	591.9
180°	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9

TEST NUMBER: P935085

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0
2.5°	686.5	682.7	682.7	676.3	673.8	671.8	668.7	659.0	656.5	653.9	657.8
5°	692.4	685.3	680.2	668.7	659.0	655.2	643.0	620.0	604.6	593.1	586.7
7.5°	693.6	684.6	675.1	657.1	634.0	623.8	586.7	544.4	532.9	522.7	516.2
10°	692.4	682.1	668.7	641.8	587.3	569.4	532.2	504.7	497.7	495.7	497.7
12.5°	687.9	678.2	659.7	614.8	538.6	526.5	504.7	488.7	487.4	490.6	507.9
15°	680.2	671.2	649.4	579.0	511.8	502.8	487.4	481.6	488.7	511.1	563.0
17.5°	672.5	662.3	635.4	543.8	491.3	484.9	474.0	485.5	525.2	555.3	572.6
20°	662.3	650.1	619.3	518.2	476.5	470.7	465.7	517.5	547.6	558.5	568.1
22.5°	650.1	637.3	597.5	500.2	461.2	456.7	459.8	535.5	547.6	555.3	563.6
25°	634.0	623.1	571.9	486.1	448.9	443.9	456.0	533.6	540.5	542.4	559.2
27.5°	619.3	605.3	545.0	473.3	434.2	432.3	459.3	525.2	530.3	532.2	550.2
30°	601.4	580.3	514.9	459.8	418.9	418.2	459.8	514.9	513.7	518.8	536.7
32.5°	582.8	543.1	481.0	443.2	404.2	403.5	455.3	499.6	498.3	505.3	518.8
35°	565.6	514.3	434.9	424.0	385.5	386.2	444.5	481.6	482.3	488.7	497.0
37.5°	547.6	489.3	384.3	402.8	367.7	367.7	429.8	465.0	463.7	465.7	477.1
40°	526.5	450.3	339.4	375.3	351.0	349.1	411.8	447.0	442.5	442.0	457.9
42.5°	504.0	407.3	306.2	338.8	331.8	329.2	390.0	425.3	417.0	418.9	439.4
45°	479.7	395.8	280.5	286.3	311.9	310.0	366.3	400.3	394.5	399.7	420.8
47.5°	455.3	372.7	272.2	237.6	290.8	290.1	340.1	376.0	372.7	377.9	400.3
50°	422.1	347.1	271.6	203.7	267.1	269.6	308.8	352.3	352.3	356.8	380.5
52.5°	379.1	315.7	246.6	184.4	239.5	247.2	281.2	331.8	333.0	337.5	358.7
55°	340.1	283.1	228.6	169.7	206.9	223.6	254.2	310.7	313.1	317.6	336.9
57.5°	304.3	235.7	224.8	152.4	176.8	192.8	230.5	290.1	291.4	295.3	313.8
60°	265.8	170.4	206.3	133.9	150.5	162.6	208.8	265.8	270.3	272.8	288.9
62.5°	222.2	123.6	187.0	121.1	137.7	140.3	190.9	242.8	248.5	250.4	260.0
65°	158.2	103.7	158.8	110.2	124.2	124.9	171.6	219.1	224.1	227.4	234.5
67.5°	107.0	84.5	121.1	99.9	114.0	114.6	153.1	191.5	198.5	201.1	205.6
70°	74.3	56.3	89.7	89.0	102.5	103.7	133.2	166.6	173.0	174.9	177.4
72.5°	54.4	45.5	74.3	80.0	90.3	91.6	112.7	138.4	144.8	146.7	147.9
75°	41.6	48.0	60.2	69.8	76.9	77.5	92.3	112.7	117.2	118.5	119.1
77.5°	33.3	44.8	44.2	56.3	62.7	61.5	72.4	87.1	90.9	90.9	90.9
80°	25.0	35.2	33.3	40.4	46.1	44.8	51.9	62.2	63.4	64.7	64.1
82.5°	18.5	22.4	22.4	25.6	30.8	29.5	34.6	40.4	40.4	40.4	41.6
85°	11.6	12.8	10.2	13.5	17.3	16.6	19.2	21.8	22.4	22.4	21.1
87.5°	7.1	5.7	3.2	5.2	7.6	7.6	9.0	9.6	9.0	9.0	9.0
90°	10.3	7.2	4.0	7.2	10.3	11.1	17.5	26.0	30.2	26.8	20.2
92.5°	69.9	42.9	15.9	42.9	69.9	76.7	107.8	149.3	170.0	149.0	107.0
95°	137.0	87.6	38.1	87.6	137.0	149.4	265.2	419.6	496.9	443.4	336.4
97.5°	153.2	109.5	65.9	109.5	153.2	164.1	357.3	614.8	743.6	709.8	642.1
100°	166.5	126.9	87.4	126.9	166.5	176.4	390.8	676.6	819.5	822.0	826.8
102.5°	179.4	142.6	105.6	142.6	179.4	188.7	406.2	696.0	841.0	884.0	970.2
105°	199.1	167.9	136.7	167.9	199.1	206.9	417.5	698.2	838.6	935.1	1128.2
107.5°	226.7	197.6	168.5	197.6	226.7	234.0	419.6	667.1	790.8	925.6	1195.0
110°	242.5	216.2	189.9	216.2	242.5	249.1	416.4	639.6	751.1	901.7	1202.9

TEST NUMBER: P935085

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	261.0	236.0	211.0	236.0	261.0	267.3	416.6	615.5	715.0	869.1	1177.3
115°	288.9	265.8	242.7	265.8	288.9	294.7	420.4	588.0	671.7	820.2	1117.2
117.5°	316.1	295.1	274.1	295.1	316.1	321.4	428.2	570.7	642.0	775.9	1043.9
120°	331.9	312.1	292.3	312.1	331.9	336.8	434.5	564.9	630.0	752.4	997.3
122.5°	350.2	330.2	310.3	330.2	350.2	355.2	443.7	561.8	620.8	731.1	951.6
125°	374.0	355.8	337.7	355.8	374.0	378.6	456.0	559.2	610.9	704.6	891.9
127.5°	396.6	378.2	359.8	378.2	396.6	401.2	468.3	557.8	602.6	683.0	843.8
130°	411.3	391.6	371.8	391.6	411.3	416.3	477.3	558.8	599.5	671.1	814.2
132.5°	423.6	403.9	384.1	403.9	423.6	428.6	484.6	559.2	596.6	660.7	788.8
135°	438.4	420.4	402.4	420.4	438.4	442.9	492.6	558.8	591.9	645.6	752.8
137.5°	456.7	438.9	421.1	438.9	456.7	461.2	504.4	562.2	591.0	636.4	727.1
140°	469.4	453.0	436.5	453.0	469.4	473.5	511.8	562.8	588.3	627.4	705.8
142.5°	478.8	463.7	448.5	463.7	478.8	482.7	517.9	564.8	588.3	622.7	691.5
145°	493.2	480.0	466.7	480.0	493.2	496.5	525.8	564.9	584.4	612.5	668.8
147.5°	510.7	497.9	485.0	497.9	510.7	514.0	537.5	568.7	584.4	606.5	650.8
150°	520.2	508.5	496.9	508.5	520.2	523.1	543.6	570.8	584.4	603.1	640.4
152.5°	526.9	518.0	509.2	518.0	526.9	529.1	547.5	572.0	584.4	600.3	632.2
155°	540.6	534.0	527.5	534.0	540.6	542.2	556.3	575.0	584.4	597.1	622.5
157.5°	553.7	547.4	541.0	547.4	553.7	555.3	565.0	577.9	584.4	594.2	614.0
160°	560.0	555.1	550.2	555.1	560.0	561.3	569.0	579.2	584.4	592.9	609.8
162.5°	566.7	563.0	559.2	563.0	566.7	567.7	573.2	580.6	584.4	591.5	605.8
165°	575.9	572.5	569.2	572.5	575.9	576.7	579.3	582.6	584.4	589.5	599.7
167.5°	581.6	580.0	578.3	580.0	581.6	582.0	584.1	586.8	588.3	591.6	598.3
170°	587.5	585.9	584.4	585.9	587.5	587.9	588.0	588.2	588.3	591.6	598.3
172.5°	588.2	587.9	587.5	587.9	588.2	588.3	588.3	588.3	588.3	591.0	596.2
175°	591.9	591.9	591.9	591.9	591.9	591.9	590.7	589.0	588.3	590.0	593.3
177.5°	591.9	591.9	591.9	591.9	591.9	591.9	591.0	589.7	589.0	590.4	593.1
180°	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9

TEST NUMBER: P935085

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0	677.0
2.5°	653.3	651.4	653.9	646.9	653.9	651.4	653.3	657.8	653.9	656.5	659.0
5°	573.2	570.0	559.8	551.4	559.8	570.0	573.2	586.7	593.1	604.6	620.0
7.5°	512.4	509.8	507.3	502.1	507.3	509.8	512.4	516.2	522.7	532.9	544.4
10°	498.9	499.6	503.4	502.8	503.4	499.6	498.9	497.7	495.7	497.7	504.7
12.5°	533.6	539.3	560.4	559.2	560.4	539.3	533.6	507.9	490.6	487.4	488.7
15°	573.2	575.1	579.6	580.3	579.6	575.1	573.2	563.0	511.1	488.7	481.6
17.5°	577.1	577.7	580.9	580.9	580.9	577.7	577.1	572.6	555.3	525.2	485.5
20°	573.9	575.1	581.6	582.8	581.6	575.1	573.9	568.1	558.5	547.6	517.5
22.5°	572.6	575.1	580.3	579.6	580.3	575.1	572.6	563.6	555.3	547.6	535.5
25°	566.2	566.2	566.8	567.5	566.8	566.2	566.2	559.2	542.4	540.5	533.6
27.5°	552.8	554.0	557.8	557.2	557.8	554.0	552.8	550.2	532.2	530.3	525.2
30°	540.5	539.3	536.0	533.6	536.0	539.3	540.5	536.7	518.8	513.7	514.9
32.5°	520.1	516.8	513.7	511.8	513.7	516.8	520.1	518.8	505.3	498.3	499.6
35°	495.7	496.4	495.7	493.8	495.7	496.4	495.7	497.0	488.7	482.3	481.6
37.5°	478.5	479.7	479.0	476.5	479.0	479.7	478.5	477.1	465.7	463.7	465.0
40°	460.5	461.2	460.5	458.6	460.5	461.2	460.5	457.9	442.0	442.5	447.0
42.5°	443.2	442.5	440.6	439.4	440.6	442.5	443.2	439.4	418.9	417.0	425.3
45°	423.4	424.0	420.1	418.2	420.1	424.0	423.4	420.8	399.7	394.5	400.3
47.5°	403.5	403.5	400.3	398.3	400.3	403.5	403.5	400.3	377.9	372.7	376.0
50°	382.4	381.7	377.2	376.6	377.2	381.7	382.4	380.5	356.8	352.3	352.3
52.5°	358.0	358.0	358.7	359.9	358.7	358.0	358.0	358.7	337.5	333.0	331.8
55°	336.9	337.5	342.0	343.3	342.0	337.5	336.9	336.9	317.6	313.1	310.7
57.5°	315.2	315.2	318.3	318.3	318.3	315.2	315.2	313.8	295.3	291.4	290.1
60°	290.1	291.4	293.9	293.4	293.9	291.4	290.1	288.9	272.8	270.3	265.8
62.5°	263.9	265.2	265.8	264.5	265.8	265.2	263.9	260.0	250.4	248.5	242.8
65°	236.4	237.6	238.3	236.9	238.3	237.6	236.4	234.5	227.4	224.1	219.1
67.5°	208.2	207.5	206.9	209.4	206.9	207.5	208.2	205.6	201.1	198.5	191.5
70°	179.3	179.3	178.7	180.0	178.7	179.3	179.3	177.4	174.9	173.0	166.6
72.5°	148.6	147.9	150.5	148.6	150.5	147.9	148.6	147.9	146.7	144.8	138.4
75°	118.5	119.8	118.5	120.4	118.5	119.8	118.5	119.1	118.5	117.2	112.7
77.5°	90.3	91.6	90.3	90.3	90.3	91.6	90.3	90.9	90.9	90.9	87.1
80°	64.1	63.4	63.4	62.7	63.4	63.4	64.1	64.1	64.7	63.4	62.2
82.5°	41.0	40.4	40.4	41.6	40.4	40.4	41.0	41.6	40.4	40.4	40.4
85°	22.4	23.0	21.8	21.8	21.8	23.0	22.4	21.1	22.4	22.4	21.8
87.5°	8.3	7.6	7.6	7.6	7.6	7.6	8.3	9.0	9.0	9.0	9.6
90°	15.1	15.1	15.1	15.1	15.1	15.1	15.1	20.2	26.8	30.2	26.0
92.5°	75.4	72.5	60.5	48.4	60.5	72.5	75.4	107.0	149.0	170.0	149.3
95°	256.2	247.2	210.8	174.4	210.8	247.2	256.2	336.4	443.4	496.9	419.6
97.5°	591.4	574.1	504.9	435.8	504.9	574.1	591.4	642.1	709.8	743.6	614.8
100°	830.6	809.9	727.5	645.1	727.5	809.9	830.6	826.8	822.0	819.5	676.6
102.5°	1034.7	1017.1	946.5	875.9	946.5	1017.1	1034.7	970.2	884.0	841.0	696.0
105°	1273.1	1263.7	1225.6	1187.7	1225.6	1263.7	1273.1	1128.2	935.1	838.6	698.2
107.5°	1397.1	1399.4	1408.5	1417.7	1408.5	1399.4	1397.1	1195.0	925.6	790.8	667.1
110°	1428.8	1438.7	1478.2	1517.8	1478.2	1438.7	1428.8	1202.9	901.7	751.1	639.6

TEST NUMBER: P935085

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1408.5	1423.7	1484.5	1545.2	1484.5	1423.7	1408.5	1177.3	869.1	715.0	615.5
115°	1339.9	1360.9	1445.1	1529.3	1445.1	1360.9	1339.9	1117.2	820.2	671.7	588.0
117.5°	1244.9	1268.2	1361.6	1455.0	1361.6	1268.2	1244.9	1043.9	775.9	642.0	570.7
120°	1181.0	1203.7	1294.4	1385.1	1294.4	1203.7	1181.0	997.3	752.4	630.0	564.9
122.5°	1117.0	1139.3	1228.9	1318.4	1228.9	1139.3	1117.0	951.6	731.1	620.8	561.8
125°	1032.4	1053.0	1135.4	1217.9	1135.4	1053.0	1032.4	891.9	704.6	610.9	559.2
127.5°	964.5	981.8	1051.5	1121.0	1051.5	981.8	964.5	843.8	683.0	602.6	557.8
130°	921.6	937.6	1001.9	1066.2	1001.9	937.6	921.6	814.2	671.1	599.5	558.8
132.5°	885.0	899.4	956.9	1014.5	956.9	899.4	885.0	788.8	660.7	596.6	559.2
135°	833.3	845.7	895.3	945.0	895.3	845.7	833.3	752.8	645.6	591.9	558.8
137.5°	795.2	805.4	846.0	886.6	846.0	805.4	795.2	727.1	636.4	591.0	562.2
140°	764.7	774.1	812.1	850.0	812.1	774.1	764.7	705.8	627.4	588.3	562.8
142.5°	743.2	751.4	784.1	816.7	784.1	751.4	743.2	691.5	622.7	588.3	564.8
145°	711.0	717.2	741.9	766.7	741.9	717.2	711.0	668.8	612.5	584.4	564.9
147.5°	684.1	689.2	709.7	730.1	709.7	689.2	684.1	650.8	606.5	584.4	568.7
150°	668.5	672.6	689.2	705.8	689.2	672.6	668.5	640.4	603.1	584.4	570.8
152.5°	656.2	659.3	671.8	684.4	671.8	659.3	656.2	632.2	600.3	584.4	572.0
155°	641.5	643.6	651.9	660.2	651.9	643.6	641.5	622.5	597.1	584.4	575.0
157.5°	628.8	630.2	636.1	642.0	636.1	630.2	628.8	614.0	594.2	584.4	577.9
160°	622.5	623.3	626.7	630.0	626.7	623.3	622.5	609.8	592.9	584.4	579.2
162.5°	616.5	617.2	620.5	623.6	620.5	617.2	616.5	605.8	591.5	584.4	580.6
165°	607.4	608.2	611.6	614.9	611.6	608.2	607.4	599.7	589.5	584.4	582.6
167.5°	603.4	603.8	605.1	606.5	605.1	603.8	603.4	598.3	591.6	588.3	586.8
170°	603.4	603.4	603.4	603.4	603.4	603.4	603.4	598.3	591.6	588.3	588.2
172.5°	600.2	599.9	598.7	597.4	598.7	599.9	600.2	596.2	591.0	588.3	588.3
175°	595.8	595.8	595.8	595.8	595.8	595.8	595.8	593.3	590.0	588.3	589.0
177.5°	595.1	594.7	593.3	591.9	593.3	594.7	595.1	593.1	590.4	589.0	589.7
180°	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9

TEST NUMBER: P935085

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	677.0	677.0	677.0	677.0	677.0
2.5°	668.7	671.8	673.8	676.3	682.7
5°	643.0	655.2	659.0	668.7	680.2
7.5°	586.7	623.8	634.0	657.1	675.1
10°	532.2	569.4	587.3	641.8	668.7
12.5°	504.7	526.5	538.6	614.8	659.7
15°	487.4	502.8	511.8	579.0	649.4
17.5°	474.0	484.9	491.3	543.8	635.4
20°	465.7	470.7	476.5	518.2	619.3
22.5°	459.8	456.7	461.2	500.2	597.5
25°	456.0	443.9	448.9	486.1	571.9
27.5°	459.3	432.3	434.2	473.3	545.0
30°	459.8	418.2	418.9	459.8	514.9
32.5°	455.3	403.5	404.2	443.2	481.0
35°	444.5	386.2	385.5	424.0	434.9
37.5°	429.8	367.7	367.7	402.8	384.3
40°	411.8	349.1	351.0	375.3	339.4
42.5°	390.0	329.2	331.8	338.8	306.2
45°	366.3	310.0	311.9	286.3	280.5
47.5°	340.1	290.1	290.8	237.6	272.2
50°	308.8	269.6	267.1	203.7	271.6
52.5°	281.2	247.2	239.5	184.4	246.6
55°	254.2	223.6	206.9	169.7	228.6
57.5°	230.5	192.8	176.8	152.4	224.8
60°	208.8	162.6	150.5	133.9	206.3
62.5°	190.9	140.3	137.7	121.1	187.0
65°	171.6	124.9	124.2	110.2	158.8
67.5°	153.1	114.6	114.0	99.9	121.1
70°	133.2	103.7	102.5	89.0	89.7
72.5°	112.7	91.6	90.3	80.0	74.3
75°	92.3	77.5	76.9	69.8	60.2
77.5°	72.4	61.5	62.7	56.3	44.2
80°	51.9	44.8	46.1	40.4	33.3
82.5°	34.6	29.5	30.8	25.6	22.4
85°	19.2	16.6	17.3	13.5	10.2
87.5°	9.0	7.6	7.6	5.2	3.2
90°	17.5	11.1	10.3	7.2	4.0
92.5°	107.8	76.7	69.9	42.9	15.9
95°	265.2	149.4	137.0	87.6	38.1
97.5°	357.3	164.1	153.2	109.5	65.9
100°	390.8	176.4	166.5	126.9	87.4
102.5°	406.2	188.7	179.4	142.6	105.6
105°	417.5	206.9	199.1	167.9	136.7
107.5°	419.6	234.0	226.7	197.6	168.5
110°	416.4	249.1	242.5	216.2	189.9



TEST NUMBER: P935085

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	416.6	267.3	261.0	236.0	211.0
115°	420.4	294.7	288.9	265.8	242.7
117.5°	428.2	321.4	316.1	295.1	274.1
120°	434.5	336.8	331.9	312.1	292.3
122.5°	443.7	355.2	350.2	330.2	310.3
125°	456.0	378.6	374.0	355.8	337.7
127.5°	468.3	401.2	396.6	378.2	359.8
130°	477.3	416.3	411.3	391.6	371.8
132.5°	484.6	428.6	423.6	403.9	384.1
135°	492.6	442.9	438.4	420.4	402.4
137.5°	504.4	461.2	456.7	438.9	421.1
140°	511.8	473.5	469.4	453.0	436.5
142.5°	517.9	482.7	478.8	463.7	448.5
145°	525.8	496.5	493.2	480.0	466.7
147.5°	537.5	514.0	510.7	497.9	485.0
150°	543.6	523.1	520.2	508.5	496.9
152.5°	547.5	529.1	526.9	518.0	509.2
155°	556.3	542.2	540.6	534.0	527.5
157.5°	565.0	555.3	553.7	547.4	541.0
160°	569.0	561.3	560.0	555.1	550.2
162.5°	573.2	567.7	566.7	563.0	559.2
165°	579.3	576.7	575.9	572.5	569.2
167.5°	584.1	582.0	581.6	580.0	578.3
170°	588.0	587.9	587.5	585.9	584.4
172.5°	588.3	588.3	588.2	587.9	587.5
175°	590.7	591.9	591.9	591.9	591.9
177.5°	591.0	591.9	591.9	591.9	591.9
180°	591.9	591.9	591.9	591.9	591.9

TEST NUMBER: P935085

CATALOG NUMBER: SQ4-FA-100U-050D-B2750-1D-UNV-W2A-W-4-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.16	9.87	10.26	10.97	12.48	11.95	12.67	13.05	13.77	15.28
	3H	9.62	10.26	10.73	11.37	12.90	13.28	13.92	14.39	15.02	16.55
	4H	9.80	10.41	10.93	11.52	13.06	13.71	14.32	14.83	15.42	16.96
	6H	9.92	10.48	11.05	11.59	13.13	13.98	14.54	15.11	15.65	17.19
	8H	9.91	10.45	11.05	11.57	13.11	14.04	14.57	15.17	15.70	17.24
	12H	9.88	10.38	11.02	11.50	13.07	14.07	14.58	15.21	15.70	17.26
4H	2H	10.16	10.77	11.29	11.88	13.41	12.34	12.95	13.47	14.06	15.60
	3H	11.17	11.68	12.31	12.81	14.36	13.83	14.33	14.96	15.47	17.02
	4H	11.44	11.91	12.58	13.03	14.60	14.34	14.81	15.48	15.93	17.50
	6H	11.56	11.96	12.70	13.11	14.67	14.69	15.09	15.83	16.24	17.80
	8H	11.56	11.94	12.71	13.07	14.65	14.79	15.16	15.93	16.30	17.88
	12H	11.52	11.86	12.68	13.01	14.59	14.83	15.17	15.99	16.32	17.90
8H	4H	11.88	12.25	13.02	13.39	14.97	14.46	14.83	15.60	15.97	17.54
	6H	12.14	12.44	13.30	13.62	15.20	14.88	15.19	16.04	16.37	17.94
	8H	12.18	12.45	13.35	13.60	15.20	15.02	15.29	16.19	16.45	18.04
	12H	12.15	12.39	13.33	13.55	15.17	15.11	15.35	16.28	16.50	18.13
12H	4H	11.88	12.22	13.04	13.37	14.95	14.41	14.75	15.57	15.90	17.48
	6H	12.19	12.46	13.36	13.62	15.22	14.87	15.14	16.04	16.30	17.90
	8H	12.25	12.49	13.43	13.65	15.27	15.02	15.26	16.20	16.42	18.04

END OF REPORT