

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934786

Luminaire Tested: SQ4-FA-075U-075D-B2750-1D-UNV-W2A-W-4-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934786
REPORT IS A COMBINATION OF REPORTS P933710 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-075U-075D-B2750-1D-UNV-W2A-W-4-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5358.3 lumens
Efficiency: N/A
Efficacy: 126.4 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 42.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934786

CATALOG NUMBER: SQ4-FA-075U-075D-B2750-1D-UNV-W2A-W-4-5000K

Luminous Intensity Polar Plot



TEST NUMBER: P934786

CATALOG NUMBER: SQ4-FA-075U-075D-B2750-1D-UNV-W2A-W-4-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	37	35	33
4	74	63	55	49	68	58	52	46	49	44	40	41	37	34	33	31	28
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	45	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19
8	54	41	33	28	49	38	31	27	33	27	23	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9161	9161	9161	9161
5°	9220	9249	9220	7272
10°	9148	9111	9148	6513
15°	9039	8914	9039	7442
20°	8839	8679	8839	7458
25°	8443	8338	8443	7300
30°	7932	8055	7932	6953
35°	7062	7697	7062	6572
40°	5874	7275	5874	6283
45°	5239	6782	5239	5952
50°	5553	6193	5553	5620
55°	5209	5560	5209	5427
60°	5349	4722	5349	4972
65°	4826	3903	4826	4364
70°	3321	3110	3321	3657
75°	2879	2298	2879	2753
80°	2275	1521	2275	1654
85°	1234	806	1234	685

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 8044 cd/sqm

TEST NUMBER: P934786

CATALOG NUMBER: SQ4-FA-075U-075D-B2750-1D-UNV-W2A-W-4-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.1	1.7
10°-20°	253.1	4.7
20°-30°	391.2	7.3
30°-40°	467.0	8.7
40°-50°	469.7	8.8
50°-60°	408.7	7.6
60°-70°	289.8	5.4
70°-80°	153.3	2.9
80°-90°	39.8	0.7
90°-100°	210.3	3.9
100°-110°	552.9	10.3
110°-120°	573.3	10.7
120°-130°	459.8	8.6
130°-140°	360.8	6.7
140°-150°	276.9	5.2
150°-160°	199.4	3.7
160°-170°	122.0	2.3
170°-180°	41.2	0.8
0°-30°	733.4	13.7
0°-40°	1200.3	22.4
0°-60°	2078.8	38.8
0°-90°	2561.7	47.8
90°-120°	1336.4	24.9
90°-150°	2433.9	45.4
90°-180°	2797.0	52.2
0°-180°	5358.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	987	987	987	987	987	
5°	992	1023	992	804	992	94
15°	947	1014	947	846	947	267
25°	834	945	834	828	834	383
35°	634	844	634	720	634	392
45°	409	695	409	610	409	328
55°	334	513	334	501	334	306
65°	232	309	232	346	232	221
75°	88	147	88	176	88	92
85°	15	37	15	32	15	20
90°	3	11	3	11	3	3
95°	28	127	28	127	28	31
105°	100	866	100	866	100	106
115°	177	1115	177	1115	177	175
125°	246	888	246	888	246	219
135°	293	689	293	689	293	227
145°	340	559	340	559	340	213
155°	384	481	384	481	384	177
165°	415	448	415	448	415	117
175°	431	434	431	434	431	41
180°	431	431	431	431	431	

TEST NUMBER: P934786

CATALOG NUMBER: SQ4-FA-075U-075D-B2750-1D-UNV-W2A-W-4-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3
2.5°	995.7	995.7	1001.4	1003.3	1003.3	1000.5	997.7	1000.5	1008.9	1011.7	1010.8
5°	992.0	999.6	1009.8	1011.7	1013.6	1012.6	1010.8	1012.6	1022.0	1023.9	1024.8
7.5°	984.5	998.6	1011.7	1014.5	1017.3	1014.5	1013.6	1015.4	1024.8	1026.7	1026.7
10°	975.2	994.8	1009.8	1011.7	1014.5	1011.7	1011.7	1015.4	1024.8	1026.7	1027.6
12.5°	962.1	989.2	1003.3	1005.2	1008.9	1008.0	1007.0	1010.8	1020.1	1022.0	1022.0
15°	947.2	978.9	992.0	993.9	1000.5	998.6	998.6	1002.4	1012.6	1015.4	1014.5
17.5°	926.6	965.8	980.8	983.6	988.3	987.3	988.3	992.0	1001.4	1003.3	1004.2
20°	903.3	948.1	965.8	968.7	973.3	973.3	973.3	978.0	987.3	991.1	991.1
22.5°	871.5	929.4	948.1	950.0	955.6	955.6	957.4	964.0	972.4	973.3	973.3
25°	834.2	908.9	924.8	930.4	936.0	938.8	941.6	945.3	948.1	947.2	948.1
27.5°	794.9	882.7	903.3	907.0	914.5	917.3	921.0	922.0	922.9	925.7	923.8
30°	751.0	846.3	877.1	880.9	893.0	894.9	891.1	893.0	897.7	899.5	901.4
32.5°	701.5	792.1	850.0	858.4	869.6	864.0	863.1	865.9	873.4	873.4	875.3
35°	634.3	750.1	824.8	832.3	840.7	834.2	837.9	838.8	843.5	846.3	845.4
37.5°	560.5	713.7	798.7	804.3	810.8	802.4	808.0	810.8	814.5	812.7	812.7
40°	495.1	656.7	767.8	771.6	777.2	770.6	776.2	778.1	780.0	778.1	777.2
42.5°	446.5	594.1	735.2	739.8	736.1	740.8	742.6	746.4	743.6	739.8	739.8
45°	409.2	577.3	699.7	705.3	699.7	707.1	709.9	709.9	701.5	699.7	698.7
47.5°	397.0	543.7	664.2	664.2	661.4	670.7	675.4	668.8	660.4	657.6	657.6
50°	396.1	506.3	615.6	611.9	624.9	636.1	631.5	624.9	618.4	608.1	608.1
52.5°	359.7	460.6	553.0	567.0	587.6	594.1	586.6	580.1	568.9	564.2	560.5
55°	333.5	412.9	496.0	524.1	545.5	554.0	539.9	533.4	516.6	513.8	511.9
57.5°	327.8	343.8	443.7	479.2	505.4	504.5	496.0	483.9	469.9	467.1	466.2
60°	300.7	248.4	387.7	429.7	456.8	454.0	446.5	435.3	422.3	420.4	418.5
62.5°	272.7	180.3	324.1	371.8	410.1	409.2	402.6	385.8	376.5	371.8	368.1
65°	231.6	151.3	230.7	309.2	364.4	366.2	352.2	340.1	329.7	324.1	323.2
67.5°	176.5	123.3	156.0	257.8	320.4	318.5	300.7	295.1	282.1	279.3	273.7
70°	130.8	82.2	108.3	209.2	277.4	272.7	258.7	252.2	240.0	233.5	229.8
72.5°	108.3	66.3	79.4	162.5	233.5	227.9	215.8	208.3	198.0	192.4	188.7
75°	87.8	70.0	60.7	120.5	189.6	185.9	174.7	167.2	158.8	151.3	152.2
77.5°	64.4	65.4	48.6	88.7	150.4	144.8	138.2	128.9	125.2	117.7	117.7
80°	48.6	51.4	36.4	60.7	108.3	108.3	102.7	96.2	89.7	85.9	85.9
82.5°	32.7	32.7	27.1	38.3	73.8	71.0	67.2	65.4	61.6	59.8	59.8
85°	14.9	18.7	16.8	23.4	40.2	42.0	42.0	40.2	39.2	37.4	38.3
87.5°	4.7	8.4	10.3	13.1	20.5	21.5	22.4	22.4	22.4	23.4	23.4
90°	2.9	5.2	7.6	8.1	12.8	19.0	22.0	19.6	14.7	11.0	11.0
92.5°	11.6	31.3	50.9	55.9	78.5	108.8	123.9	108.6	78.0	55.0	52.9
95°	27.8	63.9	99.9	108.9	193.3	305.9	362.2	323.2	245.2	186.7	180.1
97.5°	48.1	79.9	111.6	119.6	260.4	448.1	542.0	517.3	468.1	431.1	418.5
100°	63.7	92.5	121.3	128.5	284.8	493.2	597.3	599.1	602.7	605.4	590.4
102.5°	77.1	104.0	130.8	137.5	296.0	507.3	613.0	644.4	707.1	754.2	741.3
105°	99.6	122.4	145.1	150.8	304.3	508.9	611.2	681.6	822.4	927.9	921.0
107.5°	122.7	144.0	165.2	170.5	305.9	486.2	576.5	674.6	871.0	1018.2	1019.9
110°	138.4	157.6	176.8	181.6	303.6	466.2	547.5	657.3	876.7	1041.4	1048.6

TEST NUMBER: P934786

CATALOG NUMBER: SQ4-FA-075U-075D-B2750-1D-UNV-W2A-W-4-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	153.7	172.0	190.3	194.8	303.6	448.7	521.2	633.5	858.2	1026.7	1037.8
115°	176.9	193.7	210.6	214.8	306.4	428.5	489.6	597.9	814.3	976.6	991.9
117.5°	199.8	215.1	230.4	234.2	312.1	415.9	467.8	565.5	760.8	907.4	924.4
120°	213.1	227.5	241.9	245.5	316.7	411.7	459.2	548.4	726.9	860.8	877.3
122.5°	226.1	240.7	255.2	258.8	323.4	409.5	452.5	532.8	693.6	814.2	830.5
125°	246.1	259.4	272.6	275.9	332.4	407.7	445.3	513.6	650.2	752.5	767.6
127.5°	262.4	275.7	289.1	292.4	341.4	406.7	439.3	497.9	615.1	703.0	715.7
130°	271.0	285.4	299.8	303.5	347.9	407.2	436.9	489.1	593.5	671.7	683.4
132.5°	280.0	294.4	308.8	312.4	353.2	407.7	434.9	481.6	575.1	645.1	655.6
135°	293.3	306.4	319.5	322.8	359.0	407.3	431.4	470.5	548.8	607.5	616.5
137.5°	306.9	319.9	332.9	336.1	367.7	409.8	430.9	463.9	530.0	579.6	587.0
140°	318.2	330.2	342.1	345.1	373.0	410.2	428.8	457.4	514.4	557.3	564.2
142.5°	326.9	337.9	348.9	351.7	377.4	411.7	428.8	453.9	504.1	541.7	547.7
145°	340.2	349.9	359.5	361.9	383.2	411.7	425.9	446.5	487.5	518.3	522.8
147.5°	353.5	362.9	372.3	374.6	391.7	414.5	425.9	442.1	474.4	498.6	502.3
150°	362.2	370.7	379.2	381.4	396.2	416.0	425.9	439.5	466.8	487.3	490.3
152.5°	371.2	377.6	384.1	385.6	399.1	416.9	425.9	437.6	460.8	478.3	480.5
155°	384.5	389.3	394.0	395.2	405.4	419.1	425.9	435.2	453.6	467.6	469.1
157.5°	394.3	399.0	403.7	404.8	411.8	421.2	425.9	433.1	447.5	458.3	459.3
160°	401.0	404.6	408.2	409.1	414.7	422.2	425.9	432.1	444.5	453.7	454.3
162.5°	407.7	410.4	413.1	413.8	417.8	423.2	425.9	431.1	441.5	449.3	449.9
165°	414.9	417.3	419.7	420.4	422.3	424.7	425.9	429.6	437.1	442.7	443.4
167.5°	421.5	422.6	423.8	424.1	425.7	427.8	428.8	431.2	436.2	439.8	440.1
170°	425.9	427.0	428.2	428.5	428.6	428.7	428.8	431.2	436.2	439.8	439.8
172.5°	428.2	428.5	428.7	428.8	428.8	428.8	428.8	430.8	434.6	437.5	437.3
175°	431.4	431.4	431.4	431.4	430.6	429.4	428.8	430.0	432.4	434.3	434.3
177.5°	431.4	431.4	431.4	431.4	430.8	429.8	429.4	430.3	432.3	433.7	433.5
180°	431.4	431.4	431.4	431.4	431.4	431.4	431.4	431.4	431.4	431.4	431.4

TEST NUMBER: P934786

CATALOG NUMBER: SQ4-FA-075U-075D-B2750-1D-UNV-W2A-W-4-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3
2.5°	1012.6	1009.8	1012.6	1010.8	1011.7	1008.9	1000.5	997.7	1000.5	1003.3	1003.3
5°	1024.8	1022.9	1024.8	1024.8	1023.9	1022.0	1012.6	1010.8	1012.6	1013.6	1011.7
7.5°	1028.5	1025.7	1028.5	1026.7	1026.7	1024.8	1015.4	1013.6	1014.5	1017.3	1014.5
10°	1028.5	1025.7	1028.5	1027.6	1026.7	1024.8	1015.4	1011.7	1011.7	1014.5	1011.7
12.5°	1023.9	1022.0	1023.9	1022.0	1022.0	1020.1	1010.8	1007.0	1008.0	1008.9	1005.2
15°	1016.4	1013.6	1016.4	1014.5	1015.4	1012.6	1002.4	998.6	998.6	1000.5	993.9
17.5°	1005.2	1001.4	1005.2	1004.2	1003.3	1001.4	992.0	988.3	987.3	988.3	983.6
20°	992.0	989.2	992.0	991.1	991.1	987.3	978.0	973.3	973.3	973.3	968.7
22.5°	971.5	968.7	971.5	973.3	973.3	972.4	964.0	957.4	955.6	955.6	950.0
25°	948.1	945.3	948.1	948.1	947.2	948.1	945.3	941.6	938.8	936.0	930.4
27.5°	925.7	923.8	925.7	923.8	925.7	922.9	922.0	921.0	917.3	914.5	907.0
30°	903.3	901.4	903.3	901.4	899.5	897.7	893.0	891.1	894.9	893.0	880.9
32.5°	875.3	873.4	875.3	875.3	873.4	873.4	865.9	863.1	864.0	869.6	858.4
35°	846.3	843.5	846.3	845.4	846.3	843.5	838.8	837.9	834.2	840.7	832.3
37.5°	812.7	809.9	812.7	812.7	812.7	814.5	810.8	808.0	802.4	810.8	804.3
40°	778.1	774.4	778.1	777.2	778.1	780.0	778.1	776.2	770.6	777.2	771.6
42.5°	738.9	738.0	738.9	739.8	739.8	743.6	746.4	742.6	740.8	736.1	739.8
45°	696.9	695.0	696.9	698.7	699.7	701.5	709.9	709.9	707.1	699.7	705.3
47.5°	652.0	647.4	652.0	657.6	657.6	660.4	668.8	675.4	670.7	661.4	664.2
50°	604.4	605.3	604.4	608.1	608.1	618.4	624.9	631.5	636.1	624.9	611.9
52.5°	557.7	556.8	557.7	560.5	564.2	568.9	580.1	586.6	594.1	587.6	567.0
55°	511.0	512.9	511.0	511.9	513.8	516.6	533.4	539.9	554.0	545.5	524.1
57.5°	464.3	461.5	464.3	466.2	467.1	469.9	483.9	496.0	504.5	505.4	479.2
60°	410.1	406.4	410.1	418.5	420.4	422.3	435.3	446.5	454.0	456.8	429.7
62.5°	362.5	355.9	362.5	368.1	371.8	376.5	385.8	402.6	409.2	410.1	371.8
65°	312.0	309.2	312.0	323.2	324.1	329.7	340.1	352.2	366.2	364.4	309.2
67.5°	266.2	266.2	266.2	273.7	279.3	282.1	295.1	300.7	318.5	320.4	257.8
70°	224.2	223.2	224.2	229.8	233.5	240.0	252.2	258.7	272.7	277.4	209.2
72.5°	184.0	183.1	184.0	188.7	192.4	198.0	208.3	215.8	227.9	233.5	162.5
75°	148.5	146.6	148.5	152.2	151.3	158.8	167.2	174.7	185.9	189.6	120.5
77.5°	113.9	113.9	113.9	117.7	117.7	125.2	128.9	138.2	144.8	150.4	88.7
80°	85.0	84.1	85.0	85.9	85.9	89.7	96.2	102.7	108.3	108.3	60.7
82.5°	59.8	57.9	59.8	59.8	59.8	61.6	65.4	67.2	71.0	73.8	38.3
85°	37.4	37.4	37.4	38.3	37.4	39.2	40.2	42.0	42.0	40.2	23.4
87.5°	24.3	23.4	24.3	23.4	23.4	22.4	22.4	22.4	21.5	20.5	13.1
90°	11.0	11.0	11.0	11.0	11.0	14.7	19.6	22.0	19.0	12.8	8.1
92.5°	44.1	35.3	44.1	52.9	55.0	78.0	108.6	123.9	108.8	78.5	55.9
95°	153.6	127.1	153.6	180.1	186.7	245.2	323.2	362.2	305.9	193.3	108.9
97.5°	368.1	317.7	368.1	418.5	431.1	468.1	517.3	542.0	448.1	260.4	119.6
100°	530.3	470.2	530.3	590.4	605.4	602.7	599.1	597.3	493.2	284.8	128.5
102.5°	689.9	638.4	689.9	741.3	754.2	707.1	644.4	613.0	507.3	296.0	137.5
105°	893.4	865.7	893.4	921.0	927.9	822.4	681.6	611.2	508.9	304.3	150.8
107.5°	1026.7	1033.4	1026.7	1019.9	1018.2	871.0	674.6	576.5	486.2	305.9	170.5
110°	1077.5	1106.3	1077.5	1048.6	1041.4	876.7	657.3	547.5	466.2	303.6	181.6

TEST NUMBER: P934786

CATALOG NUMBER: SQ4-FA-075U-075D-B2750-1D-UNV-W2A-W-4-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1082.0	1126.3	1082.0	1037.8	1026.7	858.2	633.5	521.2	448.7	303.6	194.8
115°	1053.4	1114.7	1053.4	991.9	976.6	814.3	597.9	489.6	428.5	306.4	214.8
117.5°	992.5	1060.6	992.5	924.4	907.4	760.8	565.5	467.8	415.9	312.1	234.2
120°	943.4	1009.6	943.4	877.3	860.8	726.9	548.4	459.2	411.7	316.7	245.5
122.5°	895.7	961.0	895.7	830.5	814.2	693.6	532.8	452.5	409.5	323.4	258.8
125°	827.6	887.7	827.6	767.6	752.5	650.2	513.6	445.3	407.7	332.4	275.9
127.5°	766.3	817.1	766.3	715.7	703.0	615.1	497.9	439.3	406.7	341.4	292.4
130°	730.3	777.1	730.3	683.4	671.7	593.5	489.1	436.9	407.2	347.9	303.5
132.5°	697.5	739.4	697.5	655.6	645.1	575.1	481.6	434.9	407.7	353.2	312.4
135°	652.7	688.8	652.7	616.5	607.5	548.8	470.5	431.4	407.3	359.0	322.8
137.5°	616.6	646.2	616.6	587.0	579.6	530.0	463.9	430.9	409.8	367.7	336.1
140°	592.0	619.6	592.0	564.2	557.3	514.4	457.4	428.8	410.2	373.0	345.1
142.5°	571.4	595.2	571.4	547.7	541.7	504.1	453.9	428.8	411.7	377.4	351.7
145°	540.8	558.8	540.8	522.8	518.3	487.5	446.5	425.9	411.7	383.2	361.9
147.5°	517.2	532.2	517.2	502.3	498.6	474.4	442.1	425.9	414.5	391.7	374.6
150°	502.4	514.5	502.4	490.3	487.3	466.8	439.5	425.9	416.0	396.2	381.4
152.5°	489.7	498.8	489.7	480.5	478.3	460.8	437.6	425.9	416.9	399.1	385.6
155°	475.1	481.2	475.1	469.1	467.6	453.6	435.2	425.9	419.1	405.4	395.2
157.5°	463.6	467.8	463.6	459.3	458.3	447.5	433.1	425.9	421.2	411.8	404.8
160°	456.7	459.2	456.7	454.3	453.7	444.5	432.1	425.9	422.2	414.7	409.1
162.5°	452.2	454.6	452.2	449.9	449.3	441.5	431.1	425.9	423.2	417.8	413.8
165°	445.8	448.2	445.8	443.4	442.7	437.1	429.6	425.9	424.7	422.3	420.4
167.5°	441.1	442.2	441.1	440.1	439.8	436.2	431.2	428.8	427.8	425.7	424.1
170°	439.8	439.8	439.8	439.8	439.8	436.2	431.2	428.8	428.7	428.6	428.5
172.5°	436.4	435.4	436.4	437.3	437.5	434.6	430.8	428.8	428.8	428.8	428.8
175°	434.3	434.3	434.3	434.3	434.3	432.4	430.0	428.8	429.4	430.6	431.4
177.5°	432.4	431.4	432.4	433.5	433.7	432.3	430.3	429.4	429.8	430.8	431.4
180°	431.4	431.4	431.4	431.4	431.4	431.4	431.4	431.4	431.4	431.4	431.4

TEST NUMBER: P934786

CATALOG NUMBER: SQ4-FA-075U-075D-B2750-1D-UNV-W2A-W-4-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3
2.5°	1001.4	995.7	995.7	986.4	982.7	979.9	975.2	961.2	957.4	953.7	959.3
5°	1009.8	999.6	992.0	975.2	961.2	955.6	937.8	904.2	881.8	865.0	855.6
7.5°	1011.7	998.6	984.5	958.4	924.8	909.8	855.6	794.0	777.2	762.2	752.9
10°	1009.8	994.8	975.2	936.0	856.6	830.4	776.2	736.1	725.8	723.0	725.8
12.5°	1003.3	989.2	962.1	896.7	785.6	767.8	736.1	712.7	710.9	715.5	740.8
15°	992.0	978.9	947.2	844.4	746.4	733.3	710.9	702.5	712.7	745.4	821.1
17.5°	980.8	965.8	926.6	793.1	716.5	707.1	691.3	708.1	766.0	809.9	835.1
20°	965.8	948.1	903.3	755.7	695.0	686.6	679.1	754.8	798.7	814.5	828.6
22.5°	948.1	929.4	871.5	729.5	672.6	666.0	670.7	780.9	798.7	809.9	822.0
25°	924.8	908.9	834.2	709.0	654.8	647.4	665.1	778.1	788.4	791.2	815.5
27.5°	903.3	882.7	794.9	690.3	633.3	630.5	669.8	766.0	773.4	776.2	802.4
30°	877.1	846.3	751.0	670.7	610.9	610.0	670.7	751.0	749.2	756.6	782.8
32.5°	850.0	792.1	701.5	646.4	589.4	588.5	664.2	728.6	726.7	737.0	756.6
35°	824.8	750.1	634.3	618.4	562.4	563.3	648.3	702.5	703.4	712.7	724.9
37.5°	798.7	713.7	560.5	587.6	536.2	536.2	626.8	678.2	676.3	679.1	695.9
40°	767.8	656.7	495.1	547.4	511.9	509.1	600.7	652.0	645.5	644.6	667.9
42.5°	735.2	594.1	446.5	494.2	483.9	480.2	568.9	620.3	608.1	610.9	640.8
45°	699.7	577.3	409.2	417.6	455.0	452.1	534.3	583.8	575.4	582.9	613.7
47.5°	664.2	543.7	397.0	346.6	424.1	423.2	496.0	548.4	543.7	551.2	583.8
50°	615.6	506.3	396.1	297.0	389.6	393.3	450.3	513.8	513.8	520.3	554.9
52.5°	553.0	460.6	359.7	269.0	349.4	360.6	410.1	483.9	485.8	492.3	523.1
55°	496.0	412.9	333.5	247.5	301.7	326.0	370.9	453.1	456.8	463.4	491.4
57.5°	443.7	343.8	327.8	222.3	257.8	281.1	336.3	423.2	425.1	430.7	457.8
60°	387.7	248.4	300.7	195.2	219.5	237.2	304.5	387.7	394.2	398.0	421.3
62.5°	324.1	180.3	272.7	176.5	200.8	204.5	278.3	354.1	362.5	365.3	379.3
65°	230.7	151.3	231.6	160.6	181.2	182.1	250.3	319.4	326.9	331.6	341.9
67.5°	156.0	123.3	176.5	145.7	166.3	167.2	223.2	279.3	289.5	293.3	299.8
70°	108.3	82.2	130.8	129.8	149.4	151.3	194.3	242.8	252.2	255.0	258.7
72.5°	79.4	66.3	108.3	116.8	131.7	133.6	164.4	201.7	211.1	213.9	215.8
75°	60.7	70.0	87.8	101.8	112.1	113.0	134.5	164.4	170.9	172.8	173.7
77.5°	48.6	65.4	64.4	82.2	91.5	89.7	105.5	127.0	132.6	132.6	132.6
80°	36.4	51.4	48.6	58.8	67.2	65.4	75.7	90.6	92.5	94.3	93.4
82.5°	27.1	32.7	32.7	37.4	44.8	43.0	50.4	58.8	58.8	58.8	60.7
85°	16.8	18.7	14.9	19.6	25.2	24.3	28.0	31.8	32.7	32.7	30.8
87.5°	10.3	8.4	4.7	7.5	11.2	11.2	13.1	14.0	13.1	13.1	13.1
90°	7.6	5.2	2.9	5.2	7.6	8.1	12.8	19.0	22.0	19.6	14.7
92.5°	50.9	31.3	11.6	31.3	50.9	55.9	78.5	108.8	123.9	108.6	78.0
95°	99.9	63.9	27.8	63.9	99.9	108.9	193.3	305.9	362.2	323.2	245.2
97.5°	111.6	79.9	48.1	79.9	111.6	119.6	260.4	448.1	542.0	517.3	468.1
100°	121.3	92.5	63.7	92.5	121.3	128.5	284.8	493.2	597.3	599.1	602.7
102.5°	130.8	104.0	77.1	104.0	130.8	137.5	296.0	507.3	613.0	644.4	707.1
105°	145.1	122.4	99.6	122.4	145.1	150.8	304.3	508.9	611.2	681.6	822.4
107.5°	165.2	144.0	122.7	144.0	165.2	170.5	305.9	486.2	576.5	674.6	871.0
110°	176.8	157.6	138.4	157.6	176.8	181.6	303.6	466.2	547.5	657.3	876.7

TEST NUMBER: P934786

CATALOG NUMBER: SQ4-FA-075U-075D-B2750-1D-UNV-W2A-W-4-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	190.3	172.0	153.7	172.0	190.3	194.8	303.6	448.7	521.2	633.5	858.2
115°	210.6	193.7	176.9	193.7	210.6	214.8	306.4	428.5	489.6	597.9	814.3
117.5°	230.4	215.1	199.8	215.1	230.4	234.2	312.1	415.9	467.8	565.5	760.8
120°	241.9	227.5	213.1	227.5	241.9	245.5	316.7	411.7	459.2	548.4	726.9
122.5°	255.2	240.7	226.1	240.7	255.2	258.8	323.4	409.5	452.5	532.8	693.6
125°	272.6	259.4	246.1	259.4	272.6	275.9	332.4	407.7	445.3	513.6	650.2
127.5°	289.1	275.7	262.4	275.7	289.1	292.4	341.4	406.7	439.3	497.9	615.1
130°	299.8	285.4	271.0	285.4	299.8	303.5	347.9	407.2	436.9	489.1	593.5
132.5°	308.8	294.4	280.0	294.4	308.8	312.4	353.2	407.7	434.9	481.6	575.1
135°	319.5	306.4	293.3	306.4	319.5	322.8	359.0	407.3	431.4	470.5	548.8
137.5°	332.9	319.9	306.9	319.9	332.9	336.1	367.7	409.8	430.9	463.9	530.0
140°	342.1	330.2	318.2	330.2	342.1	345.1	373.0	410.2	428.8	457.4	514.4
142.5°	348.9	337.9	326.9	337.9	348.9	351.7	377.4	411.7	428.8	453.9	504.1
145°	359.5	349.9	340.2	349.9	359.5	361.9	383.2	411.7	425.9	446.5	487.5
147.5°	372.3	362.9	353.5	362.9	372.3	374.6	391.7	414.5	425.9	442.1	474.4
150°	379.2	370.7	362.2	370.7	379.2	381.4	396.2	416.0	425.9	439.5	466.8
152.5°	384.1	377.6	371.2	377.6	384.1	385.6	399.1	416.9	425.9	437.6	460.8
155°	394.0	389.3	384.5	389.3	394.0	395.2	405.4	419.1	425.9	435.2	453.6
157.5°	403.7	399.0	394.3	399.0	403.7	404.8	411.8	421.2	425.9	433.1	447.5
160°	408.2	404.6	401.0	404.6	408.2	409.1	414.7	422.2	425.9	432.1	444.5
162.5°	413.1	410.4	407.7	410.4	413.1	413.8	417.8	423.2	425.9	431.1	441.5
165°	419.7	417.3	414.9	417.3	419.7	420.4	422.3	424.7	425.9	429.6	437.1
167.5°	423.8	422.6	421.5	422.6	423.8	424.1	425.7	427.8	428.8	431.2	436.2
170°	428.2	427.0	425.9	427.0	428.2	428.5	428.6	428.7	428.8	431.2	436.2
172.5°	428.7	428.5	428.2	428.5	428.7	428.8	428.8	428.8	428.8	430.8	434.6
175°	431.4	431.4	431.4	431.4	431.4	431.4	430.6	429.4	428.8	430.0	432.4
177.5°	431.4	431.4	431.4	431.4	431.4	431.4	430.8	429.8	429.4	430.3	432.3
180°	431.4	431.4	431.4	431.4	431.4	431.4	431.4	431.4	431.4	431.4	431.4

TEST NUMBER: P934786

CATALOG NUMBER: SQ4-FA-075U-075D-B2750-1D-UNV-W2A-W-4-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3
2.5°	952.8	950.0	953.7	943.4	953.7	950.0	952.8	959.3	953.7	957.4	961.2
5°	836.0	831.4	816.4	804.3	816.4	831.4	836.0	855.6	865.0	881.8	904.2
7.5°	747.3	743.6	739.8	732.3	739.8	743.6	747.3	752.9	762.2	777.2	794.0
10°	727.7	728.6	734.2	733.3	734.2	728.6	727.7	725.8	723.0	725.8	736.1
12.5°	778.1	786.5	817.3	815.5	817.3	786.5	778.1	740.8	715.5	710.9	712.7
15°	836.0	838.8	845.4	846.3	845.4	838.8	836.0	821.1	745.4	712.7	702.5
17.5°	841.6	842.6	847.2	847.2	847.2	842.6	841.6	835.1	809.9	766.0	708.1
20°	837.0	838.8	848.2	850.0	848.2	838.8	837.0	828.6	814.5	798.7	754.8
22.5°	835.1	838.8	846.3	845.4	846.3	838.8	835.1	822.0	809.9	798.7	780.9
25°	825.7	825.7	826.7	827.6	826.7	825.7	825.7	815.5	791.2	788.4	778.1
27.5°	806.1	808.0	813.6	812.7	813.6	808.0	806.1	802.4	776.2	773.4	766.0
30°	788.4	786.5	781.9	778.1	781.9	786.5	788.4	782.8	756.6	749.2	751.0
32.5°	758.5	753.8	749.2	746.4	749.2	753.8	758.5	756.6	737.0	726.7	728.6
35°	723.0	723.9	723.0	720.2	723.0	723.9	723.0	724.9	712.7	703.4	702.5
37.5°	697.8	699.7	698.7	695.0	698.7	699.7	697.8	695.9	679.1	676.3	678.2
40°	671.6	672.6	671.6	668.8	671.6	672.6	671.6	667.9	644.6	645.5	652.0
42.5°	646.4	645.5	642.7	640.8	642.7	645.5	646.4	640.8	610.9	608.1	620.3
45°	617.5	618.4	612.8	610.0	612.8	618.4	617.5	613.7	582.9	575.4	583.8
47.5°	588.5	588.5	583.8	581.0	583.8	588.5	588.5	583.8	551.2	543.7	548.4
50°	557.7	556.8	550.2	549.3	550.2	556.8	557.7	554.9	520.3	513.8	513.8
52.5°	522.2	522.2	523.1	525.0	523.1	522.2	522.2	523.1	492.3	485.8	483.9
55°	491.4	492.3	498.8	500.7	498.8	492.3	491.4	491.4	463.4	456.8	453.1
57.5°	459.6	459.6	464.3	464.3	464.3	459.6	459.6	457.8	430.7	425.1	423.2
60°	423.2	425.1	428.8	427.9	428.8	425.1	423.2	421.3	398.0	394.2	387.7
62.5°	384.9	386.8	387.7	385.8	387.7	386.8	384.9	379.3	365.3	362.5	354.1
65°	344.7	346.6	347.5	345.7	347.5	346.6	344.7	341.9	331.6	326.9	319.4
67.5°	303.6	302.6	301.7	305.4	301.7	302.6	303.6	299.8	293.3	289.5	279.3
70°	261.5	261.5	260.6	262.5	260.6	261.5	261.5	258.7	255.0	252.2	242.8
72.5°	216.7	215.8	219.5	216.7	219.5	215.8	216.7	215.8	213.9	211.1	201.7
75°	172.8	174.7	172.8	175.6	172.8	174.7	172.8	173.7	172.8	170.9	164.4
77.5°	131.7	133.6	131.7	131.7	131.7	133.6	131.7	132.6	132.6	132.6	127.0
80°	93.4	92.5	92.5	91.5	92.5	92.5	93.4	93.4	94.3	92.5	90.6
82.5°	59.8	58.8	58.8	60.7	58.8	58.8	59.8	60.7	58.8	58.8	58.8
85°	32.7	33.6	31.8	31.8	31.8	33.6	32.7	30.8	32.7	32.7	31.8
87.5°	12.1	11.2	11.2	11.2	11.2	11.2	12.1	13.1	13.1	13.1	14.0
90°	11.0	11.0	11.0	11.0	11.0	11.0	11.0	14.7	19.6	22.0	19.0
92.5°	55.0	52.9	44.1	35.3	44.1	52.9	55.0	78.0	108.6	123.9	108.8
95°	186.7	180.1	153.6	127.1	153.6	180.1	186.7	245.2	323.2	362.2	305.9
97.5°	431.1	418.5	368.1	317.7	368.1	418.5	431.1	468.1	517.3	542.0	448.1
100°	605.4	590.4	530.3	470.2	530.3	590.4	605.4	602.7	599.1	597.3	493.2
102.5°	754.2	741.3	689.9	638.4	689.9	741.3	754.2	707.1	644.4	613.0	507.3
105°	927.9	921.0	893.4	865.7	893.4	921.0	927.9	822.4	681.6	611.2	508.9
107.5°	1018.2	1019.9	1026.7	1033.4	1026.7	1019.9	1018.2	871.0	674.6	576.5	486.2
110°	1041.4	1048.6	1077.5	1106.3	1077.5	1048.6	1041.4	876.7	657.3	547.5	466.2

TEST NUMBER: P934786

CATALOG NUMBER: SQ4-FA-075U-075D-B2750-1D-UNV-W2A-W-4-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1026.7	1037.8	1082.0	1126.3	1082.0	1037.8	1026.7	858.2	633.5	521.2	448.7
115°	976.6	991.9	1053.4	1114.7	1053.4	991.9	976.6	814.3	597.9	489.6	428.5
117.5°	907.4	924.4	992.5	1060.6	992.5	924.4	907.4	760.8	565.5	467.8	415.9
120°	860.8	877.3	943.4	1009.6	943.4	877.3	860.8	726.9	548.4	459.2	411.7
122.5°	814.2	830.5	895.7	961.0	895.7	830.5	814.2	693.6	532.8	452.5	409.5
125°	752.5	767.6	827.6	887.7	827.6	767.6	752.5	650.2	513.6	445.3	407.7
127.5°	703.0	715.7	766.3	817.1	766.3	715.7	703.0	615.1	497.9	439.3	406.7
130°	671.7	683.4	730.3	777.1	730.3	683.4	671.7	593.5	489.1	436.9	407.2
132.5°	645.1	655.6	697.5	739.4	697.5	655.6	645.1	575.1	481.6	434.9	407.7
135°	607.5	616.5	652.7	688.8	652.7	616.5	607.5	548.8	470.5	431.4	407.3
137.5°	579.6	587.0	616.6	646.2	616.6	587.0	579.6	530.0	463.9	430.9	409.8
140°	557.3	564.2	592.0	619.6	592.0	564.2	557.3	514.4	457.4	428.8	410.2
142.5°	541.7	547.7	571.4	595.2	571.4	547.7	541.7	504.1	453.9	428.8	411.7
145°	518.3	522.8	540.8	558.8	540.8	522.8	518.3	487.5	446.5	425.9	411.7
147.5°	498.6	502.3	517.2	532.2	517.2	502.3	498.6	474.4	442.1	425.9	414.5
150°	487.3	490.3	502.4	514.5	502.4	490.3	487.3	466.8	439.5	425.9	416.0
152.5°	478.3	480.5	489.7	498.8	489.7	480.5	478.3	460.8	437.6	425.9	416.9
155°	467.6	469.1	475.1	481.2	475.1	469.1	467.6	453.6	435.2	425.9	419.1
157.5°	458.3	459.3	463.6	467.8	463.6	459.3	458.3	447.5	433.1	425.9	421.2
160°	453.7	454.3	456.7	459.2	456.7	454.3	453.7	444.5	432.1	425.9	422.2
162.5°	449.3	449.9	452.2	454.6	452.2	449.9	449.3	441.5	431.1	425.9	423.2
165°	442.7	443.4	445.8	448.2	445.8	443.4	442.7	437.1	429.6	425.9	424.7
167.5°	439.8	440.1	441.1	442.2	441.1	440.1	439.8	436.2	431.2	428.8	427.8
170°	439.8	439.8	439.8	439.8	439.8	439.8	439.8	436.2	431.2	428.8	428.7
172.5°	437.5	437.3	436.4	435.4	436.4	437.3	437.5	434.6	430.8	428.8	428.8
175°	434.3	434.3	434.3	434.3	434.3	434.3	434.3	432.4	430.0	428.8	429.4
177.5°	433.7	433.5	432.4	431.4	432.4	433.5	433.7	432.3	430.3	429.4	429.8
180°	431.4	431.4	431.4	431.4	431.4	431.4	431.4	431.4	431.4	431.4	431.4

TEST NUMBER: P934786

CATALOG NUMBER: SQ4-FA-075U-075D-B2750-1D-UNV-W2A-W-4-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	987.3	987.3	987.3	987.3	987.3
2.5°	975.2	979.9	982.7	986.4	995.7
5°	937.8	955.6	961.2	975.2	992.0
7.5°	855.6	909.8	924.8	958.4	984.5
10°	776.2	830.4	856.6	936.0	975.2
12.5°	736.1	767.8	785.6	896.7	962.1
15°	710.9	733.3	746.4	844.4	947.2
17.5°	691.3	707.1	716.5	793.1	926.6
20°	679.1	686.6	695.0	755.7	903.3
22.5°	670.7	666.0	672.6	729.5	871.5
25°	665.1	647.4	654.8	709.0	834.2
27.5°	669.8	630.5	633.3	690.3	794.9
30°	670.7	610.0	610.9	670.7	751.0
32.5°	664.2	588.5	589.4	646.4	701.5
35°	648.3	563.3	562.4	618.4	634.3
37.5°	626.8	536.2	536.2	587.6	560.5
40°	600.7	509.1	511.9	547.4	495.1
42.5°	568.9	480.2	483.9	494.2	446.5
45°	534.3	452.1	455.0	417.6	409.2
47.5°	496.0	423.2	424.1	346.6	397.0
50°	450.3	393.3	389.6	297.0	396.1
52.5°	410.1	360.6	349.4	269.0	359.7
55°	370.9	326.0	301.7	247.5	333.5
57.5°	336.3	281.1	257.8	222.3	327.8
60°	304.5	237.2	219.5	195.2	300.7
62.5°	278.3	204.5	200.8	176.5	272.7
65°	250.3	182.1	181.2	160.6	231.6
67.5°	223.2	167.2	166.3	145.7	176.5
70°	194.3	151.3	149.4	129.8	130.8
72.5°	164.4	133.6	131.7	116.8	108.3
75°	134.5	113.0	112.1	101.8	87.8
77.5°	105.5	89.7	91.5	82.2	64.4
80°	75.7	65.4	67.2	58.8	48.6
82.5°	50.4	43.0	44.8	37.4	32.7
85°	28.0	24.3	25.2	19.6	14.9
87.5°	13.1	11.2	11.2	7.5	4.7
90°	12.8	8.1	7.6	5.2	2.9
92.5°	78.5	55.9	50.9	31.3	11.6
95°	193.3	108.9	99.9	63.9	27.8
97.5°	260.4	119.6	111.6	79.9	48.1
100°	284.8	128.5	121.3	92.5	63.7
102.5°	296.0	137.5	130.8	104.0	77.1
105°	304.3	150.8	145.1	122.4	99.6
107.5°	305.9	170.5	165.2	144.0	122.7
110°	303.6	181.6	176.8	157.6	138.4



TEST NUMBER: P934786

CATALOG NUMBER: SQ4-FA-075U-075D-B2750-1D-UNV-W2A-W-4-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	303.6	194.8	190.3	172.0	153.7
115°	306.4	214.8	210.6	193.7	176.9
117.5°	312.1	234.2	230.4	215.1	199.8
120°	316.7	245.5	241.9	227.5	213.1
122.5°	323.4	258.8	255.2	240.7	226.1
125°	332.4	275.9	272.6	259.4	246.1
127.5°	341.4	292.4	289.1	275.7	262.4
130°	347.9	303.5	299.8	285.4	271.0
132.5°	353.2	312.4	308.8	294.4	280.0
135°	359.0	322.8	319.5	306.4	293.3
137.5°	367.7	336.1	332.9	319.9	306.9
140°	373.0	345.1	342.1	330.2	318.2
142.5°	377.4	351.7	348.9	337.9	326.9
145°	383.2	361.9	359.5	349.9	340.2
147.5°	391.7	374.6	372.3	362.9	353.5
150°	396.2	381.4	379.2	370.7	362.2
152.5°	399.1	385.6	384.1	377.6	371.2
155°	405.4	395.2	394.0	389.3	384.5
157.5°	411.8	404.8	403.7	399.0	394.3
160°	414.7	409.1	408.2	404.6	401.0
162.5°	417.8	413.8	413.1	410.4	407.7
165°	422.3	420.4	419.7	417.3	414.9
167.5°	425.7	424.1	423.8	422.6	421.5
170°	428.6	428.5	428.2	427.0	425.9
172.5°	428.8	428.8	428.7	428.5	428.2
175°	430.6	431.4	431.4	431.4	431.4
177.5°	430.8	431.4	431.4	431.4	431.4
180°	431.4	431.4	431.4	431.4	431.4

TEST NUMBER: P934786

CATALOG NUMBER: SQ4-FA-075U-075D-B2750-1D-UNV-W2A-W-4-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.28	13.12	13.26	14.11	15.42	15.08	15.92	16.06	16.91	18.21
	3H	12.76	13.51	13.75	14.51	15.84	16.42	17.17	17.40	18.17	19.49
	4H	12.95	13.66	13.95	14.66	16.00	16.85	17.57	17.85	18.57	19.90
	6H	13.07	13.72	14.08	14.73	16.08	17.13	17.79	18.14	18.79	20.14
	8H	13.07	13.69	14.08	14.72	16.06	17.20	17.82	18.21	18.85	20.19
	12H	13.04	13.63	14.06	14.65	16.02	17.23	17.83	18.25	18.84	20.21
4H	2H	13.31	14.02	14.31	15.02	16.35	15.49	16.20	16.50	17.21	18.54
	3H	14.33	14.93	15.35	15.96	17.30	16.98	17.58	18.00	18.61	19.96
	4H	14.61	15.15	15.63	16.17	17.54	17.50	18.05	18.53	19.07	20.44
	6H	14.73	15.20	15.76	16.24	17.61	17.86	18.33	18.89	19.37	20.74
	8H	14.74	15.17	15.77	16.21	17.59	17.96	18.40	19.00	19.44	20.82
	12H	14.70	15.10	15.75	16.15	17.54	18.01	18.41	19.07	19.46	20.85
8H	4H	15.05	15.49	16.09	16.53	17.91	17.63	18.06	18.66	19.10	20.48
	6H	15.31	15.67	16.37	16.76	18.13	18.06	18.42	19.11	19.50	20.88
	8H	15.36	15.67	16.42	16.74	18.14	18.20	18.52	19.27	19.59	20.98
	12H	15.34	15.62	16.41	16.68	18.12	18.29	18.57	19.36	19.63	21.07
12H	4H	15.06	15.45	16.11	16.51	17.89	17.59	17.99	18.64	19.04	20.43
	6H	15.37	15.69	16.44	16.76	18.15	18.05	18.37	19.12	19.44	20.83
	8H	15.44	15.72	16.51	16.78	18.22	18.21	18.49	19.28	19.55	20.99

END OF REPORT