

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937501

Luminaire Tested: SQ4-FB-100U-050D-B40-1D-UNV-W2A-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937501
REPORT IS A COMBINATION OF REPORTS P933557 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-050D-B40-1D-UNV-W2A-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16140.5 lumens
Efficiency: N/A
Efficacy: 130.6 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 123.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937501

CATALOG NUMBER: SQ4-FB-100U-050D-B40-1D-UNV-W2A-W-12

Luminous Intensity Polar Plot



TEST NUMBER: P937501

CATALOG NUMBER: SQ4-FB-100U-050D-B40-1D-UNV-W2A-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37	37	37	29
1	93	88	84	81	83	79	76	73	62	60	58	46	45	44	32	31	30	30	30	23
2	84	77	71	66	75	69	64	59	54	50	47	40	38	36	28	26	25	25	25	19
3	76	67	60	54	68	60	54	49	47	43	39	35	32	30	24	22	21	21	21	16
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	21	19	18	18	18	13
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15	15	15	11
6	58	47	39	33	52	42	35	30	33	28	24	25	21	18	17	15	13	13	13	10
7	54	42	34	28	48	38	31	26	30	25	21	22	19	16	15	13	11	11	11	8
8	50	38	30	25	44	34	27	23	27	22	18	20	17	14	14	12	10	10	10	7
9	46	34	27	22	41	31	24	20	24	20	16	18	15	12	13	11	9	9	9	7
10	43	31	24	19	38	28	22	18	22	18	14	17	14	11	12	10	8	8	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1848	1848	1848
5°	1807	2137	2485
10°	1639	3116	4119
15°	1394	4072	4974
20°	1135	4720	5069
25°	947	4940	4966
30°	799	4973	4957
35°	707	4891	5085
40°	617	4786	5217
45°	558	4708	5238
50°	513	4639	5151
55°	492	4537	4923
60°	504	4340	4562
65°	526	4039	4067
70°	561	3525	3436
75°	624	2876	2681
80°	687	1997	1807
85°	622	1062	924

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5238 cd/sqm

TEST NUMBER: P937501

CATALOG NUMBER: SQ4-FB-100U-050D-B40-1D-UNV-W2A-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.3	0.5
10°-20°	342.6	2.1
20°-30°	599.3	3.7
30°-40°	771.5	4.8
40°-50°	861.7	5.3
50°-60°	825.3	5.1
60°-70°	654.1	4.1
70°-80°	384.6	2.4
80°-90°	113.6	0.7
90°-100°	865.5	5.4
100°-110°	2275.5	14.1
110°-120°	2359.4	14.6
120°-130°	1892.6	11.7
130°-140°	1485.0	9.2
140°-150°	1139.8	7.1
150°-160°	820.8	5.1
160°-170°	502.2	3.1
170°-180°	169.7	1.1
0°-30°	1019.2	6.3
0°-40°	1790.7	11.1
0°-60°	3477.7	21.5
0°-90°	4629.9	28.7
90°-120°	5500.5	34.1
90°-150°	10017.8	62.1
90°-180°	11511.0	71.3
0°-180°	16140.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	598	598	598	598	598	
5°	582	624	703	796	824	54
15°	436	805	1357	1645	1697	121
25°	279	913	1616	1687	1689	128
35°	188	872	1522	1608	1672	118
45°	129	696	1345	1541	1610	100
55°	92	442	1141	1326	1362	84
65°	73	234	848	953	967	72
75°	54	144	465	511	513	56
85°	19	44	115	127	129	20
90°	12	33	90	45	45	11
95°	114	448	1491	769	523	127
105°	410	621	2516	3819	3563	435
115°	728	884	2015	4020	4588	719
125°	1013	1136	1833	3097	3654	899
135°	1207	1329	1776	2500	2835	934
145°	1400	1490	1753	2133	2300	877
155°	1582	1627	1753	1924	1981	727
165°	1708	1730	1753	1822	1845	482
175°	1776	1776	1765	1788	1788	169
180°	1776	1776	1776	1776	1776	

TEST NUMBER: P937501

CATALOG NUMBER: SQ4-FB-100U-050D-B40-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	597.6	597.6	597.6	597.6	597.6	597.6	597.6	597.6	597.6	597.6	597.6
2.5°	597.6	597.6	601.5	603.4	607.2	609.1	613.0	616.8	628.4	630.3	634.1
5°	582.3	589.9	614.9	624.5	651.4	687.9	703.3	728.3	780.1	795.5	805.2
7.5°	559.2	576.4	637.9	653.3	720.6	816.7	857.0	910.9	993.5	1033.8	1066.4
10°	522.7	559.2	668.7	705.3	814.7	960.8	1035.7	1110.7	1235.6	1291.4	1312.5
12.5°	482.3	541.9	701.4	751.3	908.9	1122.2	1212.6	1295.2	1437.4	1512.3	1523.8
15°	436.2	516.9	732.1	805.2	1008.9	1256.7	1356.7	1458.5	1591.1	1644.9	1658.4
17.5°	395.8	497.7	760.9	837.8	1085.7	1377.8	1479.6	1564.2	1671.8	1708.3	1717.9
20°	345.9	467.0	780.1	880.1	1166.4	1466.2	1564.2	1629.5	1702.6	1725.6	1729.4
22.5°	309.4	434.2	791.7	895.5	1220.2	1520.0	1602.6	1654.5	1704.5	1712.1	1714.0
25°	278.7	397.8	789.8	912.8	1266.3	1552.6	1616.1	1654.5	1683.3	1687.2	1687.2
27.5°	249.8	357.5	782.0	916.6	1300.9	1560.4	1610.3	1637.2	1650.6	1658.4	1658.4
30°	224.8	319.0	762.9	908.9	1316.3	1552.6	1593.0	1606.5	1619.9	1631.4	1637.2
32.5°	205.6	282.5	734.0	893.5	1318.2	1533.4	1562.3	1569.9	1589.1	1616.1	1625.7
35°	188.3	246.0	701.4	872.4	1306.7	1502.7	1521.9	1529.6	1568.0	1608.4	1621.8
37.5°	171.0	219.1	659.1	835.9	1289.3	1466.2	1479.6	1493.0	1552.6	1600.7	1616.1
40°	153.8	196.0	609.1	795.5	1262.5	1422.0	1433.6	1454.7	1533.4	1589.1	1604.5
42.5°	140.3	176.8	555.3	753.3	1227.9	1372.0	1389.3	1420.1	1510.3	1569.9	1587.2
45°	128.7	157.6	497.7	695.6	1183.7	1320.1	1345.1	1387.4	1483.5	1541.1	1556.5
47.5°	117.2	144.1	438.2	636.0	1135.7	1268.2	1300.9	1348.9	1446.9	1502.7	1516.2
50°	107.6	130.6	378.6	572.6	1083.7	1212.6	1251.0	1300.9	1400.9	1452.7	1470.0
52.5°	99.9	119.2	322.8	509.2	1024.2	1154.9	1199.1	1251.0	1345.1	1395.1	1406.6
55°	92.3	109.5	274.8	442.0	962.7	1093.4	1141.4	1191.4	1283.6	1325.9	1333.6
57.5°	88.4	101.8	234.5	378.6	897.4	1024.2	1078.0	1124.1	1210.6	1243.3	1251.0
60°	82.6	96.1	203.7	324.8	826.3	958.9	1005.0	1051.1	1124.1	1151.1	1156.8
62.5°	76.9	92.3	180.6	272.8	753.3	882.0	928.2	970.4	1031.9	1051.1	1058.8
65°	73.1	88.4	163.3	234.5	678.3	801.3	847.5	883.9	933.9	953.1	956.9
67.5°	69.1	84.5	149.8	201.8	603.4	720.6	755.2	789.8	828.2	847.5	849.4
70°	63.4	80.7	138.4	178.7	526.5	628.4	657.2	693.7	724.5	734.0	739.8
72.5°	59.6	75.0	130.6	161.4	447.7	540.0	566.9	588.0	614.9	624.5	624.5
75°	53.8	67.2	123.0	144.1	367.0	442.0	465.0	486.2	507.3	511.1	505.4
77.5°	48.0	59.6	105.7	121.1	286.3	349.7	368.9	380.5	397.8	401.6	403.5
80°	40.4	51.9	82.6	94.2	207.5	257.5	270.9	280.6	296.0	296.0	299.8
82.5°	30.8	40.4	59.6	67.2	140.3	176.8	188.3	194.1	203.7	203.7	203.7
85°	19.2	25.0	38.4	44.2	84.5	107.6	115.3	117.2	124.9	126.8	126.8
87.5°	9.6	13.5	25.0	26.9	44.2	55.8	55.8	59.6	59.6	57.7	55.8
90°	11.9	21.5	30.9	33.3	52.4	77.8	90.5	80.5	60.4	45.3	45.3
92.5°	47.7	128.6	209.7	230.0	323.4	447.8	510.1	447.0	321.0	226.4	217.5
95°	114.4	262.7	411.0	448.1	795.6	1259.1	1490.8	1330.3	1009.3	768.6	741.3
97.5°	197.8	328.6	459.5	492.2	1071.7	1844.4	2230.8	2129.4	1926.5	1774.4	1722.5
100°	262.1	380.8	499.4	529.1	1172.2	2029.7	2458.5	2465.9	2480.7	2491.8	2430.0
102.5°	317.0	427.6	538.3	566.0	1218.3	2088.0	2522.8	2652.0	2910.5	3104.3	3051.3
105°	410.0	503.7	597.4	620.8	1252.5	2094.6	2515.7	2805.4	3384.8	3819.3	3790.9
107.5°	505.3	592.7	680.1	701.9	1258.8	2001.3	2372.6	2776.8	3585.0	4191.1	4198.0
110°	569.7	648.5	727.4	747.2	1249.2	1918.7	2253.4	2705.2	3608.8	4286.4	4316.1

TEST NUMBER: P937501

CATALOG NUMBER: SQ4-FB-100U-050D-B40-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	632.8	708.0	783.2	802.0	1249.7	1846.6	2145.0	2607.4	3532.2	4225.7	4271.2
115°	728.1	797.5	866.9	884.2	1261.2	1763.8	2015.1	2460.6	3351.4	4019.5	4082.6
117.5°	822.3	885.3	948.3	964.1	1284.7	1712.0	1925.8	2327.7	3131.7	3734.7	3804.7
120°	877.1	936.4	995.8	1010.6	1303.8	1694.6	1890.0	2257.3	2991.9	3542.9	3611.0
122.5°	930.7	990.6	1050.4	1065.4	1331.2	1685.5	1862.6	2193.3	2854.9	3351.0	3418.1
125°	1013.0	1067.5	1122.0	1135.7	1368.0	1677.9	1832.8	2113.8	2675.7	3097.2	3158.9
127.5°	1079.6	1134.7	1189.8	1203.6	1405.0	1673.5	1807.8	2049.0	2531.5	2893.4	2945.5
130°	1115.4	1174.7	1234.1	1248.9	1432.0	1676.2	1798.3	2013.0	2442.6	2764.7	2813.0
132.5°	1152.4	1211.7	1271.0	1285.8	1453.8	1677.8	1789.9	1982.1	2366.7	2655.1	2698.3
135°	1207.2	1261.2	1315.2	1328.7	1477.7	1676.3	1775.6	1936.6	2258.6	2500.1	2537.3
137.5°	1263.2	1316.7	1370.1	1383.5	1513.4	1686.6	1773.2	1909.3	2181.6	2385.8	2416.2
140°	1309.7	1359.0	1408.1	1420.5	1535.3	1688.3	1764.8	1882.4	2117.6	2294.0	2322.5
142.5°	1345.4	1391.0	1436.5	1447.9	1553.5	1694.4	1764.8	1868.2	2074.7	2229.6	2254.1
145°	1400.2	1439.9	1479.7	1489.6	1577.4	1694.5	1753.0	1837.4	2006.4	2133.1	2151.6
147.5°	1455.0	1493.7	1532.4	1542.0	1612.3	1706.1	1753.0	1819.5	1952.4	2052.1	2067.5
150°	1490.8	1525.7	1560.7	1569.4	1630.7	1712.2	1753.0	1809.2	1921.4	2005.6	2018.0
152.5°	1527.7	1554.2	1580.7	1587.3	1642.5	1716.1	1753.0	1800.9	1896.7	1968.6	1978.0
155°	1582.5	1602.1	1621.8	1626.7	1668.8	1724.9	1753.0	1791.1	1867.3	1924.5	1930.7
157.5°	1623.0	1642.1	1661.2	1666.0	1695.0	1733.7	1753.0	1782.6	1841.9	1886.4	1890.8
160°	1650.4	1665.3	1680.1	1683.9	1706.9	1737.6	1753.0	1778.4	1829.2	1867.3	1869.8
162.5°	1677.8	1688.9	1700.1	1702.9	1719.6	1741.8	1753.0	1774.4	1817.3	1849.5	1851.8
165°	1707.6	1717.7	1727.8	1730.3	1737.8	1747.9	1753.0	1768.4	1799.0	1822.0	1824.5
167.5°	1735.0	1739.8	1744.6	1745.8	1752.1	1760.6	1764.8	1775.0	1795.1	1810.2	1811.3
170°	1753.0	1757.8	1762.5	1763.7	1764.1	1764.6	1764.8	1775.0	1795.1	1810.2	1810.2
172.5°	1762.5	1763.5	1764.6	1764.8	1764.8	1764.8	1764.8	1772.8	1788.7	1800.7	1799.7
175°	1775.6	1775.6	1775.6	1775.6	1772.0	1767.2	1764.8	1769.9	1779.9	1787.5	1787.5
177.5°	1775.6	1775.6	1775.6	1775.6	1772.9	1769.1	1767.2	1771.2	1779.2	1785.1	1784.0
180°	1775.6	1775.6	1775.6	1775.6	1775.6	1775.6	1775.6	1775.6	1775.6	1775.6	1775.6

TEST NUMBER: P937501

CATALOG NUMBER: SQ4-FB-100U-050D-B40-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	597.6	597.6
2.5°	637.9	634.1
5°	820.5	824.4
7.5°	1104.9	1103.0
10°	1374.0	1391.2
12.5°	1569.9	1573.7
15°	1689.1	1696.7
17.5°	1735.2	1737.1
20°	1737.1	1733.3
22.5°	1715.9	1712.1
25°	1691.0	1689.1
27.5°	1667.9	1669.9
30°	1658.4	1664.1
32.5°	1658.4	1667.9
35°	1662.2	1671.8
37.5°	1660.3	1671.8
40°	1652.5	1666.0
42.5°	1631.4	1641.1
45°	1598.8	1610.3
47.5°	1556.5	1564.2
50°	1502.7	1510.3
52.5°	1435.5	1437.4
55°	1354.8	1362.4
57.5°	1268.2	1270.1
60°	1172.2	1177.9
62.5°	1070.4	1070.4
65°	962.7	966.6
67.5°	851.3	860.8
70°	737.9	739.8
72.5°	626.5	626.5
75°	511.1	513.0
77.5°	401.6	401.6
80°	297.9	299.8
82.5°	205.6	209.4
85°	128.7	128.7
87.5°	59.6	53.8
90°	45.3	45.3
92.5°	181.4	145.4
95°	632.2	523.1
97.5°	1514.9	1307.3
100°	2182.7	1935.3
102.5°	2839.5	2627.7
105°	3676.9	3563.1
107.5°	4225.6	4253.1
110°	4434.7	4553.4

TEST NUMBER: P937501

CATALOG NUMBER: SQ4-FB-100U-050D-B40-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	4453.5	4635.7
115°	4335.3	4587.9
117.5°	4084.9	4365.1
120°	3883.1	4155.4
122.5°	3686.6	3955.1
125°	3406.3	3653.6
127.5°	3154.3	3362.9
130°	3005.7	3198.5
132.5°	2870.9	3043.6
135°	2686.1	2835.0
137.5°	2538.0	2659.9
140°	2436.4	2550.2
142.5°	2352.1	2450.1
145°	2225.8	2299.9
147.5°	2128.9	2190.3
150°	2067.9	2117.6
152.5°	2015.6	2053.2
155°	1955.6	1980.6
157.5°	1908.3	1925.8
160°	1879.9	1890.0
162.5°	1861.4	1870.9
165°	1834.7	1844.7
167.5°	1815.5	1819.7
170°	1810.2	1810.2
172.5°	1796.0	1792.2
175°	1787.5	1787.5
177.5°	1779.8	1775.6
180°	1775.6	1775.6

(END OF REPORT)