

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435911

Luminaire Tested: SQ2W-FB-K-025U-050D-L935-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2019
Report Number: P1435911
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FB-K-025U-050D-L935-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3023.7 lumens
Efficiency: N/A
Efficacy: 119.5 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 25.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1435911

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1435911

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73	68
1	102	97	93	89	96	92	88	85	82	79	76	72	70	68	64	62	61	57
2	92	84	78	72	87	80	74	69	71	66	62	63	59	56	56	53	51	47
3	84	73	66	59	78	69	62	57	62	56	52	55	51	47	49	45	42	39
4	76	65	56	50	71	61	53	48	55	48	43	49	44	40	43	39	36	33
5	70	57	48	42	65	54	46	40	49	42	37	43	38	34	38	34	31	28
6	64	51	42	36	60	48	40	35	43	37	32	39	33	29	34	30	27	24
7	59	46	37	31	55	44	36	30	39	33	28	35	30	26	31	27	23	21
8	55	41	33	28	51	39	32	27	35	29	24	32	26	22	28	24	21	18
9	51	38	30	24	48	36	29	23	32	26	22	29	24	20	26	22	18	16
10	47	34	27	22	45	33	26	21	30	24	19	27	22	18	24	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3358	3358	3358	3358
5°	3274	5948	3274	5948
10°	3066	11575	3066	11575
15°	2775	13322	2775	13322
20°	2457	13952	2457	13952
25°	2173	14180	2173	14180
30°	1920	14355	1920	14355
35°	1715	15433	1715	15433
40°	1560	16398	1560	16398
45°	1438	17171	1438	17171
50°	1356	17482	1356	17482
55°	1323	17621	1323	17621
60°	1356	17534	1356	17534
65°	1414	17039	1414	17039
70°	1463	12887	1463	12887
75°	1622	7112	1622	7112
80°	1674	6601	1674	6601
85°	1667	2779	1667	2779

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 17780 cd/sqm



TEST NUMBER: P1435911

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.8	1.2
10°-20°	159.0	5.3
20°-30°	279.8	9.3
30°-40°	362.2	12.0
40°-50°	399.5	13.2
50°-60°	372.8	12.3
60°-70°	288.0	9.5
70°-80°	132.8	4.4
80°-90°	26.8	0.9
90°-100°	26.4	0.9
100°-110°	76.9	2.5
110°-120°	125.6	4.2
120°-130°	159.3	5.3
130°-140°	170.5	5.6
140°-150°	159.2	5.3
150°-160°	131.0	4.3
160°-170°	87.9	2.9
170°-180°	31.2	1.0
0°-30°	473.7	15.7
0°-40°	835.9	27.6
0°-60°	1608.1	53.2
0°-90°	2055.7	68.0
90°-120°	228.9	7.6
90°-150°	717.9	23.7
90°-180°	968.0	32.0
0°-180°	3023.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	208	208	208	208	208	
5°	202	367	202	367	202	19
15°	166	797	166	797	166	46
25°	122	796	122	796	122	56
35°	87	783	87	783	87	55
45°	63	752	63	752	63	49
55°	47	626	47	626	47	42
65°	37	446	37	446	37	36
75°	26	114	26	114	26	27
85°	9	15	9	15	9	9
90°	1	7	1	14	1	1
95°	10	8	10	45	10	13
105°	49	78	49	108	49	52
115°	94	130	94	160	94	92
125°	139	206	139	196	139	124
135°	188	270	188	217	188	146
145°	241	311	241	222	241	151
155°	286	338	286	230	286	131
165°	316	352	316	265	316	89
175°	330	345	330	311	330	31
180°	332	332	332	332	332	



TEST NUMBER: P1435911

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0
2.5°	206.4	210.3	214.2	218.4	222.7	227.3	232.3	236.5	238.7	240.8	238.7
5°	202.0	215.3	228.7	248.0	269.3	293.6	320.7	343.9	355.4	367.0	355.4
7.5°	194.2	221.3	248.4	305.9	373.4	443.6	516.3	576.6	599.7	622.8	599.7
10°	187.0	224.8	262.6	360.0	477.3	567.6	630.7	681.1	693.6	706.0	693.6
12.5°	179.0	230.3	281.6	401.9	545.2	638.9	683.2	719.6	732.4	745.2	732.4
15°	166.0	239.3	312.7	448.7	605.6	702.0	738.0	768.6	782.8	797.0	782.8
17.5°	152.6	250.2	347.8	486.5	639.0	733.0	768.7	797.3	805.1	812.8	805.1
20°	143.0	257.7	372.3	511.3	658.4	747.3	778.0	802.2	807.1	812.0	807.1
22.5°	134.2	262.4	390.6	529.7	672.6	755.6	778.8	797.5	802.8	808.0	802.8
25°	122.0	266.4	410.9	549.7	686.6	762.3	777.0	788.9	792.5	796.0	792.5
27.5°	110.2	262.8	415.4	552.5	684.3	755.0	764.6	772.7	776.1	779.6	776.1
30°	103.0	258.1	413.2	549.0	678.3	746.6	753.7	760.2	765.1	770.0	765.1
32.5°	96.6	252.4	408.2	542.3	669.2	736.0	742.7	750.5	761.0	771.6	761.0
35°	87.0	240.3	393.7	526.3	652.1	720.3	731.0	743.9	763.5	783.0	763.5
37.5°	78.8	224.8	370.9	502.2	628.6	703.0	725.3	746.7	765.6	784.4	765.6
40°	74.0	214.0	354.0	484.3	611.4	689.9	719.7	746.0	762.0	778.0	762.0
42.5°	69.2	201.7	334.3	463.5	591.7	673.2	707.9	738.0	754.0	770.0	754.0
45°	63.0	182.1	301.2	429.3	560.4	646.4	687.3	721.8	736.9	752.0	736.9
47.5°	57.2	160.7	264.1	392.8	529.9	620.1	663.5	698.8	709.8	720.8	709.8
50°	54.0	146.4	238.9	368.0	509.3	601.3	644.0	678.2	687.1	696.0	687.1
52.5°	50.8	132.6	214.4	343.7	489.0	581.7	621.9	654.0	662.2	670.4	662.2
55°	47.0	113.7	180.3	308.3	456.8	548.6	583.7	611.8	618.9	626.0	618.9
57.5°	43.6	97.4	151.2	275.1	422.5	511.2	541.1	565.0	570.8	576.6	570.8
60°	42.0	88.7	135.3	254.3	397.4	482.6	509.7	531.4	537.2	543.0	537.2
62.5°	39.6	80.2	120.8	233.5	370.2	451.1	476.1	496.2	501.6	507.0	501.6
65°	37.0	69.9	102.8	204.3	328.8	401.4	422.3	438.9	442.4	446.0	442.4
67.5°	33.4	61.3	89.2	177.6	286.1	346.9	359.9	367.9	361.3	354.6	361.3
70°	31.0	56.8	82.6	161.3	257.8	308.2	312.7	311.2	292.1	273.0	292.1
72.5°	29.4	52.3	75.3	143.5	226.8	263.5	253.7	237.4	201.2	165.0	201.2
75°	26.0	44.7	63.3	114.7	176.9	186.7	144.0	112.2	113.1	114.0	113.1
77.5°	21.2	35.2	49.1	80.7	118.1	125.5	102.9	86.2	87.0	87.8	87.0
80°	18.0	29.1	40.2	52.7	65.6	71.6	70.7	70.1	70.6	71.0	70.6
82.5°	14.8	23.1	31.3	38.8	46.0	50.0	50.9	51.4	50.8	50.2	50.8
85°	9.0	13.9	18.8	21.7	23.9	23.2	19.7	16.8	15.9	15.0	15.9
87.5°	3.4	5.4	7.6	7.2	6.0	5.3	5.3	5.4	5.5	5.5	5.5
90°	1.0	2.3	4.0	5.4	6.4	6.7	6.7	7.0	7.4	7.4	7.4
92.5°	3.7	5.8	5.9	5.9	7.2	7.8	8.3	8.4	8.7	8.7	8.7
95°	10.4	11.4	17.1	16.7	11.4	9.0	7.7	7.7	7.7	7.7	7.7
97.5°	19.8	21.3	22.2	29.8	31.5	30.4	24.8	20.8	18.6	17.6	18.6
100°	28.1	28.8	30.8	31.1	39.5	47.6	43.5	38.5	36.8	35.8	36.8
102.5°	36.4	36.8	39.9	41.3	43.3	47.8	61.8	60.2	59.1	58.9	59.1
105°	48.9	49.2	54.9	57.6	58.9	58.9	58.6	65.3	76.0	78.4	76.0
107.5°	62.2	63.8	70.5	77.6	79.2	79.6	77.8	76.8	76.4	76.7	76.4
110°	71.3	73.7	81.7	90.8	93.1	93.8	93.1	92.1	91.4	91.4	91.4



TEST NUMBER: P1435911

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	80.2	83.6	92.7	103.1	107.0	109.0	107.6	106.8	106.2	106.7	106.2
115°	93.8	98.8	110.8	121.6	129.6	130.6	130.3	130.3	129.9	129.9	129.9
117.5°	106.4	114.4	127.9	140.4	149.7	152.4	153.7	153.3	152.9	153.6	152.9
120°	115.2	124.6	140.0	154.0	163.1	167.1	168.4	167.8	168.4	167.8	168.4
122.5°	124.6	136.1	151.2	165.8	176.5	181.0	182.6	182.8	182.9	182.5	182.9
125°	138.6	152.7	170.5	185.5	196.6	201.9	203.3	203.6	204.3	206.0	204.3
127.5°	152.8	168.8	188.3	202.8	214.1	220.6	222.7	223.4	224.8	225.6	224.8
130°	162.8	180.8	200.6	214.3	225.4	232.4	236.1	237.1	238.8	238.4	238.8
132.5°	173.2	192.1	212.1	226.4	236.6	244.2	247.3	250.2	250.8	251.3	250.8
135°	188.5	209.0	229.1	243.1	252.8	260.2	264.2	266.9	268.6	269.6	268.6
137.5°	204.7	226.2	245.5	258.1	267.8	274.2	278.8	281.6	283.3	284.1	283.3
140°	215.7	236.4	255.2	268.2	276.9	283.3	287.3	290.7	292.7	292.7	292.7
142.5°	226.1	246.6	264.8	277.9	285.5	291.3	295.6	298.2	300.5	300.5	300.5
145°	240.8	261.2	277.9	291.0	297.4	302.7	307.4	309.4	310.8	310.8	310.8
147.5°	256.1	274.2	289.5	302.0	307.4	313.6	317.3	318.9	320.6	319.9	320.6
150°	265.2	282.0	296.7	308.4	313.8	319.8	323.5	324.8	326.5	325.5	326.5
152.5°	274.1	290.0	303.4	314.3	318.9	324.9	329.1	330.5	331.6	330.9	331.6
155°	286.0	300.1	312.4	322.5	326.5	332.2	336.2	337.9	339.2	337.6	339.2
157.5°	296.6	308.8	319.5	328.8	333.1	338.0	341.7	343.8	345.1	344.4	345.1
160°	303.1	314.1	323.8	332.5	336.6	340.9	344.9	347.3	348.6	347.6	348.6
162.5°	308.4	318.4	327.6	335.5	339.0	342.8	347.6	349.7	351.0	349.7	351.0
165°	316.1	324.2	332.2	338.9	341.9	344.9	349.9	352.3	353.3	352.0	353.3
167.5°	322.0	328.1	334.6	340.4	342.6	345.5	350.6	352.5	353.8	352.1	353.8
170°	325.2	330.5	336.2	340.9	342.6	345.3	350.3	352.0	353.0	351.3	353.0
172.5°	327.8	331.9	336.5	340.6	341.5	343.7	348.4	350.1	350.8	349.4	350.8
175°	330.5	332.9	336.2	338.9	338.6	339.9	343.9	345.3	346.6	344.6	346.6
177.5°	331.8	332.9	333.9	335.5	334.5	334.5	337.4	338.2	338.5	337.4	338.5
180°	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5



TEST NUMBER: P1435911

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0
2.5°	236.5	232.3	227.3	222.7	218.4	214.2	210.3	206.4	210.3	214.2	218.4
5°	343.9	320.7	293.6	269.3	248.0	228.7	215.3	202.0	215.3	228.7	248.0
7.5°	576.6	516.3	443.6	373.4	305.9	248.4	221.3	194.2	221.3	248.4	305.9
10°	681.1	630.7	567.6	477.3	360.0	262.6	224.8	187.0	224.8	262.6	360.0
12.5°	719.6	683.2	638.9	545.2	401.9	281.6	230.3	179.0	230.3	281.6	401.9
15°	768.6	738.0	702.0	605.6	448.7	312.7	239.3	166.0	239.3	312.7	448.7
17.5°	797.3	768.7	733.0	639.0	486.5	347.8	250.2	152.6	250.2	347.8	486.5
20°	802.2	778.0	747.3	658.4	511.3	372.3	257.7	143.0	257.7	372.3	511.3
22.5°	797.5	778.8	755.6	672.6	529.7	390.6	262.4	134.2	262.4	390.6	529.7
25°	788.9	777.0	762.3	686.6	549.7	410.9	266.4	122.0	266.4	410.9	549.7
27.5°	772.7	764.6	755.0	684.3	552.5	415.4	262.8	110.2	262.8	415.4	552.5
30°	760.2	753.7	746.6	678.3	549.0	413.2	258.1	103.0	258.1	413.2	549.0
32.5°	750.5	742.7	736.0	669.2	542.3	408.2	252.4	96.6	252.4	408.2	542.3
35°	743.9	731.0	720.3	652.1	526.3	393.7	240.3	87.0	240.3	393.7	526.3
37.5°	746.7	725.3	703.0	628.6	502.2	370.9	224.8	78.8	224.8	370.9	502.2
40°	746.0	719.7	689.9	611.4	484.3	354.0	214.0	74.0	214.0	354.0	484.3
42.5°	738.0	707.9	673.2	591.7	463.5	334.3	201.7	69.2	201.7	334.3	463.5
45°	721.8	687.3	646.4	560.4	429.3	301.2	182.1	63.0	182.1	301.2	429.3
47.5°	698.8	663.5	620.1	529.9	392.8	264.1	160.7	57.2	160.7	264.1	392.8
50°	678.2	644.0	601.3	509.3	368.0	238.9	146.4	54.0	146.4	238.9	368.0
52.5°	654.0	621.9	581.7	489.0	343.7	214.4	132.6	50.8	132.6	214.4	343.7
55°	611.8	583.7	548.6	456.8	308.3	180.3	113.7	47.0	113.7	180.3	308.3
57.5°	565.0	541.1	511.2	422.5	275.1	151.2	97.4	43.6	97.4	151.2	275.1
60°	531.4	509.7	482.6	397.4	254.3	135.3	88.7	42.0	88.7	135.3	254.3
62.5°	496.2	476.1	451.1	370.2	233.5	120.8	80.2	39.6	80.2	120.8	233.5
65°	438.9	422.3	401.4	328.8	204.3	102.8	69.9	37.0	69.9	102.8	204.3
67.5°	367.9	359.9	346.9	286.1	177.6	89.2	61.3	33.4	61.3	89.2	177.6
70°	311.2	312.7	308.2	257.8	161.3	82.6	56.8	31.0	56.8	82.6	161.3
72.5°	237.4	253.7	263.5	226.8	143.5	75.3	52.3	29.4	52.3	75.3	143.5
75°	112.2	144.0	186.7	176.9	114.7	63.3	44.7	26.0	44.7	63.3	114.7
77.5°	86.2	102.9	125.5	118.1	80.7	49.1	35.2	21.2	35.2	49.1	80.7
80°	70.1	70.7	71.6	65.6	52.7	40.2	29.1	18.0	29.1	40.2	52.7
82.5°	51.4	50.9	50.0	46.0	38.8	31.3	23.1	14.8	23.1	31.3	38.8
85°	16.8	19.7	23.2	23.9	21.7	18.8	13.9	9.0	13.9	18.8	21.7
87.5°	5.4	5.3	5.3	6.0	7.2	7.6	5.4	3.4	5.4	7.5	7.3
90°	7.0	6.7	6.7	6.4	5.4	4.0	2.3	1.0	2.3	3.7	6.0
92.5°	8.4	8.3	7.8	7.2	5.9	5.9	5.8	3.7	6.4	9.0	13.0
95°	7.7	7.7	9.0	11.4	16.7	17.1	11.4	10.4	14.7	20.8	26.1
97.5°	20.8	24.8	30.4	31.5	29.8	22.2	21.3	19.8	27.0	33.0	41.6
100°	38.5	43.5	47.6	39.5	31.1	30.8	28.8	28.1	35.8	41.5	49.9
102.5°	60.2	61.8	47.8	43.3	41.3	39.9	36.8	36.4	44.1	52.0	59.0
105°	65.3	58.6	58.9	58.9	57.6	54.9	49.2	48.9	57.6	66.6	75.3
107.5°	76.8	77.8	79.6	79.2	77.6	70.5	63.8	62.2	70.1	80.9	90.5
110°	92.1	93.1	93.8	93.1	90.8	81.7	73.7	71.3	78.4	89.7	100.1



TEST NUMBER: P1435911

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	106.8	107.6	109.0	107.0	103.1	92.7	83.6	80.2	87.2	98.9	109.5
115°	130.3	130.3	130.6	129.6	121.6	110.8	98.8	93.8	99.8	110.5	122.2
117.5°	153.3	153.7	152.4	149.7	140.4	127.9	114.4	106.4	111.1	122.4	134.5
120°	167.8	168.4	167.1	163.1	154.0	140.0	124.6	115.2	118.9	129.9	142.0
122.5°	182.8	182.6	181.0	176.5	165.8	151.2	136.1	124.6	126.1	136.4	148.2
125°	203.6	203.3	201.9	196.6	185.5	170.5	152.7	138.6	136.6	145.3	157.4
127.5°	223.4	222.7	220.6	214.1	202.8	188.3	168.8	152.8	148.4	153.8	164.9
130°	237.1	236.1	232.4	225.4	214.3	200.6	180.8	162.8	156.4	159.7	169.4
132.5°	250.2	247.3	244.2	236.6	226.4	212.1	192.1	173.2	164.4	165.9	173.5
135°	266.9	264.2	260.2	252.8	243.1	229.1	209.0	188.5	176.5	175.1	179.5
137.5°	281.6	278.8	274.2	267.8	258.1	245.5	226.2	204.7	189.5	185.0	186.7
140°	290.7	287.3	283.3	276.9	268.2	255.2	236.4	215.7	198.6	192.2	191.2
142.5°	298.2	295.6	291.3	285.5	277.9	264.8	246.6	226.1	208.0	199.7	197.4
145°	309.4	307.4	302.7	297.4	291.0	277.9	261.2	240.8	222.7	212.0	207.0
147.5°	318.9	317.3	313.6	307.4	302.0	289.5	274.2	256.1	237.6	224.3	217.8
150°	324.8	323.5	319.8	313.8	308.4	296.7	282.0	265.2	247.5	233.4	225.0
152.5°	330.5	329.1	324.9	318.9	314.3	303.4	290.0	274.1	256.0	242.0	233.3
155°	337.9	336.2	332.2	326.5	322.5	312.4	300.1	286.0	270.6	255.8	246.1
157.5°	343.8	341.7	338.0	333.1	328.8	319.5	308.8	296.6	283.2	269.1	259.2
160°	347.3	344.9	340.9	336.6	332.5	323.8	314.1	303.1	290.7	277.9	267.2
162.5°	349.7	347.6	342.8	339.0	335.5	327.6	318.4	308.4	297.4	286.3	276.3
165°	352.3	349.9	344.9	341.9	338.9	332.2	324.2	316.1	306.7	297.7	289.7
167.5°	352.5	350.6	345.5	342.6	340.4	334.6	328.1	322.0	314.7	307.6	300.9
170°	352.0	350.3	345.3	342.6	340.9	336.2	330.5	325.2	319.5	313.4	308.1
172.5°	350.1	348.4	343.7	341.5	340.6	336.5	331.9	327.8	323.0	318.5	314.3
175°	345.3	343.9	339.9	338.6	338.9	336.2	332.9	330.5	327.5	324.8	322.5
177.5°	338.2	337.4	334.5	334.5	335.5	333.9	332.9	331.8	330.5	329.7	328.9
180°	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5



TEST NUMBER: P1435911

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0	208.0
2.5°	222.7	227.3	232.3	236.5	238.7	240.8	238.7	236.5	232.3	227.3	222.7
5°	269.3	293.6	320.7	343.9	355.4	367.0	355.4	343.9	320.7	293.6	269.3
7.5°	373.4	443.6	516.3	576.6	599.7	622.8	599.7	576.6	516.3	443.6	373.4
10°	477.3	567.6	630.7	681.1	693.6	706.0	693.6	681.1	630.7	567.6	477.3
12.5°	545.2	638.9	683.2	719.6	732.4	745.2	732.4	719.6	683.2	638.9	545.2
15°	605.6	702.0	738.0	768.6	782.8	797.0	782.8	768.6	738.0	702.0	605.6
17.5°	639.0	733.0	768.7	797.3	805.1	812.8	805.1	797.3	768.7	733.0	639.0
20°	658.4	747.3	778.0	802.2	807.1	812.0	807.1	802.2	778.0	747.3	658.4
22.5°	672.6	755.6	778.8	797.5	802.8	808.0	802.8	797.5	778.8	755.6	672.6
25°	686.6	762.3	777.0	788.9	792.5	796.0	792.5	788.9	777.0	762.3	686.6
27.5°	684.3	755.0	764.6	772.7	776.1	779.6	776.1	772.7	764.6	755.0	684.3
30°	678.3	746.6	753.7	760.2	765.1	770.0	765.1	760.2	753.7	746.6	678.3
32.5°	669.2	736.0	742.7	750.5	761.0	771.6	761.0	750.5	742.7	736.0	669.2
35°	652.1	720.3	731.0	743.9	763.5	783.0	763.5	743.9	731.0	720.3	652.1
37.5°	628.6	703.0	725.3	746.7	765.6	784.4	765.6	746.7	725.3	703.0	628.6
40°	611.4	689.9	719.7	746.0	762.0	778.0	762.0	746.0	719.7	689.9	611.4
42.5°	591.7	673.2	707.9	738.0	754.0	770.0	754.0	738.0	707.9	673.2	591.7
45°	560.4	646.4	687.3	721.8	736.9	752.0	736.9	721.8	687.3	646.4	560.4
47.5°	529.9	620.1	663.5	698.8	709.8	720.8	709.8	698.8	663.5	620.1	529.9
50°	509.3	601.3	644.0	678.2	687.1	696.0	687.1	678.2	644.0	601.3	509.3
52.5°	489.0	581.7	621.9	654.0	662.2	670.4	662.2	654.0	621.9	581.7	489.0
55°	456.8	548.6	583.7	611.8	618.9	626.0	618.9	611.8	583.7	548.6	456.8
57.5°	422.5	511.2	541.1	565.0	570.8	576.6	570.8	565.0	541.1	511.2	422.5
60°	397.4	482.6	509.7	531.4	537.2	543.0	537.2	531.4	509.7	482.6	397.4
62.5°	370.2	451.1	476.1	496.2	501.6	507.0	501.6	496.2	476.1	451.1	370.2
65°	328.8	401.4	422.3	438.9	442.4	446.0	442.4	438.9	422.3	401.4	328.8
67.5°	286.1	346.9	359.9	367.9	361.3	354.6	361.3	367.9	359.9	346.9	286.1
70°	257.8	308.2	312.7	311.2	292.1	273.0	292.1	311.2	312.7	308.2	257.8
72.5°	226.8	263.5	253.7	237.4	201.2	165.0	201.2	237.4	253.7	263.5	226.8
75°	176.9	186.7	144.0	112.2	113.1	114.0	113.1	112.2	144.0	186.7	176.9
77.5°	118.1	125.5	102.9	86.2	87.0	87.8	87.0	86.2	102.9	125.5	118.1
80°	65.6	71.6	70.7	70.1	70.6	71.0	70.6	70.1	70.7	71.6	65.6
82.5°	46.0	50.0	50.9	51.4	50.8	50.2	50.8	51.4	50.9	50.0	46.0
85°	23.9	23.2	19.7	16.8	15.9	15.0	15.9	16.8	19.7	23.2	23.9
87.5°	6.3	6.0	6.5	6.7	7.0	6.9	7.0	6.7	6.5	6.0	6.3
90°	7.7	10.0	12.4	13.7	15.1	14.4	15.1	13.7	12.4	10.0	7.7
92.5°	15.5	19.4	22.3	24.7	25.8	25.7	25.8	24.7	22.3	19.4	15.5
95°	31.1	35.8	40.5	43.9	45.9	45.2	45.9	43.9	40.5	35.8	31.1
97.5°	48.0	54.3	59.5	62.7	64.7	66.0	64.7	62.7	59.5	54.3	48.0
100°	59.3	65.3	71.3	75.0	78.4	79.7	78.4	75.0	71.3	65.3	59.3
102.5°	68.4	76.3	82.8	86.8	89.6	91.0	89.6	86.8	82.8	76.3	68.4
105°	83.4	91.8	98.8	103.8	106.8	107.8	106.8	103.8	98.8	91.8	83.4
107.5°	98.4	107.0	113.5	119.1	122.8	124.9	122.8	119.1	113.5	107.0	98.4
110°	110.2	117.2	124.2	129.3	132.9	134.3	132.9	129.3	124.2	117.2	110.2



TEST NUMBER: P1435911

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	120.1	127.9	135.0	140.0	144.2	146.1	144.2	140.0	135.0	127.9	120.1
115°	134.0	144.3	150.7	155.4	158.4	160.1	158.4	155.4	150.7	144.3	134.0
117.5°	145.5	156.3	163.3	166.9	168.3	169.5	168.3	166.9	163.3	156.3	145.5
120°	152.7	162.8	170.8	175.5	177.2	177.8	177.2	175.5	170.8	162.8	152.7
122.5°	159.4	168.9	176.7	182.4	185.2	185.9	185.2	182.4	176.7	168.9	159.4
125°	168.8	177.8	185.9	191.6	194.6	196.2	194.6	191.6	185.9	177.8	168.8
127.5°	176.9	186.7	194.1	199.3	202.2	203.5	202.2	199.3	194.1	186.7	176.9
130°	181.5	191.6	198.9	204.6	207.3	208.6	207.3	204.6	198.9	191.6	181.5
132.5°	185.0	195.6	203.2	208.4	211.3	212.6	211.3	208.4	203.2	195.6	185.0
135°	189.2	200.3	208.3	213.3	216.0	217.3	216.0	213.3	208.3	200.3	189.2
137.5°	192.9	202.9	211.3	216.6	219.0	219.9	219.0	216.6	211.3	202.9	192.9
140°	195.6	204.3	212.6	217.7	220.4	220.7	220.4	217.7	212.6	204.3	195.6
142.5°	199.1	205.9	213.2	218.2	220.9	221.5	220.9	218.2	213.2	205.9	199.1
145°	205.3	209.3	214.3	219.0	221.4	222.0	221.4	219.0	214.3	209.3	205.3
147.5°	213.1	214.4	217.0	220.1	222.4	222.8	222.4	220.1	217.0	214.4	213.1
150°	219.0	218.7	219.7	221.7	223.7	223.4	223.7	221.7	219.7	218.7	219.0
152.5°	225.7	223.8	223.7	224.6	225.6	225.5	225.6	224.6	223.7	223.8	225.7
155°	237.1	233.4	231.4	230.7	230.7	230.4	230.7	230.7	231.4	233.4	237.1
157.5°	249.6	244.5	241.4	239.8	239.4	238.6	239.4	239.8	241.4	244.5	249.6
160°	258.2	252.5	249.5	246.8	245.8	244.8	245.8	246.8	249.5	252.5	258.2
162.5°	266.2	260.8	257.5	255.1	254.1	252.6	254.1	255.1	257.5	260.8	266.2
165°	279.3	273.6	269.9	267.9	266.6	265.2	266.6	267.9	269.9	273.6	279.3
167.5°	292.3	286.1	283.7	281.4	280.2	277.7	280.2	281.4	283.7	286.1	292.3
170°	300.4	294.7	293.4	291.3	289.0	286.3	289.0	291.3	293.4	294.7	300.4
172.5°	307.4	303.5	302.2	300.2	299.4	297.3	299.4	300.2	302.2	303.5	307.4
175°	317.5	314.5	314.5	314.1	313.1	311.1	313.1	314.1	314.5	314.5	317.5
177.5°	325.9	324.3	325.4	325.4	325.1	323.2	325.1	325.4	325.4	324.3	325.9
180°	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5	331.5



TEST NUMBER: P1435911

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	208.0	208.0	208.0	208.0
2.5°	218.4	214.2	210.3	206.4
5°	248.0	228.7	215.3	202.0
7.5°	305.9	248.4	221.3	194.2
10°	360.0	262.6	224.8	187.0
12.5°	401.9	281.6	230.3	179.0
15°	448.7	312.7	239.3	166.0
17.5°	486.5	347.8	250.2	152.6
20°	511.3	372.3	257.7	143.0
22.5°	529.7	390.6	262.4	134.2
25°	549.7	410.9	266.4	122.0
27.5°	552.5	415.4	262.8	110.2
30°	549.0	413.2	258.1	103.0
32.5°	542.3	408.2	252.4	96.6
35°	526.3	393.7	240.3	87.0
37.5°	502.2	370.9	224.8	78.8
40°	484.3	354.0	214.0	74.0
42.5°	463.5	334.3	201.7	69.2
45°	429.3	301.2	182.1	63.0
47.5°	392.8	264.1	160.7	57.2
50°	368.0	238.9	146.4	54.0
52.5°	343.7	214.4	132.6	50.8
55°	308.3	180.3	113.7	47.0
57.5°	275.1	151.2	97.4	43.6
60°	254.3	135.3	88.7	42.0
62.5°	233.5	120.8	80.2	39.6
65°	204.3	102.8	69.9	37.0
67.5°	177.6	89.2	61.3	33.4
70°	161.3	82.6	56.8	31.0
72.5°	143.5	75.3	52.3	29.4
75°	114.7	63.3	44.7	26.0
77.5°	80.7	49.1	35.2	21.2
80°	52.7	40.2	29.1	18.0
82.5°	38.8	31.3	23.1	14.8
85°	21.7	18.8	13.9	9.0
87.5°	7.3	7.5	5.4	3.4
90°	6.0	3.7	2.3	1.0
92.5°	13.0	9.0	6.4	3.7
95°	26.1	20.8	14.7	10.4
97.5°	41.6	33.0	27.0	19.8
100°	49.9	41.5	35.8	28.1
102.5°	59.0	52.0	44.1	36.4
105°	75.3	66.6	57.6	48.9
107.5°	90.5	80.9	70.1	62.2
110°	100.1	89.7	78.4	71.3

TEST NUMBER: P1435911

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	109.5	98.9	87.2	80.2
115°	122.2	110.5	99.8	93.8
117.5°	134.5	122.4	111.1	106.4
120°	142.0	129.9	118.9	115.2
122.5°	148.2	136.4	126.1	124.6
125°	157.4	145.3	136.6	138.6
127.5°	164.9	153.8	148.4	152.8
130°	169.4	159.7	156.4	162.8
132.5°	173.5	165.9	164.4	173.2
135°	179.5	175.1	176.5	188.5
137.5°	186.7	185.0	189.5	204.7
140°	191.2	192.2	198.6	215.7
142.5°	197.4	199.7	208.0	226.1
145°	207.0	212.0	222.7	240.8
147.5°	217.8	224.3	237.6	256.1
150°	225.0	233.4	247.5	265.2
152.5°	233.3	242.0	256.0	274.1
155°	246.1	255.8	270.6	286.0
157.5°	259.2	269.1	283.2	296.6
160°	267.2	277.9	290.7	303.1
162.5°	276.3	286.3	297.4	308.4
165°	289.7	297.7	306.7	316.1
167.5°	300.9	307.6	314.7	322.0
170°	308.1	313.4	319.5	325.2
172.5°	314.3	318.5	323.0	327.8
175°	322.5	324.8	327.5	330.5
177.5°	328.9	329.7	330.5	331.8
180°	331.5	331.5	331.5	331.5



TEST NUMBER: P1435911
 CATALOG NUMBER: SQ2W-FB-K-025U-050D-L935-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.88	12.97	12.66	13.78	14.77	21.48	22.57	22.26	23.37	24.36
	3H	12.84	13.82	13.63	14.64	15.65	23.10	24.08	23.89	24.90	25.91
	4H	13.25	14.17	14.06	15.00	16.02	23.29	24.21	24.10	25.04	26.07
	6H	13.51	14.37	14.34	15.20	16.24	23.38	24.23	24.20	25.06	26.10
	8H	13.61	14.43	14.45	15.28	16.32	23.40	24.22	24.23	25.07	26.11
	12H	13.67	14.45	14.51	15.29	16.36	23.39	24.16	24.23	25.01	26.08
4H	2H	16.63	17.56	17.44	18.38	19.41	21.87	22.80	22.69	23.62	24.65
	3H	17.78	18.55	18.61	19.41	20.45	23.78	24.55	24.61	25.41	26.46
	4H	18.07	18.77	18.91	19.63	20.70	24.01	24.72	24.85	25.57	26.64
	6H	18.22	18.83	19.08	19.71	20.78	24.16	24.77	25.02	25.65	26.72
	8H	18.27	18.83	19.13	19.71	20.80	24.21	24.78	25.07	25.65	26.74
	12H	18.28	18.79	19.16	19.69	20.78	24.20	24.71	25.09	25.61	26.70
8H	4H	19.29	19.85	20.15	20.73	21.82	24.12	24.69	24.99	25.57	26.66
	6H	19.55	20.02	20.44	20.94	22.03	24.33	24.80	25.22	25.72	26.81
	8H	19.66	20.07	20.56	20.98	22.09	24.43	24.84	25.33	25.75	26.86
	12H	19.71	20.07	20.61	20.98	22.13	24.44	24.81	25.35	25.71	26.87
12H	4H	19.32	19.83	20.20	20.73	21.82	24.09	24.60	24.97	25.49	26.59
	6H	19.66	20.08	20.56	20.99	22.10	24.32	24.73	25.22	25.65	26.75
	8H	19.81	20.18	20.72	21.08	22.24	24.43	24.79	25.33	25.70	26.86