

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582933

Luminaire Tested: **HCC6W05D010SL-HM60525927-61WWBB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582933  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W05D010SL-HM60525927-61WWBB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 474.9 lumens  
Efficiency: N/A  
Efficacy: 79.2 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582933  
CATALOG NUMBER: HCC6W05D010SL-HM60525927-61WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582933

CATALOG NUMBER: HCC6W05D010SL-HM60525927-61WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89					89			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78					78			
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69					69			
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	67	63	61					61			
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54					54			
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49					49			
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44					44			
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40					40			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37					37			
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34					34			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	14615	14615	14615
5°	14891	14583	14253
10°	15397	14401	13794
15°	15874	14149	13360
20°	16119	13558	12665
25°	15830	12630	11789
30°	15040	11508	10824
35°	13518	10286	9757
40°	11672	9017	8716
45°	9885	7760	7559
50°	8469	6550	6482
55°	7340	5515	5304
60°	6414	4484	3783
65°	5643	3463	2101
70°	4873	2276	1010
75°	4130	1101	402
80°	3220	474	253
85°	1950	189	189



TEST NUMBER: P582933  
 CATALOG NUMBER: HCC6W05D010SL-HM60525927-61WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	25.2	5.3
10°-20°	71.1	15.0
20°-30°	100.2	21.1
30°-40°	102.3	21.5
40°-50°	82.5	17.4
50°-60°	55.3	11.7
60°-70°	28.0	5.9
70°-80°	9.0	1.9
80°-90°	1.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	196.4	41.4
0°-40°	298.8	62.9
0°-60°	436.6	91.9
0°-90°	474.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	474.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	267	267	267	267	267	
5°	271	269	265	261	259	26
15°	280	268	249	238	235	79
25°	262	241	209	196	195	120
35°	202	184	154	145	146	126
45°	128	117	100	97	98	99
55°	77	68	58	55	56	69
65°	44	36	27	18	16	43
75°	20	14	5	2	2	21
85°	3	2	0	0	0	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582933

CATALOG NUMBER: HCC6W05D010SL-HM60525927-61WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6
2.5°	267.7	267.2	266.9	266.1	265.0	263.9	263.2	262.4	262.0
5°	270.6	270.0	268.8	267.2	265.0	262.4	260.9	259.4	259.0
7.5°	274.8	273.2	270.3	266.9	263.2	259.4	256.7	255.3	254.1
10°	276.6	274.0	270.0	264.3	258.7	254.1	250.7	248.5	247.8
12.5°	278.1	275.2	269.2	261.7	254.1	248.1	244.4	242.5	241.8
15°	279.7	276.6	268.4	258.7	249.3	242.2	238.1	236.2	235.4
17.5°	279.7	275.5	265.8	253.5	242.2	233.6	229.4	227.6	227.1
20°	276.3	271.8	259.8	245.2	232.4	222.7	218.9	217.8	217.1
22.5°	270.0	264.6	251.2	234.7	220.8	211.4	207.4	206.6	205.8
25°	261.7	256.4	241.0	223.4	208.8	199.4	196.1	195.3	194.9
27.5°	251.2	245.5	229.4	211.4	195.7	186.7	183.7	183.7	183.3
30°	237.6	231.3	215.5	197.5	181.8	173.6	171.3	171.3	171.0
32.5°	221.1	214.8	200.6	183.3	168.3	159.7	157.9	158.5	158.2
35°	202.0	196.8	183.7	166.8	153.7	145.8	145.1	145.8	145.8
37.5°	182.9	178.1	166.8	152.2	139.8	132.7	132.7	133.8	133.5
40°	163.1	159.3	148.8	136.1	126.0	121.1	120.3	121.5	121.8
42.5°	144.3	141.4	132.3	121.8	112.9	107.9	109.0	109.8	110.2
45°	127.5	124.4	117.3	106.4	100.1	96.7	96.7	97.9	97.5
47.5°	112.4	110.2	103.1	92.5	87.0	85.4	86.2	87.0	87.0
50°	99.3	95.9	89.3	81.0	76.8	74.9	75.7	76.0	76.0
52.5°	87.0	84.7	78.0	70.5	66.7	65.7	65.7	66.0	66.0
55°	76.8	74.2	68.3	60.7	57.7	56.3	55.1	54.7	55.5
57.5°	67.1	64.9	59.2	52.1	48.7	47.2	45.0	44.2	45.0
60°	58.5	56.6	51.0	44.2	40.9	37.9	35.3	33.8	34.5
62.5°	51.0	48.7	43.1	37.5	33.8	30.4	26.2	24.0	25.1
65°	43.5	41.6	35.9	30.4	26.7	22.5	17.6	16.2	16.2
67.5°	36.7	34.9	29.6	24.7	20.2	15.4	10.8	10.5	10.8
70°	30.4	28.5	24.0	19.1	14.2	9.4	6.3	6.3	6.3
72.5°	25.1	22.8	18.8	13.9	9.0	4.9	3.4	3.7	3.7
75°	19.5	17.6	13.9	9.4	5.2	2.3	1.9	1.9	1.9
77.5°	14.6	13.1	9.7	6.0	2.6	0.8	0.8	0.8	0.8
80°	10.2	8.6	6.3	3.7	1.5	0.8	0.8	0.8	0.8
82.5°	6.0	5.2	3.7	1.9	0.8	0.3	0.3	0.3	0.3
85°	3.1	2.6	1.5	0.8	0.3	0.3	0.3	0.3	0.3
87.5°	0.8	0.8	0.3	0.3	0.0	0.3	0.3	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)