

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: E395205

Luminaire Tested: **H7-1410**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: E395205  
Test Lab:  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO  
Catalog Number: H7-1410  
Description: HALO RECESSED INC - LV ADJ, 8" SPOT  
Light Source: 50MR16FL, 900 LUMENS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: 900 (1 lamp)  
Luminaire Lumens: 928.3 lumens  
Efficiency: 103.1%  
Efficacy: 15.5 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.66  
Luminous Opening: (L: 0 ' x W: -0.15 ' x H: 0 '  
CIE Type: Direct

Input Watts (W): 60  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: E395205  
CATALOG NUMBER: H7-1410

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - · - 135°-315°



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	123	123	123	123	120	120	120	120	115	115	115	110	110	110	105	105	105	103
1	112	107	102	98	109	104	100	96	100	96	93	96	93	90	92	90	88	86
2	104	96	89	84	101	94	88	83	90	85	81	87	83	79	84	80	77	75
3	97	88	80	75	95	86	79	74	83	77	73	80	76	71	78	74	70	68
4	92	82	74	68	90	80	73	68	78	72	67	76	70	66	73	69	65	63
5	87	77	69	63	85	75	68	63	73	67	62	72	66	62	70	65	61	59
6	83	72	65	60	82	71	64	59	70	63	59	68	63	58	67	62	58	56
7	80	69	61	56	78	68	61	56	66	60	56	65	60	56	64	59	55	54
8	76	65	58	54	75	65	58	53	63	57	53	62	57	53	61	56	53	51
9	73	62	56	51	72	62	55	51	61	55	51	60	54	51	59	54	50	49
10	70	60	53	49	69	59	53	49	58	52	49	57	52	48	57	52	48	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	Luminous shape not found,			
5°	reference photometric report, or contact			
10°	the photometric lab for calculations.			
15°				
20°				
25°				
30°				
35°				
40°				
45°				
50°				
55°				
60°				
65°				
70°				
75°				
80°				
85°				



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**ZONAL LUMENS:**

Zone	Lumens	% Fixture	% Lamp
0°-10°	121.8	13.1	13.5
10°-20°	291.1	31.4	32.3
20°-30°	191.8	20.7	21.3
30°-40°	47.4	5.1	5.3
40°-50°	16.4	1.8	1.8
50°-60°	8.6	0.9	1.0
60°-70°	76.4	8.2	8.5
70°-80°	118.6	12.8	13.2
80°-90°	56.1	6.0	6.2
90°-100°	0.0	0.0	0.0
100°-110°	0.0	0.0	0.0
110°-120°	0.0	0.0	0.0
120°-130°	0.0	0.0	0.0
130°-140°	0.0	0.0	0.0
140°-150°	0.0	0.0	0.0
150°-160°	0.0	0.0	0.0
160°-170°	0.0	0.0	0.0
170°-180°	0.0	0.0	0.0
0°-30°	604.8	65.1	67.2
0°-40°	652.1	70.2	72.5
0°-60°	677.2	72.9	75.2
0°-90°	928.3	100.0	103.1
90°-120°	0.0	0.0	0.0
90°-150°	0.0	0.0	0.0
90°-180°	0.0	0.0	0.0
0°-180°	928.3	100.0	103.1

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1242	1242	1242	1242	1242	
5°	1273	1273	1273	1273	1273	122
15°	1070	1070	1070	1070	1070	294
25°	396	396	396	396	396	188
35°	71	71	71	71	71	44
45°	20	20	20	20	20	16
55°	5	5	5	5	5	5
65°	3	3	3	3	3	3
75°	2	2	2	2	2	2
85°	1	1	1	1	1	1
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242
2.5°	1251	1251	1252	1252	1252	1253	1253	1252	1253	1253	1253
5°	1273	1274	1274	1274	1274	1275	1275	1275	1275	1275	1275
7.5°	1288	1288	1288	1288	1289	1289	1290	1291	1291	1292	1292
10°	1277	1277	1276	1276	1276	1276	1274	1271	1269	1267	1266
12.5°	1214	1213	1213	1215	1218	1217	1216	1217	1219	1227	1221
15°	1070	1068	1067	1067	1066	1061	1058	1057	1058	1061	1066
17.5°	931	927	925	925	917	909	904	900	897	897	900
20°	795	791	789	785	776	768	762	759	756	753	751
22.5°	606	603	604	602	599	598	600	603	600	594	589
25°	396	395	398	399	402	407	415	419	419	419	419
27.5°	250	249	250	252	256	262	269	268	267	265	264
30°	117	116	114	121	129	140	150	158	165	172	173
32.5°	94	93	92	93	94	95	96	98	100	101	99
35°	71	70	70	69	70	69	68	69	70	71	71
37.5°	50	50	50	50	50	50	50	49	48	48	48
40°	33	34	34	34	34	34	34	35	35	36	37
42.5°	26	26	26	26	27	27	27	27	27	27	27
45°	20	21	20	20	20	20	21	21	21	21	21
47.5°	16	16	15	15	15	15	16	16	16	16	16
50°	11	11	11	10	10	10	11	11	11	11	11
52.5°	6	6	6	5	5	5	6	6	6	6	6
55°	5	5	4	4	4	3	3	3	3	2	2
57.5°	4	4	4	4	3	3	3	3	2	2	1
60°	4	4	4	3	3	3	2	3	2	1	1
62.5°	4	4	3	3	3	2	2	2	2	1	1
65°	3	3	3	3	2	2	2	2	2	1	0
67.5°	3	3	3	2	2	2	2	2	1	1	0
70°	3	3	2	2	2	2	2	2	1	1	0
72.5°	2	2	2	2	2	1	1	1	1	0	0
75°	2	2	2	2	1	1	1	1	1	0	0
77.5°	2	2	2	1	1	1	1	1	1	0	0
80°	1	1	1	1	1	1	1	1	0	0	0
82.5°	1	1	1	1	1	1	1	1	0	0	0
85°	1	1	1	1	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242
2.5°	1254	1254	1254	1254	1254	1254	1255	1255	1255	1254	1254
5°	1274	1274	1275	1275	1275	1275	1275	1275	1275	1275	1275
7.5°	1292	1291	1291	1290	1290	1290	1290	1290	1290	1290	1290
10°	1266	1267	1269	1271	1275	1279	1285	1288	1286	1280	1276
12.5°	1218	1216	1216	1212	1203	1197	1194	1192	1193	1197	1202
15°	1074	1075	1075	1075	1076	1081	1072	1069	1071	1075	1076
17.5°	906	912	917	922	925	927	927	924	924	927	925
20°	753	760	770	786	790	779	771	767	767	771	779
22.5°	587	589	592	592	593	594	596	598	597	594	592
25°	420	418	415	411	412	415	418	420	419	417	413
27.5°	266	268	269	268	269	270	268	267	267	265	268
30°	170	164	156	150	161	168	169	164	164	164	166
32.5°	103	104	105	106	106	104	103	108	108	104	96
35°	71	70	70	70	72	73	73	72	69	70	70
37.5°	48	49	50	50	50	49	49	49	50	50	50
40°	36	36	35	34	36	36	35	35	35	35	36
42.5°	27	27	27	27	27	26	27	27	26	26	27
45°	21	21	21	21	21	21	21	21	21	21	21
47.5°	16	16	16	16	16	16	16	16	16	16	16
50°	11	11	11	11	11	11	11	11	11	11	11
52.5°	6	6	6	6	6	6	6	6	6	6	6
55°	2	2	3	2	2	2	3	2	2	1	2
57.5°	0	0	0	0	1	1	2	1	0	22	0
60°	0	0	0	0	0	0	17	29	62	133	149
62.5°	0	0	0	0	0	4	36	70	267	396	435
65°	0	0	0	0	0	16	47	151	393	637	780
67.5°	0	0	0	0	0	24	54	231	462	653	827
70°	0	0	0	0	4	30	80	283	495	647	813
72.5°	0	0	0	0	10	33	125	310	479	621	743
75°	0	0	0	0	13	33	148	314	447	574	659
77.5°	0	0	0	0	14	31	154	296	398	506	565
80°	0	0	0	0	13	34	143	253	336	414	463
82.5°	0	0	0	1	11	36	119	198	263	316	354
85°	0	0	0	1	8	29	85	137	180	213	239
87.5°	0	0	0	1	4	16	44	70	92	107	121
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0





TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242
2.5°	1254	1254	1254	1254	1253	1253	1253	1252	1253	1253	1252
5°	1275	1275	1274	1274	1275	1275	1275	1275	1275	1275	1274
7.5°	1290	1291	1291	1292	1292	1293	1291	1291	1290	1289	1289
10°	1272	1269	1267	1267	1267	1267	1269	1271	1274	1277	1276
12.5°	1210	1217	1217	1219	1222	1227	1220	1218	1217	1218	1219
15°	1075	1075	1074	1074	1068	1062	1058	1057	1058	1061	1066
17.5°	921	917	912	906	900	895	895	898	902	908	916
20°	786	777	764	756	752	752	757	760	763	769	776
22.5°	591	592	593	590	590	596	601	607	604	600	600
25°	410	411	416	421	423	422	420	418	417	408	402
27.5°	268	268	270	271	270	267	265	264	263	260	254
30°	164	157	153	163	168	169	166	158	148	139	129
32.5°	99	103	105	103	101	93	91	91	90	91	91
35°	71	70	69	69	69	69	68	69	69	69	70
37.5°	49	50	50	49	49	47	48	49	50	50	50
40°	36	36	35	34	35	35	36	35	35	33	33
42.5°	27	27	27	27	27	27	26	26	26	26	26
45°	21	21	21	21	21	21	21	21	21	21	21
47.5°	16	16	16	16	16	16	16	16	16	16	16
50°	11	11	11	11	11	10	10	10	10	11	11
52.5°	6	7	7	8	6	5	5	10	12	11	9
55°	2	2	21	19	10	15	23	23	19	14	9
57.5°	0	66	83	71	66	66	60	39	26	16	10
60°	172	210	224	190	172	141	90	56	32	18	11
62.5°	454	472	399	357	283	197	125	73	42	23	13
65°	796	720	636	527	388	267	177	106	58	29	15
67.5°	973	1017	901	694	524	369	246	152	84	42	19
70°	905	1003	1027	917	701	511	344	218	123	61	25
72.5°	826	888	886	886	888	699	490	313	185	91	39
75°	734	753	750	749	750	752	687	461	281	148	64
77.5°	625	621	618	617	616	617	619	624	437	243	111
80°	496	493	490	488	486	486	487	489	493	406	200
82.5°	370	367	365	363	361	360	359	360	362	365	369
85°	245	243	242	240	239	238	237	236	236	237	239
87.5°	122	121	120	119	119	118	117	117	117	116	117
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242
2.5°	1252	1252	1251	1251	1251	1252	1252	1252	1253	1253	1252
5°	1274	1274	1274	1273	1274	1274	1274	1274	1275	1275	1275
7.5°	1288	1288	1288	1288	1288	1288	1288	1289	1289	1290	1291
10°	1276	1277	1277	1277	1277	1277	1276	1276	1277	1274	1271
12.5°	1216	1214	1213	1214	1213	1214	1216	1219	1218	1217	1218
15°	1068	1067	1068	1070	1068	1067	1068	1066	1061	1058	1057
17.5°	927	926	927	931	927	926	925	916	908	902	898
20°	785	790	791	795	791	790	785	776	769	763	760
22.5°	602	605	603	606	603	605	602	600	600	604	607
25°	398	398	395	396	395	398	398	402	408	417	418
27.5°	250	249	248	250	248	249	250	254	260	263	264
30°	120	114	115	117	115	114	120	129	139	148	158
32.5°	91	91	92	94	92	91	91	91	91	90	91
35°	70	70	70	71	70	70	70	70	69	69	69
37.5°	50	50	50	50	50	50	50	50	50	50	49
40°	33	33	34	33	34	33	33	33	33	35	35
42.5°	26	26	27	26	27	26	26	26	26	26	26
45°	20	20	21	20	21	20	20	21	21	21	21
47.5°	16	16	16	16	16	16	16	16	16	16	16
50°	12	11	11	11	11	11	11	11	11	10	10
52.5°	8	7	6	6	6	6	7	7	7	7	6
55°	7	6	5	5	5	5	5	5	5	5	4
57.5°	6	5	5	4	4	4	4	5	4	4	3
60°	7	5	4	4	4	4	4	4	4	3	2
62.5°	8	5	4	4	4	4	4	4	3	2	2
65°	8	5	4	3	3	3	4	3	2	2	2
67.5°	9	5	4	3	3	3	3	2	2	1	2
70°	11	5	3	3	3	3	2	2	1	1	1
72.5°	15	6	3	2	2	2	2	1	1	1	2
75°	21	7	3	2	2	2	1	1	1	2	1
77.5°	36	9	2	2	2	1	1	1	1	1	1
80°	72	15	3	1	1	1	1	1	1	1	1
82.5°	154	34	3	1	1	0	1	1	1	1	1
85°	244	104	8	1	0	1	0	0	0	0	0
87.5°	117	119	53	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242
2.5°	1253	1253	1253	1254	1254	1254	1254	1254	1254	1255	1255
5°	1275	1275	1275	1274	1274	1275	1275	1275	1275	1275	1275
7.5°	1291	1293	1292	1292	1291	1291	1290	1290	1290	1290	1290
10°	1269	1267	1267	1267	1267	1269	1272	1276	1280	1286	1288
12.5°	1220	1227	1222	1219	1217	1217	1210	1202	1197	1193	1192
15°	1058	1062	1068	1074	1074	1075	1075	1076	1075	1071	1069
17.5°	895	895	900	906	912	917	921	925	925	924	924
20°	757	752	752	756	764	777	786	779	771	767	767
22.5°	601	596	590	590	593	592	591	592	594	597	598
25°	420	422	423	421	416	411	410	413	417	419	420
27.5°	265	267	270	271	270	268	268	268	265	267	267
30°	166	169	168	163	153	157	164	166	164	164	164
32.5°	91	93	101	103	105	103	99	96	104	108	108
35°	68	69	69	69	69	70	71	70	70	69	72
37.5°	48	47	49	49	50	50	49	50	50	50	49
40°	36	35	35	34	35	36	36	36	35	35	35
42.5°	26	27	27	27	27	27	27	27	26	26	27
45°	21	21	21	21	21	21	21	21	21	21	21
47.5°	16	16	16	16	16	16	16	16	16	16	16
50°	10	10	11	11	11	11	11	11	11	11	11
52.5°	5	5	6	6	7	7	6	6	6	6	6
55°	3	2	1	2	3	2	2	2	1	2	2
57.5°	2	2	1	0	1	1	0	0	0	0	1
60°	2	2	2	1	1	1	0	0	0	0	0
62.5°	2	2	2	2	2	1	0	0	0	0	0
65°	2	2	3	3	2	1	0	0	0	0	0
67.5°	2	2	2	2	2	1	0	0	0	0	0
70°	2	2	2	2	2	2	1	0	0	0	0
72.5°	2	2	2	2	2	2	1	0	0	0	0
75°	1	1	1	1	1	1	1	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	0	0	0
80°	1	1	1	1	1	1	1	1	0	0	0
82.5°	1	1	1	1	1	1	1	1	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242
2.5°	1255	1254	1254	1254	1254	1254	1254	1254	1253	1253	1253
5°	1275	1275	1275	1275	1275	1274	1274	1275	1275	1275	1275
7.5°	1290	1290	1290	1290	1291	1291	1292	1293	1292	1291	1291
10°	1285	1279	1275	1271	1269	1267	1266	1266	1267	1269	1271
12.5°	1194	1197	1203	1212	1216	1216	1218	1221	1222	1219	1217
15°	1072	1076	1076	1075	1075	1075	1074	1066	1061	1058	1057
17.5°	927	927	925	922	917	912	906	900	897	897	900
20°	771	779	789	786	770	760	753	751	753	756	759
22.5°	596	594	593	592	592	589	587	589	594	600	603
25°	418	415	412	411	415	418	420	419	419	419	419
27.5°	268	270	269	268	269	268	266	261	265	267	268
30°	169	168	161	150	156	164	170	173	172	165	158
32.5°	103	104	106	106	105	104	103	99	101	100	98
35°	73	73	72	69	70	70	71	71	71	70	69
37.5°	49	49	50	50	50	49	48	48	48	48	49
40°	35	36	36	34	35	36	36	37	36	35	35
42.5°	27	26	27	27	27	27	27	27	27	27	27
45°	21	21	21	21	21	21	21	21	21	21	21
47.5°	16	16	16	16	16	16	16	16	16	16	16
50°	11	11	11	11	11	11	11	11	11	10	11
52.5°	6	6	6	6	6	6	6	6	6	6	6
55°	3	2	2	2	3	2	2	2	2	3	3
57.5°	1	1	1	0	0	0	0	1	2	2	3
60°	0	0	0	0	0	0	0	1	1	2	3
62.5°	0	0	0	0	0	0	0	1	1	2	2
65°	0	0	0	0	0	0	0	0	1	2	2
67.5°	0	0	0	0	0	0	0	0	1	1	2
70°	0	0	0	0	0	0	0	0	1	1	2
72.5°	0	0	0	0	0	0	0	0	0	1	1
75°	0	0	0	0	0	0	0	0	0	1	1
77.5°	0	0	0	0	0	0	0	0	0	1	1
80°	0	0	0	0	0	0	0	0	0	0	1
82.5°	0	0	0	0	0	0	0	0	0	0	1
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0





TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242
2.5°	1253	1253	1252	1252	1252	1251	1251	1251	1252	1252	1252
5°	1275	1275	1274	1274	1274	1274	1273	1274	1274	1274	1274
7.5°	1290	1289	1289	1288	1288	1288	1288	1288	1288	1288	1289
10°	1274	1276	1276	1276	1276	1277	1277	1277	1276	1276	1276
12.5°	1216	1217	1218	1215	1213	1213	1214	1213	1213	1215	1218
15°	1058	1061	1066	1067	1067	1068	1070	1068	1067	1067	1066
17.5°	904	909	917	925	925	927	931	927	925	925	917
20°	762	768	776	785	789	791	795	791	789	785	776
22.5°	600	598	599	602	604	603	606	603	604	602	599
25°	415	407	402	399	398	395	396	395	398	399	402
27.5°	269	262	256	252	250	249	250	249	250	252	256
30°	150	140	129	121	114	115	117	115	114	121	129
32.5°	96	95	94	93	92	93	94	93	92	93	94
35°	68	69	69	69	70	70	71	70	70	69	69
37.5°	50	50	50	50	50	50	50	50	50	50	50
40°	33	34	34	34	34	34	33	34	34	34	34
42.5°	27	27	27	26	26	26	26	26	26	26	27
45°	21	20	20	20	20	21	20	21	20	20	20
47.5°	16	15	15	15	15	16	16	16	15	15	15
50°	11	10	10	10	11	11	11	11	11	10	10
52.5°	6	5	5	5	6	6	6	6	6	5	5
55°	3	3	4	4	4	5	5	5	4	4	4
57.5°	3	3	3	4	4	4	4	4	4	4	3
60°	2	3	3	3	4	4	4	4	4	3	3
62.5°	2	2	3	3	3	4	4	4	3	3	3
65°	2	2	2	3	3	3	3	3	3	3	2
67.5°	2	2	2	2	3	3	3	3	3	2	2
70°	2	2	2	2	2	3	3	3	2	2	2
72.5°	1	1	2	2	2	2	2	2	2	2	2
75°	1	1	1	2	2	2	2	2	2	2	1
77.5°	1	1	1	1	2	2	2	2	2	1	1
80°	1	1	1	1	1	1	1	1	1	1	1
82.5°	1	1	1	1	1	1	1	1	1	1	1
85°	0	0	0	1	1	1	1	1	1	1	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242
2.5°	1253	1253	1253	1253	1253	1254	1254	1254	1254	1254	1254
5°	1275	1275	1275	1275	1275	1275	1274	1274	1275	1275	1275
7.5°	1289	1290	1291	1291	1292	1293	1292	1291	1291	1290	1290
10°	1276	1274	1271	1269	1267	1266	1266	1267	1269	1271	1275
12.5°	1217	1216	1217	1219	1222	1221	1218	1216	1216	1212	1203
15°	1061	1058	1057	1058	1061	1066	1074	1075	1075	1075	1076
17.5°	909	904	900	897	897	900	906	912	917	922	925
20°	768	762	759	756	753	751	753	760	770	786	789
22.5°	598	600	603	600	594	589	587	589	592	592	593
25°	407	415	419	419	419	419	420	418	415	411	412
27.5°	262	269	268	267	265	261	266	268	269	268	269
30°	140	150	158	165	172	173	170	164	156	150	161
32.5°	95	96	98	100	101	99	103	104	105	106	106
35°	69	68	69	70	71	71	71	70	70	69	72
37.5°	50	50	49	48	48	48	48	49	50	50	50
40°	34	33	35	35	36	37	36	36	35	34	36
42.5°	27	27	27	27	27	27	27	27	27	27	27
45°	20	21	21	21	21	21	21	21	21	21	21
47.5°	15	16	16	16	16	16	16	16	16	16	16
50°	10	11	11	10	11	11	11	11	11	11	11
52.5°	5	6	6	6	6	6	6	6	6	6	6
55°	3	3	3	3	2	2	2	2	3	2	2
57.5°	3	3	3	2	2	1	0	0	0	0	1
60°	3	2	3	2	1	1	0	0	0	0	0
62.5°	2	2	2	2	1	1	0	0	0	0	0
65°	2	2	2	2	1	0	0	0	0	0	0
67.5°	2	2	2	1	1	0	0	0	0	0	0
70°	2	2	2	1	1	0	0	0	0	0	0
72.5°	1	1	1	1	0	0	0	0	0	0	0
75°	1	1	1	1	0	0	0	0	0	0	0
77.5°	1	1	1	1	0	0	0	0	0	0	0
80°	1	1	1	0	0	0	0	0	0	0	0
82.5°	1	1	1	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242
2.5°	1254	1255	1255	1255	1254	1254	1254	1254	1254	1254	1253
5°	1275	1275	1275	1275	1275	1275	1275	1275	1274	1274	1275
7.5°	1290	1290	1290	1290	1290	1290	1290	1291	1291	1292	1292
10°	1279	1285	1288	1286	1280	1276	1272	1269	1267	1267	1267
12.5°	1197	1194	1192	1193	1197	1202	1210	1217	1217	1219	1222
15°	1076	1072	1069	1071	1075	1076	1075	1075	1074	1074	1068
17.5°	927	927	924	924	925	925	921	917	912	906	900
20°	779	771	767	767	771	779	786	777	764	756	752
22.5°	594	596	598	597	594	592	591	592	593	590	590
25°	415	418	420	419	417	413	410	411	416	421	423
27.5°	270	268	267	267	265	268	268	268	270	271	270
30°	168	169	164	164	164	166	164	157	153	163	168
32.5°	104	103	108	108	104	96	99	103	105	103	101
35°	73	73	72	69	70	70	71	70	69	69	69
37.5°	49	49	49	50	50	50	49	50	50	49	49
40°	36	35	35	35	35	36	36	36	35	34	35
42.5°	26	27	27	26	26	27	27	27	27	27	27
45°	21	21	21	21	21	21	21	21	21	21	21
47.5°	16	16	16	16	16	16	16	16	16	16	16
50°	11	11	11	11	11	11	11	11	11	11	11
52.5°	6	6	6	6	6	6	6	7	7	6	6
55°	2	3	2	2	1	2	2	2	3	2	1
57.5°	1	1	1	0	0	0	0	1	1	0	1
60°	0	0	0	0	0	0	0	1	1	1	2
62.5°	0	0	0	0	0	0	0	1	2	2	2
65°	0	0	0	0	0	0	0	1	2	3	3
67.5°	0	0	0	0	0	0	0	1	2	2	2
70°	0	0	0	0	0	0	1	2	2	2	2
72.5°	0	0	0	0	0	0	1	2	2	2	2
75°	0	0	0	0	0	0	1	1	1	1	1
77.5°	0	0	0	0	0	1	1	1	1	1	1
80°	0	0	0	0	0	1	1	1	1	1	1
82.5°	0	0	0	0	0	1	1	1	1	1	1
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242
2.5°	1253	1253	1252	1253	1253	1252	1252	1252	1251	1251	1251
5°	1275	1275	1275	1275	1275	1274	1274	1274	1274	1273	1274
7.5°	1293	1291	1291	1290	1289	1289	1288	1288	1288	1288	1288
10°	1267	1269	1271	1274	1277	1276	1276	1277	1277	1277	1277
12.5°	1227	1220	1218	1217	1218	1219	1216	1214	1213	1214	1213
15°	1062	1058	1057	1058	1061	1066	1068	1067	1068	1070	1068
17.5°	895	895	898	902	908	916	925	926	927	931	927
20°	752	757	760	763	769	776	785	790	791	795	791
22.5°	596	601	607	604	600	600	602	605	603	606	603
25°	422	420	418	417	408	402	398	398	395	396	395
27.5°	267	265	264	263	260	254	250	249	248	250	248
30°	169	166	158	148	139	129	120	114	115	117	115
32.5°	93	91	91	90	91	91	91	91	92	94	92
35°	69	68	69	69	69	70	70	70	70	71	70
37.5°	47	48	49	50	50	50	50	50	50	50	50
40°	35	36	35	35	33	33	33	33	34	33	34
42.5°	27	26	26	26	26	26	26	26	27	26	27
45°	21	21	21	21	21	21	20	20	21	20	21
47.5°	16	16	16	16	16	16	16	16	16	16	16
50°	10	10	10	10	11	11	11	11	11	11	11
52.5°	5	5	6	7	7	7	7	6	6	6	6
55°	2	3	4	5	5	5	5	5	5	5	5
57.5°	2	2	3	4	4	5	4	4	4	4	5
60°	2	2	2	3	4	4	4	4	4	4	4
62.5°	2	2	2	2	3	4	4	4	4	4	4
65°	2	2	2	2	2	3	4	3	3	3	4
67.5°	2	2	2	1	2	2	3	3	3	3	4
70°	2	2	1	1	1	2	2	3	3	3	3
72.5°	2	2	2	1	1	1	2	2	2	2	3
75°	1	1	1	2	1	1	1	2	2	2	3
77.5°	1	1	1	1	1	1	1	1	2	2	2
80°	1	1	1	1	1	1	1	1	1	1	3
82.5°	1	1	1	1	1	1	1	0	1	1	3
85°	0	0	0	0	0	0	0	1	0	1	8
87.5°	0	0	0	0	0	0	0	0	0	0	53
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0





TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242
2.5°	1252	1252	1252	1253	1253	1252	1253	1253	1253	1254	1254
5°	1274	1274	1274	1275	1275	1275	1275	1275	1275	1274	1274
7.5°	1288	1288	1289	1289	1290	1291	1291	1293	1292	1292	1291
10°	1277	1276	1276	1277	1274	1271	1269	1267	1267	1267	1267
12.5°	1214	1216	1219	1218	1217	1218	1220	1227	1222	1219	1217
15°	1067	1068	1066	1061	1058	1057	1058	1062	1068	1074	1074
17.5°	926	927	916	908	902	898	895	895	900	906	912
20°	790	785	776	769	763	760	757	752	752	756	764
22.5°	605	602	600	600	604	607	601	596	590	590	593
25°	398	398	402	408	417	418	420	422	423	421	416
27.5°	249	250	254	260	263	264	265	267	270	271	270
30°	114	120	129	139	148	158	166	169	168	163	153
32.5°	91	91	91	91	90	91	91	93	101	103	105
35°	70	70	70	69	69	69	68	69	69	69	69
37.5°	50	50	50	50	50	49	48	47	49	49	50
40°	33	33	33	33	35	35	36	35	35	34	35
42.5°	26	26	26	26	26	26	26	27	27	27	27
45°	20	20	21	21	21	21	21	21	21	21	21
47.5°	16	16	16	16	16	16	16	16	16	16	16
50°	11	12	11	11	10	10	10	10	11	11	11
52.5°	7	8	9	11	12	10	5	5	6	8	7
55°	6	7	9	14	19	23	23	15	10	19	21
57.5°	5	6	10	16	26	39	60	66	66	71	83
60°	5	7	11	18	32	56	90	141	172	190	224
62.5°	5	8	13	23	42	73	125	197	283	357	399
65°	5	8	15	29	58	106	177	267	388	527	636
67.5°	5	9	19	42	84	152	246	369	524	694	901
70°	5	11	25	61	123	218	344	511	701	917	1027
72.5°	6	15	39	91	185	313	490	699	888	886	886
75°	7	21	64	148	281	461	687	752	750	749	750
77.5°	9	36	111	243	437	624	619	617	616	617	618
80°	15	72	200	406	493	489	487	486	486	488	490
82.5°	34	154	369	365	362	360	359	360	361	363	365
85°	104	244	239	237	236	236	237	238	239	240	242
87.5°	119	117	117	116	117	117	117	118	119	119	120
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242
2.5°	1254	1254	1254	1254	1255	1255	1255	1254	1254	1254	1254
5°	1275	1275	1275	1275	1275	1275	1275	1275	1275	1275	1275
7.5°	1291	1290	1290	1290	1290	1290	1290	1290	1290	1290	1291
10°	1269	1272	1276	1280	1286	1288	1285	1279	1275	1271	1269
12.5°	1217	1210	1202	1197	1193	1192	1194	1197	1203	1212	1216
15°	1075	1075	1076	1075	1071	1069	1072	1081	1076	1075	1075
17.5°	917	921	925	927	924	924	927	927	925	922	917
20°	777	786	779	771	767	767	771	779	790	786	770
22.5°	592	591	592	594	597	598	596	594	593	592	592
25°	411	410	413	417	419	420	418	415	412	411	415
27.5°	268	268	268	265	267	267	268	270	269	268	269
30°	157	164	166	164	164	164	169	168	161	150	156
32.5°	103	99	96	104	108	108	103	104	106	106	105
35°	70	71	70	70	69	72	73	73	72	70	70
37.5°	50	49	50	50	50	49	49	49	50	50	50
40°	36	36	36	35	35	35	35	36	36	34	35
42.5°	27	27	27	26	26	27	27	26	27	27	27
45°	21	21	21	21	21	21	21	21	21	21	21
47.5°	16	16	16	16	16	16	16	16	16	16	16
50°	11	11	11	11	11	11	11	11	11	11	11
52.5°	7	6	6	6	6	6	6	6	6	6	6
55°	2	2	2	1	2	2	3	2	2	2	3
57.5°	66	0	0	22	0	1	2	1	1	0	0
60°	210	172	149	133	62	29	17	0	0	0	0
62.5°	472	454	435	396	267	70	36	4	0	0	0
65°	720	796	780	637	393	151	47	16	0	0	0
67.5°	1017	973	827	653	462	231	54	24	0	0	0
70°	1003	905	813	647	495	283	80	30	4	0	0
72.5°	888	826	743	621	479	310	125	33	10	0	0
75°	753	734	659	574	447	314	148	33	13	0	0
77.5°	621	625	565	506	398	296	154	31	14	0	0
80°	493	496	463	414	336	253	143	34	13	0	0
82.5°	367	370	354	316	263	198	119	36	11	1	0
85°	243	245	239	213	180	137	85	29	8	1	0
87.5°	121	122	121	107	92	70	44	16	4	1	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242	1242
2.5°	1254	1254	1253	1253	1253	1252	1253	1253	1252	1252	1252
5°	1274	1274	1275	1275	1275	1275	1275	1275	1274	1274	1274
7.5°	1291	1292	1292	1292	1291	1291	1290	1289	1289	1288	1288
10°	1267	1266	1266	1267	1269	1271	1274	1276	1276	1276	1276
12.5°	1216	1218	1221	1227	1219	1217	1216	1217	1218	1215	1213
15°	1075	1074	1066	1061	1058	1057	1058	1061	1066	1067	1067
17.5°	912	906	900	897	897	900	904	909	917	925	925
20°	760	753	751	753	756	759	762	768	776	785	789
22.5°	589	587	589	594	600	603	600	598	599	602	604
25°	418	420	419	419	419	419	415	407	402	399	398
27.5°	268	266	264	265	267	268	269	262	256	252	250
30°	164	170	173	172	165	158	150	140	129	121	114
32.5°	104	103	99	101	100	98	96	95	94	93	92
35°	70	71	71	71	70	69	68	69	70	69	70
37.5°	49	48	48	48	48	49	50	50	50	50	50
40°	36	36	37	36	35	35	34	34	34	34	34
42.5°	27	27	27	27	27	27	27	27	27	26	26
45°	21	21	21	21	21	21	21	20	20	20	20
47.5°	16	16	16	16	16	16	16	15	15	15	15
50°	11	11	11	11	11	11	11	10	10	10	11
52.5°	6	6	6	6	6	6	6	5	5	5	6
55°	2	2	2	2	3	3	3	3	4	4	4
57.5°	0	0	1	2	2	3	3	3	3	4	4
60°	0	0	1	1	2	3	2	3	3	3	4
62.5°	0	0	1	1	2	2	2	2	3	3	3
65°	0	0	0	1	2	2	2	2	2	3	3
67.5°	0	0	0	1	1	2	2	2	2	2	3
70°	0	0	0	1	1	2	2	2	2	2	2
72.5°	0	0	0	0	1	1	1	1	2	2	2
75°	0	0	0	0	1	1	1	1	1	2	2
77.5°	0	0	0	0	1	1	1	1	1	1	2
80°	0	0	0	0	0	1	1	1	1	1	1
82.5°	0	0	0	0	0	1	1	1	1	1	1
85°	0	0	0	0	0	0	0	0	0	1	1
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395205  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	1242	1242
2.5°	1251	1251
5°	1274	1273
7.5°	1288	1288
10°	1277	1277
12.5°	1213	1214
15°	1068	1070
17.5°	927	931
20°	791	795
22.5°	603	606
25°	395	396
27.5°	249	250
30°	116	117
32.5°	93	94
35°	70	71
37.5°	50	50
40°	34	33
42.5°	26	26
45°	21	20
47.5°	16	16
50°	11	11
52.5°	6	6
55°	5	5
57.5°	4	4
60°	4	4
62.5°	4	4
65°	3	3
67.5°	3	3
70°	3	3
72.5°	2	2
75°	2	2
77.5°	2	2
80°	1	1
82.5°	1	1
85°	1	1
87.5°	0	0
90°	0	0
92.5°	0	0
95°	0	0
97.5°	0	0
100°	0	0
102.5°	0	0
105°	0	0
107.5°	0	0
110°	0	0





TEST NUMBER: E395205  
CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0	0
115°	0	0
117.5°	0	0
120°	0	0
122.5°	0	0
125°	0	0
127.5°	0	0
130°	0	0
132.5°	0	0
135°	0	0
137.5°	0	0
140°	0	0
142.5°	0	0
145°	0	0
147.5°	0	0
150°	0	0
152.5°	0	0
155°	0	0
157.5°	0	0
160°	0	0
162.5°	0	0
165°	0	0
167.5°	0	0
170°	0	0
172.5°	0	0
175°	0	0
177.5°	0	0
180°	0	0

(END OF REPORT)