

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: E395204

Luminaire Tested: **H7-1410**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: E395204  
Test Lab:  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO  
Catalog Number: H7-1410  
Description: HALO RECESSED INC - LV ADJ, 8" SPOT  
Light Source: 50MR16NSP, 900 LUMENS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: 900 (1 lamp)  
Luminaire Lumens: 691.5 lumens  
Efficiency: 76.8%  
Efficacy: 11.5 lumens/watt  
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.24  
Luminous Opening: (L: 0 ' x W: -0.15 ' x H: 0 '  
CIE Type: Direct

Input Watts (W): 60  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: E395204  
CATALOG NUMBER: H7-1410

### Luminous Intensity Polar Plot



0% Up  
100% Dn

— 0°-180°    - - 45°-225°    - - - 90°-270°    - · - 135°-315°



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	91	91	91	91	89	89	89	89	85	85	85	82	82	82	78	78	78	77
1	89	87	86	85	87	86	85	84	83	82	81	80	79	79	77	77	76	75
2	86	84	82	80	85	83	81	79	80	79	78	78	77	76	76	75	75	73
3	84	81	79	77	83	80	78	76	78	77	75	77	75	74	75	74	73	72
4	82	79	76	74	81	78	76	74	76	74	73	75	73	72	74	72	71	70
5	80	77	74	72	79	76	73	72	75	73	71	74	72	70	73	71	70	69
6	79	75	72	70	78	74	72	70	73	71	69	72	70	69	71	70	69	68
7	77	73	70	68	76	73	70	68	72	70	68	71	69	68	70	69	67	67
8	76	71	69	67	75	71	69	67	70	68	67	70	68	66	69	68	66	66
9	74	70	68	66	74	70	67	66	69	67	66	69	67	65	68	66	65	65
10	73	69	66	65	72	69	66	65	68	66	64	68	66	64	67	65	64	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	Luminous shape not found,			
5°	reference photometric report, or contact			
10°	the photometric lab for calculations.			
15°				
20°				
25°				
30°				
35°				
40°				
45°				
50°				
55°				
60°				
65°				
70°				
75°				
80°				
85°				



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**ZONAL LUMENS:**

Zone	Lumens	% Fixture	% Lamp
0°-10°	413.9	59.9	46.0
10°-20°	182.4	26.4	20.3
20°-30°	59.8	8.7	6.6
30°-40°	27.9	4.0	3.1
40°-50°	5.4	0.8	0.6
50°-60°	1.0	0.1	0.1
60°-70°	0.6	0.1	0.1
70°-80°	0.3	0.0	0.0
80°-90°	0.1	0.0	0.0
90°-100°	0.0	0.0	0.0
100°-110°	0.0	0.0	0.0
110°-120°	0.0	0.0	0.0
120°-130°	0.0	0.0	0.0
130°-140°	0.0	0.0	0.0
140°-150°	0.0	0.0	0.0
150°-160°	0.0	0.0	0.0
160°-170°	0.0	0.0	0.0
170°-180°	0.0	0.0	0.0
0°-30°	656.2	94.9	72.9
0°-40°	684.1	98.9	76.0
0°-60°	690.5	99.9	76.7
0°-90°	691.5	100.0	76.8
90°-120°	0.0	0.0	0.0
90°-150°	0.0	0.0	0.0
90°-180°	0.0	0.0	0.0
0°-180°	691.5	100.0	76.8

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	7994	7994	7994	7994	7994	
5°	5661	5661	5661	5661	5661	423
15°	531	531	531	531	531	184
25°	124	124	124	124	124	60
35°	41	41	41	41	41	28
45°	6	6	6	6	6	7
55°	5	5	5	5	5	4
65°	3	3	3	3	3	3
75°	2	2	2	2	2	2
85°	1	1	1	1	1	1
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994
2.5°	7401	7390	7383	7379	7378	7381	7388	7398	7411	7428	7448
5°	5661	5631	5608	5591	5582	5580	5585	5597	5617	5646	5592
7.5°	3745	3714	3693	3682	3682	3692	3715	3657	3616	3581	3551
10°	1966	1947	1935	1929	1929	1910	1879	1866	1855	1876	1897
12.5°	1007	1001	1002	1012	1017	1014	1015	1019	1024	1030	1036
15°	531	528	528	530	522	515	510	506	502	499	493
17.5°	307	305	305	303	300	298	303	310	315	316	317
20°	206	206	207	207	207	209	210	212	211	209	207
22.5°	151	151	152	151	150	150	150	149	148	148	150
25°	124	124	124	124	124	125	125	126	127	127	127
27.5°	108	108	108	108	107	107	107	106	107	107	107
30°	84	84	84	84	85	85	85	86	86	84	83
32.5°	56	55	55	55	56	56	57	59	60	60	60
35°	41	41	41	41	42	41	41	41	41	41	41
37.5°	30	30	30	30	30	30	31	31	31	31	31
40°	22	22	22	22	22	21	21	21	21	21	21
42.5°	11	11	11	11	11	11	11	12	12	12	11
45°	6	6	5	4	4	3	3	3	4	4	4
47.5°	6	6	5	4	3	3	3	3	2	1	1
50°	5	5	4	3	3	3	3	3	2	1	0
52.5°	5	5	4	3	3	2	2	2	1	1	0
55°	5	4	4	3	3	2	2	2	1	1	0
57.5°	4	4	3	3	2	2	2	2	1	0	0
60°	4	4	3	2	2	2	2	1	1	0	0
62.5°	4	3	3	2	2	2	2	1	1	0	0
65°	3	3	3	2	2	2	2	1	0	0	0
67.5°	3	3	2	2	2	1	1	1	0	0	0
70°	3	2	2	2	1	1	1	1	0	0	0
72.5°	2	2	2	1	1	1	1	0	0	0	0
75°	2	2	1	1	1	1	1	0	0	0	0
77.5°	2	2	1	1	1	1	1	0	0	0	0
80°	1	1	1	1	1	1	0	0	0	0	0
82.5°	1	1	1	1	0	0	0	0	0	0	0
85°	1	1	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994
2.5°	7472	7499	7530	7564	7661	7652	7650	7649	7650	7652	7661
5°	5550	5514	5484	5460	5441	5427	5419	5416	5419	5427	5440
7.5°	3524	3501	3479	3460	3443	3455	3418	3416	3418	3444	3441
10°	1917	1934	1948	1962	1966	1972	1975	1976	1975	1971	1965
12.5°	1044	1034	1024	1009	990	965	962	968	964	962	982
15°	490	505	523	531	528	522	522	523	522	518	522
17.5°	318	317	315	315	314	312	314	318	316	310	311
20°	204	201	200	206	210	211	210	211	210	209	210
22.5°	153	154	155	155	153	153	153	155	155	152	152
25°	126	126	126	126	127	128	127	126	126	127	127
27.5°	109	109	107	106	106	107	108	107	107	107	106
30°	84	83	84	84	84	83	83	84	84	84	83
32.5°	60	59	58	59	60	60	59	60	60	59	59
35°	41	42	42	42	41	41	42	42	41	42	42
37.5°	30	30	30	30	30	30	30	30	31	31	30
40°	22	22	21	21	21	21	21	21	22	22	21
42.5°	11	12	12	12	12	12	12	12	12	12	12
45°	4	4	3	3	4	4	4	4	4	3	4
47.5°	0	0	1	0	0	0	1	1	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0





TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994
2.5°	7564	7530	7499	7472	7448	7428	7411	7398	7388	7381	7378
5°	5459	5483	5513	5549	5591	5648	5618	5598	5586	5580	5582
7.5°	3459	3478	3499	3522	3549	3579	3614	3655	3719	3693	3683
10°	1978	1948	1935	1917	1898	1877	1856	1858	1876	1908	1929
12.5°	1002	1017	1028	1034	1032	1027	1022	1017	1013	1012	1016
15°	528	523	508	482	485	491	496	501	506	512	519
17.5°	312	312	314	315	315	315	313	310	304	298	299
20°	207	203	199	201	204	207	209	210	210	208	207
22.5°	152	153	154	153	151	148	147	148	149	150	150
25°	126	124	125	125	125	126	126	126	125	125	124
27.5°	106	106	107	108	108	107	107	107	107	107	107
30°	84	85	85	84	85	85	86	88	87	86	85
32.5°	60	60	60	59	60	61	61	60	59	57	55
35°	41	41	42	42	41	40	40	40	40	40	40
37.5°	30	30	31	30	30	30	30	30	30	30	30
40°	21	21	21	21	21	22	21	21	21	21	21
42.5°	12	11	11	12	12	12	11	12	12	12	12
45°	4	3	4	4	4	5	5	4	4	3	4
47.5°	0	1	0	1	1	1	0	1	1	2	3
50°	0	0	0	0	0	0	0	0	1	2	3
52.5°	0	0	0	0	0	0	0	0	1	1	2
55°	0	0	0	0	0	0	0	0	0	1	1
57.5°	0	0	0	0	0	0	0	0	0	0	1
60°	0	0	0	0	0	0	0	0	0	0	1
62.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994
2.5°	7379	7383	7390	7401	7390	7383	7379	7378	7381	7388	7398
5°	5592	5608	5631	5661	5631	5608	5592	5582	5580	5586	5598
7.5°	3683	3693	3713	3745	3713	3693	3683	3683	3693	3701	3655
10°	1929	1934	1947	1966	1947	1934	1929	1929	1908	1876	1858
12.5°	1013	1002	1000	1007	1000	1002	1013	1016	1012	1013	1017
15°	528	528	528	531	528	528	528	519	512	506	501
17.5°	303	305	305	307	305	305	303	299	298	304	310
20°	207	207	206	206	206	207	207	207	208	210	210
22.5°	151	152	151	151	151	152	151	150	150	149	148
25°	124	124	124	124	124	124	124	124	125	125	126
27.5°	107	108	108	108	108	108	107	107	107	107	107
30°	84	84	84	84	84	84	84	85	86	87	88
32.5°	54	55	55	56	55	55	54	55	57	59	60
35°	40	40	41	41	41	40	40	40	40	40	40
37.5°	30	30	30	30	30	30	30	30	30	30	30
40°	22	22	22	22	22	22	22	21	21	21	21
42.5°	11	11	11	11	11	11	11	12	12	12	12
45°	4	5	6	6	6	5	4	4	3	4	4
47.5°	4	5	5	6	5	5	4	3	2	1	1
50°	4	4	5	5	5	4	4	3	2	1	0
52.5°	3	4	5	5	5	4	3	2	1	1	0
55°	3	4	4	5	4	4	3	1	1	0	0
57.5°	2	3	4	4	4	3	2	1	0	0	0
60°	2	3	3	4	3	3	2	1	0	0	0
62.5°	1	2	3	4	3	2	1	0	0	0	0
65°	1	2	3	3	3	2	1	0	0	0	0
67.5°	0	1	2	3	2	1	0	0	0	0	0
70°	0	1	2	3	2	1	0	0	0	0	0
72.5°	0	1	2	2	2	1	0	0	0	0	0
75°	0	0	1	2	1	0	0	0	0	0	0
77.5°	0	0	1	2	1	0	0	0	0	0	0
80°	0	0	0	1	0	0	0	0	0	0	0
82.5°	0	0	0	1	0	0	0	0	0	0	0
85°	0	0	0	1	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994
2.5°	7411	7428	7448	7472	7499	7530	7564	7661	7652	7650	7649
5°	5618	5638	5591	5549	5513	5483	5459	5440	5427	5419	5416
7.5°	3614	3579	3549	3522	3499	3478	3459	3441	3444	3418	3416
10°	1856	1877	1898	1917	1935	1948	1958	1965	1971	1975	1976
12.5°	1022	1027	1032	1034	1028	1017	1002	982	962	964	968
15°	496	491	485	482	508	523	528	522	518	522	523
17.5°	313	315	315	315	314	312	312	311	310	316	318
20°	209	207	204	200	199	203	207	210	209	210	211
22.5°	147	148	151	153	154	153	152	152	152	155	155
25°	126	126	125	125	125	124	126	127	127	126	126
27.5°	107	107	108	108	107	106	106	106	107	107	107
30°	86	85	85	84	85	85	84	83	84	84	84
32.5°	61	61	60	59	60	60	60	59	59	60	60
35°	40	40	41	42	42	41	41	42	42	41	42
37.5°	30	30	30	30	30	30	30	30	31	31	30
40°	21	22	21	21	21	21	21	21	22	22	21
42.5°	11	12	12	12	11	11	12	12	12	12	12
45°	5	5	4	4	4	3	4	4	3	4	4
47.5°	0	1	1	1	0	1	0	0	0	0	1
50°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994
2.5°	7644	7641	7601	7564	7530	7499	7472	7448	7428	7411	7398
5°	5419	5427	5441	5460	5484	5514	5550	5592	5646	5617	5597
7.5°	3418	3426	3443	3460	3479	3501	3524	3551	3581	3616	3657
10°	1975	1972	1966	1962	1948	1934	1917	1897	1876	1798	1851
12.5°	962	965	990	1009	1024	1034	1044	1036	1030	1024	1019
15°	522	522	528	531	523	505	486	493	499	502	506
17.5°	314	312	314	315	315	317	318	317	316	315	310
20°	210	211	210	206	199	201	204	207	209	211	212
22.5°	153	153	153	155	155	154	153	150	147	148	149
25°	127	128	127	126	126	126	126	127	127	127	126
27.5°	107	107	106	106	107	109	108	107	107	107	106
30°	83	83	83	84	84	83	84	83	84	86	86
32.5°	59	60	60	59	58	59	60	60	60	60	59
35°	42	41	41	42	42	42	41	40	41	41	41
37.5°	30	30	30	30	30	30	30	31	31	31	31
40°	21	21	21	21	21	21	22	21	21	21	21
42.5°	12	12	12	12	12	12	11	11	12	12	12
45°	4	4	4	3	3	4	4	4	4	4	3
47.5°	1	0	0	0	1	0	0	1	1	2	3
50°	0	0	0	0	0	0	0	0	1	2	3
52.5°	0	0	0	0	0	0	0	0	1	1	2
55°	0	0	0	0	0	0	0	0	1	1	2
57.5°	0	0	0	0	0	0	0	0	0	1	2
60°	0	0	0	0	0	0	0	0	0	1	1
62.5°	0	0	0	0	0	0	0	0	0	1	1
65°	0	0	0	0	0	0	0	0	0	0	1
67.5°	0	0	0	0	0	0	0	0	0	0	1
70°	0	0	0	0	0	0	0	0	0	0	1
72.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0





TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994
2.5°	7388	7381	7378	7379	7383	7390	7401	7390	7383	7379	7378
5°	5585	5580	5582	5591	5608	5631	5661	5631	5608	5591	5582
7.5°	3715	3692	3682	3682	3693	3714	3745	3714	3693	3682	3682
10°	1879	1910	1929	1929	1935	1947	1966	1947	1935	1929	1929
12.5°	1015	1014	1017	1012	1002	1001	1007	1001	1002	1012	1017
15°	510	515	522	530	528	528	531	528	528	530	522
17.5°	303	298	300	303	305	305	307	305	305	303	300
20°	210	209	207	207	207	206	206	206	207	207	207
22.5°	150	150	150	151	152	151	151	151	152	151	150
25°	125	125	124	124	124	124	124	124	124	124	124
27.5°	107	107	107	108	108	108	108	108	108	108	107
30°	85	85	85	84	84	84	84	84	84	84	85
32.5°	57	56	56	54	55	55	56	55	55	54	56
35°	41	41	42	41	41	41	41	41	41	41	42
37.5°	31	30	30	30	30	30	30	30	30	30	30
40°	21	21	22	22	22	22	22	22	22	22	22
42.5°	11	11	11	11	11	11	11	11	11	11	11
45°	3	3	4	4	5	6	6	6	5	4	4
47.5°	3	3	3	4	5	6	6	6	5	4	3
50°	3	3	3	3	4	5	5	5	4	3	3
52.5°	2	2	3	3	4	5	5	5	4	3	3
55°	2	2	3	3	4	4	5	4	4	3	3
57.5°	2	2	2	3	3	4	4	4	3	3	2
60°	2	2	2	2	3	4	4	4	3	2	2
62.5°	2	2	2	2	3	3	4	3	3	2	2
65°	2	2	2	2	3	3	3	3	3	2	2
67.5°	1	1	2	2	2	3	3	3	2	2	2
70°	1	1	1	2	2	2	3	2	2	2	1
72.5°	1	1	1	1	2	2	2	2	2	1	1
75°	1	1	1	1	1	2	2	2	1	1	1
77.5°	1	1	1	1	1	2	2	2	1	1	1
80°	0	1	1	1	1	1	1	1	1	1	1
82.5°	0	0	0	1	1	1	1	1	1	1	0
85°	0	0	0	0	0	1	1	1	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994
2.5°	7381	7388	7398	7411	7428	7448	7472	7499	7530	7564	7601
5°	5580	5585	5597	5617	5646	5592	5550	5514	5484	5460	5441
7.5°	3692	3715	3657	3616	3581	3551	3524	3501	3479	3460	3443
10°	1910	1879	1851	1798	1876	1897	1917	1934	1948	1962	1966
12.5°	1014	1015	1019	1024	1030	1036	1044	1034	1024	1009	990
15°	515	510	506	502	499	493	486	505	523	531	528
17.5°	298	303	310	315	316	317	318	317	315	315	314
20°	209	210	212	211	209	207	204	201	199	206	210
22.5°	150	150	149	148	147	150	153	154	155	155	153
25°	125	125	126	127	127	127	126	126	126	126	127
27.5°	107	107	106	107	107	107	108	109	107	106	106
30°	85	85	86	86	84	83	84	83	84	84	83
32.5°	56	57	59	60	60	60	60	59	58	59	60
35°	41	41	41	41	41	40	41	42	42	42	41
37.5°	30	31	31	31	31	31	30	30	30	30	30
40°	21	21	21	21	21	21	22	21	21	21	21
42.5°	11	11	12	12	12	11	11	12	12	12	12
45°	3	3	3	4	4	4	4	4	3	3	4
47.5°	3	3	3	2	1	1	0	0	1	0	0
50°	3	3	3	2	1	0	0	0	0	0	0
52.5°	2	2	2	1	1	0	0	0	0	0	0
55°	2	2	2	1	1	0	0	0	0	0	0
57.5°	2	2	2	1	0	0	0	0	0	0	0
60°	2	2	1	1	0	0	0	0	0	0	0
62.5°	2	2	1	1	0	0	0	0	0	0	0
65°	2	2	1	0	0	0	0	0	0	0	0
67.5°	1	1	1	0	0	0	0	0	0	0	0
70°	1	1	1	0	0	0	0	0	0	0	0
72.5°	1	1	0	0	0	0	0	0	0	0	0
75°	1	1	0	0	0	0	0	0	0	0	0
77.5°	1	1	0	0	0	0	0	0	0	0	0
80°	1	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994
2.5°	7641	7644	7649	7650	7652	7661	7564	7530	7499	7472	7448
5°	5427	5419	5416	5419	5427	5440	5459	5483	5513	5549	5591
7.5°	3426	3418	3416	3418	3444	3441	3459	3478	3499	3522	3549
10°	1972	1975	1976	1975	1971	1965	1958	1948	1935	1917	1898
12.5°	965	962	968	964	962	982	1002	1017	1028	1034	1032
15°	522	522	523	522	518	522	528	523	508	482	485
17.5°	312	314	318	316	310	311	312	312	314	315	315
20°	211	210	211	210	209	210	207	203	199	200	204
22.5°	153	153	155	155	152	152	152	153	154	153	151
25°	128	127	126	126	127	127	126	124	125	125	125
27.5°	107	107	107	107	107	106	106	106	107	108	108
30°	83	83	84	84	84	83	84	85	85	84	85
32.5°	60	59	60	60	59	59	60	60	60	59	60
35°	41	42	42	41	42	42	41	41	42	42	41
37.5°	30	30	30	31	31	30	30	30	30	30	30
40°	21	21	21	22	22	21	21	21	21	21	21
42.5°	12	12	12	12	12	12	12	11	11	12	12
45°	4	4	4	4	3	4	4	3	4	4	4
47.5°	0	1	1	0	0	0	0	1	0	1	1
50°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994
2.5°	7428	7411	7398	7388	7381	7378	7379	7383	7390	7401	7390
5°	5638	5618	5598	5586	5580	5582	5592	5608	5631	5661	5631
7.5°	3579	3614	3655	3701	3693	3683	3683	3693	3713	3745	3713
10°	1877	1856	1858	1876	1908	1929	1929	1934	1947	1966	1947
12.5°	1027	1022	1017	1013	1012	1016	1013	1002	1000	1007	1000
15°	491	496	501	506	512	519	528	528	528	531	528
17.5°	315	313	310	304	298	299	303	305	305	307	305
20°	207	209	210	210	208	207	207	207	206	206	206
22.5°	148	147	148	149	150	150	151	152	151	151	151
25°	126	126	126	125	125	124	124	124	124	124	124
27.5°	107	107	107	107	107	107	107	108	108	108	108
30°	85	86	88	87	86	85	84	84	84	84	84
32.5°	61	61	60	59	57	55	54	55	55	56	55
35°	40	40	40	40	40	40	40	40	41	41	41
37.5°	30	30	30	30	30	30	30	30	30	30	30
40°	22	21	21	21	21	21	22	22	22	22	22
42.5°	12	11	12	12	12	12	11	11	11	11	11
45°	5	5	4	4	3	4	4	5	6	6	6
47.5°	1	0	1	1	2	3	4	5	5	6	5
50°	0	0	0	1	2	3	4	4	5	5	5
52.5°	0	0	0	1	1	2	3	4	5	5	5
55°	0	0	0	0	1	1	3	4	4	5	4
57.5°	0	0	0	0	0	1	2	3	4	4	4
60°	0	0	0	0	0	1	2	3	3	4	3
62.5°	0	0	0	0	0	0	1	2	3	4	3
65°	0	0	0	0	0	0	1	2	3	3	3
67.5°	0	0	0	0	0	0	0	1	2	3	2
70°	0	0	0	0	0	0	0	1	2	3	2
72.5°	0	0	0	0	0	0	0	1	2	2	2
75°	0	0	0	0	0	0	0	0	1	2	1
77.5°	0	0	0	0	0	0	0	0	1	2	1
80°	0	0	0	0	0	0	0	0	0	1	0
82.5°	0	0	0	0	0	0	0	0	0	1	0
85°	0	0	0	0	0	0	0	0	0	1	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0





TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994
2.5°	7383	7379	7378	7381	7388	7398	7411	7428	7448	7472	7499
5°	5608	5592	5582	5580	5586	5598	5618	5648	5591	5549	5513
7.5°	3693	3683	3683	3693	3719	3655	3614	3579	3549	3522	3499
10°	1934	1929	1929	1908	1876	1858	1856	1877	1898	1917	1935
12.5°	1002	1013	1016	1012	1013	1017	1022	1027	1032	1034	1028
15°	528	528	519	512	506	501	496	491	485	482	508
17.5°	305	303	299	298	304	310	313	315	315	315	314
20°	207	207	207	208	210	210	209	207	204	201	199
22.5°	152	151	150	150	149	148	147	148	151	153	154
25°	124	124	124	125	125	126	126	126	125	125	125
27.5°	108	107	107	107	107	107	107	107	108	108	107
30°	84	84	85	86	87	88	86	85	85	84	85
32.5°	55	54	55	57	59	60	61	61	60	59	60
35°	40	40	40	40	40	40	40	40	41	42	42
37.5°	30	30	30	30	30	30	30	30	30	30	31
40°	22	22	21	21	21	21	21	22	21	21	21
42.5°	11	11	12	12	12	12	11	12	12	12	11
45°	5	4	4	3	4	4	5	5	4	4	4
47.5°	5	4	3	2	1	1	0	1	1	1	0
50°	4	4	3	2	1	0	0	0	0	0	0
52.5°	4	3	2	1	1	0	0	0	0	0	0
55°	4	3	1	1	0	0	0	0	0	0	0
57.5°	3	2	1	0	0	0	0	0	0	0	0
60°	3	2	1	0	0	0	0	0	0	0	0
62.5°	2	1	0	0	0	0	0	0	0	0	0
65°	2	1	0	0	0	0	0	0	0	0	0
67.5°	1	0	0	0	0	0	0	0	0	0	0
70°	1	0	0	0	0	0	0	0	0	0	0
72.5°	1	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994
2.5°	7530	7564	7661	7652	7650	7649	7650	7652	7661	7564	7530
5°	5483	5459	5440	5427	5419	5416	5419	5427	5441	5460	5484
7.5°	3478	3459	3441	3444	3418	3416	3418	3455	3443	3460	3479
10°	1948	1978	1965	1971	1975	1976	1975	1972	1966	1962	1948
12.5°	1017	1002	982	962	964	968	962	965	990	1009	1024
15°	523	528	522	518	522	523	522	522	528	531	523
17.5°	312	312	311	310	316	318	314	312	314	315	315
20°	203	207	210	209	210	211	210	211	210	206	200
22.5°	153	152	152	152	155	155	153	153	153	155	155
25°	124	126	127	127	126	126	127	128	127	126	126
27.5°	106	106	106	107	107	107	108	107	106	106	107
30°	85	84	83	84	84	84	83	83	84	84	84
32.5°	60	60	59	59	60	60	59	60	60	59	58
35°	41	41	42	42	41	42	42	41	41	42	42
37.5°	30	30	30	31	31	30	30	30	30	30	30
40°	21	21	21	22	22	21	21	21	21	21	21
42.5°	11	12	12	12	12	12	12	12	12	12	12
45°	3	4	4	3	4	4	4	4	4	3	3
47.5°	1	0	0	0	0	1	1	0	0	0	1
50°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994	7994
2.5°	7499	7472	7448	7428	7411	7398	7388	7381	7378	7379	7383
5°	5514	5550	5592	5646	5617	5597	5585	5580	5582	5591	5608
7.5°	3501	3524	3551	3581	3616	3657	3715	3692	3682	3682	3693
10°	1934	1917	1897	1876	1855	1866	1879	1910	1929	1929	1935
12.5°	1034	1044	1036	1030	1024	1019	1015	1014	1017	1012	1002
15°	505	490	493	499	502	506	510	515	522	530	528
17.5°	317	318	317	316	315	310	303	298	300	303	305
20°	201	204	207	209	211	212	210	209	207	207	207
22.5°	154	153	150	148	148	149	150	150	150	151	152
25°	126	126	127	127	127	126	125	125	124	124	124
27.5°	109	109	107	107	107	106	107	107	107	108	108
30°	83	84	83	84	86	86	85	85	85	84	84
32.5°	59	60	60	60	60	59	57	56	56	55	55
35°	42	41	41	41	41	41	41	41	42	41	41
37.5°	30	30	31	31	31	31	31	30	30	30	30
40°	22	22	21	21	21	21	21	21	22	22	22
42.5°	12	11	11	12	12	12	11	11	11	11	11
45°	4	4	4	4	4	3	3	3	4	4	5
47.5°	0	0	1	1	2	3	3	3	3	4	5
50°	0	0	0	1	2	3	3	3	3	3	4
52.5°	0	0	0	1	1	2	2	2	3	3	4
55°	0	0	0	1	1	2	2	2	3	3	4
57.5°	0	0	0	0	1	2	2	2	2	3	3
60°	0	0	0	0	1	1	2	2	2	2	3
62.5°	0	0	0	0	1	1	2	2	2	2	3
65°	0	0	0	0	0	1	2	2	2	2	3
67.5°	0	0	0	0	0	1	1	1	2	2	2
70°	0	0	0	0	0	1	1	1	1	2	2
72.5°	0	0	0	0	0	0	1	1	1	1	2
75°	0	0	0	0	0	0	1	1	1	1	1
77.5°	0	0	0	0	0	0	1	1	1	1	1
80°	0	0	0	0	0	0	0	1	1	1	1
82.5°	0	0	0	0	0	0	0	0	0	1	1
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
 CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395204  
CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	7994	7994
2.5°	7390	7401
5°	5631	5661
7.5°	3714	3745
10°	1947	1966
12.5°	1001	1007
15°	528	531
17.5°	305	307
20°	206	206
22.5°	151	151
25°	124	124
27.5°	108	108
30°	84	84
32.5°	55	56
35°	41	41
37.5°	30	30
40°	22	22
42.5°	11	11
45°	6	6
47.5°	6	6
50°	5	5
52.5°	5	5
55°	4	5
57.5°	4	4
60°	4	4
62.5°	3	4
65°	3	3
67.5°	3	3
70°	2	3
72.5°	2	2
75°	2	2
77.5°	2	2
80°	1	1
82.5°	1	1
85°	1	1
87.5°	0	0
90°	0	0
92.5°	0	0
95°	0	0
97.5°	0	0
100°	0	0
102.5°	0	0
105°	0	0
107.5°	0	0
110°	0	0





TEST NUMBER: E395204  
CATALOG NUMBER: H7-1410

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	0	0
115°	0	0
117.5°	0	0
120°	0	0
122.5°	0	0
125°	0	0
127.5°	0	0
130°	0	0
132.5°	0	0
135°	0	0
137.5°	0	0
140°	0	0
142.5°	0	0
145°	0	0
147.5°	0	0
150°	0	0
152.5°	0	0
155°	0	0
157.5°	0	0
160°	0	0
162.5°	0	0
165°	0	0
167.5°	0	0
170°	0	0
172.5°	0	0
175°	0	0
177.5°	0	0
180°	0	0

(END OF REPORT)