

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P991385

Luminaire Tested: **SMD6R07FS5-935**

Issue Date: 05/20/2025



Test Information

Test Method: LM-79-08
Report Number: P991385
Test Lab: THIRD PARTY NVLAP
Issue Date: 05/20/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: SMD6R07FS5-935
Description: HALO SURFACE MOUNT 6 inch 90 CRI COLOR SELECTABLE Round FIXTURE
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 790.0 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P991385
CATALOG NUMBER: SMD6R07FS5-935

Luminous Intensity Polar Plot



TEST NUMBER: P991385

CATALOG NUMBER: SMD6R07FS5-935

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	99	95	106	101	97	94	97	94	91		93	90	88		90
2	99	90	83	77	96	88	82	76	85	79	75		81	77	73		78
3	90	79	71	64	87	77	70	63	74	68	62		72	66	61		69
4	82	70	61	54	80	69	60	54	66	59	53		64	57	52		61
5	75	62	53	47	73	61	53	46	59	52	46		57	50	45		55
6	70	56	47	41	68	55	47	40	53	46	40		52	45	40		50
7	65	51	42	36	63	50	42	36	48	41	35		47	40	35		46
8	60	46	38	32	58	46	37	32	44	37	32		43	36	31		42
9	56	43	34	29	55	42	34	29	41	34	28		40	33	28		39
10	53	39	31	26	51	39	31	26	38	31	26		37	30	26		36

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15010	15010	15010	15010
5°	15018	14979	14990	14974
10°	14974	14935	14946	14952
15°	14921	14881	14887	14892
20°	14859	14795	14806	14830
25°	14723	14717	14704	14717
30°	14604	14610	14604	14610
35°	14496	14455	14475	14482
40°	14327	14313	14305	14313
45°	14149	14118	14125	14125
50°	13953	13936	13901	13936
55°	13696	13677	13686	13677
60°	13343	13354	13299	13365
65°	12855	12972	12894	13010
70°	12182	12518	12246	12534
75°	11268	11925	11395	11946
80°	9976	11144	10165	11207
85°	7359	10064	7799	10190



TEST NUMBER: P991385
 CATALOG NUMBER: SMD6R07FS5-935

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.9	3.3
10°-20°	74.1	9.4
20°-30°	112.2	14.2
30°-40°	135.4	17.1
40°-50°	140.7	17.8
50°-60°	127.9	16.2
60°-70°	98.7	12.5
70°-80°	58.4	7.4
80°-90°	16.3	2.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.1	0.0
130°-140°	0.1	0.0
140°-150°	0.1	0.0
150°-160°	0.1	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-30°	212.2	26.9
0°-40°	347.6	44.0
0°-60°	616.2	78.0
0°-90°	789.7	100.0
90°-120°	0.1	0.0
90°-150°	0.2	0.0
90°-180°	0.0	0.0
0°-180°	790.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	274	274	274	274	274	
5°	273	272	272	272	273	26
15°	263	262	262	262	263	74
25°	243	243	243	243	243	112
35°	217	216	216	216	217	135
45°	182	182	182	182	182	141
55°	143	143	143	143	143	128
65°	99	100	99	100	99	98
75°	53	56	54	56	53	56
85°	12	16	12	16	12	14
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	



TEST NUMBER: P991385

CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	273.8	273.8	273.8	273.8	273.8	273.8	273.8	273.8	273.8	273.8	273.8
0.5°	274.0	274.1	273.7	273.7	273.8	273.4	273.9	273.7	273.6	274.1	273.6
1°	274.0	274.1	273.7	273.7	273.7	273.5	273.9	273.7	273.5	274.1	273.5
1.5°	274.0	274.1	273.6	273.7	273.7	273.3	273.8	273.5	273.5	273.8	273.3
2°	273.6	273.9	273.5	273.8	273.6	273.4	273.8	273.5	273.3	273.7	273.3
2.5°	273.6	273.8	273.6	273.7	273.3	273.4	273.7	273.2	273.3	273.5	273.1
3°	273.7	273.7	273.4	273.7	273.0	273.3	273.6	273.2	273.3	273.2	273.0
3.5°	273.5	273.5	273.3	273.4	273.0	272.9	273.5	273.1	273.2	273.1	272.9
4°	273.3	273.2	273.2	273.1	272.9	272.6	273.3	272.9	273.0	272.9	272.4
4.5°	273.1	273.1	273.0	272.7	272.4	272.5	273.1	272.8	272.7	272.5	272.2
5°	272.9	273.1	272.9	272.4	272.2	272.5	272.5	272.6	272.4	272.4	272.0
5.5°	272.7	272.9	272.7	272.2	272.0	272.0	272.4	272.3	272.2	272.2	271.7
6°	272.6	272.6	272.4	272.2	272.0	271.7	272.0	272.1	271.9	271.9	271.7
6.5°	272.0	272.1	272.1	271.8	271.3	271.4	271.7	271.9	271.4	271.7	271.2
7°	271.7	271.6	271.8	271.4	270.6	271.2	271.3	271.5	270.9	271.3	270.8
7.5°	271.4	271.4	271.4	271.0	270.4	271.0	270.8	270.9	270.8	270.7	270.6
8°	270.8	271.0	270.8	270.8	270.1	270.7	270.5	270.6	270.4	270.7	270.3
8.5°	270.3	270.6	270.3	270.3	269.6	270.2	270.1	269.9	270.0	270.2	269.8
9°	269.8	270.5	270.1	269.7	269.4	269.4	269.5	269.7	269.5	269.8	269.5
9.5°	269.5	269.9	269.7	269.4	268.7	268.9	269.2	269.2	268.9	269.4	269.0
10°	269.0	269.4	269.2	269.0	268.3	268.7	268.6	268.6	268.5	268.5	268.3
10.5°	268.4	268.8	268.5	268.4	267.6	268.2	268.3	268.2	268.0	268.2	268.0
11°	268.1	268.4	268.1	268.0	267.2	267.6	267.6	267.4	267.3	267.5	267.3
11.5°	267.7	267.7	267.4	267.4	266.8	267.0	267.0	266.7	266.9	266.9	266.8
12°	267.1	267.1	266.7	266.8	266.3	266.6	266.3	266.2	266.2	266.2	266.3
12.5°	266.4	266.6	266.0	266.2	265.7	266.1	265.6	266.0	265.7	265.6	265.7
13°	265.7	265.9	265.5	265.5	264.9	265.1	265.0	265.0	265.2	265.2	265.1
13.5°	264.8	265.0	264.8	264.9	264.2	264.4	264.4	264.6	264.5	264.6	264.3
14°	264.3	264.5	264.2	264.3	263.5	263.8	264.1	263.8	263.8	263.6	263.6
14.5°	263.5	263.8	263.6	263.1	262.9	263.1	263.5	263.2	262.9	263.0	262.9
15°	262.9	263.2	262.9	262.3	262.2	262.6	262.7	262.5	262.3	262.2	262.0
15.5°	262.0	262.4	262.2	261.7	261.4	261.7	261.9	261.8	261.8	261.5	261.5
16°	261.2	261.5	261.2	261.1	260.9	260.8	261.1	260.8	260.7	260.6	260.6
16.5°	260.4	260.7	260.5	260.4	259.9	260.0	260.3	260.1	259.7	259.9	259.9
17°	259.9	260.0	259.8	259.8	259.1	259.1	259.4	259.4	259.0	259.2	259.0
17.5°	259.2	259.2	259.1	258.8	258.3	258.4	258.9	258.6	258.8	258.7	258.6
18°	258.2	258.4	258.1	258.1	257.7	257.6	257.8	257.7	257.8	257.7	257.4
18.5°	257.2	257.6	257.3	256.9	256.9	256.8	257.3	257.0	256.8	256.9	256.5
19°	256.4	256.7	256.2	256.2	255.9	256.2	256.1	256.2	255.9	255.8	255.8
19.5°	255.5	255.7	255.2	255.5	254.8	255.3	255.4	255.3	254.8	255.0	254.8
20°	254.7	254.8	254.3	254.5	253.6	254.3	254.2	254.4	253.8	254.1	253.9
20.5°	253.5	253.5	253.4	253.4	253.0	253.4	253.1	253.5	252.8	253.1	253.2
21°	252.5	252.6	252.4	252.2	252.3	252.5	252.1	252.2	252.1	251.9	252.2
21.5°	251.4	251.6	251.1	251.1	251.0	251.4	251.1	251.2	251.2	250.9	250.9
22°	250.3	250.7	250.4	250.2	249.9	250.1	250.1	250.0	249.8	250.0	249.9



TEST NUMBER: P991385

CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	249.5	249.7	249.2	249.1	249.2	249.0	249.4	248.8	248.9	249.0	249.0
23°	248.6	248.7	248.5	247.7	248.1	248.0	248.2	247.7	247.8	247.8	247.8
23.5°	247.5	247.5	247.1	246.5	246.9	247.0	247.1	246.5	246.7	246.6	246.5
24°	245.9	246.3	246.0	245.6	245.7	246.0	245.7	245.7	245.6	245.6	245.3
24.5°	244.8	244.9	244.9	244.4	244.5	244.5	244.5	244.7	244.4	244.7	244.4
25°	243.4	243.8	243.7	243.3	243.3	243.2	243.2	243.6	243.1	243.3	243.2
25.5°	242.6	242.3	242.5	242.2	242.2	242.0	242.2	242.2	241.9	242.0	242.1
26°	241.5	241.5	241.3	241.0	240.8	241.0	241.1	240.9	241.0	240.9	240.9
26.5°	240.0	240.1	239.9	239.8	239.9	239.8	239.9	239.5	239.7	239.6	239.6
27°	238.9	238.8	238.8	238.6	238.7	238.4	238.9	238.5	238.4	238.6	238.3
27.5°	237.2	237.6	237.5	237.2	237.3	237.7	237.7	237.0	236.9	237.6	237.3
28°	236.1	236.4	236.3	235.9	235.9	236.2	235.9	236.0	235.8	235.9	235.9
28.5°	235.1	235.3	235.0	234.7	234.6	234.5	234.7	234.7	234.5	234.6	234.7
29°	233.8	233.8	233.6	233.4	233.5	233.2	233.4	233.3	233.4	233.3	233.3
29.5°	232.3	232.3	232.2	232.0	232.0	232.0	232.1	232.0	231.9	232.0	232.1
30°	230.7	231.0	230.9	230.6	230.8	230.5	231.0	230.5	230.7	230.6	230.6
30.5°	229.3	229.6	229.6	229.3	229.5	229.3	229.7	229.3	229.3	229.3	229.4
31°	228.0	228.5	228.5	227.9	228.0	228.1	228.1	227.8	227.9	227.8	228.0
31.5°	226.8	227.0	226.9	226.5	226.8	226.6	226.6	226.4	226.8	226.7	226.7
32°	225.4	225.7	225.3	225.2	225.1	225.1	225.2	225.0	225.0	225.2	225.2
32.5°	224.0	224.1	223.9	223.6	223.4	223.6	223.8	223.4	223.6	223.6	224.1
33°	222.6	222.8	222.4	221.8	222.2	222.2	222.3	222.0	222.1	222.4	222.4
33.5°	221.0	221.2	220.8	220.6	220.6	220.5	220.6	220.5	220.8	220.9	220.9
34°	219.4	219.8	219.4	219.2	219.6	219.4	219.2	219.3	219.5	219.4	219.5
34.5°	218.0	218.2	217.8	217.6	217.5	217.7	217.7	217.6	218.1	217.9	218.1
35°	216.6	216.8	216.4	216.2	216.0	216.1	216.1	215.9	216.3	216.4	216.4
35.5°	214.9	215.2	214.8	214.8	214.7	214.4	214.7	214.8	214.5	214.8	214.9
36°	213.3	213.6	213.5	213.7	213.4	213.0	212.9	213.2	213.0	213.5	213.2
36.5°	211.4	212.1	211.7	211.7	211.7	211.5	211.3	211.5	211.4	212.0	211.9
37°	210.0	210.4	210.2	209.8	210.3	209.9	209.9	210.0	209.8	210.2	210.1
37.5°	208.6	208.8	208.4	208.2	208.5	208.3	208.2	208.2	208.6	208.6	208.5
38°	207.2	207.2	206.9	206.8	206.6	206.7	206.8	206.6	206.7	206.8	206.9
38.5°	205.5	205.6	205.4	204.9	205.2	205.0	205.1	204.9	204.9	205.3	205.6
39°	203.6	203.8	203.8	203.1	203.4	203.2	203.3	203.0	203.3	203.5	203.8
39.5°	201.9	202.0	202.0	201.5	201.7	201.5	201.7	201.5	201.7	202.1	202.0
40°	200.2	200.5	200.1	199.8	200.0	199.9	200.1	199.9	199.9	200.3	200.3
40.5°	198.4	198.6	198.5	198.1	198.4	198.2	198.2	198.0	198.4	198.5	198.6
41°	196.7	196.8	196.9	196.5	196.7	196.5	196.4	196.3	196.6	196.8	196.9
41.5°	195.3	195.0	195.0	194.9	195.0	194.7	194.6	194.4	195.0	195.1	195.1
42°	193.4	193.2	193.3	192.8	192.8	192.8	192.9	192.8	193.1	193.3	193.2
42.5°	191.5	191.5	191.3	191.1	191.0	191.1	191.2	191.1	191.4	191.6	191.5
43°	189.8	189.8	189.6	189.4	189.2	189.3	189.5	189.6	189.6	189.8	189.5
43.5°	188.3	188.0	187.7	187.5	187.5	187.6	187.8	187.4	187.6	187.9	188.0
44°	186.4	186.3	186.1	185.9	185.9	185.9	185.8	185.7	185.8	186.4	186.2
44.5°	184.4	184.5	184.3	184.0	184.1	184.1	183.9	184.0	184.0	184.5	184.3

TEST NUMBER: P991385

CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	182.5	182.6	182.3	182.1	182.1	182.1	182.3	182.1	182.2	182.5	182.5
45.5°	180.7	180.8	180.7	180.5	180.5	180.3	180.6	180.5	180.7	180.8	181.2
46°	178.9	179.0	178.6	178.4	178.7	178.4	178.4	178.6	178.7	178.8	179.0
46.5°	177.1	177.1	176.6	176.5	176.9	177.0	176.6	176.7	177.0	176.9	177.2
47°	175.2	175.2	174.9	174.3	175.1	174.8	174.7	174.8	174.9	175.1	175.2
47.5°	173.4	173.5	172.8	172.6	173.2	172.8	172.9	173.2	173.3	173.1	173.3
48°	171.5	171.5	171.0	170.7	171.1	170.9	171.3	171.1	171.5	171.2	171.4
48.5°	169.3	169.4	169.3	168.9	169.2	169.2	169.1	169.0	169.4	169.4	169.5
49°	167.3	167.3	167.1	167.1	167.1	167.1	167.2	167.1	167.3	167.5	167.6
49.5°	165.4	165.3	165.1	164.9	165.2	165.0	165.2	165.2	165.3	165.5	165.6
50°	163.6	163.5	163.4	162.9	163.4	163.1	163.4	163.3	163.0	163.7	163.6
50.5°	161.5	161.3	161.4	160.9	161.2	161.3	161.3	161.2	161.5	161.8	161.7
51°	159.7	159.3	159.4	158.8	159.2	159.5	159.5	159.3	159.4	159.6	159.8
51.5°	157.6	157.2	157.5	156.8	157.2	157.4	157.2	157.1	157.6	157.7	158.1
52°	155.6	155.4	155.2	155.1	155.3	155.1	155.1	155.3	155.5	155.5	155.9
52.5°	153.5	153.4	153.0	152.8	153.1	153.1	153.1	153.0	153.4	153.6	154.1
53°	151.4	151.4	151.0	150.8	151.1	151.3	151.2	150.9	151.2	151.8	151.9
53.5°	149.5	149.4	148.9	148.7	149.1	149.0	149.3	149.0	149.2	149.5	149.7
54°	147.5	147.1	146.8	146.8	147.1	147.0	147.1	147.1	147.1	147.4	147.6
54.5°	145.3	145.1	144.8	144.6	145.1	145.0	144.7	145.0	145.3	145.3	145.5
55°	143.3	143.0	142.8	142.5	143.1	143.1	143.0	143.0	143.2	143.4	143.5
55.5°	141.4	140.9	140.8	140.3	141.1	140.9	140.9	141.0	141.2	141.4	141.5
56°	139.0	139.0	138.5	138.6	138.8	138.9	139.0	138.7	139.0	139.4	139.4
56.5°	136.9	136.8	136.4	136.3	136.4	136.8	136.9	136.9	137.1	137.2	137.5
57°	134.7	134.6	134.2	134.1	134.4	134.7	134.7	134.7	134.8	135.1	135.1
57.5°	132.6	132.4	131.9	132.0	132.4	132.6	132.6	132.8	132.4	133.0	133.2
58°	130.0	130.1	130.0	129.8	130.6	130.5	130.3	130.5	130.3	130.9	130.7
58.5°	128.1	128.0	127.7	127.7	128.4	128.3	128.1	128.4	128.3	128.6	128.7
59°	125.9	125.9	125.6	125.4	126.2	125.9	126.1	126.0	125.9	126.5	126.8
59.5°	123.5	123.5	123.3	123.2	123.8	123.8	123.9	123.8	123.6	124.2	124.5
60°	121.7	121.4	121.2	121.0	121.8	121.7	121.7	121.7	121.3	122.0	122.4
60.5°	119.2	119.2	118.9	118.9	119.6	119.7	119.5	119.5	119.1	119.8	120.1
61°	117.0	117.1	117.0	116.7	117.4	117.2	117.5	117.2	117.0	117.5	117.8
61.5°	114.7	114.7	114.6	114.3	115.1	115.4	115.3	115.0	114.7	115.2	116.0
62°	112.5	112.6	112.5	112.2	113.1	113.1	113.1	112.9	112.7	113.0	113.7
62.5°	110.1	110.2	110.3	110.3	110.8	110.9	111.0	110.8	110.4	110.8	111.6
63°	108.0	108.0	108.3	108.1	108.6	108.5	108.9	108.3	108.0	108.5	109.3
63.5°	105.6	105.7	105.9	105.8	106.5	106.3	106.6	106.2	106.0	106.3	107.2
64°	103.7	103.8	104.1	103.7	104.2	104.3	104.5	104.0	103.6	104.2	104.9
64.5°	101.4	101.5	101.7	101.7	102.1	102.1	102.5	101.9	101.7	102.2	103.1
65°	99.1	99.3	99.6	99.4	100.0	99.9	100.2	99.7	99.4	99.7	100.8
65.5°	96.8	97.1	97.5	97.3	97.9	97.9	98.0	97.5	97.0	97.5	98.5
66°	94.4	94.7	95.3	95.1	95.6	95.7	95.7	95.3	94.8	95.3	96.4
66.5°	92.2	92.6	93.0	92.9	93.5	93.4	93.7	93.0	92.5	93.0	94.1
67°	89.9	90.2	90.8	90.6	91.4	91.2	91.4	90.7	90.2	90.8	91.8

TEST NUMBER: P991385

CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	87.6	87.9	88.5	88.2	89.1	88.9	89.1	88.5	88.0	88.5	89.7
68°	85.2	85.7	86.3	86.2	86.9	86.8	87.0	86.1	85.5	86.1	87.4
68.5°	82.9	83.2	84.0	84.0	84.7	84.6	84.7	83.8	83.4	83.8	85.1
69°	80.6	81.0	81.7	81.9	82.5	82.4	82.4	81.5	81.0	81.5	82.9
69.5°	78.3	78.7	79.5	79.6	80.2	80.3	80.1	79.2	78.6	79.2	80.7
70°	76.0	76.3	77.2	77.2	78.1	78.1	78.1	76.9	76.4	76.8	78.2
70.5°	73.7	74.1	74.9	75.0	75.8	75.9	75.8	74.7	74.2	74.7	76.2
71°	71.6	71.7	72.6	72.9	73.6	73.7	73.4	72.2	71.8	72.4	73.9
71.5°	69.2	69.5	70.5	70.6	71.2	71.5	71.2	69.9	69.4	70.0	71.6
72°	66.9	67.1	68.1	68.5	69.2	69.3	69.0	67.8	67.1	67.8	69.3
72.5°	64.8	65.0	65.8	66.3	67.0	67.2	66.9	65.4	64.9	65.5	67.1
73°	62.4	62.5	63.8	64.2	64.9	65.0	64.6	63.3	62.8	63.5	64.7
73.5°	60.1	60.3	61.5	61.9	62.7	62.9	62.5	61.0	60.4	61.2	62.7
74°	57.8	58.1	59.3	59.8	60.5	60.5	60.3	58.9	58.3	59.0	60.5
74.5°	55.6	55.8	57.0	57.6	58.5	58.4	58.0	56.5	56.1	56.6	58.2
75°	53.2	53.7	54.9	55.6	56.3	56.2	55.8	54.3	53.8	54.3	55.9
75.5°	50.9	51.4	52.6	53.4	54.2	54.0	53.7	52.1	51.5	52.2	53.8
76°	48.8	49.3	50.6	51.2	51.9	52.1	51.5	49.9	49.3	50.0	51.6
76.5°	46.6	47.0	48.3	49.1	49.9	49.8	49.3	47.6	47.1	47.7	49.3
77°	44.5	45.0	46.1	46.9	47.6	47.8	47.2	45.5	44.9	45.5	47.1
77.5°	42.3	42.7	44.0	45.1	45.5	45.6	45.0	43.3	42.9	43.3	45.0
78°	40.1	40.5	41.8	42.8	43.4	43.6	42.8	41.1	40.7	41.2	42.8
78.5°	38.0	38.4	39.6	40.8	41.4	41.3	40.7	39.0	38.5	39.0	40.6
79°	35.8	36.1	37.5	38.5	39.3	39.5	38.5	36.8	36.4	36.9	38.5
79.5°	33.6	34.0	35.4	36.5	37.3	37.4	36.5	34.7	34.3	34.8	36.4
80°	31.6	31.8	33.3	34.5	35.3	35.4	34.3	32.5	32.2	32.7	34.2
80.5°	29.6	29.7	31.3	32.4	33.4	33.3	32.3	30.4	30.1	30.6	32.2
81°	27.4	27.6	29.2	30.6	31.4	31.2	30.3	28.3	28.1	28.5	30.1
81.5°	25.6	25.8	27.1	28.6	29.3	29.3	28.3	26.3	26.0	26.4	28.1
82°	23.6	23.6	25.3	26.6	27.2	27.4	26.2	24.3	24.2	24.6	26.0
82.5°	21.6	21.6	23.4	24.8	25.3	25.5	24.4	22.4	22.3	22.5	24.3
83°	19.6	19.5	21.4	22.8	23.6	23.8	22.5	20.3	20.2	20.4	22.1
83.5°	17.6	17.5	19.5	21.0	21.7	21.7	20.6	18.2	18.2	18.3	20.2
84°	15.7	15.5	17.5	19.0	19.7	19.8	18.7	16.2	16.3	16.3	18.3
84.5°	13.7	13.5	15.8	17.2	17.9	17.9	16.8	14.2	14.3	14.2	16.4
85°	11.7	11.5	13.8	15.2	16.0	15.9	15.0	12.2	12.4	12.2	14.3
85.5°	9.9	9.6	12.2	13.4	14.1	14.1	13.2	10.3	10.4	10.1	12.7
86°	7.9	7.9	10.5	11.6	12.2	12.2	11.5	8.6	8.5	8.0	10.8
86.5°	6.3	6.6	8.9	9.7	10.3	10.4	9.8	7.0	6.6	6.2	9.4
87°	5.0	5.4	7.3	7.9	8.6	8.6	8.0	5.7	5.5	4.7	7.6
87.5°	3.9	4.3	5.7	6.4	6.8	6.8	6.4	4.4	3.9	3.6	6.3
88°	2.9	3.2	4.2	4.5	5.2	5.2	4.7	3.2	2.9	2.8	4.7
88.5°	1.9	2.3	2.9	2.9	3.3	3.3	3.2	2.0	1.9	1.7	3.4
89°	1.1	1.3	1.5	1.6	1.9	1.8	1.7	1.0	0.8	0.8	1.9
89.5°	0.5	0.6	0.6	0.6	0.6	0.6	0.5	0.1	0.0	0.0	0.7

TEST NUMBER: P991385

CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.1	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.0
103°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.1	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.1	0.2	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.1	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.1	0.2	0.0
106°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.1	0.1	0.0
106.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.1	0.1	0.0
107°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.1	0.1	0.0
107.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.1	0.1	0.0
108°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.1	0.1	0.0
108.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.1	0.1	0.0
109°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.1	0.1	0.0
109.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.1	0.1	0.0
110°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.1	0.1	0.0
110.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.1	0.1	0.0
111°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.2	0.1	0.0
111.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.2	0.1	0.0
112°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.2	0.1	0.0

TEST NUMBER: P991385

CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.2	0.1	0.0
113°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.2	0.1	0.0
113.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.2	0.1	0.0
114°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.2	0.1	0.0
114.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.2	0.1	0.0
115°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.2	0.1	0.0
115.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.2	0.1	0.0
116°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.2	0.1	0.0
116.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.2	0.1	0.0
117°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.2	0.2	0.1	0.0
117.5°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.2	0.2	0.1	0.0
118°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.2	0.2	0.1	0.0
118.5°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.3	0.2	0.1	0.0
119°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.3	0.2	0.1	0.0
119.5°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.3	0.2	0.1	0.0
120°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.2	0.2	0.1	0.0
120.5°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.2	0.2	0.1	0.0
121°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.3	0.2	0.1	0.0
121.5°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.3	0.2	0.1	0.0
122°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.3	0.2	0.1	0.0
122.5°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.3	0.2	0.1	0.0
123°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.3	0.2	0.1	0.0
123.5°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.3	0.2	0.1	0.0
124°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.3	0.2	0.1	0.0
124.5°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.3	0.2	0.1	0.0
125°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.3	0.2	0.1	0.0
125.5°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.2	0.2	0.1	0.0
126°	0.0	0.0	0.0	0.0	0.3	0.0	0.0	0.2	0.2	0.1	0.0
126.5°	0.0	0.0	0.0	0.0	0.3	0.0	0.0	0.4	0.2	0.1	0.0
127°	0.0	0.0	0.0	0.0	0.3	0.0	0.0	0.0	0.2	0.1	0.0
127.5°	0.0	0.0	0.0	0.0	0.3	0.0	0.0	0.0	0.2	0.1	0.0
128°	0.0	0.0	0.0	0.0	0.3	0.0	0.0	0.0	0.2	0.1	0.0
128.5°	0.0	0.0	0.0	0.0	0.3	0.0	0.0	0.0	0.2	0.1	0.0
129°	0.0	0.0	0.0	0.0	0.3	0.0	0.0	0.3	0.2	0.1	0.0
129.5°	0.0	0.0	0.0	0.0	0.3	0.0	0.0	0.4	0.2	0.1	0.1
130°	0.0	0.0	0.0	0.0	0.3	0.0	0.0	0.0	0.2	0.1	0.1
130.5°	0.0	0.0	0.0	0.0	0.3	0.0	0.0	0.2	0.2	0.1	0.1
131°	0.0	0.0	0.0	0.0	0.3	0.0	0.0	0.0	0.2	0.1	0.1
131.5°	0.0	0.0	0.0	0.0	0.3	0.0	0.0	0.0	0.3	0.2	0.0
132°	0.0	0.0	0.0	0.0	0.4	0.0	0.0	0.3	0.0	0.1	0.0
132.5°	0.0	0.0	0.0	0.0	0.4	0.0	0.0	0.0	0.0	0.2	0.0
133°	0.0	0.0	0.0	0.0	0.4	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.0	0.0	0.0	0.0	0.4	0.0	0.0	0.0	0.4	0.0	0.0
134°	0.0	0.0	0.0	0.0	0.4	0.0	0.0	0.1	0.2	0.0	0.0
134.5°	0.0	0.0	0.0	0.0	0.4	0.1	0.0	0.1	0.0	0.0	0.0

TEST NUMBER: P991385

CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.0	0.0	0.0	0.0	0.4	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.0	0.0	0.0	0.0	0.4	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.0	0.0	0.0	0.0	0.4	0.0	0.0	0.2	0.2	0.0	0.0
136.5°	0.0	0.0	0.0	0.0	0.4	0.0	0.0	0.3	0.2	0.0	0.0
137°	0.0	0.0	0.0	0.0	0.4	0.0	0.0	0.5	0.2	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.3	0.0	0.0	0.5	0.2	0.0	0.0
138°	0.0	0.0	0.0	0.0	0.4	0.0	0.0	0.5	0.2	0.0	0.0
138.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
139°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
139.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
140.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
141°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
141.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
142°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
143°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
143.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
144°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
144.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
145.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
146°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
146.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
147°	0.0	0.0	0.0	0.0	0.4	0.0	0.0	0.5	0.2	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
148°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
148.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
149°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
149.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
150.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
151°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
151.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
152°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.5	0.2	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
153°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
153.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
154°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
154.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
155.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.7	0.2	0.0	0.0
156°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.7	0.2	0.0	0.0
156.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.7	0.2	0.0	0.0
157°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0

TEST NUMBER: P991385

CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
158°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
158.5°	0.0	0.0	0.0	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
159°	0.0	0.0	0.1	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
159.5°	0.0	0.0	0.2	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
160°	0.0	0.0	0.2	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
160.5°	0.0	0.0	0.3	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
161°	0.0	0.0	0.3	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
161.5°	0.0	0.0	0.4	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
162°	0.0	0.0	0.4	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
162.5°	0.0	0.0	0.4	0.0	0.5	0.0	0.0	0.6	0.2	0.0	0.0
163°	0.0	0.0	0.5	0.1	0.5	0.0	0.0	0.6	0.2	0.0	0.0
163.5°	0.0	0.0	0.5	0.2	0.5	0.0	0.0	0.6	0.2	0.0	0.0
164°	0.0	0.0	0.5	0.1	0.5	0.0	0.0	0.6	0.2	0.0	0.0
164.5°	0.0	0.0	0.5	0.2	0.5	0.0	0.0	0.6	0.2	0.0	0.0
165°	0.0	0.0	0.5	0.2	0.5	0.0	0.0	0.6	0.2	0.0	0.0
165.5°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
166°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
166.5°	0.1	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
167°	0.1	0.1	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
167.5°	0.0	0.1	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
168°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
168.5°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
169°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
169.5°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
170°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
170.5°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
171°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
171.5°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
172°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
172.5°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
173°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
173.5°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
174°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
174.5°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
175°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
175.5°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
176°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
176.5°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
177°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
177.5°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
178°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
178.5°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
179°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0
179.5°	0.0	0.0	0.5	0.3	0.5	0.0	0.0	0.6	0.2	0.0	0.0



TEST NUMBER: P991385
CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P991385

CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	273.8	273.8	273.8	273.8	273.8	273.8
0.5°	273.4	273.9	274.0	273.9	273.7	274.0
1°	273.3	273.9	274.0	273.8	273.7	274.0
1.5°	273.3	273.7	274.0	273.8	273.7	274.0
2°	273.3	273.4	273.8	273.7	273.7	273.6
2.5°	272.9	273.4	273.8	273.7	273.7	273.6
3°	272.9	273.3	273.6	273.7	273.7	273.7
3.5°	272.7	272.9	273.4	273.3	273.7	273.5
4°	272.5	272.7	273.3	273.1	273.8	273.3
4.5°	272.2	272.4	273.0	273.1	273.5	273.1
5°	272.1	272.1	272.9	272.9	273.5	272.9
5.5°	271.8	272.1	272.4	272.7	273.0	272.7
6°	271.7	272.0	272.3	272.3	272.6	272.6
6.5°	271.4	271.4	271.8	272.1	272.1	272.0
7°	271.0	271.2	271.6	271.5	271.9	271.7
7.5°	270.5	270.8	271.4	271.1	271.5	271.4
8°	270.2	270.8	270.8	271.1	271.2	270.8
8.5°	269.5	270.2	270.5	270.6	270.9	270.3
9°	269.4	269.5	270.0	270.2	270.5	269.8
9.5°	268.8	269.0	269.2	269.7	270.0	269.5
10°	268.3	268.6	268.9	269.3	269.2	269.0
10.5°	268.0	268.2	268.5	268.3	268.6	268.4
11°	267.1	267.6	268.2	268.1	268.0	268.1
11.5°	266.7	266.9	267.5	267.2	267.3	267.7
12°	266.4	266.3	266.9	266.8	266.8	267.1
12.5°	265.6	265.5	266.3	266.4	266.2	266.4
13°	264.8	265.1	265.6	265.5	265.3	265.7
13.5°	264.2	264.4	265.1	264.9	265.0	264.8
14°	263.6	263.9	264.5	264.3	264.4	264.3
14.5°	262.8	262.9	263.6	263.7	263.5	263.5
15°	262.1	262.4	262.7	262.9	262.7	262.9
15.5°	261.1	261.6	261.7	262.0	261.9	262.0
16°	260.3	261.0	261.2	261.3	261.4	261.2
16.5°	259.4	260.4	260.6	260.8	260.5	260.4
17°	259.1	259.8	259.9	260.1	259.9	259.9
17.5°	258.3	258.8	259.2	259.3	259.0	259.2
18°	257.4	257.8	258.3	258.4	258.2	258.2
18.5°	256.5	257.0	257.6	257.7	257.2	257.2
19°	255.9	256.2	256.4	256.7	256.4	256.4
19.5°	254.6	255.1	255.3	255.6	255.7	255.5
20°	253.5	254.2	254.4	254.7	254.8	254.7
20.5°	252.7	253.3	253.6	253.8	253.5	253.5
21°	251.9	252.0	252.7	252.6	252.4	252.5
21.5°	250.6	250.6	251.3	251.6	251.6	251.4
22°	249.5	249.7	250.4	250.5	250.8	250.3



TEST NUMBER: P991385

CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	248.5	249.0	249.5	249.4	250.0	249.5
23°	247.5	248.0	248.3	248.6	248.3	248.6
23.5°	246.5	246.8	247.1	247.5	247.1	247.5
24°	245.6	245.8	246.5	246.3	246.5	245.9
24.5°	244.3	244.5	245.4	245.4	244.9	244.8
25°	243.0	243.3	243.6	244.2	244.1	243.4
25.5°	241.9	242.1	242.6	242.6	242.7	242.6
26°	240.5	241.1	241.5	241.6	241.2	241.5
26.5°	239.5	239.8	240.1	240.2	239.9	240.0
27°	238.3	238.5	238.7	239.0	238.7	238.9
27.5°	236.9	237.3	237.7	237.8	237.6	237.2
28°	235.7	235.9	236.4	236.5	236.3	236.1
28.5°	234.6	234.6	235.2	235.2	235.2	235.1
29°	233.3	233.3	233.9	233.9	233.9	233.8
29.5°	231.9	232.1	232.8	232.6	232.7	232.3
30°	230.5	230.8	231.4	231.3	231.1	230.7
30.5°	229.3	229.6	229.9	230.0	229.8	229.3
31°	227.8	227.9	228.3	228.4	228.7	228.0
31.5°	226.5	226.4	226.9	227.0	227.1	226.8
32°	225.0	225.2	225.3	225.6	225.7	225.4
32.5°	223.7	224.0	224.0	224.1	224.1	224.0
33°	222.0	222.1	222.8	222.8	222.4	222.6
33.5°	220.6	220.8	221.1	221.1	221.0	221.0
34°	219.5	219.3	219.8	220.1	219.7	219.4
34.5°	217.7	217.8	218.4	218.3	218.3	218.0
35°	216.0	216.4	216.7	217.0	216.8	216.6
35.5°	214.6	214.8	215.1	215.2	215.2	214.9
36°	213.3	213.4	213.5	213.8	213.3	213.3
36.5°	211.7	211.7	211.9	212.1	212.0	211.4
37°	209.9	209.8	210.5	210.7	210.3	210.0
37.5°	208.5	208.3	208.7	209.0	209.0	208.6
38°	206.9	206.7	207.1	207.4	207.2	207.2
38.5°	205.3	205.1	205.3	205.7	205.3	205.5
39°	203.6	203.4	203.7	204.2	203.5	203.6
39.5°	201.9	201.7	202.3	202.4	201.8	201.9
40°	200.2	200.0	200.3	200.7	200.4	200.2
40.5°	198.5	198.4	198.4	198.8	198.7	198.4
41°	196.9	196.7	196.8	197.3	196.8	196.7
41.5°	195.2	194.7	195.1	195.2	195.4	195.3
42°	193.4	193.0	193.4	193.5	193.5	193.4
42.5°	191.6	191.6	191.7	191.8	191.7	191.5
43°	189.7	189.7	190.2	190.2	190.2	189.8
43.5°	188.1	187.7	187.9	188.2	188.3	188.3
44°	186.0	186.2	186.3	186.6	186.4	186.4
44.5°	184.4	184.1	184.4	184.6	184.2	184.4



TEST NUMBER: P991385

CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	182.5	182.2	182.6	183.1	182.9	182.5
45.5°	180.9	180.6	180.9	181.3	181.1	180.7
46°	179.2	178.8	179.0	179.5	178.9	178.9
46.5°	177.3	176.9	177.2	177.4	177.1	177.1
47°	175.4	174.9	175.3	175.4	175.3	175.2
47.5°	173.5	173.1	173.4	173.3	173.5	173.4
48°	171.7	171.3	171.7	171.8	171.5	171.5
48.5°	169.5	169.3	169.5	169.7	169.5	169.3
49°	167.4	167.3	167.5	167.8	167.6	167.3
49.5°	165.6	165.4	165.7	166.0	165.8	165.4
50°	163.7	163.4	163.7	163.8	163.7	163.6
50.5°	161.7	161.4	161.9	162.0	161.7	161.5
51°	159.9	159.3	159.8	160.0	159.7	159.7
51.5°	158.1	157.4	157.7	157.7	157.8	157.6
52°	155.9	155.3	155.5	156.0	155.8	155.6
52.5°	153.9	153.3	153.7	154.2	153.6	153.5
53°	151.9	151.4	151.7	151.8	151.8	151.4
53.5°	149.8	149.5	149.6	150.0	149.6	149.5
54°	147.6	147.5	147.8	147.9	147.5	147.5
54.5°	145.6	145.3	145.5	145.6	145.5	145.3
55°	143.5	143.1	143.5	143.5	143.4	143.3
55.5°	141.5	141.0	141.5	141.4	141.4	141.4
56°	139.4	139.0	139.6	139.1	139.2	139.0
56.5°	137.3	137.0	137.3	137.2	137.2	136.9
57°	135.3	134.7	135.2	135.1	134.8	134.7
57.5°	133.1	132.9	133.0	133.0	132.8	132.6
58°	131.0	130.7	131.0	130.7	130.6	130.0
58.5°	129.0	128.7	128.8	128.6	128.4	128.1
59°	126.8	126.5	126.6	126.5	126.2	125.9
59.5°	124.5	124.3	124.3	124.3	124.1	123.5
60°	122.4	121.9	122.3	122.2	122.0	121.7
60.5°	120.2	119.8	120.2	119.8	119.5	119.2
61°	118.0	117.6	118.0	117.7	117.4	117.0
61.5°	115.9	115.6	115.8	115.7	115.1	114.7
62°	113.8	113.4	113.3	113.3	113.0	112.5
62.5°	111.8	111.2	111.4	111.0	110.7	110.1
63°	109.6	108.8	109.2	109.0	108.5	108.0
63.5°	107.4	106.8	106.7	106.9	106.2	105.6
64°	105.1	104.7	104.7	104.5	104.1	103.7
64.5°	103.1	102.5	102.6	102.8	101.9	101.4
65°	100.9	100.3	100.5	100.5	99.6	99.1
65.5°	98.7	98.0	98.3	98.4	97.3	96.8
66°	96.6	95.8	96.2	96.2	94.8	94.4
66.5°	94.4	93.6	94.0	93.9	92.7	92.2
67°	92.1	91.4	91.7	91.8	90.4	89.9



TEST NUMBER: P991385

CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	90.0	89.2	89.4	89.3	88.1	87.6
68°	88.0	86.9	87.1	87.0	85.7	85.2
68.5°	85.7	84.7	84.9	84.7	83.4	82.9
69°	83.5	82.7	82.7	82.6	81.2	80.6
69.5°	81.2	80.2	80.4	80.3	79.0	78.3
70°	79.0	78.2	78.3	78.0	76.4	76.0
70.5°	76.9	76.0	76.1	75.8	74.3	73.7
71°	74.6	73.8	74.0	73.5	72.0	71.6
71.5°	72.7	71.7	71.5	71.2	69.8	69.2
72°	70.1	69.3	69.6	69.0	67.6	66.9
72.5°	67.8	67.1	67.3	66.7	65.3	64.8
73°	65.6	65.1	65.2	64.5	63.0	62.4
73.5°	63.7	63.0	63.2	62.2	60.9	60.1
74°	61.6	60.8	60.8	60.3	58.5	57.8
74.5°	59.4	58.8	58.8	57.7	56.3	55.6
75°	57.3	56.4	56.6	55.5	54.0	53.2
75.5°	55.1	54.3	54.5	53.3	51.8	50.9
76°	52.8	52.3	52.3	51.1	49.4	48.8
76.5°	50.8	50.1	50.3	49.0	47.2	46.6
77°	48.8	48.0	47.9	46.7	45.2	44.5
77.5°	46.5	46.0	46.0	44.8	42.9	42.3
78°	44.5	43.9	43.9	42.4	40.8	40.1
78.5°	42.4	41.7	41.8	40.5	38.6	38.0
79°	40.4	39.6	39.7	38.2	36.4	35.8
79.5°	38.2	37.6	37.6	36.0	34.3	33.6
80°	36.3	35.5	35.6	34.0	32.1	31.6
80.5°	34.2	33.5	33.5	32.0	30.0	29.6
81°	32.1	31.5	31.6	29.9	27.8	27.4
81.5°	30.0	29.5	29.5	27.7	25.9	25.6
82°	28.1	27.5	27.6	25.9	23.9	23.6
82.5°	26.2	25.8	25.9	23.9	21.7	21.6
83°	24.3	23.9	24.0	21.9	19.7	19.6
83.5°	22.5	22.0	22.1	19.9	17.7	17.6
84°	20.5	20.0	20.1	18.0	15.6	15.7
84.5°	18.8	18.1	18.2	16.2	13.6	13.7
85°	16.8	16.2	16.4	14.4	11.6	11.7
85.5°	14.9	14.3	14.5	12.6	9.5	9.9
86°	13.1	12.6	12.6	11.0	7.8	7.9
86.5°	11.2	10.8	10.7	9.3	6.3	6.3
87°	9.5	8.9	9.0	7.7	5.1	5.0
87.5°	7.7	7.1	7.1	6.4	4.0	3.9
88°	5.9	5.4	5.4	4.6	3.0	2.9
88.5°	4.2	3.7	3.7	3.2	2.1	1.9
89°	2.7	2.3	2.3	1.9	1.3	1.1
89.5°	1.1	1.0	1.1	1.0	0.5	0.5



TEST NUMBER: P991385

CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.3	0.3	0.3	0.2	0.1
90.5°	0.0	0.0	0.1	0.1	0.1	0.0
91°	0.0	0.0	0.0	0.1	0.1	0.0
91.5°	0.0	0.0	0.0	0.0	0.1	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.1	0.0	0.0
103.5°	0.0	0.0	0.0	0.1	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.1	0.0	0.0	0.0	0.0	0.0
108°	0.1	0.0	0.0	0.0	0.0	0.0
108.5°	0.1	0.0	0.0	0.0	0.0	0.0
109°	0.1	0.0	0.0	0.0	0.0	0.0
109.5°	0.2	0.0	0.0	0.0	0.0	0.0
110°	0.2	0.0	0.0	0.0	0.0	0.0
110.5°	0.2	0.0	0.0	0.0	0.0	0.0
111°	0.2	0.0	0.0	0.0	0.0	0.0
111.5°	0.2	0.0	0.0	0.0	0.0	0.0
112°	0.2	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P991385

CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.2	0.0	0.0	0.0	0.0	0.0
113°	0.2	0.0	0.0	0.0	0.0	0.0
113.5°	0.2	0.0	0.0	0.0	0.0	0.0
114°	0.2	0.0	0.0	0.0	0.0	0.0
114.5°	0.2	0.0	0.0	0.0	0.0	0.0
115°	0.2	0.0	0.0	0.0	0.0	0.0
115.5°	0.2	0.0	0.0	0.0	0.0	0.0
116°	0.2	0.0	0.0	0.0	0.0	0.0
116.5°	0.2	0.0	0.0	0.0	0.0	0.0
117°	0.2	0.0	0.0	0.0	0.0	0.0
117.5°	0.2	0.0	0.0	0.0	0.0	0.0
118°	0.2	0.0	0.0	0.0	0.0	0.0
118.5°	0.2	0.0	0.0	0.0	0.0	0.0
119°	0.2	0.0	0.0	0.0	0.0	0.0
119.5°	0.2	0.0	0.0	0.0	0.0	0.0
120°	0.2	0.0	0.0	0.0	0.0	0.0
120.5°	0.2	0.0	0.0	0.0	0.0	0.0
121°	0.2	0.0	0.0	0.0	0.0	0.0
121.5°	0.2	0.0	0.0	0.0	0.0	0.0
122°	0.2	0.0	0.0	0.0	0.0	0.0
122.5°	0.2	0.0	0.0	0.0	0.0	0.0
123°	0.2	0.0	0.0	0.0	0.0	0.0
123.5°	0.2	0.0	0.0	0.0	0.0	0.0
124°	0.2	0.0	0.0	0.0	0.0	0.0
124.5°	0.2	0.0	0.0	0.0	0.0	0.0
125°	0.2	0.0	0.0	0.0	0.0	0.0
125.5°	0.2	0.0	0.0	0.0	0.0	0.0
126°	0.2	0.0	0.0	0.0	0.0	0.0
126.5°	0.2	0.0	0.0	0.0	0.0	0.0
127°	0.2	0.0	0.0	0.0	0.0	0.0
127.5°	0.2	0.0	0.0	0.0	0.0	0.0
128°	0.2	0.0	0.0	0.0	0.0	0.0
128.5°	0.2	0.0	0.0	0.0	0.0	0.0
129°	0.2	0.0	0.0	0.0	0.0	0.0
129.5°	0.2	0.0	0.0	0.0	0.0	0.0
130°	0.2	0.0	0.0	0.0	0.0	0.0
130.5°	0.2	0.0	0.0	0.0	0.0	0.0
131°	0.2	0.0	0.0	0.0	0.0	0.0
131.5°	0.2	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.2	0.0	0.0	0.0	0.0	0.0
134°	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.4	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P991385

CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.4	0.0	0.0	0.0	0.0	0.0
135.5°	0.4	0.0	0.0	0.0	0.0	0.0
136°	0.4	0.0	0.0	0.0	0.0	0.0
136.5°	0.4	0.0	0.0	0.0	0.0	0.0
137°	0.4	0.0	0.0	0.0	0.0	0.0
137.5°	0.4	0.0	0.0	0.0	0.0	0.0
138°	0.4	0.0	0.0	0.0	0.0	0.0
138.5°	0.4	0.0	0.0	0.0	0.0	0.0
139°	0.4	0.0	0.0	0.0	0.0	0.0
139.5°	0.4	0.0	0.0	0.0	0.0	0.0
140°	0.4	0.0	0.0	0.0	0.0	0.0
140.5°	0.4	0.0	0.0	0.0	0.0	0.0
141°	0.4	0.0	0.0	0.0	0.0	0.0
141.5°	0.4	0.0	0.0	0.0	0.0	0.0
142°	0.3	0.0	0.0	0.0	0.0	0.0
142.5°	0.3	0.0	0.0	0.0	0.0	0.0
143°	0.3	0.0	0.0	0.0	0.0	0.0
143.5°	0.3	0.0	0.0	0.2	0.0	0.0
144°	0.4	0.0	0.0	0.1	0.0	0.0
144.5°	0.4	0.0	0.0	0.1	0.0	0.0
145°	0.4	0.0	0.0	0.1	0.0	0.0
145.5°	0.4	0.0	0.0	0.1	0.0	0.0
146°	0.4	0.0	0.0	0.1	0.0	0.0
146.5°	0.4	0.0	0.0	0.1	0.0	0.0
147°	0.4	0.0	0.0	0.1	0.0	0.0
147.5°	0.5	0.0	0.0	0.1	0.0	0.0
148°	0.5	0.0	0.0	0.1	0.0	0.0
148.5°	0.5	0.0	0.0	0.1	0.0	0.0
149°	0.5	0.0	0.0	0.1	0.0	0.0
149.5°	0.5	0.0	0.0	0.1	0.0	0.0
150°	0.5	0.0	0.0	0.1	0.0	0.0
150.5°	0.5	0.0	0.0	0.1	0.0	0.0
151°	0.5	0.0	0.0	0.1	0.0	0.0
151.5°	0.5	0.0	0.0	0.1	0.0	0.0
152°	0.5	0.0	0.0	0.1	0.0	0.0
152.5°	0.5	0.0	0.0	0.1	0.0	0.0
153°	0.5	0.0	0.0	0.1	0.0	0.0
153.5°	0.5	0.0	0.0	0.1	0.0	0.0
154°	0.5	0.0	0.0	0.1	0.0	0.0
154.5°	0.5	0.0	0.0	0.1	0.0	0.0
155°	0.5	0.0	0.0	0.1	0.0	0.0
155.5°	0.5	0.0	0.0	0.1	0.0	0.0
156°	0.5	0.0	0.0	0.1	0.0	0.0
156.5°	0.5	0.0	0.0	0.1	0.0	0.0
157°	0.5	0.0	0.0	0.1	0.0	0.0



TEST NUMBER: P991385

CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.5	0.0	0.0	0.2	0.0	0.0
158°	0.5	0.0	0.0	0.2	0.0	0.0
158.5°	0.5	0.0	0.0	0.2	0.0	0.0
159°	0.5	0.0	0.0	0.3	0.0	0.0
159.5°	0.5	0.0	0.0	0.3	0.0	0.0
160°	0.5	0.0	0.0	0.3	0.1	0.0
160.5°	0.5	0.0	0.0	0.3	0.1	0.0
161°	0.5	0.0	0.0	0.4	0.1	0.0
161.5°	0.5	0.0	0.0	0.4	0.1	0.0
162°	0.5	0.0	0.0	0.5	0.1	0.0
162.5°	0.5	0.0	0.0	0.5	0.1	0.0
163°	0.5	0.0	0.0	0.5	0.1	0.0
163.5°	0.5	0.0	0.0	0.6	0.1	0.0
164°	0.5	0.0	0.0	0.6	0.1	0.0
164.5°	0.5	0.0	0.0	0.7	0.1	0.0
165°	0.5	0.0	0.0	0.7	0.1	0.0
165.5°	0.5	0.0	0.0	0.7	0.1	0.0
166°	0.5	0.0	0.0	0.7	0.1	0.0
166.5°	0.5	0.0	0.0	0.7	0.1	0.1
167°	0.5	0.0	0.0	0.7	0.1	0.1
167.5°	0.5	0.0	0.0	0.7	0.1	0.0
168°	0.5	0.0	0.0	0.7	0.1	0.0
168.5°	0.5	0.0	0.0	0.7	0.1	0.0
169°	0.5	0.0	0.0	0.7	0.1	0.0
169.5°	0.5	0.0	0.0	0.7	0.1	0.0
170°	0.5	0.0	0.0	0.7	0.1	0.0
170.5°	0.5	0.0	0.0	0.7	0.1	0.0
171°	0.5	0.0	0.0	0.6	0.1	0.0
171.5°	0.5	0.0	0.0	0.6	0.1	0.0
172°	0.5	0.0	0.0	0.6	0.1	0.0
172.5°	0.5	0.0	0.0	0.6	0.1	0.0
173°	0.5	0.0	0.0	0.6	0.1	0.0
173.5°	0.5	0.0	0.0	0.6	0.1	0.0
174°	0.5	0.0	0.0	0.6	0.1	0.0
174.5°	0.5	0.0	0.0	0.6	0.1	0.0
175°	0.5	0.0	0.0	0.6	0.1	0.0
175.5°	0.5	0.0	0.0	0.6	0.1	0.0
176°	0.5	0.0	0.0	0.6	0.1	0.0
176.5°	0.5	0.0	0.0	0.6	0.1	0.0
177°	0.5	0.0	0.0	0.6	0.1	0.0
177.5°	0.5	0.0	0.0	0.6	0.1	0.0
178°	0.5	0.0	0.0	0.6	0.1	0.0
178.5°	0.5	0.0	0.0	0.6	0.2	0.0
179°	0.5	0.0	0.0	0.6	0.2	0.0
179.5°	0.5	0.0	0.0	0.6	0.2	0.0



TEST NUMBER: P991385
CATALOG NUMBER: SMD6R07FS5-935

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)