

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: HALO

Report Number: P1175574

Luminaire Tested: HLA305FS5-2700K

Issue Date: 8/26/2025

Test Information

Test Method: LM-79-2019
Report Number: P1175574
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A2501308A001)
Test Lab: INNOVATION CENTER
Issue Date: 8/26/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: HLA305FS5-2700K
Description: HLA SUPER ADJUSTABLE GIMBAL 3 inch at 2700K CCT

Light Source:
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 585.0 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.35
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 6.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: >0.9
Total Harmonic Distortion (THDi): <20
Frequency (hertz): 60
Stabilization Time: HR
Operation Time: HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1175574
CATALOG NUMBER: HLA305FS5-2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	109	104	100	96	106	102	98	95		98	94	92		94	91	89		90	88	86
2	99	91	84	78	96	89	83	77		85	80	76		82	78	74		79	75	72
3	90	80	72	65	88	78	71	65		75	69	63		72	67	62		70	65	61
4	83	71	62	55	80	69	61	55		67	60	54		64	58	53		62	57	53
5	76	63	54	48	74	62	54	47		60	52	47		58	51	46		56	50	46
6	70	57	48	41	68	56	47	41		54	47	41		52	46	41		51	45	40
7	65	52	43	37	63	51	42	37		49	42	36		48	41	36		46	40	36
8	61	47	39	33	59	46	38	33		45	38	32		44	37	32		43	37	32
9	57	43	35	29	55	43	35	29		41	34	29		40	34	29		39	33	29
10	53	40	32	27	52	39	32	27		38	31	26		37	31	26		36	31	26

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	46444	46444	46444	46444
5°	46423	46247	46335	46423
10°	46269	45958	46091	46314
15°	45971	45562	45766	46107
20°	45644	45084	45341	45784
25°	45196	44519	44833	45366
30°	44716	43855	44209	44944
35°	44142	43125	43500	44464
40°	43510	42308	42737	43968
45°	42826	41369	41865	43353
50°	42028	40323	40834	42643
55°	41136	39071	39645	41748
60°	39953	37541	38199	40655
65°	38448	35438	36268	39226
70°	36288	32570	33467	37186
75°	33212	28213	29314	34313
80°	28665	21594	23109	30181
85°	22392	11322	13838	24908

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 292.5°

Vertical Angle: 89.5°

Luminance: 90461 cd/sqm

TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.0	3.4
10°-20°	57.0	9.7
20°-30°	85.7	14.6
30°-40°	102.4	17.5
40°-50°	105.4	18.0
50°-60°	94.4	16.1
60°-70°	71.2	12.2
70°-80°	39.1	6.7
80°-90°	9.2	1.6
90°-100°	0.2	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.1	0.0
130°-140°	0.1	0.0
140°-150°	0.1	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	162.7	27.8
0°-40°	265.1	45.3
0°-60°	464.9	79.5
0°-90°	584.5	99.9
90°-120°	0.2	0.0
90°-150°	0.4	0.1
90°-180°	1.0	0.2
0°-180°	585.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	212	212	212	212	212	
5°	211	210	210	211	211	20
15°	202	201	202	203	202	57
25°	187	184	185	188	187	86
35°	165	161	162	166	165	103
45°	138	133	135	140	138	107
55°	108	102	104	109	108	96
65°	74	68	70	76	74	73
75°	39	33	35	40	39	42
85°	9	4	6	10	9	10
90°	2	0	0	3	2	1
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	211.8	211.8	211.8	211.8	211.8	211.8	211.8	211.8	211.8	211.8	211.8
0.5°	211.7	211.9	211.7	211.9	211.6	211.6	211.6	211.8	211.7	211.8	211.8
1°	211.7	211.8	211.8	211.7	211.5	211.5	211.7	211.7	211.6	211.7	211.9
1.5°	211.7	211.6	211.7	211.6	211.3	211.4	211.7	211.5	211.6	211.7	211.8
2°	211.7	211.6	211.7	211.6	211.2	211.3	211.5	211.4	211.5	211.6	211.7
2.5°	211.6	211.5	211.5	211.5	211.1	211.1	211.3	211.3	211.4	211.6	211.6
3°	211.5	211.4	211.3	211.4	211.0	210.9	211.1	211.2	211.3	211.5	211.5
3.5°	211.3	211.3	211.2	211.2	210.8	210.6	210.9	211.0	211.1	211.3	211.5
4°	211.1	211.0	211.0	211.0	210.6	210.5	210.7	210.8	210.9	211.0	211.4
4.5°	211.0	210.8	210.9	210.8	210.3	210.3	210.5	210.5	210.7	210.8	211.2
5°	210.9	210.6	210.7	210.6	210.1	210.0	210.2	210.2	210.5	210.6	210.9
5.5°	210.6	210.4	210.3	210.3	209.8	209.7	209.9	210.0	210.3	210.4	210.7
6°	210.4	210.2	210.1	210.0	209.5	209.3	209.6	209.8	210.0	210.2	210.4
6.5°	210.1	209.9	209.8	209.7	209.2	209.1	209.2	209.5	209.7	209.9	210.2
7°	209.8	209.6	209.5	209.3	208.9	208.7	208.9	209.2	209.4	209.6	209.8
7.5°	209.5	209.4	209.1	209.0	208.5	208.3	208.6	208.8	209.0	209.3	209.5
8°	209.2	209.0	208.8	208.7	208.1	207.9	208.2	208.4	208.7	209.0	209.2
8.5°	208.9	208.6	208.4	208.3	207.7	207.5	207.8	207.9	208.3	208.7	208.9
9°	208.5	208.2	208.0	207.8	207.3	207.1	207.4	207.5	207.9	208.3	208.6
9.5°	208.1	207.9	207.5	207.4	206.9	206.6	206.9	207.1	207.5	207.9	208.2
10°	207.8	207.5	207.1	207.0	206.4	206.1	206.4	206.7	207.0	207.4	207.8
10.5°	207.3	207.0	206.7	206.5	206.0	205.6	205.9	206.3	206.5	207.0	207.3
11°	206.9	206.5	206.2	206.1	205.4	205.2	205.4	205.7	206.1	206.5	206.9
11.5°	206.4	206.0	205.7	205.5	204.9	204.7	205.0	205.2	205.7	206.1	206.5
12°	205.9	205.5	205.2	205.0	204.4	204.1	204.4	204.7	205.2	205.5	206.0
12.5°	205.4	205.0	204.6	204.5	203.9	203.5	203.8	204.2	204.6	205.0	205.5
13°	204.9	204.4	204.1	203.9	203.3	202.8	203.2	203.6	204.0	204.4	204.9
13.5°	204.4	203.9	203.5	203.3	202.6	202.2	202.6	203.0	203.5	203.9	204.4
14°	203.8	203.3	202.9	202.7	202.0	201.7	202.0	202.4	202.9	203.3	203.7
14.5°	203.2	202.7	202.3	202.1	201.4	201.1	201.3	201.7	202.3	202.7	203.2
15°	202.5	202.1	201.7	201.5	200.7	200.3	200.6	201.1	201.6	202.1	202.6
15.5°	201.9	201.5	201.0	200.9	200.1	199.6	200.0	200.4	201.0	201.5	202.0
16°	201.3	200.9	200.3	200.1	199.4	198.9	199.3	199.7	200.4	200.8	201.3
16.5°	200.7	200.2	199.7	199.4	198.7	198.2	198.6	199.1	199.7	200.2	200.7
17°	200.1	199.4	199.0	198.8	198.0	197.5	197.9	198.4	198.9	199.4	200.0
17.5°	199.4	198.7	198.2	198.1	197.3	196.7	197.1	197.6	198.1	198.7	199.3
18°	198.6	198.0	197.5	197.3	196.5	195.9	196.3	196.8	197.4	198.0	198.6
18.5°	197.7	197.3	196.7	196.5	195.6	195.1	195.5	196.1	196.6	197.3	197.8
19°	197.1	196.6	196.0	195.7	194.9	194.3	194.7	195.3	195.9	196.5	197.1
19.5°	196.4	195.8	195.2	194.8	194.1	193.5	193.9	194.5	195.2	195.7	196.3
20°	195.6	194.9	194.4	194.0	193.2	192.7	193.1	193.7	194.3	194.9	195.6
20.5°	194.8	194.1	193.6	193.2	192.3	191.8	192.2	192.8	193.4	194.1	194.8
21°	193.9	193.3	192.7	192.4	191.5	190.9	191.3	192.0	192.5	193.3	193.9
21.5°	193.1	192.4	191.8	191.5	190.6	190.0	190.4	191.0	191.7	192.4	193.1
22°	192.2	191.6	190.9	190.6	189.8	189.1	189.5	190.2	190.8	191.5	192.3

TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	191.4	190.7	190.0	189.7	188.9	188.1	188.6	189.3	190.0	190.7	191.4
23°	190.6	189.7	189.2	188.8	188.0	187.2	187.7	188.4	189.1	189.7	190.5
23.5°	189.7	188.8	188.3	187.9	187.0	186.3	186.7	187.4	188.2	188.8	189.6
24°	188.7	187.9	187.3	186.9	186.0	185.3	185.7	186.4	187.2	187.9	188.6
24.5°	187.7	187.0	186.3	185.9	185.0	184.3	184.8	185.4	186.2	187.0	187.7
25°	186.8	186.0	185.3	185.0	184.0	183.2	183.7	184.4	185.3	186.0	186.7
25.5°	185.9	185.1	184.3	184.0	183.0	182.2	182.7	183.4	184.3	185.1	185.7
26°	185.0	184.2	183.4	182.9	182.0	181.2	181.6	182.4	183.2	184.0	184.7
26.5°	184.0	183.1	182.4	181.8	180.9	180.2	180.6	181.3	182.2	183.0	183.8
27°	182.9	182.0	181.4	180.8	179.9	179.2	179.6	180.3	181.1	182.0	182.8
27.5°	181.8	181.0	180.3	179.7	178.8	178.0	178.5	179.2	180.1	181.0	181.8
28°	180.8	179.9	179.2	178.7	177.7	176.9	177.5	178.2	179.0	179.9	180.7
28.5°	179.8	178.8	178.1	177.7	176.6	175.8	176.3	177.1	177.9	178.8	179.6
29°	178.8	177.8	177.0	176.5	175.5	174.7	175.2	175.9	176.8	177.7	178.5
29.5°	177.7	176.7	175.9	175.3	174.3	173.6	174.1	174.7	175.7	176.6	177.4
30°	176.6	175.6	174.8	174.2	173.2	172.4	172.9	173.6	174.6	175.4	176.3
30.5°	175.4	174.5	173.7	173.1	172.0	171.2	171.8	172.5	173.5	174.4	175.2
31°	174.3	173.4	172.6	172.0	170.9	170.0	170.6	171.3	172.3	173.2	174.1
31.5°	173.2	172.2	171.4	170.9	169.7	168.8	169.4	170.1	171.0	172.0	172.9
32°	172.0	171.0	170.1	169.7	168.5	167.7	168.2	168.9	169.9	170.9	171.8
32.5°	170.8	169.8	168.9	168.4	167.3	166.4	166.9	167.7	168.7	169.7	170.6
33°	169.7	168.7	167.8	167.2	166.1	165.1	165.7	166.5	167.5	168.5	169.4
33.5°	168.5	167.5	166.5	166.0	164.8	163.9	164.4	165.3	166.3	167.3	168.2
34°	167.3	166.3	165.4	164.8	163.6	162.6	163.2	164.0	165.1	166.1	167.0
34.5°	166.1	165.1	164.1	163.5	162.4	161.4	162.0	162.8	163.8	164.8	165.8
35°	164.9	163.8	162.8	162.2	161.1	160.1	160.7	161.5	162.5	163.6	164.6
35.5°	163.6	162.5	161.6	160.9	159.9	158.8	159.4	160.2	161.2	162.4	163.3
36°	162.3	161.3	160.3	159.7	158.5	157.5	158.1	159.0	160.0	161.1	162.1
36.5°	161.1	160.0	159.1	158.4	157.2	156.2	156.8	157.6	158.7	159.8	160.8
37°	159.8	158.7	157.8	157.1	155.9	154.9	155.5	156.3	157.3	158.4	159.6
37.5°	158.6	157.4	156.4	155.8	154.6	153.6	154.1	154.9	156.0	157.2	158.3
38°	157.3	156.0	155.2	154.5	153.2	152.2	152.7	153.6	154.7	155.8	157.0
38.5°	156.0	154.8	153.8	153.1	151.8	150.8	151.4	152.3	153.4	154.6	155.8
39°	154.7	153.5	152.4	151.8	150.5	149.5	150.0	150.9	152.0	153.2	154.5
39.5°	153.4	152.1	151.1	150.4	149.1	148.1	148.7	149.5	150.7	151.9	153.1
40°	152.0	150.7	149.6	149.0	147.8	146.6	147.2	148.1	149.3	150.5	151.7
40.5°	150.7	149.4	148.3	147.6	146.4	145.3	145.8	146.7	147.9	149.1	150.4
41°	149.3	148.0	147.0	146.2	145.0	143.8	144.4	145.3	146.5	147.7	149.0
41.5°	148.0	146.6	145.6	144.9	143.6	142.4	143.0	143.9	145.1	146.3	147.6
42°	146.6	145.2	144.2	143.5	142.1	141.0	141.6	142.5	143.6	144.9	146.2
42.5°	145.2	143.8	142.7	142.1	140.7	139.6	140.1	141.1	142.2	143.5	144.8
43°	143.8	142.4	141.3	140.6	139.3	138.1	138.7	139.6	140.9	142.1	143.4
43.5°	142.4	141.0	139.9	139.1	137.9	136.6	137.2	138.2	139.4	140.7	142.0
44°	141.0	139.6	138.5	137.7	136.4	135.1	135.7	136.7	137.9	139.2	140.6
44.5°	139.5	138.1	137.0	136.2	134.9	133.7	134.2	135.2	136.4	137.7	139.1

TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	138.1	136.6	135.5	134.8	133.4	132.2	132.8	133.7	135.0	136.3	137.7
45.5°	136.7	135.2	134.1	133.3	131.9	130.7	131.3	132.3	133.5	134.9	136.2
46°	135.2	133.8	132.6	131.8	130.5	129.3	129.8	130.8	132.0	133.4	134.8
46.5°	133.7	132.3	131.1	130.3	129.0	127.7	128.3	129.3	130.5	131.9	133.3
47°	132.2	130.8	129.7	128.8	127.5	126.2	126.7	127.7	128.9	130.4	131.8
47.5°	130.8	129.3	128.1	127.3	125.9	124.7	125.2	126.2	127.5	128.9	130.3
48°	129.3	127.8	126.6	125.8	124.4	123.1	123.7	124.7	126.0	127.4	128.8
48.5°	127.8	126.3	125.0	124.3	122.8	121.5	122.1	123.1	124.4	125.9	127.3
49°	126.3	124.8	123.5	122.8	121.3	120.0	120.6	121.6	122.9	124.3	125.8
49.5°	124.7	123.3	122.0	121.2	119.7	118.4	119.0	120.1	121.3	122.7	124.2
50°	123.2	121.7	120.5	119.6	118.2	116.8	117.4	118.4	119.7	121.2	122.6
50.5°	121.6	120.2	118.9	118.0	116.6	115.3	115.8	116.9	118.2	119.7	121.0
51°	120.1	118.6	117.3	116.5	115.1	113.7	114.3	115.3	116.7	118.1	119.5
51.5°	118.6	117.1	115.7	114.9	113.5	112.1	112.7	113.7	115.1	116.5	118.0
52°	117.1	115.5	114.2	113.4	111.9	110.5	111.0	112.1	113.4	114.9	116.4
52.5°	115.5	113.9	112.7	111.8	110.3	108.9	109.4	110.5	111.8	113.3	114.8
53°	113.9	112.3	111.1	110.2	108.7	107.3	107.9	108.9	110.2	111.8	113.2
53.5°	112.3	110.8	109.5	108.6	107.0	105.7	106.3	107.3	108.6	110.2	111.5
54°	110.7	109.2	107.8	107.0	105.5	104.0	104.6	105.7	107.0	108.6	109.9
54.5°	109.1	107.6	106.3	105.4	103.8	102.4	103.0	104.0	105.4	107.0	108.4
55°	107.6	106.0	104.6	103.7	102.2	100.8	101.3	102.4	103.7	105.3	106.8
55.5°	106.0	104.3	103.0	102.1	100.6	99.1	99.7	100.8	102.1	103.6	105.1
56°	104.3	102.7	101.4	100.4	98.9	97.5	98.0	99.1	100.5	102.0	103.5
56.5°	102.6	101.1	99.7	98.8	97.3	95.8	96.4	97.5	98.8	100.3	101.8
57°	101.0	99.4	98.1	97.2	95.6	94.1	94.7	95.7	97.1	98.7	100.2
57.5°	99.4	97.8	96.4	95.5	94.0	92.4	93.0	94.1	95.5	97.1	98.5
58°	97.7	96.2	94.8	93.8	92.4	90.8	91.4	92.5	93.8	95.4	96.9
58.5°	96.1	94.5	93.1	92.1	90.7	89.1	89.7	90.8	92.2	93.7	95.2
59°	94.4	92.9	91.4	90.4	89.0	87.4	88.0	89.1	90.5	92.1	93.5
59.5°	92.8	91.1	89.8	88.8	87.3	85.8	86.3	87.4	88.8	90.4	91.9
60°	91.1	89.4	88.1	87.1	85.6	84.1	84.6	85.7	87.1	88.7	90.2
60.5°	89.4	87.8	86.4	85.4	83.9	82.4	82.9	84.1	85.4	86.9	88.5
61°	87.7	86.2	84.7	83.7	82.2	80.7	81.2	82.4	83.7	85.2	86.8
61.5°	86.0	84.4	83.0	82.0	80.5	79.0	79.5	80.7	82.1	83.5	85.2
62°	84.4	82.7	81.3	80.3	78.8	77.2	77.8	78.9	80.3	81.9	83.5
62.5°	82.6	81.0	79.6	78.5	77.1	75.4	76.0	77.1	78.5	80.2	81.7
63°	80.8	79.3	77.9	76.8	75.3	73.7	74.2	75.4	76.8	78.5	80.0
63.5°	79.2	77.6	76.2	75.1	73.6	72.0	72.5	73.7	75.2	76.7	78.3
64°	77.5	75.9	74.4	73.4	71.8	70.2	70.8	71.9	73.4	75.0	76.5
64.5°	75.8	74.2	72.7	71.7	70.1	68.5	69.0	70.1	71.7	73.3	74.8
65°	74.1	72.5	71.0	69.9	68.3	66.7	67.2	68.4	69.9	71.5	73.1
65.5°	72.4	70.7	69.2	68.2	66.6	65.0	65.5	66.6	68.1	69.7	71.3
66°	70.6	68.9	67.5	66.4	64.8	63.2	63.7	64.9	66.4	68.0	69.5
66.5°	68.8	67.2	65.7	64.7	63.1	61.4	61.9	63.1	64.6	66.2	67.8
67°	67.1	65.5	64.0	62.9	61.3	59.7	60.2	61.4	62.8	64.5	66.0

TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	65.4	63.7	62.2	61.1	59.6	57.9	58.4	59.6	61.1	62.7	64.3
68°	63.7	62.0	60.5	59.4	57.8	56.1	56.6	57.8	59.3	60.9	62.5
68.5°	61.9	60.2	58.8	57.7	56.0	54.3	54.9	56.0	57.5	59.1	60.7
69°	60.1	58.5	57.0	55.9	54.3	52.6	53.1	54.3	55.7	57.4	58.9
69.5°	58.4	56.7	55.2	54.1	52.5	50.8	51.3	52.4	53.9	55.6	57.2
70°	56.6	55.0	53.5	52.3	50.8	49.0	49.5	50.7	52.2	53.8	55.4
70.5°	54.9	53.2	51.7	50.6	49.0	47.2	47.7	48.9	50.4	52.1	53.6
71°	53.2	51.5	50.0	48.8	47.2	45.5	46.0	47.2	48.7	50.3	51.9
71.5°	51.4	49.7	48.1	47.1	45.4	43.7	44.3	45.4	46.9	48.5	50.1
72°	49.6	48.0	46.5	45.4	43.7	42.0	42.5	43.6	45.1	46.8	48.4
72.5°	47.9	46.3	44.7	43.6	41.9	40.2	40.7	41.9	43.3	45.0	46.6
73°	46.1	44.5	43.0	41.8	40.2	38.4	38.9	40.1	41.6	43.3	44.8
73.5°	44.4	42.7	41.2	40.1	38.4	36.7	37.2	38.4	39.8	41.5	43.0
74°	42.7	41.0	39.5	38.5	36.7	35.0	35.5	36.7	38.1	39.7	41.3
74.5°	41.0	39.3	37.8	36.8	35.0	33.3	33.7	34.9	36.4	38.0	39.6
75°	39.2	37.6	36.1	35.1	33.3	31.6	32.1	33.2	34.6	36.3	37.8
75.5°	37.6	36.0	34.4	33.4	31.6	29.9	30.4	31.5	32.9	34.6	36.1
76°	35.9	34.3	32.8	31.6	29.9	28.2	28.7	29.8	31.2	32.8	34.4
76.5°	34.2	32.6	31.1	30.0	28.2	26.6	27.0	28.1	29.6	31.1	32.7
77°	32.6	30.9	29.4	28.3	26.6	24.9	25.4	26.5	27.9	29.5	31.0
77.5°	30.9	29.3	27.8	26.6	25.0	23.3	23.8	24.8	26.2	27.8	29.3
78°	29.2	27.6	26.1	25.0	23.3	21.7	22.2	23.2	24.6	26.2	27.6
78.5°	27.6	26.0	24.5	23.4	21.7	20.1	20.6	21.6	23.0	24.5	26.0
79°	25.9	24.4	22.9	21.8	20.1	18.6	19.0	20.0	21.4	22.9	24.4
79.5°	24.3	22.8	21.3	20.2	18.6	17.1	17.5	18.5	19.8	21.4	22.8
80°	22.7	21.2	19.8	18.7	17.1	15.6	16.0	17.0	18.3	19.8	21.3
80.5°	21.2	19.7	18.2	17.2	15.6	14.2	14.5	15.5	16.8	18.3	19.7
81°	19.6	18.2	16.8	15.7	14.2	12.8	13.1	14.1	15.4	16.8	18.2
81.5°	18.2	16.7	15.3	14.3	12.8	11.4	11.7	12.7	14.0	15.4	16.7
82°	16.7	15.2	13.9	12.9	11.4	10.2	10.6	11.4	12.6	13.9	15.3
82.5°	15.3	13.9	12.5	11.5	10.2	9.0	9.4	10.2	11.3	12.6	13.9
83°	13.9	12.5	11.2	10.2	9.1	7.9	8.2	9.0	10.1	11.3	12.6
83.5°	12.6	11.2	9.9	9.0	7.9	6.7	7.0	7.8	8.9	10.1	11.3
84°	11.2	9.9	8.7	7.8	6.7	5.5	5.8	6.7	7.8	9.0	10.2
84.5°	10.0	8.7	7.6	6.7	5.5	4.5	4.8	5.5	6.6	7.9	9.0
85°	8.9	7.6	6.5	5.6	4.5	3.6	3.9	4.5	5.5	6.7	7.9
85.5°	7.8	6.6	5.4	4.7	3.6	2.9	3.1	3.7	4.5	5.6	6.8
86°	6.7	5.6	4.5	3.8	2.9	2.2	2.4	2.9	3.7	4.7	5.7
86.5°	5.8	4.7	3.7	3.1	2.2	1.6	1.8	2.2	3.0	3.9	4.9
87°	4.9	3.8	3.1	2.5	1.6	1.0	1.2	1.7	2.3	3.2	4.1
87.5°	4.1	3.3	2.5	1.9	1.1	0.5	0.7	1.2	1.8	2.6	3.4
88°	3.6	2.8	1.9	1.3	0.7	0.1	0.3	0.8	1.3	2.1	2.9
88.5°	3.1	2.2	1.4	0.9	0.2	0.0	0.1	0.5	1.0	1.7	2.4
89°	2.6	1.7	1.0	0.5	0.0	0.0	0.0	0.3	0.8	1.4	2.1
89.5°	2.1	1.4	0.7	0.1	0.0	0.0	0.0	0.1	0.6	1.1	1.8

TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	1.7	1.0	0.2	0.0	0.0	0.0	0.0	0.0	0.3	0.9	1.5
90.5°	1.3	0.5	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.5	1.2
91°	0.8	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.2	0.8
91.5°	0.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.3
92°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0
122°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0
122.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0
123°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
123.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
124°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
124.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
125°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
125.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
126°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
126.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
127°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
127.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
128°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
128.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
129°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
129.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
130°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
130.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
131°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
131.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
133°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
133.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
134°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
134.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1

TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
136°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
136.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
138°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
138.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
139°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
139.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
140.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
141°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
141.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
143°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
143.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
144°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
144.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
145°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
145.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
146°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
146.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
147°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
147.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
148°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
148.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
149°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
149.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
150°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
150.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
151°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
151.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
152°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
152.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
153°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
153.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
154°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
154.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
155°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
155.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
156°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
156.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
157°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1

TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
158°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
158.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.1	0.1
159°	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.1
159.5°	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2
160°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
160.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
161°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
161.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
162°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
162.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
163°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
163.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
164°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
164.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
165°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
165.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
166°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
166.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
167°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
167.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
168°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
168.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
169°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
169.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.1
170°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.1
170.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.1	0.1	0.1
171°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.1	0.1	0.1	0.1
171.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
172°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
172.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
173°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
173.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
174°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
174.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
175.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
176°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
176.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
178°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
178.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
179°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
179.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1

TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	211.8	211.8	211.8	211.8	211.8	211.8
0.5°	212.0	211.7	211.8	211.8	211.8	211.7
1°	211.9	211.7	211.8	211.9	211.8	211.7
1.5°	211.9	211.6	211.8	211.9	211.8	211.7
2°	211.8	211.6	211.7	211.8	211.7	211.7
2.5°	211.7	211.5	211.7	211.8	211.6	211.6
3°	211.6	211.5	211.7	211.7	211.6	211.5
3.5°	211.5	211.4	211.6	211.6	211.5	211.3
4°	211.5	211.2	211.5	211.5	211.4	211.1
4.5°	211.3	211.1	211.3	211.4	211.2	211.0
5°	211.1	210.9	211.2	211.2	211.0	210.9
5.5°	210.8	210.7	211.0	211.0	210.8	210.6
6°	210.6	210.4	210.8	210.8	210.6	210.4
6.5°	210.4	210.2	210.5	210.5	210.4	210.1
7°	210.1	210.0	210.2	210.2	210.1	209.8
7.5°	209.8	209.8	210.0	210.1	209.8	209.5
8°	209.5	209.4	209.7	209.8	209.5	209.2
8.5°	209.1	209.1	209.5	209.5	209.1	208.9
9°	208.8	208.7	209.2	209.1	208.8	208.5
9.5°	208.4	208.4	208.8	208.7	208.5	208.1
10°	208.0	208.0	208.4	208.4	208.1	207.8
10.5°	207.6	207.6	208.0	208.0	207.7	207.3
11°	207.2	207.1	207.6	207.5	207.2	206.9
11.5°	206.7	206.6	207.2	207.1	206.8	206.4
12°	206.2	206.2	206.7	206.7	206.3	205.9
12.5°	205.7	205.8	206.3	206.2	205.9	205.4
13°	205.2	205.3	205.8	205.7	205.3	204.9
13.5°	204.7	204.8	205.3	205.2	204.8	204.4
14°	204.2	204.2	204.8	204.7	204.3	203.8
14.5°	203.5	203.6	204.1	204.1	203.7	203.2
15°	203.0	203.1	203.5	203.5	203.1	202.5
15.5°	202.3	202.4	203.1	203.0	202.5	201.9
16°	201.7	201.8	202.5	202.4	201.8	201.3
16.5°	201.0	201.2	201.9	201.7	201.2	200.7
17°	200.4	200.6	201.2	201.0	200.6	200.1
17.5°	199.7	199.8	200.5	200.3	199.9	199.4
18°	199.0	199.1	199.8	199.7	199.2	198.6
18.5°	198.2	198.5	199.1	199.0	198.4	197.7
19°	197.6	197.8	198.4	198.3	197.8	197.1
19.5°	196.9	197.0	197.7	197.6	197.1	196.4
20°	196.0	196.2	196.9	196.8	196.3	195.6
20.5°	195.1	195.4	196.2	196.0	195.4	194.8
21°	194.3	194.6	195.4	195.2	194.6	193.9
21.5°	193.5	193.8	194.6	194.3	193.8	193.1
22°	192.7	192.9	193.7	193.5	193.0	192.2

TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	191.9	192.1	192.9	192.7	192.2	191.4
23°	190.9	191.2	192.0	191.9	191.3	190.6
23.5°	190.0	190.4	191.2	191.0	190.4	189.7
24°	189.0	189.5	190.3	190.1	189.4	188.7
24.5°	188.1	188.6	189.4	189.2	188.5	187.7
25°	187.2	187.5	188.5	188.3	187.6	186.8
25.5°	186.2	186.6	187.5	187.3	186.6	185.9
26°	185.2	185.6	186.6	186.3	185.7	185.0
26.5°	184.2	184.7	185.6	185.3	184.7	184.0
27°	183.3	183.8	184.6	184.4	183.7	182.9
27.5°	182.2	182.7	183.7	183.4	182.7	181.8
28°	181.2	181.6	182.6	182.3	181.7	180.8
28.5°	180.1	180.6	181.6	181.4	180.6	179.8
29°	179.0	179.5	180.6	180.3	179.5	178.8
29.5°	178.0	178.5	179.6	179.3	178.5	177.7
30°	177.0	177.5	178.5	178.1	177.4	176.6
30.5°	175.9	176.4	177.5	177.1	176.3	175.4
31°	174.7	175.3	176.4	176.0	175.2	174.3
31.5°	173.6	174.2	175.3	174.9	174.1	173.2
32°	172.5	173.1	174.1	173.8	172.9	172.0
32.5°	171.3	171.9	173.0	172.7	171.8	170.8
33°	170.1	170.8	171.9	171.5	170.6	169.7
33.5°	168.9	169.7	170.8	170.4	169.5	168.5
34°	167.8	168.5	169.6	169.2	168.3	167.3
34.5°	166.6	167.3	168.4	168.1	167.2	166.1
35°	165.3	166.1	167.3	166.9	165.9	164.9
35.5°	164.1	164.9	166.1	165.7	164.7	163.6
36°	162.9	163.7	164.9	164.5	163.5	162.3
36.5°	161.7	162.5	163.7	163.3	162.3	161.1
37°	160.4	161.2	162.5	162.1	161.0	159.8
37.5°	159.2	160.0	161.2	160.8	159.9	158.6
38°	157.9	158.8	160.0	159.6	158.6	157.3
38.5°	156.7	157.5	158.8	158.3	157.3	156.0
39°	155.4	156.3	157.5	157.0	156.0	154.7
39.5°	154.0	154.9	156.3	155.8	154.7	153.4
40°	152.7	153.6	155.0	154.5	153.3	152.0
40.5°	151.4	152.3	153.6	153.1	151.9	150.7
41°	150.0	151.0	152.3	151.8	150.7	149.3
41.5°	148.6	149.7	151.0	150.5	149.3	148.0
42°	147.2	148.3	149.7	149.1	148.0	146.6
42.5°	145.8	146.9	148.3	147.7	146.6	145.2
43°	144.4	145.5	146.9	146.4	145.1	143.8
43.5°	143.0	144.1	145.5	145.0	143.7	142.4
44°	141.6	142.6	144.1	143.6	142.3	141.0
44.5°	140.2	141.2	142.7	142.1	140.9	139.5

TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	138.7	139.8	141.2	140.7	139.5	138.1
45.5°	137.3	138.4	139.8	139.3	138.0	136.7
46°	135.8	137.0	138.4	137.8	136.6	135.2
46.5°	134.3	135.4	136.9	136.4	135.1	133.7
47°	132.9	134.0	135.4	134.9	133.7	132.2
47.5°	131.4	132.5	134.0	133.4	132.2	130.8
48°	129.9	131.0	132.4	131.9	130.7	129.3
48.5°	128.3	129.5	131.0	130.4	129.2	127.8
49°	126.8	128.0	129.5	128.9	127.7	126.3
49.5°	125.3	126.5	128.0	127.4	126.2	124.7
50°	123.7	125.0	126.5	126.0	124.7	123.2
50.5°	122.2	123.4	124.9	124.4	123.2	121.6
51°	120.6	121.9	123.4	122.8	121.6	120.1
51.5°	119.0	120.3	121.9	121.3	120.0	118.6
52°	117.5	118.8	120.3	119.7	118.5	117.1
52.5°	115.9	117.2	118.7	118.2	116.9	115.5
53°	114.3	115.6	117.2	116.6	115.4	113.9
53.5°	112.7	113.9	115.5	115.0	113.8	112.3
54°	111.1	112.4	114.0	113.4	112.2	110.7
54.5°	109.5	110.8	112.4	111.8	110.6	109.1
55°	107.8	109.2	110.8	110.3	109.0	107.6
55.5°	106.3	107.5	109.2	108.7	107.4	106.0
56°	104.6	106.0	107.6	107.0	105.8	104.3
56.5°	103.0	104.3	105.9	105.4	104.1	102.6
57°	101.3	102.7	104.2	103.7	102.5	101.0
57.5°	99.6	101.0	102.6	102.1	100.9	99.4
58°	98.0	99.3	101.0	100.5	99.2	97.7
58.5°	96.3	97.7	99.4	98.9	97.6	96.1
59°	94.7	96.1	97.7	97.2	95.9	94.4
59.5°	93.0	94.4	96.0	95.5	94.2	92.8
60°	91.3	92.7	94.3	93.8	92.6	91.1
60.5°	89.6	91.0	92.7	92.2	90.9	89.4
61°	87.9	89.3	90.9	90.5	89.2	87.7
61.5°	86.2	87.6	89.3	88.8	87.5	86.0
62°	84.5	85.9	87.6	87.1	85.9	84.4
62.5°	82.9	84.2	85.9	85.4	84.2	82.6
63°	81.1	82.4	84.1	83.7	82.4	80.8
63.5°	79.4	80.7	82.4	82.0	80.7	79.2
64°	77.7	79.0	80.8	80.3	79.1	77.5
64.5°	76.0	77.3	79.0	78.5	77.3	75.8
65°	74.2	75.6	77.3	76.8	75.6	74.1
65.5°	72.5	73.8	75.5	75.1	73.8	72.4
66°	70.7	72.0	73.8	73.3	72.1	70.6
66.5°	68.9	70.3	72.1	71.6	70.4	68.8
67°	67.2	68.5	70.3	69.9	68.7	67.1

TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	65.4	66.8	68.6	68.1	66.9	65.4
68°	63.6	65.1	66.8	66.4	65.2	63.7
68.5°	61.9	63.3	65.1	64.6	63.4	61.9
69°	60.1	61.5	63.3	62.9	61.7	60.1
69.5°	58.4	59.7	61.6	61.1	59.9	58.4
70°	56.6	58.0	59.8	59.4	58.2	56.6
70.5°	54.8	56.2	58.0	57.6	56.4	54.9
71°	53.0	54.4	56.3	55.8	54.7	53.2
71.5°	51.3	52.8	54.5	54.1	52.9	51.4
72°	49.5	51.0	52.8	52.4	51.1	49.6
72.5°	47.8	49.2	51.0	50.6	49.4	47.9
73°	45.9	47.4	49.3	48.9	47.6	46.1
73.5°	44.2	45.7	47.5	47.1	45.9	44.4
74°	42.4	44.0	45.8	45.4	44.1	42.7
74.5°	40.7	42.2	44.0	43.6	42.5	41.0
75°	39.0	40.5	42.3	41.9	40.7	39.2
75.5°	37.3	38.8	40.6	40.2	39.1	37.6
76°	35.5	37.1	38.9	38.3	37.4	35.9
76.5°	33.8	35.4	37.2	36.6	35.7	34.2
77°	32.1	33.8	35.5	35.0	34.0	32.6
77.5°	30.5	32.1	33.9	33.4	32.4	30.9
78°	28.8	30.5	32.2	31.8	30.7	29.2
78.5°	27.2	28.8	30.5	30.1	29.0	27.6
79°	25.5	27.2	28.9	28.5	27.3	25.9
79.5°	23.9	25.5	27.2	26.9	25.8	24.3
80°	22.3	23.9	25.6	25.3	24.2	22.7
80.5°	20.8	22.4	24.0	23.6	22.5	21.2
81°	19.3	20.9	22.5	22.1	21.0	19.6
81.5°	17.8	19.3	20.9	20.6	19.5	18.2
82°	16.3	17.8	19.4	19.1	18.0	16.7
82.5°	14.9	16.4	17.9	17.6	16.6	15.3
83°	13.6	15.0	16.5	16.2	15.2	13.9
83.5°	12.3	13.7	15.1	14.7	13.8	12.6
84°	11.0	12.4	13.8	13.4	12.5	11.2
84.5°	9.9	11.1	12.5	12.1	11.2	10.0
85°	8.9	9.9	11.2	10.9	10.0	8.9
85.5°	7.8	8.8	10.0	9.7	8.8	7.8
86°	6.7	7.7	8.9	8.6	7.8	6.7
86.5°	5.7	6.8	7.8	7.6	6.8	5.8
87°	4.9	5.9	6.9	6.6	5.9	4.9
87.5°	4.2	5.1	6.0	5.7	5.1	4.1
88°	3.6	4.5	5.2	5.0	4.3	3.6
88.5°	3.1	3.9	4.6	4.4	3.9	3.1
89°	2.7	3.4	4.0	3.9	3.4	2.6
89.5°	2.4	3.0	3.6	3.5	3.0	2.1

TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	2.1	2.6	3.2	3.1	2.5	1.7
90.5°	1.8	2.2	2.8	2.6	2.1	1.3
91°	1.4	1.8	2.4	2.2	1.6	0.8
91.5°	0.8	1.4	2.0	1.7	1.1	0.4
92°	0.4	0.9	1.4	1.1	0.5	0.1
92.5°	0.2	0.4	0.8	0.6	0.2	0.0
93°	0.0	0.1	0.4	0.2	0.0	0.0
93.5°	0.0	0.0	0.1	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.1
118.5°	0.0	0.0	0.0	0.0	0.1	0.1
119°	0.0	0.1	0.0	0.1	0.1	0.1
119.5°	0.0	0.1	0.1	0.1	0.1	0.1
120°	0.0	0.1	0.1	0.1	0.1	0.1
120.5°	0.0	0.1	0.1	0.1	0.1	0.1
121°	0.0	0.1	0.1	0.1	0.1	0.1
121.5°	0.0	0.1	0.1	0.1	0.1	0.1
122°	0.0	0.1	0.1	0.1	0.1	0.1
122.5°	0.0	0.1	0.1	0.1	0.1	0.1
123°	0.1	0.1	0.1	0.1	0.1	0.1
123.5°	0.1	0.1	0.1	0.1	0.1	0.1
124°	0.1	0.1	0.1	0.1	0.1	0.1
124.5°	0.1	0.1	0.1	0.1	0.1	0.1
125°	0.1	0.1	0.1	0.1	0.1	0.1
125.5°	0.1	0.1	0.1	0.1	0.1	0.1
126°	0.1	0.1	0.1	0.1	0.1	0.1
126.5°	0.1	0.1	0.1	0.1	0.1	0.1
127°	0.1	0.1	0.1	0.1	0.1	0.1
127.5°	0.1	0.1	0.1	0.1	0.1	0.1
128°	0.1	0.1	0.1	0.1	0.1	0.1
128.5°	0.1	0.1	0.1	0.1	0.1	0.1
129°	0.1	0.1	0.1	0.1	0.1	0.1
129.5°	0.1	0.1	0.1	0.1	0.1	0.1
130°	0.1	0.1	0.1	0.1	0.1	0.1
130.5°	0.1	0.1	0.1	0.1	0.1	0.1
131°	0.1	0.1	0.1	0.1	0.1	0.1
131.5°	0.1	0.1	0.1	0.1	0.1	0.1
132°	0.1	0.1	0.1	0.1	0.1	0.1
132.5°	0.1	0.1	0.1	0.1	0.1	0.1
133°	0.1	0.1	0.1	0.1	0.1	0.1
133.5°	0.1	0.1	0.1	0.1	0.1	0.1
134°	0.1	0.1	0.1	0.1	0.1	0.1
134.5°	0.1	0.1	0.1	0.1	0.1	0.1

TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.1	0.1	0.1	0.1	0.1	0.1
135.5°	0.1	0.1	0.1	0.1	0.1	0.1
136°	0.1	0.1	0.1	0.1	0.1	0.1
136.5°	0.1	0.1	0.1	0.1	0.1	0.1
137°	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1
138°	0.1	0.1	0.1	0.1	0.1	0.1
138.5°	0.1	0.1	0.1	0.1	0.1	0.1
139°	0.1	0.1	0.1	0.1	0.1	0.1
139.5°	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1
140.5°	0.1	0.1	0.1	0.1	0.1	0.1
141°	0.1	0.1	0.1	0.1	0.1	0.1
141.5°	0.1	0.1	0.1	0.1	0.1	0.1
142°	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.1	0.1	0.1	0.1	0.1	0.1
143°	0.1	0.1	0.1	0.1	0.1	0.1
143.5°	0.1	0.1	0.1	0.1	0.1	0.1
144°	0.1	0.1	0.1	0.1	0.1	0.1
144.5°	0.1	0.1	0.1	0.1	0.1	0.1
145°	0.1	0.1	0.1	0.1	0.1	0.1
145.5°	0.1	0.1	0.1	0.1	0.1	0.1
146°	0.1	0.1	0.1	0.1	0.1	0.1
146.5°	0.1	0.1	0.1	0.1	0.1	0.1
147°	0.1	0.1	0.1	0.1	0.1	0.1
147.5°	0.1	0.1	0.1	0.1	0.1	0.1
148°	0.1	0.1	0.1	0.1	0.1	0.1
148.5°	0.1	0.1	0.1	0.1	0.1	0.1
149°	0.1	0.1	0.1	0.1	0.1	0.1
149.5°	0.1	0.1	0.1	0.1	0.1	0.1
150°	0.1	0.1	0.1	0.1	0.1	0.1
150.5°	0.1	0.1	0.1	0.1	0.1	0.1
151°	0.1	0.1	0.1	0.1	0.1	0.1
151.5°	0.1	0.1	0.1	0.1	0.1	0.1
152°	0.1	0.1	0.1	0.1	0.1	0.1
152.5°	0.1	0.1	0.1	0.1	0.1	0.1
153°	0.1	0.1	0.1	0.1	0.1	0.1
153.5°	0.1	0.1	0.1	0.1	0.1	0.1
154°	0.1	0.1	0.1	0.1	0.1	0.1
154.5°	0.1	0.1	0.1	0.1	0.1	0.1
155°	0.1	0.1	0.1	0.1	0.1	0.1
155.5°	0.1	0.1	0.1	0.1	0.1	0.1
156°	0.1	0.1	0.1	0.1	0.1	0.1
156.5°	0.1	0.1	0.1	0.1	0.1	0.1
157°	0.1	0.1	0.1	0.1	0.1	0.1

TEST NUMBER: P1175574

CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.1	0.1	0.1	0.1	0.1	0.1
158°	0.1	0.1	0.1	0.1	0.1	0.1
158.5°	0.1	0.1	0.1	0.1	0.1	0.1
159°	0.1	0.1	0.1	0.1	0.1	0.1
159.5°	0.2	0.1	0.1	0.1	0.1	0.1
160°	0.2	0.1	0.1	0.1	0.1	0.1
160.5°	0.2	0.1	0.1	0.1	0.1	0.1
161°	0.2	0.1	0.1	0.1	0.1	0.1
161.5°	0.2	0.1	0.1	0.1	0.1	0.1
162°	0.2	0.1	0.1	0.1	0.1	0.1
162.5°	0.2	0.1	0.1	0.1	0.1	0.1
163°	0.2	0.1	0.1	0.1	0.1	0.1
163.5°	0.2	0.1	0.1	0.1	0.1	0.1
164°	0.2	0.1	0.1	0.1	0.1	0.1
164.5°	0.2	0.1	0.1	0.1	0.1	0.1
165°	0.2	0.1	0.1	0.1	0.1	0.1
165.5°	0.2	0.1	0.1	0.1	0.1	0.1
166°	0.2	0.1	0.1	0.1	0.1	0.1
166.5°	0.2	0.1	0.1	0.1	0.1	0.1
167°	0.2	0.1	0.1	0.1	0.1	0.1
167.5°	0.2	0.1	0.1	0.1	0.1	0.1
168°	0.2	0.1	0.1	0.1	0.1	0.1
168.5°	0.2	0.1	0.1	0.1	0.1	0.1
169°	0.2	0.1	0.1	0.1	0.1	0.1
169.5°	0.2	0.1	0.1	0.1	0.1	0.1
170°	0.2	0.1	0.1	0.1	0.1	0.1
170.5°	0.1	0.1	0.1	0.1	0.1	0.1
171°	0.1	0.1	0.1	0.1	0.1	0.1
171.5°	0.1	0.1	0.1	0.1	0.1	0.1
172°	0.1	0.1	0.1	0.1	0.1	0.1
172.5°	0.1	0.1	0.1	0.1	0.1	0.1
173°	0.1	0.1	0.1	0.1	0.1	0.1
173.5°	0.1	0.1	0.1	0.1	0.1	0.1
174°	0.1	0.1	0.1	0.1	0.1	0.1
174.5°	0.1	0.1	0.1	0.1	0.1	0.1
175°	0.1	0.1	0.1	0.1	0.1	0.1
175.5°	0.1	0.1	0.1	0.1	0.1	0.1
176°	0.1	0.1	0.1	0.1	0.1	0.1
176.5°	0.1	0.1	0.1	0.1	0.1	0.1
177°	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.1	0.1	0.1	0.1	0.1	0.1
178°	0.1	0.1	0.1	0.1	0.1	0.1
178.5°	0.1	0.1	0.1	0.1	0.1	0.1
179°	0.1	0.1	0.1	0.1	0.1	0.1
179.5°	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P1175574
CATALOG NUMBER: HLA305FS5-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.1	0.1	0.1	0.1	0.1	0.1

(END OF REPORT)