

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671779

Luminaire Tested: **CCP-SA-1B-722-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671779
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1B-722-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @450mA w/ SLR
distribution lens
Light Source: (16) 2200K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2111.1 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1

Input Watts (W): 24
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 3 fc

Type IV - Short - N/A

REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	434.4	0.0	434.4
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	1676.8	0.0	1676.8
	% Fixture	79.4	0.0	79.4
Total	Lumens	2111.1	0.0	2111.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	2.5
10°-20°	110.6	5.2
20°-30°	161.8	7.7
30°-40°	228.0	10.8
40°-50°	313.3	14.8
50°-60°	427.0	20.2
60°-70°	467.3	22.1
70°-80°	269.9	12.8
80°-90°	80.9	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2111.1	100.0
0°-180°	2111.1	100.0

Coefficient of Utilization



REPORT NUMBER: P671779


CATALOG NUMBER: CCP-SA-1B-722-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	216.8	10.3			
FM	(30°-60°)	770.4	36.5			
FH	(60°-80°)	620.8	29.4			G0/660
FVH	(80°-90°)	68.7	3.3			G1/100
BL	(0°-30°)	108.0	5.1	B0/110		
BM	(30°-60°)	197.8	9.4	B0/220		
BH	(60°-80°)	116.4	5.5	B1/500		G1/500
BVH	(80°-90°)	12.2	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2
2.5°	695.7	692.0	689.1	686.3	682.6	679.8	676.0	672.3	667.6	663.9	659.2
5°	655.4	644.2	633.0	626.4	618.9	612.4	604.9	596.4	588.0	578.7	570.2
7.5°	611.4	597.4	583.3	572.1	559.9	548.7	536.5	526.2	515.9	505.6	495.3
10°	570.2	557.1	544.0	530.0	515.0	500.9	486.0	471.9	457.9	443.8	429.8
12.5°	543.1	527.2	512.2	496.3	481.3	465.4	449.4	436.3	423.2	409.2	396.1
15°	530.9	515.9	501.9	486.0	470.0	454.1	438.2	423.2	409.2	394.2	379.2
17.5°	559.9	538.4	516.9	496.3	475.7	455.1	434.5	415.7	397.0	378.3	359.6
20°	597.4	570.2	544.0	518.7	492.5	467.2	441.0	414.8	388.6	362.4	336.1
22.5°	645.1	614.2	584.3	551.5	517.8	485.0	451.3	418.5	385.8	352.1	319.3
25°	730.3	693.8	657.3	610.5	562.7	515.9	468.2	425.1	383.0	339.9	296.8
27.5°	803.4	753.8	705.1	648.9	592.7	536.5	480.3	430.7	382.0	332.4	282.8
30°	846.5	797.8	749.1	680.7	613.3	545.0	476.6	421.4	367.0	311.8	256.6
32.5°	885.8	831.5	777.2	702.3	626.4	551.5	475.7	414.8	354.9	294.0	233.1
35°	940.1	880.2	821.2	734.1	647.0	559.9	472.9	410.1	346.4	283.7	220.0
37.5°	998.1	924.2	851.1	754.7	658.2	561.8	465.4	403.6	341.8	280.0	218.2
40°	1061.8	971.9	883.0	776.2	670.4	563.7	456.9	395.1	333.3	270.6	208.8
42.5°	1103.0	1005.6	908.3	793.1	678.8	563.7	448.5	387.6	326.8	265.0	204.1
45°	1126.4	1031.8	938.2	813.7	689.1	564.6	440.1	380.2	320.2	259.4	199.4
47.5°	1136.7	1048.7	960.7	829.6	699.4	568.4	437.3	376.4	314.6	253.7	191.9
50°	1163.9	1086.2	1008.4	868.0	728.5	588.0	447.6	382.0	317.4	251.9	186.3
52.5°	1179.8	1113.3	1046.8	902.6	758.4	614.2	470.0	397.0	324.0	250.9	177.9
55°	1237.8	1174.2	1110.5	956.9	802.4	648.9	494.4	413.9	333.3	251.9	171.4
57.5°	1311.8	1244.4	1177.9	1012.2	846.5	680.7	515.0	428.8	341.8	255.6	168.5
60°	1363.3	1297.8	1233.2	1057.1	880.2	704.1	527.2	437.3	347.4	256.6	166.7
62.5°	1368.9	1284.7	1201.3	1030.0	858.6	686.3	515.0	427.9	340.8	252.8	165.7
65°	1333.3	1235.0	1136.7	972.9	809.0	645.1	481.3	401.7	322.1	241.6	162.0
67.5°	1262.2	1147.0	1031.8	882.0	732.2	582.4	432.6	364.2	296.8	228.5	160.1
70°	1096.5	995.3	895.1	765.0	635.8	505.6	375.5	319.3	264.0	207.9	151.7
72.5°	920.4	825.9	732.2	626.4	521.5	415.7	309.9	267.8	225.7	182.6	140.5
75°	705.1	633.9	563.7	485.0	406.4	326.8	248.1	217.2	186.3	155.4	124.5
77.5°	495.3	456.9	419.5	360.5	301.5	242.5	183.5	162.9	142.3	121.7	101.1
80°	336.1	314.6	294.0	251.9	209.7	166.7	124.5	111.4	97.4	84.3	70.2
82.5°	208.8	207.9	206.0	177.0	147.9	118.9	89.9	78.7	68.4	57.1	45.9
85°	95.5	111.4	126.4	110.5	94.6	78.7	62.7	55.2	47.8	39.3	31.8
87.5°	30.0	36.5	42.1	40.3	37.5	35.6	32.8	28.1	23.4	18.7	14.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2
2.5°	655.4	652.6	648.9	645.1	640.5	636.7	632.0	627.3	626.4	624.5	623.6
5°	564.6	559.0	552.4	546.8	541.2	534.7	529.0	522.5	517.8	512.2	507.5
7.5°	485.0	475.7	465.4	455.1	445.7	436.3	426.0	416.7	412.0	407.3	402.6
10°	421.4	412.0	403.6	394.2	387.6	382.0	375.5	368.9	363.3	357.7	352.1
12.5°	389.5	383.0	376.4	369.9	362.4	355.8	348.3	340.8	334.3	328.7	322.1
15°	369.9	360.5	350.2	340.8	330.5	321.2	310.9	300.6	293.1	286.5	279.0
17.5°	346.4	332.4	319.3	305.2	294.0	282.8	270.6	259.4	250.9	241.6	233.1
20°	320.2	304.3	287.5	271.5	258.4	246.3	233.1	220.0	210.7	200.4	191.0
22.5°	297.8	277.2	255.6	234.1	220.0	206.0	191.0	177.0	168.5	159.2	150.8
25°	273.4	250.9	227.5	204.1	190.1	175.1	161.1	146.1	139.5	133.9	127.3
27.5°	260.3	237.8	214.4	191.9	178.8	164.8	151.7	137.6	133.0	127.3	122.7
30°	234.1	212.5	190.1	167.6	158.2	149.8	140.5	131.1	129.2	128.3	126.4
32.5°	210.7	188.2	165.7	143.3	134.8	126.4	118.0	109.6	108.6	106.7	105.8
35°	198.5	177.0	154.5	133.0	125.5	117.0	109.6	101.1	99.3	96.4	94.6
37.5°	195.7	173.2	149.8	127.3	119.9	112.4	103.9	96.4	94.6	92.7	90.8
40°	188.2	166.7	146.1	124.5	117.0	109.6	101.1	93.6	91.8	89.9	88.0
42.5°	182.6	162.0	140.5	118.9	112.4	105.8	98.3	91.8	89.9	88.0	85.2
45°	177.9	156.4	133.9	112.4	107.7	103.0	97.4	92.7	90.8	88.0	86.1
47.5°	170.4	149.8	128.3	106.7	102.1	98.3	93.6	89.0	87.1	85.2	83.3
50°	164.8	143.3	121.7	100.2	96.4	92.7	89.0	85.2	85.2	86.1	86.1
52.5°	157.3	136.7	116.1	95.5	91.8	88.0	84.3	80.5	81.5	82.4	83.3
55°	150.8	131.1	110.5	89.9	86.1	82.4	77.7	74.0	74.9	75.8	76.8
57.5°	147.9	127.3	106.7	86.1	82.4	77.7	74.0	69.3	69.3	69.3	69.3
60°	146.1	124.5	103.9	82.4	77.7	74.0	69.3	64.6	63.7	63.7	62.7
62.5°	145.1	123.6	103.0	81.5	75.8	71.2	65.5	59.9	59.0	58.1	57.1
65°	141.4	121.7	101.1	80.5	74.0	68.4	61.8	55.2	54.3	54.3	53.4
67.5°	140.5	119.9	100.2	79.6	73.0	65.5	59.0	51.5	50.6	49.6	48.7
70°	133.0	115.2	96.4	77.7	70.2	63.7	56.2	48.7	47.8	45.9	44.9
72.5°	123.6	107.7	90.8	74.0	66.5	59.0	51.5	44.0	43.1	42.1	40.3
75°	109.6	94.6	79.6	64.6	58.1	52.4	45.9	39.3	38.4	37.5	35.6
77.5°	89.9	77.7	66.5	54.3	49.6	44.9	40.3	35.6	34.6	33.7	31.8
80°	63.7	56.2	49.6	42.1	39.3	35.6	32.8	29.0	29.0	28.1	28.1
82.5°	42.1	38.4	34.6	30.9	29.0	27.2	25.3	23.4	23.4	22.5	22.5
85°	30.0	28.1	25.3	23.4	22.5	20.6	19.7	17.8	17.8	17.8	17.8
87.5°	14.0	14.0	13.1	13.1	12.2	12.2	11.2	10.3	10.3	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2
2.5°	621.7	618.9	616.1	612.4	609.6	605.8	601.1	597.4	592.7	592.7	591.8
5°	501.9	499.1	496.3	492.5	489.7	486.0	483.2	479.4	475.7	475.7	474.7
7.5°	397.9	392.3	386.7	380.2	374.5	370.8	367.0	362.4	358.6	355.8	353.0
10°	346.4	340.8	334.3	328.7	322.1	317.4	312.7	307.1	302.4	298.7	294.9
12.5°	315.5	309.0	302.4	295.9	289.3	282.8	277.2	270.6	264.0	259.4	254.7
15°	271.5	265.0	258.4	251.9	245.3	237.8	230.3	221.9	214.4	210.7	207.9
17.5°	223.8	217.2	209.7	203.2	195.7	190.1	184.5	178.8	173.2	169.5	166.7
20°	180.7	173.2	165.7	158.2	150.8	147.0	143.3	139.5	135.8	133.0	131.1
22.5°	141.4	136.7	133.0	128.3	123.6	120.8	118.9	116.1	113.3	113.3	113.3
25°	120.8	118.0	116.1	113.3	110.5	109.6	108.6	106.7	105.8	104.9	104.9
27.5°	117.0	114.2	111.4	108.6	105.8	104.9	103.9	102.1	101.1	101.1	101.1
30°	124.5	123.6	122.7	121.7	120.8	118.9	116.1	114.2	111.4	109.6	107.7
32.5°	103.9	103.0	103.0	102.1	101.1	103.0	103.9	105.8	106.7	107.7	108.6
35°	91.8	89.9	88.0	86.1	84.3	83.3	82.4	81.5	80.5	80.5	79.6
37.5°	89.0	87.1	85.2	83.3	81.5	80.5	79.6	78.7	77.7	77.7	76.8
40°	86.1	84.3	83.3	81.5	79.6	78.7	77.7	75.8	74.9	74.0	74.0
42.5°	83.3	82.4	80.5	79.6	77.7	76.8	75.8	74.0	73.0	72.1	71.2
45°	83.3	81.5	79.6	77.7	75.8	74.9	73.0	72.1	70.2	70.2	69.3
47.5°	81.5	79.6	77.7	75.8	74.0	73.0	71.2	70.2	68.4	67.4	66.5
50°	86.1	83.3	79.6	76.8	73.0	72.1	70.2	69.3	67.4	66.5	65.5
52.5°	84.3	81.5	77.7	74.9	71.2	69.3	68.4	66.5	64.6	63.7	62.7
55°	77.7	74.9	73.0	70.2	67.4	65.5	63.7	61.8	59.9	59.0	59.0
57.5°	69.3	68.4	67.4	66.5	65.5	63.7	61.8	59.0	57.1	56.2	55.2
60°	61.8	62.7	63.7	64.6	65.5	62.7	59.9	57.1	54.3	53.4	52.4
62.5°	56.2	58.1	59.9	60.9	62.7	59.9	57.1	54.3	51.5	50.6	49.6
65°	52.4	53.4	53.4	54.3	54.3	52.4	51.5	49.6	47.8	46.8	46.8
67.5°	47.8	47.8	47.8	46.8	46.8	45.9	45.9	44.9	44.0	43.1	43.1
70°	43.1	43.1	43.1	42.1	42.1	41.2	41.2	40.3	39.3	39.3	38.4
72.5°	39.3	39.3	38.4	38.4	37.5	37.5	37.5	36.5	36.5	35.6	35.6
75°	34.6	34.6	33.7	33.7	32.8	32.8	32.8	31.8	31.8	31.8	30.9
77.5°	30.9	30.9	30.0	30.0	29.0	29.0	29.0	28.1	28.1	27.2	27.2
80°	27.2	27.2	26.2	26.2	25.3	25.3	24.3	24.3	23.4	23.4	22.5
82.5°	21.5	21.5	21.5	21.5	21.5	20.6	20.6	19.7	18.7	18.7	17.8
85°	17.8	17.8	17.8	16.9	16.9	16.9	15.9	15.9	15.0	14.0	14.0
87.5°	10.3	10.3	10.3	9.4	9.4	9.4	9.4	9.4	9.4	9.4	8.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2
2.5°	591.8	590.8	587.1	583.3	587.1	590.8	590.8	590.8	589.9	589.9	589.9
5°	474.7	473.8	471.9	470.0	470.0	469.1	471.0	472.9	474.7	476.6	478.5
7.5°	349.3	346.4	343.6	340.8	342.7	343.6	346.4	348.3	351.1	353.0	357.7
10°	291.2	287.5	284.6	281.8	280.0	278.1	276.2	275.3	273.4	271.5	273.4
12.5°	249.1	244.4	239.7	234.1	233.1	232.2	230.3	228.5	226.6	224.7	223.8
15°	204.1	200.4	198.5	195.7	191.9	188.2	186.3	185.4	183.5	181.7	180.7
17.5°	162.9	159.2	156.4	153.6	152.6	150.8	150.8	150.8	150.8	150.8	150.8
20°	128.3	125.5	125.5	124.5	124.5	123.6	124.5	125.5	125.5	126.4	127.3
22.5°	112.4	112.4	111.4	110.5	111.4	111.4	112.4	113.3	114.2	115.2	116.1
25°	103.9	103.0	103.9	104.9	104.9	104.9	105.8	105.8	106.7	106.7	106.7
27.5°	100.2	100.2	101.1	101.1	102.1	102.1	102.1	101.1	101.1	100.2	100.2
30°	105.8	103.9	103.9	103.9	103.0	102.1	101.1	101.1	100.2	99.3	98.3
32.5°	109.6	110.5	109.6	107.7	106.7	104.9	103.9	102.1	101.1	99.3	97.4
35°	79.6	78.7	80.5	81.5	82.4	83.3	84.3	85.2	85.2	86.1	86.1
37.5°	76.8	75.8	75.8	74.9	74.9	74.9	74.9	74.9	74.0	74.0	74.9
40°	73.0	72.1	72.1	71.2	71.2	70.2	70.2	70.2	70.2	70.2	70.2
42.5°	70.2	69.3	69.3	69.3	69.3	68.4	68.4	67.4	67.4	66.5	66.5
45°	69.3	68.4	67.4	66.5	66.5	65.5	65.5	65.5	64.6	64.6	64.6
47.5°	65.5	64.6	64.6	63.7	63.7	62.7	62.7	62.7	61.8	61.8	61.8
50°	63.7	62.7	62.7	61.8	61.8	60.9	60.9	60.9	59.9	59.9	59.9
52.5°	60.9	59.9	59.9	59.9	59.0	58.1	58.1	58.1	57.1	57.1	57.1
55°	58.1	57.1	57.1	57.1	56.2	55.2	55.2	55.2	54.3	54.3	54.3
57.5°	54.3	53.4	53.4	52.4	52.4	52.4	52.4	52.4	51.5	51.5	51.5
60°	51.5	50.6	50.6	49.6	49.6	48.7	48.7	48.7	48.7	48.7	48.7
62.5°	48.7	47.8	46.8	45.9	46.8	46.8	46.8	46.8	45.9	45.9	45.9
65°	45.9	44.9	44.0	43.1	43.1	43.1	43.1	43.1	43.1	43.1	43.1
67.5°	42.1	41.2	40.3	39.3	40.3	40.3	40.3	40.3	40.3	40.3	40.3
70°	38.4	37.5	37.5	36.5	36.5	35.6	35.6	36.5	36.5	36.5	36.5
72.5°	34.6	33.7	33.7	32.8	32.8	32.8	32.8	32.8	32.8	32.8	32.8
75°	30.9	30.0	30.0	29.0	29.0	29.0	29.0	29.0	29.0	29.0	29.0
77.5°	26.2	25.3	25.3	25.3	25.3	25.3	25.3	26.2	26.2	26.2	26.2
80°	22.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5
82.5°	17.8	16.9	16.9	16.9	16.9	16.9	16.9	16.9	16.9	16.9	16.9
85°	13.1	12.2	12.2	12.2	13.1	13.1	13.1	13.1	13.1	13.1	13.1
87.5°	8.4	7.5	7.5	7.5	8.4	8.4	8.4	8.4	7.5	7.5	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2
2.5°	589.9	589.9	589.9	589.0	588.0	587.1	586.1	589.0	590.8	593.6	595.5
5°	479.4	481.3	482.2	485.0	487.8	490.6	493.5	495.3	497.2	498.1	500.0
7.5°	361.4	366.1	369.9	373.6	377.3	380.2	383.9	386.7	389.5	392.3	395.1
10°	274.3	276.2	277.2	280.9	283.7	287.5	290.3	293.1	295.9	297.8	300.6
12.5°	222.8	221.0	220.0	220.0	220.0	220.0	220.0	221.9	223.8	225.7	227.5
15°	179.8	178.8	177.9	177.0	176.0	174.2	173.2	175.1	177.0	178.8	180.7
17.5°	150.8	150.8	150.8	149.8	148.9	147.9	147.0	147.9	148.9	148.9	149.8
20°	129.2	130.2	131.1	132.0	132.0	133.0	133.0	133.9	134.8	134.8	135.8
22.5°	116.1	117.0	117.0	117.0	118.0	118.0	118.0	118.9	119.9	120.8	121.7
25°	105.8	105.8	104.9	104.9	105.8	105.8	105.8	105.8	106.7	106.7	106.7
27.5°	100.2	99.3	99.3	99.3	99.3	98.3	98.3	98.3	98.3	98.3	98.3
30°	97.4	96.4	95.5	94.6	94.6	93.6	92.7	92.7	92.7	92.7	92.7
32.5°	96.4	94.6	92.7	91.8	91.8	90.8	89.9	89.0	89.0	88.0	87.1
35°	86.1	85.2	85.2	84.3	83.3	82.4	81.5	81.5	81.5	80.5	80.5
37.5°	74.9	75.8	75.8	75.8	76.8	76.8	76.8	76.8	77.7	77.7	77.7
40°	70.2	70.2	70.2	71.2	72.1	72.1	73.0	73.0	74.0	74.0	74.0
42.5°	66.5	65.5	65.5	66.5	66.5	67.4	67.4	68.4	69.3	69.3	70.2
45°	64.6	63.7	63.7	63.7	63.7	62.7	62.7	63.7	64.6	65.5	66.5
47.5°	60.9	60.9	59.9	59.9	59.9	59.9	59.9	59.9	60.9	60.9	60.9
50°	59.0	59.0	58.1	58.1	58.1	58.1	58.1	58.1	58.1	58.1	58.1
52.5°	57.1	56.2	56.2	56.2	56.2	55.2	55.2	55.2	55.2	55.2	55.2
55°	54.3	53.4	53.4	53.4	53.4	53.4	53.4	53.4	54.3	54.3	54.3
57.5°	51.5	50.6	50.6	50.6	51.5	51.5	51.5	51.5	52.4	52.4	52.4
60°	48.7	48.7	48.7	48.7	48.7	48.7	48.7	49.6	49.6	50.6	50.6
62.5°	45.9	45.9	45.9	45.9	46.8	46.8	46.8	46.8	47.8	47.8	47.8
65°	43.1	43.1	43.1	43.1	44.0	44.0	44.0	44.0	44.0	44.0	44.0
67.5°	40.3	40.3	40.3	40.3	40.3	40.3	40.3	41.2	41.2	42.1	42.1
70°	36.5	35.6	35.6	36.5	36.5	37.5	37.5	38.4	38.4	39.3	39.3
72.5°	32.8	32.8	32.8	32.8	32.8	32.8	32.8	33.7	34.6	34.6	35.6
75°	29.0	29.0	29.0	29.0	30.0	30.0	30.0	30.9	30.9	31.8	31.8
77.5°	26.2	25.3	25.3	25.3	26.2	26.2	26.2	27.2	27.2	28.1	28.1
80°	21.5	21.5	21.5	21.5	22.5	22.5	22.5	22.5	23.4	23.4	23.4
82.5°	17.8	17.8	17.8	17.8	17.8	17.8	17.8	17.8	18.7	18.7	18.7
85°	13.1	13.1	13.1	13.1	14.0	14.0	14.0	14.0	14.0	14.0	14.0
87.5°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	9.4	9.4	9.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2
2.5°	595.5	595.5	595.5	595.5	597.4	598.3	600.2	601.1	600.2	599.3	597.4
5°	500.9	501.9	501.9	502.8	502.8	502.8	502.8	502.8	504.7	506.6	508.4
7.5°	396.1	397.0	397.9	398.9	398.9	398.9	397.9	397.9	398.9	398.9	399.8
10°	303.4	307.1	309.9	312.7	310.9	308.1	306.2	303.4	303.4	303.4	302.4
12.5°	229.4	230.3	232.2	233.1	232.2	232.2	231.3	230.3	231.3	233.1	234.1
15°	181.7	181.7	182.6	182.6	183.5	184.5	184.5	185.4	187.3	188.2	190.1
17.5°	150.8	151.7	151.7	152.6	152.6	153.6	153.6	153.6	155.4	157.3	160.1
20°	135.8	135.8	135.8	135.8	135.8	134.8	134.8	133.9	134.8	136.7	137.6
22.5°	121.7	122.7	122.7	122.7	121.7	120.8	118.9	118.0	118.0	118.9	118.9
25°	106.7	105.8	105.8	104.9	104.9	105.8	105.8	105.8	106.7	106.7	107.7
27.5°	98.3	97.4	97.4	96.4	96.4	97.4	97.4	97.4	97.4	97.4	97.4
30°	91.8	91.8	90.8	89.9	90.8	90.8	91.8	91.8	92.7	92.7	93.6
32.5°	87.1	86.1	86.1	85.2	86.1	86.1	87.1	87.1	88.0	89.0	89.0
35°	80.5	80.5	80.5	80.5	80.5	80.5	79.6	79.6	79.6	79.6	79.6
37.5°	76.8	76.8	75.8	74.9	74.9	74.9	74.9	74.9	74.0	73.0	72.1
40°	74.0	73.0	73.0	72.1	71.2	71.2	70.2	69.3	69.3	68.4	68.4
42.5°	70.2	69.3	69.3	68.4	67.4	67.4	66.5	65.5	65.5	65.5	64.6
45°	65.5	65.5	64.6	63.7	63.7	63.7	62.7	62.7	62.7	62.7	61.8
47.5°	60.9	60.9	59.9	59.9	59.9	59.9	59.0	59.0	59.0	59.0	59.0
50°	58.1	58.1	58.1	58.1	58.1	58.1	57.1	57.1	57.1	57.1	57.1
52.5°	55.2	55.2	55.2	55.2	55.2	55.2	55.2	55.2	55.2	55.2	55.2
55°	54.3	54.3	54.3	54.3	54.3	54.3	53.4	53.4	53.4	54.3	54.3
57.5°	52.4	52.4	51.5	51.5	51.5	51.5	51.5	51.5	51.5	51.5	51.5
60°	50.6	50.6	50.6	50.6	50.6	50.6	50.6	50.6	50.6	50.6	50.6
62.5°	47.8	47.8	47.8	47.8	47.8	48.7	48.7	48.7	48.7	48.7	47.8
65°	44.0	44.9	44.9	44.9	44.9	44.9	44.9	44.9	44.9	44.9	44.9
67.5°	42.1	42.1	42.1	42.1	42.1	42.1	42.1	42.1	42.1	42.1	42.1
70°	39.3	39.3	38.4	38.4	38.4	39.3	39.3	39.3	39.3	39.3	39.3
72.5°	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	36.5	36.5
75°	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8
77.5°	28.1	28.1	27.2	27.2	27.2	28.1	28.1	28.1	28.1	29.0	29.0
80°	23.4	23.4	23.4	23.4	23.4	23.4	23.4	23.4	23.4	24.3	24.3
82.5°	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.7	19.7	19.7
85°	14.0	15.0	15.0	15.0	15.0	15.0	15.0	15.0	15.0	15.9	15.9
87.5°	9.4	9.4	9.4	9.4	9.4	9.4	8.4	8.4	8.4	8.4	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2
2.5°	596.4	597.4	598.3	598.3	599.3	600.2	600.2	603.9	607.7	609.6	611.4
5°	510.3	509.4	509.4	508.4	507.5	510.3	513.1	518.7	524.4	525.3	527.2
7.5°	399.8	400.8	401.7	401.7	402.6	399.8	396.1	397.0	397.9	402.6	406.4
10°	302.4	303.4	304.3	304.3	305.2	304.3	302.4	305.2	308.1	311.8	316.5
12.5°	235.0	237.8	240.6	242.5	245.3	247.2	248.1	251.9	254.7	259.4	264.0
15°	191.9	193.8	195.7	197.6	199.4	201.3	203.2	206.9	210.7	216.3	221.9
17.5°	162.0	162.0	162.9	162.9	162.9	164.8	166.7	168.5	169.5	175.1	180.7
20°	138.6	137.6	136.7	135.8	134.8	136.7	137.6	138.6	139.5	143.3	146.1
22.5°	118.9	118.9	119.9	119.9	119.9	118.9	117.0	118.0	118.0	119.9	122.7
25°	107.7	107.7	107.7	106.7	106.7	107.7	108.6	108.6	107.7	108.6	109.6
27.5°	97.4	98.3	98.3	99.3	99.3	100.2	100.2	100.2	100.2	101.1	102.1
30°	93.6	93.6	94.6	94.6	94.6	95.5	96.4	96.4	96.4	97.4	99.3
32.5°	89.9	90.8	91.8	92.7	93.6	94.6	94.6	95.5	95.5	96.4	97.4
35°	79.6	78.7	78.7	77.7	76.8	76.8	76.8	76.8	75.8	76.8	76.8
37.5°	71.2	71.2	71.2	70.2	70.2	71.2	71.2	71.2	71.2	72.1	72.1
40°	67.4	67.4	67.4	67.4	67.4	67.4	67.4	68.4	68.4	69.3	70.2
42.5°	64.6	64.6	64.6	64.6	64.6	65.5	65.5	65.5	65.5	66.5	66.5
45°	61.8	61.8	61.8	61.8	61.8	61.8	61.8	62.7	62.7	63.7	64.6
47.5°	59.0	59.0	59.0	59.0	59.0	59.9	60.9	60.9	60.9	61.8	61.8
50°	57.1	57.1	57.1	57.1	57.1	58.1	58.1	59.0	59.0	59.9	60.9
52.5°	55.2	55.2	55.2	55.2	55.2	56.2	56.2	57.1	57.1	58.1	59.0
55°	54.3	54.3	54.3	53.4	53.4	54.3	54.3	55.2	55.2	56.2	56.2
57.5°	51.5	51.5	51.5	51.5	51.5	51.5	51.5	52.4	52.4	53.4	54.3
60°	50.6	50.6	49.6	49.6	48.7	49.6	49.6	50.6	50.6	51.5	51.5
62.5°	47.8	47.8	47.8	46.8	46.8	47.8	47.8	47.8	47.8	48.7	49.6
65°	44.9	44.9	44.9	44.0	44.0	44.9	44.9	44.9	44.9	45.9	46.8
67.5°	42.1	42.1	42.1	41.2	41.2	41.2	41.2	42.1	42.1	43.1	44.0
70°	39.3	39.3	39.3	38.4	38.4	38.4	37.5	38.4	39.3	40.3	40.3
72.5°	36.5	36.5	36.5	35.6	35.6	35.6	34.6	35.6	35.6	36.5	36.5
75°	31.8	31.8	31.8	31.8	31.8	31.8	30.9	30.9	30.9	31.8	31.8
77.5°	29.0	29.0	29.0	28.1	28.1	28.1	27.2	27.2	27.2	28.1	28.1
80°	24.3	24.3	24.3	23.4	23.4	23.4	22.5	22.5	22.5	23.4	23.4
82.5°	19.7	19.7	19.7	18.7	18.7	18.7	17.8	17.8	17.8	18.7	18.7
85°	15.9	15.9	15.9	15.9	15.9	15.9	15.0	15.0	15.0	15.9	16.9
87.5°	7.5	7.5	8.4	8.4	8.4	8.4	7.5	7.5	6.6	6.6	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2
2.5°	613.3	615.2	619.9	623.6	628.3	632.0	634.8	638.6	641.4	644.2	646.1
5°	528.1	529.0	533.7	538.4	542.1	546.8	553.4	559.9	566.5	573.0	577.7
7.5°	411.1	414.8	420.4	427.0	432.6	438.2	444.8	452.3	458.8	465.4	471.9
10°	320.2	324.0	329.6	335.2	339.9	345.5	353.0	360.5	368.0	375.5	383.0
12.5°	268.7	273.4	280.0	286.5	292.1	298.7	308.1	316.5	325.8	334.3	343.6
15°	226.6	232.2	240.6	250.0	258.4	266.9	276.2	285.6	294.0	303.4	312.7
17.5°	186.3	191.9	199.4	207.9	215.4	222.8	234.1	244.4	255.6	265.9	276.2
20°	149.8	152.6	160.1	167.6	175.1	182.6	191.0	199.4	207.9	216.3	229.4
22.5°	124.5	126.4	130.2	133.0	136.7	139.5	147.9	156.4	163.9	172.3	184.5
25°	109.6	110.5	113.3	115.2	118.0	119.9	125.5	130.2	135.8	140.5	151.7
27.5°	102.1	103.0	103.9	104.9	105.8	106.7	110.5	114.2	117.0	120.8	131.1
30°	100.2	101.1	103.9	105.8	108.6	110.5	112.4	114.2	116.1	118.0	124.5
32.5°	98.3	99.3	99.3	98.3	98.3	97.4	99.3	100.2	102.1	103.0	108.6
35°	77.7	77.7	78.7	79.6	80.5	81.5	84.3	86.1	89.0	90.8	95.5
37.5°	73.0	73.0	74.0	75.8	76.8	77.7	79.6	81.5	83.3	85.2	89.9
40°	70.2	71.2	72.1	73.0	74.0	74.9	76.8	77.7	79.6	80.5	84.3
42.5°	67.4	67.4	68.4	70.2	71.2	72.1	74.0	74.9	76.8	77.7	81.5
45°	65.5	66.5	67.4	68.4	68.4	69.3	71.2	73.0	74.0	75.8	79.6
47.5°	62.7	62.7	64.6	65.5	67.4	68.4	70.2	71.2	73.0	74.0	77.7
50°	60.9	61.8	63.7	64.6	66.5	67.4	70.2	72.1	74.9	76.8	78.7
52.5°	59.0	59.9	61.8	62.7	64.6	65.5	69.3	73.0	75.8	79.6	79.6
55°	57.1	57.1	59.0	61.8	63.7	65.5	67.4	70.2	72.1	74.0	74.0
57.5°	54.3	55.2	57.1	59.9	61.8	63.7	65.5	67.4	68.4	70.2	69.3
60°	52.4	52.4	55.2	58.1	60.9	63.7	63.7	63.7	62.7	62.7	62.7
62.5°	49.6	50.6	54.3	59.0	62.7	66.5	63.7	60.9	58.1	55.2	56.2
65°	47.8	48.7	50.6	53.4	55.2	57.1	55.2	54.3	52.4	50.6	51.5
67.5°	44.0	44.9	45.9	45.9	46.8	46.8	46.8	46.8	46.8	46.8	47.8
70°	41.2	41.2	41.2	42.1	42.1	42.1	42.1	42.1	42.1	42.1	43.1
72.5°	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	38.4
75°	32.8	32.8	32.8	32.8	32.8	32.8	32.8	32.8	32.8	32.8	33.7
77.5°	29.0	29.0	29.0	29.0	29.0	29.0	29.0	29.0	28.1	28.1	29.0
80°	24.3	24.3	24.3	24.3	23.4	23.4	23.4	23.4	23.4	23.4	24.3
82.5°	19.7	19.7	19.7	19.7	18.7	18.7	18.7	18.7	17.8	17.8	18.7
85°	17.8	18.7	18.7	19.7	19.7	19.7	18.7	17.8	16.9	15.9	15.9
87.5°	7.5	7.5	7.5	7.5	6.6	6.6	6.6	6.6	6.6	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2
2.5°	648.9	650.8	652.6	655.4	659.2	662.0	664.8	670.4	677.0	682.6	688.2
5°	582.4	587.1	591.8	597.4	603.0	607.7	613.3	624.5	635.8	646.1	657.3
7.5°	477.5	484.1	489.7	499.1	507.5	516.9	525.3	539.3	552.4	566.5	579.6
10°	390.5	397.9	405.4	417.6	430.7	442.9	455.1	466.3	478.5	489.7	500.9
12.5°	353.0	361.4	370.8	378.3	386.7	394.2	401.7	414.8	427.9	441.0	454.1
15°	322.1	331.5	340.8	350.2	358.6	368.0	376.4	387.6	399.8	411.1	422.3
17.5°	286.5	295.9	306.2	316.5	326.8	337.1	347.4	363.3	379.2	394.2	410.1
20°	241.6	254.7	266.9	280.9	294.9	309.0	323.0	339.9	356.7	372.7	389.5
22.5°	196.6	208.8	221.0	237.8	254.7	270.6	287.5	309.9	331.5	353.9	375.5
25°	163.9	175.1	186.3	205.1	222.8	241.6	259.4	286.5	312.7	339.9	366.1
27.5°	141.4	151.7	162.0	181.7	201.3	220.0	239.7	269.7	298.7	328.7	357.7
30°	131.1	137.6	144.2	162.9	181.7	199.4	218.2	247.2	276.2	305.2	334.3
32.5°	114.2	119.9	125.5	142.3	159.2	175.1	191.9	221.9	250.9	280.9	309.9
35°	101.1	105.8	110.5	126.4	141.4	157.3	172.3	202.2	232.2	262.2	292.1
37.5°	93.6	98.3	102.1	116.1	131.1	145.1	159.2	189.1	218.2	248.1	277.2
40°	88.0	90.8	94.6	108.6	121.7	135.8	148.9	176.0	204.1	231.3	258.4
42.5°	84.3	88.0	90.8	103.0	116.1	128.3	140.5	166.7	192.9	218.2	244.4
45°	83.3	87.1	90.8	101.1	111.4	120.8	131.1	156.4	181.7	206.9	232.2
47.5°	81.5	84.3	88.0	96.4	103.9	112.4	119.9	145.1	170.4	194.8	220.0
50°	80.5	81.5	83.3	90.8	98.3	105.8	113.3	138.6	163.9	189.1	214.4
52.5°	79.6	79.6	79.6	86.1	92.7	98.3	104.9	130.2	156.4	181.7	206.9
55°	74.0	73.0	73.0	79.6	85.2	91.8	97.4	122.7	147.9	172.3	197.6
57.5°	68.4	67.4	66.5	72.1	77.7	83.3	89.0	114.2	140.5	165.7	191.0
60°	62.7	61.8	61.8	67.4	72.1	77.7	82.4	108.6	133.9	160.1	185.4
62.5°	56.2	57.1	57.1	61.8	67.4	72.1	76.8	103.0	130.2	156.4	182.6
65°	51.5	52.4	52.4	58.1	63.7	69.3	74.9	100.2	126.4	151.7	177.0
67.5°	47.8	48.7	48.7	55.2	60.9	67.4	73.0	95.5	118.9	141.4	163.9
70°	44.0	44.0	44.9	51.5	58.1	64.6	71.2	90.8	110.5	129.2	148.9
72.5°	39.3	40.3	41.2	47.8	53.4	59.9	65.5	83.3	101.1	118.9	136.7
75°	34.6	35.6	36.5	42.1	47.8	53.4	59.0	75.8	91.8	108.6	124.5
77.5°	30.9	31.8	32.8	37.5	42.1	46.8	51.5	63.7	76.8	89.0	101.1
80°	25.3	25.3	26.2	30.0	33.7	36.5	40.3	48.7	57.1	64.6	73.0
82.5°	18.7	19.7	19.7	22.5	24.3	27.2	29.0	33.7	37.5	42.1	45.9
85°	15.9	15.0	15.0	16.9	17.8	19.7	20.6	23.4	25.3	28.1	30.0
87.5°	6.6	5.6	5.6	6.6	8.4	9.4	10.3	10.3	11.2	11.2	11.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2
2.5°	691.0	692.9	695.7	697.6	702.3	706.0	710.7	714.4	717.2	721.9	720.0
5°	665.7	674.2	682.6	691.0	697.6	704.1	709.7	716.3	723.8	737.8	741.6
7.5°	590.8	602.1	612.4	623.6	636.7	649.8	662.9	676.0	688.2	706.0	717.2
10°	516.9	532.8	547.8	563.7	575.8	588.0	599.3	611.4	628.3	646.1	666.7
12.5°	470.0	486.0	501.9	517.8	535.6	552.4	570.2	587.1	603.0	617.0	640.5
15°	439.1	456.9	473.8	490.6	512.2	532.8	554.3	574.9	598.3	617.0	633.0
17.5°	431.7	453.2	473.8	495.3	517.8	540.3	562.7	585.2	608.6	636.7	657.3
20°	418.5	447.6	476.6	505.6	534.7	562.7	591.8	619.9	650.8	684.5	693.8
22.5°	411.1	445.7	481.3	515.9	555.2	595.5	634.8	674.2	706.9	732.2	760.3
25°	410.1	453.2	497.2	540.3	589.9	638.6	688.2	736.9	779.0	804.3	826.8
27.5°	409.2	461.6	513.1	564.6	625.5	685.4	746.3	806.2	845.5	882.0	900.8
30°	397.9	460.7	524.4	587.1	655.4	723.8	792.1	860.5	900.8	926.0	935.4
32.5°	383.9	457.9	531.8	605.8	683.5	761.2	838.0	915.7	947.6	969.1	961.6
35°	372.7	454.1	534.7	615.2	697.6	780.9	863.3	945.7	991.6	1021.5	1009.4
37.5°	362.4	447.6	532.8	618.0	714.4	810.9	907.3	1003.8	1047.8	1079.6	1065.6
40°	350.2	441.0	532.8	623.6	734.1	843.6	954.1	1063.7	1120.8	1148.0	1126.4
42.5°	339.9	434.5	530.0	624.5	742.5	860.5	978.5	1096.5	1160.1	1198.5	1171.4
45°	326.8	421.4	515.0	609.6	739.7	869.9	999.1	1129.2	1203.2	1233.2	1195.7
47.5°	312.7	406.4	499.1	591.8	730.3	868.9	1007.5	1146.1	1214.4	1250.0	1215.4
50°	308.1	401.7	494.4	588.0	737.8	888.6	1038.4	1188.2	1237.8	1266.9	1221.0
52.5°	307.1	406.4	506.6	605.8	756.6	906.4	1057.1	1206.9	1247.2	1278.1	1236.9
55°	304.3	412.0	518.7	625.5	782.8	941.0	1098.3	1255.6	1295.9	1318.4	1287.5
57.5°	307.1	423.2	538.4	654.5	816.5	978.5	1140.5	1302.4	1351.1	1367.1	1360.5
60°	309.0	432.6	555.2	678.8	837.1	995.3	1153.6	1311.8	1362.4	1401.7	1409.2
62.5°	304.3	426.0	546.8	668.5	811.8	955.1	1098.3	1241.6	1324.9	1383.0	1416.7
65°	290.3	402.6	515.9	628.3	760.3	893.3	1025.3	1157.3	1245.3	1331.5	1358.6
67.5°	259.4	354.9	450.4	545.9	661.1	776.2	890.5	1005.6	1116.1	1199.5	1236.9
70°	224.7	299.6	375.5	450.4	555.2	660.1	765.0	869.9	967.2	1059.0	1094.6
72.5°	195.7	253.7	312.7	370.8	445.7	519.7	594.6	668.5	783.7	875.5	910.1
75°	166.7	208.8	250.0	292.1	343.6	395.1	445.7	497.2	578.7	661.1	695.7
77.5°	128.3	156.4	183.5	210.7	246.3	280.9	316.5	351.1	408.2	470.0	487.8
80°	89.0	104.9	119.9	135.8	163.9	191.9	220.0	248.1	285.6	320.2	347.4
82.5°	55.2	65.5	74.9	84.3	106.7	129.2	150.8	173.2	188.2	190.1	217.2
85°	35.6	42.1	47.8	53.4	66.5	80.5	93.6	106.7	95.5	89.0	105.8
87.5°	14.0	17.8	20.6	23.4	22.5	21.5	20.6	19.7	16.9	15.0	18.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2
2.5°	721.9	724.7	727.5	729.4	732.2	733.2	734.1	734.1	735.0	736.0	737.8
5°	756.6	762.2	767.8	772.5	778.1	782.8	786.5	791.2	795.0	795.0	794.0
7.5°	727.5	741.6	755.6	769.7	783.7	794.0	803.4	813.7	823.0	824.9	826.8
10°	689.1	704.1	718.2	733.2	747.2	763.1	778.1	793.1	809.0	811.8	815.6
12.5°	653.6	671.4	689.1	706.0	723.8	735.0	746.3	756.6	767.8	775.3	782.8
15°	652.6	667.6	682.6	696.6	711.6	718.2	724.7	730.3	736.9	736.9	737.8
17.5°	674.2	683.5	692.9	701.3	710.7	711.6	713.5	714.4	715.4	712.6	709.7
20°	716.3	720.0	723.8	727.5	731.3	724.7	719.1	712.6	706.0	698.5	692.0
22.5°	778.1	769.7	761.2	752.8	744.4	733.2	721.0	709.7	697.6	688.2	678.8
25°	836.2	825.9	815.6	805.3	795.0	770.6	746.3	721.0	696.6	686.3	676.0
27.5°	913.9	898.0	882.0	866.1	850.2	817.4	784.7	751.9	719.1	701.3	684.5
30°	932.6	914.8	897.0	878.3	860.5	828.7	797.8	765.9	734.1	713.5	693.8
32.5°	959.7	939.1	918.5	898.0	877.4	846.5	815.6	783.7	752.8	734.1	714.4
35°	1004.7	981.3	957.9	933.5	910.1	878.3	847.4	815.6	783.7	762.2	741.6
37.5°	1043.1	1015.9	988.8	961.6	934.5	906.4	877.4	849.3	820.2	798.7	778.1
40°	1086.2	1056.2	1026.2	997.2	967.2	941.0	914.8	887.7	861.4	844.6	827.7
42.5°	1123.6	1087.1	1051.5	1015.9	979.4	961.6	944.8	927.0	909.2	900.8	891.4
45°	1149.8	1116.1	1081.5	1047.8	1014.1	1000.9	987.8	974.7	961.6	970.0	978.5
47.5°	1161.1	1133.9	1107.7	1081.5	1054.3	1059.0	1063.7	1067.4	1072.1	1083.3	1095.5
50°	1171.4	1156.4	1140.5	1125.5	1109.6	1127.4	1144.2	1162.0	1179.8	1203.2	1226.6
52.5°	1192.0	1183.5	1176.0	1167.6	1159.2	1190.1	1221.0	1251.9	1282.8	1309.0	1335.2
55°	1253.8	1247.2	1240.7	1233.2	1226.6	1270.6	1313.7	1357.7	1401.7	1428.9	1456.0
57.5°	1339.0	1335.2	1330.5	1326.8	1322.1	1365.2	1407.3	1449.5	1492.5	1518.7	1545.9
60°	1403.6	1404.5	1404.5	1405.4	1405.4	1438.2	1471.0	1504.7	1537.5	1559.9	1583.4
62.5°	1438.2	1436.3	1434.5	1432.6	1430.7	1457.9	1485.0	1512.2	1539.3	1556.2	1573.1
65°	1400.8	1411.1	1421.4	1431.7	1442.0	1445.7	1448.5	1452.3	1455.1	1465.4	1475.7
67.5°	1275.3	1295.9	1315.6	1336.2	1355.8	1341.8	1328.7	1314.6	1300.6	1303.4	1305.3
70°	1135.8	1159.2	1183.5	1206.9	1230.4	1197.6	1164.8	1131.1	1098.3	1087.1	1075.9
72.5°	957.9	978.5	1000.0	1020.6	1041.2	1000.9	961.6	921.4	881.1	861.4	841.8
75°	732.2	756.6	781.8	806.2	830.5	785.6	739.7	694.8	648.9	635.8	623.6
77.5°	533.7	562.7	591.8	620.8	649.8	609.6	569.3	528.1	487.8	480.3	472.9
80°	388.6	411.1	432.6	455.1	476.6	453.2	429.8	406.4	383.0	382.0	381.1
82.5°	262.2	281.8	300.6	320.2	339.0	329.6	321.2	311.8	302.4	311.8	322.1
85°	134.8	162.0	190.1	217.2	244.4	241.6	239.7	236.9	234.1	246.3	257.5
87.5°	27.2	50.6	74.0	96.4	119.9	114.2	108.6	102.1	96.4	100.2	103.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2
2.5°	738.8	739.7	739.7	739.7	739.7	739.7	737.8	736.9	735.0	733.2	730.3
5°	794.0	793.1	789.3	785.6	780.9	777.2	774.4	770.6	767.8	764.1	758.4
7.5°	828.7	830.5	824.0	818.4	811.8	805.3	798.7	792.1	785.6	779.0	765.9
10°	818.4	821.2	817.4	813.7	809.0	805.3	797.8	789.3	781.8	773.4	757.5
12.5°	789.3	796.8	795.0	793.1	791.2	789.3	784.7	779.0	774.4	768.7	750.9
15°	737.8	737.8	738.8	739.7	739.7	740.6	741.6	742.5	743.5	744.4	734.1
17.5°	706.9	704.1	704.1	704.1	704.1	704.1	707.9	712.6	716.3	720.0	717.2
20°	684.5	677.9	677.0	677.0	676.0	675.1	681.7	689.1	695.7	702.3	706.0
22.5°	669.5	660.1	659.2	658.2	657.3	656.4	664.8	673.2	681.7	690.1	703.2
25°	665.7	655.4	656.4	657.3	657.3	658.2	664.8	671.4	677.9	684.5	706.9
27.5°	666.7	649.8	650.8	651.7	651.7	652.6	662.9	672.3	682.6	692.0	720.0
30°	673.2	653.6	651.7	649.8	647.9	646.1	660.1	674.2	688.2	702.3	723.8
32.5°	695.7	677.0	672.3	667.6	662.9	658.2	675.1	691.0	707.9	723.8	741.6
35°	720.0	699.4	697.6	695.7	692.9	691.0	706.0	721.9	736.9	751.9	767.8
37.5°	756.6	736.0	734.1	731.3	729.4	726.6	743.5	759.4	776.2	792.1	806.2
40°	810.9	794.0	793.1	793.1	792.1	791.2	804.3	818.4	831.5	844.6	853.9
42.5°	883.0	874.5	877.4	881.1	883.9	886.7	897.0	908.3	918.5	928.8	926.0
45°	986.9	995.3	996.3	997.2	998.1	999.1	1001.9	1005.6	1008.4	1011.2	1000.0
47.5°	1106.8	1118.0	1123.6	1129.2	1133.9	1139.5	1135.8	1131.1	1127.4	1122.7	1094.6
50°	1249.1	1272.5	1271.6	1270.6	1268.7	1267.8	1260.3	1252.8	1244.4	1236.9	1195.7
52.5°	1361.4	1387.7	1392.3	1397.0	1401.7	1406.4	1392.3	1378.3	1363.3	1349.3	1297.8
55°	1482.2	1509.4	1510.3	1511.3	1511.3	1512.2	1492.5	1472.9	1452.3	1432.6	1379.2
57.5°	1572.1	1598.3	1595.5	1593.7	1590.8	1588.0	1564.6	1541.2	1517.8	1494.4	1441.0
60°	1605.8	1628.3	1622.7	1617.1	1610.5	1604.9	1587.1	1569.3	1550.6	1532.8	1481.3
62.5°	1589.9	1606.8	1598.3	1590.8	1582.4	1574.0	1551.5	1528.1	1505.6	1482.2	1444.8
65°	1485.0	1495.3	1484.1	1473.8	1463.5	1452.3	1433.5	1414.8	1395.1	1376.4	1351.1
67.5°	1308.1	1309.9	1309.0	1308.1	1307.1	1306.2	1279.0	1251.9	1223.8	1196.6	1194.8
70°	1065.6	1054.3	1056.2	1059.0	1060.9	1062.7	1042.1	1022.5	1001.9	981.3	990.6
72.5°	822.1	802.4	807.1	812.7	817.4	822.1	805.3	789.3	772.5	755.6	768.7
75°	610.5	598.3	603.0	608.6	613.3	618.0	611.4	604.9	597.4	590.8	603.0
77.5°	465.4	457.9	458.8	458.8	459.7	459.7	460.7	462.6	463.5	464.4	477.5
80°	379.2	378.3	377.3	376.4	374.5	373.6	383.0	392.3	401.7	411.1	417.6
82.5°	331.5	340.8	335.2	330.5	324.9	319.3	327.7	336.1	344.6	353.0	350.2
85°	269.7	280.9	270.6	260.3	249.1	238.8	246.3	252.8	260.3	266.9	263.1
87.5°	106.7	109.6	92.7	76.8	59.9	43.1	68.4	92.7	118.0	142.3	146.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2	674.2
2.5°	727.5	723.8	721.0	720.0	718.2	717.2	715.4	713.5	710.7	708.8	706.0
5°	751.9	746.3	739.7	730.3	721.9	712.6	703.2	694.8	686.3	677.0	668.5
7.5°	752.8	739.7	726.6	714.4	701.3	689.1	676.0	664.8	652.6	640.5	629.2
10°	742.5	726.6	710.7	694.8	679.8	663.9	647.9	634.8	620.8	606.7	593.6
12.5°	734.1	716.3	698.5	679.8	662.0	643.3	624.5	611.4	598.3	585.2	572.1
15°	723.8	712.6	702.3	685.4	668.5	651.7	634.8	617.0	600.2	582.4	564.6
17.5°	715.4	712.6	709.7	698.5	687.3	675.1	663.9	646.1	628.3	609.6	591.8
20°	710.7	714.4	718.2	712.6	706.9	700.4	694.8	681.7	668.5	654.5	641.4
22.5°	716.3	730.3	743.5	744.4	746.3	747.2	748.1	736.0	723.8	710.7	698.5
25°	729.4	751.9	774.4	786.5	798.7	811.8	824.0	816.5	809.0	801.5	794.0
27.5°	747.2	775.3	803.4	821.2	838.0	855.8	873.6	872.7	871.7	869.9	868.9
30°	744.4	765.9	787.5	809.0	830.5	852.1	873.6	884.8	895.1	906.4	917.6
32.5°	760.3	778.1	796.8	819.3	841.8	865.2	887.7	911.1	933.5	956.9	980.3
35°	784.7	800.6	817.4	841.8	867.1	891.4	916.7	944.8	973.8	1002.8	1030.9
37.5°	821.2	835.2	850.2	870.8	892.3	912.9	934.5	975.7	1016.9	1059.0	1100.2
40°	863.3	872.7	882.0	901.7	921.4	941.0	960.7	1012.2	1063.7	1115.2	1166.7
42.5°	924.2	921.4	918.5	934.5	951.3	967.2	984.1	1030.9	1077.7	1124.5	1171.4
45°	988.8	977.5	966.3	973.8	982.2	989.7	998.1	1045.9	1093.6	1142.3	1190.1
47.5°	1066.5	1038.4	1010.3	1003.8	997.2	989.7	983.2	1034.7	1086.2	1138.6	1190.1
50°	1154.5	1112.4	1071.2	1054.3	1036.5	1019.7	1001.9	1044.0	1087.1	1130.2	1172.3
52.5°	1246.3	1193.8	1142.3	1116.1	1089.9	1062.7	1036.5	1072.1	1108.6	1145.1	1180.7
55°	1324.9	1271.6	1217.2	1186.3	1155.4	1124.5	1093.6	1129.2	1164.8	1200.4	1236.0
57.5°	1387.7	1334.3	1280.9	1251.9	1221.9	1192.9	1162.9	1196.6	1231.3	1265.9	1299.6
60°	1430.7	1379.2	1327.7	1299.6	1271.6	1243.5	1215.4	1255.6	1295.9	1337.1	1377.4
62.5°	1408.3	1370.8	1333.3	1321.2	1309.0	1295.9	1283.7	1322.1	1359.6	1398.0	1436.3
65°	1325.9	1300.6	1275.3	1287.5	1300.6	1312.7	1325.9	1351.1	1376.4	1402.6	1427.9
67.5°	1192.0	1190.1	1187.3	1214.4	1241.6	1269.7	1296.8	1313.7	1329.6	1346.5	1363.3
70°	1000.0	1010.3	1019.7	1066.5	1113.3	1160.1	1206.9	1213.5	1220.1	1226.6	1233.2
72.5°	782.8	795.9	809.9	871.7	932.6	994.4	1056.2	1052.4	1048.7	1044.0	1040.3
75°	616.1	628.3	641.4	698.5	755.6	812.7	869.9	853.9	839.0	823.0	807.1
77.5°	491.6	504.7	518.7	572.1	625.5	679.8	733.2	694.8	656.4	618.0	579.6
80°	423.2	429.8	435.4	471.9	507.5	544.0	580.5	541.2	500.9	460.7	421.4
82.5°	347.4	343.6	340.8	362.4	383.9	405.4	427.0	389.5	352.1	313.7	276.2
85°	259.4	255.6	251.9	263.1	274.3	286.5	297.8	254.7	211.6	167.6	124.5
87.5°	150.8	154.5	158.2	170.4	182.6	195.7	207.9	163.9	119.9	74.9	30.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671779
 CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	674.2	674.2
2.5°	700.4	695.7
5°	662.0	655.4
7.5°	619.9	611.4
10°	581.5	570.2
12.5°	557.1	543.1
15°	547.8	530.9
17.5°	575.8	559.9
20°	618.9	597.4
22.5°	671.4	645.1
25°	762.2	730.3
27.5°	836.2	803.4
30°	882.0	846.5
32.5°	932.6	885.8
35°	985.0	940.1
37.5°	1048.7	998.1
40°	1114.2	1061.8
42.5°	1136.7	1103.0
45°	1158.3	1126.4
47.5°	1162.9	1136.7
50°	1167.6	1163.9
52.5°	1180.7	1179.8
55°	1236.9	1237.8
57.5°	1306.2	1311.8
60°	1369.9	1363.3
62.5°	1402.6	1368.9
65°	1380.2	1333.3
67.5°	1312.7	1262.2
70°	1164.8	1096.5
72.5°	980.3	920.4
75°	755.6	705.1
77.5°	537.5	495.3
80°	378.3	336.1
82.5°	242.5	208.8
85°	109.6	95.5
87.5°	30.9	30.0
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P671779

CATALOG NUMBER: CCP-SA-1B-722-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)