

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671784

Luminaire Tested: **CCP-SA-2A-722-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671784
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-2A-722-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @350mA w/ SLR
distribution lens
Light Source: (32) 2200K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3344.7 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 36.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 4.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	688.2	0.0	688.2
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	2656.5	0.0	2656.5
	% Fixture	79.4	0.0	79.4
Total	Lumens	3344.7	0.0	3344.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.0	2.5
10°-20°	175.2	5.2
20°-30°	256.4	7.7
30°-40°	361.2	10.8
40°-50°	496.3	14.8
50°-60°	676.5	20.2
60°-70°	740.4	22.1
70°-80°	427.6	12.8
80°-90°	128.2	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3344.7	100.0
0°-180°	3344.7	100.0

Coefficient of Utilization



REPORT NUMBER: P671784


CATALOG NUMBER: CCP-SA-2A-722-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	343.5	10.3			
FM	(30°-60°)	1220.6	36.5			
FH	(60°-80°)	983.5	29.4			G1/1800
FVH	(80°-90°)	108.9	3.3			G2/225
BL	(0°-30°)	171.1	5.1	B1/500		
BM	(30°-60°)	313.4	9.4	B1/1000		
BH	(60°-80°)	184.4	5.5	B1/500		G1/500
BVH	(80°-90°)	19.3	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1
2.5°	1102.2	1096.3	1091.8	1087.4	1081.4	1077.0	1071.1	1065.1	1057.7	1051.8	1044.4
5°	1038.4	1020.6	1002.8	992.4	980.6	970.2	958.3	945.0	931.6	916.8	903.4
7.5°	968.7	946.5	924.2	906.4	887.1	869.3	850.0	833.7	817.4	801.1	784.8
10°	903.4	882.7	861.9	839.6	815.9	793.7	769.9	747.7	725.4	703.2	680.9
12.5°	860.4	835.2	811.5	786.2	762.5	737.3	712.1	691.3	670.5	648.3	627.5
15°	841.1	817.4	795.1	769.9	744.7	719.5	694.3	670.5	648.3	624.5	600.8
17.5°	887.1	853.0	818.9	786.2	753.6	721.0	688.3	658.7	629.0	599.3	569.7
20°	946.5	903.4	861.9	821.8	780.3	740.3	698.7	657.2	615.6	574.1	532.6
22.5°	1022.1	973.2	925.7	873.8	820.4	768.4	715.0	663.1	611.2	557.8	505.9
25°	1157.1	1099.2	1041.4	967.2	891.6	817.4	741.7	673.5	606.7	538.5	470.3
27.5°	1272.8	1194.2	1117.1	1028.0	939.0	850.0	761.0	682.4	605.3	526.6	448.0
30°	1341.1	1263.9	1186.8	1078.5	971.7	863.4	755.1	667.6	581.5	494.0	406.5
32.5°	1403.4	1317.3	1231.3	1112.6	992.4	873.8	753.6	657.2	562.2	465.8	369.4
35°	1489.4	1394.5	1301.0	1163.0	1025.1	887.1	749.2	649.8	548.9	449.5	348.6
37.5°	1581.4	1464.2	1348.5	1195.7	1042.9	890.1	737.3	639.4	541.5	443.6	345.6
40°	1682.3	1539.8	1398.9	1229.8	1062.2	893.0	723.9	626.0	528.1	428.7	330.8
42.5°	1747.5	1593.2	1439.0	1256.5	1075.5	893.0	710.6	614.2	517.7	419.8	323.4
45°	1784.6	1634.8	1486.4	1289.1	1091.8	894.5	697.2	602.3	507.3	410.9	316.0
47.5°	1800.9	1661.5	1522.0	1314.4	1108.2	900.5	692.8	596.4	498.4	402.0	304.1
50°	1844.0	1720.8	1597.7	1375.2	1154.1	931.6	709.1	605.3	502.9	399.1	295.2
52.5°	1869.2	1763.8	1658.5	1430.1	1201.6	973.2	744.7	629.0	513.3	397.6	281.9
55°	1961.1	1860.3	1759.4	1516.1	1271.3	1028.0	783.3	655.7	528.1	399.1	271.5
57.5°	2078.3	1971.5	1866.2	1603.6	1341.1	1078.5	815.9	679.4	541.5	405.0	267.0
60°	2159.9	2056.1	1953.7	1674.8	1394.5	1115.6	835.2	692.8	550.4	406.5	264.1
62.5°	2168.8	2035.3	1903.3	1631.8	1360.3	1087.4	815.9	677.9	540.0	400.5	262.6
65°	2112.5	1956.7	1800.9	1541.3	1281.7	1022.1	762.5	636.4	510.3	382.7	256.6
67.5°	1999.7	1817.2	1634.8	1397.4	1160.1	922.7	685.4	577.1	470.3	362.0	253.7
70°	1737.1	1576.9	1418.2	1212.0	1007.3	801.1	594.9	505.9	418.3	329.3	240.3
72.5°	1458.2	1308.4	1160.1	992.4	826.3	658.7	491.0	424.3	357.5	289.3	222.5
75°	1117.1	1004.3	893.0	768.4	643.8	517.7	393.1	344.2	295.2	246.3	197.3
77.5°	784.8	723.9	664.6	571.1	477.7	384.2	290.8	258.1	225.5	192.9	160.2
80°	532.6	498.4	465.8	399.1	332.3	264.1	197.3	176.5	154.3	133.5	111.3
82.5°	330.8	329.3	326.4	280.4	234.4	188.4	142.4	124.6	108.3	90.5	72.7
85°	151.3	176.5	200.3	175.0	149.8	124.6	99.4	87.5	75.7	62.3	50.4
87.5°	47.5	57.9	66.8	63.8	59.3	56.4	51.9	44.5	37.1	29.7	22.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1
2.5°	1038.4	1034.0	1028.0	1022.1	1014.7	1008.8	1001.3	993.9	992.4	989.5	988.0
5°	894.5	885.6	875.2	866.3	857.4	847.1	838.2	827.8	820.4	811.5	804.0
7.5°	768.4	753.6	737.3	721.0	706.1	691.3	675.0	660.1	652.7	645.3	637.9
10°	667.6	652.7	639.4	624.5	614.2	605.3	594.9	584.5	575.6	566.7	557.8
12.5°	617.1	606.7	596.4	586.0	574.1	563.7	551.8	540.0	529.6	520.7	510.3
15°	586.0	571.1	554.8	540.0	523.7	508.8	492.5	476.2	464.3	453.9	442.1
17.5°	548.9	526.6	505.9	483.6	465.8	448.0	428.7	410.9	397.6	382.7	369.4
20°	507.3	482.1	455.4	430.2	409.4	390.2	369.4	348.6	333.8	317.5	302.6
22.5°	471.7	439.1	405.0	370.9	348.6	326.4	302.6	280.4	267.0	252.2	238.8
25°	433.2	397.6	360.5	323.4	301.1	277.4	255.2	231.4	221.0	212.1	201.8
27.5°	412.4	376.8	339.7	304.1	283.3	261.1	240.3	218.1	210.7	201.8	194.3
30°	370.9	336.7	301.1	265.5	250.7	237.4	222.5	207.7	204.7	203.2	200.3
32.5°	333.8	298.2	262.6	227.0	213.6	200.3	186.9	173.6	172.1	169.1	167.6
35°	314.5	280.4	244.8	210.7	198.8	185.4	173.6	160.2	157.2	152.8	149.8
37.5°	310.0	274.4	237.4	201.8	189.9	178.0	164.7	152.8	149.8	146.9	143.9
40°	298.2	264.1	231.4	197.3	185.4	173.6	160.2	148.3	145.4	142.4	139.4
42.5°	289.3	256.6	222.5	188.4	178.0	167.6	155.8	145.4	142.4	139.4	135.0
45°	281.9	247.7	212.1	178.0	170.6	163.2	154.3	146.9	143.9	139.4	136.5
47.5°	270.0	237.4	203.2	169.1	161.7	155.8	148.3	140.9	138.0	135.0	132.0
50°	261.1	227.0	192.9	158.7	152.8	146.9	140.9	135.0	135.0	136.5	136.5
52.5°	249.2	216.6	183.9	151.3	145.4	139.4	133.5	127.6	129.1	130.5	132.0
55°	238.8	207.7	175.0	142.4	136.5	130.5	123.1	117.2	118.7	120.2	121.6
57.5°	234.4	201.8	169.1	136.5	130.5	123.1	117.2	109.8	109.8	109.8	109.8
60°	231.4	197.3	164.7	130.5	123.1	117.2	109.8	102.4	100.9	100.9	99.4
62.5°	229.9	195.8	163.2	129.1	120.2	112.7	103.8	94.9	93.5	92.0	90.5
65°	224.0	192.9	160.2	127.6	117.2	108.3	97.9	87.5	86.0	86.0	84.6
67.5°	222.5	189.9	158.7	126.1	115.7	103.8	93.5	81.6	80.1	78.6	77.1
70°	210.7	182.5	152.8	123.1	111.3	100.9	89.0	77.1	75.7	72.7	71.2
72.5°	195.8	170.6	143.9	117.2	105.3	93.5	81.6	69.7	68.2	66.8	63.8
75°	173.6	149.8	126.1	102.4	92.0	83.1	72.7	62.3	60.8	59.3	56.4
77.5°	142.4	123.1	105.3	86.0	78.6	71.2	63.8	56.4	54.9	53.4	50.4
80°	100.9	89.0	78.6	66.8	62.3	56.4	51.9	46.0	46.0	44.5	44.5
82.5°	66.8	60.8	54.9	49.0	46.0	43.0	40.1	37.1	37.1	35.6	35.6
85°	47.5	44.5	40.1	37.1	35.6	32.6	31.2	28.2	28.2	28.2	28.2
87.5°	22.3	22.3	20.8	20.8	19.3	19.3	17.8	16.3	16.3	16.3	16.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1
2.5°	985.0	980.6	976.1	970.2	965.7	959.8	952.4	946.5	939.0	939.0	937.6
5°	795.1	790.7	786.2	780.3	775.9	769.9	765.5	759.5	753.6	753.6	752.1
7.5°	630.5	621.6	612.7	602.3	593.4	587.5	581.5	574.1	568.2	563.7	559.3
10°	548.9	540.0	529.6	520.7	510.3	502.9	495.5	486.6	479.2	473.2	467.3
12.5°	499.9	489.5	479.2	468.8	458.4	448.0	439.1	428.7	418.3	410.9	403.5
15°	430.2	419.8	409.4	399.1	388.7	376.8	364.9	351.6	339.7	333.8	329.3
17.5°	354.5	344.2	332.3	321.9	310.0	301.1	292.2	283.3	274.4	268.5	264.1
20°	286.3	274.4	262.6	250.7	238.8	232.9	227.0	221.0	215.1	210.7	207.7
22.5°	224.0	216.6	210.7	203.2	195.8	191.4	188.4	183.9	179.5	179.5	179.5
25°	191.4	186.9	183.9	179.5	175.0	173.6	172.1	169.1	167.6	166.1	166.1
27.5°	185.4	181.0	176.5	172.1	167.6	166.1	164.7	161.7	160.2	160.2	160.2
30°	197.3	195.8	194.3	192.9	191.4	188.4	183.9	181.0	176.5	173.6	170.6
32.5°	164.7	163.2	163.2	161.7	160.2	163.2	164.7	167.6	169.1	170.6	172.1
35°	145.4	142.4	139.4	136.5	133.5	132.0	130.5	129.1	127.6	127.6	126.1
37.5°	140.9	138.0	135.0	132.0	129.1	127.6	126.1	124.6	123.1	123.1	121.6
40°	136.5	133.5	132.0	129.1	126.1	124.6	123.1	120.2	118.7	117.2	117.2
42.5°	132.0	130.5	127.6	126.1	123.1	121.6	120.2	117.2	115.7	114.2	112.7
45°	132.0	129.1	126.1	123.1	120.2	118.7	115.7	114.2	111.3	111.3	109.8
47.5°	129.1	126.1	123.1	120.2	117.2	115.7	112.7	111.3	108.3	106.8	105.3
50°	136.5	132.0	126.1	121.6	115.7	114.2	111.3	109.8	106.8	105.3	103.8
52.5°	133.5	129.1	123.1	118.7	112.7	109.8	108.3	105.3	102.4	100.9	99.4
55°	123.1	118.7	115.7	111.3	106.8	103.8	100.9	97.9	94.9	93.5	93.5
57.5°	109.8	108.3	106.8	105.3	103.8	100.9	97.9	93.5	90.5	89.0	87.5
60°	97.9	99.4	100.9	102.4	103.8	99.4	94.9	90.5	86.0	84.6	83.1
62.5°	89.0	92.0	94.9	96.4	99.4	94.9	90.5	86.0	81.6	80.1	78.6
65°	83.1	84.6	84.6	86.0	86.0	83.1	81.6	78.6	75.7	74.2	74.2
67.5°	75.7	75.7	75.7	74.2	74.2	72.7	72.7	71.2	69.7	68.2	68.2
70°	68.2	68.2	68.2	66.8	66.8	65.3	65.3	63.8	62.3	62.3	60.8
72.5°	62.3	62.3	60.8	60.8	59.3	59.3	59.3	57.9	57.9	56.4	56.4
75°	54.9	54.9	53.4	53.4	51.9	51.9	51.9	50.4	50.4	50.4	49.0
77.5°	49.0	49.0	47.5	47.5	46.0	46.0	46.0	44.5	44.5	43.0	43.0
80°	43.0	43.0	41.5	41.5	40.1	40.1	38.6	38.6	37.1	37.1	35.6
82.5°	34.1	34.1	34.1	34.1	34.1	32.6	32.6	31.2	29.7	29.7	28.2
85°	28.2	28.2	28.2	26.7	26.7	26.7	25.2	25.2	23.7	22.3	22.3
87.5°	16.3	16.3	16.3	14.8	14.8	14.8	14.8	14.8	14.8	14.8	13.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1
2.5°	937.6	936.1	930.1	924.2	930.1	936.1	936.1	936.1	934.6	934.6	934.6
5°	752.1	750.6	747.7	744.7	744.7	743.2	746.2	749.2	752.1	755.1	758.1
7.5°	553.3	548.9	544.4	540.0	542.9	544.4	548.9	551.8	556.3	559.3	566.7
10°	461.4	455.4	451.0	446.5	443.6	440.6	437.6	436.1	433.2	430.2	433.2
12.5°	394.6	387.2	379.8	370.9	369.4	367.9	364.9	362.0	359.0	356.0	354.5
15°	323.4	317.5	314.5	310.0	304.1	298.2	295.2	293.7	290.8	287.8	286.3
17.5°	258.1	252.2	247.7	243.3	241.8	238.8	238.8	238.8	238.8	238.8	238.8
20°	203.2	198.8	198.8	197.3	197.3	195.8	197.3	198.8	198.8	200.3	201.8
22.5°	178.0	178.0	176.5	175.0	176.5	176.5	178.0	179.5	181.0	182.5	183.9
25°	164.7	163.2	164.7	166.1	166.1	166.1	167.6	167.6	169.1	169.1	169.1
27.5°	158.7	158.7	160.2	160.2	161.7	161.7	161.7	160.2	160.2	158.7	158.7
30°	167.6	164.7	164.7	164.7	163.2	161.7	160.2	160.2	158.7	157.2	155.8
32.5°	173.6	175.0	173.6	170.6	169.1	166.1	164.7	161.7	160.2	157.2	154.3
35°	126.1	124.6	127.6	129.1	130.5	132.0	133.5	135.0	135.0	136.5	136.5
37.5°	121.6	120.2	120.2	118.7	118.7	118.7	118.7	118.7	117.2	117.2	118.7
40°	115.7	114.2	114.2	112.7	112.7	111.3	111.3	111.3	111.3	111.3	111.3
42.5°	111.3	109.8	109.8	109.8	109.8	108.3	108.3	106.8	106.8	105.3	105.3
45°	109.8	108.3	106.8	105.3	105.3	103.8	103.8	103.8	102.4	102.4	102.4
47.5°	103.8	102.4	102.4	100.9	100.9	99.4	99.4	99.4	97.9	97.9	97.9
50°	100.9	99.4	99.4	97.9	97.9	96.4	96.4	96.4	94.9	94.9	94.9
52.5°	96.4	94.9	94.9	94.9	93.5	92.0	92.0	92.0	90.5	90.5	90.5
55°	92.0	90.5	90.5	90.5	89.0	87.5	87.5	87.5	86.0	86.0	86.0
57.5°	86.0	84.6	84.6	83.1	83.1	83.1	83.1	83.1	81.6	81.6	81.6
60°	81.6	80.1	80.1	78.6	78.6	77.1	77.1	77.1	77.1	77.1	77.1
62.5°	77.1	75.7	74.2	72.7	74.2	74.2	74.2	74.2	72.7	72.7	72.7
65°	72.7	71.2	69.7	68.2	68.2	68.2	68.2	68.2	68.2	68.2	68.2
67.5°	66.8	65.3	63.8	62.3	63.8	63.8	63.8	63.8	63.8	63.8	63.8
70°	60.8	59.3	59.3	57.9	57.9	56.4	56.4	57.9	57.9	57.9	57.9
72.5°	54.9	53.4	53.4	51.9	51.9	51.9	51.9	51.9	51.9	51.9	51.9
75°	49.0	47.5	47.5	46.0	46.0	46.0	46.0	46.0	46.0	46.0	46.0
77.5°	41.5	40.1	40.1	40.1	40.1	40.1	40.1	41.5	41.5	41.5	41.5
80°	35.6	34.1	34.1	34.1	34.1	34.1	34.1	34.1	34.1	34.1	34.1
82.5°	28.2	26.7	26.7	26.7	26.7	26.7	26.7	26.7	26.7	26.7	26.7
85°	20.8	19.3	19.3	19.3	20.8	20.8	20.8	20.8	20.8	20.8	20.8
87.5°	13.4	11.9	11.9	11.9	13.4	13.4	13.4	13.4	11.9	11.9	11.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1
2.5°	934.6	934.6	934.6	933.1	931.6	930.1	928.7	933.1	936.1	940.5	943.5
5°	759.5	762.5	764.0	768.4	772.9	777.3	781.8	784.8	787.7	789.2	792.2
7.5°	572.6	580.0	586.0	591.9	597.8	602.3	608.2	612.7	617.1	621.6	626.0
10°	434.7	437.6	439.1	445.0	449.5	455.4	459.9	464.3	468.8	471.7	476.2
12.5°	353.1	350.1	348.6	348.6	348.6	348.6	348.6	351.6	354.5	357.5	360.5
15°	284.8	283.3	281.9	280.4	278.9	275.9	274.4	277.4	280.4	283.3	286.3
17.5°	238.8	238.8	238.8	237.4	235.9	234.4	232.9	234.4	235.9	235.9	237.4
20°	204.7	206.2	207.7	209.2	209.2	210.7	210.7	212.1	213.6	213.6	215.1
22.5°	183.9	185.4	185.4	185.4	186.9	186.9	186.9	188.4	189.9	191.4	192.9
25°	167.6	167.6	166.1	166.1	167.6	167.6	167.6	167.6	169.1	169.1	169.1
27.5°	158.7	157.2	157.2	157.2	157.2	155.8	155.8	155.8	155.8	155.8	155.8
30°	154.3	152.8	151.3	149.8	149.8	148.3	146.9	146.9	146.9	146.9	146.9
32.5°	152.8	149.8	146.9	145.4	145.4	143.9	142.4	140.9	140.9	139.4	138.0
35°	136.5	135.0	135.0	133.5	132.0	130.5	129.1	129.1	129.1	127.6	127.6
37.5°	118.7	120.2	120.2	120.2	121.6	121.6	121.6	121.6	123.1	123.1	123.1
40°	111.3	111.3	111.3	112.7	114.2	114.2	115.7	115.7	117.2	117.2	117.2
42.5°	105.3	103.8	103.8	105.3	105.3	106.8	106.8	108.3	109.8	109.8	111.3
45°	102.4	100.9	100.9	100.9	100.9	99.4	99.4	100.9	102.4	103.8	105.3
47.5°	96.4	96.4	94.9	94.9	94.9	94.9	94.9	94.9	96.4	96.4	96.4
50°	93.5	93.5	92.0	92.0	92.0	92.0	92.0	92.0	92.0	92.0	92.0
52.5°	90.5	89.0	89.0	89.0	89.0	87.5	87.5	87.5	87.5	87.5	87.5
55°	86.0	84.6	84.6	84.6	84.6	84.6	84.6	84.6	86.0	86.0	86.0
57.5°	81.6	80.1	80.1	80.1	81.6	81.6	81.6	81.6	83.1	83.1	83.1
60°	77.1	77.1	77.1	77.1	77.1	77.1	77.1	78.6	78.6	80.1	80.1
62.5°	72.7	72.7	72.7	72.7	74.2	74.2	74.2	74.2	75.7	75.7	75.7
65°	68.2	68.2	68.2	68.2	69.7	69.7	69.7	69.7	69.7	69.7	69.7
67.5°	63.8	63.8	63.8	63.8	63.8	63.8	63.8	65.3	65.3	66.8	66.8
70°	57.9	56.4	56.4	57.9	57.9	59.3	59.3	60.8	60.8	62.3	62.3
72.5°	51.9	51.9	51.9	51.9	51.9	51.9	51.9	53.4	54.9	54.9	56.4
75°	46.0	46.0	46.0	46.0	47.5	47.5	47.5	49.0	49.0	50.4	50.4
77.5°	41.5	40.1	40.1	40.1	41.5	41.5	41.5	43.0	43.0	44.5	44.5
80°	34.1	34.1	34.1	34.1	35.6	35.6	35.6	35.6	37.1	37.1	37.1
82.5°	28.2	28.2	28.2	28.2	28.2	28.2	28.2	28.2	29.7	29.7	29.7
85°	20.8	20.8	20.8	20.8	22.3	22.3	22.3	22.3	22.3	22.3	22.3
87.5°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4	14.8	14.8	14.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1
2.5°	943.5	943.5	943.5	943.5	946.5	947.9	950.9	952.4	950.9	949.4	946.5
5°	793.7	795.1	795.1	796.6	796.6	796.6	796.6	796.6	799.6	802.6	805.5
7.5°	627.5	629.0	630.5	632.0	632.0	632.0	630.5	630.5	632.0	632.0	633.4
10°	480.6	486.6	491.0	495.5	492.5	488.1	485.1	480.6	480.6	480.6	479.2
12.5°	363.4	364.9	367.9	369.4	367.9	367.9	366.4	364.9	366.4	369.4	370.9
15°	287.8	287.8	289.3	289.3	290.8	292.2	292.2	293.7	296.7	298.2	301.1
17.5°	238.8	240.3	240.3	241.8	241.8	243.3	243.3	243.3	246.3	249.2	253.7
20°	215.1	215.1	215.1	215.1	215.1	213.6	213.6	212.1	213.6	216.6	218.1
22.5°	192.9	194.3	194.3	194.3	192.9	191.4	188.4	186.9	186.9	188.4	188.4
25°	169.1	167.6	167.6	166.1	166.1	167.6	167.6	167.6	169.1	169.1	170.6
27.5°	155.8	154.3	154.3	152.8	152.8	154.3	154.3	154.3	154.3	154.3	154.3
30°	145.4	145.4	143.9	142.4	143.9	143.9	145.4	145.4	146.9	146.9	148.3
32.5°	138.0	136.5	136.5	135.0	136.5	136.5	138.0	138.0	139.4	140.9	140.9
35°	127.6	127.6	127.6	127.6	127.6	127.6	126.1	126.1	126.1	126.1	126.1
37.5°	121.6	121.6	120.2	118.7	118.7	118.7	118.7	118.7	117.2	115.7	114.2
40°	117.2	115.7	115.7	114.2	112.7	112.7	111.3	109.8	109.8	108.3	108.3
42.5°	111.3	109.8	109.8	108.3	106.8	106.8	105.3	103.8	103.8	103.8	102.4
45°	103.8	103.8	102.4	100.9	100.9	100.9	99.4	99.4	99.4	99.4	97.9
47.5°	96.4	96.4	94.9	94.9	94.9	94.9	93.5	93.5	93.5	93.5	93.5
50°	92.0	92.0	92.0	92.0	92.0	92.0	90.5	90.5	90.5	90.5	90.5
52.5°	87.5	87.5	87.5	87.5	87.5	87.5	87.5	87.5	87.5	87.5	87.5
55°	86.0	86.0	86.0	86.0	86.0	86.0	84.6	84.6	84.6	86.0	86.0
57.5°	83.1	83.1	81.6	81.6	81.6	81.6	81.6	81.6	81.6	81.6	81.6
60°	80.1	80.1	80.1	80.1	80.1	80.1	80.1	80.1	80.1	80.1	80.1
62.5°	75.7	75.7	75.7	75.7	75.7	77.1	77.1	77.1	77.1	77.1	75.7
65°	69.7	71.2	71.2	71.2	71.2	71.2	71.2	71.2	71.2	71.2	71.2
67.5°	66.8	66.8	66.8	66.8	66.8	66.8	66.8	66.8	66.8	66.8	66.8
70°	62.3	62.3	60.8	60.8	60.8	62.3	62.3	62.3	62.3	62.3	62.3
72.5°	56.4	56.4	56.4	56.4	56.4	56.4	56.4	56.4	56.4	57.9	57.9
75°	50.4	50.4	50.4	50.4	50.4	50.4	50.4	50.4	50.4	50.4	50.4
77.5°	44.5	44.5	43.0	43.0	43.0	44.5	44.5	44.5	44.5	46.0	46.0
80°	37.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1	38.6	38.6
82.5°	29.7	29.7	29.7	29.7	29.7	29.7	29.7	29.7	29.7	31.2	31.2
85°	22.3	23.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7	25.2	25.2
87.5°	14.8	14.8	14.8	14.8	14.8	14.8	13.4	13.4	13.4	13.4	11.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1
2.5°	945.0	946.5	947.9	947.9	949.4	950.9	950.9	956.8	962.8	965.7	968.7
5°	808.5	807.0	807.0	805.5	804.0	808.5	812.9	821.8	830.7	832.2	835.2
7.5°	633.4	634.9	636.4	636.4	637.9	633.4	627.5	629.0	630.5	637.9	643.8
10°	479.2	480.6	482.1	482.1	483.6	482.1	479.2	483.6	488.1	494.0	501.4
12.5°	372.4	376.8	381.3	384.2	388.7	391.6	393.1	399.1	403.5	410.9	418.3
15°	304.1	307.1	310.0	313.0	316.0	318.9	321.9	327.8	333.8	342.7	351.6
17.5°	256.6	256.6	258.1	258.1	258.1	261.1	264.1	267.0	268.5	277.4	286.3
20°	219.6	218.1	216.6	215.1	213.6	216.6	218.1	219.6	221.0	227.0	231.4
22.5°	188.4	188.4	189.9	189.9	189.9	188.4	185.4	186.9	186.9	189.9	194.3
25°	170.6	170.6	170.6	169.1	169.1	170.6	172.1	172.1	170.6	172.1	173.6
27.5°	154.3	155.8	155.8	157.2	157.2	158.7	158.7	158.7	158.7	160.2	161.7
30°	148.3	148.3	149.8	149.8	149.8	151.3	152.8	152.8	152.8	154.3	157.2
32.5°	142.4	143.9	145.4	146.9	148.3	149.8	149.8	151.3	151.3	152.8	154.3
35°	126.1	124.6	124.6	123.1	121.6	121.6	121.6	121.6	120.2	121.6	121.6
37.5°	112.7	112.7	112.7	111.3	111.3	112.7	112.7	112.7	112.7	114.2	114.2
40°	106.8	106.8	106.8	106.8	106.8	106.8	106.8	108.3	108.3	109.8	111.3
42.5°	102.4	102.4	102.4	102.4	102.4	103.8	103.8	103.8	103.8	105.3	105.3
45°	97.9	97.9	97.9	97.9	97.9	97.9	97.9	99.4	99.4	100.9	102.4
47.5°	93.5	93.5	93.5	93.5	93.5	94.9	96.4	96.4	96.4	97.9	97.9
50°	90.5	90.5	90.5	90.5	90.5	92.0	92.0	93.5	93.5	94.9	96.4
52.5°	87.5	87.5	87.5	87.5	87.5	89.0	89.0	90.5	90.5	92.0	93.5
55°	86.0	86.0	86.0	84.6	84.6	86.0	86.0	87.5	87.5	89.0	89.0
57.5°	81.6	81.6	81.6	81.6	81.6	81.6	81.6	83.1	83.1	84.6	86.0
60°	80.1	80.1	78.6	78.6	77.1	78.6	78.6	80.1	80.1	81.6	81.6
62.5°	75.7	75.7	75.7	74.2	74.2	75.7	75.7	75.7	75.7	77.1	78.6
65°	71.2	71.2	71.2	69.7	69.7	71.2	71.2	71.2	71.2	72.7	74.2
67.5°	66.8	66.8	66.8	65.3	65.3	65.3	65.3	66.8	66.8	68.2	69.7
70°	62.3	62.3	62.3	60.8	60.8	60.8	59.3	60.8	62.3	63.8	63.8
72.5°	57.9	57.9	57.9	56.4	56.4	56.4	54.9	56.4	56.4	57.9	57.9
75°	50.4	50.4	50.4	50.4	50.4	50.4	49.0	49.0	49.0	50.4	50.4
77.5°	46.0	46.0	46.0	44.5	44.5	44.5	43.0	43.0	43.0	44.5	44.5
80°	38.6	38.6	38.6	37.1	37.1	37.1	35.6	35.6	35.6	37.1	37.1
82.5°	31.2	31.2	31.2	29.7	29.7	29.7	28.2	28.2	28.2	29.7	29.7
85°	25.2	25.2	25.2	25.2	25.2	25.2	23.7	23.7	23.7	25.2	26.7
87.5°	11.9	11.9	13.4	13.4	13.4	13.4	11.9	11.9	10.4	10.4	11.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1
2.5°	971.7	974.6	982.1	988.0	995.4	1001.3	1005.8	1011.7	1016.2	1020.6	1023.6
5°	836.7	838.2	845.6	853.0	858.9	866.3	876.7	887.1	897.5	907.9	915.3
7.5°	651.2	657.2	666.1	676.5	685.4	694.3	704.6	716.5	726.9	737.3	747.7
10°	507.3	513.3	522.2	531.1	538.5	547.4	559.3	571.1	583.0	594.9	606.7
12.5°	425.8	433.2	443.6	453.9	462.8	473.2	488.1	501.4	516.2	529.6	544.4
15°	359.0	367.9	381.3	396.1	409.4	422.8	437.6	452.5	465.8	480.6	495.5
17.5°	295.2	304.1	316.0	329.3	341.2	353.1	370.9	387.2	405.0	421.3	437.6
20°	237.4	241.8	253.7	265.5	277.4	289.3	302.6	316.0	329.3	342.7	363.4
22.5°	197.3	200.3	206.2	210.7	216.6	221.0	234.4	247.7	259.6	273.0	292.2
25°	173.6	175.0	179.5	182.5	186.9	189.9	198.8	206.2	215.1	222.5	240.3
27.5°	161.7	163.2	164.7	166.1	167.6	169.1	175.0	181.0	185.4	191.4	207.7
30°	158.7	160.2	164.7	167.6	172.1	175.0	178.0	181.0	183.9	186.9	197.3
32.5°	155.8	157.2	157.2	155.8	155.8	154.3	157.2	158.7	161.7	163.2	172.1
35°	123.1	123.1	124.6	126.1	127.6	129.1	133.5	136.5	140.9	143.9	151.3
37.5°	115.7	115.7	117.2	120.2	121.6	123.1	126.1	129.1	132.0	135.0	142.4
40°	111.3	112.7	114.2	115.7	117.2	118.7	121.6	123.1	126.1	127.6	133.5
42.5°	106.8	106.8	108.3	111.3	112.7	114.2	117.2	118.7	121.6	123.1	129.1
45°	103.8	105.3	106.8	108.3	108.3	109.8	112.7	115.7	117.2	120.2	126.1
47.5°	99.4	99.4	102.4	103.8	106.8	108.3	111.3	112.7	115.7	117.2	123.1
50°	96.4	97.9	100.9	102.4	105.3	106.8	111.3	114.2	118.7	121.6	124.6
52.5°	93.5	94.9	97.9	99.4	102.4	103.8	109.8	115.7	120.2	126.1	126.1
55°	90.5	90.5	93.5	97.9	100.9	103.8	106.8	111.3	114.2	117.2	117.2
57.5°	86.0	87.5	90.5	94.9	97.9	100.9	103.8	106.8	108.3	111.3	109.8
60°	83.1	83.1	87.5	92.0	96.4	100.9	100.9	100.9	99.4	99.4	99.4
62.5°	78.6	80.1	86.0	93.5	99.4	105.3	100.9	96.4	92.0	87.5	89.0
65°	75.7	77.1	80.1	84.6	87.5	90.5	87.5	86.0	83.1	80.1	81.6
67.5°	69.7	71.2	72.7	72.7	74.2	74.2	74.2	74.2	74.2	74.2	75.7
70°	65.3	65.3	65.3	66.8	66.8	66.8	66.8	66.8	66.8	66.8	68.2
72.5°	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	60.8
75°	51.9	51.9	51.9	51.9	51.9	51.9	51.9	51.9	51.9	51.9	53.4
77.5°	46.0	46.0	46.0	46.0	46.0	46.0	46.0	46.0	44.5	44.5	46.0
80°	38.6	38.6	38.6	38.6	37.1	37.1	37.1	37.1	37.1	37.1	38.6
82.5°	31.2	31.2	31.2	31.2	29.7	29.7	29.7	29.7	28.2	28.2	29.7
85°	28.2	29.7	29.7	31.2	31.2	31.2	29.7	28.2	26.7	25.2	25.2
87.5°	11.9	11.9	11.9	11.9	10.4	10.4	10.4	10.4	10.4	10.4	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1
2.5°	1028.0	1031.0	1034.0	1038.4	1044.4	1048.8	1053.3	1062.2	1072.5	1081.4	1090.3
5°	922.7	930.1	937.6	946.5	955.4	962.8	971.7	989.5	1007.3	1023.6	1041.4
7.5°	756.6	767.0	775.9	790.7	804.0	818.9	832.2	854.5	875.2	897.5	918.3
10°	618.6	630.5	642.3	661.6	682.4	701.7	721.0	738.8	758.1	775.9	793.7
12.5°	559.3	572.6	587.5	599.3	612.7	624.5	636.4	657.2	677.9	698.7	719.5
15°	510.3	525.1	540.0	554.8	568.2	583.0	596.4	614.2	633.4	651.2	669.0
17.5°	453.9	468.8	485.1	501.4	517.7	534.0	550.4	575.6	600.8	624.5	649.8
20°	382.7	403.5	422.8	445.0	467.3	489.5	511.8	538.5	565.2	590.4	617.1
22.5°	311.5	330.8	350.1	376.8	403.5	428.7	455.4	491.0	525.1	560.8	594.9
25°	259.6	277.4	295.2	324.9	353.1	382.7	410.9	453.9	495.5	538.5	580.0
27.5°	224.0	240.3	256.6	287.8	318.9	348.6	379.8	427.2	473.2	520.7	566.7
30°	207.7	218.1	228.5	258.1	287.8	316.0	345.6	391.6	437.6	483.6	529.6
32.5°	181.0	189.9	198.8	225.5	252.2	277.4	304.1	351.6	397.6	445.0	491.0
35°	160.2	167.6	175.0	200.3	224.0	249.2	273.0	320.4	367.9	415.4	462.8
37.5°	148.3	155.8	161.7	183.9	207.7	229.9	252.2	299.7	345.6	393.1	439.1
40°	139.4	143.9	149.8	172.1	192.9	215.1	235.9	278.9	323.4	366.4	409.4
42.5°	133.5	139.4	143.9	163.2	183.9	203.2	222.5	264.1	305.6	345.6	387.2
45°	132.0	138.0	143.9	160.2	176.5	191.4	207.7	247.7	287.8	327.8	367.9
47.5°	129.1	133.5	139.4	152.8	164.7	178.0	189.9	229.9	270.0	308.6	348.6
50°	127.6	129.1	132.0	143.9	155.8	167.6	179.5	219.6	259.6	299.7	339.7
52.5°	126.1	126.1	126.1	136.5	146.9	155.8	166.1	206.2	247.7	287.8	327.8
55°	117.2	115.7	115.7	126.1	135.0	145.4	154.3	194.3	234.4	273.0	313.0
57.5°	108.3	106.8	105.3	114.2	123.1	132.0	140.9	181.0	222.5	262.6	302.6
60°	99.4	97.9	97.9	106.8	114.2	123.1	130.5	172.1	212.1	253.7	293.7
62.5°	89.0	90.5	90.5	97.9	106.8	114.2	121.6	163.2	206.2	247.7	289.3
65°	81.6	83.1	83.1	92.0	100.9	109.8	118.7	158.7	200.3	240.3	280.4
67.5°	75.7	77.1	77.1	87.5	96.4	106.8	115.7	151.3	188.4	224.0	259.6
70°	69.7	69.7	71.2	81.6	92.0	102.4	112.7	143.9	175.0	204.7	235.9
72.5°	62.3	63.8	65.3	75.7	84.6	94.9	103.8	132.0	160.2	188.4	216.6
75°	54.9	56.4	57.9	66.8	75.7	84.6	93.5	120.2	145.4	172.1	197.3
77.5°	49.0	50.4	51.9	59.3	66.8	74.2	81.6	100.9	121.6	140.9	160.2
80°	40.1	40.1	41.5	47.5	53.4	57.9	63.8	77.1	90.5	102.4	115.7
82.5°	29.7	31.2	31.2	35.6	38.6	43.0	46.0	53.4	59.3	66.8	72.7
85°	25.2	23.7	23.7	26.7	28.2	31.2	32.6	37.1	40.1	44.5	47.5
87.5°	10.4	8.9	8.9	10.4	13.4	14.8	16.3	16.3	17.8	17.8	17.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1
2.5°	1094.8	1097.8	1102.2	1105.2	1112.6	1118.5	1126.0	1131.9	1136.3	1143.8	1140.8
5°	1054.7	1068.1	1081.4	1094.8	1105.2	1115.6	1124.5	1134.9	1146.7	1169.0	1174.9
7.5°	936.1	953.9	970.2	988.0	1008.8	1029.5	1050.3	1071.1	1090.3	1118.5	1136.3
10°	818.9	844.1	867.8	893.0	912.3	931.6	949.4	968.7	995.4	1023.6	1056.2
12.5°	744.7	769.9	795.1	820.4	848.5	875.2	903.4	930.1	955.4	977.6	1014.7
15°	695.7	723.9	750.6	777.3	811.5	844.1	878.2	910.8	947.9	977.6	1002.8
17.5°	683.9	718.0	750.6	784.8	820.4	856.0	891.6	927.2	964.3	1008.8	1041.4
20°	663.1	709.1	755.1	801.1	847.1	891.6	937.6	982.1	1031.0	1084.4	1099.2
22.5°	651.2	706.1	762.5	817.4	879.7	943.5	1005.8	1068.1	1120.0	1160.1	1204.6
25°	649.8	718.0	787.7	856.0	934.6	1011.7	1090.3	1167.5	1234.2	1274.3	1309.9
27.5°	648.3	731.3	812.9	894.5	991.0	1085.9	1182.3	1277.3	1339.6	1397.4	1427.1
30°	630.5	729.9	830.7	930.1	1038.4	1146.7	1255.0	1363.3	1427.1	1467.1	1482.0
32.5°	608.2	725.4	842.6	959.8	1082.9	1206.1	1327.7	1450.8	1501.3	1535.4	1523.5
35°	590.4	719.5	847.1	974.6	1105.2	1237.2	1367.8	1498.3	1571.0	1618.5	1599.2
37.5°	574.1	709.1	844.1	979.1	1131.9	1284.7	1437.5	1590.3	1660.0	1710.4	1688.2
40°	554.8	698.7	844.1	988.0	1163.0	1336.6	1511.7	1685.2	1775.7	1818.7	1784.6
42.5°	538.5	688.3	839.6	989.5	1176.4	1363.3	1550.2	1737.1	1838.0	1898.8	1855.8
45°	517.7	667.6	815.9	965.7	1171.9	1378.1	1582.9	1789.1	1906.3	1953.7	1894.4
47.5°	495.5	643.8	790.7	937.6	1157.1	1376.7	1596.2	1815.8	1924.1	1980.4	1925.5
50°	488.1	636.4	783.3	931.6	1169.0	1407.8	1645.2	1882.5	1961.1	2007.1	1934.4
52.5°	486.6	643.8	802.6	959.8	1198.6	1436.0	1674.8	1912.2	1976.0	2024.9	1959.7
55°	482.1	652.7	821.8	991.0	1240.2	1490.9	1740.1	1989.3	2053.1	2088.7	2039.8
57.5°	486.6	670.5	853.0	1036.9	1293.6	1550.2	1806.9	2063.5	2140.6	2165.9	2155.5
60°	489.5	685.4	879.7	1075.5	1326.2	1576.9	1827.6	2078.3	2158.4	2220.8	2232.6
62.5°	482.1	675.0	866.3	1059.2	1286.2	1513.1	1740.1	1967.1	2099.1	2191.1	2244.5
65°	459.9	637.9	817.4	995.4	1204.6	1415.2	1624.4	1833.6	1973.0	2109.5	2152.5
67.5°	410.9	562.2	713.5	864.9	1047.3	1229.8	1410.8	1593.2	1768.3	1900.3	1959.7
70°	356.0	474.7	594.9	713.5	879.7	1045.8	1212.0	1378.1	1532.4	1677.8	1734.2
72.5°	310.0	402.0	495.5	587.5	706.1	823.3	942.0	1059.2	1241.7	1387.0	1441.9
75°	264.1	330.8	396.1	462.8	544.4	626.0	706.1	787.7	916.8	1047.3	1102.2
77.5°	203.2	247.7	290.8	333.8	390.2	445.0	501.4	556.3	646.8	744.7	772.9
80°	140.9	166.1	189.9	215.1	259.6	304.1	348.6	393.1	452.5	507.3	550.4
82.5°	87.5	103.8	118.7	133.5	169.1	204.7	238.8	274.4	298.2	301.1	344.2
85°	56.4	66.8	75.7	84.6	105.3	127.6	148.3	169.1	151.3	140.9	167.6
87.5°	22.3	28.2	32.6	37.1	35.6	34.1	32.6	31.2	26.7	23.7	29.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1
2.5°	1143.8	1148.2	1152.7	1155.6	1160.1	1161.6	1163.0	1163.0	1164.5	1166.0	1169.0
5°	1198.6	1207.5	1216.4	1223.9	1232.8	1240.2	1246.1	1253.5	1259.5	1259.5	1258.0
7.5°	1152.7	1174.9	1197.2	1219.4	1241.7	1258.0	1272.8	1289.1	1304.0	1306.9	1309.9
10°	1091.8	1115.6	1137.8	1161.6	1183.8	1209.0	1232.8	1256.5	1281.7	1286.2	1292.1
12.5°	1035.5	1063.6	1091.8	1118.5	1146.7	1164.5	1182.3	1198.6	1216.4	1228.3	1240.2
15°	1034.0	1057.7	1081.4	1103.7	1127.4	1137.8	1148.2	1157.1	1167.5	1167.5	1169.0
17.5°	1068.1	1082.9	1097.8	1111.1	1126.0	1127.4	1130.4	1131.9	1133.4	1128.9	1124.5
20°	1134.9	1140.8	1146.7	1152.7	1158.6	1148.2	1139.3	1128.9	1118.5	1106.7	1096.3
22.5°	1232.8	1219.4	1206.1	1192.7	1179.4	1161.6	1142.3	1124.5	1105.2	1090.3	1075.5
25°	1324.7	1308.4	1292.1	1275.8	1259.5	1220.9	1182.3	1142.3	1103.7	1087.4	1071.1
27.5°	1447.9	1422.6	1397.4	1372.2	1347.0	1295.1	1243.1	1191.2	1139.3	1111.1	1084.4
30°	1477.5	1449.3	1421.2	1391.5	1363.3	1312.9	1263.9	1213.5	1163.0	1130.4	1099.2
32.5°	1520.6	1487.9	1455.3	1422.6	1390.0	1341.1	1292.1	1241.7	1192.7	1163.0	1131.9
35°	1591.8	1554.7	1517.6	1479.0	1441.9	1391.5	1342.5	1292.1	1241.7	1207.5	1174.9
37.5°	1652.6	1609.6	1566.5	1523.5	1480.5	1436.0	1390.0	1345.5	1299.5	1265.4	1232.8
40°	1720.8	1673.4	1625.9	1579.9	1532.4	1490.9	1449.3	1406.3	1364.8	1338.1	1311.4
42.5°	1780.2	1722.3	1665.9	1609.6	1551.7	1523.5	1496.8	1468.6	1440.4	1427.1	1412.3
45°	1821.7	1768.3	1713.4	1660.0	1606.6	1585.8	1565.1	1544.3	1523.5	1536.9	1550.2
47.5°	1839.5	1796.5	1754.9	1713.4	1670.4	1677.8	1685.2	1691.2	1698.6	1716.4	1735.7
50°	1855.8	1832.1	1806.9	1783.1	1757.9	1786.1	1812.8	1841.0	1869.2	1906.3	1943.3
52.5°	1888.5	1875.1	1863.2	1849.9	1836.5	1885.5	1934.4	1983.4	2032.4	2073.9	2115.4
55°	1986.4	1976.0	1965.6	1953.7	1943.3	2013.1	2081.3	2151.0	2220.8	2263.8	2306.8
57.5°	2121.4	2115.4	2108.0	2102.1	2094.7	2162.9	2229.7	2296.4	2364.6	2406.2	2449.2
60°	2223.7	2225.2	2225.2	2226.7	2226.7	2278.6	2330.5	2383.9	2435.9	2471.5	2508.5
62.5°	2278.6	2275.6	2272.7	2269.7	2266.7	2309.8	2352.8	2395.8	2438.8	2465.5	2492.2
65°	2219.3	2235.6	2251.9	2268.2	2284.5	2290.5	2294.9	2300.9	2305.3	2321.6	2337.9
67.5°	2020.5	2053.1	2084.3	2116.9	2148.1	2125.8	2105.0	2082.8	2060.5	2065.0	2068.0
70°	1799.4	1836.5	1875.1	1912.2	1949.3	1897.4	1845.4	1792.0	1740.1	1722.3	1704.5
72.5°	1517.6	1550.2	1584.3	1617.0	1649.6	1585.8	1523.5	1459.7	1395.9	1364.8	1333.6
75°	1160.1	1198.6	1238.7	1277.3	1315.8	1244.6	1171.9	1100.7	1028.0	1007.3	988.0
77.5°	845.6	891.6	937.6	983.5	1029.5	965.7	901.9	836.7	772.9	761.0	749.2
80°	615.6	651.2	685.4	721.0	755.1	718.0	680.9	643.8	606.7	605.3	603.8
82.5°	415.4	446.5	476.2	507.3	537.0	522.2	508.8	494.0	479.2	494.0	510.3
85°	213.6	256.6	301.1	344.2	387.2	382.7	379.8	375.3	370.9	390.2	408.0
87.5°	43.0	80.1	117.2	152.8	189.9	181.0	172.1	161.7	152.8	158.7	163.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1
2.5°	1170.5	1171.9	1171.9	1171.9	1171.9	1171.9	1169.0	1167.5	1164.5	1161.6	1157.1
5°	1258.0	1256.5	1250.6	1244.6	1237.2	1231.3	1226.8	1220.9	1216.4	1210.5	1201.6
7.5°	1312.9	1315.8	1305.5	1296.6	1286.2	1275.8	1265.4	1255.0	1244.6	1234.2	1213.5
10°	1296.6	1301.0	1295.1	1289.1	1281.7	1275.8	1263.9	1250.6	1238.7	1225.3	1200.1
12.5°	1250.6	1262.4	1259.5	1256.5	1253.5	1250.6	1243.1	1234.2	1226.8	1217.9	1189.7
15°	1169.0	1169.0	1170.5	1171.9	1171.9	1173.4	1174.9	1176.4	1177.9	1179.4	1163.0
17.5°	1120.0	1115.6	1115.6	1115.6	1115.6	1115.6	1121.5	1128.9	1134.9	1140.8	1136.3
20°	1084.4	1074.0	1072.5	1072.5	1071.1	1069.6	1080.0	1091.8	1102.2	1112.6	1118.5
22.5°	1060.7	1045.8	1044.4	1042.9	1041.4	1039.9	1053.3	1066.6	1080.0	1093.3	1114.1
25°	1054.7	1038.4	1039.9	1041.4	1041.4	1042.9	1053.3	1063.6	1074.0	1084.4	1120.0
27.5°	1056.2	1029.5	1031.0	1032.5	1032.5	1034.0	1050.3	1065.1	1081.4	1096.3	1140.8
30°	1066.6	1035.5	1032.5	1029.5	1026.6	1023.6	1045.8	1068.1	1090.3	1112.6	1146.7
32.5°	1102.2	1072.5	1065.1	1057.7	1050.3	1042.9	1069.6	1094.8	1121.5	1146.7	1174.9
35°	1140.8	1108.2	1105.2	1102.2	1097.8	1094.8	1118.5	1143.8	1167.5	1191.2	1216.4
37.5°	1198.6	1166.0	1163.0	1158.6	1155.6	1151.2	1177.9	1203.1	1229.8	1255.0	1277.3
40°	1284.7	1258.0	1256.5	1256.5	1255.0	1253.5	1274.3	1296.6	1317.3	1338.1	1352.9
42.5°	1398.9	1385.6	1390.0	1395.9	1400.4	1404.8	1421.2	1439.0	1455.3	1471.6	1467.1
45°	1563.6	1576.9	1578.4	1579.9	1581.4	1582.9	1587.3	1593.2	1597.7	1602.1	1584.3
47.5°	1753.5	1771.3	1780.2	1789.1	1796.5	1805.4	1799.4	1792.0	1786.1	1778.7	1734.2
50°	1978.9	2016.0	2014.5	2013.1	2010.1	2008.6	1996.7	1984.9	1971.5	1959.7	1894.4
52.5°	2157.0	2198.5	2205.9	2213.3	2220.8	2228.2	2205.9	2183.7	2159.9	2137.7	2056.1
55°	2348.3	2391.3	2392.8	2394.3	2394.3	2395.8	2364.6	2333.5	2300.9	2269.7	2185.1
57.5°	2490.7	2532.3	2527.8	2524.9	2520.4	2516.0	2478.9	2441.8	2404.7	2367.6	2283.1
60°	2544.1	2579.7	2570.8	2561.9	2551.6	2542.7	2514.5	2486.3	2456.6	2428.4	2346.8
62.5°	2518.9	2545.6	2532.3	2520.4	2507.1	2493.7	2458.1	2421.0	2385.4	2348.3	2289.0
65°	2352.8	2369.1	2351.3	2335.0	2318.7	2300.9	2271.2	2241.5	2210.4	2180.7	2140.6
67.5°	2072.4	2075.4	2073.9	2072.4	2070.9	2069.4	2026.4	1983.4	1938.9	1895.9	1892.9
70°	1688.2	1670.4	1673.4	1677.8	1680.8	1683.7	1651.1	1619.9	1587.3	1554.7	1569.5
72.5°	1302.5	1271.3	1278.7	1287.6	1295.1	1302.5	1275.8	1250.6	1223.9	1197.2	1217.9
75°	967.2	947.9	955.4	964.3	971.7	979.1	968.7	958.3	946.5	936.1	955.4
77.5°	737.3	725.4	726.9	726.9	728.4	728.4	729.9	732.8	734.3	735.8	756.6
80°	600.8	599.3	597.8	596.4	593.4	591.9	606.7	621.6	636.4	651.2	661.6
82.5°	525.1	540.0	531.1	523.7	514.8	505.9	519.2	532.6	545.9	559.3	554.8
85°	427.2	445.0	428.7	412.4	394.6	378.3	390.2	400.5	412.4	422.8	416.9
87.5°	169.1	173.6	146.9	121.6	94.9	68.2	108.3	146.9	186.9	225.5	231.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1	1068.1
2.5°	1152.7	1146.7	1142.3	1140.8	1137.8	1136.3	1133.4	1130.4	1126.0	1123.0	1118.5
5°	1191.2	1182.3	1171.9	1157.1	1143.8	1128.9	1114.1	1100.7	1087.4	1072.5	1059.2
7.5°	1192.7	1171.9	1151.2	1131.9	1111.1	1091.8	1071.1	1053.3	1034.0	1014.7	996.9
10°	1176.4	1151.2	1126.0	1100.7	1077.0	1051.8	1026.6	1005.8	983.5	961.3	940.5
12.5°	1163.0	1134.9	1106.7	1077.0	1048.8	1019.1	989.5	968.7	947.9	927.2	906.4
15°	1146.7	1128.9	1112.6	1085.9	1059.2	1032.5	1005.8	977.6	950.9	922.7	894.5
17.5°	1133.4	1128.9	1124.5	1106.7	1088.9	1069.6	1051.8	1023.6	995.4	965.7	937.6
20°	1126.0	1131.9	1137.8	1128.9	1120.0	1109.6	1100.7	1080.0	1059.2	1036.9	1016.2
22.5°	1134.9	1157.1	1177.9	1179.4	1182.3	1183.8	1185.3	1166.0	1146.7	1126.0	1106.7
25°	1155.6	1191.2	1226.8	1246.1	1265.4	1286.2	1305.5	1293.6	1281.7	1269.8	1258.0
27.5°	1183.8	1228.3	1272.8	1301.0	1327.7	1355.9	1384.1	1382.6	1381.1	1378.1	1376.7
30°	1179.4	1213.5	1247.6	1281.7	1315.8	1350.0	1384.1	1401.9	1418.2	1436.0	1453.8
32.5°	1204.6	1232.8	1262.4	1298.0	1333.6	1370.7	1406.3	1443.4	1479.0	1516.1	1553.2
35°	1243.1	1268.4	1295.1	1333.6	1373.7	1412.3	1452.3	1496.8	1542.8	1588.8	1633.3
37.5°	1301.0	1323.3	1347.0	1379.6	1413.7	1446.4	1480.5	1545.8	1611.0	1677.8	1743.1
40°	1367.8	1382.6	1397.4	1428.6	1459.7	1490.9	1522.0	1603.6	1685.2	1766.8	1848.4
42.5°	1464.2	1459.7	1455.3	1480.5	1507.2	1532.4	1559.1	1633.3	1707.5	1781.6	1855.8
45°	1566.5	1548.7	1530.9	1542.8	1556.2	1568.0	1581.4	1657.0	1732.7	1809.8	1885.5
47.5°	1689.7	1645.2	1600.7	1590.3	1579.9	1568.0	1557.6	1639.2	1720.8	1803.9	1885.5
50°	1829.1	1762.4	1697.1	1670.4	1642.2	1615.5	1587.3	1654.1	1722.3	1790.5	1857.3
52.5°	1974.5	1891.4	1809.8	1768.3	1726.8	1683.7	1642.2	1698.6	1756.4	1814.3	1870.7
55°	2099.1	2014.5	1928.5	1879.6	1830.6	1781.6	1732.7	1789.1	1845.4	1901.8	1958.2
57.5°	2198.5	2113.9	2029.4	1983.4	1935.9	1889.9	1842.5	1895.9	1950.8	2005.6	2059.1
60°	2266.7	2185.1	2103.6	2059.1	2014.5	1970.0	1925.5	1989.3	2053.1	2118.4	2182.2
62.5°	2231.1	2171.8	2112.5	2093.2	2073.9	2053.1	2033.8	2094.7	2154.0	2214.8	2275.6
65°	2100.6	2060.5	2020.5	2039.8	2060.5	2079.8	2100.6	2140.6	2180.7	2222.2	2262.3
67.5°	1888.5	1885.5	1881.0	1924.1	1967.1	2011.6	2054.6	2081.3	2106.5	2133.2	2159.9
70°	1584.3	1600.7	1615.5	1689.7	1763.8	1838.0	1912.2	1922.6	1933.0	1943.3	1953.7
72.5°	1240.2	1260.9	1283.2	1381.1	1477.5	1575.4	1673.4	1667.4	1661.5	1654.1	1648.1
75°	976.1	995.4	1016.2	1106.7	1197.2	1287.6	1378.1	1352.9	1329.2	1304.0	1278.7
77.5°	778.8	799.6	821.8	906.4	991.0	1077.0	1161.6	1100.7	1039.9	979.1	918.3
80°	670.5	680.9	689.8	747.7	804.0	861.9	919.7	857.4	793.7	729.9	667.6
82.5°	550.4	544.4	540.0	574.1	608.2	642.3	676.5	617.1	557.8	497.0	437.6
85°	410.9	405.0	399.1	416.9	434.7	453.9	471.7	403.5	335.3	265.5	197.3
87.5°	238.8	244.8	250.7	270.0	289.3	310.0	329.3	259.6	189.9	118.7	49.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1068.1	1068.1
2.5°	1109.6	1102.2
5°	1048.8	1038.4
7.5°	982.1	968.7
10°	921.2	903.4
12.5°	882.7	860.4
15°	867.8	841.1
17.5°	912.3	887.1
20°	980.6	946.5
22.5°	1063.6	1022.1
25°	1207.5	1157.1
27.5°	1324.7	1272.8
30°	1397.4	1341.1
32.5°	1477.5	1403.4
35°	1560.6	1489.4
37.5°	1661.5	1581.4
40°	1765.3	1682.3
42.5°	1800.9	1747.5
45°	1835.0	1784.6
47.5°	1842.5	1800.9
50°	1849.9	1844.0
52.5°	1870.7	1869.2
55°	1959.7	1961.1
57.5°	2069.4	2078.3
60°	2170.3	2159.9
62.5°	2222.2	2168.8
65°	2186.6	2112.5
67.5°	2079.8	1999.7
70°	1845.4	1737.1
72.5°	1553.2	1458.2
75°	1197.2	1117.1
77.5°	851.5	784.8
80°	599.3	532.6
82.5°	384.2	330.8
85°	173.6	151.3
87.5°	49.0	47.5
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P671784

CATALOG NUMBER: CCP-SA-2A-722-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)