

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671794

Luminaire Tested: **CCP-SA-1F-727-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671794
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1F-727-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @1200mA w/ SLR
distribution lens
Light Source: (16) 2700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5203.6 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 67
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 7.4 fc
 Type IV - Short - N/A

REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1070.7	0.0	1070.7
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	4132.9	0.0	4132.9
	% Fixture	79.4	0.0	79.4
Total	Lumens	5203.6	0.0	5203.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.1	2.5
10°-20°	272.6	5.2
20°-30°	398.9	7.7
30°-40°	561.9	10.8
40°-50°	772.1	14.8
50°-60°	1052.4	20.2
60°-70°	1151.9	22.1
70°-80°	665.2	12.8
80°-90°	199.4	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5203.6	100.0
0°-180°	5203.6	100.0

Coefficient of Utilization



REPORT NUMBER: P671794


CATALOG NUMBER: CCP-SA-1F-727-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	534.4	10.3			
FM	(30°-60°)	1898.9	36.5			
FH	(60°-80°)	1530.2	29.4			G1/1800
FVH	(80°-90°)	169.4	3.3			G2/225
BL	(0°-30°)	266.2	5.1	B1/500		
BM	(30°-60°)	487.5	9.4	B1/1000		
BH	(60°-80°)	286.9	5.5	B1/500		G1/500
BVH	(80°-90°)	30.0	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7
2.5°	1714.8	1705.5	1698.6	1691.7	1682.5	1675.5	1666.3	1657.1	1645.5	1636.3	1624.8
5°	1615.5	1587.8	1560.1	1544.0	1525.5	1509.4	1490.9	1470.1	1449.4	1426.3	1405.5
7.5°	1507.1	1472.4	1437.8	1410.1	1380.1	1352.4	1322.4	1297.0	1271.7	1246.3	1220.9
10°	1405.5	1373.2	1340.9	1306.3	1269.3	1234.7	1197.8	1163.2	1128.6	1093.9	1059.3
12.5°	1338.6	1299.4	1262.4	1223.2	1186.3	1147.0	1107.8	1075.5	1043.2	1008.6	976.2
15°	1308.6	1271.7	1237.0	1197.8	1158.6	1119.3	1080.1	1043.2	1008.6	971.6	934.7
17.5°	1380.1	1327.0	1274.0	1223.2	1172.4	1121.6	1070.9	1024.7	978.6	932.4	886.2
20°	1472.4	1405.5	1340.9	1278.6	1214.0	1151.6	1087.0	1022.4	957.8	893.2	828.5
22.5°	1590.1	1514.0	1440.1	1359.4	1276.3	1195.5	1112.4	1031.6	950.9	867.8	787.0
25°	1800.2	1710.2	1620.2	1504.8	1387.1	1271.7	1154.0	1047.8	943.9	837.8	731.6
27.5°	1980.2	1857.9	1737.9	1599.4	1460.9	1322.4	1184.0	1061.6	941.6	819.3	697.0
30°	2086.3	1966.3	1846.3	1677.8	1511.7	1343.2	1174.7	1038.6	904.7	768.5	632.4
32.5°	2183.3	2049.4	1915.6	1730.9	1544.0	1359.4	1172.4	1022.4	874.7	724.7	574.7
35°	2317.1	2169.4	2024.0	1809.4	1594.8	1380.1	1165.5	1010.9	853.9	699.3	542.4
37.5°	2460.2	2277.9	2097.9	1860.2	1622.5	1384.7	1147.0	994.7	842.4	690.1	537.7
40°	2617.2	2395.6	2176.4	1913.3	1652.5	1389.4	1126.3	973.9	821.6	667.0	514.7
42.5°	2718.7	2478.7	2238.7	1954.8	1673.2	1389.4	1105.5	955.5	805.5	653.1	503.1
45°	2776.4	2543.3	2312.5	2005.6	1698.6	1391.7	1084.7	937.0	789.3	639.3	491.6
47.5°	2801.8	2584.9	2367.9	2044.8	1724.0	1400.9	1077.8	927.8	775.5	625.4	473.1
50°	2868.7	2677.2	2485.6	2139.4	1795.6	1449.4	1103.2	941.6	782.4	620.8	459.3
52.5°	2908.0	2744.1	2580.2	2224.8	1869.4	1514.0	1158.6	978.6	798.5	618.5	438.5
55°	3051.1	2894.1	2737.2	2358.7	1977.9	1599.4	1218.6	1020.1	821.6	620.8	422.3
57.5°	3233.4	3067.2	2903.3	2494.8	2086.3	1677.8	1269.3	1057.0	842.4	630.1	415.4
60°	3360.3	3198.8	3039.5	2605.6	2169.4	1735.5	1299.4	1077.8	856.2	632.4	410.8
62.5°	3374.2	3166.4	2961.0	2538.7	2116.4	1691.7	1269.3	1054.7	840.1	623.1	408.5
65°	3286.5	3044.1	2801.8	2397.9	1994.0	1590.1	1186.3	990.1	793.9	595.4	399.3
67.5°	3111.1	2827.2	2543.3	2174.0	1804.8	1435.5	1066.3	897.8	731.6	563.1	394.7
70°	2702.6	2453.3	2206.4	1885.6	1567.1	1246.3	925.5	787.0	650.8	512.4	373.9
72.5°	2268.7	2035.6	1804.8	1544.0	1285.5	1024.7	763.9	660.1	556.2	450.0	346.2
75°	1737.9	1562.5	1389.4	1195.5	1001.6	805.5	611.6	535.4	459.3	383.1	307.0
77.5°	1220.9	1126.3	1033.9	888.5	743.1	597.7	452.3	401.6	350.8	300.0	249.3
80°	828.5	775.5	724.7	620.8	517.0	410.8	307.0	274.6	240.0	207.7	173.1
82.5°	514.7	512.4	507.7	436.2	364.6	293.1	221.6	193.9	168.5	140.8	113.1
85°	235.4	274.6	311.6	272.3	233.1	193.9	154.6	136.2	117.7	96.9	78.5
87.5°	73.9	90.0	103.9	99.2	92.3	87.7	80.8	69.2	57.7	46.2	34.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7
2.5°	1615.5	1608.6	1599.4	1590.1	1578.6	1569.4	1557.8	1546.3	1544.0	1539.4	1537.1
5°	1391.7	1377.8	1361.7	1347.8	1334.0	1317.8	1304.0	1287.8	1276.3	1262.4	1250.9
7.5°	1195.5	1172.4	1147.0	1121.6	1098.6	1075.5	1050.1	1027.0	1015.5	1003.9	992.4
10°	1038.6	1015.5	994.7	971.6	955.5	941.6	925.5	909.3	895.5	881.6	867.8
12.5°	960.1	943.9	927.8	911.6	893.2	877.0	858.5	840.1	823.9	810.1	793.9
15°	911.6	888.5	863.2	840.1	814.7	791.6	766.2	740.8	722.4	706.2	687.8
17.5°	853.9	819.3	787.0	752.4	724.7	697.0	667.0	639.3	618.5	595.4	574.7
20°	789.3	750.1	708.5	669.3	637.0	607.0	574.7	542.4	519.3	493.9	470.8
22.5°	733.9	683.1	630.1	577.0	542.4	507.7	470.8	436.2	415.4	392.3	371.6
25°	673.9	618.5	560.8	503.1	468.5	431.6	397.0	360.0	343.9	330.0	313.9
27.5°	641.6	586.2	528.5	473.1	440.8	406.2	373.9	339.3	327.7	313.9	302.3
30°	577.0	523.9	468.5	413.1	390.0	369.3	346.2	323.1	318.5	316.2	311.6
32.5°	519.3	463.9	408.5	353.1	332.3	311.6	290.8	270.0	267.7	263.1	260.8
35°	489.3	436.2	380.8	327.7	309.3	288.5	270.0	249.3	244.6	237.7	233.1
37.5°	482.4	427.0	369.3	313.9	295.4	276.9	256.2	237.7	233.1	228.5	223.9
40°	463.9	410.8	360.0	307.0	288.5	270.0	249.3	230.8	226.2	221.6	216.9
42.5°	450.0	399.3	346.2	293.1	276.9	260.8	242.3	226.2	221.6	216.9	210.0
45°	438.5	385.4	330.0	276.9	265.4	253.9	240.0	228.5	223.9	216.9	212.3
47.5°	420.0	369.3	316.2	263.1	251.6	242.3	230.8	219.3	214.6	210.0	205.4
50°	406.2	353.1	300.0	246.9	237.7	228.5	219.3	210.0	210.0	212.3	212.3
52.5°	387.7	337.0	286.2	235.4	226.2	216.9	207.7	198.5	200.8	203.1	205.4
55°	371.6	323.1	272.3	221.6	212.3	203.1	191.6	182.3	184.6	186.9	189.2
57.5°	364.6	313.9	263.1	212.3	203.1	191.6	182.3	170.8	170.8	170.8	170.8
60°	360.0	307.0	256.2	203.1	191.6	182.3	170.8	159.2	156.9	156.9	154.6
62.5°	357.7	304.6	253.9	200.8	186.9	175.4	161.6	147.7	145.4	143.1	140.8
65°	348.5	300.0	249.3	198.5	182.3	168.5	152.3	136.2	133.9	133.9	131.6
67.5°	346.2	295.4	246.9	196.2	180.0	161.6	145.4	126.9	124.6	122.3	120.0
70°	327.7	283.9	237.7	191.6	173.1	156.9	138.5	120.0	117.7	113.1	110.8
72.5°	304.6	265.4	223.9	182.3	163.9	145.4	126.9	108.5	106.2	103.9	99.2
75°	270.0	233.1	196.2	159.2	143.1	129.2	113.1	96.9	94.6	92.3	87.7
77.5°	221.6	191.6	163.9	133.9	122.3	110.8	99.2	87.7	85.4	83.1	78.5
80°	156.9	138.5	122.3	103.9	96.9	87.7	80.8	71.5	71.5	69.2	69.2
82.5°	103.9	94.6	85.4	76.2	71.5	66.9	62.3	57.7	57.7	55.4	55.4
85°	73.9	69.2	62.3	57.7	55.4	50.8	48.5	43.9	43.9	43.9	43.9
87.5°	34.6	34.6	32.3	32.3	30.0	30.0	27.7	25.4	25.4	25.4	25.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7
2.5°	1532.5	1525.5	1518.6	1509.4	1502.4	1493.2	1481.7	1472.4	1460.9	1460.9	1458.6
5°	1237.0	1230.1	1223.2	1214.0	1207.0	1197.8	1190.9	1181.6	1172.4	1172.4	1170.1
7.5°	980.9	967.0	953.2	937.0	923.2	913.9	904.7	893.2	883.9	877.0	870.1
10°	853.9	840.1	823.9	810.1	793.9	782.4	770.8	757.0	745.5	736.2	727.0
12.5°	777.8	761.6	745.5	729.3	713.1	697.0	683.1	667.0	650.8	639.3	627.8
15°	669.3	653.1	637.0	620.8	604.7	586.2	567.7	547.0	528.5	519.3	512.4
17.5°	551.6	535.4	517.0	500.8	482.4	468.5	454.7	440.8	427.0	417.7	410.8
20°	445.4	427.0	408.5	390.0	371.6	362.3	353.1	343.9	334.6	327.7	323.1
22.5°	348.5	337.0	327.7	316.2	304.6	297.7	293.1	286.2	279.3	279.3	279.3
25°	297.7	290.8	286.2	279.3	272.3	270.0	267.7	263.1	260.8	258.5	258.5
27.5°	288.5	281.6	274.6	267.7	260.8	258.5	256.2	251.6	249.3	249.3	249.3
30°	307.0	304.6	302.3	300.0	297.7	293.1	286.2	281.6	274.6	270.0	265.4
32.5°	256.2	253.9	253.9	251.6	249.3	253.9	256.2	260.8	263.1	265.4	267.7
35°	226.2	221.6	216.9	212.3	207.7	205.4	203.1	200.8	198.5	198.5	196.2
37.5°	219.3	214.6	210.0	205.4	200.8	198.5	196.2	193.9	191.6	191.6	189.2
40°	212.3	207.7	205.4	200.8	196.2	193.9	191.6	186.9	184.6	182.3	182.3
42.5°	205.4	203.1	198.5	196.2	191.6	189.2	186.9	182.3	180.0	177.7	175.4
45°	205.4	200.8	196.2	191.6	186.9	184.6	180.0	177.7	173.1	173.1	170.8
47.5°	200.8	196.2	191.6	186.9	182.3	180.0	175.4	173.1	168.5	166.2	163.9
50°	212.3	205.4	196.2	189.2	180.0	177.7	173.1	170.8	166.2	163.9	161.6
52.5°	207.7	200.8	191.6	184.6	175.4	170.8	168.5	163.9	159.2	156.9	154.6
55°	191.6	184.6	180.0	173.1	166.2	161.6	156.9	152.3	147.7	145.4	145.4
57.5°	170.8	168.5	166.2	163.9	161.6	156.9	152.3	145.4	140.8	138.5	136.2
60°	152.3	154.6	156.9	159.2	161.6	154.6	147.7	140.8	133.9	131.6	129.2
62.5°	138.5	143.1	147.7	150.0	154.6	147.7	140.8	133.9	126.9	124.6	122.3
65°	129.2	131.6	131.6	133.9	133.9	129.2	126.9	122.3	117.7	115.4	115.4
67.5°	117.7	117.7	117.7	115.4	115.4	113.1	113.1	110.8	108.5	106.2	106.2
70°	106.2	106.2	106.2	103.9	103.9	101.5	101.5	99.2	96.9	96.9	94.6
72.5°	96.9	96.9	94.6	94.6	92.3	92.3	92.3	90.0	90.0	87.7	87.7
75°	85.4	85.4	83.1	83.1	80.8	80.8	80.8	78.5	78.5	78.5	76.2
77.5°	76.2	76.2	73.9	73.9	71.5	71.5	71.5	69.2	69.2	66.9	66.9
80°	66.9	66.9	64.6	64.6	62.3	62.3	60.0	60.0	57.7	57.7	55.4
82.5°	53.1	53.1	53.1	53.1	53.1	50.8	50.8	48.5	46.2	46.2	43.9
85°	43.9	43.9	43.9	41.5	41.5	41.5	39.2	39.2	36.9	34.6	34.6
87.5°	25.4	25.4	25.4	23.1	23.1	23.1	23.1	23.1	23.1	23.1	20.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7
2.5°	1458.6	1456.3	1447.1	1437.8	1447.1	1456.3	1456.3	1456.3	1454.0	1454.0	1454.0
5°	1170.1	1167.8	1163.2	1158.6	1158.6	1156.3	1160.9	1165.5	1170.1	1174.7	1179.3
7.5°	860.8	853.9	847.0	840.1	844.7	847.0	853.9	858.5	865.5	870.1	881.6
10°	717.8	708.5	701.6	694.7	690.1	685.4	680.8	678.5	673.9	669.3	673.9
12.5°	613.9	602.4	590.8	577.0	574.7	572.4	567.7	563.1	558.5	553.9	551.6
15°	503.1	493.9	489.3	482.4	473.1	463.9	459.3	457.0	452.3	447.7	445.4
17.5°	401.6	392.3	385.4	378.5	376.2	371.6	371.6	371.6	371.6	371.6	371.6
20°	316.2	309.3	309.3	307.0	307.0	304.6	307.0	309.3	309.3	311.6	313.9
22.5°	276.9	276.9	274.6	272.3	274.6	274.6	276.9	279.3	281.6	283.9	286.2
25°	256.2	253.9	256.2	258.5	258.5	258.5	260.8	260.8	263.1	263.1	263.1
27.5°	246.9	246.9	249.3	249.3	251.6	251.6	251.6	249.3	249.3	246.9	246.9
30°	260.8	256.2	256.2	256.2	253.9	251.6	249.3	249.3	246.9	244.6	242.3
32.5°	270.0	272.3	270.0	265.4	263.1	258.5	256.2	251.6	249.3	244.6	240.0
35°	196.2	193.9	198.5	200.8	203.1	205.4	207.7	210.0	210.0	212.3	212.3
37.5°	189.2	186.9	186.9	184.6	184.6	184.6	184.6	184.6	182.3	182.3	184.6
40°	180.0	177.7	177.7	175.4	175.4	173.1	173.1	173.1	173.1	173.1	173.1
42.5°	173.1	170.8	170.8	170.8	170.8	168.5	168.5	166.2	166.2	163.9	163.9
45°	170.8	168.5	166.2	163.9	163.9	161.6	161.6	161.6	159.2	159.2	159.2
47.5°	161.6	159.2	159.2	156.9	156.9	154.6	154.6	154.6	152.3	152.3	152.3
50°	156.9	154.6	154.6	152.3	152.3	150.0	150.0	150.0	147.7	147.7	147.7
52.5°	150.0	147.7	147.7	147.7	145.4	143.1	143.1	143.1	140.8	140.8	140.8
55°	143.1	140.8	140.8	140.8	138.5	136.2	136.2	136.2	133.9	133.9	133.9
57.5°	133.9	131.6	131.6	129.2	129.2	129.2	129.2	129.2	126.9	126.9	126.9
60°	126.9	124.6	124.6	122.3	122.3	120.0	120.0	120.0	120.0	120.0	120.0
62.5°	120.0	117.7	115.4	113.1	115.4	115.4	115.4	115.4	113.1	113.1	113.1
65°	113.1	110.8	108.5	106.2	106.2	106.2	106.2	106.2	106.2	106.2	106.2
67.5°	103.9	101.5	99.2	96.9	99.2	99.2	99.2	99.2	99.2	99.2	99.2
70°	94.6	92.3	92.3	90.0	90.0	87.7	87.7	90.0	90.0	90.0	90.0
72.5°	85.4	83.1	83.1	80.8	80.8	80.8	80.8	80.8	80.8	80.8	80.8
75°	76.2	73.9	73.9	71.5	71.5	71.5	71.5	71.5	71.5	71.5	71.5
77.5°	64.6	62.3	62.3	62.3	62.3	62.3	62.3	64.6	64.6	64.6	64.6
80°	55.4	53.1	53.1	53.1	53.1	53.1	53.1	53.1	53.1	53.1	53.1
82.5°	43.9	41.5	41.5	41.5	41.5	41.5	41.5	41.5	41.5	41.5	41.5
85°	32.3	30.0	30.0	30.0	32.3	32.3	32.3	32.3	32.3	32.3	32.3
87.5°	20.8	18.5	18.5	18.5	20.8	20.8	20.8	20.8	18.5	18.5	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7
2.5°	1454.0	1454.0	1454.0	1451.7	1449.4	1447.1	1444.8	1451.7	1456.3	1463.2	1467.8
5°	1181.6	1186.3	1188.6	1195.5	1202.4	1209.3	1216.3	1220.9	1225.5	1227.8	1232.4
7.5°	890.9	902.4	911.6	920.9	930.1	937.0	946.2	953.2	960.1	967.0	973.9
10°	676.2	680.8	683.1	692.4	699.3	708.5	715.5	722.4	729.3	733.9	740.8
12.5°	549.3	544.7	542.4	542.4	542.4	542.4	542.4	547.0	551.6	556.2	560.8
15°	443.1	440.8	438.5	436.2	433.9	429.3	427.0	431.6	436.2	440.8	445.4
17.5°	371.6	371.6	371.6	369.3	367.0	364.6	362.3	364.6	367.0	367.0	369.3
20°	318.5	320.8	323.1	325.4	325.4	327.7	327.7	330.0	332.3	332.3	334.6
22.5°	286.2	288.5	288.5	288.5	290.8	290.8	290.8	293.1	295.4	297.7	300.0
25°	260.8	260.8	258.5	258.5	260.8	260.8	260.8	260.8	263.1	263.1	263.1
27.5°	246.9	244.6	244.6	244.6	244.6	242.3	242.3	242.3	242.3	242.3	242.3
30°	240.0	237.7	235.4	233.1	233.1	230.8	228.5	228.5	228.5	228.5	228.5
32.5°	237.7	233.1	228.5	226.2	226.2	223.9	221.6	219.3	219.3	216.9	214.6
35°	212.3	210.0	210.0	207.7	205.4	203.1	200.8	200.8	200.8	198.5	198.5
37.5°	184.6	186.9	186.9	186.9	189.2	189.2	189.2	189.2	191.6	191.6	191.6
40°	173.1	173.1	173.1	175.4	177.7	177.7	180.0	180.0	182.3	182.3	182.3
42.5°	163.9	161.6	161.6	163.9	163.9	166.2	166.2	168.5	170.8	170.8	173.1
45°	159.2	156.9	156.9	156.9	156.9	154.6	154.6	156.9	159.2	161.6	163.9
47.5°	150.0	150.0	147.7	147.7	147.7	147.7	147.7	147.7	150.0	150.0	150.0
50°	145.4	145.4	143.1	143.1	143.1	143.1	143.1	143.1	143.1	143.1	143.1
52.5°	140.8	138.5	138.5	138.5	138.5	136.2	136.2	136.2	136.2	136.2	136.2
55°	133.9	131.6	131.6	131.6	131.6	131.6	131.6	131.6	133.9	133.9	133.9
57.5°	126.9	124.6	124.6	124.6	126.9	126.9	126.9	126.9	129.2	129.2	129.2
60°	120.0	120.0	120.0	120.0	120.0	120.0	120.0	122.3	122.3	124.6	124.6
62.5°	113.1	113.1	113.1	113.1	115.4	115.4	115.4	115.4	117.7	117.7	117.7
65°	106.2	106.2	106.2	106.2	108.5	108.5	108.5	108.5	108.5	108.5	108.5
67.5°	99.2	99.2	99.2	99.2	99.2	99.2	99.2	101.5	101.5	103.9	103.9
70°	90.0	87.7	87.7	90.0	90.0	92.3	92.3	94.6	94.6	96.9	96.9
72.5°	80.8	80.8	80.8	80.8	80.8	80.8	80.8	83.1	85.4	85.4	87.7
75°	71.5	71.5	71.5	71.5	73.9	73.9	73.9	76.2	76.2	78.5	78.5
77.5°	64.6	62.3	62.3	62.3	64.6	64.6	64.6	66.9	66.9	69.2	69.2
80°	53.1	53.1	53.1	53.1	55.4	55.4	55.4	55.4	57.7	57.7	57.7
82.5°	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9	46.2	46.2	46.2
85°	32.3	32.3	32.3	32.3	34.6	34.6	34.6	34.6	34.6	34.6	34.6
87.5°	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8	23.1	23.1	23.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7
2.5°	1467.8	1467.8	1467.8	1467.8	1472.4	1474.8	1479.4	1481.7	1479.4	1477.1	1472.4
5°	1234.7	1237.0	1237.0	1239.3	1239.3	1239.3	1239.3	1239.3	1244.0	1248.6	1253.2
7.5°	976.2	978.6	980.9	983.2	983.2	983.2	980.9	980.9	983.2	983.2	985.5
10°	747.8	757.0	763.9	770.8	766.2	759.3	754.7	747.8	747.8	747.8	745.5
12.5°	565.4	567.7	572.4	574.7	572.4	572.4	570.1	567.7	570.1	574.7	577.0
15°	447.7	447.7	450.0	450.0	452.3	454.7	454.7	457.0	461.6	463.9	468.5
17.5°	371.6	373.9	373.9	376.2	376.2	378.5	378.5	378.5	383.1	387.7	394.7
20°	334.6	334.6	334.6	334.6	334.6	332.3	332.3	330.0	332.3	337.0	339.3
22.5°	300.0	302.3	302.3	302.3	300.0	297.7	293.1	290.8	290.8	293.1	293.1
25°	263.1	260.8	260.8	258.5	258.5	260.8	260.8	260.8	263.1	263.1	265.4
27.5°	242.3	240.0	240.0	237.7	237.7	240.0	240.0	240.0	240.0	240.0	240.0
30°	226.2	226.2	223.9	221.6	223.9	223.9	226.2	226.2	228.5	228.5	230.8
32.5°	214.6	212.3	212.3	210.0	212.3	212.3	214.6	214.6	216.9	219.3	219.3
35°	198.5	198.5	198.5	198.5	198.5	198.5	196.2	196.2	196.2	196.2	196.2
37.5°	189.2	189.2	186.9	184.6	184.6	184.6	184.6	184.6	182.3	180.0	177.7
40°	182.3	180.0	180.0	177.7	175.4	175.4	173.1	170.8	170.8	168.5	168.5
42.5°	173.1	170.8	170.8	168.5	166.2	166.2	163.9	161.6	161.6	161.6	159.2
45°	161.6	161.6	159.2	156.9	156.9	156.9	154.6	154.6	154.6	154.6	152.3
47.5°	150.0	150.0	147.7	147.7	147.7	147.7	145.4	145.4	145.4	145.4	145.4
50°	143.1	143.1	143.1	143.1	143.1	143.1	140.8	140.8	140.8	140.8	140.8
52.5°	136.2	136.2	136.2	136.2	136.2	136.2	136.2	136.2	136.2	136.2	136.2
55°	133.9	133.9	133.9	133.9	133.9	133.9	131.6	131.6	131.6	133.9	133.9
57.5°	129.2	129.2	126.9	126.9	126.9	126.9	126.9	126.9	126.9	126.9	126.9
60°	124.6	124.6	124.6	124.6	124.6	124.6	124.6	124.6	124.6	124.6	124.6
62.5°	117.7	117.7	117.7	117.7	117.7	120.0	120.0	120.0	120.0	120.0	117.7
65°	108.5	110.8	110.8	110.8	110.8	110.8	110.8	110.8	110.8	110.8	110.8
67.5°	103.9	103.9	103.9	103.9	103.9	103.9	103.9	103.9	103.9	103.9	103.9
70°	96.9	96.9	94.6	94.6	94.6	96.9	96.9	96.9	96.9	96.9	96.9
72.5°	87.7	87.7	87.7	87.7	87.7	87.7	87.7	87.7	87.7	90.0	90.0
75°	78.5	78.5	78.5	78.5	78.5	78.5	78.5	78.5	78.5	78.5	78.5
77.5°	69.2	69.2	66.9	66.9	66.9	69.2	69.2	69.2	69.2	71.5	71.5
80°	57.7	57.7	57.7	57.7	57.7	57.7	57.7	57.7	57.7	60.0	60.0
82.5°	46.2	46.2	46.2	46.2	46.2	46.2	46.2	46.2	46.2	48.5	48.5
85°	34.6	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9	39.2	39.2
87.5°	23.1	23.1	23.1	23.1	23.1	23.1	20.8	20.8	20.8	20.8	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7
2.5°	1470.1	1472.4	1474.8	1474.8	1477.1	1479.4	1479.4	1488.6	1497.8	1502.4	1507.1
5°	1257.8	1255.5	1255.5	1253.2	1250.9	1257.8	1264.7	1278.6	1292.4	1294.7	1299.4
7.5°	985.5	987.8	990.1	990.1	992.4	985.5	976.2	978.6	980.9	992.4	1001.6
10°	745.5	747.8	750.1	750.1	752.4	750.1	745.5	752.4	759.3	768.5	780.1
12.5°	579.3	586.2	593.1	597.7	604.7	609.3	611.6	620.8	627.8	639.3	650.8
15°	473.1	477.7	482.4	487.0	491.6	496.2	500.8	510.0	519.3	533.1	547.0
17.5°	399.3	399.3	401.6	401.6	401.6	406.2	410.8	415.4	417.7	431.6	445.4
20°	341.6	339.3	337.0	334.6	332.3	337.0	339.3	341.6	343.9	353.1	360.0
22.5°	293.1	293.1	295.4	295.4	295.4	293.1	288.5	290.8	290.8	295.4	302.3
25°	265.4	265.4	265.4	263.1	263.1	265.4	267.7	267.7	265.4	267.7	270.0
27.5°	240.0	242.3	242.3	244.6	244.6	246.9	246.9	246.9	246.9	249.3	251.6
30°	230.8	230.8	233.1	233.1	233.1	235.4	237.7	237.7	237.7	240.0	244.6
32.5°	221.6	223.9	226.2	228.5	230.8	233.1	233.1	235.4	235.4	237.7	240.0
35°	196.2	193.9	193.9	191.6	189.2	189.2	189.2	189.2	186.9	189.2	189.2
37.5°	175.4	175.4	175.4	173.1	173.1	175.4	175.4	175.4	175.4	177.7	177.7
40°	166.2	166.2	166.2	166.2	166.2	166.2	166.2	168.5	168.5	170.8	173.1
42.5°	159.2	159.2	159.2	159.2	159.2	161.6	161.6	161.6	161.6	163.9	163.9
45°	152.3	152.3	152.3	152.3	152.3	152.3	152.3	154.6	154.6	156.9	159.2
47.5°	145.4	145.4	145.4	145.4	145.4	147.7	150.0	150.0	150.0	152.3	152.3
50°	140.8	140.8	140.8	140.8	140.8	143.1	143.1	145.4	145.4	147.7	150.0
52.5°	136.2	136.2	136.2	136.2	136.2	138.5	138.5	140.8	140.8	143.1	145.4
55°	133.9	133.9	133.9	131.6	131.6	133.9	133.9	136.2	136.2	138.5	138.5
57.5°	126.9	126.9	126.9	126.9	126.9	126.9	126.9	129.2	129.2	131.6	133.9
60°	124.6	124.6	122.3	122.3	120.0	122.3	122.3	124.6	124.6	126.9	126.9
62.5°	117.7	117.7	117.7	115.4	115.4	117.7	117.7	117.7	117.7	120.0	122.3
65°	110.8	110.8	110.8	108.5	108.5	110.8	110.8	110.8	110.8	113.1	115.4
67.5°	103.9	103.9	103.9	101.5	101.5	101.5	101.5	103.9	103.9	106.2	108.5
70°	96.9	96.9	96.9	94.6	94.6	94.6	92.3	94.6	96.9	99.2	99.2
72.5°	90.0	90.0	90.0	87.7	87.7	87.7	85.4	87.7	87.7	90.0	90.0
75°	78.5	78.5	78.5	78.5	78.5	78.5	76.2	76.2	76.2	78.5	78.5
77.5°	71.5	71.5	71.5	69.2	69.2	69.2	66.9	66.9	66.9	69.2	69.2
80°	60.0	60.0	60.0	57.7	57.7	57.7	55.4	55.4	55.4	57.7	57.7
82.5°	48.5	48.5	48.5	46.2	46.2	46.2	43.9	43.9	43.9	46.2	46.2
85°	39.2	39.2	39.2	39.2	39.2	39.2	36.9	36.9	36.9	39.2	41.5
87.5°	18.5	18.5	20.8	20.8	20.8	20.8	18.5	18.5	16.2	16.2	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7
2.5°	1511.7	1516.3	1527.8	1537.1	1548.6	1557.8	1564.8	1574.0	1580.9	1587.8	1592.5
5°	1301.7	1304.0	1315.5	1327.0	1336.3	1347.8	1364.0	1380.1	1396.3	1412.4	1424.0
7.5°	1013.2	1022.4	1036.3	1052.4	1066.3	1080.1	1096.3	1114.7	1130.9	1147.0	1163.2
10°	789.3	798.5	812.4	826.2	837.8	851.6	870.1	888.5	907.0	925.5	943.9
12.5°	662.4	673.9	690.1	706.2	720.1	736.2	759.3	780.1	803.2	823.9	847.0
15°	558.5	572.4	593.1	616.2	637.0	657.8	680.8	703.9	724.7	747.8	770.8
17.5°	459.3	473.1	491.6	512.4	530.8	549.3	577.0	602.4	630.1	655.4	680.8
20°	369.3	376.2	394.7	413.1	431.6	450.0	470.8	491.6	512.4	533.1	565.4
22.5°	307.0	311.6	320.8	327.7	337.0	343.9	364.6	385.4	403.9	424.7	454.7
25°	270.0	272.3	279.3	283.9	290.8	295.4	309.3	320.8	334.6	346.2	373.9
27.5°	251.6	253.9	256.2	258.5	260.8	263.1	272.3	281.6	288.5	297.7	323.1
30°	246.9	249.3	256.2	260.8	267.7	272.3	276.9	281.6	286.2	290.8	307.0
32.5°	242.3	244.6	244.6	242.3	242.3	240.0	244.6	246.9	251.6	253.9	267.7
35°	191.6	191.6	193.9	196.2	198.5	200.8	207.7	212.3	219.3	223.9	235.4
37.5°	180.0	180.0	182.3	186.9	189.2	191.6	196.2	200.8	205.4	210.0	221.6
40°	173.1	175.4	177.7	180.0	182.3	184.6	189.2	191.6	196.2	198.5	207.7
42.5°	166.2	166.2	168.5	173.1	175.4	177.7	182.3	184.6	189.2	191.6	200.8
45°	161.6	163.9	166.2	168.5	168.5	170.8	175.4	180.0	182.3	186.9	196.2
47.5°	154.6	154.6	159.2	161.6	166.2	168.5	173.1	175.4	180.0	182.3	191.6
50°	150.0	152.3	156.9	159.2	163.9	166.2	173.1	177.7	184.6	189.2	193.9
52.5°	145.4	147.7	152.3	154.6	159.2	161.6	170.8	180.0	186.9	196.2	196.2
55°	140.8	140.8	145.4	152.3	156.9	161.6	166.2	173.1	177.7	182.3	182.3
57.5°	133.9	136.2	140.8	147.7	152.3	156.9	161.6	166.2	168.5	173.1	170.8
60°	129.2	129.2	136.2	143.1	150.0	156.9	156.9	156.9	154.6	154.6	154.6
62.5°	122.3	124.6	133.9	145.4	154.6	163.9	156.9	150.0	143.1	136.2	138.5
65°	117.7	120.0	124.6	131.6	136.2	140.8	136.2	133.9	129.2	124.6	126.9
67.5°	108.5	110.8	113.1	113.1	115.4	115.4	115.4	115.4	115.4	115.4	117.7
70°	101.5	101.5	101.5	103.9	103.9	103.9	103.9	103.9	103.9	103.9	106.2
72.5°	92.3	92.3	92.3	92.3	92.3	92.3	92.3	92.3	92.3	92.3	94.6
75°	80.8	80.8	80.8	80.8	80.8	80.8	80.8	80.8	80.8	80.8	83.1
77.5°	71.5	71.5	71.5	71.5	71.5	71.5	71.5	71.5	69.2	69.2	71.5
80°	60.0	60.0	60.0	60.0	57.7	57.7	57.7	57.7	57.7	57.7	60.0
82.5°	48.5	48.5	48.5	48.5	46.2	46.2	46.2	46.2	43.9	43.9	46.2
85°	43.9	46.2	46.2	48.5	48.5	48.5	46.2	43.9	41.5	39.2	39.2
87.5°	18.5	18.5	18.5	18.5	16.2	16.2	16.2	16.2	16.2	16.2	16.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7
2.5°	1599.4	1604.0	1608.6	1615.5	1624.8	1631.7	1638.6	1652.5	1668.6	1682.5	1696.3
5°	1435.5	1447.1	1458.6	1472.4	1486.3	1497.8	1511.7	1539.4	1567.1	1592.5	1620.2
7.5°	1177.0	1193.2	1207.0	1230.1	1250.9	1274.0	1294.7	1329.4	1361.7	1396.3	1428.6
10°	962.4	980.9	999.3	1029.3	1061.6	1091.6	1121.6	1149.3	1179.3	1207.0	1234.7
12.5°	870.1	890.9	913.9	932.4	953.2	971.6	990.1	1022.4	1054.7	1087.0	1119.3
15°	793.9	817.0	840.1	863.2	883.9	907.0	927.8	955.5	985.5	1013.2	1040.9
17.5°	706.2	729.3	754.7	780.1	805.5	830.8	856.2	895.5	934.7	971.6	1010.9
20°	595.4	627.8	657.8	692.4	727.0	761.6	796.2	837.8	879.3	918.5	960.1
22.5°	484.7	514.7	544.7	586.2	627.8	667.0	708.5	763.9	817.0	872.4	925.5
25°	403.9	431.6	459.3	505.4	549.3	595.4	639.3	706.2	770.8	837.8	902.4
27.5°	348.5	373.9	399.3	447.7	496.2	542.4	590.8	664.7	736.2	810.1	881.6
30°	323.1	339.3	355.4	401.6	447.7	491.6	537.7	609.3	680.8	752.4	823.9
32.5°	281.6	295.4	309.3	350.8	392.3	431.6	473.1	547.0	618.5	692.4	763.9
35°	249.3	260.8	272.3	311.6	348.5	387.7	424.7	498.5	572.4	646.2	720.1
37.5°	230.8	242.3	251.6	286.2	323.1	357.7	392.3	466.2	537.7	611.6	683.1
40°	216.9	223.9	233.1	267.7	300.0	334.6	367.0	433.9	503.1	570.1	637.0
42.5°	207.7	216.9	223.9	253.9	286.2	316.2	346.2	410.8	475.4	537.7	602.4
45°	205.4	214.6	223.9	249.3	274.6	297.7	323.1	385.4	447.7	510.0	572.4
47.5°	200.8	207.7	216.9	237.7	256.2	276.9	295.4	357.7	420.0	480.0	542.4
50°	198.5	200.8	205.4	223.9	242.3	260.8	279.3	341.6	403.9	466.2	528.5
52.5°	196.2	196.2	196.2	212.3	228.5	242.3	258.5	320.8	385.4	447.7	510.0
55°	182.3	180.0	180.0	196.2	210.0	226.2	240.0	302.3	364.6	424.7	487.0
57.5°	168.5	166.2	163.9	177.7	191.6	205.4	219.3	281.6	346.2	408.5	470.8
60°	154.6	152.3	152.3	166.2	177.7	191.6	203.1	267.7	330.0	394.7	457.0
62.5°	138.5	140.8	140.8	152.3	166.2	177.7	189.2	253.9	320.8	385.4	450.0
65°	126.9	129.2	129.2	143.1	156.9	170.8	184.6	246.9	311.6	373.9	436.2
67.5°	117.7	120.0	120.0	136.2	150.0	166.2	180.0	235.4	293.1	348.5	403.9
70°	108.5	108.5	110.8	126.9	143.1	159.2	175.4	223.9	272.3	318.5	367.0
72.5°	96.9	99.2	101.5	117.7	131.6	147.7	161.6	205.4	249.3	293.1	337.0
75°	85.4	87.7	90.0	103.9	117.7	131.6	145.4	186.9	226.2	267.7	307.0
77.5°	76.2	78.5	80.8	92.3	103.9	115.4	126.9	156.9	189.2	219.3	249.3
80°	62.3	62.3	64.6	73.9	83.1	90.0	99.2	120.0	140.8	159.2	180.0
82.5°	46.2	48.5	48.5	55.4	60.0	66.9	71.5	83.1	92.3	103.9	113.1
85°	39.2	36.9	36.9	41.5	43.9	48.5	50.8	57.7	62.3	69.2	73.9
87.5°	16.2	13.8	13.8	16.2	20.8	23.1	25.4	25.4	27.7	27.7	27.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7
2.5°	1703.2	1707.9	1714.8	1719.4	1730.9	1740.2	1751.7	1760.9	1767.9	1779.4	1774.8
5°	1640.9	1661.7	1682.5	1703.2	1719.4	1735.5	1749.4	1765.5	1784.0	1818.6	1827.9
7.5°	1456.3	1484.0	1509.4	1537.1	1569.4	1601.7	1634.0	1666.3	1696.3	1740.2	1767.9
10°	1274.0	1313.2	1350.1	1389.4	1419.4	1449.4	1477.1	1507.1	1548.6	1592.5	1643.2
12.5°	1158.6	1197.8	1237.0	1276.3	1320.1	1361.7	1405.5	1447.1	1486.3	1520.9	1578.6
15°	1082.4	1126.3	1167.8	1209.3	1262.4	1313.2	1366.3	1417.1	1474.8	1520.9	1560.1
17.5°	1063.9	1117.0	1167.8	1220.9	1276.3	1331.7	1387.1	1442.4	1500.1	1569.4	1620.2
20°	1031.6	1103.2	1174.7	1246.3	1317.8	1387.1	1458.6	1527.8	1604.0	1687.1	1710.2
22.5°	1013.2	1098.6	1186.3	1271.7	1368.6	1467.8	1564.8	1661.7	1742.5	1804.8	1874.0
25°	1010.9	1117.0	1225.5	1331.7	1454.0	1574.0	1696.3	1816.3	1920.2	1982.5	2037.9
27.5°	1008.6	1137.8	1264.7	1391.7	1541.7	1689.4	1839.4	1987.1	2084.0	2174.0	2220.2
30°	980.9	1135.5	1292.4	1447.1	1615.5	1784.0	1952.5	2121.0	2220.2	2282.5	2305.6
32.5°	946.2	1128.6	1310.9	1493.2	1684.8	1876.3	2065.6	2257.1	2335.6	2388.7	2370.2
35°	918.5	1119.3	1317.8	1516.3	1719.4	1924.8	2127.9	2331.0	2444.1	2517.9	2487.9
37.5°	893.2	1103.2	1313.2	1523.2	1760.9	1998.6	2236.4	2474.1	2582.5	2661.0	2626.4
40°	863.2	1087.0	1313.2	1537.1	1809.4	2079.4	2351.8	2621.8	2762.6	2829.5	2776.4
42.5°	837.8	1070.9	1306.3	1539.4	1830.2	2121.0	2411.8	2702.6	2859.5	2954.1	2887.2
45°	805.5	1038.6	1269.3	1502.4	1823.2	2144.0	2462.5	2783.3	2965.7	3039.5	2947.2
47.5°	770.8	1001.6	1230.1	1458.6	1800.2	2141.7	2483.3	2824.9	2993.4	3081.1	2995.7
50°	759.3	990.1	1218.6	1449.4	1818.6	2190.2	2559.5	2928.7	3051.1	3122.6	3009.5
52.5°	757.0	1001.6	1248.6	1493.2	1864.8	2234.1	2605.6	2974.9	3074.1	3150.3	3048.7
55°	750.1	1015.5	1278.6	1541.7	1929.4	2319.4	2707.2	3094.9	3194.1	3249.5	3173.4
57.5°	757.0	1043.2	1327.0	1613.2	2012.5	2411.8	2811.0	3210.3	3330.3	3369.5	3353.4
60°	761.6	1066.3	1368.6	1673.2	2063.3	2453.3	2843.3	3233.4	3358.0	3454.9	3473.4
62.5°	750.1	1050.1	1347.8	1647.8	2001.0	2354.1	2707.2	3060.3	3265.7	3408.8	3491.9
65°	715.5	992.4	1271.7	1548.6	1874.0	2201.7	2527.2	2852.6	3069.5	3281.8	3348.8
67.5°	639.3	874.7	1110.1	1345.5	1629.4	1913.3	2194.8	2478.7	2751.0	2956.4	3048.7
70°	553.9	738.5	925.5	1110.1	1368.6	1627.1	1885.6	2144.0	2384.1	2610.2	2697.9
72.5°	482.4	625.4	770.8	913.9	1098.6	1280.9	1465.5	1647.8	1931.7	2157.9	2243.3
75°	410.8	514.7	616.2	720.1	847.0	973.9	1098.6	1225.5	1426.3	1629.4	1714.8
77.5°	316.2	385.4	452.3	519.3	607.0	692.4	780.1	865.5	1006.2	1158.6	1202.4
80°	219.3	258.5	295.4	334.6	403.9	473.1	542.4	611.6	703.9	789.3	856.2
82.5°	136.2	161.6	184.6	207.7	263.1	318.5	371.6	427.0	463.9	468.5	535.4
85°	87.7	103.9	117.7	131.6	163.9	198.5	230.8	263.1	235.4	219.3	260.8
87.5°	34.6	43.9	50.8	57.7	55.4	53.1	50.8	48.5	41.5	36.9	46.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7
2.5°	1779.4	1786.3	1793.2	1797.9	1804.8	1807.1	1809.4	1809.4	1811.7	1814.0	1818.6
5°	1864.8	1878.6	1892.5	1904.0	1917.9	1929.4	1938.6	1950.2	1959.4	1959.4	1957.1
7.5°	1793.2	1827.9	1862.5	1897.1	1931.7	1957.1	1980.2	2005.6	2028.7	2033.3	2037.9
10°	1698.6	1735.5	1770.2	1807.1	1841.7	1880.9	1917.9	1954.8	1994.0	2001.0	2010.2
12.5°	1610.9	1654.8	1698.6	1740.2	1784.0	1811.7	1839.4	1864.8	1892.5	1910.9	1929.4
15°	1608.6	1645.5	1682.5	1717.1	1754.0	1770.2	1786.3	1800.2	1816.3	1816.3	1818.6
17.5°	1661.7	1684.8	1707.9	1728.6	1751.7	1754.0	1758.6	1760.9	1763.2	1756.3	1749.4
20°	1765.5	1774.8	1784.0	1793.2	1802.5	1786.3	1772.5	1756.3	1740.2	1721.7	1705.5
22.5°	1917.9	1897.1	1876.3	1855.6	1834.8	1807.1	1777.1	1749.4	1719.4	1696.3	1673.2
25°	2061.0	2035.6	2010.2	1984.8	1959.4	1899.4	1839.4	1777.1	1717.1	1691.7	1666.3
27.5°	2252.5	2213.3	2174.0	2134.8	2095.6	2014.8	1934.0	1853.2	1772.5	1728.6	1687.1
30°	2298.7	2254.8	2211.0	2164.8	2121.0	2042.5	1966.3	1887.9	1809.4	1758.6	1710.2
32.5°	2365.6	2314.8	2264.1	2213.3	2162.5	2086.3	2010.2	1931.7	1855.6	1809.4	1760.9
35°	2476.4	2418.7	2361.0	2301.0	2243.3	2164.8	2088.7	2010.2	1931.7	1878.6	1827.9
37.5°	2571.0	2504.1	2437.2	2370.2	2303.3	2234.1	2162.5	2093.3	2021.7	1968.6	1917.9
40°	2677.2	2603.3	2529.5	2457.9	2384.1	2319.4	2254.8	2187.9	2123.3	2081.7	2040.2
42.5°	2769.5	2679.5	2591.8	2504.1	2414.1	2370.2	2328.7	2284.8	2241.0	2220.2	2197.1
45°	2834.1	2751.0	2665.6	2582.5	2499.5	2467.2	2434.8	2402.5	2370.2	2391.0	2411.8
47.5°	2861.8	2794.9	2730.3	2665.6	2598.7	2610.2	2621.8	2631.0	2642.6	2670.2	2700.3
50°	2887.2	2850.3	2811.0	2774.1	2734.9	2778.7	2820.3	2864.1	2908.0	2965.7	3023.4
52.5°	2938.0	2917.2	2898.7	2878.0	2857.2	2933.4	3009.5	3085.7	3161.8	3226.5	3291.1
55°	3090.3	3074.1	3058.0	3039.5	3023.4	3131.8	3238.0	3346.5	3454.9	3521.9	3588.8
57.5°	3300.3	3291.1	3279.5	3270.3	3258.8	3364.9	3468.8	3572.6	3678.8	3743.4	3810.4
60°	3459.6	3461.9	3461.9	3464.2	3464.2	3544.9	3625.7	3708.8	3789.6	3845.0	3902.7
62.5°	3544.9	3540.3	3535.7	3531.1	3526.5	3593.4	3660.3	3727.3	3794.2	3835.7	3877.3
65°	3452.6	3478.0	3503.4	3528.8	3554.2	3563.4	3570.3	3579.6	3586.5	3611.9	3637.3
67.5°	3143.4	3194.1	3242.6	3293.4	3341.9	3307.2	3274.9	3240.3	3205.7	3212.6	3217.2
70°	2799.5	2857.2	2917.2	2974.9	3032.6	2951.8	2871.0	2788.0	2707.2	2679.5	2651.8
72.5°	2361.0	2411.8	2464.8	2515.6	2566.4	2467.2	2370.2	2271.0	2171.7	2123.3	2074.8
75°	1804.8	1864.8	1927.1	1987.1	2047.1	1936.3	1823.2	1712.5	1599.4	1567.1	1537.1
77.5°	1315.5	1387.1	1458.6	1530.1	1601.7	1502.4	1403.2	1301.7	1202.4	1184.0	1165.5
80°	957.8	1013.2	1066.3	1121.6	1174.7	1117.0	1059.3	1001.6	943.9	941.6	939.3
82.5°	646.2	694.7	740.8	789.3	835.5	812.4	791.6	768.5	745.5	768.5	793.9
85°	332.3	399.3	468.5	535.4	602.4	595.4	590.8	583.9	577.0	607.0	634.7
87.5°	66.9	124.6	182.3	237.7	295.4	281.6	267.7	251.6	237.7	246.9	253.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7
2.5°	1820.9	1823.2	1823.2	1823.2	1823.2	1823.2	1818.6	1816.3	1811.7	1807.1	1800.2
5°	1957.1	1954.8	1945.6	1936.3	1924.8	1915.6	1908.6	1899.4	1892.5	1883.3	1869.4
7.5°	2042.5	2047.1	2031.0	2017.1	2001.0	1984.8	1968.6	1952.5	1936.3	1920.2	1887.9
10°	2017.1	2024.0	2014.8	2005.6	1994.0	1984.8	1966.3	1945.6	1927.1	1906.3	1867.1
12.5°	1945.6	1964.0	1959.4	1954.8	1950.2	1945.6	1934.0	1920.2	1908.6	1894.8	1850.9
15°	1818.6	1818.6	1820.9	1823.2	1823.2	1825.6	1827.9	1830.2	1832.5	1834.8	1809.4
17.5°	1742.5	1735.5	1735.5	1735.5	1735.5	1735.5	1744.8	1756.3	1765.5	1774.8	1767.9
20°	1687.1	1670.9	1668.6	1668.6	1666.3	1664.0	1680.2	1698.6	1714.8	1730.9	1740.2
22.5°	1650.2	1627.1	1624.8	1622.5	1620.2	1617.8	1638.6	1659.4	1680.2	1700.9	1733.2
25°	1640.9	1615.5	1617.8	1620.2	1620.2	1622.5	1638.6	1654.8	1670.9	1687.1	1742.5
27.5°	1643.2	1601.7	1604.0	1606.3	1606.3	1608.6	1634.0	1657.1	1682.5	1705.5	1774.8
30°	1659.4	1610.9	1606.3	1601.7	1597.1	1592.5	1627.1	1661.7	1696.3	1730.9	1784.0
32.5°	1714.8	1668.6	1657.1	1645.5	1634.0	1622.5	1664.0	1703.2	1744.8	1784.0	1827.9
35°	1774.8	1724.0	1719.4	1714.8	1707.9	1703.2	1740.2	1779.4	1816.3	1853.2	1892.5
37.5°	1864.8	1814.0	1809.4	1802.5	1797.9	1790.9	1832.5	1871.7	1913.3	1952.5	1987.1
40°	1998.6	1957.1	1954.8	1954.8	1952.5	1950.2	1982.5	2017.1	2049.4	2081.7	2104.8
42.5°	2176.4	2155.6	2162.5	2171.7	2178.7	2185.6	2211.0	2238.7	2264.1	2289.4	2282.5
45°	2432.5	2453.3	2455.6	2457.9	2460.2	2462.5	2469.5	2478.7	2485.6	2492.5	2464.8
47.5°	2727.9	2755.6	2769.5	2783.3	2794.9	2808.7	2799.5	2788.0	2778.7	2767.2	2697.9
50°	3078.7	3136.4	3134.1	3131.8	3127.2	3124.9	3106.4	3088.0	3067.2	3048.7	2947.2
52.5°	3355.7	3420.3	3431.9	3443.4	3454.9	3466.5	3431.9	3397.2	3360.3	3325.7	3198.8
55°	3653.4	3720.3	3722.7	3725.0	3725.0	3727.3	3678.8	3630.3	3579.6	3531.1	3399.5
57.5°	3875.0	3939.6	3932.7	3928.1	3921.1	3914.2	3856.5	3798.8	3741.1	3683.4	3551.9
60°	3958.1	4013.5	3999.6	3985.8	3969.6	3955.8	3911.9	3868.1	3821.9	3778.0	3651.1
62.5°	3918.8	3960.4	3939.6	3921.1	3900.4	3879.6	3824.2	3766.5	3711.1	3653.4	3561.1
65°	3660.3	3685.7	3658.0	3632.6	3607.3	3579.6	3533.4	3487.2	3438.8	3392.6	3330.3
67.5°	3224.1	3228.8	3226.5	3224.1	3221.8	3219.5	3152.6	3085.7	3016.4	2949.5	2944.9
70°	2626.4	2598.7	2603.3	2610.2	2614.9	2619.5	2568.7	2520.2	2469.5	2418.7	2441.8
72.5°	2026.3	1977.9	1989.4	2003.3	2014.8	2026.3	1984.8	1945.6	1904.0	1862.5	1894.8
75°	1504.8	1474.8	1486.3	1500.1	1511.7	1523.2	1507.1	1490.9	1472.4	1456.3	1486.3
77.5°	1147.0	1128.6	1130.9	1130.9	1133.2	1133.2	1135.5	1140.1	1142.4	1144.7	1177.0
80°	934.7	932.4	930.1	927.8	923.2	920.9	943.9	967.0	990.1	1013.2	1029.3
82.5°	817.0	840.1	826.2	814.7	800.8	787.0	807.8	828.5	849.3	870.1	863.2
85°	664.7	692.4	667.0	641.6	613.9	588.5	607.0	623.1	641.6	657.8	648.5
87.5°	263.1	270.0	228.5	189.2	147.7	106.2	168.5	228.5	290.8	350.8	360.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7	1661.7
2.5°	1793.2	1784.0	1777.1	1774.8	1770.2	1767.9	1763.2	1758.6	1751.7	1747.1	1740.2
5°	1853.2	1839.4	1823.2	1800.2	1779.4	1756.3	1733.2	1712.5	1691.7	1668.6	1647.8
7.5°	1855.6	1823.2	1790.9	1760.9	1728.6	1698.6	1666.3	1638.6	1608.6	1578.6	1550.9
10°	1830.2	1790.9	1751.7	1712.5	1675.5	1636.3	1597.1	1564.8	1530.1	1495.5	1463.2
12.5°	1809.4	1765.5	1721.7	1675.5	1631.7	1585.5	1539.4	1507.1	1474.8	1442.4	1410.1
15°	1784.0	1756.3	1730.9	1689.4	1647.8	1606.3	1564.8	1520.9	1479.4	1435.5	1391.7
17.5°	1763.2	1756.3	1749.4	1721.7	1694.0	1664.0	1636.3	1592.5	1548.6	1502.4	1458.6
20°	1751.7	1760.9	1770.2	1756.3	1742.5	1726.3	1712.5	1680.2	1647.8	1613.2	1580.9
22.5°	1765.5	1800.2	1832.5	1834.8	1839.4	1841.7	1844.0	1814.0	1784.0	1751.7	1721.7
25°	1797.9	1853.2	1908.6	1938.6	1968.6	2001.0	2031.0	2012.5	1994.0	1975.6	1957.1
27.5°	1841.7	1910.9	1980.2	2024.0	2065.6	2109.4	2153.3	2151.0	2148.7	2144.0	2141.7
30°	1834.8	1887.9	1941.0	1994.0	2047.1	2100.2	2153.3	2181.0	2206.4	2234.1	2261.7
32.5°	1874.0	1917.9	1964.0	2019.4	2074.8	2132.5	2187.9	2245.6	2301.0	2358.7	2416.4
35°	1934.0	1973.3	2014.8	2074.8	2137.1	2197.1	2259.4	2328.7	2400.2	2471.8	2541.0
37.5°	2024.0	2058.7	2095.6	2146.4	2199.4	2250.2	2303.3	2404.8	2506.4	2610.2	2711.8
40°	2127.9	2151.0	2174.0	2222.5	2271.0	2319.4	2367.9	2494.8	2621.8	2748.7	2875.7
42.5°	2277.9	2271.0	2264.1	2303.3	2344.8	2384.1	2425.6	2541.0	2656.4	2771.8	2887.2
45°	2437.2	2409.5	2381.8	2400.2	2421.0	2439.5	2460.2	2577.9	2695.6	2815.6	2933.4
47.5°	2628.7	2559.5	2490.2	2474.1	2457.9	2439.5	2423.3	2550.2	2677.2	2806.4	2933.4
50°	2845.7	2741.8	2640.2	2598.7	2554.9	2513.3	2469.5	2573.3	2679.5	2785.6	2889.5
52.5°	3071.8	2942.6	2815.6	2751.0	2686.4	2619.5	2554.9	2642.6	2732.6	2822.6	2910.3
55°	3265.7	3134.1	3000.3	2924.1	2848.0	2771.8	2695.6	2783.3	2871.0	2958.7	3046.4
57.5°	3420.3	3288.8	3157.2	3085.7	3011.8	2940.3	2866.4	2949.5	3034.9	3120.3	3203.4
60°	3526.5	3399.5	3272.6	3203.4	3134.1	3064.9	2995.7	3094.9	3194.1	3295.7	3394.9
62.5°	3471.1	3378.8	3286.5	3256.5	3226.5	3194.1	3164.1	3258.8	3351.1	3445.7	3540.3
65°	3268.0	3205.7	3143.4	3173.4	3205.7	3235.7	3268.0	3330.3	3392.6	3457.2	3519.6
67.5°	2938.0	2933.4	2926.4	2993.4	3060.3	3129.5	3196.5	3238.0	3277.2	3318.8	3360.3
70°	2464.8	2490.2	2513.3	2628.7	2744.1	2859.5	2974.9	2991.0	3007.2	3023.4	3039.5
72.5°	1929.4	1961.7	1996.3	2148.7	2298.7	2451.0	2603.3	2594.1	2584.9	2573.3	2564.1
75°	1518.6	1548.6	1580.9	1721.7	1862.5	2003.3	2144.0	2104.8	2067.9	2028.7	1989.4
77.5°	1211.7	1244.0	1278.6	1410.1	1541.7	1675.5	1807.1	1712.5	1617.8	1523.2	1428.6
80°	1043.2	1059.3	1073.2	1163.2	1250.9	1340.9	1430.9	1334.0	1234.7	1135.5	1038.6
82.5°	856.2	847.0	840.1	893.2	946.2	999.3	1052.4	960.1	867.8	773.1	680.8
85°	639.3	630.1	620.8	648.5	676.2	706.2	733.9	627.8	521.6	413.1	307.0
87.5°	371.6	380.8	390.0	420.0	450.0	482.4	512.4	403.9	295.4	184.6	76.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671794
 CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1661.7	1661.7
2.5°	1726.3	1714.8
5°	1631.7	1615.5
7.5°	1527.8	1507.1
10°	1433.2	1405.5
12.5°	1373.2	1338.6
15°	1350.1	1308.6
17.5°	1419.4	1380.1
20°	1525.5	1472.4
22.5°	1654.8	1590.1
25°	1878.6	1800.2
27.5°	2061.0	1980.2
30°	2174.0	2086.3
32.5°	2298.7	2183.3
35°	2427.9	2317.1
37.5°	2584.9	2460.2
40°	2746.4	2617.2
42.5°	2801.8	2718.7
45°	2854.9	2776.4
47.5°	2866.4	2801.8
50°	2878.0	2868.7
52.5°	2910.3	2908.0
55°	3048.7	3051.1
57.5°	3219.5	3233.4
60°	3376.5	3360.3
62.5°	3457.2	3374.2
65°	3401.9	3286.5
67.5°	3235.7	3111.1
70°	2871.0	2702.6
72.5°	2416.4	2268.7
75°	1862.5	1737.9
77.5°	1324.7	1220.9
80°	932.4	828.5
82.5°	597.7	514.7
85°	270.0	235.4
87.5°	76.2	73.9
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P671794

CATALOG NUMBER: CCP-SA-1F-727-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)