

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671801

Luminaire Tested: **CCP-SA-1B-730-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671801
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1B-730-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @450mA w/ SLR
distribution lens
Light Source: (16) 3000K CCT, 70 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2609.8 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1

Input Watts (W): 24
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 3.7 fc

Type IV - Short - N/A

REPORT NUMBER: P671801
CATALOG NUMBER: CCP-SA-1B-730-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	537.0	0.0	537.0
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	2072.8	0.0	2072.8
	% Fixture	79.4	0.0	79.4
Total	Lumens	2609.8	0.0	2609.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.8	2.5
10°-20°	136.7	5.2
20°-30°	200.0	7.7
30°-40°	281.8	10.8
40°-50°	387.3	14.8
50°-60°	527.8	20.2
60°-70°	577.7	22.1
70°-80°	333.6	12.8
80°-90°	100.0	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2609.8	100.0
0°-180°	2609.8	100.0

Coefficient of Utilization



REPORT NUMBER: P671801


CATALOG NUMBER: CCP-SA-1B-730-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	268.0	10.3			
FM	(30°-60°)	952.4	36.5			
FH	(60°-80°)	767.4	29.4			G1/1800
FVH	(80°-90°)	84.9	3.3			G1/100
BL	(0°-30°)	133.5	5.1	B1/500		
BM	(30°-60°)	244.5	9.4	B1/1000		
BH	(60°-80°)	143.9	5.5	B1/500		G1/500
BVH	(80°-90°)	15.1	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4
2.5°	860.0	855.4	851.9	848.5	843.8	840.4	835.7	831.1	825.3	820.7	814.9
5°	810.3	796.4	782.5	774.4	765.1	757.0	747.8	737.3	726.9	715.3	704.9
7.5°	755.9	738.5	721.1	707.2	692.2	678.3	663.3	650.5	637.8	625.1	612.3
10°	704.9	688.7	672.5	655.2	636.6	619.3	600.8	583.4	566.0	548.7	531.3
12.5°	671.4	651.7	633.2	613.5	595.0	575.3	555.6	539.4	523.2	505.8	489.6
15°	656.3	637.8	620.4	600.8	581.1	561.4	541.7	523.2	505.8	487.3	468.8
17.5°	692.2	665.6	639.0	613.5	588.0	562.6	537.1	513.9	490.8	467.6	444.5
20°	738.5	704.9	672.5	641.3	608.9	577.6	545.2	512.8	480.4	448.0	415.6
22.5°	797.5	759.3	722.3	681.8	640.1	599.6	557.9	517.4	476.9	435.2	394.7
25°	902.9	857.7	812.6	754.7	695.7	637.8	578.8	525.5	473.4	420.2	366.9
27.5°	993.2	931.8	871.6	802.2	732.7	663.3	593.8	532.5	472.3	410.9	349.6
30°	1046.4	986.2	926.0	841.5	758.2	673.7	589.2	520.9	453.7	385.5	317.2
32.5°	1095.0	1027.9	960.7	868.1	774.4	681.8	588.0	512.8	438.7	363.5	288.2
35°	1162.2	1088.1	1015.1	907.5	799.8	692.2	584.5	507.0	428.3	350.7	272.0
37.5°	1233.9	1142.5	1052.2	933.0	813.7	694.5	575.3	498.9	422.5	346.1	269.7
40°	1312.6	1201.5	1091.5	959.6	828.8	696.8	564.9	488.5	412.1	334.5	258.1
42.5°	1363.6	1243.2	1122.8	980.4	839.2	696.8	554.5	479.2	404.0	327.6	252.3
45°	1392.5	1275.6	1159.8	1005.9	851.9	698.0	544.0	470.0	395.9	320.6	246.6
47.5°	1405.2	1296.4	1187.6	1025.6	864.7	702.6	540.6	465.3	388.9	313.7	237.3
50°	1438.8	1342.7	1246.7	1073.0	900.6	726.9	553.3	472.3	392.4	311.4	230.3
52.5°	1458.5	1376.3	1294.1	1115.9	937.6	759.3	581.1	490.8	400.5	310.2	219.9
55°	1530.2	1451.5	1372.8	1183.0	992.0	802.2	611.2	511.6	412.1	311.4	211.8
57.5°	1621.7	1538.3	1456.2	1251.3	1046.4	841.5	636.6	530.1	422.5	316.0	208.4
60°	1685.4	1604.3	1524.5	1306.8	1088.1	870.5	651.7	540.6	429.4	317.2	206.0
62.5°	1692.3	1588.1	1485.1	1273.3	1061.4	848.5	636.6	529.0	421.3	312.5	204.9
65°	1648.3	1526.8	1405.2	1202.7	1000.1	797.5	595.0	496.6	398.2	298.6	200.3
67.5°	1560.3	1418.0	1275.6	1090.4	905.2	720.0	534.8	450.3	366.9	282.4	197.9
70°	1355.5	1230.4	1106.6	945.7	786.0	625.1	464.2	394.7	326.4	257.0	187.5
72.5°	1137.8	1020.9	905.2	774.4	644.7	513.9	383.1	331.1	279.0	225.7	173.6
75°	871.6	783.6	696.8	599.6	502.4	404.0	306.7	268.5	230.3	192.1	154.0
77.5°	612.3	564.9	518.6	445.6	372.7	299.8	226.9	201.4	175.9	150.5	125.0
80°	415.6	388.9	363.5	311.4	259.3	206.0	154.0	137.7	120.4	104.2	86.8
82.5°	258.1	257.0	254.7	218.8	182.9	147.0	111.1	97.2	84.5	70.6	56.7
85°	118.1	137.7	156.3	136.6	116.9	97.2	77.6	68.3	59.0	48.6	39.4
87.5°	37.0	45.1	52.1	49.8	46.3	44.0	40.5	34.7	28.9	23.2	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4
2.5°	810.3	806.8	802.2	797.5	791.7	787.1	781.3	775.5	774.4	772.1	770.9
5°	698.0	691.0	682.9	676.0	669.0	660.9	654.0	645.9	640.1	633.2	627.4
7.5°	599.6	588.0	575.3	562.6	551.0	539.4	526.7	515.1	509.3	503.5	497.7
10°	520.9	509.3	498.9	487.3	479.2	472.3	464.2	456.1	449.1	442.2	435.2
12.5°	481.5	473.4	465.3	457.2	448.0	439.9	430.6	421.3	413.2	406.3	398.2
15°	457.2	445.6	432.9	421.3	408.6	397.0	384.3	371.6	362.3	354.2	344.9
17.5°	428.3	410.9	394.7	377.4	363.5	349.6	334.5	320.6	310.2	298.6	288.2
20°	395.9	376.2	355.4	335.7	319.5	304.4	288.2	272.0	260.4	247.7	236.1
22.5°	368.1	342.6	316.0	289.4	272.0	254.7	236.1	218.8	208.4	196.8	186.4
25°	338.0	310.2	281.3	252.3	235.0	216.5	199.1	180.6	172.5	165.5	157.4
27.5°	321.8	294.0	265.1	237.3	221.1	203.7	187.5	170.2	164.4	157.4	151.6
30°	289.4	262.8	235.0	207.2	195.6	185.2	173.6	162.1	159.7	158.6	156.3
32.5°	260.4	232.7	204.9	177.1	166.7	156.3	145.8	135.4	134.3	132.0	130.8
35°	245.4	218.8	191.0	164.4	155.1	144.7	135.4	125.0	122.7	119.2	116.9
37.5°	241.9	214.1	185.2	157.4	148.2	138.9	128.5	119.2	116.9	114.6	112.3
40°	232.7	206.0	180.6	154.0	144.7	135.4	125.0	115.8	113.4	111.1	108.8
42.5°	225.7	200.3	173.6	147.0	138.9	130.8	121.5	113.4	111.1	108.8	105.3
45°	219.9	193.3	165.5	138.9	133.1	127.3	120.4	114.6	112.3	108.8	106.5
47.5°	210.7	185.2	158.6	132.0	126.2	121.5	115.8	110.0	107.6	105.3	103.0
50°	203.7	177.1	150.5	123.9	119.2	114.6	110.0	105.3	105.3	106.5	106.5
52.5°	194.5	169.0	143.5	118.1	113.4	108.8	104.2	99.5	100.7	101.9	103.0
55°	186.4	162.1	136.6	111.1	106.5	101.9	96.1	91.4	92.6	93.8	94.9
57.5°	182.9	157.4	132.0	106.5	101.9	96.1	91.4	85.7	85.7	85.7	85.7
60°	180.6	154.0	128.5	101.9	96.1	91.4	85.7	79.9	78.7	78.7	77.6
62.5°	179.4	152.8	127.3	100.7	93.8	88.0	81.0	74.1	72.9	71.8	70.6
65°	174.8	150.5	125.0	99.5	91.4	84.5	76.4	68.3	67.1	67.1	66.0
67.5°	173.6	148.2	123.9	98.4	90.3	81.0	72.9	63.7	62.5	61.3	60.2
70°	164.4	142.4	119.2	96.1	86.8	78.7	69.5	60.2	59.0	56.7	55.6
72.5°	152.8	133.1	112.3	91.4	82.2	72.9	63.7	54.4	53.2	52.1	49.8
75°	135.4	116.9	98.4	79.9	71.8	64.8	56.7	48.6	47.5	46.3	44.0
77.5°	111.1	96.1	82.2	67.1	61.3	55.6	49.8	44.0	42.8	41.7	39.4
80°	78.7	69.5	61.3	52.1	48.6	44.0	40.5	35.9	35.9	34.7	34.7
82.5°	52.1	47.5	42.8	38.2	35.9	33.6	31.3	28.9	28.9	27.8	27.8
85°	37.0	34.7	31.3	28.9	27.8	25.5	24.3	22.0	22.0	22.0	22.0
87.5°	17.4	17.4	16.2	16.2	15.0	15.0	13.9	12.7	12.7	12.7	12.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4
2.5°	768.6	765.1	761.7	757.0	753.5	748.9	743.1	738.5	732.7	732.7	731.6
5°	620.4	617.0	613.5	608.9	605.4	600.8	597.3	592.7	588.0	588.0	586.9
7.5°	491.9	485.0	478.1	470.0	463.0	458.4	453.7	448.0	443.3	439.9	436.4
10°	428.3	421.3	413.2	406.3	398.2	392.4	386.6	379.7	373.9	369.2	364.6
12.5°	390.1	382.0	373.9	365.8	357.7	349.6	342.6	334.5	326.4	320.6	314.8
15°	335.7	327.6	319.5	311.4	303.3	294.0	284.8	274.3	265.1	260.4	257.0
17.5°	276.6	268.5	259.3	251.2	241.9	235.0	228.0	221.1	214.1	209.5	206.0
20°	223.4	214.1	204.9	195.6	186.4	181.7	177.1	172.5	167.8	164.4	162.1
22.5°	174.8	169.0	164.4	158.6	152.8	149.3	147.0	143.5	140.1	140.1	140.1
25°	149.3	145.8	143.5	140.1	136.6	135.4	134.3	132.0	130.8	129.6	129.6
27.5°	144.7	141.2	137.7	134.3	130.8	129.6	128.5	126.2	125.0	125.0	125.0
30°	154.0	152.8	151.6	150.5	149.3	147.0	143.5	141.2	137.7	135.4	133.1
32.5°	128.5	127.3	127.3	126.2	125.0	127.3	128.5	130.8	132.0	133.1	134.3
35°	113.4	111.1	108.8	106.5	104.2	103.0	101.9	100.7	99.5	99.5	98.4
37.5°	110.0	107.6	105.3	103.0	100.7	99.5	98.4	97.2	96.1	96.1	94.9
40°	106.5	104.2	103.0	100.7	98.4	97.2	96.1	93.8	92.6	91.4	91.4
42.5°	103.0	101.9	99.5	98.4	96.1	94.9	93.8	91.4	90.3	89.1	88.0
45°	103.0	100.7	98.4	96.1	93.8	92.6	90.3	89.1	86.8	86.8	85.7
47.5°	100.7	98.4	96.1	93.8	91.4	90.3	88.0	86.8	84.5	83.3	82.2
50°	106.5	103.0	98.4	94.9	90.3	89.1	86.8	85.7	83.3	82.2	81.0
52.5°	104.2	100.7	96.1	92.6	88.0	85.7	84.5	82.2	79.9	78.7	77.6
55°	96.1	92.6	90.3	86.8	83.3	81.0	78.7	76.4	74.1	72.9	72.9
57.5°	85.7	84.5	83.3	82.2	81.0	78.7	76.4	72.9	70.6	69.5	68.3
60°	76.4	77.6	78.7	79.9	81.0	77.6	74.1	70.6	67.1	66.0	64.8
62.5°	69.5	71.8	74.1	75.2	77.6	74.1	70.6	67.1	63.7	62.5	61.3
65°	64.8	66.0	66.0	67.1	67.1	64.8	63.7	61.3	59.0	57.9	57.9
67.5°	59.0	59.0	59.0	57.9	57.9	56.7	56.7	55.6	54.4	53.2	53.2
70°	53.2	53.2	53.2	52.1	52.1	50.9	50.9	49.8	48.6	48.6	47.5
72.5°	48.6	48.6	47.5	47.5	46.3	46.3	46.3	45.1	45.1	44.0	44.0
75°	42.8	42.8	41.7	41.7	40.5	40.5	40.5	39.4	39.4	39.4	38.2
77.5°	38.2	38.2	37.0	37.0	35.9	35.9	35.9	34.7	34.7	33.6	33.6
80°	33.6	33.6	32.4	32.4	31.3	31.3	30.1	30.1	28.9	28.9	27.8
82.5°	26.6	26.6	26.6	26.6	26.6	25.5	25.5	24.3	23.2	23.2	22.0
85°	22.0	22.0	22.0	20.8	20.8	20.8	19.7	19.7	18.5	17.4	17.4
87.5°	12.7	12.7	12.7	11.6	11.6	11.6	11.6	11.6	11.6	11.6	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4
2.5°	731.6	730.4	725.8	721.1	725.8	730.4	730.4	730.4	729.2	729.2	729.2
5°	586.9	585.7	583.4	581.1	581.1	579.9	582.2	584.5	586.9	589.2	591.5
7.5°	431.8	428.3	424.8	421.3	423.7	424.8	428.3	430.6	434.1	436.4	442.2
10°	360.0	355.4	351.9	348.4	346.1	343.8	341.5	340.3	338.0	335.7	338.0
12.5°	307.9	302.1	296.3	289.4	288.2	287.1	284.8	282.4	280.1	277.8	276.6
15°	252.3	247.7	245.4	241.9	237.3	232.7	230.3	229.2	226.9	224.6	223.4
17.5°	201.4	196.8	193.3	189.8	188.7	186.4	186.4	186.4	186.4	186.4	186.4
20°	158.6	155.1	155.1	154.0	154.0	152.8	154.0	155.1	155.1	156.3	157.4
22.5°	138.9	138.9	137.7	136.6	137.7	137.7	138.9	140.1	141.2	142.4	143.5
25°	128.5	127.3	128.5	129.6	129.6	129.6	130.8	130.8	132.0	132.0	132.0
27.5°	123.9	123.9	125.0	125.0	126.2	126.2	126.2	125.0	125.0	123.9	123.9
30°	130.8	128.5	128.5	128.5	127.3	126.2	125.0	125.0	123.9	122.7	121.5
32.5°	135.4	136.6	135.4	133.1	132.0	129.6	128.5	126.2	125.0	122.7	120.4
35°	98.4	97.2	99.5	100.7	101.9	103.0	104.2	105.3	105.3	106.5	106.5
37.5°	94.9	93.8	93.8	92.6	92.6	92.6	92.6	92.6	91.4	91.4	92.6
40°	90.3	89.1	89.1	88.0	88.0	86.8	86.8	86.8	86.8	86.8	86.8
42.5°	86.8	85.7	85.7	85.7	85.7	84.5	84.5	83.3	83.3	82.2	82.2
45°	85.7	84.5	83.3	82.2	82.2	81.0	81.0	81.0	79.9	79.9	79.9
47.5°	81.0	79.9	79.9	78.7	78.7	77.6	77.6	77.6	76.4	76.4	76.4
50°	78.7	77.6	77.6	76.4	76.4	75.2	75.2	75.2	74.1	74.1	74.1
52.5°	75.2	74.1	74.1	74.1	72.9	71.8	71.8	71.8	70.6	70.6	70.6
55°	71.8	70.6	70.6	70.6	69.5	68.3	68.3	68.3	67.1	67.1	67.1
57.5°	67.1	66.0	66.0	64.8	64.8	64.8	64.8	64.8	63.7	63.7	63.7
60°	63.7	62.5	62.5	61.3	61.3	60.2	60.2	60.2	60.2	60.2	60.2
62.5°	60.2	59.0	57.9	56.7	57.9	57.9	57.9	57.9	56.7	56.7	56.7
65°	56.7	55.6	54.4	53.2	53.2	53.2	53.2	53.2	53.2	53.2	53.2
67.5°	52.1	50.9	49.8	48.6	49.8	49.8	49.8	49.8	49.8	49.8	49.8
70°	47.5	46.3	46.3	45.1	45.1	44.0	44.0	45.1	45.1	45.1	45.1
72.5°	42.8	41.7	41.7	40.5	40.5	40.5	40.5	40.5	40.5	40.5	40.5
75°	38.2	37.0	37.0	35.9	35.9	35.9	35.9	35.9	35.9	35.9	35.9
77.5°	32.4	31.3	31.3	31.3	31.3	31.3	31.3	32.4	32.4	32.4	32.4
80°	27.8	26.6	26.6	26.6	26.6	26.6	26.6	26.6	26.6	26.6	26.6
82.5°	22.0	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8
85°	16.2	15.0	15.0	15.0	16.2	16.2	16.2	16.2	16.2	16.2	16.2
87.5°	10.4	9.3	9.3	9.3	10.4	10.4	10.4	10.4	9.3	9.3	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4
2.5°	729.2	729.2	729.2	728.1	726.9	725.8	724.6	728.1	730.4	733.9	736.2
5°	592.7	595.0	596.1	599.6	603.1	606.5	610.0	612.3	614.6	615.8	618.1
7.5°	446.8	452.6	457.2	461.9	466.5	470.0	474.6	478.1	481.5	485.0	488.5
10°	339.2	341.5	342.6	347.3	350.7	355.4	358.8	362.3	365.8	368.1	371.6
12.5°	275.5	273.2	272.0	272.0	272.0	272.0	272.0	274.3	276.6	279.0	281.3
15°	222.2	221.1	219.9	218.8	217.6	215.3	214.1	216.5	218.8	221.1	223.4
17.5°	186.4	186.4	186.4	185.2	184.0	182.9	181.7	182.9	184.0	184.0	185.2
20°	159.7	160.9	162.1	163.2	163.2	164.4	164.4	165.5	166.7	166.7	167.8
22.5°	143.5	144.7	144.7	144.7	145.8	145.8	145.8	147.0	148.2	149.3	150.5
25°	130.8	130.8	129.6	129.6	130.8	130.8	130.8	130.8	132.0	132.0	132.0
27.5°	123.9	122.7	122.7	122.7	122.7	121.5	121.5	121.5	121.5	121.5	121.5
30°	120.4	119.2	118.1	116.9	116.9	115.8	114.6	114.6	114.6	114.6	114.6
32.5°	119.2	116.9	114.6	113.4	113.4	112.3	111.1	110.0	110.0	108.8	107.6
35°	106.5	105.3	105.3	104.2	103.0	101.9	100.7	100.7	100.7	99.5	99.5
37.5°	92.6	93.8	93.8	93.8	94.9	94.9	94.9	94.9	96.1	96.1	96.1
40°	86.8	86.8	86.8	88.0	89.1	89.1	90.3	90.3	91.4	91.4	91.4
42.5°	82.2	81.0	81.0	82.2	82.2	83.3	83.3	84.5	85.7	85.7	86.8
45°	79.9	78.7	78.7	78.7	78.7	77.6	77.6	78.7	79.9	81.0	82.2
47.5°	75.2	75.2	74.1	74.1	74.1	74.1	74.1	74.1	75.2	75.2	75.2
50°	72.9	72.9	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.8
52.5°	70.6	69.5	69.5	69.5	69.5	68.3	68.3	68.3	68.3	68.3	68.3
55°	67.1	66.0	66.0	66.0	66.0	66.0	66.0	66.0	67.1	67.1	67.1
57.5°	63.7	62.5	62.5	62.5	63.7	63.7	63.7	63.7	64.8	64.8	64.8
60°	60.2	60.2	60.2	60.2	60.2	60.2	60.2	61.3	61.3	62.5	62.5
62.5°	56.7	56.7	56.7	56.7	57.9	57.9	57.9	57.9	59.0	59.0	59.0
65°	53.2	53.2	53.2	53.2	54.4	54.4	54.4	54.4	54.4	54.4	54.4
67.5°	49.8	49.8	49.8	49.8	49.8	49.8	49.8	50.9	50.9	52.1	52.1
70°	45.1	44.0	44.0	45.1	45.1	46.3	46.3	47.5	47.5	48.6	48.6
72.5°	40.5	40.5	40.5	40.5	40.5	40.5	40.5	41.7	42.8	42.8	44.0
75°	35.9	35.9	35.9	35.9	37.0	37.0	37.0	38.2	38.2	39.4	39.4
77.5°	32.4	31.3	31.3	31.3	32.4	32.4	32.4	33.6	33.6	34.7	34.7
80°	26.6	26.6	26.6	26.6	27.8	27.8	27.8	27.8	28.9	28.9	28.9
82.5°	22.0	22.0	22.0	22.0	22.0	22.0	22.0	22.0	23.2	23.2	23.2
85°	16.2	16.2	16.2	16.2	17.4	17.4	17.4	17.4	17.4	17.4	17.4
87.5°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	11.6	11.6	11.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4
2.5°	736.2	736.2	736.2	736.2	738.5	739.7	742.0	743.1	742.0	740.8	738.5
5°	619.3	620.4	620.4	621.6	621.6	621.6	621.6	621.6	623.9	626.2	628.5
7.5°	489.6	490.8	491.9	493.1	493.1	493.1	491.9	491.9	493.1	493.1	494.3
10°	375.0	379.7	383.1	386.6	384.3	380.8	378.5	375.0	375.0	375.0	373.9
12.5°	283.6	284.8	287.1	288.2	287.1	287.1	285.9	284.8	285.9	288.2	289.4
15°	224.6	224.6	225.7	225.7	226.9	228.0	228.0	229.2	231.5	232.7	235.0
17.5°	186.4	187.5	187.5	188.7	188.7	189.8	189.8	189.8	192.1	194.5	197.9
20°	167.8	167.8	167.8	167.8	167.8	166.7	166.7	165.5	166.7	169.0	170.2
22.5°	150.5	151.6	151.6	151.6	150.5	149.3	147.0	145.8	145.8	147.0	147.0
25°	132.0	130.8	130.8	129.6	129.6	130.8	130.8	130.8	132.0	132.0	133.1
27.5°	121.5	120.4	120.4	119.2	119.2	120.4	120.4	120.4	120.4	120.4	120.4
30°	113.4	113.4	112.3	111.1	112.3	112.3	113.4	113.4	114.6	114.6	115.8
32.5°	107.6	106.5	106.5	105.3	106.5	106.5	107.6	107.6	108.8	110.0	110.0
35°	99.5	99.5	99.5	99.5	99.5	99.5	98.4	98.4	98.4	98.4	98.4
37.5°	94.9	94.9	93.8	92.6	92.6	92.6	92.6	92.6	91.4	90.3	89.1
40°	91.4	90.3	90.3	89.1	88.0	88.0	86.8	85.7	85.7	84.5	84.5
42.5°	86.8	85.7	85.7	84.5	83.3	83.3	82.2	81.0	81.0	81.0	79.9
45°	81.0	81.0	79.9	78.7	78.7	78.7	77.6	77.6	77.6	77.6	76.4
47.5°	75.2	75.2	74.1	74.1	74.1	74.1	72.9	72.9	72.9	72.9	72.9
50°	71.8	71.8	71.8	71.8	71.8	71.8	70.6	70.6	70.6	70.6	70.6
52.5°	68.3	68.3	68.3	68.3	68.3	68.3	68.3	68.3	68.3	68.3	68.3
55°	67.1	67.1	67.1	67.1	67.1	67.1	66.0	66.0	66.0	67.1	67.1
57.5°	64.8	64.8	63.7	63.7	63.7	63.7	63.7	63.7	63.7	63.7	63.7
60°	62.5	62.5	62.5	62.5	62.5	62.5	62.5	62.5	62.5	62.5	62.5
62.5°	59.0	59.0	59.0	59.0	59.0	60.2	60.2	60.2	60.2	60.2	59.0
65°	54.4	55.6	55.6	55.6	55.6	55.6	55.6	55.6	55.6	55.6	55.6
67.5°	52.1	52.1	52.1	52.1	52.1	52.1	52.1	52.1	52.1	52.1	52.1
70°	48.6	48.6	47.5	47.5	47.5	48.6	48.6	48.6	48.6	48.6	48.6
72.5°	44.0	44.0	44.0	44.0	44.0	44.0	44.0	44.0	44.0	45.1	45.1
75°	39.4	39.4	39.4	39.4	39.4	39.4	39.4	39.4	39.4	39.4	39.4
77.5°	34.7	34.7	33.6	33.6	33.6	34.7	34.7	34.7	34.7	35.9	35.9
80°	28.9	28.9	28.9	28.9	28.9	28.9	28.9	28.9	28.9	30.1	30.1
82.5°	23.2	23.2	23.2	23.2	23.2	23.2	23.2	23.2	23.2	24.3	24.3
85°	17.4	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	19.7	19.7
87.5°	11.6	11.6	11.6	11.6	11.6	11.6	10.4	10.4	10.4	10.4	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4
2.5°	737.3	738.5	739.7	739.7	740.8	742.0	742.0	746.6	751.2	753.5	755.9
5°	630.9	629.7	629.7	628.5	627.4	630.9	634.3	641.3	648.2	649.4	651.7
7.5°	494.3	495.4	496.6	496.6	497.7	494.3	489.6	490.8	491.9	497.7	502.4
10°	373.9	375.0	376.2	376.2	377.4	376.2	373.9	377.4	380.8	385.5	391.2
12.5°	290.5	294.0	297.5	299.8	303.3	305.6	306.7	311.4	314.8	320.6	326.4
15°	237.3	239.6	241.9	244.2	246.6	248.9	251.2	255.8	260.4	267.4	274.3
17.5°	200.3	200.3	201.4	201.4	201.4	203.7	206.0	208.4	209.5	216.5	223.4
20°	171.3	170.2	169.0	167.8	166.7	169.0	170.2	171.3	172.5	177.1	180.6
22.5°	147.0	147.0	148.2	148.2	148.2	147.0	144.7	145.8	145.8	148.2	151.6
25°	133.1	133.1	133.1	132.0	132.0	133.1	134.3	134.3	133.1	134.3	135.4
27.5°	120.4	121.5	121.5	122.7	122.7	123.9	123.9	123.9	123.9	125.0	126.2
30°	115.8	115.8	116.9	116.9	116.9	118.1	119.2	119.2	119.2	120.4	122.7
32.5°	111.1	112.3	113.4	114.6	115.8	116.9	116.9	118.1	118.1	119.2	120.4
35°	98.4	97.2	97.2	96.1	94.9	94.9	94.9	94.9	93.8	94.9	94.9
37.5°	88.0	88.0	88.0	86.8	86.8	88.0	88.0	88.0	88.0	89.1	89.1
40°	83.3	83.3	83.3	83.3	83.3	83.3	83.3	84.5	84.5	85.7	86.8
42.5°	79.9	79.9	79.9	79.9	79.9	81.0	81.0	81.0	81.0	82.2	82.2
45°	76.4	76.4	76.4	76.4	76.4	76.4	76.4	77.6	77.6	78.7	79.9
47.5°	72.9	72.9	72.9	72.9	72.9	74.1	75.2	75.2	75.2	76.4	76.4
50°	70.6	70.6	70.6	70.6	70.6	71.8	71.8	72.9	72.9	74.1	75.2
52.5°	68.3	68.3	68.3	68.3	68.3	69.5	69.5	70.6	70.6	71.8	72.9
55°	67.1	67.1	67.1	66.0	66.0	67.1	67.1	68.3	68.3	69.5	69.5
57.5°	63.7	63.7	63.7	63.7	63.7	63.7	63.7	64.8	64.8	66.0	67.1
60°	62.5	62.5	61.3	61.3	60.2	61.3	61.3	62.5	62.5	63.7	63.7
62.5°	59.0	59.0	59.0	57.9	57.9	59.0	59.0	59.0	59.0	60.2	61.3
65°	55.6	55.6	55.6	54.4	54.4	55.6	55.6	55.6	55.6	56.7	57.9
67.5°	52.1	52.1	52.1	50.9	50.9	50.9	50.9	52.1	52.1	53.2	54.4
70°	48.6	48.6	48.6	47.5	47.5	47.5	46.3	47.5	48.6	49.8	49.8
72.5°	45.1	45.1	45.1	44.0	44.0	44.0	42.8	44.0	44.0	45.1	45.1
75°	39.4	39.4	39.4	39.4	39.4	39.4	38.2	38.2	38.2	39.4	39.4
77.5°	35.9	35.9	35.9	34.7	34.7	34.7	33.6	33.6	33.6	34.7	34.7
80°	30.1	30.1	30.1	28.9	28.9	28.9	27.8	27.8	27.8	28.9	28.9
82.5°	24.3	24.3	24.3	23.2	23.2	23.2	22.0	22.0	22.0	23.2	23.2
85°	19.7	19.7	19.7	19.7	19.7	19.7	18.5	18.5	18.5	19.7	20.8
87.5°	9.3	9.3	10.4	10.4	10.4	10.4	9.3	9.3	8.1	8.1	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4
2.5°	758.2	760.5	766.3	770.9	776.7	781.3	784.8	789.4	792.9	796.4	798.7
5°	652.8	654.0	659.8	665.6	670.2	676.0	684.1	692.2	700.3	708.4	714.2
7.5°	508.2	512.8	519.7	527.8	534.8	541.7	549.8	559.1	567.2	575.3	583.4
10°	395.9	400.5	407.4	414.4	420.2	427.1	436.4	445.6	454.9	464.2	473.4
12.5°	332.2	338.0	346.1	354.2	361.1	369.2	380.8	391.2	402.8	413.2	424.8
15°	280.1	287.1	297.5	309.1	319.5	329.9	341.5	353.0	363.5	375.0	386.6
17.5°	230.3	237.3	246.6	257.0	266.2	275.5	289.4	302.1	316.0	328.7	341.5
20°	185.2	188.7	197.9	207.2	216.5	225.7	236.1	246.6	257.0	267.4	283.6
22.5°	154.0	156.3	160.9	164.4	169.0	172.5	182.9	193.3	202.6	213.0	228.0
25°	135.4	136.6	140.1	142.4	145.8	148.2	155.1	160.9	167.8	173.6	187.5
27.5°	126.2	127.3	128.5	129.6	130.8	132.0	136.6	141.2	144.7	149.3	162.1
30°	123.9	125.0	128.5	130.8	134.3	136.6	138.9	141.2	143.5	145.8	154.0
32.5°	121.5	122.7	122.7	121.5	121.5	120.4	122.7	123.9	126.2	127.3	134.3
35°	96.1	96.1	97.2	98.4	99.5	100.7	104.2	106.5	110.0	112.3	118.1
37.5°	90.3	90.3	91.4	93.8	94.9	96.1	98.4	100.7	103.0	105.3	111.1
40°	86.8	88.0	89.1	90.3	91.4	92.6	94.9	96.1	98.4	99.5	104.2
42.5°	83.3	83.3	84.5	86.8	88.0	89.1	91.4	92.6	94.9	96.1	100.7
45°	81.0	82.2	83.3	84.5	84.5	85.7	88.0	90.3	91.4	93.8	98.4
47.5°	77.6	77.6	79.9	81.0	83.3	84.5	86.8	88.0	90.3	91.4	96.1
50°	75.2	76.4	78.7	79.9	82.2	83.3	86.8	89.1	92.6	94.9	97.2
52.5°	72.9	74.1	76.4	77.6	79.9	81.0	85.7	90.3	93.8	98.4	98.4
55°	70.6	70.6	72.9	76.4	78.7	81.0	83.3	86.8	89.1	91.4	91.4
57.5°	67.1	68.3	70.6	74.1	76.4	78.7	81.0	83.3	84.5	86.8	85.7
60°	64.8	64.8	68.3	71.8	75.2	78.7	78.7	78.7	77.6	77.6	77.6
62.5°	61.3	62.5	67.1	72.9	77.6	82.2	78.7	75.2	71.8	68.3	69.5
65°	59.0	60.2	62.5	66.0	68.3	70.6	68.3	67.1	64.8	62.5	63.7
67.5°	54.4	55.6	56.7	56.7	57.9	57.9	57.9	57.9	57.9	57.9	59.0
70°	50.9	50.9	50.9	52.1	52.1	52.1	52.1	52.1	52.1	52.1	53.2
72.5°	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3	47.5
75°	40.5	40.5	40.5	40.5	40.5	40.5	40.5	40.5	40.5	40.5	41.7
77.5°	35.9	35.9	35.9	35.9	35.9	35.9	35.9	35.9	34.7	34.7	35.9
80°	30.1	30.1	30.1	30.1	28.9	28.9	28.9	28.9	28.9	28.9	30.1
82.5°	24.3	24.3	24.3	24.3	23.2	23.2	23.2	23.2	22.0	22.0	23.2
85°	22.0	23.2	23.2	24.3	24.3	24.3	23.2	22.0	20.8	19.7	19.7
87.5°	9.3	9.3	9.3	9.3	8.1	8.1	8.1	8.1	8.1	8.1	8.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4
2.5°	802.2	804.5	806.8	810.3	814.9	818.4	821.8	828.8	836.9	843.8	850.8
5°	720.0	725.8	731.6	738.5	745.4	751.2	758.2	772.1	786.0	798.7	812.6
7.5°	590.3	598.4	605.4	617.0	627.4	639.0	649.4	666.7	682.9	700.3	716.5
10°	482.7	491.9	501.2	516.3	532.5	547.5	562.6	576.4	591.5	605.4	619.3
12.5°	436.4	446.8	458.4	467.6	478.1	487.3	496.6	512.8	529.0	545.2	561.4
15°	398.2	409.8	421.3	432.9	443.3	454.9	465.3	479.2	494.3	508.2	522.0
17.5°	354.2	365.8	378.5	391.2	404.0	416.7	429.4	449.1	468.8	487.3	507.0
20°	298.6	314.8	329.9	347.3	364.6	382.0	399.3	420.2	441.0	460.7	481.5
22.5°	243.1	258.1	273.2	294.0	314.8	334.5	355.4	383.1	409.8	437.5	464.2
25°	202.6	216.5	230.3	253.5	275.5	298.6	320.6	354.2	386.6	420.2	452.6
27.5°	174.8	187.5	200.3	224.6	248.9	272.0	296.3	333.4	369.2	406.3	442.2
30°	162.1	170.2	178.3	201.4	224.6	246.6	269.7	305.6	341.5	377.4	413.2
32.5°	141.2	148.2	155.1	175.9	196.8	216.5	237.3	274.3	310.2	347.3	383.1
35°	125.0	130.8	136.6	156.3	174.8	194.5	213.0	250.0	287.1	324.1	361.1
37.5°	115.8	121.5	126.2	143.5	162.1	179.4	196.8	233.8	269.7	306.7	342.6
40°	108.8	112.3	116.9	134.3	150.5	167.8	184.0	217.6	252.3	285.9	319.5
42.5°	104.2	108.8	112.3	127.3	143.5	158.6	173.6	206.0	238.4	269.7	302.1
45°	103.0	107.6	112.3	125.0	137.7	149.3	162.1	193.3	224.6	255.8	287.1
47.5°	100.7	104.2	108.8	119.2	128.5	138.9	148.2	179.4	210.7	240.8	272.0
50°	99.5	100.7	103.0	112.3	121.5	130.8	140.1	171.3	202.6	233.8	265.1
52.5°	98.4	98.4	98.4	106.5	114.6	121.5	129.6	160.9	193.3	224.6	255.8
55°	91.4	90.3	90.3	98.4	105.3	113.4	120.4	151.6	182.9	213.0	244.2
57.5°	84.5	83.3	82.2	89.1	96.1	103.0	110.0	141.2	173.6	204.9	236.1
60°	77.6	76.4	76.4	83.3	89.1	96.1	101.9	134.3	165.5	197.9	229.2
62.5°	69.5	70.6	70.6	76.4	83.3	89.1	94.9	127.3	160.9	193.3	225.7
65°	63.7	64.8	64.8	71.8	78.7	85.7	92.6	123.9	156.3	187.5	218.8
67.5°	59.0	60.2	60.2	68.3	75.2	83.3	90.3	118.1	147.0	174.8	202.6
70°	54.4	54.4	55.6	63.7	71.8	79.9	88.0	112.3	136.6	159.7	184.0
72.5°	48.6	49.8	50.9	59.0	66.0	74.1	81.0	103.0	125.0	147.0	169.0
75°	42.8	44.0	45.1	52.1	59.0	66.0	72.9	93.8	113.4	134.3	154.0
77.5°	38.2	39.4	40.5	46.3	52.1	57.9	63.7	78.7	94.9	110.0	125.0
80°	31.3	31.3	32.4	37.0	41.7	45.1	49.8	60.2	70.6	79.9	90.3
82.5°	23.2	24.3	24.3	27.8	30.1	33.6	35.9	41.7	46.3	52.1	56.7
85°	19.7	18.5	18.5	20.8	22.0	24.3	25.5	28.9	31.3	34.7	37.0
87.5°	8.1	6.9	6.9	8.1	10.4	11.6	12.7	12.7	13.9	13.9	13.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4
2.5°	854.3	856.6	860.0	862.4	868.1	872.8	878.6	883.2	886.7	892.5	890.1
5°	823.0	833.4	843.8	854.3	862.4	870.5	877.4	885.5	894.8	912.1	916.8
7.5°	730.4	744.3	757.0	770.9	787.1	803.3	819.5	835.7	850.8	872.8	886.7
10°	639.0	658.6	677.2	696.8	711.9	726.9	740.8	755.9	776.7	798.7	824.2
12.5°	581.1	600.8	620.4	640.1	662.1	682.9	704.9	725.8	745.4	762.8	791.7
15°	542.9	564.9	585.7	606.5	633.2	658.6	685.3	710.7	739.7	762.8	782.5
17.5°	533.6	560.2	585.7	612.3	640.1	667.9	695.7	723.5	752.4	787.1	812.6
20°	517.4	553.3	589.2	625.1	660.9	695.7	731.6	766.3	804.5	846.1	857.7
22.5°	508.2	551.0	595.0	637.8	686.4	736.2	784.8	833.4	873.9	905.2	939.9
25°	507.0	560.2	614.6	667.9	729.2	789.4	850.8	911.0	963.1	994.3	1022.1
27.5°	505.8	570.7	634.3	698.0	773.2	847.3	922.5	996.6	1045.2	1090.4	1113.5
30°	491.9	569.5	648.2	725.8	810.3	894.8	979.3	1063.8	1113.5	1144.8	1156.4
32.5°	474.6	566.0	657.5	748.9	845.0	941.1	1036.0	1132.1	1171.4	1198.0	1188.8
35°	460.7	561.4	660.9	760.5	862.4	965.4	1067.2	1169.1	1225.8	1262.9	1247.8
37.5°	448.0	553.3	658.6	764.0	883.2	1002.4	1121.6	1240.9	1295.3	1334.6	1317.3
40°	432.9	545.2	658.6	770.9	907.5	1042.9	1179.5	1314.9	1385.6	1419.1	1392.5
42.5°	420.2	537.1	655.2	772.1	917.9	1063.8	1209.6	1355.5	1434.2	1481.6	1448.1
45°	404.0	520.9	636.6	753.5	914.4	1075.3	1235.1	1396.0	1487.4	1524.5	1478.2
47.5°	386.6	502.4	617.0	731.6	902.9	1074.2	1245.5	1416.8	1501.3	1545.3	1502.5
50°	380.8	496.6	611.2	726.9	912.1	1098.5	1283.7	1468.9	1530.2	1566.1	1509.4
52.5°	379.7	502.4	626.2	748.9	935.3	1120.5	1306.8	1492.0	1541.8	1580.0	1529.1
55°	376.2	509.3	641.3	773.2	967.7	1163.3	1357.8	1552.2	1602.0	1629.8	1591.6
57.5°	379.7	523.2	665.6	809.1	1009.4	1209.6	1409.9	1610.1	1670.3	1690.0	1681.9
60°	382.0	534.8	686.4	839.2	1034.8	1230.4	1426.1	1621.7	1684.2	1732.8	1742.1
62.5°	376.2	526.7	676.0	826.5	1003.6	1180.7	1357.8	1534.9	1637.9	1709.7	1751.3
65°	358.8	497.7	637.8	776.7	939.9	1104.3	1267.5	1430.7	1539.5	1646.0	1679.6
67.5°	320.6	438.7	556.8	674.8	817.2	959.6	1100.8	1243.2	1379.8	1482.8	1529.1
70°	277.8	370.4	464.2	556.8	686.4	816.1	945.7	1075.3	1195.7	1309.2	1353.1
72.5°	241.9	313.7	386.6	458.4	551.0	642.4	735.0	826.5	968.8	1082.3	1125.1
75°	206.0	258.1	309.1	361.1	424.8	488.5	551.0	614.6	715.3	817.2	860.0
77.5°	158.6	193.3	226.9	260.4	304.4	347.3	391.2	434.1	504.7	581.1	603.1
80°	110.0	129.6	148.2	167.8	202.6	237.3	272.0	306.7	353.0	395.9	429.4
82.5°	68.3	81.0	92.6	104.2	132.0	159.7	186.4	214.1	232.7	235.0	268.5
85°	44.0	52.1	59.0	66.0	82.2	99.5	115.8	132.0	118.1	110.0	130.8
87.5°	17.4	22.0	25.5	28.9	27.8	26.6	25.5	24.3	20.8	18.5	23.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4
2.5°	892.5	895.9	899.4	901.7	905.2	906.3	907.5	907.5	908.7	909.8	912.1
5°	935.3	942.2	949.2	955.0	961.9	967.7	972.3	978.1	982.7	982.7	981.6
7.5°	899.4	916.8	934.1	951.5	968.8	981.6	993.2	1005.9	1017.5	1019.8	1022.1
10°	851.9	870.5	887.8	906.3	923.7	943.4	961.9	980.4	1000.1	1003.6	1008.2
12.5°	808.0	829.9	851.9	872.8	894.8	908.7	922.5	935.3	949.2	958.4	967.7
15°	806.8	825.3	843.8	861.2	879.7	887.8	895.9	902.9	911.0	911.0	912.1
17.5°	833.4	845.0	856.6	867.0	878.6	879.7	882.0	883.2	884.3	880.9	877.4
20°	885.5	890.1	894.8	899.4	904.0	895.9	889.0	880.9	872.8	863.5	855.4
22.5°	961.9	951.5	941.1	930.6	920.2	906.3	891.3	877.4	862.4	850.8	839.2
25°	1033.7	1020.9	1008.2	995.5	982.7	952.6	922.5	891.3	861.2	848.5	835.7
27.5°	1129.7	1110.1	1090.4	1070.7	1051.0	1010.5	970.0	929.5	889.0	867.0	846.1
30°	1152.9	1130.9	1108.9	1085.8	1063.8	1024.4	986.2	946.9	907.5	882.0	857.7
32.5°	1186.5	1161.0	1135.5	1110.1	1084.6	1046.4	1008.2	968.8	930.6	907.5	883.2
35°	1242.0	1213.1	1184.1	1154.1	1125.1	1085.8	1047.6	1008.2	968.8	942.2	916.8
37.5°	1289.5	1255.9	1222.3	1188.8	1155.2	1120.5	1084.6	1049.9	1014.0	987.4	961.9
40°	1342.7	1305.7	1268.6	1232.8	1195.7	1163.3	1130.9	1097.3	1064.9	1044.1	1023.3
42.5°	1389.0	1343.9	1299.9	1255.9	1210.8	1188.8	1167.9	1145.9	1124.0	1113.5	1102.0
45°	1421.4	1379.8	1336.9	1295.3	1253.6	1237.4	1221.2	1205.0	1188.8	1199.2	1209.6
47.5°	1435.3	1401.8	1369.3	1336.9	1303.4	1309.2	1314.9	1319.6	1325.4	1339.3	1354.3
50°	1448.1	1429.5	1409.9	1391.3	1371.7	1393.7	1414.5	1436.5	1458.5	1487.4	1516.4
52.5°	1473.5	1463.1	1453.8	1443.4	1433.0	1471.2	1509.4	1547.6	1585.8	1618.2	1650.6
55°	1549.9	1541.8	1533.7	1524.5	1516.4	1570.8	1624.0	1678.4	1732.8	1766.4	1799.9
57.5°	1655.3	1650.6	1644.8	1640.2	1634.4	1687.7	1739.8	1791.8	1845.1	1877.5	1911.1
60°	1735.1	1736.3	1736.3	1737.4	1737.4	1778.0	1818.5	1860.1	1900.7	1928.4	1957.4
62.5°	1778.0	1775.6	1773.3	1771.0	1768.7	1802.3	1835.8	1869.4	1903.0	1923.8	1944.6
65°	1731.7	1744.4	1757.1	1769.9	1782.6	1787.2	1790.7	1795.3	1798.8	1811.5	1824.3
67.5°	1576.5	1602.0	1626.3	1651.8	1676.1	1658.7	1642.5	1625.2	1607.8	1611.3	1613.6
70°	1404.1	1433.0	1463.1	1492.0	1521.0	1480.5	1440.0	1398.3	1357.8	1343.9	1330.0
72.5°	1184.1	1209.6	1236.2	1261.7	1287.2	1237.4	1188.8	1139.0	1089.2	1064.9	1040.6
75°	905.2	935.3	966.5	996.6	1026.7	971.2	914.4	858.9	802.2	786.0	770.9
77.5°	659.8	695.7	731.6	767.4	803.3	753.5	703.8	652.8	603.1	593.8	584.5
80°	480.4	508.2	534.8	562.6	589.2	560.2	531.3	502.4	473.4	472.3	471.1
82.5°	324.1	348.4	371.6	395.9	419.0	407.4	397.0	385.5	373.9	385.5	398.2
85°	166.7	200.3	235.0	268.5	302.1	298.6	296.3	292.9	289.4	304.4	318.3
87.5°	33.6	62.5	91.4	119.2	148.2	141.2	134.3	126.2	119.2	123.9	127.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4
2.5°	913.3	914.4	914.4	914.4	914.4	914.4	912.1	911.0	908.7	906.3	902.9
5°	981.6	980.4	975.8	971.2	965.4	960.7	957.3	952.6	949.2	944.5	937.6
7.5°	1024.4	1026.7	1018.6	1011.7	1003.6	995.5	987.4	979.3	971.2	963.1	946.9
10°	1011.7	1015.1	1010.5	1005.9	1000.1	995.5	986.2	975.8	966.5	956.1	936.4
12.5°	975.8	985.1	982.7	980.4	978.1	975.8	970.0	963.1	957.3	950.3	928.3
15°	912.1	912.1	913.3	914.4	914.4	915.6	916.8	917.9	919.1	920.2	907.5
17.5°	873.9	870.5	870.5	870.5	870.5	870.5	875.1	880.9	885.5	890.1	886.7
20°	846.1	838.0	836.9	836.9	835.7	834.6	842.7	851.9	860.0	868.1	872.8
22.5°	827.6	816.1	814.9	813.7	812.6	811.4	821.8	832.3	842.7	853.1	869.3
25°	823.0	810.3	811.4	812.6	812.6	813.7	821.8	829.9	838.0	846.1	873.9
27.5°	824.2	803.3	804.5	805.6	805.6	806.8	819.5	831.1	843.8	855.4	890.1
30°	832.3	808.0	805.6	803.3	801.0	798.7	816.1	833.4	850.8	868.1	894.8
32.5°	860.0	836.9	831.1	825.3	819.5	813.7	834.6	854.3	875.1	894.8	916.8
35°	890.1	864.7	862.4	860.0	856.6	854.3	872.8	892.5	911.0	929.5	949.2
37.5°	935.3	909.8	907.5	904.0	901.7	898.2	919.1	938.8	959.6	979.3	996.6
40°	1002.4	981.6	980.4	980.4	979.3	978.1	994.3	1011.7	1027.9	1044.1	1055.7
42.5°	1091.5	1081.1	1084.6	1089.2	1092.7	1096.2	1108.9	1122.8	1135.5	1148.3	1144.8
45°	1220.0	1230.4	1231.6	1232.8	1233.9	1235.1	1238.5	1243.2	1246.7	1250.1	1236.2
47.5°	1368.2	1382.1	1389.0	1396.0	1401.8	1408.7	1404.1	1398.3	1393.7	1387.9	1353.1
50°	1544.1	1573.1	1571.9	1570.8	1568.4	1567.3	1558.0	1548.8	1538.3	1529.1	1478.2
52.5°	1683.0	1715.4	1721.2	1727.0	1732.8	1738.6	1721.2	1703.9	1685.4	1668.0	1604.3
55°	1832.4	1865.9	1867.1	1868.2	1868.2	1869.4	1845.1	1820.8	1795.3	1771.0	1705.0
57.5°	1943.5	1975.9	1972.4	1970.1	1966.6	1963.2	1934.2	1905.3	1876.3	1847.4	1781.4
60°	1985.2	2012.9	2006.0	1999.0	1990.9	1984.0	1962.0	1940.0	1916.9	1894.9	1831.2
62.5°	1965.5	1986.3	1975.9	1966.6	1956.2	1945.8	1918.0	1889.1	1861.3	1832.4	1786.1
65°	1835.8	1848.6	1834.7	1821.9	1809.2	1795.3	1772.2	1749.0	1724.7	1701.6	1670.3
67.5°	1617.1	1619.4	1618.2	1617.1	1615.9	1614.7	1581.2	1547.6	1512.9	1479.3	1477.0
70°	1317.3	1303.4	1305.7	1309.2	1311.5	1313.8	1288.3	1264.0	1238.5	1213.1	1224.7
72.5°	1016.3	992.0	997.8	1004.7	1010.5	1016.3	995.5	975.8	955.0	934.1	950.3
75°	754.7	739.7	745.4	752.4	758.2	764.0	755.9	747.8	738.5	730.4	745.4
77.5°	575.3	566.0	567.2	567.2	568.3	568.3	569.5	571.8	573.0	574.1	590.3
80°	468.8	467.6	466.5	465.3	463.0	461.9	473.4	485.0	496.6	508.2	516.3
82.5°	409.8	421.3	414.4	408.6	401.7	394.7	405.1	415.6	426.0	436.4	432.9
85°	333.4	347.3	334.5	321.8	307.9	295.2	304.4	312.5	321.8	329.9	325.3
87.5°	132.0	135.4	114.6	94.9	74.1	53.2	84.5	114.6	145.8	175.9	180.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4	833.4
2.5°	899.4	894.8	891.3	890.1	887.8	886.7	884.3	882.0	878.6	876.2	872.8
5°	929.5	922.5	914.4	902.9	892.5	880.9	869.3	858.9	848.5	836.9	826.5
7.5°	930.6	914.4	898.2	883.2	867.0	851.9	835.7	821.8	806.8	791.7	777.9
10°	917.9	898.2	878.6	858.9	840.4	820.7	801.0	784.8	767.4	750.1	733.9
12.5°	907.5	885.5	863.5	840.4	818.4	795.2	772.1	755.9	739.7	723.5	707.2
15°	894.8	880.9	868.1	847.3	826.5	805.6	784.8	762.8	742.0	720.0	698.0
17.5°	884.3	880.9	877.4	863.5	849.6	834.6	820.7	798.7	776.7	753.5	731.6
20°	878.6	883.2	887.8	880.9	873.9	865.8	858.9	842.7	826.5	809.1	792.9
22.5°	885.5	902.9	919.1	920.2	922.5	923.7	924.9	909.8	894.8	878.6	863.5
25°	901.7	929.5	957.3	972.3	987.4	1003.6	1018.6	1009.4	1000.1	990.8	981.6
27.5°	923.7	958.4	993.2	1015.1	1036.0	1058.0	1080.0	1078.8	1077.7	1075.3	1074.2
30°	920.2	946.9	973.5	1000.1	1026.7	1053.3	1080.0	1093.9	1106.6	1120.5	1134.4
32.5°	939.9	961.9	985.1	1012.8	1040.6	1069.6	1097.3	1126.3	1154.1	1183.0	1211.9
35°	970.0	989.7	1010.5	1040.6	1071.9	1102.0	1133.2	1167.9	1203.8	1239.7	1274.4
37.5°	1015.1	1032.5	1051.0	1076.5	1103.1	1128.6	1155.2	1206.1	1257.1	1309.2	1360.1
40°	1067.2	1078.8	1090.4	1114.7	1139.0	1163.3	1187.6	1251.3	1314.9	1378.6	1442.3
42.5°	1142.5	1139.0	1135.5	1155.2	1176.0	1195.7	1216.6	1274.4	1332.3	1390.2	1448.1
45°	1222.3	1208.5	1194.6	1203.8	1214.2	1223.5	1233.9	1293.0	1352.0	1412.2	1471.2
47.5°	1318.4	1283.7	1249.0	1240.9	1232.8	1223.5	1215.4	1279.1	1342.7	1407.5	1471.2
50°	1427.2	1375.1	1324.2	1303.4	1281.4	1260.5	1238.5	1290.6	1343.9	1397.1	1449.2
52.5°	1540.7	1475.8	1412.2	1379.8	1347.4	1313.8	1281.4	1325.4	1370.5	1415.7	1459.6
55°	1637.9	1571.9	1504.8	1466.6	1428.4	1390.2	1352.0	1396.0	1440.0	1483.9	1527.9
57.5°	1715.4	1649.5	1583.5	1547.6	1510.6	1474.7	1437.6	1479.3	1522.1	1565.0	1606.6
60°	1768.7	1705.0	1641.4	1606.6	1571.9	1537.2	1502.5	1552.2	1602.0	1652.9	1702.7
62.5°	1740.9	1694.6	1648.3	1633.3	1618.2	1602.0	1587.0	1634.4	1680.7	1728.2	1775.6
65°	1639.1	1607.8	1576.5	1591.6	1607.8	1622.8	1639.1	1670.3	1701.6	1734.0	1765.2
67.5°	1473.5	1471.2	1467.7	1501.3	1534.9	1569.6	1603.2	1624.0	1643.7	1664.5	1685.4
70°	1236.2	1249.0	1260.5	1318.4	1376.3	1434.2	1492.0	1500.1	1508.3	1516.4	1524.5
72.5°	967.7	983.9	1001.3	1077.7	1152.9	1229.3	1305.7	1301.1	1296.4	1290.6	1286.0
75°	761.7	776.7	792.9	863.5	934.1	1004.7	1075.3	1055.7	1037.1	1017.5	997.8
77.5°	607.7	623.9	641.3	707.2	773.2	840.4	906.3	858.9	811.4	764.0	716.5
80°	523.2	531.3	538.2	583.4	627.4	672.5	717.7	669.0	619.3	569.5	520.9
82.5°	429.4	424.8	421.3	448.0	474.6	501.2	527.8	481.5	435.2	387.8	341.5
85°	320.6	316.0	311.4	325.3	339.2	354.2	368.1	314.8	261.6	207.2	154.0
87.5°	186.4	191.0	195.6	210.7	225.7	241.9	257.0	202.6	148.2	92.6	38.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801

CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671801
 CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	833.4	833.4
2.5°	865.8	860.0
5°	818.4	810.3
7.5°	766.3	755.9
10°	718.8	704.9
12.5°	688.7	671.4
15°	677.2	656.3
17.5°	711.9	692.2
20°	765.1	738.5
22.5°	829.9	797.5
25°	942.2	902.9
27.5°	1033.7	993.2
30°	1090.4	1046.4
32.5°	1152.9	1095.0
35°	1217.7	1162.2
37.5°	1296.4	1233.9
40°	1377.5	1312.6
42.5°	1405.2	1363.6
45°	1431.9	1392.5
47.5°	1437.6	1405.2
50°	1443.4	1438.8
52.5°	1459.6	1458.5
55°	1529.1	1530.2
57.5°	1614.7	1621.7
60°	1693.5	1685.4
62.5°	1734.0	1692.3
65°	1706.2	1648.3
67.5°	1622.8	1560.3
70°	1440.0	1355.5
72.5°	1211.9	1137.8
75°	934.1	871.6
77.5°	664.4	612.3
80°	467.6	415.6
82.5°	299.8	258.1
85°	135.4	118.1
87.5°	38.2	37.0
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671801
CATALOG NUMBER: CCP-SA-1B-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)