

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671802

Luminaire Tested: **CCP-SA-1C-730-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671802
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1C-730-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @615mA w/ SLR
distribution lens
Light Source: (16) 3000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3416.6 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 32
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 4.8 fc
 Type IV - Short - N/A

REPORT NUMBER: P671802
CATALOG NUMBER: CCP-SA-1C-730-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	703.0	0.0	703.0
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	2713.6	0.0	2713.6
	% Fixture	79.4	0.0	79.4
Total	Lumens	3416.6	0.0	3416.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.8	2.5
10°-20°	179.0	5.2
20°-30°	261.9	7.7
30°-40°	368.9	10.8
40°-50°	507.0	14.8
50°-60°	691.0	20.2
60°-70°	756.3	22.1
70°-80°	436.8	12.8
80°-90°	130.9	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3416.6	100.0
0°-180°	3416.6	100.0

Coefficient of Utilization



REPORT NUMBER: P671802


CATALOG NUMBER: CCP-SA-1C-730-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	350.9	10.3			
FM	(30°-60°)	1246.8	36.5			
FH	(60°-80°)	1004.7	29.4			G1/1800
FVH	(80°-90°)	111.2	3.3			G2/225
BL	(0°-30°)	174.8	5.1	B1/500		
BM	(30°-60°)	320.1	9.4	B1/1000		
BH	(60°-80°)	188.4	5.5	B1/500		G1/500
BVH	(80°-90°)	19.7	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1
2.5°	1125.9	1119.9	1115.3	1110.8	1104.7	1100.2	1094.1	1088.0	1080.5	1074.4	1066.8
5°	1060.8	1042.6	1024.4	1013.8	1001.7	991.0	978.9	965.3	951.6	936.5	922.9
7.5°	989.5	966.8	944.1	925.9	906.2	888.0	868.3	851.6	835.0	818.3	801.6
10°	922.9	901.6	880.4	857.7	833.5	810.7	786.5	763.7	741.0	718.3	695.6
12.5°	878.9	853.1	828.9	803.1	778.9	753.1	727.4	706.2	684.9	662.2	641.0
15°	859.2	835.0	812.2	786.5	760.7	735.0	709.2	684.9	662.2	638.0	613.7
17.5°	906.2	871.3	836.5	803.1	769.8	736.5	703.1	672.8	642.5	612.2	581.9
20°	966.8	922.9	880.4	839.5	797.1	756.2	713.7	671.3	628.9	586.4	544.0
22.5°	1044.1	994.1	945.6	892.5	838.0	785.0	730.4	677.4	624.3	569.8	516.7
25°	1182.0	1122.9	1063.8	988.0	910.7	835.0	757.7	688.0	619.8	550.1	480.4
27.5°	1300.2	1219.9	1141.1	1050.1	959.2	868.3	777.4	697.1	618.3	538.0	457.6
30°	1369.9	1291.1	1212.3	1101.7	992.6	881.9	771.3	681.9	594.0	504.6	415.2
32.5°	1433.5	1345.6	1257.8	1136.5	1013.8	892.5	769.8	671.3	574.3	475.8	377.3
35°	1521.4	1424.4	1329.0	1188.0	1047.1	906.2	765.3	663.7	560.7	459.2	356.1
37.5°	1615.4	1495.7	1377.5	1221.4	1065.3	909.2	753.1	653.1	553.1	453.1	353.1
40°	1718.4	1572.9	1429.0	1256.2	1085.0	912.2	739.5	639.5	539.5	437.9	337.9
42.5°	1785.1	1627.5	1469.9	1283.5	1098.6	912.2	725.9	627.4	528.9	428.8	330.3
45°	1823.0	1669.9	1518.4	1316.9	1115.3	913.8	712.2	615.2	518.3	419.8	322.8
47.5°	1839.7	1697.2	1554.8	1342.6	1132.0	919.8	707.7	609.2	509.2	410.7	310.6
50°	1883.6	1757.8	1632.0	1404.7	1179.0	951.6	724.3	618.3	513.7	407.6	301.6
52.5°	1909.4	1801.8	1694.2	1460.8	1227.4	994.1	760.7	642.5	524.3	406.1	287.9
55°	2003.3	1900.3	1797.2	1548.7	1298.7	1050.1	800.1	669.8	539.5	407.6	277.3
57.5°	2123.0	2013.9	1906.3	1638.1	1369.9	1101.7	833.5	694.0	553.1	413.7	272.8
60°	2206.4	2100.3	1995.7	1710.8	1424.4	1139.6	853.1	707.7	562.2	415.2	269.7
62.5°	2215.5	2079.1	1944.2	1666.9	1389.6	1110.8	833.5	692.5	551.6	409.1	268.2
65°	2157.9	1998.8	1839.7	1574.5	1309.3	1044.1	778.9	650.1	521.3	391.0	262.2
67.5°	2042.7	1856.3	1669.9	1427.5	1185.0	942.6	700.1	589.5	480.4	369.7	259.1
70°	1774.5	1610.8	1448.7	1238.1	1028.9	818.3	607.7	516.7	427.3	336.4	245.5
72.5°	1489.6	1336.6	1185.0	1013.8	844.1	672.8	501.6	433.4	365.2	295.5	227.3
75°	1141.1	1025.9	912.2	785.0	657.7	528.9	401.6	351.6	301.6	251.6	201.5
77.5°	801.6	739.5	678.9	583.4	487.9	392.5	297.0	263.7	230.3	197.0	163.7
80°	544.0	509.2	475.8	407.6	339.4	269.7	201.5	180.3	157.6	136.4	113.7
82.5°	337.9	336.4	333.4	286.4	239.4	192.5	145.5	127.3	110.6	92.4	74.3
85°	154.6	180.3	204.6	178.8	153.1	127.3	101.5	89.4	77.3	63.6	51.5
87.5°	48.5	59.1	68.2	65.2	60.6	57.6	53.0	45.5	37.9	30.3	22.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1
2.5°	1060.8	1056.2	1050.1	1044.1	1036.5	1030.4	1022.9	1015.3	1013.8	1010.7	1009.2
5°	913.8	904.7	894.1	885.0	875.9	865.3	856.2	845.6	838.0	828.9	821.3
7.5°	785.0	769.8	753.1	736.5	721.3	706.2	689.5	674.3	666.8	659.2	651.6
10°	681.9	666.8	653.1	638.0	627.4	618.3	607.7	597.1	588.0	578.9	569.8
12.5°	630.4	619.8	609.2	598.6	586.4	575.8	563.7	551.6	541.0	531.9	521.3
15°	598.6	583.4	566.7	551.6	534.9	519.8	503.1	486.4	474.3	463.7	451.6
17.5°	560.7	538.0	516.7	494.0	475.8	457.6	437.9	419.8	406.1	391.0	377.3
20°	518.3	492.5	465.2	439.5	418.2	398.5	377.3	356.1	341.0	324.3	309.1
22.5°	481.9	448.5	413.7	378.8	356.1	333.4	309.1	286.4	272.8	257.6	244.0
25°	442.5	406.1	368.2	330.3	307.6	283.4	260.6	236.4	225.8	216.7	206.1
27.5°	421.3	384.9	347.0	310.6	289.4	266.7	245.5	222.8	215.2	206.1	198.5
30°	378.8	344.0	307.6	271.3	256.1	242.5	227.3	212.2	209.1	207.6	204.6
32.5°	341.0	304.6	268.2	231.9	218.2	204.6	190.9	177.3	175.8	172.8	171.2
35°	321.3	286.4	250.0	215.2	203.1	189.4	177.3	163.7	160.6	156.1	153.1
37.5°	316.7	280.3	242.5	206.1	194.0	181.8	168.2	156.1	153.1	150.0	147.0
40°	304.6	269.7	236.4	201.5	189.4	177.3	163.7	151.5	148.5	145.5	142.4
42.5°	295.5	262.2	227.3	192.5	181.8	171.2	159.1	148.5	145.5	142.4	137.9
45°	287.9	253.1	216.7	181.8	174.3	166.7	157.6	150.0	147.0	142.4	139.4
47.5°	275.8	242.5	207.6	172.8	165.2	159.1	151.5	144.0	140.9	137.9	134.9
50°	266.7	231.9	197.0	162.1	156.1	150.0	144.0	137.9	137.9	139.4	139.4
52.5°	254.6	221.2	187.9	154.6	148.5	142.4	136.4	130.3	131.8	133.4	134.9
55°	244.0	212.2	178.8	145.5	139.4	133.4	125.8	119.7	121.2	122.7	124.3
57.5°	239.4	206.1	172.8	139.4	133.4	125.8	119.7	112.1	112.1	112.1	112.1
60°	236.4	201.5	168.2	133.4	125.8	119.7	112.1	104.6	103.0	103.0	101.5
62.5°	234.9	200.0	166.7	131.8	122.7	115.2	106.1	97.0	95.5	94.0	92.4
65°	228.8	197.0	163.7	130.3	119.7	110.6	100.0	89.4	87.9	87.9	86.4
67.5°	227.3	194.0	162.1	128.8	118.2	106.1	95.5	83.3	81.8	80.3	78.8
70°	215.2	186.4	156.1	125.8	113.7	103.0	90.9	78.8	77.3	74.3	72.7
72.5°	200.0	174.3	147.0	119.7	107.6	95.5	83.3	71.2	69.7	68.2	65.2
75°	177.3	153.1	128.8	104.6	94.0	84.9	74.3	63.6	62.1	60.6	57.6
77.5°	145.5	125.8	107.6	87.9	80.3	72.7	65.2	57.6	56.1	54.6	51.5
80°	103.0	90.9	80.3	68.2	63.6	57.6	53.0	47.0	47.0	45.5	45.5
82.5°	68.2	62.1	56.1	50.0	47.0	43.9	40.9	37.9	37.9	36.4	36.4
85°	48.5	45.5	40.9	37.9	36.4	33.3	31.8	28.8	28.8	28.8	28.8
87.5°	22.7	22.7	21.2	21.2	19.7	19.7	18.2	16.7	16.7	16.7	16.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1
2.5°	1006.2	1001.7	997.1	991.0	986.5	980.4	972.9	966.8	959.2	959.2	957.7
5°	812.2	807.7	803.1	797.1	792.5	786.5	781.9	775.9	769.8	769.8	768.3
7.5°	644.0	634.9	625.8	615.2	606.1	600.1	594.0	586.4	580.4	575.8	571.3
10°	560.7	551.6	541.0	531.9	521.3	513.7	506.1	497.0	489.5	483.4	477.3
12.5°	510.7	500.1	489.5	478.9	468.2	457.6	448.5	437.9	427.3	419.8	412.2
15°	439.5	428.8	418.2	407.6	397.0	384.9	372.8	359.1	347.0	341.0	336.4
17.5°	362.2	351.6	339.4	328.8	316.7	307.6	298.5	289.4	280.3	274.3	269.7
20°	292.5	280.3	268.2	256.1	244.0	237.9	231.9	225.8	219.7	215.2	212.2
22.5°	228.8	221.2	215.2	207.6	200.0	195.5	192.5	187.9	183.4	183.4	183.4
25°	195.5	190.9	187.9	183.4	178.8	177.3	175.8	172.8	171.2	169.7	169.7
27.5°	189.4	184.9	180.3	175.8	171.2	169.7	168.2	165.2	163.7	163.7	163.7
30°	201.5	200.0	198.5	197.0	195.5	192.5	187.9	184.9	180.3	177.3	174.3
32.5°	168.2	166.7	166.7	165.2	163.7	166.7	168.2	171.2	172.8	174.3	175.8
35°	148.5	145.5	142.4	139.4	136.4	134.9	133.4	131.8	130.3	130.3	128.8
37.5°	144.0	140.9	137.9	134.9	131.8	130.3	128.8	127.3	125.8	125.8	124.3
40°	139.4	136.4	134.9	131.8	128.8	127.3	125.8	122.7	121.2	119.7	119.7
42.5°	134.9	133.4	130.3	128.8	125.8	124.3	122.7	119.7	118.2	116.7	115.2
45°	134.9	131.8	128.8	125.8	122.7	121.2	118.2	116.7	113.7	113.7	112.1
47.5°	131.8	128.8	125.8	122.7	119.7	118.2	115.2	113.7	110.6	109.1	107.6
50°	139.4	134.9	128.8	124.3	118.2	116.7	113.7	112.1	109.1	107.6	106.1
52.5°	136.4	131.8	125.8	121.2	115.2	112.1	110.6	107.6	104.6	103.0	101.5
55°	125.8	121.2	118.2	113.7	109.1	106.1	103.0	100.0	97.0	95.5	95.5
57.5°	112.1	110.6	109.1	107.6	106.1	103.0	100.0	95.5	92.4	90.9	89.4
60°	100.0	101.5	103.0	104.6	106.1	101.5	97.0	92.4	87.9	86.4	84.9
62.5°	90.9	94.0	97.0	98.5	101.5	97.0	92.4	87.9	83.3	81.8	80.3
65°	84.9	86.4	86.4	87.9	87.9	84.9	83.3	80.3	77.3	75.8	75.8
67.5°	77.3	77.3	77.3	75.8	75.8	74.3	74.3	72.7	71.2	69.7	69.7
70°	69.7	69.7	69.7	68.2	68.2	66.7	66.7	65.2	63.6	63.6	62.1
72.5°	63.6	63.6	62.1	62.1	60.6	60.6	60.6	59.1	59.1	57.6	57.6
75°	56.1	56.1	54.6	54.6	53.0	53.0	53.0	51.5	51.5	51.5	50.0
77.5°	50.0	50.0	48.5	48.5	47.0	47.0	47.0	45.5	45.5	43.9	43.9
80°	43.9	43.9	42.4	42.4	40.9	40.9	39.4	39.4	37.9	37.9	36.4
82.5°	34.9	34.9	34.9	34.9	34.9	33.3	33.3	31.8	30.3	30.3	28.8
85°	28.8	28.8	28.8	27.3	27.3	27.3	25.8	25.8	24.2	22.7	22.7
87.5°	16.7	16.7	16.7	15.2	15.2	15.2	15.2	15.2	15.2	15.2	13.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1
2.5°	957.7	956.2	950.1	944.1	950.1	956.2	956.2	956.2	954.7	954.7	954.7
5°	768.3	766.8	763.7	760.7	760.7	759.2	762.2	765.3	768.3	771.3	774.4
7.5°	565.2	560.7	556.1	551.6	554.6	556.1	560.7	563.7	568.3	571.3	578.9
10°	471.3	465.2	460.7	456.1	453.1	450.1	447.0	445.5	442.5	439.5	442.5
12.5°	403.1	395.5	387.9	378.8	377.3	375.8	372.8	369.7	366.7	363.7	362.2
15°	330.3	324.3	321.3	316.7	310.6	304.6	301.6	300.0	297.0	294.0	292.5
17.5°	263.7	257.6	253.1	248.5	247.0	244.0	244.0	244.0	244.0	244.0	244.0
20°	207.6	203.1	203.1	201.5	201.5	200.0	201.5	203.1	203.1	204.6	206.1
22.5°	181.8	181.8	180.3	178.8	180.3	180.3	181.8	183.4	184.9	186.4	187.9
25°	168.2	166.7	168.2	169.7	169.7	169.7	171.2	171.2	172.8	172.8	172.8
27.5°	162.1	162.1	163.7	163.7	165.2	165.2	165.2	163.7	163.7	162.1	162.1
30°	171.2	168.2	168.2	168.2	166.7	165.2	163.7	163.7	162.1	160.6	159.1
32.5°	177.3	178.8	177.3	174.3	172.8	169.7	168.2	165.2	163.7	160.6	157.6
35°	128.8	127.3	130.3	131.8	133.4	134.9	136.4	137.9	137.9	139.4	139.4
37.5°	124.3	122.7	122.7	121.2	121.2	121.2	121.2	121.2	119.7	119.7	121.2
40°	118.2	116.7	116.7	115.2	115.2	113.7	113.7	113.7	113.7	113.7	113.7
42.5°	113.7	112.1	112.1	112.1	112.1	110.6	110.6	109.1	109.1	107.6	107.6
45°	112.1	110.6	109.1	107.6	107.6	106.1	106.1	106.1	104.6	104.6	104.6
47.5°	106.1	104.6	104.6	103.0	103.0	101.5	101.5	101.5	100.0	100.0	100.0
50°	103.0	101.5	101.5	100.0	100.0	98.5	98.5	98.5	97.0	97.0	97.0
52.5°	98.5	97.0	97.0	97.0	95.5	94.0	94.0	94.0	92.4	92.4	92.4
55°	94.0	92.4	92.4	92.4	90.9	89.4	89.4	89.4	87.9	87.9	87.9
57.5°	87.9	86.4	86.4	84.9	84.9	84.9	84.9	84.9	83.3	83.3	83.3
60°	83.3	81.8	81.8	80.3	80.3	78.8	78.8	78.8	78.8	78.8	78.8
62.5°	78.8	77.3	75.8	74.3	75.8	75.8	75.8	75.8	74.3	74.3	74.3
65°	74.3	72.7	71.2	69.7	69.7	69.7	69.7	69.7	69.7	69.7	69.7
67.5°	68.2	66.7	65.2	63.6	65.2	65.2	65.2	65.2	65.2	65.2	65.2
70°	62.1	60.6	60.6	59.1	59.1	57.6	57.6	59.1	59.1	59.1	59.1
72.5°	56.1	54.6	54.6	53.0	53.0	53.0	53.0	53.0	53.0	53.0	53.0
75°	50.0	48.5	48.5	47.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0
77.5°	42.4	40.9	40.9	40.9	40.9	40.9	40.9	42.4	42.4	42.4	42.4
80°	36.4	34.9	34.9	34.9	34.9	34.9	34.9	34.9	34.9	34.9	34.9
82.5°	28.8	27.3	27.3	27.3	27.3	27.3	27.3	27.3	27.3	27.3	27.3
85°	21.2	19.7	19.7	19.7	21.2	21.2	21.2	21.2	21.2	21.2	21.2
87.5°	13.6	12.1	12.1	12.1	13.6	13.6	13.6	13.6	12.1	12.1	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1
2.5°	954.7	954.7	954.7	953.2	951.6	950.1	948.6	953.2	956.2	960.7	963.8
5°	775.9	778.9	780.4	785.0	789.5	794.1	798.6	801.6	804.7	806.2	809.2
7.5°	584.9	592.5	598.6	604.6	610.7	615.2	621.3	625.8	630.4	634.9	639.5
10°	444.0	447.0	448.5	454.6	459.2	465.2	469.8	474.3	478.9	481.9	486.4
12.5°	360.7	357.6	356.1	356.1	356.1	356.1	356.1	359.1	362.2	365.2	368.2
15°	290.9	289.4	287.9	286.4	284.9	281.9	280.3	283.4	286.4	289.4	292.5
17.5°	244.0	244.0	244.0	242.5	240.9	239.4	237.9	239.4	240.9	240.9	242.5
20°	209.1	210.6	212.2	213.7	213.7	215.2	215.2	216.7	218.2	218.2	219.7
22.5°	187.9	189.4	189.4	189.4	190.9	190.9	190.9	192.5	194.0	195.5	197.0
25°	171.2	171.2	169.7	169.7	171.2	171.2	171.2	171.2	172.8	172.8	172.8
27.5°	162.1	160.6	160.6	160.6	160.6	159.1	159.1	159.1	159.1	159.1	159.1
30°	157.6	156.1	154.6	153.1	153.1	151.5	150.0	150.0	150.0	150.0	150.0
32.5°	156.1	153.1	150.0	148.5	148.5	147.0	145.5	144.0	144.0	142.4	140.9
35°	139.4	137.9	137.9	136.4	134.9	133.4	131.8	131.8	131.8	130.3	130.3
37.5°	121.2	122.7	122.7	122.7	124.3	124.3	124.3	124.3	125.8	125.8	125.8
40°	113.7	113.7	113.7	115.2	116.7	116.7	118.2	118.2	119.7	119.7	119.7
42.5°	107.6	106.1	106.1	107.6	107.6	109.1	109.1	110.6	112.1	112.1	113.7
45°	104.6	103.0	103.0	103.0	103.0	101.5	101.5	103.0	104.6	106.1	107.6
47.5°	98.5	98.5	97.0	97.0	97.0	97.0	97.0	97.0	98.5	98.5	98.5
50°	95.5	95.5	94.0	94.0	94.0	94.0	94.0	94.0	94.0	94.0	94.0
52.5°	92.4	90.9	90.9	90.9	90.9	89.4	89.4	89.4	89.4	89.4	89.4
55°	87.9	86.4	86.4	86.4	86.4	86.4	86.4	86.4	87.9	87.9	87.9
57.5°	83.3	81.8	81.8	81.8	83.3	83.3	83.3	83.3	84.9	84.9	84.9
60°	78.8	78.8	78.8	78.8	78.8	78.8	78.8	80.3	80.3	81.8	81.8
62.5°	74.3	74.3	74.3	74.3	75.8	75.8	75.8	75.8	77.3	77.3	77.3
65°	69.7	69.7	69.7	69.7	71.2	71.2	71.2	71.2	71.2	71.2	71.2
67.5°	65.2	65.2	65.2	65.2	65.2	65.2	65.2	66.7	66.7	68.2	68.2
70°	59.1	57.6	57.6	59.1	59.1	60.6	60.6	62.1	62.1	63.6	63.6
72.5°	53.0	53.0	53.0	53.0	53.0	53.0	53.0	54.6	56.1	56.1	57.6
75°	47.0	47.0	47.0	47.0	48.5	48.5	48.5	50.0	50.0	51.5	51.5
77.5°	42.4	40.9	40.9	40.9	42.4	42.4	42.4	43.9	43.9	45.5	45.5
80°	34.9	34.9	34.9	34.9	36.4	36.4	36.4	36.4	37.9	37.9	37.9
82.5°	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8	30.3	30.3	30.3
85°	21.2	21.2	21.2	21.2	22.7	22.7	22.7	22.7	22.7	22.7	22.7
87.5°	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6	15.2	15.2	15.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1
2.5°	963.8	963.8	963.8	963.8	966.8	968.3	971.3	972.9	971.3	969.8	966.8
5°	810.7	812.2	812.2	813.8	813.8	813.8	813.8	813.8	816.8	819.8	822.8
7.5°	641.0	642.5	644.0	645.5	645.5	645.5	644.0	644.0	645.5	645.5	647.1
10°	491.0	497.0	501.6	506.1	503.1	498.6	495.5	491.0	491.0	491.0	489.5
12.5°	371.3	372.8	375.8	377.3	375.8	375.8	374.3	372.8	374.3	377.3	378.8
15°	294.0	294.0	295.5	295.5	297.0	298.5	298.5	300.0	303.1	304.6	307.6
17.5°	244.0	245.5	245.5	247.0	247.0	248.5	248.5	248.5	251.6	254.6	259.1
20°	219.7	219.7	219.7	219.7	219.7	218.2	218.2	216.7	218.2	221.2	222.8
22.5°	197.0	198.5	198.5	198.5	197.0	195.5	192.5	190.9	190.9	192.5	192.5
25°	172.8	171.2	171.2	169.7	169.7	171.2	171.2	171.2	172.8	172.8	174.3
27.5°	159.1	157.6	157.6	156.1	156.1	157.6	157.6	157.6	157.6	157.6	157.6
30°	148.5	148.5	147.0	145.5	147.0	147.0	148.5	148.5	150.0	150.0	151.5
32.5°	140.9	139.4	139.4	137.9	139.4	139.4	140.9	140.9	142.4	144.0	144.0
35°	130.3	130.3	130.3	130.3	130.3	130.3	128.8	128.8	128.8	128.8	128.8
37.5°	124.3	124.3	122.7	121.2	121.2	121.2	121.2	121.2	119.7	118.2	116.7
40°	119.7	118.2	118.2	116.7	115.2	115.2	113.7	112.1	112.1	110.6	110.6
42.5°	113.7	112.1	112.1	110.6	109.1	109.1	107.6	106.1	106.1	106.1	104.6
45°	106.1	106.1	104.6	103.0	103.0	103.0	101.5	101.5	101.5	101.5	100.0
47.5°	98.5	98.5	97.0	97.0	97.0	97.0	95.5	95.5	95.5	95.5	95.5
50°	94.0	94.0	94.0	94.0	94.0	94.0	92.4	92.4	92.4	92.4	92.4
52.5°	89.4	89.4	89.4	89.4	89.4	89.4	89.4	89.4	89.4	89.4	89.4
55°	87.9	87.9	87.9	87.9	87.9	87.9	86.4	86.4	86.4	87.9	87.9
57.5°	84.9	84.9	83.3	83.3	83.3	83.3	83.3	83.3	83.3	83.3	83.3
60°	81.8	81.8	81.8	81.8	81.8	81.8	81.8	81.8	81.8	81.8	81.8
62.5°	77.3	77.3	77.3	77.3	77.3	78.8	78.8	78.8	78.8	78.8	77.3
65°	71.2	72.7	72.7	72.7	72.7	72.7	72.7	72.7	72.7	72.7	72.7
67.5°	68.2	68.2	68.2	68.2	68.2	68.2	68.2	68.2	68.2	68.2	68.2
70°	63.6	63.6	62.1	62.1	62.1	63.6	63.6	63.6	63.6	63.6	63.6
72.5°	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6	59.1	59.1
75°	51.5	51.5	51.5	51.5	51.5	51.5	51.5	51.5	51.5	51.5	51.5
77.5°	45.5	45.5	43.9	43.9	43.9	45.5	45.5	45.5	45.5	47.0	47.0
80°	37.9	37.9	37.9	37.9	37.9	37.9	37.9	37.9	37.9	39.4	39.4
82.5°	30.3	30.3	30.3	30.3	30.3	30.3	30.3	30.3	30.3	31.8	31.8
85°	22.7	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	25.8	25.8
87.5°	15.2	15.2	15.2	15.2	15.2	15.2	13.6	13.6	13.6	13.6	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1
2.5°	965.3	966.8	968.3	968.3	969.8	971.3	971.3	977.4	983.5	986.5	989.5
5°	825.9	824.4	824.4	822.8	821.3	825.9	830.4	839.5	848.6	850.1	853.1
7.5°	647.1	648.6	650.1	650.1	651.6	647.1	641.0	642.5	644.0	651.6	657.7
10°	489.5	491.0	492.5	492.5	494.0	492.5	489.5	494.0	498.6	504.6	512.2
12.5°	380.4	384.9	389.4	392.5	397.0	400.1	401.6	407.6	412.2	419.8	427.3
15°	310.6	313.7	316.7	319.7	322.8	325.8	328.8	334.9	341.0	350.0	359.1
17.5°	262.2	262.2	263.7	263.7	263.7	266.7	269.7	272.8	274.3	283.4	292.5
20°	224.3	222.8	221.2	219.7	218.2	221.2	222.8	224.3	225.8	231.9	236.4
22.5°	192.5	192.5	194.0	194.0	194.0	192.5	189.4	190.9	190.9	194.0	198.5
25°	174.3	174.3	174.3	172.8	172.8	174.3	175.8	175.8	174.3	175.8	177.3
27.5°	157.6	159.1	159.1	160.6	160.6	162.1	162.1	162.1	162.1	163.7	165.2
30°	151.5	151.5	153.1	153.1	153.1	154.6	156.1	156.1	156.1	157.6	160.6
32.5°	145.5	147.0	148.5	150.0	151.5	153.1	153.1	154.6	154.6	156.1	157.6
35°	128.8	127.3	127.3	125.8	124.3	124.3	124.3	124.3	122.7	124.3	124.3
37.5°	115.2	115.2	115.2	113.7	113.7	115.2	115.2	115.2	115.2	116.7	116.7
40°	109.1	109.1	109.1	109.1	109.1	109.1	109.1	110.6	110.6	112.1	113.7
42.5°	104.6	104.6	104.6	104.6	104.6	106.1	106.1	106.1	106.1	107.6	107.6
45°	100.0	100.0	100.0	100.0	100.0	100.0	100.0	101.5	101.5	103.0	104.6
47.5°	95.5	95.5	95.5	95.5	95.5	97.0	98.5	98.5	98.5	100.0	100.0
50°	92.4	92.4	92.4	92.4	92.4	94.0	94.0	95.5	95.5	97.0	98.5
52.5°	89.4	89.4	89.4	89.4	89.4	90.9	90.9	92.4	92.4	94.0	95.5
55°	87.9	87.9	87.9	86.4	86.4	87.9	87.9	89.4	89.4	90.9	90.9
57.5°	83.3	83.3	83.3	83.3	83.3	83.3	83.3	84.9	84.9	86.4	87.9
60°	81.8	81.8	80.3	80.3	78.8	80.3	80.3	81.8	81.8	83.3	83.3
62.5°	77.3	77.3	77.3	75.8	75.8	77.3	77.3	77.3	77.3	78.8	80.3
65°	72.7	72.7	72.7	71.2	71.2	72.7	72.7	72.7	72.7	74.3	75.8
67.5°	68.2	68.2	68.2	66.7	66.7	66.7	66.7	68.2	68.2	69.7	71.2
70°	63.6	63.6	63.6	62.1	62.1	62.1	60.6	62.1	63.6	65.2	65.2
72.5°	59.1	59.1	59.1	57.6	57.6	57.6	56.1	57.6	57.6	59.1	59.1
75°	51.5	51.5	51.5	51.5	51.5	51.5	50.0	50.0	50.0	51.5	51.5
77.5°	47.0	47.0	47.0	45.5	45.5	45.5	43.9	43.9	43.9	45.5	45.5
80°	39.4	39.4	39.4	37.9	37.9	37.9	36.4	36.4	36.4	37.9	37.9
82.5°	31.8	31.8	31.8	30.3	30.3	30.3	28.8	28.8	28.8	30.3	30.3
85°	25.8	25.8	25.8	25.8	25.8	25.8	24.2	24.2	24.2	25.8	27.3
87.5°	12.1	12.1	13.6	13.6	13.6	13.6	12.1	12.1	10.6	10.6	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1
2.5°	992.6	995.6	1003.2	1009.2	1016.8	1022.9	1027.4	1033.5	1038.0	1042.6	1045.6
5°	854.7	856.2	863.8	871.3	877.4	885.0	895.6	906.2	916.8	927.4	935.0
7.5°	665.2	671.3	680.4	691.0	700.1	709.2	719.8	731.9	742.5	753.1	763.7
10°	518.3	524.3	533.4	542.5	550.1	559.2	571.3	583.4	595.5	607.7	619.8
12.5°	434.9	442.5	453.1	463.7	472.8	483.4	498.6	512.2	527.3	541.0	556.1
15°	366.7	375.8	389.4	404.6	418.2	431.9	447.0	462.2	475.8	491.0	506.1
17.5°	301.6	310.6	322.8	336.4	348.5	360.7	378.8	395.5	413.7	430.4	447.0
20°	242.5	247.0	259.1	271.3	283.4	295.5	309.1	322.8	336.4	350.0	371.3
22.5°	201.5	204.6	210.6	215.2	221.2	225.8	239.4	253.1	265.2	278.8	298.5
25°	177.3	178.8	183.4	186.4	190.9	194.0	203.1	210.6	219.7	227.3	245.5
27.5°	165.2	166.7	168.2	169.7	171.2	172.8	178.8	184.9	189.4	195.5	212.2
30°	162.1	163.7	168.2	171.2	175.8	178.8	181.8	184.9	187.9	190.9	201.5
32.5°	159.1	160.6	160.6	159.1	159.1	157.6	160.6	162.1	165.2	166.7	175.8
35°	125.8	125.8	127.3	128.8	130.3	131.8	136.4	139.4	144.0	147.0	154.6
37.5°	118.2	118.2	119.7	122.7	124.3	125.8	128.8	131.8	134.9	137.9	145.5
40°	113.7	115.2	116.7	118.2	119.7	121.2	124.3	125.8	128.8	130.3	136.4
42.5°	109.1	109.1	110.6	113.7	115.2	116.7	119.7	121.2	124.3	125.8	131.8
45°	106.1	107.6	109.1	110.6	110.6	112.1	115.2	118.2	119.7	122.7	128.8
47.5°	101.5	101.5	104.6	106.1	109.1	110.6	113.7	115.2	118.2	119.7	125.8
50°	98.5	100.0	103.0	104.6	107.6	109.1	113.7	116.7	121.2	124.3	127.3
52.5°	95.5	97.0	100.0	101.5	104.6	106.1	112.1	118.2	122.7	128.8	128.8
55°	92.4	92.4	95.5	100.0	103.0	106.1	109.1	113.7	116.7	119.7	119.7
57.5°	87.9	89.4	92.4	97.0	100.0	103.0	106.1	109.1	110.6	113.7	112.1
60°	84.9	84.9	89.4	94.0	98.5	103.0	103.0	103.0	101.5	101.5	101.5
62.5°	80.3	81.8	87.9	95.5	101.5	107.6	103.0	98.5	94.0	89.4	90.9
65°	77.3	78.8	81.8	86.4	89.4	92.4	89.4	87.9	84.9	81.8	83.3
67.5°	71.2	72.7	74.3	74.3	75.8	75.8	75.8	75.8	75.8	75.8	77.3
70°	66.7	66.7	66.7	68.2	68.2	68.2	68.2	68.2	68.2	68.2	69.7
72.5°	60.6	60.6	60.6	60.6	60.6	60.6	60.6	60.6	60.6	60.6	62.1
75°	53.0	53.0	53.0	53.0	53.0	53.0	53.0	53.0	53.0	53.0	54.6
77.5°	47.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0	45.5	45.5	47.0
80°	39.4	39.4	39.4	39.4	37.9	37.9	37.9	37.9	37.9	37.9	39.4
82.5°	31.8	31.8	31.8	31.8	30.3	30.3	30.3	30.3	28.8	28.8	30.3
85°	28.8	30.3	30.3	31.8	31.8	31.8	30.3	28.8	27.3	25.8	25.8
87.5°	12.1	12.1	12.1	12.1	10.6	10.6	10.6	10.6	10.6	10.6	10.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1
2.5°	1050.1	1053.2	1056.2	1060.8	1066.8	1071.4	1075.9	1085.0	1095.6	1104.7	1113.8
5°	942.6	950.1	957.7	966.8	975.9	983.5	992.6	1010.7	1028.9	1045.6	1063.8
7.5°	772.8	783.4	792.5	807.7	821.3	836.5	850.1	872.8	894.1	916.8	938.0
10°	631.9	644.0	656.2	675.9	697.1	716.8	736.5	754.7	774.4	792.5	810.7
12.5°	571.3	584.9	600.1	612.2	625.8	638.0	650.1	671.3	692.5	713.7	735.0
15°	521.3	536.4	551.6	566.7	580.4	595.5	609.2	627.4	647.1	665.2	683.4
17.5°	463.7	478.9	495.5	512.2	528.9	545.5	562.2	588.0	613.7	638.0	663.7
20°	391.0	412.2	431.9	454.6	477.3	500.1	522.8	550.1	577.4	603.1	630.4
22.5°	318.2	337.9	357.6	384.9	412.2	437.9	465.2	501.6	536.4	572.8	607.7
25°	265.2	283.4	301.6	331.9	360.7	391.0	419.8	463.7	506.1	550.1	592.5
27.5°	228.8	245.5	262.2	294.0	325.8	356.1	387.9	436.4	483.4	531.9	578.9
30°	212.2	222.8	233.4	263.7	294.0	322.8	353.1	400.1	447.0	494.0	541.0
32.5°	184.9	194.0	203.1	230.3	257.6	283.4	310.6	359.1	406.1	454.6	501.6
35°	163.7	171.2	178.8	204.6	228.8	254.6	278.8	327.3	375.8	424.3	472.8
37.5°	151.5	159.1	165.2	187.9	212.2	234.9	257.6	306.1	353.1	401.6	448.5
40°	142.4	147.0	153.1	175.8	197.0	219.7	240.9	284.9	330.3	374.3	418.2
42.5°	136.4	142.4	147.0	166.7	187.9	207.6	227.3	269.7	312.2	353.1	395.5
45°	134.9	140.9	147.0	163.7	180.3	195.5	212.2	253.1	294.0	334.9	375.8
47.5°	131.8	136.4	142.4	156.1	168.2	181.8	194.0	234.9	275.8	315.2	356.1
50°	130.3	131.8	134.9	147.0	159.1	171.2	183.4	224.3	265.2	306.1	347.0
52.5°	128.8	128.8	128.8	139.4	150.0	159.1	169.7	210.6	253.1	294.0	334.9
55°	119.7	118.2	118.2	128.8	137.9	148.5	157.6	198.5	239.4	278.8	319.7
57.5°	110.6	109.1	107.6	116.7	125.8	134.9	144.0	184.9	227.3	268.2	309.1
60°	101.5	100.0	100.0	109.1	116.7	125.8	133.4	175.8	216.7	259.1	300.0
62.5°	90.9	92.4	92.4	100.0	109.1	116.7	124.3	166.7	210.6	253.1	295.5
65°	83.3	84.9	84.9	94.0	103.0	112.1	121.2	162.1	204.6	245.5	286.4
67.5°	77.3	78.8	78.8	89.4	98.5	109.1	118.2	154.6	192.5	228.8	265.2
70°	71.2	71.2	72.7	83.3	94.0	104.6	115.2	147.0	178.8	209.1	240.9
72.5°	63.6	65.2	66.7	77.3	86.4	97.0	106.1	134.9	163.7	192.5	221.2
75°	56.1	57.6	59.1	68.2	77.3	86.4	95.5	122.7	148.5	175.8	201.5
77.5°	50.0	51.5	53.0	60.6	68.2	75.8	83.3	103.0	124.3	144.0	163.7
80°	40.9	40.9	42.4	48.5	54.6	59.1	65.2	78.8	92.4	104.6	118.2
82.5°	30.3	31.8	31.8	36.4	39.4	43.9	47.0	54.6	60.6	68.2	74.3
85°	25.8	24.2	24.2	27.3	28.8	31.8	33.3	37.9	40.9	45.5	48.5
87.5°	10.6	9.1	9.1	10.6	13.6	15.2	16.7	16.7	18.2	18.2	18.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1
2.5°	1118.3	1121.4	1125.9	1128.9	1136.5	1142.6	1150.2	1156.2	1160.8	1168.3	1165.3
5°	1077.4	1091.1	1104.7	1118.3	1128.9	1139.6	1148.6	1159.3	1171.4	1194.1	1200.2
7.5°	956.2	974.4	991.0	1009.2	1030.4	1051.7	1072.9	1094.1	1113.8	1142.6	1160.8
10°	836.5	862.2	886.5	912.2	931.9	951.6	969.8	989.5	1016.8	1045.6	1078.9
12.5°	760.7	786.5	812.2	838.0	866.8	894.1	922.9	950.1	975.9	998.6	1036.5
15°	710.7	739.5	766.8	794.1	828.9	862.2	897.1	930.4	968.3	998.6	1024.4
17.5°	698.6	733.4	766.8	801.6	838.0	874.4	910.7	947.1	985.0	1030.4	1063.8
20°	677.4	724.3	771.3	818.3	865.3	910.7	957.7	1003.2	1053.2	1107.7	1122.9
22.5°	665.2	721.3	778.9	835.0	898.6	963.8	1027.4	1091.1	1144.1	1185.0	1230.5
25°	663.7	733.4	804.7	874.4	954.7	1033.5	1113.8	1192.6	1260.8	1301.7	1338.1
27.5°	662.2	747.1	830.4	913.8	1012.3	1109.2	1207.7	1304.7	1368.4	1427.5	1457.8
30°	644.0	745.6	848.6	950.1	1060.8	1171.4	1282.0	1392.6	1457.8	1498.7	1513.8
32.5°	621.3	741.0	860.7	980.4	1106.2	1232.0	1356.3	1482.0	1533.5	1568.4	1556.3
35°	603.1	735.0	865.3	995.6	1128.9	1263.8	1397.2	1530.5	1604.8	1653.3	1633.6
37.5°	586.4	724.3	862.2	1000.1	1156.2	1312.3	1468.4	1624.5	1695.7	1747.2	1724.5
40°	566.7	713.7	862.2	1009.2	1188.0	1365.3	1544.2	1721.5	1813.9	1857.8	1823.0
42.5°	550.1	703.1	857.7	1010.7	1201.7	1392.6	1583.6	1774.5	1877.5	1939.7	1895.7
45°	528.9	681.9	833.5	986.5	1197.1	1407.8	1616.9	1827.5	1947.2	1995.7	1935.1
47.5°	506.1	657.7	807.7	957.7	1182.0	1406.3	1630.5	1854.8	1965.4	2023.0	1966.9
50°	498.6	650.1	800.1	951.6	1194.1	1438.1	1680.5	1923.0	2003.3	2050.3	1976.0
52.5°	497.0	657.7	819.8	980.4	1224.4	1466.9	1710.8	1953.3	2018.5	2068.5	2001.8
55°	492.5	666.8	839.5	1012.3	1266.8	1522.9	1777.5	2032.1	2097.3	2133.6	2083.6
57.5°	497.0	684.9	871.3	1059.2	1321.4	1583.6	1845.7	2107.9	2186.7	2212.4	2201.8
60°	500.1	700.1	898.6	1098.6	1354.7	1610.8	1866.9	2123.0	2204.9	2268.5	2280.6
62.5°	492.5	689.5	885.0	1082.0	1313.8	1545.7	1777.5	2009.4	2144.2	2238.2	2292.7
65°	469.8	651.6	835.0	1016.8	1230.5	1445.7	1659.3	1873.0	2015.4	2154.8	2198.8
67.5°	419.8	574.3	728.9	883.5	1069.8	1256.2	1441.1	1627.5	1806.3	1941.2	2001.8
70°	363.7	484.9	607.7	728.9	898.6	1068.3	1238.1	1407.8	1565.4	1713.9	1771.5
72.5°	316.7	410.7	506.1	600.1	721.3	841.0	962.3	1082.0	1268.4	1416.9	1472.9
75°	269.7	337.9	404.6	472.8	556.1	639.5	721.3	804.7	936.5	1069.8	1125.9
77.5°	207.6	253.1	297.0	341.0	398.5	454.6	512.2	568.3	660.7	760.7	789.5
80°	144.0	169.7	194.0	219.7	265.2	310.6	356.1	401.6	462.2	518.3	562.2
82.5°	89.4	106.1	121.2	136.4	172.8	209.1	244.0	280.3	304.6	307.6	351.6
85°	57.6	68.2	77.3	86.4	107.6	130.3	151.5	172.8	154.6	144.0	171.2
87.5°	22.7	28.8	33.3	37.9	36.4	34.9	33.3	31.8	27.3	24.2	30.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1
2.5°	1168.3	1172.9	1177.4	1180.5	1185.0	1186.5	1188.0	1188.0	1189.6	1191.1	1194.1
5°	1224.4	1233.5	1242.6	1250.2	1259.3	1266.8	1272.9	1280.5	1286.5	1286.5	1285.0
7.5°	1177.4	1200.2	1222.9	1245.6	1268.4	1285.0	1300.2	1316.9	1332.0	1335.0	1338.1
10°	1115.3	1139.6	1162.3	1186.5	1209.3	1235.0	1259.3	1283.5	1309.3	1313.8	1319.9
12.5°	1057.7	1086.5	1115.3	1142.6	1171.4	1189.6	1207.7	1224.4	1242.6	1254.7	1266.8
15°	1056.2	1080.5	1104.7	1127.4	1151.7	1162.3	1172.9	1182.0	1192.6	1192.6	1194.1
17.5°	1091.1	1106.2	1121.4	1135.0	1150.2	1151.7	1154.7	1156.2	1157.7	1153.2	1148.6
20°	1159.3	1165.3	1171.4	1177.4	1183.5	1172.9	1163.8	1153.2	1142.6	1130.5	1119.9
22.5°	1259.3	1245.6	1232.0	1218.4	1204.7	1186.5	1166.8	1148.6	1128.9	1113.8	1098.6
25°	1353.2	1336.6	1319.9	1303.2	1286.5	1247.1	1207.7	1166.8	1127.4	1110.8	1094.1
27.5°	1479.0	1453.2	1427.5	1401.7	1376.0	1322.9	1269.9	1216.8	1163.8	1135.0	1107.7
30°	1509.3	1480.5	1451.7	1421.4	1392.6	1341.1	1291.1	1239.6	1188.0	1154.7	1122.9
32.5°	1553.2	1519.9	1486.6	1453.2	1419.9	1369.9	1319.9	1268.4	1218.4	1188.0	1156.2
35°	1626.0	1588.1	1550.2	1510.8	1472.9	1421.4	1371.4	1319.9	1268.4	1233.5	1200.2
37.5°	1688.1	1644.2	1600.2	1556.3	1512.3	1466.9	1419.9	1374.4	1327.5	1292.6	1259.3
40°	1757.8	1709.3	1660.8	1613.9	1565.4	1522.9	1480.5	1436.6	1394.1	1366.9	1339.6
42.5°	1818.4	1759.3	1701.8	1644.2	1585.1	1556.3	1529.0	1500.2	1471.4	1457.8	1442.6
45°	1860.9	1806.3	1750.2	1695.7	1641.1	1619.9	1598.7	1577.5	1556.3	1569.9	1583.6
47.5°	1879.1	1835.1	1792.7	1750.2	1706.3	1713.9	1721.5	1727.5	1735.1	1753.3	1773.0
50°	1895.7	1871.5	1845.7	1821.5	1795.7	1824.5	1851.8	1880.6	1909.4	1947.2	1985.1
52.5°	1929.1	1915.4	1903.3	1889.7	1876.0	1926.0	1976.0	2026.0	2076.0	2118.5	2160.9
55°	2029.1	2018.5	2007.9	1995.7	1985.1	2056.3	2126.1	2197.3	2268.5	2312.4	2356.4
57.5°	2167.0	2160.9	2153.3	2147.3	2139.7	2209.4	2277.6	2345.8	2415.5	2457.9	2501.9
60°	2271.5	2273.0	2273.0	2274.6	2274.6	2327.6	2380.6	2435.2	2488.2	2524.6	2562.5
62.5°	2327.6	2324.6	2321.5	2318.5	2315.5	2359.4	2403.4	2447.3	2491.3	2518.5	2545.8
65°	2267.0	2283.7	2300.3	2317.0	2333.7	2339.7	2344.3	2350.3	2354.9	2371.5	2388.2
67.5°	2063.9	2097.3	2129.1	2162.4	2194.2	2171.5	2150.3	2127.6	2104.8	2109.4	2112.4
70°	1838.1	1876.0	1915.4	1953.3	1991.2	1938.2	1885.1	1830.6	1777.5	1759.3	1741.2
72.5°	1550.2	1583.6	1618.4	1651.7	1685.1	1619.9	1556.3	1491.1	1426.0	1394.1	1362.3
75°	1185.0	1224.4	1265.3	1304.7	1344.1	1271.4	1197.1	1124.4	1050.1	1028.9	1009.2
77.5°	863.8	910.7	957.7	1004.7	1051.7	986.5	921.3	854.7	789.5	777.4	765.3
80°	628.9	665.2	700.1	736.5	771.3	733.4	695.6	657.7	619.8	618.3	616.8
82.5°	424.3	456.1	486.4	518.3	548.6	533.4	519.8	504.6	489.5	504.6	521.3
85°	218.2	262.2	307.6	351.6	395.5	391.0	387.9	383.4	378.8	398.5	416.7
87.5°	43.9	81.8	119.7	156.1	194.0	184.9	175.8	165.2	156.1	162.1	166.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1
2.5°	1195.6	1197.1	1197.1	1197.1	1197.1	1197.1	1194.1	1192.6	1189.6	1186.5	1182.0
5°	1285.0	1283.5	1277.5	1271.4	1263.8	1257.8	1253.2	1247.1	1242.6	1236.5	1227.4
7.5°	1341.1	1344.1	1333.5	1324.4	1313.8	1303.2	1292.6	1282.0	1271.4	1260.8	1239.6
10°	1324.4	1329.0	1322.9	1316.9	1309.3	1303.2	1291.1	1277.5	1265.3	1251.7	1225.9
12.5°	1277.5	1289.6	1286.5	1283.5	1280.5	1277.5	1269.9	1260.8	1253.2	1244.1	1215.3
15°	1194.1	1194.1	1195.6	1197.1	1197.1	1198.7	1200.2	1201.7	1203.2	1204.7	1188.0
17.5°	1144.1	1139.6	1139.6	1139.6	1139.6	1139.6	1145.6	1153.2	1159.3	1165.3	1160.8
20°	1107.7	1097.1	1095.6	1095.6	1094.1	1092.6	1103.2	1115.3	1125.9	1136.5	1142.6
22.5°	1083.5	1068.3	1066.8	1065.3	1063.8	1062.3	1075.9	1089.5	1103.2	1116.8	1138.0
25°	1077.4	1060.8	1062.3	1063.8	1063.8	1065.3	1075.9	1086.5	1097.1	1107.7	1144.1
27.5°	1078.9	1051.7	1053.2	1054.7	1054.7	1056.2	1072.9	1088.0	1104.7	1119.9	1165.3
30°	1089.5	1057.7	1054.7	1051.7	1048.6	1045.6	1068.3	1091.1	1113.8	1136.5	1171.4
32.5°	1125.9	1095.6	1088.0	1080.5	1072.9	1065.3	1092.6	1118.3	1145.6	1171.4	1200.2
35°	1165.3	1132.0	1128.9	1125.9	1121.4	1118.3	1142.6	1168.3	1192.6	1216.8	1242.6
37.5°	1224.4	1191.1	1188.0	1183.5	1180.5	1175.9	1203.2	1229.0	1256.2	1282.0	1304.7
40°	1312.3	1285.0	1283.5	1283.5	1282.0	1280.5	1301.7	1324.4	1345.6	1366.9	1382.0
42.5°	1429.0	1415.4	1419.9	1426.0	1430.5	1435.0	1451.7	1469.9	1486.6	1503.2	1498.7
45°	1597.2	1610.8	1612.3	1613.9	1615.4	1616.9	1621.4	1627.5	1632.0	1636.6	1618.4
47.5°	1791.2	1809.3	1818.4	1827.5	1835.1	1844.2	1838.1	1830.6	1824.5	1816.9	1771.5
50°	2021.5	2059.4	2057.9	2056.3	2053.3	2051.8	2039.7	2027.6	2013.9	2001.8	1935.1
52.5°	2203.3	2245.8	2253.3	2260.9	2268.5	2276.1	2253.3	2230.6	2206.4	2183.6	2100.3
55°	2398.8	2442.8	2444.3	2445.8	2445.8	2447.3	2415.5	2383.7	2350.3	2318.5	2232.1
57.5°	2544.3	2586.7	2582.2	2579.1	2574.6	2570.1	2532.2	2494.3	2456.4	2418.5	2332.1
60°	2598.8	2635.2	2626.1	2617.0	2606.4	2597.3	2568.5	2539.8	2509.4	2480.7	2397.3
62.5°	2573.1	2600.4	2586.7	2574.6	2561.0	2547.3	2511.0	2473.1	2436.7	2398.8	2338.2
65°	2403.4	2420.0	2401.9	2385.2	2368.5	2350.3	2320.0	2289.7	2257.9	2227.6	2186.7
67.5°	2117.0	2120.0	2118.5	2117.0	2115.4	2113.9	2070.0	2026.0	1980.6	1936.6	1933.6
70°	1724.5	1706.3	1709.3	1713.9	1716.9	1719.9	1686.6	1654.8	1621.4	1588.1	1603.3
72.5°	1330.5	1298.7	1306.2	1315.3	1322.9	1330.5	1303.2	1277.5	1250.2	1222.9	1244.1
75°	988.0	968.3	975.9	985.0	992.6	1000.1	989.5	978.9	966.8	956.2	975.9
77.5°	753.1	741.0	742.5	742.5	744.0	744.0	745.6	748.6	750.1	751.6	772.8
80°	613.7	612.2	610.7	609.2	606.1	604.6	619.8	634.9	650.1	665.2	675.9
82.5°	536.4	551.6	542.5	534.9	525.8	516.7	530.4	544.0	557.7	571.3	566.7
85°	436.4	454.6	437.9	421.3	403.1	386.4	398.5	409.1	421.3	431.9	425.8
87.5°	172.8	177.3	150.0	124.3	97.0	69.7	110.6	150.0	190.9	230.3	236.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1	1091.1
2.5°	1177.4	1171.4	1166.8	1165.3	1162.3	1160.8	1157.7	1154.7	1150.2	1147.1	1142.6
5°	1216.8	1207.7	1197.1	1182.0	1168.3	1153.2	1138.0	1124.4	1110.8	1095.6	1082.0
7.5°	1218.4	1197.1	1175.9	1156.2	1135.0	1115.3	1094.1	1075.9	1056.2	1036.5	1018.3
10°	1201.7	1175.9	1150.2	1124.4	1100.2	1074.4	1048.6	1027.4	1004.7	982.0	960.7
12.5°	1188.0	1159.3	1130.5	1100.2	1071.4	1041.1	1010.7	989.5	968.3	947.1	925.9
15°	1171.4	1153.2	1136.5	1109.2	1082.0	1054.7	1027.4	998.6	971.3	942.6	913.8
17.5°	1157.7	1153.2	1148.6	1130.5	1112.3	1092.6	1074.4	1045.6	1016.8	986.5	957.7
20°	1150.2	1156.2	1162.3	1153.2	1144.1	1133.5	1124.4	1103.2	1082.0	1059.2	1038.0
22.5°	1159.3	1182.0	1203.2	1204.7	1207.7	1209.3	1210.8	1191.1	1171.4	1150.2	1130.5
25°	1180.5	1216.8	1253.2	1272.9	1292.6	1313.8	1333.5	1321.4	1309.3	1297.2	1285.0
27.5°	1209.3	1254.7	1300.2	1329.0	1356.3	1385.0	1413.8	1412.3	1410.8	1407.8	1406.3
30°	1204.7	1239.6	1274.4	1309.3	1344.1	1379.0	1413.8	1432.0	1448.7	1466.9	1485.1
32.5°	1230.5	1259.3	1289.6	1325.9	1362.3	1400.2	1436.6	1474.4	1510.8	1548.7	1586.6
35°	1269.9	1295.6	1322.9	1362.3	1403.2	1442.6	1483.5	1529.0	1576.0	1623.0	1668.4
37.5°	1329.0	1351.7	1376.0	1409.3	1444.1	1477.5	1512.3	1579.0	1645.7	1713.9	1780.6
40°	1397.2	1412.3	1427.5	1459.3	1491.1	1522.9	1554.8	1638.1	1721.5	1804.8	1888.1
42.5°	1495.7	1491.1	1486.6	1512.3	1539.6	1565.4	1592.6	1668.4	1744.2	1820.0	1895.7
45°	1600.2	1582.0	1563.9	1576.0	1589.6	1601.7	1615.4	1692.7	1769.9	1848.7	1926.0
47.5°	1726.0	1680.5	1635.1	1624.5	1613.9	1601.7	1591.1	1674.5	1757.8	1842.7	1926.0
50°	1868.4	1800.3	1733.6	1706.3	1677.5	1650.2	1621.4	1689.6	1759.3	1829.0	1897.2
52.5°	2016.9	1932.1	1848.7	1806.3	1763.9	1719.9	1677.5	1735.1	1794.2	1853.3	1910.9
55°	2144.2	2057.9	1970.0	1920.0	1870.0	1820.0	1769.9	1827.5	1885.1	1942.7	2000.3
57.5°	2245.8	2159.4	2073.0	2026.0	1977.6	1930.6	1882.1	1936.6	1992.7	2048.8	2103.3
60°	2315.5	2232.1	2148.8	2103.3	2057.9	2012.4	1966.9	2032.1	2097.3	2163.9	2229.1
62.5°	2279.1	2218.5	2157.9	2138.2	2118.5	2097.3	2077.6	2139.7	2200.3	2262.4	2324.6
65°	2145.8	2104.8	2063.9	2083.6	2104.8	2124.5	2145.8	2186.7	2227.6	2270.0	2310.9
67.5°	1929.1	1926.0	1921.5	1965.4	2009.4	2054.8	2098.8	2126.1	2151.8	2179.1	2206.4
70°	1618.4	1635.1	1650.2	1726.0	1801.8	1877.5	1953.3	1963.9	1974.5	1985.1	1995.7
72.5°	1266.8	1288.1	1310.8	1410.8	1509.3	1609.3	1709.3	1703.3	1697.2	1689.6	1683.6
75°	997.1	1016.8	1038.0	1130.5	1222.9	1315.3	1407.8	1382.0	1357.8	1332.0	1306.2
77.5°	795.6	816.8	839.5	925.9	1012.3	1100.2	1186.5	1124.4	1062.3	1000.1	938.0
80°	684.9	695.6	704.6	763.7	821.3	880.4	939.5	875.9	810.7	745.6	681.9
82.5°	562.2	556.1	551.6	586.4	621.3	656.2	691.0	630.4	569.8	507.6	447.0
85°	419.8	413.7	407.6	425.8	444.0	463.7	481.9	412.2	342.5	271.3	201.5
87.5°	244.0	250.0	256.1	275.8	295.5	316.7	336.4	265.2	194.0	121.2	50.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671802
 CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1091.1	1091.1
2.5°	1133.5	1125.9
5°	1071.4	1060.8
7.5°	1003.2	989.5
10°	941.0	922.9
12.5°	901.6	878.9
15°	886.5	859.2
17.5°	931.9	906.2
20°	1001.7	966.8
22.5°	1086.5	1044.1
25°	1233.5	1182.0
27.5°	1353.2	1300.2
30°	1427.5	1369.9
32.5°	1509.3	1433.5
35°	1594.2	1521.4
37.5°	1697.2	1615.4
40°	1803.3	1718.4
42.5°	1839.7	1785.1
45°	1874.5	1823.0
47.5°	1882.1	1839.7
50°	1889.7	1883.6
52.5°	1910.9	1909.4
55°	2001.8	2003.3
57.5°	2113.9	2123.0
60°	2217.0	2206.4
62.5°	2270.0	2215.5
65°	2233.6	2157.9
67.5°	2124.5	2042.7
70°	1885.1	1774.5
72.5°	1586.6	1489.6
75°	1222.9	1141.1
77.5°	869.8	801.6
80°	612.2	544.0
82.5°	392.5	337.9
85°	177.3	154.6
87.5°	50.0	48.5
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P671802

CATALOG NUMBER: CCP-SA-1C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)