

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671811

Luminaire Tested: **CCP-SA-1A-735-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671811
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1A-735-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @350mA w/ SLR
distribution lens
Light Source: (16) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2239.3 lumens
Efficiency: N/A
Efficacy: 124.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1

Input Watts (W): 18
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 3.2 fc

Type IV - Short - N/A

REPORT NUMBER: P671811
CATALOG NUMBER: CCP-SA-1A-735-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	460.7	0.0	460.7
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	1778.5	0.0	1778.5
	% Fixture	79.4	0.0	79.4
Total	Lumens	2239.3	0.0	2239.3
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.6	2.5
10°-20°	117.3	5.2
20°-30°	171.6	7.7
30°-40°	241.8	10.8
40°-50°	332.3	14.8
50°-60°	452.9	20.2
60°-70°	495.7	22.1
70°-80°	286.3	12.8
80°-90°	85.8	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2239.3	100.0
0°-180°	2239.3	100.0



REPORT NUMBER: P671811


CATALOG NUMBER: CCP-SA-1A-735-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	230.0	10.3			
FM	(30°-60°)	817.2	36.5			
FH	(60°-80°)	658.5	29.4			G0/660
FVH	(80°-90°)	72.9	3.3			G1/100
BL	(0°-30°)	114.5	5.1	B1/500		
BM	(30°-60°)	209.8	9.4	B0/220		
BH	(60°-80°)	123.5	5.5	B1/500		G1/500
BVH	(80°-90°)	12.9	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1
2.5°	737.9	734.0	731.0	728.0	724.0	721.0	717.1	713.1	708.1	704.2	699.2
5°	695.2	683.3	671.4	664.4	656.5	649.5	641.6	632.7	623.7	613.8	604.8
7.5°	648.5	633.6	618.7	606.8	593.9	582.0	569.1	558.2	547.2	536.3	525.4
10°	604.8	590.9	577.0	562.1	546.2	531.3	515.5	500.6	485.7	470.8	455.9
12.5°	576.0	559.2	543.3	526.4	510.5	493.6	476.7	462.8	448.9	434.0	420.1
15°	563.1	547.2	532.3	515.5	498.6	481.7	464.8	448.9	434.0	418.1	402.2
17.5°	593.9	571.1	548.2	526.4	504.5	482.7	460.8	441.0	421.1	401.2	381.4
20°	633.6	604.8	577.0	550.2	522.4	495.6	467.8	440.0	412.2	384.4	356.5
22.5°	684.3	651.5	619.7	585.0	549.2	514.5	478.7	443.9	409.2	373.4	338.7
25°	774.7	735.9	697.2	647.5	596.9	547.2	496.6	450.9	406.2	360.5	314.8
27.5°	852.1	799.5	747.9	688.3	628.7	569.1	509.5	456.9	405.2	352.6	299.9
30°	897.8	846.2	794.5	722.0	650.5	578.0	505.5	446.9	389.3	330.7	272.1
32.5°	939.5	881.9	824.3	744.9	664.4	585.0	504.5	440.0	376.4	311.9	247.3
35°	997.1	933.6	871.0	778.6	686.3	593.9	501.6	435.0	367.5	300.9	233.4
37.5°	1058.7	980.3	902.8	800.5	698.2	595.9	493.6	428.1	362.5	297.0	231.4
40°	1126.3	1030.9	936.6	823.3	711.1	597.9	484.7	419.1	353.6	287.0	221.5
42.5°	1170.0	1066.7	963.4	841.2	720.1	597.9	475.7	411.2	346.6	281.1	216.5
45°	1194.8	1094.5	995.2	863.1	731.0	598.9	466.8	403.2	339.7	275.1	211.5
47.5°	1205.7	1112.4	1019.0	880.0	741.9	602.9	463.8	399.3	333.7	269.2	203.6
50°	1234.5	1152.1	1069.6	920.7	772.7	623.7	474.7	405.2	336.7	267.2	197.6
52.5°	1251.4	1180.9	1110.4	957.4	804.5	651.5	498.6	421.1	343.6	266.2	188.7
55°	1313.0	1245.4	1177.9	1015.0	851.2	688.3	524.4	439.0	353.6	267.2	181.8
57.5°	1391.4	1319.9	1249.4	1073.6	897.8	722.0	546.2	454.9	362.5	271.1	178.8
60°	1446.1	1376.5	1308.0	1121.3	933.6	746.9	559.2	463.8	368.5	272.1	176.8
62.5°	1452.0	1362.6	1274.2	1092.5	910.7	728.0	546.2	453.9	361.5	268.2	175.8
65°	1414.3	1310.0	1205.7	1031.9	858.1	684.3	510.5	426.1	341.7	256.2	171.8
67.5°	1338.8	1216.6	1094.5	935.6	776.7	617.8	458.8	386.3	314.8	242.3	169.8
70°	1163.0	1055.7	949.5	811.4	674.4	536.3	398.3	338.7	280.1	220.5	160.9
72.5°	976.3	876.0	776.7	664.4	553.2	441.0	328.7	284.0	239.4	193.7	149.0
75°	747.9	672.4	597.9	514.5	431.0	346.6	263.2	230.4	197.6	164.9	132.1
77.5°	525.4	484.7	444.9	382.4	319.8	257.2	194.7	172.8	151.0	129.1	107.3
80°	356.5	333.7	311.9	267.2	222.5	176.8	132.1	118.2	103.3	89.4	74.5
82.5°	221.5	220.5	218.5	187.7	156.9	126.1	95.3	83.4	72.5	60.6	48.7
85°	101.3	118.2	134.1	117.2	100.3	83.4	66.5	58.6	50.7	41.7	33.8
87.5°	31.8	38.7	44.7	42.7	39.7	37.7	34.8	29.8	24.8	19.9	14.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1
2.5°	695.2	692.2	688.3	684.3	679.3	675.4	670.4	665.4	664.4	662.4	661.5
5°	598.9	592.9	586.0	580.0	574.1	567.1	561.1	554.2	549.2	543.3	538.3
7.5°	514.5	504.5	493.6	482.7	472.8	462.8	451.9	442.0	437.0	432.0	427.1
10°	446.9	437.0	428.1	418.1	411.2	405.2	398.3	391.3	385.4	379.4	373.4
12.5°	413.2	406.2	399.3	392.3	384.4	377.4	369.5	361.5	354.6	348.6	341.7
15°	392.3	382.4	371.4	361.5	350.6	340.7	329.7	318.8	310.9	303.9	296.0
17.5°	367.5	352.6	338.7	323.8	311.9	299.9	287.0	275.1	266.2	256.2	247.3
20°	339.7	322.8	304.9	288.0	274.1	261.2	247.3	233.4	223.5	212.5	202.6
22.5°	315.8	294.0	271.1	248.3	233.4	218.5	202.6	187.7	178.8	168.8	159.9
25°	290.0	266.2	241.3	216.5	201.6	185.7	170.8	154.9	148.0	142.0	135.1
27.5°	276.1	252.3	227.4	203.6	189.7	174.8	160.9	146.0	141.0	135.1	130.1
30°	248.3	225.5	201.6	177.8	167.8	158.9	149.0	139.0	137.1	136.1	134.1
32.5°	223.5	199.6	175.8	152.0	143.0	134.1	125.1	116.2	115.2	113.2	112.2
35°	210.6	187.7	163.9	141.0	133.1	124.1	116.2	107.3	105.3	102.3	100.3
37.5°	207.6	183.7	158.9	135.1	127.1	119.2	110.2	102.3	100.3	98.3	96.3
40°	199.6	176.8	154.9	132.1	124.1	116.2	107.3	99.3	97.3	95.3	93.4
42.5°	193.7	171.8	149.0	126.1	119.2	112.2	104.3	97.3	95.3	93.4	90.4
45°	188.7	165.9	142.0	119.2	114.2	109.2	103.3	98.3	96.3	93.4	91.4
47.5°	180.8	158.9	136.1	113.2	108.3	104.3	99.3	94.4	92.4	90.4	88.4
50°	174.8	152.0	129.1	106.3	102.3	98.3	94.4	90.4	90.4	91.4	91.4
52.5°	166.9	145.0	123.2	101.3	97.3	93.4	89.4	85.4	86.4	87.4	88.4
55°	159.9	139.0	117.2	95.3	91.4	87.4	82.4	78.5	79.5	80.4	81.4
57.5°	156.9	135.1	113.2	91.4	87.4	82.4	78.5	73.5	73.5	73.5	73.5
60°	154.9	132.1	110.2	87.4	82.4	78.5	73.5	68.5	67.5	67.5	66.5
62.5°	153.9	131.1	109.2	86.4	80.4	75.5	69.5	63.6	62.6	61.6	60.6
65°	150.0	129.1	107.3	85.4	78.5	72.5	65.5	58.6	57.6	57.6	56.6
67.5°	149.0	127.1	106.3	84.4	77.5	69.5	62.6	54.6	53.6	52.6	51.6
70°	141.0	122.2	102.3	82.4	74.5	67.5	59.6	51.6	50.7	48.7	47.7
72.5°	131.1	114.2	96.3	78.5	70.5	62.6	54.6	46.7	45.7	44.7	42.7
75°	116.2	100.3	84.4	68.5	61.6	55.6	48.7	41.7	40.7	39.7	37.7
77.5°	95.3	82.4	70.5	57.6	52.6	47.7	42.7	37.7	36.7	35.8	33.8
80°	67.5	59.6	52.6	44.7	41.7	37.7	34.8	30.8	30.8	29.8	29.8
82.5°	44.7	40.7	36.7	32.8	30.8	28.8	26.8	24.8	24.8	23.8	23.8
85°	31.8	29.8	26.8	24.8	23.8	21.8	20.9	18.9	18.9	18.9	18.9
87.5°	14.9	14.9	13.9	13.9	12.9	12.9	11.9	10.9	10.9	10.9	10.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1
2.5°	659.5	656.5	653.5	649.5	646.6	642.6	637.6	633.6	628.7	628.7	627.7
5°	532.3	529.4	526.4	522.4	519.4	515.5	512.5	508.5	504.5	504.5	503.5
7.5°	422.1	416.1	410.2	403.2	397.3	393.3	389.3	384.4	380.4	377.4	374.4
10°	367.5	361.5	354.6	348.6	341.7	336.7	331.7	325.8	320.8	316.8	312.8
12.5°	334.7	327.7	320.8	313.8	306.9	299.9	294.0	287.0	280.1	275.1	270.1
15°	288.0	281.1	274.1	267.2	260.2	252.3	244.3	235.4	227.4	223.5	220.5
17.5°	237.4	230.4	222.5	215.5	207.6	201.6	195.7	189.7	183.7	179.8	176.8
20°	191.7	183.7	175.8	167.8	159.9	155.9	152.0	148.0	144.0	141.0	139.0
22.5°	150.0	145.0	141.0	136.1	131.1	128.1	126.1	123.2	120.2	120.2	120.2
25°	128.1	125.1	123.2	120.2	117.2	116.2	115.2	113.2	112.2	111.2	111.2
27.5°	124.1	121.2	118.2	115.2	112.2	111.2	110.2	108.3	107.3	107.3	107.3
30°	132.1	131.1	130.1	129.1	128.1	126.1	123.2	121.2	118.2	116.2	114.2
32.5°	110.2	109.2	109.2	108.3	107.3	109.2	110.2	112.2	113.2	114.2	115.2
35°	97.3	95.3	93.4	91.4	89.4	88.4	87.4	86.4	85.4	85.4	84.4
37.5°	94.4	92.4	90.4	88.4	86.4	85.4	84.4	83.4	82.4	82.4	81.4
40°	91.4	89.4	88.4	86.4	84.4	83.4	82.4	80.4	79.5	78.5	78.5
42.5°	88.4	87.4	85.4	84.4	82.4	81.4	80.4	78.5	77.5	76.5	75.5
45°	88.4	86.4	84.4	82.4	80.4	79.5	77.5	76.5	74.5	74.5	73.5
47.5°	86.4	84.4	82.4	80.4	78.5	77.5	75.5	74.5	72.5	71.5	70.5
50°	91.4	88.4	84.4	81.4	77.5	76.5	74.5	73.5	71.5	70.5	69.5
52.5°	89.4	86.4	82.4	79.5	75.5	73.5	72.5	70.5	68.5	67.5	66.5
55°	82.4	79.5	77.5	74.5	71.5	69.5	67.5	65.5	63.6	62.6	62.6
57.5°	73.5	72.5	71.5	70.5	69.5	67.5	65.5	62.6	60.6	59.6	58.6
60°	65.5	66.5	67.5	68.5	69.5	66.5	63.6	60.6	57.6	56.6	55.6
62.5°	59.6	61.6	63.6	64.6	66.5	63.6	60.6	57.6	54.6	53.6	52.6
65°	55.6	56.6	56.6	57.6	57.6	55.6	54.6	52.6	50.7	49.7	49.7
67.5°	50.7	50.7	50.7	49.7	49.7	48.7	48.7	47.7	46.7	45.7	45.7
70°	45.7	45.7	45.7	44.7	44.7	43.7	43.7	42.7	41.7	41.7	40.7
72.5°	41.7	41.7	40.7	40.7	39.7	39.7	39.7	38.7	38.7	37.7	37.7
75°	36.7	36.7	35.8	35.8	34.8	34.8	34.8	33.8	33.8	33.8	32.8
77.5°	32.8	32.8	31.8	31.8	30.8	30.8	30.8	29.8	29.8	28.8	28.8
80°	28.8	28.8	27.8	27.8	26.8	26.8	25.8	25.8	24.8	24.8	23.8
82.5°	22.8	22.8	22.8	22.8	22.8	21.8	21.8	20.9	19.9	19.9	18.9
85°	18.9	18.9	18.9	17.9	17.9	17.9	16.9	16.9	15.9	14.9	14.9
87.5°	10.9	10.9	10.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1
2.5°	627.7	626.7	622.7	618.7	622.7	626.7	626.7	626.7	625.7	625.7	625.7
5°	503.5	502.5	500.6	498.6	498.6	497.6	499.6	501.6	503.5	505.5	507.5
7.5°	370.5	367.5	364.5	361.5	363.5	364.5	367.5	369.5	372.4	374.4	379.4
10°	308.9	304.9	301.9	298.9	297.0	295.0	293.0	292.0	290.0	288.0	290.0
12.5°	264.2	259.2	254.3	248.3	247.3	246.3	244.3	242.3	240.3	238.4	237.4
15°	216.5	212.5	210.6	207.6	203.6	199.6	197.6	196.6	194.7	192.7	191.7
17.5°	172.8	168.8	165.9	162.9	161.9	159.9	159.9	159.9	159.9	159.9	159.9
20°	136.1	133.1	133.1	132.1	132.1	131.1	132.1	133.1	133.1	134.1	135.1
22.5°	119.2	119.2	118.2	117.2	118.2	118.2	119.2	120.2	121.2	122.2	123.2
25°	110.2	109.2	110.2	111.2	111.2	111.2	112.2	112.2	113.2	113.2	113.2
27.5°	106.3	106.3	107.3	107.3	108.3	108.3	108.3	107.3	107.3	106.3	106.3
30°	112.2	110.2	110.2	110.2	109.2	108.3	107.3	107.3	106.3	105.3	104.3
32.5°	116.2	117.2	116.2	114.2	113.2	111.2	110.2	108.3	107.3	105.3	103.3
35°	84.4	83.4	85.4	86.4	87.4	88.4	89.4	90.4	90.4	91.4	91.4
37.5°	81.4	80.4	80.4	79.5	79.5	79.5	79.5	79.5	78.5	78.5	79.5
40°	77.5	76.5	76.5	75.5	75.5	74.5	74.5	74.5	74.5	74.5	74.5
42.5°	74.5	73.5	73.5	73.5	73.5	72.5	72.5	71.5	71.5	70.5	70.5
45°	73.5	72.5	71.5	70.5	70.5	69.5	69.5	69.5	68.5	68.5	68.5
47.5°	69.5	68.5	68.5	67.5	67.5	66.5	66.5	66.5	65.5	65.5	65.5
50°	67.5	66.5	66.5	65.5	65.5	64.6	64.6	64.6	63.6	63.6	63.6
52.5°	64.6	63.6	63.6	63.6	62.6	61.6	61.6	61.6	60.6	60.6	60.6
55°	61.6	60.6	60.6	60.6	59.6	58.6	58.6	58.6	57.6	57.6	57.6
57.5°	57.6	56.6	56.6	55.6	55.6	55.6	55.6	55.6	54.6	54.6	54.6
60°	54.6	53.6	53.6	52.6	52.6	51.6	51.6	51.6	51.6	51.6	51.6
62.5°	51.6	50.7	49.7	48.7	49.7	49.7	49.7	49.7	48.7	48.7	48.7
65°	48.7	47.7	46.7	45.7	45.7	45.7	45.7	45.7	45.7	45.7	45.7
67.5°	44.7	43.7	42.7	41.7	42.7	42.7	42.7	42.7	42.7	42.7	42.7
70°	40.7	39.7	39.7	38.7	38.7	37.7	37.7	38.7	38.7	38.7	38.7
72.5°	36.7	35.8	35.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8
75°	32.8	31.8	31.8	30.8	30.8	30.8	30.8	30.8	30.8	30.8	30.8
77.5°	27.8	26.8	26.8	26.8	26.8	26.8	26.8	27.8	27.8	27.8	27.8
80°	23.8	22.8	22.8	22.8	22.8	22.8	22.8	22.8	22.8	22.8	22.8
82.5°	18.9	17.9	17.9	17.9	17.9	17.9	17.9	17.9	17.9	17.9	17.9
85°	13.9	12.9	12.9	12.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9
87.5°	8.9	7.9	7.9	7.9	8.9	8.9	8.9	8.9	7.9	7.9	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1
2.5°	625.7	625.7	625.7	624.7	623.7	622.7	621.7	624.7	626.7	629.7	631.7
5°	508.5	510.5	511.5	514.5	517.4	520.4	523.4	525.4	527.4	528.4	530.4
7.5°	383.4	388.3	392.3	396.3	400.2	403.2	407.2	410.2	413.2	416.1	419.1
10°	291.0	293.0	294.0	298.0	300.9	304.9	307.9	310.9	313.8	315.8	318.8
12.5°	236.4	234.4	233.4	233.4	233.4	233.4	233.4	235.4	237.4	239.4	241.3
15°	190.7	189.7	188.7	187.7	186.7	184.7	183.7	185.7	187.7	189.7	191.7
17.5°	159.9	159.9	159.9	158.9	157.9	156.9	155.9	156.9	157.9	157.9	158.9
20°	137.1	138.1	139.0	140.0	140.0	141.0	141.0	142.0	143.0	143.0	144.0
22.5°	123.2	124.1	124.1	124.1	125.1	125.1	125.1	126.1	127.1	128.1	129.1
25°	112.2	112.2	111.2	111.2	112.2	112.2	112.2	112.2	113.2	113.2	113.2
27.5°	106.3	105.3	105.3	105.3	105.3	104.3	104.3	104.3	104.3	104.3	104.3
30°	103.3	102.3	101.3	100.3	100.3	99.3	98.3	98.3	98.3	98.3	98.3
32.5°	102.3	100.3	98.3	97.3	97.3	96.3	95.3	94.4	94.4	93.4	92.4
35°	91.4	90.4	90.4	89.4	88.4	87.4	86.4	86.4	86.4	85.4	85.4
37.5°	79.5	80.4	80.4	80.4	81.4	81.4	81.4	81.4	82.4	82.4	82.4
40°	74.5	74.5	74.5	75.5	76.5	76.5	77.5	77.5	78.5	78.5	78.5
42.5°	70.5	69.5	69.5	70.5	70.5	71.5	71.5	72.5	73.5	73.5	74.5
45°	68.5	67.5	67.5	67.5	67.5	66.5	66.5	67.5	68.5	69.5	70.5
47.5°	64.6	64.6	63.6	63.6	63.6	63.6	63.6	63.6	64.6	64.6	64.6
50°	62.6	62.6	61.6	61.6	61.6	61.6	61.6	61.6	61.6	61.6	61.6
52.5°	60.6	59.6	59.6	59.6	59.6	58.6	58.6	58.6	58.6	58.6	58.6
55°	57.6	56.6	56.6	56.6	56.6	56.6	56.6	56.6	57.6	57.6	57.6
57.5°	54.6	53.6	53.6	53.6	54.6	54.6	54.6	54.6	55.6	55.6	55.6
60°	51.6	51.6	51.6	51.6	51.6	51.6	51.6	52.6	52.6	53.6	53.6
62.5°	48.7	48.7	48.7	48.7	49.7	49.7	49.7	49.7	50.7	50.7	50.7
65°	45.7	45.7	45.7	45.7	46.7	46.7	46.7	46.7	46.7	46.7	46.7
67.5°	42.7	42.7	42.7	42.7	42.7	42.7	42.7	43.7	43.7	44.7	44.7
70°	38.7	37.7	37.7	38.7	38.7	39.7	39.7	40.7	40.7	41.7	41.7
72.5°	34.8	34.8	34.8	34.8	34.8	34.8	34.8	35.8	36.7	36.7	37.7
75°	30.8	30.8	30.8	30.8	31.8	31.8	31.8	32.8	32.8	33.8	33.8
77.5°	27.8	26.8	26.8	26.8	27.8	27.8	27.8	28.8	28.8	29.8	29.8
80°	22.8	22.8	22.8	22.8	23.8	23.8	23.8	23.8	24.8	24.8	24.8
82.5°	18.9	18.9	18.9	18.9	18.9	18.9	18.9	18.9	19.9	19.9	19.9
85°	13.9	13.9	13.9	13.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9
87.5°	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	9.9	9.9	9.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1
2.5°	631.7	631.7	631.7	631.7	633.6	634.6	636.6	637.6	636.6	635.6	633.6
5°	531.3	532.3	532.3	533.3	533.3	533.3	533.3	533.3	535.3	537.3	539.3
7.5°	420.1	421.1	422.1	423.1	423.1	423.1	422.1	422.1	423.1	423.1	424.1
10°	321.8	325.8	328.7	331.7	329.7	326.8	324.8	321.8	321.8	321.8	320.8
12.5°	243.3	244.3	246.3	247.3	246.3	246.3	245.3	244.3	245.3	247.3	248.3
15°	192.7	192.7	193.7	193.7	194.7	195.7	195.7	196.6	198.6	199.6	201.6
17.5°	159.9	160.9	160.9	161.9	161.9	162.9	162.9	162.9	164.9	166.9	169.8
20°	144.0	144.0	144.0	144.0	144.0	143.0	143.0	142.0	143.0	145.0	146.0
22.5°	129.1	130.1	130.1	130.1	129.1	128.1	126.1	125.1	125.1	126.1	126.1
25°	113.2	112.2	112.2	111.2	111.2	112.2	112.2	112.2	113.2	113.2	114.2
27.5°	104.3	103.3	103.3	102.3	102.3	103.3	103.3	103.3	103.3	103.3	103.3
30°	97.3	97.3	96.3	95.3	96.3	96.3	97.3	97.3	98.3	98.3	99.3
32.5°	92.4	91.4	91.4	90.4	91.4	91.4	92.4	92.4	93.4	94.4	94.4
35°	85.4	85.4	85.4	85.4	85.4	85.4	84.4	84.4	84.4	84.4	84.4
37.5°	81.4	81.4	80.4	79.5	79.5	79.5	79.5	79.5	78.5	77.5	76.5
40°	78.5	77.5	77.5	76.5	75.5	75.5	74.5	73.5	73.5	72.5	72.5
42.5°	74.5	73.5	73.5	72.5	71.5	71.5	70.5	69.5	69.5	69.5	68.5
45°	69.5	69.5	68.5	67.5	67.5	67.5	66.5	66.5	66.5	66.5	65.5
47.5°	64.6	64.6	63.6	63.6	63.6	63.6	62.6	62.6	62.6	62.6	62.6
50°	61.6	61.6	61.6	61.6	61.6	61.6	60.6	60.6	60.6	60.6	60.6
52.5°	58.6	58.6	58.6	58.6	58.6	58.6	58.6	58.6	58.6	58.6	58.6
55°	57.6	57.6	57.6	57.6	57.6	57.6	56.6	56.6	56.6	57.6	57.6
57.5°	55.6	55.6	54.6	54.6	54.6	54.6	54.6	54.6	54.6	54.6	54.6
60°	53.6	53.6	53.6	53.6	53.6	53.6	53.6	53.6	53.6	53.6	53.6
62.5°	50.7	50.7	50.7	50.7	50.7	51.6	51.6	51.6	51.6	51.6	50.7
65°	46.7	47.7	47.7	47.7	47.7	47.7	47.7	47.7	47.7	47.7	47.7
67.5°	44.7	44.7	44.7	44.7	44.7	44.7	44.7	44.7	44.7	44.7	44.7
70°	41.7	41.7	40.7	40.7	40.7	41.7	41.7	41.7	41.7	41.7	41.7
72.5°	37.7	37.7	37.7	37.7	37.7	37.7	37.7	37.7	37.7	38.7	38.7
75°	33.8	33.8	33.8	33.8	33.8	33.8	33.8	33.8	33.8	33.8	33.8
77.5°	29.8	29.8	28.8	28.8	28.8	29.8	29.8	29.8	29.8	30.8	30.8
80°	24.8	24.8	24.8	24.8	24.8	24.8	24.8	24.8	24.8	25.8	25.8
82.5°	19.9	19.9	19.9	19.9	19.9	19.9	19.9	19.9	19.9	20.9	20.9
85°	14.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9	16.9	16.9
87.5°	9.9	9.9	9.9	9.9	9.9	9.9	8.9	8.9	8.9	8.9	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1
2.5°	632.7	633.6	634.6	634.6	635.6	636.6	636.6	640.6	644.6	646.6	648.5
5°	541.3	540.3	540.3	539.3	538.3	541.3	544.3	550.2	556.2	557.2	559.2
7.5°	424.1	425.1	426.1	426.1	427.1	424.1	420.1	421.1	422.1	427.1	431.0
10°	320.8	321.8	322.8	322.8	323.8	322.8	320.8	323.8	326.8	330.7	335.7
12.5°	249.3	252.3	255.2	257.2	260.2	262.2	263.2	267.2	270.1	275.1	280.1
15°	203.6	205.6	207.6	209.6	211.5	213.5	215.5	219.5	223.5	229.4	235.4
17.5°	171.8	171.8	172.8	172.8	172.8	174.8	176.8	178.8	179.8	185.7	191.7
20°	147.0	146.0	145.0	144.0	143.0	145.0	146.0	147.0	148.0	152.0	154.9
22.5°	126.1	126.1	127.1	127.1	127.1	126.1	124.1	125.1	125.1	127.1	130.1
25°	114.2	114.2	114.2	113.2	113.2	114.2	115.2	115.2	114.2	115.2	116.2
27.5°	103.3	104.3	104.3	105.3	105.3	106.3	106.3	106.3	106.3	107.3	108.3
30°	99.3	99.3	100.3	100.3	100.3	101.3	102.3	102.3	102.3	103.3	105.3
32.5°	95.3	96.3	97.3	98.3	99.3	100.3	100.3	101.3	101.3	102.3	103.3
35°	84.4	83.4	83.4	82.4	81.4	81.4	81.4	81.4	80.4	81.4	81.4
37.5°	75.5	75.5	75.5	74.5	74.5	75.5	75.5	75.5	75.5	76.5	76.5
40°	71.5	71.5	71.5	71.5	71.5	71.5	71.5	72.5	72.5	73.5	74.5
42.5°	68.5	68.5	68.5	68.5	68.5	69.5	69.5	69.5	69.5	70.5	70.5
45°	65.5	65.5	65.5	65.5	65.5	65.5	65.5	66.5	66.5	67.5	68.5
47.5°	62.6	62.6	62.6	62.6	62.6	63.6	64.6	64.6	64.6	65.5	65.5
50°	60.6	60.6	60.6	60.6	60.6	61.6	61.6	62.6	62.6	63.6	64.6
52.5°	58.6	58.6	58.6	58.6	58.6	59.6	59.6	60.6	60.6	61.6	62.6
55°	57.6	57.6	57.6	56.6	56.6	57.6	57.6	58.6	58.6	59.6	59.6
57.5°	54.6	54.6	54.6	54.6	54.6	54.6	54.6	55.6	55.6	56.6	57.6
60°	53.6	53.6	52.6	52.6	51.6	52.6	52.6	53.6	53.6	54.6	54.6
62.5°	50.7	50.7	50.7	49.7	49.7	50.7	50.7	50.7	50.7	51.6	52.6
65°	47.7	47.7	47.7	46.7	46.7	47.7	47.7	47.7	47.7	48.7	49.7
67.5°	44.7	44.7	44.7	43.7	43.7	43.7	43.7	44.7	44.7	45.7	46.7
70°	41.7	41.7	41.7	40.7	40.7	40.7	39.7	40.7	41.7	42.7	42.7
72.5°	38.7	38.7	38.7	37.7	37.7	37.7	36.7	37.7	37.7	38.7	38.7
75°	33.8	33.8	33.8	33.8	33.8	33.8	32.8	32.8	32.8	33.8	33.8
77.5°	30.8	30.8	30.8	29.8	29.8	29.8	28.8	28.8	28.8	29.8	29.8
80°	25.8	25.8	25.8	24.8	24.8	24.8	23.8	23.8	23.8	24.8	24.8
82.5°	20.9	20.9	20.9	19.9	19.9	19.9	18.9	18.9	18.9	19.9	19.9
85°	16.9	16.9	16.9	16.9	16.9	16.9	15.9	15.9	15.9	16.9	17.9
87.5°	7.9	7.9	8.9	8.9	8.9	8.9	7.9	7.9	7.0	7.0	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1
2.5°	650.5	652.5	657.5	661.5	666.4	670.4	673.4	677.3	680.3	683.3	685.3
5°	560.2	561.1	566.1	571.1	575.0	580.0	587.0	593.9	600.9	607.8	612.8
7.5°	436.0	440.0	445.9	452.9	458.8	464.8	471.8	479.7	486.7	493.6	500.6
10°	339.7	343.6	349.6	355.6	360.5	366.5	374.4	382.4	390.3	398.3	406.2
12.5°	285.0	290.0	297.0	303.9	309.9	316.8	326.8	335.7	345.6	354.6	364.5
15°	240.3	246.3	255.2	265.2	274.1	283.1	293.0	302.9	311.9	321.8	331.7
17.5°	197.6	203.6	211.5	220.5	228.4	236.4	248.3	259.2	271.1	282.1	293.0
20°	158.9	161.9	169.8	177.8	185.7	193.7	202.6	211.5	220.5	229.4	243.3
22.5°	132.1	134.1	138.1	141.0	145.0	148.0	156.9	165.9	173.8	182.7	195.7
25°	116.2	117.2	120.2	122.2	125.1	127.1	133.1	138.1	144.0	149.0	160.9
27.5°	108.3	109.2	110.2	111.2	112.2	113.2	117.2	121.2	124.1	128.1	139.0
30°	106.3	107.3	110.2	112.2	115.2	117.2	119.2	121.2	123.2	125.1	132.1
32.5°	104.3	105.3	105.3	104.3	104.3	103.3	105.3	106.3	108.3	109.2	115.2
35°	82.4	82.4	83.4	84.4	85.4	86.4	89.4	91.4	94.4	96.3	101.3
37.5°	77.5	77.5	78.5	80.4	81.4	82.4	84.4	86.4	88.4	90.4	95.3
40°	74.5	75.5	76.5	77.5	78.5	79.5	81.4	82.4	84.4	85.4	89.4
42.5°	71.5	71.5	72.5	74.5	75.5	76.5	78.5	79.5	81.4	82.4	86.4
45°	69.5	70.5	71.5	72.5	72.5	73.5	75.5	77.5	78.5	80.4	84.4
47.5°	66.5	66.5	68.5	69.5	71.5	72.5	74.5	75.5	77.5	78.5	82.4
50°	64.6	65.5	67.5	68.5	70.5	71.5	74.5	76.5	79.5	81.4	83.4
52.5°	62.6	63.6	65.5	66.5	68.5	69.5	73.5	77.5	80.4	84.4	84.4
55°	60.6	60.6	62.6	65.5	67.5	69.5	71.5	74.5	76.5	78.5	78.5
57.5°	57.6	58.6	60.6	63.6	65.5	67.5	69.5	71.5	72.5	74.5	73.5
60°	55.6	55.6	58.6	61.6	64.6	67.5	67.5	67.5	66.5	66.5	66.5
62.5°	52.6	53.6	57.6	62.6	66.5	70.5	67.5	64.6	61.6	58.6	59.6
65°	50.7	51.6	53.6	56.6	58.6	60.6	58.6	57.6	55.6	53.6	54.6
67.5°	46.7	47.7	48.7	48.7	49.7	49.7	49.7	49.7	49.7	49.7	50.7
70°	43.7	43.7	43.7	44.7	44.7	44.7	44.7	44.7	44.7	44.7	45.7
72.5°	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	40.7
75°	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	35.8
77.5°	30.8	30.8	30.8	30.8	30.8	30.8	30.8	30.8	29.8	29.8	30.8
80°	25.8	25.8	25.8	25.8	24.8	24.8	24.8	24.8	24.8	24.8	25.8
82.5°	20.9	20.9	20.9	20.9	19.9	19.9	19.9	19.9	18.9	18.9	19.9
85°	18.9	19.9	19.9	20.9	20.9	20.9	19.9	18.9	17.9	16.9	16.9
87.5°	7.9	7.9	7.9	7.9	7.0	7.0	7.0	7.0	7.0	7.0	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1
2.5°	688.3	690.3	692.2	695.2	699.2	702.2	705.2	711.1	718.1	724.0	730.0
5°	617.8	622.7	627.7	633.6	639.6	644.6	650.5	662.4	674.4	685.3	697.2
7.5°	506.5	513.5	519.4	529.4	538.3	548.2	557.2	572.1	586.0	600.9	614.8
10°	414.2	422.1	430.0	443.0	456.9	469.8	482.7	494.6	507.5	519.4	531.3
12.5°	374.4	383.4	393.3	401.2	410.2	418.1	426.1	440.0	453.9	467.8	481.7
15°	341.7	351.6	361.5	371.4	380.4	390.3	399.3	411.2	424.1	436.0	447.9
17.5°	303.9	313.8	324.8	335.7	346.6	357.5	368.5	385.4	402.2	418.1	435.0
20°	256.2	270.1	283.1	298.0	312.8	327.7	342.6	360.5	378.4	395.3	413.2
22.5°	208.6	221.5	234.4	252.3	270.1	287.0	304.9	328.7	351.6	375.4	398.3
25°	173.8	185.7	197.6	217.5	236.4	256.2	275.1	303.9	331.7	360.5	388.3
27.5°	150.0	160.9	171.8	192.7	213.5	233.4	254.3	286.0	316.8	348.6	379.4
30°	139.0	146.0	152.9	172.8	192.7	211.5	231.4	262.2	293.0	323.8	354.6
32.5°	121.2	127.1	133.1	151.0	168.8	185.7	203.6	235.4	266.2	298.0	328.7
35°	107.3	112.2	117.2	134.1	150.0	166.9	182.7	214.5	246.3	278.1	309.9
37.5°	99.3	104.3	108.3	123.2	139.0	153.9	168.8	200.6	231.4	263.2	294.0
40°	93.4	96.3	100.3	115.2	129.1	144.0	157.9	186.7	216.5	245.3	274.1
42.5°	89.4	93.4	96.3	109.2	123.2	136.1	149.0	176.8	204.6	231.4	259.2
45°	88.4	92.4	96.3	107.3	118.2	128.1	139.0	165.9	192.7	219.5	246.3
47.5°	86.4	89.4	93.4	102.3	110.2	119.2	127.1	153.9	180.8	206.6	233.4
50°	85.4	86.4	88.4	96.3	104.3	112.2	120.2	147.0	173.8	200.6	227.4
52.5°	84.4	84.4	84.4	91.4	98.3	104.3	111.2	138.1	165.9	192.7	219.5
55°	78.5	77.5	77.5	84.4	90.4	97.3	103.3	130.1	156.9	182.7	209.6
57.5°	72.5	71.5	70.5	76.5	82.4	88.4	94.4	121.2	149.0	175.8	202.6
60°	66.5	65.5	65.5	71.5	76.5	82.4	87.4	115.2	142.0	169.8	196.6
62.5°	59.6	60.6	60.6	65.5	71.5	76.5	81.4	109.2	138.1	165.9	193.7
65°	54.6	55.6	55.6	61.6	67.5	73.5	79.5	106.3	134.1	160.9	187.7
67.5°	50.7	51.6	51.6	58.6	64.6	71.5	77.5	101.3	126.1	150.0	173.8
70°	46.7	46.7	47.7	54.6	61.6	68.5	75.5	96.3	117.2	137.1	157.9
72.5°	41.7	42.7	43.7	50.7	56.6	63.6	69.5	88.4	107.3	126.1	145.0
75°	36.7	37.7	38.7	44.7	50.7	56.6	62.6	80.4	97.3	115.2	132.1
77.5°	32.8	33.8	34.8	39.7	44.7	49.7	54.6	67.5	81.4	94.4	107.3
80°	26.8	26.8	27.8	31.8	35.8	38.7	42.7	51.6	60.6	68.5	77.5
82.5°	19.9	20.9	20.9	23.8	25.8	28.8	30.8	35.8	39.7	44.7	48.7
85°	16.9	15.9	15.9	17.9	18.9	20.9	21.8	24.8	26.8	29.8	31.8
87.5°	7.0	6.0	6.0	7.0	8.9	9.9	10.9	10.9	11.9	11.9	11.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1
2.5°	733.0	734.9	737.9	739.9	744.9	748.9	753.8	757.8	760.8	765.7	763.8
5°	706.1	715.1	724.0	733.0	739.9	746.9	752.8	759.8	767.7	782.6	786.6
7.5°	626.7	638.6	649.5	661.5	675.4	689.3	703.2	717.1	730.0	748.9	760.8
10°	548.2	565.1	581.0	597.9	610.8	623.7	635.6	648.5	666.4	685.3	707.1
12.5°	498.6	515.5	532.3	549.2	568.1	586.0	604.8	622.7	639.6	654.5	679.3
15°	465.8	484.7	502.5	520.4	543.3	565.1	588.0	609.8	634.6	654.5	671.4
17.5°	457.9	480.7	502.5	525.4	549.2	573.1	596.9	620.7	645.6	675.4	697.2
20°	443.9	474.7	505.5	536.3	567.1	596.9	627.7	657.5	690.3	726.0	735.9
22.5°	436.0	472.8	510.5	547.2	589.0	631.7	673.4	715.1	749.8	776.7	806.5
25°	435.0	480.7	527.4	573.1	625.7	677.3	730.0	781.6	826.3	853.1	877.0
27.5°	434.0	489.6	544.3	598.9	663.4	727.0	791.6	855.1	896.8	935.6	955.4
30°	422.1	488.6	556.2	622.7	695.2	767.7	840.2	912.7	955.4	982.2	992.2
32.5°	407.2	485.7	564.1	642.6	725.0	807.5	888.9	971.3	1005.1	1027.9	1020.0
35°	395.3	481.7	567.1	652.5	739.9	828.3	915.7	1003.1	1051.8	1083.6	1070.6
37.5°	384.4	474.7	565.1	655.5	757.8	860.1	962.4	1064.7	1111.4	1145.1	1130.2
40°	371.4	467.8	565.1	661.5	778.6	894.8	1012.0	1128.2	1188.8	1217.6	1194.8
42.5°	360.5	460.8	562.1	662.4	787.6	912.7	1037.9	1163.0	1230.5	1271.3	1242.5
45°	346.6	446.9	546.2	646.6	784.6	922.7	1059.7	1197.8	1276.2	1308.0	1268.3
47.5°	331.7	431.0	529.4	627.7	774.7	921.7	1068.7	1215.6	1288.1	1325.9	1289.1
50°	326.8	426.1	524.4	623.7	782.6	942.5	1101.4	1260.3	1313.0	1343.8	1295.1
52.5°	325.8	431.0	537.3	642.6	802.5	961.4	1121.3	1280.2	1322.9	1355.7	1312.0
55°	322.8	437.0	550.2	663.4	830.3	998.1	1165.0	1331.8	1374.6	1398.4	1365.6
57.5°	325.8	448.9	571.1	694.2	866.0	1037.9	1209.7	1381.5	1433.2	1450.0	1443.1
60°	327.7	458.8	589.0	720.1	887.9	1055.7	1223.6	1391.4	1445.1	1486.8	1494.7
62.5°	322.8	451.9	580.0	709.1	861.1	1013.0	1165.0	1316.9	1405.3	1466.9	1502.7
65°	307.9	427.1	547.2	666.4	806.5	947.5	1087.5	1227.6	1320.9	1412.3	1441.1
67.5°	275.1	376.4	477.7	579.0	701.2	823.3	944.5	1066.7	1183.9	1272.3	1312.0
70°	238.4	317.8	398.3	477.7	589.0	700.2	811.4	922.7	1025.9	1123.3	1161.0
72.5°	207.6	269.2	331.7	393.3	472.8	551.2	630.7	709.1	831.3	928.6	965.4
75°	176.8	221.5	265.2	309.9	364.5	419.1	472.8	527.4	613.8	701.2	737.9
77.5°	136.1	165.9	194.7	223.5	261.2	298.0	335.7	372.4	433.0	498.6	517.4
80°	94.4	111.2	127.1	144.0	173.8	203.6	233.4	263.2	302.9	339.7	368.5
82.5°	58.6	69.5	79.5	89.4	113.2	137.1	159.9	183.7	199.6	201.6	230.4
85°	37.7	44.7	50.7	56.6	70.5	85.4	99.3	113.2	101.3	94.4	112.2
87.5°	14.9	18.9	21.8	24.8	23.8	22.8	21.8	20.9	17.9	15.9	19.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1
2.5°	765.7	768.7	771.7	773.7	776.7	777.7	778.6	778.6	779.6	780.6	782.6
5°	802.5	808.4	814.4	819.4	825.3	830.3	834.3	839.2	843.2	843.2	842.2
7.5°	771.7	786.6	801.5	816.4	831.3	842.2	852.1	863.1	873.0	875.0	877.0
10°	731.0	746.9	761.8	777.7	792.6	809.4	825.3	841.2	858.1	861.1	865.1
12.5°	693.2	712.1	731.0	748.9	767.7	779.6	791.6	802.5	814.4	822.3	830.3
15°	692.2	708.1	724.0	738.9	754.8	761.8	768.7	774.7	781.6	781.6	782.6
17.5°	715.1	725.0	734.9	743.9	753.8	754.8	756.8	757.8	758.8	755.8	752.8
20°	759.8	763.8	767.7	771.7	775.7	768.7	762.8	755.8	748.9	740.9	734.0
22.5°	825.3	816.4	807.5	798.5	789.6	777.7	764.7	752.8	739.9	730.0	720.1
25°	886.9	876.0	865.1	854.1	843.2	817.4	791.6	764.7	738.9	728.0	717.1
27.5°	969.3	952.5	935.6	918.7	901.8	867.0	832.3	797.5	762.8	743.9	726.0
30°	989.2	970.3	951.5	931.6	912.7	879.0	846.2	812.4	778.6	756.8	735.9
32.5°	1018.0	996.2	974.3	952.5	930.6	897.8	865.1	831.3	798.5	778.6	757.8
35°	1065.7	1040.8	1016.0	990.2	965.4	931.6	898.8	865.1	831.3	808.4	786.6
37.5°	1106.4	1077.6	1048.8	1020.0	991.2	961.4	930.6	900.8	870.0	847.2	825.3
40°	1152.1	1120.3	1088.5	1057.7	1025.9	998.1	970.3	941.5	913.7	895.8	878.0
42.5°	1191.8	1153.1	1115.3	1077.6	1038.9	1020.0	1002.1	983.2	964.4	955.4	945.5
45°	1219.6	1183.9	1147.1	1111.4	1075.6	1061.7	1047.8	1033.9	1020.0	1028.9	1037.9
47.5°	1231.5	1202.7	1174.9	1147.1	1118.3	1123.3	1128.2	1132.2	1137.2	1149.1	1162.0
50°	1242.5	1226.6	1209.7	1193.8	1176.9	1195.8	1213.7	1232.5	1251.4	1276.2	1301.1
52.5°	1264.3	1255.4	1247.4	1238.5	1229.5	1262.3	1295.1	1327.9	1360.6	1388.5	1416.3
55°	1329.9	1322.9	1316.0	1308.0	1301.1	1347.7	1393.4	1440.1	1486.8	1515.6	1544.4
57.5°	1420.2	1416.3	1411.3	1407.3	1402.4	1448.0	1492.7	1537.4	1583.1	1610.9	1639.7
60°	1488.8	1489.8	1489.8	1490.8	1490.8	1525.5	1560.3	1596.0	1630.8	1654.6	1679.5
62.5°	1525.5	1523.5	1521.5	1519.6	1517.6	1546.4	1575.2	1604.0	1632.8	1650.7	1668.5
65°	1485.8	1496.7	1507.6	1518.6	1529.5	1533.5	1536.4	1540.4	1543.4	1554.3	1565.2
67.5°	1352.7	1374.6	1395.4	1417.3	1438.1	1423.2	1409.3	1394.4	1379.5	1382.5	1384.5
70°	1204.7	1229.5	1255.4	1280.2	1305.0	1270.3	1235.5	1199.8	1165.0	1153.1	1141.2
72.5°	1016.0	1037.9	1060.7	1082.6	1104.4	1061.7	1020.0	977.3	934.6	913.7	892.9
75°	776.7	802.5	829.3	855.1	880.9	833.3	784.6	736.9	688.3	674.4	661.5
77.5°	566.1	596.9	627.7	658.5	689.3	646.6	603.8	560.2	517.4	509.5	501.6
80°	412.2	436.0	458.8	482.7	505.5	480.7	455.9	431.0	406.2	405.2	404.2
82.5°	278.1	298.9	318.8	339.7	359.5	349.6	340.7	330.7	320.8	330.7	341.7
85°	143.0	171.8	201.6	230.4	259.2	256.2	254.3	251.3	248.3	261.2	273.1
87.5°	28.8	53.6	78.5	102.3	127.1	121.2	115.2	108.3	102.3	106.3	109.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1
2.5°	783.6	784.6	784.6	784.6	784.6	784.6	782.6	781.6	779.6	777.7	774.7
5°	842.2	841.2	837.2	833.3	828.3	824.3	821.4	817.4	814.4	810.4	804.5
7.5°	879.0	880.9	874.0	868.0	861.1	854.1	847.2	840.2	833.3	826.3	812.4
10°	868.0	871.0	867.0	863.1	858.1	854.1	846.2	837.2	829.3	820.4	803.5
12.5°	837.2	845.2	843.2	841.2	839.2	837.2	832.3	826.3	821.4	815.4	796.5
15°	782.6	782.6	783.6	784.6	784.6	785.6	786.6	787.6	788.6	789.6	778.6
17.5°	749.8	746.9	746.9	746.9	746.9	746.9	750.8	755.8	759.8	763.8	760.8
20°	726.0	719.1	718.1	718.1	717.1	716.1	723.0	731.0	737.9	744.9	748.9
22.5°	710.1	700.2	699.2	698.2	697.2	696.2	705.2	714.1	723.0	732.0	745.9
25°	706.1	695.2	696.2	697.2	697.2	698.2	705.2	712.1	719.1	726.0	749.8
27.5°	707.1	689.3	690.3	691.2	691.2	692.2	703.2	713.1	724.0	734.0	763.8
30°	714.1	693.2	691.2	689.3	687.3	685.3	700.2	715.1	730.0	744.9	767.7
32.5°	737.9	718.1	713.1	708.1	703.2	698.2	716.1	733.0	750.8	767.7	786.6
35°	763.8	741.9	739.9	737.9	734.9	733.0	748.9	765.7	781.6	797.5	814.4
37.5°	802.5	780.6	778.6	775.7	773.7	770.7	788.6	805.5	823.3	840.2	855.1
40°	860.1	842.2	841.2	841.2	840.2	839.2	853.1	868.0	881.9	895.8	905.8
42.5°	936.6	927.6	930.6	934.6	937.6	940.5	951.5	963.4	974.3	985.2	982.2
45°	1046.8	1055.7	1056.7	1057.7	1058.7	1059.7	1062.7	1066.7	1069.6	1072.6	1060.7
47.5°	1173.9	1185.8	1191.8	1197.8	1202.7	1208.7	1204.7	1199.8	1195.8	1190.8	1161.0
50°	1324.9	1349.7	1348.7	1347.7	1345.8	1344.8	1336.8	1328.9	1319.9	1312.0	1268.3
52.5°	1444.1	1471.9	1476.8	1481.8	1486.8	1491.7	1476.8	1462.0	1446.1	1431.2	1376.5
55°	1572.2	1601.0	1602.0	1603.0	1603.0	1604.0	1583.1	1562.3	1540.4	1519.6	1462.9
57.5°	1667.5	1695.3	1692.4	1690.4	1687.4	1684.4	1659.6	1634.8	1609.9	1585.1	1528.5
60°	1703.3	1727.1	1721.2	1715.2	1708.3	1702.3	1683.4	1664.6	1644.7	1625.8	1571.2
62.5°	1686.4	1704.3	1695.3	1687.4	1678.5	1669.5	1645.7	1620.9	1597.0	1572.2	1532.5
65°	1575.2	1586.1	1574.2	1563.3	1552.3	1540.4	1520.5	1500.7	1479.8	1460.0	1433.2
67.5°	1387.5	1389.5	1388.5	1387.5	1386.5	1385.5	1356.7	1327.9	1298.1	1269.3	1267.3
70°	1130.2	1118.3	1120.3	1123.3	1125.3	1127.3	1105.4	1084.5	1062.7	1040.8	1050.8
72.5°	872.0	851.2	856.1	862.1	867.0	872.0	854.1	837.2	819.4	801.5	815.4
75°	647.5	634.6	639.6	645.6	650.5	655.5	648.5	641.6	633.6	626.7	639.6
77.5°	493.6	485.7	486.7	486.7	487.6	487.6	488.6	490.6	491.6	492.6	506.5
80°	402.2	401.2	400.2	399.3	397.3	396.3	406.2	416.1	426.1	436.0	443.0
82.5°	351.6	361.5	355.6	350.6	344.6	338.7	347.6	356.5	365.5	374.4	371.4
85°	286.0	298.0	287.0	276.1	264.2	253.3	261.2	268.2	276.1	283.1	279.1
87.5°	113.2	116.2	98.3	81.4	63.6	45.7	72.5	98.3	125.1	151.0	154.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1	715.1
2.5°	771.7	767.7	764.7	763.8	761.8	760.8	758.8	756.8	753.8	751.8	748.9
5°	797.5	791.6	784.6	774.7	765.7	755.8	745.9	736.9	728.0	718.1	709.1
7.5°	798.5	784.6	770.7	757.8	743.9	731.0	717.1	705.2	692.2	679.3	667.4
10°	787.6	770.7	753.8	736.9	721.0	704.2	687.3	673.4	658.5	643.6	629.7
12.5°	778.6	759.8	740.9	721.0	702.2	682.3	662.4	648.5	634.6	620.7	606.8
15°	767.7	755.8	744.9	727.0	709.1	691.2	673.4	654.5	636.6	617.8	598.9
17.5°	758.8	755.8	752.8	740.9	729.0	716.1	704.2	685.3	666.4	646.6	627.7
20°	753.8	757.8	761.8	755.8	749.8	742.9	736.9	723.0	709.1	694.2	680.3
22.5°	759.8	774.7	788.6	789.6	791.6	792.6	793.5	780.6	767.7	753.8	740.9
25°	773.7	797.5	821.4	834.3	847.2	861.1	874.0	866.0	858.1	850.2	842.2
27.5°	792.6	822.3	852.1	871.0	888.9	907.8	926.6	925.6	924.6	922.7	921.7
30°	789.6	812.4	835.3	858.1	880.9	903.8	926.6	938.5	949.5	961.4	973.3
32.5°	806.5	825.3	845.2	869.0	892.9	917.7	941.5	966.4	990.2	1015.0	1039.9
35°	832.3	849.2	867.0	892.9	919.7	945.5	972.3	1002.1	1032.9	1063.7	1093.5
37.5°	871.0	885.9	901.8	923.7	946.5	968.3	991.2	1034.9	1078.6	1123.3	1167.0
40°	915.7	925.6	935.6	956.4	977.3	998.1	1019.0	1073.6	1128.2	1182.9	1237.5
42.5°	980.3	977.3	974.3	991.2	1009.1	1025.9	1043.8	1093.5	1143.1	1192.8	1242.5
45°	1048.8	1036.9	1025.0	1032.9	1041.8	1049.8	1058.7	1109.4	1160.0	1211.7	1262.3
47.5°	1131.2	1101.4	1071.6	1064.7	1057.7	1049.8	1042.8	1097.5	1152.1	1207.7	1262.3
50°	1224.6	1179.9	1136.2	1118.3	1099.4	1081.6	1062.7	1107.4	1153.1	1198.8	1243.5
52.5°	1321.9	1266.3	1211.7	1183.9	1156.1	1127.3	1099.4	1137.2	1175.9	1214.7	1252.4
55°	1405.3	1348.7	1291.1	1258.4	1225.6	1192.8	1160.0	1197.8	1235.5	1273.2	1311.0
57.5°	1471.9	1415.3	1358.7	1327.9	1296.1	1265.3	1233.5	1269.3	1306.0	1342.8	1378.5
60°	1517.6	1462.9	1408.3	1378.5	1348.7	1318.9	1289.1	1331.8	1374.6	1418.3	1461.0
62.5°	1493.7	1454.0	1414.3	1401.4	1388.5	1374.6	1361.6	1402.4	1442.1	1482.8	1523.5
65°	1406.3	1379.5	1352.7	1365.6	1379.5	1392.4	1406.3	1433.2	1460.0	1487.8	1514.6
67.5°	1264.3	1262.3	1259.3	1288.1	1316.9	1346.7	1375.5	1393.4	1410.3	1428.2	1446.1
70°	1060.7	1071.6	1081.6	1131.2	1180.9	1230.5	1280.2	1287.2	1294.1	1301.1	1308.0
72.5°	830.3	844.2	859.1	924.6	989.2	1054.8	1120.3	1116.3	1112.4	1107.4	1103.4
75°	653.5	666.4	680.3	740.9	801.5	862.1	922.7	905.8	889.9	873.0	856.1
77.5°	521.4	535.3	550.2	606.8	663.4	721.0	777.7	736.9	696.2	655.5	614.8
80°	448.9	455.9	461.8	500.6	538.3	577.0	615.8	574.1	531.3	488.6	446.9
82.5°	368.5	364.5	361.5	384.4	407.2	430.0	452.9	413.2	373.4	332.7	293.0
85°	275.1	271.1	267.2	279.1	291.0	303.9	315.8	270.1	224.5	177.8	132.1
87.5°	159.9	163.9	167.8	180.8	193.7	207.6	220.5	173.8	127.1	79.5	32.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811

CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671811
 CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	715.1	715.1
2.5°	742.9	737.9
5°	702.2	695.2
7.5°	657.5	648.5
10°	616.8	604.8
12.5°	590.9	576.0
15°	581.0	563.1
17.5°	610.8	593.9
20°	656.5	633.6
22.5°	712.1	684.3
25°	808.4	774.7
27.5°	886.9	852.1
30°	935.6	897.8
32.5°	989.2	939.5
35°	1044.8	997.1
37.5°	1112.4	1058.7
40°	1181.9	1126.3
42.5°	1205.7	1170.0
45°	1228.6	1194.8
47.5°	1233.5	1205.7
50°	1238.5	1234.5
52.5°	1252.4	1251.4
55°	1312.0	1313.0
57.5°	1385.5	1391.4
60°	1453.0	1446.1
62.5°	1487.8	1452.0
65°	1463.9	1414.3
67.5°	1392.4	1338.8
70°	1235.5	1163.0
72.5°	1039.9	976.3
75°	801.5	747.9
77.5°	570.1	525.4
80°	401.2	356.5
82.5°	257.2	221.5
85°	116.2	101.3
87.5°	32.8	31.8
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671811
CATALOG NUMBER: CCP-SA-1A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)