

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671814

Luminaire Tested: **CCP-SA-1D-735-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671814
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1D-735-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @800mA w/ SLR
distribution lens
Light Source: (16) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4564.7 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 44
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 6.5 fc

Type IV - Short - N/A

REPORT NUMBER: P671814
CATALOG NUMBER: CCP-SA-1D-735-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	939.2	0.0	939.2
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3625.5	0.0	3625.5
	% Fixture	79.4	0.0	79.4
Total	Lumens	4564.7	0.0	4564.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.3	2.5
10°-20°	239.1	5.2
20°-30°	349.9	7.7
30°-40°	492.9	10.8
40°-50°	677.3	14.8
50°-60°	923.2	20.2
60°-70°	1010.5	22.1
70°-80°	583.5	12.8
80°-90°	174.9	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4564.7	100.0
0°-180°	4564.7	100.0

Coefficient of Utilization



REPORT NUMBER: P671814


CATALOG NUMBER: CCP-SA-1D-735-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	468.8	10.3			
FM	(30°-60°)	1665.8	36.5			
FH	(60°-80°)	1342.3	29.4			G1/1800
FVH	(80°-90°)	148.6	3.3			G2/225
BL	(0°-30°)	233.5	5.1	B1/500		
BM	(30°-60°)	427.7	9.4	B1/1000		
BH	(60°-80°)	251.7	5.5	B1/500		G1/500
BVH	(80°-90°)	26.3	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7
2.5°	1504.2	1496.2	1490.1	1484.0	1475.9	1469.8	1461.7	1453.6	1443.5	1435.4	1425.3
5°	1417.2	1392.9	1368.6	1354.4	1338.2	1324.1	1307.9	1289.6	1271.4	1251.2	1233.0
7.5°	1322.0	1291.7	1261.3	1237.0	1210.7	1186.4	1160.1	1137.8	1115.5	1093.3	1071.0
10°	1233.0	1204.6	1176.3	1145.9	1113.5	1083.1	1050.7	1020.4	990.0	959.6	929.3
12.5°	1174.2	1139.8	1107.4	1073.0	1040.6	1006.2	971.8	943.4	915.1	884.7	856.4
15°	1147.9	1115.5	1085.2	1050.7	1016.3	981.9	947.5	915.1	884.7	852.3	819.9
17.5°	1210.7	1164.1	1117.6	1073.0	1028.5	983.9	939.4	898.9	858.4	817.9	777.4
20°	1291.7	1233.0	1176.3	1121.6	1064.9	1010.3	953.6	896.9	840.2	783.5	726.8
22.5°	1394.9	1328.1	1263.3	1192.5	1119.6	1048.7	975.8	905.0	834.1	761.2	690.4
25°	1579.2	1500.2	1421.2	1320.0	1216.8	1115.5	1012.3	919.2	828.0	734.9	641.8
27.5°	1737.1	1629.8	1524.5	1403.0	1281.5	1160.1	1038.6	931.3	826.0	718.7	611.4
30°	1830.2	1724.9	1619.6	1471.9	1326.1	1178.3	1030.5	911.1	793.6	674.2	554.7
32.5°	1915.2	1797.8	1680.4	1518.4	1354.4	1192.5	1028.5	896.9	767.3	635.7	504.1
35°	2032.7	1903.1	1775.5	1587.3	1399.0	1210.7	1022.4	886.8	749.1	613.4	475.8
37.5°	2158.2	1998.2	1840.3	1631.8	1423.3	1214.7	1006.2	872.6	739.0	605.3	471.7
40°	2295.9	2101.5	1909.2	1678.4	1449.6	1218.8	988.0	854.4	720.7	585.1	451.5
42.5°	2384.9	2174.4	1963.8	1714.8	1467.8	1218.8	969.8	838.2	706.6	573.0	441.4
45°	2435.5	2231.1	2028.6	1759.3	1490.1	1220.8	951.5	822.0	692.4	560.8	431.2
47.5°	2457.8	2267.5	2077.2	1793.8	1512.3	1228.9	945.5	813.9	680.3	548.7	415.0
50°	2516.5	2348.5	2180.5	1876.8	1575.1	1271.4	967.7	826.0	686.3	544.6	402.9
52.5°	2550.9	2407.2	2263.5	1951.7	1639.9	1328.1	1016.3	858.4	700.5	542.6	384.7
55°	2676.5	2538.8	2401.1	2069.1	1735.0	1403.0	1069.0	894.9	720.7	544.6	370.5
57.5°	2836.4	2690.6	2546.9	2188.6	1830.2	1471.9	1113.5	927.2	739.0	552.7	364.4
60°	2947.8	2806.0	2666.3	2285.7	1903.1	1522.5	1139.8	945.5	751.1	554.7	360.4
62.5°	2959.9	2777.7	2597.5	2227.0	1856.5	1484.0	1113.5	925.2	736.9	546.6	358.3
65°	2883.0	2670.4	2457.8	2103.5	1749.2	1394.9	1040.6	868.5	696.4	522.3	350.2
67.5°	2729.1	2480.1	2231.1	1907.1	1583.2	1259.3	935.3	787.6	641.8	494.0	346.2
70°	2370.8	2152.1	1935.5	1654.1	1374.7	1093.3	811.8	690.4	570.9	449.5	328.0
72.5°	1990.1	1785.7	1583.2	1354.4	1127.7	898.9	670.1	579.0	487.9	394.8	303.7
75°	1524.5	1370.6	1218.8	1048.7	878.7	706.6	536.5	469.7	402.9	336.1	269.3
77.5°	1071.0	988.0	907.0	779.5	651.9	524.4	396.8	352.3	307.7	263.2	218.7
80°	726.8	680.3	635.7	544.6	453.5	360.4	269.3	240.9	210.6	182.2	151.8
82.5°	451.5	449.5	445.4	382.6	319.9	257.1	194.4	170.1	147.8	123.5	99.2
85°	206.5	240.9	273.3	238.9	204.5	170.1	135.6	119.4	103.3	85.0	68.8
87.5°	64.8	79.0	91.1	87.1	81.0	76.9	70.9	60.7	50.6	40.5	30.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7
2.5°	1417.2	1411.1	1403.0	1394.9	1384.8	1376.7	1366.6	1356.5	1354.4	1350.4	1348.4
5°	1220.8	1208.7	1194.5	1182.3	1170.2	1156.0	1143.9	1129.7	1119.6	1107.4	1097.3
7.5°	1048.7	1028.5	1006.2	983.9	963.7	943.4	921.2	900.9	890.8	880.7	870.6
10°	911.1	890.8	872.6	852.3	838.2	826.0	811.8	797.7	785.5	773.4	761.2
12.5°	842.2	828.0	813.9	799.7	783.5	769.3	753.1	736.9	722.8	710.6	696.4
15°	799.7	779.5	757.2	736.9	714.7	694.4	672.2	649.9	633.7	619.5	603.3
17.5°	749.1	718.7	690.4	660.0	635.7	611.4	585.1	560.8	542.6	522.3	504.1
20°	692.4	658.0	621.5	587.1	558.8	532.5	504.1	475.8	455.5	433.3	413.0
22.5°	643.8	599.3	552.7	506.1	475.8	445.4	413.0	382.6	364.4	344.2	326.0
25°	591.2	542.6	492.0	441.4	411.0	378.6	348.2	315.8	301.7	289.5	275.3
27.5°	562.8	514.2	463.6	415.0	386.7	356.3	328.0	297.6	287.5	275.3	265.2
30°	506.1	459.6	411.0	362.4	342.2	323.9	303.7	283.4	279.4	277.4	273.3
32.5°	455.5	406.9	358.3	309.8	291.5	273.3	255.1	236.9	234.8	230.8	228.8
35°	429.2	382.6	334.1	287.5	271.3	253.1	236.9	218.7	214.6	208.5	204.5
37.5°	423.1	374.5	323.9	275.3	259.1	242.9	224.7	208.5	204.5	200.4	196.4
40°	406.9	360.4	315.8	269.3	253.1	236.9	218.7	202.5	198.4	194.4	190.3
42.5°	394.8	350.2	303.7	257.1	242.9	228.8	212.6	198.4	194.4	190.3	184.2
45°	384.7	338.1	289.5	242.9	232.8	222.7	210.6	200.4	196.4	190.3	186.3
47.5°	368.5	323.9	277.4	230.8	220.7	212.6	202.5	192.3	188.3	184.2	180.2
50°	356.3	309.8	263.2	216.6	208.5	200.4	192.3	184.2	184.2	186.3	186.3
52.5°	340.1	295.6	251.0	206.5	198.4	190.3	182.2	174.1	176.1	178.2	180.2
55°	326.0	283.4	238.9	194.4	186.3	178.2	168.0	159.9	162.0	164.0	166.0
57.5°	319.9	275.3	230.8	186.3	178.2	168.0	159.9	149.8	149.8	149.8	149.8
60°	315.8	269.3	224.7	178.2	168.0	159.9	149.8	139.7	137.7	137.7	135.6
62.5°	313.8	267.2	222.7	176.1	164.0	153.9	141.7	129.6	127.5	125.5	123.5
65°	305.7	263.2	218.7	174.1	159.9	147.8	133.6	119.4	117.4	117.4	115.4
67.5°	303.7	259.1	216.6	172.1	157.9	141.7	127.5	111.4	109.3	107.3	105.3
70°	287.5	249.0	208.5	168.0	151.8	137.7	121.5	105.3	103.3	99.2	97.2
72.5°	267.2	232.8	196.4	159.9	143.7	127.5	111.4	95.2	93.1	91.1	87.1
75°	236.9	204.5	172.1	139.7	125.5	113.4	99.2	85.0	83.0	81.0	76.9
77.5°	194.4	168.0	143.7	117.4	107.3	97.2	87.1	76.9	74.9	72.9	68.8
80°	137.7	121.5	107.3	91.1	85.0	76.9	70.9	62.8	62.8	60.7	60.7
82.5°	91.1	83.0	74.9	66.8	62.8	58.7	54.7	50.6	50.6	48.6	48.6
85°	64.8	60.7	54.7	50.6	48.6	44.5	42.5	38.5	38.5	38.5	38.5
87.5°	30.4	30.4	28.3	28.3	26.3	26.3	24.3	22.3	22.3	22.3	22.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7
2.5°	1344.3	1338.2	1332.2	1324.1	1318.0	1309.9	1299.8	1291.7	1281.5	1281.5	1279.5
5°	1085.2	1079.1	1073.0	1064.9	1058.8	1050.7	1044.7	1036.6	1028.5	1028.5	1026.5
7.5°	860.4	848.3	836.1	822.0	809.8	801.7	793.6	783.5	775.4	769.3	763.3
10°	749.1	736.9	722.8	710.6	696.4	686.3	676.2	664.1	653.9	645.8	637.7
12.5°	682.3	668.1	653.9	639.8	625.6	611.4	599.3	585.1	570.9	560.8	550.7
15°	587.1	573.0	558.8	544.6	530.4	514.2	498.0	479.8	463.6	455.5	449.5
17.5°	483.9	469.7	453.5	439.3	423.1	411.0	398.8	386.7	374.5	366.4	360.4
20°	390.7	374.5	358.3	342.2	326.0	317.9	309.8	301.7	293.6	287.5	283.4
22.5°	305.7	295.6	287.5	277.4	267.2	261.2	257.1	251.0	245.0	245.0	245.0
25°	261.2	255.1	251.0	245.0	238.9	236.9	234.8	230.8	228.8	226.8	226.8
27.5°	253.1	247.0	240.9	234.8	228.8	226.8	224.7	220.7	218.7	218.7	218.7
30°	269.3	267.2	265.2	263.2	261.2	257.1	251.0	247.0	240.9	236.9	232.8
32.5°	224.7	222.7	222.7	220.7	218.7	222.7	224.7	228.8	230.8	232.8	234.8
35°	198.4	194.4	190.3	186.3	182.2	180.2	178.2	176.1	174.1	174.1	172.1
37.5°	192.3	188.3	184.2	180.2	176.1	174.1	172.1	170.1	168.0	168.0	166.0
40°	186.3	182.2	180.2	176.1	172.1	170.1	168.0	164.0	162.0	159.9	159.9
42.5°	180.2	178.2	174.1	172.1	168.0	166.0	164.0	159.9	157.9	155.9	153.9
45°	180.2	176.1	172.1	168.0	164.0	162.0	157.9	155.9	151.8	151.8	149.8
47.5°	176.1	172.1	168.0	164.0	159.9	157.9	153.9	151.8	147.8	145.8	143.7
50°	186.3	180.2	172.1	166.0	157.9	155.9	151.8	149.8	145.8	143.7	141.7
52.5°	182.2	176.1	168.0	162.0	153.9	149.8	147.8	143.7	139.7	137.7	135.6
55°	168.0	162.0	157.9	151.8	145.8	141.7	137.7	133.6	129.6	127.5	127.5
57.5°	149.8	147.8	145.8	143.7	141.7	137.7	133.6	127.5	123.5	121.5	119.4
60°	133.6	135.6	137.7	139.7	141.7	135.6	129.6	123.5	117.4	115.4	113.4
62.5°	121.5	125.5	129.6	131.6	135.6	129.6	123.5	117.4	111.4	109.3	107.3
65°	113.4	115.4	115.4	117.4	117.4	113.4	111.4	107.3	103.3	101.2	101.2
67.5°	103.3	103.3	103.3	101.2	101.2	99.2	99.2	97.2	95.2	93.1	93.1
70°	93.1	93.1	93.1	91.1	91.1	89.1	89.1	87.1	85.0	85.0	83.0
72.5°	85.0	85.0	83.0	83.0	81.0	81.0	81.0	79.0	79.0	76.9	76.9
75°	74.9	74.9	72.9	72.9	70.9	70.9	70.9	68.8	68.8	68.8	66.8
77.5°	66.8	66.8	64.8	64.8	62.8	62.8	62.8	60.7	60.7	58.7	58.7
80°	58.7	58.7	56.7	56.7	54.7	54.7	52.6	52.6	50.6	50.6	48.6
82.5°	46.6	46.6	46.6	46.6	46.6	44.5	44.5	42.5	40.5	40.5	38.5
85°	38.5	38.5	38.5	36.4	36.4	36.4	34.4	34.4	32.4	30.4	30.4
87.5°	22.3	22.3	22.3	20.2	20.2	20.2	20.2	20.2	20.2	20.2	18.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7
2.5°	1279.5	1277.5	1269.4	1261.3	1269.4	1277.5	1277.5	1277.5	1275.5	1275.5	1275.5
5°	1026.5	1024.4	1020.4	1016.3	1016.3	1014.3	1018.4	1022.4	1026.5	1030.5	1034.6
7.5°	755.2	749.1	743.0	736.9	741.0	743.0	749.1	753.1	759.2	763.3	773.4
10°	629.6	621.5	615.5	609.4	605.3	601.3	597.2	595.2	591.2	587.1	591.2
12.5°	538.5	528.4	518.3	506.1	504.1	502.1	498.0	494.0	489.9	485.9	483.9
15°	441.4	433.3	429.2	423.1	415.0	406.9	402.9	400.9	396.8	392.8	390.7
17.5°	352.3	344.2	338.1	332.0	330.0	326.0	326.0	326.0	326.0	326.0	326.0
20°	277.4	271.3	271.3	269.3	269.3	267.2	269.3	271.3	271.3	273.3	275.3
22.5°	242.9	242.9	240.9	238.9	240.9	240.9	242.9	245.0	247.0	249.0	251.0
25°	224.7	222.7	224.7	226.8	226.8	226.8	228.8	228.8	230.8	230.8	230.8
27.5°	216.6	216.6	218.7	218.7	220.7	220.7	220.7	218.7	218.7	216.6	216.6
30°	228.8	224.7	224.7	224.7	222.7	220.7	218.7	218.7	216.6	214.6	212.6
32.5°	236.9	238.9	236.9	232.8	230.8	226.8	224.7	220.7	218.7	214.6	210.6
35°	172.1	170.1	174.1	176.1	178.2	180.2	182.2	184.2	184.2	186.3	186.3
37.5°	166.0	164.0	164.0	162.0	162.0	162.0	162.0	162.0	159.9	159.9	162.0
40°	157.9	155.9	155.9	153.9	153.9	151.8	151.8	151.8	151.8	151.8	151.8
42.5°	151.8	149.8	149.8	149.8	149.8	147.8	147.8	145.8	145.8	143.7	143.7
45°	149.8	147.8	145.8	143.7	143.7	141.7	141.7	141.7	139.7	139.7	139.7
47.5°	141.7	139.7	139.7	137.7	137.7	135.6	135.6	135.6	133.6	133.6	133.6
50°	137.7	135.6	135.6	133.6	133.6	131.6	131.6	131.6	129.6	129.6	129.6
52.5°	131.6	129.6	129.6	129.6	127.5	125.5	125.5	125.5	123.5	123.5	123.5
55°	125.5	123.5	123.5	123.5	121.5	119.4	119.4	119.4	117.4	117.4	117.4
57.5°	117.4	115.4	115.4	113.4	113.4	113.4	113.4	113.4	111.4	111.4	111.4
60°	111.4	109.3	109.3	107.3	107.3	105.3	105.3	105.3	105.3	105.3	105.3
62.5°	105.3	103.3	101.2	99.2	101.2	101.2	101.2	101.2	99.2	99.2	99.2
65°	99.2	97.2	95.2	93.1	93.1	93.1	93.1	93.1	93.1	93.1	93.1
67.5°	91.1	89.1	87.1	85.0	87.1	87.1	87.1	87.1	87.1	87.1	87.1
70°	83.0	81.0	81.0	79.0	79.0	76.9	76.9	79.0	79.0	79.0	79.0
72.5°	74.9	72.9	72.9	70.9	70.9	70.9	70.9	70.9	70.9	70.9	70.9
75°	66.8	64.8	64.8	62.8	62.8	62.8	62.8	62.8	62.8	62.8	62.8
77.5°	56.7	54.7	54.7	54.7	54.7	54.7	54.7	56.7	56.7	56.7	56.7
80°	48.6	46.6	46.6	46.6	46.6	46.6	46.6	46.6	46.6	46.6	46.6
82.5°	38.5	36.4	36.4	36.4	36.4	36.4	36.4	36.4	36.4	36.4	36.4
85°	28.3	26.3	26.3	26.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3
87.5°	18.2	16.2	16.2	16.2	18.2	18.2	18.2	18.2	16.2	16.2	16.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7
2.5°	1275.5	1275.5	1275.5	1273.4	1271.4	1269.4	1267.4	1273.4	1277.5	1283.6	1287.6
5°	1036.6	1040.6	1042.6	1048.7	1054.8	1060.9	1066.9	1071.0	1075.0	1077.1	1081.1
7.5°	781.5	791.6	799.7	807.8	815.9	822.0	830.1	836.1	842.2	848.3	854.4
10°	593.2	597.2	599.3	607.4	613.4	621.5	627.6	633.7	639.8	643.8	649.9
12.5°	481.8	477.8	475.8	475.8	475.8	475.8	475.8	479.8	483.9	487.9	492.0
15°	388.7	386.7	384.7	382.6	380.6	376.6	374.5	378.6	382.6	386.7	390.7
17.5°	326.0	326.0	326.0	323.9	321.9	319.9	317.9	319.9	321.9	321.9	323.9
20°	279.4	281.4	283.4	285.5	285.5	287.5	287.5	289.5	291.5	291.5	293.6
22.5°	251.0	253.1	253.1	253.1	255.1	255.1	255.1	257.1	259.1	261.2	263.2
25°	228.8	228.8	226.8	226.8	228.8	228.8	228.8	228.8	230.8	230.8	230.8
27.5°	216.6	214.6	214.6	214.6	214.6	212.6	212.6	212.6	212.6	212.6	212.6
30°	210.6	208.5	206.5	204.5	204.5	202.5	200.4	200.4	200.4	200.4	200.4
32.5°	208.5	204.5	200.4	198.4	198.4	196.4	194.4	192.3	192.3	190.3	188.3
35°	186.3	184.2	184.2	182.2	180.2	178.2	176.1	176.1	176.1	174.1	174.1
37.5°	162.0	164.0	164.0	164.0	166.0	166.0	166.0	166.0	168.0	168.0	168.0
40°	151.8	151.8	151.8	153.9	155.9	155.9	157.9	157.9	159.9	159.9	159.9
42.5°	143.7	141.7	141.7	143.7	143.7	145.8	145.8	147.8	149.8	149.8	151.8
45°	139.7	137.7	137.7	137.7	137.7	135.6	135.6	137.7	139.7	141.7	143.7
47.5°	131.6	131.6	129.6	129.6	129.6	129.6	129.6	129.6	131.6	131.6	131.6
50°	127.5	127.5	125.5	125.5	125.5	125.5	125.5	125.5	125.5	125.5	125.5
52.5°	123.5	121.5	121.5	121.5	121.5	119.4	119.4	119.4	119.4	119.4	119.4
55°	117.4	115.4	115.4	115.4	115.4	115.4	115.4	115.4	117.4	117.4	117.4
57.5°	111.4	109.3	109.3	109.3	111.4	111.4	111.4	111.4	113.4	113.4	113.4
60°	105.3	105.3	105.3	105.3	105.3	105.3	105.3	107.3	107.3	109.3	109.3
62.5°	99.2	99.2	99.2	99.2	101.2	101.2	101.2	101.2	103.3	103.3	103.3
65°	93.1	93.1	93.1	93.1	95.2	95.2	95.2	95.2	95.2	95.2	95.2
67.5°	87.1	87.1	87.1	87.1	87.1	87.1	87.1	89.1	89.1	91.1	91.1
70°	79.0	76.9	76.9	79.0	79.0	81.0	81.0	83.0	83.0	85.0	85.0
72.5°	70.9	70.9	70.9	70.9	70.9	70.9	70.9	72.9	74.9	74.9	76.9
75°	62.8	62.8	62.8	62.8	64.8	64.8	64.8	66.8	66.8	68.8	68.8
77.5°	56.7	54.7	54.7	54.7	56.7	56.7	56.7	58.7	58.7	60.7	60.7
80°	46.6	46.6	46.6	46.6	48.6	48.6	48.6	48.6	50.6	50.6	50.6
82.5°	38.5	38.5	38.5	38.5	38.5	38.5	38.5	38.5	40.5	40.5	40.5
85°	28.3	28.3	28.3	28.3	30.4	30.4	30.4	30.4	30.4	30.4	30.4
87.5°	18.2	18.2	18.2	18.2	18.2	18.2	18.2	18.2	20.2	20.2	20.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7
2.5°	1287.6	1287.6	1287.6	1287.6	1291.7	1293.7	1297.7	1299.8	1297.7	1295.7	1291.7
5°	1083.1	1085.2	1085.2	1087.2	1087.2	1087.2	1087.2	1087.2	1091.2	1095.3	1099.3
7.5°	856.4	858.4	860.4	862.5	862.5	862.5	860.4	860.4	862.5	862.5	864.5
10°	656.0	664.1	670.1	676.2	672.2	666.1	662.0	656.0	656.0	656.0	653.9
12.5°	496.0	498.0	502.1	504.1	502.1	502.1	500.1	498.0	500.1	504.1	506.1
15°	392.8	392.8	394.8	394.8	396.8	398.8	398.8	400.9	404.9	406.9	411.0
17.5°	326.0	328.0	328.0	330.0	330.0	332.0	332.0	332.0	336.1	340.1	346.2
20°	293.6	293.6	293.6	293.6	293.6	291.5	291.5	289.5	291.5	295.6	297.6
22.5°	263.2	265.2	265.2	265.2	263.2	261.2	257.1	255.1	255.1	257.1	257.1
25°	230.8	228.8	228.8	226.8	226.8	228.8	228.8	228.8	230.8	230.8	232.8
27.5°	212.6	210.6	210.6	208.5	208.5	210.6	210.6	210.6	210.6	210.6	210.6
30°	198.4	198.4	196.4	194.4	196.4	196.4	198.4	198.4	200.4	200.4	202.5
32.5°	188.3	186.3	186.3	184.2	186.3	186.3	188.3	188.3	190.3	192.3	192.3
35°	174.1	174.1	174.1	174.1	174.1	174.1	172.1	172.1	172.1	172.1	172.1
37.5°	166.0	166.0	164.0	162.0	162.0	162.0	162.0	162.0	159.9	157.9	155.9
40°	159.9	157.9	157.9	155.9	153.9	153.9	151.8	149.8	149.8	147.8	147.8
42.5°	151.8	149.8	149.8	147.8	145.8	145.8	143.7	141.7	141.7	141.7	139.7
45°	141.7	141.7	139.7	137.7	137.7	137.7	135.6	135.6	135.6	135.6	133.6
47.5°	131.6	131.6	129.6	129.6	129.6	129.6	127.5	127.5	127.5	127.5	127.5
50°	125.5	125.5	125.5	125.5	125.5	125.5	123.5	123.5	123.5	123.5	123.5
52.5°	119.4	119.4	119.4	119.4	119.4	119.4	119.4	119.4	119.4	119.4	119.4
55°	117.4	117.4	117.4	117.4	117.4	117.4	115.4	115.4	115.4	117.4	117.4
57.5°	113.4	113.4	111.4	111.4	111.4	111.4	111.4	111.4	111.4	111.4	111.4
60°	109.3	109.3	109.3	109.3	109.3	109.3	109.3	109.3	109.3	109.3	109.3
62.5°	103.3	103.3	103.3	103.3	103.3	105.3	105.3	105.3	105.3	105.3	103.3
65°	95.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2
67.5°	91.1	91.1	91.1	91.1	91.1	91.1	91.1	91.1	91.1	91.1	91.1
70°	85.0	85.0	83.0	83.0	83.0	85.0	85.0	85.0	85.0	85.0	85.0
72.5°	76.9	76.9	76.9	76.9	76.9	76.9	76.9	76.9	76.9	79.0	79.0
75°	68.8	68.8	68.8	68.8	68.8	68.8	68.8	68.8	68.8	68.8	68.8
77.5°	60.7	60.7	58.7	58.7	58.7	60.7	60.7	60.7	60.7	62.8	62.8
80°	50.6	50.6	50.6	50.6	50.6	50.6	50.6	50.6	50.6	52.6	52.6
82.5°	40.5	40.5	40.5	40.5	40.5	40.5	40.5	40.5	40.5	42.5	42.5
85°	30.4	32.4	32.4	32.4	32.4	32.4	32.4	32.4	32.4	34.4	34.4
87.5°	20.2	20.2	20.2	20.2	20.2	20.2	18.2	18.2	18.2	18.2	16.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7
2.5°	1289.6	1291.7	1293.7	1293.7	1295.7	1297.7	1297.7	1305.8	1313.9	1318.0	1322.0
5°	1103.4	1101.4	1101.4	1099.3	1097.3	1103.4	1109.5	1121.6	1133.8	1135.8	1139.8
7.5°	864.5	866.5	868.5	868.5	870.6	864.5	856.4	858.4	860.4	870.6	878.7
10°	653.9	656.0	658.0	658.0	660.0	658.0	653.9	660.0	666.1	674.2	684.3
12.5°	508.2	514.2	520.3	524.4	530.4	534.5	536.5	544.6	550.7	560.8	570.9
15°	415.0	419.1	423.1	427.2	431.2	435.3	439.3	447.4	455.5	467.7	479.8
17.5°	350.2	350.2	352.3	352.3	352.3	356.3	360.4	364.4	366.4	378.6	390.7
20°	299.6	297.6	295.6	293.6	291.5	295.6	297.6	299.6	301.7	309.8	315.8
22.5°	257.1	257.1	259.1	259.1	259.1	257.1	253.1	255.1	255.1	259.1	265.2
25°	232.8	232.8	232.8	230.8	230.8	232.8	234.8	234.8	232.8	234.8	236.9
27.5°	210.6	212.6	212.6	214.6	214.6	216.6	216.6	216.6	216.6	218.7	220.7
30°	202.5	202.5	204.5	204.5	204.5	206.5	208.5	208.5	208.5	210.6	214.6
32.5°	194.4	196.4	198.4	200.4	202.5	204.5	204.5	206.5	206.5	208.5	210.6
35°	172.1	170.1	170.1	168.0	166.0	166.0	166.0	166.0	164.0	166.0	166.0
37.5°	153.9	153.9	153.9	151.8	151.8	153.9	153.9	153.9	153.9	155.9	155.9
40°	145.8	145.8	145.8	145.8	145.8	145.8	145.8	147.8	147.8	149.8	151.8
42.5°	139.7	139.7	139.7	139.7	139.7	141.7	141.7	141.7	141.7	143.7	143.7
45°	133.6	133.6	133.6	133.6	133.6	133.6	133.6	135.6	135.6	137.7	139.7
47.5°	127.5	127.5	127.5	127.5	127.5	129.6	131.6	131.6	131.6	133.6	133.6
50°	123.5	123.5	123.5	123.5	123.5	125.5	125.5	127.5	127.5	129.6	131.6
52.5°	119.4	119.4	119.4	119.4	119.4	121.5	121.5	123.5	123.5	125.5	127.5
55°	117.4	117.4	117.4	115.4	115.4	117.4	117.4	119.4	119.4	121.5	121.5
57.5°	111.4	111.4	111.4	111.4	111.4	111.4	111.4	113.4	113.4	115.4	117.4
60°	109.3	109.3	107.3	107.3	105.3	107.3	107.3	109.3	109.3	111.4	111.4
62.5°	103.3	103.3	103.3	101.2	101.2	103.3	103.3	103.3	103.3	105.3	107.3
65°	97.2	97.2	97.2	95.2	95.2	97.2	97.2	97.2	97.2	99.2	101.2
67.5°	91.1	91.1	91.1	89.1	89.1	89.1	89.1	91.1	91.1	93.1	95.2
70°	85.0	85.0	85.0	83.0	83.0	83.0	81.0	83.0	85.0	87.1	87.1
72.5°	79.0	79.0	79.0	76.9	76.9	76.9	74.9	76.9	76.9	79.0	79.0
75°	68.8	68.8	68.8	68.8	68.8	68.8	66.8	66.8	66.8	68.8	68.8
77.5°	62.8	62.8	62.8	60.7	60.7	60.7	58.7	58.7	58.7	60.7	60.7
80°	52.6	52.6	52.6	50.6	50.6	50.6	48.6	48.6	48.6	50.6	50.6
82.5°	42.5	42.5	42.5	40.5	40.5	40.5	38.5	38.5	38.5	40.5	40.5
85°	34.4	34.4	34.4	34.4	34.4	34.4	32.4	32.4	32.4	34.4	36.4
87.5°	16.2	16.2	18.2	18.2	18.2	18.2	16.2	16.2	14.2	14.2	16.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7
2.5°	1326.1	1330.1	1340.3	1348.4	1358.5	1366.6	1372.7	1380.8	1386.8	1392.9	1396.9
5°	1141.9	1143.9	1154.0	1164.1	1172.2	1182.3	1196.5	1210.7	1224.9	1239.0	1249.2
7.5°	888.8	896.9	909.0	923.2	935.3	947.5	961.7	977.9	992.0	1006.2	1020.4
10°	692.4	700.5	712.6	724.8	734.9	747.1	763.3	779.5	795.7	811.8	828.0
12.5°	581.0	591.2	605.3	619.5	631.7	645.8	666.1	684.3	704.5	722.8	743.0
15°	489.9	502.1	520.3	540.6	558.8	577.0	597.2	617.5	635.7	656.0	676.2
17.5°	402.9	415.0	431.2	449.5	465.6	481.8	506.1	528.4	552.7	575.0	597.2
20°	323.9	330.0	346.2	362.4	378.6	394.8	413.0	431.2	449.5	467.7	496.0
22.5°	269.3	273.3	281.4	287.5	295.6	301.7	319.9	338.1	354.3	372.5	398.8
25°	236.9	238.9	245.0	249.0	255.1	259.1	271.3	281.4	293.6	303.7	328.0
27.5°	220.7	222.7	224.7	226.8	228.8	230.8	238.9	247.0	253.1	261.2	283.4
30°	216.6	218.7	224.7	228.8	234.8	238.9	242.9	247.0	251.0	255.1	269.3
32.5°	212.6	214.6	214.6	212.6	212.6	210.6	214.6	216.6	220.7	222.7	234.8
35°	168.0	168.0	170.1	172.1	174.1	176.1	182.2	186.3	192.3	196.4	206.5
37.5°	157.9	157.9	159.9	164.0	166.0	168.0	172.1	176.1	180.2	184.2	194.4
40°	151.8	153.9	155.9	157.9	159.9	162.0	166.0	168.0	172.1	174.1	182.2
42.5°	145.8	145.8	147.8	151.8	153.9	155.9	159.9	162.0	166.0	168.0	176.1
45°	141.7	143.7	145.8	147.8	147.8	149.8	153.9	157.9	159.9	164.0	172.1
47.5°	135.6	135.6	139.7	141.7	145.8	147.8	151.8	153.9	157.9	159.9	168.0
50°	131.6	133.6	137.7	139.7	143.7	145.8	151.8	155.9	162.0	166.0	170.1
52.5°	127.5	129.6	133.6	135.6	139.7	141.7	149.8	157.9	164.0	172.1	172.1
55°	123.5	123.5	127.5	133.6	137.7	141.7	145.8	151.8	155.9	159.9	159.9
57.5°	117.4	119.4	123.5	129.6	133.6	137.7	141.7	145.8	147.8	151.8	149.8
60°	113.4	113.4	119.4	125.5	131.6	137.7	137.7	137.7	135.6	135.6	135.6
62.5°	107.3	109.3	117.4	127.5	135.6	143.7	137.7	131.6	125.5	119.4	121.5
65°	103.3	105.3	109.3	115.4	119.4	123.5	119.4	117.4	113.4	109.3	111.4
67.5°	95.2	97.2	99.2	99.2	101.2	101.2	101.2	101.2	101.2	101.2	103.3
70°	89.1	89.1	89.1	91.1	91.1	91.1	91.1	91.1	91.1	91.1	93.1
72.5°	81.0	81.0	81.0	81.0	81.0	81.0	81.0	81.0	81.0	81.0	83.0
75°	70.9	70.9	70.9	70.9	70.9	70.9	70.9	70.9	70.9	70.9	72.9
77.5°	62.8	62.8	62.8	62.8	62.8	62.8	62.8	62.8	60.7	60.7	62.8
80°	52.6	52.6	52.6	52.6	50.6	50.6	50.6	50.6	50.6	50.6	52.6
82.5°	42.5	42.5	42.5	42.5	40.5	40.5	40.5	40.5	38.5	38.5	40.5
85°	38.5	40.5	40.5	42.5	42.5	42.5	40.5	38.5	36.4	34.4	34.4
87.5°	16.2	16.2	16.2	16.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7
2.5°	1403.0	1407.1	1411.1	1417.2	1425.3	1431.4	1437.4	1449.6	1463.8	1475.9	1488.1
5°	1259.3	1269.4	1279.5	1291.7	1303.8	1313.9	1326.1	1350.4	1374.7	1396.9	1421.2
7.5°	1032.5	1046.7	1058.8	1079.1	1097.3	1117.6	1135.8	1166.1	1194.5	1224.9	1253.2
10°	844.2	860.4	876.6	903.0	931.3	957.6	983.9	1008.2	1034.6	1058.8	1083.1
12.5°	763.3	781.5	801.7	817.9	836.1	852.3	868.5	896.9	925.2	953.6	981.9
15°	696.4	716.7	736.9	757.2	775.4	795.7	813.9	838.2	864.5	888.8	913.1
17.5°	619.5	639.8	662.0	684.3	706.6	728.8	751.1	785.5	819.9	852.3	886.8
20°	522.3	550.7	577.0	607.4	637.7	668.1	698.5	734.9	771.4	805.8	842.2
22.5°	425.2	451.5	477.8	514.2	550.7	585.1	621.5	670.1	716.7	765.3	811.8
25°	354.3	378.6	402.9	443.4	481.8	522.3	560.8	619.5	676.2	734.9	791.6
27.5°	305.7	328.0	350.2	392.8	435.3	475.8	518.3	583.1	645.8	710.6	773.4
30°	283.4	297.6	311.8	352.3	392.8	431.2	471.7	534.5	597.2	660.0	722.8
32.5°	247.0	259.1	271.3	307.7	344.2	378.6	415.0	479.8	542.6	607.4	670.1
35°	218.7	228.8	238.9	273.3	305.7	340.1	372.5	437.3	502.1	566.9	631.7
37.5°	202.5	212.6	220.7	251.0	283.4	313.8	344.2	409.0	471.7	536.5	599.3
40°	190.3	196.4	204.5	234.8	263.2	293.6	321.9	380.6	441.4	500.1	558.8
42.5°	182.2	190.3	196.4	222.7	251.0	277.4	303.7	360.4	417.1	471.7	528.4
45°	180.2	188.3	196.4	218.7	240.9	261.2	283.4	338.1	392.8	447.4	502.1
47.5°	176.1	182.2	190.3	208.5	224.7	242.9	259.1	313.8	368.5	421.1	475.8
50°	174.1	176.1	180.2	196.4	212.6	228.8	245.0	299.6	354.3	409.0	463.6
52.5°	172.1	172.1	172.1	186.3	200.4	212.6	226.8	281.4	338.1	392.8	447.4
55°	159.9	157.9	157.9	172.1	184.2	198.4	210.6	265.2	319.9	372.5	427.2
57.5°	147.8	145.8	143.7	155.9	168.0	180.2	192.3	247.0	303.7	358.3	413.0
60°	135.6	133.6	133.6	145.8	155.9	168.0	178.2	234.8	289.5	346.2	400.9
62.5°	121.5	123.5	123.5	133.6	145.8	155.9	166.0	222.7	281.4	338.1	394.8
65°	111.4	113.4	113.4	125.5	137.7	149.8	162.0	216.6	273.3	328.0	382.6
67.5°	103.3	105.3	105.3	119.4	131.6	145.8	157.9	206.5	257.1	305.7	354.3
70°	95.2	95.2	97.2	111.4	125.5	139.7	153.9	196.4	238.9	279.4	321.9
72.5°	85.0	87.1	89.1	103.3	115.4	129.6	141.7	180.2	218.7	257.1	295.6
75°	74.9	76.9	79.0	91.1	103.3	115.4	127.5	164.0	198.4	234.8	269.3
77.5°	66.8	68.8	70.9	81.0	91.1	101.2	111.4	137.7	166.0	192.3	218.7
80°	54.7	54.7	56.7	64.8	72.9	79.0	87.1	105.3	123.5	139.7	157.9
82.5°	40.5	42.5	42.5	48.6	52.6	58.7	62.8	72.9	81.0	91.1	99.2
85°	34.4	32.4	32.4	36.4	38.5	42.5	44.5	50.6	54.7	60.7	64.8
87.5°	14.2	12.1	12.1	14.2	18.2	20.2	22.3	22.3	24.3	24.3	24.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7
2.5°	1494.1	1498.2	1504.2	1508.3	1518.4	1526.5	1536.6	1544.7	1550.8	1560.9	1556.9
5°	1439.5	1457.7	1475.9	1494.1	1508.3	1522.5	1534.6	1548.8	1565.0	1595.4	1603.5
7.5°	1277.5	1301.8	1324.1	1348.4	1376.7	1405.0	1433.4	1461.7	1488.1	1526.5	1550.8
10°	1117.6	1152.0	1184.4	1218.8	1245.1	1271.4	1295.7	1322.0	1358.5	1396.9	1441.5
12.5°	1016.3	1050.7	1085.2	1119.6	1158.0	1194.5	1233.0	1269.4	1303.8	1334.2	1384.8
15°	949.5	988.0	1024.4	1060.9	1107.4	1152.0	1198.5	1243.1	1293.7	1334.2	1368.6
17.5°	933.3	979.9	1024.4	1071.0	1119.6	1168.2	1216.8	1265.4	1316.0	1376.7	1421.2
20°	905.0	967.7	1030.5	1093.3	1156.0	1216.8	1279.5	1340.3	1407.1	1480.0	1500.2
22.5°	888.8	963.7	1040.6	1115.5	1200.6	1287.6	1372.7	1457.7	1528.5	1583.2	1643.9
25°	886.8	979.9	1075.0	1168.2	1275.5	1380.8	1488.1	1593.3	1684.4	1739.1	1787.7
27.5°	884.7	998.1	1109.5	1220.8	1352.4	1482.0	1613.6	1743.1	1828.2	1907.1	1947.6
30°	860.4	996.1	1133.8	1269.4	1417.2	1565.0	1712.8	1860.6	1947.6	2002.3	2022.5
32.5°	830.1	990.0	1150.0	1309.9	1477.9	1646.0	1812.0	1980.0	2048.9	2095.4	2079.2
35°	805.8	981.9	1156.0	1330.1	1508.3	1688.5	1866.6	2044.8	2144.0	2208.8	2182.5
37.5°	783.5	967.7	1152.0	1336.2	1544.7	1753.3	1961.8	2170.3	2265.5	2334.3	2304.0
40°	757.2	953.6	1152.0	1348.4	1587.3	1824.1	2063.0	2299.9	2423.4	2482.1	2435.5
42.5°	734.9	939.4	1145.9	1350.4	1605.5	1860.6	2115.7	2370.8	2508.4	2591.4	2532.7
45°	706.6	911.1	1113.5	1318.0	1599.4	1880.8	2160.2	2441.6	2601.6	2666.3	2585.4
47.5°	676.2	878.7	1079.1	1279.5	1579.2	1878.8	2178.4	2478.1	2625.9	2702.8	2627.9
50°	666.1	868.5	1069.0	1271.4	1595.4	1921.3	2245.2	2569.2	2676.5	2739.2	2640.0
52.5°	664.1	878.7	1095.3	1309.9	1635.8	1959.8	2285.7	2609.7	2696.7	2763.5	2674.4
55°	658.0	890.8	1121.6	1352.4	1692.5	2034.7	2374.8	2714.9	2802.0	2850.6	2783.8
57.5°	664.1	915.1	1164.1	1415.2	1765.4	2115.7	2465.9	2816.2	2921.4	2955.9	2941.7
60°	668.1	935.3	1200.6	1467.8	1810.0	2152.1	2494.3	2836.4	2945.7	3030.8	3047.0
62.5°	658.0	921.2	1182.3	1445.5	1755.3	2065.1	2374.8	2684.6	2864.8	2990.3	3063.2
65°	627.6	870.6	1115.5	1358.5	1643.9	1931.4	2216.9	2502.4	2692.7	2878.9	2937.6
67.5°	560.8	767.3	973.8	1180.3	1429.3	1678.4	1925.4	2174.4	2413.3	2593.5	2674.4
70°	485.9	647.9	811.8	973.8	1200.6	1427.3	1654.1	1880.8	2091.4	2289.8	2366.7
72.5°	423.1	548.7	676.2	801.7	963.7	1123.6	1285.6	1445.5	1694.6	1893.0	1967.9
75°	360.4	451.5	540.6	631.7	743.0	854.4	963.7	1075.0	1251.2	1429.3	1504.2
77.5°	277.4	338.1	396.8	455.5	532.5	607.4	684.3	759.2	882.7	1016.3	1054.8
80°	192.3	226.8	259.1	293.6	354.3	415.0	475.8	536.5	617.5	692.4	751.1
82.5°	119.4	141.7	162.0	182.2	230.8	279.4	326.0	374.5	406.9	411.0	469.7
85°	76.9	91.1	103.3	115.4	143.7	174.1	202.5	230.8	206.5	192.3	228.8
87.5°	30.4	38.5	44.5	50.6	48.6	46.6	44.5	42.5	36.4	32.4	40.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7
2.5°	1560.9	1567.0	1573.1	1577.1	1583.2	1585.2	1587.3	1587.3	1589.3	1591.3	1595.4
5°	1635.8	1648.0	1660.1	1670.3	1682.4	1692.5	1700.6	1710.8	1718.9	1718.9	1716.8
7.5°	1573.1	1603.5	1633.8	1664.2	1694.6	1716.8	1737.1	1759.3	1779.6	1783.6	1787.7
10°	1490.1	1522.5	1552.8	1585.2	1615.6	1650.0	1682.4	1714.8	1749.2	1755.3	1763.4
12.5°	1413.1	1451.6	1490.1	1526.5	1565.0	1589.3	1613.6	1635.8	1660.1	1676.3	1692.5
15°	1411.1	1443.5	1475.9	1506.3	1538.7	1552.8	1567.0	1579.2	1593.3	1593.3	1595.4
17.5°	1457.7	1477.9	1498.2	1516.4	1536.6	1538.7	1542.7	1544.7	1546.8	1540.7	1534.6
20°	1548.8	1556.9	1565.0	1573.1	1581.2	1567.0	1554.9	1540.7	1526.5	1510.3	1496.2
22.5°	1682.4	1664.2	1646.0	1627.7	1609.5	1585.2	1558.9	1534.6	1508.3	1488.1	1467.8
25°	1807.9	1785.7	1763.4	1741.1	1718.9	1666.2	1613.6	1558.9	1506.3	1484.0	1461.7
27.5°	1976.0	1941.6	1907.1	1872.7	1838.3	1767.4	1696.6	1625.7	1554.9	1516.4	1480.0
30°	2016.5	1978.0	1939.5	1899.0	1860.6	1791.7	1724.9	1656.1	1587.3	1542.7	1500.2
32.5°	2075.2	2030.6	1986.1	1941.6	1897.0	1830.2	1763.4	1694.6	1627.7	1587.3	1544.7
35°	2172.4	2121.7	2071.1	2018.5	1967.9	1899.0	1832.2	1763.4	1694.6	1648.0	1603.5
37.5°	2255.4	2196.6	2137.9	2079.2	2020.5	1959.8	1897.0	1836.3	1773.5	1727.0	1682.4
40°	2348.5	2283.7	2218.9	2156.2	2091.4	2034.7	1978.0	1919.3	1862.6	1826.2	1789.7
42.5°	2429.5	2350.5	2273.6	2196.6	2117.7	2079.2	2042.8	2004.3	1965.8	1947.6	1927.4
45°	2486.2	2413.3	2338.4	2265.5	2192.6	2164.3	2135.9	2107.6	2079.2	2097.4	2115.7
47.5°	2510.5	2451.7	2395.1	2338.4	2279.7	2289.8	2299.9	2308.0	2318.1	2342.4	2368.7
50°	2532.7	2500.3	2465.9	2433.5	2399.1	2437.6	2474.0	2512.5	2550.9	2601.6	2652.2
52.5°	2577.3	2559.0	2542.8	2524.6	2506.4	2573.2	2640.0	2706.8	2773.6	2830.3	2887.0
55°	2710.9	2696.7	2682.5	2666.3	2652.2	2747.3	2840.5	2935.6	3030.8	3089.5	3148.2
57.5°	2895.1	2887.0	2876.9	2868.8	2858.7	2951.8	3042.9	3134.0	3227.2	3283.8	3342.6
60°	3034.8	3036.8	3036.8	3038.9	3038.9	3109.7	3180.6	3253.5	3324.3	3372.9	3423.5
62.5°	3109.7	3105.7	3101.6	3097.6	3093.5	3152.2	3211.0	3269.7	3328.4	3364.8	3401.3
65°	3028.7	3051.0	3073.3	3095.6	3117.8	3125.9	3132.0	3140.1	3146.2	3168.4	3190.7
67.5°	2757.5	2802.0	2844.5	2889.0	2931.6	2901.2	2872.9	2842.5	2812.1	2818.2	2822.2
70°	2455.8	2506.4	2559.0	2609.7	2660.3	2589.4	2518.6	2445.7	2374.8	2350.5	2326.2
72.5°	2071.1	2115.7	2162.2	2206.8	2251.3	2164.3	2079.2	1992.2	1905.1	1862.6	1820.1
75°	1583.2	1635.8	1690.5	1743.1	1795.8	1698.6	1599.4	1502.2	1403.0	1374.7	1348.4
77.5°	1154.0	1216.8	1279.5	1342.3	1405.0	1318.0	1230.9	1141.9	1054.8	1038.6	1022.4
80°	840.2	888.8	935.3	983.9	1030.5	979.9	929.3	878.7	828.0	826.0	824.0
82.5°	566.9	609.4	649.9	692.4	732.9	712.6	694.4	674.2	653.9	674.2	696.4
85°	291.5	350.2	411.0	469.7	528.4	522.3	518.3	512.2	506.1	532.5	556.8
87.5°	58.7	109.3	159.9	208.5	259.1	247.0	234.8	220.7	208.5	216.6	222.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7
2.5°	1597.4	1599.4	1599.4	1599.4	1599.4	1599.4	1595.4	1593.3	1589.3	1585.2	1579.2
5°	1716.8	1714.8	1706.7	1698.6	1688.5	1680.4	1674.3	1666.2	1660.1	1652.0	1639.9
7.5°	1791.7	1795.8	1781.6	1769.5	1755.3	1741.1	1727.0	1712.8	1698.6	1684.4	1656.1
10°	1769.5	1775.5	1767.4	1759.3	1749.2	1741.1	1724.9	1706.7	1690.5	1672.3	1637.9
12.5°	1706.7	1722.9	1718.9	1714.8	1710.8	1706.7	1696.6	1684.4	1674.3	1662.2	1623.7
15°	1595.4	1595.4	1597.4	1599.4	1599.4	1601.4	1603.5	1605.5	1607.5	1609.5	1587.3
17.5°	1528.5	1522.5	1522.5	1522.5	1522.5	1522.5	1530.6	1540.7	1548.8	1556.9	1550.8
20°	1480.0	1465.8	1463.8	1463.8	1461.7	1459.7	1473.9	1490.1	1504.2	1518.4	1526.5
22.5°	1447.6	1427.3	1425.3	1423.3	1421.2	1419.2	1437.4	1455.7	1473.9	1492.1	1520.4
25°	1439.5	1417.2	1419.2	1421.2	1421.2	1423.3	1437.4	1451.6	1465.8	1480.0	1528.5
27.5°	1441.5	1405.0	1407.1	1409.1	1409.1	1411.1	1433.4	1453.6	1475.9	1496.2	1556.9
30°	1455.7	1413.1	1409.1	1405.0	1401.0	1396.9	1427.3	1457.7	1488.1	1518.4	1565.0
32.5°	1504.2	1463.8	1453.6	1443.5	1433.4	1423.3	1459.7	1494.1	1530.6	1565.0	1603.5
35°	1556.9	1512.3	1508.3	1504.2	1498.2	1494.1	1526.5	1560.9	1593.3	1625.7	1660.1
37.5°	1635.8	1591.3	1587.3	1581.2	1577.1	1571.1	1607.5	1641.9	1678.4	1712.8	1743.1
40°	1753.3	1716.8	1714.8	1714.8	1712.8	1710.8	1739.1	1769.5	1797.8	1826.2	1846.4
42.5°	1909.2	1890.9	1897.0	1905.1	1911.2	1917.3	1939.5	1963.8	1986.1	2008.4	2002.3
45°	2133.9	2152.1	2154.1	2156.2	2158.2	2160.2	2166.3	2174.4	2180.5	2186.5	2162.2
47.5°	2393.0	2417.3	2429.5	2441.6	2451.7	2463.9	2455.8	2445.7	2437.6	2427.4	2366.7
50°	2700.8	2751.4	2749.4	2747.3	2743.3	2741.3	2725.1	2708.9	2690.6	2674.4	2585.4
52.5°	2943.7	3000.4	3010.5	3020.6	3030.8	3040.9	3010.5	2980.2	2947.8	2917.4	2806.0
55°	3204.9	3263.6	3265.6	3267.6	3267.6	3269.7	3227.2	3184.6	3140.1	3097.6	2982.2
57.5°	3399.2	3455.9	3449.9	3445.8	3439.7	3433.7	3383.0	3332.4	3281.8	3231.2	3115.8
60°	3472.1	3520.7	3508.6	3496.4	3482.2	3470.1	3431.6	3393.2	3352.7	3314.2	3202.9
62.5°	3437.7	3474.1	3455.9	3439.7	3421.5	3403.3	3354.7	3304.1	3255.5	3204.9	3123.9
65°	3211.0	3233.2	3208.9	3186.7	3164.4	3140.1	3099.6	3059.1	3016.6	2976.1	2921.4
67.5°	2828.3	2832.4	2830.3	2828.3	2826.3	2824.3	2765.6	2706.8	2646.1	2587.4	2583.3
70°	2304.0	2279.7	2283.7	2289.8	2293.8	2297.9	2253.3	2210.8	2166.3	2121.7	2142.0
72.5°	1777.6	1735.0	1745.2	1757.3	1767.4	1777.6	1741.1	1706.7	1670.3	1633.8	1662.2
75°	1320.0	1293.7	1303.8	1316.0	1326.1	1336.2	1322.0	1307.9	1291.7	1277.5	1303.8
77.5°	1006.2	990.0	992.0	992.0	994.1	994.1	996.1	1000.1	1002.2	1004.2	1032.5
80°	819.9	817.9	815.9	813.9	809.8	807.8	828.0	848.3	868.5	888.8	903.0
82.5°	716.7	736.9	724.8	714.7	702.5	690.4	708.6	726.8	745.0	763.3	757.2
85°	583.1	607.4	585.1	562.8	538.5	516.3	532.5	546.6	562.8	577.0	568.9
87.5°	230.8	236.9	200.4	166.0	129.6	93.1	147.8	200.4	255.1	307.7	315.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7	1457.7
2.5°	1573.1	1565.0	1558.9	1556.9	1552.8	1550.8	1546.8	1542.7	1536.6	1532.6	1526.5
5°	1625.7	1613.6	1599.4	1579.2	1560.9	1540.7	1520.4	1502.2	1484.0	1463.8	1445.5
7.5°	1627.7	1599.4	1571.1	1544.7	1516.4	1490.1	1461.7	1437.4	1411.1	1384.8	1360.5
10°	1605.5	1571.1	1536.6	1502.2	1469.8	1435.4	1401.0	1372.7	1342.3	1311.9	1283.6
12.5°	1587.3	1548.8	1510.3	1469.8	1431.4	1390.9	1350.4	1322.0	1293.7	1265.4	1237.0
15°	1565.0	1540.7	1518.4	1482.0	1445.5	1409.1	1372.7	1334.2	1297.7	1259.3	1220.8
17.5°	1546.8	1540.7	1534.6	1510.3	1486.0	1459.7	1435.4	1396.9	1358.5	1318.0	1279.5
20°	1536.6	1544.7	1552.8	1540.7	1528.5	1514.4	1502.2	1473.9	1445.5	1415.2	1386.8
22.5°	1548.8	1579.2	1607.5	1609.5	1613.6	1615.6	1617.6	1591.3	1565.0	1536.6	1510.3
25°	1577.1	1625.7	1674.3	1700.6	1727.0	1755.3	1781.6	1765.4	1749.2	1733.0	1716.8
27.5°	1615.6	1676.3	1737.1	1775.5	1812.0	1850.4	1888.9	1886.9	1884.9	1880.8	1878.8
30°	1609.5	1656.1	1702.7	1749.2	1795.8	1842.4	1888.9	1913.2	1935.5	1959.8	1984.1
32.5°	1643.9	1682.4	1722.9	1771.5	1820.1	1870.7	1919.3	1969.9	2018.5	2069.1	2119.7
35°	1696.6	1731.0	1767.4	1820.1	1874.7	1927.4	1982.0	2042.8	2105.5	2168.3	2229.0
37.5°	1775.5	1805.9	1838.3	1882.8	1929.4	1973.9	2020.5	2109.6	2198.7	2289.8	2378.9
40°	1866.6	1886.9	1907.1	1949.7	1992.2	2034.7	2077.2	2188.6	2299.9	2411.3	2522.6
42.5°	1998.2	1992.2	1986.1	2020.5	2057.0	2091.4	2127.8	2229.0	2330.3	2431.5	2532.7
45°	2137.9	2113.6	2089.3	2105.5	2123.8	2140.0	2158.2	2261.4	2364.7	2470.0	2573.2
47.5°	2306.0	2245.2	2184.5	2170.3	2156.2	2140.0	2125.8	2237.1	2348.5	2461.9	2573.2
50°	2496.3	2405.2	2316.1	2279.7	2241.2	2204.7	2166.3	2257.4	2350.5	2443.6	2534.8
52.5°	2694.7	2581.3	2470.0	2413.3	2356.6	2297.9	2241.2	2318.1	2397.1	2476.0	2553.0
55°	2864.8	2749.4	2631.9	2565.1	2498.3	2431.5	2364.7	2441.6	2518.6	2595.5	2672.4
57.5°	3000.4	2885.0	2769.6	2706.8	2642.1	2579.3	2514.5	2587.4	2662.3	2737.2	2810.1
60°	3093.5	2982.2	2870.8	2810.1	2749.4	2688.6	2627.9	2714.9	2802.0	2891.1	2978.1
62.5°	3044.9	2964.0	2883.0	2856.7	2830.3	2802.0	2775.7	2858.7	2939.7	3022.7	3105.7
65°	2866.8	2812.1	2757.5	2783.8	2812.1	2838.4	2866.8	2921.4	2976.1	3032.8	3087.5
67.5°	2577.3	2573.2	2567.1	2625.9	2684.6	2745.3	2804.0	2840.5	2874.9	2911.3	2947.8
70°	2162.2	2184.5	2204.7	2306.0	2407.2	2508.4	2609.7	2623.8	2638.0	2652.2	2666.3
72.5°	1692.5	1720.9	1751.2	1884.9	2016.5	2150.1	2283.7	2275.6	2267.5	2257.4	2249.3
75°	1332.2	1358.5	1386.8	1510.3	1633.8	1757.3	1880.8	1846.4	1814.0	1779.6	1745.2
77.5°	1062.9	1091.2	1121.6	1237.0	1352.4	1469.8	1585.2	1502.2	1419.2	1336.2	1253.2
80°	915.1	929.3	941.4	1020.4	1097.3	1176.3	1255.2	1170.2	1083.1	996.1	911.1
82.5°	751.1	743.0	736.9	783.5	830.1	876.6	923.2	842.2	761.2	678.2	597.2
85°	560.8	552.7	544.6	568.9	593.2	619.5	643.8	550.7	457.6	362.4	269.3
87.5°	326.0	334.1	342.2	368.5	394.8	423.1	449.5	354.3	259.1	162.0	66.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671814
 CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1457.7	1457.7
2.5°	1514.4	1504.2
5°	1431.4	1417.2
7.5°	1340.3	1322.0
10°	1257.3	1233.0
12.5°	1204.6	1174.2
15°	1184.4	1147.9
17.5°	1245.1	1210.7
20°	1338.2	1291.7
22.5°	1451.6	1394.9
25°	1648.0	1579.2
27.5°	1807.9	1737.1
30°	1907.1	1830.2
32.5°	2016.5	1915.2
35°	2129.8	2032.7
37.5°	2267.5	2158.2
40°	2409.2	2295.9
42.5°	2457.8	2384.9
45°	2504.4	2435.5
47.5°	2514.5	2457.8
50°	2524.6	2516.5
52.5°	2553.0	2550.9
55°	2674.4	2676.5
57.5°	2824.3	2836.4
60°	2961.9	2947.8
62.5°	3032.8	2959.9
65°	2984.2	2883.0
67.5°	2838.4	2729.1
70°	2518.6	2370.8
72.5°	2119.7	1990.1
75°	1633.8	1524.5
77.5°	1162.1	1071.0
80°	817.9	726.8
82.5°	524.4	451.5
85°	236.9	206.5
87.5°	66.8	64.8
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P671814

CATALOG NUMBER: CCP-SA-1D-735-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)