

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671827

Luminaire Tested: **CCP-SA-1F-740-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671827
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1F-740-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @1200mA w/ SLR
distribution lens
Light Source: (16) 4000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6222.1 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 67
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 8.8 fc

Type IV - Short - N/A

REPORT NUMBER: P671827
CATALOG NUMBER: CCP-SA-1F-740-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1280.2	0.0	1280.2
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	4941.9	0.0	4941.9
	% Fixture	79.4	0.0	79.4
Total	Lumens	6222.1	0.0	6222.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.4	2.5
10°-20°	326.0	5.2
20°-30°	476.9	7.7
30°-40°	671.9	10.8
40°-50°	923.3	14.8
50°-60°	1258.4	20.2
60°-70°	1377.4	22.1
70°-80°	795.4	12.8
80°-90°	238.4	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6222.1	100.0
0°-180°	6222.1	100.0

Coefficient of Utilization



REPORT NUMBER: P671827


CATALOG NUMBER: CCP-SA-1F-740-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	639.0	10.3			
FM	(30°-60°)	2270.6	36.5			
FH	(60°-80°)	1829.7	29.4			G2/5000
FVH	(80°-90°)	202.5	3.3			G2/225
BL	(0°-30°)	318.3	5.1	B1/500		
BM	(30°-60°)	583.0	9.4	B1/1000		
BH	(60°-80°)	343.1	5.5	B1/500		G1/500
BVH	(80°-90°)	35.9	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	2050.4	2039.4	2031.1	2022.8	2011.8	2003.5	1992.5	1981.4	1967.6	1956.6	1942.8
5°	1931.8	1898.6	1865.5	1846.2	1824.1	1804.8	1782.7	1757.9	1733.1	1705.5	1680.6
7.5°	1802.1	1760.7	1719.3	1686.2	1650.3	1617.2	1581.3	1550.9	1520.6	1490.2	1459.9
10°	1680.6	1642.0	1603.4	1562.0	1517.8	1476.4	1432.3	1390.9	1349.5	1308.1	1266.7
12.5°	1600.6	1553.7	1509.5	1462.6	1418.5	1371.6	1324.6	1286.0	1247.4	1206.0	1167.3
15°	1564.7	1520.6	1479.2	1432.3	1385.4	1338.4	1291.5	1247.4	1206.0	1161.8	1117.7
17.5°	1650.3	1586.8	1523.3	1462.6	1401.9	1341.2	1280.5	1225.3	1170.1	1114.9	1059.7
20°	1760.7	1680.6	1603.4	1528.9	1451.6	1377.1	1299.8	1222.5	1145.3	1068.0	990.7
22.5°	1901.4	1810.3	1722.0	1625.4	1526.1	1429.5	1330.2	1233.6	1137.0	1037.6	941.0
25°	2152.5	2044.9	1937.3	1799.3	1658.6	1520.6	1379.8	1252.9	1128.7	1001.8	874.8
27.5°	2367.8	2221.5	2078.0	1912.4	1746.9	1581.3	1415.7	1269.4	1125.9	979.7	833.4
30°	2494.7	2351.2	2207.7	2006.3	1807.6	1606.1	1404.7	1241.8	1081.8	919.0	756.1
32.5°	2610.6	2450.6	2290.5	2069.7	1846.2	1625.4	1401.9	1222.5	1045.9	866.5	687.2
35°	2770.7	2594.1	2420.2	2163.6	1906.9	1650.3	1393.6	1208.7	1021.1	836.2	648.5
37.5°	2941.8	2723.8	2508.5	2224.3	1940.0	1655.8	1371.6	1189.4	1007.3	825.1	643.0
40°	3129.5	2864.5	2602.4	2287.8	1975.9	1661.3	1346.7	1164.6	982.4	797.5	615.4
42.5°	3250.9	2963.9	2676.9	2337.4	2000.8	1661.3	1321.9	1142.5	963.1	781.0	601.6
45°	3319.9	3041.2	2765.2	2398.1	2031.1	1664.1	1297.0	1120.4	943.8	764.4	587.8
47.5°	3350.2	3090.8	2831.4	2445.1	2061.5	1675.1	1288.8	1109.4	927.2	747.9	565.7
50°	3430.3	3201.2	2972.2	2558.2	2147.0	1733.1	1319.1	1125.9	935.5	742.3	549.2
52.5°	3477.2	3281.2	3085.3	2660.3	2235.3	1810.3	1385.4	1170.1	954.8	739.6	524.3
55°	3648.3	3460.6	3273.0	2820.4	2365.0	1912.4	1457.1	1219.8	982.4	742.3	505.0
57.5°	3866.3	3667.6	3471.7	2983.2	2494.7	2006.3	1517.8	1263.9	1007.3	753.4	496.7
60°	4018.1	3824.9	3634.5	3115.7	2594.1	2075.3	1553.7	1288.8	1023.8	756.1	491.2
62.5°	4034.6	3786.3	3540.6	3035.6	2530.6	2022.8	1517.8	1261.2	1004.5	745.1	488.5
65°	3929.8	3640.0	3350.2	2867.3	2384.4	1901.4	1418.5	1183.9	949.3	712.0	477.4
67.5°	3720.0	3380.6	3041.2	2599.6	2158.1	1716.5	1275.0	1073.5	874.8	673.4	471.9
70°	3231.6	2933.5	2638.2	2254.6	1873.8	1490.2	1106.6	941.0	778.2	612.6	447.1
72.5°	2712.8	2434.0	2158.1	1846.2	1537.1	1225.3	913.4	789.3	665.1	538.1	413.9
75°	2078.0	1868.3	1661.3	1429.5	1197.7	963.1	731.3	640.2	549.2	458.1	367.0
77.5°	1459.9	1346.7	1236.3	1062.5	888.6	714.8	540.9	480.2	419.5	358.8	298.0
80°	990.7	927.2	866.5	742.3	618.2	491.2	367.0	328.4	287.0	248.4	207.0
82.5°	615.4	612.6	607.1	521.6	436.0	350.5	264.9	231.8	201.5	168.3	135.2
85°	281.5	328.4	372.6	325.6	278.7	231.8	184.9	162.8	140.7	115.9	93.8
87.5°	88.3	107.6	124.2	118.7	110.4	104.9	96.6	82.8	69.0	55.2	41.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	1931.8	1923.5	1912.4	1901.4	1887.6	1876.6	1862.8	1849.0	1846.2	1840.7	1837.9
5°	1664.1	1647.5	1628.2	1611.6	1595.1	1575.8	1559.2	1539.9	1526.1	1509.5	1495.7
7.5°	1429.5	1401.9	1371.6	1341.2	1313.6	1286.0	1255.6	1228.1	1214.3	1200.5	1186.7
10°	1241.8	1214.3	1189.4	1161.8	1142.5	1125.9	1106.6	1087.3	1070.7	1054.2	1037.6
12.5°	1148.0	1128.7	1109.4	1090.1	1068.0	1048.7	1026.6	1004.5	985.2	968.6	949.3
15°	1090.1	1062.5	1032.1	1004.5	974.2	946.6	916.2	885.9	863.8	844.5	822.4
17.5°	1021.1	979.7	941.0	899.7	866.5	833.4	797.5	764.4	739.6	712.0	687.2
20°	943.8	896.9	847.2	800.3	761.7	725.8	687.2	648.5	620.9	590.6	563.0
22.5°	877.6	816.9	753.4	689.9	648.5	607.1	563.0	521.6	496.7	469.1	444.3
25°	805.8	739.6	670.6	601.6	560.2	516.1	474.7	430.5	411.2	394.6	375.3
27.5°	767.2	701.0	632.0	565.7	527.1	485.7	447.1	405.7	391.9	375.3	361.5
30°	689.9	626.4	560.2	494.0	466.4	441.5	413.9	386.4	380.8	378.1	372.6
32.5°	620.9	554.7	488.5	422.2	397.4	372.6	347.7	322.9	320.1	314.6	311.8
35°	585.0	521.6	455.3	391.9	369.8	345.0	322.9	298.0	292.5	284.2	278.7
37.5°	576.8	510.5	441.5	375.3	353.2	331.2	306.3	284.2	278.7	273.2	267.7
40°	554.7	491.2	430.5	367.0	345.0	322.9	298.0	276.0	270.4	264.9	259.4
42.5°	538.1	477.4	413.9	350.5	331.2	311.8	289.8	270.4	264.9	259.4	251.1
45°	524.3	460.9	394.6	331.2	317.4	303.6	287.0	273.2	267.7	259.4	253.9
47.5°	502.3	441.5	378.1	314.6	300.8	289.8	276.0	262.2	256.6	251.1	245.6
50°	485.7	422.2	358.8	295.3	284.2	273.2	262.2	251.1	251.1	253.9	253.9
52.5°	463.6	402.9	342.2	281.5	270.4	259.4	248.4	237.3	240.1	242.9	245.6
55°	444.3	386.4	325.6	264.9	253.9	242.9	229.1	218.0	220.8	223.5	226.3
57.5°	436.0	375.3	314.6	253.9	242.9	229.1	218.0	204.2	204.2	204.2	204.2
60°	430.5	367.0	306.3	242.9	229.1	218.0	204.2	190.4	187.7	187.7	184.9
62.5°	427.7	364.3	303.6	240.1	223.5	209.7	193.2	176.6	173.9	171.1	168.3
65°	416.7	358.8	298.0	237.3	218.0	201.5	182.1	162.8	160.1	160.1	157.3
67.5°	413.9	353.2	295.3	234.6	215.3	193.2	173.9	151.8	149.0	146.3	143.5
70°	391.9	339.4	284.2	229.1	207.0	187.7	165.6	143.5	140.7	135.2	132.5
72.5°	364.3	317.4	267.7	218.0	195.9	173.9	151.8	129.7	126.9	124.2	118.7
75°	322.9	278.7	234.6	190.4	171.1	154.5	135.2	115.9	113.1	110.4	104.9
77.5°	264.9	229.1	195.9	160.1	146.3	132.5	118.7	104.9	102.1	99.3	93.8
80°	187.7	165.6	146.3	124.2	115.9	104.9	96.6	85.5	85.5	82.8	82.8
82.5°	124.2	113.1	102.1	91.1	85.5	80.0	74.5	69.0	69.0	66.2	66.2
85°	88.3	82.8	74.5	69.0	66.2	60.7	58.0	52.4	52.4	52.4	52.4
87.5°	41.4	41.4	38.6	38.6	35.9	35.9	33.1	30.4	30.4	30.4	30.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	1832.4	1824.1	1815.9	1804.8	1796.5	1785.5	1771.7	1760.7	1746.9	1746.9	1744.1
5°	1479.2	1470.9	1462.6	1451.6	1443.3	1432.3	1424.0	1412.9	1401.9	1401.9	1399.2
7.5°	1172.9	1156.3	1139.7	1120.4	1103.9	1092.8	1081.8	1068.0	1057.0	1048.7	1040.4
10°	1021.1	1004.5	985.2	968.6	949.3	935.5	921.7	905.2	891.4	880.3	869.3
12.5°	930.0	910.7	891.4	872.1	852.7	833.4	816.9	797.5	778.2	764.4	750.6
15°	800.3	781.0	761.7	742.3	723.0	701.0	678.9	654.0	632.0	620.9	612.6
17.5°	659.6	640.2	618.2	598.8	576.8	560.2	543.7	527.1	510.5	499.5	491.2
20°	532.6	510.5	488.5	466.4	444.3	433.3	422.2	411.2	400.2	391.9	386.4
22.5°	416.7	402.9	391.9	378.1	364.3	356.0	350.5	342.2	333.9	333.9	333.9
25°	356.0	347.7	342.2	333.9	325.6	322.9	320.1	314.6	311.8	309.1	309.1
27.5°	345.0	336.7	328.4	320.1	311.8	309.1	306.3	300.8	298.0	298.0	298.0
30°	367.0	364.3	361.5	358.8	356.0	350.5	342.2	336.7	328.4	322.9	317.4
32.5°	306.3	303.6	303.6	300.8	298.0	303.6	306.3	311.8	314.6	317.4	320.1
35°	270.4	264.9	259.4	253.9	248.4	245.6	242.9	240.1	237.3	237.3	234.6
37.5°	262.2	256.6	251.1	245.6	240.1	237.3	234.6	231.8	229.1	229.1	226.3
40°	253.9	248.4	245.6	240.1	234.6	231.8	229.1	223.5	220.8	218.0	218.0
42.5°	245.6	242.9	237.3	234.6	229.1	226.3	223.5	218.0	215.3	212.5	209.7
45°	245.6	240.1	234.6	229.1	223.5	220.8	215.3	212.5	207.0	207.0	204.2
47.5°	240.1	234.6	229.1	223.5	218.0	215.3	209.7	207.0	201.5	198.7	195.9
50°	253.9	245.6	234.6	226.3	215.3	212.5	207.0	204.2	198.7	195.9	193.2
52.5°	248.4	240.1	229.1	220.8	209.7	204.2	201.5	195.9	190.4	187.7	184.9
55°	229.1	220.8	215.3	207.0	198.7	193.2	187.7	182.1	176.6	173.9	173.9
57.5°	204.2	201.5	198.7	195.9	193.2	187.7	182.1	173.9	168.3	165.6	162.8
60°	182.1	184.9	187.7	190.4	193.2	184.9	176.6	168.3	160.1	157.3	154.5
62.5°	165.6	171.1	176.6	179.4	184.9	176.6	168.3	160.1	151.8	149.0	146.3
65°	154.5	157.3	157.3	160.1	160.1	154.5	151.8	146.3	140.7	138.0	138.0
67.5°	140.7	140.7	140.7	138.0	138.0	135.2	135.2	132.5	129.7	126.9	126.9
70°	126.9	126.9	126.9	124.2	124.2	121.4	121.4	118.7	115.9	115.9	113.1
72.5°	115.9	115.9	113.1	113.1	110.4	110.4	110.4	107.6	107.6	104.9	104.9
75°	102.1	102.1	99.3	99.3	96.6	96.6	96.6	93.8	93.8	93.8	91.1
77.5°	91.1	91.1	88.3	88.3	85.5	85.5	85.5	82.8	82.8	80.0	80.0
80°	80.0	80.0	77.3	77.3	74.5	74.5	71.8	71.8	69.0	69.0	66.2
82.5°	63.5	63.5	63.5	63.5	63.5	60.7	60.7	58.0	55.2	55.2	52.4
85°	52.4	52.4	52.4	49.7	49.7	49.7	46.9	46.9	44.2	41.4	41.4
87.5°	30.4	30.4	30.4	27.6	27.6	27.6	27.6	27.6	27.6	27.6	24.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	1744.1	1741.3	1730.3	1719.3	1730.3	1741.3	1741.3	1741.3	1738.6	1738.6	1738.6
5°	1399.2	1396.4	1390.9	1385.4	1385.4	1382.6	1388.1	1393.6	1399.2	1404.7	1410.2
7.5°	1029.4	1021.1	1012.8	1004.5	1010.0	1012.8	1021.1	1026.6	1034.9	1040.4	1054.2
10°	858.3	847.2	838.9	830.7	825.1	819.6	814.1	811.3	805.8	800.3	805.8
12.5°	734.1	720.3	706.5	689.9	687.2	684.4	678.9	673.4	667.8	662.3	659.6
15°	601.6	590.6	585.0	576.8	565.7	554.7	549.2	546.4	540.9	535.4	532.6
17.5°	480.2	469.1	460.9	452.6	449.8	444.3	444.3	444.3	444.3	444.3	444.3
20°	378.1	369.8	369.8	367.0	367.0	364.3	367.0	369.8	369.8	372.6	375.3
22.5°	331.2	331.2	328.4	325.6	328.4	328.4	331.2	333.9	336.7	339.4	342.2
25°	306.3	303.6	306.3	309.1	309.1	309.1	311.8	311.8	314.6	314.6	314.6
27.5°	295.3	295.3	298.0	298.0	300.8	300.8	300.8	298.0	298.0	295.3	295.3
30°	311.8	306.3	306.3	306.3	303.6	300.8	298.0	298.0	295.3	292.5	289.8
32.5°	322.9	325.6	322.9	317.4	314.6	309.1	306.3	300.8	298.0	292.5	287.0
35°	234.6	231.8	237.3	240.1	242.9	245.6	248.4	251.1	251.1	253.9	253.9
37.5°	226.3	223.5	223.5	220.8	220.8	220.8	220.8	220.8	218.0	218.0	220.8
40°	215.3	212.5	212.5	209.7	209.7	207.0	207.0	207.0	207.0	207.0	207.0
42.5°	207.0	204.2	204.2	204.2	204.2	201.5	201.5	198.7	198.7	195.9	195.9
45°	204.2	201.5	198.7	195.9	195.9	193.2	193.2	193.2	190.4	190.4	190.4
47.5°	193.2	190.4	190.4	187.7	187.7	184.9	184.9	184.9	182.1	182.1	182.1
50°	187.7	184.9	184.9	182.1	182.1	179.4	179.4	179.4	176.6	176.6	176.6
52.5°	179.4	176.6	176.6	176.6	173.9	171.1	171.1	171.1	168.3	168.3	168.3
55°	171.1	168.3	168.3	168.3	165.6	162.8	162.8	162.8	160.1	160.1	160.1
57.5°	160.1	157.3	157.3	154.5	154.5	154.5	154.5	154.5	151.8	151.8	151.8
60°	151.8	149.0	149.0	146.3	146.3	143.5	143.5	143.5	143.5	143.5	143.5
62.5°	143.5	140.7	138.0	135.2	138.0	138.0	138.0	138.0	135.2	135.2	135.2
65°	135.2	132.5	129.7	126.9	126.9	126.9	126.9	126.9	126.9	126.9	126.9
67.5°	124.2	121.4	118.7	115.9	118.7	118.7	118.7	118.7	118.7	118.7	118.7
70°	113.1	110.4	110.4	107.6	107.6	104.9	104.9	107.6	107.6	107.6	107.6
72.5°	102.1	99.3	99.3	96.6	96.6	96.6	96.6	96.6	96.6	96.6	96.6
75°	91.1	88.3	88.3	85.5	85.5	85.5	85.5	85.5	85.5	85.5	85.5
77.5°	77.3	74.5	74.5	74.5	74.5	74.5	74.5	77.3	77.3	77.3	77.3
80°	66.2	63.5	63.5	63.5	63.5	63.5	63.5	63.5	63.5	63.5	63.5
82.5°	52.4	49.7	49.7	49.7	49.7	49.7	49.7	49.7	49.7	49.7	49.7
85°	38.6	35.9	35.9	35.9	38.6	38.6	38.6	38.6	38.6	38.6	38.6
87.5°	24.8	22.1	22.1	22.1	24.8	24.8	24.8	24.8	22.1	22.1	22.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	1738.6	1738.6	1738.6	1735.8	1733.1	1730.3	1727.6	1735.8	1741.3	1749.6	1755.1
5°	1412.9	1418.5	1421.2	1429.5	1437.8	1446.1	1454.3	1459.9	1465.4	1468.1	1473.7
7.5°	1065.2	1079.0	1090.1	1101.1	1112.1	1120.4	1131.5	1139.7	1148.0	1156.3	1164.6
10°	808.6	814.1	816.9	827.9	836.2	847.2	855.5	863.8	872.1	877.6	885.9
12.5°	656.8	651.3	648.5	648.5	648.5	648.5	648.5	654.0	659.6	665.1	670.6
15°	529.9	527.1	524.3	521.6	518.8	513.3	510.5	516.1	521.6	527.1	532.6
17.5°	444.3	444.3	444.3	441.5	438.8	436.0	433.3	436.0	438.8	438.8	441.5
20°	380.8	383.6	386.4	389.1	389.1	391.9	391.9	394.6	397.4	397.4	400.2
22.5°	342.2	345.0	345.0	345.0	347.7	347.7	347.7	350.5	353.2	356.0	358.8
25°	311.8	311.8	309.1	309.1	311.8	311.8	311.8	311.8	314.6	314.6	314.6
27.5°	295.3	292.5	292.5	292.5	292.5	289.8	289.8	289.8	289.8	289.8	289.8
30°	287.0	284.2	281.5	278.7	278.7	276.0	273.2	273.2	273.2	273.2	273.2
32.5°	284.2	278.7	273.2	270.4	270.4	267.7	264.9	262.2	262.2	259.4	256.6
35°	253.9	251.1	251.1	248.4	245.6	242.9	240.1	240.1	240.1	237.3	237.3
37.5°	220.8	223.5	223.5	223.5	226.3	226.3	226.3	226.3	229.1	229.1	229.1
40°	207.0	207.0	207.0	209.7	212.5	212.5	215.3	215.3	218.0	218.0	218.0
42.5°	195.9	193.2	193.2	195.9	195.9	198.7	198.7	201.5	204.2	204.2	207.0
45°	190.4	187.7	187.7	187.7	187.7	184.9	184.9	187.7	190.4	193.2	195.9
47.5°	179.4	179.4	176.6	176.6	176.6	176.6	176.6	176.6	179.4	179.4	179.4
50°	173.9	173.9	171.1	171.1	171.1	171.1	171.1	171.1	171.1	171.1	171.1
52.5°	168.3	165.6	165.6	165.6	165.6	162.8	162.8	162.8	162.8	162.8	162.8
55°	160.1	157.3	157.3	157.3	157.3	157.3	157.3	157.3	160.1	160.1	160.1
57.5°	151.8	149.0	149.0	149.0	151.8	151.8	151.8	151.8	154.5	154.5	154.5
60°	143.5	143.5	143.5	143.5	143.5	143.5	143.5	146.3	146.3	149.0	149.0
62.5°	135.2	135.2	135.2	135.2	138.0	138.0	138.0	138.0	140.7	140.7	140.7
65°	126.9	126.9	126.9	126.9	129.7	129.7	129.7	129.7	129.7	129.7	129.7
67.5°	118.7	118.7	118.7	118.7	118.7	118.7	118.7	121.4	121.4	124.2	124.2
70°	107.6	104.9	104.9	107.6	107.6	110.4	110.4	113.1	113.1	115.9	115.9
72.5°	96.6	96.6	96.6	96.6	96.6	96.6	96.6	99.3	102.1	102.1	104.9
75°	85.5	85.5	85.5	85.5	88.3	88.3	88.3	91.1	91.1	93.8	93.8
77.5°	77.3	74.5	74.5	74.5	77.3	77.3	77.3	80.0	80.0	82.8	82.8
80°	63.5	63.5	63.5	63.5	66.2	66.2	66.2	66.2	69.0	69.0	69.0
82.5°	52.4	52.4	52.4	52.4	52.4	52.4	52.4	52.4	55.2	55.2	55.2
85°	38.6	38.6	38.6	38.6	41.4	41.4	41.4	41.4	41.4	41.4	41.4
87.5°	24.8	24.8	24.8	24.8	24.8	24.8	24.8	24.8	27.6	27.6	27.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	1755.1	1755.1	1755.1	1755.1	1760.7	1763.4	1768.9	1771.7	1768.9	1766.2	1760.7
5°	1476.4	1479.2	1479.2	1481.9	1481.9	1481.9	1481.9	1481.9	1487.5	1493.0	1498.5
7.5°	1167.3	1170.1	1172.9	1175.6	1175.6	1175.6	1172.9	1172.9	1175.6	1175.6	1178.4
10°	894.1	905.2	913.4	921.7	916.2	907.9	902.4	894.1	894.1	894.1	891.4
12.5°	676.1	678.9	684.4	687.2	684.4	684.4	681.6	678.9	681.6	687.2	689.9
15°	535.4	535.4	538.1	538.1	540.9	543.7	543.7	546.4	551.9	554.7	560.2
17.5°	444.3	447.1	447.1	449.8	449.8	452.6	452.6	452.6	458.1	463.6	471.9
20°	400.2	400.2	400.2	400.2	400.2	397.4	397.4	394.6	397.4	402.9	405.7
22.5°	358.8	361.5	361.5	361.5	358.8	356.0	350.5	347.7	347.7	350.5	350.5
25°	314.6	311.8	311.8	309.1	309.1	311.8	311.8	311.8	314.6	314.6	317.4
27.5°	289.8	287.0	287.0	284.2	284.2	287.0	287.0	287.0	287.0	287.0	287.0
30°	270.4	270.4	267.7	264.9	267.7	267.7	270.4	270.4	273.2	273.2	276.0
32.5°	256.6	253.9	253.9	251.1	253.9	253.9	256.6	256.6	259.4	262.2	262.2
35°	237.3	237.3	237.3	237.3	237.3	237.3	234.6	234.6	234.6	234.6	234.6
37.5°	226.3	226.3	223.5	220.8	220.8	220.8	220.8	220.8	218.0	215.3	212.5
40°	218.0	215.3	215.3	212.5	209.7	209.7	207.0	204.2	204.2	201.5	201.5
42.5°	207.0	204.2	204.2	201.5	198.7	198.7	195.9	193.2	193.2	193.2	190.4
45°	193.2	193.2	190.4	187.7	187.7	187.7	184.9	184.9	184.9	184.9	182.1
47.5°	179.4	179.4	176.6	176.6	176.6	176.6	173.9	173.9	173.9	173.9	173.9
50°	171.1	171.1	171.1	171.1	171.1	171.1	168.3	168.3	168.3	168.3	168.3
52.5°	162.8	162.8	162.8	162.8	162.8	162.8	162.8	162.8	162.8	162.8	162.8
55°	160.1	160.1	160.1	160.1	160.1	160.1	157.3	157.3	157.3	160.1	160.1
57.5°	154.5	154.5	151.8	151.8	151.8	151.8	151.8	151.8	151.8	151.8	151.8
60°	149.0	149.0	149.0	149.0	149.0	149.0	149.0	149.0	149.0	149.0	149.0
62.5°	140.7	140.7	140.7	140.7	140.7	143.5	143.5	143.5	143.5	143.5	140.7
65°	129.7	132.5	132.5	132.5	132.5	132.5	132.5	132.5	132.5	132.5	132.5
67.5°	124.2	124.2	124.2	124.2	124.2	124.2	124.2	124.2	124.2	124.2	124.2
70°	115.9	115.9	113.1	113.1	113.1	115.9	115.9	115.9	115.9	115.9	115.9
72.5°	104.9	104.9	104.9	104.9	104.9	104.9	104.9	104.9	104.9	107.6	107.6
75°	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8
77.5°	82.8	82.8	80.0	80.0	80.0	82.8	82.8	82.8	82.8	85.5	85.5
80°	69.0	69.0	69.0	69.0	69.0	69.0	69.0	69.0	69.0	71.8	71.8
82.5°	55.2	55.2	55.2	55.2	55.2	55.2	55.2	55.2	55.2	58.0	58.0
85°	41.4	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2	46.9	46.9
87.5°	27.6	27.6	27.6	27.6	27.6	27.6	24.8	24.8	24.8	24.8	22.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	1757.9	1760.7	1763.4	1763.4	1766.2	1768.9	1768.9	1780.0	1791.0	1796.5	1802.1
5°	1504.0	1501.3	1501.3	1498.5	1495.7	1504.0	1512.3	1528.9	1545.4	1548.2	1553.7
7.5°	1178.4	1181.1	1183.9	1183.9	1186.7	1178.4	1167.3	1170.1	1172.9	1186.7	1197.7
10°	891.4	894.1	896.9	896.9	899.7	896.9	891.4	899.7	907.9	919.0	932.8
12.5°	692.7	701.0	709.2	714.8	723.0	728.6	731.3	742.3	750.6	764.4	778.2
15°	565.7	571.3	576.8	582.3	587.8	593.3	598.8	609.9	620.9	637.5	654.0
17.5°	477.4	477.4	480.2	480.2	480.2	485.7	491.2	496.7	499.5	516.1	532.6
20°	408.4	405.7	402.9	400.2	397.4	402.9	405.7	408.4	411.2	422.2	430.5
22.5°	350.5	350.5	353.2	353.2	353.2	350.5	345.0	347.7	347.7	353.2	361.5
25°	317.4	317.4	317.4	314.6	314.6	317.4	320.1	320.1	317.4	320.1	322.9
27.5°	287.0	289.8	289.8	292.5	292.5	295.3	295.3	295.3	295.3	298.0	300.8
30°	276.0	276.0	278.7	278.7	278.7	281.5	284.2	284.2	284.2	287.0	292.5
32.5°	264.9	267.7	270.4	273.2	276.0	278.7	278.7	281.5	281.5	284.2	287.0
35°	234.6	231.8	231.8	229.1	226.3	226.3	226.3	226.3	223.5	226.3	226.3
37.5°	209.7	209.7	209.7	207.0	207.0	209.7	209.7	209.7	209.7	212.5	212.5
40°	198.7	198.7	198.7	198.7	198.7	198.7	198.7	201.5	201.5	204.2	207.0
42.5°	190.4	190.4	190.4	190.4	190.4	193.2	193.2	193.2	193.2	195.9	195.9
45°	182.1	182.1	182.1	182.1	182.1	182.1	182.1	184.9	184.9	187.7	190.4
47.5°	173.9	173.9	173.9	173.9	173.9	176.6	179.4	179.4	179.4	182.1	182.1
50°	168.3	168.3	168.3	168.3	168.3	171.1	171.1	173.9	173.9	176.6	179.4
52.5°	162.8	162.8	162.8	162.8	162.8	165.6	165.6	168.3	168.3	171.1	173.9
55°	160.1	160.1	160.1	157.3	157.3	160.1	160.1	162.8	162.8	165.6	165.6
57.5°	151.8	151.8	151.8	151.8	151.8	151.8	151.8	154.5	154.5	157.3	160.1
60°	149.0	149.0	146.3	146.3	143.5	146.3	146.3	149.0	149.0	151.8	151.8
62.5°	140.7	140.7	140.7	138.0	138.0	140.7	140.7	140.7	140.7	143.5	146.3
65°	132.5	132.5	132.5	129.7	129.7	132.5	132.5	132.5	132.5	135.2	138.0
67.5°	124.2	124.2	124.2	121.4	121.4	121.4	121.4	124.2	124.2	126.9	129.7
70°	115.9	115.9	115.9	113.1	113.1	113.1	110.4	113.1	115.9	118.7	118.7
72.5°	107.6	107.6	107.6	104.9	104.9	104.9	102.1	104.9	104.9	107.6	107.6
75°	93.8	93.8	93.8	93.8	93.8	93.8	91.1	91.1	91.1	93.8	93.8
77.5°	85.5	85.5	85.5	82.8	82.8	82.8	80.0	80.0	80.0	82.8	82.8
80°	71.8	71.8	71.8	69.0	69.0	69.0	66.2	66.2	66.2	69.0	69.0
82.5°	58.0	58.0	58.0	55.2	55.2	55.2	52.4	52.4	52.4	55.2	55.2
85°	46.9	46.9	46.9	46.9	46.9	46.9	44.2	44.2	44.2	46.9	49.7
87.5°	22.1	22.1	24.8	24.8	24.8	24.8	22.1	22.1	19.3	19.3	22.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	1807.6	1813.1	1826.9	1837.9	1851.7	1862.8	1871.1	1882.1	1890.4	1898.6	1904.2
5°	1556.5	1559.2	1573.0	1586.8	1597.8	1611.6	1631.0	1650.3	1669.6	1688.9	1702.7
7.5°	1211.5	1222.5	1239.1	1258.4	1275.0	1291.5	1310.8	1332.9	1352.2	1371.6	1390.9
10°	943.8	954.8	971.4	988.0	1001.8	1018.3	1040.4	1062.5	1084.5	1106.6	1128.7
12.5°	792.0	805.8	825.1	844.5	861.0	880.3	907.9	932.8	960.4	985.2	1012.8
15°	667.8	684.4	709.2	736.8	761.7	786.5	814.1	841.7	866.5	894.1	921.7
17.5°	549.2	565.7	587.8	612.6	634.7	656.8	689.9	720.3	753.4	783.7	814.1
20°	441.5	449.8	471.9	494.0	516.1	538.1	563.0	587.8	612.6	637.5	676.1
22.5°	367.0	372.6	383.6	391.9	402.9	411.2	436.0	460.9	482.9	507.8	543.7
25°	322.9	325.6	333.9	339.4	347.7	353.2	369.8	383.6	400.2	413.9	447.1
27.5°	300.8	303.6	306.3	309.1	311.8	314.6	325.6	336.7	345.0	356.0	386.4
30°	295.3	298.0	306.3	311.8	320.1	325.6	331.2	336.7	342.2	347.7	367.0
32.5°	289.8	292.5	292.5	289.8	289.8	287.0	292.5	295.3	300.8	303.6	320.1
35°	229.1	229.1	231.8	234.6	237.3	240.1	248.4	253.9	262.2	267.7	281.5
37.5°	215.3	215.3	218.0	223.5	226.3	229.1	234.6	240.1	245.6	251.1	264.9
40°	207.0	209.7	212.5	215.3	218.0	220.8	226.3	229.1	234.6	237.3	248.4
42.5°	198.7	198.7	201.5	207.0	209.7	212.5	218.0	220.8	226.3	229.1	240.1
45°	193.2	195.9	198.7	201.5	201.5	204.2	209.7	215.3	218.0	223.5	234.6
47.5°	184.9	184.9	190.4	193.2	198.7	201.5	207.0	209.7	215.3	218.0	229.1
50°	179.4	182.1	187.7	190.4	195.9	198.7	207.0	212.5	220.8	226.3	231.8
52.5°	173.9	176.6	182.1	184.9	190.4	193.2	204.2	215.3	223.5	234.6	234.6
55°	168.3	168.3	173.9	182.1	187.7	193.2	198.7	207.0	212.5	218.0	218.0
57.5°	160.1	162.8	168.3	176.6	182.1	187.7	193.2	198.7	201.5	207.0	204.2
60°	154.5	154.5	162.8	171.1	179.4	187.7	187.7	187.7	184.9	184.9	184.9
62.5°	146.3	149.0	160.1	173.9	184.9	195.9	187.7	179.4	171.1	162.8	165.6
65°	140.7	143.5	149.0	157.3	162.8	168.3	162.8	160.1	154.5	149.0	151.8
67.5°	129.7	132.5	135.2	135.2	138.0	138.0	138.0	138.0	138.0	138.0	140.7
70°	121.4	121.4	121.4	124.2	124.2	124.2	124.2	124.2	124.2	124.2	126.9
72.5°	110.4	110.4	110.4	110.4	110.4	110.4	110.4	110.4	110.4	110.4	113.1
75°	96.6	96.6	96.6	96.6	96.6	96.6	96.6	96.6	96.6	96.6	99.3
77.5°	85.5	85.5	85.5	85.5	85.5	85.5	85.5	85.5	82.8	82.8	85.5
80°	71.8	71.8	71.8	71.8	69.0	69.0	69.0	69.0	69.0	69.0	71.8
82.5°	58.0	58.0	58.0	58.0	55.2	55.2	55.2	55.2	52.4	52.4	55.2
85°	52.4	55.2	55.2	58.0	58.0	58.0	55.2	52.4	49.7	46.9	46.9
87.5°	22.1	22.1	22.1	22.1	19.3	19.3	19.3	19.3	19.3	19.3	19.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	1912.4	1918.0	1923.5	1931.8	1942.8	1951.1	1959.4	1975.9	1995.2	2011.8	2028.4
5°	1716.5	1730.3	1744.1	1760.7	1777.2	1791.0	1807.6	1840.7	1873.8	1904.2	1937.3
7.5°	1407.4	1426.7	1443.3	1470.9	1495.7	1523.3	1548.2	1589.6	1628.2	1669.6	1708.2
10°	1150.8	1172.9	1194.9	1230.8	1269.4	1305.3	1341.2	1374.3	1410.2	1443.3	1476.4
12.5°	1040.4	1065.2	1092.8	1114.9	1139.7	1161.8	1183.9	1222.5	1261.2	1299.8	1338.4
15°	949.3	976.9	1004.5	1032.1	1057.0	1084.5	1109.4	1142.5	1178.4	1211.5	1244.6
17.5°	844.5	872.1	902.4	932.8	963.1	993.5	1023.8	1070.7	1117.7	1161.8	1208.7
20°	712.0	750.6	786.5	827.9	869.3	910.7	952.1	1001.8	1051.4	1098.3	1148.0
22.5°	579.5	615.4	651.3	701.0	750.6	797.5	847.2	913.4	976.9	1043.2	1106.6
25°	482.9	516.1	549.2	604.4	656.8	712.0	764.4	844.5	921.7	1001.8	1079.0
27.5°	416.7	447.1	477.4	535.4	593.3	648.5	706.5	794.8	880.3	968.6	1054.2
30°	386.4	405.7	425.0	480.2	535.4	587.8	643.0	728.6	814.1	899.7	985.2
32.5°	336.7	353.2	369.8	419.5	469.1	516.1	565.7	654.0	739.6	827.9	913.4
35°	298.0	311.8	325.6	372.6	416.7	463.6	507.8	596.1	684.4	772.7	861.0
37.5°	276.0	289.8	300.8	342.2	386.4	427.7	469.1	557.5	643.0	731.3	816.9
40°	259.4	267.7	278.7	320.1	358.8	400.2	438.8	518.8	601.6	681.6	761.7
42.5°	248.4	259.4	267.7	303.6	342.2	378.1	413.9	491.2	568.5	643.0	720.3
45°	245.6	256.6	267.7	298.0	328.4	356.0	386.4	460.9	535.4	609.9	684.4
47.5°	240.1	248.4	259.4	284.2	306.3	331.2	353.2	427.7	502.3	574.0	648.5
50°	237.3	240.1	245.6	267.7	289.8	311.8	333.9	408.4	482.9	557.5	632.0
52.5°	234.6	234.6	234.6	253.9	273.2	289.8	309.1	383.6	460.9	535.4	609.9
55°	218.0	215.3	215.3	234.6	251.1	270.4	287.0	361.5	436.0	507.8	582.3
57.5°	201.5	198.7	195.9	212.5	229.1	245.6	262.2	336.7	413.9	488.5	563.0
60°	184.9	182.1	182.1	198.7	212.5	229.1	242.9	320.1	394.6	471.9	546.4
62.5°	165.6	168.3	168.3	182.1	198.7	212.5	226.3	303.6	383.6	460.9	538.1
65°	151.8	154.5	154.5	171.1	187.7	204.2	220.8	295.3	372.6	447.1	521.6
67.5°	140.7	143.5	143.5	162.8	179.4	198.7	215.3	281.5	350.5	416.7	482.9
70°	129.7	129.7	132.5	151.8	171.1	190.4	209.7	267.7	325.6	380.8	438.8
72.5°	115.9	118.7	121.4	140.7	157.3	176.6	193.2	245.6	298.0	350.5	402.9
75°	102.1	104.9	107.6	124.2	140.7	157.3	173.9	223.5	270.4	320.1	367.0
77.5°	91.1	93.8	96.6	110.4	124.2	138.0	151.8	187.7	226.3	262.2	298.0
80°	74.5	74.5	77.3	88.3	99.3	107.6	118.7	143.5	168.3	190.4	215.3
82.5°	55.2	58.0	58.0	66.2	71.8	80.0	85.5	99.3	110.4	124.2	135.2
85°	46.9	44.2	44.2	49.7	52.4	58.0	60.7	69.0	74.5	82.8	88.3
87.5°	19.3	16.6	16.6	19.3	24.8	27.6	30.4	30.4	33.1	33.1	33.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	2036.6	2042.2	2050.4	2056.0	2069.7	2080.8	2094.6	2105.6	2113.9	2127.7	2122.2
5°	1962.1	1987.0	2011.8	2036.6	2056.0	2075.3	2091.8	2111.1	2133.2	2174.6	2185.7
7.5°	1741.3	1774.5	1804.8	1837.9	1876.6	1915.2	1953.8	1992.5	2028.4	2080.8	2113.9
10°	1523.3	1570.2	1614.4	1661.3	1697.2	1733.1	1766.2	1802.1	1851.7	1904.2	1964.9
12.5°	1385.4	1432.3	1479.2	1526.1	1578.5	1628.2	1680.6	1730.3	1777.2	1818.6	1887.6
15°	1294.3	1346.7	1396.4	1446.1	1509.5	1570.2	1633.7	1694.4	1763.4	1818.6	1865.5
17.5°	1272.2	1335.7	1396.4	1459.9	1526.1	1592.3	1658.6	1724.8	1793.8	1876.6	1937.3
20°	1233.6	1319.1	1404.7	1490.2	1575.8	1658.6	1744.1	1826.9	1918.0	2017.3	2044.9
22.5°	1211.5	1313.6	1418.5	1520.6	1636.5	1755.1	1871.1	1987.0	2083.5	2158.1	2240.8
25°	1208.7	1335.7	1465.4	1592.3	1738.6	1882.1	2028.4	2171.9	2296.0	2370.6	2436.8
27.5°	1206.0	1360.5	1512.3	1664.1	1843.5	2020.1	2199.5	2376.1	2492.0	2599.6	2654.8
30°	1172.9	1357.8	1545.4	1730.3	1931.8	2133.2	2334.7	2536.1	2654.8	2729.3	2756.9
32.5°	1131.5	1349.5	1567.5	1785.5	2014.6	2243.6	2469.9	2699.0	2792.8	2856.3	2834.2
35°	1098.3	1338.4	1575.8	1813.1	2056.0	2301.6	2544.4	2787.3	2922.5	3010.8	2974.9
37.5°	1068.0	1319.1	1570.2	1821.4	2105.6	2389.9	2674.1	2958.4	3088.1	3181.9	3140.5
40°	1032.1	1299.8	1570.2	1837.9	2163.6	2486.5	2812.1	3135.0	3303.3	3383.3	3319.9
42.5°	1001.8	1280.5	1562.0	1840.7	2188.4	2536.1	2883.8	3231.6	3419.2	3532.4	3452.3
45°	963.1	1241.8	1517.8	1796.5	2180.1	2563.7	2944.6	3328.2	3546.2	3634.5	3524.1
47.5°	921.7	1197.7	1470.9	1744.1	2152.5	2561.0	2969.4	3377.8	3579.3	3684.2	3582.0
50°	907.9	1183.9	1457.1	1733.1	2174.6	2618.9	3060.5	3502.0	3648.3	3733.8	3598.6
52.5°	905.2	1197.7	1493.0	1785.5	2229.8	2671.4	3115.7	3557.2	3675.9	3766.9	3645.5
55°	896.9	1214.3	1528.9	1843.5	2307.1	2773.5	3237.1	3700.7	3819.4	3885.6	3794.5
57.5°	905.2	1247.4	1586.8	1929.0	2406.4	2883.8	3361.3	3838.7	3982.2	4029.1	4009.8
60°	910.7	1275.0	1636.5	2000.8	2467.1	2933.5	3399.9	3866.3	4015.3	4131.2	4153.3
62.5°	896.9	1255.6	1611.6	1970.4	2392.6	2814.9	3237.1	3659.3	3904.9	4076.0	4175.4
65°	855.5	1186.7	1520.6	1851.7	2240.8	2632.7	3021.8	3410.9	3670.4	3924.2	4004.3
67.5°	764.4	1045.9	1327.4	1608.9	1948.3	2287.8	2624.4	2963.9	3289.5	3535.1	3645.5
70°	662.3	883.1	1106.6	1327.4	1636.5	1945.6	2254.6	2563.7	2850.7	3121.2	3226.0
72.5°	576.8	747.9	921.7	1092.8	1313.6	1531.6	1752.4	1970.4	2309.8	2580.3	2682.4
75°	491.2	615.4	736.8	861.0	1012.8	1164.6	1313.6	1465.4	1705.5	1948.3	2050.4
77.5°	378.1	460.9	540.9	620.9	725.8	827.9	932.8	1034.9	1203.2	1385.4	1437.8
80°	262.2	309.1	353.2	400.2	482.9	565.7	648.5	731.3	841.7	943.8	1023.8
82.5°	162.8	193.2	220.8	248.4	314.6	380.8	444.3	510.5	554.7	560.2	640.2
85°	104.9	124.2	140.7	157.3	195.9	237.3	276.0	314.6	281.5	262.2	311.8
87.5°	41.4	52.4	60.7	69.0	66.2	63.5	60.7	58.0	49.7	44.2	55.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	2127.7	2136.0	2144.3	2149.8	2158.1	2160.8	2163.6	2163.6	2166.3	2169.1	2174.6
5°	2229.8	2246.4	2262.9	2276.7	2293.3	2307.1	2318.1	2331.9	2343.0	2343.0	2340.2
7.5°	2144.3	2185.7	2227.0	2268.4	2309.8	2340.2	2367.8	2398.1	2425.7	2431.3	2436.8
10°	2031.1	2075.3	2116.7	2160.8	2202.2	2249.1	2293.3	2337.4	2384.4	2392.6	2403.7
12.5°	1926.2	1978.7	2031.1	2080.8	2133.2	2166.3	2199.5	2229.8	2262.9	2285.0	2307.1
15°	1923.5	1967.6	2011.8	2053.2	2097.3	2116.7	2136.0	2152.5	2171.9	2171.9	2174.6
17.5°	1987.0	2014.6	2042.2	2067.0	2094.6	2097.3	2102.9	2105.6	2108.4	2100.1	2091.8
20°	2111.1	2122.2	2133.2	2144.3	2155.3	2136.0	2119.4	2100.1	2080.8	2058.7	2039.4
22.5°	2293.3	2268.4	2243.6	2218.8	2193.9	2160.8	2124.9	2091.8	2056.0	2028.4	2000.8
25°	2464.4	2434.0	2403.7	2373.3	2343.0	2271.2	2199.5	2124.9	2053.2	2022.8	1992.5
27.5°	2693.4	2646.5	2599.6	2552.7	2505.8	2409.2	2312.6	2216.0	2119.4	2067.0	2017.3
30°	2748.6	2696.2	2643.8	2588.6	2536.1	2442.3	2351.2	2257.4	2163.6	2102.9	2044.9
32.5°	2828.7	2767.9	2707.2	2646.5	2585.8	2494.7	2403.7	2309.8	2218.8	2163.6	2105.6
35°	2961.1	2892.1	2823.1	2751.4	2682.4	2588.6	2497.5	2403.7	2309.8	2246.4	2185.7
37.5°	3074.3	2994.2	2914.2	2834.2	2754.1	2671.4	2585.8	2503.0	2417.5	2354.0	2293.3
40°	3201.2	3112.9	3024.6	2939.0	2850.7	2773.5	2696.2	2616.2	2538.9	2489.2	2439.5
42.5°	3311.6	3204.0	3099.1	2994.2	2886.6	2834.2	2784.5	2732.1	2679.6	2654.8	2627.2
45°	3388.9	3289.5	3187.4	3088.1	2988.7	2950.1	2911.4	2872.8	2834.2	2859.0	2883.8
47.5°	3422.0	3342.0	3264.7	3187.4	3107.4	3121.2	3135.0	3146.0	3159.8	3192.9	3228.8
50°	3452.3	3408.2	3361.3	3317.1	3270.2	3322.6	3372.3	3424.7	3477.2	3546.2	3615.2
52.5°	3513.1	3488.2	3466.1	3441.3	3416.5	3507.5	3598.6	3689.7	3780.7	3858.0	3935.3
55°	3695.2	3675.9	3656.6	3634.5	3615.2	3744.9	3871.8	4001.5	4131.2	4211.2	4291.3
57.5°	3946.3	3935.3	3921.5	3910.4	3896.6	4023.6	4147.8	4272.0	4398.9	4476.2	4556.2
60°	4136.7	4139.5	4139.5	4142.3	4142.3	4238.8	4335.4	4434.8	4531.4	4597.6	4666.6
62.5°	4238.8	4233.3	4227.8	4222.3	4216.8	4296.8	4376.8	4456.9	4536.9	4586.6	4636.2
65°	4128.5	4158.8	4189.2	4219.5	4249.9	4260.9	4269.2	4280.2	4288.5	4318.9	4349.2
67.5°	3758.7	3819.4	3877.3	3938.0	3996.0	3954.6	3916.0	3874.6	3833.2	3841.5	3847.0
70°	3347.5	3416.5	3488.2	3557.2	3626.2	3529.6	3433.0	3333.7	3237.1	3204.0	3170.9
72.5°	2823.1	2883.8	2947.3	3008.0	3068.7	2950.1	2834.2	2715.5	2596.8	2538.9	2480.9
75°	2158.1	2229.8	2304.3	2376.1	2447.8	2315.4	2180.1	2047.7	1912.4	1873.8	1837.9
77.5°	1573.0	1658.6	1744.1	1829.7	1915.2	1796.5	1677.9	1556.5	1437.8	1415.7	1393.6
80°	1145.3	1211.5	1275.0	1341.2	1404.7	1335.7	1266.7	1197.7	1128.7	1125.9	1123.2
82.5°	772.7	830.7	885.9	943.8	999.0	971.4	946.6	919.0	891.4	919.0	949.3
85°	397.4	477.4	560.2	640.2	720.3	712.0	706.5	698.2	689.9	725.8	758.9
87.5°	80.0	149.0	218.0	284.2	353.2	336.7	320.1	300.8	284.2	295.3	303.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	2177.4	2180.1	2180.1	2180.1	2180.1	2180.1	2174.6	2171.9	2166.3	2160.8	2152.5
5°	2340.2	2337.4	2326.4	2315.4	2301.6	2290.5	2282.2	2271.2	2262.9	2251.9	2235.3
7.5°	2442.3	2447.8	2428.5	2411.9	2392.6	2373.3	2354.0	2334.7	2315.4	2296.0	2257.4
10°	2411.9	2420.2	2409.2	2398.1	2384.4	2373.3	2351.2	2326.4	2304.3	2279.5	2232.6
12.5°	2326.4	2348.5	2343.0	2337.4	2331.9	2326.4	2312.6	2296.0	2282.2	2265.7	2213.3
15°	2174.6	2174.6	2177.4	2180.1	2180.1	2182.9	2185.7	2188.4	2191.2	2193.9	2163.6
17.5°	2083.5	2075.3	2075.3	2075.3	2075.3	2075.3	2086.3	2100.1	2111.1	2122.2	2113.9
20°	2017.3	1998.0	1995.2	1995.2	1992.5	1989.7	2009.0	2031.1	2050.4	2069.7	2080.8
22.5°	1973.2	1945.6	1942.8	1940.0	1937.3	1934.5	1959.4	1984.2	2009.0	2033.9	2072.5
25°	1962.1	1931.8	1934.5	1937.3	1937.3	1940.0	1959.4	1978.7	1998.0	2017.3	2083.5
27.5°	1964.9	1915.2	1918.0	1920.7	1920.7	1923.5	1953.8	1981.4	2011.8	2039.4	2122.2
30°	1984.2	1926.2	1920.7	1915.2	1909.7	1904.2	1945.6	1987.0	2028.4	2069.7	2133.2
32.5°	2050.4	1995.2	1981.4	1967.6	1953.8	1940.0	1989.7	2036.6	2086.3	2133.2	2185.7
35°	2122.2	2061.5	2056.0	2050.4	2042.2	2036.6	2080.8	2127.7	2171.9	2216.0	2262.9
37.5°	2229.8	2169.1	2163.6	2155.3	2149.8	2141.5	2191.2	2238.1	2287.8	2334.7	2376.1
40°	2389.9	2340.2	2337.4	2337.4	2334.7	2331.9	2370.6	2411.9	2450.6	2489.2	2516.8
42.5°	2602.4	2577.5	2585.8	2596.8	2605.1	2613.4	2643.8	2676.9	2707.2	2737.6	2729.3
45°	2908.7	2933.5	2936.3	2939.0	2941.8	2944.6	2952.8	2963.9	2972.2	2980.4	2947.3
47.5°	3261.9	3295.0	3311.6	3328.2	3342.0	3358.5	3347.5	3333.7	3322.6	3308.8	3226.0
50°	3681.4	3750.4	3747.6	3744.9	3739.3	3736.6	3714.5	3692.4	3667.6	3645.5	3524.1
52.5°	4012.6	4089.8	4103.6	4117.4	4131.2	4145.0	4103.6	4062.2	4018.1	3976.7	3824.9
55°	4368.5	4448.6	4451.3	4454.1	4454.1	4456.9	4398.9	4341.0	4280.2	4222.3	4065.0
57.5°	4633.5	4710.7	4702.5	4696.9	4688.7	4680.4	4611.4	4542.4	4473.4	4404.4	4247.1
60°	4732.8	4799.1	4782.5	4765.9	4746.6	4730.1	4677.6	4625.2	4570.0	4517.6	4365.8
62.5°	4685.9	4735.6	4710.7	4688.7	4663.8	4639.0	4572.8	4503.8	4437.5	4368.5	4258.2
65°	4376.8	4407.2	4374.1	4343.7	4313.4	4280.2	4225.0	4169.9	4111.9	4056.7	3982.2
67.5°	3855.3	3860.8	3858.0	3855.3	3852.5	3849.7	3769.7	3689.7	3606.9	3526.9	3521.3
70°	3140.5	3107.4	3112.9	3121.2	3126.7	3132.2	3071.5	3013.6	2952.8	2892.1	2919.7
72.5°	2423.0	2365.0	2378.8	2395.4	2409.2	2423.0	2373.3	2326.4	2276.7	2227.0	2265.7
75°	1799.3	1763.4	1777.2	1793.8	1807.6	1821.4	1802.1	1782.7	1760.7	1741.3	1777.2
77.5°	1371.6	1349.5	1352.2	1352.2	1355.0	1355.0	1357.8	1363.3	1366.0	1368.8	1407.4
80°	1117.7	1114.9	1112.1	1109.4	1103.9	1101.1	1128.7	1156.3	1183.9	1211.5	1230.8
82.5°	976.9	1004.5	988.0	974.2	957.6	941.0	965.9	990.7	1015.6	1040.4	1032.1
85°	794.8	827.9	797.5	767.2	734.1	703.7	725.8	745.1	767.2	786.5	775.5
87.5°	314.6	322.9	273.2	226.3	176.6	126.9	201.5	273.2	347.7	419.5	430.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0	1987.0
2.5°	2144.3	2133.2	2124.9	2122.2	2116.7	2113.9	2108.4	2102.9	2094.6	2089.1	2080.8
5°	2216.0	2199.5	2180.1	2152.5	2127.7	2100.1	2072.5	2047.7	2022.8	1995.2	1970.4
7.5°	2218.8	2180.1	2141.5	2105.6	2067.0	2031.1	1992.5	1959.4	1923.5	1887.6	1854.5
10°	2188.4	2141.5	2094.6	2047.7	2003.5	1956.6	1909.7	1871.1	1829.7	1788.3	1749.6
12.5°	2163.6	2111.1	2058.7	2003.5	1951.1	1895.9	1840.7	1802.1	1763.4	1724.8	1686.2
15°	2133.2	2100.1	2069.7	2020.1	1970.4	1920.7	1871.1	1818.6	1768.9	1716.5	1664.1
17.5°	2108.4	2100.1	2091.8	2058.7	2025.6	1989.7	1956.6	1904.2	1851.7	1796.5	1744.1
20°	2094.6	2105.6	2116.7	2100.1	2083.5	2064.2	2047.7	2009.0	1970.4	1929.0	1890.4
22.5°	2111.1	2152.5	2191.2	2193.9	2199.5	2202.2	2205.0	2169.1	2133.2	2094.6	2058.7
25°	2149.8	2216.0	2282.2	2318.1	2354.0	2392.6	2428.5	2406.4	2384.4	2362.3	2340.2
27.5°	2202.2	2285.0	2367.8	2420.2	2469.9	2522.3	2574.8	2572.0	2569.2	2563.7	2561.0
30°	2193.9	2257.4	2320.9	2384.4	2447.8	2511.3	2574.8	2607.9	2638.2	2671.4	2704.5
32.5°	2240.8	2293.3	2348.5	2414.7	2480.9	2549.9	2616.2	2685.2	2751.4	2820.4	2889.4
35°	2312.6	2359.5	2409.2	2480.9	2555.4	2627.2	2701.7	2784.5	2870.1	2955.6	3038.4
37.5°	2420.2	2461.6	2505.8	2566.5	2630.0	2690.7	2754.1	2875.6	2997.0	3121.2	3242.6
40°	2544.4	2572.0	2599.6	2657.6	2715.5	2773.5	2831.4	2983.2	3135.0	3286.8	3438.5
42.5°	2723.8	2715.5	2707.2	2754.1	2803.8	2850.7	2900.4	3038.4	3176.4	3314.4	3452.3
45°	2914.2	2881.1	2848.0	2870.1	2894.9	2917.0	2941.8	3082.5	3223.3	3366.8	3507.5
47.5°	3143.3	3060.5	2977.7	2958.4	2939.0	2917.0	2897.6	3049.4	3201.2	3355.8	3507.5
50°	3402.7	3278.5	3157.1	3107.4	3054.9	3005.3	2952.8	3077.0	3204.0	3330.9	3455.1
52.5°	3673.1	3518.6	3366.8	3289.5	3212.2	3132.2	3054.9	3159.8	3267.4	3375.1	3479.9
55°	3904.9	3747.6	3587.6	3496.5	3405.4	3314.4	3223.3	3328.2	3433.0	3537.9	3642.8
57.5°	4089.8	3932.5	3775.2	3689.7	3601.4	3515.8	3427.5	3526.9	3629.0	3731.1	3830.4
60°	4216.8	4065.0	3913.2	3830.4	3747.6	3664.8	3582.0	3700.7	3819.4	3940.8	4059.5
62.5°	4150.5	4040.1	3929.8	3893.9	3858.0	3819.4	3783.5	3896.6	4007.0	4120.2	4233.3
65°	3907.7	3833.2	3758.7	3794.5	3833.2	3869.0	3907.7	3982.2	4056.7	4134.0	4208.5
67.5°	3513.1	3507.5	3499.3	3579.3	3659.3	3742.1	3822.1	3871.8	3918.7	3968.4	4018.1
70°	2947.3	2977.7	3005.3	3143.3	3281.2	3419.2	3557.2	3576.5	3595.8	3615.2	3634.5
72.5°	2307.1	2345.7	2387.1	2569.2	2748.6	2930.8	3112.9	3101.9	3090.8	3077.0	3066.0
75°	1815.9	1851.7	1890.4	2058.7	2227.0	2395.4	2563.7	2516.8	2472.7	2425.7	2378.8
77.5°	1448.8	1487.5	1528.9	1686.2	1843.5	2003.5	2160.8	2047.7	1934.5	1821.4	1708.2
80°	1247.4	1266.7	1283.2	1390.9	1495.7	1603.4	1711.0	1595.1	1476.4	1357.8	1241.8
82.5°	1023.8	1012.8	1004.5	1068.0	1131.5	1194.9	1258.4	1148.0	1037.6	924.5	814.1
85°	764.4	753.4	742.3	775.5	808.6	844.5	877.6	750.6	623.7	494.0	367.0
87.5°	444.3	455.3	466.4	502.3	538.1	576.8	612.6	482.9	353.2	220.8	91.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827

CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671827
 CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1987.0	1987.0
2.5°	2064.2	2050.4
5°	1951.1	1931.8
7.5°	1826.9	1802.1
10°	1713.8	1680.6
12.5°	1642.0	1600.6
15°	1614.4	1564.7
17.5°	1697.2	1650.3
20°	1824.1	1760.7
22.5°	1978.7	1901.4
25°	2246.4	2152.5
27.5°	2464.4	2367.8
30°	2599.6	2494.7
32.5°	2748.6	2610.6
35°	2903.2	2770.7
37.5°	3090.8	2941.8
40°	3284.0	3129.5
42.5°	3350.2	3250.9
45°	3413.7	3319.9
47.5°	3427.5	3350.2
50°	3441.3	3430.3
52.5°	3479.9	3477.2
55°	3645.5	3648.3
57.5°	3849.7	3866.3
60°	4037.4	4018.1
62.5°	4134.0	4034.6
65°	4067.7	3929.8
67.5°	3869.0	3720.0
70°	3433.0	3231.6
72.5°	2889.4	2712.8
75°	2227.0	2078.0
77.5°	1584.0	1459.9
80°	1114.9	990.7
82.5°	714.8	615.4
85°	322.9	281.5
87.5°	91.1	88.3
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671827
CATALOG NUMBER: CCP-SA-1F-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)