

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671835

Luminaire Tested: **CCP-SA-1C-750-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671835
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1C-750-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @615mA w/ SLR
distribution lens
Light Source: (16) 5000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3838 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 32
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 5.4 fc

Type IV - Short - N/A

REPORT NUMBER: P671835
CATALOG NUMBER: CCP-SA-1C-750-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	789.7	0.0	789.7
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3048.3	0.0	3048.3
	% Fixture	79.4	0.0	79.4
Total	Lumens	3838.0	0.0	3838.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.2	2.5
10°-20°	201.1	5.2
20°-30°	294.2	7.7
30°-40°	414.5	10.8
40°-50°	569.5	14.8
50°-60°	776.2	20.2
60°-70°	849.6	22.1
70°-80°	490.7	12.8
80°-90°	147.1	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3838.0	100.0
0°-180°	3838.0	100.0

Coefficient of Utilization



REPORT NUMBER: P671835


CATALOG NUMBER: CCP-SA-1C-750-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	394.2	10.3			
FM	(30°-60°)	1400.6	36.5			
FH	(60°-80°)	1128.6	29.4			G1/1800
FVH	(80°-90°)	124.9	3.3			G2/225
BL	(0°-30°)	196.3	5.1	B1/500		
BM	(30°-60°)	359.6	9.4	B1/1000		
BH	(60°-80°)	211.6	5.5	B1/500		G1/500
BVH	(80°-90°)	22.1	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6
2.5°	1264.8	1258.0	1252.9	1247.7	1240.9	1235.8	1229.0	1222.2	1213.7	1206.9	1198.4
5°	1191.6	1171.1	1150.7	1138.8	1125.2	1113.3	1099.7	1084.3	1069.0	1052.0	1036.7
7.5°	1111.6	1086.0	1060.5	1040.1	1017.9	997.5	975.4	956.7	937.9	919.2	900.5
10°	1036.7	1012.8	989.0	963.5	936.2	910.7	883.5	857.9	832.4	806.9	781.3
12.5°	987.3	958.4	931.1	902.2	875.0	846.0	817.1	793.2	769.4	743.9	720.1
15°	965.2	937.9	912.4	883.5	854.5	825.6	796.7	769.4	743.9	716.6	689.4
17.5°	1017.9	978.8	939.6	902.2	864.7	827.3	789.8	755.8	721.8	687.7	653.7
20°	1086.0	1036.7	989.0	943.0	895.4	849.4	801.8	754.1	706.4	658.8	611.1
22.5°	1172.8	1116.7	1062.2	1002.6	941.3	881.8	820.5	760.9	701.3	640.0	580.5
25°	1327.8	1261.4	1195.0	1109.9	1023.1	937.9	851.1	772.8	696.2	617.9	539.6
27.5°	1460.5	1370.3	1281.8	1179.7	1077.5	975.4	873.3	783.0	694.5	604.3	514.1
30°	1538.8	1450.3	1361.8	1237.5	1115.0	990.7	866.4	766.0	667.3	566.8	466.4
32.5°	1610.3	1511.6	1412.9	1276.7	1138.8	1002.6	864.7	754.1	645.2	534.5	423.9
35°	1709.1	1600.1	1492.9	1334.6	1176.3	1017.9	859.6	745.6	629.8	515.8	400.0
37.5°	1814.6	1680.1	1547.3	1372.0	1196.7	1021.3	846.0	733.7	621.3	509.0	396.6
40°	1930.3	1766.9	1605.2	1411.2	1218.8	1024.8	830.7	718.3	606.0	491.9	379.6
42.5°	2005.2	1828.2	1651.2	1441.8	1234.1	1024.8	815.4	704.7	594.1	481.7	371.1
45°	2047.8	1875.9	1705.7	1479.3	1252.9	1026.5	800.1	691.1	582.2	471.5	362.6
47.5°	2066.5	1906.5	1746.5	1508.2	1271.6	1033.3	794.9	684.3	572.0	461.3	349.0
50°	2115.9	1974.6	1833.3	1578.0	1324.3	1069.0	813.7	694.5	577.1	457.9	338.7
52.5°	2144.8	2024.0	1903.1	1641.0	1378.8	1116.7	854.5	721.8	589.0	456.2	323.4
55°	2250.4	2134.6	2018.9	1739.7	1458.8	1179.7	898.8	752.4	606.0	457.9	311.5
57.5°	2384.8	2262.3	2141.4	1840.1	1538.8	1237.5	936.2	779.6	621.3	464.7	306.4
60°	2478.5	2359.3	2241.9	1921.8	1600.1	1280.1	958.4	794.9	631.5	466.4	303.0
62.5°	2488.7	2335.5	2184.0	1872.5	1561.0	1247.7	936.2	777.9	619.6	459.6	301.3
65°	2424.0	2245.3	2066.5	1768.6	1470.7	1172.8	875.0	730.3	585.6	439.2	294.5
67.5°	2294.6	2085.3	1875.9	1603.5	1331.2	1058.8	786.4	662.2	539.6	415.3	291.1
70°	1993.3	1809.5	1627.3	1390.7	1155.8	919.2	682.6	580.5	480.0	377.9	275.8
72.5°	1673.3	1501.4	1331.2	1138.8	948.2	755.8	563.4	486.8	410.2	331.9	255.3
75°	1281.8	1152.4	1024.8	881.8	738.8	594.1	451.1	394.9	338.7	282.6	226.4
77.5°	900.5	830.7	762.6	655.4	548.1	440.9	333.6	296.2	258.7	221.3	183.8
80°	611.1	572.0	534.5	457.9	381.3	303.0	226.4	202.6	177.0	153.2	127.7
82.5°	379.6	377.9	374.5	321.7	269.0	216.2	163.4	143.0	124.3	103.8	83.4
85°	173.6	202.6	229.8	200.9	171.9	143.0	114.1	100.4	86.8	71.5	57.9
87.5°	54.5	66.4	76.6	73.2	68.1	64.7	59.6	51.1	42.6	34.0	25.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6
2.5°	1191.6	1186.5	1179.7	1172.8	1164.3	1157.5	1149.0	1140.5	1138.8	1135.4	1133.7
5°	1026.5	1016.2	1004.3	994.1	983.9	972.0	961.8	949.9	941.3	931.1	922.6
7.5°	881.8	864.7	846.0	827.3	810.3	793.2	774.5	757.5	749.0	740.5	732.0
10°	766.0	749.0	733.7	716.6	704.7	694.5	682.6	670.7	660.5	650.3	640.0
12.5°	708.1	696.2	684.3	672.4	658.8	646.9	633.2	619.6	607.7	597.5	585.6
15°	672.4	655.4	636.6	619.6	600.9	583.9	565.1	546.4	532.8	520.9	507.3
17.5°	629.8	604.3	580.5	554.9	534.5	514.1	491.9	471.5	456.2	439.2	423.9
20°	582.2	553.2	522.6	493.7	469.8	447.7	423.9	400.0	383.0	364.3	347.3
22.5°	541.3	503.9	464.7	425.6	400.0	374.5	347.3	321.7	306.4	289.4	274.1
25°	497.1	456.2	413.6	371.1	345.6	318.3	292.8	265.6	253.6	243.4	231.5
27.5°	473.2	432.4	389.8	349.0	325.1	299.6	275.8	250.2	241.7	231.5	223.0
30°	425.6	386.4	345.6	304.7	287.7	272.4	255.3	238.3	234.9	233.2	229.8
32.5°	383.0	342.2	301.3	260.4	245.1	229.8	214.5	199.2	197.5	194.1	192.4
35°	360.9	321.7	280.9	241.7	228.1	212.8	199.2	183.8	180.4	175.3	171.9
37.5°	355.8	314.9	272.4	231.5	217.9	204.3	188.9	175.3	171.9	168.5	165.1
40°	342.2	303.0	265.6	226.4	212.8	199.2	183.8	170.2	166.8	163.4	160.0
42.5°	331.9	294.5	255.3	216.2	204.3	192.4	178.7	166.8	163.4	160.0	154.9
45°	323.4	284.3	243.4	204.3	195.8	187.2	177.0	168.5	165.1	160.0	156.6
47.5°	309.8	272.4	233.2	194.1	185.5	178.7	170.2	161.7	158.3	154.9	151.5
50°	299.6	260.4	221.3	182.1	175.3	168.5	161.7	154.9	154.9	156.6	156.6
52.5°	286.0	248.5	211.1	173.6	166.8	160.0	153.2	146.4	148.1	149.8	151.5
55°	274.1	238.3	200.9	163.4	156.6	149.8	141.3	134.5	136.2	137.9	139.6
57.5°	269.0	231.5	194.1	156.6	149.8	141.3	134.5	126.0	126.0	126.0	126.0
60°	265.6	226.4	188.9	149.8	141.3	134.5	126.0	117.5	115.8	115.8	114.1
62.5°	263.8	224.7	187.2	148.1	137.9	129.4	119.2	108.9	107.2	105.5	103.8
65°	257.0	221.3	183.8	146.4	134.5	124.3	112.3	100.4	98.7	98.7	97.0
67.5°	255.3	217.9	182.1	144.7	132.8	119.2	107.2	93.6	91.9	90.2	88.5
70°	241.7	209.4	175.3	141.3	127.7	115.8	102.1	88.5	86.8	83.4	81.7
72.5°	224.7	195.8	165.1	134.5	120.9	107.2	93.6	80.0	78.3	76.6	73.2
75°	199.2	171.9	144.7	117.5	105.5	95.3	83.4	71.5	69.8	68.1	64.7
77.5°	163.4	141.3	120.9	98.7	90.2	81.7	73.2	64.7	63.0	61.3	57.9
80°	115.8	102.1	90.2	76.6	71.5	64.7	59.6	52.8	52.8	51.1	51.1
82.5°	76.6	69.8	63.0	56.2	52.8	49.4	46.0	42.6	42.6	40.9	40.9
85°	54.5	51.1	46.0	42.6	40.9	37.4	35.7	32.3	32.3	32.3	32.3
87.5°	25.5	25.5	23.8	23.8	22.1	22.1	20.4	18.7	18.7	18.7	18.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6
2.5°	1130.3	1125.2	1120.1	1113.3	1108.2	1101.4	1092.8	1086.0	1077.5	1077.5	1075.8
5°	912.4	907.3	902.2	895.4	890.3	883.5	878.4	871.6	864.7	864.7	863.0
7.5°	723.5	713.2	703.0	691.1	680.9	674.1	667.3	658.8	652.0	646.9	641.7
10°	629.8	619.6	607.7	597.5	585.6	577.1	568.6	558.3	549.8	543.0	536.2
12.5°	573.7	561.7	549.8	537.9	526.0	514.1	503.9	491.9	480.0	471.5	463.0
15°	493.7	481.7	469.8	457.9	446.0	432.4	418.8	403.4	389.8	383.0	377.9
17.5°	406.8	394.9	381.3	369.4	355.8	345.6	335.3	325.1	314.9	308.1	303.0
20°	328.5	314.9	301.3	287.7	274.1	267.3	260.4	253.6	246.8	241.7	238.3
22.5°	257.0	248.5	241.7	233.2	224.7	219.6	216.2	211.1	206.0	206.0	206.0
25°	219.6	214.5	211.1	206.0	200.9	199.2	197.5	194.1	192.4	190.7	190.7
27.5°	212.8	207.7	202.6	197.5	192.4	190.7	188.9	185.5	183.8	183.8	183.8
30°	226.4	224.7	223.0	221.3	219.6	216.2	211.1	207.7	202.6	199.2	195.8
32.5°	188.9	187.2	187.2	185.5	183.8	187.2	188.9	192.4	194.1	195.8	197.5
35°	166.8	163.4	160.0	156.6	153.2	151.5	149.8	148.1	146.4	146.4	144.7
37.5°	161.7	158.3	154.9	151.5	148.1	146.4	144.7	143.0	141.3	141.3	139.6
40°	156.6	153.2	151.5	148.1	144.7	143.0	141.3	137.9	136.2	134.5	134.5
42.5°	151.5	149.8	146.4	144.7	141.3	139.6	137.9	134.5	132.8	131.1	129.4
45°	151.5	148.1	144.7	141.3	137.9	136.2	132.8	131.1	127.7	127.7	126.0
47.5°	148.1	144.7	141.3	137.9	134.5	132.8	129.4	127.7	124.3	122.6	120.9
50°	156.6	151.5	144.7	139.6	132.8	131.1	127.7	126.0	122.6	120.9	119.2
52.5°	153.2	148.1	141.3	136.2	129.4	126.0	124.3	120.9	117.5	115.8	114.1
55°	141.3	136.2	132.8	127.7	122.6	119.2	115.8	112.3	108.9	107.2	107.2
57.5°	126.0	124.3	122.6	120.9	119.2	115.8	112.3	107.2	103.8	102.1	100.4
60°	112.3	114.1	115.8	117.5	119.2	114.1	108.9	103.8	98.7	97.0	95.3
62.5°	102.1	105.5	108.9	110.6	114.1	108.9	103.8	98.7	93.6	91.9	90.2
65°	95.3	97.0	97.0	98.7	98.7	95.3	93.6	90.2	86.8	85.1	85.1
67.5°	86.8	86.8	86.8	85.1	85.1	83.4	83.4	81.7	80.0	78.3	78.3
70°	78.3	78.3	78.3	76.6	76.6	74.9	74.9	73.2	71.5	71.5	69.8
72.5°	71.5	71.5	69.8	69.8	68.1	68.1	68.1	66.4	66.4	64.7	64.7
75°	63.0	63.0	61.3	61.3	59.6	59.6	59.6	57.9	57.9	57.9	56.2
77.5°	56.2	56.2	54.5	54.5	52.8	52.8	52.8	51.1	51.1	49.4	49.4
80°	49.4	49.4	47.7	47.7	46.0	46.0	44.3	44.3	42.6	42.6	40.9
82.5°	39.2	39.2	39.2	39.2	39.2	37.4	37.4	35.7	34.0	34.0	32.3
85°	32.3	32.3	32.3	30.6	30.6	30.6	28.9	28.9	27.2	25.5	25.5
87.5°	18.7	18.7	18.7	17.0	17.0	17.0	17.0	17.0	17.0	17.0	15.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6
2.5°	1075.8	1074.1	1067.3	1060.5	1067.3	1074.1	1074.1	1074.1	1072.4	1072.4	1072.4
5°	863.0	861.3	857.9	854.5	854.5	852.8	856.2	859.6	863.0	866.4	869.8
7.5°	634.9	629.8	624.7	619.6	623.0	624.7	629.8	633.2	638.3	641.7	650.3
10°	529.4	522.6	517.5	512.4	509.0	505.6	502.2	500.5	497.1	493.7	497.1
12.5°	452.8	444.3	435.8	425.6	423.9	422.2	418.8	415.3	411.9	408.5	406.8
15°	371.1	364.3	360.9	355.8	349.0	342.2	338.7	337.0	333.6	330.2	328.5
17.5°	296.2	289.4	284.3	279.2	277.5	274.1	274.1	274.1	274.1	274.1	274.1
20°	233.2	228.1	228.1	226.4	226.4	224.7	226.4	228.1	228.1	229.8	231.5
22.5°	204.3	204.3	202.6	200.9	202.6	202.6	204.3	206.0	207.7	209.4	211.1
25°	188.9	187.2	188.9	190.7	190.7	190.7	192.4	192.4	194.1	194.1	194.1
27.5°	182.1	182.1	183.8	183.8	185.5	185.5	185.5	183.8	183.8	182.1	182.1
30°	192.4	188.9	188.9	188.9	187.2	185.5	183.8	183.8	182.1	180.4	178.7
32.5°	199.2	200.9	199.2	195.8	194.1	190.7	188.9	185.5	183.8	180.4	177.0
35°	144.7	143.0	146.4	148.1	149.8	151.5	153.2	154.9	154.9	156.6	156.6
37.5°	139.6	137.9	137.9	136.2	136.2	136.2	136.2	136.2	134.5	134.5	136.2
40°	132.8	131.1	131.1	129.4	129.4	127.7	127.7	127.7	127.7	127.7	127.7
42.5°	127.7	126.0	126.0	126.0	126.0	124.3	124.3	122.6	122.6	120.9	120.9
45°	126.0	124.3	122.6	120.9	120.9	119.2	119.2	119.2	117.5	117.5	117.5
47.5°	119.2	117.5	117.5	115.8	115.8	114.1	114.1	114.1	112.3	112.3	112.3
50°	115.8	114.1	114.1	112.3	112.3	110.6	110.6	110.6	108.9	108.9	108.9
52.5°	110.6	108.9	108.9	108.9	107.2	105.5	105.5	105.5	103.8	103.8	103.8
55°	105.5	103.8	103.8	103.8	102.1	100.4	100.4	100.4	98.7	98.7	98.7
57.5°	98.7	97.0	97.0	95.3	95.3	95.3	95.3	95.3	93.6	93.6	93.6
60°	93.6	91.9	91.9	90.2	90.2	88.5	88.5	88.5	88.5	88.5	88.5
62.5°	88.5	86.8	85.1	83.4	85.1	85.1	85.1	85.1	83.4	83.4	83.4
65°	83.4	81.7	80.0	78.3	78.3	78.3	78.3	78.3	78.3	78.3	78.3
67.5°	76.6	74.9	73.2	71.5	73.2	73.2	73.2	73.2	73.2	73.2	73.2
70°	69.8	68.1	68.1	66.4	66.4	64.7	64.7	66.4	66.4	66.4	66.4
72.5°	63.0	61.3	61.3	59.6	59.6	59.6	59.6	59.6	59.6	59.6	59.6
75°	56.2	54.5	54.5	52.8	52.8	52.8	52.8	52.8	52.8	52.8	52.8
77.5°	47.7	46.0	46.0	46.0	46.0	46.0	46.0	47.7	47.7	47.7	47.7
80°	40.9	39.2	39.2	39.2	39.2	39.2	39.2	39.2	39.2	39.2	39.2
82.5°	32.3	30.6	30.6	30.6	30.6	30.6	30.6	30.6	30.6	30.6	30.6
85°	23.8	22.1	22.1	22.1	23.8	23.8	23.8	23.8	23.8	23.8	23.8
87.5°	15.3	13.6	13.6	13.6	15.3	15.3	15.3	15.3	13.6	13.6	13.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6
2.5°	1072.4	1072.4	1072.4	1070.7	1069.0	1067.3	1065.6	1070.7	1074.1	1079.2	1082.6
5°	871.6	875.0	876.7	881.8	886.9	892.0	897.1	900.5	903.9	905.6	909.0
7.5°	657.1	665.6	672.4	679.2	686.0	691.1	697.9	703.0	708.1	713.2	718.3
10°	498.8	502.2	503.9	510.7	515.8	522.6	527.7	532.8	537.9	541.3	546.4
12.5°	405.1	401.7	400.0	400.0	400.0	400.0	400.0	403.4	406.8	410.2	413.6
15°	326.8	325.1	323.4	321.7	320.0	316.6	314.9	318.3	321.7	325.1	328.5
17.5°	274.1	274.1	274.1	272.4	270.7	269.0	267.3	269.0	270.7	270.7	272.4
20°	234.9	236.6	238.3	240.0	240.0	241.7	241.7	243.4	245.1	245.1	246.8
22.5°	211.1	212.8	212.8	212.8	214.5	214.5	214.5	216.2	217.9	219.6	221.3
25°	192.4	192.4	190.7	190.7	192.4	192.4	192.4	192.4	194.1	194.1	194.1
27.5°	182.1	180.4	180.4	180.4	180.4	178.7	178.7	178.7	178.7	178.7	178.7
30°	177.0	175.3	173.6	171.9	171.9	170.2	168.5	168.5	168.5	168.5	168.5
32.5°	175.3	171.9	168.5	166.8	166.8	165.1	163.4	161.7	161.7	160.0	158.3
35°	156.6	154.9	154.9	153.2	151.5	149.8	148.1	148.1	148.1	146.4	146.4
37.5°	136.2	137.9	137.9	137.9	139.6	139.6	139.6	139.6	141.3	141.3	141.3
40°	127.7	127.7	127.7	129.4	131.1	131.1	132.8	132.8	134.5	134.5	134.5
42.5°	120.9	119.2	119.2	120.9	120.9	122.6	122.6	124.3	126.0	126.0	127.7
45°	117.5	115.8	115.8	115.8	115.8	114.1	114.1	115.8	117.5	119.2	120.9
47.5°	110.6	110.6	108.9	108.9	108.9	108.9	108.9	108.9	110.6	110.6	110.6
50°	107.2	107.2	105.5	105.5	105.5	105.5	105.5	105.5	105.5	105.5	105.5
52.5°	103.8	102.1	102.1	102.1	102.1	100.4	100.4	100.4	100.4	100.4	100.4
55°	98.7	97.0	97.0	97.0	97.0	97.0	97.0	97.0	98.7	98.7	98.7
57.5°	93.6	91.9	91.9	91.9	93.6	93.6	93.6	93.6	95.3	95.3	95.3
60°	88.5	88.5	88.5	88.5	88.5	88.5	88.5	90.2	90.2	91.9	91.9
62.5°	83.4	83.4	83.4	83.4	85.1	85.1	85.1	85.1	86.8	86.8	86.8
65°	78.3	78.3	78.3	78.3	80.0	80.0	80.0	80.0	80.0	80.0	80.0
67.5°	73.2	73.2	73.2	73.2	73.2	73.2	73.2	74.9	74.9	76.6	76.6
70°	66.4	64.7	64.7	66.4	66.4	68.1	68.1	69.8	69.8	71.5	71.5
72.5°	59.6	59.6	59.6	59.6	59.6	59.6	59.6	61.3	63.0	63.0	64.7
75°	52.8	52.8	52.8	52.8	54.5	54.5	54.5	56.2	56.2	57.9	57.9
77.5°	47.7	46.0	46.0	46.0	47.7	47.7	47.7	49.4	49.4	51.1	51.1
80°	39.2	39.2	39.2	39.2	40.9	40.9	40.9	40.9	42.6	42.6	42.6
82.5°	32.3	32.3	32.3	32.3	32.3	32.3	32.3	32.3	34.0	34.0	34.0
85°	23.8	23.8	23.8	23.8	25.5	25.5	25.5	25.5	25.5	25.5	25.5
87.5°	15.3	15.3	15.3	15.3	15.3	15.3	15.3	15.3	17.0	17.0	17.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6
2.5°	1082.6	1082.6	1082.6	1082.6	1086.0	1087.7	1091.1	1092.8	1091.1	1089.4	1086.0
5°	910.7	912.4	912.4	914.1	914.1	914.1	914.1	914.1	917.5	920.9	924.3
7.5°	720.1	721.8	723.5	725.2	725.2	725.2	723.5	723.5	725.2	725.2	726.9
10°	551.5	558.3	563.4	568.6	565.1	560.0	556.6	551.5	551.5	551.5	549.8
12.5°	417.1	418.8	422.2	423.9	422.2	422.2	420.5	418.8	420.5	423.9	425.6
15°	330.2	330.2	331.9	331.9	333.6	335.3	335.3	337.0	340.4	342.2	345.6
17.5°	274.1	275.8	275.8	277.5	277.5	279.2	279.2	279.2	282.6	286.0	291.1
20°	246.8	246.8	246.8	246.8	246.8	245.1	245.1	243.4	245.1	248.5	250.2
22.5°	221.3	223.0	223.0	223.0	221.3	219.6	216.2	214.5	214.5	216.2	216.2
25°	194.1	192.4	192.4	190.7	190.7	192.4	192.4	192.4	194.1	194.1	195.8
27.5°	178.7	177.0	177.0	175.3	175.3	177.0	177.0	177.0	177.0	177.0	177.0
30°	166.8	166.8	165.1	163.4	165.1	165.1	166.8	166.8	168.5	168.5	170.2
32.5°	158.3	156.6	156.6	154.9	156.6	156.6	158.3	158.3	160.0	161.7	161.7
35°	146.4	146.4	146.4	146.4	146.4	146.4	144.7	144.7	144.7	144.7	144.7
37.5°	139.6	139.6	137.9	136.2	136.2	136.2	136.2	136.2	134.5	132.8	131.1
40°	134.5	132.8	132.8	131.1	129.4	129.4	127.7	126.0	126.0	124.3	124.3
42.5°	127.7	126.0	126.0	124.3	122.6	122.6	120.9	119.2	119.2	119.2	117.5
45°	119.2	119.2	117.5	115.8	115.8	115.8	114.1	114.1	114.1	114.1	112.3
47.5°	110.6	110.6	108.9	108.9	108.9	108.9	107.2	107.2	107.2	107.2	107.2
50°	105.5	105.5	105.5	105.5	105.5	105.5	103.8	103.8	103.8	103.8	103.8
52.5°	100.4	100.4	100.4	100.4	100.4	100.4	100.4	100.4	100.4	100.4	100.4
55°	98.7	98.7	98.7	98.7	98.7	98.7	97.0	97.0	97.0	98.7	98.7
57.5°	95.3	95.3	93.6	93.6	93.6	93.6	93.6	93.6	93.6	93.6	93.6
60°	91.9	91.9	91.9	91.9	91.9	91.9	91.9	91.9	91.9	91.9	91.9
62.5°	86.8	86.8	86.8	86.8	86.8	88.5	88.5	88.5	88.5	88.5	86.8
65°	80.0	81.7	81.7	81.7	81.7	81.7	81.7	81.7	81.7	81.7	81.7
67.5°	76.6	76.6	76.6	76.6	76.6	76.6	76.6	76.6	76.6	76.6	76.6
70°	71.5	71.5	69.8	69.8	69.8	71.5	71.5	71.5	71.5	71.5	71.5
72.5°	64.7	64.7	64.7	64.7	64.7	64.7	64.7	64.7	64.7	66.4	66.4
75°	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9
77.5°	51.1	51.1	49.4	49.4	49.4	51.1	51.1	51.1	51.1	52.8	52.8
80°	42.6	42.6	42.6	42.6	42.6	42.6	42.6	42.6	42.6	44.3	44.3
82.5°	34.0	34.0	34.0	34.0	34.0	34.0	34.0	34.0	34.0	35.7	35.7
85°	25.5	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2	28.9	28.9
87.5°	17.0	17.0	17.0	17.0	17.0	17.0	15.3	15.3	15.3	15.3	13.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6
2.5°	1084.3	1086.0	1087.7	1087.7	1089.4	1091.1	1091.1	1097.9	1104.8	1108.2	1111.6
5°	927.7	926.0	926.0	924.3	922.6	927.7	932.8	943.0	953.3	955.0	958.4
7.5°	726.9	728.6	730.3	730.3	732.0	726.9	720.1	721.8	723.5	732.0	738.8
10°	549.8	551.5	553.2	553.2	554.9	553.2	549.8	554.9	560.0	566.8	575.4
12.5°	427.3	432.4	437.5	440.9	446.0	449.4	451.1	457.9	463.0	471.5	480.0
15°	349.0	352.4	355.8	359.2	362.6	366.0	369.4	376.2	383.0	393.2	403.4
17.5°	294.5	294.5	296.2	296.2	296.2	299.6	303.0	306.4	308.1	318.3	328.5
20°	251.9	250.2	248.5	246.8	245.1	248.5	250.2	251.9	253.6	260.4	265.6
22.5°	216.2	216.2	217.9	217.9	217.9	216.2	212.8	214.5	214.5	217.9	223.0
25°	195.8	195.8	195.8	194.1	194.1	195.8	197.5	197.5	195.8	197.5	199.2
27.5°	177.0	178.7	178.7	180.4	180.4	182.1	182.1	182.1	182.1	183.8	185.5
30°	170.2	170.2	171.9	171.9	171.9	173.6	175.3	175.3	175.3	177.0	180.4
32.5°	163.4	165.1	166.8	168.5	170.2	171.9	171.9	173.6	173.6	175.3	177.0
35°	144.7	143.0	143.0	141.3	139.6	139.6	139.6	139.6	137.9	139.6	139.6
37.5°	129.4	129.4	129.4	127.7	127.7	129.4	129.4	129.4	129.4	131.1	131.1
40°	122.6	122.6	122.6	122.6	122.6	122.6	122.6	124.3	124.3	126.0	127.7
42.5°	117.5	117.5	117.5	117.5	117.5	119.2	119.2	119.2	119.2	120.9	120.9
45°	112.3	112.3	112.3	112.3	112.3	112.3	112.3	114.1	114.1	115.8	117.5
47.5°	107.2	107.2	107.2	107.2	107.2	108.9	110.6	110.6	110.6	112.3	112.3
50°	103.8	103.8	103.8	103.8	103.8	105.5	105.5	107.2	107.2	108.9	110.6
52.5°	100.4	100.4	100.4	100.4	100.4	102.1	102.1	103.8	103.8	105.5	107.2
55°	98.7	98.7	98.7	97.0	97.0	98.7	98.7	100.4	100.4	102.1	102.1
57.5°	93.6	93.6	93.6	93.6	93.6	93.6	93.6	95.3	95.3	97.0	98.7
60°	91.9	91.9	90.2	90.2	88.5	90.2	90.2	91.9	91.9	93.6	93.6
62.5°	86.8	86.8	86.8	85.1	85.1	86.8	86.8	86.8	86.8	88.5	90.2
65°	81.7	81.7	81.7	80.0	80.0	81.7	81.7	81.7	81.7	83.4	85.1
67.5°	76.6	76.6	76.6	74.9	74.9	74.9	74.9	76.6	76.6	78.3	80.0
70°	71.5	71.5	71.5	69.8	69.8	69.8	68.1	69.8	71.5	73.2	73.2
72.5°	66.4	66.4	66.4	64.7	64.7	64.7	63.0	64.7	64.7	66.4	66.4
75°	57.9	57.9	57.9	57.9	57.9	57.9	56.2	56.2	56.2	57.9	57.9
77.5°	52.8	52.8	52.8	51.1	51.1	51.1	49.4	49.4	49.4	51.1	51.1
80°	44.3	44.3	44.3	42.6	42.6	42.6	40.9	40.9	40.9	42.6	42.6
82.5°	35.7	35.7	35.7	34.0	34.0	34.0	32.3	32.3	32.3	34.0	34.0
85°	28.9	28.9	28.9	28.9	28.9	28.9	27.2	27.2	27.2	28.9	30.6
87.5°	13.6	13.6	15.3	15.3	15.3	15.3	13.6	13.6	11.9	11.9	13.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6
2.5°	1115.0	1118.4	1126.9	1133.7	1142.2	1149.0	1154.1	1160.9	1166.0	1171.1	1174.6
5°	960.1	961.8	970.3	978.8	985.6	994.1	1006.0	1017.9	1029.9	1041.8	1050.3
7.5°	747.3	754.1	764.3	776.2	786.4	796.7	808.6	822.2	834.1	846.0	857.9
10°	582.2	589.0	599.2	609.4	617.9	628.1	641.7	655.4	669.0	682.6	696.2
12.5°	488.5	497.1	509.0	520.9	531.1	543.0	560.0	575.4	592.4	607.7	624.7
15°	411.9	422.2	437.5	454.5	469.8	485.1	502.2	519.2	534.5	551.5	568.6
17.5°	338.7	349.0	362.6	377.9	391.5	405.1	425.6	444.3	464.7	483.4	502.2
20°	272.4	277.5	291.1	304.7	318.3	331.9	347.3	362.6	377.9	393.2	417.1
22.5°	226.4	229.8	236.6	241.7	248.5	253.6	269.0	284.3	297.9	313.2	335.3
25°	199.2	200.9	206.0	209.4	214.5	217.9	228.1	236.6	246.8	255.3	275.8
27.5°	185.5	187.2	188.9	190.7	192.4	194.1	200.9	207.7	212.8	219.6	238.3
30°	182.1	183.8	188.9	192.4	197.5	200.9	204.3	207.7	211.1	214.5	226.4
32.5°	178.7	180.4	180.4	178.7	178.7	177.0	180.4	182.1	185.5	187.2	197.5
35°	141.3	141.3	143.0	144.7	146.4	148.1	153.2	156.6	161.7	165.1	173.6
37.5°	132.8	132.8	134.5	137.9	139.6	141.3	144.7	148.1	151.5	154.9	163.4
40°	127.7	129.4	131.1	132.8	134.5	136.2	139.6	141.3	144.7	146.4	153.2
42.5°	122.6	122.6	124.3	127.7	129.4	131.1	134.5	136.2	139.6	141.3	148.1
45°	119.2	120.9	122.6	124.3	124.3	126.0	129.4	132.8	134.5	137.9	144.7
47.5°	114.1	114.1	117.5	119.2	122.6	124.3	127.7	129.4	132.8	134.5	141.3
50°	110.6	112.3	115.8	117.5	120.9	122.6	127.7	131.1	136.2	139.6	143.0
52.5°	107.2	108.9	112.3	114.1	117.5	119.2	126.0	132.8	137.9	144.7	144.7
55°	103.8	103.8	107.2	112.3	115.8	119.2	122.6	127.7	131.1	134.5	134.5
57.5°	98.7	100.4	103.8	108.9	112.3	115.8	119.2	122.6	124.3	127.7	126.0
60°	95.3	95.3	100.4	105.5	110.6	115.8	115.8	115.8	114.1	114.1	114.1
62.5°	90.2	91.9	98.7	107.2	114.1	120.9	115.8	110.6	105.5	100.4	102.1
65°	86.8	88.5	91.9	97.0	100.4	103.8	100.4	98.7	95.3	91.9	93.6
67.5°	80.0	81.7	83.4	83.4	85.1	85.1	85.1	85.1	85.1	85.1	86.8
70°	74.9	74.9	74.9	76.6	76.6	76.6	76.6	76.6	76.6	76.6	78.3
72.5°	68.1	68.1	68.1	68.1	68.1	68.1	68.1	68.1	68.1	68.1	69.8
75°	59.6	59.6	59.6	59.6	59.6	59.6	59.6	59.6	59.6	59.6	61.3
77.5°	52.8	52.8	52.8	52.8	52.8	52.8	52.8	52.8	51.1	51.1	52.8
80°	44.3	44.3	44.3	44.3	42.6	42.6	42.6	42.6	42.6	42.6	44.3
82.5°	35.7	35.7	35.7	35.7	34.0	34.0	34.0	34.0	32.3	32.3	34.0
85°	32.3	34.0	34.0	35.7	35.7	35.7	34.0	32.3	30.6	28.9	28.9
87.5°	13.6	13.6	13.6	13.6	11.9	11.9	11.9	11.9	11.9	11.9	11.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6
2.5°	1179.7	1183.1	1186.5	1191.6	1198.4	1203.5	1208.6	1218.8	1230.7	1240.9	1251.2
5°	1058.8	1067.3	1075.8	1086.0	1096.2	1104.8	1115.0	1135.4	1155.8	1174.6	1195.0
7.5°	868.1	880.1	890.3	907.3	922.6	939.6	955.0	980.5	1004.3	1029.9	1053.7
10°	709.8	723.5	737.1	759.2	783.0	805.2	827.3	847.7	869.8	890.3	910.7
12.5°	641.7	657.1	674.1	687.7	703.0	716.6	730.3	754.1	777.9	801.8	825.6
15°	585.6	602.6	619.6	636.6	652.0	669.0	684.3	704.7	726.9	747.3	767.7
17.5°	520.9	537.9	556.6	575.4	594.1	612.8	631.5	660.5	689.4	716.6	745.6
20°	439.2	463.0	485.1	510.7	536.2	561.7	587.3	617.9	648.6	677.5	708.1
22.5°	357.5	379.6	401.7	432.4	463.0	491.9	522.6	563.4	602.6	643.4	682.6
25°	297.9	318.3	338.7	372.8	405.1	439.2	471.5	520.9	568.6	617.9	665.6
27.5°	257.0	275.8	294.5	330.2	366.0	400.0	435.8	490.2	543.0	597.5	650.3
30°	238.3	250.2	262.1	296.2	330.2	362.6	396.6	449.4	502.2	554.9	607.7
32.5°	207.7	217.9	228.1	258.7	289.4	318.3	349.0	403.4	456.2	510.7	563.4
35°	183.8	192.4	200.9	229.8	257.0	286.0	313.2	367.7	422.2	476.6	531.1
37.5°	170.2	178.7	185.5	211.1	238.3	263.8	289.4	343.9	396.6	451.1	503.9
40°	160.0	165.1	171.9	197.5	221.3	246.8	270.7	320.0	371.1	420.5	469.8
42.5°	153.2	160.0	165.1	187.2	211.1	233.2	255.3	303.0	350.7	396.6	444.3
45°	151.5	158.3	165.1	183.8	202.6	219.6	238.3	284.3	330.2	376.2	422.2
47.5°	148.1	153.2	160.0	175.3	188.9	204.3	217.9	263.8	309.8	354.1	400.0
50°	146.4	148.1	151.5	165.1	178.7	192.4	206.0	251.9	297.9	343.9	389.8
52.5°	144.7	144.7	144.7	156.6	168.5	178.7	190.7	236.6	284.3	330.2	376.2
55°	134.5	132.8	132.8	144.7	154.9	166.8	177.0	223.0	269.0	313.2	359.2
57.5°	124.3	122.6	120.9	131.1	141.3	151.5	161.7	207.7	255.3	301.3	347.3
60°	114.1	112.3	112.3	122.6	131.1	141.3	149.8	197.5	243.4	291.1	337.0
62.5°	102.1	103.8	103.8	112.3	122.6	131.1	139.6	187.2	236.6	284.3	331.9
65°	93.6	95.3	95.3	105.5	115.8	126.0	136.2	182.1	229.8	275.8	321.7
67.5°	86.8	88.5	88.5	100.4	110.6	122.6	132.8	173.6	216.2	257.0	297.9
70°	80.0	80.0	81.7	93.6	105.5	117.5	129.4	165.1	200.9	234.9	270.7
72.5°	71.5	73.2	74.9	86.8	97.0	108.9	119.2	151.5	183.8	216.2	248.5
75°	63.0	64.7	66.4	76.6	86.8	97.0	107.2	137.9	166.8	197.5	226.4
77.5°	56.2	57.9	59.6	68.1	76.6	85.1	93.6	115.8	139.6	161.7	183.8
80°	46.0	46.0	47.7	54.5	61.3	66.4	73.2	88.5	103.8	117.5	132.8
82.5°	34.0	35.7	35.7	40.9	44.3	49.4	52.8	61.3	68.1	76.6	83.4
85°	28.9	27.2	27.2	30.6	32.3	35.7	37.4	42.6	46.0	51.1	54.5
87.5°	11.9	10.2	10.2	11.9	15.3	17.0	18.7	18.7	20.4	20.4	20.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6
2.5°	1256.3	1259.7	1264.8	1268.2	1276.7	1283.5	1292.0	1298.8	1303.9	1312.4	1309.0
5°	1210.3	1225.6	1240.9	1256.3	1268.2	1280.1	1290.3	1302.2	1315.8	1341.4	1348.2
7.5°	1074.1	1094.5	1113.3	1133.7	1157.5	1181.4	1205.2	1229.0	1251.2	1283.5	1303.9
10°	939.6	968.6	995.8	1024.8	1046.9	1069.0	1089.4	1111.6	1142.2	1174.6	1212.0
12.5°	854.5	883.5	912.4	941.3	973.7	1004.3	1036.7	1067.3	1096.2	1121.8	1164.3
15°	798.4	830.7	861.3	892.0	931.1	968.6	1007.7	1045.2	1087.7	1121.8	1150.7
17.5°	784.7	823.9	861.3	900.5	941.3	982.2	1023.1	1063.9	1106.5	1157.5	1195.0
20°	760.9	813.7	866.4	919.2	972.0	1023.1	1075.8	1126.9	1183.1	1244.3	1261.4
22.5°	747.3	810.3	875.0	937.9	1009.4	1082.6	1154.1	1225.6	1285.2	1331.2	1382.2
25°	745.6	823.9	903.9	982.2	1072.4	1160.9	1251.2	1339.7	1416.3	1462.2	1503.1
27.5°	743.9	839.2	932.8	1026.5	1137.1	1246.0	1356.7	1465.6	1537.1	1603.5	1637.6
30°	723.5	837.5	953.3	1067.3	1191.6	1315.8	1440.1	1564.4	1637.6	1683.5	1700.5
32.5°	697.9	832.4	966.9	1101.4	1242.6	1383.9	1523.5	1664.8	1722.7	1761.8	1748.2
35°	677.5	825.6	972.0	1118.4	1268.2	1419.7	1569.5	1719.3	1802.7	1857.2	1835.0
37.5°	658.8	813.7	968.6	1123.5	1298.8	1474.1	1649.5	1824.8	1904.8	1962.7	1937.2
40°	636.6	801.8	968.6	1133.7	1334.6	1533.7	1734.6	1933.8	2037.6	2087.0	2047.8
42.5°	617.9	789.8	963.5	1135.4	1349.9	1564.4	1778.8	1993.3	2109.1	2178.9	2129.5
45°	594.1	766.0	936.2	1108.2	1344.8	1581.4	1816.3	2052.9	2187.4	2241.9	2173.8
47.5°	568.6	738.8	907.3	1075.8	1327.8	1579.7	1831.6	2083.6	2207.8	2272.5	2209.5
50°	560.0	730.3	898.8	1069.0	1341.4	1615.4	1887.8	2160.2	2250.4	2303.1	2219.7
52.5°	558.3	738.8	920.9	1101.4	1375.4	1647.8	1921.8	2194.2	2267.4	2323.6	2248.7
55°	553.2	749.0	943.0	1137.1	1423.1	1710.8	1996.7	2282.7	2355.9	2396.8	2340.6
57.5°	558.3	769.4	978.8	1189.9	1484.4	1778.8	2073.3	2367.8	2456.3	2485.3	2473.4
60°	561.7	786.4	1009.4	1234.1	1521.8	1809.5	2097.2	2384.8	2476.8	2548.3	2561.9
62.5°	553.2	774.5	994.1	1215.4	1475.8	1736.3	1996.7	2257.2	2408.7	2514.2	2575.5
65°	527.7	732.0	937.9	1142.2	1382.2	1623.9	1864.0	2104.0	2264.0	2420.6	2470.0
67.5°	471.5	645.2	818.8	992.4	1201.8	1411.2	1618.8	1828.2	2029.1	2180.6	2248.7
70°	408.5	544.7	682.6	818.8	1009.4	1200.1	1390.7	1581.4	1758.4	1925.2	1989.9
72.5°	355.8	461.3	568.6	674.1	810.3	944.7	1080.9	1215.4	1424.8	1591.6	1654.6
75°	303.0	379.6	454.5	531.1	624.7	718.3	810.3	903.9	1052.0	1201.8	1264.8
77.5°	233.2	284.3	333.6	383.0	447.7	510.7	575.4	638.3	742.2	854.5	886.9
80°	161.7	190.7	217.9	246.8	297.9	349.0	400.0	451.1	519.2	582.2	631.5
82.5°	100.4	119.2	136.2	153.2	194.1	234.9	274.1	314.9	342.2	345.6	394.9
85°	64.7	76.6	86.8	97.0	120.9	146.4	170.2	194.1	173.6	161.7	192.4
87.5°	25.5	32.3	37.4	42.6	40.9	39.2	37.4	35.7	30.6	27.2	34.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6
2.5°	1312.4	1317.5	1322.6	1326.1	1331.2	1332.9	1334.6	1334.6	1336.3	1338.0	1341.4
5°	1375.4	1385.6	1395.8	1404.4	1414.6	1423.1	1429.9	1438.4	1445.2	1445.2	1443.5
7.5°	1322.6	1348.2	1373.7	1399.2	1424.8	1443.5	1460.5	1479.3	1496.3	1499.7	1503.1
10°	1252.9	1280.1	1305.6	1332.9	1358.4	1387.3	1414.6	1441.8	1470.7	1475.8	1482.7
12.5°	1188.2	1220.5	1252.9	1283.5	1315.8	1336.3	1356.7	1375.4	1395.8	1409.5	1423.1
15°	1186.5	1213.7	1240.9	1266.5	1293.7	1305.6	1317.5	1327.8	1339.7	1339.7	1341.4
17.5°	1225.6	1242.6	1259.7	1275.0	1292.0	1293.7	1297.1	1298.8	1300.5	1295.4	1290.3
20°	1302.2	1309.0	1315.8	1322.6	1329.5	1317.5	1307.3	1295.4	1283.5	1269.9	1258.0
22.5°	1414.6	1399.2	1383.9	1368.6	1353.3	1332.9	1310.7	1290.3	1268.2	1251.2	1234.1
25°	1520.1	1501.4	1482.7	1463.9	1445.2	1400.9	1356.7	1310.7	1266.5	1247.7	1229.0
27.5°	1661.4	1632.5	1603.5	1574.6	1545.6	1486.1	1426.5	1366.9	1307.3	1275.0	1244.3
30°	1695.4	1663.1	1630.8	1596.7	1564.4	1506.5	1450.3	1392.4	1334.6	1297.1	1261.4
32.5°	1744.8	1707.4	1669.9	1632.5	1595.0	1538.8	1482.7	1424.8	1368.6	1334.6	1298.8
35°	1826.5	1784.0	1741.4	1697.1	1654.6	1596.7	1540.5	1482.7	1424.8	1385.6	1348.2
37.5°	1896.3	1846.9	1797.6	1748.2	1698.8	1647.8	1595.0	1543.9	1491.2	1452.0	1414.6
40°	1974.6	1920.1	1865.7	1812.9	1758.4	1710.8	1663.1	1613.7	1566.1	1535.4	1504.8
42.5°	2042.7	1976.3	1911.6	1846.9	1780.6	1748.2	1717.6	1685.2	1652.9	1637.6	1620.5
45°	2090.4	2029.1	1966.1	1904.8	1843.5	1819.7	1795.9	1772.0	1748.2	1763.5	1778.8
47.5°	2110.8	2061.4	2013.8	1966.1	1916.7	1925.2	1933.8	1940.6	1949.1	1969.5	1991.6
50°	2129.5	2102.3	2073.3	2046.1	2017.2	2049.5	2080.1	2112.5	2144.8	2187.4	2229.9
52.5°	2167.0	2151.6	2138.0	2122.7	2107.4	2163.6	2219.7	2275.9	2332.1	2379.7	2427.4
55°	2279.3	2267.4	2255.5	2241.9	2229.9	2309.9	2388.3	2468.3	2548.3	2597.6	2647.0
57.5°	2434.2	2427.4	2418.9	2412.1	2403.6	2481.9	2558.5	2635.1	2713.4	2761.0	2810.4
60°	2551.7	2553.4	2553.4	2555.1	2555.1	2614.7	2674.2	2735.5	2795.1	2835.9	2878.5
62.5°	2614.7	2611.2	2607.8	2604.4	2601.0	2650.4	2699.8	2749.1	2798.5	2829.1	2859.8
65°	2546.6	2565.3	2584.0	2602.7	2621.5	2628.3	2633.4	2640.2	2645.3	2664.0	2682.7
67.5°	2318.5	2355.9	2391.7	2429.1	2464.9	2439.3	2415.5	2390.0	2364.4	2369.5	2372.9
70°	2064.8	2107.4	2151.6	2194.2	2236.8	2177.2	2117.6	2056.3	1996.7	1976.3	1955.9
72.5°	1741.4	1778.8	1818.0	1855.4	1892.9	1819.7	1748.2	1675.0	1601.8	1566.1	1530.3
75°	1331.2	1375.4	1421.4	1465.6	1509.9	1428.2	1344.8	1263.1	1179.7	1155.8	1133.7
77.5°	970.3	1023.1	1075.8	1128.6	1181.4	1108.2	1035.0	960.1	886.9	873.3	859.6
80°	706.4	747.3	786.4	827.3	866.4	823.9	781.3	738.8	696.2	694.5	692.8
82.5°	476.6	512.4	546.4	582.2	616.2	599.2	583.9	566.8	549.8	566.8	585.6
85°	245.1	294.5	345.6	394.9	444.3	439.2	435.8	430.7	425.6	447.7	468.1
87.5°	49.4	91.9	134.5	175.3	217.9	207.7	197.5	185.5	175.3	182.1	187.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6
2.5°	1343.1	1344.8	1344.8	1344.8	1344.8	1344.8	1341.4	1339.7	1336.3	1332.9	1327.8
5°	1443.5	1441.8	1435.0	1428.2	1419.7	1412.9	1407.8	1400.9	1395.8	1389.0	1378.8
7.5°	1506.5	1509.9	1498.0	1487.8	1475.8	1463.9	1452.0	1440.1	1428.2	1416.3	1392.4
10°	1487.8	1492.9	1486.1	1479.3	1470.7	1463.9	1450.3	1435.0	1421.4	1406.1	1377.1
12.5°	1435.0	1448.6	1445.2	1441.8	1438.4	1435.0	1426.5	1416.3	1407.8	1397.5	1365.2
15°	1341.4	1341.4	1343.1	1344.8	1344.8	1346.5	1348.2	1349.9	1351.6	1353.3	1334.6
17.5°	1285.2	1280.1	1280.1	1280.1	1280.1	1280.1	1286.9	1295.4	1302.2	1309.0	1303.9
20°	1244.3	1232.4	1230.7	1230.7	1229.0	1227.3	1239.2	1252.9	1264.8	1276.7	1283.5
22.5°	1217.1	1200.1	1198.4	1196.7	1195.0	1193.3	1208.6	1223.9	1239.2	1254.6	1278.4
25°	1210.3	1191.6	1193.3	1195.0	1195.0	1196.7	1208.6	1220.5	1232.4	1244.3	1285.2
27.5°	1212.0	1181.4	1183.1	1184.8	1184.8	1186.5	1205.2	1222.2	1240.9	1258.0	1309.0
30°	1223.9	1188.2	1184.8	1181.4	1178.0	1174.6	1200.1	1225.6	1251.2	1276.7	1315.8
32.5°	1264.8	1230.7	1222.2	1213.7	1205.2	1196.7	1227.3	1256.3	1286.9	1315.8	1348.2
35°	1309.0	1271.6	1268.2	1264.8	1259.7	1256.3	1283.5	1312.4	1339.7	1366.9	1395.8
37.5°	1375.4	1338.0	1334.6	1329.5	1326.1	1320.9	1351.6	1380.5	1411.2	1440.1	1465.6
40°	1474.1	1443.5	1441.8	1441.8	1440.1	1438.4	1462.2	1487.8	1511.6	1535.4	1552.4
42.5°	1605.2	1589.9	1595.0	1601.8	1606.9	1612.0	1630.8	1651.2	1669.9	1688.6	1683.5
45°	1794.2	1809.5	1811.2	1812.9	1814.6	1816.3	1821.4	1828.2	1833.3	1838.4	1818.0
47.5°	2012.1	2032.5	2042.7	2052.9	2061.4	2071.6	2064.8	2056.3	2049.5	2041.0	1989.9
50°	2270.8	2313.4	2311.7	2309.9	2306.5	2304.8	2291.2	2277.6	2262.3	2248.7	2173.8
52.5°	2475.1	2522.7	2531.2	2539.8	2548.3	2556.8	2531.2	2505.7	2478.5	2452.9	2359.3
55°	2694.7	2744.0	2745.7	2747.4	2747.4	2749.1	2713.4	2677.6	2640.2	2604.4	2507.4
57.5°	2858.1	2905.7	2900.6	2897.2	2892.1	2887.0	2844.5	2801.9	2759.3	2716.8	2619.8
60°	2919.4	2960.2	2950.0	2939.8	2927.9	2917.7	2885.3	2853.0	2818.9	2786.6	2693.0
62.5°	2890.4	2921.1	2905.7	2892.1	2876.8	2861.5	2820.6	2778.1	2737.2	2694.7	2626.6
65°	2699.8	2718.5	2698.1	2679.3	2660.6	2640.2	2606.1	2572.1	2536.3	2502.3	2456.3
67.5°	2378.0	2381.4	2379.7	2378.0	2376.3	2374.6	2325.3	2275.9	2224.8	2175.5	2172.1
70°	1937.2	1916.7	1920.1	1925.2	1928.6	1932.1	1894.6	1858.9	1821.4	1784.0	1801.0
72.5°	1494.6	1458.8	1467.3	1477.6	1486.1	1494.6	1463.9	1435.0	1404.4	1373.7	1397.5
75°	1109.9	1087.7	1096.2	1106.5	1115.0	1123.5	1111.6	1099.7	1086.0	1074.1	1096.2
77.5°	846.0	832.4	834.1	834.1	835.8	835.8	837.5	840.9	842.6	844.3	868.1
80°	689.4	687.7	686.0	684.3	680.9	679.2	696.2	713.2	730.3	747.3	759.2
82.5°	602.6	619.6	609.4	600.9	590.7	580.5	595.8	611.1	626.4	641.7	636.6
85°	490.2	510.7	491.9	473.2	452.8	434.1	447.7	459.6	473.2	485.1	478.3
87.5°	194.1	199.2	168.5	139.6	108.9	78.3	124.3	168.5	214.5	258.7	265.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6	1225.6
2.5°	1322.6	1315.8	1310.7	1309.0	1305.6	1303.9	1300.5	1297.1	1292.0	1288.6	1283.5
5°	1366.9	1356.7	1344.8	1327.8	1312.4	1295.4	1278.4	1263.1	1247.7	1230.7	1215.4
7.5°	1368.6	1344.8	1320.9	1298.8	1275.0	1252.9	1229.0	1208.6	1186.5	1164.3	1143.9
10°	1349.9	1320.9	1292.0	1263.1	1235.8	1206.9	1178.0	1154.1	1128.6	1103.1	1079.2
12.5°	1334.6	1302.2	1269.9	1235.8	1203.5	1169.4	1135.4	1111.6	1087.7	1063.9	1040.1
15°	1315.8	1295.4	1276.7	1246.0	1215.4	1184.8	1154.1	1121.8	1091.1	1058.8	1026.5
17.5°	1300.5	1295.4	1290.3	1269.9	1249.4	1227.3	1206.9	1174.6	1142.2	1108.2	1075.8
20°	1292.0	1298.8	1305.6	1295.4	1285.2	1273.3	1263.1	1239.2	1215.4	1189.9	1166.0
22.5°	1302.2	1327.8	1351.6	1353.3	1356.7	1358.4	1360.1	1338.0	1315.8	1292.0	1269.9
25°	1326.1	1366.9	1407.8	1429.9	1452.0	1475.8	1498.0	1484.4	1470.7	1457.1	1443.5
27.5°	1358.4	1409.5	1460.5	1492.9	1523.5	1555.9	1588.2	1586.5	1584.8	1581.4	1579.7
30°	1353.3	1392.4	1431.6	1470.7	1509.9	1549.0	1588.2	1608.6	1627.3	1647.8	1668.2
32.5°	1382.2	1414.6	1448.6	1489.5	1530.3	1572.9	1613.7	1656.3	1697.1	1739.7	1782.3
35°	1426.5	1455.4	1486.1	1530.3	1576.3	1620.5	1666.5	1717.6	1770.3	1823.1	1874.2
37.5°	1492.9	1518.4	1545.6	1583.1	1622.2	1659.7	1698.8	1773.7	1848.6	1925.2	2000.1
40°	1569.5	1586.5	1603.5	1639.3	1675.0	1710.8	1746.5	1840.1	1933.8	2027.4	2121.0
42.5°	1680.1	1675.0	1669.9	1698.8	1729.5	1758.4	1789.1	1874.2	1959.3	2044.4	2129.5
45°	1797.6	1777.1	1756.7	1770.3	1785.7	1799.3	1814.6	1901.4	1988.2	2076.7	2163.6
47.5°	1938.9	1887.8	1836.7	1824.8	1812.9	1799.3	1787.4	1881.0	1974.6	2069.9	2163.6
50°	2098.9	2022.3	1947.4	1916.7	1884.4	1853.7	1821.4	1898.0	1976.3	2054.6	2131.2
52.5°	2265.7	2170.4	2076.7	2029.1	1981.4	1932.1	1884.4	1949.1	2015.5	2081.8	2146.5
55°	2408.7	2311.7	2212.9	2156.7	2100.6	2044.4	1988.2	2052.9	2117.6	2182.3	2247.0
57.5°	2522.7	2425.7	2328.7	2275.9	2221.4	2168.7	2114.2	2175.5	2238.5	2301.4	2362.7
60°	2601.0	2507.4	2413.8	2362.7	2311.7	2260.6	2209.5	2282.7	2355.9	2430.8	2504.0
62.5°	2560.2	2492.1	2424.0	2401.9	2379.7	2355.9	2333.8	2403.6	2471.7	2541.5	2611.2
65°	2410.4	2364.4	2318.5	2340.6	2364.4	2386.5	2410.4	2456.3	2502.3	2550.0	2595.9
67.5°	2167.0	2163.6	2158.4	2207.8	2257.2	2308.2	2357.6	2388.3	2417.2	2447.8	2478.5
70°	1818.0	1836.7	1853.7	1938.9	2024.0	2109.1	2194.2	2206.1	2218.0	2229.9	2241.9
72.5°	1423.1	1446.9	1472.4	1584.8	1695.4	1807.8	1920.1	1913.3	1906.5	1898.0	1891.2
75°	1120.1	1142.2	1166.0	1269.9	1373.7	1477.6	1581.4	1552.4	1525.2	1496.3	1467.3
77.5°	893.7	917.5	943.0	1040.1	1137.1	1235.8	1332.9	1263.1	1193.3	1123.5	1053.7
80°	769.4	781.3	791.5	857.9	922.6	989.0	1055.4	983.9	910.7	837.5	766.0
82.5°	631.5	624.7	619.6	658.8	697.9	737.1	776.2	708.1	640.0	570.3	502.2
85°	471.5	464.7	457.9	478.3	498.8	520.9	541.3	463.0	384.7	304.7	226.4
87.5°	274.1	280.9	287.7	309.8	331.9	355.8	377.9	297.9	217.9	136.2	56.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835

CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671835
 CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1225.6	1225.6
2.5°	1273.3	1264.8
5°	1203.5	1191.6
7.5°	1126.9	1111.6
10°	1057.1	1036.7
12.5°	1012.8	987.3
15°	995.8	965.2
17.5°	1046.9	1017.9
20°	1125.2	1086.0
22.5°	1220.5	1172.8
25°	1385.6	1327.8
27.5°	1520.1	1460.5
30°	1603.5	1538.8
32.5°	1695.4	1610.3
35°	1790.8	1709.1
37.5°	1906.5	1814.6
40°	2025.7	1930.3
42.5°	2066.5	2005.2
45°	2105.7	2047.8
47.5°	2114.2	2066.5
50°	2122.7	2115.9
52.5°	2146.5	2144.8
55°	2248.7	2250.4
57.5°	2374.6	2384.8
60°	2490.4	2478.5
62.5°	2550.0	2488.7
65°	2509.1	2424.0
67.5°	2386.5	2294.6
70°	2117.6	1993.3
72.5°	1782.3	1673.3
75°	1373.7	1281.8
77.5°	977.1	900.5
80°	687.7	611.1
82.5°	440.9	379.6
85°	199.2	173.6
87.5°	56.2	54.5
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671835
CATALOG NUMBER: CCP-SA-1C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)