

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671836

Luminaire Tested: **CCP-SA-1D-750-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671836
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1D-750-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @800mA w/ SLR
distribution lens
Light Source: (16) 5000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4734.2 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 44
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 6.7 fc

Type IV - Short - N/A

REPORT NUMBER: P671836
CATALOG NUMBER: CCP-SA-1D-750-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	974.1	0.0	974.1
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3760.0	0.0	3760.0
	% Fixture	79.4	0.0	79.4
Total	Lumens	4734.2	0.0	4734.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.5	2.5
10°-20°	248.0	5.2
20°-30°	362.9	7.7
30°-40°	511.2	10.8
40°-50°	702.5	14.8
50°-60°	957.5	20.2
60°-70°	1048.0	22.1
70°-80°	605.2	12.8
80°-90°	181.4	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4734.2	100.0
0°-180°	4734.2	100.0

Coefficient of Utilization



REPORT NUMBER: P671836


CATALOG NUMBER: CCP-SA-1D-750-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	486.2	10.3			
FM	(30°-60°)	1727.6	36.5			
FH	(60°-80°)	1392.1	29.4			G1/1800
FVH	(80°-90°)	154.1	3.3			G2/225
BL	(0°-30°)	242.2	5.1	B1/500		
BM	(30°-60°)	443.6	9.4	B1/1000		
BH	(60°-80°)	261.1	5.5	B1/500		G1/500
BVH	(80°-90°)	27.3	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8
2.5°	1560.1	1551.7	1545.4	1539.1	1530.7	1524.4	1516.0	1507.6	1497.1	1488.7	1478.2
5°	1469.8	1444.6	1419.4	1404.7	1387.9	1373.2	1356.4	1337.5	1318.6	1297.6	1278.7
7.5°	1371.1	1339.6	1308.1	1282.9	1255.6	1230.4	1203.1	1180.0	1156.9	1133.8	1110.7
10°	1278.7	1249.3	1219.9	1188.4	1154.8	1123.3	1089.7	1058.2	1026.7	995.3	963.8
12.5°	1217.8	1182.1	1148.5	1112.8	1079.2	1043.5	1007.9	978.5	949.1	917.6	888.2
15°	1190.5	1156.9	1125.4	1089.7	1054.0	1018.3	982.7	949.1	917.6	884.0	850.4
17.5°	1255.6	1207.3	1159.0	1112.8	1066.6	1020.4	974.3	932.3	890.3	848.3	806.3
20°	1339.6	1278.7	1219.9	1163.2	1104.4	1047.7	989.0	930.2	871.4	812.6	753.8
22.5°	1446.7	1377.4	1310.2	1236.7	1161.1	1087.6	1012.1	938.6	865.1	789.5	716.0
25°	1637.8	1555.9	1474.0	1369.0	1261.9	1156.9	1049.8	953.3	858.8	762.2	665.6
27.5°	1801.5	1690.2	1581.1	1455.1	1329.1	1203.1	1077.1	965.9	856.7	745.4	634.1
30°	1898.1	1788.9	1679.8	1526.5	1375.3	1222.0	1068.7	944.9	823.1	699.2	575.3
32.5°	1986.3	1864.5	1742.7	1574.8	1404.7	1236.7	1066.6	930.2	795.8	659.3	522.8
35°	2108.1	1973.7	1841.4	1646.2	1450.9	1255.6	1060.3	919.7	776.9	636.2	493.4
37.5°	2238.3	2072.4	1908.6	1692.3	1476.1	1259.8	1043.5	905.0	766.4	627.8	489.2
40°	2381.0	2179.5	1980.0	1740.6	1503.4	1264.0	1024.6	886.1	747.5	606.8	468.2
42.5°	2473.4	2255.1	2036.7	1778.4	1522.3	1264.0	1005.8	869.3	732.8	594.2	457.7
45°	2525.9	2313.9	2103.9	1824.6	1545.4	1266.1	986.9	852.5	718.1	581.6	447.2
47.5°	2549.0	2351.7	2154.3	1860.3	1568.5	1274.5	980.6	844.1	705.5	569.0	430.4
50°	2609.9	2435.6	2261.4	1946.4	1633.6	1318.6	1003.7	856.7	711.8	564.8	417.8
52.5°	2645.6	2496.5	2347.5	2024.1	1700.7	1377.4	1054.0	890.3	726.5	562.7	398.9
55°	2775.8	2633.0	2490.2	2145.9	1799.4	1455.1	1108.6	928.1	747.5	564.8	384.2
57.5°	2941.7	2790.5	2641.4	2269.8	1898.1	1526.5	1154.8	961.7	766.4	573.2	377.9
60°	3057.1	2910.2	2765.3	2370.5	1973.7	1579.0	1182.1	980.6	779.0	575.3	373.7
62.5°	3069.7	2880.8	2693.9	2309.7	1925.4	1539.1	1154.8	959.6	764.3	566.9	371.6
65°	2990.0	2769.5	2549.0	2181.6	1814.1	1446.7	1079.2	900.8	722.3	541.7	363.2
67.5°	2830.4	2572.1	2313.9	1977.9	1642.0	1306.0	970.1	816.8	665.6	512.3	359.0
70°	2458.7	2232.0	2007.3	1715.4	1425.7	1133.8	842.0	716.0	592.1	466.1	340.1
72.5°	2064.0	1851.9	1642.0	1404.7	1169.5	932.3	695.0	600.5	506.0	409.4	315.0
75°	1581.1	1421.5	1264.0	1087.6	911.3	732.8	556.4	487.1	417.8	348.5	279.3
77.5°	1110.7	1024.6	940.7	808.4	676.1	543.8	411.5	365.3	319.2	273.0	226.8
80°	753.8	705.5	659.3	564.8	470.3	373.7	279.3	249.9	218.4	189.0	157.5
82.5°	468.2	466.1	461.9	396.8	331.8	266.7	201.6	176.4	153.3	128.1	102.9
85°	214.2	249.9	283.5	247.8	212.1	176.4	140.7	123.9	107.1	88.2	71.4
87.5°	67.2	81.9	94.5	90.3	84.0	79.8	73.5	63.0	52.5	42.0	31.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8
2.5°	1469.8	1463.5	1455.1	1446.7	1436.2	1427.8	1417.3	1406.8	1404.7	1400.5	1398.4
5°	1266.1	1253.5	1238.8	1226.2	1213.6	1198.9	1186.3	1171.6	1161.1	1148.5	1138.0
7.5°	1087.6	1066.6	1043.5	1020.4	999.5	978.5	955.4	934.4	923.9	913.4	902.9
10°	944.9	923.9	905.0	884.0	869.3	856.7	842.0	827.3	814.7	802.1	789.5
12.5°	873.5	858.8	844.1	829.4	812.6	797.9	781.1	764.3	749.6	737.0	722.3
15°	829.4	808.4	785.3	764.3	741.2	720.2	697.1	674.0	657.2	642.5	625.7
17.5°	776.9	745.4	716.0	684.5	659.3	634.1	606.8	581.6	562.7	541.7	522.8
20°	718.1	682.4	644.6	608.9	579.5	552.2	522.8	493.4	472.4	449.3	428.3
22.5°	667.7	621.5	573.2	524.9	493.4	461.9	428.3	396.8	377.9	356.9	338.0
25°	613.1	562.7	510.2	457.7	426.2	392.6	361.1	327.6	312.9	300.3	285.6
27.5°	583.7	533.3	480.8	430.4	401.0	369.5	340.1	308.7	298.2	285.6	275.1
30°	524.9	476.6	426.2	375.8	354.8	336.0	315.0	294.0	289.8	287.7	283.5
32.5°	472.4	422.0	371.6	321.3	302.4	283.5	264.6	245.7	243.6	239.4	237.3
35°	445.1	396.8	346.4	298.2	281.4	262.5	245.7	226.8	222.6	216.3	212.1
37.5°	438.8	388.4	336.0	285.6	268.8	252.0	233.1	216.3	212.1	207.9	203.7
40°	422.0	373.7	327.6	279.3	262.5	245.7	226.8	210.0	205.8	201.6	197.4
42.5°	409.4	363.2	315.0	266.7	252.0	237.3	220.5	205.8	201.6	197.4	191.1
45°	398.9	350.6	300.3	252.0	241.5	231.0	218.4	207.9	203.7	197.4	193.2
47.5°	382.1	336.0	287.7	239.4	228.9	220.5	210.0	199.5	195.3	191.1	186.9
50°	369.5	321.3	273.0	224.7	216.3	207.9	199.5	191.1	191.1	193.2	193.2
52.5°	352.7	306.6	260.4	214.2	205.8	197.4	189.0	180.6	182.7	184.8	186.9
55°	338.0	294.0	247.8	201.6	193.2	184.8	174.3	165.9	168.0	170.1	172.2
57.5°	331.8	285.6	239.4	193.2	184.8	174.3	165.9	155.4	155.4	155.4	155.4
60°	327.6	279.3	233.1	184.8	174.3	165.9	155.4	144.9	142.8	142.8	140.7
62.5°	325.5	277.2	231.0	182.7	170.1	159.6	147.0	134.4	132.3	130.2	128.1
65°	317.1	273.0	226.8	180.6	165.9	153.3	138.6	123.9	121.8	121.8	119.7
67.5°	315.0	268.8	224.7	178.5	163.8	147.0	132.3	115.5	113.4	111.3	109.2
70°	298.2	258.3	216.3	174.3	157.5	142.8	126.0	109.2	107.1	102.9	100.8
72.5°	277.2	241.5	203.7	165.9	149.1	132.3	115.5	98.7	96.6	94.5	90.3
75°	245.7	212.1	178.5	144.9	130.2	117.6	102.9	88.2	86.1	84.0	79.8
77.5°	201.6	174.3	149.1	121.8	111.3	100.8	90.3	79.8	77.7	75.6	71.4
80°	142.8	126.0	111.3	94.5	88.2	79.8	73.5	65.1	65.1	63.0	63.0
82.5°	94.5	86.1	77.7	69.3	65.1	60.9	56.7	52.5	52.5	50.4	50.4
85°	67.2	63.0	56.7	52.5	50.4	46.2	44.1	39.9	39.9	39.9	39.9
87.5°	31.5	31.5	29.4	29.4	27.3	27.3	25.2	23.1	23.1	23.1	23.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8
2.5°	1394.2	1387.9	1381.6	1373.2	1366.9	1358.5	1348.0	1339.6	1329.1	1329.1	1327.0
5°	1125.4	1119.1	1112.8	1104.4	1098.1	1089.7	1083.4	1075.0	1066.6	1066.6	1064.5
7.5°	892.4	879.8	867.2	852.5	839.9	831.5	823.1	812.6	804.2	797.9	791.6
10°	776.9	764.3	749.6	737.0	722.3	711.8	701.3	688.7	678.2	669.8	661.4
12.5°	707.6	692.9	678.2	663.5	648.8	634.1	621.5	606.8	592.1	581.6	571.1
15°	608.9	594.2	579.5	564.8	550.1	533.3	516.5	497.6	480.8	472.4	466.1
17.5°	501.8	487.1	470.3	455.6	438.8	426.2	413.6	401.0	388.4	380.0	373.7
20°	405.2	388.4	371.6	354.8	338.0	329.7	321.3	312.9	304.5	298.2	294.0
22.5°	317.1	306.6	298.2	287.7	277.2	270.9	266.7	260.4	254.1	254.1	254.1
25°	270.9	264.6	260.4	254.1	247.8	245.7	243.6	239.4	237.3	235.2	235.2
27.5°	262.5	256.2	249.9	243.6	237.3	235.2	233.1	228.9	226.8	226.8	226.8
30°	279.3	277.2	275.1	273.0	270.9	266.7	260.4	256.2	249.9	245.7	241.5
32.5°	233.1	231.0	231.0	228.9	226.8	231.0	233.1	237.3	239.4	241.5	243.6
35°	205.8	201.6	197.4	193.2	189.0	186.9	184.8	182.7	180.6	180.6	178.5
37.5°	199.5	195.3	191.1	186.9	182.7	180.6	178.5	176.4	174.3	174.3	172.2
40°	193.2	189.0	186.9	182.7	178.5	176.4	174.3	170.1	168.0	165.9	165.9
42.5°	186.9	184.8	180.6	178.5	174.3	172.2	170.1	165.9	163.8	161.7	159.6
45°	186.9	182.7	178.5	174.3	170.1	168.0	163.8	161.7	157.5	157.5	155.4
47.5°	182.7	178.5	174.3	170.1	165.9	163.8	159.6	157.5	153.3	151.2	149.1
50°	193.2	186.9	178.5	172.2	163.8	161.7	157.5	155.4	151.2	149.1	147.0
52.5°	189.0	182.7	174.3	168.0	159.6	155.4	153.3	149.1	144.9	142.8	140.7
55°	174.3	168.0	163.8	157.5	151.2	147.0	142.8	138.6	134.4	132.3	132.3
57.5°	155.4	153.3	151.2	149.1	147.0	142.8	138.6	132.3	128.1	126.0	123.9
60°	138.6	140.7	142.8	144.9	147.0	140.7	134.4	128.1	121.8	119.7	117.6
62.5°	126.0	130.2	134.4	136.5	140.7	134.4	128.1	121.8	115.5	113.4	111.3
65°	117.6	119.7	119.7	121.8	121.8	117.6	115.5	111.3	107.1	105.0	105.0
67.5°	107.1	107.1	107.1	105.0	105.0	102.9	102.9	100.8	98.7	96.6	96.6
70°	96.6	96.6	96.6	94.5	94.5	92.4	92.4	90.3	88.2	88.2	86.1
72.5°	88.2	88.2	86.1	86.1	84.0	84.0	84.0	81.9	81.9	79.8	79.8
75°	77.7	77.7	75.6	75.6	73.5	73.5	73.5	71.4	71.4	71.4	69.3
77.5°	69.3	69.3	67.2	67.2	65.1	65.1	65.1	63.0	63.0	60.9	60.9
80°	60.9	60.9	58.8	58.8	56.7	56.7	54.6	54.6	52.5	52.5	50.4
82.5°	48.3	48.3	48.3	48.3	48.3	46.2	46.2	44.1	42.0	42.0	39.9
85°	39.9	39.9	39.9	37.8	37.8	37.8	35.7	35.7	33.6	31.5	31.5
87.5°	23.1	23.1	23.1	21.0	21.0	21.0	21.0	21.0	21.0	21.0	18.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8
2.5°	1327.0	1324.9	1316.5	1308.1	1316.5	1324.9	1324.9	1324.9	1322.8	1322.8	1322.8
5°	1064.5	1062.4	1058.2	1054.0	1054.0	1051.9	1056.1	1060.3	1064.5	1068.7	1072.9
7.5°	783.2	776.9	770.6	764.3	768.5	770.6	776.9	781.1	787.4	791.6	802.1
10°	653.0	644.6	638.3	632.0	627.8	623.6	619.4	617.3	613.1	608.9	613.1
12.5°	558.5	548.0	537.5	524.9	522.8	520.7	516.5	512.3	508.1	503.9	501.8
15°	457.7	449.3	445.1	438.8	430.4	422.0	417.8	415.7	411.5	407.3	405.2
17.5°	365.3	356.9	350.6	344.3	342.2	338.0	338.0	338.0	338.0	338.0	338.0
20°	287.7	281.4	281.4	279.3	279.3	277.2	279.3	281.4	281.4	283.5	285.6
22.5°	252.0	252.0	249.9	247.8	249.9	249.9	252.0	254.1	256.2	258.3	260.4
25°	233.1	231.0	233.1	235.2	235.2	235.2	237.3	237.3	239.4	239.4	239.4
27.5°	224.7	224.7	226.8	226.8	228.9	228.9	228.9	226.8	226.8	224.7	224.7
30°	237.3	233.1	233.1	233.1	231.0	228.9	226.8	226.8	224.7	222.6	220.5
32.5°	245.7	247.8	245.7	241.5	239.4	235.2	233.1	228.9	226.8	222.6	218.4
35°	178.5	176.4	180.6	182.7	184.8	186.9	189.0	191.1	191.1	193.2	193.2
37.5°	172.2	170.1	170.1	168.0	168.0	168.0	168.0	168.0	165.9	165.9	168.0
40°	163.8	161.7	161.7	159.6	159.6	157.5	157.5	157.5	157.5	157.5	157.5
42.5°	157.5	155.4	155.4	155.4	155.4	153.3	153.3	151.2	151.2	149.1	149.1
45°	155.4	153.3	151.2	149.1	149.1	147.0	147.0	147.0	144.9	144.9	144.9
47.5°	147.0	144.9	144.9	142.8	142.8	140.7	140.7	140.7	138.6	138.6	138.6
50°	142.8	140.7	140.7	138.6	138.6	136.5	136.5	136.5	134.4	134.4	134.4
52.5°	136.5	134.4	134.4	134.4	132.3	130.2	130.2	130.2	128.1	128.1	128.1
55°	130.2	128.1	128.1	128.1	126.0	123.9	123.9	123.9	121.8	121.8	121.8
57.5°	121.8	119.7	119.7	117.6	117.6	117.6	117.6	117.6	115.5	115.5	115.5
60°	115.5	113.4	113.4	111.3	111.3	109.2	109.2	109.2	109.2	109.2	109.2
62.5°	109.2	107.1	105.0	102.9	105.0	105.0	105.0	105.0	102.9	102.9	102.9
65°	102.9	100.8	98.7	96.6	96.6	96.6	96.6	96.6	96.6	96.6	96.6
67.5°	94.5	92.4	90.3	88.2	90.3	90.3	90.3	90.3	90.3	90.3	90.3
70°	86.1	84.0	84.0	81.9	81.9	79.8	79.8	81.9	81.9	81.9	81.9
72.5°	77.7	75.6	75.6	73.5	73.5	73.5	73.5	73.5	73.5	73.5	73.5
75°	69.3	67.2	67.2	65.1	65.1	65.1	65.1	65.1	65.1	65.1	65.1
77.5°	58.8	56.7	56.7	56.7	56.7	56.7	56.7	58.8	58.8	58.8	58.8
80°	50.4	48.3	48.3	48.3	48.3	48.3	48.3	48.3	48.3	48.3	48.3
82.5°	39.9	37.8	37.8	37.8	37.8	37.8	37.8	37.8	37.8	37.8	37.8
85°	29.4	27.3	27.3	27.3	29.4	29.4	29.4	29.4	29.4	29.4	29.4
87.5°	18.9	16.8	16.8	16.8	18.9	18.9	18.9	18.9	16.8	16.8	16.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8
2.5°	1322.8	1322.8	1322.8	1320.7	1318.6	1316.5	1314.4	1320.7	1324.9	1331.2	1335.4
5°	1075.0	1079.2	1081.3	1087.6	1093.9	1100.2	1106.5	1110.7	1114.9	1117.0	1121.2
7.5°	810.5	821.0	829.4	837.8	846.2	852.5	860.9	867.2	873.5	879.8	886.1
10°	615.2	619.4	621.5	629.9	636.2	644.6	650.9	657.2	663.5	667.7	674.0
12.5°	499.7	495.5	493.4	493.4	493.4	493.4	493.4	497.6	501.8	506.0	510.2
15°	403.1	401.0	398.9	396.8	394.7	390.5	388.4	392.6	396.8	401.0	405.2
17.5°	338.0	338.0	338.0	336.0	333.9	331.8	329.7	331.8	333.9	333.9	336.0
20°	289.8	291.9	294.0	296.1	296.1	298.2	298.2	300.3	302.4	302.4	304.5
22.5°	260.4	262.5	262.5	262.5	264.6	264.6	264.6	266.7	268.8	270.9	273.0
25°	237.3	237.3	235.2	235.2	237.3	237.3	237.3	237.3	239.4	239.4	239.4
27.5°	224.7	222.6	222.6	222.6	222.6	220.5	220.5	220.5	220.5	220.5	220.5
30°	218.4	216.3	214.2	212.1	212.1	210.0	207.9	207.9	207.9	207.9	207.9
32.5°	216.3	212.1	207.9	205.8	205.8	203.7	201.6	199.5	199.5	197.4	195.3
35°	193.2	191.1	191.1	189.0	186.9	184.8	182.7	182.7	182.7	180.6	180.6
37.5°	168.0	170.1	170.1	170.1	172.2	172.2	172.2	172.2	174.3	174.3	174.3
40°	157.5	157.5	157.5	159.6	161.7	161.7	163.8	163.8	165.9	165.9	165.9
42.5°	149.1	147.0	147.0	149.1	149.1	151.2	151.2	153.3	155.4	155.4	157.5
45°	144.9	142.8	142.8	142.8	142.8	140.7	140.7	142.8	144.9	147.0	149.1
47.5°	136.5	136.5	134.4	134.4	134.4	134.4	134.4	134.4	136.5	136.5	136.5
50°	132.3	132.3	130.2	130.2	130.2	130.2	130.2	130.2	130.2	130.2	130.2
52.5°	128.1	126.0	126.0	126.0	126.0	123.9	123.9	123.9	123.9	123.9	123.9
55°	121.8	119.7	119.7	119.7	119.7	119.7	119.7	119.7	121.8	121.8	121.8
57.5°	115.5	113.4	113.4	113.4	115.5	115.5	115.5	115.5	117.6	117.6	117.6
60°	109.2	109.2	109.2	109.2	109.2	109.2	109.2	111.3	111.3	113.4	113.4
62.5°	102.9	102.9	102.9	102.9	105.0	105.0	105.0	105.0	107.1	107.1	107.1
65°	96.6	96.6	96.6	96.6	98.7	98.7	98.7	98.7	98.7	98.7	98.7
67.5°	90.3	90.3	90.3	90.3	90.3	90.3	90.3	92.4	92.4	94.5	94.5
70°	81.9	79.8	79.8	81.9	81.9	84.0	84.0	86.1	86.1	88.2	88.2
72.5°	73.5	73.5	73.5	73.5	73.5	73.5	73.5	75.6	77.7	77.7	79.8
75°	65.1	65.1	65.1	65.1	67.2	67.2	67.2	69.3	69.3	71.4	71.4
77.5°	58.8	56.7	56.7	56.7	58.8	58.8	58.8	60.9	60.9	63.0	63.0
80°	48.3	48.3	48.3	48.3	50.4	50.4	50.4	50.4	52.5	52.5	52.5
82.5°	39.9	39.9	39.9	39.9	39.9	39.9	39.9	39.9	42.0	42.0	42.0
85°	29.4	29.4	29.4	29.4	31.5	31.5	31.5	31.5	31.5	31.5	31.5
87.5°	18.9	18.9	18.9	18.9	18.9	18.9	18.9	18.9	21.0	21.0	21.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8
2.5°	1335.4	1335.4	1335.4	1335.4	1339.6	1341.7	1345.9	1348.0	1345.9	1343.8	1339.6
5°	1123.3	1125.4	1125.4	1127.5	1127.5	1127.5	1127.5	1127.5	1131.7	1135.9	1140.1
7.5°	888.2	890.3	892.4	894.5	894.5	894.5	892.4	892.4	894.5	894.5	896.6
10°	680.3	688.7	695.0	701.3	697.1	690.8	686.6	680.3	680.3	680.3	678.2
12.5°	514.4	516.5	520.7	522.8	520.7	520.7	518.6	516.5	518.6	522.8	524.9
15°	407.3	407.3	409.4	409.4	411.5	413.6	413.6	415.7	419.9	422.0	426.2
17.5°	338.0	340.1	340.1	342.2	342.2	344.3	344.3	344.3	348.5	352.7	359.0
20°	304.5	304.5	304.5	304.5	304.5	302.4	302.4	300.3	302.4	306.6	308.7
22.5°	273.0	275.1	275.1	275.1	273.0	270.9	266.7	264.6	264.6	266.7	266.7
25°	239.4	237.3	237.3	235.2	235.2	237.3	237.3	237.3	239.4	239.4	241.5
27.5°	220.5	218.4	218.4	216.3	216.3	218.4	218.4	218.4	218.4	218.4	218.4
30°	205.8	205.8	203.7	201.6	203.7	203.7	205.8	205.8	207.9	207.9	210.0
32.5°	195.3	193.2	193.2	191.1	193.2	193.2	195.3	195.3	197.4	199.5	199.5
35°	180.6	180.6	180.6	180.6	180.6	180.6	178.5	178.5	178.5	178.5	178.5
37.5°	172.2	172.2	170.1	168.0	168.0	168.0	168.0	168.0	165.9	163.8	161.7
40°	165.9	163.8	163.8	161.7	159.6	159.6	157.5	155.4	155.4	153.3	153.3
42.5°	157.5	155.4	155.4	153.3	151.2	151.2	149.1	147.0	147.0	147.0	144.9
45°	147.0	147.0	144.9	142.8	142.8	142.8	140.7	140.7	140.7	140.7	138.6
47.5°	136.5	136.5	134.4	134.4	134.4	134.4	132.3	132.3	132.3	132.3	132.3
50°	130.2	130.2	130.2	130.2	130.2	130.2	128.1	128.1	128.1	128.1	128.1
52.5°	123.9	123.9	123.9	123.9	123.9	123.9	123.9	123.9	123.9	123.9	123.9
55°	121.8	121.8	121.8	121.8	121.8	121.8	119.7	119.7	119.7	121.8	121.8
57.5°	117.6	117.6	115.5	115.5	115.5	115.5	115.5	115.5	115.5	115.5	115.5
60°	113.4	113.4	113.4	113.4	113.4	113.4	113.4	113.4	113.4	113.4	113.4
62.5°	107.1	107.1	107.1	107.1	107.1	109.2	109.2	109.2	109.2	109.2	107.1
65°	98.7	100.8	100.8	100.8	100.8	100.8	100.8	100.8	100.8	100.8	100.8
67.5°	94.5	94.5	94.5	94.5	94.5	94.5	94.5	94.5	94.5	94.5	94.5
70°	88.2	88.2	86.1	86.1	86.1	88.2	88.2	88.2	88.2	88.2	88.2
72.5°	79.8	79.8	79.8	79.8	79.8	79.8	79.8	79.8	79.8	81.9	81.9
75°	71.4	71.4	71.4	71.4	71.4	71.4	71.4	71.4	71.4	71.4	71.4
77.5°	63.0	63.0	60.9	60.9	60.9	63.0	63.0	63.0	63.0	65.1	65.1
80°	52.5	52.5	52.5	52.5	52.5	52.5	52.5	52.5	52.5	54.6	54.6
82.5°	42.0	42.0	42.0	42.0	42.0	42.0	42.0	42.0	42.0	44.1	44.1
85°	31.5	33.6	33.6	33.6	33.6	33.6	33.6	33.6	33.6	35.7	35.7
87.5°	21.0	21.0	21.0	21.0	21.0	21.0	18.9	18.9	18.9	18.9	16.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8
2.5°	1337.5	1339.6	1341.7	1341.7	1343.8	1345.9	1345.9	1354.3	1362.7	1366.9	1371.1
5°	1144.3	1142.2	1142.2	1140.1	1138.0	1144.3	1150.6	1163.2	1175.8	1177.9	1182.1
7.5°	896.6	898.7	900.8	900.8	902.9	896.6	888.2	890.3	892.4	902.9	911.3
10°	678.2	680.3	682.4	682.4	684.5	682.4	678.2	684.5	690.8	699.2	709.7
12.5°	527.0	533.3	539.6	543.8	550.1	554.3	556.4	564.8	571.1	581.6	592.1
15°	430.4	434.6	438.8	443.0	447.2	451.4	455.6	464.0	472.4	485.0	497.6
17.5°	363.2	363.2	365.3	365.3	365.3	369.5	373.7	377.9	380.0	392.6	405.2
20°	310.8	308.7	306.6	304.5	302.4	306.6	308.7	310.8	312.9	321.3	327.6
22.5°	266.7	266.7	268.8	268.8	268.8	266.7	262.5	264.6	264.6	268.8	275.1
25°	241.5	241.5	241.5	239.4	239.4	241.5	243.6	243.6	241.5	243.6	245.7
27.5°	218.4	220.5	220.5	222.6	222.6	224.7	224.7	224.7	224.7	226.8	228.9
30°	210.0	210.0	212.1	212.1	212.1	214.2	216.3	216.3	216.3	218.4	222.6
32.5°	201.6	203.7	205.8	207.9	210.0	212.1	212.1	214.2	214.2	216.3	218.4
35°	178.5	176.4	176.4	174.3	172.2	172.2	172.2	172.2	170.1	172.2	172.2
37.5°	159.6	159.6	159.6	157.5	157.5	159.6	159.6	159.6	159.6	161.7	161.7
40°	151.2	151.2	151.2	151.2	151.2	151.2	151.2	153.3	153.3	155.4	157.5
42.5°	144.9	144.9	144.9	144.9	144.9	147.0	147.0	147.0	147.0	149.1	149.1
45°	138.6	138.6	138.6	138.6	138.6	138.6	138.6	140.7	140.7	142.8	144.9
47.5°	132.3	132.3	132.3	132.3	132.3	134.4	136.5	136.5	136.5	138.6	138.6
50°	128.1	128.1	128.1	128.1	128.1	130.2	130.2	132.3	132.3	134.4	136.5
52.5°	123.9	123.9	123.9	123.9	123.9	126.0	126.0	128.1	128.1	130.2	132.3
55°	121.8	121.8	121.8	119.7	119.7	121.8	121.8	123.9	123.9	126.0	126.0
57.5°	115.5	115.5	115.5	115.5	115.5	115.5	115.5	117.6	117.6	119.7	121.8
60°	113.4	113.4	111.3	111.3	109.2	111.3	111.3	113.4	113.4	115.5	115.5
62.5°	107.1	107.1	107.1	105.0	105.0	107.1	107.1	107.1	107.1	109.2	111.3
65°	100.8	100.8	100.8	98.7	98.7	100.8	100.8	100.8	100.8	102.9	105.0
67.5°	94.5	94.5	94.5	92.4	92.4	92.4	92.4	94.5	94.5	96.6	98.7
70°	88.2	88.2	88.2	86.1	86.1	86.1	84.0	86.1	88.2	90.3	90.3
72.5°	81.9	81.9	81.9	79.8	79.8	79.8	77.7	79.8	79.8	81.9	81.9
75°	71.4	71.4	71.4	71.4	71.4	71.4	69.3	69.3	69.3	71.4	71.4
77.5°	65.1	65.1	65.1	63.0	63.0	63.0	60.9	60.9	60.9	63.0	63.0
80°	54.6	54.6	54.6	52.5	52.5	52.5	50.4	50.4	50.4	52.5	52.5
82.5°	44.1	44.1	44.1	42.0	42.0	42.0	39.9	39.9	39.9	42.0	42.0
85°	35.7	35.7	35.7	35.7	35.7	35.7	33.6	33.6	33.6	35.7	37.8
87.5°	16.8	16.8	18.9	18.9	18.9	18.9	16.8	16.8	14.7	14.7	16.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8
2.5°	1375.3	1379.5	1390.0	1398.4	1408.9	1417.3	1423.6	1432.0	1438.3	1444.6	1448.8
5°	1184.2	1186.3	1196.8	1207.3	1215.7	1226.2	1240.9	1255.6	1270.3	1285.0	1295.5
7.5°	921.8	930.2	942.8	957.5	970.1	982.7	997.4	1014.1	1028.8	1043.5	1058.2
10°	718.1	726.5	739.1	751.7	762.2	774.8	791.6	808.4	825.2	842.0	858.8
12.5°	602.6	613.1	627.8	642.5	655.1	669.8	690.8	709.7	730.7	749.6	770.6
15°	508.1	520.7	539.6	560.6	579.5	598.4	619.4	640.4	659.3	680.3	701.3
17.5°	417.8	430.4	447.2	466.1	482.9	499.7	524.9	548.0	573.2	596.3	619.4
20°	336.0	342.2	359.0	375.8	392.6	409.4	428.3	447.2	466.1	485.0	514.4
22.5°	279.3	283.5	291.9	298.2	306.6	312.9	331.8	350.6	367.4	386.3	413.6
25°	245.7	247.8	254.1	258.3	264.6	268.8	281.4	291.9	304.5	315.0	340.1
27.5°	228.9	231.0	233.1	235.2	237.3	239.4	247.8	256.2	262.5	270.9	294.0
30°	224.7	226.8	233.1	237.3	243.6	247.8	252.0	256.2	260.4	264.6	279.3
32.5°	220.5	222.6	222.6	220.5	220.5	218.4	222.6	224.7	228.9	231.0	243.6
35°	174.3	174.3	176.4	178.5	180.6	182.7	189.0	193.2	199.5	203.7	214.2
37.5°	163.8	163.8	165.9	170.1	172.2	174.3	178.5	182.7	186.9	191.1	201.6
40°	157.5	159.6	161.7	163.8	165.9	168.0	172.2	174.3	178.5	180.6	189.0
42.5°	151.2	151.2	153.3	157.5	159.6	161.7	165.9	168.0	172.2	174.3	182.7
45°	147.0	149.1	151.2	153.3	153.3	155.4	159.6	163.8	165.9	170.1	178.5
47.5°	140.7	140.7	144.9	147.0	151.2	153.3	157.5	159.6	163.8	165.9	174.3
50°	136.5	138.6	142.8	144.9	149.1	151.2	157.5	161.7	168.0	172.2	176.4
52.5°	132.3	134.4	138.6	140.7	144.9	147.0	155.4	163.8	170.1	178.5	178.5
55°	128.1	128.1	132.3	138.6	142.8	147.0	151.2	157.5	161.7	165.9	165.9
57.5°	121.8	123.9	128.1	134.4	138.6	142.8	147.0	151.2	153.3	157.5	155.4
60°	117.6	117.6	123.9	130.2	136.5	142.8	142.8	142.8	140.7	140.7	140.7
62.5°	111.3	113.4	121.8	132.3	140.7	149.1	142.8	136.5	130.2	123.9	126.0
65°	107.1	109.2	113.4	119.7	123.9	128.1	123.9	121.8	117.6	113.4	115.5
67.5°	98.7	100.8	102.9	102.9	105.0	105.0	105.0	105.0	105.0	105.0	107.1
70°	92.4	92.4	92.4	94.5	94.5	94.5	94.5	94.5	94.5	94.5	96.6
72.5°	84.0	84.0	84.0	84.0	84.0	84.0	84.0	84.0	84.0	84.0	86.1
75°	73.5	73.5	73.5	73.5	73.5	73.5	73.5	73.5	73.5	73.5	75.6
77.5°	65.1	65.1	65.1	65.1	65.1	65.1	65.1	65.1	63.0	63.0	65.1
80°	54.6	54.6	54.6	54.6	52.5	52.5	52.5	52.5	52.5	52.5	54.6
82.5°	44.1	44.1	44.1	44.1	42.0	42.0	42.0	42.0	39.9	39.9	42.0
85°	39.9	42.0	42.0	44.1	44.1	44.1	42.0	39.9	37.8	35.7	35.7
87.5°	16.8	16.8	16.8	16.8	14.7	14.7	14.7	14.7	14.7	14.7	14.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8
2.5°	1455.1	1459.3	1463.5	1469.8	1478.2	1484.5	1490.8	1503.4	1518.1	1530.7	1543.3
5°	1306.0	1316.5	1327.0	1339.6	1352.2	1362.7	1375.3	1400.5	1425.7	1448.8	1474.0
7.5°	1070.8	1085.5	1098.1	1119.1	1138.0	1159.0	1177.9	1209.4	1238.8	1270.3	1299.7
10°	875.6	892.4	909.2	936.5	965.9	993.2	1020.4	1045.6	1072.9	1098.1	1123.3
12.5°	791.6	810.5	831.5	848.3	867.2	884.0	900.8	930.2	959.6	989.0	1018.3
15°	722.3	743.3	764.3	785.3	804.2	825.2	844.1	869.3	896.6	921.8	947.0
17.5°	642.5	663.5	686.6	709.7	732.8	755.9	779.0	814.7	850.4	884.0	919.7
20°	541.7	571.1	598.4	629.9	661.4	692.9	724.4	762.2	800.0	835.7	873.5
22.5°	440.9	468.2	495.5	533.3	571.1	606.8	644.6	695.0	743.3	793.7	842.0
25°	367.4	392.6	417.8	459.8	499.7	541.7	581.6	642.5	701.3	762.2	821.0
27.5°	317.1	340.1	363.2	407.3	451.4	493.4	537.5	604.7	669.8	737.0	802.1
30°	294.0	308.7	323.4	365.3	407.3	447.2	489.2	554.3	619.4	684.5	749.6
32.5°	256.2	268.8	281.4	319.2	356.9	392.6	430.4	497.6	562.7	629.9	695.0
35°	226.8	237.3	247.8	283.5	317.1	352.7	386.3	453.5	520.7	587.9	655.1
37.5°	210.0	220.5	228.9	260.4	294.0	325.5	356.9	424.1	489.2	556.4	621.5
40°	197.4	203.7	212.1	243.6	273.0	304.5	333.9	394.7	457.7	518.6	579.5
42.5°	189.0	197.4	203.7	231.0	260.4	287.7	315.0	373.7	432.5	489.2	548.0
45°	186.9	195.3	203.7	226.8	249.9	270.9	294.0	350.6	407.3	464.0	520.7
47.5°	182.7	189.0	197.4	216.3	233.1	252.0	268.8	325.5	382.1	436.7	493.4
50°	180.6	182.7	186.9	203.7	220.5	237.3	254.1	310.8	367.4	424.1	480.8
52.5°	178.5	178.5	178.5	193.2	207.9	220.5	235.2	291.9	350.6	407.3	464.0
55°	165.9	163.8	163.8	178.5	191.1	205.8	218.4	275.1	331.8	386.3	443.0
57.5°	153.3	151.2	149.1	161.7	174.3	186.9	199.5	256.2	315.0	371.6	428.3
60°	140.7	138.6	138.6	151.2	161.7	174.3	184.8	243.6	300.3	359.0	415.7
62.5°	126.0	128.1	128.1	138.6	151.2	161.7	172.2	231.0	291.9	350.6	409.4
65°	115.5	117.6	117.6	130.2	142.8	155.4	168.0	224.7	283.5	340.1	396.8
67.5°	107.1	109.2	109.2	123.9	136.5	151.2	163.8	214.2	266.7	317.1	367.4
70°	98.7	98.7	100.8	115.5	130.2	144.9	159.6	203.7	247.8	289.8	333.9
72.5°	88.2	90.3	92.4	107.1	119.7	134.4	147.0	186.9	226.8	266.7	306.6
75°	77.7	79.8	81.9	94.5	107.1	119.7	132.3	170.1	205.8	243.6	279.3
77.5°	69.3	71.4	73.5	84.0	94.5	105.0	115.5	142.8	172.2	199.5	226.8
80°	56.7	56.7	58.8	67.2	75.6	81.9	90.3	109.2	128.1	144.9	163.8
82.5°	42.0	44.1	44.1	50.4	54.6	60.9	65.1	75.6	84.0	94.5	102.9
85°	35.7	33.6	33.6	37.8	39.9	44.1	46.2	52.5	56.7	63.0	67.2
87.5°	14.7	12.6	12.6	14.7	18.9	21.0	23.1	23.1	25.2	25.2	25.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8
2.5°	1549.6	1553.8	1560.1	1564.3	1574.8	1583.2	1593.7	1602.1	1608.4	1618.9	1614.7
5°	1492.9	1511.8	1530.7	1549.6	1564.3	1579.0	1591.6	1606.3	1623.1	1654.6	1663.0
7.5°	1324.9	1350.1	1373.2	1398.4	1427.8	1457.2	1486.6	1516.0	1543.3	1583.2	1608.4
10°	1159.0	1194.7	1228.3	1264.0	1291.3	1318.6	1343.8	1371.1	1408.9	1448.8	1495.0
12.5°	1054.0	1089.7	1125.4	1161.1	1201.0	1238.8	1278.7	1316.5	1352.2	1383.7	1436.2
15°	984.8	1024.6	1062.4	1100.2	1148.5	1194.7	1243.0	1289.2	1341.7	1383.7	1419.4
17.5°	968.0	1016.2	1062.4	1110.7	1161.1	1211.5	1261.9	1312.3	1364.8	1427.8	1474.0
20°	938.6	1003.7	1068.7	1133.8	1198.9	1261.9	1327.0	1390.0	1459.3	1534.9	1555.9
22.5°	921.8	999.5	1079.2	1156.9	1245.1	1335.4	1423.6	1511.8	1585.3	1642.0	1704.9
25°	919.7	1016.2	1114.9	1211.5	1322.8	1432.0	1543.3	1652.5	1746.9	1803.6	1854.0
27.5°	917.6	1035.1	1150.6	1266.1	1402.6	1537.0	1673.5	1807.8	1896.0	1977.9	2019.9
30°	892.4	1033.0	1175.8	1316.5	1469.8	1623.1	1776.3	1929.6	2019.9	2076.6	2097.6
32.5°	860.9	1026.7	1192.6	1358.5	1532.8	1707.0	1879.2	2053.5	2124.9	2173.2	2156.4
35°	835.7	1018.3	1198.9	1379.5	1564.3	1751.1	1935.9	2120.7	2223.6	2290.8	2263.5
37.5°	812.6	1003.7	1194.7	1385.8	1602.1	1818.3	2034.6	2250.9	2349.6	2420.9	2389.4
40°	785.3	989.0	1194.7	1398.4	1646.2	1891.8	2139.6	2385.2	2513.3	2574.2	2525.9
42.5°	762.2	974.3	1188.4	1400.5	1665.1	1929.6	2194.2	2458.7	2601.5	2687.6	2626.7
45°	732.8	944.9	1154.8	1366.9	1658.8	1950.6	2240.4	2532.2	2698.1	2765.3	2681.3
47.5°	701.3	911.3	1119.1	1327.0	1637.8	1948.5	2259.3	2570.0	2723.3	2803.1	2725.4
50°	690.8	900.8	1108.6	1318.6	1654.6	1992.6	2328.6	2664.5	2775.8	2840.9	2738.0
52.5°	688.7	911.3	1135.9	1358.5	1696.5	2032.5	2370.5	2706.5	2796.8	2866.1	2773.7
55°	682.4	923.9	1163.2	1402.6	1755.3	2110.2	2462.9	2815.7	2906.0	2956.4	2887.1
57.5°	688.7	949.1	1207.3	1467.7	1830.9	2194.2	2557.4	2920.7	3029.9	3065.5	3050.8
60°	692.9	970.1	1245.1	1522.3	1877.1	2232.0	2586.8	2941.7	3055.0	3143.2	3160.0
62.5°	682.4	955.4	1226.2	1499.2	1820.4	2141.7	2462.9	2784.2	2971.1	3101.2	3176.8
65°	650.9	902.9	1156.9	1408.9	1704.9	2003.1	2299.2	2595.2	2792.6	2985.8	3046.6
67.5°	581.6	795.8	1010.0	1224.1	1482.4	1740.6	1996.8	2255.1	2502.8	2689.7	2773.7
70°	503.9	671.9	842.0	1010.0	1245.1	1480.3	1715.4	1950.6	2169.0	2374.7	2454.5
72.5°	438.8	569.0	701.3	831.5	999.5	1165.3	1333.3	1499.2	1757.4	1963.2	2040.9
75°	373.7	468.2	560.6	655.1	770.6	886.1	999.5	1114.9	1297.6	1482.4	1560.1
77.5°	287.7	350.6	411.5	472.4	552.2	629.9	709.7	787.4	915.5	1054.0	1093.9
80°	199.5	235.2	268.8	304.5	367.4	430.4	493.4	556.4	640.4	718.1	779.0
82.5°	123.9	147.0	168.0	189.0	239.4	289.8	338.0	388.4	422.0	426.2	487.1
85°	79.8	94.5	107.1	119.7	149.1	180.6	210.0	239.4	214.2	199.5	237.3
87.5°	31.5	39.9	46.2	52.5	50.4	48.3	46.2	44.1	37.8	33.6	42.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8
2.5°	1618.9	1625.2	1631.5	1635.7	1642.0	1644.1	1646.2	1646.2	1648.3	1650.4	1654.6
5°	1696.5	1709.1	1721.7	1732.2	1744.8	1755.3	1763.7	1774.2	1782.6	1782.6	1780.5
7.5°	1631.5	1663.0	1694.4	1725.9	1757.4	1780.5	1801.5	1824.6	1845.6	1849.8	1854.0
10°	1545.4	1579.0	1610.5	1644.1	1675.6	1711.2	1744.8	1778.4	1814.1	1820.4	1828.8
12.5°	1465.6	1505.5	1545.4	1583.2	1623.1	1648.3	1673.5	1696.5	1721.7	1738.5	1755.3
15°	1463.5	1497.1	1530.7	1562.2	1595.8	1610.5	1625.2	1637.8	1652.5	1652.5	1654.6
17.5°	1511.8	1532.8	1553.8	1572.7	1593.7	1595.8	1600.0	1602.1	1604.2	1597.9	1591.6
20°	1606.3	1614.7	1623.1	1631.5	1639.9	1625.2	1612.6	1597.9	1583.2	1566.4	1551.7
22.5°	1744.8	1725.9	1707.0	1688.2	1669.3	1644.1	1616.8	1591.6	1564.3	1543.3	1522.3
25°	1875.0	1851.9	1828.8	1805.7	1782.6	1728.0	1673.5	1616.8	1562.2	1539.1	1516.0
27.5°	2049.3	2013.6	1977.9	1942.2	1906.5	1833.0	1759.5	1686.1	1612.6	1572.7	1534.9
30°	2091.3	2051.4	2011.5	1969.5	1929.6	1858.2	1788.9	1717.5	1646.2	1600.0	1555.9
32.5°	2152.2	2106.0	2059.8	2013.6	1967.4	1898.1	1828.8	1757.4	1688.2	1646.2	1602.1
35°	2253.0	2200.5	2148.0	2093.4	2040.9	1969.5	1900.2	1828.8	1757.4	1709.1	1663.0
37.5°	2339.1	2278.2	2217.3	2156.4	2095.5	2032.5	1967.4	1904.4	1839.3	1791.0	1744.8
40°	2435.6	2368.4	2301.3	2236.2	2169.0	2110.2	2051.4	1990.5	1931.7	1893.9	1856.1
42.5°	2519.6	2437.7	2358.0	2278.2	2196.3	2156.4	2118.6	2078.7	2038.8	2019.9	1998.9
45°	2578.4	2502.8	2425.1	2349.6	2274.0	2244.6	2215.2	2185.8	2156.4	2175.3	2194.2
47.5°	2603.6	2542.7	2483.9	2425.1	2364.3	2374.7	2385.2	2393.6	2404.1	2429.3	2456.6
50°	2626.7	2593.1	2557.4	2523.8	2488.1	2528.0	2565.8	2605.7	2645.6	2698.1	2750.6
52.5°	2672.9	2654.0	2637.2	2618.3	2599.4	2668.7	2738.0	2807.3	2876.6	2935.4	2994.2
55°	2811.5	2796.8	2782.1	2765.3	2750.6	2849.3	2945.9	3044.5	3143.2	3204.1	3265.0
57.5°	3002.6	2994.2	2983.7	2975.3	2964.8	3061.3	3155.8	3250.3	3346.9	3405.7	3466.6
60°	3147.4	3149.5	3149.5	3151.6	3151.6	3225.1	3298.6	3374.2	3447.7	3498.1	3550.6
62.5°	3225.1	3220.9	3216.7	3212.5	3208.3	3269.2	3330.1	3391.0	3451.9	3489.7	3527.5
65°	3141.1	3164.2	3187.3	3210.4	3233.5	3241.9	3248.2	3256.6	3262.9	3286.0	3309.1
67.5°	2859.8	2906.0	2950.1	2996.3	3040.4	3008.9	2979.5	2948.0	2916.5	2922.8	2927.0
70°	2546.9	2599.4	2654.0	2706.5	2759.0	2685.5	2612.0	2536.4	2462.9	2437.7	2412.5
72.5°	2148.0	2194.2	2242.5	2288.7	2334.9	2244.6	2156.4	2066.1	1975.8	1931.7	1887.6
75°	1642.0	1696.5	1753.2	1807.8	1862.4	1761.6	1658.8	1558.0	1455.1	1425.7	1398.4
77.5°	1196.8	1261.9	1327.0	1392.1	1457.2	1366.9	1276.6	1184.2	1093.9	1077.1	1060.3
80°	871.4	921.8	970.1	1020.4	1068.7	1016.2	963.8	911.3	858.8	856.7	854.6
82.5°	587.9	632.0	674.0	718.1	760.1	739.1	720.2	699.2	678.2	699.2	722.3
85°	302.4	363.2	426.2	487.1	548.0	541.7	537.5	531.2	524.9	552.2	577.4
87.5°	60.9	113.4	165.9	216.3	268.8	256.2	243.6	228.9	216.3	224.7	231.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8
2.5°	1656.7	1658.8	1658.8	1658.8	1658.8	1658.8	1654.6	1652.5	1648.3	1644.1	1637.8
5°	1780.5	1778.4	1770.0	1761.6	1751.1	1742.7	1736.4	1728.0	1721.7	1713.3	1700.7
7.5°	1858.2	1862.4	1847.7	1835.1	1820.4	1805.7	1791.0	1776.3	1761.6	1746.9	1717.5
10°	1835.1	1841.4	1833.0	1824.6	1814.1	1805.7	1788.9	1770.0	1753.2	1734.3	1698.6
12.5°	1770.0	1786.8	1782.6	1778.4	1774.2	1770.0	1759.5	1746.9	1736.4	1723.8	1684.0
15°	1654.6	1654.6	1656.7	1658.8	1658.8	1660.9	1663.0	1665.1	1667.2	1669.3	1646.2
17.5°	1585.3	1579.0	1579.0	1579.0	1579.0	1579.0	1587.4	1597.9	1606.3	1614.7	1608.4
20°	1534.9	1520.2	1518.1	1518.1	1516.0	1513.9	1528.6	1545.4	1560.1	1574.8	1583.2
22.5°	1501.3	1480.3	1478.2	1476.1	1474.0	1471.9	1490.8	1509.7	1528.6	1547.5	1576.9
25°	1492.9	1469.8	1471.9	1474.0	1474.0	1476.1	1490.8	1505.5	1520.2	1534.9	1585.3
27.5°	1495.0	1457.2	1459.3	1461.4	1461.4	1463.5	1486.6	1507.6	1530.7	1551.7	1614.7
30°	1509.7	1465.6	1461.4	1457.2	1453.0	1448.8	1480.3	1511.8	1543.3	1574.8	1623.1
32.5°	1560.1	1518.1	1507.6	1497.1	1486.6	1476.1	1513.9	1549.6	1587.4	1623.1	1663.0
35°	1614.7	1568.5	1564.3	1560.1	1553.8	1549.6	1583.2	1618.9	1652.5	1686.1	1721.7
37.5°	1696.5	1650.4	1646.2	1639.9	1635.7	1629.4	1667.2	1702.8	1740.6	1776.3	1807.8
40°	1818.3	1780.5	1778.4	1778.4	1776.3	1774.2	1803.6	1835.1	1864.5	1893.9	1914.9
42.5°	1980.0	1961.1	1967.4	1975.8	1982.1	1988.4	2011.5	2036.7	2059.8	2082.9	2076.6
45°	2213.1	2232.0	2234.1	2236.2	2238.3	2240.4	2246.7	2255.1	2261.4	2267.7	2242.5
47.5°	2481.8	2507.0	2519.6	2532.2	2542.7	2555.3	2546.9	2536.4	2528.0	2517.5	2454.5
50°	2801.0	2853.5	2851.4	2849.3	2845.1	2843.0	2826.2	2809.4	2790.5	2773.7	2681.3
52.5°	3052.9	3111.7	3122.2	3132.7	3143.2	3153.7	3122.2	3090.7	3057.1	3025.7	2910.2
55°	3323.8	3384.7	3386.8	3388.9	3388.9	3391.0	3346.9	3302.8	3256.6	3212.5	3092.8
57.5°	3525.4	3584.2	3577.9	3573.7	3567.4	3561.1	3508.6	3456.1	3403.6	3351.1	3231.4
60°	3601.0	3651.4	3638.8	3626.2	3611.5	3598.9	3559.0	3519.1	3477.1	3437.2	3321.7
62.5°	3565.3	3603.1	3584.2	3567.4	3548.5	3529.6	3479.2	3426.7	3376.3	3323.8	3239.8
65°	3330.1	3353.2	3328.0	3304.9	3281.8	3256.6	3214.6	3172.6	3128.5	3086.5	3029.9
67.5°	2933.3	2937.5	2935.4	2933.3	2931.2	2929.1	2868.2	2807.3	2744.3	2683.4	2679.2
70°	2389.4	2364.3	2368.4	2374.7	2378.9	2383.1	2337.0	2292.9	2246.7	2200.5	2221.5
72.5°	1843.5	1799.4	1809.9	1822.5	1833.0	1843.5	1805.7	1770.0	1732.2	1694.4	1723.8
75°	1369.0	1341.7	1352.2	1364.8	1375.3	1385.8	1371.1	1356.4	1339.6	1324.9	1352.2
77.5°	1043.5	1026.7	1028.8	1028.8	1030.9	1030.9	1033.0	1037.2	1039.3	1041.4	1070.8
80°	850.4	848.3	846.2	844.1	839.9	837.8	858.8	879.8	900.8	921.8	936.5
82.5°	743.3	764.3	751.7	741.2	728.6	716.0	734.9	753.8	772.7	791.6	785.3
85°	604.7	629.9	606.8	583.7	558.5	535.4	552.2	566.9	583.7	598.4	590.0
87.5°	239.4	245.7	207.9	172.2	134.4	96.6	153.3	207.9	264.6	319.2	327.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8	1511.8
2.5°	1631.5	1623.1	1616.8	1614.7	1610.5	1608.4	1604.2	1600.0	1593.7	1589.5	1583.2
5°	1686.1	1673.5	1658.8	1637.8	1618.9	1597.9	1576.9	1558.0	1539.1	1518.1	1499.2
7.5°	1688.2	1658.8	1629.4	1602.1	1572.7	1545.4	1516.0	1490.8	1463.5	1436.2	1411.0
10°	1665.1	1629.4	1593.7	1558.0	1524.4	1488.7	1453.0	1423.6	1392.1	1360.6	1331.2
12.5°	1646.2	1606.3	1566.4	1524.4	1484.5	1442.5	1400.5	1371.1	1341.7	1312.3	1282.9
15°	1623.1	1597.9	1574.8	1537.0	1499.2	1461.4	1423.6	1383.7	1345.9	1306.0	1266.1
17.5°	1604.2	1597.9	1591.6	1566.4	1541.2	1513.9	1488.7	1448.8	1408.9	1366.9	1327.0
20°	1593.7	1602.1	1610.5	1597.9	1585.3	1570.6	1558.0	1528.6	1499.2	1467.7	1438.3
22.5°	1606.3	1637.8	1667.2	1669.3	1673.5	1675.6	1677.7	1650.4	1623.1	1593.7	1566.4
25°	1635.7	1686.1	1736.4	1763.7	1791.0	1820.4	1847.7	1830.9	1814.1	1797.3	1780.5
27.5°	1675.6	1738.5	1801.5	1841.4	1879.2	1919.1	1959.0	1956.9	1954.8	1950.6	1948.5
30°	1669.3	1717.5	1765.8	1814.1	1862.4	1910.7	1959.0	1984.2	2007.3	2032.5	2057.7
32.5°	1704.9	1744.8	1786.8	1837.2	1887.6	1940.1	1990.5	2043.0	2093.4	2145.9	2198.4
35°	1759.5	1795.2	1833.0	1887.6	1944.3	1998.9	2055.6	2118.6	2183.7	2248.8	2311.8
37.5°	1841.4	1872.9	1906.5	1952.7	2001.0	2047.2	2095.5	2187.9	2280.3	2374.7	2467.1
40°	1935.9	1956.9	1977.9	2022.0	2066.1	2110.2	2154.3	2269.8	2385.2	2500.7	2616.2
42.5°	2072.4	2066.1	2059.8	2095.5	2133.3	2169.0	2206.8	2311.8	2416.7	2521.7	2626.7
45°	2217.3	2192.1	2166.9	2183.7	2202.6	2219.4	2238.3	2345.4	2452.4	2561.6	2668.7
47.5°	2391.5	2328.6	2265.6	2250.9	2236.2	2219.4	2204.7	2320.2	2435.6	2553.2	2668.7
50°	2588.9	2494.4	2402.0	2364.3	2324.4	2286.6	2246.7	2341.2	2437.7	2534.3	2628.8
52.5°	2794.7	2677.1	2561.6	2502.8	2444.0	2383.1	2324.4	2404.1	2486.0	2567.9	2647.7
55°	2971.1	2851.4	2729.6	2660.3	2591.0	2521.7	2452.4	2532.2	2612.0	2691.8	2771.6
57.5°	3111.7	2992.1	2872.4	2807.3	2740.1	2675.0	2607.8	2683.4	2761.1	2838.8	2914.4
60°	3208.3	3092.8	2977.4	2914.4	2851.4	2788.4	2725.4	2815.7	2906.0	2998.4	3088.6
62.5°	3157.9	3073.9	2990.0	2962.7	2935.4	2906.0	2878.7	2964.8	3048.7	3134.8	3220.9
65°	2973.2	2916.5	2859.8	2887.1	2916.5	2943.8	2973.2	3029.9	3086.5	3145.3	3202.0
67.5°	2672.9	2668.7	2662.4	2723.3	2784.2	2847.2	2908.1	2945.9	2981.6	3019.4	3057.1
70°	2242.5	2265.6	2286.6	2391.5	2496.5	2601.5	2706.5	2721.2	2735.9	2750.6	2765.3
72.5°	1755.3	1784.7	1816.2	1954.8	2091.3	2229.9	2368.4	2360.1	2351.7	2341.2	2332.8
75°	1381.6	1408.9	1438.3	1566.4	1694.4	1822.5	1950.6	1914.9	1881.3	1845.6	1809.9
77.5°	1102.3	1131.7	1163.2	1282.9	1402.6	1524.4	1644.1	1558.0	1471.9	1385.8	1299.7
80°	949.1	963.8	976.4	1058.2	1138.0	1219.9	1301.8	1213.6	1123.3	1033.0	944.9
82.5°	779.0	770.6	764.3	812.6	860.9	909.2	957.5	873.5	789.5	703.4	619.4
85°	581.6	573.2	564.8	590.0	615.2	642.5	667.7	571.1	474.5	375.8	279.3
87.5°	338.0	346.4	354.8	382.1	409.4	438.8	466.1	367.4	268.8	168.0	69.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836

CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671836
 CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1511.8	1511.8
2.5°	1570.6	1560.1
5°	1484.5	1469.8
7.5°	1390.0	1371.1
10°	1303.9	1278.7
12.5°	1249.3	1217.8
15°	1228.3	1190.5
17.5°	1291.3	1255.6
20°	1387.9	1339.6
22.5°	1505.5	1446.7
25°	1709.1	1637.8
27.5°	1875.0	1801.5
30°	1977.9	1898.1
32.5°	2091.3	1986.3
35°	2208.9	2108.1
37.5°	2351.7	2238.3
40°	2498.6	2381.0
42.5°	2549.0	2473.4
45°	2597.3	2525.9
47.5°	2607.8	2549.0
50°	2618.3	2609.9
52.5°	2647.7	2645.6
55°	2773.7	2775.8
57.5°	2929.1	2941.7
60°	3071.8	3057.1
62.5°	3145.3	3069.7
65°	3094.9	2990.0
67.5°	2943.8	2830.4
70°	2612.0	2458.7
72.5°	2198.4	2064.0
75°	1694.4	1581.1
77.5°	1205.2	1110.7
80°	848.3	753.8
82.5°	543.8	468.2
85°	245.7	214.2
87.5°	69.3	67.2
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671836
CATALOG NUMBER: CCP-SA-1D-750-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)