

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671849

Luminaire Tested: **CCP-SA-1F-760-U-SLR**

Issue Date: 04/16/2023



Test Information

Test Method: LM-79-08
Report Number: P671849
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1F-760-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @1200mA w/ SLR
distribution lens
Light Source: (16) 5700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6364.6 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 67
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 9 fc

Type IV - Short - N/A

REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1309.6	0.0	1309.6
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	5055.0	0.0	5055.0
	% Fixture	79.4	0.0	79.4
Total	Lumens	6364.6	0.0	6364.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.9	2.5
10°-20°	333.4	5.2
20°-30°	487.8	7.7
30°-40°	687.3	10.8
40°-50°	944.4	14.8
50°-60°	1287.3	20.2
60°-70°	1408.9	22.1
70°-80°	813.6	12.8
80°-90°	243.9	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6364.6	100.0
0°-180°	6364.6	100.0

Coefficient of Utilization



REPORT NUMBER: P671849


CATALOG NUMBER: CCP-SA-1F-760-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	653.7	10.3			
FM	(30°-60°)	2322.6	36.5			
FH	(60°-80°)	1871.6	29.4			G2/5000
FVH	(80°-90°)	207.2	3.3			G2/225
BL	(0°-30°)	325.6	5.1	B1/500		
BM	(30°-60°)	596.3	9.4	B1/1000		
BH	(60°-80°)	351.0	5.5	B1/500		G1/500
BVH	(80°-90°)	36.7	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5
2.5°	2097.4	2086.1	2077.6	2069.2	2057.9	2049.4	2038.1	2026.8	2012.7	2001.4	1987.3
5°	1976.0	1942.1	1908.3	1888.5	1865.9	1846.2	1823.6	1798.2	1772.8	1744.5	1719.1
7.5°	1843.3	1801.0	1758.6	1724.8	1688.1	1654.2	1617.5	1586.4	1555.4	1524.3	1493.3
10°	1719.1	1679.6	1640.1	1597.7	1552.6	1510.2	1465.1	1422.7	1380.4	1338.0	1295.7
12.5°	1637.3	1589.3	1544.1	1496.1	1451.0	1403.0	1355.0	1315.5	1275.9	1233.6	1194.1
15°	1600.6	1555.4	1513.1	1465.1	1417.1	1369.1	1321.1	1275.9	1233.6	1188.4	1143.3
17.5°	1688.1	1623.1	1558.2	1496.1	1434.0	1371.9	1309.8	1253.4	1196.9	1140.4	1084.0
20°	1801.0	1719.1	1640.1	1563.9	1484.8	1408.6	1329.6	1250.5	1171.5	1092.4	1013.4
22.5°	1945.0	1851.8	1761.5	1662.7	1561.0	1462.2	1360.6	1261.8	1163.0	1061.4	962.6
25°	2201.8	2091.7	1981.6	1840.5	1696.5	1555.4	1411.4	1281.6	1154.6	1024.7	894.8
27.5°	2422.0	2272.4	2125.6	1956.2	1786.9	1617.5	1448.1	1298.5	1151.7	1002.1	852.5
30°	2551.9	2405.1	2258.3	2052.2	1849.0	1642.9	1436.8	1270.3	1106.6	940.0	773.5
32.5°	2670.4	2506.7	2343.0	2117.1	1888.5	1662.7	1434.0	1250.5	1069.9	886.4	702.9
35°	2834.2	2653.5	2475.6	2213.1	1950.6	1688.1	1425.5	1236.4	1044.5	855.3	663.4
37.5°	3009.2	2786.2	2566.0	2275.2	1984.5	1693.7	1403.0	1216.7	1030.3	844.0	657.7
40°	3201.1	2930.1	2662.0	2340.2	2021.2	1699.4	1377.6	1191.2	1004.9	815.8	629.5
42.5°	3325.3	3031.8	2738.2	2391.0	2046.6	1699.4	1352.2	1168.7	985.2	798.9	615.4
45°	3395.9	3110.8	2828.5	2453.1	2077.6	1702.2	1326.7	1146.1	965.4	781.9	601.3
47.5°	3427.0	3161.6	2896.3	2501.1	2108.7	1713.5	1318.3	1134.8	948.5	765.0	578.7
50°	3508.8	3274.5	3040.2	2616.8	2196.2	1772.8	1349.3	1151.7	956.9	759.3	561.7
52.5°	3556.8	3356.4	3156.0	2721.2	2286.5	1851.8	1417.1	1196.9	976.7	756.5	536.3
55°	3731.8	3539.9	3347.9	2885.0	2419.2	1956.2	1490.5	1247.7	1004.9	759.3	516.6
57.5°	3954.8	3751.6	3551.2	3051.5	2551.9	2052.2	1552.6	1292.9	1030.3	770.6	508.1
60°	4110.1	3912.5	3717.7	3187.0	2653.5	2122.8	1589.3	1318.3	1047.3	773.5	502.5
62.5°	4127.0	3873.0	3621.7	3105.1	2588.6	2069.2	1552.6	1290.0	1027.5	762.2	499.6
65°	4019.8	3723.4	3427.0	2933.0	2439.0	1945.0	1451.0	1211.0	971.1	728.3	488.4
67.5°	3805.2	3458.0	3110.8	2659.1	2207.5	1755.8	1304.2	1098.1	894.8	688.8	482.7
70°	3305.6	3000.7	2698.7	2306.3	1916.7	1524.3	1132.0	962.6	796.0	626.7	457.3
72.5°	2774.9	2489.8	2207.5	1888.5	1572.3	1253.4	934.4	807.3	680.3	550.5	423.4
75°	2125.6	1911.1	1699.4	1462.2	1225.1	985.2	748.1	654.9	561.7	468.6	375.4
77.5°	1493.3	1377.6	1264.6	1086.8	909.0	731.1	553.3	491.2	429.1	367.0	304.9
80°	1013.4	948.5	886.4	759.3	632.3	502.5	375.4	335.9	293.6	254.1	211.7
82.5°	629.5	626.7	621.0	533.5	446.0	358.5	271.0	237.1	206.1	172.2	138.3
85°	287.9	335.9	381.1	333.1	285.1	237.1	189.1	166.5	144.0	118.6	96.0
87.5°	90.3	110.1	127.0	121.4	112.9	107.3	98.8	84.7	70.6	56.5	42.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5
2.5°	1976.0	1967.5	1956.2	1945.0	1930.8	1919.5	1905.4	1891.3	1888.5	1882.8	1880.0
5°	1702.2	1685.2	1665.5	1648.6	1631.6	1611.9	1594.9	1575.2	1561.0	1544.1	1530.0
7.5°	1462.2	1434.0	1403.0	1371.9	1343.7	1315.5	1284.4	1256.2	1242.1	1227.9	1213.8
10°	1270.3	1242.1	1216.7	1188.4	1168.7	1151.7	1132.0	1112.2	1095.3	1078.3	1061.4
12.5°	1174.3	1154.6	1134.8	1115.0	1092.4	1072.7	1050.1	1027.5	1007.8	990.8	971.1
15°	1115.0	1086.8	1055.8	1027.5	996.5	968.2	937.2	906.1	883.6	863.8	841.2
17.5°	1044.5	1002.1	962.6	920.3	886.4	852.5	815.8	781.9	756.5	728.3	702.9
20°	965.4	917.4	866.6	818.6	779.1	742.4	702.9	663.4	635.1	604.1	575.9
22.5°	897.7	835.6	770.6	705.7	663.4	621.0	575.9	533.5	508.1	479.9	454.5
25°	824.3	756.5	686.0	615.4	573.0	527.9	485.5	440.4	420.6	403.7	383.9
27.5°	784.8	717.0	646.4	578.7	539.2	496.8	457.3	415.0	400.8	383.9	369.8
30°	705.7	640.8	573.0	505.3	477.1	451.7	423.4	395.2	389.6	386.7	381.1
32.5°	635.1	567.4	499.6	431.9	406.5	381.1	355.7	330.3	327.5	321.8	319.0
35°	598.4	533.5	465.8	400.8	378.3	352.9	330.3	304.9	299.2	290.8	285.1
37.5°	590.0	522.2	451.7	383.9	361.3	338.7	313.3	290.8	285.1	279.5	273.8
40°	567.4	502.5	440.4	375.4	352.9	330.3	304.9	282.3	276.6	271.0	265.3
42.5°	550.5	488.4	423.4	358.5	338.7	319.0	296.4	276.6	271.0	265.3	256.9
45°	536.3	471.4	403.7	338.7	324.6	310.5	293.6	279.5	273.8	265.3	259.7
47.5°	513.8	451.7	386.7	321.8	307.7	296.4	282.3	268.2	262.5	256.9	251.2
50°	496.8	431.9	367.0	302.0	290.8	279.5	268.2	256.9	256.9	259.7	259.7
52.5°	474.2	412.1	350.0	287.9	276.6	265.3	254.1	242.8	245.6	248.4	251.2
55°	454.5	395.2	333.1	271.0	259.7	248.4	234.3	223.0	225.8	228.7	231.5
57.5°	446.0	383.9	321.8	259.7	248.4	234.3	223.0	208.9	208.9	208.9	208.9
60°	440.4	375.4	313.3	248.4	234.3	223.0	208.9	194.8	192.0	192.0	189.1
62.5°	437.5	372.6	310.5	245.6	228.7	214.5	197.6	180.7	177.8	175.0	172.2
65°	426.3	367.0	304.9	242.8	223.0	206.1	186.3	166.5	163.7	163.7	160.9
67.5°	423.4	361.3	302.0	239.9	220.2	197.6	177.8	155.3	152.4	149.6	146.8
70°	400.8	347.2	290.8	234.3	211.7	192.0	169.4	146.8	144.0	138.3	135.5
72.5°	372.6	324.6	273.8	223.0	200.4	177.8	155.3	132.7	129.9	127.0	121.4
75°	330.3	285.1	239.9	194.8	175.0	158.1	138.3	118.6	115.7	112.9	107.3
77.5°	271.0	234.3	200.4	163.7	149.6	135.5	121.4	107.3	104.4	101.6	96.0
80°	192.0	169.4	149.6	127.0	118.6	107.3	98.8	87.5	87.5	84.7	84.7
82.5°	127.0	115.7	104.4	93.2	87.5	81.9	76.2	70.6	70.6	67.7	67.7
85°	90.3	84.7	76.2	70.6	67.7	62.1	59.3	53.6	53.6	53.6	53.6
87.5°	42.3	42.3	39.5	39.5	36.7	36.7	33.9	31.1	31.1	31.1	31.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5
2.5°	1874.4	1865.9	1857.4	1846.2	1837.7	1826.4	1812.3	1801.0	1786.9	1786.9	1784.0
5°	1513.1	1504.6	1496.1	1484.8	1476.4	1465.1	1456.6	1445.3	1434.0	1434.0	1431.2
7.5°	1199.7	1182.8	1165.8	1146.1	1129.1	1117.9	1106.6	1092.4	1081.2	1072.7	1064.2
10°	1044.5	1027.5	1007.8	990.8	971.1	956.9	942.8	925.9	911.8	900.5	889.2
12.5°	951.3	931.5	911.8	892.0	872.3	852.5	835.6	815.8	796.0	781.9	767.8
15°	818.6	798.9	779.1	759.3	739.6	717.0	694.4	669.0	646.4	635.1	626.7
17.5°	674.7	654.9	632.3	612.6	590.0	573.0	556.1	539.2	522.2	510.9	502.5
20°	544.8	522.2	499.6	477.1	454.5	443.2	431.9	420.6	409.3	400.8	395.2
22.5°	426.3	412.1	400.8	386.7	372.6	364.1	358.5	350.0	341.6	341.6	341.6
25°	364.1	355.7	350.0	341.6	333.1	330.3	327.5	321.8	319.0	316.2	316.2
27.5°	352.9	344.4	335.9	327.5	319.0	316.2	313.3	307.7	304.9	304.9	304.9
30°	375.4	372.6	369.8	367.0	364.1	358.5	350.0	344.4	335.9	330.3	324.6
32.5°	313.3	310.5	310.5	307.7	304.9	310.5	313.3	319.0	321.8	324.6	327.5
35°	276.6	271.0	265.3	259.7	254.1	251.2	248.4	245.6	242.8	242.8	239.9
37.5°	268.2	262.5	256.9	251.2	245.6	242.8	239.9	237.1	234.3	234.3	231.5
40°	259.7	254.1	251.2	245.6	239.9	237.1	234.3	228.7	225.8	223.0	223.0
42.5°	251.2	248.4	242.8	239.9	234.3	231.5	228.7	223.0	220.2	217.4	214.5
45°	251.2	245.6	239.9	234.3	228.7	225.8	220.2	217.4	211.7	211.7	208.9
47.5°	245.6	239.9	234.3	228.7	223.0	220.2	214.5	211.7	206.1	203.2	200.4
50°	259.7	251.2	239.9	231.5	220.2	217.4	211.7	208.9	203.2	200.4	197.6
52.5°	254.1	245.6	234.3	225.8	214.5	208.9	206.1	200.4	194.8	192.0	189.1
55°	234.3	225.8	220.2	211.7	203.2	197.6	192.0	186.3	180.7	177.8	177.8
57.5°	208.9	206.1	203.2	200.4	197.6	192.0	186.3	177.8	172.2	169.4	166.5
60°	186.3	189.1	192.0	194.8	197.6	189.1	180.7	172.2	163.7	160.9	158.1
62.5°	169.4	175.0	180.7	183.5	189.1	180.7	172.2	163.7	155.3	152.4	149.6
65°	158.1	160.9	160.9	163.7	163.7	158.1	155.3	149.6	144.0	141.1	141.1
67.5°	144.0	144.0	144.0	141.1	141.1	138.3	138.3	135.5	132.7	129.9	129.9
70°	129.9	129.9	129.9	127.0	127.0	124.2	124.2	121.4	118.6	118.6	115.7
72.5°	118.6	118.6	115.7	115.7	112.9	112.9	112.9	110.1	110.1	107.3	107.3
75°	104.4	104.4	101.6	101.6	98.8	98.8	98.8	96.0	96.0	96.0	93.2
77.5°	93.2	93.2	90.3	90.3	87.5	87.5	87.5	84.7	84.7	81.9	81.9
80°	81.9	81.9	79.0	79.0	76.2	76.2	73.4	73.4	70.6	70.6	67.7
82.5°	64.9	64.9	64.9	64.9	64.9	62.1	62.1	59.3	56.5	56.5	53.6
85°	53.6	53.6	53.6	50.8	50.8	50.8	48.0	48.0	45.2	42.3	42.3
87.5°	31.1	31.1	31.1	28.2	28.2	28.2	28.2	28.2	28.2	28.2	25.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5
2.5°	1784.0	1781.2	1769.9	1758.6	1769.9	1781.2	1781.2	1781.2	1778.4	1778.4	1778.4
5°	1431.2	1428.4	1422.7	1417.1	1417.1	1414.3	1419.9	1425.5	1431.2	1436.8	1442.5
7.5°	1052.9	1044.5	1036.0	1027.5	1033.2	1036.0	1044.5	1050.1	1058.6	1064.2	1078.3
10°	877.9	866.6	858.1	849.7	844.0	838.4	832.7	829.9	824.3	818.6	824.3
12.5°	750.9	736.8	722.7	705.7	702.9	700.1	694.4	688.8	683.1	677.5	674.7
15°	615.4	604.1	598.4	590.0	578.7	567.4	561.7	558.9	553.3	547.6	544.8
17.5°	491.2	479.9	471.4	462.9	460.1	454.5	454.5	454.5	454.5	454.5	454.5
20°	386.7	378.3	378.3	375.4	375.4	372.6	375.4	378.3	378.3	381.1	383.9
22.5°	338.7	338.7	335.9	333.1	335.9	335.9	338.7	341.6	344.4	347.2	350.0
25°	313.3	310.5	313.3	316.2	316.2	316.2	319.0	319.0	321.8	321.8	321.8
27.5°	302.0	302.0	304.9	304.9	307.7	307.7	307.7	304.9	304.9	302.0	302.0
30°	319.0	313.3	313.3	313.3	310.5	307.7	304.9	304.9	302.0	299.2	296.4
32.5°	330.3	333.1	330.3	324.6	321.8	316.2	313.3	307.7	304.9	299.2	293.6
35°	239.9	237.1	242.8	245.6	248.4	251.2	254.1	256.9	256.9	259.7	259.7
37.5°	231.5	228.7	228.7	225.8	225.8	225.8	225.8	225.8	223.0	223.0	225.8
40°	220.2	217.4	217.4	214.5	214.5	211.7	211.7	211.7	211.7	211.7	211.7
42.5°	211.7	208.9	208.9	208.9	208.9	206.1	206.1	203.2	203.2	200.4	200.4
45°	208.9	206.1	203.2	200.4	200.4	197.6	197.6	197.6	194.8	194.8	194.8
47.5°	197.6	194.8	194.8	192.0	192.0	189.1	189.1	189.1	186.3	186.3	186.3
50°	192.0	189.1	189.1	186.3	186.3	183.5	183.5	183.5	180.7	180.7	180.7
52.5°	183.5	180.7	180.7	180.7	177.8	175.0	175.0	175.0	172.2	172.2	172.2
55°	175.0	172.2	172.2	172.2	169.4	166.5	166.5	166.5	163.7	163.7	163.7
57.5°	163.7	160.9	160.9	158.1	158.1	158.1	158.1	158.1	155.3	155.3	155.3
60°	155.3	152.4	152.4	149.6	149.6	146.8	146.8	146.8	146.8	146.8	146.8
62.5°	146.8	144.0	141.1	138.3	141.1	141.1	141.1	141.1	138.3	138.3	138.3
65°	138.3	135.5	132.7	129.9	129.9	129.9	129.9	129.9	129.9	129.9	129.9
67.5°	127.0	124.2	121.4	118.6	121.4	121.4	121.4	121.4	121.4	121.4	121.4
70°	115.7	112.9	112.9	110.1	110.1	107.3	107.3	110.1	110.1	110.1	110.1
72.5°	104.4	101.6	101.6	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8
75°	93.2	90.3	90.3	87.5	87.5	87.5	87.5	87.5	87.5	87.5	87.5
77.5°	79.0	76.2	76.2	76.2	76.2	76.2	76.2	79.0	79.0	79.0	79.0
80°	67.7	64.9	64.9	64.9	64.9	64.9	64.9	64.9	64.9	64.9	64.9
82.5°	53.6	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8
85°	39.5	36.7	36.7	36.7	39.5	39.5	39.5	39.5	39.5	39.5	39.5
87.5°	25.4	22.6	22.6	22.6	25.4	25.4	25.4	25.4	22.6	22.6	22.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5
2.5°	1778.4	1778.4	1778.4	1775.6	1772.8	1769.9	1767.1	1775.6	1781.2	1789.7	1795.3
5°	1445.3	1451.0	1453.8	1462.2	1470.7	1479.2	1487.6	1493.3	1498.9	1501.8	1507.4
7.5°	1089.6	1103.7	1115.0	1126.3	1137.6	1146.1	1157.4	1165.8	1174.3	1182.8	1191.2
10°	827.1	832.7	835.6	846.9	855.3	866.6	875.1	883.6	892.0	897.7	906.1
12.5°	671.8	666.2	663.4	663.4	663.4	663.4	663.4	669.0	674.7	680.3	686.0
15°	542.0	539.2	536.3	533.5	530.7	525.1	522.2	527.9	533.5	539.2	544.8
17.5°	454.5	454.5	454.5	451.7	448.8	446.0	443.2	446.0	448.8	448.8	451.7
20°	389.6	392.4	395.2	398.0	398.0	400.8	400.8	403.7	406.5	406.5	409.3
22.5°	350.0	352.9	352.9	352.9	355.7	355.7	355.7	358.5	361.3	364.1	367.0
25°	319.0	319.0	316.2	316.2	319.0	319.0	319.0	319.0	321.8	321.8	321.8
27.5°	302.0	299.2	299.2	299.2	299.2	296.4	296.4	296.4	296.4	296.4	296.4
30°	293.6	290.8	287.9	285.1	285.1	282.3	279.5	279.5	279.5	279.5	279.5
32.5°	290.8	285.1	279.5	276.6	276.6	273.8	271.0	268.2	268.2	265.3	262.5
35°	259.7	256.9	256.9	254.1	251.2	248.4	245.6	245.6	245.6	242.8	242.8
37.5°	225.8	228.7	228.7	228.7	231.5	231.5	231.5	231.5	234.3	234.3	234.3
40°	211.7	211.7	211.7	214.5	217.4	217.4	220.2	220.2	223.0	223.0	223.0
42.5°	200.4	197.6	197.6	200.4	200.4	203.2	203.2	206.1	208.9	208.9	211.7
45°	194.8	192.0	192.0	192.0	192.0	189.1	189.1	192.0	194.8	197.6	200.4
47.5°	183.5	183.5	180.7	180.7	180.7	180.7	180.7	180.7	183.5	183.5	183.5
50°	177.8	177.8	175.0	175.0	175.0	175.0	175.0	175.0	175.0	175.0	175.0
52.5°	172.2	169.4	169.4	169.4	169.4	166.5	166.5	166.5	166.5	166.5	166.5
55°	163.7	160.9	160.9	160.9	160.9	160.9	160.9	160.9	163.7	163.7	163.7
57.5°	155.3	152.4	152.4	152.4	155.3	155.3	155.3	155.3	158.1	158.1	158.1
60°	146.8	146.8	146.8	146.8	146.8	146.8	146.8	149.6	149.6	152.4	152.4
62.5°	138.3	138.3	138.3	138.3	141.1	141.1	141.1	141.1	144.0	144.0	144.0
65°	129.9	129.9	129.9	129.9	132.7	132.7	132.7	132.7	132.7	132.7	132.7
67.5°	121.4	121.4	121.4	121.4	121.4	121.4	121.4	124.2	124.2	127.0	127.0
70°	110.1	107.3	107.3	110.1	110.1	112.9	112.9	115.7	115.7	118.6	118.6
72.5°	98.8	98.8	98.8	98.8	98.8	98.8	98.8	101.6	104.4	104.4	107.3
75°	87.5	87.5	87.5	87.5	90.3	90.3	90.3	93.2	93.2	96.0	96.0
77.5°	79.0	76.2	76.2	76.2	79.0	79.0	79.0	81.9	81.9	84.7	84.7
80°	64.9	64.9	64.9	64.9	67.7	67.7	67.7	67.7	70.6	70.6	70.6
82.5°	53.6	53.6	53.6	53.6	53.6	53.6	53.6	53.6	56.5	56.5	56.5
85°	39.5	39.5	39.5	39.5	42.3	42.3	42.3	42.3	42.3	42.3	42.3
87.5°	25.4	25.4	25.4	25.4	25.4	25.4	25.4	25.4	28.2	28.2	28.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5
2.5°	1795.3	1795.3	1795.3	1795.3	1801.0	1803.8	1809.5	1812.3	1809.5	1806.6	1801.0
5°	1510.2	1513.1	1513.1	1515.9	1515.9	1515.9	1515.9	1515.9	1521.5	1527.2	1532.8
7.5°	1194.1	1196.9	1199.7	1202.5	1202.5	1202.5	1199.7	1199.7	1202.5	1202.5	1205.4
10°	914.6	925.9	934.4	942.8	937.2	928.7	923.1	914.6	914.6	914.6	911.8
12.5°	691.6	694.4	700.1	702.9	700.1	700.1	697.2	694.4	697.2	702.9	705.7
15°	547.6	547.6	550.5	550.5	553.3	556.1	556.1	558.9	564.6	567.4	573.0
17.5°	454.5	457.3	457.3	460.1	460.1	462.9	462.9	462.9	468.6	474.2	482.7
20°	409.3	409.3	409.3	409.3	409.3	406.5	406.5	403.7	406.5	412.1	415.0
22.5°	367.0	369.8	369.8	369.8	367.0	364.1	358.5	355.7	355.7	358.5	358.5
25°	321.8	319.0	319.0	316.2	316.2	319.0	319.0	319.0	321.8	321.8	324.6
27.5°	296.4	293.6	293.6	290.8	290.8	293.6	293.6	293.6	293.6	293.6	293.6
30°	276.6	276.6	273.8	271.0	273.8	273.8	276.6	276.6	279.5	279.5	282.3
32.5°	262.5	259.7	259.7	256.9	259.7	259.7	262.5	262.5	265.3	268.2	268.2
35°	242.8	242.8	242.8	242.8	242.8	242.8	239.9	239.9	239.9	239.9	239.9
37.5°	231.5	231.5	228.7	225.8	225.8	225.8	225.8	225.8	223.0	220.2	217.4
40°	223.0	220.2	220.2	217.4	214.5	214.5	211.7	208.9	208.9	206.1	206.1
42.5°	211.7	208.9	208.9	206.1	203.2	203.2	200.4	197.6	197.6	197.6	194.8
45°	197.6	197.6	194.8	192.0	192.0	192.0	189.1	189.1	189.1	189.1	186.3
47.5°	183.5	183.5	180.7	180.7	180.7	180.7	177.8	177.8	177.8	177.8	177.8
50°	175.0	175.0	175.0	175.0	175.0	175.0	172.2	172.2	172.2	172.2	172.2
52.5°	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5
55°	163.7	163.7	163.7	163.7	163.7	163.7	160.9	160.9	160.9	163.7	163.7
57.5°	158.1	158.1	155.3	155.3	155.3	155.3	155.3	155.3	155.3	155.3	155.3
60°	152.4	152.4	152.4	152.4	152.4	152.4	152.4	152.4	152.4	152.4	152.4
62.5°	144.0	144.0	144.0	144.0	144.0	146.8	146.8	146.8	146.8	146.8	144.0
65°	132.7	135.5	135.5	135.5	135.5	135.5	135.5	135.5	135.5	135.5	135.5
67.5°	127.0	127.0	127.0	127.0	127.0	127.0	127.0	127.0	127.0	127.0	127.0
70°	118.6	118.6	115.7	115.7	115.7	118.6	118.6	118.6	118.6	118.6	118.6
72.5°	107.3	107.3	107.3	107.3	107.3	107.3	107.3	107.3	107.3	110.1	110.1
75°	96.0	96.0	96.0	96.0	96.0	96.0	96.0	96.0	96.0	96.0	96.0
77.5°	84.7	84.7	81.9	81.9	81.9	84.7	84.7	84.7	84.7	87.5	87.5
80°	70.6	70.6	70.6	70.6	70.6	70.6	70.6	70.6	70.6	73.4	73.4
82.5°	56.5	56.5	56.5	56.5	56.5	56.5	56.5	56.5	56.5	59.3	59.3
85°	42.3	45.2	45.2	45.2	45.2	45.2	45.2	45.2	45.2	48.0	48.0
87.5°	28.2	28.2	28.2	28.2	28.2	28.2	25.4	25.4	25.4	25.4	22.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849
 CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5
2.5°	1798.2	1801.0	1803.8	1803.8	1806.6	1809.5	1809.5	1820.7	1832.0	1837.7	1843.3
5°	1538.5	1535.6	1535.6	1532.8	1530.0	1538.5	1546.9	1563.9	1580.8	1583.6	1589.3
7.5°	1205.4	1208.2	1211.0	1211.0	1213.8	1205.4	1194.1	1196.9	1199.7	1213.8	1225.1
10°	911.8	914.6	917.4	917.4	920.3	917.4	911.8	920.3	928.7	940.0	954.1
12.5°	708.5	717.0	725.5	731.1	739.6	745.2	748.1	759.3	767.8	781.9	796.0
15°	578.7	584.3	590.0	595.6	601.3	606.9	612.6	623.9	635.1	652.1	669.0
17.5°	488.4	488.4	491.2	491.2	491.2	496.8	502.5	508.1	510.9	527.9	544.8
20°	417.8	415.0	412.1	409.3	406.5	412.1	415.0	417.8	420.6	431.9	440.4
22.5°	358.5	358.5	361.3	361.3	361.3	358.5	352.9	355.7	355.7	361.3	369.8
25°	324.6	324.6	324.6	321.8	321.8	324.6	327.5	327.5	324.6	327.5	330.3
27.5°	293.6	296.4	296.4	299.2	299.2	302.0	302.0	302.0	302.0	304.9	307.7
30°	282.3	282.3	285.1	285.1	285.1	287.9	290.8	290.8	290.8	293.6	299.2
32.5°	271.0	273.8	276.6	279.5	282.3	285.1	285.1	287.9	287.9	290.8	293.6
35°	239.9	237.1	237.1	234.3	231.5	231.5	231.5	231.5	228.7	231.5	231.5
37.5°	214.5	214.5	214.5	211.7	211.7	214.5	214.5	214.5	214.5	217.4	217.4
40°	203.2	203.2	203.2	203.2	203.2	203.2	203.2	206.1	206.1	208.9	211.7
42.5°	194.8	194.8	194.8	194.8	194.8	197.6	197.6	197.6	197.6	200.4	200.4
45°	186.3	186.3	186.3	186.3	186.3	186.3	186.3	189.1	189.1	192.0	194.8
47.5°	177.8	177.8	177.8	177.8	177.8	180.7	183.5	183.5	183.5	186.3	186.3
50°	172.2	172.2	172.2	172.2	172.2	175.0	175.0	177.8	177.8	180.7	183.5
52.5°	166.5	166.5	166.5	166.5	166.5	169.4	169.4	172.2	172.2	175.0	177.8
55°	163.7	163.7	163.7	160.9	160.9	163.7	163.7	166.5	166.5	169.4	169.4
57.5°	155.3	155.3	155.3	155.3	155.3	155.3	155.3	158.1	158.1	160.9	163.7
60°	152.4	152.4	149.6	149.6	146.8	149.6	149.6	152.4	152.4	155.3	155.3
62.5°	144.0	144.0	144.0	141.1	141.1	144.0	144.0	144.0	144.0	146.8	149.6
65°	135.5	135.5	135.5	132.7	132.7	135.5	135.5	135.5	135.5	138.3	141.1
67.5°	127.0	127.0	127.0	124.2	124.2	124.2	124.2	127.0	127.0	129.9	132.7
70°	118.6	118.6	118.6	115.7	115.7	115.7	112.9	115.7	118.6	121.4	121.4
72.5°	110.1	110.1	110.1	107.3	107.3	107.3	104.4	107.3	107.3	110.1	110.1
75°	96.0	96.0	96.0	96.0	96.0	96.0	93.2	93.2	93.2	96.0	96.0
77.5°	87.5	87.5	87.5	84.7	84.7	84.7	81.9	81.9	81.9	84.7	84.7
80°	73.4	73.4	73.4	70.6	70.6	70.6	67.7	67.7	67.7	70.6	70.6
82.5°	59.3	59.3	59.3	56.5	56.5	56.5	53.6	53.6	53.6	56.5	56.5
85°	48.0	48.0	48.0	48.0	48.0	48.0	45.2	45.2	45.2	48.0	50.8
87.5°	22.6	22.6	25.4	25.4	25.4	25.4	22.6	22.6	19.8	19.8	22.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849
 CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5
2.5°	1849.0	1854.6	1868.7	1880.0	1894.1	1905.4	1913.9	1925.2	1933.7	1942.1	1947.8
5°	1592.1	1594.9	1609.0	1623.1	1634.4	1648.6	1668.3	1688.1	1707.8	1727.6	1741.7
7.5°	1239.2	1250.5	1267.5	1287.2	1304.2	1321.1	1340.9	1363.4	1383.2	1403.0	1422.7
10°	965.4	976.7	993.6	1010.6	1024.7	1041.6	1064.2	1086.8	1109.4	1132.0	1154.6
12.5°	810.2	824.3	844.0	863.8	880.7	900.5	928.7	954.1	982.4	1007.8	1036.0
15°	683.1	700.1	725.5	753.7	779.1	804.5	832.7	861.0	886.4	914.6	942.8
17.5°	561.7	578.7	601.3	626.7	649.3	671.8	705.7	736.8	770.6	801.7	832.7
20°	451.7	460.1	482.7	505.3	527.9	550.5	575.9	601.3	626.7	652.1	691.6
22.5°	375.4	381.1	392.4	400.8	412.1	420.6	446.0	471.4	494.0	519.4	556.1
25°	330.3	333.1	341.6	347.2	355.7	361.3	378.3	392.4	409.3	423.4	457.3
27.5°	307.7	310.5	313.3	316.2	319.0	321.8	333.1	344.4	352.9	364.1	395.2
30°	302.0	304.9	313.3	319.0	327.5	333.1	338.7	344.4	350.0	355.7	375.4
32.5°	296.4	299.2	299.2	296.4	296.4	293.6	299.2	302.0	307.7	310.5	327.5
35°	234.3	234.3	237.1	239.9	242.8	245.6	254.1	259.7	268.2	273.8	287.9
37.5°	220.2	220.2	223.0	228.7	231.5	234.3	239.9	245.6	251.2	256.9	271.0
40°	211.7	214.5	217.4	220.2	223.0	225.8	231.5	234.3	239.9	242.8	254.1
42.5°	203.2	203.2	206.1	211.7	214.5	217.4	223.0	225.8	231.5	234.3	245.6
45°	197.6	200.4	203.2	206.1	206.1	208.9	214.5	220.2	223.0	228.7	239.9
47.5°	189.1	189.1	194.8	197.6	203.2	206.1	211.7	214.5	220.2	223.0	234.3
50°	183.5	186.3	192.0	194.8	200.4	203.2	211.7	217.4	225.8	231.5	237.1
52.5°	177.8	180.7	186.3	189.1	194.8	197.6	208.9	220.2	228.7	239.9	239.9
55°	172.2	172.2	177.8	186.3	192.0	197.6	203.2	211.7	217.4	223.0	223.0
57.5°	163.7	166.5	172.2	180.7	186.3	192.0	197.6	203.2	206.1	211.7	208.9
60°	158.1	158.1	166.5	175.0	183.5	192.0	192.0	192.0	189.1	189.1	189.1
62.5°	149.6	152.4	163.7	177.8	189.1	200.4	192.0	183.5	175.0	166.5	169.4
65°	144.0	146.8	152.4	160.9	166.5	172.2	166.5	163.7	158.1	152.4	155.3
67.5°	132.7	135.5	138.3	138.3	141.1	141.1	141.1	141.1	141.1	141.1	144.0
70°	124.2	124.2	124.2	127.0	127.0	127.0	127.0	127.0	127.0	127.0	129.9
72.5°	112.9	112.9	112.9	112.9	112.9	112.9	112.9	112.9	112.9	112.9	115.7
75°	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	101.6
77.5°	87.5	87.5	87.5	87.5	87.5	87.5	87.5	87.5	84.7	84.7	87.5
80°	73.4	73.4	73.4	73.4	70.6	70.6	70.6	70.6	70.6	70.6	73.4
82.5°	59.3	59.3	59.3	59.3	56.5	56.5	56.5	56.5	53.6	53.6	56.5
85°	53.6	56.5	56.5	59.3	59.3	59.3	56.5	53.6	50.8	48.0	48.0
87.5°	22.6	22.6	22.6	22.6	19.8	19.8	19.8	19.8	19.8	19.8	19.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5
2.5°	1956.2	1961.9	1967.5	1976.0	1987.3	1995.8	2004.2	2021.2	2040.9	2057.9	2074.8
5°	1755.8	1769.9	1784.0	1801.0	1817.9	1832.0	1849.0	1882.8	1916.7	1947.8	1981.6
7.5°	1439.7	1459.4	1476.4	1504.6	1530.0	1558.2	1583.6	1626.0	1665.5	1707.8	1747.4
10°	1177.1	1199.7	1222.3	1259.0	1298.5	1335.2	1371.9	1405.8	1442.5	1476.4	1510.2
12.5°	1064.2	1089.6	1117.9	1140.4	1165.8	1188.4	1211.0	1250.5	1290.0	1329.6	1369.1
15°	971.1	999.3	1027.5	1055.8	1081.2	1109.4	1134.8	1168.7	1205.4	1239.2	1273.1
17.5°	863.8	892.0	923.1	954.1	985.2	1016.2	1047.3	1095.3	1143.3	1188.4	1236.4
20°	728.3	767.8	804.5	846.9	889.2	931.5	973.9	1024.7	1075.5	1123.5	1174.3
22.5°	592.8	629.5	666.2	717.0	767.8	815.8	866.6	934.4	999.3	1067.0	1132.0
25°	494.0	527.9	561.7	618.2	671.8	728.3	781.9	863.8	942.8	1024.7	1103.7
27.5°	426.3	457.3	488.4	547.6	606.9	663.4	722.7	813.0	900.5	990.8	1078.3
30°	395.2	415.0	434.7	491.2	547.6	601.3	657.7	745.2	832.7	920.3	1007.8
32.5°	344.4	361.3	378.3	429.1	479.9	527.9	578.7	669.0	756.5	846.9	934.4
35°	304.9	319.0	333.1	381.1	426.3	474.2	519.4	609.7	700.1	790.4	880.7
37.5°	282.3	296.4	307.7	350.0	395.2	437.5	479.9	570.2	657.7	748.1	835.6
40°	265.3	273.8	285.1	327.5	367.0	409.3	448.8	530.7	615.4	697.2	779.1
42.5°	254.1	265.3	273.8	310.5	350.0	386.7	423.4	502.5	581.5	657.7	736.8
45°	251.2	262.5	273.8	304.9	335.9	364.1	395.2	471.4	547.6	623.9	700.1
47.5°	245.6	254.1	265.3	290.8	313.3	338.7	361.3	437.5	513.8	587.2	663.4
50°	242.8	245.6	251.2	273.8	296.4	319.0	341.6	417.8	494.0	570.2	646.4
52.5°	239.9	239.9	239.9	259.7	279.5	296.4	316.2	392.4	471.4	547.6	623.9
55°	223.0	220.2	220.2	239.9	256.9	276.6	293.6	369.8	446.0	519.4	595.6
57.5°	206.1	203.2	200.4	217.4	234.3	251.2	268.2	344.4	423.4	499.6	575.9
60°	189.1	186.3	186.3	203.2	217.4	234.3	248.4	327.5	403.7	482.7	558.9
62.5°	169.4	172.2	172.2	186.3	203.2	217.4	231.5	310.5	392.4	471.4	550.5
65°	155.3	158.1	158.1	175.0	192.0	208.9	225.8	302.0	381.1	457.3	533.5
67.5°	144.0	146.8	146.8	166.5	183.5	203.2	220.2	287.9	358.5	426.3	494.0
70°	132.7	132.7	135.5	155.3	175.0	194.8	214.5	273.8	333.1	389.6	448.8
72.5°	118.6	121.4	124.2	144.0	160.9	180.7	197.6	251.2	304.9	358.5	412.1
75°	104.4	107.3	110.1	127.0	144.0	160.9	177.8	228.7	276.6	327.5	375.4
77.5°	93.2	96.0	98.8	112.9	127.0	141.1	155.3	192.0	231.5	268.2	304.9
80°	76.2	76.2	79.0	90.3	101.6	110.1	121.4	146.8	172.2	194.8	220.2
82.5°	56.5	59.3	59.3	67.7	73.4	81.9	87.5	101.6	112.9	127.0	138.3
85°	48.0	45.2	45.2	50.8	53.6	59.3	62.1	70.6	76.2	84.7	90.3
87.5°	19.8	16.9	16.9	19.8	25.4	28.2	31.1	31.1	33.9	33.9	33.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5
2.5°	2083.3	2088.9	2097.4	2103.0	2117.1	2128.4	2142.6	2153.8	2162.3	2176.4	2170.8
5°	2007.1	2032.5	2057.9	2083.3	2103.0	2122.8	2139.7	2159.5	2182.1	2224.4	2235.7
7.5°	1781.2	1815.1	1846.2	1880.0	1919.5	1959.1	1998.6	2038.1	2074.8	2128.4	2162.3
10°	1558.2	1606.2	1651.4	1699.4	1736.1	1772.8	1806.6	1843.3	1894.1	1947.8	2009.9
12.5°	1417.1	1465.1	1513.1	1561.0	1614.7	1665.5	1719.1	1769.9	1817.9	1860.3	1930.8
15°	1323.9	1377.6	1428.4	1479.2	1544.1	1606.2	1671.1	1733.2	1803.8	1860.3	1908.3
17.5°	1301.3	1366.3	1428.4	1493.3	1561.0	1628.8	1696.5	1764.3	1834.9	1919.5	1981.6
20°	1261.8	1349.3	1436.8	1524.3	1611.9	1696.5	1784.0	1868.7	1961.9	2063.5	2091.7
22.5°	1239.2	1343.7	1451.0	1555.4	1674.0	1795.3	1913.9	2032.5	2131.3	2207.5	2292.2
25°	1236.4	1366.3	1498.9	1628.8	1778.4	1925.2	2074.8	2221.6	2348.6	2424.8	2492.6
27.5°	1233.6	1391.7	1546.9	1702.2	1885.7	2066.3	2249.8	2430.5	2549.0	2659.1	2715.6
30°	1199.7	1388.8	1580.8	1769.9	1976.0	2182.1	2388.1	2594.2	2715.6	2791.8	2820.0
32.5°	1157.4	1380.4	1603.4	1826.4	2060.7	2295.0	2526.5	2760.8	2856.7	2921.7	2899.1
35°	1123.5	1369.1	1611.9	1854.6	2103.0	2354.3	2602.7	2851.1	2989.4	3079.7	3043.0
37.5°	1092.4	1349.3	1606.2	1863.1	2153.8	2444.6	2735.4	3026.1	3158.8	3254.8	3212.4
40°	1055.8	1329.6	1606.2	1880.0	2213.1	2543.4	2876.5	3206.8	3379.0	3460.8	3395.9
42.5°	1024.7	1309.8	1597.7	1882.8	2238.5	2594.2	2949.9	3305.6	3497.5	3613.3	3531.4
45°	985.2	1270.3	1552.6	1837.7	2230.1	2622.4	3012.0	3404.4	3627.4	3717.7	3604.8
47.5°	942.8	1225.1	1504.6	1784.0	2201.8	2619.6	3037.4	3455.2	3661.3	3768.5	3664.1
50°	928.7	1211.0	1490.5	1772.8	2224.4	2678.9	3130.6	3582.2	3731.8	3819.3	3681.0
52.5°	925.9	1225.1	1527.2	1826.4	2280.9	2732.5	3187.0	3638.7	3760.1	3853.2	3729.0
55°	917.4	1242.1	1563.9	1885.7	2359.9	2837.0	3311.2	3785.5	3906.8	3974.6	3881.4
57.5°	925.9	1275.9	1623.1	1973.2	2461.5	2949.9	3438.2	3926.6	4073.4	4121.4	4101.6
60°	931.5	1304.2	1674.0	2046.6	2523.6	3000.7	3477.8	3954.8	4107.3	4225.8	4248.4
62.5°	917.4	1284.4	1648.6	2015.5	2447.4	2879.3	3311.2	3743.1	3994.3	4169.4	4271.0
65°	875.1	1213.8	1555.4	1894.1	2292.2	2693.0	3091.0	3489.1	3754.4	4014.1	4096.0
67.5°	781.9	1069.9	1357.8	1645.7	1992.9	2340.2	2684.5	3031.8	3364.9	3616.1	3729.0
70°	677.5	903.3	1132.0	1357.8	1674.0	1990.1	2306.3	2622.4	2916.0	3192.7	3299.9
72.5°	590.0	765.0	942.8	1117.9	1343.7	1566.7	1792.5	2015.5	2362.7	2639.4	2743.8
75°	502.5	629.5	753.7	880.7	1036.0	1191.2	1343.7	1498.9	1744.5	1992.9	2097.4
77.5°	386.7	471.4	553.3	635.1	742.4	846.9	954.1	1058.6	1230.8	1417.1	1470.7
80°	268.2	316.2	361.3	409.3	494.0	578.7	663.4	748.1	861.0	965.4	1047.3
82.5°	166.5	197.6	225.8	254.1	321.8	389.6	454.5	522.2	567.4	573.0	654.9
85°	107.3	127.0	144.0	160.9	200.4	242.8	282.3	321.8	287.9	268.2	319.0
87.5°	42.3	53.6	62.1	70.6	67.7	64.9	62.1	59.3	50.8	45.2	56.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849
 CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5
2.5°	2176.4	2184.9	2193.4	2199.0	2207.5	2210.3	2213.1	2213.1	2215.9	2218.8	2224.4
5°	2280.9	2297.8	2314.7	2328.9	2345.8	2359.9	2371.2	2385.3	2396.6	2396.6	2393.8
7.5°	2193.4	2235.7	2278.0	2320.4	2362.7	2393.8	2422.0	2453.1	2481.3	2486.9	2492.6
10°	2077.6	2122.8	2165.1	2210.3	2252.6	2300.6	2345.8	2391.0	2439.0	2447.4	2458.7
12.5°	1970.4	2024.0	2077.6	2128.4	2182.1	2215.9	2249.8	2280.9	2314.7	2337.3	2359.9
15°	1967.5	2012.7	2057.9	2100.2	2145.4	2165.1	2184.9	2201.8	2221.6	2221.6	2224.4
17.5°	2032.5	2060.7	2088.9	2114.3	2142.6	2145.4	2151.0	2153.8	2156.7	2148.2	2139.7
20°	2159.5	2170.8	2182.1	2193.4	2204.7	2184.9	2168.0	2148.2	2128.4	2105.9	2086.1
22.5°	2345.8	2320.4	2295.0	2269.6	2244.2	2210.3	2173.6	2139.7	2103.0	2074.8	2046.6
25°	2520.8	2489.8	2458.7	2427.7	2396.6	2323.2	2249.8	2173.6	2100.2	2069.2	2038.1
27.5°	2755.1	2707.1	2659.1	2611.1	2563.2	2464.4	2365.6	2266.8	2168.0	2114.3	2063.5
30°	2811.6	2757.9	2704.3	2647.8	2594.2	2498.2	2405.1	2309.1	2213.1	2151.0	2091.7
32.5°	2893.4	2831.3	2769.2	2707.1	2645.0	2551.9	2458.7	2362.7	2269.6	2213.1	2153.8
35°	3028.9	2958.4	2887.8	2814.4	2743.8	2647.8	2554.7	2458.7	2362.7	2297.8	2235.7
37.5°	3144.7	3062.8	2980.9	2899.1	2817.2	2732.5	2645.0	2560.3	2472.8	2407.9	2345.8
40°	3274.5	3184.2	3093.9	3006.3	2916.0	2837.0	2757.9	2676.1	2597.0	2546.2	2495.4
42.5°	3387.4	3277.3	3170.1	3062.8	2952.7	2899.1	2848.3	2794.6	2741.0	2715.6	2687.4
45°	3466.5	3364.9	3260.4	3158.8	3057.2	3017.6	2978.1	2938.6	2899.1	2924.5	2949.9
47.5°	3500.3	3418.5	3339.4	3260.4	3178.5	3192.7	3206.8	3218.1	3232.2	3266.1	3302.7
50°	3531.4	3486.2	3438.2	3393.1	3345.1	3398.7	3449.5	3503.2	3556.8	3627.4	3697.9
52.5°	3593.5	3568.1	3545.5	3520.1	3494.7	3587.9	3681.0	3774.2	3867.3	3946.4	4025.4
55°	3779.8	3760.1	3740.3	3717.7	3697.9	3830.6	3960.5	4093.1	4225.8	4307.7	4389.5
57.5°	4036.7	4025.4	4011.3	4000.0	3985.9	4115.7	4242.8	4369.8	4499.6	4578.7	4660.5
60°	4231.5	4234.3	4234.3	4237.1	4237.1	4335.9	4434.7	4536.3	4635.1	4702.9	4773.5
62.5°	4335.9	4330.3	4324.6	4319.0	4313.3	4395.2	4477.1	4558.9	4640.8	4691.6	4742.4
65°	4223.0	4254.1	4285.1	4316.2	4347.2	4358.5	4367.0	4378.3	4386.7	4417.8	4448.8
67.5°	3844.7	3906.8	3966.1	4028.2	4087.5	4045.2	4005.6	3963.3	3921.0	3929.4	3935.1
70°	3424.1	3494.7	3568.1	3638.7	3709.2	3610.4	3511.6	3410.0	3311.2	3277.3	3243.5
72.5°	2887.8	2949.9	3014.8	3076.9	3139.0	3017.6	2899.1	2777.7	2656.3	2597.0	2537.8
75°	2207.5	2280.9	2357.1	2430.5	2503.9	2368.4	2230.1	2094.6	1956.2	1916.7	1880.0
77.5°	1609.0	1696.5	1784.0	1871.6	1959.1	1837.7	1716.3	1592.1	1470.7	1448.1	1425.5
80°	1171.5	1239.2	1304.2	1371.9	1436.8	1366.3	1295.7	1225.1	1154.6	1151.7	1148.9
82.5°	790.4	849.7	906.1	965.4	1021.9	993.6	968.2	940.0	911.8	940.0	971.1
85°	406.5	488.4	573.0	654.9	736.8	728.3	722.7	714.2	705.7	742.4	776.3
87.5°	81.9	152.4	223.0	290.8	361.3	344.4	327.5	307.7	290.8	302.0	310.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5
2.5°	2227.2	2230.1	2230.1	2230.1	2230.1	2230.1	2224.4	2221.6	2215.9	2210.3	2201.8
5°	2393.8	2391.0	2379.7	2368.4	2354.3	2343.0	2334.5	2323.2	2314.7	2303.5	2286.5
7.5°	2498.2	2503.9	2484.1	2467.2	2447.4	2427.7	2407.9	2388.1	2368.4	2348.6	2309.1
10°	2467.2	2475.6	2464.4	2453.1	2439.0	2427.7	2405.1	2379.7	2357.1	2331.7	2283.7
12.5°	2379.7	2402.3	2396.6	2391.0	2385.3	2379.7	2365.6	2348.6	2334.5	2317.6	2263.9
15°	2224.4	2224.4	2227.2	2230.1	2230.1	2232.9	2235.7	2238.5	2241.4	2244.2	2213.1
17.5°	2131.3	2122.8	2122.8	2122.8	2122.8	2122.8	2134.1	2148.2	2159.5	2170.8	2162.3
20°	2063.5	2043.8	2040.9	2040.9	2038.1	2035.3	2055.0	2077.6	2097.4	2117.1	2128.4
22.5°	2018.3	1990.1	1987.3	1984.5	1981.6	1978.8	2004.2	2029.6	2055.0	2080.4	2120.0
25°	2007.1	1976.0	1978.8	1981.6	1981.6	1984.5	2004.2	2024.0	2043.8	2063.5	2131.3
27.5°	2009.9	1959.1	1961.9	1964.7	1964.7	1967.5	1998.6	2026.8	2057.9	2086.1	2170.8
30°	2029.6	1970.4	1964.7	1959.1	1953.4	1947.8	1990.1	2032.5	2074.8	2117.1	2182.1
32.5°	2097.4	2040.9	2026.8	2012.7	1998.6	1984.5	2035.3	2083.3	2134.1	2182.1	2235.7
35°	2170.8	2108.7	2103.0	2097.4	2088.9	2083.3	2128.4	2176.4	2221.6	2266.8	2314.7
37.5°	2280.9	2218.8	2213.1	2204.7	2199.0	2190.5	2241.4	2289.3	2340.2	2388.1	2430.5
40°	2444.6	2393.8	2391.0	2391.0	2388.1	2385.3	2424.8	2467.2	2506.7	2546.2	2574.4
42.5°	2662.0	2636.6	2645.0	2656.3	2664.8	2673.2	2704.3	2738.2	2769.2	2800.3	2791.8
45°	2975.3	3000.7	3003.5	3006.3	3009.2	3012.0	3020.5	3031.8	3040.2	3048.7	3014.8
47.5°	3336.6	3370.5	3387.4	3404.4	3418.5	3435.4	3424.1	3410.0	3398.7	3384.6	3299.9
50°	3765.7	3836.3	3833.4	3830.6	3825.0	3822.2	3799.6	3777.0	3751.6	3729.0	3604.8
52.5°	4104.4	4183.5	4197.6	4211.7	4225.8	4239.9	4197.6	4155.3	4110.1	4067.7	3912.5
55°	4468.6	4550.5	4553.3	4556.1	4556.1	4558.9	4499.6	4440.4	4378.3	4319.0	4158.1
57.5°	4739.6	4818.6	4810.2	4804.5	4796.0	4787.6	4717.0	4646.4	4575.9	4505.3	4344.4
60°	4841.2	4909.0	4892.0	4875.1	4855.3	4838.4	4784.7	4731.1	4674.7	4621.0	4465.8
62.5°	4793.2	4844.0	4818.6	4796.0	4770.6	4745.2	4677.5	4606.9	4539.2	4468.6	4355.7
65°	4477.1	4508.1	4474.2	4443.2	4412.1	4378.3	4321.8	4265.3	4206.1	4149.6	4073.4
67.5°	3943.5	3949.2	3946.4	3943.5	3940.7	3937.9	3856.0	3774.2	3689.5	3607.6	3602.0
70°	3212.4	3178.5	3184.2	3192.7	3198.3	3203.9	3141.8	3082.6	3020.5	2958.4	2986.6
72.5°	2478.5	2419.2	2433.3	2450.2	2464.4	2478.5	2427.7	2379.7	2328.9	2278.0	2317.6
75°	1840.5	1803.8	1817.9	1834.9	1849.0	1863.1	1843.3	1823.6	1801.0	1781.2	1817.9
77.5°	1403.0	1380.4	1383.2	1383.2	1386.0	1386.0	1388.8	1394.5	1397.3	1400.1	1439.7
80°	1143.3	1140.4	1137.6	1134.8	1129.1	1126.3	1154.6	1182.8	1211.0	1239.2	1259.0
82.5°	999.3	1027.5	1010.6	996.5	979.5	962.6	988.0	1013.4	1038.8	1064.2	1055.8
85°	813.0	846.9	815.8	784.8	750.9	719.8	742.4	762.2	784.8	804.5	793.2
87.5°	321.8	330.3	279.5	231.5	180.7	129.9	206.1	279.5	355.7	429.1	440.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5	2032.5
2.5°	2193.4	2182.1	2173.6	2170.8	2165.1	2162.3	2156.7	2151.0	2142.6	2136.9	2128.4
5°	2266.8	2249.8	2230.1	2201.8	2176.4	2148.2	2120.0	2094.6	2069.2	2040.9	2015.5
7.5°	2269.6	2230.1	2190.5	2153.8	2114.3	2077.6	2038.1	2004.2	1967.5	1930.8	1897.0
10°	2238.5	2190.5	2142.6	2094.6	2049.4	2001.4	1953.4	1913.9	1871.6	1829.2	1789.7
12.5°	2213.1	2159.5	2105.9	2049.4	1995.8	1939.3	1882.8	1843.3	1803.8	1764.3	1724.8
15°	2182.1	2148.2	2117.1	2066.3	2015.5	1964.7	1913.9	1860.3	1809.5	1755.8	1702.2
17.5°	2156.7	2148.2	2139.7	2105.9	2072.0	2035.3	2001.4	1947.8	1894.1	1837.7	1784.0
20°	2142.6	2153.8	2165.1	2148.2	2131.3	2111.5	2094.6	2055.0	2015.5	1973.2	1933.7
22.5°	2159.5	2201.8	2241.4	2244.2	2249.8	2252.6	2255.5	2218.8	2182.1	2142.6	2105.9
25°	2199.0	2266.8	2334.5	2371.2	2407.9	2447.4	2484.1	2461.5	2439.0	2416.4	2393.8
27.5°	2252.6	2337.3	2422.0	2475.6	2526.5	2580.1	2633.7	2630.9	2628.1	2622.4	2619.6
30°	2244.2	2309.1	2374.0	2439.0	2503.9	2568.8	2633.7	2667.6	2698.7	2732.5	2766.4
32.5°	2292.2	2345.8	2402.3	2470.0	2537.8	2608.3	2676.1	2746.6	2814.4	2885.0	2955.5
35°	2365.6	2413.5	2464.4	2537.8	2614.0	2687.4	2763.6	2848.3	2935.8	3023.3	3108.0
37.5°	2475.6	2518.0	2563.2	2625.3	2690.2	2752.3	2817.2	2941.4	3065.6	3192.7	3316.9
40°	2602.7	2630.9	2659.1	2718.4	2777.7	2837.0	2896.3	3051.5	3206.8	3362.0	3517.3
42.5°	2786.2	2777.7	2769.2	2817.2	2868.0	2916.0	2966.8	3108.0	3249.1	3390.3	3531.4
45°	2980.9	2947.1	2913.2	2935.8	2961.2	2983.8	3009.2	3153.1	3297.1	3443.9	3587.9
47.5°	3215.2	3130.6	3045.9	3026.1	3006.3	2983.8	2964.0	3119.3	3274.5	3432.6	3587.9
50°	3480.6	3353.6	3229.4	3178.5	3124.9	3074.1	3020.5	3147.5	3277.3	3407.2	3534.2
52.5°	3757.2	3599.1	3443.9	3364.9	3285.8	3203.9	3124.9	3232.2	3342.3	3452.4	3559.6
55°	3994.3	3833.4	3669.7	3576.6	3483.4	3390.3	3297.1	3404.4	3511.6	3618.9	3726.2
57.5°	4183.5	4022.6	3861.7	3774.2	3683.8	3596.3	3506.0	3607.6	3712.1	3816.5	3918.1
60°	4313.3	4158.1	4002.8	3918.1	3833.4	3748.8	3664.1	3785.5	3906.8	4031.0	4152.4
62.5°	4245.6	4132.7	4019.8	3983.1	3946.4	3906.8	3870.1	3985.9	4098.8	4214.5	4330.3
65°	3997.2	3921.0	3844.7	3881.4	3921.0	3957.7	3997.2	4073.4	4149.6	4228.6	4304.9
67.5°	3593.5	3587.9	3579.4	3661.3	3743.1	3827.8	3909.7	3960.5	4008.5	4059.3	4110.1
70°	3014.8	3045.9	3074.1	3215.2	3356.4	3497.5	3638.7	3658.4	3678.2	3697.9	3717.7
72.5°	2359.9	2399.4	2441.8	2628.1	2811.6	2997.9	3184.2	3172.9	3161.6	3147.5	3136.2
75°	1857.4	1894.1	1933.7	2105.9	2278.0	2450.2	2622.4	2574.4	2529.3	2481.3	2433.3
77.5°	1482.0	1521.5	1563.9	1724.8	1885.7	2049.4	2210.3	2094.6	1978.8	1863.1	1747.4
80°	1275.9	1295.7	1312.6	1422.7	1530.0	1640.1	1750.2	1631.6	1510.2	1388.8	1270.3
82.5°	1047.3	1036.0	1027.5	1092.4	1157.4	1222.3	1287.2	1174.3	1061.4	945.7	832.7
85°	781.9	770.6	759.3	793.2	827.1	863.8	897.7	767.8	638.0	505.3	375.4
87.5°	454.5	465.8	477.1	513.8	550.5	590.0	626.7	494.0	361.3	225.8	93.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671849
 CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	2032.5	2032.5
2.5°	2111.5	2097.4
5°	1995.8	1976.0
7.5°	1868.7	1843.3
10°	1753.0	1719.1
12.5°	1679.6	1637.3
15°	1651.4	1600.6
17.5°	1736.1	1688.1
20°	1865.9	1801.0
22.5°	2024.0	1945.0
25°	2297.8	2201.8
27.5°	2520.8	2422.0
30°	2659.1	2551.9
32.5°	2811.6	2670.4
35°	2969.6	2834.2
37.5°	3161.6	3009.2
40°	3359.2	3201.1
42.5°	3427.0	3325.3
45°	3491.9	3395.9
47.5°	3506.0	3427.0
50°	3520.1	3508.8
52.5°	3559.6	3556.8
55°	3729.0	3731.8
57.5°	3937.9	3954.8
60°	4129.8	4110.1
62.5°	4228.6	4127.0
65°	4160.9	4019.8
67.5°	3957.7	3805.2
70°	3511.6	3305.6
72.5°	2955.5	2774.9
75°	2278.0	2125.6
77.5°	1620.3	1493.3
80°	1140.4	1013.4
82.5°	731.1	629.5
85°	330.3	287.9
87.5°	93.2	90.3
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P671849

CATALOG NUMBER: CCP-SA-1F-760-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)