

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671878

Luminaire Tested: **CCP-SA-1B-835-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671878
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1B-835-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @450mA w/ SLR
distribution lens
Light Source: (16) 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2361.6 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1

Input Watts (W): 24
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P671878
CATALOG NUMBER: CCP-SA-1B-835-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	485.9	0.0	485.9
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	1875.7	0.0	1875.7
	% Fixture	79.4	0.0	79.4
Total	Lumens	2361.6	0.0	2361.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.6	2.5
10°-20°	123.7	5.2
20°-30°	181.0	7.7
30°-40°	255.0	10.8
40°-50°	350.4	14.8
50°-60°	477.6	20.2
60°-70°	522.8	22.1
70°-80°	301.9	12.8
80°-90°	90.5	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2361.6	100.0
0°-180°	2361.6	100.0

Coefficient of Utilization



REPORT NUMBER: P671878


CATALOG NUMBER: CCP-SA-1B-835-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	242.5	10.3			
FM	(30°-60°)	861.8	36.5			
FH	(60°-80°)	694.5	29.4			G1/1800
FVH	(80°-90°)	76.9	3.3			G1/100
BL	(0°-30°)	120.8	5.1	B1/500		
BM	(30°-60°)	221.3	9.4	B1/1000		
BH	(60°-80°)	130.2	5.5	B1/500		G1/500
BVH	(80°-90°)	13.6	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2
2.5°	778.2	774.1	770.9	767.8	763.6	760.4	756.3	752.1	746.8	742.6	737.4
5°	733.2	720.6	708.1	700.7	692.4	685.0	676.6	667.2	657.8	647.3	637.9
7.5°	684.0	668.3	652.6	640.0	626.4	613.8	600.2	588.7	577.1	565.6	554.1
10°	637.9	623.2	608.6	592.9	576.1	560.4	543.6	527.9	512.2	496.5	480.8
12.5°	607.5	589.7	572.9	555.1	538.4	520.6	502.8	488.1	473.4	457.7	443.1
15°	593.9	577.1	561.4	543.6	525.8	508.0	490.2	473.4	457.7	441.0	424.2
17.5°	626.4	602.3	578.2	555.1	532.1	509.1	486.0	465.1	444.1	423.2	402.2
20°	668.3	637.9	608.6	580.3	551.0	522.7	493.3	464.0	434.7	405.4	376.0
22.5°	721.7	687.1	653.6	616.9	579.2	542.6	504.9	468.2	431.5	393.8	357.2
25°	817.0	776.2	735.3	682.9	629.5	577.1	523.7	475.5	428.4	380.2	332.0
27.5°	898.7	843.2	788.7	725.9	663.0	600.2	537.3	481.8	427.4	371.8	316.3
30°	946.9	892.4	838.0	761.5	686.1	609.6	533.1	471.3	410.6	348.8	287.0
32.5°	990.9	930.1	869.4	785.6	700.7	616.9	532.1	464.0	397.0	328.9	260.8
35°	1051.6	984.6	918.6	821.2	723.8	626.4	529.0	458.8	387.6	317.4	246.1
37.5°	1116.6	1033.8	952.1	844.2	736.4	628.5	520.6	451.4	382.3	313.2	244.1
40°	1187.8	1087.2	987.7	868.3	750.0	630.6	511.2	442.0	372.9	302.7	233.6
42.5°	1233.9	1125.0	1016.0	887.2	759.4	630.6	501.7	433.6	365.6	296.4	228.3
45°	1260.1	1154.3	1049.5	910.2	770.9	631.6	492.3	425.3	358.2	290.1	223.1
47.5°	1271.6	1173.1	1074.7	928.0	782.4	635.8	489.2	421.1	351.9	283.9	214.7
50°	1302.0	1215.0	1128.1	971.0	814.9	657.8	500.7	427.4	355.1	281.8	208.4
52.5°	1319.8	1245.4	1171.0	1009.7	848.4	687.1	525.8	444.1	362.4	280.7	199.0
55°	1384.7	1313.5	1242.3	1070.5	897.7	725.9	553.0	463.0	372.9	281.8	191.7
57.5°	1467.5	1392.0	1317.7	1132.3	946.9	761.5	576.1	479.7	382.3	286.0	188.5
60°	1525.1	1451.8	1379.5	1182.6	984.6	787.7	589.7	489.2	388.6	287.0	186.4
62.5°	1531.4	1437.1	1343.9	1152.2	960.5	767.8	576.1	478.7	381.3	282.8	185.4
65°	1491.6	1381.6	1271.6	1088.3	905.0	721.7	538.4	449.4	360.3	270.2	181.2
67.5°	1411.9	1283.1	1154.3	986.7	819.1	651.5	483.9	407.5	332.0	255.6	179.1
70°	1226.6	1113.4	1001.4	855.8	711.2	565.6	420.0	357.2	295.4	232.5	169.7
72.5°	1029.6	923.8	819.1	700.7	583.4	465.1	346.7	299.6	252.4	204.3	157.1
75°	788.7	709.1	630.6	542.6	454.6	365.6	277.6	243.0	208.4	173.9	139.3
77.5°	554.1	511.2	469.3	403.3	337.3	271.3	205.3	182.3	159.2	136.2	113.1
80°	376.0	351.9	328.9	281.8	234.6	186.4	139.3	124.6	108.9	94.3	78.6
82.5°	233.6	232.5	230.4	198.0	165.5	133.0	100.6	88.0	76.5	63.9	51.3
85°	106.8	124.6	141.4	123.6	105.8	88.0	70.2	61.8	53.4	44.0	35.6
87.5°	33.5	40.9	47.1	45.0	41.9	39.8	36.7	31.4	26.2	20.9	15.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2
2.5°	733.2	730.1	725.9	721.7	716.4	712.3	707.0	701.8	700.7	698.6	697.6
5°	631.6	625.3	618.0	611.7	605.4	598.1	591.8	584.5	579.2	572.9	567.7
7.5°	542.6	532.1	520.6	509.1	498.6	488.1	476.6	466.1	460.9	455.6	450.4
10°	471.3	460.9	451.4	441.0	433.6	427.4	420.0	412.7	406.4	400.1	393.8
12.5°	435.7	428.4	421.1	413.7	405.4	398.0	389.6	381.3	373.9	367.7	360.3
15°	413.7	403.3	391.7	381.3	369.7	359.3	347.8	336.2	327.8	320.5	312.1
17.5°	387.6	371.8	357.2	341.5	328.9	316.3	302.7	290.1	280.7	270.2	260.8
20°	358.2	340.4	321.6	303.8	289.1	275.5	260.8	246.1	235.7	224.2	213.7
22.5°	333.1	310.0	286.0	261.9	246.1	230.4	213.7	198.0	188.5	178.1	168.6
25°	305.9	280.7	254.5	228.3	212.6	195.9	180.2	163.4	156.1	149.8	142.5
27.5°	291.2	266.0	239.9	214.7	200.1	184.3	169.7	154.0	148.7	142.5	137.2
30°	261.9	237.8	212.6	187.5	177.0	167.6	157.1	146.6	144.5	143.5	141.4
32.5°	235.7	210.5	185.4	160.3	150.8	141.4	132.0	122.6	121.5	119.4	118.4
35°	222.1	198.0	172.8	148.7	140.4	130.9	122.6	113.1	111.0	107.9	105.8
37.5°	218.9	193.8	167.6	142.5	134.1	125.7	116.3	107.9	105.8	103.7	101.6
40°	210.5	186.4	163.4	139.3	130.9	122.6	113.1	104.7	102.6	100.6	98.5
42.5°	204.3	181.2	157.1	133.0	125.7	118.4	110.0	102.6	100.6	98.5	95.3
45°	199.0	174.9	149.8	125.7	120.5	115.2	108.9	103.7	101.6	98.5	96.4
47.5°	190.6	167.6	143.5	119.4	114.2	110.0	104.7	99.5	97.4	95.3	93.2
50°	184.3	160.3	136.2	112.1	107.9	103.7	99.5	95.3	95.3	96.4	96.4
52.5°	176.0	152.9	129.9	106.8	102.6	98.5	94.3	90.1	91.1	92.2	93.2
55°	168.6	146.6	123.6	100.6	96.4	92.2	86.9	82.7	83.8	84.8	85.9
57.5°	165.5	142.5	119.4	96.4	92.2	86.9	82.7	77.5	77.5	77.5	77.5
60°	163.4	139.3	116.3	92.2	86.9	82.7	77.5	72.3	71.2	71.2	70.2
62.5°	162.4	138.3	115.2	91.1	84.8	79.6	73.3	67.0	66.0	64.9	63.9
65°	158.2	136.2	113.1	90.1	82.7	76.5	69.1	61.8	60.8	60.8	59.7
67.5°	157.1	134.1	112.1	89.0	81.7	73.3	66.0	57.6	56.6	55.5	54.5
70°	148.7	128.8	107.9	86.9	78.6	71.2	62.8	54.5	53.4	51.3	50.3
72.5°	138.3	120.5	101.6	82.7	74.4	66.0	57.6	49.2	48.2	47.1	45.0
75°	122.6	105.8	89.0	72.3	64.9	58.7	51.3	44.0	42.9	41.9	39.8
77.5°	100.6	86.9	74.4	60.8	55.5	50.3	45.0	39.8	38.8	37.7	35.6
80°	71.2	62.8	55.5	47.1	44.0	39.8	36.7	32.5	32.5	31.4	31.4
82.5°	47.1	42.9	38.8	34.6	32.5	30.4	28.3	26.2	26.2	25.1	25.1
85°	33.5	31.4	28.3	26.2	25.1	23.0	22.0	19.9	19.9	19.9	19.9
87.5°	15.7	15.7	14.7	14.7	13.6	13.6	12.6	11.5	11.5	11.5	11.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2
2.5°	695.5	692.4	689.2	685.0	681.9	677.7	672.5	668.3	663.0	663.0	662.0
5°	561.4	558.3	555.1	551.0	547.8	543.6	540.5	536.3	532.1	532.1	531.1
7.5°	445.2	438.9	432.6	425.3	419.0	414.8	410.6	405.4	401.2	398.0	394.9
10°	387.6	381.3	373.9	367.7	360.3	355.1	349.8	343.6	338.3	334.1	329.9
12.5°	353.0	345.7	338.3	331.0	323.7	316.3	310.0	302.7	295.4	290.1	284.9
15°	303.8	296.4	289.1	281.8	274.4	266.0	257.7	248.2	239.9	235.7	232.5
17.5°	250.3	243.0	234.6	227.3	218.9	212.6	206.3	200.1	193.8	189.6	186.4
20°	202.2	193.8	185.4	177.0	168.6	164.4	160.3	156.1	151.9	148.7	146.6
22.5°	158.2	152.9	148.7	143.5	138.3	135.1	133.0	129.9	126.7	126.7	126.7
25°	135.1	132.0	129.9	126.7	123.6	122.6	121.5	119.4	118.4	117.3	117.3
27.5°	130.9	127.8	124.6	121.5	118.4	117.3	116.3	114.2	113.1	113.1	113.1
30°	139.3	138.3	137.2	136.2	135.1	133.0	129.9	127.8	124.6	122.6	120.5
32.5°	116.3	115.2	115.2	114.2	113.1	115.2	116.3	118.4	119.4	120.5	121.5
35°	102.6	100.6	98.5	96.4	94.3	93.2	92.2	91.1	90.1	90.1	89.0
37.5°	99.5	97.4	95.3	93.2	91.1	90.1	89.0	88.0	86.9	86.9	85.9
40°	96.4	94.3	93.2	91.1	89.0	88.0	86.9	84.8	83.8	82.7	82.7
42.5°	93.2	92.2	90.1	89.0	86.9	85.9	84.8	82.7	81.7	80.7	79.6
45°	93.2	91.1	89.0	86.9	84.8	83.8	81.7	80.7	78.6	78.6	77.5
47.5°	91.1	89.0	86.9	84.8	82.7	81.7	79.6	78.6	76.5	75.4	74.4
50°	96.4	93.2	89.0	85.9	81.7	80.7	78.6	77.5	75.4	74.4	73.3
52.5°	94.3	91.1	86.9	83.8	79.6	77.5	76.5	74.4	72.3	71.2	70.2
55°	86.9	83.8	81.7	78.6	75.4	73.3	71.2	69.1	67.0	66.0	66.0
57.5°	77.5	76.5	75.4	74.4	73.3	71.2	69.1	66.0	63.9	62.8	61.8
60°	69.1	70.2	71.2	72.3	73.3	70.2	67.0	63.9	60.8	59.7	58.7
62.5°	62.8	64.9	67.0	68.1	70.2	67.0	63.9	60.8	57.6	56.6	55.5
65°	58.7	59.7	59.7	60.8	60.8	58.7	57.6	55.5	53.4	52.4	52.4
67.5°	53.4	53.4	53.4	52.4	52.4	51.3	51.3	50.3	49.2	48.2	48.2
70°	48.2	48.2	48.2	47.1	47.1	46.1	46.1	45.0	44.0	44.0	42.9
72.5°	44.0	44.0	42.9	42.9	41.9	41.9	41.9	40.9	40.9	39.8	39.8
75°	38.8	38.8	37.7	37.7	36.7	36.7	36.7	35.6	35.6	35.6	34.6
77.5°	34.6	34.6	33.5	33.5	32.5	32.5	32.5	31.4	31.4	30.4	30.4
80°	30.4	30.4	29.3	29.3	28.3	28.3	27.2	27.2	26.2	26.2	25.1
82.5°	24.1	24.1	24.1	24.1	24.1	23.0	23.0	22.0	20.9	20.9	19.9
85°	19.9	19.9	19.9	18.9	18.9	18.9	17.8	17.8	16.8	15.7	15.7
87.5°	11.5	11.5	11.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	9.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2
2.5°	662.0	660.9	656.7	652.6	656.7	660.9	660.9	660.9	659.9	659.9	659.9
5°	531.1	530.0	527.9	525.8	525.8	524.8	526.9	529.0	531.1	533.1	535.2
7.5°	390.7	387.6	384.4	381.3	383.4	384.4	387.6	389.6	392.8	394.9	400.1
10°	325.8	321.6	318.4	315.3	313.2	311.1	309.0	307.9	305.9	303.8	305.9
12.5°	278.6	273.4	268.1	261.9	260.8	259.8	257.7	255.6	253.5	251.4	250.3
15°	228.3	224.2	222.1	218.9	214.7	210.5	208.4	207.4	205.3	203.2	202.2
17.5°	182.3	178.1	174.9	171.8	170.7	168.6	168.6	168.6	168.6	168.6	168.6
20°	143.5	140.4	140.4	139.3	139.3	138.3	139.3	140.4	140.4	141.4	142.5
22.5°	125.7	125.7	124.6	123.6	124.6	124.6	125.7	126.7	127.8	128.8	129.9
25°	116.3	115.2	116.3	117.3	117.3	117.3	118.4	118.4	119.4	119.4	119.4
27.5°	112.1	112.1	113.1	113.1	114.2	114.2	114.2	113.1	113.1	112.1	112.1
30°	118.4	116.3	116.3	116.3	115.2	114.2	113.1	113.1	112.1	111.0	110.0
32.5°	122.6	123.6	122.6	120.5	119.4	117.3	116.3	114.2	113.1	111.0	108.9
35°	89.0	88.0	90.1	91.1	92.2	93.2	94.3	95.3	95.3	96.4	96.4
37.5°	85.9	84.8	84.8	83.8	83.8	83.8	83.8	83.8	82.7	82.7	83.8
40°	81.7	80.7	80.7	79.6	79.6	78.6	78.6	78.6	78.6	78.6	78.6
42.5°	78.6	77.5	77.5	77.5	77.5	76.5	76.5	75.4	75.4	74.4	74.4
45°	77.5	76.5	75.4	74.4	74.4	73.3	73.3	73.3	72.3	72.3	72.3
47.5°	73.3	72.3	72.3	71.2	71.2	70.2	70.2	70.2	69.1	69.1	69.1
50°	71.2	70.2	70.2	69.1	69.1	68.1	68.1	68.1	67.0	67.0	67.0
52.5°	68.1	67.0	67.0	67.0	66.0	64.9	64.9	64.9	63.9	63.9	63.9
55°	64.9	63.9	63.9	63.9	62.8	61.8	61.8	61.8	60.8	60.8	60.8
57.5°	60.8	59.7	59.7	58.7	58.7	58.7	58.7	58.7	57.6	57.6	57.6
60°	57.6	56.6	56.6	55.5	55.5	54.5	54.5	54.5	54.5	54.5	54.5
62.5°	54.5	53.4	52.4	51.3	52.4	52.4	52.4	52.4	51.3	51.3	51.3
65°	51.3	50.3	49.2	48.2	48.2	48.2	48.2	48.2	48.2	48.2	48.2
67.5°	47.1	46.1	45.0	44.0	45.0	45.0	45.0	45.0	45.0	45.0	45.0
70°	42.9	41.9	41.9	40.9	40.9	39.8	39.8	40.9	40.9	40.9	40.9
72.5°	38.8	37.7	37.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7
75°	34.6	33.5	33.5	32.5	32.5	32.5	32.5	32.5	32.5	32.5	32.5
77.5°	29.3	28.3	28.3	28.3	28.3	28.3	28.3	29.3	29.3	29.3	29.3
80°	25.1	24.1	24.1	24.1	24.1	24.1	24.1	24.1	24.1	24.1	24.1
82.5°	19.9	18.9	18.9	18.9	18.9	18.9	18.9	18.9	18.9	18.9	18.9
85°	14.7	13.6	13.6	13.6	14.7	14.7	14.7	14.7	14.7	14.7	14.7
87.5°	9.4	8.4	8.4	8.4	9.4	9.4	9.4	9.4	8.4	8.4	8.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2
2.5°	659.9	659.9	659.9	658.8	657.8	656.7	655.7	658.8	660.9	664.1	666.2
5°	536.3	538.4	539.4	542.6	545.7	548.9	552.0	554.1	556.2	557.2	559.3
7.5°	404.3	409.5	413.7	417.9	422.1	425.3	429.5	432.6	435.7	438.9	442.0
10°	306.9	309.0	310.0	314.2	317.4	321.6	324.7	327.8	331.0	333.1	336.2
12.5°	249.3	247.2	246.1	246.1	246.1	246.1	246.1	248.2	250.3	252.4	254.5
15°	201.1	200.1	199.0	198.0	196.9	194.8	193.8	195.9	198.0	200.1	202.2
17.5°	168.6	168.6	168.6	167.6	166.5	165.5	164.4	165.5	166.5	166.5	167.6
20°	144.5	145.6	146.6	147.7	147.7	148.7	148.7	149.8	150.8	150.8	151.9
22.5°	129.9	130.9	130.9	130.9	132.0	132.0	132.0	133.0	134.1	135.1	136.2
25°	118.4	118.4	117.3	117.3	118.4	118.4	118.4	118.4	119.4	119.4	119.4
27.5°	112.1	111.0	111.0	111.0	111.0	110.0	110.0	110.0	110.0	110.0	110.0
30°	108.9	107.9	106.8	105.8	105.8	104.7	103.7	103.7	103.7	103.7	103.7
32.5°	107.9	105.8	103.7	102.6	102.6	101.6	100.6	99.5	99.5	98.5	97.4
35°	96.4	95.3	95.3	94.3	93.2	92.2	91.1	91.1	91.1	90.1	90.1
37.5°	83.8	84.8	84.8	84.8	85.9	85.9	85.9	85.9	86.9	86.9	86.9
40°	78.6	78.6	78.6	79.6	80.7	80.7	81.7	81.7	82.7	82.7	82.7
42.5°	74.4	73.3	73.3	74.4	74.4	75.4	75.4	76.5	77.5	77.5	78.6
45°	72.3	71.2	71.2	71.2	71.2	70.2	70.2	71.2	72.3	73.3	74.4
47.5°	68.1	68.1	67.0	67.0	67.0	67.0	67.0	67.0	68.1	68.1	68.1
50°	66.0	66.0	64.9	64.9	64.9	64.9	64.9	64.9	64.9	64.9	64.9
52.5°	63.9	62.8	62.8	62.8	62.8	61.8	61.8	61.8	61.8	61.8	61.8
55°	60.8	59.7	59.7	59.7	59.7	59.7	59.7	59.7	60.8	60.8	60.8
57.5°	57.6	56.6	56.6	56.6	57.6	57.6	57.6	57.6	58.7	58.7	58.7
60°	54.5	54.5	54.5	54.5	54.5	54.5	54.5	55.5	55.5	56.6	56.6
62.5°	51.3	51.3	51.3	51.3	52.4	52.4	52.4	52.4	53.4	53.4	53.4
65°	48.2	48.2	48.2	48.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2
67.5°	45.0	45.0	45.0	45.0	45.0	45.0	45.0	46.1	46.1	47.1	47.1
70°	40.9	39.8	39.8	40.9	40.9	41.9	41.9	42.9	42.9	44.0	44.0
72.5°	36.7	36.7	36.7	36.7	36.7	36.7	36.7	37.7	38.8	38.8	39.8
75°	32.5	32.5	32.5	32.5	33.5	33.5	33.5	34.6	34.6	35.6	35.6
77.5°	29.3	28.3	28.3	28.3	29.3	29.3	29.3	30.4	30.4	31.4	31.4
80°	24.1	24.1	24.1	24.1	25.1	25.1	25.1	25.1	26.2	26.2	26.2
82.5°	19.9	19.9	19.9	19.9	19.9	19.9	19.9	19.9	20.9	20.9	20.9
85°	14.7	14.7	14.7	14.7	15.7	15.7	15.7	15.7	15.7	15.7	15.7
87.5°	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	10.5	10.5	10.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2
2.5°	666.2	666.2	666.2	666.2	668.3	669.3	671.4	672.5	671.4	670.4	668.3
5°	560.4	561.4	561.4	562.5	562.5	562.5	562.5	562.5	564.6	566.7	568.8
7.5°	443.1	444.1	445.2	446.2	446.2	446.2	445.2	445.2	446.2	446.2	447.3
10°	339.4	343.6	346.7	349.8	347.8	344.6	342.5	339.4	339.4	339.4	338.3
12.5°	256.6	257.7	259.8	260.8	259.8	259.8	258.7	257.7	258.7	260.8	261.9
15°	203.2	203.2	204.3	204.3	205.3	206.3	206.3	207.4	209.5	210.5	212.6
17.5°	168.6	169.7	169.7	170.7	170.7	171.8	171.8	171.8	173.9	176.0	179.1
20°	151.9	151.9	151.9	151.9	151.9	150.8	150.8	149.8	150.8	152.9	154.0
22.5°	136.2	137.2	137.2	137.2	136.2	135.1	133.0	132.0	132.0	133.0	133.0
25°	119.4	118.4	118.4	117.3	117.3	118.4	118.4	118.4	119.4	119.4	120.5
27.5°	110.0	108.9	108.9	107.9	107.9	108.9	108.9	108.9	108.9	108.9	108.9
30°	102.6	102.6	101.6	100.6	101.6	101.6	102.6	102.6	103.7	103.7	104.7
32.5°	97.4	96.4	96.4	95.3	96.4	96.4	97.4	97.4	98.5	99.5	99.5
35°	90.1	90.1	90.1	90.1	90.1	90.1	89.0	89.0	89.0	89.0	89.0
37.5°	85.9	85.9	84.8	83.8	83.8	83.8	83.8	83.8	82.7	81.7	80.7
40°	82.7	81.7	81.7	80.7	79.6	79.6	78.6	77.5	77.5	76.5	76.5
42.5°	78.6	77.5	77.5	76.5	75.4	75.4	74.4	73.3	73.3	73.3	72.3
45°	73.3	73.3	72.3	71.2	71.2	71.2	70.2	70.2	70.2	70.2	69.1
47.5°	68.1	68.1	67.0	67.0	67.0	67.0	66.0	66.0	66.0	66.0	66.0
50°	64.9	64.9	64.9	64.9	64.9	64.9	63.9	63.9	63.9	63.9	63.9
52.5°	61.8	61.8	61.8	61.8	61.8	61.8	61.8	61.8	61.8	61.8	61.8
55°	60.8	60.8	60.8	60.8	60.8	60.8	59.7	59.7	59.7	60.8	60.8
57.5°	58.7	58.7	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6
60°	56.6	56.6	56.6	56.6	56.6	56.6	56.6	56.6	56.6	56.6	56.6
62.5°	53.4	53.4	53.4	53.4	53.4	54.5	54.5	54.5	54.5	54.5	53.4
65°	49.2	50.3	50.3	50.3	50.3	50.3	50.3	50.3	50.3	50.3	50.3
67.5°	47.1	47.1	47.1	47.1	47.1	47.1	47.1	47.1	47.1	47.1	47.1
70°	44.0	44.0	42.9	42.9	42.9	44.0	44.0	44.0	44.0	44.0	44.0
72.5°	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8	40.9	40.9
75°	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6
77.5°	31.4	31.4	30.4	30.4	30.4	31.4	31.4	31.4	31.4	32.5	32.5
80°	26.2	26.2	26.2	26.2	26.2	26.2	26.2	26.2	26.2	27.2	27.2
82.5°	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9	22.0	22.0
85°	15.7	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.8	17.8	17.8
87.5°	10.5	10.5	10.5	10.5	10.5	10.5	9.4	9.4	9.4	9.4	8.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2
2.5°	667.2	668.3	669.3	669.3	670.4	671.4	671.4	675.6	679.8	681.9	684.0
5°	570.9	569.8	569.8	568.8	567.7	570.9	574.0	580.3	586.6	587.6	589.7
7.5°	447.3	448.3	449.4	449.4	450.4	447.3	443.1	444.1	445.2	450.4	454.6
10°	338.3	339.4	340.4	340.4	341.5	340.4	338.3	341.5	344.6	348.8	354.0
12.5°	262.9	266.0	269.2	271.3	274.4	276.5	277.6	281.8	284.9	290.1	295.4
15°	214.7	216.8	218.9	221.0	223.1	225.2	227.3	231.5	235.7	242.0	248.2
17.5°	181.2	181.2	182.3	182.3	182.3	184.3	186.4	188.5	189.6	195.9	202.2
20°	155.0	154.0	152.9	151.9	150.8	152.9	154.0	155.0	156.1	160.3	163.4
22.5°	133.0	133.0	134.1	134.1	134.1	133.0	130.9	132.0	132.0	134.1	137.2
25°	120.5	120.5	120.5	119.4	119.4	120.5	121.5	121.5	120.5	121.5	122.6
27.5°	108.9	110.0	110.0	111.0	111.0	112.1	112.1	112.1	112.1	113.1	114.2
30°	104.7	104.7	105.8	105.8	105.8	106.8	107.9	107.9	107.9	108.9	111.0
32.5°	100.6	101.6	102.6	103.7	104.7	105.8	105.8	106.8	106.8	107.9	108.9
35°	89.0	88.0	88.0	86.9	85.9	85.9	85.9	85.9	84.8	85.9	85.9
37.5°	79.6	79.6	79.6	78.6	78.6	79.6	79.6	79.6	79.6	80.7	80.7
40°	75.4	75.4	75.4	75.4	75.4	75.4	75.4	76.5	76.5	77.5	78.6
42.5°	72.3	72.3	72.3	72.3	72.3	73.3	73.3	73.3	73.3	74.4	74.4
45°	69.1	69.1	69.1	69.1	69.1	69.1	69.1	70.2	70.2	71.2	72.3
47.5°	66.0	66.0	66.0	66.0	66.0	67.0	68.1	68.1	68.1	69.1	69.1
50°	63.9	63.9	63.9	63.9	63.9	64.9	64.9	66.0	66.0	67.0	68.1
52.5°	61.8	61.8	61.8	61.8	61.8	62.8	62.8	63.9	63.9	64.9	66.0
55°	60.8	60.8	60.8	59.7	59.7	60.8	60.8	61.8	61.8	62.8	62.8
57.5°	57.6	57.6	57.6	57.6	57.6	57.6	57.6	58.7	58.7	59.7	60.8
60°	56.6	56.6	55.5	55.5	54.5	55.5	55.5	56.6	56.6	57.6	57.6
62.5°	53.4	53.4	53.4	52.4	52.4	53.4	53.4	53.4	53.4	54.5	55.5
65°	50.3	50.3	50.3	49.2	49.2	50.3	50.3	50.3	50.3	51.3	52.4
67.5°	47.1	47.1	47.1	46.1	46.1	46.1	46.1	47.1	47.1	48.2	49.2
70°	44.0	44.0	44.0	42.9	42.9	42.9	41.9	42.9	44.0	45.0	45.0
72.5°	40.9	40.9	40.9	39.8	39.8	39.8	38.8	39.8	39.8	40.9	40.9
75°	35.6	35.6	35.6	35.6	35.6	35.6	34.6	34.6	34.6	35.6	35.6
77.5°	32.5	32.5	32.5	31.4	31.4	31.4	30.4	30.4	30.4	31.4	31.4
80°	27.2	27.2	27.2	26.2	26.2	26.2	25.1	25.1	25.1	26.2	26.2
82.5°	22.0	22.0	22.0	20.9	20.9	20.9	19.9	19.9	19.9	20.9	20.9
85°	17.8	17.8	17.8	17.8	17.8	17.8	16.8	16.8	16.8	17.8	18.9
87.5°	8.4	8.4	9.4	9.4	9.4	9.4	8.4	8.4	7.3	7.3	8.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2
2.5°	686.1	688.2	693.4	697.6	702.8	707.0	710.2	714.4	717.5	720.6	722.7
5°	590.8	591.8	597.0	602.3	606.5	611.7	619.0	626.4	633.7	641.0	646.3
7.5°	459.8	464.0	470.3	477.6	483.9	490.2	497.5	505.9	513.2	520.6	527.9
10°	358.2	362.4	368.7	375.0	380.2	386.5	394.9	403.3	411.6	420.0	428.4
12.5°	300.6	305.9	313.2	320.5	326.8	334.1	344.6	354.0	364.5	373.9	384.4
15°	253.5	259.8	269.2	279.7	289.1	298.5	309.0	319.5	328.9	339.4	349.8
17.5°	208.4	214.7	223.1	232.5	240.9	249.3	261.9	273.4	286.0	297.5	309.0
20°	167.6	170.7	179.1	187.5	195.9	204.3	213.7	223.1	232.5	242.0	256.6
22.5°	139.3	141.4	145.6	148.7	152.9	156.1	165.5	174.9	183.3	192.7	206.3
25°	122.6	123.6	126.7	128.8	132.0	134.1	140.4	145.6	151.9	157.1	169.7
27.5°	114.2	115.2	116.3	117.3	118.4	119.4	123.6	127.8	130.9	135.1	146.6
30°	112.1	113.1	116.3	118.4	121.5	123.6	125.7	127.8	129.9	132.0	139.3
32.5°	110.0	111.0	111.0	110.0	110.0	108.9	111.0	112.1	114.2	115.2	121.5
35°	86.9	86.9	88.0	89.0	90.1	91.1	94.3	96.4	99.5	101.6	106.8
37.5°	81.7	81.7	82.7	84.8	85.9	86.9	89.0	91.1	93.2	95.3	100.6
40°	78.6	79.6	80.7	81.7	82.7	83.8	85.9	86.9	89.0	90.1	94.3
42.5°	75.4	75.4	76.5	78.6	79.6	80.7	82.7	83.8	85.9	86.9	91.1
45°	73.3	74.4	75.4	76.5	76.5	77.5	79.6	81.7	82.7	84.8	89.0
47.5°	70.2	70.2	72.3	73.3	75.4	76.5	78.6	79.6	81.7	82.7	86.9
50°	68.1	69.1	71.2	72.3	74.4	75.4	78.6	80.7	83.8	85.9	88.0
52.5°	66.0	67.0	69.1	70.2	72.3	73.3	77.5	81.7	84.8	89.0	89.0
55°	63.9	63.9	66.0	69.1	71.2	73.3	75.4	78.6	80.7	82.7	82.7
57.5°	60.8	61.8	63.9	67.0	69.1	71.2	73.3	75.4	76.5	78.6	77.5
60°	58.7	58.7	61.8	64.9	68.1	71.2	71.2	71.2	70.2	70.2	70.2
62.5°	55.5	56.6	60.8	66.0	70.2	74.4	71.2	68.1	64.9	61.8	62.8
65°	53.4	54.5	56.6	59.7	61.8	63.9	61.8	60.8	58.7	56.6	57.6
67.5°	49.2	50.3	51.3	51.3	52.4	52.4	52.4	52.4	52.4	52.4	53.4
70°	46.1	46.1	46.1	47.1	47.1	47.1	47.1	47.1	47.1	47.1	48.2
72.5°	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	42.9
75°	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7	37.7
77.5°	32.5	32.5	32.5	32.5	32.5	32.5	32.5	32.5	31.4	31.4	32.5
80°	27.2	27.2	27.2	27.2	26.2	26.2	26.2	26.2	26.2	26.2	27.2
82.5°	22.0	22.0	22.0	22.0	20.9	20.9	20.9	20.9	19.9	19.9	20.9
85°	19.9	20.9	20.9	22.0	22.0	22.0	20.9	19.9	18.9	17.8	17.8
87.5°	8.4	8.4	8.4	8.4	7.3	7.3	7.3	7.3	7.3	7.3	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2
2.5°	725.9	728.0	730.1	733.2	737.4	740.5	743.7	750.0	757.3	763.6	769.9
5°	651.5	656.7	662.0	668.3	674.6	679.8	686.1	698.6	711.2	722.7	735.3
7.5°	534.2	541.5	547.8	558.3	567.7	578.2	587.6	603.3	618.0	633.7	648.4
10°	436.8	445.2	453.5	467.2	481.8	495.4	509.1	521.6	535.2	547.8	560.4
12.5°	394.9	404.3	414.8	423.2	432.6	441.0	449.4	464.0	478.7	493.3	508.0
15°	360.3	370.8	381.3	391.7	401.2	411.6	421.1	433.6	447.3	459.8	472.4
17.5°	320.5	331.0	342.5	354.0	365.6	377.1	388.6	406.4	424.2	441.0	458.8
20°	270.2	284.9	298.5	314.2	329.9	345.7	361.4	380.2	399.1	416.9	435.7
22.5°	220.0	233.6	247.2	266.0	284.9	302.7	321.6	346.7	370.8	395.9	420.0
25°	183.3	195.9	208.4	229.4	249.3	270.2	290.1	320.5	349.8	380.2	409.5
27.5°	158.2	169.7	181.2	203.2	225.2	246.1	268.1	301.7	334.1	367.7	400.1
30°	146.6	154.0	161.3	182.3	203.2	223.1	244.1	276.5	309.0	341.5	373.9
32.5°	127.8	134.1	140.4	159.2	178.1	195.9	214.7	248.2	280.7	314.2	346.7
35°	113.1	118.4	123.6	141.4	158.2	176.0	192.7	226.2	259.8	293.3	326.8
37.5°	104.7	110.0	114.2	129.9	146.6	162.4	178.1	211.6	244.1	277.6	310.0
40°	98.5	101.6	105.8	121.5	136.2	151.9	166.5	196.9	228.3	258.7	289.1
42.5°	94.3	98.5	101.6	115.2	129.9	143.5	157.1	186.4	215.8	244.1	273.4
45°	93.2	97.4	101.6	113.1	124.6	135.1	146.6	174.9	203.2	231.5	259.8
47.5°	91.1	94.3	98.5	107.9	116.3	125.7	134.1	162.4	190.6	217.9	246.1
50°	90.1	91.1	93.2	101.6	110.0	118.4	126.7	155.0	183.3	211.6	239.9
52.5°	89.0	89.0	89.0	96.4	103.7	110.0	117.3	145.6	174.9	203.2	231.5
55°	82.7	81.7	81.7	89.0	95.3	102.6	108.9	137.2	165.5	192.7	221.0
57.5°	76.5	75.4	74.4	80.7	86.9	93.2	99.5	127.8	157.1	185.4	213.7
60°	70.2	69.1	69.1	75.4	80.7	86.9	92.2	121.5	149.8	179.1	207.4
62.5°	62.8	63.9	63.9	69.1	75.4	80.7	85.9	115.2	145.6	174.9	204.3
65°	57.6	58.7	58.7	64.9	71.2	77.5	83.8	112.1	141.4	169.7	198.0
67.5°	53.4	54.5	54.5	61.8	68.1	75.4	81.7	106.8	133.0	158.2	183.3
70°	49.2	49.2	50.3	57.6	64.9	72.3	79.6	101.6	123.6	144.5	166.5
72.5°	44.0	45.0	46.1	53.4	59.7	67.0	73.3	93.2	113.1	133.0	152.9
75°	38.8	39.8	40.9	47.1	53.4	59.7	66.0	84.8	102.6	121.5	139.3
77.5°	34.6	35.6	36.7	41.9	47.1	52.4	57.6	71.2	85.9	99.5	113.1
80°	28.3	28.3	29.3	33.5	37.7	40.9	45.0	54.5	63.9	72.3	81.7
82.5°	20.9	22.0	22.0	25.1	27.2	30.4	32.5	37.7	41.9	47.1	51.3
85°	17.8	16.8	16.8	18.9	19.9	22.0	23.0	26.2	28.3	31.4	33.5
87.5°	7.3	6.3	6.3	7.3	9.4	10.5	11.5	11.5	12.6	12.6	12.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2
2.5°	773.0	775.1	778.2	780.3	785.6	789.8	795.0	799.2	802.3	807.6	805.5
5°	744.7	754.2	763.6	773.0	780.3	787.7	794.0	801.3	809.7	825.4	829.6
7.5°	660.9	673.5	685.0	697.6	712.3	726.9	741.6	756.3	769.9	789.8	802.3
10°	578.2	596.0	612.8	630.6	644.2	657.8	670.4	684.0	702.8	722.7	745.8
12.5°	525.8	543.6	561.4	579.2	599.1	618.0	637.9	656.7	674.6	690.3	716.4
15°	491.2	511.2	530.0	548.9	572.9	596.0	620.1	643.1	669.3	690.3	708.1
17.5°	482.9	507.0	530.0	554.1	579.2	604.4	629.5	654.7	680.8	712.3	735.3
20°	468.2	500.7	533.1	565.6	598.1	629.5	662.0	693.4	728.0	765.7	776.2
22.5°	459.8	498.6	538.4	577.1	621.1	666.2	710.2	754.2	790.8	819.1	850.5
25°	458.8	507.0	556.2	604.4	659.9	714.4	769.9	824.3	871.5	899.8	924.9
27.5°	457.7	516.4	574.0	631.6	699.7	766.7	834.8	901.8	945.8	986.7	1007.6
30°	445.2	515.3	586.6	656.7	733.2	809.7	886.1	962.6	1007.6	1035.9	1046.4
32.5°	429.5	512.2	594.9	677.7	764.6	851.6	937.5	1024.4	1060.0	1084.1	1075.7
35°	416.9	508.0	598.1	688.2	780.3	873.6	965.7	1057.9	1109.2	1142.8	1129.1
37.5°	405.4	500.7	596.0	691.3	799.2	907.1	1015.0	1122.9	1172.1	1207.7	1192.0
40°	391.7	493.3	596.0	697.6	821.2	943.7	1067.3	1189.9	1253.8	1284.2	1260.1
42.5°	380.2	486.0	592.9	698.6	830.6	962.6	1094.6	1226.6	1297.8	1340.7	1310.3
45°	365.6	471.3	576.1	681.9	827.5	973.1	1117.6	1263.2	1346.0	1379.5	1337.6
47.5°	349.8	454.6	558.3	662.0	817.0	972.0	1127.0	1282.1	1358.5	1398.3	1359.6
50°	344.6	449.4	553.0	657.8	825.4	994.0	1161.6	1329.2	1384.7	1417.2	1365.9
52.5°	343.6	454.6	566.7	677.7	846.3	1013.9	1182.6	1350.2	1395.2	1429.8	1383.7
55°	340.4	460.9	580.3	699.7	875.7	1052.7	1228.6	1404.6	1449.7	1474.8	1440.2
57.5°	343.6	473.4	602.3	732.2	913.4	1094.6	1275.8	1457.0	1511.5	1529.3	1521.9
60°	345.7	483.9	621.1	759.4	936.4	1113.4	1290.4	1467.5	1524.0	1568.0	1576.4
62.5°	340.4	476.6	611.7	747.9	908.1	1068.4	1228.6	1388.9	1482.1	1547.1	1584.8
65°	324.7	450.4	577.1	702.8	850.5	999.3	1146.9	1294.6	1393.1	1489.5	1519.8
67.5°	290.1	397.0	503.8	610.7	739.5	868.3	996.1	1125.0	1248.5	1341.8	1383.7
70°	251.4	335.2	420.0	503.8	621.1	738.4	855.8	973.1	1082.0	1184.7	1224.5
72.5°	218.9	283.9	349.8	414.8	498.6	581.3	665.1	747.9	876.7	979.4	1018.1
75°	186.4	233.6	279.7	326.8	384.4	442.0	498.6	556.2	647.3	739.5	778.2
77.5°	143.5	174.9	205.3	235.7	275.5	314.2	354.0	392.8	456.7	525.8	545.7
80°	99.5	117.3	134.1	151.9	183.3	214.7	246.1	277.6	319.5	358.2	388.6
82.5°	61.8	73.3	83.8	94.3	119.4	144.5	168.6	193.8	210.5	212.6	243.0
85°	39.8	47.1	53.4	59.7	74.4	90.1	104.7	119.4	106.8	99.5	118.4
87.5°	15.7	19.9	23.0	26.2	25.1	24.1	23.0	22.0	18.9	16.8	20.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2
2.5°	807.6	810.7	813.9	816.0	819.1	820.1	821.2	821.2	822.2	823.3	825.4
5°	846.3	852.6	858.9	864.1	870.4	875.7	879.8	885.1	889.3	889.3	888.2
7.5°	813.9	829.6	845.3	861.0	876.7	888.2	898.7	910.2	920.7	922.8	924.9
10°	770.9	787.7	803.4	820.1	835.9	853.7	870.4	887.2	905.0	908.1	912.3
12.5°	731.1	751.0	770.9	789.8	809.7	822.2	834.8	846.3	858.9	867.3	875.7
15°	730.1	746.8	763.6	779.3	796.1	803.4	810.7	817.0	824.3	824.3	825.4
17.5°	754.2	764.6	775.1	784.5	795.0	796.1	798.1	799.2	800.2	797.1	794.0
20°	801.3	805.5	809.7	813.9	818.1	810.7	804.4	797.1	789.8	781.4	774.1
22.5°	870.4	861.0	851.6	842.1	832.7	820.1	806.5	794.0	780.3	769.9	759.4
25°	935.4	923.8	912.3	900.8	889.3	862.0	834.8	806.5	779.3	767.8	756.3
27.5°	1022.3	1004.5	986.7	968.9	951.1	914.4	877.8	841.1	804.4	784.5	765.7
30°	1043.3	1023.3	1003.4	982.5	962.6	927.0	892.4	856.8	821.2	798.1	776.2
32.5°	1073.6	1050.6	1027.5	1004.5	981.5	946.9	912.3	876.7	842.1	821.2	799.2
35°	1123.9	1097.7	1071.5	1044.3	1018.1	982.5	947.9	912.3	876.7	852.6	829.6
37.5°	1166.8	1136.5	1106.1	1075.7	1045.3	1013.9	981.5	950.0	917.6	893.5	870.4
40°	1215.0	1181.5	1148.0	1115.5	1082.0	1052.7	1023.3	993.0	963.6	944.8	925.9
42.5°	1256.9	1216.1	1176.3	1136.5	1095.6	1075.7	1056.9	1037.0	1017.1	1007.6	997.2
45°	1286.3	1248.5	1209.8	1172.1	1134.4	1119.7	1105.0	1090.4	1075.7	1085.1	1094.6
47.5°	1298.8	1268.5	1239.1	1209.8	1179.4	1184.7	1189.9	1194.1	1199.3	1211.9	1225.5
50°	1310.3	1293.6	1275.8	1259.0	1241.2	1261.1	1280.0	1299.9	1319.8	1346.0	1372.1
52.5°	1333.4	1324.0	1315.6	1306.2	1296.7	1331.3	1365.9	1400.4	1435.0	1464.3	1493.6
55°	1402.5	1395.2	1387.9	1379.5	1372.1	1421.4	1469.6	1518.8	1568.0	1598.4	1628.8
57.5°	1497.8	1493.6	1488.4	1484.2	1479.0	1527.2	1574.3	1621.4	1669.6	1698.9	1729.3
60°	1570.1	1571.2	1571.2	1572.2	1572.2	1608.9	1645.5	1683.2	1719.9	1745.0	1771.2
62.5°	1608.9	1606.8	1604.7	1602.6	1600.5	1630.9	1661.2	1691.6	1722.0	1740.8	1759.7
65°	1567.0	1578.5	1590.0	1601.5	1613.1	1617.2	1620.4	1624.6	1627.7	1639.2	1650.8
67.5°	1426.6	1449.7	1471.7	1494.7	1516.7	1501.0	1486.3	1470.6	1454.9	1458.0	1460.1
70°	1270.5	1296.7	1324.0	1350.2	1376.3	1339.7	1303.0	1265.3	1228.6	1216.1	1203.5
72.5°	1071.5	1094.6	1118.7	1141.7	1164.8	1119.7	1075.7	1030.7	985.6	963.6	941.6
75°	819.1	846.3	874.6	901.8	929.1	878.8	827.5	777.2	725.9	711.2	697.6
77.5°	597.0	629.5	662.0	694.5	726.9	681.9	636.8	590.8	545.7	537.3	529.0
80°	434.7	459.8	483.9	509.1	533.1	507.0	480.8	454.6	428.4	427.4	426.3
82.5°	293.3	315.3	336.2	358.2	379.2	368.7	359.3	348.8	338.3	348.8	360.3
85°	150.8	181.2	212.6	243.0	273.4	270.2	268.1	265.0	261.9	275.5	288.0
87.5°	30.4	56.6	82.7	107.9	134.1	127.8	121.5	114.2	107.9	112.1	115.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2
2.5°	826.4	827.5	827.5	827.5	827.5	827.5	825.4	824.3	822.2	820.1	817.0
5°	888.2	887.2	883.0	878.8	873.6	869.4	866.2	862.0	858.9	854.7	848.4
7.5°	927.0	929.1	921.7	915.5	908.1	900.8	893.5	886.1	878.8	871.5	856.8
10°	915.5	918.6	914.4	910.2	905.0	900.8	892.4	883.0	874.6	865.2	847.4
12.5°	883.0	891.4	889.3	887.2	885.1	883.0	877.8	871.5	866.2	859.9	840.0
15°	825.4	825.4	826.4	827.5	827.5	828.5	829.6	830.6	831.7	832.7	821.2
17.5°	790.8	787.7	787.7	787.7	787.7	787.7	791.9	797.1	801.3	805.5	802.3
20°	765.7	758.3	757.3	757.3	756.3	755.2	762.5	770.9	778.2	785.6	789.8
22.5°	748.9	738.4	737.4	736.4	735.3	734.3	743.7	753.1	762.5	772.0	786.6
25°	744.7	733.2	734.3	735.3	735.3	736.4	743.7	751.0	758.3	765.7	790.8
27.5°	745.8	726.9	728.0	729.0	729.0	730.1	741.6	752.1	763.6	774.1	805.5
30°	753.1	731.1	729.0	726.9	724.8	722.7	738.4	754.2	769.9	785.6	809.7
32.5°	778.2	757.3	752.1	746.8	741.6	736.4	755.2	773.0	791.9	809.7	829.6
35°	805.5	782.4	780.3	778.2	775.1	773.0	789.8	807.6	824.3	841.1	858.9
37.5°	846.3	823.3	821.2	818.1	816.0	812.8	831.7	849.5	868.3	886.1	901.8
40°	907.1	888.2	887.2	887.2	886.1	885.1	899.8	915.5	930.1	944.8	955.3
42.5°	987.7	978.3	981.5	985.6	988.8	991.9	1003.4	1016.0	1027.5	1039.1	1035.9
45°	1104.0	1113.4	1114.5	1115.5	1116.6	1117.6	1120.8	1125.0	1128.1	1131.2	1118.7
47.5°	1238.1	1250.6	1256.9	1263.2	1268.5	1274.7	1270.5	1265.3	1261.1	1255.9	1224.5
50°	1397.3	1423.5	1422.4	1421.4	1419.3	1418.2	1409.9	1401.5	1392.0	1383.7	1337.6
52.5°	1523.0	1552.3	1557.5	1562.8	1568.0	1573.3	1557.5	1541.8	1525.1	1509.4	1451.8
55°	1658.1	1688.5	1689.5	1690.6	1690.6	1691.6	1669.6	1647.6	1624.6	1602.6	1542.9
57.5°	1758.7	1788.0	1784.8	1782.7	1779.6	1776.5	1750.3	1724.1	1697.9	1671.7	1612.0
60°	1796.4	1821.5	1815.2	1808.9	1801.6	1795.3	1775.4	1755.5	1734.6	1714.7	1657.1
62.5°	1778.6	1797.4	1788.0	1779.6	1770.2	1760.7	1735.6	1709.4	1684.3	1658.1	1616.2
65°	1661.2	1672.8	1660.2	1648.7	1637.1	1624.6	1603.6	1582.7	1560.7	1539.7	1511.5
67.5°	1463.3	1465.4	1464.3	1463.3	1462.2	1461.2	1430.8	1400.4	1369.0	1338.6	1336.5
70°	1192.0	1179.4	1181.5	1184.7	1186.7	1188.8	1165.8	1143.8	1120.8	1097.7	1108.2
72.5°	919.7	897.7	902.9	909.2	914.4	919.7	900.8	883.0	864.1	845.3	859.9
75°	682.9	669.3	674.6	680.8	686.1	691.3	684.0	676.6	668.3	660.9	674.6
77.5°	520.6	512.2	513.2	513.2	514.3	514.3	515.3	517.4	518.5	519.5	534.2
80°	424.2	423.2	422.1	421.1	419.0	417.9	428.4	438.9	449.4	459.8	467.2
82.5°	370.8	381.3	375.0	369.7	363.5	357.2	366.6	376.0	385.5	394.9	391.7
85°	301.7	314.2	302.7	291.2	278.6	267.1	275.5	282.8	291.2	298.5	294.3
87.5°	119.4	122.6	103.7	85.9	67.0	48.2	76.5	103.7	132.0	159.2	163.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2	754.2
2.5°	813.9	809.7	806.5	805.5	803.4	802.3	800.2	798.1	795.0	792.9	789.8
5°	841.1	834.8	827.5	817.0	807.6	797.1	786.6	777.2	767.8	757.3	747.9
7.5°	842.1	827.5	812.8	799.2	784.5	770.9	756.3	743.7	730.1	716.4	703.9
10°	830.6	812.8	795.0	777.2	760.4	742.6	724.8	710.2	694.5	678.7	664.1
12.5°	821.2	801.3	781.4	760.4	740.5	719.6	698.6	684.0	669.3	654.7	640.0
15°	809.7	797.1	785.6	766.7	747.9	729.0	710.2	690.3	671.4	651.5	631.6
17.5°	800.2	797.1	794.0	781.4	768.8	755.2	742.6	722.7	702.8	681.9	662.0
20°	795.0	799.2	803.4	797.1	790.8	783.5	777.2	762.5	747.9	732.2	717.5
22.5°	801.3	817.0	831.7	832.7	834.8	835.9	836.9	823.3	809.7	795.0	781.4
25°	816.0	841.1	866.2	879.8	893.5	908.1	921.7	913.4	905.0	896.6	888.2
27.5°	835.9	867.3	898.7	918.6	937.5	957.4	977.3	976.2	975.2	973.1	972.0
30°	832.7	856.8	880.9	905.0	929.1	953.2	977.3	989.8	1001.4	1013.9	1026.5
32.5°	850.5	870.4	891.4	916.5	941.6	967.8	993.0	1019.2	1044.3	1070.5	1096.7
35°	877.8	895.6	914.4	941.6	969.9	997.2	1025.4	1056.9	1089.3	1121.8	1153.2
37.5°	918.6	934.3	951.1	974.1	998.2	1021.3	1045.3	1091.4	1137.5	1184.7	1230.7
40°	965.7	976.2	986.7	1008.7	1030.7	1052.7	1074.7	1132.3	1189.9	1247.5	1305.1
42.5°	1033.8	1030.7	1027.5	1045.3	1064.2	1082.0	1100.9	1153.2	1205.6	1258.0	1310.3
45°	1106.1	1093.5	1081.0	1089.3	1098.8	1107.1	1116.6	1170.0	1223.4	1277.9	1331.3
47.5°	1193.0	1161.6	1130.2	1122.9	1115.5	1107.1	1099.8	1157.4	1215.0	1273.7	1331.3
50°	1291.5	1244.4	1198.3	1179.4	1159.5	1140.7	1120.8	1167.9	1216.1	1264.3	1311.4
52.5°	1394.1	1335.5	1277.9	1248.5	1219.2	1188.8	1159.5	1199.3	1240.2	1281.0	1320.8
55°	1482.1	1422.4	1361.7	1327.1	1292.5	1258.0	1223.4	1263.2	1303.0	1342.8	1382.6
57.5°	1552.3	1492.6	1432.9	1400.4	1366.9	1334.4	1300.9	1338.6	1377.4	1416.1	1453.8
60°	1600.5	1542.9	1485.3	1453.8	1422.4	1391.0	1359.6	1404.6	1449.7	1495.7	1540.8
62.5°	1575.4	1533.5	1491.6	1477.9	1464.3	1449.7	1436.0	1479.0	1520.9	1563.8	1606.8
65°	1483.2	1454.9	1426.6	1440.2	1454.9	1468.5	1483.2	1511.5	1539.7	1569.1	1597.3
67.5°	1333.4	1331.3	1328.2	1358.5	1388.9	1420.3	1450.7	1469.6	1487.4	1506.2	1525.1
70°	1118.7	1130.2	1140.7	1193.0	1245.4	1297.8	1350.2	1357.5	1364.8	1372.1	1379.5
72.5°	875.7	890.3	906.0	975.2	1043.3	1112.4	1181.5	1177.3	1173.1	1167.9	1163.7
75°	689.2	702.8	717.5	781.4	845.3	909.2	973.1	955.3	938.5	920.7	902.9
77.5°	549.9	564.6	580.3	640.0	699.7	760.4	820.1	777.2	734.3	691.3	648.4
80°	473.4	480.8	487.1	527.9	567.7	608.6	649.4	605.4	560.4	515.3	471.3
82.5°	388.6	384.4	381.3	405.4	429.5	453.5	477.6	435.7	393.8	350.9	309.0
85°	290.1	286.0	281.8	294.3	306.9	320.5	333.1	284.9	236.7	187.5	139.3
87.5°	168.6	172.8	177.0	190.6	204.3	218.9	232.5	183.3	134.1	83.8	34.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671878

CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671878
 CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	754.2	754.2
2.5°	783.5	778.2
5°	740.5	733.2
7.5°	693.4	684.0
10°	650.5	637.9
12.5°	623.2	607.5
15°	612.8	593.9
17.5°	644.2	626.4
20°	692.4	668.3
22.5°	751.0	721.7
25°	852.6	817.0
27.5°	935.4	898.7
30°	986.7	946.9
32.5°	1043.3	990.9
35°	1101.9	1051.6
37.5°	1173.1	1116.6
40°	1246.5	1187.8
42.5°	1271.6	1233.9
45°	1295.7	1260.1
47.5°	1300.9	1271.6
50°	1306.2	1302.0
52.5°	1320.8	1319.8
55°	1383.7	1384.7
57.5°	1461.2	1467.5
60°	1532.4	1525.1
62.5°	1569.1	1531.4
65°	1543.9	1491.6
67.5°	1468.5	1411.9
70°	1303.0	1226.6
72.5°	1096.7	1029.6
75°	845.3	788.7
77.5°	601.2	554.1
80°	423.2	376.0
82.5°	271.3	233.6
85°	122.6	106.8
87.5°	34.6	33.5
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671878
CATALOG NUMBER: CCP-SA-1B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)