

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671879

Luminaire Tested: **CCP-SA-1C-835-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671879
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1C-835-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @615mA w/ SLR
distribution lens
Light Source: (16) 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3091.7 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 32
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 4.4 fc
 Type IV - Short - N/A

REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	636.1	0.0	636.1
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	2455.6	0.0	2455.6
	% Fixture	79.4	0.0	79.4
Total	Lumens	3091.7	0.0	3091.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.7	2.5
10°-20°	162.0	5.2
20°-30°	237.0	7.7
30°-40°	333.9	10.8
40°-50°	458.8	14.8
50°-60°	625.3	20.2
60°-70°	684.4	22.1
70°-80°	395.2	12.8
80°-90°	118.5	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3091.7	100.0
0°-180°	3091.7	100.0

Coefficient of Utilization



REPORT NUMBER: P671879


CATALOG NUMBER: CCP-SA-1C-835-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	317.5	10.3			
FM	(30°-60°)	1128.3	36.5			
FH	(60°-80°)	909.1	29.4			G1/1800
FVH	(80°-90°)	100.6	3.3			G2/225
BL	(0°-30°)	158.1	5.1	B1/500		
BM	(30°-60°)	289.7	9.4	B1/1000		
BH	(60°-80°)	170.5	5.5	B1/500		G1/500
BVH	(80°-90°)	17.8	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3
2.5°	1018.8	1013.4	1009.2	1005.1	999.6	995.5	990.0	984.6	977.7	972.2	965.4
5°	959.9	943.4	927.0	917.4	906.4	896.8	885.8	873.5	861.1	847.4	835.1
7.5°	895.4	874.9	854.3	837.8	820.0	803.6	785.7	770.6	755.6	740.5	725.4
10°	835.1	815.9	796.7	776.1	754.2	733.6	711.7	691.1	670.5	650.0	629.4
12.5°	795.3	772.0	750.1	726.8	704.8	681.5	658.2	639.0	619.8	599.2	580.0
15°	777.5	755.6	735.0	711.7	688.4	665.1	641.7	619.8	599.2	577.3	555.4
17.5°	820.0	788.5	756.9	726.8	696.6	666.4	636.3	608.8	581.4	554.0	526.6
20°	874.9	835.1	796.7	759.7	721.3	684.3	645.9	607.5	569.1	530.7	492.3
22.5°	944.8	899.5	855.7	807.7	758.3	710.3	660.9	612.9	565.0	515.6	467.6
25°	1069.6	1016.1	962.6	894.1	824.1	755.6	685.6	622.5	560.8	497.8	434.7
27.5°	1176.5	1103.9	1032.6	950.3	868.0	785.7	703.5	630.8	559.5	486.8	414.1
30°	1239.6	1168.3	1097.0	996.9	898.2	798.1	698.0	617.1	537.5	456.6	375.7
32.5°	1297.2	1217.7	1138.1	1028.4	917.4	807.7	696.6	607.5	519.7	430.6	341.4
35°	1376.7	1289.0	1202.6	1075.1	947.5	820.0	692.5	600.6	507.4	415.5	322.2
37.5°	1461.8	1353.4	1246.5	1105.2	964.0	822.7	681.5	591.0	500.5	410.0	319.5
40°	1555.0	1423.4	1293.1	1136.8	981.8	825.5	669.2	578.7	488.2	396.3	305.8
42.5°	1615.3	1472.7	1330.1	1161.4	994.2	825.5	656.8	567.7	478.6	388.1	298.9
45°	1649.6	1511.1	1374.0	1191.6	1009.2	826.9	644.5	556.7	469.0	379.8	292.1
47.5°	1664.7	1535.8	1406.9	1214.9	1024.3	832.3	640.4	551.2	460.7	371.6	281.1
50°	1704.5	1590.6	1476.8	1271.1	1066.8	861.1	655.5	559.5	464.9	368.9	272.9
52.5°	1727.8	1630.4	1533.1	1321.9	1110.7	899.5	688.4	581.4	474.5	367.5	260.5
55°	1812.8	1719.5	1626.3	1401.4	1175.2	950.3	724.0	606.1	488.2	368.9	250.9
57.5°	1921.1	1822.4	1725.0	1482.3	1239.6	996.9	754.2	628.0	500.5	374.4	246.8
60°	1996.5	1900.6	1805.9	1548.1	1289.0	1031.2	772.0	640.4	508.7	375.7	244.1
62.5°	2004.8	1881.4	1759.3	1508.4	1257.4	1005.1	754.2	626.7	499.1	370.2	242.7
65°	1952.7	1808.7	1664.7	1424.7	1184.8	944.8	704.8	588.3	471.7	353.8	237.2
67.5°	1848.4	1679.8	1511.1	1291.7	1072.3	852.9	633.5	533.4	434.7	334.6	234.5
70°	1605.7	1457.6	1310.9	1120.3	931.1	740.5	549.9	467.6	386.7	304.4	222.1
72.5°	1347.9	1209.4	1072.3	917.4	763.8	608.8	453.9	392.2	330.5	267.4	205.7
75°	1032.6	928.3	825.5	710.3	595.1	478.6	363.4	318.1	272.9	227.6	182.4
77.5°	725.4	669.2	614.3	527.9	441.5	355.2	268.8	238.6	208.4	178.3	148.1
80°	492.3	460.7	430.6	368.9	307.2	244.1	182.4	163.2	142.6	123.4	102.8
82.5°	305.8	304.4	301.7	259.2	216.7	174.1	131.6	115.2	100.1	83.6	67.2
85°	139.9	163.2	185.1	161.8	138.5	115.2	91.9	80.9	69.9	57.6	46.6
87.5°	43.9	53.5	61.7	59.0	54.8	52.1	48.0	41.1	34.3	27.4	20.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3
2.5°	959.9	955.8	950.3	944.8	937.9	932.4	925.6	918.7	917.4	914.6	913.3
5°	826.9	818.6	809.0	800.8	792.6	783.0	774.8	765.2	758.3	750.1	743.2
7.5°	710.3	696.6	681.5	666.4	652.7	639.0	623.9	610.2	603.3	596.5	589.6
10°	617.1	603.3	591.0	577.3	567.7	559.5	549.9	540.3	532.0	523.8	515.6
12.5°	570.4	560.8	551.2	541.6	530.7	521.1	510.1	499.1	489.5	481.3	471.7
15°	541.6	527.9	512.8	499.1	484.1	470.3	455.3	440.2	429.2	419.6	408.6
17.5°	507.4	486.8	467.6	447.0	430.6	414.1	396.3	379.8	367.5	353.8	341.4
20°	469.0	445.7	421.0	397.7	378.5	360.6	341.4	322.2	308.5	293.4	279.7
22.5°	436.1	405.9	374.4	342.8	322.2	301.7	279.7	259.2	246.8	233.1	220.8
25°	400.4	367.5	333.2	298.9	278.4	256.4	235.9	213.9	204.3	196.1	186.5
27.5°	381.2	348.3	314.0	281.1	261.9	241.3	222.1	201.6	194.7	186.5	179.6
30°	342.8	311.3	278.4	245.5	231.7	219.4	205.7	192.0	189.2	187.9	185.1
32.5°	308.5	275.6	242.7	209.8	197.5	185.1	172.8	160.4	159.1	156.3	155.0
35°	290.7	259.2	226.3	194.7	183.7	171.4	160.4	148.1	145.4	141.2	138.5
37.5°	286.6	253.7	219.4	186.5	175.5	164.5	152.2	141.2	138.5	135.8	133.0
40°	275.6	244.1	213.9	182.4	171.4	160.4	148.1	137.1	134.4	131.6	128.9
42.5°	267.4	237.2	205.7	174.1	164.5	155.0	144.0	134.4	131.6	128.9	124.8
45°	260.5	229.0	196.1	164.5	157.7	150.8	142.6	135.8	133.0	128.9	126.2
47.5°	249.6	219.4	187.9	156.3	149.5	144.0	137.1	130.3	127.5	124.8	122.0
50°	241.3	209.8	178.3	146.7	141.2	135.8	130.3	124.8	124.8	126.2	126.2
52.5°	230.4	200.2	170.0	139.9	134.4	128.9	123.4	117.9	119.3	120.7	122.0
55°	220.8	192.0	161.8	131.6	126.2	120.7	113.8	108.3	109.7	111.1	112.4
57.5°	216.7	186.5	156.3	126.2	120.7	113.8	108.3	101.5	101.5	101.5	101.5
60°	213.9	182.4	152.2	120.7	113.8	108.3	101.5	94.6	93.2	93.2	91.9
62.5°	212.5	181.0	150.8	119.3	111.1	104.2	96.0	87.8	86.4	85.0	83.6
65°	207.1	178.3	148.1	117.9	108.3	100.1	90.5	80.9	79.5	79.5	78.2
67.5°	205.7	175.5	146.7	116.6	107.0	96.0	86.4	75.4	74.0	72.7	71.3
70°	194.7	168.7	141.2	113.8	102.8	93.2	82.3	71.3	69.9	67.2	65.8
72.5°	181.0	157.7	133.0	108.3	97.4	86.4	75.4	64.4	63.1	61.7	59.0
75°	160.4	138.5	116.6	94.6	85.0	76.8	67.2	57.6	56.2	54.8	52.1
77.5°	131.6	113.8	97.4	79.5	72.7	65.8	59.0	52.1	50.7	49.4	46.6
80°	93.2	82.3	72.7	61.7	57.6	52.1	48.0	42.5	42.5	41.1	41.1
82.5°	61.7	56.2	50.7	45.3	42.5	39.8	37.0	34.3	34.3	32.9	32.9
85°	43.9	41.1	37.0	34.3	32.9	30.2	28.8	26.1	26.1	26.1	26.1
87.5°	20.6	20.6	19.2	19.2	17.8	17.8	16.5	15.1	15.1	15.1	15.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3
2.5°	910.5	906.4	902.3	896.8	892.7	887.2	880.3	874.9	868.0	868.0	866.6
5°	735.0	730.9	726.8	721.3	717.2	711.7	707.6	702.1	696.6	696.6	695.2
7.5°	582.8	574.6	566.3	556.7	548.5	543.0	537.5	530.7	525.2	521.1	517.0
10°	507.4	499.1	489.5	481.3	471.7	464.9	458.0	449.8	442.9	437.4	431.9
12.5°	462.1	452.5	442.9	433.3	423.7	414.1	405.9	396.3	386.7	379.8	373.0
15°	397.7	388.1	378.5	368.9	359.3	348.3	337.3	325.0	314.0	308.5	304.4
17.5°	327.7	318.1	307.2	297.6	286.6	278.4	270.1	261.9	253.7	248.2	244.1
20°	264.7	253.7	242.7	231.7	220.8	215.3	209.8	204.3	198.8	194.7	192.0
22.5°	207.1	200.2	194.7	187.9	181.0	176.9	174.1	170.0	165.9	165.9	165.9
25°	176.9	172.8	170.0	165.9	161.8	160.4	159.1	156.3	155.0	153.6	153.6
27.5°	171.4	167.3	163.2	159.1	155.0	153.6	152.2	149.5	148.1	148.1	148.1
30°	182.4	181.0	179.6	178.3	176.9	174.1	170.0	167.3	163.2	160.4	157.7
32.5°	152.2	150.8	150.8	149.5	148.1	150.8	152.2	155.0	156.3	157.7	159.1
35°	134.4	131.6	128.9	126.2	123.4	122.0	120.7	119.3	117.9	117.9	116.6
37.5°	130.3	127.5	124.8	122.0	119.3	117.9	116.6	115.2	113.8	113.8	112.4
40°	126.2	123.4	122.0	119.3	116.6	115.2	113.8	111.1	109.7	108.3	108.3
42.5°	122.0	120.7	117.9	116.6	113.8	112.4	111.1	108.3	107.0	105.6	104.2
45°	122.0	119.3	116.6	113.8	111.1	109.7	107.0	105.6	102.8	102.8	101.5
47.5°	119.3	116.6	113.8	111.1	108.3	107.0	104.2	102.8	100.1	98.7	97.4
50°	126.2	122.0	116.6	112.4	107.0	105.6	102.8	101.5	98.7	97.4	96.0
52.5°	123.4	119.3	113.8	109.7	104.2	101.5	100.1	97.4	94.6	93.2	91.9
55°	113.8	109.7	107.0	102.8	98.7	96.0	93.2	90.5	87.8	86.4	86.4
57.5°	101.5	100.1	98.7	97.4	96.0	93.2	90.5	86.4	83.6	82.3	80.9
60°	90.5	91.9	93.2	94.6	96.0	91.9	87.8	83.6	79.5	78.2	76.8
62.5°	82.3	85.0	87.8	89.1	91.9	87.8	83.6	79.5	75.4	74.0	72.7
65°	76.8	78.2	78.2	79.5	79.5	76.8	75.4	72.7	69.9	68.6	68.6
67.5°	69.9	69.9	69.9	68.6	68.6	67.2	67.2	65.8	64.4	63.1	63.1
70°	63.1	63.1	63.1	61.7	61.7	60.3	60.3	59.0	57.6	57.6	56.2
72.5°	57.6	57.6	56.2	56.2	54.8	54.8	54.8	53.5	53.5	52.1	52.1
75°	50.7	50.7	49.4	49.4	48.0	48.0	48.0	46.6	46.6	46.6	45.3
77.5°	45.3	45.3	43.9	43.9	42.5	42.5	42.5	41.1	41.1	39.8	39.8
80°	39.8	39.8	38.4	38.4	37.0	37.0	35.7	35.7	34.3	34.3	32.9
82.5°	31.5	31.5	31.5	31.5	31.5	30.2	30.2	28.8	27.4	27.4	26.1
85°	26.1	26.1	26.1	24.7	24.7	24.7	23.3	23.3	21.9	20.6	20.6
87.5°	15.1	15.1	15.1	13.7	13.7	13.7	13.7	13.7	13.7	13.7	12.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3
2.5°	866.6	865.3	859.8	854.3	859.8	865.3	865.3	865.3	863.9	863.9	863.9
5°	695.2	693.9	691.1	688.4	688.4	687.0	689.7	692.5	695.2	698.0	700.7
7.5°	511.5	507.4	503.2	499.1	501.9	503.2	507.4	510.1	514.2	517.0	523.8
10°	426.5	421.0	416.9	412.7	410.0	407.3	404.5	403.1	400.4	397.7	400.4
12.5°	364.8	357.9	351.0	342.8	341.4	340.1	337.3	334.6	331.8	329.1	327.7
15°	298.9	293.4	290.7	286.6	281.1	275.6	272.9	271.5	268.8	266.0	264.7
17.5°	238.6	233.1	229.0	224.9	223.5	220.8	220.8	220.8	220.8	220.8	220.8
20°	187.9	183.7	183.7	182.4	182.4	181.0	182.4	183.7	183.7	185.1	186.5
22.5°	164.5	164.5	163.2	161.8	163.2	163.2	164.5	165.9	167.3	168.7	170.0
25°	152.2	150.8	152.2	153.6	153.6	153.6	155.0	155.0	156.3	156.3	156.3
27.5°	146.7	146.7	148.1	148.1	149.5	149.5	149.5	148.1	148.1	146.7	146.7
30°	155.0	152.2	152.2	152.2	150.8	149.5	148.1	148.1	146.7	145.4	144.0
32.5°	160.4	161.8	160.4	157.7	156.3	153.6	152.2	149.5	148.1	145.4	142.6
35°	116.6	115.2	117.9	119.3	120.7	122.0	123.4	124.8	124.8	126.2	126.2
37.5°	112.4	111.1	111.1	109.7	109.7	109.7	109.7	109.7	108.3	108.3	109.7
40°	107.0	105.6	105.6	104.2	104.2	102.8	102.8	102.8	102.8	102.8	102.8
42.5°	102.8	101.5	101.5	101.5	101.5	100.1	100.1	98.7	98.7	97.4	97.4
45°	101.5	100.1	98.7	97.4	97.4	96.0	96.0	96.0	94.6	94.6	94.6
47.5°	96.0	94.6	94.6	93.2	93.2	91.9	91.9	91.9	90.5	90.5	90.5
50°	93.2	91.9	91.9	90.5	90.5	89.1	89.1	89.1	87.8	87.8	87.8
52.5°	89.1	87.8	87.8	87.8	86.4	85.0	85.0	85.0	83.6	83.6	83.6
55°	85.0	83.6	83.6	83.6	82.3	80.9	80.9	80.9	79.5	79.5	79.5
57.5°	79.5	78.2	78.2	76.8	76.8	76.8	76.8	76.8	75.4	75.4	75.4
60°	75.4	74.0	74.0	72.7	72.7	71.3	71.3	71.3	71.3	71.3	71.3
62.5°	71.3	69.9	68.6	67.2	68.6	68.6	68.6	68.6	67.2	67.2	67.2
65°	67.2	65.8	64.4	63.1	63.1	63.1	63.1	63.1	63.1	63.1	63.1
67.5°	61.7	60.3	59.0	57.6	59.0	59.0	59.0	59.0	59.0	59.0	59.0
70°	56.2	54.8	54.8	53.5	53.5	52.1	52.1	53.5	53.5	53.5	53.5
72.5°	50.7	49.4	49.4	48.0	48.0	48.0	48.0	48.0	48.0	48.0	48.0
75°	45.3	43.9	43.9	42.5	42.5	42.5	42.5	42.5	42.5	42.5	42.5
77.5°	38.4	37.0	37.0	37.0	37.0	37.0	37.0	38.4	38.4	38.4	38.4
80°	32.9	31.5	31.5	31.5	31.5	31.5	31.5	31.5	31.5	31.5	31.5
82.5°	26.1	24.7	24.7	24.7	24.7	24.7	24.7	24.7	24.7	24.7	24.7
85°	19.2	17.8	17.8	17.8	19.2	19.2	19.2	19.2	19.2	19.2	19.2
87.5°	12.3	11.0	11.0	11.0	12.3	12.3	12.3	12.3	11.0	11.0	11.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3
2.5°	863.9	863.9	863.9	862.5	861.1	859.8	858.4	862.5	865.3	869.4	872.1
5°	702.1	704.8	706.2	710.3	714.4	718.5	722.6	725.4	728.1	729.5	732.2
7.5°	529.3	536.2	541.6	547.1	552.6	556.7	562.2	566.3	570.4	574.6	578.7
10°	401.8	404.5	405.9	411.4	415.5	421.0	425.1	429.2	433.3	436.1	440.2
12.5°	326.4	323.6	322.2	322.2	322.2	322.2	322.2	325.0	327.7	330.5	333.2
15°	263.3	261.9	260.5	259.2	257.8	255.1	253.7	256.4	259.2	261.9	264.7
17.5°	220.8	220.8	220.8	219.4	218.0	216.7	215.3	216.7	218.0	218.0	219.4
20°	189.2	190.6	192.0	193.3	193.3	194.7	194.7	196.1	197.5	197.5	198.8
22.5°	170.0	171.4	171.4	171.4	172.8	172.8	172.8	174.1	175.5	176.9	178.3
25°	155.0	155.0	153.6	153.6	155.0	155.0	155.0	155.0	156.3	156.3	156.3
27.5°	146.7	145.4	145.4	145.4	145.4	144.0	144.0	144.0	144.0	144.0	144.0
30°	142.6	141.2	139.9	138.5	138.5	137.1	135.8	135.8	135.8	135.8	135.8
32.5°	141.2	138.5	135.8	134.4	134.4	133.0	131.6	130.3	130.3	128.9	127.5
35°	126.2	124.8	124.8	123.4	122.0	120.7	119.3	119.3	119.3	117.9	117.9
37.5°	109.7	111.1	111.1	111.1	112.4	112.4	112.4	112.4	113.8	113.8	113.8
40°	102.8	102.8	102.8	104.2	105.6	105.6	107.0	107.0	108.3	108.3	108.3
42.5°	97.4	96.0	96.0	97.4	97.4	98.7	98.7	100.1	101.5	101.5	102.8
45°	94.6	93.2	93.2	93.2	93.2	91.9	91.9	93.2	94.6	96.0	97.4
47.5°	89.1	89.1	87.8	87.8	87.8	87.8	87.8	87.8	89.1	89.1	89.1
50°	86.4	86.4	85.0	85.0	85.0	85.0	85.0	85.0	85.0	85.0	85.0
52.5°	83.6	82.3	82.3	82.3	82.3	80.9	80.9	80.9	80.9	80.9	80.9
55°	79.5	78.2	78.2	78.2	78.2	78.2	78.2	78.2	79.5	79.5	79.5
57.5°	75.4	74.0	74.0	74.0	75.4	75.4	75.4	75.4	76.8	76.8	76.8
60°	71.3	71.3	71.3	71.3	71.3	71.3	71.3	72.7	72.7	74.0	74.0
62.5°	67.2	67.2	67.2	67.2	68.6	68.6	68.6	68.6	69.9	69.9	69.9
65°	63.1	63.1	63.1	63.1	64.4	64.4	64.4	64.4	64.4	64.4	64.4
67.5°	59.0	59.0	59.0	59.0	59.0	59.0	59.0	60.3	60.3	61.7	61.7
70°	53.5	52.1	52.1	53.5	53.5	54.8	54.8	56.2	56.2	57.6	57.6
72.5°	48.0	48.0	48.0	48.0	48.0	48.0	48.0	49.4	50.7	50.7	52.1
75°	42.5	42.5	42.5	42.5	43.9	43.9	43.9	45.3	45.3	46.6	46.6
77.5°	38.4	37.0	37.0	37.0	38.4	38.4	38.4	39.8	39.8	41.1	41.1
80°	31.5	31.5	31.5	31.5	32.9	32.9	32.9	32.9	34.3	34.3	34.3
82.5°	26.1	26.1	26.1	26.1	26.1	26.1	26.1	26.1	27.4	27.4	27.4
85°	19.2	19.2	19.2	19.2	20.6	20.6	20.6	20.6	20.6	20.6	20.6
87.5°	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	13.7	13.7	13.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3
2.5°	872.1	872.1	872.1	872.1	874.9	876.2	879.0	880.3	879.0	877.6	874.9
5°	733.6	735.0	735.0	736.4	736.4	736.4	736.4	736.4	739.1	741.8	744.6
7.5°	580.0	581.4	582.8	584.2	584.2	584.2	582.8	582.8	584.2	584.2	585.5
10°	444.3	449.8	453.9	458.0	455.3	451.1	448.4	444.3	444.3	444.3	442.9
12.5°	336.0	337.3	340.1	341.4	340.1	340.1	338.7	337.3	338.7	341.4	342.8
15°	266.0	266.0	267.4	267.4	268.8	270.1	270.1	271.5	274.2	275.6	278.4
17.5°	220.8	222.1	222.1	223.5	223.5	224.9	224.9	224.9	227.6	230.4	234.5
20°	198.8	198.8	198.8	198.8	198.8	197.5	197.5	196.1	197.5	200.2	201.6
22.5°	178.3	179.6	179.6	179.6	178.3	176.9	174.1	172.8	172.8	174.1	174.1
25°	156.3	155.0	155.0	153.6	153.6	155.0	155.0	155.0	156.3	156.3	157.7
27.5°	144.0	142.6	142.6	141.2	141.2	142.6	142.6	142.6	142.6	142.6	142.6
30°	134.4	134.4	133.0	131.6	133.0	133.0	134.4	134.4	135.8	135.8	137.1
32.5°	127.5	126.2	126.2	124.8	126.2	126.2	127.5	127.5	128.9	130.3	130.3
35°	117.9	117.9	117.9	117.9	117.9	117.9	116.6	116.6	116.6	116.6	116.6
37.5°	112.4	112.4	111.1	109.7	109.7	109.7	109.7	109.7	108.3	107.0	105.6
40°	108.3	107.0	107.0	105.6	104.2	104.2	102.8	101.5	101.5	100.1	100.1
42.5°	102.8	101.5	101.5	100.1	98.7	98.7	97.4	96.0	96.0	96.0	94.6
45°	96.0	96.0	94.6	93.2	93.2	93.2	91.9	91.9	91.9	91.9	90.5
47.5°	89.1	89.1	87.8	87.8	87.8	87.8	86.4	86.4	86.4	86.4	86.4
50°	85.0	85.0	85.0	85.0	85.0	85.0	83.6	83.6	83.6	83.6	83.6
52.5°	80.9	80.9	80.9	80.9	80.9	80.9	80.9	80.9	80.9	80.9	80.9
55°	79.5	79.5	79.5	79.5	79.5	79.5	78.2	78.2	78.2	79.5	79.5
57.5°	76.8	76.8	75.4	75.4	75.4	75.4	75.4	75.4	75.4	75.4	75.4
60°	74.0	74.0	74.0	74.0	74.0	74.0	74.0	74.0	74.0	74.0	74.0
62.5°	69.9	69.9	69.9	69.9	69.9	71.3	71.3	71.3	71.3	71.3	69.9
65°	64.4	65.8	65.8	65.8	65.8	65.8	65.8	65.8	65.8	65.8	65.8
67.5°	61.7	61.7	61.7	61.7	61.7	61.7	61.7	61.7	61.7	61.7	61.7
70°	57.6	57.6	56.2	56.2	56.2	57.6	57.6	57.6	57.6	57.6	57.6
72.5°	52.1	52.1	52.1	52.1	52.1	52.1	52.1	52.1	52.1	53.5	53.5
75°	46.6	46.6	46.6	46.6	46.6	46.6	46.6	46.6	46.6	46.6	46.6
77.5°	41.1	41.1	39.8	39.8	39.8	41.1	41.1	41.1	41.1	42.5	42.5
80°	34.3	34.3	34.3	34.3	34.3	34.3	34.3	34.3	34.3	35.7	35.7
82.5°	27.4	27.4	27.4	27.4	27.4	27.4	27.4	27.4	27.4	28.8	28.8
85°	20.6	21.9	21.9	21.9	21.9	21.9	21.9	21.9	21.9	23.3	23.3
87.5°	13.7	13.7	13.7	13.7	13.7	13.7	12.3	12.3	12.3	12.3	11.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3
2.5°	873.5	874.9	876.2	876.2	877.6	879.0	879.0	884.5	889.9	892.7	895.4
5°	747.3	746.0	746.0	744.6	743.2	747.3	751.4	759.7	767.9	769.3	772.0
7.5°	585.5	586.9	588.3	588.3	589.6	585.5	580.0	581.4	582.8	589.6	595.1
10°	442.9	444.3	445.7	445.7	447.0	445.7	442.9	447.0	451.1	456.6	463.5
12.5°	344.2	348.3	352.4	355.2	359.3	362.0	363.4	368.9	373.0	379.8	386.7
15°	281.1	283.8	286.6	289.3	292.1	294.8	297.6	303.0	308.5	316.8	325.0
17.5°	237.2	237.2	238.6	238.6	238.6	241.3	244.1	246.8	248.2	256.4	264.7
20°	202.9	201.6	200.2	198.8	197.5	200.2	201.6	202.9	204.3	209.8	213.9
22.5°	174.1	174.1	175.5	175.5	175.5	174.1	171.4	172.8	172.8	175.5	179.6
25°	157.7	157.7	157.7	156.3	156.3	157.7	159.1	159.1	157.7	159.1	160.4
27.5°	142.6	144.0	144.0	145.4	145.4	146.7	146.7	146.7	146.7	148.1	149.5
30°	137.1	137.1	138.5	138.5	138.5	139.9	141.2	141.2	141.2	142.6	145.4
32.5°	131.6	133.0	134.4	135.8	137.1	138.5	138.5	139.9	139.9	141.2	142.6
35°	116.6	115.2	115.2	113.8	112.4	112.4	112.4	112.4	111.1	112.4	112.4
37.5°	104.2	104.2	104.2	102.8	102.8	104.2	104.2	104.2	104.2	105.6	105.6
40°	98.7	98.7	98.7	98.7	98.7	98.7	98.7	100.1	100.1	101.5	102.8
42.5°	94.6	94.6	94.6	94.6	94.6	96.0	96.0	96.0	96.0	97.4	97.4
45°	90.5	90.5	90.5	90.5	90.5	90.5	90.5	91.9	91.9	93.2	94.6
47.5°	86.4	86.4	86.4	86.4	86.4	87.8	89.1	89.1	89.1	90.5	90.5
50°	83.6	83.6	83.6	83.6	83.6	85.0	85.0	86.4	86.4	87.8	89.1
52.5°	80.9	80.9	80.9	80.9	80.9	82.3	82.3	83.6	83.6	85.0	86.4
55°	79.5	79.5	79.5	78.2	78.2	79.5	79.5	80.9	80.9	82.3	82.3
57.5°	75.4	75.4	75.4	75.4	75.4	75.4	75.4	76.8	76.8	78.2	79.5
60°	74.0	74.0	72.7	72.7	71.3	72.7	72.7	74.0	74.0	75.4	75.4
62.5°	69.9	69.9	69.9	68.6	68.6	69.9	69.9	69.9	69.9	71.3	72.7
65°	65.8	65.8	65.8	64.4	64.4	65.8	65.8	65.8	65.8	67.2	68.6
67.5°	61.7	61.7	61.7	60.3	60.3	60.3	60.3	61.7	61.7	63.1	64.4
70°	57.6	57.6	57.6	56.2	56.2	56.2	54.8	56.2	57.6	59.0	59.0
72.5°	53.5	53.5	53.5	52.1	52.1	52.1	50.7	52.1	52.1	53.5	53.5
75°	46.6	46.6	46.6	46.6	46.6	46.6	45.3	45.3	45.3	46.6	46.6
77.5°	42.5	42.5	42.5	41.1	41.1	41.1	39.8	39.8	39.8	41.1	41.1
80°	35.7	35.7	35.7	34.3	34.3	34.3	32.9	32.9	32.9	34.3	34.3
82.5°	28.8	28.8	28.8	27.4	27.4	27.4	26.1	26.1	26.1	27.4	27.4
85°	23.3	23.3	23.3	23.3	23.3	23.3	21.9	21.9	21.9	23.3	24.7
87.5°	11.0	11.0	12.3	12.3	12.3	12.3	11.0	11.0	9.6	9.6	11.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3
2.5°	898.2	900.9	907.8	913.3	920.1	925.6	929.7	935.2	939.3	943.4	946.2
5°	773.4	774.8	781.6	788.5	794.0	800.8	810.4	820.0	829.6	839.2	846.1
7.5°	602.0	607.5	615.7	625.3	633.5	641.7	651.3	662.3	671.9	681.5	691.1
10°	469.0	474.5	482.7	490.9	497.8	506.0	517.0	527.9	538.9	549.9	560.8
12.5°	393.5	400.4	410.0	419.6	427.8	437.4	451.1	463.5	477.2	489.5	503.2
15°	331.8	340.1	352.4	366.1	378.5	390.8	404.5	418.2	430.6	444.3	458.0
17.5°	272.9	281.1	292.1	304.4	315.4	326.4	342.8	357.9	374.4	389.4	404.5
20°	219.4	223.5	234.5	245.5	256.4	267.4	279.7	292.1	304.4	316.8	336.0
22.5°	182.4	185.1	190.6	194.7	200.2	204.3	216.7	229.0	240.0	252.3	270.1
25°	160.4	161.8	165.9	168.7	172.8	175.5	183.7	190.6	198.8	205.7	222.1
27.5°	149.5	150.8	152.2	153.6	155.0	156.3	161.8	167.3	171.4	176.9	192.0
30°	146.7	148.1	152.2	155.0	159.1	161.8	164.5	167.3	170.0	172.8	182.4
32.5°	144.0	145.4	145.4	144.0	144.0	142.6	145.4	146.7	149.5	150.8	159.1
35°	113.8	113.8	115.2	116.6	117.9	119.3	123.4	126.2	130.3	133.0	139.9
37.5°	107.0	107.0	108.3	111.1	112.4	113.8	116.6	119.3	122.0	124.8	131.6
40°	102.8	104.2	105.6	107.0	108.3	109.7	112.4	113.8	116.6	117.9	123.4
42.5°	98.7	98.7	100.1	102.8	104.2	105.6	108.3	109.7	112.4	113.8	119.3
45°	96.0	97.4	98.7	100.1	100.1	101.5	104.2	107.0	108.3	111.1	116.6
47.5°	91.9	91.9	94.6	96.0	98.7	100.1	102.8	104.2	107.0	108.3	113.8
50°	89.1	90.5	93.2	94.6	97.4	98.7	102.8	105.6	109.7	112.4	115.2
52.5°	86.4	87.8	90.5	91.9	94.6	96.0	101.5	107.0	111.1	116.6	116.6
55°	83.6	83.6	86.4	90.5	93.2	96.0	98.7	102.8	105.6	108.3	108.3
57.5°	79.5	80.9	83.6	87.8	90.5	93.2	96.0	98.7	100.1	102.8	101.5
60°	76.8	76.8	80.9	85.0	89.1	93.2	93.2	93.2	91.9	91.9	91.9
62.5°	72.7	74.0	79.5	86.4	91.9	97.4	93.2	89.1	85.0	80.9	82.3
65°	69.9	71.3	74.0	78.2	80.9	83.6	80.9	79.5	76.8	74.0	75.4
67.5°	64.4	65.8	67.2	67.2	68.6	68.6	68.6	68.6	68.6	68.6	69.9
70°	60.3	60.3	60.3	61.7	61.7	61.7	61.7	61.7	61.7	61.7	63.1
72.5°	54.8	54.8	54.8	54.8	54.8	54.8	54.8	54.8	54.8	54.8	56.2
75°	48.0	48.0	48.0	48.0	48.0	48.0	48.0	48.0	48.0	48.0	49.4
77.5°	42.5	42.5	42.5	42.5	42.5	42.5	42.5	42.5	41.1	41.1	42.5
80°	35.7	35.7	35.7	35.7	34.3	34.3	34.3	34.3	34.3	34.3	35.7
82.5°	28.8	28.8	28.8	28.8	27.4	27.4	27.4	27.4	26.1	26.1	27.4
85°	26.1	27.4	27.4	28.8	28.8	28.8	27.4	26.1	24.7	23.3	23.3
87.5°	11.0	11.0	11.0	11.0	9.6	9.6	9.6	9.6	9.6	9.6	9.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3
2.5°	950.3	953.0	955.8	959.9	965.4	969.5	973.6	981.8	991.4	999.6	1007.9
5°	852.9	859.8	866.6	874.9	883.1	889.9	898.2	914.6	931.1	946.2	962.6
7.5°	699.3	708.9	717.2	730.9	743.2	756.9	769.3	789.8	809.0	829.6	848.8
10°	571.8	582.8	593.8	611.6	630.8	648.6	666.4	682.9	700.7	717.2	733.6
12.5°	517.0	529.3	543.0	554.0	566.3	577.3	588.3	607.5	626.7	645.9	665.1
15°	471.7	485.4	499.1	512.8	525.2	538.9	551.2	567.7	585.5	602.0	618.4
17.5°	419.6	433.3	448.4	463.5	478.6	493.6	508.7	532.0	555.4	577.3	600.6
20°	353.8	373.0	390.8	411.4	431.9	452.5	473.1	497.8	522.4	545.8	570.4
22.5°	288.0	305.8	323.6	348.3	373.0	396.3	421.0	453.9	485.4	518.3	549.9
25°	240.0	256.4	272.9	300.3	326.4	353.8	379.8	419.6	458.0	497.8	536.2
27.5°	207.1	222.1	237.2	266.0	294.8	322.2	351.0	394.9	437.4	481.3	523.8
30°	192.0	201.6	211.2	238.6	266.0	292.1	319.5	362.0	404.5	447.0	489.5
32.5°	167.3	175.5	183.7	208.4	233.1	256.4	281.1	325.0	367.5	411.4	453.9
35°	148.1	155.0	161.8	185.1	207.1	230.4	252.3	296.2	340.1	383.9	427.8
37.5°	137.1	144.0	149.5	170.0	192.0	212.5	233.1	277.0	319.5	363.4	405.9
40°	128.9	133.0	138.5	159.1	178.3	198.8	218.0	257.8	298.9	338.7	378.5
42.5°	123.4	128.9	133.0	150.8	170.0	187.9	205.7	244.1	282.5	319.5	357.9
45°	122.0	127.5	133.0	148.1	163.2	176.9	192.0	229.0	266.0	303.0	340.1
47.5°	119.3	123.4	128.9	141.2	152.2	164.5	175.5	212.5	249.6	285.2	322.2
50°	117.9	119.3	122.0	133.0	144.0	155.0	165.9	202.9	240.0	277.0	314.0
52.5°	116.6	116.6	116.6	126.2	135.8	144.0	153.6	190.6	229.0	266.0	303.0
55°	108.3	107.0	107.0	116.6	124.8	134.4	142.6	179.6	216.7	252.3	289.3
57.5°	100.1	98.7	97.4	105.6	113.8	122.0	130.3	167.3	205.7	242.7	279.7
60°	91.9	90.5	90.5	98.7	105.6	113.8	120.7	159.1	196.1	234.5	271.5
62.5°	82.3	83.6	83.6	90.5	98.7	105.6	112.4	150.8	190.6	229.0	267.4
65°	75.4	76.8	76.8	85.0	93.2	101.5	109.7	146.7	185.1	222.1	259.2
67.5°	69.9	71.3	71.3	80.9	89.1	98.7	107.0	139.9	174.1	207.1	240.0
70°	64.4	64.4	65.8	75.4	85.0	94.6	104.2	133.0	161.8	189.2	218.0
72.5°	57.6	59.0	60.3	69.9	78.2	87.8	96.0	122.0	148.1	174.1	200.2
75°	50.7	52.1	53.5	61.7	69.9	78.2	86.4	111.1	134.4	159.1	182.4
77.5°	45.3	46.6	48.0	54.8	61.7	68.6	75.4	93.2	112.4	130.3	148.1
80°	37.0	37.0	38.4	43.9	49.4	53.5	59.0	71.3	83.6	94.6	107.0
82.5°	27.4	28.8	28.8	32.9	35.7	39.8	42.5	49.4	54.8	61.7	67.2
85°	23.3	21.9	21.9	24.7	26.1	28.8	30.2	34.3	37.0	41.1	43.9
87.5°	9.6	8.2	8.2	9.6	12.3	13.7	15.1	15.1	16.5	16.5	16.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3
2.5°	1012.0	1014.7	1018.8	1021.6	1028.4	1033.9	1040.8	1046.3	1050.4	1057.2	1054.5
5°	975.0	987.3	999.6	1012.0	1021.6	1031.2	1039.4	1049.0	1060.0	1080.5	1086.0
7.5°	865.3	881.7	896.8	913.3	932.4	951.6	970.8	990.0	1007.9	1033.9	1050.4
10°	756.9	780.2	802.2	825.5	843.3	861.1	877.6	895.4	920.1	946.2	976.3
12.5°	688.4	711.7	735.0	758.3	784.4	809.0	835.1	859.8	883.1	903.7	937.9
15°	643.1	669.2	693.9	718.5	750.1	780.2	811.8	841.9	876.2	903.7	927.0
17.5°	632.1	663.7	693.9	725.4	758.3	791.2	824.1	857.0	891.3	932.4	962.6
20°	612.9	655.5	698.0	740.5	783.0	824.1	866.6	907.8	953.0	1002.4	1016.1
22.5°	602.0	652.7	704.8	755.6	813.2	872.1	929.7	987.3	1035.3	1072.3	1113.5
25°	600.6	663.7	728.1	791.2	863.9	935.2	1007.9	1079.2	1140.9	1177.9	1210.8
27.5°	599.2	676.0	751.4	826.9	916.0	1003.8	1092.9	1180.6	1238.2	1291.7	1319.1
30°	582.8	674.7	767.9	859.8	959.9	1060.0	1160.1	1260.2	1319.1	1356.2	1369.9
32.5°	562.2	670.5	778.9	887.2	1001.0	1114.8	1227.3	1341.1	1387.7	1419.2	1408.3
35°	545.8	665.1	783.0	900.9	1021.6	1143.6	1264.3	1385.0	1452.2	1496.0	1478.2
37.5°	530.7	655.5	780.2	905.0	1046.3	1187.5	1328.7	1470.0	1534.4	1581.1	1560.5
40°	512.8	645.9	780.2	913.3	1075.1	1235.5	1397.3	1557.7	1641.4	1681.2	1649.6
42.5°	497.8	636.3	776.1	914.6	1087.4	1260.2	1433.0	1605.7	1699.0	1755.2	1715.4
45°	478.6	617.1	754.2	892.7	1083.3	1273.9	1463.1	1653.7	1762.1	1805.9	1751.1
47.5°	458.0	595.1	730.9	866.6	1069.6	1272.5	1475.5	1678.4	1778.5	1830.6	1779.9
50°	451.1	588.3	724.0	861.1	1080.5	1301.3	1520.7	1740.1	1812.8	1855.3	1788.1
52.5°	449.8	595.1	741.8	887.2	1108.0	1327.4	1548.1	1767.5	1826.5	1871.8	1811.4
55°	445.7	603.3	759.7	916.0	1146.4	1378.1	1608.5	1838.8	1897.8	1930.7	1885.5
57.5°	449.8	619.8	788.5	958.5	1195.7	1433.0	1670.2	1907.4	1978.7	2002.0	1992.4
60°	452.5	633.5	813.2	994.2	1225.9	1457.6	1689.4	1921.1	1995.2	2052.8	2063.7
62.5°	445.7	623.9	800.8	979.1	1188.9	1398.7	1608.5	1818.3	1940.3	2025.3	2074.7
65°	425.1	589.6	755.6	920.1	1113.5	1308.2	1501.5	1694.9	1823.8	1949.9	1989.7
67.5°	379.8	519.7	659.6	799.4	968.1	1136.8	1304.1	1472.7	1634.5	1756.6	1811.4
70°	329.1	438.8	549.9	659.6	813.2	966.7	1120.3	1273.9	1416.5	1550.9	1603.0
72.5°	286.6	371.6	458.0	543.0	652.7	761.0	870.7	979.1	1147.7	1282.1	1332.9
75°	244.1	305.8	366.1	427.8	503.2	578.7	652.7	728.1	847.4	968.1	1018.8
77.5°	187.9	229.0	268.8	308.5	360.6	411.4	463.5	514.2	597.9	688.4	714.4
80°	130.3	153.6	175.5	198.8	240.0	281.1	322.2	363.4	418.2	469.0	508.7
82.5°	80.9	96.0	109.7	123.4	156.3	189.2	220.8	253.7	275.6	278.4	318.1
85°	52.1	61.7	69.9	78.2	97.4	117.9	137.1	156.3	139.9	130.3	155.0
87.5°	20.6	26.1	30.2	34.3	32.9	31.5	30.2	28.8	24.7	21.9	27.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3
2.5°	1057.2	1061.3	1065.5	1068.2	1072.3	1073.7	1075.1	1075.1	1076.4	1077.8	1080.5
5°	1108.0	1116.2	1124.4	1131.3	1139.5	1146.4	1151.8	1158.7	1164.2	1164.2	1162.8
7.5°	1065.5	1086.0	1106.6	1127.2	1147.7	1162.8	1176.5	1191.6	1205.3	1208.1	1210.8
10°	1009.2	1031.2	1051.7	1073.7	1094.3	1117.6	1139.5	1161.4	1184.8	1188.9	1194.4
12.5°	957.1	983.2	1009.2	1033.9	1060.0	1076.4	1092.9	1108.0	1124.4	1135.4	1146.4
15°	955.8	977.7	999.6	1020.2	1042.1	1051.7	1061.3	1069.6	1079.2	1079.2	1080.5
17.5°	987.3	1001.0	1014.7	1027.1	1040.8	1042.1	1044.9	1046.3	1047.6	1043.5	1039.4
20°	1049.0	1054.5	1060.0	1065.5	1070.9	1061.3	1053.1	1043.5	1033.9	1023.0	1013.4
22.5°	1139.5	1127.2	1114.8	1102.5	1090.1	1073.7	1055.9	1039.4	1021.6	1007.9	994.2
25°	1224.5	1209.4	1194.4	1179.3	1164.2	1128.5	1092.9	1055.9	1020.2	1005.1	990.0
27.5°	1338.3	1315.0	1291.7	1268.4	1245.1	1197.1	1149.1	1101.1	1053.1	1027.1	1002.4
30°	1365.8	1339.7	1313.7	1286.2	1260.2	1213.6	1168.3	1121.7	1075.1	1044.9	1016.1
32.5°	1405.5	1375.4	1345.2	1315.0	1284.9	1239.6	1194.4	1147.7	1102.5	1075.1	1046.3
35°	1471.4	1437.1	1402.8	1367.1	1332.9	1286.2	1241.0	1194.4	1147.7	1116.2	1086.0
37.5°	1527.6	1487.8	1448.0	1408.3	1368.5	1327.4	1284.9	1243.7	1201.2	1169.7	1139.5
40°	1590.6	1546.8	1502.9	1460.4	1416.5	1378.1	1339.7	1299.9	1261.5	1236.9	1212.2
42.5°	1645.5	1592.0	1539.9	1487.8	1434.3	1408.3	1383.6	1357.5	1331.5	1319.1	1305.4
45°	1683.9	1634.5	1583.8	1534.4	1485.1	1465.9	1446.7	1427.5	1408.3	1420.6	1433.0
47.5°	1700.3	1660.6	1622.2	1583.8	1544.0	1550.9	1557.7	1563.2	1570.1	1586.5	1604.4
50°	1715.4	1693.5	1670.2	1648.2	1624.9	1651.0	1675.7	1701.7	1727.8	1762.1	1796.3
52.5°	1745.6	1733.3	1722.3	1709.9	1697.6	1742.9	1788.1	1833.4	1878.6	1917.0	1955.4
55°	1836.1	1826.5	1816.9	1805.9	1796.3	1860.8	1923.9	1988.3	2052.8	2092.5	2132.3
57.5°	1960.9	1955.4	1948.5	1943.1	1936.2	1999.3	2061.0	2122.7	2185.8	2224.2	2263.9
60°	2055.5	2056.9	2056.9	2058.2	2058.2	2106.2	2154.2	2203.6	2251.6	2284.5	2318.8
62.5°	2106.2	2103.5	2100.8	2098.0	2095.3	2135.0	2174.8	2214.6	2254.3	2279.0	2303.7
65°	2051.4	2066.5	2081.6	2096.6	2111.7	2117.2	2121.3	2126.8	2130.9	2146.0	2161.1
67.5°	1867.6	1897.8	1926.6	1956.8	1985.6	1965.0	1945.8	1925.2	1904.7	1908.8	1911.5
70°	1663.3	1697.6	1733.3	1767.5	1801.8	1753.8	1705.8	1656.5	1608.5	1592.0	1575.6
72.5°	1402.8	1433.0	1464.5	1494.7	1524.8	1465.9	1408.3	1349.3	1290.3	1261.5	1232.8
75°	1072.3	1108.0	1145.0	1180.6	1216.3	1150.5	1083.3	1017.5	950.3	931.1	913.3
77.5°	781.6	824.1	866.6	909.1	951.6	892.7	833.7	773.4	714.4	703.5	692.5
80°	569.1	602.0	633.5	666.4	698.0	663.7	629.4	595.1	560.8	559.5	558.1
82.5°	383.9	412.7	440.2	469.0	496.4	482.7	470.3	456.6	442.9	456.6	471.7
85°	197.5	237.2	278.4	318.1	357.9	353.8	351.0	346.9	342.8	360.6	377.1
87.5°	39.8	74.0	108.3	141.2	175.5	167.3	159.1	149.5	141.2	146.7	150.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3
2.5°	1081.9	1083.3	1083.3	1083.3	1083.3	1083.3	1080.5	1079.2	1076.4	1073.7	1069.6
5°	1162.8	1161.4	1156.0	1150.5	1143.6	1138.1	1134.0	1128.5	1124.4	1118.9	1110.7
7.5°	1213.6	1216.3	1206.7	1198.5	1188.9	1179.3	1169.7	1160.1	1150.5	1140.9	1121.7
10°	1198.5	1202.6	1197.1	1191.6	1184.8	1179.3	1168.3	1156.0	1145.0	1132.7	1109.3
12.5°	1156.0	1166.9	1164.2	1161.4	1158.7	1156.0	1149.1	1140.9	1134.0	1125.8	1099.7
15°	1080.5	1080.5	1081.9	1083.3	1083.3	1084.7	1086.0	1087.4	1088.8	1090.1	1075.1
17.5°	1035.3	1031.2	1031.2	1031.2	1031.2	1031.2	1036.7	1043.5	1049.0	1054.5	1050.4
20°	1002.4	992.8	991.4	991.4	990.0	988.7	998.3	1009.2	1018.8	1028.4	1033.9
22.5°	980.4	966.7	965.4	964.0	962.6	961.2	973.6	985.9	998.3	1010.6	1029.8
25°	975.0	959.9	961.2	962.6	962.6	964.0	973.6	983.2	992.8	1002.4	1035.3
27.5°	976.3	951.6	953.0	954.4	954.4	955.8	970.8	984.6	999.6	1013.4	1054.5
30°	985.9	957.1	954.4	951.6	948.9	946.2	966.7	987.3	1007.9	1028.4	1060.0
32.5°	1018.8	991.4	984.6	977.7	970.8	964.0	988.7	1012.0	1036.7	1060.0	1086.0
35°	1054.5	1024.3	1021.6	1018.8	1014.7	1012.0	1033.9	1057.2	1079.2	1101.1	1124.4
37.5°	1108.0	1077.8	1075.1	1070.9	1068.2	1064.1	1088.8	1112.1	1136.8	1160.1	1180.6
40°	1187.5	1162.8	1161.4	1161.4	1160.1	1158.7	1177.9	1198.5	1217.7	1236.9	1250.6
42.5°	1293.1	1280.7	1284.9	1290.3	1294.5	1298.6	1313.7	1330.1	1345.2	1360.3	1356.2
45°	1445.3	1457.6	1459.0	1460.4	1461.8	1463.1	1467.2	1472.7	1476.8	1480.9	1464.5
47.5°	1620.8	1637.3	1645.5	1653.7	1660.6	1668.8	1663.3	1656.5	1651.0	1644.1	1603.0
50°	1829.2	1863.5	1862.2	1860.8	1858.0	1856.7	1845.7	1834.7	1822.4	1811.4	1751.1
52.5°	1993.8	2032.2	2039.0	2045.9	2052.8	2059.6	2039.0	2018.5	1996.5	1976.0	1900.6
55°	2170.7	2210.5	2211.8	2213.2	2213.2	2214.6	2185.8	2157.0	2126.8	2098.0	2019.9
57.5°	2302.3	2340.7	2336.6	2333.9	2329.8	2325.6	2291.4	2257.1	2222.8	2188.5	2110.4
60°	2351.7	2384.6	2376.4	2368.1	2358.5	2350.3	2324.3	2298.2	2270.8	2244.7	2169.3
62.5°	2328.4	2353.1	2340.7	2329.8	2317.4	2305.1	2272.2	2237.9	2205.0	2170.7	2115.8
65°	2174.8	2189.9	2173.4	2158.3	2143.3	2126.8	2099.4	2072.0	2043.2	2015.7	1978.7
67.5°	1915.6	1918.4	1917.0	1915.6	1914.3	1912.9	1873.1	1833.4	1792.2	1752.5	1749.7
70°	1560.5	1544.0	1546.8	1550.9	1553.6	1556.4	1526.2	1497.4	1467.2	1437.1	1450.8
72.5°	1204.0	1175.2	1182.0	1190.2	1197.1	1204.0	1179.3	1156.0	1131.3	1106.6	1125.8
75°	894.1	876.2	883.1	891.3	898.2	905.0	895.4	885.8	874.9	865.3	883.1
77.5°	681.5	670.5	671.9	671.9	673.3	673.3	674.7	677.4	678.8	680.1	699.3
80°	555.4	554.0	552.6	551.2	548.5	547.1	560.8	574.6	588.3	602.0	611.6
82.5°	485.4	499.1	490.9	484.1	475.8	467.6	479.9	492.3	504.6	517.0	512.8
85°	394.9	411.4	396.3	381.2	364.8	349.7	360.6	370.2	381.2	390.8	385.3
87.5°	156.3	160.4	135.8	112.4	87.8	63.1	100.1	135.8	172.8	208.4	213.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3	987.3
2.5°	1065.5	1060.0	1055.9	1054.5	1051.7	1050.4	1047.6	1044.9	1040.8	1038.0	1033.9
5°	1101.1	1092.9	1083.3	1069.6	1057.2	1043.5	1029.8	1017.5	1005.1	991.4	979.1
7.5°	1102.5	1083.3	1064.1	1046.3	1027.1	1009.2	990.0	973.6	955.8	937.9	921.5
10°	1087.4	1064.1	1040.8	1017.5	995.5	972.2	948.9	929.7	909.1	888.6	869.4
12.5°	1075.1	1049.0	1023.0	995.5	969.5	942.0	914.6	895.4	876.2	857.0	837.8
15°	1060.0	1043.5	1028.4	1003.8	979.1	954.4	929.7	903.7	879.0	852.9	826.9
17.5°	1047.6	1043.5	1039.4	1023.0	1006.5	988.7	972.2	946.2	920.1	892.7	866.6
20°	1040.8	1046.3	1051.7	1043.5	1035.3	1025.7	1017.5	998.3	979.1	958.5	939.3
22.5°	1049.0	1069.6	1088.8	1090.1	1092.9	1094.3	1095.6	1077.8	1060.0	1040.8	1023.0
25°	1068.2	1101.1	1134.0	1151.8	1169.7	1188.9	1206.7	1195.7	1184.8	1173.8	1162.8
27.5°	1094.3	1135.4	1176.5	1202.6	1227.3	1253.3	1279.4	1278.0	1276.6	1273.9	1272.5
30°	1090.1	1121.7	1153.2	1184.8	1216.3	1247.8	1279.4	1295.8	1310.9	1327.4	1343.8
32.5°	1113.5	1139.5	1166.9	1199.8	1232.8	1267.0	1299.9	1334.2	1367.1	1401.4	1435.7
35°	1149.1	1172.4	1197.1	1232.8	1269.8	1305.4	1342.5	1383.6	1426.1	1468.6	1509.7
37.5°	1202.6	1223.2	1245.1	1275.3	1306.8	1337.0	1368.5	1428.8	1489.2	1550.9	1611.2
40°	1264.3	1278.0	1291.7	1320.5	1349.3	1378.1	1406.9	1482.3	1557.7	1633.2	1708.6
42.5°	1353.4	1349.3	1345.2	1368.5	1393.2	1416.5	1441.2	1509.7	1578.3	1646.9	1715.4
45°	1448.0	1431.6	1415.1	1426.1	1438.4	1449.4	1461.8	1531.7	1601.6	1672.9	1742.9
47.5°	1561.9	1520.7	1479.6	1470.0	1460.4	1449.4	1439.8	1515.2	1590.6	1667.4	1742.9
50°	1690.8	1629.0	1568.7	1544.0	1518.0	1493.3	1467.2	1528.9	1592.0	1655.1	1716.8
52.5°	1825.1	1748.3	1672.9	1634.5	1596.1	1556.4	1518.0	1570.1	1623.6	1677.0	1729.1
55°	1940.3	1862.2	1782.6	1737.4	1692.1	1646.9	1601.6	1653.7	1705.8	1757.9	1810.0
57.5°	2032.2	1954.0	1875.9	1833.4	1789.5	1747.0	1703.1	1752.5	1803.2	1853.9	1903.3
60°	2095.3	2019.9	1944.4	1903.3	1862.2	1821.0	1779.9	1838.8	1897.8	1958.1	2017.1
62.5°	2062.4	2007.5	1952.7	1934.8	1917.0	1897.8	1880.0	1936.2	1991.1	2047.3	2103.5
65°	1941.7	1904.7	1867.6	1885.5	1904.7	1922.5	1941.7	1978.7	2015.7	2054.1	2091.2
67.5°	1745.6	1742.9	1738.7	1778.5	1818.3	1859.4	1899.2	1923.9	1947.2	1971.9	1996.5
70°	1464.5	1479.6	1493.3	1561.9	1630.4	1699.0	1767.5	1777.1	1786.7	1796.3	1805.9
72.5°	1146.4	1165.6	1186.1	1276.6	1365.8	1456.3	1546.8	1541.3	1535.8	1528.9	1523.5
75°	902.3	920.1	939.3	1023.0	1106.6	1190.2	1273.9	1250.6	1228.6	1205.3	1182.0
77.5°	719.9	739.1	759.7	837.8	916.0	995.5	1073.7	1017.5	961.2	905.0	848.8
80°	619.8	629.4	637.6	691.1	743.2	796.7	850.2	792.6	733.6	674.7	617.1
82.5°	508.7	503.2	499.1	530.7	562.2	593.8	625.3	570.4	515.6	459.4	404.5
85°	379.8	374.4	368.9	385.3	401.8	419.6	436.1	373.0	309.9	245.5	182.4
87.5°	220.8	226.3	231.7	249.6	267.4	286.6	304.4	240.0	175.5	109.7	45.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671879

CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	987.3	987.3
2.5°	1025.7	1018.8
5°	969.5	959.9
7.5°	907.8	895.4
10°	851.5	835.1
12.5°	815.9	795.3
15°	802.2	777.5
17.5°	843.3	820.0
20°	906.4	874.9
22.5°	983.2	944.8
25°	1116.2	1069.6
27.5°	1224.5	1176.5
30°	1291.7	1239.6
32.5°	1365.8	1297.2
35°	1442.6	1376.7
37.5°	1535.8	1461.8
40°	1631.8	1555.0
42.5°	1664.7	1615.3
45°	1696.2	1649.6
47.5°	1703.1	1664.7
50°	1709.9	1704.5
52.5°	1729.1	1727.8
55°	1811.4	1812.8
57.5°	1912.9	1921.1
60°	2006.1	1996.5
62.5°	2054.1	2004.8
65°	2021.2	1952.7
67.5°	1922.5	1848.4
70°	1705.8	1605.7
72.5°	1435.7	1347.9
75°	1106.6	1032.6
77.5°	787.1	725.4
80°	554.0	492.3
82.5°	355.2	305.8
85°	160.4	139.9
87.5°	45.3	43.9
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671879
CATALOG NUMBER: CCP-SA-1C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)