

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671900

Luminaire Tested: **CCP-SA-1B-850-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671900
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1B-850-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @450mA w/ SLR
distribution lens
Light Source: (16) 5000K CCT, 80 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2500.9 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 24
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 3.5 fc
 Type IV - Short - N/A

REPORT NUMBER: P671900
CATALOG NUMBER: CCP-SA-1B-850-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	514.6	0.0	514.6
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	1986.3	0.0	1986.3
	% Fixture	79.4	0.0	79.4
Total	Lumens	2500.9	0.0	2500.9
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.1	2.5
10°-20°	131.0	5.2
20°-30°	191.7	7.7
30°-40°	270.1	10.8
40°-50°	371.1	14.8
50°-60°	505.8	20.2
60°-70°	553.6	22.1
70°-80°	319.7	12.8
80°-90°	95.8	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2500.9	100.0
0°-180°	2500.9	100.0



REPORT NUMBER: P671900


CATALOG NUMBER: CCP-SA-1B-850-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	256.9	10.3			
FM	(30°-60°)	912.7	36.5			
FH	(60°-80°)	735.4	29.4			G1/1800
FVH	(80°-90°)	81.4	3.3			G1/100
BL	(0°-30°)	127.9	5.1	B1/500		
BM	(30°-60°)	234.3	9.4	B1/1000		
BH	(60°-80°)	137.9	5.5	B1/500		G1/500
BVH	(80°-90°)	14.4	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6
2.5°	824.1	819.7	816.4	813.1	808.6	805.3	800.9	796.4	790.9	786.4	780.9
5°	776.5	763.1	749.8	742.1	733.2	725.4	716.6	706.6	696.6	685.5	675.5
7.5°	724.3	707.7	691.0	677.7	663.3	650.0	635.6	623.4	611.2	599.0	586.8
10°	675.5	660.0	644.5	627.8	610.1	593.4	575.7	559.0	542.4	525.8	509.1
12.5°	643.3	624.5	606.7	587.9	570.1	551.3	532.4	516.9	501.4	484.7	469.2
15°	628.9	611.2	594.5	575.7	556.8	538.0	519.1	501.4	484.7	467.0	449.2
17.5°	663.3	637.8	612.3	587.9	563.5	539.1	514.7	492.5	470.3	448.1	425.9
20°	707.7	675.5	644.5	614.5	583.4	553.5	522.4	491.4	460.3	429.3	398.2
22.5°	764.3	727.6	692.2	653.3	613.4	574.6	534.6	495.8	457.0	417.1	378.2
25°	865.2	821.9	778.7	723.2	666.6	611.2	554.6	503.6	453.7	402.6	351.6
27.5°	951.7	892.9	835.2	768.7	702.1	635.6	569.0	510.2	452.6	393.8	335.0
30°	1002.7	945.1	887.4	806.4	726.5	645.6	564.6	499.1	434.8	369.4	303.9
32.5°	1049.3	985.0	920.7	831.9	742.1	653.3	563.5	491.4	420.4	348.3	276.2
35°	1113.7	1042.7	972.8	869.6	766.5	663.3	560.2	485.8	410.4	336.1	260.7
37.5°	1182.4	1094.8	1008.3	894.0	779.8	665.5	551.3	478.1	404.9	331.7	258.4
40°	1257.9	1151.4	1046.0	919.5	794.2	667.7	541.3	468.1	394.9	320.6	247.4
42.5°	1306.7	1191.3	1075.9	939.5	804.2	667.7	531.3	459.2	387.1	313.9	241.8
45°	1334.4	1222.4	1111.4	963.9	816.4	668.9	521.3	450.3	379.4	307.3	236.3
47.5°	1346.6	1242.3	1138.1	982.8	828.6	673.3	518.0	445.9	372.7	300.6	227.4
50°	1378.8	1286.7	1194.6	1028.2	863.0	696.6	530.2	452.6	376.0	298.4	220.7
52.5°	1397.6	1318.9	1240.1	1069.3	898.5	727.6	556.8	470.3	383.8	297.3	210.8
55°	1466.4	1391.0	1315.5	1133.6	950.6	768.7	585.7	490.3	394.9	298.4	203.0
57.5°	1554.0	1474.2	1395.4	1199.1	1002.7	806.4	610.1	508.0	404.9	302.8	199.7
60°	1615.0	1537.4	1460.8	1252.3	1042.7	834.1	624.5	518.0	411.5	303.9	197.4
62.5°	1621.7	1521.8	1423.1	1220.1	1017.2	813.1	610.1	506.9	403.8	299.5	196.3
65°	1579.5	1463.1	1346.6	1152.5	958.4	764.3	570.1	475.9	381.6	286.2	191.9
67.5°	1495.2	1358.8	1222.4	1044.9	867.4	689.9	512.5	431.5	351.6	270.6	189.7
70°	1298.9	1179.1	1060.4	906.2	753.2	599.0	444.8	378.2	312.8	246.2	179.7
72.5°	1090.4	978.3	867.4	742.1	617.8	492.5	367.2	317.2	267.3	216.3	166.4
75°	835.2	750.9	667.7	574.6	481.4	387.1	293.9	257.3	220.7	184.1	147.5
77.5°	586.8	541.3	496.9	427.0	357.2	287.3	217.4	193.0	168.6	144.2	119.8
80°	398.2	372.7	348.3	298.4	248.5	197.4	147.5	132.0	115.4	99.8	83.2
82.5°	247.4	246.2	244.0	209.6	175.3	140.9	106.5	93.2	81.0	67.7	54.4
85°	113.1	132.0	149.7	130.9	112.0	93.2	74.3	65.4	56.6	46.6	37.7
87.5°	35.5	43.3	49.9	47.7	44.4	42.2	38.8	33.3	27.7	22.2	16.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6
2.5°	776.5	773.1	768.7	764.3	758.7	754.3	748.7	743.2	742.1	739.8	738.7
5°	668.9	662.2	654.4	647.8	641.1	633.4	626.7	618.9	613.4	606.7	601.2
7.5°	574.6	563.5	551.3	539.1	528.0	516.9	504.7	493.6	488.1	482.5	477.0
10°	499.1	488.1	478.1	467.0	459.2	452.6	444.8	437.0	430.4	423.7	417.1
12.5°	461.4	453.7	445.9	438.1	429.3	421.5	412.6	403.8	396.0	389.3	381.6
15°	438.1	427.0	414.8	403.8	391.6	380.5	368.3	356.1	347.2	339.4	330.5
17.5°	410.4	393.8	378.2	361.6	348.3	335.0	320.6	307.3	297.3	286.2	276.2
20°	379.4	360.5	340.5	321.7	306.1	291.7	276.2	260.7	249.6	237.4	226.3
22.5°	352.7	328.3	302.8	277.3	260.7	244.0	226.3	209.6	199.7	188.6	178.6
25°	323.9	297.3	269.5	241.8	225.2	207.4	190.8	173.0	165.3	158.6	150.9
27.5°	308.4	281.7	254.0	227.4	211.9	195.2	179.7	163.1	157.5	150.9	145.3
30°	277.3	251.8	225.2	198.6	187.5	177.5	166.4	155.3	153.1	152.0	149.7
32.5°	249.6	223.0	196.3	169.7	159.7	149.7	139.8	129.8	128.7	126.5	125.3
35°	235.2	209.6	183.0	157.5	148.6	138.7	129.8	119.8	117.6	114.2	112.0
37.5°	231.8	205.2	177.5	150.9	142.0	133.1	123.1	114.2	112.0	109.8	107.6
40°	223.0	197.4	173.0	147.5	138.7	129.8	119.8	110.9	108.7	106.5	104.3
42.5°	216.3	191.9	166.4	140.9	133.1	125.3	116.5	108.7	106.5	104.3	100.9
45°	210.8	185.2	158.6	133.1	127.6	122.0	115.4	109.8	107.6	104.3	102.0
47.5°	201.9	177.5	152.0	126.5	120.9	116.5	110.9	105.4	103.2	100.9	98.7
50°	195.2	169.7	144.2	118.7	114.2	109.8	105.4	100.9	100.9	102.0	102.0
52.5°	186.3	161.9	137.5	113.1	108.7	104.3	99.8	95.4	96.5	97.6	98.7
55°	178.6	155.3	130.9	106.5	102.0	97.6	92.1	87.6	88.7	89.8	91.0
57.5°	175.3	150.9	126.5	102.0	97.6	92.1	87.6	82.1	82.1	82.1	82.1
60°	173.0	147.5	123.1	97.6	92.1	87.6	82.1	76.5	75.4	75.4	74.3
62.5°	171.9	146.4	122.0	96.5	89.8	84.3	77.6	71.0	69.9	68.8	67.7
65°	167.5	144.2	119.8	95.4	87.6	81.0	73.2	65.4	64.3	64.3	63.2
67.5°	166.4	142.0	118.7	94.3	86.5	77.6	69.9	61.0	59.9	58.8	57.7
70°	157.5	136.4	114.2	92.1	83.2	75.4	66.6	57.7	56.6	54.4	53.2
72.5°	146.4	127.6	107.6	87.6	78.8	69.9	61.0	52.1	51.0	49.9	47.7
75°	129.8	112.0	94.3	76.5	68.8	62.1	54.4	46.6	45.5	44.4	42.2
77.5°	106.5	92.1	78.8	64.3	58.8	53.2	47.7	42.2	41.0	39.9	37.7
80°	75.4	66.6	58.8	49.9	46.6	42.2	38.8	34.4	34.4	33.3	33.3
82.5°	49.9	45.5	41.0	36.6	34.4	32.2	29.9	27.7	27.7	26.6	26.6
85°	35.5	33.3	29.9	27.7	26.6	24.4	23.3	21.1	21.1	21.1	21.1
87.5°	16.6	16.6	15.5	15.5	14.4	14.4	13.3	12.2	12.2	12.2	12.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6
2.5°	736.5	733.2	729.9	725.4	722.1	717.7	712.1	707.7	702.1	702.1	701.0
5°	594.5	591.2	587.9	583.4	580.1	575.7	572.4	567.9	563.5	563.5	562.4
7.5°	471.4	464.8	458.1	450.3	443.7	439.3	434.8	429.3	424.8	421.5	418.2
10°	410.4	403.8	396.0	389.3	381.6	376.0	370.5	363.8	358.3	353.8	349.4
12.5°	373.8	366.0	358.3	350.5	342.7	335.0	328.3	320.6	312.8	307.3	301.7
15°	321.7	313.9	306.1	298.4	290.6	281.7	272.9	262.9	254.0	249.6	246.2
17.5°	265.1	257.3	248.5	240.7	231.8	225.2	218.5	211.9	205.2	200.8	197.4
20°	214.1	205.2	196.3	187.5	178.6	174.1	169.7	165.3	160.8	157.5	155.3
22.5°	167.5	161.9	157.5	152.0	146.4	143.1	140.9	137.5	134.2	134.2	134.2
25°	143.1	139.8	137.5	134.2	130.9	129.8	128.7	126.5	125.3	124.2	124.2
27.5°	138.7	135.3	132.0	128.7	125.3	124.2	123.1	120.9	119.8	119.8	119.8
30°	147.5	146.4	145.3	144.2	143.1	140.9	137.5	135.3	132.0	129.8	127.6
32.5°	123.1	122.0	122.0	120.9	119.8	122.0	123.1	125.3	126.5	127.6	128.7
35°	108.7	106.5	104.3	102.0	99.8	98.7	97.6	96.5	95.4	95.4	94.3
37.5°	105.4	103.2	100.9	98.7	96.5	95.4	94.3	93.2	92.1	92.1	91.0
40°	102.0	99.8	98.7	96.5	94.3	93.2	92.1	89.8	88.7	87.6	87.6
42.5°	98.7	97.6	95.4	94.3	92.1	91.0	89.8	87.6	86.5	85.4	84.3
45°	98.7	96.5	94.3	92.1	89.8	88.7	86.5	85.4	83.2	83.2	82.1
47.5°	96.5	94.3	92.1	89.8	87.6	86.5	84.3	83.2	81.0	79.9	78.8
50°	102.0	98.7	94.3	91.0	86.5	85.4	83.2	82.1	79.9	78.8	77.6
52.5°	99.8	96.5	92.1	88.7	84.3	82.1	81.0	78.8	76.5	75.4	74.3
55°	92.1	88.7	86.5	83.2	79.9	77.6	75.4	73.2	71.0	69.9	69.9
57.5°	82.1	81.0	79.9	78.8	77.6	75.4	73.2	69.9	67.7	66.6	65.4
60°	73.2	74.3	75.4	76.5	77.6	74.3	71.0	67.7	64.3	63.2	62.1
62.5°	66.6	68.8	71.0	72.1	74.3	71.0	67.7	64.3	61.0	59.9	58.8
65°	62.1	63.2	63.2	64.3	64.3	62.1	61.0	58.8	56.6	55.5	55.5
67.5°	56.6	56.6	56.6	55.5	55.5	54.4	54.4	53.2	52.1	51.0	51.0
70°	51.0	51.0	51.0	49.9	49.9	48.8	48.8	47.7	46.6	46.6	45.5
72.5°	46.6	46.6	45.5	45.5	44.4	44.4	44.4	43.3	43.3	42.2	42.2
75°	41.0	41.0	39.9	39.9	38.8	38.8	38.8	37.7	37.7	37.7	36.6
77.5°	36.6	36.6	35.5	35.5	34.4	34.4	34.4	33.3	33.3	32.2	32.2
80°	32.2	32.2	31.1	31.1	29.9	29.9	28.8	28.8	27.7	27.7	26.6
82.5°	25.5	25.5	25.5	25.5	25.5	24.4	24.4	23.3	22.2	22.2	21.1
85°	21.1	21.1	21.1	20.0	20.0	20.0	18.9	18.9	17.7	16.6	16.6
87.5°	12.2	12.2	12.2	11.1	11.1	11.1	11.1	11.1	11.1	11.1	10.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6
2.5°	701.0	699.9	695.5	691.0	695.5	699.9	699.9	699.9	698.8	698.8	698.8
5°	562.4	561.3	559.0	556.8	556.8	555.7	557.9	560.2	562.4	564.6	566.8
7.5°	413.7	410.4	407.1	403.8	406.0	407.1	410.4	412.6	416.0	418.2	423.7
10°	345.0	340.5	337.2	333.9	331.7	329.4	327.2	326.1	323.9	321.7	323.9
12.5°	295.1	289.5	284.0	277.3	276.2	275.1	272.9	270.6	268.4	266.2	265.1
15°	241.8	237.4	235.2	231.8	227.4	223.0	220.7	219.6	217.4	215.2	214.1
17.5°	193.0	188.6	185.2	181.9	180.8	178.6	178.6	178.6	178.6	178.6	178.6
20°	152.0	148.6	148.6	147.5	147.5	146.4	147.5	148.6	148.6	149.7	150.9
22.5°	133.1	133.1	132.0	130.9	132.0	132.0	133.1	134.2	135.3	136.4	137.5
25°	123.1	122.0	123.1	124.2	124.2	124.2	125.3	125.3	126.5	126.5	126.5
27.5°	118.7	118.7	119.8	119.8	120.9	120.9	120.9	119.8	119.8	118.7	118.7
30°	125.3	123.1	123.1	123.1	122.0	120.9	119.8	119.8	118.7	117.6	116.5
32.5°	129.8	130.9	129.8	127.6	126.5	124.2	123.1	120.9	119.8	117.6	115.4
35°	94.3	93.2	95.4	96.5	97.6	98.7	99.8	100.9	100.9	102.0	102.0
37.5°	91.0	89.8	89.8	88.7	88.7	88.7	88.7	88.7	87.6	87.6	88.7
40°	86.5	85.4	85.4	84.3	84.3	83.2	83.2	83.2	83.2	83.2	83.2
42.5°	83.2	82.1	82.1	82.1	82.1	81.0	81.0	79.9	79.9	78.8	78.8
45°	82.1	81.0	79.9	78.8	78.8	77.6	77.6	77.6	76.5	76.5	76.5
47.5°	77.6	76.5	76.5	75.4	75.4	74.3	74.3	74.3	73.2	73.2	73.2
50°	75.4	74.3	74.3	73.2	73.2	72.1	72.1	72.1	71.0	71.0	71.0
52.5°	72.1	71.0	71.0	71.0	69.9	68.8	68.8	68.8	67.7	67.7	67.7
55°	68.8	67.7	67.7	67.7	66.6	65.4	65.4	65.4	64.3	64.3	64.3
57.5°	64.3	63.2	63.2	62.1	62.1	62.1	62.1	62.1	61.0	61.0	61.0
60°	61.0	59.9	59.9	58.8	58.8	57.7	57.7	57.7	57.7	57.7	57.7
62.5°	57.7	56.6	55.5	54.4	55.5	55.5	55.5	55.5	54.4	54.4	54.4
65°	54.4	53.2	52.1	51.0	51.0	51.0	51.0	51.0	51.0	51.0	51.0
67.5°	49.9	48.8	47.7	46.6	47.7	47.7	47.7	47.7	47.7	47.7	47.7
70°	45.5	44.4	44.4	43.3	43.3	42.2	42.2	43.3	43.3	43.3	43.3
72.5°	41.0	39.9	39.9	38.8	38.8	38.8	38.8	38.8	38.8	38.8	38.8
75°	36.6	35.5	35.5	34.4	34.4	34.4	34.4	34.4	34.4	34.4	34.4
77.5°	31.1	29.9	29.9	29.9	29.9	29.9	29.9	31.1	31.1	31.1	31.1
80°	26.6	25.5	25.5	25.5	25.5	25.5	25.5	25.5	25.5	25.5	25.5
82.5°	21.1	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0
85°	15.5	14.4	14.4	14.4	15.5	15.5	15.5	15.5	15.5	15.5	15.5
87.5°	10.0	8.9	8.9	8.9	10.0	10.0	10.0	10.0	8.9	8.9	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6
2.5°	698.8	698.8	698.8	697.7	696.6	695.5	694.4	697.7	699.9	703.2	705.5
5°	567.9	570.1	571.2	574.6	577.9	581.2	584.6	586.8	589.0	590.1	592.3
7.5°	428.2	433.7	438.1	442.6	447.0	450.3	454.8	458.1	461.4	464.8	468.1
10°	325.0	327.2	328.3	332.8	336.1	340.5	343.9	347.2	350.5	352.7	356.1
12.5°	264.0	261.8	260.7	260.7	260.7	260.7	260.7	262.9	265.1	267.3	269.5
15°	213.0	211.9	210.8	209.6	208.5	206.3	205.2	207.4	209.6	211.9	214.1
17.5°	178.6	178.6	178.6	177.5	176.4	175.3	174.1	175.3	176.4	176.4	177.5
20°	153.1	154.2	155.3	156.4	156.4	157.5	157.5	158.6	159.7	159.7	160.8
22.5°	137.5	138.7	138.7	138.7	139.8	139.8	139.8	140.9	142.0	143.1	144.2
25°	125.3	125.3	124.2	124.2	125.3	125.3	125.3	125.3	126.5	126.5	126.5
27.5°	118.7	117.6	117.6	117.6	117.6	116.5	116.5	116.5	116.5	116.5	116.5
30°	115.4	114.2	113.1	112.0	112.0	110.9	109.8	109.8	109.8	109.8	109.8
32.5°	114.2	112.0	109.8	108.7	108.7	107.6	106.5	105.4	105.4	104.3	103.2
35°	102.0	100.9	100.9	99.8	98.7	97.6	96.5	96.5	96.5	95.4	95.4
37.5°	88.7	89.8	89.8	89.8	91.0	91.0	91.0	91.0	92.1	92.1	92.1
40°	83.2	83.2	83.2	84.3	85.4	85.4	86.5	86.5	87.6	87.6	87.6
42.5°	78.8	77.6	77.6	78.8	78.8	79.9	79.9	81.0	82.1	82.1	83.2
45°	76.5	75.4	75.4	75.4	75.4	74.3	74.3	75.4	76.5	77.6	78.8
47.5°	72.1	72.1	71.0	71.0	71.0	71.0	71.0	71.0	72.1	72.1	72.1
50°	69.9	69.9	68.8	68.8	68.8	68.8	68.8	68.8	68.8	68.8	68.8
52.5°	67.7	66.6	66.6	66.6	66.6	65.4	65.4	65.4	65.4	65.4	65.4
55°	64.3	63.2	63.2	63.2	63.2	63.2	63.2	63.2	64.3	64.3	64.3
57.5°	61.0	59.9	59.9	59.9	61.0	61.0	61.0	61.0	62.1	62.1	62.1
60°	57.7	57.7	57.7	57.7	57.7	57.7	57.7	58.8	58.8	59.9	59.9
62.5°	54.4	54.4	54.4	54.4	55.5	55.5	55.5	55.5	56.6	56.6	56.6
65°	51.0	51.0	51.0	51.0	52.1	52.1	52.1	52.1	52.1	52.1	52.1
67.5°	47.7	47.7	47.7	47.7	47.7	47.7	47.7	48.8	48.8	49.9	49.9
70°	43.3	42.2	42.2	43.3	43.3	44.4	44.4	45.5	45.5	46.6	46.6
72.5°	38.8	38.8	38.8	38.8	38.8	38.8	38.8	39.9	41.0	41.0	42.2
75°	34.4	34.4	34.4	34.4	35.5	35.5	35.5	36.6	36.6	37.7	37.7
77.5°	31.1	29.9	29.9	29.9	31.1	31.1	31.1	32.2	32.2	33.3	33.3
80°	25.5	25.5	25.5	25.5	26.6	26.6	26.6	26.6	27.7	27.7	27.7
82.5°	21.1	21.1	21.1	21.1	21.1	21.1	21.1	21.1	22.2	22.2	22.2
85°	15.5	15.5	15.5	15.5	16.6	16.6	16.6	16.6	16.6	16.6	16.6
87.5°	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0	11.1	11.1	11.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900
 CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6
2.5°	705.5	705.5	705.5	705.5	707.7	708.8	711.0	712.1	711.0	709.9	707.7
5°	593.4	594.5	594.5	595.7	595.7	595.7	595.7	595.7	597.9	600.1	602.3
7.5°	469.2	470.3	471.4	472.5	472.5	472.5	471.4	471.4	472.5	472.5	473.6
10°	359.4	363.8	367.2	370.5	368.3	364.9	362.7	359.4	359.4	359.4	358.3
12.5°	271.8	272.9	275.1	276.2	275.1	275.1	274.0	272.9	274.0	276.2	277.3
15°	215.2	215.2	216.3	216.3	217.4	218.5	218.5	219.6	221.8	223.0	225.2
17.5°	178.6	179.7	179.7	180.8	180.8	181.9	181.9	181.9	184.1	186.3	189.7
20°	160.8	160.8	160.8	160.8	160.8	159.7	159.7	158.6	159.7	161.9	163.1
22.5°	144.2	145.3	145.3	145.3	144.2	143.1	140.9	139.8	139.8	140.9	140.9
25°	126.5	125.3	125.3	124.2	124.2	125.3	125.3	125.3	126.5	126.5	127.6
27.5°	116.5	115.4	115.4	114.2	114.2	115.4	115.4	115.4	115.4	115.4	115.4
30°	108.7	108.7	107.6	106.5	107.6	107.6	108.7	108.7	109.8	109.8	110.9
32.5°	103.2	102.0	102.0	100.9	102.0	102.0	103.2	103.2	104.3	105.4	105.4
35°	95.4	95.4	95.4	95.4	95.4	95.4	94.3	94.3	94.3	94.3	94.3
37.5°	91.0	91.0	89.8	88.7	88.7	88.7	88.7	88.7	87.6	86.5	85.4
40°	87.6	86.5	86.5	85.4	84.3	84.3	83.2	82.1	82.1	81.0	81.0
42.5°	83.2	82.1	82.1	81.0	79.9	79.9	78.8	77.6	77.6	77.6	76.5
45°	77.6	77.6	76.5	75.4	75.4	75.4	74.3	74.3	74.3	74.3	73.2
47.5°	72.1	72.1	71.0	71.0	71.0	71.0	69.9	69.9	69.9	69.9	69.9
50°	68.8	68.8	68.8	68.8	68.8	68.8	67.7	67.7	67.7	67.7	67.7
52.5°	65.4	65.4	65.4	65.4	65.4	65.4	65.4	65.4	65.4	65.4	65.4
55°	64.3	64.3	64.3	64.3	64.3	64.3	63.2	63.2	63.2	64.3	64.3
57.5°	62.1	62.1	61.0	61.0	61.0	61.0	61.0	61.0	61.0	61.0	61.0
60°	59.9	59.9	59.9	59.9	59.9	59.9	59.9	59.9	59.9	59.9	59.9
62.5°	56.6	56.6	56.6	56.6	56.6	57.7	57.7	57.7	57.7	57.7	56.6
65°	52.1	53.2	53.2	53.2	53.2	53.2	53.2	53.2	53.2	53.2	53.2
67.5°	49.9	49.9	49.9	49.9	49.9	49.9	49.9	49.9	49.9	49.9	49.9
70°	46.6	46.6	45.5	45.5	45.5	46.6	46.6	46.6	46.6	46.6	46.6
72.5°	42.2	42.2	42.2	42.2	42.2	42.2	42.2	42.2	42.2	43.3	43.3
75°	37.7	37.7	37.7	37.7	37.7	37.7	37.7	37.7	37.7	37.7	37.7
77.5°	33.3	33.3	32.2	32.2	32.2	33.3	33.3	33.3	33.3	34.4	34.4
80°	27.7	27.7	27.7	27.7	27.7	27.7	27.7	27.7	27.7	28.8	28.8
82.5°	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	23.3	23.3
85°	16.6	17.7	17.7	17.7	17.7	17.7	17.7	17.7	17.7	18.9	18.9
87.5°	11.1	11.1	11.1	11.1	11.1	11.1	10.0	10.0	10.0	10.0	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6
2.5°	706.6	707.7	708.8	708.8	709.9	711.0	711.0	715.4	719.9	722.1	724.3
5°	604.5	603.4	603.4	602.3	601.2	604.5	607.9	614.5	621.2	622.3	624.5
7.5°	473.6	474.7	475.9	475.9	477.0	473.6	469.2	470.3	471.4	477.0	481.4
10°	358.3	359.4	360.5	360.5	361.6	360.5	358.3	361.6	364.9	369.4	374.9
12.5°	278.4	281.7	285.1	287.3	290.6	292.8	293.9	298.4	301.7	307.3	312.8
15°	227.4	229.6	231.8	234.0	236.3	238.5	240.7	245.1	249.6	256.2	262.9
17.5°	191.9	191.9	193.0	193.0	193.0	195.2	197.4	199.7	200.8	207.4	214.1
20°	164.2	163.1	161.9	160.8	159.7	161.9	163.1	164.2	165.3	169.7	173.0
22.5°	140.9	140.9	142.0	142.0	142.0	140.9	138.7	139.8	139.8	142.0	145.3
25°	127.6	127.6	127.6	126.5	126.5	127.6	128.7	128.7	127.6	128.7	129.8
27.5°	115.4	116.5	116.5	117.6	117.6	118.7	118.7	118.7	118.7	119.8	120.9
30°	110.9	110.9	112.0	112.0	112.0	113.1	114.2	114.2	114.2	115.4	117.6
32.5°	106.5	107.6	108.7	109.8	110.9	112.0	112.0	113.1	113.1	114.2	115.4
35°	94.3	93.2	93.2	92.1	91.0	91.0	91.0	91.0	89.8	91.0	91.0
37.5°	84.3	84.3	84.3	83.2	83.2	84.3	84.3	84.3	84.3	85.4	85.4
40°	79.9	79.9	79.9	79.9	79.9	79.9	79.9	81.0	81.0	82.1	83.2
42.5°	76.5	76.5	76.5	76.5	76.5	77.6	77.6	77.6	77.6	78.8	78.8
45°	73.2	73.2	73.2	73.2	73.2	73.2	73.2	74.3	74.3	75.4	76.5
47.5°	69.9	69.9	69.9	69.9	69.9	71.0	72.1	72.1	72.1	73.2	73.2
50°	67.7	67.7	67.7	67.7	67.7	68.8	68.8	69.9	69.9	71.0	72.1
52.5°	65.4	65.4	65.4	65.4	65.4	66.6	66.6	67.7	67.7	68.8	69.9
55°	64.3	64.3	64.3	63.2	63.2	64.3	64.3	65.4	65.4	66.6	66.6
57.5°	61.0	61.0	61.0	61.0	61.0	61.0	61.0	62.1	62.1	63.2	64.3
60°	59.9	59.9	58.8	58.8	57.7	58.8	58.8	59.9	59.9	61.0	61.0
62.5°	56.6	56.6	56.6	55.5	55.5	56.6	56.6	56.6	56.6	57.7	58.8
65°	53.2	53.2	53.2	52.1	52.1	53.2	53.2	53.2	53.2	54.4	55.5
67.5°	49.9	49.9	49.9	48.8	48.8	48.8	48.8	49.9	49.9	51.0	52.1
70°	46.6	46.6	46.6	45.5	45.5	45.5	44.4	45.5	46.6	47.7	47.7
72.5°	43.3	43.3	43.3	42.2	42.2	42.2	41.0	42.2	42.2	43.3	43.3
75°	37.7	37.7	37.7	37.7	37.7	37.7	36.6	36.6	36.6	37.7	37.7
77.5°	34.4	34.4	34.4	33.3	33.3	33.3	32.2	32.2	32.2	33.3	33.3
80°	28.8	28.8	28.8	27.7	27.7	27.7	26.6	26.6	26.6	27.7	27.7
82.5°	23.3	23.3	23.3	22.2	22.2	22.2	21.1	21.1	21.1	22.2	22.2
85°	18.9	18.9	18.9	18.9	18.9	18.9	17.7	17.7	17.7	18.9	20.0
87.5°	8.9	8.9	10.0	10.0	10.0	10.0	8.9	8.9	7.8	7.8	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6
2.5°	726.5	728.8	734.3	738.7	744.3	748.7	752.1	756.5	759.8	763.1	765.4
5°	625.6	626.7	632.3	637.8	642.2	647.8	655.5	663.3	671.1	678.8	684.4
7.5°	486.9	491.4	498.0	505.8	512.5	519.1	526.9	535.8	543.5	551.3	559.0
10°	379.4	383.8	390.4	397.1	402.6	409.3	418.2	427.0	435.9	444.8	453.7
12.5°	318.3	323.9	331.7	339.4	346.1	353.8	364.9	374.9	386.0	396.0	407.1
15°	268.4	275.1	285.1	296.2	306.1	316.1	327.2	338.3	348.3	359.4	370.5
17.5°	220.7	227.4	236.3	246.2	255.1	264.0	277.3	289.5	302.8	315.0	327.2
20°	177.5	180.8	189.7	198.6	207.4	216.3	226.3	236.3	246.2	256.2	271.8
22.5°	147.5	149.7	154.2	157.5	161.9	165.3	175.3	185.2	194.1	204.1	218.5
25°	129.8	130.9	134.2	136.4	139.8	142.0	148.6	154.2	160.8	166.4	179.7
27.5°	120.9	122.0	123.1	124.2	125.3	126.5	130.9	135.3	138.7	143.1	155.3
30°	118.7	119.8	123.1	125.3	128.7	130.9	133.1	135.3	137.5	139.8	147.5
32.5°	116.5	117.6	117.6	116.5	116.5	115.4	117.6	118.7	120.9	122.0	128.7
35°	92.1	92.1	93.2	94.3	95.4	96.5	99.8	102.0	105.4	107.6	113.1
37.5°	86.5	86.5	87.6	89.8	91.0	92.1	94.3	96.5	98.7	100.9	106.5
40°	83.2	84.3	85.4	86.5	87.6	88.7	91.0	92.1	94.3	95.4	99.8
42.5°	79.9	79.9	81.0	83.2	84.3	85.4	87.6	88.7	91.0	92.1	96.5
45°	77.6	78.8	79.9	81.0	81.0	82.1	84.3	86.5	87.6	89.8	94.3
47.5°	74.3	74.3	76.5	77.6	79.9	81.0	83.2	84.3	86.5	87.6	92.1
50°	72.1	73.2	75.4	76.5	78.8	79.9	83.2	85.4	88.7	91.0	93.2
52.5°	69.9	71.0	73.2	74.3	76.5	77.6	82.1	86.5	89.8	94.3	94.3
55°	67.7	67.7	69.9	73.2	75.4	77.6	79.9	83.2	85.4	87.6	87.6
57.5°	64.3	65.4	67.7	71.0	73.2	75.4	77.6	79.9	81.0	83.2	82.1
60°	62.1	62.1	65.4	68.8	72.1	75.4	75.4	75.4	74.3	74.3	74.3
62.5°	58.8	59.9	64.3	69.9	74.3	78.8	75.4	72.1	68.8	65.4	66.6
65°	56.6	57.7	59.9	63.2	65.4	67.7	65.4	64.3	62.1	59.9	61.0
67.5°	52.1	53.2	54.4	54.4	55.5	55.5	55.5	55.5	55.5	55.5	56.6
70°	48.8	48.8	48.8	49.9	49.9	49.9	49.9	49.9	49.9	49.9	51.0
72.5°	44.4	44.4	44.4	44.4	44.4	44.4	44.4	44.4	44.4	44.4	45.5
75°	38.8	38.8	38.8	38.8	38.8	38.8	38.8	38.8	38.8	38.8	39.9
77.5°	34.4	34.4	34.4	34.4	34.4	34.4	34.4	34.4	33.3	33.3	34.4
80°	28.8	28.8	28.8	28.8	27.7	27.7	27.7	27.7	27.7	27.7	28.8
82.5°	23.3	23.3	23.3	23.3	22.2	22.2	22.2	22.2	21.1	21.1	22.2
85°	21.1	22.2	22.2	23.3	23.3	23.3	22.2	21.1	20.0	18.9	18.9
87.5°	8.9	8.9	8.9	8.9	7.8	7.8	7.8	7.8	7.8	7.8	7.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6
2.5°	768.7	770.9	773.1	776.5	780.9	784.2	787.5	794.2	802.0	808.6	815.3
5°	689.9	695.5	701.0	707.7	714.3	719.9	726.5	739.8	753.2	765.4	778.7
7.5°	565.7	573.5	580.1	591.2	601.2	612.3	622.3	638.9	654.4	671.1	686.6
10°	462.5	471.4	480.3	494.7	510.2	524.7	539.1	552.4	566.8	580.1	593.4
12.5°	418.2	428.2	439.3	448.1	458.1	467.0	475.9	491.4	506.9	522.4	538.0
15°	381.6	392.7	403.8	414.8	424.8	435.9	445.9	459.2	473.6	486.9	500.3
17.5°	339.4	350.5	362.7	374.9	387.1	399.3	411.5	430.4	449.2	467.0	485.8
20°	286.2	301.7	316.1	332.8	349.4	366.0	382.7	402.6	422.6	441.5	461.4
22.5°	232.9	247.4	261.8	281.7	301.7	320.6	340.5	367.2	392.7	419.3	444.8
25°	194.1	207.4	220.7	242.9	264.0	286.2	307.3	339.4	370.5	402.6	433.7
27.5°	167.5	179.7	191.9	215.2	238.5	260.7	284.0	319.5	353.8	389.3	423.7
30°	155.3	163.1	170.8	193.0	215.2	236.3	258.4	292.8	327.2	361.6	396.0
32.5°	135.3	142.0	148.6	168.6	188.6	207.4	227.4	262.9	297.3	332.8	367.2
35°	119.8	125.3	130.9	149.7	167.5	186.3	204.1	239.6	275.1	310.6	346.1
37.5°	110.9	116.5	120.9	137.5	155.3	171.9	188.6	224.1	258.4	293.9	328.3
40°	104.3	107.6	112.0	128.7	144.2	160.8	176.4	208.5	241.8	274.0	306.1
42.5°	99.8	104.3	107.6	122.0	137.5	152.0	166.4	197.4	228.5	258.4	289.5
45°	98.7	103.2	107.6	119.8	132.0	143.1	155.3	185.2	215.2	245.1	275.1
47.5°	96.5	99.8	104.3	114.2	123.1	133.1	142.0	171.9	201.9	230.7	260.7
50°	95.4	96.5	98.7	107.6	116.5	125.3	134.2	164.2	194.1	224.1	254.0
52.5°	94.3	94.3	94.3	102.0	109.8	116.5	124.2	154.2	185.2	215.2	245.1
55°	87.6	86.5	86.5	94.3	100.9	108.7	115.4	145.3	175.3	204.1	234.0
57.5°	81.0	79.9	78.8	85.4	92.1	98.7	105.4	135.3	166.4	196.3	226.3
60°	74.3	73.2	73.2	79.9	85.4	92.1	97.6	128.7	158.6	189.7	219.6
62.5°	66.6	67.7	67.7	73.2	79.9	85.4	91.0	122.0	154.2	185.2	216.3
65°	61.0	62.1	62.1	68.8	75.4	82.1	88.7	118.7	149.7	179.7	209.6
67.5°	56.6	57.7	57.7	65.4	72.1	79.9	86.5	113.1	140.9	167.5	194.1
70°	52.1	52.1	53.2	61.0	68.8	76.5	84.3	107.6	130.9	153.1	176.4
72.5°	46.6	47.7	48.8	56.6	63.2	71.0	77.6	98.7	119.8	140.9	161.9
75°	41.0	42.2	43.3	49.9	56.6	63.2	69.9	89.8	108.7	128.7	147.5
77.5°	36.6	37.7	38.8	44.4	49.9	55.5	61.0	75.4	91.0	105.4	119.8
80°	29.9	29.9	31.1	35.5	39.9	43.3	47.7	57.7	67.7	76.5	86.5
82.5°	22.2	23.3	23.3	26.6	28.8	32.2	34.4	39.9	44.4	49.9	54.4
85°	18.9	17.7	17.7	20.0	21.1	23.3	24.4	27.7	29.9	33.3	35.5
87.5°	7.8	6.7	6.7	7.8	10.0	11.1	12.2	12.2	13.3	13.3	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6
2.5°	818.6	820.8	824.1	826.4	831.9	836.4	841.9	846.3	849.7	855.2	853.0
5°	788.7	798.6	808.6	818.6	826.4	834.1	840.8	848.6	857.4	874.1	878.5
7.5°	699.9	713.2	725.4	738.7	754.3	769.8	785.3	800.9	815.3	836.4	849.7
10°	612.3	631.1	648.9	667.7	682.2	696.6	709.9	724.3	744.3	765.4	789.8
12.5°	556.8	575.7	594.5	613.4	634.5	654.4	675.5	695.5	714.3	731.0	758.7
15°	520.2	541.3	561.3	581.2	606.7	631.1	656.7	681.1	708.8	731.0	749.8
17.5°	511.3	536.9	561.3	586.8	613.4	640.0	666.6	693.3	721.0	754.3	778.7
20°	495.8	530.2	564.6	599.0	633.4	666.6	701.0	734.3	770.9	810.8	821.9
22.5°	486.9	528.0	570.1	611.2	657.8	705.5	752.1	798.6	837.5	867.4	900.7
25°	485.8	536.9	589.0	640.0	698.8	756.5	815.3	873.0	922.9	952.8	979.4
27.5°	484.7	546.8	607.9	668.9	741.0	811.9	884.0	955.0	1001.6	1044.9	1067.1
30°	471.4	545.7	621.2	695.5	776.5	857.4	938.4	1019.4	1067.1	1097.0	1108.1
32.5°	454.8	542.4	630.0	717.7	809.7	901.8	992.8	1084.8	1122.5	1148.0	1139.2
35°	441.5	538.0	633.4	728.8	826.4	925.1	1022.7	1120.3	1174.7	1210.2	1195.7
37.5°	429.3	530.2	631.1	732.1	846.3	960.6	1074.8	1189.1	1241.2	1278.9	1262.3
40°	414.8	522.4	631.1	738.7	869.6	999.4	1130.3	1260.1	1327.7	1359.9	1334.4
42.5°	402.6	514.7	627.8	739.8	879.6	1019.4	1159.1	1298.9	1374.3	1419.8	1387.6
45°	387.1	499.1	610.1	722.1	876.3	1030.5	1183.5	1337.7	1425.3	1460.8	1416.5
47.5°	370.5	481.4	591.2	701.0	865.2	1029.4	1193.5	1357.7	1438.7	1480.8	1439.8
50°	364.9	475.9	585.7	696.6	874.1	1052.6	1230.1	1407.6	1466.4	1500.8	1446.4
52.5°	363.8	481.4	600.1	717.7	896.2	1073.7	1252.3	1429.8	1477.5	1514.1	1465.3
55°	360.5	488.1	614.5	741.0	927.3	1114.8	1301.1	1487.5	1535.2	1561.8	1525.2
57.5°	363.8	501.4	637.8	775.3	967.2	1159.1	1351.0	1542.9	1600.6	1619.5	1611.7
60°	366.0	512.5	657.8	804.2	991.6	1179.1	1366.6	1554.0	1613.9	1660.5	1669.4
62.5°	360.5	504.7	647.8	792.0	961.7	1131.4	1301.1	1470.8	1569.5	1638.3	1678.2
65°	343.9	477.0	611.2	744.3	900.7	1058.2	1214.6	1371.0	1475.3	1577.3	1609.5
67.5°	307.3	420.4	533.5	646.7	783.1	919.5	1054.9	1191.3	1322.2	1420.9	1465.3
70°	266.2	355.0	444.8	533.5	657.8	782.0	906.2	1030.5	1145.8	1254.5	1296.7
72.5°	231.8	300.6	370.5	439.3	528.0	615.6	704.4	792.0	928.4	1037.1	1078.2
75°	197.4	247.4	296.2	346.1	407.1	468.1	528.0	589.0	685.5	783.1	824.1
77.5°	152.0	185.2	217.4	249.6	291.7	332.8	374.9	416.0	483.6	556.8	577.9
80°	105.4	124.2	142.0	160.8	194.1	227.4	260.7	293.9	338.3	379.4	411.5
82.5°	65.4	77.6	88.7	99.8	126.5	153.1	178.6	205.2	223.0	225.2	257.3
85°	42.2	49.9	56.6	63.2	78.8	95.4	110.9	126.5	113.1	105.4	125.3
87.5°	16.6	21.1	24.4	27.7	26.6	25.5	24.4	23.3	20.0	17.7	22.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6
2.5°	855.2	858.5	861.9	864.1	867.4	868.5	869.6	869.6	870.7	871.8	874.1
5°	896.2	902.9	909.6	915.1	921.8	927.3	931.7	937.3	941.7	941.7	940.6
7.5°	861.9	878.5	895.1	911.8	928.4	940.6	951.7	963.9	975.0	977.2	979.4
10°	816.4	834.1	850.8	868.5	885.2	904.0	921.8	939.5	958.4	961.7	966.1
12.5°	774.2	795.3	816.4	836.4	857.4	870.7	884.0	896.2	909.6	918.4	927.3
15°	773.1	790.9	808.6	825.3	843.0	850.8	858.5	865.2	873.0	873.0	874.1
17.5°	798.6	809.7	820.8	830.8	841.9	843.0	845.2	846.3	847.4	844.1	840.8
20°	848.6	853.0	857.4	861.9	866.3	858.5	851.9	844.1	836.4	827.5	819.7
22.5°	921.8	911.8	901.8	891.8	881.8	868.5	854.1	840.8	826.4	815.3	804.2
25°	990.5	978.3	966.1	953.9	941.7	912.9	884.0	854.1	825.3	813.1	800.9
27.5°	1082.6	1063.7	1044.9	1026.0	1007.2	968.3	929.5	890.7	851.9	830.8	810.8
30°	1104.8	1083.7	1062.6	1040.4	1019.4	981.7	945.1	907.3	869.6	845.2	821.9
32.5°	1136.9	1112.5	1088.1	1063.7	1039.3	1002.7	966.1	928.4	891.8	869.6	846.3
35°	1190.2	1162.5	1134.7	1105.9	1078.2	1040.4	1003.8	966.1	928.4	902.9	878.5
37.5°	1235.7	1203.5	1171.3	1139.2	1107.0	1073.7	1039.3	1006.1	971.7	946.2	921.8
40°	1286.7	1251.2	1215.7	1181.3	1145.8	1114.8	1083.7	1051.5	1020.5	1000.5	980.5
42.5°	1331.1	1287.8	1245.7	1203.5	1160.2	1139.2	1119.2	1098.1	1077.1	1067.1	1056.0
45°	1362.1	1322.2	1281.1	1241.2	1201.3	1185.8	1170.2	1154.7	1139.2	1149.2	1159.1
47.5°	1375.4	1343.3	1312.2	1281.1	1249.0	1254.5	1260.1	1264.5	1270.1	1283.4	1297.8
50°	1387.6	1369.9	1351.0	1333.3	1314.4	1335.5	1355.5	1376.5	1397.6	1425.3	1453.1
52.5°	1412.0	1402.1	1393.2	1383.2	1373.2	1409.8	1446.4	1483.0	1519.6	1550.7	1581.7
55°	1485.2	1477.5	1469.7	1460.8	1453.1	1505.2	1556.2	1608.4	1660.5	1692.7	1724.8
57.5°	1586.2	1581.7	1576.2	1571.8	1566.2	1617.2	1667.2	1717.1	1768.1	1799.2	1831.3
60°	1662.7	1663.8	1663.8	1664.9	1664.9	1703.8	1742.6	1782.5	1821.3	1848.0	1875.7
62.5°	1703.8	1701.5	1699.3	1697.1	1694.9	1727.1	1759.2	1791.4	1823.6	1843.5	1863.5
65°	1659.4	1671.6	1683.8	1696.0	1708.2	1712.6	1716.0	1720.4	1723.7	1735.9	1748.1
67.5°	1510.8	1535.2	1558.5	1582.9	1606.1	1589.5	1574.0	1557.3	1540.7	1544.0	1546.3
70°	1345.5	1373.2	1402.1	1429.8	1457.5	1418.7	1379.9	1339.9	1301.1	1287.8	1274.5
72.5°	1134.7	1159.1	1184.6	1209.0	1233.5	1185.8	1139.2	1091.5	1043.8	1020.5	997.2
75°	867.4	896.2	926.2	955.0	983.9	930.6	876.3	823.0	768.7	753.2	738.7
77.5°	632.3	666.6	701.0	735.4	769.8	722.1	674.4	625.6	577.9	569.0	560.2
80°	460.3	486.9	512.5	539.1	564.6	536.9	509.1	481.4	453.7	452.6	451.5
82.5°	310.6	333.9	356.1	379.4	401.5	390.4	380.5	369.4	358.3	369.4	381.6
85°	159.7	191.9	225.2	257.3	289.5	286.2	284.0	280.6	277.3	291.7	305.0
87.5°	32.2	59.9	87.6	114.2	142.0	135.3	128.7	120.9	114.2	118.7	122.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900
 CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6
2.5°	875.2	876.3	876.3	876.3	876.3	876.3	874.1	873.0	870.7	868.5	865.2
5°	940.6	939.5	935.1	930.6	925.1	920.7	917.3	912.9	909.6	905.1	898.5
7.5°	981.7	983.9	976.1	969.5	961.7	953.9	946.2	938.4	930.6	922.9	907.3
10°	969.5	972.8	968.3	963.9	958.4	953.9	945.1	935.1	926.2	916.2	897.4
12.5°	935.1	943.9	941.7	939.5	937.3	935.1	929.5	922.9	917.3	910.7	889.6
15°	874.1	874.1	875.2	876.3	876.3	877.4	878.5	879.6	880.7	881.8	869.6
17.5°	837.5	834.1	834.1	834.1	834.1	834.1	838.6	844.1	848.6	853.0	849.7
20°	810.8	803.1	802.0	802.0	800.9	799.7	807.5	816.4	824.1	831.9	836.4
22.5°	793.1	782.0	780.9	779.8	778.7	777.6	787.5	797.5	807.5	817.5	833.0
25°	788.7	776.5	777.6	778.7	778.7	779.8	787.5	795.3	803.1	810.8	837.5
27.5°	789.8	769.8	770.9	772.0	772.0	773.1	785.3	796.4	808.6	819.7	853.0
30°	797.5	774.2	772.0	769.8	767.6	765.4	782.0	798.6	815.3	831.9	857.4
32.5°	824.1	802.0	796.4	790.9	785.3	779.8	799.7	818.6	838.6	857.4	878.5
35°	853.0	828.6	826.4	824.1	820.8	818.6	836.4	855.2	873.0	890.7	909.6
37.5°	896.2	871.8	869.6	866.3	864.1	860.8	880.7	899.6	919.5	938.4	955.0
40°	960.6	940.6	939.5	939.5	938.4	937.3	952.8	969.5	985.0	1000.5	1011.6
42.5°	1046.0	1036.0	1039.3	1043.8	1047.1	1050.4	1062.6	1075.9	1088.1	1100.3	1097.0
45°	1169.1	1179.1	1180.2	1181.3	1182.4	1183.5	1186.9	1191.3	1194.6	1198.0	1184.6
47.5°	1311.1	1324.4	1331.1	1337.7	1343.3	1349.9	1345.5	1339.9	1335.5	1330.0	1296.7
50°	1479.7	1507.4	1506.3	1505.2	1503.0	1501.9	1493.0	1484.1	1474.2	1465.3	1416.5
52.5°	1612.8	1643.9	1649.4	1655.0	1660.5	1666.0	1649.4	1632.8	1615.0	1598.4	1537.4
55°	1755.9	1788.1	1789.2	1790.3	1790.3	1791.4	1768.1	1744.8	1720.4	1697.1	1633.9
57.5°	1862.4	1893.4	1890.1	1887.9	1884.6	1881.2	1853.5	1825.8	1798.0	1770.3	1707.1
60°	1902.3	1928.9	1922.3	1915.6	1907.9	1901.2	1880.1	1859.1	1836.9	1815.8	1754.8
62.5°	1883.5	1903.4	1893.4	1884.6	1874.6	1864.6	1838.0	1810.2	1783.6	1755.9	1711.5
65°	1759.2	1771.4	1758.1	1745.9	1733.7	1720.4	1698.2	1676.0	1652.7	1630.6	1600.6
67.5°	1549.6	1551.8	1550.7	1549.6	1548.5	1547.4	1515.2	1483.0	1449.7	1417.6	1415.4
70°	1262.3	1249.0	1251.2	1254.5	1256.7	1259.0	1234.6	1211.3	1186.9	1162.5	1173.6
72.5°	973.9	950.6	956.1	962.8	968.3	973.9	953.9	935.1	915.1	895.1	910.7
75°	723.2	708.8	714.3	721.0	726.5	732.1	724.3	716.6	707.7	699.9	714.3
77.5°	551.3	542.4	543.5	543.5	544.6	544.6	545.7	548.0	549.1	550.2	565.7
80°	449.2	448.1	447.0	445.9	443.7	442.6	453.7	464.8	475.9	486.9	494.7
82.5°	392.7	403.8	397.1	391.6	384.9	378.2	388.2	398.2	408.2	418.2	414.8
85°	319.5	332.8	320.6	308.4	295.1	282.9	291.7	299.5	308.4	316.1	311.7
87.5°	126.5	129.8	109.8	91.0	71.0	51.0	81.0	109.8	139.8	168.6	173.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6	798.6
2.5°	861.9	857.4	854.1	853.0	850.8	849.7	847.4	845.2	841.9	839.7	836.4
5°	890.7	884.0	876.3	865.2	855.2	844.1	833.0	823.0	813.1	802.0	792.0
7.5°	891.8	876.3	860.8	846.3	830.8	816.4	800.9	787.5	773.1	758.7	745.4
10°	879.6	860.8	841.9	823.0	805.3	786.4	767.6	752.1	735.4	718.8	703.2
12.5°	869.6	848.6	827.5	805.3	784.2	762.0	739.8	724.3	708.8	693.3	677.7
15°	857.4	844.1	831.9	811.9	792.0	772.0	752.1	731.0	711.0	689.9	668.9
17.5°	847.4	844.1	840.8	827.5	814.2	799.7	786.4	765.4	744.3	722.1	701.0
20°	841.9	846.3	850.8	844.1	837.5	829.7	823.0	807.5	792.0	775.3	759.8
22.5°	848.6	865.2	880.7	881.8	884.0	885.2	886.3	871.8	857.4	841.9	827.5
25°	864.1	890.7	917.3	931.7	946.2	961.7	976.1	967.2	958.4	949.5	940.6
27.5°	885.2	918.4	951.7	972.8	992.8	1013.8	1034.9	1033.8	1032.7	1030.5	1029.4
30°	881.8	907.3	932.9	958.4	983.9	1009.4	1034.9	1048.2	1060.4	1073.7	1087.0
32.5°	900.7	921.8	943.9	970.6	997.2	1024.9	1051.5	1079.3	1105.9	1133.6	1161.4
35°	929.5	948.4	968.3	997.2	1027.1	1056.0	1085.9	1119.2	1153.6	1188.0	1221.2
37.5°	972.8	989.4	1007.2	1031.6	1057.1	1081.5	1107.0	1155.8	1204.6	1254.5	1303.3
40°	1022.7	1033.8	1044.9	1068.2	1091.5	1114.8	1138.1	1199.1	1260.1	1321.1	1382.1
42.5°	1094.8	1091.5	1088.1	1107.0	1127.0	1145.8	1165.8	1221.2	1276.7	1332.2	1387.6
45°	1171.3	1158.0	1144.7	1153.6	1163.6	1172.4	1182.4	1239.0	1295.6	1353.2	1409.8
47.5°	1263.4	1230.1	1196.8	1189.1	1181.3	1172.4	1164.7	1225.7	1286.7	1348.8	1409.8
50°	1367.7	1317.8	1268.9	1249.0	1227.9	1207.9	1186.9	1236.8	1287.8	1338.8	1388.7
52.5°	1476.4	1414.3	1353.2	1322.2	1291.1	1259.0	1227.9	1270.1	1313.3	1356.6	1398.7
55°	1569.5	1506.3	1442.0	1405.4	1368.8	1332.2	1295.6	1337.7	1379.9	1422.0	1464.2
57.5°	1643.9	1580.6	1517.4	1483.0	1447.5	1413.1	1377.6	1417.6	1458.6	1499.7	1539.6
60°	1694.9	1633.9	1572.9	1539.6	1506.3	1473.0	1439.8	1487.5	1535.2	1584.0	1631.7
62.5°	1668.3	1623.9	1579.5	1565.1	1550.7	1535.2	1520.7	1566.2	1610.6	1656.1	1701.5
65°	1570.7	1540.7	1510.8	1525.2	1540.7	1555.1	1570.7	1600.6	1630.6	1661.6	1691.6
67.5°	1412.0	1409.8	1406.5	1438.7	1470.8	1504.1	1536.3	1556.2	1575.1	1595.1	1615.0
70°	1184.6	1196.8	1207.9	1263.4	1318.9	1374.3	1429.8	1437.5	1445.3	1453.1	1460.8
72.5°	927.3	942.8	959.5	1032.7	1104.8	1178.0	1251.2	1246.8	1242.3	1236.8	1232.3
75°	729.9	744.3	759.8	827.5	895.1	962.8	1030.5	1011.6	993.9	975.0	956.1
77.5°	582.3	597.9	614.5	677.7	741.0	805.3	868.5	823.0	777.6	732.1	686.6
80°	501.4	509.1	515.8	559.0	601.2	644.5	687.7	641.1	593.4	545.7	499.1
82.5°	411.5	407.1	403.8	429.3	454.8	480.3	505.8	461.4	417.1	371.6	327.2
85°	307.3	302.8	298.4	311.7	325.0	339.4	352.7	301.7	250.7	198.6	147.5
87.5°	178.6	183.0	187.5	201.9	216.3	231.8	246.2	194.1	142.0	88.7	36.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900

CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671900
 CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	798.6	798.6
2.5°	829.7	824.1
5°	784.2	776.5
7.5°	734.3	724.3
10°	688.8	675.5
12.5°	660.0	643.3
15°	648.9	628.9
17.5°	682.2	663.3
20°	733.2	707.7
22.5°	795.3	764.3
25°	902.9	865.2
27.5°	990.5	951.7
30°	1044.9	1002.7
32.5°	1104.8	1049.3
35°	1166.9	1113.7
37.5°	1242.3	1182.4
40°	1320.0	1257.9
42.5°	1346.6	1306.7
45°	1372.1	1334.4
47.5°	1377.6	1346.6
50°	1383.2	1378.8
52.5°	1398.7	1397.6
55°	1465.3	1466.4
57.5°	1547.4	1554.0
60°	1622.8	1615.0
62.5°	1661.6	1621.7
65°	1635.0	1579.5
67.5°	1555.1	1495.2
70°	1379.9	1298.9
72.5°	1161.4	1090.4
75°	895.1	835.2
77.5°	636.7	586.8
80°	448.1	398.2
82.5°	287.3	247.4
85°	129.8	113.1
87.5°	36.6	35.5
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671900
CATALOG NUMBER: CCP-SA-1B-850-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)