

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675946

Luminaire Tested: **CCW-SA-1E-722-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P675946
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-1E-722-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/
SLR distribution lens
Light Source: (16) 2200K CCT, 70 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4179.4 lumens
Efficiency: N/A
Efficacy: 74.5 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 56.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P675946
 CATALOG NUMBER: CCW-SA-1E-722-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 5.9 fc
 Type IV - Short - N/A

REPORT NUMBER: P675946
CATALOG NUMBER: CCW-SA-1E-722-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P675946

CATALOG NUMBER: CCW-SA-1E-722-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	859.9	0.0	859.9
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3319.4	0.0	3319.4
	% Fixture	79.4	0.0	79.4
Total	Lumens	4179.4	0.0	4179.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.7	2.5
10°-20°	219.0	5.2
20°-30°	320.3	7.7
30°-40°	451.3	10.8
40°-50°	620.2	14.8
50°-60°	845.3	20.2
60°-70°	925.2	22.1
70°-80°	534.3	12.8
80°-90°	160.2	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4179.4	100.0
0°-180°	4179.4	100.0

Coefficient of Utilization



REPORT NUMBER: P675946


CATALOG NUMBER: CCW-SA-1E-722-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	429.2	10.3			
FM	(30°-60°)	1525.2	36.5			
FH	(60°-80°)	1229.0	29.4			G1/1800
FVH	(80°-90°)	136.0	3.3			G2/225
BL	(0°-30°)	213.8	5.1	B1/500		
BM	(30°-60°)	391.6	9.4	B1/1000		
BH	(60°-80°)	230.5	5.5	B1/500		G1/500
BVH	(80°-90°)	24.1	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P675946

CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	1377.3	1369.9	1364.3	1358.7	1351.3	1345.8	1338.3	1330.9	1321.7	1314.2	1305.0
5°	1297.6	1275.3	1253.1	1240.1	1225.3	1212.3	1197.5	1180.8	1164.1	1145.6	1128.9
7.5°	1210.4	1182.6	1154.8	1132.6	1108.5	1086.2	1062.1	1041.8	1021.4	1001.0	980.6
10°	1128.9	1102.9	1077.0	1049.2	1019.5	991.7	962.0	934.2	906.4	878.6	850.8
12.5°	1075.1	1043.6	1013.9	982.4	952.8	921.3	889.8	863.8	837.9	810.0	784.1
15°	1051.0	1021.4	993.6	962.0	930.5	899.0	867.5	837.9	810.0	780.4	750.7
17.5°	1108.5	1065.9	1023.2	982.4	941.7	900.9	860.1	823.0	785.9	748.9	711.8
20°	1182.6	1128.9	1077.0	1026.9	975.0	925.0	873.1	821.2	769.3	717.4	665.5
22.5°	1277.2	1216.0	1156.7	1091.8	1025.1	960.2	893.5	828.6	763.7	697.0	632.1
25°	1445.9	1373.6	1301.3	1208.6	1114.0	1021.4	926.8	841.6	758.1	672.9	587.6
27.5°	1590.4	1492.2	1395.8	1284.6	1173.4	1062.1	950.9	852.7	756.3	658.0	559.8
30°	1675.7	1579.3	1482.9	1347.6	1214.1	1078.8	943.5	834.1	726.6	617.3	507.9
32.5°	1753.6	1646.0	1538.5	1390.2	1240.1	1091.8	941.7	821.2	702.5	582.0	461.6
35°	1861.1	1742.4	1625.7	1453.3	1280.9	1108.5	936.1	811.9	685.9	561.7	435.6
37.5°	1976.0	1829.6	1685.0	1494.0	1303.1	1112.2	921.3	798.9	676.6	554.2	431.9
40°	2102.0	1924.1	1748.0	1536.7	1327.2	1115.9	904.6	782.2	659.9	535.7	413.4
42.5°	2183.6	1990.8	1798.0	1570.0	1343.9	1115.9	887.9	767.4	646.9	524.6	404.1
45°	2229.9	2042.7	1857.4	1610.8	1364.3	1117.8	871.2	752.6	633.9	513.5	394.8
47.5°	2250.3	2076.1	1901.8	1642.3	1384.7	1125.2	865.7	745.2	622.8	502.3	380.0
50°	2304.1	2150.2	1996.4	1718.3	1442.1	1164.1	886.0	756.3	628.4	498.6	368.9
52.5°	2335.6	2204.0	2072.4	1786.9	1501.5	1216.0	930.5	785.9	641.4	496.8	352.2
55°	2450.5	2324.5	2198.4	1894.4	1588.6	1284.6	978.7	819.3	659.9	498.6	339.2
57.5°	2597.0	2463.5	2331.9	2003.8	1675.7	1347.6	1019.5	849.0	676.6	506.0	333.7
60°	2698.9	2569.2	2441.3	2092.8	1742.4	1393.9	1043.6	865.7	687.7	507.9	330.0
62.5°	2710.0	2543.2	2378.2	2039.0	1699.8	1358.7	1019.5	847.1	674.7	500.5	328.1
65°	2639.6	2445.0	2250.3	1925.9	1601.6	1277.2	952.8	795.2	637.7	478.2	320.7
67.5°	2498.7	2270.7	2042.7	1746.1	1449.6	1153.0	856.4	721.1	587.6	452.3	317.0
70°	2170.6	1970.4	1772.1	1514.4	1258.6	1001.0	743.3	632.1	522.7	411.5	300.3
72.5°	1822.1	1634.9	1449.6	1240.1	1032.5	823.0	613.6	530.1	446.7	361.5	278.0
75°	1395.8	1254.9	1115.9	960.2	804.5	646.9	491.2	430.0	368.9	307.7	246.5
77.5°	980.6	904.6	830.4	713.7	596.9	480.1	363.3	322.5	281.8	241.0	200.2
80°	665.5	622.8	582.0	498.6	415.2	330.0	246.5	220.6	192.8	166.8	139.0
82.5°	413.4	411.5	407.8	350.3	292.9	235.4	178.0	155.7	135.3	113.1	90.8
85°	189.1	220.6	250.2	218.7	187.2	155.7	124.2	109.4	94.5	77.9	63.0
87.5°	59.3	72.3	83.4	79.7	74.1	70.4	64.9	55.6	46.3	37.1	27.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946

CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946

CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	1297.6	1292.0	1284.6	1277.2	1267.9	1260.5	1251.2	1241.9	1240.1	1236.4	1234.5
5°	1117.8	1106.6	1093.7	1082.5	1071.4	1058.4	1047.3	1034.3	1025.1	1013.9	1004.7
7.5°	960.2	941.7	921.3	900.9	882.3	863.8	843.4	824.9	815.6	806.3	797.1
10°	834.1	815.6	798.9	780.4	767.4	756.3	743.3	730.3	719.2	708.1	697.0
12.5°	771.1	758.1	745.2	732.2	717.4	704.4	689.6	674.7	661.8	650.6	637.7
15°	732.2	713.7	693.3	674.7	654.3	635.8	615.4	595.0	580.2	567.2	552.4
17.5°	685.9	658.0	632.1	604.3	582.0	559.8	535.7	513.5	496.8	478.2	461.6
20°	633.9	602.4	569.1	537.6	511.6	487.5	461.6	435.6	417.1	396.7	378.1
22.5°	589.5	548.7	506.0	463.4	435.6	407.8	378.1	350.3	333.7	315.1	298.4
25°	541.3	496.8	450.4	404.1	376.3	346.6	318.8	289.2	276.2	265.1	252.1
27.5°	515.3	470.8	424.5	380.0	354.0	326.2	300.3	272.5	263.2	252.1	242.8
30°	463.4	420.8	376.3	331.8	313.3	296.6	278.0	259.5	255.8	254.0	250.2
32.5°	417.1	372.6	328.1	283.6	266.9	250.2	233.6	216.9	215.0	211.3	209.5
35°	393.0	350.3	305.9	263.2	248.4	231.7	216.9	200.2	196.5	190.9	187.2
37.5°	387.4	342.9	296.6	252.1	237.3	222.4	205.8	190.9	187.2	183.5	179.8
40°	372.6	330.0	289.2	246.5	231.7	216.9	200.2	185.4	181.7	178.0	174.2
42.5°	361.5	320.7	278.0	235.4	222.4	209.5	194.6	181.7	178.0	174.2	168.7
45°	352.2	309.6	265.1	222.4	213.2	203.9	192.8	183.5	179.8	174.2	170.5
47.5°	337.4	296.6	254.0	211.3	202.0	194.6	185.4	176.1	172.4	168.7	165.0
50°	326.2	283.6	241.0	198.3	190.9	183.5	176.1	168.7	168.7	170.5	170.5
52.5°	311.4	270.6	229.9	189.1	181.7	174.2	166.8	159.4	161.3	163.1	165.0
55°	298.4	259.5	218.7	178.0	170.5	163.1	153.9	146.4	148.3	150.1	152.0
57.5°	292.9	252.1	211.3	170.5	163.1	153.9	146.4	137.2	137.2	137.2	137.2
60°	289.2	246.5	205.8	163.1	153.9	146.4	137.2	127.9	126.0	126.0	124.2
62.5°	287.3	244.7	203.9	161.3	150.1	140.9	129.8	118.6	116.8	114.9	113.1
65°	279.9	241.0	200.2	159.4	146.4	135.3	122.3	109.4	107.5	107.5	105.7
67.5°	278.0	237.3	198.3	157.6	144.6	129.8	116.8	102.0	100.1	98.2	96.4
70°	263.2	228.0	190.9	153.9	139.0	126.0	111.2	96.4	94.5	90.8	89.0
72.5°	244.7	213.2	179.8	146.4	131.6	116.8	102.0	87.1	85.3	83.4	79.7
75°	216.9	187.2	157.6	127.9	114.9	103.8	90.8	77.9	76.0	74.1	70.4
77.5°	178.0	153.9	131.6	107.5	98.2	89.0	79.7	70.4	68.6	66.7	63.0
80°	126.0	111.2	98.2	83.4	77.9	70.4	64.9	57.5	57.5	55.6	55.6
82.5°	83.4	76.0	68.6	61.2	57.5	53.8	50.0	46.3	46.3	44.5	44.5
85°	59.3	55.6	50.0	46.3	44.5	40.8	38.9	35.2	35.2	35.2	35.2
87.5°	27.8	27.8	26.0	26.0	24.1	24.1	22.2	20.4	20.4	20.4	20.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946
 CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946

CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	1230.8	1225.3	1219.7	1212.3	1206.7	1199.3	1190.0	1182.6	1173.4	1173.4	1171.5
5°	993.6	988.0	982.4	975.0	969.5	962.0	956.5	949.1	941.7	941.7	939.8
7.5°	787.8	776.7	765.6	752.6	741.5	734.0	726.6	717.4	709.9	704.4	698.8
10°	685.9	674.7	661.8	650.6	637.7	628.4	619.1	608.0	598.7	591.3	583.9
12.5°	624.7	611.7	598.7	585.8	572.8	559.8	548.7	535.7	522.7	513.5	504.2
15°	537.6	524.6	511.6	498.6	485.7	470.8	456.0	439.3	424.5	417.1	411.5
17.5°	443.0	430.0	415.2	402.2	387.4	376.3	365.2	354.0	342.9	335.5	330.0
20°	357.8	342.9	328.1	313.3	298.4	291.0	283.6	276.2	268.8	263.2	259.5
22.5°	279.9	270.6	263.2	254.0	244.7	239.1	235.4	229.9	224.3	224.3	224.3
25°	239.1	233.6	229.9	224.3	218.7	216.9	215.0	211.3	209.5	207.6	207.6
27.5°	231.7	226.1	220.6	215.0	209.5	207.6	205.8	202.0	200.2	200.2	200.2
30°	246.5	244.7	242.8	241.0	239.1	235.4	229.9	226.1	220.6	216.9	213.2
32.5°	205.8	203.9	203.9	202.0	200.2	203.9	205.8	209.5	211.3	213.2	215.0
35°	181.7	178.0	174.2	170.5	166.8	165.0	163.1	161.3	159.4	159.4	157.6
37.5°	176.1	172.4	168.7	165.0	161.3	159.4	157.6	155.7	153.9	153.9	152.0
40°	170.5	166.8	165.0	161.3	157.6	155.7	153.9	150.1	148.3	146.4	146.4
42.5°	165.0	163.1	159.4	157.6	153.9	152.0	150.1	146.4	144.6	142.7	140.9
45°	165.0	161.3	157.6	153.9	150.1	148.3	144.6	142.7	139.0	139.0	137.2
47.5°	161.3	157.6	153.9	150.1	146.4	144.6	140.9	139.0	135.3	133.5	131.6
50°	170.5	165.0	157.6	152.0	144.6	142.7	139.0	137.2	133.5	131.6	129.8
52.5°	166.8	161.3	153.9	148.3	140.9	137.2	135.3	131.6	127.9	126.0	124.2
55°	153.9	148.3	144.6	139.0	133.5	129.8	126.0	122.3	118.6	116.8	116.8
57.5°	137.2	135.3	133.5	131.6	129.8	126.0	122.3	116.8	113.1	111.2	109.4
60°	122.3	124.2	126.0	127.9	129.8	124.2	118.6	113.1	107.5	105.7	103.8
62.5°	111.2	114.9	118.6	120.5	124.2	118.6	113.1	107.5	102.0	100.1	98.2
65°	103.8	105.7	105.7	107.5	107.5	103.8	102.0	98.2	94.5	92.7	92.7
67.5°	94.5	94.5	94.5	92.7	92.7	90.8	90.8	89.0	87.1	85.3	85.3
70°	85.3	85.3	85.3	83.4	83.4	81.6	81.6	79.7	77.9	77.9	76.0
72.5°	77.9	77.9	76.0	76.0	74.1	74.1	74.1	72.3	72.3	70.4	70.4
75°	68.6	68.6	66.7	66.7	64.9	64.9	64.9	63.0	63.0	63.0	61.2
77.5°	61.2	61.2	59.3	59.3	57.5	57.5	57.5	55.6	55.6	53.8	53.8
80°	53.8	53.8	51.9	51.9	50.0	50.0	48.2	48.2	46.3	46.3	44.5
82.5°	42.6	42.6	42.6	42.6	42.6	40.8	40.8	38.9	37.1	37.1	35.2
85°	35.2	35.2	35.2	33.4	33.4	33.4	31.5	31.5	29.7	27.8	27.8
87.5°	20.4	20.4	20.4	18.5	18.5	18.5	18.5	18.5	18.5	18.5	16.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946
 CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946

CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	1171.5	1169.7	1162.2	1154.8	1162.2	1169.7	1169.7	1169.7	1167.8	1167.8	1167.8
5°	939.8	937.9	934.2	930.5	930.5	928.7	932.4	936.1	939.8	943.5	947.2
7.5°	691.4	685.9	680.3	674.7	678.4	680.3	685.9	689.6	695.1	698.8	708.1
10°	576.5	569.1	563.5	558.0	554.2	550.5	546.8	545.0	541.3	537.6	541.3
12.5°	493.1	483.8	474.5	463.4	461.6	459.7	456.0	452.3	448.6	444.9	443.0
15°	404.1	396.7	393.0	387.4	380.0	372.6	368.9	367.0	363.3	359.6	357.8
17.5°	322.5	315.1	309.6	304.0	302.1	298.4	298.4	298.4	298.4	298.4	298.4
20°	254.0	248.4	248.4	246.5	246.5	244.7	246.5	248.4	248.4	250.2	252.1
22.5°	222.4	222.4	220.6	218.7	220.6	220.6	222.4	224.3	226.1	228.0	229.9
25°	205.8	203.9	205.8	207.6	207.6	207.6	209.5	209.5	211.3	211.3	211.3
27.5°	198.3	198.3	200.2	200.2	202.0	202.0	202.0	200.2	200.2	198.3	198.3
30°	209.5	205.8	205.8	205.8	203.9	202.0	200.2	200.2	198.3	196.5	194.6
32.5°	216.9	218.7	216.9	213.2	211.3	207.6	205.8	202.0	200.2	196.5	192.8
35°	157.6	155.7	159.4	161.3	163.1	165.0	166.8	168.7	168.7	170.5	170.5
37.5°	152.0	150.1	150.1	148.3	148.3	148.3	148.3	148.3	146.4	146.4	148.3
40°	144.6	142.7	142.7	140.9	140.9	139.0	139.0	139.0	139.0	139.0	139.0
42.5°	139.0	137.2	137.2	137.2	137.2	135.3	135.3	133.5	133.5	131.6	131.6
45°	137.2	135.3	133.5	131.6	131.6	129.8	129.8	129.8	127.9	127.9	127.9
47.5°	129.8	127.9	127.9	126.0	126.0	124.2	124.2	124.2	122.3	122.3	122.3
50°	126.0	124.2	124.2	122.3	122.3	120.5	120.5	120.5	118.6	118.6	118.6
52.5°	120.5	118.6	118.6	118.6	116.8	114.9	114.9	114.9	113.1	113.1	113.1
55°	114.9	113.1	113.1	113.1	111.2	109.4	109.4	109.4	107.5	107.5	107.5
57.5°	107.5	105.7	105.7	103.8	103.8	103.8	103.8	103.8	102.0	102.0	102.0
60°	102.0	100.1	100.1	98.2	98.2	96.4	96.4	96.4	96.4	96.4	96.4
62.5°	96.4	94.5	92.7	90.8	92.7	92.7	92.7	92.7	90.8	90.8	90.8
65°	90.8	89.0	87.1	85.3	85.3	85.3	85.3	85.3	85.3	85.3	85.3
67.5°	83.4	81.6	79.7	77.9	79.7	79.7	79.7	79.7	79.7	79.7	79.7
70°	76.0	74.1	74.1	72.3	72.3	70.4	70.4	72.3	72.3	72.3	72.3
72.5°	68.6	66.7	66.7	64.9	64.9	64.9	64.9	64.9	64.9	64.9	64.9
75°	61.2	59.3	59.3	57.5	57.5	57.5	57.5	57.5	57.5	57.5	57.5
77.5°	51.9	50.0	50.0	50.0	50.0	50.0	50.0	51.9	51.9	51.9	51.9
80°	44.5	42.6	42.6	42.6	42.6	42.6	42.6	42.6	42.6	42.6	42.6
82.5°	35.2	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4
85°	26.0	24.1	24.1	24.1	26.0	26.0	26.0	26.0	26.0	26.0	26.0
87.5°	16.7	14.8	14.8	14.8	16.7	16.7	16.7	16.7	14.8	14.8	14.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946

CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675946

CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	1167.8	1167.8	1167.8	1165.9	1164.1	1162.2	1160.4	1165.9	1169.7	1175.2	1178.9
5°	949.1	952.8	954.6	960.2	965.8	971.3	976.9	980.6	984.3	986.1	989.9
7.5°	715.5	724.8	732.2	739.6	747.0	752.6	760.0	765.6	771.1	776.7	782.2
10°	543.1	546.8	548.7	556.1	561.7	569.1	574.6	580.2	585.8	589.5	595.0
12.5°	441.2	437.5	435.6	435.6	435.6	435.6	435.6	439.3	443.0	446.7	450.4
15°	355.9	354.0	352.2	350.3	348.5	344.8	342.9	346.6	350.3	354.0	357.8
17.5°	298.4	298.4	298.4	296.6	294.7	292.9	291.0	292.9	294.7	294.7	296.6
20°	255.8	257.7	259.5	261.4	261.4	263.2	263.2	265.1	266.9	266.9	268.8
22.5°	229.9	231.7	231.7	231.7	233.6	233.6	233.6	235.4	237.3	239.1	241.0
25°	209.5	209.5	207.6	207.6	209.5	209.5	209.5	209.5	211.3	211.3	211.3
27.5°	198.3	196.5	196.5	196.5	196.5	194.6	194.6	194.6	194.6	194.6	194.6
30°	192.8	190.9	189.1	187.2	187.2	185.4	183.5	183.5	183.5	183.5	183.5
32.5°	190.9	187.2	183.5	181.7	181.7	179.8	178.0	176.1	176.1	174.2	172.4
35°	170.5	168.7	168.7	166.8	165.0	163.1	161.3	161.3	161.3	159.4	159.4
37.5°	148.3	150.1	150.1	150.1	152.0	152.0	152.0	152.0	153.9	153.9	153.9
40°	139.0	139.0	139.0	140.9	142.7	142.7	144.6	144.6	146.4	146.4	146.4
42.5°	131.6	129.8	129.8	131.6	131.6	133.5	133.5	135.3	137.2	137.2	139.0
45°	127.9	126.0	126.0	126.0	126.0	124.2	124.2	126.0	127.9	129.8	131.6
47.5°	120.5	120.5	118.6	118.6	118.6	118.6	118.6	118.6	120.5	120.5	120.5
50°	116.8	116.8	114.9	114.9	114.9	114.9	114.9	114.9	114.9	114.9	114.9
52.5°	113.1	111.2	111.2	111.2	111.2	109.4	109.4	109.4	109.4	109.4	109.4
55°	107.5	105.7	105.7	105.7	105.7	105.7	105.7	105.7	107.5	107.5	107.5
57.5°	102.0	100.1	100.1	100.1	102.0	102.0	102.0	102.0	103.8	103.8	103.8
60°	96.4	96.4	96.4	96.4	96.4	96.4	96.4	98.2	98.2	100.1	100.1
62.5°	90.8	90.8	90.8	90.8	92.7	92.7	92.7	92.7	94.5	94.5	94.5
65°	85.3	85.3	85.3	85.3	87.1	87.1	87.1	87.1	87.1	87.1	87.1
67.5°	79.7	79.7	79.7	79.7	79.7	79.7	79.7	81.6	81.6	83.4	83.4
70°	72.3	70.4	70.4	72.3	72.3	74.1	74.1	76.0	76.0	77.9	77.9
72.5°	64.9	64.9	64.9	64.9	64.9	64.9	64.9	66.7	68.6	68.6	70.4
75°	57.5	57.5	57.5	57.5	59.3	59.3	59.3	61.2	61.2	63.0	63.0
77.5°	51.9	50.0	50.0	50.0	51.9	51.9	51.9	53.8	53.8	55.6	55.6
80°	42.6	42.6	42.6	42.6	44.5	44.5	44.5	44.5	46.3	46.3	46.3
82.5°	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2	37.1	37.1	37.1
85°	26.0	26.0	26.0	26.0	27.8	27.8	27.8	27.8	27.8	27.8	27.8
87.5°	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7	18.5	18.5	18.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946
 CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675946

CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	1178.9	1178.9	1178.9	1178.9	1182.6	1184.5	1188.2	1190.0	1188.2	1186.3	1182.6
5°	991.7	993.6	993.6	995.4	995.4	995.4	995.4	995.4	999.1	1002.8	1006.5
7.5°	784.1	785.9	787.8	789.7	789.7	789.7	787.8	787.8	789.7	789.7	791.5
10°	600.6	608.0	613.6	619.1	615.4	609.9	606.1	600.6	600.6	600.6	598.7
12.5°	454.1	456.0	459.7	461.6	459.7	459.7	457.9	456.0	457.9	461.6	463.4
15°	359.6	359.6	361.5	361.5	363.3	365.2	365.2	367.0	370.7	372.6	376.3
17.5°	298.4	300.3	300.3	302.1	302.1	304.0	304.0	304.0	307.7	311.4	317.0
20°	268.8	268.8	268.8	268.8	268.8	266.9	266.9	265.1	266.9	270.6	272.5
22.5°	241.0	242.8	242.8	242.8	241.0	239.1	235.4	233.6	233.6	235.4	235.4
25°	211.3	209.5	209.5	207.6	207.6	209.5	209.5	209.5	211.3	211.3	213.2
27.5°	194.6	192.8	192.8	190.9	190.9	192.8	192.8	192.8	192.8	192.8	192.8
30°	181.7	181.7	179.8	178.0	179.8	179.8	181.7	181.7	183.5	183.5	185.4
32.5°	172.4	170.5	170.5	168.7	170.5	170.5	172.4	172.4	174.2	176.1	176.1
35°	159.4	159.4	159.4	159.4	159.4	159.4	157.6	157.6	157.6	157.6	157.6
37.5°	152.0	152.0	150.1	148.3	148.3	148.3	148.3	148.3	146.4	144.6	142.7
40°	146.4	144.6	144.6	142.7	140.9	140.9	139.0	137.2	137.2	135.3	135.3
42.5°	139.0	137.2	137.2	135.3	133.5	133.5	131.6	129.8	129.8	129.8	127.9
45°	129.8	129.8	127.9	126.0	126.0	126.0	124.2	124.2	124.2	124.2	122.3
47.5°	120.5	120.5	118.6	118.6	118.6	118.6	116.8	116.8	116.8	116.8	116.8
50°	114.9	114.9	114.9	114.9	114.9	114.9	113.1	113.1	113.1	113.1	113.1
52.5°	109.4	109.4	109.4	109.4	109.4	109.4	109.4	109.4	109.4	109.4	109.4
55°	107.5	107.5	107.5	107.5	107.5	107.5	105.7	105.7	105.7	107.5	107.5
57.5°	103.8	103.8	102.0	102.0	102.0	102.0	102.0	102.0	102.0	102.0	102.0
60°	100.1	100.1	100.1	100.1	100.1	100.1	100.1	100.1	100.1	100.1	100.1
62.5°	94.5	94.5	94.5	94.5	94.5	96.4	96.4	96.4	96.4	96.4	94.5
65°	87.1	89.0	89.0	89.0	89.0	89.0	89.0	89.0	89.0	89.0	89.0
67.5°	83.4	83.4	83.4	83.4	83.4	83.4	83.4	83.4	83.4	83.4	83.4
70°	77.9	77.9	76.0	76.0	76.0	77.9	77.9	77.9	77.9	77.9	77.9
72.5°	70.4	70.4	70.4	70.4	70.4	70.4	70.4	70.4	70.4	72.3	72.3
75°	63.0	63.0	63.0	63.0	63.0	63.0	63.0	63.0	63.0	63.0	63.0
77.5°	55.6	55.6	53.8	53.8	53.8	55.6	55.6	55.6	55.6	57.5	57.5
80°	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3	48.2	48.2
82.5°	37.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1	38.9	38.9
85°	27.8	29.7	29.7	29.7	29.7	29.7	29.7	29.7	29.7	31.5	31.5
87.5°	18.5	18.5	18.5	18.5	18.5	18.5	16.7	16.7	16.7	16.7	14.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946
 CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946

CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	1180.8	1182.6	1184.5	1184.5	1186.3	1188.2	1188.2	1195.6	1203.0	1206.7	1210.4
5°	1010.2	1008.4	1008.4	1006.5	1004.7	1010.2	1015.8	1026.9	1038.0	1039.9	1043.6
7.5°	791.5	793.4	795.2	795.2	797.1	791.5	784.1	785.9	787.8	797.1	804.5
10°	598.7	600.6	602.4	602.4	604.3	602.4	598.7	604.3	609.9	617.3	626.5
12.5°	465.3	470.8	476.4	480.1	485.7	489.4	491.2	498.6	504.2	513.5	522.7
15°	380.0	383.7	387.4	391.1	394.8	398.5	402.2	409.7	417.1	428.2	439.3
17.5°	320.7	320.7	322.5	322.5	322.5	326.2	330.0	333.7	335.5	346.6	357.8
20°	274.3	272.5	270.6	268.8	266.9	270.6	272.5	274.3	276.2	283.6	289.2
22.5°	235.4	235.4	237.3	237.3	237.3	235.4	231.7	233.6	233.6	237.3	242.8
25°	213.2	213.2	213.2	211.3	211.3	213.2	215.0	215.0	213.2	215.0	216.9
27.5°	192.8	194.6	194.6	196.5	196.5	198.3	198.3	198.3	198.3	200.2	202.0
30°	185.4	185.4	187.2	187.2	187.2	189.1	190.9	190.9	190.9	192.8	196.5
32.5°	178.0	179.8	181.7	183.5	185.4	187.2	187.2	189.1	189.1	190.9	192.8
35°	157.6	155.7	155.7	153.9	152.0	152.0	152.0	152.0	150.1	152.0	152.0
37.5°	140.9	140.9	140.9	139.0	139.0	140.9	140.9	140.9	140.9	142.7	142.7
40°	133.5	133.5	133.5	133.5	133.5	133.5	133.5	135.3	135.3	137.2	139.0
42.5°	127.9	127.9	127.9	127.9	127.9	129.8	129.8	129.8	129.8	131.6	131.6
45°	122.3	122.3	122.3	122.3	122.3	122.3	122.3	124.2	124.2	126.0	127.9
47.5°	116.8	116.8	116.8	116.8	116.8	118.6	120.5	120.5	120.5	122.3	122.3
50°	113.1	113.1	113.1	113.1	113.1	114.9	114.9	116.8	116.8	118.6	120.5
52.5°	109.4	109.4	109.4	109.4	109.4	111.2	111.2	113.1	113.1	114.9	116.8
55°	107.5	107.5	107.5	105.7	105.7	107.5	107.5	109.4	109.4	111.2	111.2
57.5°	102.0	102.0	102.0	102.0	102.0	102.0	102.0	103.8	103.8	105.7	107.5
60°	100.1	100.1	98.2	98.2	96.4	98.2	98.2	100.1	100.1	102.0	102.0
62.5°	94.5	94.5	94.5	92.7	92.7	94.5	94.5	94.5	94.5	96.4	98.2
65°	89.0	89.0	89.0	87.1	87.1	89.0	89.0	89.0	89.0	90.8	92.7
67.5°	83.4	83.4	83.4	81.6	81.6	81.6	81.6	83.4	83.4	85.3	87.1
70°	77.9	77.9	77.9	76.0	76.0	76.0	74.1	76.0	77.9	79.7	79.7
72.5°	72.3	72.3	72.3	70.4	70.4	70.4	68.6	70.4	70.4	72.3	72.3
75°	63.0	63.0	63.0	63.0	63.0	63.0	61.2	61.2	61.2	63.0	63.0
77.5°	57.5	57.5	57.5	55.6	55.6	55.6	53.8	53.8	53.8	55.6	55.6
80°	48.2	48.2	48.2	46.3	46.3	46.3	44.5	44.5	44.5	46.3	46.3
82.5°	38.9	38.9	38.9	37.1	37.1	37.1	35.2	35.2	35.2	37.1	37.1
85°	31.5	31.5	31.5	31.5	31.5	31.5	29.7	29.7	29.7	31.5	33.4
87.5°	14.8	14.8	16.7	16.7	16.7	16.7	14.8	14.8	13.0	13.0	14.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946
 CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946

CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	1214.1	1217.9	1227.1	1234.5	1243.8	1251.2	1256.8	1264.2	1269.8	1275.3	1279.0
5°	1045.5	1047.3	1056.6	1065.9	1073.3	1082.5	1095.5	1108.5	1121.5	1134.4	1143.7
7.5°	813.8	821.2	832.3	845.3	856.4	867.5	880.5	895.3	908.3	921.3	934.2
10°	633.9	641.4	652.5	663.6	672.9	684.0	698.8	713.7	728.5	743.3	758.1
12.5°	532.0	541.3	554.2	567.2	578.3	591.3	609.9	626.5	645.1	661.8	680.3
15°	448.6	459.7	476.4	494.9	511.6	528.3	546.8	565.4	582.0	600.6	619.1
17.5°	368.9	380.0	394.8	411.5	426.3	441.2	463.4	483.8	506.0	526.4	546.8
20°	296.6	302.1	317.0	331.8	346.6	361.5	378.1	394.8	411.5	428.2	454.1
22.5°	246.5	250.2	257.7	263.2	270.6	276.2	292.9	309.6	324.4	341.1	365.2
25°	216.9	218.7	224.3	228.0	233.6	237.3	248.4	257.7	268.8	278.0	300.3
27.5°	202.0	203.9	205.8	207.6	209.5	211.3	218.7	226.1	231.7	239.1	259.5
30°	198.3	200.2	205.8	209.5	215.0	218.7	222.4	226.1	229.9	233.6	246.5
32.5°	194.6	196.5	196.5	194.6	194.6	192.8	196.5	198.3	202.0	203.9	215.0
35°	153.9	153.9	155.7	157.6	159.4	161.3	166.8	170.5	176.1	179.8	189.1
37.5°	144.6	144.6	146.4	150.1	152.0	153.9	157.6	161.3	165.0	168.7	178.0
40°	139.0	140.9	142.7	144.6	146.4	148.3	152.0	153.9	157.6	159.4	166.8
42.5°	133.5	133.5	135.3	139.0	140.9	142.7	146.4	148.3	152.0	153.9	161.3
45°	129.8	131.6	133.5	135.3	135.3	137.2	140.9	144.6	146.4	150.1	157.6
47.5°	124.2	124.2	127.9	129.8	133.5	135.3	139.0	140.9	144.6	146.4	153.9
50°	120.5	122.3	126.0	127.9	131.6	133.5	139.0	142.7	148.3	152.0	155.7
52.5°	116.8	118.6	122.3	124.2	127.9	129.8	137.2	144.6	150.1	157.6	157.6
55°	113.1	113.1	116.8	122.3	126.0	129.8	133.5	139.0	142.7	146.4	146.4
57.5°	107.5	109.4	113.1	118.6	122.3	126.0	129.8	133.5	135.3	139.0	137.2
60°	103.8	103.8	109.4	114.9	120.5	126.0	126.0	126.0	124.2	124.2	124.2
62.5°	98.2	100.1	107.5	116.8	124.2	131.6	126.0	120.5	114.9	109.4	111.2
65°	94.5	96.4	100.1	105.7	109.4	113.1	109.4	107.5	103.8	100.1	102.0
67.5°	87.1	89.0	90.8	90.8	92.7	92.7	92.7	92.7	92.7	92.7	94.5
70°	81.6	81.6	81.6	83.4	83.4	83.4	83.4	83.4	83.4	83.4	85.3
72.5°	74.1	74.1	74.1	74.1	74.1	74.1	74.1	74.1	74.1	74.1	76.0
75°	64.9	64.9	64.9	64.9	64.9	64.9	64.9	64.9	64.9	64.9	66.7
77.5°	57.5	57.5	57.5	57.5	57.5	57.5	57.5	57.5	55.6	55.6	57.5
80°	48.2	48.2	48.2	48.2	46.3	46.3	46.3	46.3	46.3	46.3	48.2
82.5°	38.9	38.9	38.9	38.9	37.1	37.1	37.1	37.1	35.2	35.2	37.1
85°	35.2	37.1	37.1	38.9	38.9	38.9	37.1	35.2	33.4	31.5	31.5
87.5°	14.8	14.8	14.8	14.8	13.0	13.0	13.0	13.0	13.0	13.0	13.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946
 CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675946

CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	1284.6	1288.3	1292.0	1297.6	1305.0	1310.5	1316.1	1327.2	1340.2	1351.3	1362.4
5°	1153.0	1162.2	1171.5	1182.6	1193.8	1203.0	1214.1	1236.4	1258.6	1279.0	1301.3
7.5°	945.4	958.3	969.5	988.0	1004.7	1023.2	1039.9	1067.7	1093.7	1121.5	1147.4
10°	773.0	787.8	802.6	826.7	852.7	876.8	900.9	923.1	947.2	969.5	991.7
12.5°	698.8	715.5	734.0	748.9	765.6	780.4	795.2	821.2	847.1	873.1	899.0
15°	637.7	656.2	674.7	693.3	709.9	728.5	745.2	767.4	791.5	813.8	836.0
17.5°	567.2	585.8	606.1	626.5	646.9	667.3	687.7	719.2	750.7	780.4	811.9
20°	478.2	504.2	528.3	556.1	583.9	611.7	639.5	672.9	706.2	737.8	771.1
22.5°	389.3	413.4	437.5	470.8	504.2	535.7	569.1	613.6	656.2	700.7	743.3
25°	324.4	346.6	368.9	406.0	441.2	478.2	513.5	567.2	619.1	672.9	724.8
27.5°	279.9	300.3	320.7	359.6	398.5	435.6	474.5	533.9	591.3	650.6	708.1
30°	259.5	272.5	285.5	322.5	359.6	394.8	431.9	489.4	546.8	604.3	661.8
32.5°	226.1	237.3	248.4	281.8	315.1	346.6	380.0	439.3	496.8	556.1	613.6
35°	200.2	209.5	218.7	250.2	279.9	311.4	341.1	400.4	459.7	519.0	578.3
37.5°	185.4	194.6	202.0	229.9	259.5	287.3	315.1	374.4	431.9	491.2	548.7
40°	174.2	179.8	187.2	215.0	241.0	268.8	294.7	348.5	404.1	457.9	511.6
42.5°	166.8	174.2	179.8	203.9	229.9	254.0	278.0	330.0	381.9	431.9	483.8
45°	165.0	172.4	179.8	200.2	220.6	239.1	259.5	309.6	359.6	409.7	459.7
47.5°	161.3	166.8	174.2	190.9	205.8	222.4	237.3	287.3	337.4	385.6	435.6
50°	159.4	161.3	165.0	179.8	194.6	209.5	224.3	274.3	324.4	374.4	424.5
52.5°	157.6	157.6	157.6	170.5	183.5	194.6	207.6	257.7	309.6	359.6	409.7
55°	146.4	144.6	144.6	157.6	168.7	181.7	192.8	242.8	292.9	341.1	391.1
57.5°	135.3	133.5	131.6	142.7	153.9	165.0	176.1	226.1	278.0	328.1	378.1
60°	124.2	122.3	122.3	133.5	142.7	153.9	163.1	215.0	265.1	317.0	367.0
62.5°	111.2	113.1	113.1	122.3	133.5	142.7	152.0	203.9	257.7	309.6	361.5
65°	102.0	103.8	103.8	114.9	126.0	137.2	148.3	198.3	250.2	300.3	350.3
67.5°	94.5	96.4	96.4	109.4	120.5	133.5	144.6	189.1	235.4	279.9	324.4
70°	87.1	87.1	89.0	102.0	114.9	127.9	140.9	179.8	218.7	255.8	294.7
72.5°	77.9	79.7	81.6	94.5	105.7	118.6	129.8	165.0	200.2	235.4	270.6
75°	68.6	70.4	72.3	83.4	94.5	105.7	116.8	150.1	181.7	215.0	246.5
77.5°	61.2	63.0	64.9	74.1	83.4	92.7	102.0	126.0	152.0	176.1	200.2
80°	50.0	50.0	51.9	59.3	66.7	72.3	79.7	96.4	113.1	127.9	144.6
82.5°	37.1	38.9	38.9	44.5	48.2	53.8	57.5	66.7	74.1	83.4	90.8
85°	31.5	29.7	29.7	33.4	35.2	38.9	40.8	46.3	50.0	55.6	59.3
87.5°	13.0	11.1	11.1	13.0	16.7	18.5	20.4	20.4	22.2	22.2	22.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946
 CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946

CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	1368.0	1371.7	1377.3	1381.0	1390.2	1397.7	1406.9	1414.3	1419.9	1429.2	1425.5
5°	1317.9	1334.6	1351.3	1368.0	1381.0	1393.9	1405.1	1418.0	1432.9	1460.7	1468.1
7.5°	1169.7	1191.9	1212.3	1234.5	1260.5	1286.4	1312.4	1338.3	1362.4	1397.7	1419.9
10°	1023.2	1054.7	1084.4	1115.9	1140.0	1164.1	1186.3	1210.4	1243.8	1279.0	1319.8
12.5°	930.5	962.0	993.6	1025.1	1060.3	1093.7	1128.9	1162.2	1193.8	1221.6	1267.9
15°	869.4	904.6	937.9	971.3	1013.9	1054.7	1097.4	1138.1	1184.5	1221.6	1253.1
17.5°	854.5	897.2	937.9	980.6	1025.1	1069.6	1114.0	1158.5	1204.9	1260.5	1301.3
20°	828.6	886.0	943.5	1001.0	1058.4	1114.0	1171.5	1227.1	1288.3	1355.0	1373.6
22.5°	813.8	882.3	952.8	1021.4	1099.2	1178.9	1256.8	1334.6	1399.5	1449.6	1505.2
25°	811.9	897.2	984.3	1069.6	1167.8	1264.2	1362.4	1458.8	1542.2	1592.3	1636.8
27.5°	810.0	913.9	1015.8	1117.8	1238.2	1356.9	1477.4	1596.0	1673.9	1746.1	1783.2
30°	787.8	912.0	1038.0	1162.2	1297.6	1432.9	1568.2	1703.5	1783.2	1833.3	1851.8
32.5°	760.0	906.4	1052.9	1199.3	1353.2	1507.0	1659.0	1812.9	1875.9	1918.5	1903.7
35°	737.8	899.0	1058.4	1217.9	1381.0	1545.9	1709.1	1872.2	1963.0	2022.3	1998.2
37.5°	717.4	886.0	1054.7	1223.4	1414.3	1605.3	1796.2	1987.1	2074.2	2137.3	2109.5
40°	693.3	873.1	1054.7	1234.5	1453.3	1670.1	1888.9	2105.8	2218.8	2272.6	2229.9
42.5°	672.9	860.1	1049.2	1236.4	1469.9	1703.5	1937.1	2170.6	2296.7	2372.7	2318.9
45°	646.9	834.1	1019.5	1206.7	1464.4	1722.0	1977.8	2235.5	2381.9	2441.3	2367.1
47.5°	619.1	804.5	988.0	1171.5	1445.9	1720.2	1994.5	2268.9	2404.2	2474.6	2406.0
50°	609.9	795.2	978.7	1164.1	1460.7	1759.1	2055.7	2352.3	2450.5	2508.0	2417.2
52.5°	608.0	804.5	1002.8	1199.3	1497.8	1794.3	2092.8	2389.4	2469.1	2530.2	2448.7
55°	602.4	815.6	1026.9	1238.2	1549.7	1862.9	2174.3	2485.8	2565.5	2609.9	2548.8
57.5°	608.0	837.9	1065.9	1295.7	1616.4	1937.1	2257.8	2578.4	2674.8	2706.3	2693.4
60°	611.7	856.4	1099.2	1343.9	1657.2	1970.4	2283.7	2597.0	2697.1	2774.9	2789.8
62.5°	602.4	843.4	1082.5	1323.5	1607.1	1890.7	2174.3	2457.9	2622.9	2737.8	2804.6
65°	574.6	797.1	1021.4	1243.8	1505.2	1768.4	2029.8	2291.1	2465.4	2635.9	2689.7
67.5°	513.5	702.5	891.6	1080.7	1308.7	1536.7	1762.8	1990.8	2209.6	2374.5	2448.7
70°	444.9	593.2	743.3	891.6	1099.2	1306.8	1514.4	1722.0	1914.8	2096.5	2166.9
72.5°	387.4	502.3	619.1	734.0	882.3	1028.8	1177.1	1323.5	1551.5	1733.2	1801.8
75°	330.0	413.4	494.9	578.3	680.3	782.2	882.3	984.3	1145.6	1308.7	1377.3
77.5°	254.0	309.6	363.3	417.1	487.5	556.1	626.5	695.1	808.2	930.5	965.8
80°	176.1	207.6	237.3	268.8	324.4	380.0	435.6	491.2	565.4	633.9	687.7
82.5°	109.4	129.8	148.3	166.8	211.3	255.8	298.4	342.9	372.6	376.3	430.0
85°	70.4	83.4	94.5	105.7	131.6	159.4	185.4	211.3	189.1	176.1	209.5
87.5°	27.8	35.2	40.8	46.3	44.5	42.6	40.8	38.9	33.4	29.7	37.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946

CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675946

CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	1429.2	1434.7	1440.3	1444.0	1449.6	1451.4	1453.3	1453.3	1455.1	1457.0	1460.7
5°	1497.8	1508.9	1520.0	1529.3	1540.4	1549.7	1557.1	1566.3	1573.8	1573.8	1571.9
7.5°	1440.3	1468.1	1495.9	1523.7	1551.5	1571.9	1590.4	1610.8	1629.4	1633.1	1636.8
10°	1364.3	1393.9	1421.8	1451.4	1479.2	1510.7	1540.4	1570.0	1601.6	1607.1	1614.5
12.5°	1293.9	1329.1	1364.3	1397.7	1432.9	1455.1	1477.4	1497.8	1520.0	1534.8	1549.7
15°	1292.0	1321.7	1351.3	1379.1	1408.8	1421.8	1434.7	1445.9	1458.8	1458.8	1460.7
17.5°	1334.6	1353.2	1371.7	1388.4	1406.9	1408.8	1412.5	1414.3	1416.2	1410.6	1405.1
20°	1418.0	1425.5	1432.9	1440.3	1447.7	1434.7	1423.6	1410.6	1397.7	1382.8	1369.9
22.5°	1540.4	1523.7	1507.0	1490.3	1473.7	1451.4	1427.3	1405.1	1381.0	1362.4	1343.9
25°	1655.3	1634.9	1614.5	1594.1	1573.8	1525.6	1477.4	1427.3	1379.1	1358.7	1338.3
27.5°	1809.2	1777.7	1746.1	1714.6	1683.1	1618.2	1553.4	1488.5	1423.6	1388.4	1355.0
30°	1846.2	1811.0	1775.8	1738.7	1703.5	1640.5	1579.3	1516.3	1453.3	1412.5	1373.6
32.5°	1900.0	1859.2	1818.4	1777.7	1736.9	1675.7	1614.5	1551.5	1490.3	1453.3	1414.3
35°	1989.0	1942.6	1896.3	1848.1	1801.8	1738.7	1677.6	1614.5	1551.5	1508.9	1468.1
37.5°	2065.0	2011.2	1957.5	1903.7	1849.9	1794.3	1736.9	1681.3	1623.8	1581.2	1540.4
40°	2150.2	2090.9	2031.6	1974.1	1914.8	1862.9	1811.0	1757.3	1705.4	1672.0	1638.6
42.5°	2224.4	2152.1	2081.7	2011.2	1938.9	1903.7	1870.3	1835.1	1799.9	1783.2	1764.7
45°	2276.3	2209.6	2141.0	2074.2	2007.5	1981.6	1955.6	1929.7	1903.7	1920.4	1937.1
47.5°	2298.5	2244.8	2192.9	2141.0	2087.2	2096.5	2105.8	2113.2	2122.4	2144.7	2168.8
50°	2318.9	2289.3	2257.8	2228.1	2196.6	2231.8	2265.2	2300.4	2335.6	2381.9	2428.3
52.5°	2359.7	2343.0	2328.2	2311.5	2294.8	2356.0	2417.2	2478.3	2539.5	2591.4	2643.3
55°	2482.0	2469.1	2456.1	2441.3	2428.3	2515.4	2600.7	2687.8	2774.9	2828.7	2882.4
57.5°	2650.7	2643.3	2634.0	2626.6	2617.4	2702.6	2786.0	2869.5	2954.7	3006.6	3060.4
60°	2778.6	2780.5	2780.5	2782.3	2782.3	2847.2	2912.1	2978.8	3043.7	3088.2	3134.5
62.5°	2847.2	2843.5	2839.8	2836.1	2832.4	2886.1	2939.9	2993.7	3047.4	3080.8	3114.1
65°	2773.1	2793.5	2813.8	2834.2	2854.6	2862.0	2867.6	2875.0	2880.6	2901.0	2921.4
67.5°	2524.7	2565.5	2604.4	2645.2	2684.1	2656.3	2630.3	2602.5	2574.7	2580.3	2584.0
70°	2248.5	2294.8	2343.0	2389.4	2435.7	2370.8	2305.9	2239.2	2174.3	2152.1	2129.8
72.5°	1896.3	1937.1	1979.7	2020.5	2061.3	1981.6	1903.7	1824.0	1744.3	1705.4	1666.4
75°	1449.6	1497.8	1547.8	1596.0	1644.2	1555.2	1464.4	1375.4	1284.6	1258.6	1234.5
77.5°	1056.6	1114.0	1171.5	1229.0	1286.4	1206.7	1127.0	1045.5	965.8	950.9	936.1
80°	769.3	813.8	856.4	900.9	943.5	897.2	850.8	804.5	758.1	756.3	754.4
82.5°	519.0	558.0	595.0	633.9	671.0	652.5	635.8	617.3	598.7	617.3	637.7
85°	266.9	320.7	376.3	430.0	483.8	478.2	474.5	469.0	463.4	487.5	509.8
87.5°	53.8	100.1	146.4	190.9	237.3	226.1	215.0	202.0	190.9	198.3	203.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946
 CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675946

CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	1462.5	1464.4	1464.4	1464.4	1464.4	1464.4	1460.7	1458.8	1455.1	1451.4	1445.9
5°	1571.9	1570.0	1562.6	1555.2	1545.9	1538.5	1533.0	1525.6	1520.0	1512.6	1501.5
7.5°	1640.5	1644.2	1631.2	1620.1	1607.1	1594.1	1581.2	1568.2	1555.2	1542.2	1516.3
10°	1620.1	1625.7	1618.2	1610.8	1601.6	1594.1	1579.3	1562.6	1547.8	1531.1	1499.6
12.5°	1562.6	1577.5	1573.8	1570.0	1566.3	1562.6	1553.4	1542.2	1533.0	1521.9	1486.6
15°	1460.7	1460.7	1462.5	1464.4	1464.4	1466.2	1468.1	1469.9	1471.8	1473.7	1453.3
17.5°	1399.5	1393.9	1393.9	1393.9	1393.9	1393.9	1401.4	1410.6	1418.0	1425.5	1419.9
20°	1355.0	1342.0	1340.2	1340.2	1338.3	1336.5	1349.5	1364.3	1377.3	1390.2	1397.7
22.5°	1325.4	1306.8	1305.0	1303.1	1301.3	1299.4	1316.1	1332.8	1349.5	1366.1	1392.1
25°	1317.9	1297.6	1299.4	1301.3	1301.3	1303.1	1316.1	1329.1	1342.0	1355.0	1399.5
27.5°	1319.8	1286.4	1288.3	1290.1	1290.1	1292.0	1312.4	1330.9	1351.3	1369.9	1425.5
30°	1332.8	1293.9	1290.1	1286.4	1282.7	1279.0	1306.8	1334.6	1362.4	1390.2	1432.9
32.5°	1377.3	1340.2	1330.9	1321.7	1312.4	1303.1	1336.5	1368.0	1401.4	1432.9	1468.1
35°	1425.5	1384.7	1381.0	1377.3	1371.7	1368.0	1397.7	1429.2	1458.8	1488.5	1520.0
37.5°	1497.8	1457.0	1453.3	1447.7	1444.0	1438.4	1471.8	1503.3	1536.7	1568.2	1596.0
40°	1605.3	1571.9	1570.0	1570.0	1568.2	1566.3	1592.3	1620.1	1646.0	1672.0	1690.5
42.5°	1748.0	1731.3	1736.9	1744.3	1749.9	1755.4	1775.8	1798.0	1818.4	1838.8	1833.3
45°	1953.8	1970.4	1972.3	1974.1	1976.0	1977.8	1983.4	1990.8	1996.4	2001.9	1979.7
47.5°	2191.0	2213.3	2224.4	2235.5	2244.8	2255.9	2248.5	2239.2	2231.8	2222.5	2166.9
50°	2472.8	2519.1	2517.3	2515.4	2511.7	2509.8	2495.0	2480.2	2463.5	2448.7	2367.1
52.5°	2695.2	2747.1	2756.4	2765.7	2774.9	2784.2	2756.4	2728.6	2698.9	2671.1	2569.2
55°	2934.3	2988.1	2989.9	2991.8	2991.8	2993.7	2954.7	2915.8	2875.0	2836.1	2730.4
57.5°	3112.3	3164.2	3158.6	3154.9	3149.4	3143.8	3097.5	3051.1	3004.8	2958.4	2852.8
60°	3179.0	3223.5	3212.4	3201.3	3188.3	3177.2	3141.9	3106.7	3069.7	3034.4	2932.5
62.5°	3147.5	3180.9	3164.2	3149.4	3132.7	3116.0	3071.5	3025.2	2980.7	2934.3	2860.2
65°	2939.9	2960.3	2938.0	2917.7	2897.3	2875.0	2837.9	2800.9	2761.9	2724.9	2674.8
67.5°	2589.6	2593.3	2591.4	2589.6	2587.7	2585.8	2532.1	2478.3	2422.7	2369.0	2365.3
70°	2109.5	2087.2	2090.9	2096.5	2100.2	2103.9	2063.1	2024.2	1983.4	1942.6	1961.2
72.5°	1627.5	1588.6	1597.9	1609.0	1618.2	1627.5	1594.1	1562.6	1529.3	1495.9	1521.9
75°	1208.6	1184.5	1193.8	1204.9	1214.1	1223.4	1210.4	1197.5	1182.6	1169.7	1193.8
77.5°	921.3	906.4	908.3	908.3	910.1	910.1	912.0	915.7	917.6	919.4	945.4
80°	750.7	748.9	747.0	745.2	741.5	739.6	758.1	776.7	795.2	813.8	826.7
82.5°	656.2	674.7	663.6	654.3	643.2	632.1	648.8	665.5	682.1	698.8	693.3
85°	533.9	556.1	535.7	515.3	493.1	472.7	487.5	500.5	515.3	528.3	520.9
87.5°	211.3	216.9	183.5	152.0	118.6	85.3	135.3	183.5	233.6	281.8	289.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946
 CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946

CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6	1334.6
2.5°	1440.3	1432.9	1427.3	1425.5	1421.8	1419.9	1416.2	1412.5	1406.9	1403.2	1397.7
5°	1488.5	1477.4	1464.4	1445.9	1429.2	1410.6	1392.1	1375.4	1358.7	1340.2	1323.5
7.5°	1490.3	1464.4	1438.4	1414.3	1388.4	1364.3	1338.3	1316.1	1292.0	1267.9	1245.7
10°	1469.9	1438.4	1406.9	1375.4	1345.8	1314.2	1282.7	1256.8	1229.0	1201.2	1175.2
12.5°	1453.3	1418.0	1382.8	1345.8	1310.5	1273.5	1236.4	1210.4	1184.5	1158.5	1132.6
15°	1432.9	1410.6	1390.2	1356.9	1323.5	1290.1	1256.8	1221.6	1188.2	1153.0	1117.8
17.5°	1416.2	1410.6	1405.1	1382.8	1360.6	1336.5	1314.2	1279.0	1243.8	1206.7	1171.5
20°	1406.9	1414.3	1421.8	1410.6	1399.5	1386.5	1375.4	1349.5	1323.5	1295.7	1269.8
22.5°	1418.0	1445.9	1471.8	1473.7	1477.4	1479.2	1481.1	1457.0	1432.9	1406.9	1382.8
25°	1444.0	1488.5	1533.0	1557.1	1581.2	1607.1	1631.2	1616.4	1601.6	1586.7	1571.9
27.5°	1479.2	1534.8	1590.4	1625.7	1659.0	1694.2	1729.5	1727.6	1725.8	1722.0	1720.2
30°	1473.7	1516.3	1558.9	1601.6	1644.2	1686.8	1729.5	1751.7	1772.1	1794.3	1816.6
32.5°	1505.2	1540.4	1577.5	1621.9	1666.4	1712.8	1757.3	1803.6	1848.1	1894.4	1940.8
35°	1553.4	1584.9	1618.2	1666.4	1716.5	1764.7	1814.7	1870.3	1927.8	1985.3	2040.9
37.5°	1625.7	1653.5	1683.1	1723.9	1766.5	1807.3	1849.9	1931.5	2013.1	2096.5	2178.0
40°	1709.1	1727.6	1746.1	1785.1	1824.0	1862.9	1901.8	2003.8	2105.8	2207.7	2309.7
42.5°	1829.6	1824.0	1818.4	1849.9	1883.3	1914.8	1948.2	2040.9	2133.6	2226.2	2318.9
45°	1957.5	1935.2	1913.0	1927.8	1944.5	1959.3	1976.0	2070.5	2165.1	2261.5	2356.0
47.5°	2111.3	2055.7	2000.1	1987.1	1974.1	1959.3	1946.3	2048.3	2150.2	2254.0	2356.0
50°	2285.6	2202.1	2120.6	2087.2	2052.0	2018.6	1983.4	2066.8	2152.1	2237.4	2320.8
52.5°	2467.2	2363.4	2261.5	2209.6	2157.7	2103.9	2052.0	2122.4	2194.7	2267.0	2337.5
55°	2622.9	2517.3	2409.8	2348.6	2287.4	2226.2	2165.1	2235.5	2305.9	2376.4	2446.8
57.5°	2747.1	2641.5	2535.8	2478.3	2419.0	2361.6	2302.2	2369.0	2437.6	2506.1	2572.9
60°	2832.4	2730.4	2628.5	2572.9	2517.3	2461.7	2406.0	2485.8	2565.5	2647.0	2726.7
62.5°	2787.9	2713.8	2639.6	2615.5	2591.4	2565.5	2541.4	2617.4	2691.5	2767.5	2843.5
65°	2624.8	2574.7	2524.7	2548.8	2574.7	2598.8	2624.8	2674.8	2724.9	2776.8	2826.8
67.5°	2359.7	2356.0	2350.4	2404.2	2457.9	2513.6	2567.3	2600.7	2632.2	2665.6	2698.9
70°	1979.7	2000.1	2018.6	2111.3	2204.0	2296.7	2389.4	2402.3	2415.3	2428.3	2441.3
72.5°	1549.7	1575.6	1603.4	1725.8	1846.2	1968.6	2090.9	2083.5	2076.1	2066.8	2059.4
75°	1219.7	1243.8	1269.8	1382.8	1495.9	1609.0	1722.0	1690.5	1660.9	1629.4	1597.9
77.5°	973.2	999.1	1026.9	1132.6	1238.2	1345.8	1451.4	1375.4	1299.4	1223.4	1147.4
80°	837.9	850.8	861.9	934.2	1004.7	1077.0	1149.3	1071.4	991.7	912.0	834.1
82.5°	687.7	680.3	674.7	717.4	760.0	802.6	845.3	771.1	697.0	621.0	546.8
85°	513.5	506.0	498.6	520.9	543.1	567.2	589.5	504.2	418.9	331.8	246.5
87.5°	298.4	305.9	313.3	337.4	361.5	387.4	411.5	324.4	237.3	148.3	61.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946
 CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675946
 CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1334.6	1334.6
2.5°	1386.5	1377.3
5°	1310.5	1297.6
7.5°	1227.1	1210.4
10°	1151.1	1128.9
12.5°	1102.9	1075.1
15°	1084.4	1051.0
17.5°	1140.0	1108.5
20°	1225.3	1182.6
22.5°	1329.1	1277.2
25°	1508.9	1445.9
27.5°	1655.3	1590.4
30°	1746.1	1675.7
32.5°	1846.2	1753.6
35°	1950.0	1861.1
37.5°	2076.1	1976.0
40°	2205.8	2102.0
42.5°	2250.3	2183.6
45°	2293.0	2229.9
47.5°	2302.2	2250.3
50°	2311.5	2304.1
52.5°	2337.5	2335.6
55°	2448.7	2450.5
57.5°	2585.8	2597.0
60°	2711.9	2698.9
62.5°	2776.8	2710.0
65°	2732.3	2639.6
67.5°	2598.8	2498.7
70°	2305.9	2170.6
72.5°	1940.8	1822.1
75°	1495.9	1395.8
77.5°	1064.0	980.6
80°	748.9	665.5
82.5°	480.1	413.4
85°	216.9	189.1
87.5°	61.2	59.3
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P675946
CATALOG NUMBER: CCW-SA-1E-722-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)