

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675950

Luminaire Tested: **CCW-SA-2C-722-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P675950
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2C-722-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @615mA w/
SLR distribution lens
Light Source: (32) 2200K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5526.9 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 7.8 fc

Type IV - Short - N/A

REPORT NUMBER: P675950
CATALOG NUMBER: CCW-SA-2C-722-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1137.2	0.0	1137.2
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	4389.7	0.0	4389.7
	% Fixture	79.4	0.0	79.4
Total	Lumens	5526.9	0.0	5526.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.1	2.5
10°-20°	289.6	5.2
20°-30°	423.6	7.7
30°-40°	596.8	10.8
40°-50°	820.1	14.8
50°-60°	1117.8	20.2
60°-70°	1223.5	22.1
70°-80°	706.6	12.8
80°-90°	211.8	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5526.9	100.0
0°-180°	5526.9	100.0

Coefficient of Utilization



REPORT NUMBER: P675950


CATALOG NUMBER: CCW-SA-2C-722-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	567.6	10.3			
FM	(30°-60°)	2017.0	36.5			
FH	(60°-80°)	1625.3	29.4			G1/1800
FVH	(80°-90°)	179.9	3.3			G2/225
BL	(0°-30°)	282.7	5.1	B1/500		
BM	(30°-60°)	517.8	9.4	B1/1000		
BH	(60°-80°)	304.8	5.5	B1/500		G1/500
BVH	(80°-90°)	31.9	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0
2.5°	1821.3	1811.5	1804.2	1796.8	1787.0	1779.7	1769.9	1760.1	1747.8	1738.0	1725.7
5°	1715.9	1686.5	1657.1	1639.9	1620.3	1603.2	1583.6	1561.5	1539.4	1514.9	1492.9
7.5°	1600.7	1564.0	1527.2	1497.8	1465.9	1436.5	1404.6	1377.7	1350.7	1323.7	1296.8
10°	1492.9	1458.5	1424.2	1387.5	1348.2	1311.5	1272.2	1235.5	1198.7	1161.9	1125.2
12.5°	1421.8	1380.1	1340.9	1299.2	1260.0	1218.3	1176.6	1142.3	1108.0	1071.2	1036.9
15°	1389.9	1350.7	1313.9	1272.2	1230.6	1188.9	1147.2	1108.0	1071.2	1032.0	992.8
17.5°	1465.9	1409.5	1353.1	1299.2	1245.3	1191.3	1137.4	1088.4	1039.4	990.3	941.3
20°	1564.0	1492.9	1424.2	1358.0	1289.4	1223.2	1154.6	1085.9	1017.3	948.7	880.0
22.5°	1689.0	1608.1	1529.6	1443.8	1355.6	1269.8	1181.5	1095.7	1010.0	921.7	835.9
25°	1912.0	1816.4	1720.8	1598.3	1473.3	1350.7	1225.7	1112.9	1002.6	889.8	777.1
27.5°	2103.2	1973.3	1845.9	1698.8	1551.7	1404.6	1257.5	1127.6	1000.1	870.2	740.3
30°	2216.0	2088.5	1961.1	1782.1	1605.6	1426.7	1247.7	1103.1	960.9	816.3	671.7
32.5°	2319.0	2176.8	2034.6	1838.5	1639.9	1443.8	1245.3	1085.9	929.1	769.7	610.4
35°	2461.1	2304.3	2149.8	1921.8	1693.9	1465.9	1237.9	1073.7	907.0	742.8	576.1
37.5°	2613.1	2419.5	2228.3	1975.8	1723.3	1470.8	1218.3	1056.5	894.7	732.9	571.2
40°	2779.8	2544.5	2311.6	2032.2	1755.2	1475.7	1196.3	1034.5	872.7	708.4	546.6
42.5°	2887.7	2632.7	2377.8	2076.3	1777.2	1475.7	1174.2	1014.9	855.5	693.7	534.4
45°	2949.0	2701.4	2456.2	2130.2	1804.2	1478.2	1152.1	995.2	838.4	679.0	522.1
47.5°	2975.9	2745.5	2515.1	2171.9	1831.1	1488.0	1144.8	985.4	823.6	664.3	502.5
50°	3047.0	2843.6	2640.1	2272.4	1907.1	1539.4	1171.7	1000.1	831.0	659.4	487.8
52.5°	3088.7	2914.6	2740.6	2363.1	1985.6	1608.1	1230.6	1039.4	848.2	657.0	465.8
55°	3240.7	3074.0	2907.3	2505.3	2100.8	1698.8	1294.3	1083.5	872.7	659.4	448.6
57.5°	3434.3	3257.8	3083.8	2649.9	2216.0	1782.1	1348.2	1122.7	894.7	669.2	441.2
60°	3569.1	3397.6	3228.4	2767.6	2304.3	1843.4	1380.1	1144.8	909.4	671.7	436.3
62.5°	3583.9	3363.2	3145.1	2696.5	2247.9	1796.8	1348.2	1120.3	892.3	661.9	433.9
65°	3490.7	3233.3	2975.9	2546.9	2118.0	1689.0	1260.0	1051.6	843.3	632.4	424.1
67.5°	3304.4	3002.9	2701.4	2309.2	1916.9	1524.7	1132.5	953.6	777.1	598.1	419.2
70°	2870.5	2605.8	2343.5	2002.7	1664.5	1323.7	983.0	835.9	691.3	544.2	397.1
72.5°	2409.7	2162.1	1916.9	1639.9	1365.4	1088.4	811.4	701.1	590.8	478.0	367.7
75°	1845.9	1659.6	1475.7	1269.8	1063.9	855.5	649.6	568.7	487.8	406.9	326.0
77.5°	1296.8	1196.3	1098.2	943.8	789.3	634.9	480.5	426.5	372.6	318.7	264.7
80°	880.0	823.6	769.7	659.4	549.1	436.3	326.0	291.7	254.9	220.6	183.9
82.5°	546.6	544.2	539.3	463.3	387.3	311.3	235.3	205.9	178.9	149.5	120.1
85°	250.0	291.7	330.9	289.3	247.6	205.9	164.2	144.6	125.0	103.0	83.3
87.5°	78.4	95.6	110.3	105.4	98.1	93.2	85.8	73.5	61.3	49.0	36.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0
2.5°	1715.9	1708.6	1698.8	1689.0	1676.7	1666.9	1654.7	1642.4	1639.9	1635.0	1632.6
5°	1478.2	1463.4	1446.3	1431.6	1416.9	1399.7	1385.0	1367.8	1355.6	1340.9	1328.6
7.5°	1269.8	1245.3	1218.3	1191.3	1166.8	1142.3	1115.4	1090.8	1078.6	1066.3	1054.1
10°	1103.1	1078.6	1056.5	1032.0	1014.9	1000.1	983.0	965.8	951.1	936.4	921.7
12.5°	1019.8	1002.6	985.4	968.3	948.7	931.5	911.9	892.3	875.1	860.4	843.3
15°	968.3	943.8	916.8	892.3	865.3	840.8	813.8	786.9	767.3	750.1	730.5
17.5°	907.0	870.2	835.9	799.1	769.7	740.3	708.4	679.0	657.0	632.4	610.4
20°	838.4	796.7	752.6	710.9	676.6	644.7	610.4	576.1	551.6	524.6	500.1
22.5°	779.5	725.6	669.2	612.8	576.1	539.3	500.1	463.3	441.2	416.7	394.7
25°	715.8	657.0	595.7	534.4	497.6	458.4	421.6	382.4	365.2	350.5	333.4
27.5°	681.5	622.6	561.4	502.5	468.2	431.4	397.1	360.3	348.1	333.4	321.1
30°	612.8	556.5	497.6	438.8	414.3	392.2	367.7	343.2	338.3	335.8	330.9
32.5°	551.6	492.7	433.9	375.1	353.0	330.9	308.9	286.8	284.4	279.5	277.0
35°	519.7	463.3	404.5	348.1	328.5	306.4	286.8	264.7	259.8	252.5	247.6
37.5°	512.3	453.5	392.2	333.4	313.8	294.2	272.1	252.5	247.6	242.7	237.8
40°	492.7	436.3	382.4	326.0	306.4	286.8	264.7	245.1	240.2	235.3	230.4
42.5°	478.0	424.1	367.7	311.3	294.2	277.0	257.4	240.2	235.3	230.4	223.1
45°	465.8	409.4	350.5	294.2	281.9	269.6	254.9	242.7	237.8	230.4	225.5
47.5°	446.1	392.2	335.8	279.5	267.2	257.4	245.1	232.9	228.0	223.1	218.2
50°	431.4	375.1	318.7	262.3	252.5	242.7	232.9	223.1	223.1	225.5	225.5
52.5°	411.8	357.9	304.0	250.0	240.2	230.4	220.6	210.8	213.3	215.7	218.2
55°	394.7	343.2	289.3	235.3	225.5	215.7	203.5	193.7	196.1	198.6	201.0
57.5°	387.3	333.4	279.5	225.5	215.7	203.5	193.7	181.4	181.4	181.4	181.4
60°	382.4	326.0	272.1	215.7	203.5	193.7	181.4	169.1	166.7	166.7	164.2
62.5°	380.0	323.6	269.6	213.3	198.6	186.3	171.6	156.9	154.4	152.0	149.5
65°	370.2	318.7	264.7	210.8	193.7	178.9	161.8	144.6	142.2	142.2	139.7
67.5°	367.7	313.8	262.3	208.4	191.2	171.6	154.4	134.8	132.4	129.9	127.5
70°	348.1	301.5	252.5	203.5	183.9	166.7	147.1	127.5	125.0	120.1	117.7
72.5°	323.6	281.9	237.8	193.7	174.0	154.4	134.8	115.2	112.8	110.3	105.4
75°	286.8	247.6	208.4	169.1	152.0	137.3	120.1	103.0	100.5	98.1	93.2
77.5°	235.3	203.5	174.0	142.2	129.9	117.7	105.4	93.2	90.7	88.2	83.3
80°	166.7	147.1	129.9	110.3	103.0	93.2	85.8	76.0	76.0	73.5	73.5
82.5°	110.3	100.5	90.7	80.9	76.0	71.1	66.2	61.3	61.3	58.8	58.8
85°	78.4	73.5	66.2	61.3	58.8	53.9	51.5	46.6	46.6	46.6	46.6
87.5°	36.8	36.8	34.3	34.3	31.9	31.9	29.4	27.0	27.0	27.0	27.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0
2.5°	1627.7	1620.3	1613.0	1603.2	1595.8	1586.0	1573.8	1564.0	1551.7	1551.7	1549.2
5°	1313.9	1306.6	1299.2	1289.4	1282.0	1272.2	1264.9	1255.1	1245.3	1245.3	1242.8
7.5°	1041.8	1027.1	1012.4	995.2	980.5	970.7	960.9	948.7	938.9	931.5	924.2
10°	907.0	892.3	875.1	860.4	843.3	831.0	818.7	804.0	791.8	782.0	772.2
12.5°	826.1	808.9	791.8	774.6	757.5	740.3	725.6	708.4	691.3	679.0	666.8
15°	710.9	693.7	676.6	659.4	642.3	622.6	603.0	581.0	561.4	551.6	544.2
17.5°	585.9	568.7	549.1	531.9	512.3	497.6	482.9	468.2	453.5	443.7	436.3
20°	473.1	453.5	433.9	414.3	394.7	384.9	375.1	365.2	355.4	348.1	343.2
22.5°	370.2	357.9	348.1	335.8	323.6	316.2	311.3	304.0	296.6	296.6	296.6
25°	316.2	308.9	304.0	296.6	289.3	286.8	284.4	279.5	277.0	274.5	274.5
27.5°	306.4	299.1	291.7	284.4	277.0	274.5	272.1	267.2	264.7	264.7	264.7
30°	326.0	323.6	321.1	318.7	316.2	311.3	304.0	299.1	291.7	286.8	281.9
32.5°	272.1	269.6	269.6	267.2	264.7	269.6	272.1	277.0	279.5	281.9	284.4
35°	240.2	235.3	230.4	225.5	220.6	218.2	215.7	213.3	210.8	210.8	208.4
37.5°	232.9	228.0	223.1	218.2	213.3	210.8	208.4	205.9	203.5	203.5	201.0
40°	225.5	220.6	218.2	213.3	208.4	205.9	203.5	198.6	196.1	193.7	193.7
42.5°	218.2	215.7	210.8	208.4	203.5	201.0	198.6	193.7	191.2	188.8	186.3
45°	218.2	213.3	208.4	203.5	198.6	196.1	191.2	188.8	183.9	183.9	181.4
47.5°	213.3	208.4	203.5	198.6	193.7	191.2	186.3	183.9	178.9	176.5	174.0
50°	225.5	218.2	208.4	201.0	191.2	188.8	183.9	181.4	176.5	174.0	171.6
52.5°	220.6	213.3	203.5	196.1	186.3	181.4	178.9	174.0	169.1	166.7	164.2
55°	203.5	196.1	191.2	183.9	176.5	171.6	166.7	161.8	156.9	154.4	154.4
57.5°	181.4	178.9	176.5	174.0	171.6	166.7	161.8	154.4	149.5	147.1	144.6
60°	161.8	164.2	166.7	169.1	171.6	164.2	156.9	149.5	142.2	139.7	137.3
62.5°	147.1	152.0	156.9	159.3	164.2	156.9	149.5	142.2	134.8	132.4	129.9
65°	137.3	139.7	139.7	142.2	142.2	137.3	134.8	129.9	125.0	122.6	122.6
67.5°	125.0	125.0	125.0	122.6	122.6	120.1	120.1	117.7	115.2	112.8	112.8
70°	112.8	112.8	112.8	110.3	110.3	107.9	107.9	105.4	103.0	103.0	100.5
72.5°	103.0	103.0	100.5	100.5	98.1	98.1	98.1	95.6	95.6	93.2	93.2
75°	90.7	90.7	88.2	88.2	85.8	85.8	85.8	83.3	83.3	83.3	80.9
77.5°	80.9	80.9	78.4	78.4	76.0	76.0	76.0	73.5	73.5	71.1	71.1
80°	71.1	71.1	68.6	68.6	66.2	66.2	63.7	63.7	61.3	61.3	58.8
82.5°	56.4	56.4	56.4	56.4	56.4	53.9	53.9	51.5	49.0	49.0	46.6
85°	46.6	46.6	46.6	44.1	44.1	44.1	41.7	41.7	39.2	36.8	36.8
87.5°	27.0	27.0	27.0	24.5	24.5	24.5	24.5	24.5	24.5	24.5	22.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950
 CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0
2.5°	1549.2	1546.8	1537.0	1527.2	1537.0	1546.8	1546.8	1546.8	1544.3	1544.3	1544.3
5°	1242.8	1240.4	1235.5	1230.6	1230.6	1228.1	1233.0	1237.9	1242.8	1247.7	1252.6
7.5°	914.3	907.0	899.6	892.3	897.2	899.6	907.0	911.9	919.3	924.2	936.4
10°	762.4	752.6	745.2	737.9	732.9	728.0	723.1	720.7	715.8	710.9	715.8
12.5°	652.1	639.8	627.5	612.8	610.4	607.9	603.0	598.1	593.2	588.3	585.9
15°	534.4	524.6	519.7	512.3	502.5	492.7	487.8	485.4	480.5	475.6	473.1
17.5°	426.5	416.7	409.4	402.0	399.6	394.7	394.7	394.7	394.7	394.7	394.7
20°	335.8	328.5	328.5	326.0	326.0	323.6	326.0	328.5	328.5	330.9	333.4
22.5°	294.2	294.2	291.7	289.3	291.7	291.7	294.2	296.6	299.1	301.5	304.0
25°	272.1	269.6	272.1	274.5	274.5	274.5	277.0	277.0	279.5	279.5	279.5
27.5°	262.3	262.3	264.7	264.7	267.2	267.2	267.2	264.7	264.7	262.3	262.3
30°	277.0	272.1	272.1	272.1	269.6	267.2	264.7	264.7	262.3	259.8	257.4
32.5°	286.8	289.3	286.8	281.9	279.5	274.5	272.1	267.2	264.7	259.8	254.9
35°	208.4	205.9	210.8	213.3	215.7	218.2	220.6	223.1	223.1	225.5	225.5
37.5°	201.0	198.6	198.6	196.1	196.1	196.1	196.1	196.1	193.7	193.7	196.1
40°	191.2	188.8	188.8	186.3	186.3	183.9	183.9	183.9	183.9	183.9	183.9
42.5°	183.9	181.4	181.4	181.4	181.4	178.9	178.9	176.5	176.5	174.0	174.0
45°	181.4	178.9	176.5	174.0	174.0	171.6	171.6	171.6	169.1	169.1	169.1
47.5°	171.6	169.1	169.1	166.7	166.7	164.2	164.2	164.2	161.8	161.8	161.8
50°	166.7	164.2	164.2	161.8	161.8	159.3	159.3	159.3	156.9	156.9	156.9
52.5°	159.3	156.9	156.9	156.9	154.4	152.0	152.0	152.0	149.5	149.5	149.5
55°	152.0	149.5	149.5	149.5	147.1	144.6	144.6	144.6	142.2	142.2	142.2
57.5°	142.2	139.7	139.7	137.3	137.3	137.3	137.3	137.3	134.8	134.8	134.8
60°	134.8	132.4	132.4	129.9	129.9	127.5	127.5	127.5	127.5	127.5	127.5
62.5°	127.5	125.0	122.6	120.1	122.6	122.6	122.6	122.6	120.1	120.1	120.1
65°	120.1	117.7	115.2	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8
67.5°	110.3	107.9	105.4	103.0	105.4	105.4	105.4	105.4	105.4	105.4	105.4
70°	100.5	98.1	98.1	95.6	95.6	93.2	93.2	95.6	95.6	95.6	95.6
72.5°	90.7	88.2	88.2	85.8	85.8	85.8	85.8	85.8	85.8	85.8	85.8
75°	80.9	78.4	78.4	76.0	76.0	76.0	76.0	76.0	76.0	76.0	76.0
77.5°	68.6	66.2	66.2	66.2	66.2	66.2	66.2	68.6	68.6	68.6	68.6
80°	58.8	56.4	56.4	56.4	56.4	56.4	56.4	56.4	56.4	56.4	56.4
82.5°	46.6	44.1	44.1	44.1	44.1	44.1	44.1	44.1	44.1	44.1	44.1
85°	34.3	31.9	31.9	31.9	34.3	34.3	34.3	34.3	34.3	34.3	34.3
87.5°	22.1	19.6	19.6	19.6	22.1	22.1	22.1	22.1	19.6	19.6	19.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0
2.5°	1544.3	1544.3	1544.3	1541.9	1539.4	1537.0	1534.5	1541.9	1546.8	1554.1	1559.0
5°	1255.1	1260.0	1262.4	1269.8	1277.1	1284.5	1291.9	1296.8	1301.7	1304.1	1309.0
7.5°	946.2	958.5	968.3	978.1	987.9	995.2	1005.0	1012.4	1019.8	1027.1	1034.5
10°	718.2	723.1	725.6	735.4	742.8	752.6	759.9	767.3	774.6	779.5	786.9
12.5°	583.4	578.5	576.1	576.1	576.1	576.1	576.1	581.0	585.9	590.8	595.7
15°	470.7	468.2	465.8	463.3	460.9	455.9	453.5	458.4	463.3	468.2	473.1
17.5°	394.7	394.7	394.7	392.2	389.8	387.3	384.9	387.3	389.8	389.8	392.2
20°	338.3	340.7	343.2	345.6	345.6	348.1	348.1	350.5	353.0	353.0	355.4
22.5°	304.0	306.4	306.4	306.4	308.9	308.9	308.9	311.3	313.8	316.2	318.7
25°	277.0	277.0	274.5	274.5	277.0	277.0	277.0	277.0	279.5	279.5	279.5
27.5°	262.3	259.8	259.8	259.8	259.8	257.4	257.4	257.4	257.4	257.4	257.4
30°	254.9	252.5	250.0	247.6	247.6	245.1	242.7	242.7	242.7	242.7	242.7
32.5°	252.5	247.6	242.7	240.2	240.2	237.8	235.3	232.9	232.9	230.4	228.0
35°	225.5	223.1	223.1	220.6	218.2	215.7	213.3	213.3	213.3	210.8	210.8
37.5°	196.1	198.6	198.6	198.6	201.0	201.0	201.0	201.0	203.5	203.5	203.5
40°	183.9	183.9	183.9	186.3	188.8	188.8	191.2	191.2	193.7	193.7	193.7
42.5°	174.0	171.6	171.6	174.0	174.0	176.5	176.5	178.9	181.4	181.4	183.9
45°	169.1	166.7	166.7	166.7	166.7	164.2	164.2	166.7	169.1	171.6	174.0
47.5°	159.3	159.3	156.9	156.9	156.9	156.9	156.9	156.9	159.3	159.3	159.3
50°	154.4	154.4	152.0	152.0	152.0	152.0	152.0	152.0	152.0	152.0	152.0
52.5°	149.5	147.1	147.1	147.1	147.1	144.6	144.6	144.6	144.6	144.6	144.6
55°	142.2	139.7	139.7	139.7	139.7	139.7	139.7	139.7	142.2	142.2	142.2
57.5°	134.8	132.4	132.4	132.4	134.8	134.8	134.8	134.8	137.3	137.3	137.3
60°	127.5	127.5	127.5	127.5	127.5	127.5	127.5	129.9	129.9	132.4	132.4
62.5°	120.1	120.1	120.1	120.1	122.6	122.6	122.6	122.6	125.0	125.0	125.0
65°	112.8	112.8	112.8	112.8	115.2	115.2	115.2	115.2	115.2	115.2	115.2
67.5°	105.4	105.4	105.4	105.4	105.4	105.4	105.4	107.9	107.9	110.3	110.3
70°	95.6	93.2	93.2	95.6	95.6	98.1	98.1	100.5	100.5	103.0	103.0
72.5°	85.8	85.8	85.8	85.8	85.8	85.8	85.8	88.2	90.7	90.7	93.2
75°	76.0	76.0	76.0	76.0	78.4	78.4	78.4	80.9	80.9	83.3	83.3
77.5°	68.6	66.2	66.2	66.2	68.6	68.6	68.6	71.1	71.1	73.5	73.5
80°	56.4	56.4	56.4	56.4	58.8	58.8	58.8	58.8	61.3	61.3	61.3
82.5°	46.6	46.6	46.6	46.6	46.6	46.6	46.6	46.6	49.0	49.0	49.0
85°	34.3	34.3	34.3	34.3	36.8	36.8	36.8	36.8	36.8	36.8	36.8
87.5°	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	24.5	24.5	24.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950
 CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0
2.5°	1559.0	1559.0	1559.0	1559.0	1564.0	1566.4	1571.3	1573.8	1571.3	1568.9	1564.0
5°	1311.5	1313.9	1313.9	1316.4	1316.4	1316.4	1316.4	1316.4	1321.3	1326.2	1331.1
7.5°	1036.9	1039.4	1041.8	1044.3	1044.3	1044.3	1041.8	1041.8	1044.3	1044.3	1046.7
10°	794.2	804.0	811.4	818.7	813.8	806.5	801.6	794.2	794.2	794.2	791.8
12.5°	600.6	603.0	607.9	610.4	607.9	607.9	605.5	603.0	605.5	610.4	612.8
15°	475.6	475.6	478.0	478.0	480.5	482.9	482.9	485.4	490.3	492.7	497.6
17.5°	394.7	397.1	397.1	399.6	399.6	402.0	402.0	402.0	406.9	411.8	419.2
20°	355.4	355.4	355.4	355.4	355.4	353.0	353.0	350.5	353.0	357.9	360.3
22.5°	318.7	321.1	321.1	321.1	318.7	316.2	311.3	308.9	308.9	311.3	311.3
25°	279.5	277.0	277.0	274.5	274.5	277.0	277.0	277.0	279.5	279.5	281.9
27.5°	257.4	254.9	254.9	252.5	252.5	254.9	254.9	254.9	254.9	254.9	254.9
30°	240.2	240.2	237.8	235.3	237.8	237.8	240.2	240.2	242.7	242.7	245.1
32.5°	228.0	225.5	225.5	223.1	225.5	225.5	228.0	228.0	230.4	232.9	232.9
35°	210.8	210.8	210.8	210.8	210.8	210.8	208.4	208.4	208.4	208.4	208.4
37.5°	201.0	201.0	198.6	196.1	196.1	196.1	196.1	196.1	193.7	191.2	188.8
40°	193.7	191.2	191.2	188.8	186.3	186.3	183.9	181.4	181.4	178.9	178.9
42.5°	183.9	181.4	181.4	178.9	176.5	176.5	174.0	171.6	171.6	171.6	169.1
45°	171.6	171.6	169.1	166.7	166.7	166.7	164.2	164.2	164.2	164.2	161.8
47.5°	159.3	159.3	156.9	156.9	156.9	156.9	154.4	154.4	154.4	154.4	154.4
50°	152.0	152.0	152.0	152.0	152.0	152.0	149.5	149.5	149.5	149.5	149.5
52.5°	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6
55°	142.2	142.2	142.2	142.2	142.2	142.2	139.7	139.7	139.7	142.2	142.2
57.5°	137.3	137.3	134.8	134.8	134.8	134.8	134.8	134.8	134.8	134.8	134.8
60°	132.4	132.4	132.4	132.4	132.4	132.4	132.4	132.4	132.4	132.4	132.4
62.5°	125.0	125.0	125.0	125.0	125.0	127.5	127.5	127.5	127.5	127.5	125.0
65°	115.2	117.7	117.7	117.7	117.7	117.7	117.7	117.7	117.7	117.7	117.7
67.5°	110.3	110.3	110.3	110.3	110.3	110.3	110.3	110.3	110.3	110.3	110.3
70°	103.0	103.0	100.5	100.5	100.5	103.0	103.0	103.0	103.0	103.0	103.0
72.5°	93.2	93.2	93.2	93.2	93.2	93.2	93.2	93.2	93.2	95.6	95.6
75°	83.3	83.3	83.3	83.3	83.3	83.3	83.3	83.3	83.3	83.3	83.3
77.5°	73.5	73.5	71.1	71.1	71.1	73.5	73.5	73.5	73.5	76.0	76.0
80°	61.3	61.3	61.3	61.3	61.3	61.3	61.3	61.3	61.3	63.7	63.7
82.5°	49.0	49.0	49.0	49.0	49.0	49.0	49.0	49.0	49.0	51.5	51.5
85°	36.8	39.2	39.2	39.2	39.2	39.2	39.2	39.2	39.2	41.7	41.7
87.5°	24.5	24.5	24.5	24.5	24.5	24.5	22.1	22.1	22.1	22.1	19.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950
 CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0
2.5°	1561.5	1564.0	1566.4	1566.4	1568.9	1571.3	1571.3	1581.1	1590.9	1595.8	1600.7
5°	1336.0	1333.5	1333.5	1331.1	1328.6	1336.0	1343.3	1358.0	1372.7	1375.2	1380.1
7.5°	1046.7	1049.2	1051.6	1051.6	1054.1	1046.7	1036.9	1039.4	1041.8	1054.1	1063.9
10°	791.8	794.2	796.7	796.7	799.1	796.7	791.8	799.1	806.5	816.3	828.6
12.5°	615.3	622.6	630.0	634.9	642.3	647.2	649.6	659.4	666.8	679.0	691.3
15°	502.5	507.4	512.3	517.2	522.1	527.0	531.9	541.7	551.6	566.3	581.0
17.5°	424.1	424.1	426.5	426.5	426.5	431.4	436.3	441.2	443.7	458.4	473.1
20°	362.8	360.3	357.9	355.4	353.0	357.9	360.3	362.8	365.2	375.1	382.4
22.5°	311.3	311.3	313.8	313.8	313.8	311.3	306.4	308.9	308.9	313.8	321.1
25°	281.9	281.9	281.9	279.5	279.5	281.9	284.4	284.4	281.9	284.4	286.8
27.5°	254.9	257.4	257.4	259.8	259.8	262.3	262.3	262.3	262.3	264.7	267.2
30°	245.1	245.1	247.6	247.6	247.6	250.0	252.5	252.5	252.5	254.9	259.8
32.5°	235.3	237.8	240.2	242.7	245.1	247.6	247.6	250.0	250.0	252.5	254.9
35°	208.4	205.9	205.9	203.5	201.0	201.0	201.0	201.0	198.6	201.0	201.0
37.5°	186.3	186.3	186.3	183.9	183.9	186.3	186.3	186.3	186.3	188.8	188.8
40°	176.5	176.5	176.5	176.5	176.5	176.5	176.5	178.9	178.9	181.4	183.9
42.5°	169.1	169.1	169.1	169.1	169.1	171.6	171.6	171.6	171.6	174.0	174.0
45°	161.8	161.8	161.8	161.8	161.8	161.8	161.8	164.2	164.2	166.7	169.1
47.5°	154.4	154.4	154.4	154.4	154.4	156.9	159.3	159.3	159.3	161.8	161.8
50°	149.5	149.5	149.5	149.5	149.5	152.0	152.0	154.4	154.4	156.9	159.3
52.5°	144.6	144.6	144.6	144.6	144.6	147.1	147.1	149.5	149.5	152.0	154.4
55°	142.2	142.2	142.2	139.7	139.7	142.2	142.2	144.6	144.6	147.1	147.1
57.5°	134.8	134.8	134.8	134.8	134.8	134.8	134.8	137.3	137.3	139.7	142.2
60°	132.4	132.4	129.9	129.9	127.5	129.9	129.9	132.4	132.4	134.8	134.8
62.5°	125.0	125.0	125.0	122.6	122.6	125.0	125.0	125.0	125.0	127.5	129.9
65°	117.7	117.7	117.7	115.2	115.2	117.7	117.7	117.7	117.7	120.1	122.6
67.5°	110.3	110.3	110.3	107.9	107.9	107.9	107.9	110.3	110.3	112.8	115.2
70°	103.0	103.0	103.0	100.5	100.5	100.5	98.1	100.5	103.0	105.4	105.4
72.5°	95.6	95.6	95.6	93.2	93.2	93.2	90.7	93.2	93.2	95.6	95.6
75°	83.3	83.3	83.3	83.3	83.3	83.3	80.9	80.9	80.9	83.3	83.3
77.5°	76.0	76.0	76.0	73.5	73.5	73.5	71.1	71.1	71.1	73.5	73.5
80°	63.7	63.7	63.7	61.3	61.3	61.3	58.8	58.8	58.8	61.3	61.3
82.5°	51.5	51.5	51.5	49.0	49.0	49.0	46.6	46.6	46.6	49.0	49.0
85°	41.7	41.7	41.7	41.7	41.7	41.7	39.2	39.2	39.2	41.7	44.1
87.5°	19.6	19.6	22.1	22.1	22.1	22.1	19.6	19.6	17.2	17.2	19.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950
 CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0
2.5°	1605.6	1610.5	1622.8	1632.6	1644.8	1654.7	1662.0	1671.8	1679.2	1686.5	1691.4
5°	1382.6	1385.0	1397.3	1409.5	1419.3	1431.6	1448.7	1465.9	1483.1	1500.2	1512.5
7.5°	1076.1	1085.9	1100.6	1117.8	1132.5	1147.2	1164.4	1184.0	1201.2	1218.3	1235.5
10°	838.4	848.2	862.9	877.6	889.8	904.5	924.2	943.8	963.4	983.0	1002.6
12.5°	703.5	715.8	732.9	750.1	764.8	782.0	806.5	828.6	853.1	875.1	899.6
15°	593.2	607.9	630.0	654.5	676.6	698.6	723.1	747.7	769.7	794.2	818.7
17.5°	487.8	502.5	522.1	544.2	563.8	583.4	612.8	639.8	669.2	696.2	723.1
20°	392.2	399.6	419.2	438.8	458.4	478.0	500.1	522.1	544.2	566.3	600.6
22.5°	326.0	330.9	340.7	348.1	357.9	365.2	387.3	409.4	429.0	451.0	482.9
25°	286.8	289.3	296.6	301.5	308.9	313.8	328.5	340.7	355.4	367.7	397.1
27.5°	267.2	269.6	272.1	274.5	277.0	279.5	289.3	299.1	306.4	316.2	343.2
30°	262.3	264.7	272.1	277.0	284.4	289.3	294.2	299.1	304.0	308.9	326.0
32.5°	257.4	259.8	259.8	257.4	257.4	254.9	259.8	262.3	267.2	269.6	284.4
35°	203.5	203.5	205.9	208.4	210.8	213.3	220.6	225.5	232.9	237.8	250.0
37.5°	191.2	191.2	193.7	198.6	201.0	203.5	208.4	213.3	218.2	223.1	235.3
40°	183.9	186.3	188.8	191.2	193.7	196.1	201.0	203.5	208.4	210.8	220.6
42.5°	176.5	176.5	178.9	183.9	186.3	188.8	193.7	196.1	201.0	203.5	213.3
45°	171.6	174.0	176.5	178.9	178.9	181.4	186.3	191.2	193.7	198.6	208.4
47.5°	164.2	164.2	169.1	171.6	176.5	178.9	183.9	186.3	191.2	193.7	203.5
50°	159.3	161.8	166.7	169.1	174.0	176.5	183.9	188.8	196.1	201.0	205.9
52.5°	154.4	156.9	161.8	164.2	169.1	171.6	181.4	191.2	198.6	208.4	208.4
55°	149.5	149.5	154.4	161.8	166.7	171.6	176.5	183.9	188.8	193.7	193.7
57.5°	142.2	144.6	149.5	156.9	161.8	166.7	171.6	176.5	178.9	183.9	181.4
60°	137.3	137.3	144.6	152.0	159.3	166.7	166.7	166.7	164.2	164.2	164.2
62.5°	129.9	132.4	142.2	154.4	164.2	174.0	166.7	159.3	152.0	144.6	147.1
65°	125.0	127.5	132.4	139.7	144.6	149.5	144.6	142.2	137.3	132.4	134.8
67.5°	115.2	117.7	120.1	120.1	122.6	122.6	122.6	122.6	122.6	122.6	125.0
70°	107.9	107.9	107.9	110.3	110.3	110.3	110.3	110.3	110.3	110.3	112.8
72.5°	98.1	98.1	98.1	98.1	98.1	98.1	98.1	98.1	98.1	98.1	100.5
75°	85.8	85.8	85.8	85.8	85.8	85.8	85.8	85.8	85.8	85.8	88.2
77.5°	76.0	76.0	76.0	76.0	76.0	76.0	76.0	76.0	73.5	73.5	76.0
80°	63.7	63.7	63.7	63.7	61.3	61.3	61.3	61.3	61.3	61.3	63.7
82.5°	51.5	51.5	51.5	51.5	49.0	49.0	49.0	49.0	46.6	46.6	49.0
85°	46.6	49.0	49.0	51.5	51.5	51.5	49.0	46.6	44.1	41.7	41.7
87.5°	19.6	19.6	19.6	19.6	17.2	17.2	17.2	17.2	17.2	17.2	17.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950
 CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0
2.5°	1698.8	1703.7	1708.6	1715.9	1725.7	1733.1	1740.4	1755.2	1772.3	1787.0	1801.7
5°	1524.7	1537.0	1549.2	1564.0	1578.7	1590.9	1605.6	1635.0	1664.5	1691.4	1720.8
7.5°	1250.2	1267.3	1282.0	1306.6	1328.6	1353.1	1375.2	1412.0	1446.3	1483.1	1517.4
10°	1022.2	1041.8	1061.4	1093.3	1127.6	1159.5	1191.3	1220.8	1252.6	1282.0	1311.5
12.5°	924.2	946.2	970.7	990.3	1012.4	1032.0	1051.6	1085.9	1120.3	1154.6	1188.9
15°	843.3	867.8	892.3	916.8	938.9	963.4	985.4	1014.9	1046.7	1076.1	1105.6
17.5°	750.1	774.6	801.6	828.6	855.5	882.5	909.4	951.1	992.8	1032.0	1073.7
20°	632.4	666.8	698.6	735.4	772.2	808.9	845.7	889.8	934.0	975.6	1019.8
22.5°	514.8	546.6	578.5	622.6	666.8	708.4	752.6	811.4	867.8	926.6	983.0
25°	429.0	458.4	487.8	536.8	583.4	632.4	679.0	750.1	818.7	889.8	958.5
27.5°	370.2	397.1	424.1	475.6	527.0	576.1	627.5	706.0	782.0	860.4	936.4
30°	343.2	360.3	377.5	426.5	475.6	522.1	571.2	647.2	723.1	799.1	875.1
32.5°	299.1	313.8	328.5	372.6	416.7	458.4	502.5	581.0	657.0	735.4	811.4
35°	264.7	277.0	289.3	330.9	370.2	411.8	451.0	529.5	607.9	686.4	764.8
37.5°	245.1	257.4	267.2	304.0	343.2	380.0	416.7	495.2	571.2	649.6	725.6
40°	230.4	237.8	247.6	284.4	318.7	355.4	389.8	460.9	534.4	605.5	676.6
42.5°	220.6	230.4	237.8	269.6	304.0	335.8	367.7	436.3	505.0	571.2	639.8
45°	218.2	228.0	237.8	264.7	291.7	316.2	343.2	409.4	475.6	541.7	607.9
47.5°	213.3	220.6	230.4	252.5	272.1	294.2	313.8	380.0	446.1	509.9	576.1
50°	210.8	213.3	218.2	237.8	257.4	277.0	296.6	362.8	429.0	495.2	561.4
52.5°	208.4	208.4	208.4	225.5	242.7	257.4	274.5	340.7	409.4	475.6	541.7
55°	193.7	191.2	191.2	208.4	223.1	240.2	254.9	321.1	387.3	451.0	517.2
57.5°	178.9	176.5	174.0	188.8	203.5	218.2	232.9	299.1	367.7	433.9	500.1
60°	164.2	161.8	161.8	176.5	188.8	203.5	215.7	284.4	350.5	419.2	485.4
62.5°	147.1	149.5	149.5	161.8	176.5	188.8	201.0	269.6	340.7	409.4	478.0
65°	134.8	137.3	137.3	152.0	166.7	181.4	196.1	262.3	330.9	397.1	463.3
67.5°	125.0	127.5	127.5	144.6	159.3	176.5	191.2	250.0	311.3	370.2	429.0
70°	115.2	115.2	117.7	134.8	152.0	169.1	186.3	237.8	289.3	338.3	389.8
72.5°	103.0	105.4	107.9	125.0	139.7	156.9	171.6	218.2	264.7	311.3	357.9
75°	90.7	93.2	95.6	110.3	125.0	139.7	154.4	198.6	240.2	284.4	326.0
77.5°	80.9	83.3	85.8	98.1	110.3	122.6	134.8	166.7	201.0	232.9	264.7
80°	66.2	66.2	68.6	78.4	88.2	95.6	105.4	127.5	149.5	169.1	191.2
82.5°	49.0	51.5	51.5	58.8	63.7	71.1	76.0	88.2	98.1	110.3	120.1
85°	41.7	39.2	39.2	44.1	46.6	51.5	53.9	61.3	66.2	73.5	78.4
87.5°	17.2	14.7	14.7	17.2	22.1	24.5	27.0	27.0	29.4	29.4	29.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950
 CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0
2.5°	1809.1	1814.0	1821.3	1826.2	1838.5	1848.3	1860.6	1870.4	1877.7	1890.0	1885.1
5°	1742.9	1765.0	1787.0	1809.1	1826.2	1843.4	1858.1	1875.3	1894.9	1931.7	1941.5
7.5°	1546.8	1576.2	1603.2	1632.6	1666.9	1701.2	1735.5	1769.9	1801.7	1848.3	1877.7
10°	1353.1	1394.8	1434.0	1475.7	1507.6	1539.4	1568.9	1600.7	1644.8	1691.4	1745.4
12.5°	1230.6	1272.2	1313.9	1355.6	1402.2	1446.3	1492.9	1537.0	1578.7	1615.4	1676.7
15°	1149.7	1196.3	1240.4	1284.5	1340.9	1394.8	1451.2	1505.1	1566.4	1615.4	1657.1
17.5°	1130.1	1186.4	1240.4	1296.8	1355.6	1414.4	1473.3	1532.1	1593.4	1666.9	1720.8
20°	1095.7	1171.7	1247.7	1323.7	1399.7	1473.3	1549.2	1622.8	1703.7	1791.9	1816.4
22.5°	1076.1	1166.8	1260.0	1350.7	1453.6	1559.0	1662.0	1765.0	1850.8	1916.9	1990.5
25°	1073.7	1186.4	1301.7	1414.4	1544.3	1671.8	1801.7	1929.2	2039.5	2105.7	2164.5
27.5°	1071.2	1208.5	1343.3	1478.2	1637.5	1794.4	1953.7	2110.6	2213.6	2309.2	2358.2
30°	1041.8	1206.1	1372.7	1537.0	1715.9	1894.9	2073.8	2252.8	2358.2	2424.4	2448.9
32.5°	1005.0	1198.7	1392.4	1586.0	1789.5	1992.9	2193.9	2397.4	2480.8	2537.1	2517.5
35°	975.6	1188.9	1399.7	1610.5	1826.2	2044.4	2260.1	2475.8	2596.0	2674.4	2642.5
37.5°	948.7	1171.7	1394.8	1617.9	1870.4	2122.9	2375.3	2627.8	2743.0	2826.4	2789.6
40°	916.8	1154.6	1394.8	1632.6	1921.8	2208.7	2497.9	2784.7	2934.2	3005.3	2949.0
42.5°	889.8	1137.4	1387.5	1635.0	1943.9	2252.8	2561.6	2870.5	3037.2	3137.7	3066.6
45°	855.5	1103.1	1348.2	1595.8	1936.6	2277.3	2615.6	2956.3	3150.0	3228.4	3130.4
47.5°	818.7	1063.9	1306.6	1549.2	1912.0	2274.8	2637.6	3000.4	3179.4	3272.5	3181.8
50°	806.5	1051.6	1294.3	1539.4	1931.7	2326.3	2718.5	3110.7	3240.7	3316.7	3196.5
52.5°	804.0	1063.9	1326.2	1586.0	1980.7	2372.9	2767.6	3159.8	3265.2	3346.1	3238.2
55°	796.7	1078.6	1358.0	1637.5	2049.3	2463.6	2875.4	3287.2	3392.6	3451.5	3370.6
57.5°	804.0	1108.0	1409.5	1713.5	2137.6	2561.6	2985.7	3409.8	3537.3	3579.0	3561.8
60°	808.9	1132.5	1453.6	1777.2	2191.5	2605.8	3020.0	3434.3	3566.7	3669.7	3689.3
62.5°	796.7	1115.4	1431.6	1750.3	2125.3	2500.4	2875.4	3250.5	3468.6	3620.6	3708.9
65°	759.9	1054.1	1350.7	1644.8	1990.5	2338.6	2684.2	3029.9	3260.3	3485.8	3556.9
67.5°	679.0	929.1	1179.1	1429.1	1730.6	2032.2	2331.2	2632.7	2922.0	3140.2	3238.2
70°	588.3	784.4	983.0	1179.1	1453.6	1728.2	2002.7	2277.3	2532.2	2772.5	2865.6
72.5°	512.3	664.3	818.7	970.7	1166.8	1360.5	1556.6	1750.3	2051.8	2292.0	2382.7
75°	436.3	546.6	654.5	764.8	899.6	1034.5	1166.8	1301.7	1514.9	1730.6	1821.3
77.5°	335.8	409.4	480.5	551.6	644.7	735.4	828.6	919.3	1068.8	1230.6	1277.1
80°	232.9	274.5	313.8	355.4	429.0	502.5	576.1	649.6	747.7	838.4	909.4
82.5°	144.6	171.6	196.1	220.6	279.5	338.3	394.7	453.5	492.7	497.6	568.7
85°	93.2	110.3	125.0	139.7	174.0	210.8	245.1	279.5	250.0	232.9	277.0
87.5°	36.8	46.6	53.9	61.3	58.8	56.4	53.9	51.5	44.1	39.2	49.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950
 CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0
2.5°	1890.0	1897.3	1904.7	1909.6	1916.9	1919.4	1921.8	1921.8	1924.3	1926.8	1931.7
5°	1980.7	1995.4	2010.1	2022.4	2037.1	2049.3	2059.1	2071.4	2081.2	2081.2	2078.7
7.5°	1904.7	1941.5	1978.2	2015.0	2051.8	2078.7	2103.2	2130.2	2154.7	2159.6	2164.5
10°	1804.2	1843.4	1880.2	1919.4	1956.2	1997.8	2037.1	2076.3	2118.0	2125.3	2135.1
12.5°	1711.0	1757.6	1804.2	1848.3	1894.9	1924.3	1953.7	1980.7	2010.1	2029.7	2049.3
15°	1708.6	1747.8	1787.0	1823.8	1863.0	1880.2	1897.3	1912.0	1929.2	1929.2	1931.7
17.5°	1765.0	1789.5	1814.0	1836.1	1860.6	1863.0	1867.9	1870.4	1872.8	1865.5	1858.1
20°	1875.3	1885.1	1894.9	1904.7	1914.5	1897.3	1882.6	1865.5	1848.3	1828.7	1811.5
22.5°	2037.1	2015.0	1992.9	1970.9	1948.8	1919.4	1887.5	1858.1	1826.2	1801.7	1777.2
25°	2189.0	2162.1	2135.1	2108.1	2081.2	2017.4	1953.7	1887.5	1823.8	1796.8	1769.9
27.5°	2392.5	2350.8	2309.2	2267.5	2225.8	2140.0	2054.2	1968.4	1882.6	1836.1	1791.9
30°	2441.5	2395.0	2348.4	2299.4	2252.8	2169.4	2088.5	2005.2	1921.8	1867.9	1816.4
32.5°	2512.6	2458.7	2404.8	2350.8	2296.9	2216.0	2135.1	2051.8	1970.9	1921.8	1870.4
35°	2630.3	2569.0	2507.7	2444.0	2382.7	2299.4	2218.5	2135.1	2051.8	1995.4	1941.5
37.5°	2730.8	2659.7	2588.6	2517.5	2446.4	2372.9	2296.9	2223.4	2147.4	2091.0	2037.1
40°	2843.6	2765.1	2686.7	2610.7	2532.2	2463.6	2395.0	2323.9	2255.2	2211.1	2167.0
42.5°	2941.6	2846.0	2752.9	2659.7	2564.1	2517.5	2473.4	2426.8	2380.2	2358.2	2333.7
45°	3010.2	2922.0	2831.3	2743.0	2654.8	2620.5	2586.2	2551.8	2517.5	2539.6	2561.6
47.5°	3039.7	2968.6	2899.9	2831.3	2760.2	2772.5	2784.7	2794.5	2806.8	2836.2	2868.1
50°	3066.6	3027.4	2985.7	2946.5	2904.8	2951.4	2995.5	3042.1	3088.7	3150.0	3211.3
52.5°	3120.6	3098.5	3078.9	3056.8	3034.8	3115.6	3196.5	3277.4	3358.3	3427.0	3495.6
55°	3282.3	3265.2	3248.0	3228.4	3211.3	3326.5	3439.2	3554.4	3669.7	3740.7	3811.8
57.5°	3505.4	3495.6	3483.3	3473.5	3461.3	3574.0	3684.4	3794.7	3907.4	3976.1	4047.2
60°	3674.6	3677.0	3677.0	3679.5	3679.5	3765.3	3851.0	3939.3	4025.1	4083.9	4145.2
62.5°	3765.3	3760.3	3755.4	3750.5	3745.6	3816.7	3887.8	3958.9	4030.0	4074.1	4118.2
65°	3667.2	3694.2	3721.1	3748.1	3775.1	3784.9	3792.2	3802.0	3809.4	3836.3	3863.3
67.5°	3338.7	3392.6	3444.1	3498.1	3549.5	3512.8	3478.4	3441.7	3404.9	3412.3	3417.2
70°	2973.5	3034.8	3098.5	3159.8	3221.1	3135.3	3049.5	2961.2	2875.4	2846.0	2816.6
72.5°	2507.7	2561.6	2618.0	2672.0	2725.9	2620.5	2517.5	2412.1	2306.7	2255.2	2203.8
75°	1916.9	1980.7	2046.9	2110.6	2174.3	2056.7	1936.6	1818.9	1698.8	1664.5	1632.6
77.5°	1397.3	1473.3	1549.2	1625.2	1701.2	1595.8	1490.4	1382.6	1277.1	1257.5	1237.9
80°	1017.3	1076.1	1132.5	1191.3	1247.7	1186.4	1125.2	1063.9	1002.6	1000.1	997.7
82.5°	686.4	737.9	786.9	838.4	887.4	862.9	840.8	816.3	791.8	816.3	843.3
85°	353.0	424.1	497.6	568.7	639.8	632.4	627.5	620.2	612.8	644.7	674.1
87.5°	71.1	132.4	193.7	252.5	313.8	299.1	284.4	267.2	252.5	262.3	269.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950
 CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0
2.5°	1934.1	1936.6	1936.6	1936.6	1936.6	1936.6	1931.7	1929.2	1924.3	1919.4	1912.0
5°	2078.7	2076.3	2066.5	2056.7	2044.4	2034.6	2027.3	2017.4	2010.1	2000.3	1985.6
7.5°	2169.4	2174.3	2157.2	2142.5	2125.3	2108.1	2091.0	2073.8	2056.7	2039.5	2005.2
10°	2142.5	2149.8	2140.0	2130.2	2118.0	2108.1	2088.5	2066.5	2046.9	2024.8	1983.1
12.5°	2066.5	2086.1	2081.2	2076.3	2071.4	2066.5	2054.2	2039.5	2027.3	2012.5	1966.0
15°	1931.7	1931.7	1934.1	1936.6	1936.6	1939.0	1941.5	1943.9	1946.4	1948.8	1921.8
17.5°	1850.8	1843.4	1843.4	1843.4	1843.4	1843.4	1853.2	1865.5	1875.3	1885.1	1877.7
20°	1791.9	1774.8	1772.3	1772.3	1769.9	1767.4	1784.6	1804.2	1821.3	1838.5	1848.3
22.5°	1752.7	1728.2	1725.7	1723.3	1720.8	1718.4	1740.4	1762.5	1784.6	1806.6	1841.0
25°	1742.9	1715.9	1718.4	1720.8	1720.8	1723.3	1740.4	1757.6	1774.8	1791.9	1850.8
27.5°	1745.4	1701.2	1703.7	1706.1	1706.1	1708.6	1735.5	1760.1	1787.0	1811.5	1885.1
30°	1762.5	1711.0	1706.1	1701.2	1696.3	1691.4	1728.2	1765.0	1801.7	1838.5	1894.9
32.5°	1821.3	1772.3	1760.1	1747.8	1735.5	1723.3	1767.4	1809.1	1853.2	1894.9	1941.5
35°	1885.1	1831.1	1826.2	1821.3	1814.0	1809.1	1848.3	1890.0	1929.2	1968.4	2010.1
37.5°	1980.7	1926.8	1921.8	1914.5	1909.6	1902.2	1946.4	1988.0	2032.2	2073.8	2110.6
40°	2122.9	2078.7	2076.3	2076.3	2073.8	2071.4	2105.7	2142.5	2176.8	2211.1	2235.6
42.5°	2311.6	2289.5	2296.9	2306.7	2314.1	2321.4	2348.4	2377.8	2404.8	2431.7	2424.4
45°	2583.7	2605.8	2608.2	2610.7	2613.1	2615.6	2622.9	2632.7	2640.1	2647.4	2618.0
47.5°	2897.5	2926.9	2941.6	2956.3	2968.6	2983.3	2973.5	2961.2	2951.4	2939.2	2865.6
50°	3270.1	3331.4	3328.9	3326.5	3321.6	3319.1	3299.5	3279.9	3257.8	3238.2	3130.4
52.5°	3564.2	3632.9	3645.1	3657.4	3669.7	3681.9	3645.1	3608.4	3569.1	3532.4	3397.6
55°	3880.5	3951.6	3954.0	3956.5	3956.5	3958.9	3907.4	3856.0	3802.0	3750.5	3610.8
57.5°	4115.8	4184.4	4177.1	4172.2	4164.8	4157.5	4096.2	4034.9	3973.6	3912.3	3772.6
60°	4204.0	4262.9	4248.2	4233.5	4216.3	4201.6	4155.0	4108.4	4059.4	4012.8	3878.0
62.5°	4162.4	4206.5	4184.4	4164.8	4142.8	4120.7	4061.9	4000.6	3941.7	3880.5	3782.4
65°	3887.8	3914.8	3885.4	3858.4	3831.4	3802.0	3753.0	3704.0	3652.5	3603.5	3537.3
67.5°	3424.5	3429.4	3427.0	3424.5	3422.1	3419.6	3348.5	3277.4	3203.9	3132.8	3127.9
70°	2789.6	2760.2	2765.1	2772.5	2777.4	2782.3	2728.3	2676.9	2622.9	2569.0	2593.5
72.5°	2152.3	2100.8	2113.1	2127.8	2140.0	2152.3	2108.1	2066.5	2022.4	1978.2	2012.5
75°	1598.3	1566.4	1578.7	1593.4	1605.6	1617.9	1600.7	1583.6	1564.0	1546.8	1578.7
77.5°	1218.3	1198.7	1201.2	1201.2	1203.6	1203.6	1206.1	1211.0	1213.4	1215.9	1250.2
80°	992.8	990.3	987.9	985.4	980.5	978.1	1002.6	1027.1	1051.6	1076.1	1093.3
82.5°	867.8	892.3	877.6	865.3	850.6	835.9	858.0	880.0	902.1	924.2	916.8
85°	706.0	735.4	708.4	681.5	652.1	625.1	644.7	661.9	681.5	698.6	688.8
87.5°	279.5	286.8	242.7	201.0	156.9	112.8	178.9	242.7	308.9	372.6	382.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950
 CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675950

CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0	1765.0
2.5°	1904.7	1894.9	1887.5	1885.1	1880.2	1877.7	1872.8	1867.9	1860.6	1855.7	1848.3
5°	1968.4	1953.7	1936.6	1912.0	1890.0	1865.5	1841.0	1818.9	1796.8	1772.3	1750.3
7.5°	1970.9	1936.6	1902.2	1870.4	1836.1	1804.2	1769.9	1740.4	1708.6	1676.7	1647.3
10°	1943.9	1902.2	1860.6	1818.9	1779.7	1738.0	1696.3	1662.0	1625.2	1588.5	1554.1
12.5°	1921.8	1875.3	1828.7	1779.7	1733.1	1684.1	1635.0	1600.7	1566.4	1532.1	1497.8
15°	1894.9	1865.5	1838.5	1794.4	1750.3	1706.1	1662.0	1615.4	1571.3	1524.7	1478.2
17.5°	1872.8	1865.5	1858.1	1828.7	1799.3	1767.4	1738.0	1691.4	1644.8	1595.8	1549.2
20°	1860.6	1870.4	1880.2	1865.5	1850.8	1833.6	1818.9	1784.6	1750.3	1713.5	1679.2
22.5°	1875.3	1912.0	1946.4	1948.8	1953.7	1956.2	1958.6	1926.8	1894.9	1860.6	1828.7
25°	1909.6	1968.4	2027.3	2059.1	2091.0	2125.3	2157.2	2137.6	2118.0	2098.3	2078.7
27.5°	1956.2	2029.7	2103.2	2149.8	2193.9	2240.5	2287.1	2284.6	2282.2	2277.3	2274.8
30°	1948.8	2005.2	2061.6	2118.0	2174.3	2230.7	2287.1	2316.5	2343.5	2372.9	2402.3
32.5°	1990.5	2037.1	2086.1	2144.9	2203.8	2265.0	2323.9	2385.2	2444.0	2505.3	2566.5
35°	2054.2	2095.9	2140.0	2203.8	2269.9	2333.7	2399.9	2473.4	2549.4	2625.4	2698.9
37.5°	2149.8	2186.6	2225.8	2279.7	2336.1	2390.1	2446.4	2554.3	2662.2	2772.5	2880.3
40°	2260.1	2284.6	2309.2	2360.6	2412.1	2463.6	2515.1	2649.9	2784.7	2919.5	3054.4
42.5°	2419.5	2412.1	2404.8	2446.4	2490.6	2532.2	2576.4	2698.9	2821.5	2944.1	3066.6
45°	2588.6	2559.2	2529.8	2549.4	2571.5	2591.1	2613.1	2738.1	2863.2	2990.6	3115.6
47.5°	2792.1	2718.5	2645.0	2627.8	2610.7	2591.1	2573.9	2708.7	2843.6	2980.8	3115.6
50°	3022.5	2912.2	2804.3	2760.2	2713.6	2669.5	2622.9	2733.2	2846.0	2958.8	3069.1
52.5°	3262.7	3125.5	2990.6	2922.0	2853.4	2782.3	2713.6	2806.8	2902.4	2998.0	3091.1
55°	3468.6	3328.9	3186.7	3105.8	3024.9	2944.1	2863.2	2956.3	3049.5	3142.6	3235.8
57.5°	3632.9	3493.2	3353.4	3277.4	3199.0	3123.0	3044.6	3132.8	3223.5	3314.2	3402.5
60°	3745.6	3610.8	3476.0	3402.5	3328.9	3255.4	3181.8	3287.2	3392.6	3500.5	3605.9
62.5°	3686.8	3588.8	3490.7	3458.8	3427.0	3392.6	3360.8	3461.3	3559.3	3659.8	3760.3
65°	3471.1	3404.9	3338.7	3370.6	3404.9	3436.8	3471.1	3537.3	3603.5	3672.1	3738.3
67.5°	3120.6	3115.6	3108.3	3179.4	3250.5	3324.0	3395.1	3439.2	3480.9	3525.0	3569.1
70°	2618.0	2645.0	2669.5	2792.1	2914.6	3037.2	3159.8	3176.9	3194.1	3211.3	3228.4
72.5°	2049.3	2083.6	2120.4	2282.2	2441.5	2603.3	2765.1	2755.3	2745.5	2733.2	2723.4
75°	1613.0	1644.8	1679.2	1828.7	1978.2	2127.8	2277.3	2235.6	2196.4	2154.7	2113.1
77.5°	1287.0	1321.3	1358.0	1497.8	1637.5	1779.7	1919.4	1818.9	1718.4	1617.9	1517.4
80°	1108.0	1125.2	1139.9	1235.5	1328.6	1424.2	1519.8	1416.9	1311.5	1206.1	1103.1
82.5°	909.4	899.6	892.3	948.7	1005.0	1061.4	1117.8	1019.8	921.7	821.2	723.1
85°	679.0	669.2	659.4	688.8	718.2	750.1	779.5	666.8	554.0	438.8	326.0
87.5°	394.7	404.5	414.3	446.1	478.0	512.3	544.2	429.0	313.8	196.1	80.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950
 CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675950
 CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1765.0	1765.0
2.5°	1833.6	1821.3
5°	1733.1	1715.9
7.5°	1622.8	1600.7
10°	1522.3	1492.9
12.5°	1458.5	1421.8
15°	1434.0	1389.9
17.5°	1507.6	1465.9
20°	1620.3	1564.0
22.5°	1757.6	1689.0
25°	1995.4	1912.0
27.5°	2189.0	2103.2
30°	2309.2	2216.0
32.5°	2441.5	2319.0
35°	2578.8	2461.1
37.5°	2745.5	2613.1
40°	2917.1	2779.8
42.5°	2975.9	2887.7
45°	3032.3	2949.0
47.5°	3044.6	2975.9
50°	3056.8	3047.0
52.5°	3091.1	3088.7
55°	3238.2	3240.7
57.5°	3419.6	3434.3
60°	3586.3	3569.1
62.5°	3672.1	3583.9
65°	3613.3	3490.7
67.5°	3436.8	3304.4
70°	3049.5	2870.5
72.5°	2566.5	2409.7
75°	1978.2	1845.9
77.5°	1407.1	1296.8
80°	990.3	880.0
82.5°	634.9	546.6
85°	286.8	250.0
87.5°	80.9	78.4
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P675950
CATALOG NUMBER: CCW-SA-2C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)