

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675968

Luminaire Tested: **CCW-SA-1E-730-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P675968
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-1E-730-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/
SLR distribution lens
Light Source: (16) 3000K CCT, 70 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5166.6 lumens
Efficiency: N/A
Efficacy: 92.1 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 56.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P675968

CATALOG NUMBER: CCW-SA-1E-730-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 7.3 fc

Type IV - Short - N/A

REPORT NUMBER: P675968
CATALOG NUMBER: CCW-SA-1E-730-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P675968

CATALOG NUMBER: CCW-SA-1E-730-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1063.1	0.0	1063.1
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	4103.6	0.0	4103.6
	% Fixture	79.4	0.0	79.4
Total	Lumens	5166.6	0.0	5166.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.2	2.5
10°-20°	270.7	5.2
20°-30°	396.0	7.7
30°-40°	557.9	10.8
40°-50°	766.7	14.8
50°-60°	1045.0	20.2
60°-70°	1143.7	22.1
70°-80°	660.5	12.8
80°-90°	198.0	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5166.6	100.0
0°-180°	5166.6	100.0

Coefficient of Utilization



REPORT NUMBER: P675968


CATALOG NUMBER: CCW-SA-1E-730-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	530.6	10.3			
FM	(30°-60°)	1885.5	36.5			
FH	(60°-80°)	1519.3	29.4			G1/1800
FVH	(80°-90°)	168.2	3.3			G2/225
BL	(0°-30°)	264.3	5.1	B1/500		
BM	(30°-60°)	484.1	9.4	B1/1000		
BH	(60°-80°)	284.9	5.5	B1/500		G1/500
BVH	(80°-90°)	29.8	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P675968

CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9
2.5°	1702.6	1693.4	1686.6	1679.7	1670.5	1663.6	1654.5	1645.3	1633.9	1624.7	1613.2
5°	1604.1	1576.6	1549.1	1533.0	1514.7	1498.7	1480.3	1459.7	1439.1	1416.2	1395.5
7.5°	1496.4	1462.0	1427.6	1400.1	1370.3	1342.8	1313.0	1287.8	1262.6	1237.4	1212.2
10°	1395.5	1363.5	1331.4	1297.0	1260.3	1226.0	1189.3	1154.9	1120.6	1086.2	1051.8
12.5°	1329.1	1290.1	1253.5	1214.5	1177.8	1138.9	1099.9	1067.9	1035.8	1001.4	969.3
15°	1299.3	1262.6	1228.3	1189.3	1150.3	1111.4	1072.4	1035.8	1001.4	964.7	928.1
17.5°	1370.3	1317.6	1264.9	1214.5	1164.1	1113.7	1063.3	1017.4	971.6	925.8	879.9
20°	1462.0	1395.5	1331.4	1269.5	1205.3	1143.5	1079.3	1015.1	951.0	886.8	822.7
22.5°	1578.9	1503.2	1429.9	1349.7	1267.2	1187.0	1104.5	1024.3	944.1	861.6	781.4
25°	1787.4	1698.0	1608.7	1494.1	1377.2	1262.6	1145.8	1040.4	937.2	831.8	726.4
27.5°	1966.1	1844.7	1725.5	1588.0	1450.5	1313.0	1175.6	1054.1	934.9	813.5	692.0
30°	2071.5	1952.4	1833.2	1665.9	1500.9	1333.7	1166.4	1031.2	898.3	763.1	627.9
32.5°	2167.8	2034.9	1902.0	1718.6	1533.0	1349.7	1164.1	1015.1	868.5	719.5	570.6
35°	2300.7	2154.0	2009.7	1796.6	1583.4	1370.3	1157.2	1003.7	847.9	694.3	538.5
37.5°	2442.8	2261.7	2083.0	1847.0	1610.9	1374.9	1138.9	987.6	836.4	685.2	533.9
40°	2598.6	2378.6	2160.9	1899.7	1640.7	1379.5	1118.3	967.0	815.8	662.3	511.0
42.5°	2699.4	2461.1	2222.8	1940.9	1661.4	1379.5	1097.6	948.7	799.7	648.5	499.6
45°	2756.7	2525.3	2296.1	1991.3	1686.6	1381.8	1077.0	930.4	783.7	634.8	488.1
47.5°	2781.9	2566.5	2351.1	2030.3	1711.8	1391.0	1070.1	921.2	770.0	621.0	469.8
50°	2848.4	2658.2	2468.0	2124.2	1782.8	1439.1	1095.3	934.9	776.8	616.4	456.0
52.5°	2887.3	2724.6	2561.9	2209.0	1856.1	1503.2	1150.3	971.6	792.9	614.1	435.4
55°	3029.4	2873.6	2717.7	2341.9	1963.8	1588.0	1209.9	1012.9	815.8	616.4	419.3
57.5°	3210.4	3045.4	2882.7	2477.1	2071.5	1665.9	1260.3	1049.5	836.4	625.6	412.5
60°	3336.5	3176.1	3017.9	2587.1	2154.0	1723.2	1290.1	1070.1	850.2	627.9	407.9
62.5°	3350.2	3144.0	2940.0	2520.7	2101.3	1679.7	1260.3	1047.2	834.1	618.7	405.6
65°	3263.1	3022.5	2781.9	2380.9	1979.9	1578.9	1177.8	983.1	788.3	591.2	396.4
67.5°	3089.0	2807.1	2525.3	2158.6	1792.0	1425.3	1058.7	891.4	726.4	559.1	391.9
70°	2683.4	2435.9	2190.7	1872.2	1555.9	1237.4	918.9	781.4	646.2	508.7	371.2
72.5°	2252.6	2021.1	1792.0	1533.0	1276.4	1017.4	758.5	655.4	552.3	446.8	343.7
75°	1725.5	1551.4	1379.5	1187.0	994.5	799.7	607.3	531.6	456.0	380.4	304.8
77.5°	1212.2	1118.3	1026.6	882.2	737.9	593.5	449.1	398.7	348.3	297.9	247.5
80°	822.7	770.0	719.5	616.4	513.3	407.9	304.8	272.7	238.3	206.2	171.9
82.5°	511.0	508.7	504.1	433.1	362.1	291.0	220.0	192.5	167.3	139.8	112.3
85°	233.7	272.7	309.4	270.4	231.4	192.5	153.5	135.2	116.9	96.2	77.9
87.5°	73.3	89.4	103.1	98.5	91.7	87.1	80.2	68.7	57.3	45.8	34.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968
 CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675968

CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9
2.5°	1604.1	1597.2	1588.0	1578.9	1567.4	1558.2	1546.8	1535.3	1533.0	1528.4	1526.2
5°	1381.8	1368.0	1352.0	1338.3	1324.5	1308.5	1294.7	1278.7	1267.2	1253.5	1242.0
7.5°	1187.0	1164.1	1138.9	1113.7	1090.8	1067.9	1042.6	1019.7	1008.3	996.8	985.4
10°	1031.2	1008.3	987.6	964.7	948.7	934.9	918.9	902.9	889.1	875.4	861.6
12.5°	953.3	937.2	921.2	905.2	886.8	870.8	852.4	834.1	818.1	804.3	788.3
15°	905.2	882.2	857.0	834.1	808.9	786.0	760.8	735.6	717.2	701.2	682.9
17.5°	847.9	813.5	781.4	747.0	719.5	692.0	662.3	634.8	614.1	591.2	570.6
20°	783.7	744.7	703.5	664.5	632.5	602.7	570.6	538.5	515.6	490.4	467.5
22.5°	728.7	678.3	625.6	572.9	538.5	504.1	467.5	433.1	412.5	389.6	368.9
25°	669.1	614.1	556.8	499.6	465.2	428.5	394.1	357.5	341.4	327.7	311.6
27.5°	637.0	582.0	524.8	469.8	437.7	403.3	371.2	336.9	325.4	311.6	300.2
30°	572.9	520.2	465.2	410.2	387.3	366.6	343.7	320.8	316.2	313.9	309.4
32.5°	515.6	460.6	405.6	350.6	330.0	309.4	288.7	268.1	265.8	261.2	258.9
35°	485.8	433.1	378.1	325.4	307.1	286.4	268.1	247.5	242.9	236.0	231.4
37.5°	478.9	423.9	366.6	311.6	293.3	275.0	254.4	236.0	231.4	226.9	222.3
40°	460.6	407.9	357.5	304.8	286.4	268.1	247.5	229.2	224.6	220.0	215.4
42.5°	446.8	396.4	343.7	291.0	275.0	258.9	240.6	224.6	220.0	215.4	208.5
45°	435.4	382.7	327.7	275.0	263.5	252.1	238.3	226.9	222.3	215.4	210.8
47.5°	417.1	366.6	313.9	261.2	249.8	240.6	229.2	217.7	213.1	208.5	203.9
50°	403.3	350.6	297.9	245.2	236.0	226.9	217.7	208.5	208.5	210.8	210.8
52.5°	385.0	334.6	284.1	233.7	224.6	215.4	206.2	197.1	199.4	201.7	203.9
55°	368.9	320.8	270.4	220.0	210.8	201.7	190.2	181.0	183.3	185.6	187.9
57.5°	362.1	311.6	261.2	210.8	201.7	190.2	181.0	169.6	169.6	169.6	169.6
60°	357.5	304.8	254.4	201.7	190.2	181.0	169.6	158.1	155.8	155.8	153.5
62.5°	355.2	302.5	252.1	199.4	185.6	174.2	160.4	146.7	144.4	142.1	139.8
65°	346.0	297.9	247.5	197.1	181.0	167.3	151.2	135.2	132.9	132.9	130.6
67.5°	343.7	293.3	245.2	194.8	178.7	160.4	144.4	126.0	123.7	121.5	119.2
70°	325.4	281.9	236.0	190.2	171.9	155.8	137.5	119.2	116.9	112.3	110.0
72.5°	302.5	263.5	222.3	181.0	162.7	144.4	126.0	107.7	105.4	103.1	98.5
75°	268.1	231.4	194.8	158.1	142.1	128.3	112.3	96.2	94.0	91.7	87.1
77.5°	220.0	190.2	162.7	132.9	121.5	110.0	98.5	87.1	84.8	82.5	77.9
80°	155.8	137.5	121.5	103.1	96.2	87.1	80.2	71.0	71.0	68.7	68.7
82.5°	103.1	94.0	84.8	75.6	71.0	66.5	61.9	57.3	57.3	55.0	55.0
85°	73.3	68.7	61.9	57.3	55.0	50.4	48.1	43.5	43.5	43.5	43.5
87.5°	34.4	34.4	32.1	32.1	29.8	29.8	27.5	25.2	25.2	25.2	25.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968
 CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675968

CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9
2.5°	1521.6	1514.7	1507.8	1498.7	1491.8	1482.6	1471.2	1462.0	1450.5	1450.5	1448.2
5°	1228.3	1221.4	1214.5	1205.3	1198.5	1189.3	1182.4	1173.3	1164.1	1164.1	1161.8
7.5°	973.9	960.1	946.4	930.4	916.6	907.4	898.3	886.8	877.7	870.8	863.9
10°	847.9	834.1	818.1	804.3	788.3	776.8	765.4	751.6	740.2	731.0	721.8
12.5°	772.2	756.2	740.2	724.1	708.1	692.0	678.3	662.3	646.2	634.8	623.3
15°	664.5	648.5	632.5	616.4	600.4	582.0	563.7	543.1	524.8	515.6	508.7
17.5°	547.7	531.6	513.3	497.3	478.9	465.2	451.4	437.7	423.9	414.8	407.9
20°	442.3	423.9	405.6	387.3	368.9	359.8	350.6	341.4	332.3	325.4	320.8
22.5°	346.0	334.6	325.4	313.9	302.5	295.6	291.0	284.1	277.3	277.3	277.3
25°	295.6	288.7	284.1	277.3	270.4	268.1	265.8	261.2	258.9	256.7	256.7
27.5°	286.4	279.6	272.7	265.8	258.9	256.7	254.4	249.8	247.5	247.5	247.5
30°	304.8	302.5	300.2	297.9	295.6	291.0	284.1	279.6	272.7	268.1	263.5
32.5°	254.4	252.1	252.1	249.8	247.5	252.1	254.4	258.9	261.2	263.5	265.8
35°	224.6	220.0	215.4	210.8	206.2	203.9	201.7	199.4	197.1	197.1	194.8
37.5°	217.7	213.1	208.5	203.9	199.4	197.1	194.8	192.5	190.2	190.2	187.9
40°	210.8	206.2	203.9	199.4	194.8	192.5	190.2	185.6	183.3	181.0	181.0
42.5°	203.9	201.7	197.1	194.8	190.2	187.9	185.6	181.0	178.7	176.4	174.2
45°	203.9	199.4	194.8	190.2	185.6	183.3	178.7	176.4	171.9	171.9	169.6
47.5°	199.4	194.8	190.2	185.6	181.0	178.7	174.2	171.9	167.3	165.0	162.7
50°	210.8	203.9	194.8	187.9	178.7	176.4	171.9	169.6	165.0	162.7	160.4
52.5°	206.2	199.4	190.2	183.3	174.2	169.6	167.3	162.7	158.1	155.8	153.5
55°	190.2	183.3	178.7	171.9	165.0	160.4	155.8	151.2	146.7	144.4	144.4
57.5°	169.6	167.3	165.0	162.7	160.4	155.8	151.2	144.4	139.8	137.5	135.2
60°	151.2	153.5	155.8	158.1	160.4	153.5	146.7	139.8	132.9	130.6	128.3
62.5°	137.5	142.1	146.7	148.9	153.5	146.7	139.8	132.9	126.0	123.7	121.5
65°	128.3	130.6	130.6	132.9	132.9	128.3	126.0	121.5	116.9	114.6	114.6
67.5°	116.9	116.9	116.9	114.6	114.6	112.3	112.3	110.0	107.7	105.4	105.4
70°	105.4	105.4	105.4	103.1	103.1	100.8	100.8	98.5	96.2	96.2	94.0
72.5°	96.2	96.2	94.0	94.0	91.7	91.7	91.7	89.4	89.4	87.1	87.1
75°	84.8	84.8	82.5	82.5	80.2	80.2	80.2	77.9	77.9	77.9	75.6
77.5°	75.6	75.6	73.3	73.3	71.0	71.0	71.0	68.7	68.7	66.5	66.5
80°	66.5	66.5	64.2	64.2	61.9	61.9	59.6	59.6	57.3	57.3	55.0
82.5°	52.7	52.7	52.7	52.7	52.7	50.4	50.4	48.1	45.8	45.8	43.5
85°	43.5	43.5	43.5	41.2	41.2	41.2	39.0	39.0	36.7	34.4	34.4
87.5°	25.2	25.2	25.2	22.9	22.9	22.9	22.9	22.9	22.9	22.9	20.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968
 CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675968

CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9
2.5°	1448.2	1446.0	1436.8	1427.6	1436.8	1446.0	1446.0	1446.0	1443.7	1443.7	1443.7
5°	1161.8	1159.5	1154.9	1150.3	1150.3	1148.1	1152.6	1157.2	1161.8	1166.4	1171.0
7.5°	854.7	847.9	841.0	834.1	838.7	841.0	847.9	852.4	859.3	863.9	875.4
10°	712.7	703.5	696.6	689.7	685.2	680.6	676.0	673.7	669.1	664.5	669.1
12.5°	609.5	598.1	586.6	572.9	570.6	568.3	563.7	559.1	554.5	550.0	547.7
15°	499.6	490.4	485.8	478.9	469.8	460.6	456.0	453.7	449.1	444.6	442.3
17.5°	398.7	389.6	382.7	375.8	373.5	368.9	368.9	368.9	368.9	368.9	368.9
20°	313.9	307.1	307.1	304.8	304.8	302.5	304.8	307.1	307.1	309.4	311.6
22.5°	275.0	275.0	272.7	270.4	272.7	272.7	275.0	277.3	279.6	281.9	284.1
25°	254.4	252.1	254.4	256.7	256.7	256.7	258.9	258.9	261.2	261.2	261.2
27.5°	245.2	245.2	247.5	247.5	249.8	249.8	249.8	247.5	247.5	245.2	245.2
30°	258.9	254.4	254.4	254.4	252.1	249.8	247.5	247.5	245.2	242.9	240.6
32.5°	268.1	270.4	268.1	263.5	261.2	256.7	254.4	249.8	247.5	242.9	238.3
35°	194.8	192.5	197.1	199.4	201.7	203.9	206.2	208.5	208.5	210.8	210.8
37.5°	187.9	185.6	185.6	183.3	183.3	183.3	183.3	183.3	181.0	181.0	183.3
40°	178.7	176.4	176.4	174.2	174.2	171.9	171.9	171.9	171.9	171.9	171.9
42.5°	171.9	169.6	169.6	169.6	169.6	167.3	167.3	165.0	165.0	162.7	162.7
45°	169.6	167.3	165.0	162.7	162.7	160.4	160.4	160.4	158.1	158.1	158.1
47.5°	160.4	158.1	158.1	155.8	155.8	153.5	153.5	153.5	151.2	151.2	151.2
50°	155.8	153.5	153.5	151.2	151.2	148.9	148.9	148.9	146.7	146.7	146.7
52.5°	148.9	146.7	146.7	146.7	144.4	142.1	142.1	142.1	139.8	139.8	139.8
55°	142.1	139.8	139.8	139.8	137.5	135.2	135.2	135.2	132.9	132.9	132.9
57.5°	132.9	130.6	130.6	128.3	128.3	128.3	128.3	128.3	126.0	126.0	126.0
60°	126.0	123.7	123.7	121.5	121.5	119.2	119.2	119.2	119.2	119.2	119.2
62.5°	119.2	116.9	114.6	112.3	114.6	114.6	114.6	114.6	112.3	112.3	112.3
65°	112.3	110.0	107.7	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4
67.5°	103.1	100.8	98.5	96.2	98.5	98.5	98.5	98.5	98.5	98.5	98.5
70°	94.0	91.7	91.7	89.4	89.4	87.1	87.1	89.4	89.4	89.4	89.4
72.5°	84.8	82.5	82.5	80.2	80.2	80.2	80.2	80.2	80.2	80.2	80.2
75°	75.6	73.3	73.3	71.0	71.0	71.0	71.0	71.0	71.0	71.0	71.0
77.5°	64.2	61.9	61.9	61.9	61.9	61.9	61.9	64.2	64.2	64.2	64.2
80°	55.0	52.7	52.7	52.7	52.7	52.7	52.7	52.7	52.7	52.7	52.7
82.5°	43.5	41.2	41.2	41.2	41.2	41.2	41.2	41.2	41.2	41.2	41.2
85°	32.1	29.8	29.8	29.8	32.1	32.1	32.1	32.1	32.1	32.1	32.1
87.5°	20.6	18.3	18.3	18.3	20.6	20.6	20.6	20.6	18.3	18.3	18.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968
 CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968

CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9
2.5°	1443.7	1443.7	1443.7	1441.4	1439.1	1436.8	1434.5	1441.4	1446.0	1452.8	1457.4
5°	1173.3	1177.8	1180.1	1187.0	1193.9	1200.8	1207.6	1212.2	1216.8	1219.1	1223.7
7.5°	884.5	896.0	905.2	914.3	923.5	930.4	939.5	946.4	953.3	960.1	967.0
10°	671.4	676.0	678.3	687.5	694.3	703.5	710.4	717.2	724.1	728.7	735.6
12.5°	545.4	540.8	538.5	538.5	538.5	538.5	538.5	543.1	547.7	552.3	556.8
15°	440.0	437.7	435.4	433.1	430.8	426.2	423.9	428.5	433.1	437.7	442.3
17.5°	368.9	368.9	368.9	366.6	364.4	362.1	359.8	362.1	364.4	364.4	366.6
20°	316.2	318.5	320.8	323.1	323.1	325.4	325.4	327.7	330.0	330.0	332.3
22.5°	284.1	286.4	286.4	286.4	288.7	288.7	288.7	291.0	293.3	295.6	297.9
25°	258.9	258.9	256.7	256.7	258.9	258.9	258.9	258.9	261.2	261.2	261.2
27.5°	245.2	242.9	242.9	242.9	242.9	240.6	240.6	240.6	240.6	240.6	240.6
30°	238.3	236.0	233.7	231.4	231.4	229.2	226.9	226.9	226.9	226.9	226.9
32.5°	236.0	231.4	226.9	224.6	224.6	222.3	220.0	217.7	217.7	215.4	213.1
35°	210.8	208.5	208.5	206.2	203.9	201.7	199.4	199.4	199.4	197.1	197.1
37.5°	183.3	185.6	185.6	185.6	187.9	187.9	187.9	187.9	190.2	190.2	190.2
40°	171.9	171.9	171.9	174.2	176.4	176.4	178.7	178.7	181.0	181.0	181.0
42.5°	162.7	160.4	160.4	162.7	162.7	165.0	165.0	167.3	169.6	169.6	171.9
45°	158.1	155.8	155.8	155.8	155.8	153.5	153.5	155.8	158.1	160.4	162.7
47.5°	148.9	148.9	146.7	146.7	146.7	146.7	146.7	146.7	148.9	148.9	148.9
50°	144.4	144.4	142.1	142.1	142.1	142.1	142.1	142.1	142.1	142.1	142.1
52.5°	139.8	137.5	137.5	137.5	137.5	135.2	135.2	135.2	135.2	135.2	135.2
55°	132.9	130.6	130.6	130.6	130.6	130.6	130.6	130.6	132.9	132.9	132.9
57.5°	126.0	123.7	123.7	123.7	126.0	126.0	126.0	126.0	128.3	128.3	128.3
60°	119.2	119.2	119.2	119.2	119.2	119.2	119.2	121.5	121.5	123.7	123.7
62.5°	112.3	112.3	112.3	112.3	114.6	114.6	114.6	114.6	116.9	116.9	116.9
65°	105.4	105.4	105.4	105.4	107.7	107.7	107.7	107.7	107.7	107.7	107.7
67.5°	98.5	98.5	98.5	98.5	98.5	98.5	98.5	100.8	100.8	103.1	103.1
70°	89.4	87.1	87.1	89.4	89.4	91.7	91.7	94.0	94.0	96.2	96.2
72.5°	80.2	80.2	80.2	80.2	80.2	80.2	80.2	82.5	84.8	84.8	87.1
75°	71.0	71.0	71.0	71.0	73.3	73.3	73.3	75.6	75.6	77.9	77.9
77.5°	64.2	61.9	61.9	61.9	64.2	64.2	64.2	66.5	66.5	68.7	68.7
80°	52.7	52.7	52.7	52.7	55.0	55.0	55.0	55.0	57.3	57.3	57.3
82.5°	43.5	43.5	43.5	43.5	43.5	43.5	43.5	43.5	45.8	45.8	45.8
85°	32.1	32.1	32.1	32.1	34.4	34.4	34.4	34.4	34.4	34.4	34.4
87.5°	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	22.9	22.9	22.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968
 CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968

CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9
2.5°	1457.4	1457.4	1457.4	1457.4	1462.0	1464.3	1468.9	1471.2	1468.9	1466.6	1462.0
5°	1226.0	1228.3	1228.3	1230.5	1230.5	1230.5	1230.5	1230.5	1235.1	1239.7	1244.3
7.5°	969.3	971.6	973.9	976.2	976.2	976.2	973.9	973.9	976.2	976.2	978.5
10°	742.5	751.6	758.5	765.4	760.8	753.9	749.3	742.5	742.5	742.5	740.2
12.5°	561.4	563.7	568.3	570.6	568.3	568.3	566.0	563.7	566.0	570.6	572.9
15°	444.6	444.6	446.8	446.8	449.1	451.4	451.4	453.7	458.3	460.6	465.2
17.5°	368.9	371.2	371.2	373.5	373.5	375.8	375.8	375.8	380.4	385.0	391.9
20°	332.3	332.3	332.3	332.3	332.3	330.0	330.0	327.7	330.0	334.6	336.9
22.5°	297.9	300.2	300.2	300.2	297.9	295.6	291.0	288.7	288.7	291.0	291.0
25°	261.2	258.9	258.9	256.7	256.7	258.9	258.9	258.9	261.2	261.2	263.5
27.5°	240.6	238.3	238.3	236.0	236.0	238.3	238.3	238.3	238.3	238.3	238.3
30°	224.6	224.6	222.3	220.0	222.3	222.3	224.6	224.6	226.9	226.9	229.2
32.5°	213.1	210.8	210.8	208.5	210.8	210.8	213.1	213.1	215.4	217.7	217.7
35°	197.1	197.1	197.1	197.1	197.1	197.1	194.8	194.8	194.8	194.8	194.8
37.5°	187.9	187.9	185.6	183.3	183.3	183.3	183.3	183.3	181.0	178.7	176.4
40°	181.0	178.7	178.7	176.4	174.2	174.2	171.9	169.6	169.6	167.3	167.3
42.5°	171.9	169.6	169.6	167.3	165.0	165.0	162.7	160.4	160.4	160.4	158.1
45°	160.4	160.4	158.1	155.8	155.8	155.8	153.5	153.5	153.5	153.5	151.2
47.5°	148.9	148.9	146.7	146.7	146.7	146.7	144.4	144.4	144.4	144.4	144.4
50°	142.1	142.1	142.1	142.1	142.1	142.1	139.8	139.8	139.8	139.8	139.8
52.5°	135.2	135.2	135.2	135.2	135.2	135.2	135.2	135.2	135.2	135.2	135.2
55°	132.9	132.9	132.9	132.9	132.9	132.9	130.6	130.6	130.6	132.9	132.9
57.5°	128.3	128.3	126.0	126.0	126.0	126.0	126.0	126.0	126.0	126.0	126.0
60°	123.7	123.7	123.7	123.7	123.7	123.7	123.7	123.7	123.7	123.7	123.7
62.5°	116.9	116.9	116.9	116.9	116.9	119.2	119.2	119.2	119.2	119.2	116.9
65°	107.7	110.0	110.0	110.0	110.0	110.0	110.0	110.0	110.0	110.0	110.0
67.5°	103.1	103.1	103.1	103.1	103.1	103.1	103.1	103.1	103.1	103.1	103.1
70°	96.2	96.2	94.0	94.0	94.0	96.2	96.2	96.2	96.2	96.2	96.2
72.5°	87.1	87.1	87.1	87.1	87.1	87.1	87.1	87.1	87.1	89.4	89.4
75°	77.9	77.9	77.9	77.9	77.9	77.9	77.9	77.9	77.9	77.9	77.9
77.5°	68.7	68.7	66.5	66.5	66.5	68.7	68.7	68.7	68.7	71.0	71.0
80°	57.3	57.3	57.3	57.3	57.3	57.3	57.3	57.3	57.3	59.6	59.6
82.5°	45.8	45.8	45.8	45.8	45.8	45.8	45.8	45.8	45.8	48.1	48.1
85°	34.4	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7	39.0	39.0
87.5°	22.9	22.9	22.9	22.9	22.9	22.9	20.6	20.6	20.6	20.6	18.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968
 CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675968

CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9
2.5°	1459.7	1462.0	1464.3	1464.3	1466.6	1468.9	1468.9	1478.0	1487.2	1491.8	1496.4
5°	1248.9	1246.6	1246.6	1244.3	1242.0	1248.9	1255.8	1269.5	1283.3	1285.5	1290.1
7.5°	978.5	980.8	983.1	983.1	985.4	978.5	969.3	971.6	973.9	985.4	994.5
10°	740.2	742.5	744.7	744.7	747.0	744.7	740.2	747.0	753.9	763.1	774.5
12.5°	575.2	582.0	588.9	593.5	600.4	605.0	607.3	616.4	623.3	634.8	646.2
15°	469.8	474.3	478.9	483.5	488.1	492.7	497.3	506.4	515.6	529.3	543.1
17.5°	396.4	396.4	398.7	398.7	398.7	403.3	407.9	412.5	414.8	428.5	442.3
20°	339.1	336.9	334.6	332.3	330.0	334.6	336.9	339.1	341.4	350.6	357.5
22.5°	291.0	291.0	293.3	293.3	293.3	291.0	286.4	288.7	288.7	293.3	300.2
25°	263.5	263.5	263.5	261.2	261.2	263.5	265.8	265.8	263.5	265.8	268.1
27.5°	238.3	240.6	240.6	242.9	242.9	245.2	245.2	245.2	245.2	247.5	249.8
30°	229.2	229.2	231.4	231.4	231.4	233.7	236.0	236.0	236.0	238.3	242.9
32.5°	220.0	222.3	224.6	226.9	229.2	231.4	231.4	233.7	233.7	236.0	238.3
35°	194.8	192.5	192.5	190.2	187.9	187.9	187.9	187.9	185.6	187.9	187.9
37.5°	174.2	174.2	174.2	171.9	171.9	174.2	174.2	174.2	174.2	176.4	176.4
40°	165.0	165.0	165.0	165.0	165.0	165.0	165.0	167.3	167.3	169.6	171.9
42.5°	158.1	158.1	158.1	158.1	158.1	160.4	160.4	160.4	160.4	162.7	162.7
45°	151.2	151.2	151.2	151.2	151.2	151.2	151.2	153.5	153.5	155.8	158.1
47.5°	144.4	144.4	144.4	144.4	144.4	146.7	148.9	148.9	148.9	151.2	151.2
50°	139.8	139.8	139.8	139.8	139.8	142.1	142.1	144.4	144.4	146.7	148.9
52.5°	135.2	135.2	135.2	135.2	135.2	137.5	137.5	139.8	139.8	142.1	144.4
55°	132.9	132.9	132.9	130.6	130.6	132.9	132.9	135.2	135.2	137.5	137.5
57.5°	126.0	126.0	126.0	126.0	126.0	126.0	126.0	128.3	128.3	130.6	132.9
60°	123.7	123.7	121.5	121.5	119.2	121.5	121.5	123.7	123.7	126.0	126.0
62.5°	116.9	116.9	116.9	114.6	114.6	116.9	116.9	116.9	116.9	119.2	121.5
65°	110.0	110.0	110.0	107.7	107.7	110.0	110.0	110.0	110.0	112.3	114.6
67.5°	103.1	103.1	103.1	100.8	100.8	100.8	100.8	103.1	103.1	105.4	107.7
70°	96.2	96.2	96.2	94.0	94.0	94.0	91.7	94.0	96.2	98.5	98.5
72.5°	89.4	89.4	89.4	87.1	87.1	87.1	84.8	87.1	87.1	89.4	89.4
75°	77.9	77.9	77.9	77.9	77.9	77.9	75.6	75.6	75.6	77.9	77.9
77.5°	71.0	71.0	71.0	68.7	68.7	68.7	66.5	66.5	66.5	68.7	68.7
80°	59.6	59.6	59.6	57.3	57.3	57.3	55.0	55.0	55.0	57.3	57.3
82.5°	48.1	48.1	48.1	45.8	45.8	45.8	43.5	43.5	43.5	45.8	45.8
85°	39.0	39.0	39.0	39.0	39.0	39.0	36.7	36.7	36.7	39.0	41.2
87.5°	18.3	18.3	20.6	20.6	20.6	20.6	18.3	18.3	16.0	16.0	18.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968
 CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675968

CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9
2.5°	1500.9	1505.5	1517.0	1526.2	1537.6	1546.8	1553.7	1562.8	1569.7	1576.6	1581.2
5°	1292.4	1294.7	1306.2	1317.6	1326.8	1338.3	1354.3	1370.3	1386.4	1402.4	1413.9
7.5°	1006.0	1015.1	1028.9	1044.9	1058.7	1072.4	1088.5	1106.8	1122.8	1138.9	1154.9
10°	783.7	792.9	806.6	820.4	831.8	845.6	863.9	882.2	900.6	918.9	937.2
12.5°	657.7	669.1	685.2	701.2	715.0	731.0	753.9	774.5	797.5	818.1	841.0
15°	554.5	568.3	588.9	611.8	632.5	653.1	676.0	698.9	719.5	742.5	765.4
17.5°	456.0	469.8	488.1	508.7	527.1	545.4	572.9	598.1	625.6	650.8	676.0
20°	366.6	373.5	391.9	410.2	428.5	446.8	467.5	488.1	508.7	529.3	561.4
22.5°	304.8	309.4	318.5	325.4	334.6	341.4	362.1	382.7	401.0	421.6	451.4
25°	268.1	270.4	277.3	281.9	288.7	293.3	307.1	318.5	332.3	343.7	371.2
27.5°	249.8	252.1	254.4	256.7	258.9	261.2	270.4	279.6	286.4	295.6	320.8
30°	245.2	247.5	254.4	258.9	265.8	270.4	275.0	279.6	284.1	288.7	304.8
32.5°	240.6	242.9	242.9	240.6	240.6	238.3	242.9	245.2	249.8	252.1	265.8
35°	190.2	190.2	192.5	194.8	197.1	199.4	206.2	210.8	217.7	222.3	233.7
37.5°	178.7	178.7	181.0	185.6	187.9	190.2	194.8	199.4	203.9	208.5	220.0
40°	171.9	174.2	176.4	178.7	181.0	183.3	187.9	190.2	194.8	197.1	206.2
42.5°	165.0	165.0	167.3	171.9	174.2	176.4	181.0	183.3	187.9	190.2	199.4
45°	160.4	162.7	165.0	167.3	167.3	169.6	174.2	178.7	181.0	185.6	194.8
47.5°	153.5	153.5	158.1	160.4	165.0	167.3	171.9	174.2	178.7	181.0	190.2
50°	148.9	151.2	155.8	158.1	162.7	165.0	171.9	176.4	183.3	187.9	192.5
52.5°	144.4	146.7	151.2	153.5	158.1	160.4	169.6	178.7	185.6	194.8	194.8
55°	139.8	139.8	144.4	151.2	155.8	160.4	165.0	171.9	176.4	181.0	181.0
57.5°	132.9	135.2	139.8	146.7	151.2	155.8	160.4	165.0	167.3	171.9	169.6
60°	128.3	128.3	135.2	142.1	148.9	155.8	155.8	155.8	153.5	153.5	153.5
62.5°	121.5	123.7	132.9	144.4	153.5	162.7	155.8	148.9	142.1	135.2	137.5
65°	116.9	119.2	123.7	130.6	135.2	139.8	135.2	132.9	128.3	123.7	126.0
67.5°	107.7	110.0	112.3	112.3	114.6	114.6	114.6	114.6	114.6	114.6	116.9
70°	100.8	100.8	100.8	103.1	103.1	103.1	103.1	103.1	103.1	103.1	105.4
72.5°	91.7	91.7	91.7	91.7	91.7	91.7	91.7	91.7	91.7	91.7	94.0
75°	80.2	80.2	80.2	80.2	80.2	80.2	80.2	80.2	80.2	80.2	82.5
77.5°	71.0	71.0	71.0	71.0	71.0	71.0	71.0	71.0	68.7	68.7	71.0
80°	59.6	59.6	59.6	59.6	57.3	57.3	57.3	57.3	57.3	57.3	59.6
82.5°	48.1	48.1	48.1	48.1	45.8	45.8	45.8	45.8	43.5	43.5	45.8
85°	43.5	45.8	45.8	48.1	48.1	48.1	45.8	43.5	41.2	39.0	39.0
87.5°	18.3	18.3	18.3	18.3	16.0	16.0	16.0	16.0	16.0	16.0	16.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968
 CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968

CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9
2.5°	1588.0	1592.6	1597.2	1604.1	1613.2	1620.1	1627.0	1640.7	1656.8	1670.5	1684.3
5°	1425.3	1436.8	1448.2	1462.0	1475.7	1487.2	1500.9	1528.4	1555.9	1581.2	1608.7
7.5°	1168.7	1184.7	1198.5	1221.4	1242.0	1264.9	1285.5	1319.9	1352.0	1386.4	1418.5
10°	955.6	973.9	992.2	1022.0	1054.1	1083.9	1113.7	1141.2	1171.0	1198.5	1226.0
12.5°	863.9	884.5	907.4	925.8	946.4	964.7	983.1	1015.1	1047.2	1079.3	1111.4
15°	788.3	811.2	834.1	857.0	877.7	900.6	921.2	948.7	978.5	1006.0	1033.5
17.5°	701.2	724.1	749.3	774.5	799.7	824.9	850.2	889.1	928.1	964.7	1003.7
20°	591.2	623.3	653.1	687.5	721.8	756.2	790.6	831.8	873.1	912.0	953.3
22.5°	481.2	511.0	540.8	582.0	623.3	662.3	703.5	758.5	811.2	866.2	918.9
25°	401.0	428.5	456.0	501.8	545.4	591.2	634.8	701.2	765.4	831.8	896.0
27.5°	346.0	371.2	396.4	444.6	492.7	538.5	586.6	660.0	731.0	804.3	875.4
30°	320.8	336.9	352.9	398.7	444.6	488.1	533.9	605.0	676.0	747.0	818.1
32.5°	279.6	293.3	307.1	348.3	389.6	428.5	469.8	543.1	614.1	687.5	758.5
35°	247.5	258.9	270.4	309.4	346.0	385.0	421.6	495.0	568.3	641.6	715.0
37.5°	229.2	240.6	249.8	284.1	320.8	355.2	389.6	462.9	533.9	607.3	678.3
40°	215.4	222.3	231.4	265.8	297.9	332.3	364.4	430.8	499.6	566.0	632.5
42.5°	206.2	215.4	222.3	252.1	284.1	313.9	343.7	407.9	472.1	533.9	598.1
45°	203.9	213.1	222.3	247.5	272.7	295.6	320.8	382.7	444.6	506.4	568.3
47.5°	199.4	206.2	215.4	236.0	254.4	275.0	293.3	355.2	417.1	476.6	538.5
50°	197.1	199.4	203.9	222.3	240.6	258.9	277.3	339.1	401.0	462.9	524.8
52.5°	194.8	194.8	194.8	210.8	226.9	240.6	256.7	318.5	382.7	444.6	506.4
55°	181.0	178.7	178.7	194.8	208.5	224.6	238.3	300.2	362.1	421.6	483.5
57.5°	167.3	165.0	162.7	176.4	190.2	203.9	217.7	279.6	343.7	405.6	467.5
60°	153.5	151.2	151.2	165.0	176.4	190.2	201.7	265.8	327.7	391.9	453.7
62.5°	137.5	139.8	139.8	151.2	165.0	176.4	187.9	252.1	318.5	382.7	446.8
65°	126.0	128.3	128.3	142.1	155.8	169.6	183.3	245.2	309.4	371.2	433.1
67.5°	116.9	119.2	119.2	135.2	148.9	165.0	178.7	233.7	291.0	346.0	401.0
70°	107.7	107.7	110.0	126.0	142.1	158.1	174.2	222.3	270.4	316.2	364.4
72.5°	96.2	98.5	100.8	116.9	130.6	146.7	160.4	203.9	247.5	291.0	334.6
75°	84.8	87.1	89.4	103.1	116.9	130.6	144.4	185.6	224.6	265.8	304.8
77.5°	75.6	77.9	80.2	91.7	103.1	114.6	126.0	155.8	187.9	217.7	247.5
80°	61.9	61.9	64.2	73.3	82.5	89.4	98.5	119.2	139.8	158.1	178.7
82.5°	45.8	48.1	48.1	55.0	59.6	66.5	71.0	82.5	91.7	103.1	112.3
85°	39.0	36.7	36.7	41.2	43.5	48.1	50.4	57.3	61.9	68.7	73.3
87.5°	16.0	13.7	13.7	16.0	20.6	22.9	25.2	25.2	27.5	27.5	27.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968
 CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968

CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9
2.5°	1691.1	1695.7	1702.6	1707.2	1718.6	1727.8	1739.3	1748.4	1755.3	1766.8	1762.2
5°	1629.3	1649.9	1670.5	1691.1	1707.2	1723.2	1737.0	1753.0	1771.3	1805.7	1814.9
7.5°	1446.0	1473.5	1498.7	1526.2	1558.2	1590.3	1622.4	1654.5	1684.3	1727.8	1755.3
10°	1264.9	1303.9	1340.5	1379.5	1409.3	1439.1	1466.6	1496.4	1537.6	1581.2	1631.6
12.5°	1150.3	1189.3	1228.3	1267.2	1310.8	1352.0	1395.5	1436.8	1475.7	1510.1	1567.4
15°	1074.7	1118.3	1159.5	1200.8	1253.5	1303.9	1356.6	1407.0	1464.3	1510.1	1549.1
17.5°	1056.4	1109.1	1159.5	1212.2	1267.2	1322.2	1377.2	1432.2	1489.5	1558.2	1608.7
20°	1024.3	1095.3	1166.4	1237.4	1308.5	1377.2	1448.2	1517.0	1592.6	1675.1	1698.0
22.5°	1006.0	1090.8	1177.8	1262.6	1358.9	1457.4	1553.7	1649.9	1730.1	1792.0	1860.7
25°	1003.7	1109.1	1216.8	1322.2	1443.7	1562.8	1684.3	1803.4	1906.5	1968.4	2023.4
27.5°	1001.4	1129.7	1255.8	1381.8	1530.7	1677.4	1826.3	1973.0	2069.2	2158.6	2204.4
30°	973.9	1127.4	1283.3	1436.8	1604.1	1771.3	1938.6	2105.9	2204.4	2266.3	2289.2
32.5°	939.5	1120.6	1301.6	1482.6	1672.8	1863.0	2050.9	2241.1	2319.0	2371.7	2353.4
35°	912.0	1111.4	1308.5	1505.5	1707.2	1911.1	2112.8	2314.4	2426.7	2500.1	2470.3
37.5°	886.8	1095.3	1303.9	1512.4	1748.4	1984.5	2220.5	2456.5	2564.2	2642.1	2607.8
40°	857.0	1079.3	1303.9	1526.2	1796.6	2064.7	2335.1	2603.2	2743.0	2809.4	2756.7
42.5°	831.8	1063.3	1297.0	1528.4	1817.2	2105.9	2394.6	2683.4	2839.2	2933.2	2866.7
45°	799.7	1031.2	1260.3	1491.8	1810.3	2128.8	2445.1	2763.6	2944.6	3017.9	2926.3
47.5°	765.4	994.5	1221.4	1448.2	1787.4	2126.5	2465.7	2804.8	2972.1	3059.2	2974.4
50°	753.9	983.1	1209.9	1439.1	1805.7	2174.7	2541.3	2907.9	3029.4	3100.4	2988.2
52.5°	751.6	994.5	1239.7	1482.6	1851.6	2218.2	2587.1	2953.8	3052.3	3127.9	3027.1
55°	744.7	1008.3	1269.5	1530.7	1915.7	2303.0	2688.0	3072.9	3171.5	3226.5	3150.8
57.5°	751.6	1035.8	1317.6	1601.8	1998.2	2394.6	2791.1	3187.5	3306.7	3345.6	3329.6
60°	756.2	1058.7	1358.9	1661.4	2048.6	2435.9	2823.2	3210.4	3334.2	3430.4	3448.7
62.5°	744.7	1042.6	1338.3	1636.1	1986.8	2337.4	2688.0	3038.6	3242.5	3384.6	3467.1
65°	710.4	985.4	1262.6	1537.6	1860.7	2186.1	2509.2	2832.3	3047.7	3258.6	3325.0
67.5°	634.8	868.5	1102.2	1336.0	1617.8	1899.7	2179.2	2461.1	2731.5	2935.4	3027.1
70°	550.0	733.3	918.9	1102.2	1358.9	1615.5	1872.2	2128.8	2367.1	2591.7	2678.8
72.5°	478.9	621.0	765.4	907.4	1090.8	1271.8	1455.1	1636.1	1918.0	2142.6	2227.4
75°	407.9	511.0	611.8	715.0	841.0	967.0	1090.8	1216.8	1416.2	1617.8	1702.6
77.5°	313.9	382.7	449.1	515.6	602.7	687.5	774.5	859.3	999.1	1150.3	1193.9
80°	217.7	256.7	293.3	332.3	401.0	469.8	538.5	607.3	698.9	783.7	850.2
82.5°	135.2	160.4	183.3	206.2	261.2	316.2	368.9	423.9	460.6	465.2	531.6
85°	87.1	103.1	116.9	130.6	162.7	197.1	229.2	261.2	233.7	217.7	258.9
87.5°	34.4	43.5	50.4	57.3	55.0	52.7	50.4	48.1	41.2	36.7	45.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968
 CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968

CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9
2.5°	1766.8	1773.6	1780.5	1785.1	1792.0	1794.3	1796.6	1796.6	1798.8	1801.1	1805.7
5°	1851.6	1865.3	1879.1	1890.5	1904.3	1915.7	1924.9	1936.3	1945.5	1945.5	1943.2
7.5°	1780.5	1814.9	1849.3	1883.6	1918.0	1943.2	1966.1	1991.3	2014.3	2018.8	2023.4
10°	1686.6	1723.2	1757.6	1794.3	1828.6	1867.6	1904.3	1940.9	1979.9	1986.8	1995.9
12.5°	1599.5	1643.0	1686.6	1727.8	1771.3	1798.8	1826.3	1851.6	1879.1	1897.4	1915.7
15°	1597.2	1633.9	1670.5	1704.9	1741.6	1757.6	1773.6	1787.4	1803.4	1803.4	1805.7
17.5°	1649.9	1672.8	1695.7	1716.4	1739.3	1741.6	1746.1	1748.4	1750.7	1743.9	1737.0
20°	1753.0	1762.2	1771.3	1780.5	1789.7	1773.6	1759.9	1743.9	1727.8	1709.5	1693.4
22.5°	1904.3	1883.6	1863.0	1842.4	1821.8	1794.3	1764.5	1737.0	1707.2	1684.3	1661.4
25°	2046.3	2021.1	1995.9	1970.7	1945.5	1885.9	1826.3	1764.5	1704.9	1679.7	1654.5
27.5°	2236.5	2197.6	2158.6	2119.7	2080.7	2000.5	1920.3	1840.1	1759.9	1716.4	1675.1
30°	2282.4	2238.8	2195.3	2149.5	2105.9	2028.0	1952.4	1874.5	1796.6	1746.1	1698.0
32.5°	2348.8	2298.4	2248.0	2197.6	2147.2	2071.5	1995.9	1918.0	1842.4	1796.6	1748.4
35°	2458.8	2401.5	2344.2	2284.7	2227.4	2149.5	2073.8	1995.9	1918.0	1865.3	1814.9
37.5°	2552.8	2486.3	2419.9	2353.4	2286.9	2218.2	2147.2	2078.4	2007.4	1954.7	1904.3
40°	2658.2	2584.8	2511.5	2440.5	2367.1	2303.0	2238.8	2172.4	2108.2	2067.0	2025.7
42.5°	2749.8	2660.5	2573.4	2486.3	2396.9	2353.4	2312.1	2268.6	2225.1	2204.4	2181.5
45°	2814.0	2731.5	2646.7	2564.2	2481.7	2449.6	2417.6	2385.5	2353.4	2374.0	2394.6
47.5°	2841.5	2775.0	2710.9	2646.7	2580.3	2591.7	2603.2	2612.3	2623.8	2651.3	2681.1
50°	2866.7	2830.0	2791.1	2754.4	2715.5	2759.0	2800.2	2843.8	2887.3	2944.6	3001.9
52.5°	2917.1	2896.5	2878.2	2857.5	2836.9	2912.5	2988.2	3063.8	3139.4	3203.6	3267.7
55°	3068.4	3052.3	3036.3	3017.9	3001.9	3109.6	3215.0	3322.7	3430.4	3496.9	3563.3
57.5°	3276.9	3267.7	3256.3	3247.1	3235.6	3341.0	3444.2	3547.3	3652.7	3716.9	3783.3
60°	3435.0	3437.3	3437.3	3439.6	3439.6	3519.8	3600.0	3682.5	3762.7	3817.7	3875.0
62.5°	3519.8	3515.2	3510.6	3506.0	3501.5	3567.9	3634.4	3700.8	3767.3	3808.5	3849.8
65°	3428.1	3453.3	3478.5	3503.7	3529.0	3538.1	3545.0	3554.2	3561.0	3586.2	3611.4
67.5°	3121.1	3171.5	3219.6	3270.0	3318.1	3283.8	3251.7	3217.3	3182.9	3189.8	3194.4
70°	2779.6	2836.9	2896.5	2953.8	3011.1	2930.9	2850.7	2768.2	2688.0	2660.5	2633.0
72.5°	2344.2	2394.6	2447.3	2497.8	2548.2	2449.6	2353.4	2254.9	2156.3	2108.2	2060.1
75°	1792.0	1851.6	1913.4	1973.0	2032.6	1922.6	1810.3	1700.3	1588.0	1555.9	1526.2
77.5°	1306.2	1377.2	1448.2	1519.3	1590.3	1491.8	1393.2	1292.4	1193.9	1175.6	1157.2
80°	951.0	1006.0	1058.7	1113.7	1166.4	1109.1	1051.8	994.5	937.2	934.9	932.7
82.5°	641.6	689.7	735.6	783.7	829.5	806.6	786.0	763.1	740.2	763.1	788.3
85°	330.0	396.4	465.2	531.6	598.1	591.2	586.6	579.8	572.9	602.7	630.2
87.5°	66.5	123.7	181.0	236.0	293.3	279.6	265.8	249.8	236.0	245.2	252.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968
 CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968

CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9
2.5°	1808.0	1810.3	1810.3	1810.3	1810.3	1810.3	1805.7	1803.4	1798.8	1794.3	1787.4
5°	1943.2	1940.9	1931.8	1922.6	1911.1	1902.0	1895.1	1885.9	1879.1	1869.9	1856.1
7.5°	2028.0	2032.6	2016.5	2002.8	1986.8	1970.7	1954.7	1938.6	1922.6	1906.5	1874.5
10°	2002.8	2009.7	2000.5	1991.3	1979.9	1970.7	1952.4	1931.8	1913.4	1892.8	1853.8
12.5°	1931.8	1950.1	1945.5	1940.9	1936.3	1931.8	1920.3	1906.5	1895.1	1881.3	1837.8
15°	1805.7	1805.7	1808.0	1810.3	1810.3	1812.6	1814.9	1817.2	1819.5	1821.8	1796.6
17.5°	1730.1	1723.2	1723.2	1723.2	1723.2	1723.2	1732.4	1743.9	1753.0	1762.2	1755.3
20°	1675.1	1659.1	1656.8	1656.8	1654.5	1652.2	1668.2	1686.6	1702.6	1718.6	1727.8
22.5°	1638.4	1615.5	1613.2	1610.9	1608.7	1606.4	1627.0	1647.6	1668.2	1688.9	1720.9
25°	1629.3	1604.1	1606.4	1608.7	1608.7	1610.9	1627.0	1643.0	1659.1	1675.1	1730.1
27.5°	1631.6	1590.3	1592.6	1594.9	1594.9	1597.2	1622.4	1645.3	1670.5	1693.4	1762.2
30°	1647.6	1599.5	1594.9	1590.3	1585.7	1581.2	1615.5	1649.9	1684.3	1718.6	1771.3
32.5°	1702.6	1656.8	1645.3	1633.9	1622.4	1610.9	1652.2	1691.1	1732.4	1771.3	1814.9
35°	1762.2	1711.8	1707.2	1702.6	1695.7	1691.1	1727.8	1766.8	1803.4	1840.1	1879.1
37.5°	1851.6	1801.1	1796.6	1789.7	1785.1	1778.2	1819.5	1858.4	1899.7	1938.6	1973.0
40°	1984.5	1943.2	1940.9	1940.9	1938.6	1936.3	1968.4	2002.8	2034.9	2067.0	2089.9
42.5°	2160.9	2140.3	2147.2	2156.3	2163.2	2170.1	2195.3	2222.8	2248.0	2273.2	2266.3
45°	2415.3	2435.9	2438.2	2440.5	2442.8	2445.1	2451.9	2461.1	2468.0	2474.8	2447.3
47.5°	2708.6	2736.1	2749.8	2763.6	2775.0	2788.8	2779.6	2768.2	2759.0	2747.5	2678.8
50°	3056.9	3114.2	3111.9	3109.6	3105.0	3102.7	3084.4	3066.1	3045.4	3027.1	2926.3
52.5°	3331.9	3396.0	3407.5	3419.0	3430.4	3441.9	3407.5	3373.1	3336.5	3302.1	3176.1
55°	3627.5	3693.9	3696.2	3698.5	3698.5	3700.8	3652.7	3604.6	3554.2	3506.0	3375.4
57.5°	3847.5	3911.6	3904.8	3900.2	3893.3	3886.4	3829.1	3771.9	3714.6	3657.3	3526.7
60°	3930.0	3985.0	3971.2	3957.5	3941.4	3927.7	3884.1	3840.6	3794.8	3751.2	3625.2
62.5°	3891.0	3932.3	3911.6	3893.3	3872.7	3852.1	3797.1	3739.8	3684.8	3627.5	3535.8
65°	3634.4	3659.6	3632.1	3606.9	3581.7	3554.2	3508.3	3462.5	3414.4	3368.5	3306.7
67.5°	3201.3	3205.8	3203.6	3201.3	3199.0	3196.7	3130.2	3063.8	2995.0	2928.6	2924.0
70°	2607.8	2580.3	2584.8	2591.7	2596.3	2600.9	2550.5	2502.3	2451.9	2401.5	2424.4
72.5°	2012.0	1963.8	1975.3	1989.0	2000.5	2012.0	1970.7	1931.8	1890.5	1849.3	1881.3
75°	1494.1	1464.3	1475.7	1489.5	1500.9	1512.4	1496.4	1480.3	1462.0	1446.0	1475.7
77.5°	1138.9	1120.6	1122.8	1122.8	1125.1	1125.1	1127.4	1132.0	1134.3	1136.6	1168.7
80°	928.1	925.8	923.5	921.2	916.6	914.3	937.2	960.1	983.1	1006.0	1022.0
82.5°	811.2	834.1	820.4	808.9	795.2	781.4	802.0	822.7	843.3	863.9	857.0
85°	660.0	687.5	662.3	637.0	609.5	584.3	602.7	618.7	637.0	653.1	643.9
87.5°	261.2	268.1	226.9	187.9	146.7	105.4	167.3	226.9	288.7	348.3	357.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968

CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968

CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9	1649.9
2.5°	1780.5	1771.3	1764.5	1762.2	1757.6	1755.3	1750.7	1746.1	1739.3	1734.7	1727.8
5°	1840.1	1826.3	1810.3	1787.4	1766.8	1743.9	1720.9	1700.3	1679.7	1656.8	1636.1
7.5°	1842.4	1810.3	1778.2	1748.4	1716.4	1686.6	1654.5	1627.0	1597.2	1567.4	1539.9
10°	1817.2	1778.2	1739.3	1700.3	1663.6	1624.7	1585.7	1553.7	1519.3	1484.9	1452.8
12.5°	1796.6	1753.0	1709.5	1663.6	1620.1	1574.3	1528.4	1496.4	1464.3	1432.2	1400.1
15°	1771.3	1743.9	1718.6	1677.4	1636.1	1594.9	1553.7	1510.1	1468.9	1425.3	1381.8
17.5°	1750.7	1743.9	1737.0	1709.5	1682.0	1652.2	1624.7	1581.2	1537.6	1491.8	1448.2
20°	1739.3	1748.4	1757.6	1743.9	1730.1	1714.1	1700.3	1668.2	1636.1	1601.8	1569.7
22.5°	1753.0	1787.4	1819.5	1821.8	1826.3	1828.6	1830.9	1801.1	1771.3	1739.3	1709.5
25°	1785.1	1840.1	1895.1	1924.9	1954.7	1986.8	2016.5	1998.2	1979.9	1961.5	1943.2
27.5°	1828.6	1897.4	1966.1	2009.7	2050.9	2094.5	2138.0	2135.7	2133.4	2128.8	2126.5
30°	1821.8	1874.5	1927.2	1979.9	2032.6	2085.3	2138.0	2165.5	2190.7	2218.2	2245.7
32.5°	1860.7	1904.3	1950.1	2005.1	2060.1	2117.4	2172.4	2229.7	2284.7	2341.9	2399.2
35°	1920.3	1959.3	2000.5	2060.1	2122.0	2181.5	2243.4	2312.1	2383.2	2454.2	2523.0
37.5°	2009.7	2044.0	2080.7	2131.1	2183.8	2234.2	2286.9	2387.8	2488.6	2591.7	2692.5
40°	2112.8	2135.7	2158.6	2206.7	2254.9	2303.0	2351.1	2477.1	2603.2	2729.2	2855.2
42.5°	2261.7	2254.9	2248.0	2286.9	2328.2	2367.1	2408.4	2523.0	2637.5	2752.1	2866.7
45°	2419.9	2392.4	2364.9	2383.2	2403.8	2422.1	2442.8	2559.6	2676.5	2795.7	2912.5
47.5°	2610.0	2541.3	2472.6	2456.5	2440.5	2422.1	2406.1	2532.1	2658.2	2786.5	2912.5
50°	2825.5	2722.3	2621.5	2580.3	2536.7	2495.5	2451.9	2555.1	2660.5	2765.9	2869.0
52.5°	3050.0	2921.7	2795.7	2731.5	2667.3	2600.9	2536.7	2623.8	2713.2	2802.5	2889.6
55°	3242.5	3111.9	2979.0	2903.4	2827.7	2752.1	2676.5	2763.6	2850.7	2937.7	3024.8
57.5°	3396.0	3265.4	3134.8	3063.8	2990.4	2919.4	2846.1	2928.6	3013.4	3098.1	3180.6
60°	3501.5	3375.4	3249.4	3180.6	3111.9	3043.1	2974.4	3072.9	3171.5	3272.3	3370.8
62.5°	3446.5	3354.8	3263.1	3233.3	3203.6	3171.5	3141.7	3235.6	3327.3	3421.2	3515.2
65°	3244.8	3182.9	3121.1	3150.8	3182.9	3212.7	3244.8	3306.7	3368.5	3432.7	3494.6
67.5°	2917.1	2912.5	2905.7	2972.1	3038.6	3107.3	3173.8	3215.0	3254.0	3295.2	3336.5
70°	2447.3	2472.6	2495.5	2610.0	2724.6	2839.2	2953.8	2969.8	2985.9	3001.9	3017.9
72.5°	1915.7	1947.8	1982.2	2133.4	2282.4	2433.6	2584.8	2575.7	2566.5	2555.1	2545.9
75°	1507.8	1537.6	1569.7	1709.5	1849.3	1989.0	2128.8	2089.9	2053.2	2014.3	1975.3
77.5°	1203.1	1235.1	1269.5	1400.1	1530.7	1663.6	1794.3	1700.3	1606.4	1512.4	1418.5
80°	1035.8	1051.8	1065.6	1154.9	1242.0	1331.4	1420.7	1324.5	1226.0	1127.4	1031.2
82.5°	850.2	841.0	834.1	886.8	939.5	992.2	1044.9	953.3	861.6	767.7	676.0
85°	634.8	625.6	616.4	643.9	671.4	701.2	728.7	623.3	517.9	410.2	304.8
87.5°	368.9	378.1	387.3	417.1	446.8	478.9	508.7	401.0	293.3	183.3	75.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968
 CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675968
 CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1649.9	1649.9
2.5°	1714.1	1702.6
5°	1620.1	1604.1
7.5°	1517.0	1496.4
10°	1423.0	1395.5
12.5°	1363.5	1329.1
15°	1340.5	1299.3
17.5°	1409.3	1370.3
20°	1514.7	1462.0
22.5°	1643.0	1578.9
25°	1865.3	1787.4
27.5°	2046.3	1966.1
30°	2158.6	2071.5
32.5°	2282.4	2167.8
35°	2410.7	2300.7
37.5°	2566.5	2442.8
40°	2726.9	2598.6
42.5°	2781.9	2699.4
45°	2834.6	2756.7
47.5°	2846.1	2781.9
50°	2857.5	2848.4
52.5°	2889.6	2887.3
55°	3027.1	3029.4
57.5°	3196.7	3210.4
60°	3352.5	3336.5
62.5°	3432.7	3350.2
65°	3377.7	3263.1
67.5°	3212.7	3089.0
70°	2850.7	2683.4
72.5°	2399.2	2252.6
75°	1849.3	1725.5
77.5°	1315.3	1212.2
80°	925.8	822.7
82.5°	593.5	511.0
85°	268.1	233.7
87.5°	75.6	73.3
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P675968
CATALOG NUMBER: CCW-SA-1E-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)