

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675972

Luminaire Tested: **CCW-SA-2C-730-U-SLR**

Issue Date: 04/25/2023



Test Information

Test Method: LM-79-08
Report Number: P675972
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2C-730-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @615mA w/
SLR distribution lens
Light Source: (32) 3000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6832.5 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 9.7 fc

Type IV - Short - N/A

REPORT NUMBER: P675972
CATALOG NUMBER: CCW-SA-2C-730-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1405.8	0.0	1405.8
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	5426.7	0.0	5426.7
	% Fixture	79.4	0.0	79.4
Total	Lumens	6832.5	0.0	6832.5
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.5	2.5
10°-20°	358.0	5.2
20°-30°	523.7	7.7
30°-40°	737.8	10.8
40°-50°	1013.8	14.8
50°-60°	1381.9	20.2
60°-70°	1512.5	22.1
70°-80°	873.5	12.8
80°-90°	261.8	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6832.5	100.0
0°-180°	6832.5	100.0

Coefficient of Utilization



REPORT NUMBER: P675972


CATALOG NUMBER: CCW-SA-2C-730-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	701.7	10.3			
FM	(30°-60°)	2493.4	36.5			
FH	(60°-80°)	2009.2	29.4			G2/5000
FVH	(80°-90°)	222.4	3.3			G2/225
BL	(0°-30°)	349.5	5.1	B1/500		
BM	(30°-60°)	640.2	9.4	B1/1000		
BH	(60°-80°)	376.8	5.5	B1/500		G1/500
BVH	(80°-90°)	39.4	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9
2.5°	2251.6	2239.5	2230.4	2221.3	2209.2	2200.1	2187.9	2175.8	2160.7	2148.5	2133.4
5°	2121.3	2084.9	2048.5	2027.3	2003.1	1981.9	1957.6	1930.4	1903.1	1872.8	1845.5
7.5°	1978.8	1933.4	1887.9	1851.6	1812.2	1775.8	1736.4	1703.1	1669.7	1636.4	1603.1
10°	1845.5	1803.1	1760.7	1715.2	1666.7	1621.3	1572.8	1527.3	1481.9	1436.4	1390.9
12.5°	1757.6	1706.1	1657.6	1606.1	1557.6	1506.1	1454.6	1412.2	1369.7	1324.3	1281.9
15°	1718.2	1669.7	1624.3	1572.8	1521.3	1469.7	1418.2	1369.7	1324.3	1275.8	1227.3
17.5°	1812.2	1742.5	1672.8	1606.1	1539.4	1472.8	1406.1	1345.5	1284.9	1224.3	1163.7
20°	1933.4	1845.5	1760.7	1678.8	1594.0	1512.2	1427.3	1342.5	1257.6	1172.8	1087.9
22.5°	2087.9	1987.9	1891.0	1784.9	1675.8	1569.7	1460.6	1354.6	1248.5	1139.4	1033.4
25°	2363.7	2245.5	2127.3	1975.8	1821.3	1669.7	1515.2	1375.8	1239.4	1100.0	960.6
27.5°	2600.1	2439.5	2281.9	2100.1	1918.2	1736.4	1554.6	1394.0	1236.4	1075.8	915.2
30°	2739.5	2581.9	2424.3	2203.1	1984.9	1763.7	1542.5	1363.7	1187.9	1009.1	830.3
32.5°	2866.8	2691.0	2515.2	2272.8	2027.3	1784.9	1539.4	1342.5	1148.5	951.5	754.6
35°	3042.5	2848.6	2657.7	2375.8	2094.0	1812.2	1530.3	1327.3	1121.2	918.2	712.1
37.5°	3230.4	2991.0	2754.6	2442.5	2130.4	1818.2	1506.1	1306.1	1106.1	906.1	706.1
40°	3436.5	3145.5	2857.7	2512.2	2169.8	1824.3	1478.8	1278.8	1078.8	875.8	675.8
42.5°	3569.8	3254.6	2939.5	2566.7	2197.0	1824.3	1451.6	1254.6	1057.6	857.6	660.6
45°	3645.6	3339.5	3036.5	2633.4	2230.4	1827.3	1424.3	1230.3	1036.4	839.4	645.5
47.5°	3678.9	3394.0	3109.2	2684.9	2263.7	1839.4	1415.2	1218.2	1018.2	821.2	621.2
50°	3766.8	3515.3	3263.7	2809.2	2357.6	1903.1	1448.5	1236.4	1027.3	815.2	603.0
52.5°	3818.3	3603.1	3388.0	2921.3	2454.6	1987.9	1521.3	1284.9	1048.5	812.1	575.8
55°	4006.2	3800.1	3594.0	3097.1	2597.0	2100.1	1600.0	1339.4	1078.8	815.2	554.6
57.5°	4245.6	4027.4	3812.2	3275.9	2739.5	2203.1	1666.7	1387.9	1106.1	827.3	545.5
60°	4412.3	4200.1	3991.0	3421.3	2848.6	2278.9	1706.1	1415.2	1124.3	830.3	539.4
62.5°	4430.4	4157.7	3888.0	3333.4	2778.9	2221.3	1666.7	1384.9	1103.1	818.2	536.4
65°	4315.3	3997.1	3678.9	3148.6	2618.3	2087.9	1557.6	1300.0	1042.5	781.8	524.3
67.5°	4085.0	3712.2	3339.5	2854.6	2369.8	1884.9	1400.0	1178.8	960.6	739.4	518.2
70°	3548.6	3221.3	2897.1	2475.8	2057.6	1636.4	1215.2	1033.4	854.6	672.7	490.9
72.5°	2978.9	2672.8	2369.8	2027.3	1687.9	1345.5	1003.1	866.7	730.3	590.9	454.6
75°	2281.9	2051.6	1824.3	1569.7	1315.2	1057.6	803.1	703.1	603.0	503.0	403.0
77.5°	1603.1	1478.8	1357.6	1166.7	975.8	784.9	594.0	527.3	460.6	394.0	327.3
80°	1087.9	1018.2	951.5	815.2	678.8	539.4	403.0	360.6	315.2	272.7	227.3
82.5°	675.8	672.7	666.7	572.7	478.8	384.9	290.9	254.6	221.2	184.9	148.5
85°	309.1	360.6	409.1	357.6	306.1	254.6	203.0	178.8	154.5	127.3	103.0
87.5°	97.0	118.2	136.4	130.3	121.2	115.2	106.1	90.9	75.8	60.6	45.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9
2.5°	2121.3	2112.2	2100.1	2087.9	2072.8	2060.7	2045.5	2030.4	2027.3	2021.3	2018.2
5°	1827.3	1809.1	1787.9	1769.7	1751.6	1730.4	1712.2	1691.0	1675.8	1657.6	1642.5
7.5°	1569.7	1539.4	1506.1	1472.8	1442.5	1412.2	1378.8	1348.5	1333.4	1318.2	1303.1
10°	1363.7	1333.4	1306.1	1275.8	1254.6	1236.4	1215.2	1194.0	1175.8	1157.6	1139.4
12.5°	1260.6	1239.4	1218.2	1197.0	1172.8	1151.5	1127.3	1103.1	1081.8	1063.7	1042.5
15°	1197.0	1166.7	1133.4	1103.1	1069.7	1039.4	1006.1	972.8	948.5	927.3	903.1
17.5°	1121.2	1075.8	1033.4	987.9	951.5	915.2	875.8	839.4	812.1	781.8	754.6
20°	1036.4	984.9	930.3	878.8	836.4	797.0	754.6	712.1	681.8	648.5	618.2
22.5°	963.7	897.0	827.3	757.6	712.1	666.7	618.2	572.7	545.5	515.2	487.9
25°	884.9	812.1	736.4	660.6	615.2	566.7	521.2	472.7	451.5	433.3	412.1
27.5°	842.4	769.7	694.0	621.2	578.8	533.3	490.9	445.5	430.3	412.1	397.0
30°	757.6	687.9	615.2	542.4	512.1	484.9	454.6	424.3	418.2	415.2	409.1
32.5°	681.8	609.1	536.4	463.6	436.4	409.1	381.8	354.6	351.5	345.5	342.4
35°	642.4	572.7	500.0	430.3	406.1	378.8	354.6	327.3	321.2	312.1	306.1
37.5°	633.4	560.6	484.9	412.1	387.9	363.6	336.4	312.1	306.1	300.0	293.9
40°	609.1	539.4	472.7	403.0	378.8	354.6	327.3	303.0	297.0	290.9	284.9
42.5°	590.9	524.3	454.6	384.9	363.6	342.4	318.2	297.0	290.9	284.9	275.8
45°	575.8	506.1	433.3	363.6	348.5	333.3	315.2	300.0	293.9	284.9	278.8
47.5°	551.5	484.9	415.2	345.5	330.3	318.2	303.0	287.9	281.8	275.8	269.7
50°	533.3	463.6	394.0	324.3	312.1	300.0	287.9	275.8	275.8	278.8	278.8
52.5°	509.1	442.4	375.8	309.1	297.0	284.9	272.7	260.6	263.6	266.7	269.7
55°	487.9	424.3	357.6	290.9	278.8	266.7	251.5	239.4	242.4	245.5	248.5
57.5°	478.8	412.1	345.5	278.8	266.7	251.5	239.4	224.2	224.2	224.2	224.2
60°	472.7	403.0	336.4	266.7	251.5	239.4	224.2	209.1	206.1	206.1	203.0
62.5°	469.7	400.0	333.3	263.6	245.5	230.3	212.1	193.9	190.9	187.9	184.9
65°	457.6	394.0	327.3	260.6	239.4	221.2	200.0	178.8	175.8	175.8	172.7
67.5°	454.6	387.9	324.3	257.6	236.4	212.1	190.9	166.7	163.6	160.6	157.6
70°	430.3	372.7	312.1	251.5	227.3	206.1	181.8	157.6	154.5	148.5	145.5
72.5°	400.0	348.5	293.9	239.4	215.2	190.9	166.7	142.4	139.4	136.4	130.3
75°	354.6	306.1	257.6	209.1	187.9	169.7	148.5	127.3	124.2	121.2	115.2
77.5°	290.9	251.5	215.2	175.8	160.6	145.5	130.3	115.2	112.1	109.1	103.0
80°	206.1	181.8	160.6	136.4	127.3	115.2	106.1	93.9	93.9	90.9	90.9
82.5°	136.4	124.2	112.1	100.0	93.9	87.9	81.8	75.8	75.8	72.7	72.7
85°	97.0	90.9	81.8	75.8	72.7	66.7	63.6	57.6	57.6	57.6	57.6
87.5°	45.5	45.5	42.4	42.4	39.4	39.4	36.4	33.3	33.3	33.3	33.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9
2.5°	2012.2	2003.1	1994.0	1981.9	1972.8	1960.7	1945.5	1933.4	1918.2	1918.2	1915.2
5°	1624.3	1615.2	1606.1	1594.0	1584.9	1572.8	1563.7	1551.6	1539.4	1539.4	1536.4
7.5°	1287.9	1269.7	1251.6	1230.3	1212.2	1200.0	1187.9	1172.8	1160.6	1151.5	1142.5
10°	1121.2	1103.1	1081.8	1063.7	1042.5	1027.3	1012.2	994.0	978.8	966.7	954.6
12.5°	1021.2	1000.0	978.8	957.6	936.4	915.2	897.0	875.8	854.6	839.4	824.3
15°	878.8	857.6	836.4	815.2	794.0	769.7	745.5	718.2	694.0	681.8	672.7
17.5°	724.3	703.1	678.8	657.6	633.4	615.2	597.0	578.8	560.6	548.5	539.4
20°	584.9	560.6	536.4	512.1	487.9	475.8	463.6	451.5	439.4	430.3	424.3
22.5°	457.6	442.4	430.3	415.2	400.0	390.9	384.9	375.8	366.7	366.7	366.7
25°	390.9	381.8	375.8	366.7	357.6	354.6	351.5	345.5	342.4	339.4	339.4
27.5°	378.8	369.7	360.6	351.5	342.4	339.4	336.4	330.3	327.3	327.3	327.3
30°	403.0	400.0	397.0	394.0	390.9	384.9	375.8	369.7	360.6	354.6	348.5
32.5°	336.4	333.3	333.3	330.3	327.3	333.3	336.4	342.4	345.5	348.5	351.5
35°	297.0	290.9	284.9	278.8	272.7	269.7	266.7	263.6	260.6	260.6	257.6
37.5°	287.9	281.8	275.8	269.7	263.6	260.6	257.6	254.6	251.5	251.5	248.5
40°	278.8	272.7	269.7	263.6	257.6	254.6	251.5	245.5	242.4	239.4	239.4
42.5°	269.7	266.7	260.6	257.6	251.5	248.5	245.5	239.4	236.4	233.3	230.3
45°	269.7	263.6	257.6	251.5	245.5	242.4	236.4	233.3	227.3	227.3	224.2
47.5°	263.6	257.6	251.5	245.5	239.4	236.4	230.3	227.3	221.2	218.2	215.2
50°	278.8	269.7	257.6	248.5	236.4	233.3	227.3	224.2	218.2	215.2	212.1
52.5°	272.7	263.6	251.5	242.4	230.3	224.2	221.2	215.2	209.1	206.1	203.0
55°	251.5	242.4	236.4	227.3	218.2	212.1	206.1	200.0	193.9	190.9	190.9
57.5°	224.2	221.2	218.2	215.2	212.1	206.1	200.0	190.9	184.9	181.8	178.8
60°	200.0	203.0	206.1	209.1	212.1	203.0	193.9	184.9	175.8	172.7	169.7
62.5°	181.8	187.9	193.9	197.0	203.0	193.9	184.9	175.8	166.7	163.6	160.6
65°	169.7	172.7	172.7	175.8	175.8	169.7	166.7	160.6	154.5	151.5	151.5
67.5°	154.5	154.5	154.5	151.5	151.5	148.5	148.5	145.5	142.4	139.4	139.4
70°	139.4	139.4	139.4	136.4	136.4	133.3	133.3	130.3	127.3	127.3	124.2
72.5°	127.3	127.3	124.2	124.2	121.2	121.2	121.2	118.2	118.2	115.2	115.2
75°	112.1	112.1	109.1	109.1	106.1	106.1	106.1	103.0	103.0	103.0	100.0
77.5°	100.0	100.0	97.0	97.0	93.9	93.9	93.9	90.9	90.9	87.9	87.9
80°	87.9	87.9	84.9	84.9	81.8	81.8	78.8	78.8	75.8	75.8	72.7
82.5°	69.7	69.7	69.7	69.7	69.7	66.7	66.7	63.6	60.6	60.6	57.6
85°	57.6	57.6	57.6	54.5	54.5	54.5	51.5	51.5	48.5	45.5	45.5
87.5°	33.3	33.3	33.3	30.3	30.3	30.3	30.3	30.3	30.3	30.3	27.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9
2.5°	1915.2	1912.2	1900.1	1887.9	1900.1	1912.2	1912.2	1912.2	1909.1	1909.1	1909.1
5°	1536.4	1533.4	1527.3	1521.3	1521.3	1518.2	1524.3	1530.3	1536.4	1542.5	1548.5
7.5°	1130.3	1121.2	1112.2	1103.1	1109.1	1112.2	1121.2	1127.3	1136.4	1142.5	1157.6
10°	942.5	930.3	921.2	912.1	906.1	900.0	894.0	890.9	884.9	878.8	884.9
12.5°	806.1	790.9	775.8	757.6	754.6	751.5	745.5	739.4	733.4	727.3	724.3
15°	660.6	648.5	642.4	633.4	621.2	609.1	603.0	600.0	594.0	587.9	584.9
17.5°	527.3	515.2	506.1	497.0	494.0	487.9	487.9	487.9	487.9	487.9	487.9
20°	415.2	406.1	406.1	403.0	403.0	400.0	403.0	406.1	406.1	409.1	412.1
22.5°	363.6	363.6	360.6	357.6	360.6	360.6	363.6	366.7	369.7	372.7	375.8
25°	336.4	333.3	336.4	339.4	339.4	339.4	342.4	342.4	345.5	345.5	345.5
27.5°	324.3	324.3	327.3	327.3	330.3	330.3	330.3	327.3	327.3	324.3	324.3
30°	342.4	336.4	336.4	336.4	333.3	330.3	327.3	327.3	324.3	321.2	318.2
32.5°	354.6	357.6	354.6	348.5	345.5	339.4	336.4	330.3	327.3	321.2	315.2
35°	257.6	254.6	260.6	263.6	266.7	269.7	272.7	275.8	275.8	278.8	278.8
37.5°	248.5	245.5	245.5	242.4	242.4	242.4	242.4	242.4	239.4	239.4	242.4
40°	236.4	233.3	233.3	230.3	230.3	227.3	227.3	227.3	227.3	227.3	227.3
42.5°	227.3	224.2	224.2	224.2	224.2	221.2	221.2	218.2	218.2	215.2	215.2
45°	224.2	221.2	218.2	215.2	215.2	212.1	212.1	212.1	209.1	209.1	209.1
47.5°	212.1	209.1	209.1	206.1	206.1	203.0	203.0	203.0	200.0	200.0	200.0
50°	206.1	203.0	203.0	200.0	200.0	197.0	197.0	197.0	193.9	193.9	193.9
52.5°	197.0	193.9	193.9	193.9	190.9	187.9	187.9	187.9	184.9	184.9	184.9
55°	187.9	184.9	184.9	184.9	181.8	178.8	178.8	178.8	175.8	175.8	175.8
57.5°	175.8	172.7	172.7	169.7	169.7	169.7	169.7	169.7	166.7	166.7	166.7
60°	166.7	163.6	163.6	160.6	160.6	157.6	157.6	157.6	157.6	157.6	157.6
62.5°	157.6	154.5	151.5	148.5	151.5	151.5	151.5	151.5	148.5	148.5	148.5
65°	148.5	145.5	142.4	139.4	139.4	139.4	139.4	139.4	139.4	139.4	139.4
67.5°	136.4	133.3	130.3	127.3	130.3	130.3	130.3	130.3	130.3	130.3	130.3
70°	124.2	121.2	121.2	118.2	118.2	115.2	115.2	118.2	118.2	118.2	118.2
72.5°	112.1	109.1	109.1	106.1	106.1	106.1	106.1	106.1	106.1	106.1	106.1
75°	100.0	97.0	97.0	93.9	93.9	93.9	93.9	93.9	93.9	93.9	93.9
77.5°	84.9	81.8	81.8	81.8	81.8	81.8	81.8	84.9	84.9	84.9	84.9
80°	72.7	69.7	69.7	69.7	69.7	69.7	69.7	69.7	69.7	69.7	69.7
82.5°	57.6	54.5	54.5	54.5	54.5	54.5	54.5	54.5	54.5	54.5	54.5
85°	42.4	39.4	39.4	39.4	42.4	42.4	42.4	42.4	42.4	42.4	42.4
87.5°	27.3	24.2	24.2	24.2	27.3	27.3	27.3	27.3	24.2	24.2	24.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9
2.5°	1909.1	1909.1	1909.1	1906.1	1903.1	1900.1	1897.0	1906.1	1912.2	1921.3	1927.3
5°	1551.6	1557.6	1560.7	1569.7	1578.8	1587.9	1597.0	1603.1	1609.1	1612.2	1618.2
7.5°	1169.7	1184.9	1197.0	1209.1	1221.2	1230.3	1242.5	1251.6	1260.6	1269.7	1278.8
10°	887.9	894.0	897.0	909.1	918.2	930.3	939.4	948.5	957.6	963.7	972.8
12.5°	721.2	715.2	712.1	712.1	712.1	712.1	712.1	718.2	724.3	730.3	736.4
15°	581.8	578.8	575.8	572.7	569.7	563.7	560.6	566.7	572.7	578.8	584.9
17.5°	487.9	487.9	487.9	484.9	481.8	478.8	475.8	478.8	481.8	481.8	484.9
20°	418.2	421.2	424.3	427.3	427.3	430.3	430.3	433.3	436.4	436.4	439.4
22.5°	375.8	378.8	378.8	378.8	381.8	381.8	381.8	384.9	387.9	390.9	394.0
25°	342.4	342.4	339.4	339.4	342.4	342.4	342.4	342.4	345.5	345.5	345.5
27.5°	324.3	321.2	321.2	321.2	321.2	318.2	318.2	318.2	318.2	318.2	318.2
30°	315.2	312.1	309.1	306.1	306.1	303.0	300.0	300.0	300.0	300.0	300.0
32.5°	312.1	306.1	300.0	297.0	297.0	293.9	290.9	287.9	287.9	284.9	281.8
35°	278.8	275.8	275.8	272.7	269.7	266.7	263.6	263.6	263.6	260.6	260.6
37.5°	242.4	245.5	245.5	245.5	248.5	248.5	248.5	248.5	251.5	251.5	251.5
40°	227.3	227.3	227.3	230.3	233.3	233.3	236.4	236.4	239.4	239.4	239.4
42.5°	215.2	212.1	212.1	215.2	215.2	218.2	218.2	221.2	224.2	224.2	227.3
45°	209.1	206.1	206.1	206.1	206.1	203.0	203.0	206.1	209.1	212.1	215.2
47.5°	197.0	197.0	193.9	193.9	193.9	193.9	193.9	193.9	197.0	197.0	197.0
50°	190.9	190.9	187.9	187.9	187.9	187.9	187.9	187.9	187.9	187.9	187.9
52.5°	184.9	181.8	181.8	181.8	181.8	178.8	178.8	178.8	178.8	178.8	178.8
55°	175.8	172.7	172.7	172.7	172.7	172.7	172.7	172.7	175.8	175.8	175.8
57.5°	166.7	163.6	163.6	163.6	166.7	166.7	166.7	166.7	169.7	169.7	169.7
60°	157.6	157.6	157.6	157.6	157.6	157.6	157.6	160.6	160.6	163.6	163.6
62.5°	148.5	148.5	148.5	148.5	151.5	151.5	151.5	151.5	154.5	154.5	154.5
65°	139.4	139.4	139.4	139.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4
67.5°	130.3	130.3	130.3	130.3	130.3	130.3	130.3	133.3	133.3	136.4	136.4
70°	118.2	115.2	115.2	118.2	118.2	121.2	121.2	124.2	124.2	127.3	127.3
72.5°	106.1	106.1	106.1	106.1	106.1	106.1	106.1	109.1	112.1	112.1	115.2
75°	93.9	93.9	93.9	93.9	97.0	97.0	97.0	100.0	100.0	103.0	103.0
77.5°	84.9	81.8	81.8	81.8	84.9	84.9	84.9	87.9	87.9	90.9	90.9
80°	69.7	69.7	69.7	69.7	72.7	72.7	72.7	72.7	75.8	75.8	75.8
82.5°	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6	60.6	60.6	60.6
85°	42.4	42.4	42.4	42.4	45.5	45.5	45.5	45.5	45.5	45.5	45.5
87.5°	27.3	27.3	27.3	27.3	27.3	27.3	27.3	27.3	30.3	30.3	30.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9
2.5°	1927.3	1927.3	1927.3	1927.3	1933.4	1936.4	1942.5	1945.5	1942.5	1939.5	1933.4
5°	1621.3	1624.3	1624.3	1627.3	1627.3	1627.3	1627.3	1627.3	1633.4	1639.4	1645.5
7.5°	1281.9	1284.9	1287.9	1290.9	1290.9	1290.9	1287.9	1287.9	1290.9	1290.9	1294.0
10°	981.8	994.0	1003.1	1012.2	1006.1	997.0	990.9	981.8	981.8	981.8	978.8
12.5°	742.4	745.5	751.5	754.6	751.5	751.5	748.5	745.5	748.5	754.6	757.6
15°	587.9	587.9	590.9	590.9	594.0	597.0	597.0	600.0	606.1	609.1	615.2
17.5°	487.9	490.9	490.9	494.0	494.0	497.0	497.0	497.0	503.0	509.1	518.2
20°	439.4	439.4	439.4	439.4	439.4	436.4	436.4	433.3	436.4	442.4	445.5
22.5°	394.0	397.0	397.0	397.0	394.0	390.9	384.9	381.8	381.8	384.9	384.9
25°	345.5	342.4	342.4	339.4	339.4	342.4	342.4	342.4	345.5	345.5	348.5
27.5°	318.2	315.2	315.2	312.1	312.1	315.2	315.2	315.2	315.2	315.2	315.2
30°	297.0	297.0	293.9	290.9	293.9	293.9	297.0	297.0	300.0	300.0	303.0
32.5°	281.8	278.8	278.8	275.8	278.8	278.8	281.8	281.8	284.9	287.9	287.9
35°	260.6	260.6	260.6	260.6	260.6	260.6	257.6	257.6	257.6	257.6	257.6
37.5°	248.5	248.5	245.5	242.4	242.4	242.4	242.4	242.4	239.4	236.4	233.3
40°	239.4	236.4	236.4	233.3	230.3	230.3	227.3	224.2	224.2	221.2	221.2
42.5°	227.3	224.2	224.2	221.2	218.2	218.2	215.2	212.1	212.1	212.1	209.1
45°	212.1	212.1	209.1	206.1	206.1	206.1	203.0	203.0	203.0	203.0	200.0
47.5°	197.0	197.0	193.9	193.9	193.9	193.9	190.9	190.9	190.9	190.9	190.9
50°	187.9	187.9	187.9	187.9	187.9	187.9	184.9	184.9	184.9	184.9	184.9
52.5°	178.8	178.8	178.8	178.8	178.8	178.8	178.8	178.8	178.8	178.8	178.8
55°	175.8	175.8	175.8	175.8	175.8	175.8	172.7	172.7	172.7	175.8	175.8
57.5°	169.7	169.7	166.7	166.7	166.7	166.7	166.7	166.7	166.7	166.7	166.7
60°	163.6	163.6	163.6	163.6	163.6	163.6	163.6	163.6	163.6	163.6	163.6
62.5°	154.5	154.5	154.5	154.5	154.5	157.6	157.6	157.6	157.6	157.6	154.5
65°	142.4	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5
67.5°	136.4	136.4	136.4	136.4	136.4	136.4	136.4	136.4	136.4	136.4	136.4
70°	127.3	127.3	124.2	124.2	124.2	127.3	127.3	127.3	127.3	127.3	127.3
72.5°	115.2	115.2	115.2	115.2	115.2	115.2	115.2	115.2	115.2	118.2	118.2
75°	103.0	103.0	103.0	103.0	103.0	103.0	103.0	103.0	103.0	103.0	103.0
77.5°	90.9	90.9	87.9	87.9	87.9	90.9	90.9	90.9	90.9	93.9	93.9
80°	75.8	75.8	75.8	75.8	75.8	75.8	75.8	75.8	75.8	78.8	78.8
82.5°	60.6	60.6	60.6	60.6	60.6	60.6	60.6	60.6	60.6	63.6	63.6
85°	45.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5	51.5	51.5
87.5°	30.3	30.3	30.3	30.3	30.3	30.3	27.3	27.3	27.3	27.3	24.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9
2.5°	1930.4	1933.4	1936.4	1936.4	1939.5	1942.5	1942.5	1954.6	1966.7	1972.8	1978.8
5°	1651.6	1648.5	1648.5	1645.5	1642.5	1651.6	1660.7	1678.8	1697.0	1700.0	1706.1
7.5°	1294.0	1297.0	1300.0	1300.0	1303.1	1294.0	1281.9	1284.9	1287.9	1303.1	1315.2
10°	978.8	981.8	984.9	984.9	987.9	984.9	978.8	987.9	997.0	1009.1	1024.3
12.5°	760.6	769.7	778.8	784.9	794.0	800.0	803.1	815.2	824.3	839.4	854.6
15°	621.2	627.3	633.4	639.4	645.5	651.5	657.6	669.7	681.8	700.0	718.2
17.5°	524.3	524.3	527.3	527.3	527.3	533.3	539.4	545.5	548.5	566.7	584.9
20°	448.5	445.5	442.4	439.4	436.4	442.4	445.5	448.5	451.5	463.6	472.7
22.5°	384.9	384.9	387.9	387.9	387.9	384.9	378.8	381.8	381.8	387.9	397.0
25°	348.5	348.5	348.5	345.5	345.5	348.5	351.5	351.5	348.5	351.5	354.6
27.5°	315.2	318.2	318.2	321.2	321.2	324.3	324.3	324.3	324.3	327.3	330.3
30°	303.0	303.0	306.1	306.1	306.1	309.1	312.1	312.1	312.1	315.2	321.2
32.5°	290.9	293.9	297.0	300.0	303.0	306.1	306.1	309.1	309.1	312.1	315.2
35°	257.6	254.6	254.6	251.5	248.5	248.5	248.5	248.5	245.5	248.5	248.5
37.5°	230.3	230.3	230.3	227.3	227.3	230.3	230.3	230.3	230.3	233.3	233.3
40°	218.2	218.2	218.2	218.2	218.2	218.2	218.2	221.2	221.2	224.2	227.3
42.5°	209.1	209.1	209.1	209.1	209.1	212.1	212.1	212.1	212.1	215.2	215.2
45°	200.0	200.0	200.0	200.0	200.0	200.0	200.0	203.0	203.0	206.1	209.1
47.5°	190.9	190.9	190.9	190.9	190.9	193.9	197.0	197.0	197.0	200.0	200.0
50°	184.9	184.9	184.9	184.9	184.9	187.9	187.9	190.9	190.9	193.9	197.0
52.5°	178.8	178.8	178.8	178.8	178.8	181.8	181.8	184.9	184.9	187.9	190.9
55°	175.8	175.8	175.8	172.7	172.7	175.8	175.8	178.8	178.8	181.8	181.8
57.5°	166.7	166.7	166.7	166.7	166.7	166.7	166.7	169.7	169.7	172.7	175.8
60°	163.6	163.6	160.6	160.6	157.6	160.6	160.6	163.6	163.6	166.7	166.7
62.5°	154.5	154.5	154.5	151.5	151.5	154.5	154.5	154.5	154.5	157.6	160.6
65°	145.5	145.5	145.5	142.4	142.4	145.5	145.5	145.5	145.5	148.5	151.5
67.5°	136.4	136.4	136.4	133.3	133.3	133.3	133.3	136.4	136.4	139.4	142.4
70°	127.3	127.3	127.3	124.2	124.2	124.2	121.2	124.2	127.3	130.3	130.3
72.5°	118.2	118.2	118.2	115.2	115.2	115.2	112.1	115.2	115.2	118.2	118.2
75°	103.0	103.0	103.0	103.0	103.0	103.0	100.0	100.0	100.0	103.0	103.0
77.5°	93.9	93.9	93.9	90.9	90.9	90.9	87.9	87.9	87.9	90.9	90.9
80°	78.8	78.8	78.8	75.8	75.8	75.8	72.7	72.7	72.7	75.8	75.8
82.5°	63.6	63.6	63.6	60.6	60.6	60.6	57.6	57.6	57.6	60.6	60.6
85°	51.5	51.5	51.5	51.5	51.5	51.5	48.5	48.5	48.5	51.5	54.5
87.5°	24.2	24.2	27.3	27.3	27.3	27.3	24.2	24.2	21.2	21.2	24.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9
2.5°	1984.9	1991.0	2006.1	2018.2	2033.4	2045.5	2054.6	2066.7	2075.8	2084.9	2091.0
5°	1709.1	1712.2	1727.3	1742.5	1754.6	1769.7	1791.0	1812.2	1833.4	1854.6	1869.8
7.5°	1330.3	1342.5	1360.6	1381.9	1400.0	1418.2	1439.4	1463.7	1484.9	1506.1	1527.3
10°	1036.4	1048.5	1066.7	1084.9	1100.0	1118.2	1142.5	1166.7	1190.9	1215.2	1239.4
12.5°	869.7	884.9	906.1	927.3	945.5	966.7	997.0	1024.3	1054.6	1081.8	1112.2
15°	733.4	751.5	778.8	809.1	836.4	863.7	894.0	924.3	951.5	981.8	1012.2
17.5°	603.0	621.2	645.5	672.7	697.0	721.2	757.6	790.9	827.3	860.6	894.0
20°	484.9	494.0	518.2	542.4	566.7	590.9	618.2	645.5	672.7	700.0	742.4
22.5°	403.0	409.1	421.2	430.3	442.4	451.5	478.8	506.1	530.3	557.6	597.0
25°	354.6	357.6	366.7	372.7	381.8	387.9	406.1	421.2	439.4	454.6	490.9
27.5°	330.3	333.3	336.4	339.4	342.4	345.5	357.6	369.7	378.8	390.9	424.3
30°	324.3	327.3	336.4	342.4	351.5	357.6	363.6	369.7	375.8	381.8	403.0
32.5°	318.2	321.2	321.2	318.2	318.2	315.2	321.2	324.3	330.3	333.3	351.5
35°	251.5	251.5	254.6	257.6	260.6	263.6	272.7	278.8	287.9	293.9	309.1
37.5°	236.4	236.4	239.4	245.5	248.5	251.5	257.6	263.6	269.7	275.8	290.9
40°	227.3	230.3	233.3	236.4	239.4	242.4	248.5	251.5	257.6	260.6	272.7
42.5°	218.2	218.2	221.2	227.3	230.3	233.3	239.4	242.4	248.5	251.5	263.6
45°	212.1	215.2	218.2	221.2	221.2	224.2	230.3	236.4	239.4	245.5	257.6
47.5°	203.0	203.0	209.1	212.1	218.2	221.2	227.3	230.3	236.4	239.4	251.5
50°	197.0	200.0	206.1	209.1	215.2	218.2	227.3	233.3	242.4	248.5	254.6
52.5°	190.9	193.9	200.0	203.0	209.1	212.1	224.2	236.4	245.5	257.6	257.6
55°	184.9	184.9	190.9	200.0	206.1	212.1	218.2	227.3	233.3	239.4	239.4
57.5°	175.8	178.8	184.9	193.9	200.0	206.1	212.1	218.2	221.2	227.3	224.2
60°	169.7	169.7	178.8	187.9	197.0	206.1	206.1	206.1	203.0	203.0	203.0
62.5°	160.6	163.6	175.8	190.9	203.0	215.2	206.1	197.0	187.9	178.8	181.8
65°	154.5	157.6	163.6	172.7	178.8	184.9	178.8	175.8	169.7	163.6	166.7
67.5°	142.4	145.5	148.5	148.5	151.5	151.5	151.5	151.5	151.5	151.5	154.5
70°	133.3	133.3	133.3	136.4	136.4	136.4	136.4	136.4	136.4	136.4	139.4
72.5°	121.2	121.2	121.2	121.2	121.2	121.2	121.2	121.2	121.2	121.2	124.2
75°	106.1	106.1	106.1	106.1	106.1	106.1	106.1	106.1	106.1	106.1	109.1
77.5°	93.9	93.9	93.9	93.9	93.9	93.9	93.9	93.9	90.9	90.9	93.9
80°	78.8	78.8	78.8	78.8	75.8	75.8	75.8	75.8	75.8	75.8	78.8
82.5°	63.6	63.6	63.6	63.6	60.6	60.6	60.6	60.6	57.6	57.6	60.6
85°	57.6	60.6	60.6	63.6	63.6	63.6	60.6	57.6	54.5	51.5	51.5
87.5°	24.2	24.2	24.2	24.2	21.2	21.2	21.2	21.2	21.2	21.2	21.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972
 CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9
2.5°	2100.1	2106.1	2112.2	2121.3	2133.4	2142.5	2151.6	2169.8	2191.0	2209.2	2227.3
5°	1884.9	1900.1	1915.2	1933.4	1951.6	1966.7	1984.9	2021.3	2057.6	2091.0	2127.3
7.5°	1545.5	1566.7	1584.9	1615.2	1642.5	1672.8	1700.0	1745.5	1787.9	1833.4	1875.8
10°	1263.7	1287.9	1312.2	1351.6	1394.0	1433.4	1472.8	1509.1	1548.5	1584.9	1621.3
12.5°	1142.5	1169.7	1200.0	1224.3	1251.6	1275.8	1300.0	1342.5	1384.9	1427.3	1469.7
15°	1042.5	1072.8	1103.1	1133.4	1160.6	1190.9	1218.2	1254.6	1294.0	1330.3	1366.7
17.5°	927.3	957.6	990.9	1024.3	1057.6	1090.9	1124.3	1175.8	1227.3	1275.8	1327.3
20°	781.8	824.3	863.7	909.1	954.6	1000.0	1045.5	1100.0	1154.6	1206.1	1260.6
22.5°	636.4	675.8	715.2	769.7	824.3	875.8	930.3	1003.1	1072.8	1145.5	1215.2
25°	530.3	566.7	603.0	663.7	721.2	781.8	839.4	927.3	1012.2	1100.0	1184.9
27.5°	457.6	490.9	524.3	587.9	651.5	712.1	775.8	872.8	966.7	1063.7	1157.6
30°	424.3	445.5	466.7	527.3	587.9	645.5	706.1	800.0	894.0	987.9	1081.8
32.5°	369.7	387.9	406.1	460.6	515.2	566.7	621.2	718.2	812.1	909.1	1003.1
35°	327.3	342.4	357.6	409.1	457.6	509.1	557.6	654.6	751.5	848.5	945.5
37.5°	303.0	318.2	330.3	375.8	424.3	469.7	515.2	612.1	706.1	803.1	897.0
40°	284.9	293.9	306.1	351.5	394.0	439.4	481.8	569.7	660.6	748.5	836.4
42.5°	272.7	284.9	293.9	333.3	375.8	415.2	454.6	539.4	624.3	706.1	790.9
45°	269.7	281.8	293.9	327.3	360.6	390.9	424.3	506.1	587.9	669.7	751.5
47.5°	263.6	272.7	284.9	312.1	336.4	363.6	387.9	469.7	551.5	630.3	712.1
50°	260.6	263.6	269.7	293.9	318.2	342.4	366.7	448.5	530.3	612.1	694.0
52.5°	257.6	257.6	257.6	278.8	300.0	318.2	339.4	421.2	506.1	587.9	669.7
55°	239.4	236.4	236.4	257.6	275.8	297.0	315.2	397.0	478.8	557.6	639.4
57.5°	221.2	218.2	215.2	233.3	251.5	269.7	287.9	369.7	454.6	536.4	618.2
60°	203.0	200.0	200.0	218.2	233.3	251.5	266.7	351.5	433.3	518.2	600.0
62.5°	181.8	184.9	184.9	200.0	218.2	233.3	248.5	333.3	421.2	506.1	590.9
65°	166.7	169.7	169.7	187.9	206.1	224.2	242.4	324.3	409.1	490.9	572.7
67.5°	154.5	157.6	157.6	178.8	197.0	218.2	236.4	309.1	384.9	457.6	530.3
70°	142.4	142.4	145.5	166.7	187.9	209.1	230.3	293.9	357.6	418.2	481.8
72.5°	127.3	130.3	133.3	154.5	172.7	193.9	212.1	269.7	327.3	384.9	442.4
75°	112.1	115.2	118.2	136.4	154.5	172.7	190.9	245.5	297.0	351.5	403.0
77.5°	100.0	103.0	106.1	121.2	136.4	151.5	166.7	206.1	248.5	287.9	327.3
80°	81.8	81.8	84.9	97.0	109.1	118.2	130.3	157.6	184.9	209.1	236.4
82.5°	60.6	63.6	63.6	72.7	78.8	87.9	93.9	109.1	121.2	136.4	148.5
85°	51.5	48.5	48.5	54.5	57.6	63.6	66.7	75.8	81.8	90.9	97.0
87.5°	21.2	18.2	18.2	21.2	27.3	30.3	33.3	33.3	36.4	36.4	36.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9
2.5°	2236.4	2242.5	2251.6	2257.6	2272.8	2284.9	2300.1	2312.2	2321.3	2336.4	2330.4
5°	2154.6	2181.9	2209.2	2236.4	2257.6	2278.9	2297.0	2318.2	2342.5	2387.9	2400.1
7.5°	1912.2	1948.5	1981.9	2018.2	2060.7	2103.1	2145.5	2187.9	2227.3	2284.9	2321.3
10°	1672.8	1724.3	1772.8	1824.3	1863.7	1903.1	1939.5	1978.8	2033.4	2091.0	2157.6
12.5°	1521.3	1572.8	1624.3	1675.8	1733.4	1787.9	1845.5	1900.1	1951.6	1997.0	2072.8
15°	1421.3	1478.8	1533.4	1587.9	1657.6	1724.3	1794.0	1860.7	1936.4	1997.0	2048.5
17.5°	1397.0	1466.7	1533.4	1603.1	1675.8	1748.5	1821.3	1894.0	1969.8	2060.7	2127.3
20°	1354.6	1448.5	1542.5	1636.4	1730.4	1821.3	1915.2	2006.1	2106.1	2215.2	2245.5
22.5°	1330.3	1442.5	1557.6	1669.7	1797.0	1927.3	2054.6	2181.9	2287.9	2369.8	2460.7
25°	1327.3	1466.7	1609.1	1748.5	1909.1	2066.7	2227.3	2384.9	2521.3	2603.1	2675.8
27.5°	1324.3	1494.0	1660.7	1827.3	2024.3	2218.2	2415.2	2609.2	2736.4	2854.6	2915.2
30°	1287.9	1491.0	1697.0	1900.1	2121.3	2342.5	2563.7	2784.9	2915.2	2997.1	3027.4
32.5°	1242.5	1481.9	1721.3	1960.7	2212.2	2463.7	2712.2	2963.7	3066.8	3136.5	3112.2
35°	1206.1	1469.7	1730.4	1991.0	2257.6	2527.3	2794.0	3060.7	3209.2	3306.2	3266.8
37.5°	1172.8	1448.5	1724.3	2000.1	2312.2	2624.3	2936.4	3248.6	3391.0	3494.0	3448.6
40°	1133.4	1427.3	1724.3	2018.2	2375.8	2730.4	3088.0	3442.5	3627.4	3715.3	3645.6
42.5°	1100.0	1406.1	1715.2	2021.3	2403.1	2784.9	3166.8	3548.6	3754.7	3878.9	3791.0
45°	1057.6	1363.7	1666.7	1972.8	2394.0	2815.2	3233.4	3654.7	3894.1	3991.0	3869.8
47.5°	1012.2	1315.2	1615.2	1915.2	2363.7	2812.2	3260.7	3709.2	3930.4	4045.6	3933.4
50°	997.0	1300.0	1600.0	1903.1	2387.9	2875.8	3360.7	3845.6	4006.2	4100.1	3951.6
52.5°	994.0	1315.2	1639.4	1960.7	2448.6	2933.4	3421.3	3906.2	4036.5	4136.5	4003.1
55°	984.9	1333.4	1678.8	2024.3	2533.4	3045.5	3554.6	4063.8	4194.1	4266.8	4166.8
57.5°	994.0	1369.7	1742.5	2118.2	2642.5	3166.8	3691.0	4215.3	4372.9	4424.4	4403.2
60°	1000.0	1400.0	1797.0	2197.0	2709.2	3221.3	3733.4	4245.6	4409.2	4536.5	4560.7
62.5°	984.9	1378.8	1769.7	2163.7	2627.3	3091.0	3554.6	4018.3	4288.0	4475.9	4585.0
65°	939.4	1303.1	1669.7	2033.4	2460.7	2891.0	3318.3	3745.6	4030.4	4309.2	4397.1
67.5°	839.4	1148.5	1457.6	1766.7	2139.5	2512.2	2881.9	3254.6	3612.2	3881.9	4003.1
70°	727.3	969.7	1215.2	1457.6	1797.0	2136.4	2475.8	2815.2	3130.4	3427.4	3542.5
72.5°	633.4	821.2	1012.2	1200.0	1442.5	1681.9	1924.3	2163.7	2536.4	2833.4	2945.5
75°	539.4	675.8	809.1	945.5	1112.2	1278.8	1442.5	1609.1	1872.8	2139.5	2251.6
77.5°	415.2	506.1	594.0	681.8	797.0	909.1	1024.3	1136.4	1321.3	1521.3	1578.8
80°	287.9	339.4	387.9	439.4	530.3	621.2	712.1	803.1	924.3	1036.4	1124.3
82.5°	178.8	212.1	242.4	272.7	345.5	418.2	487.9	560.6	609.1	615.2	703.1
85°	115.2	136.4	154.5	172.7	215.2	260.6	303.0	345.5	309.1	287.9	342.4
87.5°	45.5	57.6	66.7	75.8	72.7	69.7	66.7	63.6	54.5	48.5	60.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972
 CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9
2.5°	2336.4	2345.5	2354.6	2360.7	2369.8	2372.8	2375.8	2375.8	2378.9	2381.9	2387.9
5°	2448.6	2466.7	2484.9	2500.1	2518.3	2533.4	2545.5	2560.7	2572.8	2572.8	2569.8
7.5°	2354.6	2400.1	2445.5	2491.0	2536.4	2569.8	2600.1	2633.4	2663.7	2669.8	2675.8
10°	2230.4	2278.9	2324.3	2372.8	2418.3	2469.8	2518.3	2566.7	2618.3	2627.3	2639.5
12.5°	2115.2	2172.8	2230.4	2284.9	2342.5	2378.9	2415.2	2448.6	2484.9	2509.2	2533.4
15°	2112.2	2160.7	2209.2	2254.6	2303.1	2324.3	2345.5	2363.7	2384.9	2384.9	2387.9
17.5°	2181.9	2212.2	2242.5	2269.8	2300.1	2303.1	2309.2	2312.2	2315.2	2306.1	2297.0
20°	2318.2	2330.4	2342.5	2354.6	2366.7	2345.5	2327.3	2306.1	2284.9	2260.7	2239.5
22.5°	2518.3	2491.0	2463.7	2436.4	2409.2	2372.8	2333.4	2297.0	2257.6	2227.3	2197.0
25°	2706.1	2672.8	2639.5	2606.1	2572.8	2494.0	2415.2	2333.4	2254.6	2221.3	2187.9
27.5°	2957.7	2906.1	2854.6	2803.1	2751.6	2645.5	2539.5	2433.4	2327.3	2269.8	2215.2
30°	3018.3	2960.7	2903.1	2842.5	2784.9	2681.9	2581.9	2478.9	2375.8	2309.2	2245.5
32.5°	3106.2	3039.5	2972.8	2906.1	2839.5	2739.5	2639.5	2536.4	2436.4	2375.8	2312.2
35°	3251.6	3175.9	3100.1	3021.3	2945.5	2842.5	2742.5	2639.5	2536.4	2466.7	2400.1
37.5°	3375.9	3288.0	3200.1	3112.2	3024.3	2933.4	2839.5	2748.6	2654.6	2584.9	2518.3
40°	3515.3	3418.3	3321.3	3227.4	3130.4	3045.5	2960.7	2872.8	2788.0	2733.4	2678.9
42.5°	3636.5	3518.3	3403.1	3288.0	3169.8	3112.2	3057.7	3000.1	2942.5	2915.2	2884.9
45°	3721.3	3612.2	3500.1	3391.0	3281.9	3239.5	3197.1	3154.6	3112.2	3139.5	3166.8
47.5°	3757.7	3669.8	3585.0	3500.1	3412.2	3427.4	3442.5	3454.6	3469.8	3506.2	3545.6
50°	3791.0	3742.5	3691.0	3642.5	3591.0	3648.6	3703.1	3760.7	3818.3	3894.1	3969.8
52.5°	3857.7	3830.4	3806.2	3778.9	3751.6	3851.6	3951.6	4051.6	4151.6	4236.5	4321.3
55°	4057.7	4036.5	4015.3	3991.0	3969.8	4112.2	4251.6	4394.1	4536.5	4624.4	4712.3
57.5°	4333.5	4321.3	4306.2	4294.1	4278.9	4418.3	4554.7	4691.0	4830.4	4915.3	5003.2
60°	4542.6	4545.6	4545.6	4548.6	4548.6	4654.7	4760.7	4869.8	4975.9	5048.6	5124.4
62.5°	4654.7	4648.6	4642.6	4636.5	4630.4	4718.3	4806.2	4894.1	4982.0	5036.5	5091.1
65°	4533.5	4566.8	4600.1	4633.5	4666.8	4678.9	4688.0	4700.1	4709.2	4742.6	4775.9
67.5°	4127.4	4194.1	4257.7	4324.4	4388.0	4342.6	4300.1	4254.7	4209.2	4218.3	4224.4
70°	3675.9	3751.6	3830.4	3906.2	3981.9	3875.9	3769.8	3660.7	3554.6	3518.3	3481.9
72.5°	3100.1	3166.8	3236.5	3303.1	3369.8	3239.5	3112.2	2981.9	2851.6	2788.0	2724.3
75°	2369.8	2448.6	2530.4	2609.2	2688.0	2542.5	2394.0	2248.6	2100.1	2057.6	2018.2
77.5°	1727.3	1821.3	1915.2	2009.1	2103.1	1972.8	1842.5	1709.1	1578.8	1554.6	1530.3
80°	1257.6	1330.3	1400.0	1472.8	1542.5	1466.7	1390.9	1315.2	1239.4	1236.4	1233.4
82.5°	848.5	912.1	972.8	1036.4	1097.0	1066.7	1039.4	1009.1	978.8	1009.1	1042.5
85°	436.4	524.3	615.2	703.1	790.9	781.8	775.8	766.7	757.6	797.0	833.4
87.5°	87.9	163.6	239.4	312.1	387.9	369.7	351.5	330.3	312.1	324.3	333.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9
2.5°	2391.0	2394.0	2394.0	2394.0	2394.0	2394.0	2387.9	2384.9	2378.9	2372.8	2363.7
5°	2569.8	2566.7	2554.6	2542.5	2527.3	2515.2	2506.1	2494.0	2484.9	2472.8	2454.6
7.5°	2681.9	2688.0	2666.7	2648.6	2627.3	2606.1	2584.9	2563.7	2542.5	2521.3	2478.9
10°	2648.6	2657.7	2645.5	2633.4	2618.3	2606.1	2581.9	2554.6	2530.4	2503.1	2451.6
12.5°	2554.6	2578.9	2572.8	2566.7	2560.7	2554.6	2539.5	2521.3	2506.1	2488.0	2430.4
15°	2387.9	2387.9	2391.0	2394.0	2394.0	2397.0	2400.1	2403.1	2406.1	2409.2	2375.8
17.5°	2287.9	2278.9	2278.9	2278.9	2278.9	2278.9	2291.0	2306.1	2318.2	2330.4	2321.3
20°	2215.2	2194.0	2191.0	2191.0	2187.9	2184.9	2206.1	2230.4	2251.6	2272.8	2284.9
22.5°	2166.7	2136.4	2133.4	2130.4	2127.3	2124.3	2151.6	2178.9	2206.1	2233.4	2275.8
25°	2154.6	2121.3	2124.3	2127.3	2127.3	2130.4	2151.6	2172.8	2194.0	2215.2	2287.9
27.5°	2157.6	2103.1	2106.1	2109.2	2109.2	2112.2	2145.5	2175.8	2209.2	2239.5	2330.4
30°	2178.9	2115.2	2109.2	2103.1	2097.0	2091.0	2136.4	2181.9	2227.3	2272.8	2342.5
32.5°	2251.6	2191.0	2175.8	2160.7	2145.5	2130.4	2184.9	2236.4	2291.0	2342.5	2400.1
35°	2330.4	2263.7	2257.6	2251.6	2242.5	2236.4	2284.9	2336.4	2384.9	2433.4	2484.9
37.5°	2448.6	2381.9	2375.8	2366.7	2360.7	2351.6	2406.1	2457.6	2512.2	2563.7	2609.2
40°	2624.3	2569.8	2566.7	2566.7	2563.7	2560.7	2603.1	2648.6	2691.0	2733.4	2763.7
42.5°	2857.7	2830.4	2839.5	2851.6	2860.7	2869.8	2903.1	2939.5	2972.8	3006.1	2997.1
45°	3194.0	3221.3	3224.3	3227.4	3230.4	3233.4	3242.5	3254.6	3263.7	3272.8	3236.5
47.5°	3581.9	3618.3	3636.5	3654.7	3669.8	3688.0	3675.9	3660.7	3648.6	3633.4	3542.5
50°	4042.5	4118.3	4115.3	4112.2	4106.2	4103.2	4078.9	4054.7	4027.4	4003.1	3869.8
52.5°	4406.2	4491.0	4506.2	4521.3	4536.5	4551.6	4506.2	4460.7	4412.3	4366.8	4200.1
55°	4797.1	4885.0	4888.0	4891.1	4891.1	4894.1	4830.4	4766.8	4700.1	4636.5	4463.8
57.5°	5088.0	5172.9	5163.8	5157.7	5148.6	5139.5	5063.8	4988.0	4912.3	4836.5	4663.8
60°	5197.1	5269.9	5251.7	5233.5	5212.3	5194.1	5136.5	5078.9	5018.3	4960.8	4794.1
62.5°	5145.6	5200.2	5172.9	5148.6	5121.4	5094.1	5021.4	4945.6	4872.9	4797.1	4675.9
65°	4806.2	4839.5	4803.2	4769.8	4736.5	4700.1	4639.5	4578.9	4515.3	4454.7	4372.9
67.5°	4233.5	4239.5	4236.5	4233.5	4230.4	4227.4	4139.5	4051.6	3960.7	3872.8	3866.8
70°	3448.6	3412.2	3418.3	3427.4	3433.4	3439.5	3372.8	3309.2	3242.5	3175.9	3206.2
72.5°	2660.7	2597.0	2612.2	2630.4	2645.5	2660.7	2606.1	2554.6	2500.1	2445.5	2488.0
75°	1975.8	1936.4	1951.6	1969.8	1984.9	2000.1	1978.8	1957.6	1933.4	1912.2	1951.6
77.5°	1506.1	1481.9	1484.9	1484.9	1487.9	1487.9	1491.0	1497.0	1500.0	1503.1	1545.5
80°	1227.3	1224.3	1221.2	1218.2	1212.2	1209.1	1239.4	1269.7	1300.0	1330.3	1351.6
82.5°	1072.8	1103.1	1084.9	1069.7	1051.5	1033.4	1060.6	1087.9	1115.2	1142.5	1133.4
85°	872.8	909.1	875.8	842.4	806.1	772.7	797.0	818.2	842.4	863.7	851.5
87.5°	345.5	354.6	300.0	248.5	193.9	139.4	221.2	300.0	381.8	460.6	472.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9	2181.9
2.5°	2354.6	2342.5	2333.4	2330.4	2324.3	2321.3	2315.2	2309.2	2300.1	2294.0	2284.9
5°	2433.4	2415.2	2394.0	2363.7	2336.4	2306.1	2275.8	2248.6	2221.3	2191.0	2163.7
7.5°	2436.4	2394.0	2351.6	2312.2	2269.8	2230.4	2187.9	2151.6	2112.2	2072.8	2036.4
10°	2403.1	2351.6	2300.1	2248.6	2200.1	2148.5	2097.0	2054.6	2009.1	1963.7	1921.3
12.5°	2375.8	2318.2	2260.7	2200.1	2142.5	2081.9	2021.3	1978.8	1936.4	1894.0	1851.6
15°	2342.5	2306.1	2272.8	2218.2	2163.7	2109.2	2054.6	1997.0	1942.5	1884.9	1827.3
17.5°	2315.2	2306.1	2297.0	2260.7	2224.3	2184.9	2148.5	2091.0	2033.4	1972.8	1915.2
20°	2300.1	2312.2	2324.3	2306.1	2287.9	2266.7	2248.6	2206.1	2163.7	2118.2	2075.8
22.5°	2318.2	2363.7	2406.1	2409.2	2415.2	2418.3	2421.3	2381.9	2342.5	2300.1	2260.7
25°	2360.7	2433.4	2506.1	2545.5	2584.9	2627.3	2666.7	2642.5	2618.3	2594.0	2569.8
27.5°	2418.3	2509.2	2600.1	2657.7	2712.2	2769.8	2827.4	2824.3	2821.3	2815.2	2812.2
30°	2409.2	2478.9	2548.6	2618.3	2688.0	2757.7	2827.4	2863.7	2897.1	2933.4	2969.8
32.5°	2460.7	2518.3	2578.9	2651.6	2724.3	2800.1	2872.8	2948.6	3021.3	3097.1	3172.8
35°	2539.5	2591.0	2645.5	2724.3	2806.1	2884.9	2966.8	3057.7	3151.6	3245.5	3336.5
37.5°	2657.7	2703.1	2751.6	2818.3	2888.0	2954.6	3024.3	3157.7	3291.0	3427.4	3560.7
40°	2794.0	2824.3	2854.6	2918.3	2981.9	3045.5	3109.2	3275.9	3442.5	3609.2	3775.9
42.5°	2991.0	2981.9	2972.8	3024.3	3078.9	3130.4	3184.9	3336.5	3488.0	3639.5	3791.0
45°	3200.1	3163.7	3127.4	3151.6	3178.9	3203.1	3230.4	3384.9	3539.5	3697.1	3851.6
47.5°	3451.6	3360.7	3269.8	3248.6	3227.4	3203.1	3181.9	3348.6	3515.3	3685.0	3851.6
50°	3736.5	3600.1	3466.8	3412.2	3354.6	3300.1	3242.5	3378.9	3518.3	3657.7	3794.1
52.5°	4033.5	3863.7	3697.1	3612.2	3527.4	3439.5	3354.6	3469.8	3588.0	3706.2	3821.3
55°	4288.0	4115.3	3939.5	3839.5	3739.5	3639.5	3539.5	3654.7	3769.8	3885.0	4000.1
57.5°	4491.0	4318.3	4145.6	4051.6	3954.7	3860.7	3763.7	3872.8	3985.0	4097.1	4206.2
60°	4630.4	4463.8	4297.1	4206.2	4115.3	4024.4	3933.4	4063.8	4194.1	4327.4	4457.7
62.5°	4557.7	4436.5	4315.3	4275.9	4236.5	4194.1	4154.7	4278.9	4400.1	4524.4	4648.6
65°	4291.0	4209.2	4127.4	4166.8	4209.2	4248.6	4291.0	4372.9	4454.7	4539.5	4621.3
67.5°	3857.7	3851.6	3842.5	3930.4	4018.3	4109.2	4197.1	4251.6	4303.2	4357.7	4412.3
70°	3236.5	3269.8	3300.1	3451.6	3603.1	3754.7	3906.2	3927.4	3948.6	3969.8	3991.0
72.5°	2533.4	2575.8	2621.3	2821.3	3018.3	3218.3	3418.3	3406.2	3394.0	3378.9	3366.8
75°	1994.0	2033.4	2075.8	2260.7	2445.5	2630.4	2815.2	2763.7	2715.2	2663.7	2612.2
77.5°	1591.0	1633.4	1678.8	1851.6	2024.3	2200.1	2372.8	2248.6	2124.3	2000.1	1875.8
80°	1369.7	1390.9	1409.1	1527.3	1642.5	1760.7	1878.8	1751.6	1621.3	1491.0	1363.7
82.5°	1124.3	1112.2	1103.1	1172.8	1242.5	1312.2	1381.9	1260.6	1139.4	1015.2	894.0
85°	839.4	827.3	815.2	851.5	887.9	927.3	963.7	824.3	684.9	542.4	403.0
87.5°	487.9	500.0	512.1	551.5	590.9	633.4	672.7	530.3	387.9	242.4	100.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675972
 CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	2181.9	2181.9
2.5°	2266.7	2251.6
5°	2142.5	2121.3
7.5°	2006.1	1978.8
10°	1881.9	1845.5
12.5°	1803.1	1757.6
15°	1772.8	1718.2
17.5°	1863.7	1812.2
20°	2003.1	1933.4
22.5°	2172.8	2087.9
25°	2466.7	2363.7
27.5°	2706.1	2600.1
30°	2854.6	2739.5
32.5°	3018.3	2866.8
35°	3188.0	3042.5
37.5°	3394.0	3230.4
40°	3606.2	3436.5
42.5°	3678.9	3569.8
45°	3748.6	3645.6
47.5°	3763.7	3678.9
50°	3778.9	3766.8
52.5°	3821.3	3818.3
55°	4003.1	4006.2
57.5°	4227.4	4245.6
60°	4433.5	4412.3
62.5°	4539.5	4430.4
65°	4466.8	4315.3
67.5°	4248.6	4085.0
70°	3769.8	3548.6
72.5°	3172.8	2978.9
75°	2445.5	2281.9
77.5°	1739.4	1603.1
80°	1224.3	1087.9
82.5°	784.9	675.8
85°	354.6	309.1
87.5°	100.0	97.0
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P675972

CATALOG NUMBER: CCW-SA-2C-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)