

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675981

Luminaire Tested: **CCW-SA-2A-735-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P675981
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2A-735-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @350mA w/
SLR distribution lens
Light Source: (32) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4478.5 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 36.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P675981
CATALOG NUMBER: CCW-SA-2A-735-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	921.5	0.0	921.5
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3557.1	0.0	3557.1
	% Fixture	79.4	0.0	79.4
Total	Lumens	4478.5	0.0	4478.5
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.1	2.5
10°-20°	234.6	5.2
20°-30°	343.3	7.7
30°-40°	483.6	10.8
40°-50°	664.6	14.8
50°-60°	905.8	20.2
60°-70°	991.4	22.1
70°-80°	572.5	12.8
80°-90°	171.6	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4478.5	100.0
0°-180°	4478.5	100.0

Coefficient of Utilization



REPORT NUMBER: P675981


CATALOG NUMBER: CCW-SA-2A-735-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	460.0	10.3			
FM	(30°-60°)	1634.4	36.5			
FH	(60°-80°)	1317.0	29.4			G1/1800
FVH	(80°-90°)	145.8	3.3			G2/225
BL	(0°-30°)	229.1	5.1	B1/500		
BM	(30°-60°)	419.6	9.4	B1/1000		
BH	(60°-80°)	247.0	5.5	B1/500		G1/500
BVH	(80°-90°)	25.8	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2
2.5°	1475.9	1467.9	1462.0	1456.0	1448.0	1442.1	1434.1	1426.2	1416.3	1408.3	1398.4
5°	1390.4	1366.6	1342.8	1328.9	1313.0	1299.1	1283.2	1265.3	1247.4	1227.6	1209.7
7.5°	1297.1	1267.3	1237.5	1213.7	1187.8	1164.0	1138.2	1116.3	1094.5	1072.6	1050.8
10°	1209.7	1181.9	1154.1	1124.3	1092.5	1062.7	1030.9	1001.1	971.3	941.5	911.7
12.5°	1152.1	1118.3	1086.5	1052.8	1021.0	987.2	953.4	925.6	897.8	868.0	840.2
15°	1126.3	1094.5	1064.7	1030.9	997.1	963.4	929.6	897.8	868.0	836.3	804.5
17.5°	1187.8	1142.2	1096.5	1052.8	1009.1	965.4	921.7	881.9	842.2	802.5	762.8
20°	1267.3	1209.7	1154.1	1100.4	1044.8	991.2	935.6	880.0	824.3	768.7	713.1
22.5°	1368.6	1303.0	1239.5	1170.0	1098.5	1028.9	957.4	887.9	818.4	746.9	677.3
25°	1549.4	1471.9	1394.4	1295.1	1193.8	1094.5	993.2	901.8	812.4	721.0	629.7
27.5°	1704.3	1599.0	1495.7	1376.5	1257.4	1138.2	1019.0	913.7	810.4	705.2	599.9
30°	1795.7	1692.4	1589.1	1444.1	1301.1	1156.1	1011.1	893.9	778.6	661.5	544.3
32.5°	1879.1	1763.9	1648.7	1489.8	1328.9	1170.0	1009.1	880.0	752.8	623.7	494.6
35°	1994.3	1867.2	1742.0	1557.3	1372.6	1187.8	1003.1	870.0	734.9	601.9	466.8
37.5°	2117.4	1960.5	1805.6	1601.0	1396.4	1191.8	987.2	856.1	725.0	593.9	462.8
40°	2252.5	2061.8	1873.1	1646.7	1422.2	1195.8	969.3	838.2	707.1	574.1	443.0
42.5°	2339.9	2133.3	1926.8	1682.4	1440.1	1195.8	951.5	822.3	693.2	562.1	433.0
45°	2389.6	2189.0	1990.3	1726.1	1462.0	1197.8	933.6	806.5	679.3	550.2	423.1
47.5°	2411.4	2224.7	2038.0	1759.9	1483.8	1205.7	927.6	798.5	667.4	538.3	407.2
50°	2469.0	2304.2	2139.3	1841.3	1545.4	1247.4	949.5	810.4	673.4	534.3	395.3
52.5°	2502.8	2361.8	2220.7	1914.8	1608.9	1303.0	997.1	842.2	687.3	532.3	377.4
55°	2626.0	2490.9	2355.8	2030.0	1702.3	1376.5	1048.8	878.0	707.1	534.3	363.5
57.5°	2782.9	2639.9	2498.8	2147.2	1795.7	1444.1	1092.5	909.7	725.0	542.3	357.5
60°	2892.1	2753.1	2616.0	2242.6	1867.2	1493.7	1118.3	927.6	736.9	544.3	353.6
62.5°	2904.0	2725.3	2548.5	2185.0	1821.5	1456.0	1092.5	907.8	723.0	536.3	351.6
65°	2828.6	2620.0	2411.4	2063.8	1716.2	1368.6	1021.0	852.1	683.3	512.5	343.6
67.5°	2677.6	2433.3	2189.0	1871.1	1553.3	1235.5	917.7	772.7	629.7	484.7	339.7
70°	2326.0	2111.5	1898.9	1622.8	1348.7	1072.6	796.5	677.3	560.2	441.0	321.8
72.5°	1952.6	1752.0	1553.3	1328.9	1106.4	881.9	657.5	568.1	478.7	387.3	298.0
75°	1495.7	1344.8	1195.8	1028.9	862.1	693.2	526.4	460.8	395.3	329.7	264.2
77.5°	1050.8	969.3	889.9	764.7	639.6	514.5	389.3	345.6	301.9	258.2	214.5
80°	713.1	667.4	623.7	534.3	444.9	353.6	264.2	236.4	206.6	178.8	149.0
82.5°	443.0	441.0	437.0	375.4	313.8	252.3	190.7	166.9	145.0	121.2	97.3
85°	202.6	236.4	268.2	234.4	200.6	166.9	133.1	117.2	101.3	83.4	67.5
87.5°	63.6	77.5	89.4	85.4	79.5	75.5	69.5	59.6	49.7	39.7	29.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981
 CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2
2.5°	1390.4	1384.5	1376.5	1368.6	1358.7	1350.7	1340.8	1330.9	1328.9	1324.9	1322.9
5°	1197.8	1185.8	1171.9	1160.0	1148.1	1134.2	1122.3	1108.4	1098.5	1086.5	1076.6
7.5°	1028.9	1009.1	987.2	965.4	945.5	925.6	903.8	883.9	874.0	864.1	854.1
10°	893.9	874.0	856.1	836.3	822.3	810.4	796.5	782.6	770.7	758.8	746.9
12.5°	826.3	812.4	798.5	784.6	768.7	754.8	738.9	723.0	709.1	697.2	683.3
15°	784.6	764.7	742.9	723.0	701.2	681.3	659.5	637.6	621.7	607.8	591.9
17.5°	734.9	705.2	677.3	647.5	623.7	599.9	574.1	550.2	532.3	512.5	494.6
20°	679.3	645.6	609.8	576.0	548.2	522.4	494.6	466.8	446.9	425.1	405.2
22.5°	631.7	588.0	542.3	496.6	466.8	437.0	405.2	375.4	357.5	337.7	319.8
25°	580.0	532.3	482.7	433.0	403.2	371.4	341.7	309.9	296.0	284.0	270.1
27.5°	552.2	504.5	454.9	407.2	379.4	349.6	321.8	292.0	282.1	270.1	260.2
30°	496.6	450.9	403.2	355.6	335.7	317.8	298.0	278.1	274.1	272.1	268.2
32.5°	446.9	399.3	351.6	303.9	286.0	268.2	250.3	232.4	230.4	226.4	224.5
35°	421.1	375.4	327.7	282.1	266.2	248.3	232.4	214.5	210.6	204.6	200.6
37.5°	415.1	367.5	317.8	270.1	254.3	238.4	220.5	204.6	200.6	196.6	192.7
40°	399.3	353.6	309.9	264.2	248.3	232.4	214.5	198.6	194.7	190.7	186.7
42.5°	387.3	343.6	298.0	252.3	238.4	224.5	208.6	194.7	190.7	186.7	180.8
45°	377.4	331.7	284.0	238.4	228.4	218.5	206.6	196.6	192.7	186.7	182.7
47.5°	361.5	317.8	272.1	226.4	216.5	208.6	198.6	188.7	184.7	180.8	176.8
50°	349.6	303.9	258.2	212.5	204.6	196.6	188.7	180.8	180.8	182.7	182.7
52.5°	333.7	290.0	246.3	202.6	194.7	186.7	178.8	170.8	172.8	174.8	176.8
55°	319.8	278.1	234.4	190.7	182.7	174.8	164.9	156.9	158.9	160.9	162.9
57.5°	313.8	270.1	226.4	182.7	174.8	164.9	156.9	147.0	147.0	147.0	147.0
60°	309.9	264.2	220.5	174.8	164.9	156.9	147.0	137.1	135.1	135.1	133.1
62.5°	307.9	262.2	218.5	172.8	160.9	151.0	139.0	127.1	125.1	123.2	121.2
65°	299.9	258.2	214.5	170.8	156.9	145.0	131.1	117.2	115.2	115.2	113.2
67.5°	298.0	254.3	212.5	168.8	154.9	139.0	125.1	109.2	107.3	105.3	103.3
70°	282.1	244.3	204.6	164.9	149.0	135.1	119.2	103.3	101.3	97.3	95.3
72.5°	262.2	228.4	192.7	156.9	141.0	125.1	109.2	93.4	91.4	89.4	85.4
75°	232.4	200.6	168.8	137.1	123.2	111.2	97.3	83.4	81.4	79.5	75.5
77.5°	190.7	164.9	141.0	115.2	105.3	95.3	85.4	75.5	73.5	71.5	67.5
80°	135.1	119.2	105.3	89.4	83.4	75.5	69.5	61.6	61.6	59.6	59.6
82.5°	89.4	81.4	73.5	65.5	61.6	57.6	53.6	49.7	49.7	47.7	47.7
85°	63.6	59.6	53.6	49.7	47.7	43.7	41.7	37.7	37.7	37.7	37.7
87.5°	29.8	29.8	27.8	27.8	25.8	25.8	23.8	21.8	21.8	21.8	21.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2
2.5°	1318.9	1313.0	1307.0	1299.1	1293.1	1285.2	1275.2	1267.3	1257.4	1257.4	1255.4
5°	1064.7	1058.7	1052.8	1044.8	1038.9	1030.9	1025.0	1017.0	1009.1	1009.1	1007.1
7.5°	844.2	832.3	820.4	806.5	794.5	786.6	778.6	768.7	760.8	754.8	748.9
10°	734.9	723.0	709.1	697.2	683.3	673.4	663.4	651.5	641.6	633.6	625.7
12.5°	669.4	655.5	641.6	627.7	613.8	599.9	588.0	574.1	560.2	550.2	540.3
15°	576.0	562.1	548.2	534.3	520.4	504.5	488.6	470.8	454.9	446.9	441.0
17.5°	474.7	460.8	444.9	431.0	415.1	403.2	391.3	379.4	367.5	359.5	353.6
20°	383.4	367.5	351.6	335.7	319.8	311.9	303.9	296.0	288.0	282.1	278.1
22.5°	299.9	290.0	282.1	272.1	262.2	256.2	252.3	246.3	240.3	240.3	240.3
25°	256.2	250.3	246.3	240.3	234.4	232.4	230.4	226.4	224.5	222.5	222.5
27.5°	248.3	242.3	236.4	230.4	224.5	222.5	220.5	216.5	214.5	214.5	214.5
30°	264.2	262.2	260.2	258.2	256.2	252.3	246.3	242.3	236.4	232.4	228.4
32.5°	220.5	218.5	218.5	216.5	214.5	218.5	220.5	224.5	226.4	228.4	230.4
35°	194.7	190.7	186.7	182.7	178.8	176.8	174.8	172.8	170.8	170.8	168.8
37.5°	188.7	184.7	180.8	176.8	172.8	170.8	168.8	166.9	164.9	164.9	162.9
40°	182.7	178.8	176.8	172.8	168.8	166.9	164.9	160.9	158.9	156.9	156.9
42.5°	176.8	174.8	170.8	168.8	164.9	162.9	160.9	156.9	154.9	152.9	151.0
45°	176.8	172.8	168.8	164.9	160.9	158.9	154.9	152.9	149.0	149.0	147.0
47.5°	172.8	168.8	164.9	160.9	156.9	154.9	151.0	149.0	145.0	143.0	141.0
50°	182.7	176.8	168.8	162.9	154.9	152.9	149.0	147.0	143.0	141.0	139.0
52.5°	178.8	172.8	164.9	158.9	151.0	147.0	145.0	141.0	137.1	135.1	133.1
55°	164.9	158.9	154.9	149.0	143.0	139.0	135.1	131.1	127.1	125.1	125.1
57.5°	147.0	145.0	143.0	141.0	139.0	135.1	131.1	125.1	121.2	119.2	117.2
60°	131.1	133.1	135.1	137.1	139.0	133.1	127.1	121.2	115.2	113.2	111.2
62.5°	119.2	123.2	127.1	129.1	133.1	127.1	121.2	115.2	109.2	107.3	105.3
65°	111.2	113.2	113.2	115.2	115.2	111.2	109.2	105.3	101.3	99.3	99.3
67.5°	101.3	101.3	101.3	99.3	99.3	97.3	97.3	95.3	93.4	91.4	91.4
70°	91.4	91.4	91.4	89.4	89.4	87.4	87.4	85.4	83.4	83.4	81.4
72.5°	83.4	83.4	81.4	81.4	79.5	79.5	79.5	77.5	77.5	75.5	75.5
75°	73.5	73.5	71.5	71.5	69.5	69.5	69.5	67.5	67.5	67.5	65.5
77.5°	65.5	65.5	63.6	63.6	61.6	61.6	61.6	59.6	59.6	57.6	57.6
80°	57.6	57.6	55.6	55.6	53.6	53.6	51.6	51.6	49.7	49.7	47.7
82.5°	45.7	45.7	45.7	45.7	45.7	43.7	43.7	41.7	39.7	39.7	37.7
85°	37.7	37.7	37.7	35.8	35.8	35.8	33.8	33.8	31.8	29.8	29.8
87.5°	21.8	21.8	21.8	19.9	19.9	19.9	19.9	19.9	19.9	19.9	17.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981
 CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2
2.5°	1255.4	1253.4	1245.4	1237.5	1245.4	1253.4	1253.4	1253.4	1251.4	1251.4	1251.4
5°	1007.1	1005.1	1001.1	997.1	997.1	995.2	999.1	1003.1	1007.1	1011.1	1015.0
7.5°	740.9	734.9	729.0	723.0	727.0	729.0	734.9	738.9	744.9	748.9	758.8
10°	617.8	609.8	603.8	597.9	593.9	589.9	586.0	584.0	580.0	576.0	580.0
12.5°	528.4	518.4	508.5	496.6	494.6	492.6	488.6	484.7	480.7	476.7	474.7
15°	433.0	425.1	421.1	415.1	407.2	399.3	395.3	393.3	389.3	385.4	383.4
17.5°	345.6	337.7	331.7	325.8	323.8	319.8	319.8	319.8	319.8	319.8	319.8
20°	272.1	266.2	266.2	264.2	264.2	262.2	264.2	266.2	266.2	268.2	270.1
22.5°	238.4	238.4	236.4	234.4	236.4	236.4	238.4	240.3	242.3	244.3	246.3
25°	220.5	218.5	220.5	222.5	222.5	222.5	224.5	224.5	226.4	226.4	226.4
27.5°	212.5	212.5	214.5	214.5	216.5	216.5	216.5	214.5	214.5	212.5	212.5
30°	224.5	220.5	220.5	220.5	218.5	216.5	214.5	214.5	212.5	210.6	208.6
32.5°	232.4	234.4	232.4	228.4	226.4	222.5	220.5	216.5	214.5	210.6	206.6
35°	168.8	166.9	170.8	172.8	174.8	176.8	178.8	180.8	180.8	182.7	182.7
37.5°	162.9	160.9	160.9	158.9	158.9	158.9	158.9	158.9	156.9	156.9	158.9
40°	154.9	152.9	152.9	151.0	151.0	149.0	149.0	149.0	149.0	149.0	149.0
42.5°	149.0	147.0	147.0	147.0	147.0	145.0	145.0	143.0	143.0	141.0	141.0
45°	147.0	145.0	143.0	141.0	141.0	139.0	139.0	139.0	137.1	137.1	137.1
47.5°	139.0	137.1	137.1	135.1	135.1	133.1	133.1	133.1	131.1	131.1	131.1
50°	135.1	133.1	133.1	131.1	131.1	129.1	129.1	129.1	127.1	127.1	127.1
52.5°	129.1	127.1	127.1	127.1	125.1	123.2	123.2	123.2	121.2	121.2	121.2
55°	123.2	121.2	121.2	121.2	119.2	117.2	117.2	117.2	115.2	115.2	115.2
57.5°	115.2	113.2	113.2	111.2	111.2	111.2	111.2	111.2	109.2	109.2	109.2
60°	109.2	107.3	107.3	105.3	105.3	103.3	103.3	103.3	103.3	103.3	103.3
62.5°	103.3	101.3	99.3	97.3	99.3	99.3	99.3	99.3	97.3	97.3	97.3
65°	97.3	95.3	93.4	91.4	91.4	91.4	91.4	91.4	91.4	91.4	91.4
67.5°	89.4	87.4	85.4	83.4	85.4	85.4	85.4	85.4	85.4	85.4	85.4
70°	81.4	79.5	79.5	77.5	77.5	75.5	75.5	77.5	77.5	77.5	77.5
72.5°	73.5	71.5	71.5	69.5	69.5	69.5	69.5	69.5	69.5	69.5	69.5
75°	65.5	63.6	63.6	61.6	61.6	61.6	61.6	61.6	61.6	61.6	61.6
77.5°	55.6	53.6	53.6	53.6	53.6	53.6	53.6	55.6	55.6	55.6	55.6
80°	47.7	45.7	45.7	45.7	45.7	45.7	45.7	45.7	45.7	45.7	45.7
82.5°	37.7	35.8	35.8	35.8	35.8	35.8	35.8	35.8	35.8	35.8	35.8
85°	27.8	25.8	25.8	25.8	27.8	27.8	27.8	27.8	27.8	27.8	27.8
87.5°	17.9	15.9	15.9	15.9	17.9	17.9	17.9	17.9	15.9	15.9	15.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2
2.5°	1251.4	1251.4	1251.4	1249.4	1247.4	1245.4	1243.5	1249.4	1253.4	1259.3	1263.3
5°	1017.0	1021.0	1023.0	1028.9	1034.9	1040.8	1046.8	1050.8	1054.8	1056.7	1060.7
7.5°	766.7	776.7	784.6	792.6	800.5	806.5	814.4	820.4	826.3	832.3	838.2
10°	582.0	586.0	588.0	595.9	601.9	609.8	615.8	621.7	627.7	631.7	637.6
12.5°	472.8	468.8	466.8	466.8	466.8	466.8	466.8	470.8	474.7	478.7	482.7
15°	381.4	379.4	377.4	375.4	373.4	369.5	367.5	371.4	375.4	379.4	383.4
17.5°	319.8	319.8	319.8	317.8	315.8	313.8	311.9	313.8	315.8	315.8	317.8
20°	274.1	276.1	278.1	280.1	280.1	282.1	282.1	284.0	286.0	286.0	288.0
22.5°	246.3	248.3	248.3	248.3	250.3	250.3	250.3	252.3	254.3	256.2	258.2
25°	224.5	224.5	222.5	222.5	224.5	224.5	224.5	224.5	226.4	226.4	226.4
27.5°	212.5	210.6	210.6	210.6	210.6	208.6	208.6	208.6	208.6	208.6	208.6
30°	206.6	204.6	202.6	200.6	200.6	198.6	196.6	196.6	196.6	196.6	196.6
32.5°	204.6	200.6	196.6	194.7	194.7	192.7	190.7	188.7	188.7	186.7	184.7
35°	182.7	180.8	180.8	178.8	176.8	174.8	172.8	172.8	172.8	170.8	170.8
37.5°	158.9	160.9	160.9	160.9	162.9	162.9	162.9	162.9	164.9	164.9	164.9
40°	149.0	149.0	149.0	151.0	152.9	152.9	154.9	154.9	156.9	156.9	156.9
42.5°	141.0	139.0	139.0	141.0	141.0	143.0	143.0	145.0	147.0	147.0	149.0
45°	137.1	135.1	135.1	135.1	135.1	133.1	133.1	135.1	137.1	139.0	141.0
47.5°	129.1	129.1	127.1	127.1	127.1	127.1	127.1	127.1	129.1	129.1	129.1
50°	125.1	125.1	123.2	123.2	123.2	123.2	123.2	123.2	123.2	123.2	123.2
52.5°	121.2	119.2	119.2	119.2	119.2	117.2	117.2	117.2	117.2	117.2	117.2
55°	115.2	113.2	113.2	113.2	113.2	113.2	113.2	113.2	115.2	115.2	115.2
57.5°	109.2	107.3	107.3	107.3	109.2	109.2	109.2	109.2	111.2	111.2	111.2
60°	103.3	103.3	103.3	103.3	103.3	103.3	103.3	105.3	105.3	107.3	107.3
62.5°	97.3	97.3	97.3	97.3	99.3	99.3	99.3	99.3	101.3	101.3	101.3
65°	91.4	91.4	91.4	91.4	93.4	93.4	93.4	93.4	93.4	93.4	93.4
67.5°	85.4	85.4	85.4	85.4	85.4	85.4	85.4	87.4	87.4	89.4	89.4
70°	77.5	75.5	75.5	77.5	77.5	79.5	79.5	81.4	81.4	83.4	83.4
72.5°	69.5	69.5	69.5	69.5	69.5	69.5	69.5	71.5	73.5	73.5	75.5
75°	61.6	61.6	61.6	61.6	63.6	63.6	63.6	65.5	65.5	67.5	67.5
77.5°	55.6	53.6	53.6	53.6	55.6	55.6	55.6	57.6	57.6	59.6	59.6
80°	45.7	45.7	45.7	45.7	47.7	47.7	47.7	47.7	49.7	49.7	49.7
82.5°	37.7	37.7	37.7	37.7	37.7	37.7	37.7	37.7	39.7	39.7	39.7
85°	27.8	27.8	27.8	27.8	29.8	29.8	29.8	29.8	29.8	29.8	29.8
87.5°	17.9	17.9	17.9	17.9	17.9	17.9	17.9	17.9	19.9	19.9	19.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981
 CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2
2.5°	1263.3	1263.3	1263.3	1263.3	1267.3	1269.3	1273.2	1275.2	1273.2	1271.3	1267.3
5°	1062.7	1064.7	1064.7	1066.7	1066.7	1066.7	1066.7	1066.7	1070.6	1074.6	1078.6
7.5°	840.2	842.2	844.2	846.2	846.2	846.2	844.2	844.2	846.2	846.2	848.2
10°	643.6	651.5	657.5	663.4	659.5	653.5	649.5	643.6	643.6	643.6	641.6
12.5°	486.7	488.6	492.6	494.6	492.6	492.6	490.6	488.6	490.6	494.6	496.6
15°	385.4	385.4	387.3	387.3	389.3	391.3	391.3	393.3	397.3	399.3	403.2
17.5°	319.8	321.8	321.8	323.8	323.8	325.8	325.8	325.8	329.7	333.7	339.7
20°	288.0	288.0	288.0	288.0	288.0	286.0	286.0	284.0	286.0	290.0	292.0
22.5°	258.2	260.2	260.2	260.2	258.2	256.2	252.3	250.3	250.3	252.3	252.3
25°	226.4	224.5	224.5	222.5	222.5	224.5	224.5	224.5	226.4	226.4	228.4
27.5°	208.6	206.6	206.6	204.6	204.6	206.6	206.6	206.6	206.6	206.6	206.6
30°	194.7	194.7	192.7	190.7	192.7	192.7	194.7	194.7	196.6	196.6	198.6
32.5°	184.7	182.7	182.7	180.8	182.7	182.7	184.7	184.7	186.7	188.7	188.7
35°	170.8	170.8	170.8	170.8	170.8	170.8	168.8	168.8	168.8	168.8	168.8
37.5°	162.9	162.9	160.9	158.9	158.9	158.9	158.9	158.9	156.9	154.9	152.9
40°	156.9	154.9	154.9	152.9	151.0	151.0	149.0	147.0	147.0	145.0	145.0
42.5°	149.0	147.0	147.0	145.0	143.0	143.0	141.0	139.0	139.0	139.0	137.1
45°	139.0	139.0	137.1	135.1	135.1	135.1	133.1	133.1	133.1	133.1	131.1
47.5°	129.1	129.1	127.1	127.1	127.1	127.1	125.1	125.1	125.1	125.1	125.1
50°	123.2	123.2	123.2	123.2	123.2	123.2	121.2	121.2	121.2	121.2	121.2
52.5°	117.2	117.2	117.2	117.2	117.2	117.2	117.2	117.2	117.2	117.2	117.2
55°	115.2	115.2	115.2	115.2	115.2	115.2	113.2	113.2	113.2	115.2	115.2
57.5°	111.2	111.2	109.2	109.2	109.2	109.2	109.2	109.2	109.2	109.2	109.2
60°	107.3	107.3	107.3	107.3	107.3	107.3	107.3	107.3	107.3	107.3	107.3
62.5°	101.3	101.3	101.3	101.3	101.3	103.3	103.3	103.3	103.3	103.3	101.3
65°	93.4	95.3	95.3	95.3	95.3	95.3	95.3	95.3	95.3	95.3	95.3
67.5°	89.4	89.4	89.4	89.4	89.4	89.4	89.4	89.4	89.4	89.4	89.4
70°	83.4	83.4	81.4	81.4	81.4	83.4	83.4	83.4	83.4	83.4	83.4
72.5°	75.5	75.5	75.5	75.5	75.5	75.5	75.5	75.5	75.5	77.5	77.5
75°	67.5	67.5	67.5	67.5	67.5	67.5	67.5	67.5	67.5	67.5	67.5
77.5°	59.6	59.6	57.6	57.6	57.6	59.6	59.6	59.6	59.6	61.6	61.6
80°	49.7	49.7	49.7	49.7	49.7	49.7	49.7	49.7	49.7	51.6	51.6
82.5°	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	41.7	41.7
85°	29.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	33.8	33.8
87.5°	19.9	19.9	19.9	19.9	19.9	19.9	17.9	17.9	17.9	17.9	15.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981
 CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2
2.5°	1265.3	1267.3	1269.3	1269.3	1271.3	1273.2	1273.2	1281.2	1289.1	1293.1	1297.1
5°	1082.6	1080.6	1080.6	1078.6	1076.6	1082.6	1088.5	1100.4	1112.4	1114.3	1118.3
7.5°	848.2	850.2	852.1	852.1	854.1	848.2	840.2	842.2	844.2	854.1	862.1
10°	641.6	643.6	645.6	645.6	647.5	645.6	641.6	647.5	653.5	661.5	671.4
12.5°	498.6	504.5	510.5	514.5	520.4	524.4	526.4	534.3	540.3	550.2	560.2
15°	407.2	411.2	415.1	419.1	423.1	427.1	431.0	439.0	446.9	458.8	470.8
17.5°	343.6	343.6	345.6	345.6	345.6	349.6	353.6	357.5	359.5	371.4	383.4
20°	294.0	292.0	290.0	288.0	286.0	290.0	292.0	294.0	296.0	303.9	309.9
22.5°	252.3	252.3	254.3	254.3	254.3	252.3	248.3	250.3	250.3	254.3	260.2
25°	228.4	228.4	228.4	226.4	226.4	228.4	230.4	230.4	228.4	230.4	232.4
27.5°	206.6	208.6	208.6	210.6	210.6	212.5	212.5	212.5	212.5	214.5	216.5
30°	198.6	198.6	200.6	200.6	200.6	202.6	204.6	204.6	204.6	206.6	210.6
32.5°	190.7	192.7	194.7	196.6	198.6	200.6	200.6	202.6	202.6	204.6	206.6
35°	168.8	166.9	166.9	164.9	162.9	162.9	162.9	162.9	160.9	162.9	162.9
37.5°	151.0	151.0	151.0	149.0	149.0	151.0	151.0	151.0	151.0	152.9	152.9
40°	143.0	143.0	143.0	143.0	143.0	143.0	143.0	145.0	145.0	147.0	149.0
42.5°	137.1	137.1	137.1	137.1	137.1	139.0	139.0	139.0	139.0	141.0	141.0
45°	131.1	131.1	131.1	131.1	131.1	131.1	131.1	133.1	133.1	135.1	137.1
47.5°	125.1	125.1	125.1	125.1	125.1	127.1	129.1	129.1	129.1	131.1	131.1
50°	121.2	121.2	121.2	121.2	121.2	123.2	123.2	125.1	125.1	127.1	129.1
52.5°	117.2	117.2	117.2	117.2	117.2	119.2	119.2	121.2	121.2	123.2	125.1
55°	115.2	115.2	115.2	113.2	113.2	115.2	115.2	117.2	117.2	119.2	119.2
57.5°	109.2	109.2	109.2	109.2	109.2	109.2	109.2	111.2	111.2	113.2	115.2
60°	107.3	107.3	105.3	105.3	103.3	105.3	105.3	107.3	107.3	109.2	109.2
62.5°	101.3	101.3	101.3	99.3	99.3	101.3	101.3	101.3	101.3	103.3	105.3
65°	95.3	95.3	95.3	93.4	93.4	95.3	95.3	95.3	95.3	97.3	99.3
67.5°	89.4	89.4	89.4	87.4	87.4	87.4	87.4	89.4	89.4	91.4	93.4
70°	83.4	83.4	83.4	81.4	81.4	81.4	79.5	81.4	83.4	85.4	85.4
72.5°	77.5	77.5	77.5	75.5	75.5	75.5	73.5	75.5	75.5	77.5	77.5
75°	67.5	67.5	67.5	67.5	67.5	67.5	65.5	65.5	65.5	67.5	67.5
77.5°	61.6	61.6	61.6	59.6	59.6	59.6	57.6	57.6	57.6	59.6	59.6
80°	51.6	51.6	51.6	49.7	49.7	49.7	47.7	47.7	47.7	49.7	49.7
82.5°	41.7	41.7	41.7	39.7	39.7	39.7	37.7	37.7	37.7	39.7	39.7
85°	33.8	33.8	33.8	33.8	33.8	33.8	31.8	31.8	31.8	33.8	35.8
87.5°	15.9	15.9	17.9	17.9	17.9	17.9	15.9	15.9	13.9	13.9	15.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981
 CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2
2.5°	1301.1	1305.0	1315.0	1322.9	1332.8	1340.8	1346.7	1354.7	1360.6	1366.6	1370.6
5°	1120.3	1122.3	1132.2	1142.2	1150.1	1160.0	1173.9	1187.8	1201.7	1215.6	1225.6
7.5°	872.0	880.0	891.9	905.8	917.7	929.6	943.5	959.4	973.3	987.2	1001.1
10°	679.3	687.3	699.2	711.1	721.0	733.0	748.9	764.7	780.6	796.5	812.4
12.5°	570.1	580.0	593.9	607.8	619.7	633.6	653.5	671.4	691.2	709.1	729.0
15°	480.7	492.6	510.5	530.4	548.2	566.1	586.0	605.8	623.7	643.6	663.4
17.5°	395.3	407.2	423.1	441.0	456.9	472.8	496.6	518.4	542.3	564.1	586.0
20°	317.8	323.8	339.7	355.6	371.4	387.3	405.2	423.1	441.0	458.8	486.7
22.5°	264.2	268.2	276.1	282.1	290.0	296.0	313.8	331.7	347.6	365.5	391.3
25°	232.4	234.4	240.3	244.3	250.3	254.3	266.2	276.1	288.0	298.0	321.8
27.5°	216.5	218.5	220.5	222.5	224.5	226.4	234.4	242.3	248.3	256.2	278.1
30°	212.5	214.5	220.5	224.5	230.4	234.4	238.4	242.3	246.3	250.3	264.2
32.5°	208.6	210.6	210.6	208.6	208.6	206.6	210.6	212.5	216.5	218.5	230.4
35°	164.9	164.9	166.9	168.8	170.8	172.8	178.8	182.7	188.7	192.7	202.6
37.5°	154.9	154.9	156.9	160.9	162.9	164.9	168.8	172.8	176.8	180.8	190.7
40°	149.0	151.0	152.9	154.9	156.9	158.9	162.9	164.9	168.8	170.8	178.8
42.5°	143.0	143.0	145.0	149.0	151.0	152.9	156.9	158.9	162.9	164.9	172.8
45°	139.0	141.0	143.0	145.0	145.0	147.0	151.0	154.9	156.9	160.9	168.8
47.5°	133.1	133.1	137.1	139.0	143.0	145.0	149.0	151.0	154.9	156.9	164.9
50°	129.1	131.1	135.1	137.1	141.0	143.0	149.0	152.9	158.9	162.9	166.9
52.5°	125.1	127.1	131.1	133.1	137.1	139.0	147.0	154.9	160.9	168.8	168.8
55°	121.2	121.2	125.1	131.1	135.1	139.0	143.0	149.0	152.9	156.9	156.9
57.5°	115.2	117.2	121.2	127.1	131.1	135.1	139.0	143.0	145.0	149.0	147.0
60°	111.2	111.2	117.2	123.2	129.1	135.1	135.1	135.1	133.1	133.1	133.1
62.5°	105.3	107.3	115.2	125.1	133.1	141.0	135.1	129.1	123.2	117.2	119.2
65°	101.3	103.3	107.3	113.2	117.2	121.2	117.2	115.2	111.2	107.3	109.2
67.5°	93.4	95.3	97.3	97.3	99.3	99.3	99.3	99.3	99.3	99.3	101.3
70°	87.4	87.4	87.4	89.4	89.4	89.4	89.4	89.4	89.4	89.4	91.4
72.5°	79.5	79.5	79.5	79.5	79.5	79.5	79.5	79.5	79.5	79.5	81.4
75°	69.5	69.5	69.5	69.5	69.5	69.5	69.5	69.5	69.5	69.5	71.5
77.5°	61.6	61.6	61.6	61.6	61.6	61.6	61.6	61.6	59.6	59.6	61.6
80°	51.6	51.6	51.6	51.6	49.7	49.7	49.7	49.7	49.7	49.7	51.6
82.5°	41.7	41.7	41.7	41.7	39.7	39.7	39.7	39.7	37.7	37.7	39.7
85°	37.7	39.7	39.7	41.7	41.7	41.7	39.7	37.7	35.8	33.8	33.8
87.5°	15.9	15.9	15.9	15.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981
 CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2
2.5°	1376.5	1380.5	1384.5	1390.4	1398.4	1404.3	1410.3	1422.2	1436.1	1448.0	1460.0
5°	1235.5	1245.4	1255.4	1267.3	1279.2	1289.1	1301.1	1324.9	1348.7	1370.6	1394.4
7.5°	1013.0	1026.9	1038.9	1058.7	1076.6	1096.5	1114.3	1144.1	1171.9	1201.7	1229.5
10°	828.3	844.2	860.1	885.9	913.7	939.5	965.4	989.2	1015.0	1038.9	1062.7
12.5°	748.9	766.7	786.6	802.5	820.4	836.3	852.1	880.0	907.8	935.6	963.4
15°	683.3	703.2	723.0	742.9	760.8	780.6	798.5	822.3	848.2	872.0	895.8
17.5°	607.8	627.7	649.5	671.4	693.2	715.1	736.9	770.7	804.5	836.3	870.0
20°	512.5	540.3	566.1	595.9	625.7	655.5	685.3	721.0	756.8	790.6	826.3
22.5°	417.1	443.0	468.8	504.5	540.3	574.1	609.8	657.5	703.2	750.8	796.5
25°	347.6	371.4	395.3	435.0	472.8	512.5	550.2	607.8	663.4	721.0	776.7
27.5°	299.9	321.8	343.6	385.4	427.1	466.8	508.5	572.1	633.6	697.2	758.8
30°	278.1	292.0	305.9	345.6	385.4	423.1	462.8	524.4	586.0	647.5	709.1
32.5°	242.3	254.3	266.2	301.9	337.7	371.4	407.2	470.8	532.3	595.9	657.5
35°	214.5	224.5	234.4	268.2	299.9	333.7	365.5	429.1	492.6	556.2	619.7
37.5°	198.6	208.6	216.5	246.3	278.1	307.9	337.7	401.2	462.8	526.4	588.0
40°	186.7	192.7	200.6	230.4	258.2	288.0	315.8	373.4	433.0	490.6	548.2
42.5°	178.8	186.7	192.7	218.5	246.3	272.1	298.0	353.6	409.2	462.8	518.4
45°	176.8	184.7	192.7	214.5	236.4	256.2	278.1	331.7	385.4	439.0	492.6
47.5°	172.8	178.8	186.7	204.6	220.5	238.4	254.3	307.9	361.5	413.2	466.8
50°	170.8	172.8	176.8	192.7	208.6	224.5	240.3	294.0	347.6	401.2	454.9
52.5°	168.8	168.8	168.8	182.7	196.6	208.6	222.5	276.1	331.7	385.4	439.0
55°	156.9	154.9	154.9	168.8	180.8	194.7	206.6	260.2	313.8	365.5	419.1
57.5°	145.0	143.0	141.0	152.9	164.9	176.8	188.7	242.3	298.0	351.6	405.2
60°	133.1	131.1	131.1	143.0	152.9	164.9	174.8	230.4	284.0	339.7	393.3
62.5°	119.2	121.2	121.2	131.1	143.0	152.9	162.9	218.5	276.1	331.7	387.3
65°	109.2	111.2	111.2	123.2	135.1	147.0	158.9	212.5	268.2	321.8	375.4
67.5°	101.3	103.3	103.3	117.2	129.1	143.0	154.9	202.6	252.3	299.9	347.6
70°	93.4	93.4	95.3	109.2	123.2	137.1	151.0	192.7	234.4	274.1	315.8
72.5°	83.4	85.4	87.4	101.3	113.2	127.1	139.0	176.8	214.5	252.3	290.0
75°	73.5	75.5	77.5	89.4	101.3	113.2	125.1	160.9	194.7	230.4	264.2
77.5°	65.5	67.5	69.5	79.5	89.4	99.3	109.2	135.1	162.9	188.7	214.5
80°	53.6	53.6	55.6	63.6	71.5	77.5	85.4	103.3	121.2	137.1	154.9
82.5°	39.7	41.7	41.7	47.7	51.6	57.6	61.6	71.5	79.5	89.4	97.3
85°	33.8	31.8	31.8	35.8	37.7	41.7	43.7	49.7	53.6	59.6	63.6
87.5°	13.9	11.9	11.9	13.9	17.9	19.9	21.8	21.8	23.8	23.8	23.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981
 CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2
2.5°	1465.9	1469.9	1475.9	1479.8	1489.8	1497.7	1507.6	1515.6	1521.5	1531.5	1527.5
5°	1412.3	1430.2	1448.0	1465.9	1479.8	1493.7	1505.7	1519.6	1535.4	1565.2	1573.2
7.5°	1253.4	1277.2	1299.1	1322.9	1350.7	1378.5	1406.3	1434.1	1460.0	1497.7	1521.5
10°	1096.5	1130.2	1162.0	1195.8	1221.6	1247.4	1271.3	1297.1	1332.8	1370.6	1414.3
12.5°	997.1	1030.9	1064.7	1098.5	1136.2	1171.9	1209.7	1245.4	1279.2	1309.0	1358.7
15°	931.6	969.3	1005.1	1040.8	1086.5	1130.2	1175.9	1219.6	1269.3	1309.0	1342.8
17.5°	915.7	961.4	1005.1	1050.8	1098.5	1146.1	1193.8	1241.5	1291.1	1350.7	1394.4
20°	887.9	949.5	1011.1	1072.6	1134.2	1193.8	1255.4	1315.0	1380.5	1452.0	1471.9
22.5°	872.0	945.5	1021.0	1094.5	1177.9	1263.3	1346.7	1430.2	1499.7	1553.3	1612.9
25°	870.0	961.4	1054.8	1146.1	1251.4	1354.7	1460.0	1563.3	1652.6	1706.3	1753.9
27.5°	868.0	979.3	1088.5	1197.8	1326.9	1454.0	1583.1	1710.2	1793.7	1871.1	1910.9
30°	844.2	977.3	1112.4	1245.4	1390.4	1535.4	1680.5	1825.5	1910.9	1964.5	1984.4
32.5°	814.4	971.3	1128.2	1285.2	1450.0	1614.9	1777.8	1942.6	2010.2	2055.9	2040.0
35°	790.6	963.4	1134.2	1305.0	1479.8	1656.6	1831.4	2006.2	2103.5	2167.1	2141.3
37.5°	768.7	949.5	1130.2	1311.0	1515.6	1720.2	1924.8	2129.4	2222.7	2290.3	2260.5
40°	742.9	935.6	1130.2	1322.9	1557.3	1789.7	2024.1	2256.5	2377.7	2435.3	2389.6
42.5°	721.0	921.7	1124.3	1324.9	1575.2	1825.5	2075.7	2326.0	2461.1	2542.5	2484.9
45°	693.2	893.9	1092.5	1293.1	1569.2	1845.3	2119.4	2395.5	2552.5	2616.0	2536.6
47.5°	663.4	862.1	1058.7	1255.4	1549.4	1843.3	2137.3	2431.3	2576.3	2651.8	2578.3
50°	653.5	852.1	1048.8	1247.4	1565.2	1885.0	2202.9	2520.7	2626.0	2687.5	2590.2
52.5°	651.5	862.1	1074.6	1285.2	1605.0	1922.8	2242.6	2560.4	2645.8	2711.4	2624.0
55°	645.6	874.0	1100.4	1326.9	1660.6	1996.3	2330.0	2663.7	2749.1	2796.8	2731.2
57.5°	651.5	897.8	1142.2	1388.5	1732.1	2075.7	2419.4	2763.0	2866.3	2900.1	2886.2
60°	655.5	917.7	1177.9	1440.1	1775.8	2111.5	2447.2	2782.9	2890.1	2973.6	2989.5
62.5°	645.6	903.8	1160.0	1418.3	1722.2	2026.1	2330.0	2633.9	2810.7	2933.8	3005.3
65°	615.8	854.1	1094.5	1332.8	1612.9	1895.0	2175.1	2455.1	2641.8	2824.6	2882.2
67.5°	550.2	752.8	955.4	1158.0	1402.4	1646.7	1889.0	2133.3	2367.7	2544.5	2624.0
70°	476.7	635.6	796.5	955.4	1177.9	1400.4	1622.8	1845.3	2051.9	2246.6	2322.0
72.5°	415.1	538.3	663.4	786.6	945.5	1102.4	1261.3	1418.3	1662.6	1857.2	1930.7
75°	353.6	443.0	530.4	619.7	729.0	838.2	945.5	1054.8	1227.6	1402.4	1475.9
77.5°	272.1	331.7	389.3	446.9	522.4	595.9	671.4	744.9	866.0	997.1	1034.9
80°	188.7	222.5	254.3	288.0	347.6	407.2	466.8	526.4	605.8	679.3	736.9
82.5°	117.2	139.0	158.9	178.8	226.4	274.1	319.8	367.5	399.3	403.2	460.8
85°	75.5	89.4	101.3	113.2	141.0	170.8	198.6	226.4	202.6	188.7	224.5
87.5°	29.8	37.7	43.7	49.7	47.7	45.7	43.7	41.7	35.8	31.8	39.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2
2.5°	1531.5	1537.4	1543.4	1547.4	1553.3	1555.3	1557.3	1557.3	1559.3	1561.3	1565.2
5°	1605.0	1616.9	1628.8	1638.7	1650.7	1660.6	1668.5	1678.5	1686.4	1686.4	1684.4
7.5°	1543.4	1573.2	1603.0	1632.8	1662.6	1684.4	1704.3	1726.1	1746.0	1750.0	1753.9
10°	1462.0	1493.7	1523.5	1555.3	1585.1	1618.9	1650.7	1682.4	1716.2	1722.2	1730.1
12.5°	1386.5	1424.2	1462.0	1497.7	1535.4	1559.3	1583.1	1605.0	1628.8	1644.7	1660.6
15°	1384.5	1416.3	1448.0	1477.8	1509.6	1523.5	1537.4	1549.4	1563.3	1563.3	1565.2
17.5°	1430.2	1450.0	1469.9	1487.8	1507.6	1509.6	1513.6	1515.6	1517.6	1511.6	1505.7
20°	1519.6	1527.5	1535.4	1543.4	1551.3	1537.4	1525.5	1511.6	1497.7	1481.8	1467.9
22.5°	1650.7	1632.8	1614.9	1597.0	1579.1	1555.3	1529.5	1505.7	1479.8	1460.0	1440.1
25°	1773.8	1752.0	1730.1	1708.3	1686.4	1634.8	1583.1	1529.5	1477.8	1456.0	1434.1
27.5°	1938.7	1904.9	1871.1	1837.4	1803.6	1734.1	1664.6	1595.0	1525.5	1487.8	1452.0
30°	1978.4	1940.7	1902.9	1863.2	1825.5	1757.9	1692.4	1624.8	1557.3	1513.6	1471.9
32.5°	2036.0	1992.3	1948.6	1904.9	1861.2	1795.7	1730.1	1662.6	1597.0	1557.3	1515.6
35°	2131.4	2081.7	2032.0	1980.4	1930.7	1863.2	1797.6	1730.1	1662.6	1616.9	1573.2
37.5°	2212.8	2155.2	2097.6	2040.0	1982.4	1922.8	1861.2	1801.6	1740.0	1694.4	1650.7
40°	2304.2	2240.6	2177.0	2115.5	2051.9	1996.3	1940.7	1883.1	1827.4	1791.7	1755.9
42.5°	2383.6	2306.2	2230.7	2155.2	2077.7	2040.0	2004.2	1966.5	1928.7	1910.9	1891.0
45°	2439.2	2367.7	2294.2	2222.7	2151.2	2123.4	2095.6	2067.8	2040.0	2057.9	2075.7
47.5°	2463.1	2405.5	2349.8	2294.2	2236.6	2246.6	2256.5	2264.4	2274.4	2298.2	2324.0
50°	2484.9	2453.1	2419.4	2387.6	2353.8	2391.6	2427.3	2465.1	2502.8	2552.5	2602.1
52.5°	2528.6	2510.7	2494.9	2477.0	2459.1	2524.6	2590.2	2655.7	2721.3	2776.9	2832.5
55°	2659.7	2645.8	2631.9	2616.0	2602.1	2695.5	2786.8	2880.2	2973.6	3031.2	3088.8
57.5°	2840.5	2832.5	2822.6	2814.7	2804.7	2896.1	2985.5	3074.9	3166.2	3221.9	3279.5
60°	2977.5	2979.5	2979.5	2981.5	2981.5	3051.0	3120.6	3192.1	3261.6	3309.3	3358.9
62.5°	3051.0	3047.1	3043.1	3039.1	3035.1	3092.7	3150.3	3208.0	3265.6	3301.3	3337.1
65°	2971.6	2993.4	3015.3	3037.1	3059.0	3066.9	3072.9	3080.8	3086.8	3108.6	3130.5
67.5°	2705.4	2749.1	2790.8	2834.5	2876.2	2846.4	2818.6	2788.8	2759.0	2765.0	2769.0
70°	2409.4	2459.1	2510.7	2560.4	2610.1	2540.5	2471.0	2399.5	2330.0	2306.2	2282.3
72.5°	2032.0	2075.7	2121.4	2165.1	2208.8	2123.4	2040.0	1954.6	1869.2	1827.4	1785.7
75°	1553.3	1605.0	1658.6	1710.2	1761.9	1666.5	1569.2	1473.9	1376.5	1348.7	1322.9
77.5°	1132.2	1193.8	1255.4	1316.9	1378.5	1293.1	1207.7	1120.3	1034.9	1019.0	1003.1
80°	824.3	872.0	917.7	965.4	1011.1	961.4	911.7	862.1	812.4	810.4	808.4
82.5°	556.2	597.9	637.6	679.3	719.1	699.2	681.3	661.5	641.6	661.5	683.3
85°	286.0	343.6	403.2	460.8	518.4	512.5	508.5	502.5	496.6	522.4	546.2
87.5°	57.6	107.3	156.9	204.6	254.3	242.3	230.4	216.5	204.6	212.5	218.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2
2.5°	1567.2	1569.2	1569.2	1569.2	1569.2	1569.2	1565.2	1563.3	1559.3	1555.3	1549.4
5°	1684.4	1682.4	1674.5	1666.5	1656.6	1648.7	1642.7	1634.8	1628.8	1620.9	1608.9
7.5°	1757.9	1761.9	1748.0	1736.1	1722.2	1708.3	1694.4	1680.5	1666.5	1652.6	1624.8
10°	1736.1	1742.0	1734.1	1726.1	1716.2	1708.3	1692.4	1674.5	1658.6	1640.7	1607.0
12.5°	1674.5	1690.4	1686.4	1682.4	1678.5	1674.5	1664.6	1652.6	1642.7	1630.8	1593.1
15°	1565.2	1565.2	1567.2	1569.2	1569.2	1571.2	1573.2	1575.2	1577.2	1579.1	1557.3
17.5°	1499.7	1493.7	1493.7	1493.7	1493.7	1493.7	1501.7	1511.6	1519.6	1527.5	1521.5
20°	1452.0	1438.1	1436.1	1436.1	1434.1	1432.2	1446.1	1462.0	1475.9	1489.8	1497.7
22.5°	1420.2	1400.4	1398.4	1396.4	1394.4	1392.4	1410.3	1428.2	1446.1	1463.9	1491.7
25°	1412.3	1390.4	1392.4	1394.4	1394.4	1396.4	1410.3	1424.2	1438.1	1452.0	1499.7
27.5°	1414.3	1378.5	1380.5	1382.5	1382.5	1384.5	1406.3	1426.2	1448.0	1467.9	1527.5
30°	1428.2	1386.5	1382.5	1378.5	1374.6	1370.6	1400.4	1430.2	1460.0	1489.8	1535.4
32.5°	1475.9	1436.1	1426.2	1416.3	1406.3	1396.4	1432.2	1465.9	1501.7	1535.4	1573.2
35°	1527.5	1483.8	1479.8	1475.9	1469.9	1465.9	1497.7	1531.5	1563.3	1595.0	1628.8
37.5°	1605.0	1561.3	1557.3	1551.3	1547.4	1541.4	1577.2	1610.9	1646.7	1680.5	1710.2
40°	1720.2	1684.4	1682.4	1682.4	1680.5	1678.5	1706.3	1736.1	1763.9	1791.7	1811.5
42.5°	1873.1	1855.2	1861.2	1869.2	1875.1	1881.1	1902.9	1926.8	1948.6	1970.5	1964.5
45°	2093.6	2111.5	2113.5	2115.5	2117.4	2119.4	2125.4	2133.3	2139.3	2145.3	2121.4
47.5°	2347.9	2371.7	2383.6	2395.5	2405.5	2417.4	2409.4	2399.5	2391.6	2381.6	2322.0
50°	2649.8	2699.4	2697.5	2695.5	2691.5	2689.5	2673.6	2657.7	2639.9	2624.0	2536.6
52.5°	2888.2	2943.8	2953.7	2963.6	2973.6	2983.5	2953.7	2923.9	2892.1	2862.3	2753.1
55°	3144.4	3202.0	3204.0	3206.0	3206.0	3208.0	3166.2	3124.5	3080.8	3039.1	2925.9
57.5°	3335.1	3390.7	3384.7	3380.8	3374.8	3368.8	3319.2	3269.5	3219.9	3170.2	3057.0
60°	3406.6	3454.3	3442.3	3430.4	3416.5	3404.6	3366.9	3329.1	3289.4	3251.7	3142.4
62.5°	3372.8	3408.6	3390.7	3374.8	3356.9	3339.1	3291.4	3241.7	3194.0	3144.4	3064.9
65°	3150.3	3172.2	3148.4	3126.5	3104.7	3080.8	3041.1	3001.4	2959.7	2919.9	2866.3
67.5°	2774.9	2778.9	2776.9	2774.9	2772.9	2771.0	2713.4	2655.7	2596.2	2538.6	2534.6
70°	2260.5	2236.6	2240.6	2246.6	2250.5	2254.5	2210.8	2169.1	2125.4	2081.7	2101.6
72.5°	1744.0	1702.3	1712.2	1724.2	1734.1	1744.0	1708.3	1674.5	1638.7	1603.0	1630.8
75°	1295.1	1269.3	1279.2	1291.1	1301.1	1311.0	1297.1	1283.2	1267.3	1253.4	1279.2
77.5°	987.2	971.3	973.3	973.3	975.3	975.3	977.3	981.3	983.2	985.2	1013.0
80°	804.5	802.5	800.5	798.5	794.5	792.6	812.4	832.3	852.1	872.0	885.9
82.5°	703.2	723.0	711.1	701.2	689.3	677.3	695.2	713.1	731.0	748.9	742.9
85°	572.1	595.9	574.1	552.2	528.4	506.5	522.4	536.3	552.2	566.1	558.2
87.5°	226.4	232.4	196.6	162.9	127.1	91.4	145.0	196.6	250.3	301.9	309.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981

CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2	1430.2
2.5°	1543.4	1535.4	1529.5	1527.5	1523.5	1521.5	1517.6	1513.6	1507.6	1503.7	1497.7
5°	1595.0	1583.1	1569.2	1549.4	1531.5	1511.6	1491.7	1473.9	1456.0	1436.1	1418.3
7.5°	1597.0	1569.2	1541.4	1515.6	1487.8	1462.0	1434.1	1410.3	1384.5	1358.7	1334.8
10°	1575.2	1541.4	1507.6	1473.9	1442.1	1408.3	1374.6	1346.7	1316.9	1287.2	1259.3
12.5°	1557.3	1519.6	1481.8	1442.1	1404.3	1364.6	1324.9	1297.1	1269.3	1241.5	1213.7
15°	1535.4	1511.6	1489.8	1454.0	1418.3	1382.5	1346.7	1309.0	1273.2	1235.5	1197.8
17.5°	1517.6	1511.6	1505.7	1481.8	1458.0	1432.2	1408.3	1370.6	1332.8	1293.1	1255.4
20°	1507.6	1515.6	1523.5	1511.6	1499.7	1485.8	1473.9	1446.1	1418.3	1388.5	1360.6
22.5°	1519.6	1549.4	1577.2	1579.1	1583.1	1585.1	1587.1	1561.3	1535.4	1507.6	1481.8
25°	1547.4	1595.0	1642.7	1668.5	1694.4	1722.2	1748.0	1732.1	1716.2	1700.3	1684.4
27.5°	1585.1	1644.7	1704.3	1742.0	1777.8	1815.5	1853.3	1851.3	1849.3	1845.3	1843.3
30°	1579.1	1624.8	1670.5	1716.2	1761.9	1807.6	1853.3	1877.1	1898.9	1922.8	1946.6
32.5°	1612.9	1650.7	1690.4	1738.1	1785.7	1835.4	1883.1	1932.7	1980.4	2030.0	2079.7
35°	1664.6	1698.3	1734.1	1785.7	1839.4	1891.0	1944.6	2004.2	2065.8	2127.4	2187.0
37.5°	1742.0	1771.8	1803.6	1847.3	1893.0	1936.7	1982.4	2069.8	2157.2	2246.6	2334.0
40°	1831.4	1851.3	1871.1	1912.9	1954.6	1996.3	2038.0	2147.2	2256.5	2365.7	2475.0
42.5°	1960.5	1954.6	1948.6	1982.4	2018.1	2051.9	2087.7	2187.0	2286.3	2385.6	2484.9
45°	2097.6	2073.7	2049.9	2065.8	2083.7	2099.6	2117.4	2218.8	2320.1	2423.3	2524.6
47.5°	2262.5	2202.9	2143.3	2129.4	2115.5	2099.6	2085.7	2194.9	2304.2	2415.4	2524.6
50°	2449.2	2359.8	2272.4	2236.6	2198.9	2163.1	2125.4	2214.8	2306.2	2397.5	2486.9
52.5°	2643.8	2532.6	2423.3	2367.7	2312.1	2254.5	2198.9	2274.4	2351.8	2429.3	2504.8
55°	2810.7	2697.5	2582.3	2516.7	2451.2	2385.6	2320.1	2395.5	2471.0	2546.5	2622.0
57.5°	2943.8	2830.5	2717.3	2655.7	2592.2	2530.6	2467.0	2538.6	2612.0	2685.5	2757.1
60°	3035.1	2925.9	2816.6	2757.1	2697.5	2637.9	2578.3	2663.7	2749.1	2836.5	2921.9
62.5°	2987.5	2908.0	2828.6	2802.7	2776.9	2749.1	2723.3	2804.7	2884.2	2965.6	3047.1
65°	2812.7	2759.0	2705.4	2731.2	2759.0	2784.9	2812.7	2866.3	2919.9	2975.5	3029.2
67.5°	2528.6	2524.6	2518.7	2576.3	2633.9	2693.5	2751.1	2786.8	2820.6	2856.4	2892.1
70°	2121.4	2143.3	2163.1	2262.5	2361.8	2461.1	2560.4	2574.3	2588.2	2602.1	2616.0
72.5°	1660.6	1688.4	1718.2	1849.3	1978.4	2109.5	2240.6	2232.7	2224.7	2214.8	2206.8
75°	1307.0	1332.8	1360.6	1481.8	1603.0	1724.2	1845.3	1811.5	1779.8	1746.0	1712.2
77.5°	1042.8	1070.6	1100.4	1213.7	1326.9	1442.1	1555.3	1473.9	1392.4	1311.0	1229.5
80°	897.8	911.7	923.7	1001.1	1076.6	1154.1	1231.5	1148.1	1062.7	977.3	893.9
82.5°	736.9	729.0	723.0	768.7	814.4	860.1	905.8	826.3	746.9	665.4	586.0
85°	550.2	542.3	534.3	558.2	582.0	607.8	631.7	540.3	448.9	355.6	264.2
87.5°	319.8	327.7	335.7	361.5	387.3	415.1	441.0	347.6	254.3	158.9	65.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981
 CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675981
 CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1430.2	1430.2
2.5°	1485.8	1475.9
5°	1404.3	1390.4
7.5°	1315.0	1297.1
10°	1233.5	1209.7
12.5°	1181.9	1152.1
15°	1162.0	1126.3
17.5°	1221.6	1187.8
20°	1313.0	1267.3
22.5°	1424.2	1368.6
25°	1616.9	1549.4
27.5°	1773.8	1704.3
30°	1871.1	1795.7
32.5°	1978.4	1879.1
35°	2089.6	1994.3
37.5°	2224.7	2117.4
40°	2363.8	2252.5
42.5°	2411.4	2339.9
45°	2457.1	2389.6
47.5°	2467.0	2411.4
50°	2477.0	2469.0
52.5°	2504.8	2502.8
55°	2624.0	2626.0
57.5°	2771.0	2782.9
60°	2906.0	2892.1
62.5°	2975.5	2904.0
65°	2927.9	2828.6
67.5°	2784.9	2677.6
70°	2471.0	2326.0
72.5°	2079.7	1952.6
75°	1603.0	1495.7
77.5°	1140.2	1050.8
80°	802.5	713.1
82.5°	514.5	443.0
85°	232.4	202.6
87.5°	65.5	63.6
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P675981
CATALOG NUMBER: CCW-SA-2A-735-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)