

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675986

Luminaire Tested: **CCW-SA-1A-740-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P675986
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-1A-740-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @350mA w/
SLR distribution lens
Light Source: (16) 4000K CCT, 70 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2270.4 lumens
Efficiency: N/A
Efficacy: 126.1 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1

Input Watts (W): 18
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 3.2 fc

Type IV - Short - N/A

REPORT NUMBER: P675986
CATALOG NUMBER: CCW-SA-1A-740-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	467.1	0.0	467.1
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	1803.2	0.0	1803.2
	% Fixture	79.4	0.0	79.4
Total	Lumens	2270.4	0.0	2270.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	2.5
10°-20°	118.9	5.2
20°-30°	174.0	7.7
30°-40°	245.2	10.8
40°-50°	336.9	14.8
50°-60°	459.2	20.2
60°-70°	502.6	22.1
70°-80°	290.2	12.8
80°-90°	87.0	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2270.4	100.0
0°-180°	2270.4	100.0

Coefficient of Utilization



REPORT NUMBER: P675986


CATALOG NUMBER: CCW-SA-1A-740-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	233.2	10.3			
FM	(30°-60°)	828.5	36.5			
FH	(60°-80°)	667.6	29.4			G1/1800
FVH	(80°-90°)	73.9	3.3			G1/100
BL	(0°-30°)	116.1	5.1	B1/500		
BM	(30°-60°)	212.7	9.4	B0/220		
BH	(60°-80°)	125.2	5.5	B1/500		G1/500
BVH	(80°-90°)	13.1	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0
2.5°	748.2	744.2	741.1	738.1	734.1	731.1	727.0	723.0	718.0	713.9	708.9
5°	704.9	692.8	680.7	673.7	665.6	658.6	650.5	641.4	632.4	622.3	613.2
7.5°	657.6	642.4	627.3	615.3	602.2	590.1	577.0	565.9	554.8	543.8	532.7
10°	613.2	599.1	585.0	569.9	553.8	538.7	522.6	507.5	492.4	477.3	462.2
12.5°	584.0	566.9	550.8	533.7	517.6	500.5	483.3	469.2	455.2	440.0	425.9
15°	571.0	554.8	539.7	522.6	505.5	488.4	471.3	455.2	440.0	423.9	407.8
17.5°	602.2	579.0	555.8	533.7	511.5	489.4	467.2	447.1	427.0	406.8	386.7
20°	642.4	613.2	585.0	557.9	529.7	502.5	474.3	446.1	417.9	389.7	361.5
22.5°	693.8	660.6	628.3	593.1	556.9	521.6	485.4	450.1	414.9	378.6	343.4
25°	785.4	746.2	706.9	656.5	605.2	554.8	503.5	457.2	411.9	365.5	319.2
27.5°	864.0	810.6	758.2	697.8	637.4	577.0	516.6	463.2	410.8	357.5	304.1
30°	910.3	857.9	805.6	732.1	659.6	586.1	512.5	453.1	394.7	335.3	275.9
32.5°	952.6	894.2	835.8	755.2	673.7	593.1	511.5	446.1	381.6	316.2	250.7
35°	1011.0	946.6	883.1	789.5	695.8	602.2	508.5	441.1	372.6	305.1	236.6
37.5°	1073.4	993.9	915.3	811.6	707.9	604.2	500.5	434.0	367.5	301.1	234.6
40°	1141.9	1045.2	949.6	834.8	721.0	606.2	491.4	424.9	358.5	291.0	224.6
42.5°	1186.2	1081.5	976.8	852.9	730.1	606.2	482.3	416.9	351.4	285.0	219.5
45°	1211.4	1109.7	1009.0	875.1	741.1	607.2	473.3	408.8	344.4	278.9	214.5
47.5°	1222.5	1127.8	1033.2	892.2	752.2	611.2	470.3	404.8	338.3	272.9	206.4
50°	1251.7	1168.1	1084.5	933.5	783.4	632.4	481.3	410.8	341.4	270.9	200.4
52.5°	1268.8	1197.3	1125.8	970.7	815.6	660.6	505.5	427.0	348.4	269.9	191.3
55°	1331.2	1262.7	1194.3	1029.1	863.0	697.8	531.7	445.1	358.5	270.9	184.3
57.5°	1410.8	1338.3	1266.8	1088.5	910.3	732.1	553.8	461.2	367.5	274.9	181.3
60°	1466.1	1395.7	1326.2	1136.9	946.6	757.2	566.9	470.3	373.6	275.9	179.2
62.5°	1472.2	1381.6	1291.9	1107.7	923.4	738.1	553.8	460.2	366.5	271.9	178.2
65°	1433.9	1328.2	1222.5	1046.2	870.0	693.8	517.6	432.0	346.4	259.8	174.2
67.5°	1357.4	1233.5	1109.7	948.6	787.5	626.3	465.2	391.7	319.2	245.7	172.2
70°	1179.2	1070.4	962.7	822.7	683.7	543.8	403.8	343.4	284.0	223.5	163.1
72.5°	989.9	888.1	787.5	673.7	560.9	447.1	333.3	288.0	242.7	196.4	151.0
75°	758.2	681.7	606.2	521.6	437.0	351.4	266.8	233.6	200.4	167.2	133.9
77.5°	532.7	491.4	451.1	387.7	324.2	260.8	197.4	175.2	153.1	130.9	108.8
80°	361.5	338.3	316.2	270.9	225.6	179.2	133.9	119.8	104.7	90.6	75.5
82.5°	224.6	223.5	221.5	190.3	159.1	127.9	96.7	84.6	73.5	61.4	49.3
85°	102.7	119.8	135.9	118.8	101.7	84.6	67.5	59.4	51.4	42.3	34.2
87.5°	32.2	39.3	45.3	43.3	40.3	38.3	35.2	30.2	25.2	20.1	15.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986
 CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0
2.5°	704.9	701.9	697.8	693.8	688.8	684.7	679.7	674.7	673.7	671.6	670.6
5°	607.2	601.2	594.1	588.1	582.0	575.0	568.9	561.9	556.9	550.8	545.8
7.5°	521.6	511.5	500.5	489.4	479.3	469.2	458.2	448.1	443.1	438.0	433.0
10°	453.1	443.1	434.0	423.9	416.9	410.8	403.8	396.7	390.7	384.7	378.6
12.5°	418.9	411.9	404.8	397.8	389.7	382.6	374.6	366.5	359.5	353.4	346.4
15°	397.8	387.7	376.6	366.5	355.5	345.4	334.3	323.2	315.2	308.1	300.1
17.5°	372.6	357.5	343.4	328.3	316.2	304.1	291.0	278.9	269.9	259.8	250.7
20°	344.4	327.3	309.1	292.0	277.9	264.8	250.7	236.6	226.6	215.5	205.4
22.5°	320.2	298.1	274.9	251.7	236.6	221.5	205.4	190.3	181.3	171.2	162.1
25°	294.0	269.9	244.7	219.5	204.4	188.3	173.2	157.1	150.0	144.0	136.9
27.5°	279.9	255.8	230.6	206.4	192.3	177.2	163.1	148.0	143.0	136.9	131.9
30°	251.7	228.6	204.4	180.2	170.2	161.1	151.0	141.0	139.0	138.0	135.9
32.5°	226.6	202.4	178.2	154.1	145.0	135.9	126.9	117.8	116.8	114.8	113.8
35°	213.5	190.3	166.1	143.0	134.9	125.9	117.8	108.8	106.7	103.7	101.7
37.5°	210.5	186.3	161.1	136.9	128.9	120.8	111.8	103.7	101.7	99.7	97.7
40°	202.4	179.2	157.1	133.9	125.9	117.8	108.8	100.7	98.7	96.7	94.7
42.5°	196.4	174.2	151.0	127.9	120.8	113.8	105.7	98.7	96.7	94.7	91.6
45°	191.3	168.2	144.0	120.8	115.8	110.8	104.7	99.7	97.7	94.7	92.6
47.5°	183.3	161.1	138.0	114.8	109.8	105.7	100.7	95.7	93.6	91.6	89.6
50°	177.2	154.1	130.9	107.7	103.7	99.7	95.7	91.6	91.6	92.6	92.6
52.5°	169.2	147.0	124.9	102.7	98.7	94.7	90.6	86.6	87.6	88.6	89.6
55°	162.1	141.0	118.8	96.7	92.6	88.6	83.6	79.6	80.6	81.6	82.6
57.5°	159.1	136.9	114.8	92.6	88.6	83.6	79.6	74.5	74.5	74.5	74.5
60°	157.1	133.9	111.8	88.6	83.6	79.6	74.5	69.5	68.5	68.5	67.5
62.5°	156.1	132.9	110.8	87.6	81.6	76.5	70.5	64.4	63.4	62.4	61.4
65°	152.1	130.9	108.8	86.6	79.6	73.5	66.5	59.4	58.4	58.4	57.4
67.5°	151.0	128.9	107.7	85.6	78.5	70.5	63.4	55.4	54.4	53.4	52.4
70°	143.0	123.9	103.7	83.6	75.5	68.5	60.4	52.4	51.4	49.3	48.3
72.5°	132.9	115.8	97.7	79.6	71.5	63.4	55.4	47.3	46.3	45.3	43.3
75°	117.8	101.7	85.6	69.5	62.4	56.4	49.3	42.3	41.3	40.3	38.3
77.5°	96.7	83.6	71.5	58.4	53.4	48.3	43.3	38.3	37.3	36.3	34.2
80°	68.5	60.4	53.4	45.3	42.3	38.3	35.2	31.2	31.2	30.2	30.2
82.5°	45.3	41.3	37.3	33.2	31.2	29.2	27.2	25.2	25.2	24.2	24.2
85°	32.2	30.2	27.2	25.2	24.2	22.2	21.1	19.1	19.1	19.1	19.1
87.5°	15.1	15.1	14.1	14.1	13.1	13.1	12.1	11.1	11.1	11.1	11.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986
 CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0
2.5°	668.6	665.6	662.6	658.6	655.5	651.5	646.5	642.4	637.4	637.4	636.4
5°	539.7	536.7	533.7	529.7	526.6	522.6	519.6	515.6	511.5	511.5	510.5
7.5°	428.0	421.9	415.9	408.8	402.8	398.8	394.7	389.7	385.7	382.6	379.6
10°	372.6	366.5	359.5	353.4	346.4	341.4	336.3	330.3	325.3	321.2	317.2
12.5°	339.3	332.3	325.3	318.2	311.2	304.1	298.1	291.0	284.0	278.9	273.9
15°	292.0	285.0	277.9	270.9	263.8	255.8	247.7	238.7	230.6	226.6	223.5
17.5°	240.7	233.6	225.6	218.5	210.5	204.4	198.4	192.3	186.3	182.3	179.2
20°	194.3	186.3	178.2	170.2	162.1	158.1	154.1	150.0	146.0	143.0	141.0
22.5°	152.1	147.0	143.0	138.0	132.9	129.9	127.9	124.9	121.8	121.8	121.8
25°	129.9	126.9	124.9	121.8	118.8	117.8	116.8	114.8	113.8	112.8	112.8
27.5°	125.9	122.9	119.8	116.8	113.8	112.8	111.8	109.8	108.8	108.8	108.8
30°	133.9	132.9	131.9	130.9	129.9	127.9	124.9	122.9	119.8	117.8	115.8
32.5°	111.8	110.8	110.8	109.8	108.8	110.8	111.8	113.8	114.8	115.8	116.8
35°	98.7	96.7	94.7	92.6	90.6	89.6	88.6	87.6	86.6	86.6	85.6
37.5°	95.7	93.6	91.6	89.6	87.6	86.6	85.6	84.6	83.6	83.6	82.6
40°	92.6	90.6	89.6	87.6	85.6	84.6	83.6	81.6	80.6	79.6	79.6
42.5°	89.6	88.6	86.6	85.6	83.6	82.6	81.6	79.6	78.5	77.5	76.5
45°	89.6	87.6	85.6	83.6	81.6	80.6	78.5	77.5	75.5	75.5	74.5
47.5°	87.6	85.6	83.6	81.6	79.6	78.5	76.5	75.5	73.5	72.5	71.5
50°	92.6	89.6	85.6	82.6	78.5	77.5	75.5	74.5	72.5	71.5	70.5
52.5°	90.6	87.6	83.6	80.6	76.5	74.5	73.5	71.5	69.5	68.5	67.5
55°	83.6	80.6	78.5	75.5	72.5	70.5	68.5	66.5	64.4	63.4	63.4
57.5°	74.5	73.5	72.5	71.5	70.5	68.5	66.5	63.4	61.4	60.4	59.4
60°	66.5	67.5	68.5	69.5	70.5	67.5	64.4	61.4	58.4	57.4	56.4
62.5°	60.4	62.4	64.4	65.5	67.5	64.4	61.4	58.4	55.4	54.4	53.4
65°	56.4	57.4	57.4	58.4	58.4	56.4	55.4	53.4	51.4	50.3	50.3
67.5°	51.4	51.4	51.4	50.3	50.3	49.3	49.3	48.3	47.3	46.3	46.3
70°	46.3	46.3	46.3	45.3	45.3	44.3	44.3	43.3	42.3	42.3	41.3
72.5°	42.3	42.3	41.3	41.3	40.3	40.3	40.3	39.3	39.3	38.3	38.3
75°	37.3	37.3	36.3	36.3	35.2	35.2	35.2	34.2	34.2	34.2	33.2
77.5°	33.2	33.2	32.2	32.2	31.2	31.2	31.2	30.2	30.2	29.2	29.2
80°	29.2	29.2	28.2	28.2	27.2	27.2	26.2	26.2	25.2	25.2	24.2
82.5°	23.2	23.2	23.2	23.2	23.2	22.2	22.2	21.1	20.1	20.1	19.1
85°	19.1	19.1	19.1	18.1	18.1	18.1	17.1	17.1	16.1	15.1	15.1
87.5°	11.1	11.1	11.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1	9.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0
2.5°	636.4	635.4	631.4	627.3	631.4	635.4	635.4	635.4	634.4	634.4	634.4
5°	510.5	509.5	507.5	505.5	505.5	504.5	506.5	508.5	510.5	512.5	514.6
7.5°	375.6	372.6	369.6	366.5	368.6	369.6	372.6	374.6	377.6	379.6	384.7
10°	313.2	309.1	306.1	303.1	301.1	299.1	297.1	296.0	294.0	292.0	294.0
12.5°	267.9	262.8	257.8	251.7	250.7	249.7	247.7	245.7	243.7	241.7	240.7
15°	219.5	215.5	213.5	210.5	206.4	202.4	200.4	199.4	197.4	195.4	194.3
17.5°	175.2	171.2	168.2	165.1	164.1	162.1	162.1	162.1	162.1	162.1	162.1
20°	138.0	134.9	134.9	133.9	133.9	132.9	133.9	134.9	134.9	135.9	136.9
22.5°	120.8	120.8	119.8	118.8	119.8	119.8	120.8	121.8	122.9	123.9	124.9
25°	111.8	110.8	111.8	112.8	112.8	112.8	113.8	113.8	114.8	114.8	114.8
27.5°	107.7	107.7	108.8	108.8	109.8	109.8	109.8	108.8	108.8	107.7	107.7
30°	113.8	111.8	111.8	111.8	110.8	109.8	108.8	108.8	107.7	106.7	105.7
32.5°	117.8	118.8	117.8	115.8	114.8	112.8	111.8	109.8	108.8	106.7	104.7
35°	85.6	84.6	86.6	87.6	88.6	89.6	90.6	91.6	91.6	92.6	92.6
37.5°	82.6	81.6	81.6	80.6	80.6	80.6	80.6	80.6	79.6	79.6	80.6
40°	78.5	77.5	77.5	76.5	76.5	75.5	75.5	75.5	75.5	75.5	75.5
42.5°	75.5	74.5	74.5	74.5	74.5	73.5	73.5	72.5	72.5	71.5	71.5
45°	74.5	73.5	72.5	71.5	71.5	70.5	70.5	70.5	69.5	69.5	69.5
47.5°	70.5	69.5	69.5	68.5	68.5	67.5	67.5	67.5	66.5	66.5	66.5
50°	68.5	67.5	67.5	66.5	66.5	65.5	65.5	65.5	64.4	64.4	64.4
52.5°	65.5	64.4	64.4	64.4	63.4	62.4	62.4	62.4	61.4	61.4	61.4
55°	62.4	61.4	61.4	61.4	60.4	59.4	59.4	59.4	58.4	58.4	58.4
57.5°	58.4	57.4	57.4	56.4	56.4	56.4	56.4	56.4	55.4	55.4	55.4
60°	55.4	54.4	54.4	53.4	53.4	52.4	52.4	52.4	52.4	52.4	52.4
62.5°	52.4	51.4	50.3	49.3	50.3	50.3	50.3	50.3	49.3	49.3	49.3
65°	49.3	48.3	47.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3
67.5°	45.3	44.3	43.3	42.3	43.3	43.3	43.3	43.3	43.3	43.3	43.3
70°	41.3	40.3	40.3	39.3	39.3	38.3	38.3	39.3	39.3	39.3	39.3
72.5°	37.3	36.3	36.3	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2
75°	33.2	32.2	32.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2
77.5°	28.2	27.2	27.2	27.2	27.2	27.2	27.2	28.2	28.2	28.2	28.2
80°	24.2	23.2	23.2	23.2	23.2	23.2	23.2	23.2	23.2	23.2	23.2
82.5°	19.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1
85°	14.1	13.1	13.1	13.1	14.1	14.1	14.1	14.1	14.1	14.1	14.1
87.5°	9.1	8.1	8.1	8.1	9.1	9.1	9.1	9.1	8.1	8.1	8.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0
2.5°	634.4	634.4	634.4	633.4	632.4	631.4	630.4	633.4	635.4	638.4	640.4
5°	515.6	517.6	518.6	521.6	524.6	527.7	530.7	532.7	534.7	535.7	537.7
7.5°	388.7	393.7	397.8	401.8	405.8	408.8	412.9	415.9	418.9	421.9	424.9
10°	295.0	297.1	298.1	302.1	305.1	309.1	312.2	315.2	318.2	320.2	323.2
12.5°	239.7	237.6	236.6	236.6	236.6	236.6	236.6	238.7	240.7	242.7	244.7
15°	193.3	192.3	191.3	190.3	189.3	187.3	186.3	188.3	190.3	192.3	194.3
17.5°	162.1	162.1	162.1	161.1	160.1	159.1	158.1	159.1	160.1	160.1	161.1
20°	139.0	140.0	141.0	142.0	142.0	143.0	143.0	144.0	145.0	145.0	146.0
22.5°	124.9	125.9	125.9	125.9	126.9	126.9	126.9	127.9	128.9	129.9	130.9
25°	113.8	113.8	112.8	112.8	113.8	113.8	113.8	113.8	114.8	114.8	114.8
27.5°	107.7	106.7	106.7	106.7	106.7	105.7	105.7	105.7	105.7	105.7	105.7
30°	104.7	103.7	102.7	101.7	101.7	100.7	99.7	99.7	99.7	99.7	99.7
32.5°	103.7	101.7	99.7	98.7	98.7	97.7	96.7	95.7	95.7	94.7	93.6
35°	92.6	91.6	91.6	90.6	89.6	88.6	87.6	87.6	87.6	86.6	86.6
37.5°	80.6	81.6	81.6	81.6	82.6	82.6	82.6	82.6	83.6	83.6	83.6
40°	75.5	75.5	75.5	76.5	77.5	77.5	78.5	78.5	79.6	79.6	79.6
42.5°	71.5	70.5	70.5	71.5	71.5	72.5	72.5	73.5	74.5	74.5	75.5
45°	69.5	68.5	68.5	68.5	68.5	67.5	67.5	68.5	69.5	70.5	71.5
47.5°	65.5	65.5	64.4	64.4	64.4	64.4	64.4	64.4	65.5	65.5	65.5
50°	63.4	63.4	62.4	62.4	62.4	62.4	62.4	62.4	62.4	62.4	62.4
52.5°	61.4	60.4	60.4	60.4	60.4	59.4	59.4	59.4	59.4	59.4	59.4
55°	58.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	58.4	58.4	58.4
57.5°	55.4	54.4	54.4	54.4	55.4	55.4	55.4	55.4	56.4	56.4	56.4
60°	52.4	52.4	52.4	52.4	52.4	52.4	52.4	53.4	53.4	54.4	54.4
62.5°	49.3	49.3	49.3	49.3	50.3	50.3	50.3	50.3	51.4	51.4	51.4
65°	46.3	46.3	46.3	46.3	47.3	47.3	47.3	47.3	47.3	47.3	47.3
67.5°	43.3	43.3	43.3	43.3	43.3	43.3	43.3	44.3	44.3	45.3	45.3
70°	39.3	38.3	38.3	39.3	39.3	40.3	40.3	41.3	41.3	42.3	42.3
72.5°	35.2	35.2	35.2	35.2	35.2	35.2	35.2	36.3	37.3	37.3	38.3
75°	31.2	31.2	31.2	31.2	32.2	32.2	32.2	33.2	33.2	34.2	34.2
77.5°	28.2	27.2	27.2	27.2	28.2	28.2	28.2	29.2	29.2	30.2	30.2
80°	23.2	23.2	23.2	23.2	24.2	24.2	24.2	24.2	25.2	25.2	25.2
82.5°	19.1	19.1	19.1	19.1	19.1	19.1	19.1	19.1	20.1	20.1	20.1
85°	14.1	14.1	14.1	14.1	15.1	15.1	15.1	15.1	15.1	15.1	15.1
87.5°	9.1	9.1	9.1	9.1	9.1	9.1	9.1	9.1	10.1	10.1	10.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0
2.5°	640.4	640.4	640.4	640.4	642.4	643.5	645.5	646.5	645.5	644.5	642.4
5°	538.7	539.7	539.7	540.7	540.7	540.7	540.7	540.7	542.8	544.8	546.8
7.5°	425.9	427.0	428.0	429.0	429.0	429.0	428.0	428.0	429.0	429.0	430.0
10°	326.3	330.3	333.3	336.3	334.3	331.3	329.3	326.3	326.3	326.3	325.3
12.5°	246.7	247.7	249.7	250.7	249.7	249.7	248.7	247.7	248.7	250.7	251.7
15°	195.4	195.4	196.4	196.4	197.4	198.4	198.4	199.4	201.4	202.4	204.4
17.5°	162.1	163.1	163.1	164.1	164.1	165.1	165.1	165.1	167.2	169.2	172.2
20°	146.0	146.0	146.0	146.0	146.0	145.0	145.0	144.0	145.0	147.0	148.0
22.5°	130.9	131.9	131.9	131.9	130.9	129.9	127.9	126.9	126.9	127.9	127.9
25°	114.8	113.8	113.8	112.8	112.8	113.8	113.8	113.8	114.8	114.8	115.8
27.5°	105.7	104.7	104.7	103.7	103.7	104.7	104.7	104.7	104.7	104.7	104.7
30°	98.7	98.7	97.7	96.7	97.7	97.7	98.7	98.7	99.7	99.7	100.7
32.5°	93.6	92.6	92.6	91.6	92.6	92.6	93.6	93.6	94.7	95.7	95.7
35°	86.6	86.6	86.6	86.6	86.6	86.6	85.6	85.6	85.6	85.6	85.6
37.5°	82.6	82.6	81.6	80.6	80.6	80.6	80.6	80.6	79.6	78.5	77.5
40°	79.6	78.5	78.5	77.5	76.5	76.5	75.5	74.5	74.5	73.5	73.5
42.5°	75.5	74.5	74.5	73.5	72.5	72.5	71.5	70.5	70.5	70.5	69.5
45°	70.5	70.5	69.5	68.5	68.5	68.5	67.5	67.5	67.5	67.5	66.5
47.5°	65.5	65.5	64.4	64.4	64.4	64.4	63.4	63.4	63.4	63.4	63.4
50°	62.4	62.4	62.4	62.4	62.4	62.4	61.4	61.4	61.4	61.4	61.4
52.5°	59.4	59.4	59.4	59.4	59.4	59.4	59.4	59.4	59.4	59.4	59.4
55°	58.4	58.4	58.4	58.4	58.4	58.4	57.4	57.4	57.4	58.4	58.4
57.5°	56.4	56.4	55.4	55.4	55.4	55.4	55.4	55.4	55.4	55.4	55.4
60°	54.4	54.4	54.4	54.4	54.4	54.4	54.4	54.4	54.4	54.4	54.4
62.5°	51.4	51.4	51.4	51.4	51.4	52.4	52.4	52.4	52.4	52.4	51.4
65°	47.3	48.3	48.3	48.3	48.3	48.3	48.3	48.3	48.3	48.3	48.3
67.5°	45.3	45.3	45.3	45.3	45.3	45.3	45.3	45.3	45.3	45.3	45.3
70°	42.3	42.3	41.3	41.3	41.3	42.3	42.3	42.3	42.3	42.3	42.3
72.5°	38.3	38.3	38.3	38.3	38.3	38.3	38.3	38.3	38.3	39.3	39.3
75°	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2
77.5°	30.2	30.2	29.2	29.2	29.2	30.2	30.2	30.2	30.2	31.2	31.2
80°	25.2	25.2	25.2	25.2	25.2	25.2	25.2	25.2	25.2	26.2	26.2
82.5°	20.1	20.1	20.1	20.1	20.1	20.1	20.1	20.1	20.1	21.1	21.1
85°	15.1	16.1	16.1	16.1	16.1	16.1	16.1	16.1	16.1	17.1	17.1
87.5°	10.1	10.1	10.1	10.1	10.1	10.1	9.1	9.1	9.1	9.1	8.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986
 CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0
2.5°	641.4	642.4	643.5	643.5	644.5	645.5	645.5	649.5	653.5	655.5	657.6
5°	548.8	547.8	547.8	546.8	545.8	548.8	551.8	557.9	563.9	564.9	566.9
7.5°	430.0	431.0	432.0	432.0	433.0	430.0	425.9	427.0	428.0	433.0	437.0
10°	325.3	326.3	327.3	327.3	328.3	327.3	325.3	328.3	331.3	335.3	340.4
12.5°	252.7	255.8	258.8	260.8	263.8	265.8	266.8	270.9	273.9	278.9	284.0
15°	206.4	208.4	210.5	212.5	214.5	216.5	218.5	222.5	226.6	232.6	238.7
17.5°	174.2	174.2	175.2	175.2	175.2	177.2	179.2	181.3	182.3	188.3	194.3
20°	149.0	148.0	147.0	146.0	145.0	147.0	148.0	149.0	150.0	154.1	157.1
22.5°	127.9	127.9	128.9	128.9	128.9	127.9	125.9	126.9	126.9	128.9	131.9
25°	115.8	115.8	115.8	114.8	114.8	115.8	116.8	116.8	115.8	116.8	117.8
27.5°	104.7	105.7	105.7	106.7	106.7	107.7	107.7	107.7	107.7	108.8	109.8
30°	100.7	100.7	101.7	101.7	101.7	102.7	103.7	103.7	103.7	104.7	106.7
32.5°	96.7	97.7	98.7	99.7	100.7	101.7	101.7	102.7	102.7	103.7	104.7
35°	85.6	84.6	84.6	83.6	82.6	82.6	82.6	82.6	81.6	82.6	82.6
37.5°	76.5	76.5	76.5	75.5	75.5	76.5	76.5	76.5	76.5	77.5	77.5
40°	72.5	72.5	72.5	72.5	72.5	72.5	72.5	73.5	73.5	74.5	75.5
42.5°	69.5	69.5	69.5	69.5	69.5	70.5	70.5	70.5	70.5	71.5	71.5
45°	66.5	66.5	66.5	66.5	66.5	66.5	66.5	67.5	67.5	68.5	69.5
47.5°	63.4	63.4	63.4	63.4	63.4	64.4	65.5	65.5	65.5	66.5	66.5
50°	61.4	61.4	61.4	61.4	61.4	62.4	62.4	63.4	63.4	64.4	65.5
52.5°	59.4	59.4	59.4	59.4	59.4	60.4	60.4	61.4	61.4	62.4	63.4
55°	58.4	58.4	58.4	57.4	57.4	58.4	58.4	59.4	59.4	60.4	60.4
57.5°	55.4	55.4	55.4	55.4	55.4	55.4	55.4	56.4	56.4	57.4	58.4
60°	54.4	54.4	53.4	53.4	52.4	53.4	53.4	54.4	54.4	55.4	55.4
62.5°	51.4	51.4	51.4	50.3	50.3	51.4	51.4	51.4	51.4	52.4	53.4
65°	48.3	48.3	48.3	47.3	47.3	48.3	48.3	48.3	48.3	49.3	50.3
67.5°	45.3	45.3	45.3	44.3	44.3	44.3	44.3	45.3	45.3	46.3	47.3
70°	42.3	42.3	42.3	41.3	41.3	41.3	40.3	41.3	42.3	43.3	43.3
72.5°	39.3	39.3	39.3	38.3	38.3	38.3	37.3	38.3	38.3	39.3	39.3
75°	34.2	34.2	34.2	34.2	34.2	34.2	33.2	33.2	33.2	34.2	34.2
77.5°	31.2	31.2	31.2	30.2	30.2	30.2	29.2	29.2	29.2	30.2	30.2
80°	26.2	26.2	26.2	25.2	25.2	25.2	24.2	24.2	24.2	25.2	25.2
82.5°	21.1	21.1	21.1	20.1	20.1	20.1	19.1	19.1	19.1	20.1	20.1
85°	17.1	17.1	17.1	17.1	17.1	17.1	16.1	16.1	16.1	17.1	18.1
87.5°	8.1	8.1	9.1	9.1	9.1	9.1	8.1	8.1	7.0	7.0	8.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986
 CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0
2.5°	659.6	661.6	666.6	670.6	675.7	679.7	682.7	686.8	689.8	692.8	694.8
5°	567.9	568.9	574.0	579.0	583.0	588.1	595.1	602.2	609.2	616.3	621.3
7.5°	442.1	446.1	452.1	459.2	465.2	471.3	478.3	486.4	493.4	500.5	507.5
10°	344.4	348.4	354.5	360.5	365.5	371.6	379.6	387.7	395.7	403.8	411.9
12.5°	289.0	294.0	301.1	308.1	314.2	321.2	331.3	340.4	350.4	359.5	369.6
15°	243.7	249.7	258.8	268.9	277.9	287.0	297.1	307.1	316.2	326.3	336.3
17.5°	200.4	206.4	214.5	223.5	231.6	239.7	251.7	262.8	274.9	286.0	297.1
20°	161.1	164.1	172.2	180.2	188.3	196.4	205.4	214.5	223.5	232.6	246.7
22.5°	133.9	135.9	140.0	143.0	147.0	150.0	159.1	168.2	176.2	185.3	198.4
25°	117.8	118.8	121.8	123.9	126.9	128.9	134.9	140.0	146.0	151.0	163.1
27.5°	109.8	110.8	111.8	112.8	113.8	114.8	118.8	122.9	125.9	129.9	141.0
30°	107.7	108.8	111.8	113.8	116.8	118.8	120.8	122.9	124.9	126.9	133.9
32.5°	105.7	106.7	106.7	105.7	105.7	104.7	106.7	107.7	109.8	110.8	116.8
35°	83.6	83.6	84.6	85.6	86.6	87.6	90.6	92.6	95.7	97.7	102.7
37.5°	78.5	78.5	79.6	81.6	82.6	83.6	85.6	87.6	89.6	91.6	96.7
40°	75.5	76.5	77.5	78.5	79.6	80.6	82.6	83.6	85.6	86.6	90.6
42.5°	72.5	72.5	73.5	75.5	76.5	77.5	79.6	80.6	82.6	83.6	87.6
45°	70.5	71.5	72.5	73.5	73.5	74.5	76.5	78.5	79.6	81.6	85.6
47.5°	67.5	67.5	69.5	70.5	72.5	73.5	75.5	76.5	78.5	79.6	83.6
50°	65.5	66.5	68.5	69.5	71.5	72.5	75.5	77.5	80.6	82.6	84.6
52.5°	63.4	64.4	66.5	67.5	69.5	70.5	74.5	78.5	81.6	85.6	85.6
55°	61.4	61.4	63.4	66.5	68.5	70.5	72.5	75.5	77.5	79.6	79.6
57.5°	58.4	59.4	61.4	64.4	66.5	68.5	70.5	72.5	73.5	75.5	74.5
60°	56.4	56.4	59.4	62.4	65.5	68.5	68.5	68.5	67.5	67.5	67.5
62.5°	53.4	54.4	58.4	63.4	67.5	71.5	68.5	65.5	62.4	59.4	60.4
65°	51.4	52.4	54.4	57.4	59.4	61.4	59.4	58.4	56.4	54.4	55.4
67.5°	47.3	48.3	49.3	49.3	50.3	50.3	50.3	50.3	50.3	50.3	51.4
70°	44.3	44.3	44.3	45.3	45.3	45.3	45.3	45.3	45.3	45.3	46.3
72.5°	40.3	40.3	40.3	40.3	40.3	40.3	40.3	40.3	40.3	40.3	41.3
75°	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2	36.3
77.5°	31.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2	30.2	30.2	31.2
80°	26.2	26.2	26.2	26.2	25.2	25.2	25.2	25.2	25.2	25.2	26.2
82.5°	21.1	21.1	21.1	21.1	20.1	20.1	20.1	20.1	19.1	19.1	20.1
85°	19.1	20.1	20.1	21.1	21.1	21.1	20.1	19.1	18.1	17.1	17.1
87.5°	8.1	8.1	8.1	8.1	7.0	7.0	7.0	7.0	7.0	7.0	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0
2.5°	697.8	699.8	701.9	704.9	708.9	711.9	714.9	721.0	728.0	734.1	740.1
5°	626.3	631.4	636.4	642.4	648.5	653.5	659.6	671.6	683.7	694.8	706.9
7.5°	513.6	520.6	526.6	536.7	545.8	555.8	564.9	580.0	594.1	609.2	623.3
10°	419.9	428.0	436.0	449.1	463.2	476.3	489.4	501.5	514.6	526.6	538.7
12.5°	379.6	388.7	398.8	406.8	415.9	423.9	432.0	446.1	460.2	474.3	488.4
15°	346.4	356.5	366.5	376.6	385.7	395.7	404.8	416.9	430.0	442.1	454.1
17.5°	308.1	318.2	329.3	340.4	351.4	362.5	373.6	390.7	407.8	423.9	441.1
20°	259.8	273.9	287.0	302.1	317.2	332.3	347.4	365.5	383.7	400.8	418.9
22.5°	211.5	224.6	237.6	255.8	273.9	291.0	309.1	333.3	356.5	380.6	403.8
25°	176.2	188.3	200.4	220.5	239.7	259.8	278.9	308.1	336.3	365.5	393.7
27.5°	152.1	163.1	174.2	195.4	216.5	236.6	257.8	290.0	321.2	353.4	384.7
30°	141.0	148.0	155.1	175.2	195.4	214.5	234.6	265.8	297.1	328.3	359.5
32.5°	122.9	128.9	134.9	153.1	171.2	188.3	206.4	238.7	269.9	302.1	333.3
35°	108.8	113.8	118.8	135.9	152.1	169.2	185.3	217.5	249.7	282.0	314.2
37.5°	100.7	105.7	109.8	124.9	141.0	156.1	171.2	203.4	234.6	266.8	298.1
40°	94.7	97.7	101.7	116.8	130.9	146.0	160.1	189.3	219.5	248.7	277.9
42.5°	90.6	94.7	97.7	110.8	124.9	138.0	151.0	179.2	207.4	234.6	262.8
45°	89.6	93.6	97.7	108.8	119.8	129.9	141.0	168.2	195.4	222.5	249.7
47.5°	87.6	90.6	94.7	103.7	111.8	120.8	128.9	156.1	183.3	209.4	236.6
50°	86.6	87.6	89.6	97.7	105.7	113.8	121.8	149.0	176.2	203.4	230.6
52.5°	85.6	85.6	85.6	92.6	99.7	105.7	112.8	140.0	168.2	195.4	222.5
55°	79.6	78.5	78.5	85.6	91.6	98.7	104.7	131.9	159.1	185.3	212.5
57.5°	73.5	72.5	71.5	77.5	83.6	89.6	95.7	122.9	151.0	178.2	205.4
60°	67.5	66.5	66.5	72.5	77.5	83.6	88.6	116.8	144.0	172.2	199.4
62.5°	60.4	61.4	61.4	66.5	72.5	77.5	82.6	110.8	140.0	168.2	196.4
65°	55.4	56.4	56.4	62.4	68.5	74.5	80.6	107.7	135.9	163.1	190.3
67.5°	51.4	52.4	52.4	59.4	65.5	72.5	78.5	102.7	127.9	152.1	176.2
70°	47.3	47.3	48.3	55.4	62.4	69.5	76.5	97.7	118.8	139.0	160.1
72.5°	42.3	43.3	44.3	51.4	57.4	64.4	70.5	89.6	108.8	127.9	147.0
75°	37.3	38.3	39.3	45.3	51.4	57.4	63.4	81.6	98.7	116.8	133.9
77.5°	33.2	34.2	35.2	40.3	45.3	50.3	55.4	68.5	82.6	95.7	108.8
80°	27.2	27.2	28.2	32.2	36.3	39.3	43.3	52.4	61.4	69.5	78.5
82.5°	20.1	21.1	21.1	24.2	26.2	29.2	31.2	36.3	40.3	45.3	49.3
85°	17.1	16.1	16.1	18.1	19.1	21.1	22.2	25.2	27.2	30.2	32.2
87.5°	7.0	6.0	6.0	7.0	9.1	10.1	11.1	11.1	12.1	12.1	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986
 CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0
2.5°	743.1	745.2	748.2	750.2	755.2	759.3	764.3	768.3	771.3	776.4	774.4
5°	716.0	725.0	734.1	743.1	750.2	757.2	763.3	770.3	778.4	793.5	797.5
7.5°	635.4	647.5	658.6	670.6	684.7	698.8	712.9	727.0	740.1	759.3	771.3
10°	555.8	573.0	589.1	606.2	619.3	632.4	644.5	657.6	675.7	694.8	717.0
12.5°	505.5	522.6	539.7	556.9	576.0	594.1	613.2	631.4	648.5	663.6	688.8
15°	472.3	491.4	509.5	527.7	550.8	573.0	596.1	618.3	643.5	663.6	680.7
17.5°	464.2	487.4	509.5	532.7	556.9	581.0	605.2	629.4	654.5	684.7	706.9
20°	450.1	481.3	512.5	543.8	575.0	605.2	636.4	666.6	699.8	736.1	746.2
22.5°	442.1	479.3	517.6	554.8	597.1	640.4	682.7	725.0	760.3	787.5	817.7
25°	441.1	487.4	534.7	581.0	634.4	686.8	740.1	792.5	837.8	865.0	889.2
27.5°	440.0	496.4	551.8	607.2	672.7	737.1	802.6	867.0	909.3	948.6	968.7
30°	428.0	495.4	563.9	631.4	704.9	778.4	851.9	925.4	968.7	995.9	1006.0
32.5°	412.9	492.4	572.0	651.5	735.1	818.7	901.2	984.8	1019.1	1042.2	1034.2
35°	400.8	488.4	575.0	661.6	750.2	839.8	928.4	1017.0	1066.4	1098.6	1085.5
37.5°	389.7	481.3	573.0	664.6	768.3	872.0	975.8	1079.5	1126.8	1161.0	1145.9
40°	376.6	474.3	573.0	670.6	789.5	907.3	1026.1	1143.9	1205.3	1234.5	1211.4
42.5°	365.5	467.2	569.9	671.6	798.5	925.4	1052.3	1179.2	1247.6	1288.9	1259.7
45°	351.4	453.1	553.8	655.5	795.5	935.5	1074.4	1214.4	1294.0	1326.2	1285.9
47.5°	336.3	437.0	536.7	636.4	785.4	934.5	1083.5	1232.5	1306.0	1344.3	1307.0
50°	331.3	432.0	531.7	632.4	793.5	955.6	1116.7	1277.8	1331.2	1362.4	1313.1
52.5°	330.3	437.0	544.8	651.5	813.6	974.7	1136.9	1298.0	1341.3	1374.5	1330.2
55°	327.3	443.1	557.9	672.7	841.8	1012.0	1181.2	1350.3	1393.6	1417.8	1384.6
57.5°	330.3	455.2	579.0	703.9	878.1	1052.3	1226.5	1400.7	1453.1	1470.2	1463.1
60°	332.3	465.2	597.1	730.1	900.2	1070.4	1240.6	1410.8	1465.1	1507.4	1515.5
62.5°	327.3	458.2	588.1	719.0	873.0	1027.1	1181.2	1335.2	1424.9	1487.3	1523.5
65°	312.2	433.0	554.8	675.7	817.7	960.6	1102.6	1244.6	1339.3	1431.9	1461.1
67.5°	278.9	381.6	484.4	587.1	710.9	834.8	957.6	1081.5	1200.3	1289.9	1330.2
70°	241.7	322.2	403.8	484.4	597.1	709.9	822.7	935.5	1040.2	1138.9	1177.1
72.5°	210.5	272.9	336.3	398.8	479.3	558.9	639.4	719.0	842.8	941.5	978.8
75°	179.2	224.6	268.9	314.2	369.6	424.9	479.3	534.7	622.3	710.9	748.2
77.5°	138.0	168.2	197.4	226.6	264.8	302.1	340.4	377.6	439.0	505.5	524.6
80°	95.7	112.8	128.9	146.0	176.2	206.4	236.6	266.8	307.1	344.4	373.6
82.5°	59.4	70.5	80.6	90.6	114.8	139.0	162.1	186.3	202.4	204.4	233.6
85°	38.3	45.3	51.4	57.4	71.5	86.6	100.7	114.8	102.7	95.7	113.8
87.5°	15.1	19.1	22.2	25.2	24.2	23.2	22.2	21.1	18.1	16.1	20.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986
 CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0
2.5°	776.4	779.4	782.4	784.4	787.5	788.5	789.5	789.5	790.5	791.5	793.5
5°	813.6	819.7	825.7	830.7	836.8	841.8	845.9	850.9	854.9	854.9	853.9
7.5°	782.4	797.5	812.6	827.7	842.8	853.9	864.0	875.1	885.1	887.1	889.2
10°	741.1	757.2	772.3	788.5	803.6	820.7	836.8	852.9	870.0	873.0	877.1
12.5°	702.9	722.0	741.1	759.3	778.4	790.5	802.6	813.6	825.7	833.8	841.8
15°	701.9	718.0	734.1	749.2	765.3	772.3	779.4	785.4	792.5	792.5	793.5
17.5°	725.0	735.1	745.2	754.2	764.3	765.3	767.3	768.3	769.3	766.3	763.3
20°	770.3	774.4	778.4	782.4	786.4	779.4	773.4	766.3	759.3	751.2	744.2
22.5°	836.8	827.7	818.7	809.6	800.5	788.5	775.4	763.3	750.2	740.1	730.1
25°	899.2	888.1	877.1	866.0	854.9	828.7	802.6	775.4	749.2	738.1	727.0
27.5°	982.8	965.7	948.6	931.4	914.3	879.1	843.8	808.6	773.4	754.2	736.1
30°	1002.9	983.8	964.7	944.5	925.4	891.2	857.9	823.7	789.5	767.3	746.2
32.5°	1032.1	1010.0	987.8	965.7	943.5	910.3	877.1	842.8	809.6	789.5	768.3
35°	1080.5	1055.3	1030.1	1003.9	978.8	944.5	911.3	877.1	842.8	819.7	797.5
37.5°	1121.8	1092.6	1063.4	1034.2	1005.0	974.7	943.5	913.3	882.1	858.9	836.8
40°	1168.1	1135.9	1103.6	1072.4	1040.2	1012.0	983.8	954.6	926.4	908.3	890.2
42.5°	1208.4	1169.1	1130.8	1092.6	1053.3	1034.2	1016.0	996.9	977.8	968.7	958.6
45°	1236.6	1200.3	1163.0	1126.8	1090.5	1076.5	1062.4	1048.3	1034.2	1043.2	1052.3
47.5°	1248.6	1219.4	1191.2	1163.0	1133.8	1138.9	1143.9	1147.9	1153.0	1165.1	1178.2
50°	1259.7	1243.6	1226.5	1210.4	1193.3	1212.4	1230.5	1249.6	1268.8	1294.0	1319.1
52.5°	1281.9	1272.8	1264.8	1255.7	1246.6	1279.9	1313.1	1346.3	1379.5	1407.7	1435.9
55°	1348.3	1341.3	1334.2	1326.2	1319.1	1366.5	1412.8	1460.1	1507.4	1536.6	1565.8
57.5°	1440.0	1435.9	1430.9	1426.9	1421.8	1468.2	1513.5	1558.8	1605.1	1633.3	1662.5
60°	1509.4	1510.5	1510.5	1511.5	1511.5	1546.7	1581.9	1618.2	1653.4	1677.6	1702.8
62.5°	1546.7	1544.7	1542.7	1540.7	1538.6	1567.9	1597.1	1626.3	1655.5	1673.6	1691.7
65°	1506.4	1517.5	1528.6	1539.7	1550.7	1554.8	1557.8	1561.8	1564.8	1575.9	1587.0
67.5°	1371.5	1393.6	1414.8	1436.9	1458.1	1443.0	1428.9	1413.8	1398.7	1401.7	1403.7
70°	1221.5	1246.6	1272.8	1298.0	1323.2	1287.9	1252.7	1216.4	1181.2	1169.1	1157.0
72.5°	1030.1	1052.3	1075.4	1097.6	1119.8	1076.5	1034.2	990.9	947.6	926.4	905.3
75°	787.5	813.6	840.8	867.0	893.2	844.8	795.5	747.2	697.8	683.7	670.6
77.5°	574.0	605.2	636.4	667.6	698.8	655.5	612.2	567.9	524.6	516.6	508.5
80°	417.9	442.1	465.2	489.4	512.5	487.4	462.2	437.0	411.9	410.8	409.8
82.5°	282.0	303.1	323.2	344.4	364.5	354.5	345.4	335.3	325.3	335.3	346.4
85°	145.0	174.2	204.4	233.6	262.8	259.8	257.8	254.8	251.7	264.8	276.9
87.5°	29.2	54.4	79.6	103.7	128.9	122.9	116.8	109.8	103.7	107.7	110.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986
 CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0
2.5°	794.5	795.5	795.5	795.5	795.5	795.5	793.5	792.5	790.5	788.5	785.4
5°	853.9	852.9	848.9	844.8	839.8	835.8	832.8	828.7	825.7	821.7	815.6
7.5°	891.2	893.2	886.1	880.1	873.0	866.0	858.9	851.9	844.8	837.8	823.7
10°	880.1	883.1	879.1	875.1	870.0	866.0	857.9	848.9	840.8	831.8	814.6
12.5°	848.9	856.9	854.9	852.9	850.9	848.9	843.8	837.8	832.8	826.7	807.6
15°	793.5	793.5	794.5	795.5	795.5	796.5	797.5	798.5	799.5	800.5	789.5
17.5°	760.3	757.2	757.2	757.2	757.2	757.2	761.3	766.3	770.3	774.4	771.3
20°	736.1	729.0	728.0	728.0	727.0	726.0	733.1	741.1	748.2	755.2	759.3
22.5°	720.0	709.9	708.9	707.9	706.9	705.9	714.9	724.0	733.1	742.1	756.2
25°	716.0	704.9	705.9	706.9	706.9	707.9	714.9	722.0	729.0	736.1	760.3
27.5°	717.0	698.8	699.8	700.9	700.9	701.9	712.9	723.0	734.1	744.2	774.4
30°	724.0	702.9	700.9	698.8	696.8	694.8	709.9	725.0	740.1	755.2	778.4
32.5°	748.2	728.0	723.0	718.0	712.9	707.9	726.0	743.1	761.3	778.4	797.5
35°	774.4	752.2	750.2	748.2	745.2	743.1	759.3	776.4	792.5	808.6	825.7
37.5°	813.6	791.5	789.5	786.4	784.4	781.4	799.5	816.7	834.8	851.9	867.0
40°	872.0	853.9	852.9	852.9	851.9	850.9	865.0	880.1	894.2	908.3	918.4
42.5°	949.6	940.5	943.5	947.6	950.6	953.6	964.7	976.8	987.8	998.9	995.9
45°	1061.3	1070.4	1071.4	1072.4	1073.4	1074.4	1077.5	1081.5	1084.5	1087.5	1075.4
47.5°	1190.2	1202.3	1208.4	1214.4	1219.4	1225.5	1221.5	1216.4	1212.4	1207.4	1177.1
50°	1343.3	1368.5	1367.5	1366.5	1364.4	1363.4	1355.4	1347.3	1338.3	1330.2	1285.9
52.5°	1464.1	1492.3	1497.4	1502.4	1507.4	1512.5	1497.4	1482.3	1466.1	1451.0	1395.7
55°	1594.0	1623.2	1624.2	1625.2	1625.2	1626.3	1605.1	1584.0	1561.8	1540.7	1483.3
57.5°	1690.7	1718.9	1715.9	1713.9	1710.8	1707.8	1682.6	1657.5	1632.3	1607.1	1549.7
60°	1727.0	1751.1	1745.1	1739.0	1732.0	1725.9	1706.8	1687.7	1667.5	1648.4	1593.0
62.5°	1709.8	1728.0	1718.9	1710.8	1701.8	1692.7	1668.5	1643.4	1619.2	1594.0	1553.8
65°	1597.1	1608.1	1596.0	1585.0	1573.9	1561.8	1541.7	1521.5	1500.4	1480.2	1453.1
67.5°	1406.7	1408.8	1407.7	1406.7	1405.7	1404.7	1375.5	1346.3	1316.1	1286.9	1284.9
70°	1145.9	1133.8	1135.9	1138.9	1140.9	1142.9	1120.8	1099.6	1077.5	1055.3	1065.4
72.5°	884.1	863.0	868.0	874.0	879.1	884.1	866.0	848.9	830.7	812.6	826.7
75°	656.5	643.5	648.5	654.5	659.6	664.6	657.6	650.5	642.4	635.4	648.5
77.5°	500.5	492.4	493.4	493.4	494.4	494.4	495.4	497.4	498.4	499.5	513.6
80°	407.8	406.8	405.8	404.8	402.8	401.8	411.9	421.9	432.0	442.1	449.1
82.5°	356.5	366.5	360.5	355.5	349.4	343.4	352.4	361.5	370.6	379.6	376.6
85°	290.0	302.1	291.0	279.9	267.9	256.8	264.8	271.9	279.9	287.0	283.0
87.5°	114.8	117.8	99.7	82.6	64.4	46.3	73.5	99.7	126.9	153.1	157.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986
 CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986

CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0	725.0
2.5°	782.4	778.4	775.4	774.4	772.3	771.3	769.3	767.3	764.3	762.3	759.3
5°	808.6	802.6	795.5	785.4	776.4	766.3	756.2	747.2	738.1	728.0	719.0
7.5°	809.6	795.5	781.4	768.3	754.2	741.1	727.0	714.9	701.9	688.8	676.7
10°	798.5	781.4	764.3	747.2	731.1	713.9	696.8	682.7	667.6	652.5	638.4
12.5°	789.5	770.3	751.2	731.1	711.9	691.8	671.6	657.6	643.5	629.4	615.3
15°	778.4	766.3	755.2	737.1	719.0	700.9	682.7	663.6	645.5	626.3	607.2
17.5°	769.3	766.3	763.3	751.2	739.1	726.0	713.9	694.8	675.7	655.5	636.4
20°	764.3	768.3	772.3	766.3	760.3	753.2	747.2	733.1	719.0	703.9	689.8
22.5°	770.3	785.4	799.5	800.5	802.6	803.6	804.6	791.5	778.4	764.3	751.2
25°	784.4	808.6	832.8	845.9	858.9	873.0	886.1	878.1	870.0	862.0	853.9
27.5°	803.6	833.8	864.0	883.1	901.2	920.4	939.5	938.5	937.5	935.5	934.5
30°	800.5	823.7	846.9	870.0	893.2	916.3	939.5	951.6	962.7	974.7	986.8
32.5°	817.7	836.8	856.9	881.1	905.3	930.4	954.6	979.8	1003.9	1029.1	1054.3
35°	843.8	861.0	879.1	905.3	932.5	958.6	985.8	1016.0	1047.2	1078.5	1108.7
37.5°	883.1	898.2	914.3	936.5	959.6	981.8	1005.0	1049.3	1093.6	1138.9	1183.2
40°	928.4	938.5	948.6	969.7	990.9	1012.0	1033.2	1088.5	1143.9	1199.3	1254.7
42.5°	993.9	990.9	987.8	1005.0	1023.1	1040.2	1058.3	1108.7	1159.0	1209.4	1259.7
45°	1063.4	1051.3	1039.2	1047.2	1056.3	1064.4	1073.4	1124.8	1176.1	1228.5	1279.9
47.5°	1146.9	1116.7	1086.5	1079.5	1072.4	1064.4	1057.3	1112.7	1168.1	1224.5	1279.9
50°	1241.6	1196.3	1152.0	1133.8	1114.7	1096.6	1077.5	1122.8	1169.1	1215.4	1260.7
52.5°	1340.3	1283.9	1228.5	1200.3	1172.1	1142.9	1114.7	1153.0	1192.3	1231.5	1269.8
55°	1424.9	1367.5	1309.1	1275.8	1242.6	1209.4	1176.1	1214.4	1252.7	1290.9	1329.2
57.5°	1492.3	1434.9	1377.5	1346.3	1314.1	1282.9	1250.7	1286.9	1324.2	1361.4	1397.7
60°	1538.6	1483.3	1427.9	1397.7	1367.5	1337.3	1307.0	1350.3	1393.6	1438.0	1481.3
62.5°	1514.5	1474.2	1433.9	1420.8	1407.7	1393.6	1380.6	1421.8	1462.1	1503.4	1544.7
65°	1425.9	1398.7	1371.5	1384.6	1398.7	1411.8	1425.9	1453.1	1480.2	1508.4	1535.6
67.5°	1281.9	1279.9	1276.8	1306.0	1335.2	1365.5	1394.7	1412.8	1429.9	1448.0	1466.1
70°	1075.4	1086.5	1096.6	1146.9	1197.3	1247.6	1298.0	1305.0	1312.1	1319.1	1326.2
72.5°	841.8	855.9	871.0	937.5	1002.9	1069.4	1135.9	1131.8	1127.8	1122.8	1118.7
75°	662.6	675.7	689.8	751.2	812.6	874.0	935.5	918.4	902.2	885.1	868.0
77.5°	528.7	542.8	557.9	615.3	672.7	731.1	788.5	747.2	705.9	664.6	623.3
80°	455.2	462.2	468.2	507.5	545.8	585.0	624.3	582.0	538.7	495.4	453.1
82.5°	373.6	369.6	366.5	389.7	412.9	436.0	459.2	418.9	378.6	337.3	297.1
85°	278.9	274.9	270.9	283.0	295.0	308.1	320.2	273.9	227.6	180.2	133.9
87.5°	162.1	166.1	170.2	183.3	196.4	210.5	223.5	176.2	128.9	80.6	33.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986
 CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675986
 CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	725.0	725.0
2.5°	753.2	748.2
5°	711.9	704.9
7.5°	666.6	657.6
10°	625.3	613.2
12.5°	599.1	584.0
15°	589.1	571.0
17.5°	619.3	602.2
20°	665.6	642.4
22.5°	722.0	693.8
25°	819.7	785.4
27.5°	899.2	864.0
30°	948.6	910.3
32.5°	1002.9	952.6
35°	1059.3	1011.0
37.5°	1127.8	1073.4
40°	1198.3	1141.9
42.5°	1222.5	1186.2
45°	1245.6	1211.4
47.5°	1250.7	1222.5
50°	1255.7	1251.7
52.5°	1269.8	1268.8
55°	1330.2	1331.2
57.5°	1404.7	1410.8
60°	1473.2	1466.1
62.5°	1508.4	1472.2
65°	1484.3	1433.9
67.5°	1411.8	1357.4
70°	1252.7	1179.2
72.5°	1054.3	989.9
75°	812.6	758.2
77.5°	578.0	532.7
80°	406.8	361.5
82.5°	260.8	224.6
85°	117.8	102.7
87.5°	33.2	32.2
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P675986
CATALOG NUMBER: CCW-SA-1A-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)