

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675988

Luminaire Tested: **CCW-SA-1C-740-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P675988
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-1C-740-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @615mA w/
SLR distribution lens
Light Source: (16) 4000K CCT, 70 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3752.1 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 32
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 5.3 fc

Type IV - Short - N/A

REPORT NUMBER: P675988
CATALOG NUMBER: CCW-SA-1C-740-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	772.0	0.0	772.0
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	2980.1	0.0	2980.1
	% Fixture	79.4	0.0	79.4
Total	Lumens	3752.1	0.0	3752.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.1	2.5
10°-20°	196.6	5.2
20°-30°	287.6	7.7
30°-40°	405.2	10.8
40°-50°	556.8	14.8
50°-60°	758.9	20.2
60°-70°	830.6	22.1
70°-80°	479.7	12.8
80°-90°	143.8	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3752.1	100.0
0°-180°	3752.1	100.0

Coefficient of Utilization



REPORT NUMBER: P675988


CATALOG NUMBER: CCW-SA-1C-740-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	385.3	10.3			
FM	(30°-60°)	1369.2	36.5			
FH	(60°-80°)	1103.3	29.4			G1/1800
FVH	(80°-90°)	122.1	3.3			G2/225
BL	(0°-30°)	191.9	5.1	B1/500		
BM	(30°-60°)	351.5	9.4	B1/1000		
BH	(60°-80°)	206.9	5.5	B1/500		G1/500
BVH	(80°-90°)	21.7	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2
2.5°	1236.5	1229.8	1224.8	1219.8	1213.2	1208.2	1201.5	1194.9	1186.5	1179.9	1171.6
5°	1164.9	1144.9	1125.0	1113.3	1100.0	1088.3	1075.0	1060.1	1045.1	1028.4	1013.5
7.5°	1086.7	1061.7	1036.8	1016.8	995.2	975.2	953.6	935.2	916.9	898.6	880.3
10°	1013.5	990.2	966.9	941.9	915.3	890.3	863.7	838.7	813.8	788.8	763.8
12.5°	965.2	936.9	910.3	882.0	855.4	827.1	798.8	775.5	752.2	727.2	703.9
15°	943.6	916.9	892.0	863.7	835.4	807.1	778.8	752.2	727.2	700.6	674.0
17.5°	995.2	956.9	918.6	882.0	845.4	808.8	772.2	738.9	705.6	672.3	639.0
20°	1061.7	1013.5	966.9	921.9	875.3	830.4	783.8	737.2	690.6	644.0	597.4
22.5°	1146.6	1091.7	1038.4	980.2	920.3	862.0	802.1	743.9	685.6	625.7	567.5
25°	1298.0	1233.1	1168.2	1085.0	1000.1	916.9	832.1	755.5	680.6	604.1	527.5
27.5°	1427.8	1339.6	1253.1	1153.2	1053.4	953.6	853.7	765.5	679.0	590.8	502.6
30°	1504.4	1417.8	1331.3	1209.8	1090.0	968.5	847.0	748.9	652.3	554.2	456.0
32.5°	1574.3	1477.8	1381.2	1248.1	1113.3	980.2	845.4	737.2	630.7	522.5	414.4
35°	1670.8	1564.3	1459.4	1304.7	1149.9	995.2	840.4	728.9	615.7	504.2	391.1
37.5°	1774.0	1642.5	1512.7	1341.3	1169.9	998.5	827.1	717.2	607.4	497.6	387.7
40°	1887.1	1727.4	1569.3	1379.6	1191.5	1001.8	812.1	702.3	592.4	480.9	371.1
42.5°	1960.4	1787.3	1614.2	1409.5	1206.5	1001.8	797.1	689.0	580.8	471.0	362.8
45°	2002.0	1833.9	1667.5	1446.1	1224.8	1003.5	782.1	675.6	569.1	461.0	354.5
47.5°	2020.3	1863.8	1707.4	1474.4	1243.1	1010.1	777.2	669.0	559.2	451.0	341.1
50°	2068.5	1930.4	1792.3	1542.7	1294.7	1045.1	795.5	679.0	564.1	447.7	331.2
52.5°	2096.8	1978.7	1860.5	1604.2	1348.0	1091.7	835.4	705.6	575.8	446.0	316.2
55°	2200.0	2086.8	1973.7	1700.7	1426.2	1153.2	878.7	735.5	592.4	447.7	304.5
57.5°	2331.5	2211.6	2093.5	1798.9	1504.4	1209.8	915.3	762.2	607.4	454.3	299.5
60°	2423.0	2306.5	2191.7	1878.8	1564.3	1251.4	936.9	777.2	617.4	456.0	296.2
62.5°	2433.0	2283.2	2135.1	1830.6	1526.0	1219.8	915.3	760.5	605.7	449.3	294.6
65°	2369.7	2195.0	2020.3	1729.0	1437.8	1146.6	855.4	713.9	572.5	429.3	287.9
67.5°	2243.3	2038.6	1833.9	1567.6	1301.4	1035.1	768.8	647.3	527.5	406.0	284.6
70°	1948.7	1769.0	1590.9	1359.6	1129.9	898.6	667.3	567.5	469.3	369.4	269.6
72.5°	1635.8	1467.8	1301.4	1113.3	926.9	738.9	550.8	475.9	401.1	324.5	249.6
75°	1253.1	1126.6	1001.8	862.0	722.2	580.8	441.0	386.1	331.2	276.2	221.3
77.5°	880.3	812.1	745.5	640.7	535.9	431.0	326.2	289.6	252.9	216.3	179.7
80°	597.4	559.2	522.5	447.7	372.8	296.2	221.3	198.0	173.1	149.8	124.8
82.5°	371.1	369.4	366.1	314.5	262.9	211.3	159.8	139.8	121.5	101.5	81.5
85°	169.7	198.0	224.7	196.4	168.1	139.8	111.5	98.2	84.9	69.9	56.6
87.5°	53.3	64.9	74.9	71.6	66.6	63.2	58.2	49.9	41.6	33.3	25.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2
2.5°	1164.9	1159.9	1153.2	1146.6	1138.3	1131.6	1123.3	1115.0	1113.3	1110.0	1108.3
5°	1003.5	993.5	981.8	971.9	961.9	950.2	940.2	928.6	920.3	910.3	902.0
7.5°	862.0	845.4	827.1	808.8	792.1	775.5	757.2	740.5	732.2	723.9	715.6
10°	748.9	732.2	717.2	700.6	689.0	679.0	667.3	655.7	645.7	635.7	625.7
12.5°	692.3	680.6	669.0	657.3	644.0	632.4	619.1	605.7	594.1	584.1	572.5
15°	657.3	640.7	622.4	605.7	587.4	570.8	552.5	534.2	520.9	509.2	495.9
17.5°	615.7	590.8	567.5	542.5	522.5	502.6	480.9	461.0	446.0	429.3	414.4
20°	569.1	540.8	510.9	482.6	459.3	437.7	414.4	391.1	374.4	356.1	339.5
22.5°	529.2	492.6	454.3	416.0	391.1	366.1	339.5	314.5	299.5	282.9	267.9
25°	485.9	446.0	404.4	362.8	337.8	311.2	286.2	259.6	248.0	238.0	226.3
27.5°	462.6	422.7	381.1	341.1	317.9	292.9	269.6	244.6	236.3	226.3	218.0
30°	416.0	377.8	337.8	297.9	281.2	266.3	249.6	233.0	229.7	228.0	224.7
32.5°	374.4	334.5	294.6	254.6	239.6	224.7	209.7	194.7	193.0	189.7	188.0
35°	352.8	314.5	274.6	236.3	223.0	208.0	194.7	179.7	176.4	171.4	168.1
37.5°	347.8	307.9	266.3	226.3	213.0	199.7	184.7	171.4	168.1	164.7	161.4
40°	334.5	296.2	259.6	221.3	208.0	194.7	179.7	166.4	163.1	159.8	156.4
42.5°	324.5	287.9	249.6	211.3	199.7	188.0	174.7	163.1	159.8	156.4	151.4
45°	316.2	277.9	238.0	199.7	191.4	183.1	173.1	164.7	161.4	156.4	153.1
47.5°	302.9	266.3	228.0	189.7	181.4	174.7	166.4	158.1	154.8	151.4	148.1
50°	292.9	254.6	216.3	178.1	171.4	164.7	158.1	151.4	151.4	153.1	153.1
52.5°	279.6	243.0	206.4	169.7	163.1	156.4	149.8	143.1	144.8	146.4	148.1
55°	267.9	233.0	196.4	159.8	153.1	146.4	138.1	131.5	133.1	134.8	136.5
57.5°	262.9	226.3	189.7	153.1	146.4	138.1	131.5	123.1	123.1	123.1	123.1
60°	259.6	221.3	184.7	146.4	138.1	131.5	123.1	114.8	113.2	113.2	111.5
62.5°	257.9	219.7	183.1	144.8	134.8	126.5	116.5	106.5	104.8	103.2	101.5
65°	251.3	216.3	179.7	143.1	131.5	121.5	109.8	98.2	96.5	96.5	94.9
67.5°	249.6	213.0	178.1	141.5	129.8	116.5	104.8	91.5	89.9	88.2	86.5
70°	236.3	204.7	171.4	138.1	124.8	113.2	99.8	86.5	84.9	81.5	79.9
72.5°	219.7	191.4	161.4	131.5	118.2	104.8	91.5	78.2	76.6	74.9	71.6
75°	194.7	168.1	141.5	114.8	103.2	93.2	81.5	69.9	68.2	66.6	63.2
77.5°	159.8	138.1	118.2	96.5	88.2	79.9	71.6	63.2	61.6	59.9	56.6
80°	113.2	99.8	88.2	74.9	69.9	63.2	58.2	51.6	51.6	49.9	49.9
82.5°	74.9	68.2	61.6	54.9	51.6	48.3	44.9	41.6	41.6	39.9	39.9
85°	53.3	49.9	44.9	41.6	39.9	36.6	34.9	31.6	31.6	31.6	31.6
87.5°	25.0	25.0	23.3	23.3	21.6	21.6	20.0	18.3	18.3	18.3	18.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2
2.5°	1105.0	1100.0	1095.0	1088.3	1083.4	1076.7	1068.4	1061.7	1053.4	1053.4	1051.7
5°	892.0	887.0	882.0	875.3	870.3	863.7	858.7	852.0	845.4	845.4	843.7
7.5°	707.3	697.3	687.3	675.6	665.7	659.0	652.3	644.0	637.4	632.4	627.4
10°	615.7	605.7	594.1	584.1	572.5	564.1	555.8	545.8	537.5	530.9	524.2
12.5°	560.8	549.2	537.5	525.9	514.2	502.6	492.6	480.9	469.3	461.0	452.6
15°	482.6	471.0	459.3	447.7	436.0	422.7	409.4	394.4	381.1	374.4	369.4
17.5°	397.7	386.1	372.8	361.1	347.8	337.8	327.8	317.9	307.9	301.2	296.2
20°	321.2	307.9	294.6	281.2	267.9	261.3	254.6	248.0	241.3	236.3	233.0
22.5°	251.3	243.0	236.3	228.0	219.7	214.7	211.3	206.4	201.4	201.4	201.4
25°	214.7	209.7	206.4	201.4	196.4	194.7	193.0	189.7	188.0	186.4	186.4
27.5°	208.0	203.0	198.0	193.0	188.0	186.4	184.7	181.4	179.7	179.7	179.7
30°	221.3	219.7	218.0	216.3	214.7	211.3	206.4	203.0	198.0	194.7	191.4
32.5°	184.7	183.1	183.1	181.4	179.7	183.1	184.7	188.0	189.7	191.4	193.0
35°	163.1	159.8	156.4	153.1	149.8	148.1	146.4	144.8	143.1	143.1	141.5
37.5°	158.1	154.8	151.4	148.1	144.8	143.1	141.5	139.8	138.1	138.1	136.5
40°	153.1	149.8	148.1	144.8	141.5	139.8	138.1	134.8	133.1	131.5	131.5
42.5°	148.1	146.4	143.1	141.5	138.1	136.5	134.8	131.5	129.8	128.1	126.5
45°	148.1	144.8	141.5	138.1	134.8	133.1	129.8	128.1	124.8	124.8	123.1
47.5°	144.8	141.5	138.1	134.8	131.5	129.8	126.5	124.8	121.5	119.8	118.2
50°	153.1	148.1	141.5	136.5	129.8	128.1	124.8	123.1	119.8	118.2	116.5
52.5°	149.8	144.8	138.1	133.1	126.5	123.1	121.5	118.2	114.8	113.2	111.5
55°	138.1	133.1	129.8	124.8	119.8	116.5	113.2	109.8	106.5	104.8	104.8
57.5°	123.1	121.5	119.8	118.2	116.5	113.2	109.8	104.8	101.5	99.8	98.2
60°	109.8	111.5	113.2	114.8	116.5	111.5	106.5	101.5	96.5	94.9	93.2
62.5°	99.8	103.2	106.5	108.2	111.5	106.5	101.5	96.5	91.5	89.9	88.2
65°	93.2	94.9	94.9	96.5	96.5	93.2	91.5	88.2	84.9	83.2	83.2
67.5°	84.9	84.9	84.9	83.2	83.2	81.5	81.5	79.9	78.2	76.6	76.6
70°	76.6	76.6	76.6	74.9	74.9	73.2	73.2	71.6	69.9	69.9	68.2
72.5°	69.9	69.9	68.2	68.2	66.6	66.6	66.6	64.9	64.9	63.2	63.2
75°	61.6	61.6	59.9	59.9	58.2	58.2	58.2	56.6	56.6	56.6	54.9
77.5°	54.9	54.9	53.3	53.3	51.6	51.6	51.6	49.9	49.9	48.3	48.3
80°	48.3	48.3	46.6	46.6	44.9	44.9	43.3	43.3	41.6	41.6	39.9
82.5°	38.3	38.3	38.3	38.3	38.3	36.6	36.6	34.9	33.3	33.3	31.6
85°	31.6	31.6	31.6	30.0	30.0	30.0	28.3	28.3	26.6	25.0	25.0
87.5°	18.3	18.3	18.3	16.6	16.6	16.6	16.6	16.6	16.6	16.6	15.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988
 CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2
2.5°	1051.7	1050.1	1043.4	1036.8	1043.4	1050.1	1050.1	1050.1	1048.4	1048.4	1048.4
5°	843.7	842.1	838.7	835.4	835.4	833.7	837.1	840.4	843.7	847.0	850.4
7.5°	620.7	615.7	610.7	605.7	609.1	610.7	615.7	619.1	624.1	627.4	635.7
10°	517.5	510.9	505.9	500.9	497.6	494.2	490.9	489.3	485.9	482.6	485.9
12.5°	442.7	434.3	426.0	416.0	414.4	412.7	409.4	406.0	402.7	399.4	397.7
15°	362.8	356.1	352.8	347.8	341.1	334.5	331.2	329.5	326.2	322.8	321.2
17.5°	289.6	282.9	277.9	272.9	271.3	267.9	267.9	267.9	267.9	267.9	267.9
20°	228.0	223.0	223.0	221.3	221.3	219.7	221.3	223.0	223.0	224.7	226.3
22.5°	199.7	199.7	198.0	196.4	198.0	198.0	199.7	201.4	203.0	204.7	206.4
25°	184.7	183.1	184.7	186.4	186.4	186.4	188.0	188.0	189.7	189.7	189.7
27.5°	178.1	178.1	179.7	179.7	181.4	181.4	181.4	179.7	179.7	178.1	178.1
30°	188.0	184.7	184.7	184.7	183.1	181.4	179.7	179.7	178.1	176.4	174.7
32.5°	194.7	196.4	194.7	191.4	189.7	186.4	184.7	181.4	179.7	176.4	173.1
35°	141.5	139.8	143.1	144.8	146.4	148.1	149.8	151.4	151.4	153.1	153.1
37.5°	136.5	134.8	134.8	133.1	133.1	133.1	133.1	133.1	131.5	131.5	133.1
40°	129.8	128.1	128.1	126.5	126.5	124.8	124.8	124.8	124.8	124.8	124.8
42.5°	124.8	123.1	123.1	123.1	123.1	121.5	121.5	119.8	119.8	118.2	118.2
45°	123.1	121.5	119.8	118.2	118.2	116.5	116.5	116.5	114.8	114.8	114.8
47.5°	116.5	114.8	114.8	113.2	113.2	111.5	111.5	111.5	109.8	109.8	109.8
50°	113.2	111.5	111.5	109.8	109.8	108.2	108.2	108.2	106.5	106.5	106.5
52.5°	108.2	106.5	106.5	106.5	104.8	103.2	103.2	103.2	101.5	101.5	101.5
55°	103.2	101.5	101.5	101.5	99.8	98.2	98.2	98.2	96.5	96.5	96.5
57.5°	96.5	94.9	94.9	93.2	93.2	93.2	93.2	93.2	91.5	91.5	91.5
60°	91.5	89.9	89.9	88.2	88.2	86.5	86.5	86.5	86.5	86.5	86.5
62.5°	86.5	84.9	83.2	81.5	83.2	83.2	83.2	83.2	81.5	81.5	81.5
65°	81.5	79.9	78.2	76.6	76.6	76.6	76.6	76.6	76.6	76.6	76.6
67.5°	74.9	73.2	71.6	69.9	71.6	71.6	71.6	71.6	71.6	71.6	71.6
70°	68.2	66.6	66.6	64.9	64.9	63.2	63.2	64.9	64.9	64.9	64.9
72.5°	61.6	59.9	59.9	58.2	58.2	58.2	58.2	58.2	58.2	58.2	58.2
75°	54.9	53.3	53.3	51.6	51.6	51.6	51.6	51.6	51.6	51.6	51.6
77.5°	46.6	44.9	44.9	44.9	44.9	44.9	44.9	46.6	46.6	46.6	46.6
80°	39.9	38.3	38.3	38.3	38.3	38.3	38.3	38.3	38.3	38.3	38.3
82.5°	31.6	30.0	30.0	30.0	30.0	30.0	30.0	30.0	30.0	30.0	30.0
85°	23.3	21.6	21.6	21.6	23.3	23.3	23.3	23.3	23.3	23.3	23.3
87.5°	15.0	13.3	13.3	13.3	15.0	15.0	15.0	15.0	13.3	13.3	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988
 CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2
2.5°	1048.4	1048.4	1048.4	1046.7	1045.1	1043.4	1041.8	1046.7	1050.1	1055.1	1058.4
5°	852.0	855.4	857.0	862.0	867.0	872.0	877.0	880.3	883.7	885.3	888.6
7.5°	642.4	650.7	657.3	664.0	670.6	675.6	682.3	687.3	692.3	697.3	702.3
10°	487.6	490.9	492.6	499.2	504.2	510.9	515.9	520.9	525.9	529.2	534.2
12.5°	396.1	392.7	391.1	391.1	391.1	391.1	391.1	394.4	397.7	401.1	404.4
15°	319.5	317.9	316.2	314.5	312.9	309.5	307.9	311.2	314.5	317.9	321.2
17.5°	267.9	267.9	267.9	266.3	264.6	262.9	261.3	262.9	264.6	264.6	266.3
20°	229.7	231.3	233.0	234.6	234.6	236.3	236.3	238.0	239.6	239.6	241.3
22.5°	206.4	208.0	208.0	208.0	209.7	209.7	209.7	211.3	213.0	214.7	216.3
25°	188.0	188.0	186.4	186.4	188.0	188.0	188.0	188.0	189.7	189.7	189.7
27.5°	178.1	176.4	176.4	176.4	176.4	174.7	174.7	174.7	174.7	174.7	174.7
30°	173.1	171.4	169.7	168.1	168.1	166.4	164.7	164.7	164.7	164.7	164.7
32.5°	171.4	168.1	164.7	163.1	163.1	161.4	159.8	158.1	158.1	156.4	154.8
35°	153.1	151.4	151.4	149.8	148.1	146.4	144.8	144.8	144.8	143.1	143.1
37.5°	133.1	134.8	134.8	134.8	136.5	136.5	136.5	136.5	138.1	138.1	138.1
40°	124.8	124.8	124.8	126.5	128.1	128.1	129.8	129.8	131.5	131.5	131.5
42.5°	118.2	116.5	116.5	118.2	118.2	119.8	119.8	121.5	123.1	123.1	124.8
45°	114.8	113.2	113.2	113.2	113.2	111.5	111.5	113.2	114.8	116.5	118.2
47.5°	108.2	108.2	106.5	106.5	106.5	106.5	106.5	106.5	108.2	108.2	108.2
50°	104.8	104.8	103.2	103.2	103.2	103.2	103.2	103.2	103.2	103.2	103.2
52.5°	101.5	99.8	99.8	99.8	99.8	98.2	98.2	98.2	98.2	98.2	98.2
55°	96.5	94.9	94.9	94.9	94.9	94.9	94.9	94.9	96.5	96.5	96.5
57.5°	91.5	89.9	89.9	89.9	91.5	91.5	91.5	91.5	93.2	93.2	93.2
60°	86.5	86.5	86.5	86.5	86.5	86.5	86.5	88.2	88.2	89.9	89.9
62.5°	81.5	81.5	81.5	81.5	83.2	83.2	83.2	83.2	84.9	84.9	84.9
65°	76.6	76.6	76.6	76.6	78.2	78.2	78.2	78.2	78.2	78.2	78.2
67.5°	71.6	71.6	71.6	71.6	71.6	71.6	71.6	73.2	73.2	74.9	74.9
70°	64.9	63.2	63.2	64.9	64.9	66.6	66.6	68.2	68.2	69.9	69.9
72.5°	58.2	58.2	58.2	58.2	58.2	58.2	58.2	59.9	61.6	61.6	63.2
75°	51.6	51.6	51.6	51.6	53.3	53.3	53.3	54.9	54.9	56.6	56.6
77.5°	46.6	44.9	44.9	44.9	46.6	46.6	46.6	48.3	48.3	49.9	49.9
80°	38.3	38.3	38.3	38.3	39.9	39.9	39.9	39.9	41.6	41.6	41.6
82.5°	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6	33.3	33.3	33.3
85°	23.3	23.3	23.3	23.3	25.0	25.0	25.0	25.0	25.0	25.0	25.0
87.5°	15.0	15.0	15.0	15.0	15.0	15.0	15.0	15.0	16.6	16.6	16.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988
 CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2
2.5°	1058.4	1058.4	1058.4	1058.4	1061.7	1063.4	1066.7	1068.4	1066.7	1065.0	1061.7
5°	890.3	892.0	892.0	893.6	893.6	893.6	893.6	893.6	897.0	900.3	903.6
7.5°	703.9	705.6	707.3	708.9	708.9	708.9	707.3	707.3	708.9	708.9	710.6
10°	539.2	545.8	550.8	555.8	552.5	547.5	544.2	539.2	539.2	539.2	537.5
12.5°	407.7	409.4	412.7	414.4	412.7	412.7	411.0	409.4	411.0	414.4	416.0
15°	322.8	322.8	324.5	324.5	326.2	327.8	327.8	329.5	332.8	334.5	337.8
17.5°	267.9	269.6	269.6	271.3	271.3	272.9	272.9	272.9	276.2	279.6	284.6
20°	241.3	241.3	241.3	241.3	241.3	239.6	239.6	238.0	239.6	243.0	244.6
22.5°	216.3	218.0	218.0	218.0	216.3	214.7	211.3	209.7	209.7	211.3	211.3
25°	189.7	188.0	188.0	186.4	186.4	188.0	188.0	188.0	189.7	189.7	191.4
27.5°	174.7	173.1	173.1	171.4	171.4	173.1	173.1	173.1	173.1	173.1	173.1
30°	163.1	163.1	161.4	159.8	161.4	161.4	163.1	163.1	164.7	164.7	166.4
32.5°	154.8	153.1	153.1	151.4	153.1	153.1	154.8	154.8	156.4	158.1	158.1
35°	143.1	143.1	143.1	143.1	143.1	143.1	141.5	141.5	141.5	141.5	141.5
37.5°	136.5	136.5	134.8	133.1	133.1	133.1	133.1	133.1	131.5	129.8	128.1
40°	131.5	129.8	129.8	128.1	126.5	126.5	124.8	123.1	123.1	121.5	121.5
42.5°	124.8	123.1	123.1	121.5	119.8	119.8	118.2	116.5	116.5	116.5	114.8
45°	116.5	116.5	114.8	113.2	113.2	113.2	111.5	111.5	111.5	111.5	109.8
47.5°	108.2	108.2	106.5	106.5	106.5	106.5	104.8	104.8	104.8	104.8	104.8
50°	103.2	103.2	103.2	103.2	103.2	103.2	101.5	101.5	101.5	101.5	101.5
52.5°	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2
55°	96.5	96.5	96.5	96.5	96.5	96.5	94.9	94.9	94.9	96.5	96.5
57.5°	93.2	93.2	91.5	91.5	91.5	91.5	91.5	91.5	91.5	91.5	91.5
60°	89.9	89.9	89.9	89.9	89.9	89.9	89.9	89.9	89.9	89.9	89.9
62.5°	84.9	84.9	84.9	84.9	84.9	86.5	86.5	86.5	86.5	86.5	84.9
65°	78.2	79.9	79.9	79.9	79.9	79.9	79.9	79.9	79.9	79.9	79.9
67.5°	74.9	74.9	74.9	74.9	74.9	74.9	74.9	74.9	74.9	74.9	74.9
70°	69.9	69.9	68.2	68.2	68.2	69.9	69.9	69.9	69.9	69.9	69.9
72.5°	63.2	63.2	63.2	63.2	63.2	63.2	63.2	63.2	63.2	64.9	64.9
75°	56.6	56.6	56.6	56.6	56.6	56.6	56.6	56.6	56.6	56.6	56.6
77.5°	49.9	49.9	48.3	48.3	48.3	49.9	49.9	49.9	49.9	51.6	51.6
80°	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6	43.3	43.3
82.5°	33.3	33.3	33.3	33.3	33.3	33.3	33.3	33.3	33.3	34.9	34.9
85°	25.0	26.6	26.6	26.6	26.6	26.6	26.6	26.6	26.6	28.3	28.3
87.5°	16.6	16.6	16.6	16.6	16.6	16.6	15.0	15.0	15.0	15.0	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988
 CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2
2.5°	1060.1	1061.7	1063.4	1063.4	1065.0	1066.7	1066.7	1073.4	1080.0	1083.4	1086.7
5°	907.0	905.3	905.3	903.6	902.0	907.0	911.9	921.9	931.9	933.6	936.9
7.5°	710.6	712.3	713.9	713.9	715.6	710.6	703.9	705.6	707.3	715.6	722.2
10°	537.5	539.2	540.8	540.8	542.5	540.8	537.5	542.5	547.5	554.2	562.5
12.5°	417.7	422.7	427.7	431.0	436.0	439.3	441.0	447.7	452.6	461.0	469.3
15°	341.1	344.5	347.8	351.1	354.5	357.8	361.1	367.8	374.4	384.4	394.4
17.5°	287.9	287.9	289.6	289.6	289.6	292.9	296.2	299.5	301.2	311.2	321.2
20°	246.3	244.6	243.0	241.3	239.6	243.0	244.6	246.3	248.0	254.6	259.6
22.5°	211.3	211.3	213.0	213.0	213.0	211.3	208.0	209.7	209.7	213.0	218.0
25°	191.4	191.4	191.4	189.7	189.7	191.4	193.0	193.0	191.4	193.0	194.7
27.5°	173.1	174.7	174.7	176.4	176.4	178.1	178.1	178.1	178.1	179.7	181.4
30°	166.4	166.4	168.1	168.1	168.1	169.7	171.4	171.4	171.4	173.1	176.4
32.5°	159.8	161.4	163.1	164.7	166.4	168.1	168.1	169.7	169.7	171.4	173.1
35°	141.5	139.8	139.8	138.1	136.5	136.5	136.5	136.5	134.8	136.5	136.5
37.5°	126.5	126.5	126.5	124.8	124.8	126.5	126.5	126.5	126.5	128.1	128.1
40°	119.8	119.8	119.8	119.8	119.8	119.8	119.8	121.5	121.5	123.1	124.8
42.5°	114.8	114.8	114.8	114.8	114.8	116.5	116.5	116.5	116.5	118.2	118.2
45°	109.8	109.8	109.8	109.8	109.8	109.8	109.8	111.5	111.5	113.2	114.8
47.5°	104.8	104.8	104.8	104.8	104.8	106.5	108.2	108.2	108.2	109.8	109.8
50°	101.5	101.5	101.5	101.5	101.5	103.2	103.2	104.8	104.8	106.5	108.2
52.5°	98.2	98.2	98.2	98.2	98.2	99.8	99.8	101.5	101.5	103.2	104.8
55°	96.5	96.5	96.5	94.9	94.9	96.5	96.5	98.2	98.2	99.8	99.8
57.5°	91.5	91.5	91.5	91.5	91.5	91.5	91.5	93.2	93.2	94.9	96.5
60°	89.9	89.9	88.2	88.2	86.5	88.2	88.2	89.9	89.9	91.5	91.5
62.5°	84.9	84.9	84.9	83.2	83.2	84.9	84.9	84.9	84.9	86.5	88.2
65°	79.9	79.9	79.9	78.2	78.2	79.9	79.9	79.9	79.9	81.5	83.2
67.5°	74.9	74.9	74.9	73.2	73.2	73.2	73.2	74.9	74.9	76.6	78.2
70°	69.9	69.9	69.9	68.2	68.2	68.2	66.6	68.2	69.9	71.6	71.6
72.5°	64.9	64.9	64.9	63.2	63.2	63.2	61.6	63.2	63.2	64.9	64.9
75°	56.6	56.6	56.6	56.6	56.6	56.6	54.9	54.9	54.9	56.6	56.6
77.5°	51.6	51.6	51.6	49.9	49.9	49.9	48.3	48.3	48.3	49.9	49.9
80°	43.3	43.3	43.3	41.6	41.6	41.6	39.9	39.9	39.9	41.6	41.6
82.5°	34.9	34.9	34.9	33.3	33.3	33.3	31.6	31.6	31.6	33.3	33.3
85°	28.3	28.3	28.3	28.3	28.3	28.3	26.6	26.6	26.6	28.3	30.0
87.5°	13.3	13.3	15.0	15.0	15.0	15.0	13.3	13.3	11.6	11.6	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2
2.5°	1090.0	1093.3	1101.7	1108.3	1116.6	1123.3	1128.3	1134.9	1139.9	1144.9	1148.3
5°	938.6	940.2	948.6	956.9	963.5	971.9	983.5	995.2	1006.8	1018.5	1026.8
7.5°	730.6	737.2	747.2	758.8	768.8	778.8	790.5	803.8	815.4	827.1	838.7
10°	569.1	575.8	585.8	595.8	604.1	614.1	627.4	640.7	654.0	667.3	680.6
12.5°	477.6	485.9	497.6	509.2	519.2	530.9	547.5	562.5	579.1	594.1	610.7
15°	402.7	412.7	427.7	444.3	459.3	474.3	490.9	507.6	522.5	539.2	555.8
17.5°	331.2	341.1	354.5	369.4	382.8	396.1	416.0	434.3	454.3	472.6	490.9
20°	266.3	271.3	284.6	297.9	311.2	324.5	339.5	354.5	369.4	384.4	407.7
22.5°	221.3	224.7	231.3	236.3	243.0	248.0	262.9	277.9	291.2	306.2	327.8
25°	194.7	196.4	201.4	204.7	209.7	213.0	223.0	231.3	241.3	249.6	269.6
27.5°	181.4	183.1	184.7	186.4	188.0	189.7	196.4	203.0	208.0	214.7	233.0
30°	178.1	179.7	184.7	188.0	193.0	196.4	199.7	203.0	206.4	209.7	221.3
32.5°	174.7	176.4	176.4	174.7	174.7	173.1	176.4	178.1	181.4	183.1	193.0
35°	138.1	138.1	139.8	141.5	143.1	144.8	149.8	153.1	158.1	161.4	169.7
37.5°	129.8	129.8	131.5	134.8	136.5	138.1	141.5	144.8	148.1	151.4	159.8
40°	124.8	126.5	128.1	129.8	131.5	133.1	136.5	138.1	141.5	143.1	149.8
42.5°	119.8	119.8	121.5	124.8	126.5	128.1	131.5	133.1	136.5	138.1	144.8
45°	116.5	118.2	119.8	121.5	121.5	123.1	126.5	129.8	131.5	134.8	141.5
47.5°	111.5	111.5	114.8	116.5	119.8	121.5	124.8	126.5	129.8	131.5	138.1
50°	108.2	109.8	113.2	114.8	118.2	119.8	124.8	128.1	133.1	136.5	139.8
52.5°	104.8	106.5	109.8	111.5	114.8	116.5	123.1	129.8	134.8	141.5	141.5
55°	101.5	101.5	104.8	109.8	113.2	116.5	119.8	124.8	128.1	131.5	131.5
57.5°	96.5	98.2	101.5	106.5	109.8	113.2	116.5	119.8	121.5	124.8	123.1
60°	93.2	93.2	98.2	103.2	108.2	113.2	113.2	113.2	111.5	111.5	111.5
62.5°	88.2	89.9	96.5	104.8	111.5	118.2	113.2	108.2	103.2	98.2	99.8
65°	84.9	86.5	89.9	94.9	98.2	101.5	98.2	96.5	93.2	89.9	91.5
67.5°	78.2	79.9	81.5	81.5	83.2	83.2	83.2	83.2	83.2	83.2	84.9
70°	73.2	73.2	73.2	74.9	74.9	74.9	74.9	74.9	74.9	74.9	76.6
72.5°	66.6	66.6	66.6	66.6	66.6	66.6	66.6	66.6	66.6	66.6	68.2
75°	58.2	58.2	58.2	58.2	58.2	58.2	58.2	58.2	58.2	58.2	59.9
77.5°	51.6	51.6	51.6	51.6	51.6	51.6	51.6	51.6	49.9	49.9	51.6
80°	43.3	43.3	43.3	43.3	41.6	41.6	41.6	41.6	41.6	41.6	43.3
82.5°	34.9	34.9	34.9	34.9	33.3	33.3	33.3	33.3	31.6	31.6	33.3
85°	31.6	33.3	33.3	34.9	34.9	34.9	33.3	31.6	30.0	28.3	28.3
87.5°	13.3	13.3	13.3	13.3	11.6	11.6	11.6	11.6	11.6	11.6	11.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988
 CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2
2.5°	1153.2	1156.6	1159.9	1164.9	1171.6	1176.5	1181.5	1191.5	1203.2	1213.2	1223.1
5°	1035.1	1043.4	1051.7	1061.7	1071.7	1080.0	1090.0	1110.0	1129.9	1148.3	1168.2
7.5°	848.7	860.4	870.3	887.0	902.0	918.6	933.6	958.5	981.8	1006.8	1030.1
10°	693.9	707.3	720.6	742.2	765.5	787.1	808.8	828.7	850.4	870.3	890.3
12.5°	627.4	642.4	659.0	672.3	687.3	700.6	713.9	737.2	760.5	783.8	807.1
15°	572.5	589.1	605.7	622.4	637.4	654.0	669.0	689.0	710.6	730.6	750.5
17.5°	509.2	525.9	544.2	562.5	580.8	599.1	617.4	645.7	674.0	700.6	728.9
20°	429.3	452.6	474.3	499.2	524.2	549.2	574.1	604.1	634.0	662.3	692.3
22.5°	349.5	371.1	392.7	422.7	452.6	480.9	510.9	550.8	589.1	629.0	667.3
25°	291.2	311.2	331.2	364.4	396.1	429.3	461.0	509.2	555.8	604.1	650.7
27.5°	251.3	269.6	287.9	322.8	357.8	391.1	426.0	479.3	530.9	584.1	635.7
30°	233.0	244.6	256.3	289.6	322.8	354.5	387.7	439.3	490.9	542.5	594.1
32.5°	203.0	213.0	223.0	252.9	282.9	311.2	341.1	394.4	446.0	499.2	550.8
35°	179.7	188.0	196.4	224.7	251.3	279.6	306.2	359.5	412.7	466.0	519.2
37.5°	166.4	174.7	181.4	206.4	233.0	257.9	282.9	336.2	387.7	441.0	492.6
40°	156.4	161.4	168.1	193.0	216.3	241.3	264.6	312.9	362.8	411.0	459.3
42.5°	149.8	156.4	161.4	183.1	206.4	228.0	249.6	296.2	342.8	387.7	434.3
45°	148.1	154.8	161.4	179.7	198.0	214.7	233.0	277.9	322.8	367.8	412.7
47.5°	144.8	149.8	156.4	171.4	184.7	199.7	213.0	257.9	302.9	346.1	391.1
50°	143.1	144.8	148.1	161.4	174.7	188.0	201.4	246.3	291.2	336.2	381.1
52.5°	141.5	141.5	141.5	153.1	164.7	174.7	186.4	231.3	277.9	322.8	367.8
55°	131.5	129.8	129.8	141.5	151.4	163.1	173.1	218.0	262.9	306.2	351.1
57.5°	121.5	119.8	118.2	128.1	138.1	148.1	158.1	203.0	249.6	294.6	339.5
60°	111.5	109.8	109.8	119.8	128.1	138.1	146.4	193.0	238.0	284.6	329.5
62.5°	99.8	101.5	101.5	109.8	119.8	128.1	136.5	183.1	231.3	277.9	324.5
65°	91.5	93.2	93.2	103.2	113.2	123.1	133.1	178.1	224.7	269.6	314.5
67.5°	84.9	86.5	86.5	98.2	108.2	119.8	129.8	169.7	211.3	251.3	291.2
70°	78.2	78.2	79.9	91.5	103.2	114.8	126.5	161.4	196.4	229.7	264.6
72.5°	69.9	71.6	73.2	84.9	94.9	106.5	116.5	148.1	179.7	211.3	243.0
75°	61.6	63.2	64.9	74.9	84.9	94.9	104.8	134.8	163.1	193.0	221.3
77.5°	54.9	56.6	58.2	66.6	74.9	83.2	91.5	113.2	136.5	158.1	179.7
80°	44.9	44.9	46.6	53.3	59.9	64.9	71.6	86.5	101.5	114.8	129.8
82.5°	33.3	34.9	34.9	39.9	43.3	48.3	51.6	59.9	66.6	74.9	81.5
85°	28.3	26.6	26.6	30.0	31.6	34.9	36.6	41.6	44.9	49.9	53.3
87.5°	11.6	10.0	10.0	11.6	15.0	16.6	18.3	18.3	20.0	20.0	20.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988
 CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2
2.5°	1228.1	1231.5	1236.5	1239.8	1248.1	1254.8	1263.1	1269.7	1274.7	1283.1	1279.7
5°	1183.2	1198.2	1213.2	1228.1	1239.8	1251.4	1261.4	1273.1	1286.4	1311.3	1318.0
7.5°	1050.1	1070.0	1088.3	1108.3	1131.6	1154.9	1178.2	1201.5	1223.1	1254.8	1274.7
10°	918.6	946.9	973.5	1001.8	1023.4	1045.1	1065.0	1086.7	1116.6	1148.3	1184.9
12.5°	835.4	863.7	892.0	920.3	951.9	981.8	1013.5	1043.4	1071.7	1096.7	1138.3
15°	780.5	812.1	842.1	872.0	910.3	946.9	985.2	1021.8	1063.4	1096.7	1125.0
17.5°	767.2	805.4	842.1	880.3	920.3	960.2	1000.1	1040.1	1081.7	1131.6	1168.2
20°	743.9	795.5	847.0	898.6	950.2	1000.1	1051.7	1101.7	1156.6	1216.5	1233.1
22.5°	730.6	792.1	855.4	916.9	986.8	1058.4	1128.3	1198.2	1256.4	1301.4	1351.3
25°	728.9	805.4	883.7	960.2	1048.4	1134.9	1223.1	1309.7	1384.6	1429.5	1469.4
27.5°	727.2	820.4	911.9	1003.5	1111.6	1218.1	1326.3	1432.8	1502.7	1567.6	1600.9
30°	707.3	818.8	931.9	1043.4	1164.9	1286.4	1407.9	1529.3	1600.9	1645.8	1662.5
32.5°	682.3	813.8	945.2	1076.7	1214.8	1352.9	1489.4	1627.5	1684.1	1722.4	1709.1
35°	662.3	807.1	950.2	1093.3	1239.8	1387.9	1534.3	1680.8	1762.3	1815.6	1793.9
37.5°	644.0	795.5	946.9	1098.3	1269.7	1441.1	1612.5	1784.0	1862.2	1918.8	1893.8
40°	622.4	783.8	946.9	1108.3	1304.7	1499.4	1695.8	1890.5	1992.0	2040.2	2002.0
42.5°	604.1	772.2	941.9	1110.0	1319.7	1529.3	1739.0	1948.7	2061.9	2130.1	2081.8
45°	580.8	748.9	915.3	1083.4	1314.7	1546.0	1775.6	2007.0	2138.4	2191.7	2125.1
47.5°	555.8	722.2	887.0	1051.7	1298.0	1544.3	1790.6	2036.9	2158.4	2221.6	2160.1
50°	547.5	713.9	878.7	1045.1	1311.3	1579.3	1845.5	2111.8	2200.0	2251.6	2170.0
52.5°	545.8	722.2	900.3	1076.7	1344.6	1610.9	1878.8	2145.1	2216.6	2271.5	2198.3
55°	540.8	732.2	921.9	1111.6	1391.2	1672.5	1952.0	2231.6	2303.2	2343.1	2288.2
57.5°	545.8	752.2	956.9	1163.2	1451.1	1739.0	2026.9	2314.8	2401.4	2429.6	2418.0
60°	549.2	768.8	986.8	1206.5	1487.7	1769.0	2050.2	2331.5	2421.3	2491.2	2504.5
62.5°	540.8	757.2	971.9	1188.2	1442.8	1697.4	1952.0	2206.6	2354.8	2457.9	2517.8
65°	515.9	715.6	916.9	1116.6	1351.3	1587.6	1822.2	2056.9	2213.3	2366.4	2414.7
67.5°	461.0	630.7	800.5	970.2	1174.9	1379.6	1582.6	1787.3	1983.7	2131.8	2198.3
70°	399.4	532.5	667.3	800.5	986.8	1173.2	1359.6	1546.0	1719.1	1882.1	1945.4
72.5°	347.8	451.0	555.8	659.0	792.1	923.6	1056.7	1188.2	1392.9	1556.0	1617.5
75°	296.2	371.1	444.3	519.2	610.7	702.3	792.1	883.7	1028.4	1174.9	1236.5
77.5°	228.0	277.9	326.2	374.4	437.7	499.2	562.5	624.1	725.6	835.4	867.0
80°	158.1	186.4	213.0	241.3	291.2	341.1	391.1	441.0	507.6	569.1	617.4
82.5°	98.2	116.5	133.1	149.8	189.7	229.7	267.9	307.9	334.5	337.8	386.1
85°	63.2	74.9	84.9	94.9	118.2	143.1	166.4	189.7	169.7	158.1	188.0
87.5°	25.0	31.6	36.6	41.6	39.9	38.3	36.6	34.9	30.0	26.6	33.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988
 CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2
2.5°	1283.1	1288.0	1293.0	1296.4	1301.4	1303.0	1304.7	1304.7	1306.3	1308.0	1311.3
5°	1344.6	1354.6	1364.6	1372.9	1382.9	1391.2	1397.9	1406.2	1412.9	1412.9	1411.2
7.5°	1293.0	1318.0	1343.0	1367.9	1392.9	1411.2	1427.8	1446.1	1462.8	1466.1	1469.4
10°	1224.8	1251.4	1276.4	1303.0	1328.0	1356.3	1382.9	1409.5	1437.8	1442.8	1449.5
12.5°	1161.6	1193.2	1224.8	1254.8	1286.4	1306.3	1326.3	1344.6	1364.6	1377.9	1391.2
15°	1159.9	1186.5	1213.2	1238.1	1264.7	1276.4	1288.0	1298.0	1309.7	1309.7	1311.3
17.5°	1198.2	1214.8	1231.5	1246.4	1263.1	1264.7	1268.1	1269.7	1271.4	1266.4	1261.4
20°	1273.1	1279.7	1286.4	1293.0	1299.7	1288.0	1278.1	1266.4	1254.8	1241.4	1229.8
22.5°	1382.9	1367.9	1352.9	1338.0	1323.0	1303.0	1281.4	1261.4	1239.8	1223.1	1206.5
25°	1486.1	1467.8	1449.5	1431.2	1412.9	1369.6	1326.3	1281.4	1238.1	1219.8	1201.5
27.5°	1624.2	1595.9	1567.6	1539.3	1511.0	1452.8	1394.5	1336.3	1278.1	1246.4	1216.5
30°	1657.5	1625.9	1594.2	1561.0	1529.3	1472.8	1417.8	1361.3	1304.7	1268.1	1233.1
32.5°	1705.7	1669.1	1632.5	1595.9	1559.3	1504.4	1449.5	1392.9	1338.0	1304.7	1269.7
35°	1785.6	1744.0	1702.4	1659.1	1617.5	1561.0	1506.0	1449.5	1392.9	1354.6	1318.0
37.5°	1853.8	1805.6	1757.3	1709.1	1660.8	1610.9	1559.3	1509.4	1457.8	1419.5	1382.9
40°	1930.4	1877.1	1823.9	1772.3	1719.1	1672.5	1625.9	1577.6	1531.0	1501.1	1471.1
42.5°	1997.0	1932.1	1868.8	1805.6	1740.7	1709.1	1679.1	1647.5	1615.9	1600.9	1584.3
45°	2043.6	1983.7	1922.1	1862.2	1802.3	1779.0	1755.7	1732.4	1709.1	1724.0	1739.0
47.5°	2063.5	2015.3	1968.7	1922.1	1873.8	1882.1	1890.5	1897.1	1905.4	1925.4	1947.0
50°	2081.8	2055.2	2026.9	2000.3	1972.0	2003.6	2033.6	2065.2	2096.8	2138.4	2180.0
52.5°	2118.4	2103.5	2090.2	2075.2	2060.2	2115.1	2170.0	2225.0	2279.9	2326.5	2373.1
55°	2228.3	2216.6	2205.0	2191.7	2180.0	2258.2	2334.8	2413.0	2491.2	2539.5	2587.7
57.5°	2379.7	2373.1	2364.7	2358.1	2349.8	2426.3	2501.2	2576.1	2652.6	2699.2	2747.5
60°	2494.5	2496.2	2496.2	2497.9	2497.9	2556.1	2614.4	2674.3	2732.5	2772.5	2814.1
62.5°	2556.1	2552.8	2549.5	2546.1	2542.8	2591.1	2639.3	2687.6	2735.8	2765.8	2795.8
65°	2489.6	2507.9	2526.2	2544.5	2562.8	2569.4	2574.4	2581.1	2586.1	2604.4	2622.7
67.5°	2266.6	2303.2	2338.1	2374.7	2409.7	2384.7	2361.4	2336.4	2311.5	2316.5	2319.8
70°	2018.6	2060.2	2103.5	2145.1	2186.7	2128.4	2070.2	2010.3	1952.0	1932.1	1912.1
72.5°	1702.4	1739.0	1777.3	1813.9	1850.5	1779.0	1709.1	1637.5	1566.0	1531.0	1496.1
75°	1301.4	1344.6	1389.6	1432.8	1476.1	1396.2	1314.7	1234.8	1153.2	1129.9	1108.3
77.5°	948.6	1000.1	1051.7	1103.3	1154.9	1083.4	1011.8	938.6	867.0	853.7	840.4
80°	690.6	730.6	768.8	808.8	847.0	805.4	763.8	722.2	680.6	679.0	677.3
82.5°	466.0	500.9	534.2	569.1	602.4	585.8	570.8	554.2	537.5	554.2	572.5
85°	239.6	287.9	337.8	386.1	434.3	429.3	426.0	421.0	416.0	437.7	457.6
87.5°	48.3	89.9	131.5	171.4	213.0	203.0	193.0	181.4	171.4	178.1	183.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2
2.5°	1313.0	1314.7	1314.7	1314.7	1314.7	1314.7	1311.3	1309.7	1306.3	1303.0	1298.0
5°	1411.2	1409.5	1402.9	1396.2	1387.9	1381.2	1376.2	1369.6	1364.6	1357.9	1348.0
7.5°	1472.8	1476.1	1464.4	1454.5	1442.8	1431.2	1419.5	1407.9	1396.2	1384.6	1361.3
10°	1454.5	1459.4	1452.8	1446.1	1437.8	1431.2	1417.8	1402.9	1389.6	1374.6	1346.3
12.5°	1402.9	1416.2	1412.9	1409.5	1406.2	1402.9	1394.5	1384.6	1376.2	1366.3	1334.6
15°	1311.3	1311.3	1313.0	1314.7	1314.7	1316.3	1318.0	1319.7	1321.3	1323.0	1304.7
17.5°	1256.4	1251.4	1251.4	1251.4	1251.4	1251.4	1258.1	1266.4	1273.1	1279.7	1274.7
20°	1216.5	1204.8	1203.2	1203.2	1201.5	1199.8	1211.5	1224.8	1236.5	1248.1	1254.8
22.5°	1189.9	1173.2	1171.6	1169.9	1168.2	1166.6	1181.5	1196.5	1211.5	1226.5	1249.8
25°	1183.2	1164.9	1166.6	1168.2	1168.2	1169.9	1181.5	1193.2	1204.8	1216.5	1256.4
27.5°	1184.9	1154.9	1156.6	1158.2	1158.2	1159.9	1178.2	1194.9	1213.2	1229.8	1279.7
30°	1196.5	1161.6	1158.2	1154.9	1151.6	1148.3	1173.2	1198.2	1223.1	1248.1	1286.4
32.5°	1236.5	1203.2	1194.9	1186.5	1178.2	1169.9	1199.8	1228.1	1258.1	1286.4	1318.0
35°	1279.7	1243.1	1239.8	1236.5	1231.5	1228.1	1254.8	1283.1	1309.7	1336.3	1364.6
37.5°	1344.6	1308.0	1304.7	1299.7	1296.4	1291.4	1321.3	1349.6	1379.6	1407.9	1432.8
40°	1441.1	1411.2	1409.5	1409.5	1407.9	1406.2	1429.5	1454.5	1477.8	1501.1	1517.7
42.5°	1569.3	1554.3	1559.3	1566.0	1570.9	1575.9	1594.2	1614.2	1632.5	1650.8	1645.8
45°	1754.0	1769.0	1770.6	1772.3	1774.0	1775.6	1780.6	1787.3	1792.3	1797.3	1777.3
47.5°	1967.0	1987.0	1997.0	2007.0	2015.3	2025.3	2018.6	2010.3	2003.6	1995.3	1945.4
50°	2220.0	2261.6	2259.9	2258.2	2254.9	2253.2	2239.9	2226.6	2211.6	2198.3	2125.1
52.5°	2419.7	2466.3	2474.6	2482.9	2491.2	2499.5	2474.6	2449.6	2423.0	2398.0	2306.5
55°	2634.3	2682.6	2684.3	2685.9	2685.9	2687.6	2652.6	2617.7	2581.1	2546.1	2451.3
57.5°	2794.1	2840.7	2835.7	2832.4	2827.4	2822.4	2780.8	2739.2	2697.6	2656.0	2561.1
60°	2854.0	2893.9	2884.0	2874.0	2862.3	2852.3	2820.7	2789.1	2755.8	2724.2	2632.7
62.5°	2825.7	2855.7	2840.7	2827.4	2812.4	2797.4	2757.5	2715.9	2675.9	2634.3	2567.8
65°	2639.3	2657.6	2637.7	2619.4	2601.0	2581.1	2547.8	2514.5	2479.6	2446.3	2401.4
67.5°	2324.8	2328.1	2326.5	2324.8	2323.1	2321.5	2273.2	2225.0	2175.0	2126.8	2123.4
70°	1893.8	1873.8	1877.1	1882.1	1885.5	1888.8	1852.2	1817.2	1780.6	1744.0	1760.7
72.5°	1461.1	1426.2	1434.5	1444.5	1452.8	1461.1	1431.2	1402.9	1372.9	1343.0	1366.3
75°	1085.0	1063.4	1071.7	1081.7	1090.0	1098.3	1086.7	1075.0	1061.7	1050.1	1071.7
77.5°	827.1	813.8	815.4	815.4	817.1	817.1	818.8	822.1	823.7	825.4	848.7
80°	674.0	672.3	670.6	669.0	665.7	664.0	680.6	697.3	713.9	730.6	742.2
82.5°	589.1	605.7	595.8	587.4	577.5	567.5	582.4	597.4	612.4	627.4	622.4
85°	479.3	499.2	480.9	462.6	442.7	424.4	437.7	449.3	462.6	474.3	467.6
87.5°	189.7	194.7	164.7	136.5	106.5	76.6	121.5	164.7	209.7	252.9	259.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2	1198.2
2.5°	1293.0	1286.4	1281.4	1279.7	1276.4	1274.7	1271.4	1268.1	1263.1	1259.8	1254.8
5°	1336.3	1326.3	1314.7	1298.0	1283.1	1266.4	1249.8	1234.8	1219.8	1203.2	1188.2
7.5°	1338.0	1314.7	1291.4	1269.7	1246.4	1224.8	1201.5	1181.5	1159.9	1138.3	1118.3
10°	1319.7	1291.4	1263.1	1234.8	1208.2	1179.9	1151.6	1128.3	1103.3	1078.4	1055.1
12.5°	1304.7	1273.1	1241.4	1208.2	1176.5	1143.3	1110.0	1086.7	1063.4	1040.1	1016.8
15°	1286.4	1266.4	1248.1	1218.1	1188.2	1158.2	1128.3	1096.7	1066.7	1035.1	1003.5
17.5°	1271.4	1266.4	1261.4	1241.4	1221.5	1199.8	1179.9	1148.3	1116.6	1083.4	1051.7
20°	1263.1	1269.7	1276.4	1266.4	1256.4	1244.8	1234.8	1211.5	1188.2	1163.2	1139.9
22.5°	1273.1	1298.0	1321.3	1323.0	1326.3	1328.0	1329.6	1308.0	1286.4	1263.1	1241.4
25°	1296.4	1336.3	1376.2	1397.9	1419.5	1442.8	1464.4	1451.1	1437.8	1424.5	1411.2
27.5°	1328.0	1377.9	1427.8	1459.4	1489.4	1521.0	1552.6	1551.0	1549.3	1546.0	1544.3
30°	1323.0	1361.3	1399.5	1437.8	1476.1	1514.4	1552.6	1572.6	1590.9	1610.9	1630.9
32.5°	1351.3	1382.9	1416.2	1456.1	1496.1	1537.7	1577.6	1619.2	1659.1	1700.7	1742.4
35°	1394.5	1422.8	1452.8	1496.1	1541.0	1584.3	1629.2	1679.1	1730.7	1782.3	1832.2
37.5°	1459.4	1484.4	1511.0	1547.6	1585.9	1622.5	1660.8	1734.0	1807.3	1882.1	1955.4
40°	1534.3	1551.0	1567.6	1602.6	1637.5	1672.5	1707.4	1798.9	1890.5	1982.0	2073.5
42.5°	1642.5	1637.5	1632.5	1660.8	1690.8	1719.1	1749.0	1832.2	1915.4	1998.6	2081.8
45°	1757.3	1737.4	1717.4	1730.7	1745.7	1759.0	1774.0	1858.8	1943.7	2030.2	2115.1
47.5°	1895.5	1845.5	1795.6	1784.0	1772.3	1759.0	1747.3	1838.9	1930.4	2023.6	2115.1
50°	2051.9	1977.0	1903.8	1873.8	1842.2	1812.2	1780.6	1855.5	1932.1	2008.6	2083.5
52.5°	2215.0	2121.8	2030.2	1983.7	1937.1	1888.8	1842.2	1905.4	1970.3	2035.2	2098.5
55°	2354.8	2259.9	2163.4	2108.5	2053.5	1998.6	1943.7	2007.0	2070.2	2133.4	2196.7
57.5°	2466.3	2371.4	2276.5	2225.0	2171.7	2120.1	2066.9	2126.8	2188.3	2249.9	2309.8
60°	2542.8	2451.3	2359.7	2309.8	2259.9	2210.0	2160.1	2231.6	2303.2	2376.4	2447.9
62.5°	2502.9	2436.3	2369.7	2348.1	2326.5	2303.2	2281.5	2349.8	2416.3	2484.6	2552.8
65°	2356.4	2311.5	2266.6	2288.2	2311.5	2333.1	2356.4	2401.4	2446.3	2492.9	2537.8
67.5°	2118.4	2115.1	2110.1	2158.4	2206.6	2256.6	2304.8	2334.8	2363.1	2393.0	2423.0
70°	1777.3	1795.6	1812.2	1895.5	1978.7	2061.9	2145.1	2156.7	2168.4	2180.0	2191.7
72.5°	1391.2	1414.5	1439.5	1549.3	1657.5	1767.3	1877.1	1870.5	1863.8	1855.5	1848.9
75°	1095.0	1116.6	1139.9	1241.4	1343.0	1444.5	1546.0	1517.7	1491.1	1462.8	1434.5
77.5°	873.7	897.0	921.9	1016.8	1111.6	1208.2	1303.0	1234.8	1166.6	1098.3	1030.1
80°	752.2	763.8	773.8	838.7	902.0	966.9	1031.8	961.9	890.3	818.8	748.9
82.5°	617.4	610.7	605.7	644.0	682.3	720.6	758.8	692.3	625.7	557.5	490.9
85°	461.0	454.3	447.7	467.6	487.6	509.2	529.2	452.6	376.1	297.9	221.3
87.5°	267.9	274.6	281.2	302.9	324.5	347.8	369.4	291.2	213.0	133.1	54.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988
 CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675988
 CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1198.2	1198.2
2.5°	1244.8	1236.5
5°	1176.5	1164.9
7.5°	1101.7	1086.7
10°	1033.4	1013.5
12.5°	990.2	965.2
15°	973.5	943.6
17.5°	1023.4	995.2
20°	1100.0	1061.7
22.5°	1193.2	1146.6
25°	1354.6	1298.0
27.5°	1486.1	1427.8
30°	1567.6	1504.4
32.5°	1657.5	1574.3
35°	1750.7	1670.8
37.5°	1863.8	1774.0
40°	1980.3	1887.1
42.5°	2020.3	1960.4
45°	2058.5	2002.0
47.5°	2066.9	2020.3
50°	2075.2	2068.5
52.5°	2098.5	2096.8
55°	2198.3	2200.0
57.5°	2321.5	2331.5
60°	2434.6	2423.0
62.5°	2492.9	2433.0
65°	2452.9	2369.7
67.5°	2333.1	2243.3
70°	2070.2	1948.7
72.5°	1742.4	1635.8
75°	1343.0	1253.1
77.5°	955.2	880.3
80°	672.3	597.4
82.5°	431.0	371.1
85°	194.7	169.7
87.5°	54.9	53.3
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P675988

CATALOG NUMBER: CCW-SA-1C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)