

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675997

Luminaire Tested: **CCW-SA-1A-750-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P675997
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-1A-750-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @350mA w/
SLR distribution lens
Light Source: (16) 5000K CCT, 70 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2322.4 lumens
Efficiency: N/A
Efficacy: 129.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 18
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 3.3 fc
 Type IV - Short - N/A

REPORT NUMBER: P675997
CATALOG NUMBER: CCW-SA-1A-750-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	477.9	0.0	477.9
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	1844.5	0.0	1844.5
	% Fixture	79.4	0.0	79.4
Total	Lumens	2322.4	0.0	2322.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.6	2.5
10°-20°	121.7	5.2
20°-30°	178.0	7.7
30°-40°	250.8	10.8
40°-50°	344.6	14.8
50°-60°	469.7	20.2
60°-70°	514.1	22.1
70°-80°	296.9	12.8
80°-90°	89.0	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2322.4	100.0
0°-180°	2322.4	100.0

Coefficient of Utilization



REPORT NUMBER: P675997


CATALOG NUMBER: CCW-SA-1A-750-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	238.5	10.3			
FM	(30°-60°)	847.5	36.5			
FH	(60°-80°)	682.9	29.4			G1/1800
FVH	(80°-90°)	75.6	3.3			G1/100
BL	(0°-30°)	118.8	5.1	B1/500		
BM	(30°-60°)	217.6	9.4	B0/220		
BH	(60°-80°)	128.1	5.5	B1/500		G1/500
BVH	(80°-90°)	13.4	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6
2.5°	765.3	761.2	758.1	755.0	750.9	747.8	743.7	739.6	734.4	730.3	725.1
5°	721.0	708.7	696.3	689.1	680.8	673.6	665.4	656.1	646.9	636.6	627.3
7.5°	672.6	657.2	641.7	629.3	616.0	603.6	590.2	578.9	567.5	556.2	544.9
10°	627.3	612.9	598.4	583.0	566.5	551.1	534.6	519.1	503.7	488.2	472.8
12.5°	597.4	579.9	563.4	545.9	529.4	511.9	494.4	480.0	465.6	450.1	435.7
15°	584.0	567.5	552.1	534.6	517.1	499.6	482.1	465.6	450.1	433.6	417.2
17.5°	616.0	592.3	568.6	545.9	523.3	500.6	477.9	457.3	436.7	416.1	395.5
20°	657.2	627.3	598.4	570.6	541.8	514.0	485.1	456.3	427.5	398.6	369.8
22.5°	709.7	675.7	642.7	606.7	569.6	533.6	496.5	460.4	424.4	387.3	351.2
25°	803.4	763.3	723.1	671.6	619.0	567.5	515.0	467.6	421.3	373.9	326.5
27.5°	883.8	829.2	775.6	713.8	652.0	590.2	528.4	473.8	420.3	365.7	311.1
30°	931.1	877.6	824.0	748.8	674.7	599.5	524.3	463.5	403.8	343.0	282.2
32.5°	974.4	914.7	854.9	772.5	689.1	606.7	523.3	456.3	390.4	323.4	256.5
35°	1034.1	968.2	903.3	807.5	711.8	616.0	520.2	451.2	381.1	312.1	242.1
37.5°	1098.0	1016.6	936.3	830.2	724.1	618.0	511.9	443.9	376.0	308.0	240.0
40°	1168.1	1069.2	971.3	853.9	737.5	620.1	502.7	434.7	366.7	297.7	229.7
42.5°	1213.4	1106.3	999.1	872.4	746.8	620.1	493.4	426.4	359.5	291.5	224.5
45°	1239.1	1135.1	1032.1	895.1	758.1	621.1	484.1	418.2	352.3	285.3	219.4
47.5°	1250.5	1153.6	1056.8	912.6	769.4	625.2	481.0	414.1	346.1	279.1	211.2
50°	1280.3	1194.8	1109.3	954.8	801.4	646.9	492.4	420.3	349.2	277.1	205.0
52.5°	1297.8	1224.7	1151.6	992.9	834.3	675.7	517.1	436.7	356.4	276.0	195.7
55°	1361.7	1291.7	1221.6	1052.7	882.7	713.8	543.9	455.3	366.7	277.1	188.5
57.5°	1443.1	1368.9	1295.8	1113.5	931.1	748.8	566.5	471.8	376.0	281.2	185.4
60°	1499.7	1427.6	1356.5	1162.9	968.2	774.6	579.9	481.0	382.1	282.2	183.3
62.5°	1505.9	1413.2	1321.5	1133.0	944.5	755.0	566.5	470.7	374.9	278.1	182.3
65°	1466.8	1358.6	1250.5	1070.2	889.9	709.7	529.4	441.9	354.3	265.7	178.2
67.5°	1388.5	1261.8	1135.1	970.3	805.5	640.7	475.9	400.7	326.5	251.3	176.1
70°	1206.2	1094.9	984.7	841.5	699.4	556.2	413.0	351.2	290.5	228.7	166.9
72.5°	1012.5	908.5	805.5	689.1	573.7	457.3	340.9	294.6	248.2	200.9	154.5
75°	775.6	697.3	620.1	533.6	447.0	359.5	273.0	239.0	205.0	171.0	137.0
77.5°	544.9	502.7	461.5	396.6	331.7	266.8	201.9	179.2	156.6	133.9	111.2
80°	369.8	346.1	323.4	277.1	230.7	183.3	137.0	122.6	107.1	92.7	77.3
82.5°	229.7	228.7	226.6	194.7	162.7	130.8	98.9	86.5	75.2	62.8	50.5
85°	105.1	122.6	139.1	121.5	104.0	86.5	69.0	60.8	52.5	43.3	35.0
87.5°	33.0	40.2	46.4	44.3	41.2	39.1	36.1	30.9	25.8	20.6	15.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997
 CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6
2.5°	721.0	717.9	713.8	709.7	704.5	700.4	695.3	690.1	689.1	687.0	686.0
5°	621.1	614.9	607.7	601.5	595.4	588.1	582.0	574.8	569.6	563.4	558.3
7.5°	533.6	523.3	511.9	500.6	490.3	480.0	468.7	458.4	453.2	448.1	442.9
10°	463.5	453.2	443.9	433.6	426.4	420.3	413.0	405.8	399.7	393.5	387.3
12.5°	428.5	421.3	414.1	406.9	398.6	391.4	383.2	374.9	367.7	361.5	354.3
15°	406.9	396.6	385.2	374.9	363.6	353.3	342.0	330.6	322.4	315.2	306.9
17.5°	381.1	365.7	351.2	335.8	323.4	311.1	297.7	285.3	276.0	265.7	256.5
20°	352.3	334.8	316.2	298.7	284.3	270.9	256.5	242.1	231.8	220.4	210.1
22.5°	327.5	304.9	281.2	257.5	242.1	226.6	210.1	194.7	185.4	175.1	165.8
25°	300.8	276.0	250.3	224.5	209.1	192.6	177.2	160.7	153.5	147.3	140.1
27.5°	286.3	261.6	235.9	211.2	196.7	181.3	166.9	151.4	146.3	140.1	134.9
30°	257.5	233.8	209.1	184.4	174.1	164.8	154.5	144.2	142.1	141.1	139.1
32.5°	231.8	207.0	182.3	157.6	148.3	139.1	129.8	120.5	119.5	117.4	116.4
35°	218.4	194.7	170.0	146.3	138.0	128.8	120.5	111.2	109.2	106.1	104.0
37.5°	215.3	190.6	164.8	140.1	131.8	123.6	114.3	106.1	104.0	102.0	99.9
40°	207.0	183.3	160.7	137.0	128.8	120.5	111.2	103.0	100.9	98.9	96.8
42.5°	200.9	178.2	154.5	130.8	123.6	116.4	108.2	100.9	98.9	96.8	93.7
45°	195.7	172.0	147.3	123.6	118.5	113.3	107.1	102.0	99.9	96.8	94.8
47.5°	187.5	164.8	141.1	117.4	112.3	108.2	103.0	97.9	95.8	93.7	91.7
50°	181.3	157.6	133.9	110.2	106.1	102.0	97.9	93.7	93.7	94.8	94.8
52.5°	173.0	150.4	127.7	105.1	100.9	96.8	92.7	88.6	89.6	90.6	91.7
55°	165.8	144.2	121.5	98.9	94.8	90.6	85.5	81.4	82.4	83.4	84.5
57.5°	162.7	140.1	117.4	94.8	90.6	85.5	81.4	76.2	76.2	76.2	76.2
60°	160.7	137.0	114.3	90.6	85.5	81.4	76.2	71.1	70.0	70.0	69.0
62.5°	159.7	136.0	113.3	89.6	83.4	78.3	72.1	65.9	64.9	63.9	62.8
65°	155.5	133.9	111.2	88.6	81.4	75.2	68.0	60.8	59.7	59.7	58.7
67.5°	154.5	131.8	110.2	87.6	80.3	72.1	64.9	56.7	55.6	54.6	53.6
70°	146.3	126.7	106.1	85.5	77.3	70.0	61.8	53.6	52.5	50.5	49.4
72.5°	136.0	118.5	99.9	81.4	73.1	64.9	56.7	48.4	47.4	46.4	44.3
75°	120.5	104.0	87.6	71.1	63.9	57.7	50.5	43.3	42.2	41.2	39.1
77.5°	98.9	85.5	73.1	59.7	54.6	49.4	44.3	39.1	38.1	37.1	35.0
80°	70.0	61.8	54.6	46.4	43.3	39.1	36.1	31.9	31.9	30.9	30.9
82.5°	46.4	42.2	38.1	34.0	31.9	29.9	27.8	25.8	25.8	24.7	24.7
85°	33.0	30.9	27.8	25.8	24.7	22.7	21.6	19.6	19.6	19.6	19.6
87.5°	15.5	15.5	14.4	14.4	13.4	13.4	12.4	11.3	11.3	11.3	11.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6
2.5°	683.9	680.8	677.8	673.6	670.5	666.4	661.3	657.2	652.0	652.0	651.0
5°	552.1	549.0	545.9	541.8	538.7	534.6	531.5	527.4	523.3	523.3	522.2
7.5°	437.8	431.6	425.4	418.2	412.0	407.9	403.8	398.6	394.5	391.4	388.3
10°	381.1	374.9	367.7	361.5	354.3	349.2	344.0	337.8	332.7	328.6	324.5
12.5°	347.1	339.9	332.7	325.5	318.3	311.1	304.9	297.7	290.5	285.3	280.2
15°	298.7	291.5	284.3	277.1	269.9	261.6	253.4	244.1	235.9	231.8	228.7
17.5°	246.2	239.0	230.7	223.5	215.3	209.1	202.9	196.7	190.6	186.4	183.3
20°	198.8	190.6	182.3	174.1	165.8	161.7	157.6	153.5	149.4	146.3	144.2
22.5°	155.5	150.4	146.3	141.1	136.0	132.9	130.8	127.7	124.6	124.6	124.6
25°	132.9	129.8	127.7	124.6	121.5	120.5	119.5	117.4	116.4	115.4	115.4
27.5°	128.8	125.7	122.6	119.5	116.4	115.4	114.3	112.3	111.2	111.2	111.2
30°	137.0	136.0	134.9	133.9	132.9	130.8	127.7	125.7	122.6	120.5	118.5
32.5°	114.3	113.3	113.3	112.3	111.2	113.3	114.3	116.4	117.4	118.5	119.5
35°	100.9	98.9	96.8	94.8	92.7	91.7	90.6	89.6	88.6	88.6	87.6
37.5°	97.9	95.8	93.7	91.7	89.6	88.6	87.6	86.5	85.5	85.5	84.5
40°	94.8	92.7	91.7	89.6	87.6	86.5	85.5	83.4	82.4	81.4	81.4
42.5°	91.7	90.6	88.6	87.6	85.5	84.5	83.4	81.4	80.3	79.3	78.3
45°	91.7	89.6	87.6	85.5	83.4	82.4	80.3	79.3	77.3	77.3	76.2
47.5°	89.6	87.6	85.5	83.4	81.4	80.3	78.3	77.3	75.2	74.2	73.1
50°	94.8	91.7	87.6	84.5	80.3	79.3	77.3	76.2	74.2	73.1	72.1
52.5°	92.7	89.6	85.5	82.4	78.3	76.2	75.2	73.1	71.1	70.0	69.0
55°	85.5	82.4	80.3	77.3	74.2	72.1	70.0	68.0	65.9	64.9	64.9
57.5°	76.2	75.2	74.2	73.1	72.1	70.0	68.0	64.9	62.8	61.8	60.8
60°	68.0	69.0	70.0	71.1	72.1	69.0	65.9	62.8	59.7	58.7	57.7
62.5°	61.8	63.9	65.9	67.0	69.0	65.9	62.8	59.7	56.7	55.6	54.6
65°	57.7	58.7	58.7	59.7	59.7	57.7	56.7	54.6	52.5	51.5	51.5
67.5°	52.5	52.5	52.5	51.5	51.5	50.5	50.5	49.4	48.4	47.4	47.4
70°	47.4	47.4	47.4	46.4	46.4	45.3	45.3	44.3	43.3	43.3	42.2
72.5°	43.3	43.3	42.2	42.2	41.2	41.2	41.2	40.2	40.2	39.1	39.1
75°	38.1	38.1	37.1	37.1	36.1	36.1	36.1	35.0	35.0	35.0	34.0
77.5°	34.0	34.0	33.0	33.0	31.9	31.9	31.9	30.9	30.9	29.9	29.9
80°	29.9	29.9	28.8	28.8	27.8	27.8	26.8	26.8	25.8	25.8	24.7
82.5°	23.7	23.7	23.7	23.7	23.7	22.7	22.7	21.6	20.6	20.6	19.6
85°	19.6	19.6	19.6	18.5	18.5	18.5	17.5	17.5	16.5	15.5	15.5
87.5°	11.3	11.3	11.3	10.3	10.3	10.3	10.3	10.3	10.3	10.3	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997
 CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6
2.5°	651.0	649.9	645.8	641.7	645.8	649.9	649.9	649.9	648.9	648.9	648.9
5°	522.2	521.2	519.1	517.1	517.1	516.0	518.1	520.2	522.2	524.3	526.3
7.5°	384.2	381.1	378.0	374.9	377.0	378.0	381.1	383.2	386.3	388.3	393.5
10°	320.3	316.2	313.1	310.0	308.0	305.9	303.9	302.8	300.8	298.7	300.8
12.5°	274.0	268.8	263.7	257.5	256.5	255.4	253.4	251.3	249.3	247.2	246.2
15°	224.5	220.4	218.4	215.3	211.2	207.0	205.0	203.9	201.9	199.8	198.8
17.5°	179.2	175.1	172.0	168.9	167.9	165.8	165.8	165.8	165.8	165.8	165.8
20°	141.1	138.0	138.0	137.0	137.0	136.0	137.0	138.0	138.0	139.1	140.1
22.5°	123.6	123.6	122.6	121.5	122.6	122.6	123.6	124.6	125.7	126.7	127.7
25°	114.3	113.3	114.3	115.4	115.4	115.4	116.4	116.4	117.4	117.4	117.4
27.5°	110.2	110.2	111.2	111.2	112.3	112.3	112.3	111.2	111.2	110.2	110.2
30°	116.4	114.3	114.3	114.3	113.3	112.3	111.2	111.2	110.2	109.2	108.2
32.5°	120.5	121.5	120.5	118.5	117.4	115.4	114.3	112.3	111.2	109.2	107.1
35°	87.6	86.5	88.6	89.6	90.6	91.7	92.7	93.7	93.7	94.8	94.8
37.5°	84.5	83.4	83.4	82.4	82.4	82.4	82.4	82.4	81.4	81.4	82.4
40°	80.3	79.3	79.3	78.3	78.3	77.3	77.3	77.3	77.3	77.3	77.3
42.5°	77.3	76.2	76.2	76.2	76.2	75.2	75.2	74.2	74.2	73.1	73.1
45°	76.2	75.2	74.2	73.1	73.1	72.1	72.1	72.1	71.1	71.1	71.1
47.5°	72.1	71.1	71.1	70.0	70.0	69.0	69.0	69.0	68.0	68.0	68.0
50°	70.0	69.0	69.0	68.0	68.0	67.0	67.0	67.0	65.9	65.9	65.9
52.5°	67.0	65.9	65.9	65.9	64.9	63.9	63.9	63.9	62.8	62.8	62.8
55°	63.9	62.8	62.8	62.8	61.8	60.8	60.8	60.8	59.7	59.7	59.7
57.5°	59.7	58.7	58.7	57.7	57.7	57.7	57.7	57.7	56.7	56.7	56.7
60°	56.7	55.6	55.6	54.6	54.6	53.6	53.6	53.6	53.6	53.6	53.6
62.5°	53.6	52.5	51.5	50.5	51.5	51.5	51.5	51.5	50.5	50.5	50.5
65°	50.5	49.4	48.4	47.4	47.4	47.4	47.4	47.4	47.4	47.4	47.4
67.5°	46.4	45.3	44.3	43.3	44.3	44.3	44.3	44.3	44.3	44.3	44.3
70°	42.2	41.2	41.2	40.2	40.2	39.1	39.1	40.2	40.2	40.2	40.2
72.5°	38.1	37.1	37.1	36.1	36.1	36.1	36.1	36.1	36.1	36.1	36.1
75°	34.0	33.0	33.0	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.9
77.5°	28.8	27.8	27.8	27.8	27.8	27.8	27.8	28.8	28.8	28.8	28.8
80°	24.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7
82.5°	19.6	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5
85°	14.4	13.4	13.4	13.4	14.4	14.4	14.4	14.4	14.4	14.4	14.4
87.5°	9.3	8.2	8.2	8.2	9.3	9.3	9.3	9.3	8.2	8.2	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6
2.5°	648.9	648.9	648.9	647.9	646.9	645.8	644.8	647.9	649.9	653.0	655.1
5°	527.4	529.4	530.5	533.6	536.6	539.7	542.8	544.9	546.9	548.0	550.0
7.5°	397.6	402.7	406.9	411.0	415.1	418.2	422.3	425.4	428.5	431.6	434.7
10°	301.8	303.9	304.9	309.0	312.1	316.2	319.3	322.4	325.5	327.5	330.6
12.5°	245.1	243.1	242.1	242.1	242.1	242.1	242.1	244.1	246.2	248.2	250.3
15°	197.8	196.7	195.7	194.7	193.6	191.6	190.6	192.6	194.7	196.7	198.8
17.5°	165.8	165.8	165.8	164.8	163.8	162.7	161.7	162.7	163.8	163.8	164.8
20°	142.1	143.2	144.2	145.2	145.2	146.3	146.3	147.3	148.3	148.3	149.4
22.5°	127.7	128.8	128.8	128.8	129.8	129.8	129.8	130.8	131.8	132.9	133.9
25°	116.4	116.4	115.4	115.4	116.4	116.4	116.4	116.4	117.4	117.4	117.4
27.5°	110.2	109.2	109.2	109.2	109.2	108.2	108.2	108.2	108.2	108.2	108.2
30°	107.1	106.1	105.1	104.0	104.0	103.0	102.0	102.0	102.0	102.0	102.0
32.5°	106.1	104.0	102.0	100.9	100.9	99.9	98.9	97.9	97.9	96.8	95.8
35°	94.8	93.7	93.7	92.7	91.7	90.6	89.6	89.6	89.6	88.6	88.6
37.5°	82.4	83.4	83.4	83.4	84.5	84.5	84.5	84.5	85.5	85.5	85.5
40°	77.3	77.3	77.3	78.3	79.3	79.3	80.3	80.3	81.4	81.4	81.4
42.5°	73.1	72.1	72.1	73.1	73.1	74.2	74.2	75.2	76.2	76.2	77.3
45°	71.1	70.0	70.0	70.0	70.0	69.0	69.0	70.0	71.1	72.1	73.1
47.5°	67.0	67.0	65.9	65.9	65.9	65.9	65.9	65.9	67.0	67.0	67.0
50°	64.9	64.9	63.9	63.9	63.9	63.9	63.9	63.9	63.9	63.9	63.9
52.5°	62.8	61.8	61.8	61.8	61.8	60.8	60.8	60.8	60.8	60.8	60.8
55°	59.7	58.7	58.7	58.7	58.7	58.7	58.7	58.7	59.7	59.7	59.7
57.5°	56.7	55.6	55.6	55.6	56.7	56.7	56.7	56.7	57.7	57.7	57.7
60°	53.6	53.6	53.6	53.6	53.6	53.6	53.6	54.6	54.6	55.6	55.6
62.5°	50.5	50.5	50.5	50.5	51.5	51.5	51.5	51.5	52.5	52.5	52.5
65°	47.4	47.4	47.4	47.4	48.4	48.4	48.4	48.4	48.4	48.4	48.4
67.5°	44.3	44.3	44.3	44.3	44.3	44.3	44.3	45.3	45.3	46.4	46.4
70°	40.2	39.1	39.1	40.2	40.2	41.2	41.2	42.2	42.2	43.3	43.3
72.5°	36.1	36.1	36.1	36.1	36.1	36.1	36.1	37.1	38.1	38.1	39.1
75°	31.9	31.9	31.9	31.9	33.0	33.0	33.0	34.0	34.0	35.0	35.0
77.5°	28.8	27.8	27.8	27.8	28.8	28.8	28.8	29.9	29.9	30.9	30.9
80°	23.7	23.7	23.7	23.7	24.7	24.7	24.7	24.7	25.8	25.8	25.8
82.5°	19.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6	20.6	20.6	20.6
85°	14.4	14.4	14.4	14.4	15.5	15.5	15.5	15.5	15.5	15.5	15.5
87.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	10.3	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997
 CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6
2.5°	655.1	655.1	655.1	655.1	657.2	658.2	660.2	661.3	660.2	659.2	657.2
5°	551.1	552.1	552.1	553.1	553.1	553.1	553.1	553.1	555.2	557.2	559.3
7.5°	435.7	436.7	437.8	438.8	438.8	438.8	437.8	437.8	438.8	438.8	439.8
10°	333.7	337.8	340.9	344.0	342.0	338.9	336.8	333.7	333.7	333.7	332.7
12.5°	252.4	253.4	255.4	256.5	255.4	255.4	254.4	253.4	254.4	256.5	257.5
15°	199.8	199.8	200.9	200.9	201.9	202.9	202.9	203.9	206.0	207.0	209.1
17.5°	165.8	166.9	166.9	167.9	167.9	168.9	168.9	168.9	171.0	173.0	176.1
20°	149.4	149.4	149.4	149.4	149.4	148.3	148.3	147.3	148.3	150.4	151.4
22.5°	133.9	134.9	134.9	134.9	133.9	132.9	130.8	129.8	129.8	130.8	130.8
25°	117.4	116.4	116.4	115.4	115.4	116.4	116.4	116.4	117.4	117.4	118.5
27.5°	108.2	107.1	107.1	106.1	106.1	107.1	107.1	107.1	107.1	107.1	107.1
30°	100.9	100.9	99.9	98.9	99.9	99.9	100.9	100.9	102.0	102.0	103.0
32.5°	95.8	94.8	94.8	93.7	94.8	94.8	95.8	95.8	96.8	97.9	97.9
35°	88.6	88.6	88.6	88.6	88.6	88.6	87.6	87.6	87.6	87.6	87.6
37.5°	84.5	84.5	83.4	82.4	82.4	82.4	82.4	82.4	81.4	80.3	79.3
40°	81.4	80.3	80.3	79.3	78.3	78.3	77.3	76.2	76.2	75.2	75.2
42.5°	77.3	76.2	76.2	75.2	74.2	74.2	73.1	72.1	72.1	72.1	71.1
45°	72.1	72.1	71.1	70.0	70.0	70.0	69.0	69.0	69.0	69.0	68.0
47.5°	67.0	67.0	65.9	65.9	65.9	65.9	64.9	64.9	64.9	64.9	64.9
50°	63.9	63.9	63.9	63.9	63.9	63.9	62.8	62.8	62.8	62.8	62.8
52.5°	60.8	60.8	60.8	60.8	60.8	60.8	60.8	60.8	60.8	60.8	60.8
55°	59.7	59.7	59.7	59.7	59.7	59.7	58.7	58.7	58.7	59.7	59.7
57.5°	57.7	57.7	56.7	56.7	56.7	56.7	56.7	56.7	56.7	56.7	56.7
60°	55.6	55.6	55.6	55.6	55.6	55.6	55.6	55.6	55.6	55.6	55.6
62.5°	52.5	52.5	52.5	52.5	52.5	53.6	53.6	53.6	53.6	53.6	52.5
65°	48.4	49.4	49.4	49.4	49.4	49.4	49.4	49.4	49.4	49.4	49.4
67.5°	46.4	46.4	46.4	46.4	46.4	46.4	46.4	46.4	46.4	46.4	46.4
70°	43.3	43.3	42.2	42.2	42.2	43.3	43.3	43.3	43.3	43.3	43.3
72.5°	39.1	39.1	39.1	39.1	39.1	39.1	39.1	39.1	39.1	40.2	40.2
75°	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0	35.0
77.5°	30.9	30.9	29.9	29.9	29.9	30.9	30.9	30.9	30.9	31.9	31.9
80°	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8	26.8	26.8
82.5°	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	21.6	21.6
85°	15.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	17.5	17.5
87.5°	10.3	10.3	10.3	10.3	10.3	10.3	9.3	9.3	9.3	9.3	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997
 CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6
2.5°	656.1	657.2	658.2	658.2	659.2	660.2	660.2	664.4	668.5	670.5	672.6
5°	561.4	560.3	560.3	559.3	558.3	561.4	564.5	570.6	576.8	577.8	579.9
7.5°	439.8	440.9	441.9	441.9	442.9	439.8	435.7	436.7	437.8	442.9	447.0
10°	332.7	333.7	334.8	334.8	335.8	334.8	332.7	335.8	338.9	343.0	348.1
12.5°	258.5	261.6	264.7	266.8	269.9	271.9	273.0	277.1	280.2	285.3	290.5
15°	211.2	213.2	215.3	217.3	219.4	221.5	223.5	227.6	231.8	237.9	244.1
17.5°	178.2	178.2	179.2	179.2	179.2	181.3	183.3	185.4	186.4	192.6	198.8
20°	152.4	151.4	150.4	149.4	148.3	150.4	151.4	152.4	153.5	157.6	160.7
22.5°	130.8	130.8	131.8	131.8	131.8	130.8	128.8	129.8	129.8	131.8	134.9
25°	118.5	118.5	118.5	117.4	117.4	118.5	119.5	119.5	118.5	119.5	120.5
27.5°	107.1	108.2	108.2	109.2	109.2	110.2	110.2	110.2	110.2	111.2	112.3
30°	103.0	103.0	104.0	104.0	104.0	105.1	106.1	106.1	106.1	107.1	109.2
32.5°	98.9	99.9	100.9	102.0	103.0	104.0	104.0	105.1	105.1	106.1	107.1
35°	87.6	86.5	86.5	85.5	84.5	84.5	84.5	84.5	83.4	84.5	84.5
37.5°	78.3	78.3	78.3	77.3	77.3	78.3	78.3	78.3	78.3	79.3	79.3
40°	74.2	74.2	74.2	74.2	74.2	74.2	74.2	75.2	75.2	76.2	77.3
42.5°	71.1	71.1	71.1	71.1	71.1	72.1	72.1	72.1	72.1	73.1	73.1
45°	68.0	68.0	68.0	68.0	68.0	68.0	68.0	69.0	69.0	70.0	71.1
47.5°	64.9	64.9	64.9	64.9	64.9	65.9	67.0	67.0	67.0	68.0	68.0
50°	62.8	62.8	62.8	62.8	62.8	63.9	63.9	64.9	64.9	65.9	67.0
52.5°	60.8	60.8	60.8	60.8	60.8	61.8	61.8	62.8	62.8	63.9	64.9
55°	59.7	59.7	59.7	58.7	58.7	59.7	59.7	60.8	60.8	61.8	61.8
57.5°	56.7	56.7	56.7	56.7	56.7	56.7	56.7	57.7	57.7	58.7	59.7
60°	55.6	55.6	54.6	54.6	53.6	54.6	54.6	55.6	55.6	56.7	56.7
62.5°	52.5	52.5	52.5	51.5	51.5	52.5	52.5	52.5	52.5	53.6	54.6
65°	49.4	49.4	49.4	48.4	48.4	49.4	49.4	49.4	49.4	50.5	51.5
67.5°	46.4	46.4	46.4	45.3	45.3	45.3	45.3	46.4	46.4	47.4	48.4
70°	43.3	43.3	43.3	42.2	42.2	42.2	41.2	42.2	43.3	44.3	44.3
72.5°	40.2	40.2	40.2	39.1	39.1	39.1	38.1	39.1	39.1	40.2	40.2
75°	35.0	35.0	35.0	35.0	35.0	35.0	34.0	34.0	34.0	35.0	35.0
77.5°	31.9	31.9	31.9	30.9	30.9	30.9	29.9	29.9	29.9	30.9	30.9
80°	26.8	26.8	26.8	25.8	25.8	25.8	24.7	24.7	24.7	25.8	25.8
82.5°	21.6	21.6	21.6	20.6	20.6	20.6	19.6	19.6	19.6	20.6	20.6
85°	17.5	17.5	17.5	17.5	17.5	17.5	16.5	16.5	16.5	17.5	18.5
87.5°	8.2	8.2	9.3	9.3	9.3	9.3	8.2	8.2	7.2	7.2	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997
 CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6
2.5°	674.7	676.7	681.9	686.0	691.1	695.3	698.4	702.5	705.6	708.7	710.7
5°	580.9	582.0	587.1	592.3	596.4	601.5	608.7	616.0	623.2	630.4	635.5
7.5°	452.2	456.3	462.5	469.7	475.9	482.1	489.3	497.5	504.7	511.9	519.1
10°	352.3	356.4	362.6	368.8	373.9	380.1	388.3	396.6	404.8	413.0	421.3
12.5°	295.6	300.8	308.0	315.2	321.4	328.6	338.9	348.1	358.5	367.7	378.0
15°	249.3	255.4	264.7	275.0	284.3	293.6	303.9	314.2	323.4	333.7	344.0
17.5°	205.0	211.2	219.4	228.7	236.9	245.1	257.5	268.8	281.2	292.5	303.9
20°	164.8	167.9	176.1	184.4	192.6	200.9	210.1	219.4	228.7	237.9	252.4
22.5°	137.0	139.1	143.2	146.3	150.4	153.5	162.7	172.0	180.3	189.5	202.9
25°	120.5	121.5	124.6	126.7	129.8	131.8	138.0	143.2	149.4	154.5	166.9
27.5°	112.3	113.3	114.3	115.4	116.4	117.4	121.5	125.7	128.8	132.9	144.2
30°	110.2	111.2	114.3	116.4	119.5	121.5	123.6	125.7	127.7	129.8	137.0
32.5°	108.2	109.2	109.2	108.2	108.2	107.1	109.2	110.2	112.3	113.3	119.5
35°	85.5	85.5	86.5	87.6	88.6	89.6	92.7	94.8	97.9	99.9	105.1
37.5°	80.3	80.3	81.4	83.4	84.5	85.5	87.6	89.6	91.7	93.7	98.9
40°	77.3	78.3	79.3	80.3	81.4	82.4	84.5	85.5	87.6	88.6	92.7
42.5°	74.2	74.2	75.2	77.3	78.3	79.3	81.4	82.4	84.5	85.5	89.6
45°	72.1	73.1	74.2	75.2	75.2	76.2	78.3	80.3	81.4	83.4	87.6
47.5°	69.0	69.0	71.1	72.1	74.2	75.2	77.3	78.3	80.3	81.4	85.5
50°	67.0	68.0	70.0	71.1	73.1	74.2	77.3	79.3	82.4	84.5	86.5
52.5°	64.9	65.9	68.0	69.0	71.1	72.1	76.2	80.3	83.4	87.6	87.6
55°	62.8	62.8	64.9	68.0	70.0	72.1	74.2	77.3	79.3	81.4	81.4
57.5°	59.7	60.8	62.8	65.9	68.0	70.0	72.1	74.2	75.2	77.3	76.2
60°	57.7	57.7	60.8	63.9	67.0	70.0	70.0	70.0	69.0	69.0	69.0
62.5°	54.6	55.6	59.7	64.9	69.0	73.1	70.0	67.0	63.9	60.8	61.8
65°	52.5	53.6	55.6	58.7	60.8	62.8	60.8	59.7	57.7	55.6	56.7
67.5°	48.4	49.4	50.5	50.5	51.5	51.5	51.5	51.5	51.5	51.5	52.5
70°	45.3	45.3	45.3	46.4	46.4	46.4	46.4	46.4	46.4	46.4	47.4
72.5°	41.2	41.2	41.2	41.2	41.2	41.2	41.2	41.2	41.2	41.2	42.2
75°	36.1	36.1	36.1	36.1	36.1	36.1	36.1	36.1	36.1	36.1	37.1
77.5°	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.9	30.9	30.9	31.9
80°	26.8	26.8	26.8	26.8	25.8	25.8	25.8	25.8	25.8	25.8	26.8
82.5°	21.6	21.6	21.6	21.6	20.6	20.6	20.6	20.6	19.6	19.6	20.6
85°	19.6	20.6	20.6	21.6	21.6	21.6	20.6	19.6	18.5	17.5	17.5
87.5°	8.2	8.2	8.2	8.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6
2.5°	713.8	715.9	717.9	721.0	725.1	728.2	731.3	737.5	744.7	750.9	757.1
5°	640.7	645.8	651.0	657.2	663.3	668.5	674.7	687.0	699.4	710.7	723.1
7.5°	525.3	532.5	538.7	549.0	558.3	568.6	577.8	593.3	607.7	623.2	637.6
10°	429.5	437.8	446.0	459.4	473.8	487.2	500.6	513.0	526.3	538.7	551.1
12.5°	388.3	397.6	407.9	416.1	425.4	433.6	441.9	456.3	470.7	485.1	499.6
15°	354.3	364.6	374.9	385.2	394.5	404.8	414.1	426.4	439.8	452.2	464.5
17.5°	315.2	325.5	336.8	348.1	359.5	370.8	382.1	399.7	417.2	433.6	451.2
20°	265.7	280.2	293.6	309.0	324.5	339.9	355.4	373.9	392.4	410.0	428.5
22.5°	216.3	229.7	243.1	261.6	280.2	297.7	316.2	340.9	364.6	389.4	413.0
25°	180.3	192.6	205.0	225.6	245.1	265.7	285.3	315.2	344.0	373.9	402.7
27.5°	155.5	166.9	178.2	199.8	221.5	242.1	263.7	296.6	328.6	361.5	393.5
30°	144.2	151.4	158.6	179.2	199.8	219.4	240.0	271.9	303.9	335.8	367.7
32.5°	125.7	131.8	138.0	156.6	175.1	192.6	211.2	244.1	276.0	309.0	340.9
35°	111.2	116.4	121.5	139.1	155.5	173.0	189.5	222.5	255.4	288.4	321.4
37.5°	103.0	108.2	112.3	127.7	144.2	159.7	175.1	208.1	240.0	273.0	304.9
40°	96.8	99.9	104.0	119.5	133.9	149.4	163.8	193.6	224.5	254.4	284.3
42.5°	92.7	96.8	99.9	113.3	127.7	141.1	154.5	183.3	212.2	240.0	268.8
45°	91.7	95.8	99.9	111.2	122.6	132.9	144.2	172.0	199.8	227.6	255.4
47.5°	89.6	92.7	96.8	106.1	114.3	123.6	131.8	159.7	187.5	214.2	242.1
50°	88.6	89.6	91.7	99.9	108.2	116.4	124.6	152.4	180.3	208.1	235.9
52.5°	87.6	87.6	87.6	94.8	102.0	108.2	115.4	143.2	172.0	199.8	227.6
55°	81.4	80.3	80.3	87.6	93.7	100.9	107.1	134.9	162.7	189.5	217.3
57.5°	75.2	74.2	73.1	79.3	85.5	91.7	97.9	125.7	154.5	182.3	210.1
60°	69.0	68.0	68.0	74.2	79.3	85.5	90.6	119.5	147.3	176.1	203.9
62.5°	61.8	62.8	62.8	68.0	74.2	79.3	84.5	113.3	143.2	172.0	200.9
65°	56.7	57.7	57.7	63.9	70.0	76.2	82.4	110.2	139.1	166.9	194.7
67.5°	52.5	53.6	53.6	60.8	67.0	74.2	80.3	105.1	130.8	155.5	180.3
70°	48.4	48.4	49.4	56.7	63.9	71.1	78.3	99.9	121.5	142.1	163.8
72.5°	43.3	44.3	45.3	52.5	58.7	65.9	72.1	91.7	111.2	130.8	150.4
75°	38.1	39.1	40.2	46.4	52.5	58.7	64.9	83.4	100.9	119.5	137.0
77.5°	34.0	35.0	36.1	41.2	46.4	51.5	56.7	70.0	84.5	97.9	111.2
80°	27.8	27.8	28.8	33.0	37.1	40.2	44.3	53.6	62.8	71.1	80.3
82.5°	20.6	21.6	21.6	24.7	26.8	29.9	31.9	37.1	41.2	46.4	50.5
85°	17.5	16.5	16.5	18.5	19.6	21.6	22.7	25.8	27.8	30.9	33.0
87.5°	7.2	6.2	6.2	7.2	9.3	10.3	11.3	11.3	12.4	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6
2.5°	760.2	762.2	765.3	767.4	772.5	776.6	781.8	785.9	789.0	794.2	792.1
5°	732.4	741.6	750.9	760.2	767.4	774.6	780.8	788.0	796.2	811.7	815.8
7.5°	649.9	662.3	673.6	686.0	700.4	714.8	729.3	743.7	757.1	776.6	789.0
10°	568.6	586.1	602.6	620.1	633.5	646.9	659.2	672.6	691.1	710.7	733.4
12.5°	517.1	534.6	552.1	569.6	589.2	607.7	627.3	645.8	663.3	678.8	704.5
15°	483.1	502.7	521.2	539.7	563.4	586.1	609.8	632.4	658.2	678.8	696.3
17.5°	474.8	498.5	521.2	544.9	569.6	594.3	619.0	643.8	669.5	700.4	723.1
20°	460.4	492.4	524.3	556.2	588.1	619.0	651.0	681.9	715.9	753.0	763.3
22.5°	452.2	490.3	529.4	567.5	610.8	655.1	698.4	741.6	777.7	805.5	836.4
25°	451.2	498.5	546.9	594.3	648.9	702.5	757.1	810.6	857.0	884.8	909.5
27.5°	450.1	507.8	564.5	621.1	688.1	754.0	820.9	886.9	930.1	970.3	990.9
30°	437.8	506.8	576.8	645.8	721.0	796.2	871.4	946.6	990.9	1018.7	1029.0
32.5°	422.3	503.7	585.1	666.4	751.9	837.4	921.9	1007.4	1042.4	1066.1	1057.8
35°	410.0	499.6	588.1	676.7	767.4	859.0	949.7	1040.3	1090.8	1123.8	1110.4
37.5°	398.6	492.4	586.1	679.8	785.9	892.0	998.1	1104.2	1152.6	1187.6	1172.2
40°	385.2	485.1	586.1	686.0	807.5	928.1	1049.6	1170.1	1232.9	1262.8	1239.1
42.5°	373.9	477.9	583.0	687.0	816.8	946.6	1076.4	1206.2	1276.2	1318.4	1288.6
45°	359.5	463.5	566.5	670.5	813.7	956.9	1099.0	1242.2	1323.6	1356.5	1315.3
47.5°	344.0	447.0	549.0	651.0	803.4	955.9	1108.3	1260.8	1335.9	1375.1	1337.0
50°	338.9	441.9	543.9	646.9	811.7	977.5	1142.3	1307.1	1361.7	1393.6	1343.2
52.5°	337.8	447.0	557.2	666.4	832.3	997.1	1162.9	1327.7	1372.0	1406.0	1360.7
55°	334.8	453.2	570.6	688.1	861.1	1035.2	1208.2	1381.3	1425.6	1450.3	1416.3
57.5°	337.8	465.6	592.3	720.0	898.2	1076.4	1254.6	1432.8	1486.3	1503.8	1496.6
60°	339.9	475.9	610.8	746.8	920.8	1094.9	1269.0	1443.1	1498.7	1542.0	1550.2
62.5°	334.8	468.7	601.5	735.4	893.0	1050.6	1208.2	1365.8	1457.5	1521.4	1558.4
65°	319.3	442.9	567.5	691.1	836.4	982.6	1127.9	1273.1	1369.9	1464.7	1494.6
67.5°	285.3	390.4	495.4	600.5	727.2	853.9	979.6	1106.3	1227.8	1319.5	1360.7
70°	247.2	329.6	413.0	495.4	610.8	726.2	841.5	956.9	1064.0	1165.0	1204.1
72.5°	215.3	279.1	344.0	407.9	490.3	571.7	654.1	735.4	862.1	963.1	1001.2
75°	183.3	229.7	275.0	321.4	378.0	434.7	490.3	546.9	636.6	727.2	765.3
77.5°	141.1	172.0	201.9	231.8	270.9	309.0	348.1	386.3	449.1	517.1	536.6
80°	97.9	115.4	131.8	149.4	180.3	211.2	242.1	273.0	314.2	352.3	382.1
82.5°	60.8	72.1	82.4	92.7	117.4	142.1	165.8	190.6	207.0	209.1	239.0
85°	39.1	46.4	52.5	58.7	73.1	88.6	103.0	117.4	105.1	97.9	116.4
87.5°	15.5	19.6	22.7	25.8	24.7	23.7	22.7	21.6	18.5	16.5	20.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997
 CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6
2.5°	794.2	797.2	800.3	802.4	805.5	806.5	807.5	807.5	808.6	809.6	811.7
5°	832.3	838.4	844.6	849.8	856.0	861.1	865.2	870.4	874.5	874.5	873.5
7.5°	800.3	815.8	831.2	846.7	862.1	873.5	883.8	895.1	905.4	907.5	909.5
10°	758.1	774.6	790.0	806.5	822.0	839.5	856.0	872.4	889.9	893.0	897.2
12.5°	719.0	738.5	758.1	776.6	796.2	808.6	820.9	832.3	844.6	852.9	861.1
15°	717.9	734.4	750.9	766.3	782.8	790.0	797.2	803.4	810.6	810.6	811.7
17.5°	741.6	751.9	762.2	771.5	781.8	782.8	784.9	785.9	786.9	783.9	780.8
20°	788.0	792.1	796.2	800.3	804.5	797.2	791.1	783.9	776.6	768.4	761.2
22.5°	856.0	846.7	837.4	828.1	818.9	806.5	793.1	780.8	767.4	757.1	746.8
25°	919.8	908.5	897.2	885.8	874.5	847.7	820.9	793.1	766.3	755.0	743.7
27.5°	1005.3	987.8	970.3	952.8	935.3	899.2	863.2	827.1	791.1	771.5	753.0
30°	1025.9	1006.3	986.8	966.2	946.6	911.6	877.6	842.6	807.5	784.9	763.3
32.5°	1055.8	1033.1	1010.5	987.8	965.1	931.1	897.2	862.1	828.1	807.5	785.9
35°	1105.2	1079.5	1053.7	1026.9	1001.2	966.2	932.2	897.2	862.1	838.4	815.8
37.5°	1147.5	1117.6	1087.7	1057.8	1028.0	997.1	965.1	934.2	902.3	878.6	856.0
40°	1194.8	1161.9	1128.9	1097.0	1064.0	1035.2	1006.3	976.5	947.6	929.1	910.5
42.5°	1236.0	1195.9	1156.7	1117.6	1077.4	1057.8	1039.3	1019.7	1000.2	990.9	980.6
45°	1264.9	1227.8	1189.7	1152.6	1115.5	1101.1	1086.7	1072.3	1057.8	1067.1	1076.4
47.5°	1277.2	1247.4	1218.5	1189.7	1159.8	1165.0	1170.1	1174.2	1179.4	1191.7	1205.1
50°	1288.6	1272.1	1254.6	1238.1	1220.6	1240.2	1258.7	1278.3	1297.8	1323.6	1349.3
52.5°	1311.2	1302.0	1293.7	1284.4	1275.2	1309.2	1343.2	1377.1	1411.1	1440.0	1468.8
55°	1379.2	1372.0	1364.8	1356.5	1349.3	1397.7	1445.1	1493.5	1542.0	1571.8	1601.7
57.5°	1472.9	1468.8	1463.7	1459.6	1454.4	1501.8	1548.1	1594.5	1641.9	1670.7	1700.6
60°	1544.0	1545.0	1545.0	1546.1	1546.1	1582.1	1618.2	1655.3	1691.3	1716.0	1741.8
62.5°	1582.1	1580.1	1578.0	1575.9	1573.9	1603.8	1633.6	1663.5	1693.4	1711.9	1730.4
65°	1540.9	1552.3	1563.6	1574.9	1586.2	1590.4	1593.5	1597.6	1600.7	1612.0	1623.3
67.5°	1402.9	1425.6	1447.2	1469.9	1491.5	1476.0	1461.6	1446.2	1430.7	1433.8	1435.9
70°	1249.4	1275.2	1302.0	1327.7	1353.5	1317.4	1281.4	1244.3	1208.2	1195.9	1183.5
72.5°	1053.7	1076.4	1100.1	1122.7	1145.4	1101.1	1057.8	1013.5	969.3	947.6	926.0
75°	805.5	832.3	860.1	886.9	913.6	864.2	813.7	764.3	713.8	699.4	686.0
77.5°	587.1	619.0	651.0	682.9	714.8	670.5	626.3	580.9	536.6	528.4	520.2
80°	427.5	452.2	475.9	500.6	524.3	498.5	472.8	447.0	421.3	420.3	419.2
82.5°	288.4	310.0	330.6	352.3	372.9	362.6	353.3	343.0	332.7	343.0	354.3
85°	148.3	178.2	209.1	239.0	268.8	265.7	263.7	260.6	257.5	270.9	283.3
87.5°	29.9	55.6	81.4	106.1	131.8	125.7	119.5	112.3	106.1	110.2	113.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997
 CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6
2.5°	812.7	813.7	813.7	813.7	813.7	813.7	811.7	810.6	808.6	806.5	803.4
5°	873.5	872.4	868.3	864.2	859.0	854.9	851.8	847.7	844.6	840.5	834.3
7.5°	911.6	913.6	906.4	900.2	893.0	885.8	878.6	871.4	864.2	857.0	842.6
10°	900.2	903.3	899.2	895.1	889.9	885.8	877.6	868.3	860.1	850.8	833.3
12.5°	868.3	876.6	874.5	872.4	870.4	868.3	863.2	857.0	851.8	845.7	826.1
15°	811.7	811.7	812.7	813.7	813.7	814.8	815.8	816.8	817.8	818.9	807.5
17.5°	777.7	774.6	774.6	774.6	774.6	774.6	778.7	783.9	788.0	792.1	789.0
20°	753.0	745.7	744.7	744.7	743.7	742.7	749.9	758.1	765.3	772.5	776.6
22.5°	736.5	726.2	725.1	724.1	723.1	722.1	731.3	740.6	749.9	759.1	773.6
25°	732.4	721.0	722.1	723.1	723.1	724.1	731.3	738.5	745.7	753.0	777.7
27.5°	733.4	714.8	715.9	716.9	716.9	717.9	729.3	739.6	750.9	761.2	792.1
30°	740.6	719.0	716.9	714.8	712.8	710.7	726.2	741.6	757.1	772.5	796.2
32.5°	765.3	744.7	739.6	734.4	729.3	724.1	742.7	760.2	778.7	796.2	815.8
35°	792.1	769.4	767.4	765.3	762.2	760.2	776.6	794.2	810.6	827.1	844.6
37.5°	832.3	809.6	807.5	804.5	802.4	799.3	817.8	835.4	853.9	871.4	886.9
40°	892.0	873.5	872.4	872.4	871.4	870.4	884.8	900.2	914.7	929.1	939.4
42.5°	971.3	962.0	965.1	969.3	972.3	975.4	986.8	999.1	1010.5	1021.8	1018.7
45°	1085.7	1094.9	1096.0	1097.0	1098.0	1099.0	1102.1	1106.3	1109.3	1112.4	1100.1
47.5°	1217.5	1229.9	1236.0	1242.2	1247.4	1253.5	1249.4	1244.3	1240.2	1235.0	1204.1
50°	1374.1	1399.8	1398.8	1397.7	1395.7	1394.7	1386.4	1378.2	1368.9	1360.7	1315.3
52.5°	1497.7	1526.5	1531.7	1536.8	1542.0	1547.1	1531.7	1516.2	1499.7	1484.3	1427.6
55°	1630.5	1660.4	1661.4	1662.5	1662.5	1663.5	1641.9	1620.2	1597.6	1575.9	1517.2
57.5°	1729.4	1758.3	1755.2	1753.1	1750.0	1746.9	1721.2	1695.4	1669.7	1643.9	1585.2
60°	1766.5	1791.2	1785.0	1778.9	1771.7	1765.5	1745.9	1726.3	1705.7	1686.2	1629.5
62.5°	1749.0	1767.5	1758.3	1750.0	1740.7	1731.5	1706.8	1681.0	1656.3	1630.5	1589.3
65°	1633.6	1645.0	1632.6	1621.3	1609.9	1597.6	1577.0	1556.4	1534.7	1514.1	1486.3
67.5°	1439.0	1441.0	1440.0	1439.0	1437.9	1436.9	1407.0	1377.1	1346.2	1316.4	1314.3
70°	1172.2	1159.8	1161.9	1165.0	1167.0	1169.1	1146.4	1124.8	1102.1	1079.5	1089.8
72.5°	904.4	882.7	887.9	894.1	899.2	904.4	885.8	868.3	849.8	831.2	845.7
75°	671.6	658.2	663.3	669.5	674.7	679.8	672.6	665.4	657.2	649.9	663.3
77.5°	511.9	503.7	504.7	504.7	505.7	505.7	506.8	508.8	509.9	510.9	525.3
80°	417.2	416.1	415.1	414.1	412.0	411.0	421.3	431.6	441.9	452.2	459.4
82.5°	364.6	374.9	368.8	363.6	357.4	351.2	360.5	369.8	379.1	388.3	385.2
85°	296.6	309.0	297.7	286.3	274.0	262.7	270.9	278.1	286.3	293.6	289.4
87.5°	117.4	120.5	102.0	84.5	65.9	47.4	75.2	102.0	129.8	156.6	160.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997
 CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6	741.6
2.5°	800.3	796.2	793.1	792.1	790.0	789.0	786.9	784.9	781.8	779.7	776.6
5°	827.1	820.9	813.7	803.4	794.2	783.9	773.6	764.3	755.0	744.7	735.4
7.5°	828.1	813.7	799.3	785.9	771.5	758.1	743.7	731.3	717.9	704.5	692.2
10°	816.8	799.3	781.8	764.3	747.8	730.3	712.8	698.4	682.9	667.5	653.0
12.5°	807.5	788.0	768.4	747.8	728.2	707.6	687.0	672.6	658.2	643.8	629.3
15°	796.2	783.9	772.5	754.0	735.4	716.9	698.4	678.8	660.2	640.7	621.1
17.5°	786.9	783.9	780.8	768.4	756.0	742.7	730.3	710.7	691.1	670.5	651.0
20°	781.8	785.9	790.0	783.9	777.7	770.5	764.3	749.9	735.4	720.0	705.6
22.5°	788.0	803.4	817.8	818.9	820.9	822.0	823.0	809.6	796.2	781.8	768.4
25°	802.4	827.1	851.8	865.2	878.6	893.0	906.4	898.2	889.9	881.7	873.5
27.5°	822.0	852.9	883.8	903.3	921.9	941.4	961.0	960.0	959.0	956.9	955.9
30°	818.9	842.6	866.3	889.9	913.6	937.3	961.0	973.4	984.7	997.1	1009.4
32.5°	836.4	856.0	876.6	901.3	926.0	951.7	976.5	1002.2	1026.9	1052.7	1078.4
35°	863.2	880.7	899.2	926.0	953.8	980.6	1008.4	1039.3	1071.2	1103.2	1134.1
37.5°	903.3	918.8	935.3	957.9	981.6	1004.3	1028.0	1073.3	1118.6	1165.0	1210.3
40°	949.7	960.0	970.3	991.9	1013.5	1035.2	1056.8	1113.5	1170.1	1226.8	1283.4
42.5°	1016.6	1013.5	1010.5	1028.0	1046.5	1064.0	1082.6	1134.1	1185.6	1237.1	1288.6
45°	1087.7	1075.4	1063.0	1071.2	1080.5	1088.7	1098.0	1150.5	1203.1	1256.6	1309.2
47.5°	1173.2	1142.3	1111.4	1104.2	1097.0	1088.7	1081.5	1138.2	1194.8	1252.5	1309.2
50°	1270.0	1223.7	1178.4	1159.8	1140.2	1121.7	1102.1	1148.5	1195.9	1243.2	1289.6
52.5°	1371.0	1313.3	1256.6	1227.8	1199.0	1169.1	1140.2	1179.4	1219.6	1259.7	1298.9
55°	1457.5	1398.8	1339.0	1305.0	1271.1	1237.1	1203.1	1242.2	1281.4	1320.5	1359.6
57.5°	1526.5	1467.8	1409.1	1377.1	1344.2	1312.3	1279.3	1316.4	1354.5	1392.6	1429.7
60°	1573.9	1517.2	1460.6	1429.7	1398.8	1367.9	1337.0	1381.3	1425.6	1470.9	1515.2
62.5°	1549.2	1508.0	1466.8	1453.4	1440.0	1425.6	1412.2	1454.4	1495.6	1537.8	1580.1
65°	1458.5	1430.7	1402.9	1416.3	1430.7	1444.1	1458.5	1486.3	1514.1	1543.0	1570.8
67.5°	1311.2	1309.2	1306.1	1335.9	1365.8	1396.7	1426.6	1445.1	1462.6	1481.2	1499.7
70°	1100.1	1111.4	1121.7	1173.2	1224.7	1276.2	1327.7	1334.9	1342.1	1349.3	1356.5
72.5°	861.1	875.5	891.0	959.0	1025.9	1093.9	1161.9	1157.8	1153.6	1148.5	1144.4
75°	677.8	691.1	705.6	768.4	831.2	894.1	956.9	939.4	922.9	905.4	887.9
77.5°	540.8	555.2	570.6	629.3	688.1	747.8	806.5	764.3	722.1	679.8	637.6
80°	465.6	472.8	479.0	519.1	558.3	598.4	638.6	595.4	551.1	506.8	463.5
82.5°	382.1	378.0	374.9	398.6	422.3	446.0	469.7	428.5	387.3	345.1	303.9
85°	285.3	281.2	277.1	289.4	301.8	315.2	327.5	280.2	232.8	184.4	137.0
87.5°	165.8	170.0	174.1	187.5	200.9	215.3	228.7	180.3	131.8	82.4	34.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997
 CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675997
 CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	741.6	741.6
2.5°	770.5	765.3
5°	728.2	721.0
7.5°	681.9	672.6
10°	639.6	627.3
12.5°	612.9	597.4
15°	602.6	584.0
17.5°	633.5	616.0
20°	680.8	657.2
22.5°	738.5	709.7
25°	838.4	803.4
27.5°	919.8	883.8
30°	970.3	931.1
32.5°	1025.9	974.4
35°	1083.6	1034.1
37.5°	1153.6	1098.0
40°	1225.7	1168.1
42.5°	1250.5	1213.4
45°	1274.1	1239.1
47.5°	1279.3	1250.5
50°	1284.4	1280.3
52.5°	1298.9	1297.8
55°	1360.7	1361.7
57.5°	1436.9	1443.1
60°	1506.9	1499.7
62.5°	1543.0	1505.9
65°	1518.3	1466.8
67.5°	1444.1	1388.5
70°	1281.4	1206.2
72.5°	1078.4	1012.5
75°	831.2	775.6
77.5°	591.2	544.9
80°	416.1	369.8
82.5°	266.8	229.7
85°	120.5	105.1
87.5°	34.0	33.0
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P675997

CATALOG NUMBER: CCW-SA-1A-750-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)