

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P676005

Luminaire Tested: **CCW-SA-2C-750-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P676005
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2C-750-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @615mA w/
SLR distribution lens
Light Source: (32) 5000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7675.1 lumens
Efficiency: N/A
Efficacy: 123.6 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G3

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 10.9 fc

Type IV - Short - N/A

REPORT NUMBER: P676005
CATALOG NUMBER: CCW-SA-2C-750-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1579.2	0.0	1579.2
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	6095.9	0.0	6095.9
	% Fixture	79.4	0.0	79.4
Total	Lumens	7675.1	0.0	7675.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.5	2.5
10°-20°	402.1	5.2
20°-30°	588.3	7.7
30°-40°	828.8	10.8
40°-50°	1138.9	14.8
50°-60°	1552.3	20.2
60°-70°	1699.0	22.1
70°-80°	981.2	12.8
80°-90°	294.1	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7675.1	100.0
0°-180°	7675.1	100.0

Coefficient of Utilization



REPORT NUMBER: P676005


CATALOG NUMBER: CCW-SA-2C-750-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	788.3	10.3			
FM	(30°-60°)	2800.9	36.5			
FH	(60°-80°)	2257.0	29.4			G2/5000
FVH	(80°-90°)	249.8	3.3			G3/500
BL	(0°-30°)	392.6	5.1	B1/500		
BM	(30°-60°)	719.1	9.4	B1/1000		
BH	(60°-80°)	423.2	5.5	B1/500		G1/500
BVH	(80°-90°)	44.3	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G3

Type IV Short



REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0
2.5°	2529.3	2515.6	2505.4	2495.2	2481.6	2471.4	2457.8	2444.2	2427.1	2413.5	2396.5
5°	2382.9	2342.0	2301.2	2277.4	2250.1	2226.3	2199.1	2168.4	2137.8	2103.7	2073.1
7.5°	2222.9	2171.8	2120.8	2079.9	2035.7	1994.8	1950.6	1913.1	1875.7	1838.2	1800.8
10°	2073.1	2025.4	1977.8	1926.7	1872.3	1821.2	1766.7	1715.7	1664.6	1613.6	1562.5
12.5°	1974.4	1916.5	1862.1	1804.2	1749.7	1691.8	1634.0	1586.3	1538.7	1487.6	1439.9
15°	1930.1	1875.7	1824.6	1766.7	1708.9	1651.0	1593.1	1538.7	1487.6	1433.1	1378.7
17.5°	2035.7	1957.4	1879.1	1804.2	1729.3	1654.4	1579.5	1511.4	1443.3	1375.3	1307.2
20°	2171.8	2073.1	1977.8	1885.9	1790.6	1698.7	1603.3	1508.0	1412.7	1317.4	1222.1
22.5°	2345.4	2233.1	2124.2	2005.0	1882.5	1763.3	1640.8	1521.6	1402.5	1279.9	1160.8
25°	2655.2	2522.4	2389.7	2219.5	2045.9	1875.7	1702.1	1545.5	1392.3	1235.7	1079.1
27.5°	2920.7	2740.3	2563.3	2359.1	2154.8	1950.6	1746.3	1565.9	1388.9	1208.5	1028.0
30°	3077.3	2900.3	2723.3	2474.8	2229.7	1981.2	1732.7	1531.9	1334.4	1133.6	932.7
32.5°	3220.3	3022.9	2825.4	2553.1	2277.4	2005.0	1729.3	1508.0	1290.2	1068.9	847.6
35°	3417.7	3199.9	2985.4	2668.8	2352.2	2035.7	1719.1	1491.0	1259.5	1031.4	800.0
37.5°	3628.8	3359.9	3094.3	2743.7	2393.1	2042.5	1691.8	1467.2	1242.5	1017.8	793.2
40°	3860.3	3533.5	3210.1	2822.0	2437.3	2049.3	1661.2	1436.5	1211.9	983.8	759.1
42.5°	4010.0	3656.0	3302.0	2883.3	2468.0	2049.3	1630.6	1409.3	1188.0	963.4	742.1
45°	4095.2	3751.3	3410.9	2958.2	2505.4	2052.7	1599.9	1382.1	1164.2	942.9	725.1
47.5°	4132.6	3812.6	3492.6	3016.0	2542.9	2066.3	1589.7	1368.5	1143.8	922.5	697.8
50°	4231.3	3948.8	3666.2	3155.6	2648.4	2137.8	1627.2	1388.9	1154.0	915.7	677.4
52.5°	4289.2	4047.5	3805.8	3281.6	2757.3	2233.1	1708.9	1443.3	1177.8	912.3	646.8
55°	4500.2	4268.8	4037.3	3479.0	2917.3	2359.1	1797.4	1504.6	1211.9	915.7	623.0
57.5°	4769.2	4524.1	4282.4	3679.8	3077.3	2474.8	1872.3	1559.1	1242.5	929.3	612.7
60°	4956.4	4718.1	4483.2	3843.2	3199.9	2559.9	1916.5	1589.7	1262.9	932.7	605.9
62.5°	4976.8	4670.4	4367.5	3744.5	3121.6	2495.2	1872.3	1555.7	1239.1	919.1	602.5
65°	4847.5	4490.0	4132.6	3536.9	2941.2	2345.4	1749.7	1460.4	1171.0	878.3	588.9
67.5°	4588.7	4170.0	3751.3	3206.7	2662.0	2117.4	1572.7	1324.2	1079.1	830.6	582.1
70°	3986.2	3618.6	3254.3	2781.2	2311.4	1838.2	1365.1	1160.8	960.0	755.7	551.5
72.5°	3346.2	3002.4	2662.0	2277.4	1896.1	1511.4	1126.8	973.6	820.4	663.8	510.6
75°	2563.3	2304.6	2049.3	1763.3	1477.4	1188.0	902.1	789.8	677.4	565.1	452.7
77.5°	1800.8	1661.2	1525.0	1310.6	1096.1	881.7	667.2	592.3	517.4	442.5	367.6
80°	1222.1	1143.8	1068.9	915.7	762.5	605.9	452.7	405.1	354.0	306.4	255.3
82.5°	759.1	755.7	748.9	643.4	537.9	432.3	326.8	285.9	248.5	207.7	166.8
85°	347.2	405.1	459.6	401.7	343.8	285.9	228.1	200.8	173.6	143.0	115.7
87.5°	108.9	132.8	153.2	146.4	136.2	129.4	119.1	102.1	85.1	68.1	51.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005
 CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0
2.5°	2382.9	2372.7	2359.1	2345.4	2328.4	2314.8	2297.8	2280.8	2277.4	2270.5	2267.1
5°	2052.7	2032.3	2008.4	1988.0	1967.6	1943.8	1923.3	1899.5	1882.5	1862.1	1845.0
7.5°	1763.3	1729.3	1691.8	1654.4	1620.4	1586.3	1548.9	1514.8	1497.8	1480.8	1463.8
10°	1531.9	1497.8	1467.2	1433.1	1409.3	1388.9	1365.1	1341.2	1320.8	1300.4	1279.9
12.5°	1416.1	1392.3	1368.5	1344.6	1317.4	1293.6	1266.3	1239.1	1215.3	1194.8	1171.0
15°	1344.6	1310.6	1273.1	1239.1	1201.7	1167.6	1130.2	1092.7	1065.5	1041.7	1014.4
17.5°	1259.5	1208.5	1160.8	1109.7	1068.9	1028.0	983.8	942.9	912.3	878.3	847.6
20°	1164.2	1106.3	1045.1	987.2	939.5	895.3	847.6	800.0	765.9	728.5	694.4
22.5°	1082.5	1007.6	929.3	851.0	800.0	748.9	694.4	643.4	612.7	578.7	548.1
25°	994.0	912.3	827.2	742.1	691.0	636.6	585.5	531.0	507.2	486.8	463.0
27.5°	946.3	864.6	779.5	697.8	650.2	599.1	551.5	500.4	483.4	463.0	445.9
30°	851.0	772.7	691.0	609.3	575.3	544.7	510.6	476.6	469.8	466.4	459.6
32.5°	765.9	684.2	602.5	520.8	490.2	459.6	428.9	398.3	394.9	388.1	384.7
35°	721.7	643.4	561.7	483.4	456.2	425.5	398.3	367.6	360.8	350.6	343.8
37.5°	711.5	629.8	544.7	463.0	435.7	408.5	377.9	350.6	343.8	337.0	330.2
40°	684.2	605.9	531.0	452.7	425.5	398.3	367.6	340.4	333.6	326.8	320.0
42.5°	663.8	588.9	510.6	432.3	408.5	384.7	357.4	333.6	326.8	320.0	309.8
45°	646.8	568.5	486.8	408.5	391.5	374.5	354.0	337.0	330.2	320.0	313.2
47.5°	619.5	544.7	466.4	388.1	371.0	357.4	340.4	323.4	316.6	309.8	303.0
50°	599.1	520.8	442.5	364.2	350.6	337.0	323.4	309.8	309.8	313.2	313.2
52.5°	571.9	497.0	422.1	347.2	333.6	320.0	306.4	292.8	296.2	299.6	303.0
55°	548.1	476.6	401.7	326.8	313.2	299.6	282.5	268.9	272.3	275.7	279.1
57.5°	537.9	463.0	388.1	313.2	299.6	282.5	268.9	251.9	251.9	251.9	251.9
60°	531.0	452.7	377.9	299.6	282.5	268.9	251.9	234.9	231.5	231.5	228.1
62.5°	527.6	449.3	374.5	296.2	275.7	258.7	238.3	217.9	214.5	211.1	207.7
65°	514.0	442.5	367.6	292.8	268.9	248.5	224.7	200.8	197.4	197.4	194.0
67.5°	510.6	435.7	364.2	289.3	265.5	238.3	214.5	187.2	183.8	180.4	177.0
70°	483.4	418.7	350.6	282.5	255.3	231.5	204.2	177.0	173.6	166.8	163.4
72.5°	449.3	391.5	330.2	268.9	241.7	214.5	187.2	160.0	156.6	153.2	146.4
75°	398.3	343.8	289.3	234.9	211.1	190.6	166.8	143.0	139.6	136.2	129.4
77.5°	326.8	282.5	241.7	197.4	180.4	163.4	146.4	129.4	126.0	122.5	115.7
80°	231.5	204.2	180.4	153.2	143.0	129.4	119.1	105.5	105.5	102.1	102.1
82.5°	153.2	139.6	126.0	112.3	105.5	98.7	91.9	85.1	85.1	81.7	81.7
85°	108.9	102.1	91.9	85.1	81.7	74.9	71.5	64.7	64.7	64.7	64.7
87.5°	51.1	51.1	47.7	47.7	44.3	44.3	40.8	37.4	37.4	37.4	37.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0
2.5°	2260.3	2250.1	2239.9	2226.3	2216.1	2202.5	2185.4	2171.8	2154.8	2154.8	2151.4
5°	1824.6	1814.4	1804.2	1790.6	1780.4	1766.7	1756.5	1742.9	1729.3	1729.3	1725.9
7.5°	1446.7	1426.3	1405.9	1382.1	1361.6	1348.0	1334.4	1317.4	1303.8	1293.6	1283.4
10°	1259.5	1239.1	1215.3	1194.8	1171.0	1154.0	1137.0	1116.6	1099.5	1085.9	1072.3
12.5°	1147.2	1123.4	1099.5	1075.7	1051.9	1028.0	1007.6	983.8	960.0	942.9	925.9
15°	987.2	963.4	939.5	915.7	891.9	864.6	837.4	806.8	779.5	765.9	755.7
17.5°	813.6	789.8	762.5	738.7	711.5	691.0	670.6	650.2	629.8	616.1	605.9
20°	657.0	629.8	602.5	575.3	548.1	534.4	520.8	507.2	493.6	483.4	476.6
22.5°	514.0	497.0	483.4	466.4	449.3	439.1	432.3	422.1	411.9	411.9	411.9
25°	439.1	428.9	422.1	411.9	401.7	398.3	394.9	388.1	384.7	381.3	381.3
27.5°	425.5	415.3	405.1	394.9	384.7	381.3	377.9	371.0	367.6	367.6	367.6
30°	452.7	449.3	445.9	442.5	439.1	432.3	422.1	415.3	405.1	398.3	391.5
32.5°	377.9	374.5	374.5	371.0	367.6	374.5	377.9	384.7	388.1	391.5	394.9
35°	333.6	326.8	320.0	313.2	306.4	303.0	299.6	296.2	292.8	292.8	289.3
37.5°	323.4	316.6	309.8	303.0	296.2	292.8	289.3	285.9	282.5	282.5	279.1
40°	313.2	306.4	303.0	296.2	289.3	285.9	282.5	275.7	272.3	268.9	268.9
42.5°	303.0	299.6	292.8	289.3	282.5	279.1	275.7	268.9	265.5	262.1	258.7
45°	303.0	296.2	289.3	282.5	275.7	272.3	265.5	262.1	255.3	255.3	251.9
47.5°	296.2	289.3	282.5	275.7	268.9	265.5	258.7	255.3	248.5	245.1	241.7
50°	313.2	303.0	289.3	279.1	265.5	262.1	255.3	251.9	245.1	241.7	238.3
52.5°	306.4	296.2	282.5	272.3	258.7	251.9	248.5	241.7	234.9	231.5	228.1
55°	282.5	272.3	265.5	255.3	245.1	238.3	231.5	224.7	217.9	214.5	214.5
57.5°	251.9	248.5	245.1	241.7	238.3	231.5	224.7	214.5	207.7	204.2	200.8
60°	224.7	228.1	231.5	234.9	238.3	228.1	217.9	207.7	197.4	194.0	190.6
62.5°	204.2	211.1	217.9	221.3	228.1	217.9	207.7	197.4	187.2	183.8	180.4
65°	190.6	194.0	194.0	197.4	197.4	190.6	187.2	180.4	173.6	170.2	170.2
67.5°	173.6	173.6	173.6	170.2	170.2	166.8	166.8	163.4	160.0	156.6	156.6
70°	156.6	156.6	156.6	153.2	153.2	149.8	149.8	146.4	143.0	143.0	139.6
72.5°	143.0	143.0	139.6	139.6	136.2	136.2	136.2	132.8	132.8	129.4	129.4
75°	126.0	126.0	122.5	122.5	119.1	119.1	119.1	115.7	115.7	115.7	112.3
77.5°	112.3	112.3	108.9	108.9	105.5	105.5	105.5	102.1	102.1	98.7	98.7
80°	98.7	98.7	95.3	95.3	91.9	91.9	88.5	88.5	85.1	85.1	81.7
82.5°	78.3	78.3	78.3	78.3	78.3	74.9	74.9	71.5	68.1	68.1	64.7
85°	64.7	64.7	64.7	61.3	61.3	61.3	57.9	57.9	54.5	51.1	51.1
87.5°	37.4	37.4	37.4	34.0	34.0	34.0	34.0	34.0	34.0	34.0	30.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005
 CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0
2.5°	2151.4	2148.0	2134.4	2120.8	2134.4	2148.0	2148.0	2148.0	2144.6	2144.6	2144.6
5°	1725.9	1722.5	1715.7	1708.9	1708.9	1705.5	1712.3	1719.1	1725.9	1732.7	1739.5
7.5°	1269.7	1259.5	1249.3	1239.1	1245.9	1249.3	1259.5	1266.3	1276.5	1283.4	1300.4
10°	1058.7	1045.1	1034.9	1024.6	1017.8	1011.0	1004.2	1000.8	994.0	987.2	994.0
12.5°	905.5	888.5	871.5	851.0	847.6	844.2	837.4	830.6	823.8	817.0	813.6
15°	742.1	728.5	721.7	711.5	697.8	684.2	677.4	674.0	667.2	660.4	657.0
17.5°	592.3	578.7	568.5	558.3	554.9	548.1	548.1	548.1	548.1	548.1	548.1
20°	466.4	456.2	456.2	452.7	452.7	449.3	452.7	456.2	456.2	459.6	463.0
22.5°	408.5	408.5	405.1	401.7	405.1	405.1	408.5	411.9	415.3	418.7	422.1
25°	377.9	374.5	377.9	381.3	381.3	381.3	384.7	384.7	388.1	388.1	388.1
27.5°	364.2	364.2	367.6	367.6	371.0	371.0	371.0	367.6	367.6	364.2	364.2
30°	384.7	377.9	377.9	377.9	374.5	371.0	367.6	367.6	364.2	360.8	357.4
32.5°	398.3	401.7	398.3	391.5	388.1	381.3	377.9	371.0	367.6	360.8	354.0
35°	289.3	285.9	292.8	296.2	299.6	303.0	306.4	309.8	309.8	313.2	313.2
37.5°	279.1	275.7	275.7	272.3	272.3	272.3	272.3	272.3	268.9	268.9	272.3
40°	265.5	262.1	262.1	258.7	258.7	255.3	255.3	255.3	255.3	255.3	255.3
42.5°	255.3	251.9	251.9	251.9	251.9	248.5	248.5	245.1	245.1	241.7	241.7
45°	251.9	248.5	245.1	241.7	241.7	238.3	238.3	238.3	234.9	234.9	234.9
47.5°	238.3	234.9	234.9	231.5	231.5	228.1	228.1	228.1	224.7	224.7	224.7
50°	231.5	228.1	228.1	224.7	224.7	221.3	221.3	221.3	217.9	217.9	217.9
52.5°	221.3	217.9	217.9	217.9	214.5	211.1	211.1	211.1	207.7	207.7	207.7
55°	211.1	207.7	207.7	207.7	204.2	200.8	200.8	200.8	197.4	197.4	197.4
57.5°	197.4	194.0	194.0	190.6	190.6	190.6	190.6	190.6	187.2	187.2	187.2
60°	187.2	183.8	183.8	180.4	180.4	177.0	177.0	177.0	177.0	177.0	177.0
62.5°	177.0	173.6	170.2	166.8	170.2	170.2	170.2	170.2	166.8	166.8	166.8
65°	166.8	163.4	160.0	156.6	156.6	156.6	156.6	156.6	156.6	156.6	156.6
67.5°	153.2	149.8	146.4	143.0	146.4	146.4	146.4	146.4	146.4	146.4	146.4
70°	139.6	136.2	136.2	132.8	132.8	129.4	129.4	132.8	132.8	132.8	132.8
72.5°	126.0	122.5	122.5	119.1	119.1	119.1	119.1	119.1	119.1	119.1	119.1
75°	112.3	108.9	108.9	105.5	105.5	105.5	105.5	105.5	105.5	105.5	105.5
77.5°	95.3	91.9	91.9	91.9	91.9	91.9	91.9	95.3	95.3	95.3	95.3
80°	81.7	78.3	78.3	78.3	78.3	78.3	78.3	78.3	78.3	78.3	78.3
82.5°	64.7	61.3	61.3	61.3	61.3	61.3	61.3	61.3	61.3	61.3	61.3
85°	47.7	44.3	44.3	44.3	47.7	47.7	47.7	47.7	47.7	47.7	47.7
87.5°	30.6	27.2	27.2	27.2	30.6	30.6	30.6	30.6	27.2	27.2	27.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005
 CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0
2.5°	2144.6	2144.6	2144.6	2141.2	2137.8	2134.4	2131.0	2141.2	2148.0	2158.2	2165.0
5°	1742.9	1749.7	1753.1	1763.3	1773.5	1783.8	1794.0	1800.8	1807.6	1811.0	1817.8
7.5°	1314.0	1331.0	1344.6	1358.2	1371.9	1382.1	1395.7	1405.9	1416.1	1426.3	1436.5
10°	997.4	1004.2	1007.6	1021.2	1031.4	1045.1	1055.3	1065.5	1075.7	1082.5	1092.7
12.5°	810.2	803.4	800.0	800.0	800.0	800.0	800.0	806.8	813.6	820.4	827.2
15°	653.6	650.2	646.8	643.4	640.0	633.2	629.8	636.6	643.4	650.2	657.0
17.5°	548.1	548.1	548.1	544.7	541.3	537.9	534.4	537.9	541.3	541.3	544.7
20°	469.8	473.2	476.6	480.0	480.0	483.4	483.4	486.8	490.2	490.2	493.6
22.5°	422.1	425.5	425.5	425.5	428.9	428.9	428.9	432.3	435.7	439.1	442.5
25°	384.7	384.7	381.3	381.3	384.7	384.7	384.7	384.7	388.1	388.1	388.1
27.5°	364.2	360.8	360.8	360.8	360.8	357.4	357.4	357.4	357.4	357.4	357.4
30°	354.0	350.6	347.2	343.8	343.8	340.4	337.0	337.0	337.0	337.0	337.0
32.5°	350.6	343.8	337.0	333.6	333.6	330.2	326.8	323.4	323.4	320.0	316.6
35°	313.2	309.8	309.8	306.4	303.0	299.6	296.2	296.2	296.2	292.8	292.8
37.5°	272.3	275.7	275.7	275.7	279.1	279.1	279.1	279.1	282.5	282.5	282.5
40°	255.3	255.3	255.3	258.7	262.1	262.1	265.5	265.5	268.9	268.9	268.9
42.5°	241.7	238.3	238.3	241.7	241.7	245.1	245.1	248.5	251.9	251.9	255.3
45°	234.9	231.5	231.5	231.5	231.5	228.1	228.1	231.5	234.9	238.3	241.7
47.5°	221.3	221.3	217.9	217.9	217.9	217.9	217.9	217.9	221.3	221.3	221.3
50°	214.5	214.5	211.1	211.1	211.1	211.1	211.1	211.1	211.1	211.1	211.1
52.5°	207.7	204.2	204.2	204.2	204.2	200.8	200.8	200.8	200.8	200.8	200.8
55°	197.4	194.0	194.0	194.0	194.0	194.0	194.0	194.0	197.4	197.4	197.4
57.5°	187.2	183.8	183.8	183.8	187.2	187.2	187.2	187.2	190.6	190.6	190.6
60°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	180.4	180.4	183.8	183.8
62.5°	166.8	166.8	166.8	166.8	170.2	170.2	170.2	170.2	173.6	173.6	173.6
65°	156.6	156.6	156.6	156.6	160.0	160.0	160.0	160.0	160.0	160.0	160.0
67.5°	146.4	146.4	146.4	146.4	146.4	146.4	146.4	149.8	149.8	153.2	153.2
70°	132.8	129.4	129.4	132.8	132.8	136.2	136.2	139.6	139.6	143.0	143.0
72.5°	119.1	119.1	119.1	119.1	119.1	119.1	119.1	122.5	126.0	126.0	129.4
75°	105.5	105.5	105.5	105.5	108.9	108.9	108.9	112.3	112.3	115.7	115.7
77.5°	95.3	91.9	91.9	91.9	95.3	95.3	95.3	98.7	98.7	102.1	102.1
80°	78.3	78.3	78.3	78.3	81.7	81.7	81.7	81.7	85.1	85.1	85.1
82.5°	64.7	64.7	64.7	64.7	64.7	64.7	64.7	64.7	68.1	68.1	68.1
85°	47.7	47.7	47.7	47.7	51.1	51.1	51.1	51.1	51.1	51.1	51.1
87.5°	30.6	30.6	30.6	30.6	30.6	30.6	30.6	30.6	34.0	34.0	34.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005
 CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0
2.5°	2165.0	2165.0	2165.0	2165.0	2171.8	2175.2	2182.0	2185.4	2182.0	2178.6	2171.8
5°	1821.2	1824.6	1824.6	1828.0	1828.0	1828.0	1828.0	1828.0	1834.8	1841.6	1848.4
7.5°	1439.9	1443.3	1446.7	1450.2	1450.2	1450.2	1446.7	1446.7	1450.2	1450.2	1453.6
10°	1102.9	1116.6	1126.8	1137.0	1130.2	1120.0	1113.1	1102.9	1102.9	1102.9	1099.5
12.5°	834.0	837.4	844.2	847.6	844.2	844.2	840.8	837.4	840.8	847.6	851.0
15°	660.4	660.4	663.8	663.8	667.2	670.6	670.6	674.0	680.8	684.2	691.0
17.5°	548.1	551.5	551.5	554.9	554.9	558.3	558.3	558.3	565.1	571.9	582.1
20°	493.6	493.6	493.6	493.6	493.6	490.2	490.2	486.8	490.2	497.0	500.4
22.5°	442.5	445.9	445.9	445.9	442.5	439.1	432.3	428.9	428.9	432.3	432.3
25°	388.1	384.7	384.7	381.3	381.3	384.7	384.7	384.7	388.1	388.1	391.5
27.5°	357.4	354.0	354.0	350.6	350.6	354.0	354.0	354.0	354.0	354.0	354.0
30°	333.6	333.6	330.2	326.8	330.2	330.2	333.6	333.6	337.0	337.0	340.4
32.5°	316.6	313.2	313.2	309.8	313.2	313.2	316.6	316.6	320.0	323.4	323.4
35°	292.8	292.8	292.8	292.8	292.8	292.8	289.3	289.3	289.3	289.3	289.3
37.5°	279.1	279.1	275.7	272.3	272.3	272.3	272.3	272.3	268.9	265.5	262.1
40°	268.9	265.5	265.5	262.1	258.7	258.7	255.3	251.9	251.9	248.5	248.5
42.5°	255.3	251.9	251.9	248.5	245.1	245.1	241.7	238.3	238.3	238.3	234.9
45°	238.3	238.3	234.9	231.5	231.5	231.5	228.1	228.1	228.1	228.1	224.7
47.5°	221.3	221.3	217.9	217.9	217.9	217.9	214.5	214.5	214.5	214.5	214.5
50°	211.1	211.1	211.1	211.1	211.1	211.1	207.7	207.7	207.7	207.7	207.7
52.5°	200.8	200.8	200.8	200.8	200.8	200.8	200.8	200.8	200.8	200.8	200.8
55°	197.4	197.4	197.4	197.4	197.4	197.4	194.0	194.0	194.0	197.4	197.4
57.5°	190.6	190.6	187.2	187.2	187.2	187.2	187.2	187.2	187.2	187.2	187.2
60°	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8	183.8
62.5°	173.6	173.6	173.6	173.6	173.6	177.0	177.0	177.0	177.0	177.0	173.6
65°	160.0	163.4	163.4	163.4	163.4	163.4	163.4	163.4	163.4	163.4	163.4
67.5°	153.2	153.2	153.2	153.2	153.2	153.2	153.2	153.2	153.2	153.2	153.2
70°	143.0	143.0	139.6	139.6	139.6	143.0	143.0	143.0	143.0	143.0	143.0
72.5°	129.4	129.4	129.4	129.4	129.4	129.4	129.4	129.4	129.4	132.8	132.8
75°	115.7	115.7	115.7	115.7	115.7	115.7	115.7	115.7	115.7	115.7	115.7
77.5°	102.1	102.1	98.7	98.7	98.7	102.1	102.1	102.1	102.1	105.5	105.5
80°	85.1	85.1	85.1	85.1	85.1	85.1	85.1	85.1	85.1	88.5	88.5
82.5°	68.1	68.1	68.1	68.1	68.1	68.1	68.1	68.1	68.1	71.5	71.5
85°	51.1	54.5	54.5	54.5	54.5	54.5	54.5	54.5	54.5	57.9	57.9
87.5°	34.0	34.0	34.0	34.0	34.0	34.0	30.6	30.6	30.6	30.6	27.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005
 CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0
2.5°	2168.4	2171.8	2175.2	2175.2	2178.6	2182.0	2182.0	2195.7	2209.3	2216.1	2222.9
5°	1855.2	1851.8	1851.8	1848.4	1845.0	1855.2	1865.5	1885.9	1906.3	1909.7	1916.5
7.5°	1453.6	1457.0	1460.4	1460.4	1463.8	1453.6	1439.9	1443.3	1446.7	1463.8	1477.4
10°	1099.5	1102.9	1106.3	1106.3	1109.7	1106.3	1099.5	1109.7	1120.0	1133.6	1150.6
12.5°	854.4	864.6	874.9	881.7	891.9	898.7	902.1	915.7	925.9	942.9	960.0
15°	697.8	704.7	711.5	718.3	725.1	731.9	738.7	752.3	765.9	786.4	806.8
17.5°	588.9	588.9	592.3	592.3	592.3	599.1	605.9	612.7	616.1	636.6	657.0
20°	503.8	500.4	497.0	493.6	490.2	497.0	500.4	503.8	507.2	520.8	531.0
22.5°	432.3	432.3	435.7	435.7	435.7	432.3	425.5	428.9	428.9	435.7	445.9
25°	391.5	391.5	391.5	388.1	388.1	391.5	394.9	394.9	391.5	394.9	398.3
27.5°	354.0	357.4	357.4	360.8	360.8	364.2	364.2	364.2	364.2	367.6	371.0
30°	340.4	340.4	343.8	343.8	343.8	347.2	350.6	350.6	350.6	354.0	360.8
32.5°	326.8	330.2	333.6	337.0	340.4	343.8	343.8	347.2	347.2	350.6	354.0
35°	289.3	285.9	285.9	282.5	279.1	279.1	279.1	279.1	275.7	279.1	279.1
37.5°	258.7	258.7	258.7	255.3	255.3	258.7	258.7	258.7	258.7	262.1	262.1
40°	245.1	245.1	245.1	245.1	245.1	245.1	245.1	248.5	248.5	251.9	255.3
42.5°	234.9	234.9	234.9	234.9	234.9	238.3	238.3	238.3	238.3	241.7	241.7
45°	224.7	224.7	224.7	224.7	224.7	224.7	224.7	228.1	228.1	231.5	234.9
47.5°	214.5	214.5	214.5	214.5	214.5	217.9	221.3	221.3	221.3	224.7	224.7
50°	207.7	207.7	207.7	207.7	207.7	211.1	211.1	214.5	214.5	217.9	221.3
52.5°	200.8	200.8	200.8	200.8	200.8	204.2	204.2	207.7	207.7	211.1	214.5
55°	197.4	197.4	197.4	194.0	194.0	197.4	197.4	200.8	200.8	204.2	204.2
57.5°	187.2	187.2	187.2	187.2	187.2	187.2	187.2	190.6	190.6	194.0	197.4
60°	183.8	183.8	180.4	180.4	177.0	180.4	180.4	183.8	183.8	187.2	187.2
62.5°	173.6	173.6	173.6	170.2	170.2	173.6	173.6	173.6	173.6	177.0	180.4
65°	163.4	163.4	163.4	160.0	160.0	163.4	163.4	163.4	163.4	166.8	170.2
67.5°	153.2	153.2	153.2	149.8	149.8	149.8	149.8	153.2	153.2	156.6	160.0
70°	143.0	143.0	143.0	139.6	139.6	139.6	136.2	139.6	143.0	146.4	146.4
72.5°	132.8	132.8	132.8	129.4	129.4	129.4	126.0	129.4	129.4	132.8	132.8
75°	115.7	115.7	115.7	115.7	115.7	115.7	112.3	112.3	112.3	115.7	115.7
77.5°	105.5	105.5	105.5	102.1	102.1	102.1	98.7	98.7	98.7	102.1	102.1
80°	88.5	88.5	88.5	85.1	85.1	85.1	81.7	81.7	81.7	85.1	85.1
82.5°	71.5	71.5	71.5	68.1	68.1	68.1	64.7	64.7	64.7	68.1	68.1
85°	57.9	57.9	57.9	57.9	57.9	57.9	54.5	54.5	54.5	57.9	61.3
87.5°	27.2	27.2	30.6	30.6	30.6	30.6	27.2	27.2	23.8	23.8	27.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005
 CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0
2.5°	2229.7	2236.5	2253.5	2267.1	2284.2	2297.8	2308.0	2321.6	2331.8	2342.0	2348.8
5°	1919.9	1923.3	1940.3	1957.4	1971.0	1988.0	2011.8	2035.7	2059.5	2083.3	2100.3
7.5°	1494.4	1508.0	1528.4	1552.3	1572.7	1593.1	1617.0	1644.2	1668.0	1691.8	1715.7
10°	1164.2	1177.8	1198.2	1218.7	1235.7	1256.1	1283.4	1310.6	1337.8	1365.1	1392.3
12.5°	977.0	994.0	1017.8	1041.7	1062.1	1085.9	1120.0	1150.6	1184.6	1215.3	1249.3
15°	823.8	844.2	874.9	908.9	939.5	970.2	1004.2	1038.3	1068.9	1102.9	1137.0
17.5°	677.4	697.8	725.1	755.7	782.9	810.2	851.0	888.5	929.3	966.8	1004.2
20°	544.7	554.9	582.1	609.3	636.6	663.8	694.4	725.1	755.7	786.4	834.0
22.5°	452.7	459.6	473.2	483.4	497.0	507.2	537.9	568.5	595.7	626.4	670.6
25°	398.3	401.7	411.9	418.7	428.9	435.7	456.2	473.2	493.6	510.6	551.5
27.5°	371.0	374.5	377.9	381.3	384.7	388.1	401.7	415.3	425.5	439.1	476.6
30°	364.2	367.6	377.9	384.7	394.9	401.7	408.5	415.3	422.1	428.9	452.7
32.5°	357.4	360.8	360.8	357.4	357.4	354.0	360.8	364.2	371.0	374.5	394.9
35°	282.5	282.5	285.9	289.3	292.8	296.2	306.4	313.2	323.4	330.2	347.2
37.5°	265.5	265.5	268.9	275.7	279.1	282.5	289.3	296.2	303.0	309.8	326.8
40°	255.3	258.7	262.1	265.5	268.9	272.3	279.1	282.5	289.3	292.8	306.4
42.5°	245.1	245.1	248.5	255.3	258.7	262.1	268.9	272.3	279.1	282.5	296.2
45°	238.3	241.7	245.1	248.5	248.5	251.9	258.7	265.5	268.9	275.7	289.3
47.5°	228.1	228.1	234.9	238.3	245.1	248.5	255.3	258.7	265.5	268.9	282.5
50°	221.3	224.7	231.5	234.9	241.7	245.1	255.3	262.1	272.3	279.1	285.9
52.5°	214.5	217.9	224.7	228.1	234.9	238.3	251.9	265.5	275.7	289.3	289.3
55°	207.7	207.7	214.5	224.7	231.5	238.3	245.1	255.3	262.1	268.9	268.9
57.5°	197.4	200.8	207.7	217.9	224.7	231.5	238.3	245.1	248.5	255.3	251.9
60°	190.6	190.6	200.8	211.1	221.3	231.5	231.5	231.5	228.1	228.1	228.1
62.5°	180.4	183.8	197.4	214.5	228.1	241.7	231.5	221.3	211.1	200.8	204.2
65°	173.6	177.0	183.8	194.0	200.8	207.7	200.8	197.4	190.6	183.8	187.2
67.5°	160.0	163.4	166.8	166.8	170.2	170.2	170.2	170.2	170.2	170.2	173.6
70°	149.8	149.8	149.8	153.2	153.2	153.2	153.2	153.2	153.2	153.2	156.6
72.5°	136.2	136.2	136.2	136.2	136.2	136.2	136.2	136.2	136.2	136.2	139.6
75°	119.1	119.1	119.1	119.1	119.1	119.1	119.1	119.1	119.1	119.1	122.5
77.5°	105.5	105.5	105.5	105.5	105.5	105.5	105.5	105.5	102.1	102.1	105.5
80°	88.5	88.5	88.5	88.5	85.1	85.1	85.1	85.1	85.1	85.1	88.5
82.5°	71.5	71.5	71.5	71.5	68.1	68.1	68.1	68.1	64.7	64.7	68.1
85°	64.7	68.1	68.1	71.5	71.5	71.5	68.1	64.7	61.3	57.9	57.9
87.5°	27.2	27.2	27.2	27.2	23.8	23.8	23.8	23.8	23.8	23.8	23.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005
 CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0
2.5°	2359.1	2365.9	2372.7	2382.9	2396.5	2406.7	2416.9	2437.3	2461.2	2481.6	2502.0
5°	2117.4	2134.4	2151.4	2171.8	2192.3	2209.3	2229.7	2270.5	2311.4	2348.8	2389.7
7.5°	1736.1	1759.9	1780.4	1814.4	1845.0	1879.1	1909.7	1960.8	2008.4	2059.5	2107.1
10°	1419.5	1446.7	1474.0	1518.2	1565.9	1610.1	1654.4	1695.2	1739.5	1780.4	1821.2
12.5°	1283.4	1314.0	1348.0	1375.3	1405.9	1433.1	1460.4	1508.0	1555.7	1603.3	1651.0
15°	1171.0	1205.1	1239.1	1273.1	1303.8	1337.8	1368.5	1409.3	1453.6	1494.4	1535.3
17.5°	1041.7	1075.7	1113.1	1150.6	1188.0	1225.5	1262.9	1320.8	1378.7	1433.1	1491.0
20°	878.3	925.9	970.2	1021.2	1072.3	1123.4	1174.4	1235.7	1297.0	1354.8	1416.1
22.5°	714.9	759.1	803.4	864.6	925.9	983.8	1045.1	1126.8	1205.1	1286.8	1365.1
25°	595.7	636.6	677.4	745.5	810.2	878.3	942.9	1041.7	1137.0	1235.7	1331.0
27.5°	514.0	551.5	588.9	660.4	731.9	800.0	871.5	980.4	1085.9	1194.8	1300.4
30°	476.6	500.4	524.2	592.3	660.4	725.1	793.2	898.7	1004.2	1109.7	1215.3
32.5°	415.3	435.7	456.2	517.4	578.7	636.6	697.8	806.8	912.3	1021.2	1126.8
35°	367.6	384.7	401.7	459.6	514.0	571.9	626.4	735.3	844.2	953.2	1062.1
37.5°	340.4	357.4	371.0	422.1	476.6	527.6	578.7	687.6	793.2	902.1	1007.6
40°	320.0	330.2	343.8	394.9	442.5	493.6	541.3	640.0	742.1	840.8	939.5
42.5°	306.4	320.0	330.2	374.5	422.1	466.4	510.6	605.9	701.2	793.2	888.5
45°	303.0	316.6	330.2	367.6	405.1	439.1	476.6	568.5	660.4	752.3	844.2
47.5°	296.2	306.4	320.0	350.6	377.9	408.5	435.7	527.6	619.5	708.1	800.0
50°	292.8	296.2	303.0	330.2	357.4	384.7	411.9	503.8	595.7	687.6	779.5
52.5°	289.3	289.3	289.3	313.2	337.0	357.4	381.3	473.2	568.5	660.4	752.3
55°	268.9	265.5	265.5	289.3	309.8	333.6	354.0	445.9	537.9	626.4	718.3
57.5°	248.5	245.1	241.7	262.1	282.5	303.0	323.4	415.3	510.6	602.5	694.4
60°	228.1	224.7	224.7	245.1	262.1	282.5	299.6	394.9	486.8	582.1	674.0
62.5°	204.2	207.7	207.7	224.7	245.1	262.1	279.1	374.5	473.2	568.5	663.8
65°	187.2	190.6	190.6	211.1	231.5	251.9	272.3	364.2	459.6	551.5	643.4
67.5°	173.6	177.0	177.0	200.8	221.3	245.1	265.5	347.2	432.3	514.0	595.7
70°	160.0	160.0	163.4	187.2	211.1	234.9	258.7	330.2	401.7	469.8	541.3
72.5°	143.0	146.4	149.8	173.6	194.0	217.9	238.3	303.0	367.6	432.3	497.0
75°	126.0	129.4	132.8	153.2	173.6	194.0	214.5	275.7	333.6	394.9	452.7
77.5°	112.3	115.7	119.1	136.2	153.2	170.2	187.2	231.5	279.1	323.4	367.6
80°	91.9	91.9	95.3	108.9	122.5	132.8	146.4	177.0	207.7	234.9	265.5
82.5°	68.1	71.5	71.5	81.7	88.5	98.7	105.5	122.5	136.2	153.2	166.8
85°	57.9	54.5	54.5	61.3	64.7	71.5	74.9	85.1	91.9	102.1	108.9
87.5°	23.8	20.4	20.4	23.8	30.6	34.0	37.4	37.4	40.8	40.8	40.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005
 CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0
2.5°	2512.2	2519.0	2529.3	2536.1	2553.1	2566.7	2583.7	2597.3	2607.6	2624.6	2617.8
5°	2420.3	2451.0	2481.6	2512.2	2536.1	2559.9	2580.3	2604.1	2631.4	2682.4	2696.1
7.5°	2148.0	2188.8	2226.3	2267.1	2314.8	2362.5	2410.1	2457.8	2502.0	2566.7	2607.6
10°	1879.1	1936.9	1991.4	2049.3	2093.5	2137.8	2178.6	2222.9	2284.2	2348.8	2423.7
12.5°	1708.9	1766.7	1824.6	1882.5	1947.2	2008.4	2073.1	2134.4	2192.3	2243.3	2328.4
15°	1596.5	1661.2	1722.5	1783.8	1862.1	1936.9	2015.2	2090.1	2175.2	2243.3	2301.2
17.5°	1569.3	1647.6	1722.5	1800.8	1882.5	1964.2	2045.9	2127.6	2212.7	2314.8	2389.7
20°	1521.6	1627.2	1732.7	1838.2	1943.8	2045.9	2151.4	2253.5	2365.9	2488.4	2522.4
22.5°	1494.4	1620.4	1749.7	1875.7	2018.6	2165.0	2308.0	2451.0	2570.1	2662.0	2764.1
25°	1491.0	1647.6	1807.6	1964.2	2144.6	2321.6	2502.0	2679.0	2832.2	2924.1	3005.8
27.5°	1487.6	1678.2	1865.5	2052.7	2273.9	2491.8	2713.1	2930.9	3073.9	3206.7	3274.8
30°	1446.7	1674.8	1906.3	2134.4	2382.9	2631.4	2879.9	3128.4	3274.8	3366.7	3400.7
32.5°	1395.7	1664.6	1933.5	2202.5	2485.0	2767.5	3046.7	3329.2	3445.0	3523.3	3496.0
35°	1354.8	1651.0	1943.8	2236.5	2536.1	2839.0	3138.6	3438.2	3605.0	3713.9	3669.6
37.5°	1317.4	1627.2	1936.9	2246.7	2597.3	2948.0	3298.6	3649.2	3809.2	3924.9	3873.9
40°	1273.1	1603.3	1936.9	2267.1	2668.8	3067.1	3468.8	3867.1	4074.7	4173.4	4095.2
42.5°	1235.7	1579.5	1926.7	2270.5	2699.5	3128.4	3557.3	3986.2	4217.7	4357.3	4258.5
45°	1188.0	1531.9	1872.3	2216.1	2689.3	3162.4	3632.2	4105.4	4374.3	4483.2	4347.1
47.5°	1137.0	1477.4	1814.4	2151.4	2655.2	3159.0	3662.8	4166.6	4415.1	4544.5	4418.5
50°	1120.0	1460.4	1797.4	2137.8	2682.4	3230.5	3775.2	4319.8	4500.2	4605.8	4439.0
52.5°	1116.6	1477.4	1841.6	2202.5	2750.5	3295.2	3843.2	4387.9	4534.3	4646.6	4496.8
55°	1106.3	1497.8	1885.9	2273.9	2845.8	3421.1	3993.0	4564.9	4711.3	4793.0	4680.7
57.5°	1116.6	1538.7	1957.4	2379.5	2968.4	3557.3	4146.2	4735.1	4912.1	4970.0	4946.2
60°	1123.4	1572.7	2018.6	2468.0	3043.3	3618.6	4193.9	4769.2	4953.0	5096.0	5123.2
62.5°	1106.3	1548.9	1988.0	2430.5	2951.4	3472.2	3993.0	4513.9	4816.8	5027.9	5150.4
65°	1055.3	1463.8	1875.7	2284.2	2764.1	3247.5	3727.5	4207.5	4527.5	4840.7	4939.4
67.5°	942.9	1290.2	1637.4	1984.6	2403.3	2822.0	3237.3	3656.0	4057.7	4360.7	4496.8
70°	817.0	1089.3	1365.1	1637.4	2018.6	2399.9	2781.2	3162.4	3516.5	3850.1	3979.4
72.5°	711.5	922.5	1137.0	1348.0	1620.4	1889.3	2161.6	2430.5	2849.2	3182.8	3308.8
75°	605.9	759.1	908.9	1062.1	1249.3	1436.5	1620.4	1807.6	2103.7	2403.3	2529.3
77.5°	466.4	568.5	667.2	765.9	895.3	1021.2	1150.6	1276.5	1484.2	1708.9	1773.5
80°	323.4	381.3	435.7	493.6	595.7	697.8	800.0	902.1	1038.3	1164.2	1262.9
82.5°	200.8	238.3	272.3	306.4	388.1	469.8	548.1	629.8	684.2	691.0	789.8
85°	129.4	153.2	173.6	194.0	241.7	292.8	340.4	388.1	347.2	323.4	384.7
87.5°	51.1	64.7	74.9	85.1	81.7	78.3	74.9	71.5	61.3	54.5	68.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005
 CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0
2.5°	2624.6	2634.8	2645.0	2651.8	2662.0	2665.4	2668.8	2668.8	2672.2	2675.6	2682.4
5°	2750.5	2771.0	2791.4	2808.4	2828.8	2845.8	2859.5	2876.5	2890.1	2890.1	2886.7
7.5°	2645.0	2696.1	2747.1	2798.2	2849.2	2886.7	2920.7	2958.2	2992.2	2999.0	3005.8
10°	2505.4	2559.9	2611.0	2665.4	2716.5	2774.4	2828.8	2883.3	2941.2	2951.4	2965.0
12.5°	2376.1	2440.8	2505.4	2566.7	2631.4	2672.2	2713.1	2750.5	2791.4	2818.6	2845.8
15°	2372.7	2427.1	2481.6	2532.7	2587.1	2611.0	2634.8	2655.2	2679.0	2679.0	2682.4
17.5°	2451.0	2485.0	2519.0	2549.7	2583.7	2587.1	2593.9	2597.3	2600.7	2590.5	2580.3
20°	2604.1	2617.8	2631.4	2645.0	2658.6	2634.8	2614.4	2590.5	2566.7	2539.5	2515.6
22.5°	2828.8	2798.2	2767.5	2736.9	2706.3	2665.4	2621.2	2580.3	2536.1	2502.0	2468.0
25°	3039.9	3002.4	2965.0	2927.5	2890.1	2801.6	2713.1	2621.2	2532.7	2495.2	2457.8
27.5°	3322.4	3264.5	3206.7	3148.8	3090.9	2971.8	2852.6	2733.5	2614.4	2549.7	2488.4
30°	3390.5	3325.8	3261.1	3193.1	3128.4	3012.6	2900.3	2784.6	2668.8	2593.9	2522.4
32.5°	3489.2	3414.3	3339.4	3264.5	3189.7	3077.3	2965.0	2849.2	2736.9	2668.8	2597.3
35°	3652.6	3567.5	3482.4	3393.9	3308.8	3193.1	3080.7	2965.0	2849.2	2771.0	2696.1
37.5°	3792.2	3693.5	3594.7	3496.0	3397.3	3295.2	3189.7	3087.5	2982.0	2903.7	2828.8
40°	3948.8	3839.8	3730.9	3625.4	3516.5	3421.1	3325.8	3227.1	3131.8	3070.5	3009.2
42.5°	4084.9	3952.2	3822.8	3693.5	3560.7	3496.0	3434.8	3370.1	3305.4	3274.8	3240.7
45°	4180.3	4057.7	3931.8	3809.2	3686.7	3639.0	3591.3	3543.7	3496.0	3526.7	3557.3
47.5°	4221.1	4122.4	4027.1	3931.8	3833.0	3850.1	3867.1	3880.7	3897.7	3938.6	3982.8
50°	4258.5	4204.1	4146.2	4091.7	4033.9	4098.6	4159.8	4224.5	4289.2	4374.3	4459.4
52.5°	4333.4	4302.8	4275.6	4244.9	4214.3	4326.6	4439.0	4551.3	4663.6	4759.0	4854.3
55°	4558.1	4534.3	4510.5	4483.2	4459.4	4619.4	4776.0	4936.0	5096.0	5194.7	5293.4
57.5°	4867.9	4854.3	4837.2	4823.6	4806.6	4963.2	5116.4	5269.6	5426.2	5521.5	5620.2
60°	5102.8	5106.2	5106.2	5109.6	5109.6	5228.7	5347.9	5470.4	5589.6	5671.3	5756.4
62.5°	5228.7	5221.9	5215.1	5208.3	5201.5	5300.2	5398.9	5497.6	5596.4	5657.6	5718.9
65°	5092.6	5130.0	5167.4	5204.9	5242.3	5256.0	5266.2	5279.8	5290.0	5327.4	5364.9
67.5°	4636.4	4711.3	4782.8	4857.7	4929.2	4878.1	4830.4	4779.4	4728.3	4738.5	4745.3
70°	4129.2	4214.3	4302.8	4387.9	4473.0	4353.9	4234.7	4112.2	3993.0	3952.2	3911.3
72.5°	3482.4	3557.3	3635.6	3710.5	3785.4	3639.0	3496.0	3349.7	3203.3	3131.8	3060.3
75°	2662.0	2750.5	2842.4	2930.9	3019.5	2856.1	2689.3	2525.9	2359.1	2311.4	2267.1
77.5°	1940.3	2045.9	2151.4	2256.9	2362.5	2216.1	2069.7	1919.9	1773.5	1746.3	1719.1
80°	1412.7	1494.4	1572.7	1654.4	1732.7	1647.6	1562.5	1477.4	1392.3	1388.9	1385.5
82.5°	953.2	1024.6	1092.7	1164.2	1232.3	1198.2	1167.6	1133.6	1099.5	1133.6	1171.0
85°	490.2	588.9	691.0	789.8	888.5	878.3	871.5	861.2	851.0	895.3	936.1
87.5°	98.7	183.8	268.9	350.6	435.7	415.3	394.9	371.0	350.6	364.2	374.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0
2.5°	2685.8	2689.3	2689.3	2689.3	2689.3	2689.3	2682.4	2679.0	2672.2	2665.4	2655.2
5°	2886.7	2883.3	2869.7	2856.1	2839.0	2825.4	2815.2	2801.6	2791.4	2777.8	2757.3
7.5°	3012.6	3019.5	2995.6	2975.2	2951.4	2927.5	2903.7	2879.9	2856.1	2832.2	2784.6
10°	2975.2	2985.4	2971.8	2958.2	2941.2	2927.5	2900.3	2869.7	2842.4	2811.8	2753.9
12.5°	2869.7	2896.9	2890.1	2883.3	2876.5	2869.7	2852.6	2832.2	2815.2	2794.8	2730.1
15°	2682.4	2682.4	2685.8	2689.3	2689.3	2692.7	2696.1	2699.5	2702.9	2706.3	2668.8
17.5°	2570.1	2559.9	2559.9	2559.9	2559.9	2559.9	2573.5	2590.5	2604.1	2617.8	2607.6
20°	2488.4	2464.6	2461.2	2461.2	2457.8	2454.4	2478.2	2505.4	2529.3	2553.1	2566.7
22.5°	2433.9	2399.9	2396.5	2393.1	2389.7	2386.3	2416.9	2447.6	2478.2	2508.8	2556.5
25°	2420.3	2382.9	2386.3	2389.7	2389.7	2393.1	2416.9	2440.8	2464.6	2488.4	2570.1
27.5°	2423.7	2362.5	2365.9	2369.3	2369.3	2372.7	2410.1	2444.2	2481.6	2515.6	2617.8
30°	2447.6	2376.1	2369.3	2362.5	2355.6	2348.8	2399.9	2451.0	2502.0	2553.1	2631.4
32.5°	2529.3	2461.2	2444.2	2427.1	2410.1	2393.1	2454.4	2512.2	2573.5	2631.4	2696.1
35°	2617.8	2542.9	2536.1	2529.3	2519.0	2512.2	2566.7	2624.6	2679.0	2733.5	2791.4
37.5°	2750.5	2675.6	2668.8	2658.6	2651.8	2641.6	2702.9	2760.7	2822.0	2879.9	2930.9
40°	2948.0	2886.7	2883.3	2883.3	2879.9	2876.5	2924.1	2975.2	3022.9	3070.5	3104.6
42.5°	3210.1	3179.4	3189.7	3203.3	3213.5	3223.7	3261.1	3302.0	3339.4	3376.9	3366.7
45°	3587.9	3618.6	3622.0	3625.4	3628.8	3632.2	3642.4	3656.0	3666.2	3676.4	3635.6
47.5°	4023.7	4064.5	4084.9	4105.4	4122.4	4142.8	4129.2	4112.2	4098.6	4081.5	3979.4
50°	4541.1	4626.2	4622.8	4619.4	4612.6	4609.2	4581.9	4554.7	4524.1	4496.8	4347.1
52.5°	4949.6	5044.9	5061.9	5078.9	5096.0	5113.0	5061.9	5010.9	4956.4	4905.3	4718.1
55°	5388.7	5487.4	5490.8	5494.2	5494.2	5497.6	5426.2	5354.7	5279.8	5208.3	5014.3
57.5°	5715.5	5810.8	5800.6	5793.8	5783.6	5773.4	5688.3	5603.2	5518.1	5433.0	5238.9
60°	5838.1	5919.8	5899.3	5878.9	5855.1	5834.7	5770.0	5705.3	5637.2	5572.5	5385.3
62.5°	5780.2	5841.5	5810.8	5783.6	5753.0	5722.3	5640.6	5555.5	5473.8	5388.7	5252.6
65°	5398.9	5436.4	5395.5	5358.1	5320.6	5279.8	5211.7	5143.6	5072.1	5004.1	4912.1
67.5°	4755.6	4762.4	4759.0	4755.6	4752.1	4748.7	4650.0	4551.3	4449.2	4350.5	4343.7
70°	3873.9	3833.0	3839.8	3850.1	3856.9	3863.7	3788.8	3717.3	3642.4	3567.5	3601.6
72.5°	2988.8	2917.3	2934.3	2954.8	2971.8	2988.8	2927.5	2869.7	2808.4	2747.1	2794.8
75°	2219.5	2175.2	2192.3	2212.7	2229.7	2246.7	2222.9	2199.1	2171.8	2148.0	2192.3
77.5°	1691.8	1664.6	1668.0	1668.0	1671.4	1671.4	1674.8	1681.6	1685.0	1688.4	1736.1
80°	1378.7	1375.3	1371.9	1368.5	1361.6	1358.2	1392.3	1426.3	1460.4	1494.4	1518.2
82.5°	1205.1	1239.1	1218.7	1201.7	1181.2	1160.8	1191.4	1222.1	1252.7	1283.4	1273.1
85°	980.4	1021.2	983.8	946.3	905.5	868.0	895.3	919.1	946.3	970.2	956.6
87.5°	388.1	398.3	337.0	279.1	217.9	156.6	248.5	337.0	428.9	517.4	531.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0	2451.0
2.5°	2645.0	2631.4	2621.2	2617.8	2611.0	2607.6	2600.7	2593.9	2583.7	2576.9	2566.7
5°	2733.5	2713.1	2689.3	2655.2	2624.6	2590.5	2556.5	2525.9	2495.2	2461.2	2430.5
7.5°	2736.9	2689.3	2641.6	2597.3	2549.7	2505.4	2457.8	2416.9	2372.7	2328.4	2287.6
10°	2699.5	2641.6	2583.7	2525.9	2471.4	2413.5	2355.6	2308.0	2256.9	2205.9	2158.2
12.5°	2668.8	2604.1	2539.5	2471.4	2406.7	2338.6	2270.5	2222.9	2175.2	2127.6	2079.9
15°	2631.4	2590.5	2553.1	2491.8	2430.5	2369.3	2308.0	2243.3	2182.0	2117.4	2052.7
17.5°	2600.7	2590.5	2580.3	2539.5	2498.6	2454.4	2413.5	2348.8	2284.2	2216.1	2151.4
20°	2583.7	2597.3	2611.0	2590.5	2570.1	2546.3	2525.9	2478.2	2430.5	2379.5	2331.8
22.5°	2604.1	2655.2	2702.9	2706.3	2713.1	2716.5	2719.9	2675.6	2631.4	2583.7	2539.5
25°	2651.8	2733.5	2815.2	2859.5	2903.7	2951.4	2995.6	2968.4	2941.2	2913.9	2886.7
27.5°	2716.5	2818.6	2920.7	2985.4	3046.7	3111.4	3176.0	3172.6	3169.2	3162.4	3159.0
30°	2706.3	2784.6	2862.9	2941.2	3019.5	3097.7	3176.0	3216.9	3254.3	3295.2	3336.0
32.5°	2764.1	2828.8	2896.9	2978.6	3060.3	3145.4	3227.1	3312.2	3393.9	3479.0	3564.1
35°	2852.6	2910.5	2971.8	3060.3	3152.2	3240.7	3332.6	3434.8	3540.3	3645.8	3747.9
37.5°	2985.4	3036.5	3090.9	3165.8	3244.1	3319.0	3397.3	3547.1	3696.9	3850.1	3999.8
40°	3138.6	3172.6	3206.7	3278.2	3349.7	3421.1	3492.6	3679.8	3867.1	4054.3	4241.5
42.5°	3359.9	3349.7	3339.4	3397.3	3458.6	3516.5	3577.7	3747.9	3918.1	4088.3	4258.5
45°	3594.7	3553.9	3513.0	3540.3	3570.9	3598.2	3628.8	3802.4	3976.0	4153.0	4326.6
47.5°	3877.3	3775.2	3673.0	3649.2	3625.4	3598.2	3574.3	3761.5	3948.8	4139.4	4326.6
50°	4197.3	4044.1	3894.3	3833.0	3768.4	3707.1	3642.4	3795.6	3952.2	4108.8	4262.0
52.5°	4530.9	4340.2	4153.0	4057.7	3962.4	3863.7	3768.4	3897.7	4030.5	4163.2	4292.6
55°	4816.8	4622.8	4425.4	4313.0	4200.7	4088.3	3976.0	4105.4	4234.7	4364.1	4493.4
57.5°	5044.9	4850.9	4656.8	4551.3	4442.4	4336.8	4227.9	4350.5	4476.4	4602.4	4724.9
60°	5201.5	5014.3	4827.0	4724.9	4622.8	4520.7	4418.5	4564.9	4711.3	4861.1	5007.5
62.5°	5119.8	4983.6	4847.5	4803.2	4759.0	4711.3	4667.0	4806.6	4942.8	5082.3	5221.9
65°	4820.2	4728.3	4636.4	4680.7	4728.3	4772.6	4820.2	4912.1	5004.1	5099.4	5191.3
67.5°	4333.4	4326.6	4316.4	4415.1	4513.9	4616.0	4714.7	4776.0	4833.8	4895.1	4956.4
70°	3635.6	3673.0	3707.1	3877.3	4047.5	4217.7	4387.9	4411.7	4435.6	4459.4	4483.2
72.5°	2845.8	2893.5	2944.6	3169.2	3390.5	3615.2	3839.8	3826.2	3812.6	3795.6	3782.0
75°	2239.9	2284.2	2331.8	2539.5	2747.1	2954.8	3162.4	3104.6	3050.1	2992.2	2934.3
77.5°	1787.2	1834.8	1885.9	2079.9	2273.9	2471.4	2665.4	2525.9	2386.3	2246.7	2107.1
80°	1538.7	1562.5	1582.9	1715.7	1845.0	1977.8	2110.6	1967.6	1821.2	1674.8	1531.9
82.5°	1262.9	1249.3	1239.1	1317.4	1395.7	1474.0	1552.3	1416.1	1279.9	1140.4	1004.2
85°	942.9	929.3	915.7	956.6	997.4	1041.7	1082.5	925.9	769.3	609.3	452.7
87.5°	548.1	561.7	575.3	619.5	663.8	711.5	755.7	595.7	435.7	272.3	112.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005

CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676005
 CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	2451.0	2451.0
2.5°	2546.3	2529.3
5°	2406.7	2382.9
7.5°	2253.5	2222.9
10°	2114.0	2073.1
12.5°	2025.4	1974.4
15°	1991.4	1930.1
17.5°	2093.5	2035.7
20°	2250.1	2171.8
22.5°	2440.8	2345.4
25°	2771.0	2655.2
27.5°	3039.9	2920.7
30°	3206.7	3077.3
32.5°	3390.5	3220.3
35°	3581.1	3417.7
37.5°	3812.6	3628.8
40°	4050.9	3860.3
42.5°	4132.6	4010.0
45°	4210.9	4095.2
47.5°	4227.9	4132.6
50°	4244.9	4231.3
52.5°	4292.6	4289.2
55°	4496.8	4500.2
57.5°	4748.7	4769.2
60°	4980.2	4956.4
62.5°	5099.4	4976.8
65°	5017.7	4847.5
67.5°	4772.6	4588.7
70°	4234.7	3986.2
72.5°	3564.1	3346.2
75°	2747.1	2563.3
77.5°	1954.0	1800.8
80°	1375.3	1222.1
82.5°	881.7	759.1
85°	398.3	347.2
87.5°	112.3	108.9
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P676005
CATALOG NUMBER: CCW-SA-2C-750-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)