

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P676015

Luminaire Tested: **CCW-SA-2B-760-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P676015
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2B-760-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @450mA w/
SLR distribution lens
Light Source: (32) 5700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5862.5 lumens
Efficiency: N/A
Efficacy: 127.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 46
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P676015

CATALOG NUMBER: CCW-SA-2B-760-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 8.3 fc
 Type IV - Short - N/A

REPORT NUMBER: P676015
CATALOG NUMBER: CCW-SA-2B-760-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P676015

CATALOG NUMBER: CCW-SA-2B-760-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1206.2	0.0	1206.2
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	4656.2	0.0	4656.2
	% Fixture	79.4	0.0	79.4
Total	Lumens	5862.5	0.0	5862.5
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.5	2.5
10°-20°	307.1	5.2
20°-30°	449.4	7.7
30°-40°	633.1	10.8
40°-50°	869.9	14.8
50°-60°	1185.7	20.2
60°-70°	1297.7	22.1
70°-80°	749.4	12.8
80°-90°	224.7	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5862.5	100.0
0°-180°	5862.5	100.0

Coefficient of Utilization



REPORT NUMBER: P676015


CATALOG NUMBER: CCW-SA-2B-760-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	602.1	10.3			
FM	(30°-60°)	2139.4	36.5			
FH	(60°-80°)	1723.9	29.4			G1/1800
FVH	(80°-90°)	190.8	3.3			G2/225
BL	(0°-30°)	299.9	5.1	B1/500		
BM	(30°-60°)	549.3	9.4	B1/1000		
BH	(60°-80°)	323.3	5.5	B1/500		G1/500
BVH	(80°-90°)	33.8	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P676015

CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1
2.5°	1931.9	1921.5	1913.7	1905.9	1895.5	1887.7	1877.3	1866.9	1853.9	1843.5	1830.5
5°	1820.1	1788.9	1757.7	1739.5	1718.7	1700.5	1679.7	1656.3	1632.9	1606.9	1583.5
7.5°	1697.9	1658.9	1619.9	1588.7	1554.9	1523.7	1489.9	1461.3	1432.7	1404.1	1375.5
10°	1583.5	1547.1	1510.7	1471.7	1430.1	1391.1	1349.5	1310.5	1271.5	1232.5	1193.5
12.5°	1508.1	1463.9	1422.3	1378.1	1336.5	1292.3	1248.1	1211.7	1175.3	1136.3	1099.9
15°	1474.3	1432.7	1393.7	1349.5	1305.3	1261.1	1216.9	1175.3	1136.3	1094.7	1053.1
17.5°	1554.9	1495.1	1435.3	1378.1	1320.9	1263.7	1206.5	1154.5	1102.5	1050.5	998.5
20°	1658.9	1583.5	1510.7	1440.5	1367.7	1297.5	1224.7	1151.9	1079.1	1006.3	933.5
22.5°	1791.5	1705.7	1622.5	1531.5	1437.9	1346.9	1253.3	1162.3	1071.3	977.7	886.7
25°	2028.1	1926.7	1825.3	1695.3	1562.7	1432.7	1300.1	1180.5	1063.5	943.9	824.3
27.5°	2230.9	2093.1	1957.9	1801.9	1645.9	1489.9	1333.9	1196.1	1060.9	923.1	785.3
30°	2350.6	2215.3	2080.1	1890.3	1703.1	1513.3	1323.5	1170.1	1019.3	865.9	712.4
32.5°	2459.8	2309.0	2158.1	1950.1	1739.5	1531.5	1320.9	1151.9	985.5	816.5	647.4
35°	2610.6	2444.2	2280.4	2038.5	1796.7	1554.9	1313.1	1138.9	962.1	787.9	611.0
37.5°	2771.8	2566.4	2363.6	2095.7	1827.9	1560.1	1292.3	1120.7	949.1	777.5	605.8
40°	2948.6	2699.0	2452.0	2155.5	1861.7	1565.3	1268.9	1097.3	925.7	751.4	579.8
42.5°	3063.0	2792.6	2522.2	2202.3	1885.1	1565.3	1245.5	1076.5	907.5	735.8	566.8
45°	3128.0	2865.4	2605.4	2259.5	1913.7	1567.9	1222.1	1055.7	889.3	720.2	553.8
47.5°	3156.6	2912.2	2667.8	2303.8	1942.3	1578.3	1214.3	1045.3	873.7	704.6	533.0
50°	3232.0	3016.2	2800.4	2410.4	2022.9	1632.9	1242.9	1060.9	881.5	699.4	517.4
52.5°	3276.2	3091.6	2907.0	2506.6	2106.1	1705.7	1305.3	1102.5	899.7	696.8	494.0
55°	3437.4	3260.6	3083.8	2657.4	2228.3	1801.9	1372.9	1149.3	925.7	699.4	475.8
57.5°	3642.8	3455.6	3271.0	2810.8	2350.6	1890.3	1430.1	1190.9	949.1	709.8	468.0
60°	3785.9	3603.8	3424.4	2935.6	2444.2	1955.3	1463.9	1214.3	964.7	712.4	462.8
62.5°	3801.5	3567.4	3336.0	2860.2	2384.4	1905.9	1430.1	1188.3	946.5	702.0	460.2
65°	3702.6	3429.6	3156.6	2701.6	2246.5	1791.5	1336.5	1115.5	894.5	670.8	449.8
67.5°	3505.0	3185.2	2865.4	2449.4	2033.3	1617.3	1201.3	1011.5	824.3	634.4	444.6
70°	3044.8	2764.0	2485.8	2124.3	1765.5	1404.1	1042.7	886.7	733.2	577.2	421.2
72.5°	2556.0	2293.4	2033.3	1739.5	1448.3	1154.5	860.7	743.6	626.6	507.0	390.0
75°	1957.9	1760.3	1565.3	1346.9	1128.5	907.5	689.0	603.2	517.4	431.6	345.8
77.5°	1375.5	1268.9	1164.9	1001.1	837.3	673.4	509.6	452.4	395.2	338.0	280.8
80°	933.5	873.7	816.5	699.4	582.4	462.8	345.8	309.4	270.4	234.0	195.0
82.5°	579.8	577.2	572.0	491.4	410.8	330.2	249.6	218.4	189.8	158.6	127.4
85°	265.2	309.4	351.0	306.8	262.6	218.4	174.2	153.4	132.6	109.2	88.4
87.5°	83.2	101.4	117.0	111.8	104.0	98.8	91.0	78.0	65.0	52.0	39.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015
 CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676015

CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1
2.5°	1820.1	1812.3	1801.9	1791.5	1778.5	1768.1	1755.1	1742.1	1739.5	1734.3	1731.7
5°	1567.9	1552.3	1534.1	1518.5	1502.9	1484.7	1469.1	1450.9	1437.9	1422.3	1409.3
7.5°	1346.9	1320.9	1292.3	1263.7	1237.7	1211.7	1183.1	1157.1	1144.1	1131.1	1118.1
10°	1170.1	1144.1	1120.7	1094.7	1076.5	1060.9	1042.7	1024.5	1008.9	993.3	977.7
12.5°	1081.7	1063.5	1045.3	1027.1	1006.3	988.1	967.3	946.5	928.3	912.7	894.5
15°	1027.1	1001.1	972.5	946.5	917.9	891.9	863.3	834.7	813.9	795.7	774.9
17.5°	962.1	923.1	886.7	847.7	816.5	785.3	751.4	720.2	696.8	670.8	647.4
20°	889.3	845.1	798.3	754.1	717.6	683.8	647.4	611.0	585.0	556.4	530.4
22.5°	826.9	769.7	709.8	650.0	611.0	572.0	530.4	491.4	468.0	442.0	418.6
25°	759.3	696.8	631.8	566.8	527.8	486.2	447.2	405.6	387.4	371.8	353.6
27.5°	722.8	660.4	595.4	533.0	496.6	457.6	421.2	382.2	369.2	353.6	340.6
30°	650.0	590.2	527.8	465.4	439.4	416.0	390.0	364.0	358.8	356.2	351.0
32.5°	585.0	522.6	460.2	397.8	374.4	351.0	327.6	304.2	301.6	296.4	293.8
35°	551.2	491.4	429.0	369.2	348.4	325.0	304.2	280.8	275.6	267.8	262.6
37.5°	543.4	481.0	416.0	353.6	332.8	312.0	288.6	267.8	262.6	257.4	252.2
40°	522.6	462.8	405.6	345.8	325.0	304.2	280.8	260.0	254.8	249.6	244.4
42.5°	507.0	449.8	390.0	330.2	312.0	293.8	273.0	254.8	249.6	244.4	236.6
45°	494.0	434.2	371.8	312.0	299.0	286.0	270.4	257.4	252.2	244.4	239.2
47.5°	473.2	416.0	356.2	296.4	283.4	273.0	260.0	247.0	241.8	236.6	231.4
50°	457.6	397.8	338.0	278.2	267.8	257.4	247.0	236.6	236.6	239.2	239.2
52.5°	436.8	379.6	322.4	265.2	254.8	244.4	234.0	223.6	226.2	228.8	231.4
55°	418.6	364.0	306.8	249.6	239.2	228.8	215.8	205.4	208.0	210.6	213.2
57.5°	410.8	353.6	296.4	239.2	228.8	215.8	205.4	192.4	192.4	192.4	192.4
60°	405.6	345.8	288.6	228.8	215.8	205.4	192.4	179.4	176.8	176.8	174.2
62.5°	403.0	343.2	286.0	226.2	210.6	197.6	182.0	166.4	163.8	161.2	158.6
65°	392.6	338.0	280.8	223.6	205.4	189.8	171.6	153.4	150.8	150.8	148.2
67.5°	390.0	332.8	278.2	221.0	202.8	182.0	163.8	143.0	140.4	137.8	135.2
70°	369.2	319.8	267.8	215.8	195.0	176.8	156.0	135.2	132.6	127.4	124.8
72.5°	343.2	299.0	252.2	205.4	184.6	163.8	143.0	122.2	119.6	117.0	111.8
75°	304.2	262.6	221.0	179.4	161.2	145.6	127.4	109.2	106.6	104.0	98.8
77.5°	249.6	215.8	184.6	150.8	137.8	124.8	111.8	98.8	96.2	93.6	88.4
80°	176.8	156.0	137.8	117.0	109.2	98.8	91.0	80.6	80.6	78.0	78.0
82.5°	117.0	106.6	96.2	85.8	80.6	75.4	70.2	65.0	65.0	62.4	62.4
85°	83.2	78.0	70.2	65.0	62.4	57.2	54.6	49.4	49.4	49.4	49.4
87.5°	39.0	39.0	36.4	36.4	33.8	33.8	31.2	28.6	28.6	28.6	28.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015

CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015

CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1
2.5°	1726.5	1718.7	1710.9	1700.5	1692.7	1682.3	1669.3	1658.9	1645.9	1645.9	1643.3
5°	1393.7	1385.9	1378.1	1367.7	1359.9	1349.5	1341.7	1331.3	1320.9	1320.9	1318.3
7.5°	1105.1	1089.5	1073.9	1055.7	1040.1	1029.7	1019.3	1006.3	995.9	988.1	980.3
10°	962.1	946.5	928.3	912.7	894.5	881.5	868.5	852.9	839.9	829.5	819.1
12.5°	876.3	858.1	839.9	821.7	803.5	785.3	769.7	751.4	733.2	720.2	707.2
15°	754.1	735.8	717.6	699.4	681.2	660.4	639.6	616.2	595.4	585.0	577.2
17.5°	621.4	603.2	582.4	564.2	543.4	527.8	512.2	496.6	481.0	470.6	462.8
20°	501.8	481.0	460.2	439.4	418.6	408.2	397.8	387.4	377.0	369.2	364.0
22.5°	392.6	379.6	369.2	356.2	343.2	335.4	330.2	322.4	314.6	314.6	314.6
25°	335.4	327.6	322.4	314.6	306.8	304.2	301.6	296.4	293.8	291.2	291.2
27.5°	325.0	317.2	309.4	301.6	293.8	291.2	288.6	283.4	280.8	280.8	280.8
30°	345.8	343.2	340.6	338.0	335.4	330.2	322.4	317.2	309.4	304.2	299.0
32.5°	288.6	286.0	286.0	283.4	280.8	286.0	288.6	293.8	296.4	299.0	301.6
35°	254.8	249.6	244.4	239.2	234.0	231.4	228.8	226.2	223.6	223.6	221.0
37.5°	247.0	241.8	236.6	231.4	226.2	223.6	221.0	218.4	215.8	215.8	213.2
40°	239.2	234.0	231.4	226.2	221.0	218.4	215.8	210.6	208.0	205.4	205.4
42.5°	231.4	228.8	223.6	221.0	215.8	213.2	210.6	205.4	202.8	200.2	197.6
45°	231.4	226.2	221.0	215.8	210.6	208.0	202.8	200.2	195.0	195.0	192.4
47.5°	226.2	221.0	215.8	210.6	205.4	202.8	197.6	195.0	189.8	187.2	184.6
50°	239.2	231.4	221.0	213.2	202.8	200.2	195.0	192.4	187.2	184.6	182.0
52.5°	234.0	226.2	215.8	208.0	197.6	192.4	189.8	184.6	179.4	176.8	174.2
55°	215.8	208.0	202.8	195.0	187.2	182.0	176.8	171.6	166.4	163.8	163.8
57.5°	192.4	189.8	187.2	184.6	182.0	176.8	171.6	163.8	158.6	156.0	153.4
60°	171.6	174.2	176.8	179.4	182.0	174.2	166.4	158.6	150.8	148.2	145.6
62.5°	156.0	161.2	166.4	169.0	174.2	166.4	158.6	150.8	143.0	140.4	137.8
65°	145.6	148.2	148.2	150.8	150.8	145.6	143.0	137.8	132.6	130.0	130.0
67.5°	132.6	132.6	132.6	130.0	130.0	127.4	127.4	124.8	122.2	119.6	119.6
70°	119.6	119.6	119.6	117.0	117.0	114.4	114.4	111.8	109.2	109.2	106.6
72.5°	109.2	109.2	106.6	106.6	104.0	104.0	104.0	101.4	101.4	98.8	98.8
75°	96.2	96.2	93.6	93.6	91.0	91.0	91.0	88.4	88.4	88.4	85.8
77.5°	85.8	85.8	83.2	83.2	80.6	80.6	80.6	78.0	78.0	75.4	75.4
80°	75.4	75.4	72.8	72.8	70.2	70.2	67.6	67.6	65.0	65.0	62.4
82.5°	59.8	59.8	59.8	59.8	59.8	57.2	57.2	54.6	52.0	52.0	49.4
85°	49.4	49.4	49.4	46.8	46.8	46.8	44.2	44.2	41.6	39.0	39.0
87.5°	28.6	28.6	28.6	26.0	26.0	26.0	26.0	26.0	26.0	26.0	23.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015
 CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015

CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1
2.5°	1643.3	1640.7	1630.3	1619.9	1630.3	1640.7	1640.7	1640.7	1638.1	1638.1	1638.1
5°	1318.3	1315.7	1310.5	1305.3	1305.3	1302.7	1307.9	1313.1	1318.3	1323.5	1328.7
7.5°	969.9	962.1	954.3	946.5	951.7	954.3	962.1	967.3	975.1	980.3	993.3
10°	808.7	798.3	790.5	782.7	777.5	772.3	767.1	764.5	759.3	754.1	759.3
12.5°	691.6	678.6	665.6	650.0	647.4	644.8	639.6	634.4	629.2	624.0	621.4
15°	566.8	556.4	551.2	543.4	533.0	522.6	517.4	514.8	509.6	504.4	501.8
17.5°	452.4	442.0	434.2	426.4	423.8	418.6	418.6	418.6	418.6	418.6	418.6
20°	356.2	348.4	348.4	345.8	345.8	343.2	345.8	348.4	348.4	351.0	353.6
22.5°	312.0	312.0	309.4	306.8	309.4	309.4	312.0	314.6	317.2	319.8	322.4
25°	288.6	286.0	288.6	291.2	291.2	291.2	293.8	293.8	296.4	296.4	296.4
27.5°	278.2	278.2	280.8	280.8	283.4	283.4	283.4	280.8	280.8	278.2	278.2
30°	293.8	288.6	288.6	288.6	286.0	283.4	280.8	280.8	278.2	275.6	273.0
32.5°	304.2	306.8	304.2	299.0	296.4	291.2	288.6	283.4	280.8	275.6	270.4
35°	221.0	218.4	223.6	226.2	228.8	231.4	234.0	236.6	236.6	239.2	239.2
37.5°	213.2	210.6	210.6	208.0	208.0	208.0	208.0	208.0	205.4	205.4	208.0
40°	202.8	200.2	200.2	197.6	197.6	195.0	195.0	195.0	195.0	195.0	195.0
42.5°	195.0	192.4	192.4	192.4	192.4	189.8	189.8	187.2	187.2	184.6	184.6
45°	192.4	189.8	187.2	184.6	184.6	182.0	182.0	182.0	179.4	179.4	179.4
47.5°	182.0	179.4	179.4	176.8	176.8	174.2	174.2	174.2	171.6	171.6	171.6
50°	176.8	174.2	174.2	171.6	171.6	169.0	169.0	169.0	166.4	166.4	166.4
52.5°	169.0	166.4	166.4	166.4	163.8	161.2	161.2	161.2	158.6	158.6	158.6
55°	161.2	158.6	158.6	158.6	156.0	153.4	153.4	153.4	150.8	150.8	150.8
57.5°	150.8	148.2	148.2	145.6	145.6	145.6	145.6	145.6	143.0	143.0	143.0
60°	143.0	140.4	140.4	137.8	137.8	135.2	135.2	135.2	135.2	135.2	135.2
62.5°	135.2	132.6	130.0	127.4	130.0	130.0	130.0	130.0	127.4	127.4	127.4
65°	127.4	124.8	122.2	119.6	119.6	119.6	119.6	119.6	119.6	119.6	119.6
67.5°	117.0	114.4	111.8	109.2	111.8	111.8	111.8	111.8	111.8	111.8	111.8
70°	106.6	104.0	104.0	101.4	101.4	98.8	98.8	101.4	101.4	101.4	101.4
72.5°	96.2	93.6	93.6	91.0	91.0	91.0	91.0	91.0	91.0	91.0	91.0
75°	85.8	83.2	83.2	80.6	80.6	80.6	80.6	80.6	80.6	80.6	80.6
77.5°	72.8	70.2	70.2	70.2	70.2	70.2	70.2	72.8	72.8	72.8	72.8
80°	62.4	59.8	59.8	59.8	59.8	59.8	59.8	59.8	59.8	59.8	59.8
82.5°	49.4	46.8	46.8	46.8	46.8	46.8	46.8	46.8	46.8	46.8	46.8
85°	36.4	33.8	33.8	33.8	36.4	36.4	36.4	36.4	36.4	36.4	36.4
87.5°	23.4	20.8	20.8	20.8	23.4	23.4	23.4	23.4	20.8	20.8	20.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015
 CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676015

CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1
2.5°	1638.1	1638.1	1638.1	1635.5	1632.9	1630.3	1627.7	1635.5	1640.7	1648.5	1653.7
5°	1331.3	1336.5	1339.1	1346.9	1354.7	1362.5	1370.3	1375.5	1380.7	1383.3	1388.5
7.5°	1003.7	1016.7	1027.1	1037.5	1047.9	1055.7	1066.1	1073.9	1081.7	1089.5	1097.3
10°	761.9	767.1	769.7	780.1	787.9	798.3	806.1	813.9	821.7	826.9	834.7
12.5°	618.8	613.6	611.0	611.0	611.0	611.0	611.0	616.2	621.4	626.6	631.8
15°	499.2	496.6	494.0	491.4	488.8	483.6	481.0	486.2	491.4	496.6	501.8
17.5°	418.6	418.6	418.6	416.0	413.4	410.8	408.2	410.8	413.4	413.4	416.0
20°	358.8	361.4	364.0	366.6	366.6	369.2	369.2	371.8	374.4	374.4	377.0
22.5°	322.4	325.0	325.0	325.0	327.6	327.6	327.6	330.2	332.8	335.4	338.0
25°	293.8	293.8	291.2	291.2	293.8	293.8	293.8	293.8	296.4	296.4	296.4
27.5°	278.2	275.6	275.6	275.6	275.6	273.0	273.0	273.0	273.0	273.0	273.0
30°	270.4	267.8	265.2	262.6	262.6	260.0	257.4	257.4	257.4	257.4	257.4
32.5°	267.8	262.6	257.4	254.8	254.8	252.2	249.6	247.0	247.0	244.4	241.8
35°	239.2	236.6	236.6	234.0	231.4	228.8	226.2	226.2	226.2	223.6	223.6
37.5°	208.0	210.6	210.6	210.6	213.2	213.2	213.2	213.2	215.8	215.8	215.8
40°	195.0	195.0	195.0	197.6	200.2	200.2	202.8	202.8	205.4	205.4	205.4
42.5°	184.6	182.0	182.0	184.6	184.6	187.2	187.2	189.8	192.4	192.4	195.0
45°	179.4	176.8	176.8	176.8	176.8	174.2	174.2	176.8	179.4	182.0	184.6
47.5°	169.0	169.0	166.4	166.4	166.4	166.4	166.4	166.4	169.0	169.0	169.0
50°	163.8	163.8	161.2	161.2	161.2	161.2	161.2	161.2	161.2	161.2	161.2
52.5°	158.6	156.0	156.0	156.0	156.0	153.4	153.4	153.4	153.4	153.4	153.4
55°	150.8	148.2	148.2	148.2	148.2	148.2	148.2	148.2	150.8	150.8	150.8
57.5°	143.0	140.4	140.4	140.4	143.0	143.0	143.0	143.0	145.6	145.6	145.6
60°	135.2	135.2	135.2	135.2	135.2	135.2	135.2	137.8	137.8	140.4	140.4
62.5°	127.4	127.4	127.4	127.4	130.0	130.0	130.0	130.0	132.6	132.6	132.6
65°	119.6	119.6	119.6	119.6	122.2	122.2	122.2	122.2	122.2	122.2	122.2
67.5°	111.8	111.8	111.8	111.8	111.8	111.8	111.8	114.4	114.4	117.0	117.0
70°	101.4	98.8	98.8	101.4	101.4	104.0	104.0	106.6	106.6	109.2	109.2
72.5°	91.0	91.0	91.0	91.0	91.0	91.0	91.0	93.6	96.2	96.2	98.8
75°	80.6	80.6	80.6	80.6	83.2	83.2	83.2	85.8	85.8	88.4	88.4
77.5°	72.8	70.2	70.2	70.2	72.8	72.8	72.8	75.4	75.4	78.0	78.0
80°	59.8	59.8	59.8	59.8	62.4	62.4	62.4	62.4	65.0	65.0	65.0
82.5°	49.4	49.4	49.4	49.4	49.4	49.4	49.4	49.4	52.0	52.0	52.0
85°	36.4	36.4	36.4	36.4	39.0	39.0	39.0	39.0	39.0	39.0	39.0
87.5°	23.4	23.4	23.4	23.4	23.4	23.4	23.4	23.4	26.0	26.0	26.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015
 CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015

CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1
2.5°	1653.7	1653.7	1653.7	1653.7	1658.9	1661.5	1666.7	1669.3	1666.7	1664.1	1658.9
5°	1391.1	1393.7	1393.7	1396.3	1396.3	1396.3	1396.3	1396.3	1401.5	1406.7	1411.9
7.5°	1099.9	1102.5	1105.1	1107.7	1107.7	1107.7	1105.1	1105.1	1107.7	1107.7	1110.3
10°	842.5	852.9	860.7	868.5	863.3	855.5	850.3	842.5	842.5	842.5	839.9
12.5°	637.0	639.6	644.8	647.4	644.8	644.8	642.2	639.6	642.2	647.4	650.0
15°	504.4	504.4	507.0	507.0	509.6	512.2	512.2	514.8	520.0	522.6	527.8
17.5°	418.6	421.2	421.2	423.8	423.8	426.4	426.4	426.4	431.6	436.8	444.6
20°	377.0	377.0	377.0	377.0	377.0	374.4	374.4	371.8	374.4	379.6	382.2
22.5°	338.0	340.6	340.6	340.6	338.0	335.4	330.2	327.6	327.6	330.2	330.2
25°	296.4	293.8	293.8	291.2	291.2	293.8	293.8	293.8	296.4	296.4	299.0
27.5°	273.0	270.4	270.4	267.8	267.8	270.4	270.4	270.4	270.4	270.4	270.4
30°	254.8	254.8	252.2	249.6	252.2	252.2	254.8	254.8	257.4	257.4	260.0
32.5°	241.8	239.2	239.2	236.6	239.2	239.2	241.8	241.8	244.4	247.0	247.0
35°	223.6	223.6	223.6	223.6	223.6	223.6	221.0	221.0	221.0	221.0	221.0
37.5°	213.2	213.2	210.6	208.0	208.0	208.0	208.0	208.0	205.4	202.8	200.2
40°	205.4	202.8	202.8	200.2	197.6	197.6	195.0	192.4	192.4	189.8	189.8
42.5°	195.0	192.4	192.4	189.8	187.2	187.2	184.6	182.0	182.0	182.0	179.4
45°	182.0	182.0	179.4	176.8	176.8	176.8	174.2	174.2	174.2	174.2	171.6
47.5°	169.0	169.0	166.4	166.4	166.4	166.4	163.8	163.8	163.8	163.8	163.8
50°	161.2	161.2	161.2	161.2	161.2	161.2	158.6	158.6	158.6	158.6	158.6
52.5°	153.4	153.4	153.4	153.4	153.4	153.4	153.4	153.4	153.4	153.4	153.4
55°	150.8	150.8	150.8	150.8	150.8	150.8	148.2	148.2	148.2	150.8	150.8
57.5°	145.6	145.6	143.0	143.0	143.0	143.0	143.0	143.0	143.0	143.0	143.0
60°	140.4	140.4	140.4	140.4	140.4	140.4	140.4	140.4	140.4	140.4	140.4
62.5°	132.6	132.6	132.6	132.6	132.6	135.2	135.2	135.2	135.2	135.2	132.6
65°	122.2	124.8	124.8	124.8	124.8	124.8	124.8	124.8	124.8	124.8	124.8
67.5°	117.0	117.0	117.0	117.0	117.0	117.0	117.0	117.0	117.0	117.0	117.0
70°	109.2	109.2	106.6	106.6	106.6	109.2	109.2	109.2	109.2	109.2	109.2
72.5°	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	101.4	101.4
75°	88.4	88.4	88.4	88.4	88.4	88.4	88.4	88.4	88.4	88.4	88.4
77.5°	78.0	78.0	75.4	75.4	75.4	78.0	78.0	78.0	78.0	80.6	80.6
80°	65.0	65.0	65.0	65.0	65.0	65.0	65.0	65.0	65.0	67.6	67.6
82.5°	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0	52.0	54.6	54.6
85°	39.0	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6	44.2	44.2
87.5°	26.0	26.0	26.0	26.0	26.0	26.0	23.4	23.4	23.4	23.4	20.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015
 CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015

CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1
2.5°	1656.3	1658.9	1661.5	1661.5	1664.1	1666.7	1666.7	1677.1	1687.5	1692.7	1697.9
5°	1417.1	1414.5	1414.5	1411.9	1409.3	1417.1	1424.9	1440.5	1456.1	1458.7	1463.9
7.5°	1110.3	1112.9	1115.5	1115.5	1118.1	1110.3	1099.9	1102.5	1105.1	1118.1	1128.5
10°	839.9	842.5	845.1	845.1	847.7	845.1	839.9	847.7	855.5	865.9	878.9
12.5°	652.6	660.4	668.2	673.4	681.2	686.4	689.0	699.4	707.2	720.2	733.2
15°	533.0	538.2	543.4	548.6	553.8	559.0	564.2	574.6	585.0	600.6	616.2
17.5°	449.8	449.8	452.4	452.4	452.4	457.6	462.8	468.0	470.6	486.2	501.8
20°	384.8	382.2	379.6	377.0	374.4	379.6	382.2	384.8	387.4	397.8	405.6
22.5°	330.2	330.2	332.8	332.8	332.8	330.2	325.0	327.6	327.6	332.8	340.6
25°	299.0	299.0	299.0	296.4	296.4	299.0	301.6	301.6	299.0	301.6	304.2
27.5°	270.4	273.0	273.0	275.6	275.6	278.2	278.2	278.2	278.2	280.8	283.4
30°	260.0	260.0	262.6	262.6	262.6	265.2	267.8	267.8	267.8	270.4	275.6
32.5°	249.6	252.2	254.8	257.4	260.0	262.6	262.6	265.2	265.2	267.8	270.4
35°	221.0	218.4	218.4	215.8	213.2	213.2	213.2	213.2	210.6	213.2	213.2
37.5°	197.6	197.6	197.6	195.0	195.0	197.6	197.6	197.6	197.6	200.2	200.2
40°	187.2	187.2	187.2	187.2	187.2	187.2	187.2	189.8	189.8	192.4	195.0
42.5°	179.4	179.4	179.4	179.4	179.4	182.0	182.0	182.0	182.0	184.6	184.6
45°	171.6	171.6	171.6	171.6	171.6	171.6	171.6	174.2	174.2	176.8	179.4
47.5°	163.8	163.8	163.8	163.8	163.8	166.4	169.0	169.0	169.0	171.6	171.6
50°	158.6	158.6	158.6	158.6	158.6	161.2	161.2	163.8	163.8	166.4	169.0
52.5°	153.4	153.4	153.4	153.4	153.4	156.0	156.0	158.6	158.6	161.2	163.8
55°	150.8	150.8	150.8	148.2	148.2	150.8	150.8	153.4	153.4	156.0	156.0
57.5°	143.0	143.0	143.0	143.0	143.0	143.0	143.0	145.6	145.6	148.2	150.8
60°	140.4	140.4	137.8	137.8	135.2	137.8	137.8	140.4	140.4	143.0	143.0
62.5°	132.6	132.6	132.6	130.0	130.0	132.6	132.6	132.6	132.6	135.2	137.8
65°	124.8	124.8	124.8	122.2	122.2	124.8	124.8	124.8	124.8	127.4	130.0
67.5°	117.0	117.0	117.0	114.4	114.4	114.4	114.4	117.0	117.0	119.6	122.2
70°	109.2	109.2	109.2	106.6	106.6	106.6	104.0	106.6	109.2	111.8	111.8
72.5°	101.4	101.4	101.4	98.8	98.8	98.8	96.2	98.8	98.8	101.4	101.4
75°	88.4	88.4	88.4	88.4	88.4	88.4	85.8	85.8	85.8	88.4	88.4
77.5°	80.6	80.6	80.6	78.0	78.0	78.0	75.4	75.4	75.4	78.0	78.0
80°	67.6	67.6	67.6	65.0	65.0	65.0	62.4	62.4	62.4	65.0	65.0
82.5°	54.6	54.6	54.6	52.0	52.0	52.0	49.4	49.4	49.4	52.0	52.0
85°	44.2	44.2	44.2	44.2	44.2	44.2	41.6	41.6	41.6	44.2	46.8
87.5°	20.8	20.8	23.4	23.4	23.4	23.4	20.8	20.8	18.2	18.2	20.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015
 CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676015

CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1
2.5°	1703.1	1708.3	1721.3	1731.7	1744.7	1755.1	1762.9	1773.3	1781.1	1788.9	1794.1
5°	1466.5	1469.1	1482.1	1495.1	1505.5	1518.5	1536.7	1554.9	1573.1	1591.3	1604.3
7.5°	1141.5	1151.9	1167.5	1185.7	1201.3	1216.9	1235.1	1255.9	1274.1	1292.3	1310.5
10°	889.3	899.7	915.3	930.9	943.9	959.5	980.3	1001.1	1021.9	1042.7	1063.5
12.5°	746.2	759.3	777.5	795.7	811.3	829.5	855.5	878.9	904.9	928.3	954.3
15°	629.2	644.8	668.2	694.2	717.6	741.0	767.1	793.1	816.5	842.5	868.5
17.5°	517.4	533.0	553.8	577.2	598.0	618.8	650.0	678.6	709.8	738.4	767.1
20°	416.0	423.8	444.6	465.4	486.2	507.0	530.4	553.8	577.2	600.6	637.0
22.5°	345.8	351.0	361.4	369.2	379.6	387.4	410.8	434.2	455.0	478.4	512.2
25°	304.2	306.8	314.6	319.8	327.6	332.8	348.4	361.4	377.0	390.0	421.2
27.5°	283.4	286.0	288.6	291.2	293.8	296.4	306.8	317.2	325.0	335.4	364.0
30°	278.2	280.8	288.6	293.8	301.6	306.8	312.0	317.2	322.4	327.6	345.8
32.5°	273.0	275.6	275.6	273.0	273.0	270.4	275.6	278.2	283.4	286.0	301.6
35°	215.8	215.8	218.4	221.0	223.6	226.2	234.0	239.2	247.0	252.2	265.2
37.5°	202.8	202.8	205.4	210.6	213.2	215.8	221.0	226.2	231.4	236.6	249.6
40°	195.0	197.6	200.2	202.8	205.4	208.0	213.2	215.8	221.0	223.6	234.0
42.5°	187.2	187.2	189.8	195.0	197.6	200.2	205.4	208.0	213.2	215.8	226.2
45°	182.0	184.6	187.2	189.8	189.8	192.4	197.6	202.8	205.4	210.6	221.0
47.5°	174.2	174.2	179.4	182.0	187.2	189.8	195.0	197.6	202.8	205.4	215.8
50°	169.0	171.6	176.8	179.4	184.6	187.2	195.0	200.2	208.0	213.2	218.4
52.5°	163.8	166.4	171.6	174.2	179.4	182.0	192.4	202.8	210.6	221.0	221.0
55°	158.6	158.6	163.8	171.6	176.8	182.0	187.2	195.0	200.2	205.4	205.4
57.5°	150.8	153.4	158.6	166.4	171.6	176.8	182.0	187.2	189.8	195.0	192.4
60°	145.6	145.6	153.4	161.2	169.0	176.8	176.8	176.8	174.2	174.2	174.2
62.5°	137.8	140.4	150.8	163.8	174.2	184.6	176.8	169.0	161.2	153.4	156.0
65°	132.6	135.2	140.4	148.2	153.4	158.6	153.4	150.8	145.6	140.4	143.0
67.5°	122.2	124.8	127.4	127.4	130.0	130.0	130.0	130.0	130.0	130.0	132.6
70°	114.4	114.4	114.4	117.0	117.0	117.0	117.0	117.0	117.0	117.0	119.6
72.5°	104.0	104.0	104.0	104.0	104.0	104.0	104.0	104.0	104.0	104.0	106.6
75°	91.0	91.0	91.0	91.0	91.0	91.0	91.0	91.0	91.0	91.0	93.6
77.5°	80.6	80.6	80.6	80.6	80.6	80.6	80.6	80.6	78.0	78.0	80.6
80°	67.6	67.6	67.6	67.6	65.0	65.0	65.0	65.0	65.0	65.0	67.6
82.5°	54.6	54.6	54.6	54.6	52.0	52.0	52.0	52.0	49.4	49.4	52.0
85°	49.4	52.0	52.0	54.6	54.6	54.6	52.0	49.4	46.8	44.2	44.2
87.5°	20.8	20.8	20.8	20.8	18.2	18.2	18.2	18.2	18.2	18.2	18.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015
 CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015

CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1
2.5°	1801.9	1807.1	1812.3	1820.1	1830.5	1838.3	1846.1	1861.7	1879.9	1895.5	1911.1
5°	1617.3	1630.3	1643.3	1658.9	1674.5	1687.5	1703.1	1734.3	1765.5	1794.1	1825.3
7.5°	1326.1	1344.3	1359.9	1385.9	1409.3	1435.3	1458.7	1497.7	1534.1	1573.1	1609.5
10°	1084.3	1105.1	1125.9	1159.7	1196.1	1229.9	1263.7	1294.9	1328.7	1359.9	1391.1
12.5°	980.3	1003.7	1029.7	1050.5	1073.9	1094.7	1115.5	1151.9	1188.3	1224.7	1261.1
15°	894.5	920.5	946.5	972.5	995.9	1021.9	1045.3	1076.5	1110.3	1141.5	1172.7
17.5°	795.7	821.7	850.3	878.9	907.5	936.1	964.7	1008.9	1053.1	1094.7	1138.9
20°	670.8	707.2	741.0	780.1	819.1	858.1	897.1	943.9	990.7	1034.9	1081.7
22.5°	546.0	579.8	613.6	660.4	707.2	751.4	798.3	860.7	920.5	982.9	1042.7
25°	455.0	486.2	517.4	569.4	618.8	670.8	720.2	795.7	868.5	943.9	1016.7
27.5°	392.6	421.2	449.8	504.4	559.0	611.0	665.6	748.8	829.5	912.7	993.3
30°	364.0	382.2	400.4	452.4	504.4	553.8	605.8	686.4	767.1	847.7	928.3
32.5°	317.2	332.8	348.4	395.2	442.0	486.2	533.0	616.2	696.8	780.1	860.7
35°	280.8	293.8	306.8	351.0	392.6	436.8	478.4	561.6	644.8	728.0	811.3
37.5°	260.0	273.0	283.4	322.4	364.0	403.0	442.0	525.2	605.8	689.0	769.7
40°	244.4	252.2	262.6	301.6	338.0	377.0	413.4	488.8	566.8	642.2	717.6
42.5°	234.0	244.4	252.2	286.0	322.4	356.2	390.0	462.8	535.6	605.8	678.6
45°	231.4	241.8	252.2	280.8	309.4	335.4	364.0	434.2	504.4	574.6	644.8
47.5°	226.2	234.0	244.4	267.8	288.6	312.0	332.8	403.0	473.2	540.8	611.0
50°	223.6	226.2	231.4	252.2	273.0	293.8	314.6	384.8	455.0	525.2	595.4
52.5°	221.0	221.0	221.0	239.2	257.4	273.0	291.2	361.4	434.2	504.4	574.6
55°	205.4	202.8	202.8	221.0	236.6	254.8	270.4	340.6	410.8	478.4	548.6
57.5°	189.8	187.2	184.6	200.2	215.8	231.4	247.0	317.2	390.0	460.2	530.4
60°	174.2	171.6	171.6	187.2	200.2	215.8	228.8	301.6	371.8	444.6	514.8
62.5°	156.0	158.6	158.6	171.6	187.2	200.2	213.2	286.0	361.4	434.2	507.0
65°	143.0	145.6	145.6	161.2	176.8	192.4	208.0	278.2	351.0	421.2	491.4
67.5°	132.6	135.2	135.2	153.4	169.0	187.2	202.8	265.2	330.2	392.6	455.0
70°	122.2	122.2	124.8	143.0	161.2	179.4	197.6	252.2	306.8	358.8	413.4
72.5°	109.2	111.8	114.4	132.6	148.2	166.4	182.0	231.4	280.8	330.2	379.6
75°	96.2	98.8	101.4	117.0	132.6	148.2	163.8	210.6	254.8	301.6	345.8
77.5°	85.8	88.4	91.0	104.0	117.0	130.0	143.0	176.8	213.2	247.0	280.8
80°	70.2	70.2	72.8	83.2	93.6	101.4	111.8	135.2	158.6	179.4	202.8
82.5°	52.0	54.6	54.6	62.4	67.6	75.4	80.6	93.6	104.0	117.0	127.4
85°	44.2	41.6	41.6	46.8	49.4	54.6	57.2	65.0	70.2	78.0	83.2
87.5°	18.2	15.6	15.6	18.2	23.4	26.0	28.6	28.6	31.2	31.2	31.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015
 CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676015

CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1
2.5°	1918.9	1924.1	1931.9	1937.1	1950.1	1960.5	1973.5	1983.9	1991.7	2004.7	1999.5
5°	1848.7	1872.1	1895.5	1918.9	1937.1	1955.3	1970.9	1989.1	2009.9	2048.9	2059.3
7.5°	1640.7	1671.9	1700.5	1731.7	1768.1	1804.5	1840.9	1877.3	1911.1	1960.5	1991.7
10°	1435.3	1479.5	1521.1	1565.3	1599.1	1632.9	1664.1	1697.9	1744.7	1794.1	1851.3
12.5°	1305.3	1349.5	1393.7	1437.9	1487.3	1534.1	1583.5	1630.3	1674.5	1713.5	1778.5
15°	1219.5	1268.9	1315.7	1362.5	1422.3	1479.5	1539.3	1596.5	1661.5	1713.5	1757.7
17.5°	1198.7	1258.5	1315.7	1375.5	1437.9	1500.3	1562.7	1625.1	1690.1	1768.1	1825.3
20°	1162.3	1242.9	1323.5	1404.1	1484.7	1562.7	1643.3	1721.3	1807.1	1900.7	1926.7
22.5°	1141.5	1237.7	1336.5	1432.7	1541.9	1653.7	1762.9	1872.1	1963.1	2033.3	2111.3
25°	1138.9	1258.5	1380.7	1500.3	1638.1	1773.3	1911.1	2046.3	2163.3	2233.5	2296.0
27.5°	1136.3	1281.9	1424.9	1567.9	1736.9	1903.3	2072.3	2238.7	2348.0	2449.4	2501.4
30°	1105.1	1279.3	1456.1	1630.3	1820.1	2009.9	2199.7	2389.6	2501.4	2571.6	2597.6
32.5°	1066.1	1271.5	1476.9	1682.3	1898.1	2113.9	2327.2	2543.0	2631.4	2691.2	2670.4
35°	1034.9	1261.1	1484.7	1708.3	1937.1	2168.5	2397.4	2626.2	2753.6	2836.8	2803.0
37.5°	1006.3	1242.9	1479.5	1716.1	1983.9	2251.7	2519.6	2787.4	2909.6	2998.0	2959.0
40°	972.5	1224.7	1479.5	1731.7	2038.5	2342.8	2649.6	2953.8	3112.4	3187.8	3128.0
42.5°	943.9	1206.5	1471.7	1734.3	2061.9	2389.6	2717.2	3044.8	3221.6	3328.2	3252.8
45°	907.5	1170.1	1430.1	1692.7	2054.1	2415.6	2774.4	3135.8	3341.2	3424.4	3320.4
47.5°	868.5	1128.5	1385.9	1643.3	2028.1	2413.0	2797.8	3182.6	3372.4	3471.2	3375.0
50°	855.5	1115.5	1372.9	1632.9	2048.9	2467.6	2883.6	3299.6	3437.4	3518.0	3390.6
52.5°	852.9	1128.5	1406.7	1682.3	2100.9	2517.0	2935.6	3351.6	3463.4	3549.2	3434.8
55°	845.1	1144.1	1440.5	1736.9	2173.7	2613.2	3050.0	3486.8	3598.6	3661.0	3575.2
57.5°	852.9	1175.3	1495.1	1817.5	2267.4	2717.2	3167.0	3616.8	3752.0	3796.3	3778.1
60°	858.1	1201.3	1541.9	1885.1	2324.6	2764.0	3203.4	3642.8	3783.3	3892.5	3913.3
62.5°	845.1	1183.1	1518.5	1856.5	2254.3	2652.2	3050.0	3447.8	3679.2	3840.5	3934.1
65°	806.1	1118.1	1432.7	1744.7	2111.3	2480.6	2847.2	3213.8	3458.2	3697.4	3772.9
67.5°	720.2	985.5	1250.7	1515.9	1835.7	2155.5	2472.8	2792.6	3099.4	3330.8	3434.8
70°	624.0	832.1	1042.7	1250.7	1541.9	1833.1	2124.3	2415.6	2686.0	2940.8	3039.6
72.5°	543.4	704.6	868.5	1029.7	1237.7	1443.1	1651.1	1856.5	2176.3	2431.2	2527.4
75°	462.8	579.8	694.2	811.3	954.3	1097.3	1237.7	1380.7	1606.9	1835.7	1931.9
77.5°	356.2	434.2	509.6	585.0	683.8	780.1	878.9	975.1	1133.7	1305.3	1354.7
80°	247.0	291.2	332.8	377.0	455.0	533.0	611.0	689.0	793.1	889.3	964.7
82.5°	153.4	182.0	208.0	234.0	296.4	358.8	418.6	481.0	522.6	527.8	603.2
85°	98.8	117.0	132.6	148.2	184.6	223.6	260.0	296.4	265.2	247.0	293.8
87.5°	39.0	49.4	57.2	65.0	62.4	59.8	57.2	54.6	46.8	41.6	52.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015
 CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015

CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1
2.5°	2004.7	2012.5	2020.3	2025.5	2033.3	2035.9	2038.5	2038.5	2041.1	2043.7	2048.9
5°	2100.9	2116.5	2132.1	2145.1	2160.7	2173.7	2184.1	2197.1	2207.5	2207.5	2204.9
7.5°	2020.3	2059.3	2098.3	2137.3	2176.3	2204.9	2230.9	2259.5	2285.6	2290.8	2296.0
10°	1913.7	1955.3	1994.3	2035.9	2074.9	2119.1	2160.7	2202.3	2246.5	2254.3	2264.8
12.5°	1814.9	1864.3	1913.7	1960.5	2009.9	2041.1	2072.3	2100.9	2132.1	2152.9	2173.7
15°	1812.3	1853.9	1895.5	1934.5	1976.1	1994.3	2012.5	2028.1	2046.3	2046.3	2048.9
17.5°	1872.1	1898.1	1924.1	1947.5	1973.5	1976.1	1981.3	1983.9	1986.5	1978.7	1970.9
20°	1989.1	1999.5	2009.9	2020.3	2030.7	2012.5	1996.9	1978.7	1960.5	1939.7	1921.5
22.5°	2160.7	2137.3	2113.9	2090.5	2067.1	2035.9	2002.1	1970.9	1937.1	1911.1	1885.1
25°	2322.0	2293.4	2264.8	2236.1	2207.5	2139.9	2072.3	2002.1	1934.5	1905.9	1877.3
27.5°	2537.8	2493.6	2449.4	2405.2	2361.0	2270.0	2178.9	2087.9	1996.9	1947.5	1900.7
30°	2589.8	2540.4	2491.0	2439.0	2389.6	2301.2	2215.3	2126.9	2038.5	1981.3	1926.7
32.5°	2665.2	2608.0	2550.8	2493.6	2436.4	2350.6	2264.8	2176.3	2090.5	2038.5	1983.9
35°	2790.0	2725.0	2660.0	2592.4	2527.4	2439.0	2353.2	2264.8	2176.3	2116.5	2059.3
37.5°	2896.6	2821.2	2745.8	2670.4	2595.0	2517.0	2436.4	2358.4	2277.8	2217.9	2160.7
40°	3016.2	2933.0	2849.8	2769.2	2686.0	2613.2	2540.4	2465.0	2392.2	2345.4	2298.6
42.5°	3120.2	3018.8	2920.0	2821.2	2719.8	2670.4	2623.6	2574.2	2524.8	2501.4	2475.4
45°	3193.0	3099.4	3003.2	2909.6	2816.0	2779.6	2743.2	2706.8	2670.4	2693.8	2717.2
47.5°	3224.2	3148.8	3076.0	3003.2	2927.8	2940.8	2953.8	2964.2	2977.2	3008.4	3042.2
50°	3252.8	3211.2	3167.0	3125.4	3081.2	3130.6	3177.4	3226.8	3276.2	3341.2	3406.2
52.5°	3310.0	3286.6	3265.8	3242.4	3219.0	3304.8	3390.6	3476.4	3562.2	3635.0	3707.8
55°	3481.6	3463.4	3445.2	3424.4	3406.2	3528.4	3648.0	3770.3	3892.5	3967.9	4043.3
57.5°	3718.2	3707.8	3694.8	3684.4	3671.4	3791.1	3908.1	4025.1	4144.7	4217.5	4292.9
60°	3897.7	3900.3	3900.3	3902.9	3902.9	3993.9	4084.9	4178.5	4269.5	4331.9	4396.9
62.5°	3993.9	3988.7	3983.5	3978.3	3973.1	4048.5	4123.9	4199.3	4274.7	4321.5	4368.3
65°	3889.9	3918.5	3947.1	3975.7	4004.3	4014.7	4022.5	4032.9	4040.7	4069.3	4097.9
67.5°	3541.4	3598.6	3653.2	3710.4	3765.0	3726.0	3689.6	3650.6	3611.6	3619.4	3624.6
70°	3154.0	3219.0	3286.6	3351.6	3416.6	3325.6	3234.6	3141.0	3050.0	3018.8	2987.6
72.5°	2660.0	2717.2	2777.0	2834.2	2891.4	2779.6	2670.4	2558.6	2446.8	2392.2	2337.6
75°	2033.3	2100.9	2171.1	2238.7	2306.4	2181.5	2054.1	1929.3	1801.9	1765.5	1731.7
77.5°	1482.1	1562.7	1643.3	1723.9	1804.5	1692.7	1580.9	1466.5	1354.7	1333.9	1313.1
80°	1079.1	1141.5	1201.3	1263.7	1323.5	1258.5	1193.5	1128.5	1063.5	1060.9	1058.3
82.5°	728.0	782.7	834.7	889.3	941.3	915.3	891.9	865.9	839.9	865.9	894.5
85°	374.4	449.8	527.8	603.2	678.6	670.8	665.6	657.8	650.0	683.8	715.0
87.5°	75.4	140.4	205.4	267.8	332.8	317.2	301.6	283.4	267.8	278.2	286.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015
 CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015

CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1
2.5°	2051.5	2054.1	2054.1	2054.1	2054.1	2054.1	2048.9	2046.3	2041.1	2035.9	2028.1
5°	2204.9	2202.3	2191.9	2181.5	2168.5	2158.1	2150.3	2139.9	2132.1	2121.7	2106.1
7.5°	2301.2	2306.4	2288.2	2272.6	2254.3	2236.1	2217.9	2199.7	2181.5	2163.3	2126.9
10°	2272.6	2280.4	2270.0	2259.5	2246.5	2236.1	2215.3	2191.9	2171.1	2147.7	2103.5
12.5°	2191.9	2212.7	2207.5	2202.3	2197.1	2191.9	2178.9	2163.3	2150.3	2134.7	2085.3
15°	2048.9	2048.9	2051.5	2054.1	2054.1	2056.7	2059.3	2061.9	2064.5	2067.1	2038.5
17.5°	1963.1	1955.3	1955.3	1955.3	1955.3	1955.3	1965.7	1978.7	1989.1	1999.5	1991.7
20°	1900.7	1882.5	1879.9	1879.9	1877.3	1874.7	1892.9	1913.7	1931.9	1950.1	1960.5
22.5°	1859.1	1833.1	1830.5	1827.9	1825.3	1822.7	1846.1	1869.5	1892.9	1916.3	1952.7
25°	1848.7	1820.1	1822.7	1825.3	1825.3	1827.9	1846.1	1864.3	1882.5	1900.7	1963.1
27.5°	1851.3	1804.5	1807.1	1809.7	1809.7	1812.3	1840.9	1866.9	1895.5	1921.5	1999.5
30°	1869.5	1814.9	1809.7	1804.5	1799.3	1794.1	1833.1	1872.1	1911.1	1950.1	2009.9
32.5°	1931.9	1879.9	1866.9	1853.9	1840.9	1827.9	1874.7	1918.9	1965.7	2009.9	2059.3
35°	1999.5	1942.3	1937.1	1931.9	1924.1	1918.9	1960.5	2004.7	2046.3	2087.9	2132.1
37.5°	2100.9	2043.7	2038.5	2030.7	2025.5	2017.7	2064.5	2108.7	2155.5	2199.7	2238.7
40°	2251.7	2204.9	2202.3	2202.3	2199.7	2197.1	2233.5	2272.6	2309.0	2345.4	2371.4
42.5°	2452.0	2428.6	2436.4	2446.8	2454.6	2462.4	2491.0	2522.2	2550.8	2579.4	2571.6
45°	2740.6	2764.0	2766.6	2769.2	2771.8	2774.4	2782.2	2792.6	2800.4	2808.2	2777.0
47.5°	3073.4	3104.6	3120.2	3135.8	3148.8	3164.4	3154.0	3141.0	3130.6	3117.6	3039.6
50°	3468.6	3533.6	3531.0	3528.4	3523.2	3520.6	3499.8	3479.0	3455.6	3434.8	3320.4
52.5°	3780.7	3853.5	3866.5	3879.5	3892.5	3905.5	3866.5	3827.5	3785.9	3746.8	3603.8
55°	4116.1	4191.5	4194.1	4196.7	4196.7	4199.3	4144.7	4090.1	4032.9	3978.3	3830.1
57.5°	4365.7	4438.5	4430.7	4425.5	4417.7	4409.9	4344.9	4279.9	4214.9	4149.9	4001.7
60°	4459.3	4521.7	4506.1	4490.5	4472.3	4456.7	4407.3	4357.9	4305.9	4256.5	4113.5
62.5°	4415.1	4461.9	4438.5	4417.7	4394.3	4370.9	4308.5	4243.5	4181.1	4116.1	4012.1
65°	4123.9	4152.5	4121.3	4092.7	4064.1	4032.9	3980.9	3928.9	3874.3	3822.3	3752.0
67.5°	3632.4	3637.6	3635.0	3632.4	3629.8	3627.2	3551.8	3476.4	3398.4	3323.0	3317.8
70°	2959.0	2927.8	2933.0	2940.8	2946.0	2951.2	2894.0	2839.4	2782.2	2725.0	2751.0
72.5°	2283.0	2228.3	2241.3	2256.9	2270.0	2283.0	2236.1	2191.9	2145.1	2098.3	2134.7
75°	1695.3	1661.5	1674.5	1690.1	1703.1	1716.1	1697.9	1679.7	1658.9	1640.7	1674.5
77.5°	1292.3	1271.5	1274.1	1274.1	1276.7	1276.7	1279.3	1284.5	1287.1	1289.7	1326.1
80°	1053.1	1050.5	1047.9	1045.3	1040.1	1037.5	1063.5	1089.5	1115.5	1141.5	1159.7
82.5°	920.5	946.5	930.9	917.9	902.3	886.7	910.1	933.5	956.9	980.3	972.5
85°	748.8	780.1	751.4	722.8	691.6	663.0	683.8	702.0	722.8	741.0	730.6
87.5°	296.4	304.2	257.4	213.2	166.4	119.6	189.8	257.4	327.6	395.2	405.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015

CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676015

CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1	1872.1
2.5°	2020.3	2009.9	2002.1	1999.5	1994.3	1991.7	1986.5	1981.3	1973.5	1968.3	1960.5
5°	2087.9	2072.3	2054.1	2028.1	2004.7	1978.7	1952.7	1929.3	1905.9	1879.9	1856.5
7.5°	2090.5	2054.1	2017.7	1983.9	1947.5	1913.7	1877.3	1846.1	1812.3	1778.5	1747.3
10°	2061.9	2017.7	1973.5	1929.3	1887.7	1843.5	1799.3	1762.9	1723.9	1684.9	1648.5
12.5°	2038.5	1989.1	1939.7	1887.7	1838.3	1786.3	1734.3	1697.9	1661.5	1625.1	1588.7
15°	2009.9	1978.7	1950.1	1903.3	1856.5	1809.7	1762.9	1713.5	1666.7	1617.3	1567.9
17.5°	1986.5	1978.7	1970.9	1939.7	1908.5	1874.7	1843.5	1794.1	1744.7	1692.7	1643.3
20°	1973.5	1983.9	1994.3	1978.7	1963.1	1944.9	1929.3	1892.9	1856.5	1817.5	1781.1
22.5°	1989.1	2028.1	2064.5	2067.1	2072.3	2074.9	2077.5	2043.7	2009.9	1973.5	1939.7
25°	2025.5	2087.9	2150.3	2184.1	2217.9	2254.3	2288.2	2267.4	2246.5	2225.7	2204.9
27.5°	2074.9	2152.9	2230.9	2280.4	2327.2	2376.6	2426.0	2423.4	2420.8	2415.6	2413.0
30°	2067.1	2126.9	2186.7	2246.5	2306.4	2366.2	2426.0	2457.2	2485.8	2517.0	2548.2
32.5°	2111.3	2160.7	2212.7	2275.2	2337.6	2402.6	2465.0	2530.0	2592.4	2657.4	2722.4
35°	2178.9	2223.1	2270.0	2337.6	2407.8	2475.4	2545.6	2623.6	2704.2	2784.8	2862.8
37.5°	2280.4	2319.4	2361.0	2418.2	2478.0	2535.2	2595.0	2709.4	2823.8	2940.8	3055.2
40°	2397.4	2423.4	2449.4	2504.0	2558.6	2613.2	2667.8	2810.8	2953.8	3096.8	3239.8
42.5°	2566.4	2558.6	2550.8	2595.0	2641.8	2686.0	2732.8	2862.8	2992.8	3122.8	3252.8
45°	2745.8	2714.6	2683.4	2704.2	2727.6	2748.4	2771.8	2904.4	3037.0	3172.2	3304.8
47.5°	2961.6	2883.6	2805.6	2787.4	2769.2	2748.4	2730.2	2873.2	3016.2	3161.8	3304.8
50°	3206.0	3089.0	2974.6	2927.8	2878.4	2831.6	2782.2	2899.2	3018.8	3138.4	3255.4
52.5°	3460.8	3315.2	3172.2	3099.4	3026.6	2951.2	2878.4	2977.2	3078.6	3180.0	3278.8
55°	3679.2	3531.0	3380.2	3294.4	3208.6	3122.8	3037.0	3135.8	3234.6	3333.4	3432.2
57.5°	3853.5	3705.2	3557.0	3476.4	3393.2	3312.6	3229.4	3323.0	3419.2	3515.4	3609.0
60°	3973.1	3830.1	3687.0	3609.0	3531.0	3453.0	3375.0	3486.8	3598.6	3713.0	3824.9
62.5°	3910.7	3806.7	3702.6	3668.8	3635.0	3598.6	3564.8	3671.4	3775.5	3882.1	3988.7
65°	3681.8	3611.6	3541.4	3575.2	3611.6	3645.4	3681.8	3752.0	3822.3	3895.1	3965.3
67.5°	3310.0	3304.8	3297.0	3372.4	3447.8	3525.8	3601.2	3648.0	3692.2	3739.0	3785.9
70°	2777.0	2805.6	2831.6	2961.6	3091.6	3221.6	3351.6	3369.8	3388.0	3406.2	3424.4
72.5°	2173.7	2210.1	2249.1	2420.8	2589.8	2761.4	2933.0	2922.6	2912.2	2899.2	2888.8
75°	1710.9	1744.7	1781.1	1939.7	2098.3	2256.9	2415.6	2371.4	2329.8	2285.6	2241.3
77.5°	1365.1	1401.5	1440.5	1588.7	1736.9	1887.7	2035.9	1929.3	1822.7	1716.1	1609.5
80°	1175.3	1193.5	1209.1	1310.5	1409.3	1510.7	1612.1	1502.9	1391.1	1279.3	1170.1
82.5°	964.7	954.3	946.5	1006.3	1066.1	1125.9	1185.7	1081.7	977.7	871.1	767.1
85°	720.2	709.8	699.4	730.6	761.9	795.7	826.9	707.2	587.6	465.4	345.8
87.5°	418.6	429.0	439.4	473.2	507.0	543.4	577.2	455.0	332.8	208.0	85.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015
 CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676015
 CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1872.1	1872.1
2.5°	1944.9	1931.9
5°	1838.3	1820.1
7.5°	1721.3	1697.9
10°	1614.7	1583.5
12.5°	1547.1	1508.1
15°	1521.1	1474.3
17.5°	1599.1	1554.9
20°	1718.7	1658.9
22.5°	1864.3	1791.5
25°	2116.5	2028.1
27.5°	2322.0	2230.9
30°	2449.4	2350.6
32.5°	2589.8	2459.8
35°	2735.4	2610.6
37.5°	2912.2	2771.8
40°	3094.2	2948.6
42.5°	3156.6	3063.0
45°	3216.4	3128.0
47.5°	3229.4	3156.6
50°	3242.4	3232.0
52.5°	3278.8	3276.2
55°	3434.8	3437.4
57.5°	3627.2	3642.8
60°	3804.1	3785.9
62.5°	3895.1	3801.5
65°	3832.7	3702.6
67.5°	3645.4	3505.0
70°	3234.6	3044.8
72.5°	2722.4	2556.0
75°	2098.3	1957.9
77.5°	1492.5	1375.5
80°	1050.5	933.5
82.5°	673.4	579.8
85°	304.2	265.2
87.5°	85.8	83.2
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P676015
CATALOG NUMBER: CCW-SA-2B-760-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)