

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P676025

Luminaire Tested: **CCW-SA-2A-827-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P676025
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2A-827-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @350mA w/
SLR distribution lens
Light Source: (32) 2700K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3337.9 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 36.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 4.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P676025
CATALOG NUMBER: CCW-SA-2A-827-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	686.8	0.0	686.8
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	2651.1	0.0	2651.1
	% Fixture	79.4	0.0	79.4
Total	Lumens	3337.9	0.0	3337.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.8	2.5
10°-20°	174.9	5.2
20°-30°	255.8	7.7
30°-40°	360.4	10.8
40°-50°	495.3	14.8
50°-60°	675.1	20.2
60°-70°	738.9	22.1
70°-80°	426.7	12.8
80°-90°	127.9	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3337.9	100.0
0°-180°	3337.9	100.0

Coefficient of Utilization



REPORT NUMBER: P676025


CATALOG NUMBER: CCW-SA-2A-827-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	342.8	10.3			
FM	(30°-60°)	1218.1	36.5			
FH	(60°-80°)	981.5	29.4			G1/1800
FVH	(80°-90°)	108.6	3.3			G2/225
BL	(0°-30°)	170.7	5.1	B1/500		
BM	(30°-60°)	312.7	9.4	B1/1000		
BH	(60°-80°)	184.1	5.5	B1/500		G1/500
BVH	(80°-90°)	19.3	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9
2.5°	1100.0	1094.1	1089.6	1085.2	1079.2	1074.8	1068.9	1063.0	1055.6	1049.6	1042.2
5°	1036.3	1018.5	1000.8	990.4	978.6	968.2	956.4	943.0	929.7	914.9	901.6
7.5°	966.7	944.5	922.3	904.6	885.3	867.5	848.3	832.0	815.7	799.4	783.2
10°	901.6	880.9	860.1	837.9	814.2	792.0	768.4	746.1	723.9	701.7	679.5
12.5°	858.7	833.5	809.8	784.6	760.9	735.8	710.6	689.9	669.2	647.0	626.2
15°	839.4	815.7	793.5	768.4	743.2	718.0	692.8	669.2	647.0	623.3	599.6
17.5°	885.3	851.3	817.2	784.6	752.1	719.5	686.9	657.3	627.7	598.1	568.5
20°	944.5	901.6	860.1	820.2	778.7	738.7	697.3	655.8	614.4	572.9	531.5
22.5°	1020.0	971.2	923.8	872.0	818.7	766.9	713.6	661.8	609.9	556.6	504.8
25°	1154.7	1097.0	1039.3	965.3	889.7	815.7	740.2	672.1	605.5	537.4	469.3
27.5°	1270.2	1191.8	1114.8	1025.9	937.1	848.3	759.5	681.0	604.0	525.6	447.1
30°	1338.3	1261.3	1184.4	1076.3	969.7	861.6	753.5	666.2	580.3	493.0	405.6
32.5°	1400.5	1314.6	1228.8	1110.3	990.4	872.0	752.1	655.8	561.1	464.9	368.6
35°	1486.4	1391.6	1298.4	1160.7	1023.0	885.3	747.6	648.4	547.8	448.6	347.9
37.5°	1578.2	1461.2	1345.7	1193.2	1040.8	888.3	735.8	638.1	540.4	442.7	344.9
40°	1678.8	1536.7	1396.1	1227.3	1060.0	891.2	722.5	624.7	527.0	427.8	330.1
42.5°	1744.0	1590.0	1436.0	1253.9	1073.3	891.2	709.1	612.9	516.7	419.0	322.7
45°	1781.0	1631.5	1483.4	1286.5	1089.6	892.7	695.8	601.1	506.3	410.1	315.3
47.5°	1797.3	1658.1	1518.9	1311.7	1105.9	898.6	691.4	595.1	497.4	401.2	303.5
50°	1840.2	1717.3	1594.4	1372.4	1151.8	929.7	707.7	604.0	501.9	398.2	294.6
52.5°	1865.4	1760.3	1655.1	1427.2	1199.2	971.2	743.2	627.7	512.2	396.8	281.3
55°	1957.2	1856.5	1755.8	1513.0	1268.7	1025.9	781.7	654.4	527.0	398.2	270.9
57.5°	2074.1	1967.5	1862.4	1600.4	1338.3	1076.3	814.2	678.0	540.4	404.2	266.5
60°	2155.5	2051.9	1949.7	1671.4	1391.6	1113.3	833.5	691.4	549.2	405.6	263.5
62.5°	2164.4	2031.2	1899.4	1628.5	1357.6	1085.2	814.2	676.6	538.9	399.7	262.0
65°	2108.2	1952.7	1797.3	1538.2	1279.1	1020.0	760.9	635.1	509.3	382.0	256.1
67.5°	1995.6	1813.5	1631.5	1394.6	1157.7	920.8	684.0	575.9	469.3	361.2	253.2
70°	1733.6	1573.7	1415.3	1209.5	1005.2	799.4	593.7	504.8	417.5	328.7	239.8
72.5°	1455.3	1305.8	1157.7	990.4	824.6	657.3	490.0	423.4	356.8	288.7	222.1
75°	1114.8	1002.3	891.2	766.9	642.5	516.7	392.3	343.5	294.6	245.8	196.9
77.5°	783.2	722.5	663.2	570.0	476.7	383.4	290.2	257.6	225.0	192.5	159.9
80°	531.5	497.4	464.9	398.2	331.6	263.5	196.9	176.2	154.0	133.2	111.0
82.5°	330.1	328.7	325.7	279.8	233.9	188.0	142.1	124.4	108.1	90.3	72.5
85°	151.0	176.2	199.9	174.7	149.5	124.4	99.2	87.3	75.5	62.2	50.3
87.5°	47.4	57.7	66.6	63.7	59.2	56.3	51.8	44.4	37.0	29.6	22.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9
2.5°	1036.3	1031.9	1025.9	1020.0	1012.6	1006.7	999.3	991.9	990.4	987.5	986.0
5°	892.7	883.8	873.5	864.6	855.7	845.3	836.5	826.1	818.7	809.8	802.4
7.5°	766.9	752.1	735.8	719.5	704.7	689.9	673.6	658.8	651.4	644.0	636.6
10°	666.2	651.4	638.1	623.3	612.9	604.0	593.7	583.3	574.4	565.5	556.6
12.5°	615.9	605.5	595.1	584.8	572.9	562.6	550.7	538.9	528.5	519.6	509.3
15°	584.8	570.0	553.7	538.9	522.6	507.8	491.5	475.2	463.4	453.0	441.2
17.5°	547.8	525.6	504.8	482.6	464.9	447.1	427.8	410.1	396.8	382.0	368.6
20°	506.3	481.1	454.5	429.3	408.6	389.4	368.6	347.9	333.1	316.8	302.0
22.5°	470.8	438.2	404.2	370.1	347.9	325.7	302.0	279.8	266.5	251.7	238.4
25°	432.3	396.8	359.7	322.7	300.5	276.8	254.6	230.9	220.6	211.7	201.3
27.5°	411.6	376.0	339.0	303.5	282.8	260.6	239.8	217.6	210.2	201.3	193.9
30°	370.1	336.1	300.5	265.0	250.2	236.9	222.1	207.3	204.3	202.8	199.9
32.5°	333.1	297.6	262.0	226.5	213.2	199.9	186.5	173.2	171.7	168.8	167.3
35°	313.9	279.8	244.3	210.2	198.4	185.1	173.2	159.9	156.9	152.5	149.5
37.5°	309.4	273.9	236.9	201.3	189.5	177.7	164.3	152.5	149.5	146.6	143.6
40°	297.6	263.5	230.9	196.9	185.1	173.2	159.9	148.0	145.1	142.1	139.2
42.5°	288.7	256.1	222.1	188.0	177.7	167.3	155.4	145.1	142.1	139.2	134.7
45°	281.3	247.2	211.7	177.7	170.3	162.8	154.0	146.6	143.6	139.2	136.2
47.5°	269.4	236.9	202.8	168.8	161.4	155.4	148.0	140.6	137.7	134.7	131.8
50°	260.6	226.5	192.5	158.4	152.5	146.6	140.6	134.7	134.7	136.2	136.2
52.5°	248.7	216.1	183.6	151.0	145.1	139.2	133.2	127.3	128.8	130.3	131.8
55°	238.4	207.3	174.7	142.1	136.2	130.3	122.9	117.0	118.4	119.9	121.4
57.5°	233.9	201.3	168.8	136.2	130.3	122.9	117.0	109.6	109.6	109.6	109.6
60°	230.9	196.9	164.3	130.3	122.9	117.0	109.6	102.2	100.7	100.7	99.2
62.5°	229.5	195.4	162.8	128.8	119.9	112.5	103.6	94.7	93.3	91.8	90.3
65°	223.5	192.5	159.9	127.3	117.0	108.1	97.7	87.3	85.9	85.9	84.4
67.5°	222.1	189.5	158.4	125.8	115.5	103.6	93.3	81.4	79.9	78.5	77.0
70°	210.2	182.1	152.5	122.9	111.0	100.7	88.8	77.0	75.5	72.5	71.1
72.5°	195.4	170.3	143.6	117.0	105.1	93.3	81.4	69.6	68.1	66.6	63.7
75°	173.2	149.5	125.8	102.2	91.8	82.9	72.5	62.2	60.7	59.2	56.3
77.5°	142.1	122.9	105.1	85.9	78.5	71.1	63.7	56.3	54.8	53.3	50.3
80°	100.7	88.8	78.5	66.6	62.2	56.3	51.8	45.9	45.9	44.4	44.4
82.5°	66.6	60.7	54.8	48.9	45.9	42.9	40.0	37.0	37.0	35.5	35.5
85°	47.4	44.4	40.0	37.0	35.5	32.6	31.1	28.1	28.1	28.1	28.1
87.5°	22.2	22.2	20.7	20.7	19.2	19.2	17.8	16.3	16.3	16.3	16.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9
2.5°	983.0	978.6	974.1	968.2	963.8	957.8	950.4	944.5	937.1	937.1	935.6
5°	793.5	789.1	784.6	778.7	774.3	768.4	763.9	758.0	752.1	752.1	750.6
7.5°	629.2	620.3	611.4	601.1	592.2	586.3	580.3	572.9	567.0	562.6	558.1
10°	547.8	538.9	528.5	519.6	509.3	501.9	494.5	485.6	478.2	472.3	466.3
12.5°	498.9	488.5	478.2	467.8	457.5	447.1	438.2	427.8	417.5	410.1	402.7
15°	429.3	419.0	408.6	398.2	387.9	376.0	364.2	350.9	339.0	333.1	328.7
17.5°	353.8	343.5	331.6	321.3	309.4	300.5	291.6	282.8	273.9	268.0	263.5
20°	285.7	273.9	262.0	250.2	238.4	232.4	226.5	220.6	214.7	210.2	207.3
22.5°	223.5	216.1	210.2	202.8	195.4	191.0	188.0	183.6	179.1	179.1	179.1
25°	191.0	186.5	183.6	179.1	174.7	173.2	171.7	168.8	167.3	165.8	165.8
27.5°	185.1	180.6	176.2	171.7	167.3	165.8	164.3	161.4	159.9	159.9	159.9
30°	196.9	195.4	193.9	192.5	191.0	188.0	183.6	180.6	176.2	173.2	170.3
32.5°	164.3	162.8	162.8	161.4	159.9	162.8	164.3	167.3	168.8	170.3	171.7
35°	145.1	142.1	139.2	136.2	133.2	131.8	130.3	128.8	127.3	127.3	125.8
37.5°	140.6	137.7	134.7	131.8	128.8	127.3	125.8	124.4	122.9	122.9	121.4
40°	136.2	133.2	131.8	128.8	125.8	124.4	122.9	119.9	118.4	117.0	117.0
42.5°	131.8	130.3	127.3	125.8	122.9	121.4	119.9	117.0	115.5	114.0	112.5
45°	131.8	128.8	125.8	122.9	119.9	118.4	115.5	114.0	111.0	111.0	109.6
47.5°	128.8	125.8	122.9	119.9	117.0	115.5	112.5	111.0	108.1	106.6	105.1
50°	136.2	131.8	125.8	121.4	115.5	114.0	111.0	109.6	106.6	105.1	103.6
52.5°	133.2	128.8	122.9	118.4	112.5	109.6	108.1	105.1	102.2	100.7	99.2
55°	122.9	118.4	115.5	111.0	106.6	103.6	100.7	97.7	94.7	93.3	93.3
57.5°	109.6	108.1	106.6	105.1	103.6	100.7	97.7	93.3	90.3	88.8	87.3
60°	97.7	99.2	100.7	102.2	103.6	99.2	94.7	90.3	85.9	84.4	82.9
62.5°	88.8	91.8	94.7	96.2	99.2	94.7	90.3	85.9	81.4	79.9	78.5
65°	82.9	84.4	84.4	85.9	85.9	82.9	81.4	78.5	75.5	74.0	74.0
67.5°	75.5	75.5	75.5	74.0	74.0	72.5	72.5	71.1	69.6	68.1	68.1
70°	68.1	68.1	68.1	66.6	66.6	65.1	65.1	63.7	62.2	62.2	60.7
72.5°	62.2	62.2	60.7	60.7	59.2	59.2	59.2	57.7	57.7	56.3	56.3
75°	54.8	54.8	53.3	53.3	51.8	51.8	51.8	50.3	50.3	50.3	48.9
77.5°	48.9	48.9	47.4	47.4	45.9	45.9	45.9	44.4	44.4	42.9	42.9
80°	42.9	42.9	41.5	41.5	40.0	40.0	38.5	38.5	37.0	37.0	35.5
82.5°	34.1	34.1	34.1	34.1	34.1	32.6	32.6	31.1	29.6	29.6	28.1
85°	28.1	28.1	28.1	26.6	26.6	26.6	25.2	25.2	23.7	22.2	22.2
87.5°	16.3	16.3	16.3	14.8	14.8	14.8	14.8	14.8	14.8	14.8	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025
 CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9
2.5°	935.6	934.2	928.2	922.3	928.2	934.2	934.2	934.2	932.7	932.7	932.7
5°	750.6	749.1	746.1	743.2	743.2	741.7	744.7	747.6	750.6	753.5	756.5
7.5°	552.2	547.8	543.3	538.9	541.8	543.3	547.8	550.7	555.2	558.1	565.5
10°	460.4	454.5	450.1	445.6	442.7	439.7	436.7	435.3	432.3	429.3	432.3
12.5°	393.8	386.4	379.0	370.1	368.6	367.2	364.2	361.2	358.3	355.3	353.8
15°	322.7	316.8	313.9	309.4	303.5	297.6	294.6	293.1	290.2	287.2	285.7
17.5°	257.6	251.7	247.2	242.8	241.3	238.4	238.4	238.4	238.4	238.4	238.4
20°	202.8	198.4	198.4	196.9	196.9	195.4	196.9	198.4	198.4	199.9	201.3
22.5°	177.7	177.7	176.2	174.7	176.2	176.2	177.7	179.1	180.6	182.1	183.6
25°	164.3	162.8	164.3	165.8	165.8	165.8	167.3	167.3	168.8	168.8	168.8
27.5°	158.4	158.4	159.9	159.9	161.4	161.4	161.4	159.9	159.9	158.4	158.4
30°	167.3	164.3	164.3	164.3	162.8	161.4	159.9	159.9	158.4	156.9	155.4
32.5°	173.2	174.7	173.2	170.3	168.8	165.8	164.3	161.4	159.9	156.9	154.0
35°	125.8	124.4	127.3	128.8	130.3	131.8	133.2	134.7	134.7	136.2	136.2
37.5°	121.4	119.9	119.9	118.4	118.4	118.4	118.4	118.4	117.0	117.0	118.4
40°	115.5	114.0	114.0	112.5	112.5	111.0	111.0	111.0	111.0	111.0	111.0
42.5°	111.0	109.6	109.6	109.6	109.6	108.1	108.1	106.6	106.6	105.1	105.1
45°	109.6	108.1	106.6	105.1	105.1	103.6	103.6	103.6	102.2	102.2	102.2
47.5°	103.6	102.2	102.2	100.7	100.7	99.2	99.2	99.2	97.7	97.7	97.7
50°	100.7	99.2	99.2	97.7	97.7	96.2	96.2	96.2	94.7	94.7	94.7
52.5°	96.2	94.7	94.7	94.7	93.3	91.8	91.8	91.8	90.3	90.3	90.3
55°	91.8	90.3	90.3	90.3	88.8	87.3	87.3	87.3	85.9	85.9	85.9
57.5°	85.9	84.4	84.4	82.9	82.9	82.9	82.9	82.9	81.4	81.4	81.4
60°	81.4	79.9	79.9	78.5	78.5	77.0	77.0	77.0	77.0	77.0	77.0
62.5°	77.0	75.5	74.0	72.5	74.0	74.0	74.0	74.0	72.5	72.5	72.5
65°	72.5	71.1	69.6	68.1	68.1	68.1	68.1	68.1	68.1	68.1	68.1
67.5°	66.6	65.1	63.7	62.2	63.7	63.7	63.7	63.7	63.7	63.7	63.7
70°	60.7	59.2	59.2	57.7	57.7	56.3	56.3	57.7	57.7	57.7	57.7
72.5°	54.8	53.3	53.3	51.8	51.8	51.8	51.8	51.8	51.8	51.8	51.8
75°	48.9	47.4	47.4	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.9
77.5°	41.5	40.0	40.0	40.0	40.0	40.0	40.0	41.5	41.5	41.5	41.5
80°	35.5	34.1	34.1	34.1	34.1	34.1	34.1	34.1	34.1	34.1	34.1
82.5°	28.1	26.6	26.6	26.6	26.6	26.6	26.6	26.6	26.6	26.6	26.6
85°	20.7	19.2	19.2	19.2	20.7	20.7	20.7	20.7	20.7	20.7	20.7
87.5°	13.3	11.8	11.8	11.8	13.3	13.3	13.3	13.3	11.8	11.8	11.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9
2.5°	932.7	932.7	932.7	931.2	929.7	928.2	926.8	931.2	934.2	938.6	941.6
5°	758.0	760.9	762.4	766.9	771.3	775.8	780.2	783.2	786.1	787.6	790.6
7.5°	571.5	578.9	584.8	590.7	596.6	601.1	607.0	611.4	615.9	620.3	624.7
10°	433.8	436.7	438.2	444.1	448.6	454.5	458.9	463.4	467.8	470.8	475.2
12.5°	352.3	349.4	347.9	347.9	347.9	347.9	347.9	350.9	353.8	356.8	359.7
15°	284.2	282.8	281.3	279.8	278.3	275.4	273.9	276.8	279.8	282.8	285.7
17.5°	238.4	238.4	238.4	236.9	235.4	233.9	232.4	233.9	235.4	235.4	236.9
20°	204.3	205.8	207.3	208.7	208.7	210.2	210.2	211.7	213.2	213.2	214.7
22.5°	183.6	185.1	185.1	185.1	186.5	186.5	186.5	188.0	189.5	191.0	192.5
25°	167.3	167.3	165.8	165.8	167.3	167.3	167.3	167.3	168.8	168.8	168.8
27.5°	158.4	156.9	156.9	156.9	156.9	155.4	155.4	155.4	155.4	155.4	155.4
30°	154.0	152.5	151.0	149.5	149.5	148.0	146.6	146.6	146.6	146.6	146.6
32.5°	152.5	149.5	146.6	145.1	145.1	143.6	142.1	140.6	140.6	139.2	137.7
35°	136.2	134.7	134.7	133.2	131.8	130.3	128.8	128.8	128.8	127.3	127.3
37.5°	118.4	119.9	119.9	119.9	121.4	121.4	121.4	121.4	122.9	122.9	122.9
40°	111.0	111.0	111.0	112.5	114.0	114.0	115.5	115.5	117.0	117.0	117.0
42.5°	105.1	103.6	103.6	105.1	105.1	106.6	106.6	108.1	109.6	109.6	111.0
45°	102.2	100.7	100.7	100.7	100.7	99.2	99.2	100.7	102.2	103.6	105.1
47.5°	96.2	96.2	94.7	94.7	94.7	94.7	94.7	94.7	96.2	96.2	96.2
50°	93.3	93.3	91.8	91.8	91.8	91.8	91.8	91.8	91.8	91.8	91.8
52.5°	90.3	88.8	88.8	88.8	88.8	87.3	87.3	87.3	87.3	87.3	87.3
55°	85.9	84.4	84.4	84.4	84.4	84.4	84.4	84.4	85.9	85.9	85.9
57.5°	81.4	79.9	79.9	79.9	81.4	81.4	81.4	81.4	82.9	82.9	82.9
60°	77.0	77.0	77.0	77.0	77.0	77.0	77.0	78.5	78.5	79.9	79.9
62.5°	72.5	72.5	72.5	72.5	74.0	74.0	74.0	74.0	75.5	75.5	75.5
65°	68.1	68.1	68.1	68.1	69.6	69.6	69.6	69.6	69.6	69.6	69.6
67.5°	63.7	63.7	63.7	63.7	63.7	63.7	63.7	65.1	65.1	66.6	66.6
70°	57.7	56.3	56.3	57.7	57.7	59.2	59.2	60.7	60.7	62.2	62.2
72.5°	51.8	51.8	51.8	51.8	51.8	51.8	51.8	53.3	54.8	54.8	56.3
75°	45.9	45.9	45.9	45.9	47.4	47.4	47.4	48.9	48.9	50.3	50.3
77.5°	41.5	40.0	40.0	40.0	41.5	41.5	41.5	42.9	42.9	44.4	44.4
80°	34.1	34.1	34.1	34.1	35.5	35.5	35.5	35.5	37.0	37.0	37.0
82.5°	28.1	28.1	28.1	28.1	28.1	28.1	28.1	28.1	29.6	29.6	29.6
85°	20.7	20.7	20.7	20.7	22.2	22.2	22.2	22.2	22.2	22.2	22.2
87.5°	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	14.8	14.8	14.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025
 CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9
2.5°	941.6	941.6	941.6	941.6	944.5	946.0	949.0	950.4	949.0	947.5	944.5
5°	792.0	793.5	793.5	795.0	795.0	795.0	795.0	795.0	798.0	800.9	803.9
7.5°	626.2	627.7	629.2	630.7	630.7	630.7	629.2	629.2	630.7	630.7	632.2
10°	479.7	485.6	490.0	494.5	491.5	487.1	484.1	479.7	479.7	479.7	478.2
12.5°	362.7	364.2	367.2	368.6	367.2	367.2	365.7	364.2	365.7	368.6	370.1
15°	287.2	287.2	288.7	288.7	290.2	291.6	291.6	293.1	296.1	297.6	300.5
17.5°	238.4	239.8	239.8	241.3	241.3	242.8	242.8	242.8	245.8	248.7	253.2
20°	214.7	214.7	214.7	214.7	214.7	213.2	213.2	211.7	213.2	216.1	217.6
22.5°	192.5	193.9	193.9	193.9	192.5	191.0	188.0	186.5	186.5	188.0	188.0
25°	168.8	167.3	167.3	165.8	165.8	167.3	167.3	167.3	168.8	168.8	170.3
27.5°	155.4	154.0	154.0	152.5	152.5	154.0	154.0	154.0	154.0	154.0	154.0
30°	145.1	145.1	143.6	142.1	143.6	143.6	145.1	145.1	146.6	146.6	148.0
32.5°	137.7	136.2	136.2	134.7	136.2	136.2	137.7	137.7	139.2	140.6	140.6
35°	127.3	127.3	127.3	127.3	127.3	127.3	125.8	125.8	125.8	125.8	125.8
37.5°	121.4	121.4	119.9	118.4	118.4	118.4	118.4	118.4	117.0	115.5	114.0
40°	117.0	115.5	115.5	114.0	112.5	112.5	111.0	109.6	109.6	108.1	108.1
42.5°	111.0	109.6	109.6	108.1	106.6	106.6	105.1	103.6	103.6	103.6	102.2
45°	103.6	103.6	102.2	100.7	100.7	100.7	99.2	99.2	99.2	99.2	97.7
47.5°	96.2	96.2	94.7	94.7	94.7	94.7	93.3	93.3	93.3	93.3	93.3
50°	91.8	91.8	91.8	91.8	91.8	91.8	90.3	90.3	90.3	90.3	90.3
52.5°	87.3	87.3	87.3	87.3	87.3	87.3	87.3	87.3	87.3	87.3	87.3
55°	85.9	85.9	85.9	85.9	85.9	85.9	84.4	84.4	84.4	85.9	85.9
57.5°	82.9	82.9	81.4	81.4	81.4	81.4	81.4	81.4	81.4	81.4	81.4
60°	79.9	79.9	79.9	79.9	79.9	79.9	79.9	79.9	79.9	79.9	79.9
62.5°	75.5	75.5	75.5	75.5	75.5	77.0	77.0	77.0	77.0	77.0	75.5
65°	69.6	71.1	71.1	71.1	71.1	71.1	71.1	71.1	71.1	71.1	71.1
67.5°	66.6	66.6	66.6	66.6	66.6	66.6	66.6	66.6	66.6	66.6	66.6
70°	62.2	62.2	60.7	60.7	60.7	62.2	62.2	62.2	62.2	62.2	62.2
72.5°	56.3	56.3	56.3	56.3	56.3	56.3	56.3	56.3	56.3	57.7	57.7
75°	50.3	50.3	50.3	50.3	50.3	50.3	50.3	50.3	50.3	50.3	50.3
77.5°	44.4	44.4	42.9	42.9	42.9	44.4	44.4	44.4	44.4	45.9	45.9
80°	37.0	37.0	37.0	37.0	37.0	37.0	37.0	37.0	37.0	38.5	38.5
82.5°	29.6	29.6	29.6	29.6	29.6	29.6	29.6	29.6	29.6	31.1	31.1
85°	22.2	23.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7	25.2	25.2
87.5°	14.8	14.8	14.8	14.8	14.8	14.8	13.3	13.3	13.3	13.3	11.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025
 CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9
2.5°	943.0	944.5	946.0	946.0	947.5	949.0	949.0	954.9	960.8	963.8	966.7
5°	806.8	805.4	805.4	803.9	802.4	806.8	811.3	820.2	829.1	830.5	833.5
7.5°	632.2	633.6	635.1	635.1	636.6	632.2	626.2	627.7	629.2	636.6	642.5
10°	478.2	479.7	481.1	481.1	482.6	481.1	478.2	482.6	487.1	493.0	500.4
12.5°	371.6	376.0	380.5	383.4	387.9	390.8	392.3	398.2	402.7	410.1	417.5
15°	303.5	306.5	309.4	312.4	315.3	318.3	321.3	327.2	333.1	342.0	350.9
17.5°	256.1	256.1	257.6	257.6	257.6	260.6	263.5	266.5	268.0	276.8	285.7
20°	219.1	217.6	216.1	214.7	213.2	216.1	217.6	219.1	220.6	226.5	230.9
22.5°	188.0	188.0	189.5	189.5	189.5	188.0	185.1	186.5	186.5	189.5	193.9
25°	170.3	170.3	170.3	168.8	168.8	170.3	171.7	171.7	170.3	171.7	173.2
27.5°	154.0	155.4	155.4	156.9	156.9	158.4	158.4	158.4	158.4	159.9	161.4
30°	148.0	148.0	149.5	149.5	149.5	151.0	152.5	152.5	152.5	154.0	156.9
32.5°	142.1	143.6	145.1	146.6	148.0	149.5	149.5	151.0	151.0	152.5	154.0
35°	125.8	124.4	124.4	122.9	121.4	121.4	121.4	121.4	119.9	121.4	121.4
37.5°	112.5	112.5	112.5	111.0	111.0	112.5	112.5	112.5	112.5	114.0	114.0
40°	106.6	106.6	106.6	106.6	106.6	106.6	106.6	108.1	108.1	109.6	111.0
42.5°	102.2	102.2	102.2	102.2	102.2	103.6	103.6	103.6	103.6	105.1	105.1
45°	97.7	97.7	97.7	97.7	97.7	97.7	97.7	99.2	99.2	100.7	102.2
47.5°	93.3	93.3	93.3	93.3	93.3	94.7	96.2	96.2	96.2	97.7	97.7
50°	90.3	90.3	90.3	90.3	90.3	91.8	91.8	93.3	93.3	94.7	96.2
52.5°	87.3	87.3	87.3	87.3	87.3	88.8	88.8	90.3	90.3	91.8	93.3
55°	85.9	85.9	85.9	84.4	84.4	85.9	85.9	87.3	87.3	88.8	88.8
57.5°	81.4	81.4	81.4	81.4	81.4	81.4	81.4	82.9	82.9	84.4	85.9
60°	79.9	79.9	78.5	78.5	77.0	78.5	78.5	79.9	79.9	81.4	81.4
62.5°	75.5	75.5	75.5	74.0	74.0	75.5	75.5	75.5	75.5	77.0	78.5
65°	71.1	71.1	71.1	69.6	69.6	71.1	71.1	71.1	71.1	72.5	74.0
67.5°	66.6	66.6	66.6	65.1	65.1	65.1	65.1	66.6	66.6	68.1	69.6
70°	62.2	62.2	62.2	60.7	60.7	60.7	59.2	60.7	62.2	63.7	63.7
72.5°	57.7	57.7	57.7	56.3	56.3	56.3	54.8	56.3	56.3	57.7	57.7
75°	50.3	50.3	50.3	50.3	50.3	50.3	48.9	48.9	48.9	50.3	50.3
77.5°	45.9	45.9	45.9	44.4	44.4	44.4	42.9	42.9	42.9	44.4	44.4
80°	38.5	38.5	38.5	37.0	37.0	37.0	35.5	35.5	35.5	37.0	37.0
82.5°	31.1	31.1	31.1	29.6	29.6	29.6	28.1	28.1	28.1	29.6	29.6
85°	25.2	25.2	25.2	25.2	25.2	25.2	23.7	23.7	23.7	25.2	26.6
87.5°	11.8	11.8	13.3	13.3	13.3	13.3	11.8	11.8	10.4	10.4	11.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9
2.5°	969.7	972.7	980.1	986.0	993.4	999.3	1003.7	1009.7	1014.1	1018.5	1021.5
5°	835.0	836.5	843.9	851.3	857.2	864.6	874.9	885.3	895.7	906.0	913.4
7.5°	649.9	655.8	664.7	675.1	684.0	692.8	703.2	715.1	725.4	735.8	746.1
10°	506.3	512.2	521.1	530.0	537.4	546.3	558.1	570.0	581.8	593.7	605.5
12.5°	424.9	432.3	442.7	453.0	461.9	472.3	487.1	500.4	515.2	528.5	543.3
15°	358.3	367.2	380.5	395.3	408.6	421.9	436.7	451.5	464.9	479.7	494.5
17.5°	294.6	303.5	315.3	328.7	340.5	352.3	370.1	386.4	404.2	420.4	436.7
20°	236.9	241.3	253.2	265.0	276.8	288.7	302.0	315.3	328.7	342.0	362.7
22.5°	196.9	199.9	205.8	210.2	216.1	220.6	233.9	247.2	259.1	272.4	291.6
25°	173.2	174.7	179.1	182.1	186.5	189.5	198.4	205.8	214.7	222.1	239.8
27.5°	161.4	162.8	164.3	165.8	167.3	168.8	174.7	180.6	185.1	191.0	207.3
30°	158.4	159.9	164.3	167.3	171.7	174.7	177.7	180.6	183.6	186.5	196.9
32.5°	155.4	156.9	156.9	155.4	155.4	154.0	156.9	158.4	161.4	162.8	171.7
35°	122.9	122.9	124.4	125.8	127.3	128.8	133.2	136.2	140.6	143.6	151.0
37.5°	115.5	115.5	117.0	119.9	121.4	122.9	125.8	128.8	131.8	134.7	142.1
40°	111.0	112.5	114.0	115.5	117.0	118.4	121.4	122.9	125.8	127.3	133.2
42.5°	106.6	106.6	108.1	111.0	112.5	114.0	117.0	118.4	121.4	122.9	128.8
45°	103.6	105.1	106.6	108.1	108.1	109.6	112.5	115.5	117.0	119.9	125.8
47.5°	99.2	99.2	102.2	103.6	106.6	108.1	111.0	112.5	115.5	117.0	122.9
50°	96.2	97.7	100.7	102.2	105.1	106.6	111.0	114.0	118.4	121.4	124.4
52.5°	93.3	94.7	97.7	99.2	102.2	103.6	109.6	115.5	119.9	125.8	125.8
55°	90.3	90.3	93.3	97.7	100.7	103.6	106.6	111.0	114.0	117.0	117.0
57.5°	85.9	87.3	90.3	94.7	97.7	100.7	103.6	106.6	108.1	111.0	109.6
60°	82.9	82.9	87.3	91.8	96.2	100.7	100.7	100.7	99.2	99.2	99.2
62.5°	78.5	79.9	85.9	93.3	99.2	105.1	100.7	96.2	91.8	87.3	88.8
65°	75.5	77.0	79.9	84.4	87.3	90.3	87.3	85.9	82.9	79.9	81.4
67.5°	69.6	71.1	72.5	72.5	74.0	74.0	74.0	74.0	74.0	74.0	75.5
70°	65.1	65.1	65.1	66.6	66.6	66.6	66.6	66.6	66.6	66.6	68.1
72.5°	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.2	60.7
75°	51.8	51.8	51.8	51.8	51.8	51.8	51.8	51.8	51.8	51.8	53.3
77.5°	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.9	44.4	44.4	45.9
80°	38.5	38.5	38.5	38.5	37.0	37.0	37.0	37.0	37.0	37.0	38.5
82.5°	31.1	31.1	31.1	31.1	29.6	29.6	29.6	29.6	28.1	28.1	29.6
85°	28.1	29.6	29.6	31.1	31.1	31.1	29.6	28.1	26.6	25.2	25.2
87.5°	11.8	11.8	11.8	11.8	10.4	10.4	10.4	10.4	10.4	10.4	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025
 CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9
2.5°	1025.9	1028.9	1031.9	1036.3	1042.2	1046.7	1051.1	1060.0	1070.4	1079.2	1088.1
5°	920.8	928.2	935.6	944.5	953.4	960.8	969.7	987.5	1005.2	1021.5	1039.3
7.5°	755.0	765.4	774.3	789.1	802.4	817.2	830.5	852.7	873.5	895.7	916.4
10°	617.3	629.2	641.0	660.3	681.0	700.3	719.5	737.3	756.5	774.3	792.0
12.5°	558.1	571.5	586.3	598.1	611.4	623.3	635.1	655.8	676.6	697.3	718.0
15°	509.3	524.1	538.9	553.7	567.0	581.8	595.1	612.9	632.2	649.9	667.7
17.5°	453.0	467.8	484.1	500.4	516.7	533.0	549.2	574.4	599.6	623.3	648.4
20°	382.0	402.7	421.9	444.1	466.3	488.5	510.8	537.4	564.1	589.2	615.9
22.5°	310.9	330.1	349.4	376.0	402.7	427.8	454.5	490.0	524.1	559.6	593.7
25°	259.1	276.8	294.6	324.2	352.3	382.0	410.1	453.0	494.5	537.4	578.9
27.5°	223.5	239.8	256.1	287.2	318.3	347.9	379.0	426.4	472.3	519.6	565.5
30°	207.3	217.6	228.0	257.6	287.2	315.3	344.9	390.8	436.7	482.6	528.5
32.5°	180.6	189.5	198.4	225.0	251.7	276.8	303.5	350.9	396.8	444.1	490.0
35°	159.9	167.3	174.7	199.9	223.5	248.7	272.4	319.8	367.2	414.5	461.9
37.5°	148.0	155.4	161.4	183.6	207.3	229.5	251.7	299.1	344.9	392.3	438.2
40°	139.2	143.6	149.5	171.7	192.5	214.7	235.4	278.3	322.7	365.7	408.6
42.5°	133.2	139.2	143.6	162.8	183.6	202.8	222.1	263.5	305.0	344.9	386.4
45°	131.8	137.7	143.6	159.9	176.2	191.0	207.3	247.2	287.2	327.2	367.2
47.5°	128.8	133.2	139.2	152.5	164.3	177.7	189.5	229.5	269.4	307.9	347.9
50°	127.3	128.8	131.8	143.6	155.4	167.3	179.1	219.1	259.1	299.1	339.0
52.5°	125.8	125.8	125.8	136.2	146.6	155.4	165.8	205.8	247.2	287.2	327.2
55°	117.0	115.5	115.5	125.8	134.7	145.1	154.0	193.9	233.9	272.4	312.4
57.5°	108.1	106.6	105.1	114.0	122.9	131.8	140.6	180.6	222.1	262.0	302.0
60°	99.2	97.7	97.7	106.6	114.0	122.9	130.3	171.7	211.7	253.2	293.1
62.5°	88.8	90.3	90.3	97.7	106.6	114.0	121.4	162.8	205.8	247.2	288.7
65°	81.4	82.9	82.9	91.8	100.7	109.6	118.4	158.4	199.9	239.8	279.8
67.5°	75.5	77.0	77.0	87.3	96.2	106.6	115.5	151.0	188.0	223.5	259.1
70°	69.6	69.6	71.1	81.4	91.8	102.2	112.5	143.6	174.7	204.3	235.4
72.5°	62.2	63.7	65.1	75.5	84.4	94.7	103.6	131.8	159.9	188.0	216.1
75°	54.8	56.3	57.7	66.6	75.5	84.4	93.3	119.9	145.1	171.7	196.9
77.5°	48.9	50.3	51.8	59.2	66.6	74.0	81.4	100.7	121.4	140.6	159.9
80°	40.0	40.0	41.5	47.4	53.3	57.7	63.7	77.0	90.3	102.2	115.5
82.5°	29.6	31.1	31.1	35.5	38.5	42.9	45.9	53.3	59.2	66.6	72.5
85°	25.2	23.7	23.7	26.6	28.1	31.1	32.6	37.0	40.0	44.4	47.4
87.5°	10.4	8.9	8.9	10.4	13.3	14.8	16.3	16.3	17.8	17.8	17.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9
2.5°	1092.6	1095.5	1100.0	1102.9	1110.3	1116.3	1123.7	1129.6	1134.0	1141.4	1138.5
5°	1052.6	1065.9	1079.2	1092.6	1102.9	1113.3	1122.2	1132.5	1144.4	1166.6	1172.5
7.5°	934.2	951.9	968.2	986.0	1006.7	1027.4	1048.2	1068.9	1088.1	1116.3	1134.0
10°	817.2	842.4	866.1	891.2	910.5	929.7	947.5	966.7	993.4	1021.5	1054.1
12.5°	743.2	768.4	793.5	818.7	846.8	873.5	901.6	928.2	953.4	975.6	1012.6
15°	694.3	722.5	749.1	775.8	809.8	842.4	876.4	909.0	946.0	975.6	1000.8
17.5°	682.5	716.5	749.1	783.2	818.7	854.2	889.7	925.3	962.3	1006.7	1039.3
20°	661.8	707.7	753.5	799.4	845.3	889.7	935.6	980.1	1028.9	1082.2	1097.0
22.5°	649.9	704.7	760.9	815.7	877.9	941.6	1003.7	1065.9	1117.7	1157.7	1202.1
25°	648.4	716.5	786.1	854.2	932.7	1009.7	1088.1	1165.1	1231.7	1271.7	1307.2
27.5°	647.0	729.9	811.3	892.7	988.9	1083.7	1179.9	1274.7	1336.8	1394.6	1424.2
30°	629.2	728.4	829.1	928.2	1036.3	1144.4	1252.5	1360.5	1424.2	1464.2	1479.0
32.5°	607.0	723.9	840.9	957.8	1080.7	1203.6	1325.0	1447.9	1498.2	1532.3	1520.4
35°	589.2	718.0	845.3	972.7	1102.9	1234.7	1365.0	1495.3	1567.8	1615.2	1595.9
37.5°	572.9	707.7	842.4	977.1	1129.6	1282.1	1434.6	1587.0	1656.6	1707.0	1684.7
40°	553.7	697.3	842.4	986.0	1160.7	1333.9	1508.6	1681.8	1772.1	1815.0	1781.0
42.5°	537.4	686.9	837.9	987.5	1174.0	1360.5	1547.1	1733.6	1834.3	1895.0	1852.0
45°	516.7	666.2	814.2	963.8	1169.6	1375.3	1579.6	1785.4	1902.4	1949.7	1890.5
47.5°	494.5	642.5	789.1	935.6	1154.7	1373.9	1593.0	1812.1	1920.1	1976.4	1921.6
50°	487.1	635.1	781.7	929.7	1166.6	1404.9	1641.8	1878.7	1957.2	2003.0	1930.5
52.5°	485.6	642.5	800.9	957.8	1196.2	1433.1	1671.4	1908.3	1972.0	2020.8	1955.7
55°	481.1	651.4	820.2	988.9	1237.7	1487.8	1736.6	1985.3	2048.9	2084.5	2035.6
57.5°	485.6	669.2	851.3	1034.8	1290.9	1547.1	1803.2	2059.3	2136.3	2161.5	2151.1
60°	488.5	684.0	877.9	1073.3	1323.5	1573.7	1823.9	2074.1	2154.0	2216.2	2228.1
62.5°	481.1	673.6	864.6	1057.0	1283.5	1510.1	1736.6	1963.1	2094.8	2186.6	2239.9
65°	458.9	636.6	815.7	993.4	1202.1	1412.3	1621.1	1829.8	1969.0	2105.2	2148.1
67.5°	410.1	561.1	712.1	863.1	1045.2	1227.3	1407.9	1590.0	1764.7	1896.5	1955.7
70°	355.3	473.7	593.7	712.1	877.9	1043.7	1209.5	1375.3	1529.3	1674.4	1730.6
72.5°	309.4	401.2	494.5	586.3	704.7	821.6	940.1	1057.0	1239.1	1384.2	1439.0
75°	263.5	330.1	395.3	461.9	543.3	624.7	704.7	786.1	914.9	1045.2	1100.0
77.5°	202.8	247.2	290.2	333.1	389.4	444.1	500.4	555.2	645.5	743.2	771.3
80°	140.6	165.8	189.5	214.7	259.1	303.5	347.9	392.3	451.5	506.3	549.2
82.5°	87.3	103.6	118.4	133.2	168.8	204.3	238.4	273.9	297.6	300.5	343.5
85°	56.3	66.6	75.5	84.4	105.1	127.3	148.0	168.8	151.0	140.6	167.3
87.5°	22.2	28.1	32.6	37.0	35.5	34.1	32.6	31.1	26.6	23.7	29.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025
 CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9
2.5°	1141.4	1145.9	1150.3	1153.3	1157.7	1159.2	1160.7	1160.7	1162.2	1163.6	1166.6
5°	1196.2	1205.1	1214.0	1221.4	1230.3	1237.7	1243.6	1251.0	1256.9	1256.9	1255.4
7.5°	1150.3	1172.5	1194.7	1216.9	1239.1	1255.4	1270.2	1286.5	1301.3	1304.3	1307.2
10°	1089.6	1113.3	1135.5	1159.2	1181.4	1206.6	1230.3	1253.9	1279.1	1283.5	1289.5
12.5°	1033.4	1061.5	1089.6	1116.3	1144.4	1162.2	1179.9	1196.2	1214.0	1225.8	1237.7
15°	1031.9	1055.6	1079.2	1101.5	1125.1	1135.5	1145.9	1154.7	1165.1	1165.1	1166.6
17.5°	1065.9	1080.7	1095.5	1108.9	1123.7	1125.1	1128.1	1129.6	1131.1	1126.6	1122.2
20°	1132.5	1138.5	1144.4	1150.3	1156.2	1145.9	1137.0	1126.6	1116.3	1104.4	1094.1
22.5°	1230.3	1216.9	1203.6	1190.3	1177.0	1159.2	1139.9	1122.2	1102.9	1088.1	1073.3
25°	1322.0	1305.8	1289.5	1273.2	1256.9	1218.4	1179.9	1139.9	1101.5	1085.2	1068.9
27.5°	1444.9	1419.7	1394.6	1369.4	1344.2	1292.4	1240.6	1188.8	1137.0	1108.9	1082.2
30°	1474.5	1446.4	1418.3	1388.7	1360.5	1310.2	1261.3	1211.0	1160.7	1128.1	1097.0
32.5°	1517.5	1484.9	1452.3	1419.7	1387.2	1338.3	1289.5	1239.1	1190.3	1160.7	1129.6
35°	1588.5	1551.5	1514.5	1476.0	1439.0	1388.7	1339.8	1289.5	1239.1	1205.1	1172.5
37.5°	1649.2	1606.3	1563.4	1520.4	1477.5	1433.1	1387.2	1342.8	1296.9	1262.8	1230.3
40°	1717.3	1669.9	1622.6	1576.7	1529.3	1487.8	1446.4	1403.5	1362.0	1335.4	1308.7
42.5°	1776.5	1718.8	1662.5	1606.3	1548.5	1520.4	1493.8	1465.6	1437.5	1424.2	1409.4
45°	1818.0	1764.7	1709.9	1656.6	1603.3	1582.6	1561.9	1541.1	1520.4	1533.7	1547.1
47.5°	1835.8	1792.8	1751.4	1709.9	1667.0	1674.4	1681.8	1687.7	1695.1	1712.9	1732.1
50°	1852.0	1828.4	1803.2	1779.5	1754.3	1782.5	1809.1	1837.2	1865.4	1902.4	1939.4
52.5°	1884.6	1871.3	1859.4	1846.1	1832.8	1881.6	1930.5	1979.4	2028.2	2069.7	2111.1
55°	1982.3	1972.0	1961.6	1949.7	1939.4	2009.0	2077.1	2146.6	2216.2	2259.2	2302.1
57.5°	2117.0	2111.1	2103.7	2097.8	2090.4	2158.5	2225.1	2291.7	2359.8	2401.3	2444.2
60°	2219.2	2220.7	2220.7	2222.2	2222.2	2274.0	2325.8	2379.1	2430.9	2466.4	2503.4
62.5°	2274.0	2271.0	2268.0	2265.1	2262.1	2305.1	2348.0	2390.9	2433.9	2460.5	2487.2
65°	2214.7	2231.0	2247.3	2263.6	2279.9	2285.8	2290.3	2296.2	2300.6	2316.9	2333.2
67.5°	2016.4	2048.9	2080.0	2112.6	2143.7	2121.5	2100.8	2078.5	2056.3	2060.8	2063.7
70°	1795.8	1832.8	1871.3	1908.3	1945.3	1893.5	1841.7	1788.4	1736.6	1718.8	1701.0
72.5°	1514.5	1547.1	1581.1	1613.7	1646.3	1582.6	1520.4	1456.8	1393.1	1362.0	1330.9
75°	1157.7	1196.2	1236.2	1274.7	1313.2	1242.1	1169.6	1098.5	1025.9	1005.2	986.0
77.5°	843.9	889.7	935.6	981.5	1027.4	963.8	900.1	835.0	771.3	759.5	747.6
80°	614.4	649.9	684.0	719.5	753.5	716.5	679.5	642.5	605.5	604.0	602.5
82.5°	414.5	445.6	475.2	506.3	535.9	521.1	507.8	493.0	478.2	493.0	509.3
85°	213.2	256.1	300.5	343.5	386.4	382.0	379.0	374.6	370.1	389.4	407.1
87.5°	42.9	79.9	117.0	152.5	189.5	180.6	171.7	161.4	152.5	158.4	162.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025
 CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9
2.5°	1168.1	1169.6	1169.6	1169.6	1169.6	1169.6	1166.6	1165.1	1162.2	1159.2	1154.7
5°	1255.4	1253.9	1248.0	1242.1	1234.7	1228.8	1224.3	1218.4	1214.0	1208.0	1199.2
7.5°	1310.2	1313.2	1302.8	1293.9	1283.5	1273.2	1262.8	1252.5	1242.1	1231.7	1211.0
10°	1293.9	1298.4	1292.4	1286.5	1279.1	1273.2	1261.3	1248.0	1236.2	1222.8	1197.7
12.5°	1248.0	1259.9	1256.9	1253.9	1251.0	1248.0	1240.6	1231.7	1224.3	1215.4	1187.3
15°	1166.6	1166.6	1168.1	1169.6	1169.6	1171.0	1172.5	1174.0	1175.5	1177.0	1160.7
17.5°	1117.7	1113.3	1113.3	1113.3	1113.3	1113.3	1119.2	1126.6	1132.5	1138.5	1134.0
20°	1082.2	1071.8	1070.4	1070.4	1068.9	1067.4	1077.8	1089.6	1100.0	1110.3	1116.3
22.5°	1058.5	1043.7	1042.2	1040.8	1039.3	1037.8	1051.1	1064.4	1077.8	1091.1	1111.8
25°	1052.6	1036.3	1037.8	1039.3	1039.3	1040.8	1051.1	1061.5	1071.8	1082.2	1117.7
27.5°	1054.1	1027.4	1028.9	1030.4	1030.4	1031.9	1048.2	1063.0	1079.2	1094.1	1138.5
30°	1064.4	1033.4	1030.4	1027.4	1024.5	1021.5	1043.7	1065.9	1088.1	1110.3	1144.4
32.5°	1100.0	1070.4	1063.0	1055.6	1048.2	1040.8	1067.4	1092.6	1119.2	1144.4	1172.5
35°	1138.5	1105.9	1102.9	1100.0	1095.5	1092.6	1116.3	1141.4	1165.1	1188.8	1214.0
37.5°	1196.2	1163.6	1160.7	1156.2	1153.3	1148.8	1175.5	1200.6	1227.3	1252.5	1274.7
40°	1282.1	1255.4	1253.9	1253.9	1252.5	1251.0	1271.7	1293.9	1314.6	1335.4	1350.2
42.5°	1396.1	1382.7	1387.2	1393.1	1397.5	1402.0	1418.3	1436.0	1452.3	1468.6	1464.2
45°	1560.4	1573.7	1575.2	1576.7	1578.2	1579.6	1584.1	1590.0	1594.4	1598.9	1581.1
47.5°	1749.9	1767.7	1776.5	1785.4	1792.8	1801.7	1795.8	1788.4	1782.5	1775.1	1730.6
50°	1974.9	2011.9	2010.4	2009.0	2006.0	2004.5	1992.7	1980.8	1967.5	1955.7	1890.5
52.5°	2152.6	2194.0	2201.4	2208.8	2216.2	2223.6	2201.4	2179.2	2155.5	2133.3	2051.9
55°	2343.5	2386.5	2388.0	2389.4	2389.4	2390.9	2359.8	2328.7	2296.2	2265.1	2180.7
57.5°	2485.7	2527.1	2522.7	2519.7	2515.3	2510.8	2473.8	2436.8	2399.8	2362.8	2278.4
60°	2539.0	2574.5	2565.6	2556.7	2546.4	2537.5	2509.4	2481.2	2451.6	2423.5	2342.1
62.5°	2513.8	2540.4	2527.1	2515.3	2502.0	2488.6	2453.1	2416.1	2380.6	2343.5	2284.3
65°	2348.0	2364.3	2346.5	2330.2	2313.9	2296.2	2266.6	2237.0	2205.9	2176.3	2136.3
67.5°	2068.2	2071.1	2069.7	2068.2	2066.7	2065.2	2022.3	1979.4	1934.9	1892.0	1889.0
70°	1684.7	1667.0	1669.9	1674.4	1677.3	1680.3	1647.7	1616.6	1584.1	1551.5	1566.3
72.5°	1299.8	1268.7	1276.1	1285.0	1292.4	1299.8	1273.2	1248.0	1221.4	1194.7	1215.4
75°	965.3	946.0	953.4	962.3	969.7	977.1	966.7	956.4	944.5	934.2	953.4
77.5°	735.8	723.9	725.4	725.4	726.9	726.9	728.4	731.3	732.8	734.3	755.0
80°	599.6	598.1	596.6	595.1	592.2	590.7	605.5	620.3	635.1	649.9	660.3
82.5°	524.1	538.9	530.0	522.6	513.7	504.8	518.2	531.5	544.8	558.1	553.7
85°	426.4	444.1	427.8	411.6	393.8	377.5	389.4	399.7	411.6	421.9	416.0
87.5°	168.8	173.2	146.6	121.4	94.7	68.1	108.1	146.6	186.5	225.0	230.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9	1065.9
2.5°	1150.3	1144.4	1139.9	1138.5	1135.5	1134.0	1131.1	1128.1	1123.7	1120.7	1116.3
5°	1188.8	1179.9	1169.6	1154.7	1141.4	1126.6	1111.8	1098.5	1085.2	1070.4	1057.0
7.5°	1190.3	1169.6	1148.8	1129.6	1108.9	1089.6	1068.9	1051.1	1031.9	1012.6	994.9
10°	1174.0	1148.8	1123.7	1098.5	1074.8	1049.6	1024.5	1003.7	981.5	959.3	938.6
12.5°	1160.7	1132.5	1104.4	1074.8	1046.7	1017.1	987.5	966.7	946.0	925.3	904.6
15°	1144.4	1126.6	1110.3	1083.7	1057.0	1030.4	1003.7	975.6	949.0	920.8	892.7
17.5°	1131.1	1126.6	1122.2	1104.4	1086.6	1067.4	1049.6	1021.5	993.4	963.8	935.6
20°	1123.7	1129.6	1135.5	1126.6	1117.7	1107.4	1098.5	1077.8	1057.0	1034.8	1014.1
22.5°	1132.5	1154.7	1175.5	1177.0	1179.9	1181.4	1182.9	1163.6	1144.4	1123.7	1104.4
25°	1153.3	1188.8	1224.3	1243.6	1262.8	1283.5	1302.8	1290.9	1279.1	1267.3	1255.4
27.5°	1181.4	1225.8	1270.2	1298.4	1325.0	1353.1	1381.3	1379.8	1378.3	1375.3	1373.9
30°	1177.0	1211.0	1245.1	1279.1	1313.2	1347.2	1381.3	1399.0	1415.3	1433.1	1450.8
32.5°	1202.1	1230.3	1259.9	1295.4	1330.9	1367.9	1403.5	1440.5	1476.0	1513.0	1550.0
35°	1240.6	1265.8	1292.4	1330.9	1370.9	1409.4	1449.4	1493.8	1539.7	1585.6	1630.0
37.5°	1298.4	1320.6	1344.2	1376.8	1410.9	1443.4	1477.5	1542.6	1607.8	1674.4	1739.5
40°	1365.0	1379.8	1394.6	1425.7	1456.8	1487.8	1518.9	1600.4	1681.8	1763.2	1844.6
42.5°	1461.2	1456.8	1452.3	1477.5	1504.1	1529.3	1555.9	1630.0	1704.0	1778.0	1852.0
45°	1563.4	1545.6	1527.8	1539.7	1553.0	1564.8	1578.2	1653.7	1729.2	1806.1	1881.6
47.5°	1686.2	1641.8	1597.4	1587.0	1576.7	1564.8	1554.5	1635.9	1717.3	1800.2	1881.6
50°	1825.4	1758.8	1693.6	1667.0	1638.9	1612.2	1584.1	1650.7	1718.8	1786.9	1853.5
52.5°	1970.5	1887.6	1806.1	1764.7	1723.2	1680.3	1638.9	1695.1	1752.8	1810.6	1866.8
55°	2094.8	2010.4	1924.6	1875.7	1826.9	1778.0	1729.2	1785.4	1841.7	1897.9	1954.2
57.5°	2194.0	2109.6	2025.3	1979.4	1932.0	1886.1	1838.7	1892.0	1946.8	2001.6	2054.9
60°	2262.1	2180.7	2099.3	2054.9	2010.4	1966.0	1921.6	1985.3	2048.9	2114.1	2177.7
62.5°	2226.6	2167.4	2108.2	2088.9	2069.7	2048.9	2029.7	2090.4	2149.6	2210.3	2271.0
65°	2096.3	2056.3	2016.4	2035.6	2056.3	2075.6	2096.3	2136.3	2176.3	2217.7	2257.7
67.5°	1884.6	1881.6	1877.2	1920.1	1963.1	2007.5	2050.4	2077.1	2102.2	2128.9	2155.5
70°	1581.1	1597.4	1612.2	1686.2	1760.3	1834.3	1908.3	1918.7	1929.0	1939.4	1949.7
72.5°	1237.7	1258.4	1280.6	1378.3	1474.5	1572.2	1669.9	1664.0	1658.1	1650.7	1644.8
75°	974.1	993.4	1014.1	1104.4	1194.7	1285.0	1375.3	1350.2	1326.5	1301.3	1276.1
77.5°	777.2	798.0	820.2	904.6	988.9	1074.8	1159.2	1098.5	1037.8	977.1	916.4
80°	669.2	679.5	688.4	746.1	802.4	860.1	917.9	855.7	792.0	728.4	666.2
82.5°	549.2	543.3	538.9	572.9	607.0	641.0	675.1	615.9	556.6	495.9	436.7
85°	410.1	404.2	398.2	416.0	433.8	453.0	470.8	402.7	334.6	265.0	196.9
87.5°	238.4	244.3	250.2	269.4	288.7	309.4	328.7	259.1	189.5	118.4	48.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676025
 CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1065.9	1065.9
2.5°	1107.4	1100.0
5°	1046.7	1036.3
7.5°	980.1	966.7
10°	919.4	901.6
12.5°	880.9	858.7
15°	866.1	839.4
17.5°	910.5	885.3
20°	978.6	944.5
22.5°	1061.5	1020.0
25°	1205.1	1154.7
27.5°	1322.0	1270.2
30°	1394.6	1338.3
32.5°	1474.5	1400.5
35°	1557.4	1486.4
37.5°	1658.1	1578.2
40°	1761.7	1678.8
42.5°	1797.3	1744.0
45°	1831.3	1781.0
47.5°	1838.7	1797.3
50°	1846.1	1840.2
52.5°	1866.8	1865.4
55°	1955.7	1957.2
57.5°	2065.2	2074.1
60°	2165.9	2155.5
62.5°	2217.7	2164.4
65°	2182.2	2108.2
67.5°	2075.6	1995.6
70°	1841.7	1733.6
72.5°	1550.0	1455.3
75°	1194.7	1114.8
77.5°	849.8	783.2
80°	598.1	531.5
82.5°	383.4	330.1
85°	173.2	151.0
87.5°	48.9	47.4
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P676025

CATALOG NUMBER: CCW-SA-2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)