

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P676026

Luminaire Tested: **CCW-SA-2B-827-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P676026
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2B-827-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @450mA w/
SLR distribution lens
Light Source: (32) 2700K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4213.1 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 46
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 6 fc

Type IV - Short - N/A

REPORT NUMBER: P676026
CATALOG NUMBER: CCW-SA-2B-827-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	866.9	0.0	866.9
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3346.2	0.0	3346.2
	% Fixture	79.4	0.0	79.4
Total	Lumens	4213.1	0.0	4213.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.5	2.5
10°-20°	220.7	5.2
20°-30°	322.9	7.7
30°-40°	454.9	10.8
40°-50°	625.2	14.8
50°-60°	852.1	20.2
60°-70°	932.6	22.1
70°-80°	538.6	12.8
80°-90°	161.4	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4213.1	100.0
0°-180°	4213.1	100.0

Coefficient of Utilization



REPORT NUMBER: P676026


CATALOG NUMBER: CCW-SA-2B-827-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	432.7	10.3			
FM	(30°-60°)	1537.5	36.5			
FH	(60°-80°)	1238.9	29.4			G1/1800
FVH	(80°-90°)	137.1	3.3			G2/225
BL	(0°-30°)	215.5	5.1	B1/500		
BM	(30°-60°)	394.7	9.4	B1/1000		
BH	(60°-80°)	232.3	5.5	B1/500		G1/500
BVH	(80°-90°)	24.3	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4
2.5°	1388.4	1380.9	1375.3	1369.7	1362.2	1356.6	1349.1	1341.7	1332.3	1324.8	1315.5
5°	1308.0	1285.6	1263.2	1250.1	1235.1	1222.1	1207.1	1190.3	1173.5	1154.8	1138.0
7.5°	1220.2	1192.2	1164.1	1141.7	1117.4	1095.0	1070.7	1050.2	1029.6	1009.0	988.5
10°	1138.0	1111.8	1085.7	1057.6	1027.7	999.7	969.8	941.8	913.7	885.7	857.7
12.5°	1083.8	1052.0	1022.1	990.4	960.5	928.7	896.9	870.8	844.6	816.6	790.4
15°	1059.5	1029.6	1001.6	969.8	938.0	906.3	874.5	844.6	816.6	786.7	756.8
17.5°	1117.4	1074.4	1031.5	990.4	949.2	908.1	867.0	829.7	792.3	754.9	717.5
20°	1192.2	1138.0	1085.7	1035.2	982.9	932.4	880.1	827.8	775.5	723.1	670.8
22.5°	1287.5	1225.8	1166.0	1100.6	1033.3	967.9	900.7	835.3	769.9	702.6	637.2
25°	1457.5	1384.6	1311.8	1218.3	1123.0	1029.6	934.3	848.3	764.3	678.3	592.3
27.5°	1603.3	1504.2	1407.1	1294.9	1182.8	1070.7	958.6	859.6	762.4	663.4	564.3
30°	1689.2	1592.0	1494.9	1358.5	1223.9	1087.5	951.1	840.9	732.5	622.2	512.0
32.5°	1767.7	1659.3	1550.9	1401.4	1250.1	1100.6	949.2	827.8	708.2	586.7	465.3
35°	1876.1	1756.5	1638.8	1465.0	1291.2	1117.4	943.6	818.4	691.4	566.2	439.1
37.5°	1991.9	1844.3	1698.6	1506.1	1313.6	1121.2	928.7	805.4	682.0	558.7	435.4
40°	2119.0	1939.6	1762.1	1549.1	1337.9	1124.9	911.9	788.5	665.2	540.0	416.7
42.5°	2201.2	2006.9	1812.5	1582.7	1354.7	1124.9	895.1	773.6	652.1	528.8	407.4
45°	2247.9	2059.2	1872.3	1623.8	1375.3	1126.8	878.2	758.6	639.1	517.6	398.0
47.5°	2268.5	2092.8	1917.2	1655.6	1395.8	1134.2	872.6	751.2	627.8	506.4	383.1
50°	2322.7	2167.6	2012.5	1732.2	1453.8	1173.5	893.2	762.4	633.5	502.7	371.9
52.5°	2354.4	2221.8	2089.1	1801.3	1513.6	1225.8	938.0	792.3	646.5	500.8	355.0
55°	2470.3	2343.2	2216.2	1909.7	1601.4	1294.9	986.6	825.9	665.2	502.7	342.0
57.5°	2617.9	2483.4	2350.7	2020.0	1689.2	1358.5	1027.7	855.8	682.0	510.1	336.3
60°	2720.7	2589.9	2460.9	2109.6	1756.5	1405.2	1052.0	872.6	693.2	512.0	332.6
62.5°	2731.9	2563.7	2397.4	2055.5	1713.5	1369.7	1027.7	853.9	680.2	504.5	330.7
65°	2660.9	2464.7	2268.5	1941.5	1614.5	1287.5	960.5	801.6	642.8	482.1	323.3
67.5°	2518.9	2289.0	2059.2	1760.2	1461.2	1162.3	863.3	726.9	592.3	455.9	319.5
70°	2188.1	1986.3	1786.4	1526.6	1268.8	1009.0	749.3	637.2	526.9	414.8	302.7
72.5°	1836.8	1648.1	1461.2	1250.1	1040.8	829.7	618.5	534.4	450.3	364.4	280.3
75°	1407.1	1265.0	1124.9	967.9	811.0	652.1	495.2	433.5	371.9	310.2	248.5
77.5°	988.5	911.9	837.1	719.4	601.7	484.0	366.2	325.1	284.0	242.9	201.8
80°	670.8	627.8	586.7	502.7	418.6	332.6	248.5	222.4	194.3	168.2	140.1
82.5°	416.7	414.8	411.1	353.2	295.2	237.3	179.4	157.0	136.4	114.0	91.6
85°	190.6	222.4	252.3	220.5	188.7	157.0	125.2	110.2	95.3	78.5	63.5
87.5°	59.8	72.9	84.1	80.3	74.7	71.0	65.4	56.1	46.7	37.4	28.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4
2.5°	1308.0	1302.4	1294.9	1287.5	1278.1	1270.6	1261.3	1252.0	1250.1	1246.4	1244.5
5°	1126.8	1115.6	1102.5	1091.3	1080.0	1067.0	1055.8	1042.7	1033.3	1022.1	1012.8
7.5°	967.9	949.2	928.7	908.1	889.5	870.8	850.2	831.5	822.2	812.8	803.5
10°	840.9	822.2	805.4	786.7	773.6	762.4	749.3	736.2	725.0	713.8	702.6
12.5°	777.3	764.3	751.2	738.1	723.1	710.1	695.1	680.2	667.1	655.9	642.8
15°	738.1	719.4	698.9	680.2	659.6	640.9	620.4	599.8	584.9	571.8	556.8
17.5°	691.4	663.4	637.2	609.2	586.7	564.3	540.0	517.6	500.8	482.1	465.3
20°	639.1	607.3	573.7	541.9	515.7	491.4	465.3	439.1	420.4	399.9	381.2
22.5°	594.2	553.1	510.1	467.1	439.1	411.1	381.2	353.2	336.3	317.7	300.8
25°	545.6	500.8	454.1	407.4	379.3	349.4	321.4	291.5	278.4	267.2	254.1
27.5°	519.5	474.6	427.9	383.1	356.9	328.9	302.7	274.7	265.3	254.1	244.8
30°	467.1	424.2	379.3	334.5	315.8	299.0	280.3	261.6	257.9	256.0	252.3
32.5°	420.4	375.6	330.7	285.9	269.1	252.3	235.4	218.6	216.8	213.0	211.2
35°	396.1	353.2	308.3	265.3	250.4	233.6	218.6	201.8	198.1	192.5	188.7
37.5°	390.5	345.7	299.0	254.1	239.2	224.2	207.4	192.5	188.7	185.0	181.3
40°	375.6	332.6	291.5	248.5	233.6	218.6	201.8	186.9	183.1	179.4	175.6
42.5°	364.4	323.3	280.3	237.3	224.2	211.2	196.2	183.1	179.4	175.6	170.0
45°	355.0	312.1	267.2	224.2	214.9	205.5	194.3	185.0	181.3	175.6	171.9
47.5°	340.1	299.0	256.0	213.0	203.7	196.2	186.9	177.5	173.8	170.0	166.3
50°	328.9	285.9	242.9	199.9	192.5	185.0	177.5	170.0	170.0	171.9	171.9
52.5°	313.9	272.8	231.7	190.6	183.1	175.6	168.2	160.7	162.6	164.4	166.3
55°	300.8	261.6	220.5	179.4	171.9	164.4	155.1	147.6	149.5	151.4	153.2
57.5°	295.2	254.1	213.0	171.9	164.4	155.1	147.6	138.3	138.3	138.3	138.3
60°	291.5	248.5	207.4	164.4	155.1	147.6	138.3	128.9	127.1	127.1	125.2
62.5°	289.6	246.7	205.5	162.6	151.4	142.0	130.8	119.6	117.7	115.9	114.0
65°	282.2	242.9	201.8	160.7	147.6	136.4	123.3	110.2	108.4	108.4	106.5
67.5°	280.3	239.2	199.9	158.8	145.8	130.8	117.7	102.8	100.9	99.0	97.2
70°	265.3	229.8	192.5	155.1	140.1	127.1	112.1	97.2	95.3	91.6	89.7
72.5°	246.7	214.9	181.3	147.6	132.7	117.7	102.8	87.8	86.0	84.1	80.3
75°	218.6	188.7	158.8	128.9	115.9	104.6	91.6	78.5	76.6	74.7	71.0
77.5°	179.4	155.1	132.7	108.4	99.0	89.7	80.3	71.0	69.1	67.3	63.5
80°	127.1	112.1	99.0	84.1	78.5	71.0	65.4	57.9	57.9	56.1	56.1
82.5°	84.1	76.6	69.1	61.7	57.9	54.2	50.5	46.7	46.7	44.8	44.8
85°	59.8	56.1	50.5	46.7	44.8	41.1	39.2	35.5	35.5	35.5	35.5
87.5°	28.0	28.0	26.2	26.2	24.3	24.3	22.4	20.6	20.6	20.6	20.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4
2.5°	1240.7	1235.1	1229.5	1222.1	1216.5	1209.0	1199.6	1192.2	1182.8	1182.8	1181.0
5°	1001.6	996.0	990.4	982.9	977.3	969.8	964.2	956.7	949.2	949.2	947.4
7.5°	794.2	782.9	771.7	758.6	747.4	740.0	732.5	723.1	715.7	710.1	704.5
10°	691.4	680.2	667.1	655.9	642.8	633.5	624.1	612.9	603.6	596.1	588.6
12.5°	629.7	616.6	603.6	590.5	577.4	564.3	553.1	540.0	526.9	517.6	508.3
15°	541.9	528.8	515.7	502.7	489.6	474.6	459.7	442.9	427.9	420.4	414.8
17.5°	446.6	433.5	418.6	405.5	390.5	379.3	368.1	356.9	345.7	338.2	332.6
20°	360.6	345.7	330.7	315.8	300.8	293.4	285.9	278.4	270.9	265.3	261.6
22.5°	282.2	272.8	265.3	256.0	246.7	241.0	237.3	231.7	226.1	226.1	226.1
25°	241.0	235.4	231.7	226.1	220.5	218.6	216.8	213.0	211.2	209.3	209.3
27.5°	233.6	228.0	222.4	216.8	211.2	209.3	207.4	203.7	201.8	201.8	201.8
30°	248.5	246.7	244.8	242.9	241.0	237.3	231.7	228.0	222.4	218.6	214.9
32.5°	207.4	205.5	205.5	203.7	201.8	205.5	207.4	211.2	213.0	214.9	216.8
35°	183.1	179.4	175.6	171.9	168.2	166.3	164.4	162.6	160.7	160.7	158.8
37.5°	177.5	173.8	170.0	166.3	162.6	160.7	158.8	157.0	155.1	155.1	153.2
40°	171.9	168.2	166.3	162.6	158.8	157.0	155.1	151.4	149.5	147.6	147.6
42.5°	166.3	164.4	160.7	158.8	155.1	153.2	151.4	147.6	145.8	143.9	142.0
45°	166.3	162.6	158.8	155.1	151.4	149.5	145.8	143.9	140.1	140.1	138.3
47.5°	162.6	158.8	155.1	151.4	147.6	145.8	142.0	140.1	136.4	134.5	132.7
50°	171.9	166.3	158.8	153.2	145.8	143.9	140.1	138.3	134.5	132.7	130.8
52.5°	168.2	162.6	155.1	149.5	142.0	138.3	136.4	132.7	128.9	127.1	125.2
55°	155.1	149.5	145.8	140.1	134.5	130.8	127.1	123.3	119.6	117.7	117.7
57.5°	138.3	136.4	134.5	132.7	130.8	127.1	123.3	117.7	114.0	112.1	110.2
60°	123.3	125.2	127.1	128.9	130.8	125.2	119.6	114.0	108.4	106.5	104.6
62.5°	112.1	115.9	119.6	121.5	125.2	119.6	114.0	108.4	102.8	100.9	99.0
65°	104.6	106.5	106.5	108.4	108.4	104.6	102.8	99.0	95.3	93.4	93.4
67.5°	95.3	95.3	95.3	93.4	93.4	91.6	91.6	89.7	87.8	86.0	86.0
70°	86.0	86.0	86.0	84.1	84.1	82.2	82.2	80.3	78.5	78.5	76.6
72.5°	78.5	78.5	76.6	76.6	74.7	74.7	74.7	72.9	72.9	71.0	71.0
75°	69.1	69.1	67.3	67.3	65.4	65.4	65.4	63.5	63.5	63.5	61.7
77.5°	61.7	61.7	59.8	59.8	57.9	57.9	57.9	56.1	56.1	54.2	54.2
80°	54.2	54.2	52.3	52.3	50.5	50.5	48.6	48.6	46.7	46.7	44.8
82.5°	43.0	43.0	43.0	43.0	43.0	41.1	41.1	39.2	37.4	37.4	35.5
85°	35.5	35.5	35.5	33.6	33.6	33.6	31.8	31.8	29.9	28.0	28.0
87.5°	20.6	20.6	20.6	18.7	18.7	18.7	18.7	18.7	18.7	18.7	16.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4
2.5°	1181.0	1179.1	1171.6	1164.1	1171.6	1179.1	1179.1	1179.1	1177.2	1177.2	1177.2
5°	947.4	945.5	941.8	938.0	938.0	936.2	939.9	943.6	947.4	951.1	954.9
7.5°	697.0	691.4	685.8	680.2	683.9	685.8	691.4	695.1	700.7	704.5	713.8
10°	581.1	573.7	568.1	562.4	558.7	555.0	551.2	549.4	545.6	541.9	545.6
12.5°	497.0	487.7	478.4	467.1	465.3	463.4	459.7	455.9	452.2	448.5	446.6
15°	407.4	399.9	396.1	390.5	383.1	375.6	371.9	370.0	366.2	362.5	360.6
17.5°	325.1	317.7	312.1	306.4	304.6	300.8	300.8	300.8	300.8	300.8	300.8
20°	256.0	250.4	250.4	248.5	248.5	246.7	248.5	250.4	250.4	252.3	254.1
22.5°	224.2	224.2	222.4	220.5	222.4	222.4	224.2	226.1	228.0	229.8	231.7
25°	207.4	205.5	207.4	209.3	209.3	209.3	211.2	211.2	213.0	213.0	213.0
27.5°	199.9	199.9	201.8	201.8	203.7	203.7	203.7	201.8	201.8	199.9	199.9
30°	211.2	207.4	207.4	207.4	205.5	203.7	201.8	201.8	199.9	198.1	196.2
32.5°	218.6	220.5	218.6	214.9	213.0	209.3	207.4	203.7	201.8	198.1	194.3
35°	158.8	157.0	160.7	162.6	164.4	166.3	168.2	170.0	170.0	171.9	171.9
37.5°	153.2	151.4	151.4	149.5	149.5	149.5	149.5	149.5	147.6	147.6	149.5
40°	145.8	143.9	143.9	142.0	142.0	140.1	140.1	140.1	140.1	140.1	140.1
42.5°	140.1	138.3	138.3	138.3	138.3	136.4	136.4	134.5	134.5	132.7	132.7
45°	138.3	136.4	134.5	132.7	132.7	130.8	130.8	130.8	128.9	128.9	128.9
47.5°	130.8	128.9	128.9	127.1	127.1	125.2	125.2	125.2	123.3	123.3	123.3
50°	127.1	125.2	125.2	123.3	123.3	121.5	121.5	121.5	119.6	119.6	119.6
52.5°	121.5	119.6	119.6	119.6	117.7	115.9	115.9	115.9	114.0	114.0	114.0
55°	115.9	114.0	114.0	114.0	112.1	110.2	110.2	110.2	108.4	108.4	108.4
57.5°	108.4	106.5	106.5	104.6	104.6	104.6	104.6	104.6	102.8	102.8	102.8
60°	102.8	100.9	100.9	99.0	99.0	97.2	97.2	97.2	97.2	97.2	97.2
62.5°	97.2	95.3	93.4	91.6	93.4	93.4	93.4	93.4	91.6	91.6	91.6
65°	91.6	89.7	87.8	86.0	86.0	86.0	86.0	86.0	86.0	86.0	86.0
67.5°	84.1	82.2	80.3	78.5	80.3	80.3	80.3	80.3	80.3	80.3	80.3
70°	76.6	74.7	74.7	72.9	72.9	71.0	71.0	72.9	72.9	72.9	72.9
72.5°	69.1	67.3	67.3	65.4	65.4	65.4	65.4	65.4	65.4	65.4	65.4
75°	61.7	59.8	59.8	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9
77.5°	52.3	50.5	50.5	50.5	50.5	50.5	50.5	52.3	52.3	52.3	52.3
80°	44.8	43.0	43.0	43.0	43.0	43.0	43.0	43.0	43.0	43.0	43.0
82.5°	35.5	33.6	33.6	33.6	33.6	33.6	33.6	33.6	33.6	33.6	33.6
85°	26.2	24.3	24.3	24.3	26.2	26.2	26.2	26.2	26.2	26.2	26.2
87.5°	16.8	14.9	14.9	14.9	16.8	16.8	16.8	16.8	14.9	14.9	14.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4
2.5°	1177.2	1177.2	1177.2	1175.3	1173.5	1171.6	1169.7	1175.3	1179.1	1184.7	1188.4
5°	956.7	960.5	962.3	967.9	973.5	979.1	984.8	988.5	992.2	994.1	997.8
7.5°	721.3	730.6	738.1	745.6	753.0	758.6	766.1	771.7	777.3	782.9	788.5
10°	547.5	551.2	553.1	560.6	566.2	573.7	579.3	584.9	590.5	594.2	599.8
12.5°	444.7	441.0	439.1	439.1	439.1	439.1	439.1	442.9	446.6	450.3	454.1
15°	358.8	356.9	355.0	353.2	351.3	347.6	345.7	349.4	353.2	356.9	360.6
17.5°	300.8	300.8	300.8	299.0	297.1	295.2	293.4	295.2	297.1	297.1	299.0
20°	257.9	259.7	261.6	263.5	263.5	265.3	265.3	267.2	269.1	269.1	270.9
22.5°	231.7	233.6	233.6	233.6	235.4	235.4	235.4	237.3	239.2	241.0	242.9
25°	211.2	211.2	209.3	209.3	211.2	211.2	211.2	211.2	213.0	213.0	213.0
27.5°	199.9	198.1	198.1	198.1	198.1	196.2	196.2	196.2	196.2	196.2	196.2
30°	194.3	192.5	190.6	188.7	188.7	186.9	185.0	185.0	185.0	185.0	185.0
32.5°	192.5	188.7	185.0	183.1	183.1	181.3	179.4	177.5	177.5	175.6	173.8
35°	171.9	170.0	170.0	168.2	166.3	164.4	162.6	162.6	162.6	160.7	160.7
37.5°	149.5	151.4	151.4	151.4	153.2	153.2	153.2	153.2	155.1	155.1	155.1
40°	140.1	140.1	140.1	142.0	143.9	143.9	145.8	145.8	147.6	147.6	147.6
42.5°	132.7	130.8	130.8	132.7	132.7	134.5	134.5	136.4	138.3	138.3	140.1
45°	128.9	127.1	127.1	127.1	127.1	125.2	125.2	127.1	128.9	130.8	132.7
47.5°	121.5	121.5	119.6	119.6	119.6	119.6	119.6	119.6	121.5	121.5	121.5
50°	117.7	117.7	115.9	115.9	115.9	115.9	115.9	115.9	115.9	115.9	115.9
52.5°	114.0	112.1	112.1	112.1	112.1	110.2	110.2	110.2	110.2	110.2	110.2
55°	108.4	106.5	106.5	106.5	106.5	106.5	106.5	106.5	108.4	108.4	108.4
57.5°	102.8	100.9	100.9	100.9	102.8	102.8	102.8	102.8	104.6	104.6	104.6
60°	97.2	97.2	97.2	97.2	97.2	97.2	97.2	99.0	99.0	100.9	100.9
62.5°	91.6	91.6	91.6	91.6	93.4	93.4	93.4	93.4	95.3	95.3	95.3
65°	86.0	86.0	86.0	86.0	87.8	87.8	87.8	87.8	87.8	87.8	87.8
67.5°	80.3	80.3	80.3	80.3	80.3	80.3	80.3	82.2	82.2	84.1	84.1
70°	72.9	71.0	71.0	72.9	72.9	74.7	74.7	76.6	76.6	78.5	78.5
72.5°	65.4	65.4	65.4	65.4	65.4	65.4	65.4	67.3	69.1	69.1	71.0
75°	57.9	57.9	57.9	57.9	59.8	59.8	59.8	61.7	61.7	63.5	63.5
77.5°	52.3	50.5	50.5	50.5	52.3	52.3	52.3	54.2	54.2	56.1	56.1
80°	43.0	43.0	43.0	43.0	44.8	44.8	44.8	44.8	46.7	46.7	46.7
82.5°	35.5	35.5	35.5	35.5	35.5	35.5	35.5	35.5	37.4	37.4	37.4
85°	26.2	26.2	26.2	26.2	28.0	28.0	28.0	28.0	28.0	28.0	28.0
87.5°	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.8	18.7	18.7	18.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026
 CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4
2.5°	1188.4	1188.4	1188.4	1188.4	1192.2	1194.0	1197.8	1199.6	1197.8	1195.9	1192.2
5°	999.7	1001.6	1001.6	1003.4	1003.4	1003.4	1003.4	1003.4	1007.2	1010.9	1014.6
7.5°	790.4	792.3	794.2	796.0	796.0	796.0	794.2	794.2	796.0	796.0	797.9
10°	605.4	612.9	618.5	624.1	620.4	614.8	611.0	605.4	605.4	605.4	603.6
12.5°	457.8	459.7	463.4	465.3	463.4	463.4	461.5	459.7	461.5	465.3	467.1
15°	362.5	362.5	364.4	364.4	366.2	368.1	368.1	370.0	373.7	375.6	379.3
17.5°	300.8	302.7	302.7	304.6	304.6	306.4	306.4	306.4	310.2	313.9	319.5
20°	270.9	270.9	270.9	270.9	270.9	269.1	269.1	267.2	269.1	272.8	274.7
22.5°	242.9	244.8	244.8	244.8	242.9	241.0	237.3	235.4	235.4	237.3	237.3
25°	213.0	211.2	211.2	209.3	209.3	211.2	211.2	211.2	213.0	213.0	214.9
27.5°	196.2	194.3	194.3	192.5	192.5	194.3	194.3	194.3	194.3	194.3	194.3
30°	183.1	183.1	181.3	179.4	181.3	181.3	183.1	183.1	185.0	185.0	186.9
32.5°	173.8	171.9	171.9	170.0	171.9	171.9	173.8	173.8	175.6	177.5	177.5
35°	160.7	160.7	160.7	160.7	160.7	160.7	158.8	158.8	158.8	158.8	158.8
37.5°	153.2	153.2	151.4	149.5	149.5	149.5	149.5	149.5	147.6	145.8	143.9
40°	147.6	145.8	145.8	143.9	142.0	142.0	140.1	138.3	138.3	136.4	136.4
42.5°	140.1	138.3	138.3	136.4	134.5	134.5	132.7	130.8	130.8	130.8	128.9
45°	130.8	130.8	128.9	127.1	127.1	127.1	125.2	125.2	125.2	125.2	123.3
47.5°	121.5	121.5	119.6	119.6	119.6	119.6	117.7	117.7	117.7	117.7	117.7
50°	115.9	115.9	115.9	115.9	115.9	115.9	114.0	114.0	114.0	114.0	114.0
52.5°	110.2	110.2	110.2	110.2	110.2	110.2	110.2	110.2	110.2	110.2	110.2
55°	108.4	108.4	108.4	108.4	108.4	108.4	106.5	106.5	106.5	108.4	108.4
57.5°	104.6	104.6	102.8	102.8	102.8	102.8	102.8	102.8	102.8	102.8	102.8
60°	100.9	100.9	100.9	100.9	100.9	100.9	100.9	100.9	100.9	100.9	100.9
62.5°	95.3	95.3	95.3	95.3	95.3	97.2	97.2	97.2	97.2	97.2	95.3
65°	87.8	89.7	89.7	89.7	89.7	89.7	89.7	89.7	89.7	89.7	89.7
67.5°	84.1	84.1	84.1	84.1	84.1	84.1	84.1	84.1	84.1	84.1	84.1
70°	78.5	78.5	76.6	76.6	76.6	78.5	78.5	78.5	78.5	78.5	78.5
72.5°	71.0	71.0	71.0	71.0	71.0	71.0	71.0	71.0	71.0	72.9	72.9
75°	63.5	63.5	63.5	63.5	63.5	63.5	63.5	63.5	63.5	63.5	63.5
77.5°	56.1	56.1	54.2	54.2	54.2	56.1	56.1	56.1	56.1	57.9	57.9
80°	46.7	46.7	46.7	46.7	46.7	46.7	46.7	46.7	46.7	48.6	48.6
82.5°	37.4	37.4	37.4	37.4	37.4	37.4	37.4	37.4	37.4	39.2	39.2
85°	28.0	29.9	29.9	29.9	29.9	29.9	29.9	29.9	29.9	31.8	31.8
87.5°	18.7	18.7	18.7	18.7	18.7	18.7	16.8	16.8	16.8	16.8	14.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026
 CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4
2.5°	1190.3	1192.2	1194.0	1194.0	1195.9	1197.8	1197.8	1205.2	1212.7	1216.5	1220.2
5°	1018.4	1016.5	1016.5	1014.6	1012.8	1018.4	1024.0	1035.2	1046.4	1048.3	1052.0
7.5°	797.9	799.8	801.6	801.6	803.5	797.9	790.4	792.3	794.2	803.5	811.0
10°	603.6	605.4	607.3	607.3	609.2	607.3	603.6	609.2	614.8	622.2	631.6
12.5°	469.0	474.6	480.2	484.0	489.6	493.3	495.2	502.7	508.3	517.6	526.9
15°	383.1	386.8	390.5	394.3	398.0	401.7	405.5	413.0	420.4	431.6	442.9
17.5°	323.3	323.3	325.1	325.1	325.1	328.9	332.6	336.3	338.2	349.4	360.6
20°	276.6	274.7	272.8	270.9	269.1	272.8	274.7	276.6	278.4	285.9	291.5
22.5°	237.3	237.3	239.2	239.2	239.2	237.3	233.6	235.4	235.4	239.2	244.8
25°	214.9	214.9	214.9	213.0	213.0	214.9	216.8	216.8	214.9	216.8	218.6
27.5°	194.3	196.2	196.2	198.1	198.1	199.9	199.9	199.9	199.9	201.8	203.7
30°	186.9	186.9	188.7	188.7	188.7	190.6	192.5	192.5	192.5	194.3	198.1
32.5°	179.4	181.3	183.1	185.0	186.9	188.7	188.7	190.6	190.6	192.5	194.3
35°	158.8	157.0	157.0	155.1	153.2	153.2	153.2	153.2	151.4	153.2	153.2
37.5°	142.0	142.0	142.0	140.1	140.1	142.0	142.0	142.0	142.0	143.9	143.9
40°	134.5	134.5	134.5	134.5	134.5	134.5	134.5	136.4	136.4	138.3	140.1
42.5°	128.9	128.9	128.9	128.9	128.9	130.8	130.8	130.8	130.8	132.7	132.7
45°	123.3	123.3	123.3	123.3	123.3	123.3	123.3	125.2	125.2	127.1	128.9
47.5°	117.7	117.7	117.7	117.7	117.7	119.6	121.5	121.5	121.5	123.3	123.3
50°	114.0	114.0	114.0	114.0	114.0	115.9	115.9	117.7	117.7	119.6	121.5
52.5°	110.2	110.2	110.2	110.2	110.2	112.1	112.1	114.0	114.0	115.9	117.7
55°	108.4	108.4	108.4	106.5	106.5	108.4	108.4	110.2	110.2	112.1	112.1
57.5°	102.8	102.8	102.8	102.8	102.8	102.8	102.8	104.6	104.6	106.5	108.4
60°	100.9	100.9	99.0	99.0	97.2	99.0	99.0	100.9	100.9	102.8	102.8
62.5°	95.3	95.3	95.3	93.4	93.4	95.3	95.3	95.3	95.3	97.2	99.0
65°	89.7	89.7	89.7	87.8	87.8	89.7	89.7	89.7	89.7	91.6	93.4
67.5°	84.1	84.1	84.1	82.2	82.2	82.2	82.2	84.1	84.1	86.0	87.8
70°	78.5	78.5	78.5	76.6	76.6	76.6	74.7	76.6	78.5	80.3	80.3
72.5°	72.9	72.9	72.9	71.0	71.0	71.0	69.1	71.0	71.0	72.9	72.9
75°	63.5	63.5	63.5	63.5	63.5	63.5	61.7	61.7	61.7	63.5	63.5
77.5°	57.9	57.9	57.9	56.1	56.1	56.1	54.2	54.2	54.2	56.1	56.1
80°	48.6	48.6	48.6	46.7	46.7	46.7	44.8	44.8	44.8	46.7	46.7
82.5°	39.2	39.2	39.2	37.4	37.4	37.4	35.5	35.5	35.5	37.4	37.4
85°	31.8	31.8	31.8	31.8	31.8	31.8	29.9	29.9	29.9	31.8	33.6
87.5°	14.9	14.9	16.8	16.8	16.8	16.8	14.9	14.9	13.1	13.1	14.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4
2.5°	1223.9	1227.7	1237.0	1244.5	1253.8	1261.3	1266.9	1274.4	1280.0	1285.6	1289.3
5°	1053.9	1055.8	1065.1	1074.4	1081.9	1091.3	1104.3	1117.4	1130.5	1143.6	1152.9
7.5°	820.3	827.8	839.0	852.1	863.3	874.5	887.6	902.5	915.6	928.7	941.8
10°	639.1	646.5	657.7	669.0	678.3	689.5	704.5	719.4	734.4	749.3	764.3
12.5°	536.3	545.6	558.7	571.8	583.0	596.1	614.8	631.6	650.3	667.1	685.8
15°	452.2	463.4	480.2	498.9	515.7	532.5	551.2	569.9	586.7	605.4	624.1
17.5°	371.9	383.1	398.0	414.8	429.8	444.7	467.1	487.7	510.1	530.7	551.2
20°	299.0	304.6	319.5	334.5	349.4	364.4	381.2	398.0	414.8	431.6	457.8
22.5°	248.5	252.3	259.7	265.3	272.8	278.4	295.2	312.1	327.0	343.8	368.1
25°	218.6	220.5	226.1	229.8	235.4	239.2	250.4	259.7	270.9	280.3	302.7
27.5°	203.7	205.5	207.4	209.3	211.2	213.0	220.5	228.0	233.6	241.0	261.6
30°	199.9	201.8	207.4	211.2	216.8	220.5	224.2	228.0	231.7	235.4	248.5
32.5°	196.2	198.1	198.1	196.2	196.2	194.3	198.1	199.9	203.7	205.5	216.8
35°	155.1	155.1	157.0	158.8	160.7	162.6	168.2	171.9	177.5	181.3	190.6
37.5°	145.8	145.8	147.6	151.4	153.2	155.1	158.8	162.6	166.3	170.0	179.4
40°	140.1	142.0	143.9	145.8	147.6	149.5	153.2	155.1	158.8	160.7	168.2
42.5°	134.5	134.5	136.4	140.1	142.0	143.9	147.6	149.5	153.2	155.1	162.6
45°	130.8	132.7	134.5	136.4	136.4	138.3	142.0	145.8	147.6	151.4	158.8
47.5°	125.2	125.2	128.9	130.8	134.5	136.4	140.1	142.0	145.8	147.6	155.1
50°	121.5	123.3	127.1	128.9	132.7	134.5	140.1	143.9	149.5	153.2	157.0
52.5°	117.7	119.6	123.3	125.2	128.9	130.8	138.3	145.8	151.4	158.8	158.8
55°	114.0	114.0	117.7	123.3	127.1	130.8	134.5	140.1	143.9	147.6	147.6
57.5°	108.4	110.2	114.0	119.6	123.3	127.1	130.8	134.5	136.4	140.1	138.3
60°	104.6	104.6	110.2	115.9	121.5	127.1	127.1	127.1	125.2	125.2	125.2
62.5°	99.0	100.9	108.4	117.7	125.2	132.7	127.1	121.5	115.9	110.2	112.1
65°	95.3	97.2	100.9	106.5	110.2	114.0	110.2	108.4	104.6	100.9	102.8
67.5°	87.8	89.7	91.6	91.6	93.4	93.4	93.4	93.4	93.4	93.4	95.3
70°	82.2	82.2	82.2	84.1	84.1	84.1	84.1	84.1	84.1	84.1	86.0
72.5°	74.7	74.7	74.7	74.7	74.7	74.7	74.7	74.7	74.7	74.7	76.6
75°	65.4	65.4	65.4	65.4	65.4	65.4	65.4	65.4	65.4	65.4	67.3
77.5°	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9	56.1	56.1	57.9
80°	48.6	48.6	48.6	48.6	46.7	46.7	46.7	46.7	46.7	46.7	48.6
82.5°	39.2	39.2	39.2	39.2	37.4	37.4	37.4	37.4	35.5	35.5	37.4
85°	35.5	37.4	37.4	39.2	39.2	39.2	37.4	35.5	33.6	31.8	31.8
87.5°	14.9	14.9	14.9	14.9	13.1	13.1	13.1	13.1	13.1	13.1	13.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4
2.5°	1294.9	1298.7	1302.4	1308.0	1315.5	1321.1	1326.7	1337.9	1351.0	1362.2	1373.4
5°	1162.3	1171.6	1181.0	1192.2	1203.4	1212.7	1223.9	1246.4	1268.8	1289.3	1311.8
7.5°	953.0	966.1	977.3	996.0	1012.8	1031.5	1048.3	1076.3	1102.5	1130.5	1156.7
10°	779.2	794.2	809.1	833.4	859.6	883.8	908.1	930.6	954.9	977.3	999.7
12.5°	704.5	721.3	740.0	754.9	771.7	786.7	801.6	827.8	853.9	880.1	906.3
15°	642.8	661.5	680.2	698.9	715.7	734.4	751.2	773.6	797.9	820.3	842.7
17.5°	571.8	590.5	611.0	631.6	652.1	672.7	693.2	725.0	756.8	786.7	818.4
20°	482.1	508.3	532.5	560.6	588.6	616.6	644.7	678.3	711.9	743.7	777.3
22.5°	392.4	416.7	441.0	474.6	508.3	540.0	573.7	618.5	661.5	706.3	749.3
25°	327.0	349.4	371.9	409.2	444.7	482.1	517.6	571.8	624.1	678.3	730.6
27.5°	282.2	302.7	323.3	362.5	401.7	439.1	478.4	538.2	596.1	655.9	713.8
30°	261.6	274.7	287.8	325.1	362.5	398.0	435.4	493.3	551.2	609.2	667.1
32.5°	228.0	239.2	250.4	284.0	317.7	349.4	383.1	442.9	500.8	560.6	618.5
35°	201.8	211.2	220.5	252.3	282.2	313.9	343.8	403.6	463.4	523.2	583.0
37.5°	186.9	196.2	203.7	231.7	261.6	289.6	317.7	377.5	435.4	495.2	553.1
40°	175.6	181.3	188.7	216.8	242.9	270.9	297.1	351.3	407.4	461.5	515.7
42.5°	168.2	175.6	181.3	205.5	231.7	256.0	280.3	332.6	384.9	435.4	487.7
45°	166.3	173.8	181.3	201.8	222.4	241.0	261.6	312.1	362.5	413.0	463.4
47.5°	162.6	168.2	175.6	192.5	207.4	224.2	239.2	289.6	340.1	388.7	439.1
50°	160.7	162.6	166.3	181.3	196.2	211.2	226.1	276.6	327.0	377.5	427.9
52.5°	158.8	158.8	158.8	171.9	185.0	196.2	209.3	259.7	312.1	362.5	413.0
55°	147.6	145.8	145.8	158.8	170.0	183.1	194.3	244.8	295.2	343.8	394.3
57.5°	136.4	134.5	132.7	143.9	155.1	166.3	177.5	228.0	280.3	330.7	381.2
60°	125.2	123.3	123.3	134.5	143.9	155.1	164.4	216.8	267.2	319.5	370.0
62.5°	112.1	114.0	114.0	123.3	134.5	143.9	153.2	205.5	259.7	312.1	364.4
65°	102.8	104.6	104.6	115.9	127.1	138.3	149.5	199.9	252.3	302.7	353.2
67.5°	95.3	97.2	97.2	110.2	121.5	134.5	145.8	190.6	237.3	282.2	327.0
70°	87.8	87.8	89.7	102.8	115.9	128.9	142.0	181.3	220.5	257.9	297.1
72.5°	78.5	80.3	82.2	95.3	106.5	119.6	130.8	166.3	201.8	237.3	272.8
75°	69.1	71.0	72.9	84.1	95.3	106.5	117.7	151.4	183.1	216.8	248.5
77.5°	61.7	63.5	65.4	74.7	84.1	93.4	102.8	127.1	153.2	177.5	201.8
80°	50.5	50.5	52.3	59.8	67.3	72.9	80.3	97.2	114.0	128.9	145.8
82.5°	37.4	39.2	39.2	44.8	48.6	54.2	57.9	67.3	74.7	84.1	91.6
85°	31.8	29.9	29.9	33.6	35.5	39.2	41.1	46.7	50.5	56.1	59.8
87.5°	13.1	11.2	11.2	13.1	16.8	18.7	20.6	20.6	22.4	22.4	22.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4
2.5°	1379.0	1382.8	1388.4	1392.1	1401.4	1408.9	1418.3	1425.7	1431.3	1440.7	1437.0
5°	1328.6	1345.4	1362.2	1379.0	1392.1	1405.2	1416.4	1429.5	1444.4	1472.5	1479.9
7.5°	1179.1	1201.5	1222.1	1244.5	1270.6	1296.8	1323.0	1349.1	1373.4	1408.9	1431.3
10°	1031.5	1063.2	1093.1	1124.9	1149.2	1173.5	1195.9	1220.2	1253.8	1289.3	1330.4
12.5°	938.0	969.8	1001.6	1033.3	1068.8	1102.5	1138.0	1171.6	1203.4	1231.4	1278.1
15°	876.4	911.9	945.5	979.1	1022.1	1063.2	1106.2	1147.3	1194.0	1231.4	1263.2
17.5°	861.4	904.4	945.5	988.5	1033.3	1078.2	1123.0	1167.9	1214.6	1270.6	1311.8
20°	835.3	893.2	951.1	1009.0	1067.0	1123.0	1181.0	1237.0	1298.7	1365.9	1384.6
22.5°	820.3	889.5	960.5	1029.6	1108.1	1188.4	1266.9	1345.4	1410.8	1461.2	1517.3
25°	818.4	904.4	992.2	1078.2	1177.2	1274.4	1373.4	1470.6	1554.7	1605.1	1650.0
27.5°	816.6	921.2	1024.0	1126.8	1248.2	1367.8	1489.3	1608.9	1687.3	1760.2	1797.6
30°	794.2	919.3	1046.4	1171.6	1308.0	1444.4	1580.8	1717.2	1797.6	1848.0	1866.7
32.5°	766.1	913.7	1061.4	1209.0	1364.1	1519.2	1672.4	1827.5	1891.0	1934.0	1919.0
35°	743.7	906.3	1067.0	1227.7	1392.1	1558.4	1722.8	1887.3	1978.8	2038.6	2014.3
37.5°	723.1	893.2	1063.2	1233.3	1425.7	1618.2	1810.7	2003.1	2091.0	2154.5	2126.5
40°	698.9	880.1	1063.2	1244.5	1465.0	1683.6	1904.1	2122.7	2236.7	2290.9	2247.9
42.5°	678.3	867.0	1057.6	1246.4	1481.8	1717.2	1952.7	2188.1	2315.2	2391.8	2337.6
45°	652.1	840.9	1027.7	1216.5	1476.2	1735.9	1993.8	2253.5	2401.1	2460.9	2386.2
47.5°	624.1	811.0	996.0	1181.0	1457.5	1734.1	2010.6	2287.2	2423.6	2494.6	2425.4
50°	614.8	801.6	986.6	1173.5	1472.5	1773.3	2072.3	2371.2	2470.3	2528.2	2436.6
52.5°	612.9	811.0	1010.9	1209.0	1509.8	1808.8	2109.6	2408.6	2489.0	2550.6	2468.4
55°	607.3	822.2	1035.2	1248.2	1562.1	1877.9	2191.9	2505.8	2586.1	2631.0	2569.3
57.5°	612.9	844.6	1074.4	1306.1	1629.4	1952.7	2275.9	2599.2	2696.4	2728.2	2715.1
60°	616.6	863.3	1108.1	1354.7	1670.5	1986.3	2302.1	2617.9	2718.8	2797.3	2812.2
62.5°	607.3	850.2	1091.3	1334.2	1620.1	1906.0	2191.9	2477.8	2644.1	2759.9	2827.2
65°	579.3	803.5	1029.6	1253.8	1517.3	1782.6	2046.1	2309.6	2485.2	2657.1	2711.3
67.5°	517.6	708.2	898.8	1089.4	1319.2	1549.1	1777.0	2006.9	2227.4	2393.7	2468.4
70°	448.5	598.0	749.3	898.8	1108.1	1317.4	1526.6	1735.9	1930.3	2113.4	2184.4
72.5°	390.5	506.4	624.1	740.0	889.5	1037.1	1186.6	1334.2	1564.0	1747.1	1816.3
75°	332.6	416.7	498.9	583.0	685.8	788.5	889.5	992.2	1154.8	1319.2	1388.4
77.5°	256.0	312.1	366.2	420.4	491.4	560.6	631.6	700.7	814.7	938.0	973.5
80°	177.5	209.3	239.2	270.9	327.0	383.1	439.1	495.2	569.9	639.1	693.2
82.5°	110.2	130.8	149.5	168.2	213.0	257.9	300.8	345.7	375.6	379.3	433.5
85°	71.0	84.1	95.3	106.5	132.7	160.7	186.9	213.0	190.6	177.5	211.2
87.5°	28.0	35.5	41.1	46.7	44.8	43.0	41.1	39.2	33.6	29.9	37.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026
 CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4
2.5°	1440.7	1446.3	1451.9	1455.6	1461.2	1463.1	1465.0	1465.0	1466.8	1468.7	1472.5
5°	1509.8	1521.0	1532.2	1541.6	1552.8	1562.1	1569.6	1579.0	1586.4	1586.4	1584.6
7.5°	1451.9	1479.9	1508.0	1536.0	1564.0	1584.6	1603.3	1623.8	1642.5	1646.2	1650.0
10°	1375.3	1405.2	1433.2	1463.1	1491.1	1522.9	1552.8	1582.7	1614.5	1620.1	1627.5
12.5°	1304.3	1339.8	1375.3	1408.9	1444.4	1466.8	1489.3	1509.8	1532.2	1547.2	1562.1
15°	1302.4	1332.3	1362.2	1390.2	1420.1	1433.2	1446.3	1457.5	1470.6	1470.6	1472.5
17.5°	1345.4	1364.1	1382.8	1399.6	1418.3	1420.1	1423.9	1425.7	1427.6	1422.0	1416.4
20°	1429.5	1437.0	1444.4	1451.9	1459.4	1446.3	1435.1	1422.0	1408.9	1394.0	1380.9
22.5°	1552.8	1536.0	1519.2	1502.4	1485.5	1463.1	1438.8	1416.4	1392.1	1373.4	1354.7
25°	1668.7	1648.1	1627.5	1607.0	1586.4	1537.9	1489.3	1438.8	1390.2	1369.7	1349.1
27.5°	1823.7	1792.0	1760.2	1728.5	1696.7	1631.3	1565.9	1500.5	1435.1	1399.6	1365.9
30°	1861.1	1825.6	1790.1	1752.7	1717.2	1653.7	1592.0	1528.5	1465.0	1423.9	1384.6
32.5°	1915.3	1874.2	1833.1	1792.0	1750.9	1689.2	1627.5	1564.0	1502.4	1465.0	1425.7
35°	2005.0	1958.3	1911.6	1863.0	1816.3	1752.7	1691.1	1627.5	1564.0	1521.0	1479.9
37.5°	2081.6	2027.4	1973.2	1919.0	1864.9	1808.8	1750.9	1694.8	1636.9	1593.9	1552.8
40°	2167.6	2107.8	2048.0	1990.1	1930.3	1877.9	1825.6	1771.4	1719.1	1685.5	1651.8
42.5°	2242.3	2169.4	2098.4	2027.4	1954.6	1919.0	1885.4	1849.9	1814.4	1797.6	1778.9
45°	2294.6	2227.4	2158.2	2091.0	2023.7	1997.5	1971.4	1945.2	1919.0	1935.9	1952.7
47.5°	2317.1	2262.9	2210.5	2158.2	2104.0	2113.4	2122.7	2130.2	2139.5	2162.0	2186.3
50°	2337.6	2307.7	2275.9	2246.1	2214.3	2249.8	2283.4	2318.9	2354.4	2401.1	2447.9
52.5°	2378.7	2361.9	2347.0	2330.1	2313.3	2375.0	2436.6	2498.3	2560.0	2612.3	2664.6
55°	2502.0	2489.0	2475.9	2460.9	2447.9	2535.7	2621.6	2709.5	2797.3	2851.5	2905.7
57.5°	2672.1	2664.6	2655.3	2647.8	2638.5	2724.4	2808.5	2892.6	2978.5	3030.9	3085.1
60°	2801.0	2802.9	2802.9	2804.8	2804.8	2870.2	2935.6	3002.8	3068.2	3113.1	3159.8
62.5°	2870.2	2866.4	2862.7	2859.0	2855.2	2909.4	2963.6	3017.8	3072.0	3105.6	3139.2
65°	2795.4	2816.0	2836.5	2857.1	2877.6	2885.1	2890.7	2898.2	2903.8	2924.4	2944.9
67.5°	2545.0	2586.1	2625.4	2666.5	2705.7	2677.7	2651.5	2623.5	2595.5	2601.1	2604.8
70°	2266.6	2313.3	2361.9	2408.6	2455.3	2389.9	2324.5	2257.3	2191.9	2169.4	2147.0
72.5°	1911.6	1952.7	1995.7	2036.8	2077.9	1997.5	1919.0	1838.7	1758.3	1719.1	1679.9
75°	1461.2	1509.8	1560.3	1608.9	1657.4	1567.8	1476.2	1386.5	1294.9	1268.8	1244.5
77.5°	1065.1	1123.0	1181.0	1238.9	1296.8	1216.5	1136.1	1053.9	973.5	958.6	943.6
80°	775.5	820.3	863.3	908.1	951.1	904.4	857.7	811.0	764.3	762.4	760.5
82.5°	523.2	562.4	599.8	639.1	676.4	657.7	640.9	622.2	603.6	622.2	642.8
85°	269.1	323.3	379.3	433.5	487.7	482.1	478.4	472.8	467.1	491.4	513.9
87.5°	54.2	100.9	147.6	192.5	239.2	228.0	216.8	203.7	192.5	199.9	205.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4
2.5°	1474.3	1476.2	1476.2	1476.2	1476.2	1476.2	1472.5	1470.6	1466.8	1463.1	1457.5
5°	1584.6	1582.7	1575.2	1567.8	1558.4	1550.9	1545.3	1537.9	1532.2	1524.8	1513.6
7.5°	1653.7	1657.4	1644.4	1633.2	1620.1	1607.0	1593.9	1580.8	1567.8	1554.7	1528.5
10°	1633.2	1638.8	1631.3	1623.8	1614.5	1607.0	1592.0	1575.2	1560.3	1543.5	1511.7
12.5°	1575.2	1590.2	1586.4	1582.7	1579.0	1575.2	1565.9	1554.7	1545.3	1534.1	1498.6
15°	1472.5	1472.5	1474.3	1476.2	1476.2	1478.1	1479.9	1481.8	1483.7	1485.5	1465.0
17.5°	1410.8	1405.2	1405.2	1405.2	1405.2	1405.2	1412.7	1422.0	1429.5	1437.0	1431.3
20°	1365.9	1352.9	1351.0	1351.0	1349.1	1347.3	1360.3	1375.3	1388.4	1401.4	1408.9
22.5°	1336.0	1317.4	1315.5	1313.6	1311.8	1309.9	1326.7	1343.5	1360.3	1377.2	1403.3
25°	1328.6	1308.0	1309.9	1311.8	1311.8	1313.6	1326.7	1339.8	1352.9	1365.9	1410.8
27.5°	1330.4	1296.8	1298.7	1300.5	1300.5	1302.4	1323.0	1341.7	1362.2	1380.9	1437.0
30°	1343.5	1304.3	1300.5	1296.8	1293.1	1289.3	1317.4	1345.4	1373.4	1401.4	1444.4
32.5°	1388.4	1351.0	1341.7	1332.3	1323.0	1313.6	1347.3	1379.0	1412.7	1444.4	1479.9
35°	1437.0	1395.8	1392.1	1388.4	1382.8	1379.0	1408.9	1440.7	1470.6	1500.5	1532.2
37.5°	1509.8	1468.7	1465.0	1459.4	1455.6	1450.0	1483.7	1515.4	1549.1	1580.8	1608.9
40°	1618.2	1584.6	1582.7	1582.7	1580.8	1579.0	1605.1	1633.2	1659.3	1685.5	1704.2
42.5°	1762.1	1745.3	1750.9	1758.3	1764.0	1769.6	1790.1	1812.5	1833.1	1853.6	1848.0
45°	1969.5	1986.3	1988.2	1990.1	1991.9	1993.8	1999.4	2006.9	2012.5	2018.1	1995.7
47.5°	2208.7	2231.1	2242.3	2253.5	2262.9	2274.1	2266.6	2257.3	2249.8	2240.4	2184.4
50°	2492.7	2539.4	2537.6	2535.7	2531.9	2530.1	2515.1	2500.2	2483.4	2468.4	2386.2
52.5°	2716.9	2769.3	2778.6	2787.9	2797.3	2806.6	2778.6	2750.6	2720.7	2692.6	2589.9
55°	2958.0	3012.2	3014.0	3015.9	3015.9	3017.8	2978.5	2939.3	2898.2	2859.0	2752.4
57.5°	3137.4	3189.7	3184.1	3180.4	3174.7	3169.1	3122.4	3075.7	3029.0	2982.3	2875.8
60°	3204.6	3249.5	3238.3	3227.1	3214.0	3202.8	3167.3	3131.8	3094.4	3058.9	2956.1
62.5°	3172.9	3206.5	3189.7	3174.7	3157.9	3141.1	3096.3	3049.5	3004.7	2958.0	2883.2
65°	2963.6	2984.1	2961.7	2941.2	2920.6	2898.2	2860.8	2823.4	2784.2	2746.8	2696.4
67.5°	2610.4	2614.2	2612.3	2610.4	2608.6	2606.7	2552.5	2498.3	2442.3	2388.1	2384.3
70°	2126.5	2104.0	2107.8	2113.4	2117.1	2120.9	2079.7	2040.5	1999.4	1958.3	1977.0
72.5°	1640.6	1601.4	1610.7	1621.9	1631.3	1640.6	1607.0	1575.2	1541.6	1508.0	1534.1
75°	1218.3	1194.0	1203.4	1214.6	1223.9	1233.3	1220.2	1207.1	1192.2	1179.1	1203.4
77.5°	928.7	913.7	915.6	915.6	917.5	917.5	919.3	923.1	925.0	926.8	953.0
80°	756.8	754.9	753.0	751.2	747.4	745.6	764.3	782.9	801.6	820.3	833.4
82.5°	661.5	680.2	669.0	659.6	648.4	637.2	654.0	670.8	687.6	704.5	698.9
85°	538.2	560.6	540.0	519.5	497.0	476.5	491.4	504.5	519.5	532.5	525.1
87.5°	213.0	218.6	185.0	153.2	119.6	86.0	136.4	185.0	235.4	284.0	291.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4	1345.4
2.5°	1451.9	1444.4	1438.8	1437.0	1433.2	1431.3	1427.6	1423.9	1418.3	1414.5	1408.9
5°	1500.5	1489.3	1476.2	1457.5	1440.7	1422.0	1403.3	1386.5	1369.7	1351.0	1334.2
7.5°	1502.4	1476.2	1450.0	1425.7	1399.6	1375.3	1349.1	1326.7	1302.4	1278.1	1255.7
10°	1481.8	1450.0	1418.3	1386.5	1356.6	1324.8	1293.1	1266.9	1238.9	1210.9	1184.7
12.5°	1465.0	1429.5	1394.0	1356.6	1321.1	1283.7	1246.4	1220.2	1194.0	1167.9	1141.7
15°	1444.4	1422.0	1401.4	1367.8	1334.2	1300.5	1266.9	1231.4	1197.8	1162.3	1126.8
17.5°	1427.6	1422.0	1416.4	1394.0	1371.5	1347.3	1324.8	1289.3	1253.8	1216.5	1181.0
20°	1418.3	1425.7	1433.2	1422.0	1410.8	1397.7	1386.5	1360.3	1334.2	1306.1	1280.0
22.5°	1429.5	1457.5	1483.7	1485.5	1489.3	1491.1	1493.0	1468.7	1444.4	1418.3	1394.0
25°	1455.6	1500.5	1545.3	1569.6	1593.9	1620.1	1644.4	1629.4	1614.5	1599.5	1584.6
27.5°	1491.1	1547.2	1603.3	1638.8	1672.4	1707.9	1743.4	1741.5	1739.7	1735.9	1734.1
30°	1485.5	1528.5	1571.5	1614.5	1657.4	1700.4	1743.4	1765.8	1786.4	1808.8	1831.2
32.5°	1517.3	1552.8	1590.2	1635.0	1679.9	1726.6	1771.4	1818.1	1863.0	1909.7	1956.4
35°	1565.9	1597.6	1631.3	1679.9	1730.3	1778.9	1829.4	1885.4	1943.3	2001.3	2057.3
37.5°	1638.8	1666.8	1696.7	1737.8	1780.8	1821.9	1864.9	1947.1	2029.3	2113.4	2195.6
40°	1722.8	1741.5	1760.2	1799.5	1838.7	1877.9	1917.2	2020.0	2122.7	2225.5	2328.3
42.5°	1844.3	1838.7	1833.1	1864.9	1898.5	1930.3	1963.9	2057.3	2150.8	2244.2	2337.6
45°	1973.2	1950.8	1928.4	1943.3	1960.2	1975.1	1991.9	2087.2	2182.5	2279.7	2375.0
47.5°	2128.3	2072.3	2016.2	2003.1	1990.1	1975.1	1962.0	2064.8	2167.6	2272.2	2375.0
50°	2304.0	2219.9	2137.7	2104.0	2068.5	2034.9	1999.4	2083.5	2169.4	2255.4	2339.5
52.5°	2487.1	2382.5	2279.7	2227.4	2175.0	2120.9	2068.5	2139.5	2212.4	2285.3	2356.3
55°	2644.1	2537.6	2429.2	2367.5	2305.8	2244.2	2182.5	2253.5	2324.5	2395.5	2466.5
57.5°	2769.3	2662.7	2556.2	2498.3	2438.5	2380.6	2320.8	2388.1	2457.2	2526.3	2593.6
60°	2855.2	2752.4	2649.7	2593.6	2537.6	2481.5	2425.4	2505.8	2586.1	2668.4	2748.7
62.5°	2810.4	2735.6	2660.9	2636.6	2612.3	2586.1	2561.8	2638.5	2713.2	2789.8	2866.4
65°	2645.9	2595.5	2545.0	2569.3	2595.5	2619.8	2645.9	2696.4	2746.8	2799.2	2849.6
67.5°	2378.7	2375.0	2369.4	2423.6	2477.8	2533.8	2588.0	2621.6	2653.4	2687.0	2720.7
70°	1995.7	2016.2	2034.9	2128.3	2221.8	2315.2	2408.6	2421.7	2434.8	2447.9	2460.9
72.5°	1562.1	1588.3	1616.3	1739.7	1861.1	1984.4	2107.8	2100.3	2092.8	2083.5	2076.0
75°	1229.5	1253.8	1280.0	1394.0	1508.0	1621.9	1735.9	1704.2	1674.3	1642.5	1610.7
77.5°	981.0	1007.2	1035.2	1141.7	1248.2	1356.6	1463.1	1386.5	1309.9	1233.3	1156.7
80°	844.6	857.7	868.9	941.8	1012.8	1085.7	1158.5	1080.0	999.7	919.3	840.9
82.5°	693.2	685.8	680.2	723.1	766.1	809.1	852.1	777.3	702.6	626.0	551.2
85°	517.6	510.1	502.7	525.1	547.5	571.8	594.2	508.3	422.3	334.5	248.5
87.5°	300.8	308.3	315.8	340.1	364.4	390.5	414.8	327.0	239.2	149.5	61.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026

CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676026
 CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1345.4	1345.4
2.5°	1397.7	1388.4
5°	1321.1	1308.0
7.5°	1237.0	1220.2
10°	1160.4	1138.0
12.5°	1111.8	1083.8
15°	1093.1	1059.5
17.5°	1149.2	1117.4
20°	1235.1	1192.2
22.5°	1339.8	1287.5
25°	1521.0	1457.5
27.5°	1668.7	1603.3
30°	1760.2	1689.2
32.5°	1861.1	1767.7
35°	1965.8	1876.1
37.5°	2092.8	1991.9
40°	2223.6	2119.0
42.5°	2268.5	2201.2
45°	2311.5	2247.9
47.5°	2320.8	2268.5
50°	2330.1	2322.7
52.5°	2356.3	2354.4
55°	2468.4	2470.3
57.5°	2606.7	2617.9
60°	2733.8	2720.7
62.5°	2799.2	2731.9
65°	2754.3	2660.9
67.5°	2619.8	2518.9
70°	2324.5	2188.1
72.5°	1956.4	1836.8
75°	1508.0	1407.1
77.5°	1072.6	988.5
80°	754.9	670.8
82.5°	484.0	416.7
85°	218.6	190.6
87.5°	61.7	59.8
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P676026
CATALOG NUMBER: CCW-SA-2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)