

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P676027

Luminaire Tested: **CCW-SA-2C-827-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P676027
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2C-827-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @615mA w/
SLR distribution lens
Light Source: (32) 2700K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5515.7 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 7.8 fc
 Type IV - Short - N/A

REPORT NUMBER: P676027
CATALOG NUMBER: CCW-SA-2C-827-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1134.9	0.0	1134.9
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	4380.8	0.0	4380.8
	% Fixture	79.4	0.0	79.4
Total	Lumens	5515.7	0.0	5515.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.9	2.5
10°-20°	289.0	5.2
20°-30°	422.8	7.7
30°-40°	595.6	10.8
40°-50°	818.5	14.8
50°-60°	1115.6	20.2
60°-70°	1221.0	22.1
70°-80°	705.1	12.8
80°-90°	211.4	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5515.7	100.0
0°-180°	5515.7	100.0

Coefficient of Utilization



REPORT NUMBER: P676027


CATALOG NUMBER: CCW-SA-2C-827-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	566.5	10.3			
FM	(30°-60°)	2012.8	36.5			
FH	(60°-80°)	1621.9	29.4			G1/1800
FVH	(80°-90°)	179.5	3.3			G2/225
BL	(0°-30°)	282.1	5.1	B1/500		
BM	(30°-60°)	516.8	9.4	B1/1000		
BH	(60°-80°)	304.1	5.5	B1/500		G1/500
BVH	(80°-90°)	31.8	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4
2.5°	1817.6	1807.8	1800.5	1793.2	1783.4	1776.0	1766.3	1756.5	1744.2	1734.5	1722.2
5°	1712.4	1683.1	1653.7	1636.6	1617.0	1599.9	1580.3	1558.3	1536.3	1511.8	1489.8
7.5°	1597.5	1560.8	1524.1	1494.7	1462.9	1433.6	1401.8	1374.8	1347.9	1321.0	1294.1
10°	1489.8	1455.6	1421.3	1384.6	1345.5	1308.8	1269.7	1233.0	1196.3	1159.6	1122.9
12.5°	1418.9	1377.3	1338.2	1296.6	1257.4	1215.8	1174.2	1140.0	1105.7	1069.1	1034.8
15°	1387.1	1347.9	1311.2	1269.7	1228.1	1186.5	1144.9	1105.7	1069.1	1029.9	990.8
17.5°	1462.9	1406.6	1350.4	1296.6	1242.7	1188.9	1135.1	1086.2	1037.3	988.3	939.4
20°	1560.8	1489.8	1421.3	1355.3	1286.8	1220.7	1152.2	1083.7	1015.2	946.7	878.2
22.5°	1685.5	1604.8	1526.5	1440.9	1352.8	1267.2	1179.1	1093.5	1007.9	919.8	834.2
25°	1908.1	1812.7	1717.3	1595.0	1470.3	1347.9	1223.2	1110.6	1000.6	888.0	775.5
27.5°	2099.0	1969.3	1842.1	1695.3	1548.5	1401.8	1255.0	1125.3	998.1	868.5	738.8
30°	2211.5	2084.3	1957.1	1778.5	1602.4	1423.8	1245.2	1100.9	959.0	814.6	670.3
32.5°	2314.2	2172.4	2030.5	1834.8	1636.6	1440.9	1242.7	1083.7	927.2	768.2	609.1
35°	2456.1	2299.6	2145.4	1917.9	1690.4	1462.9	1235.4	1071.5	905.1	741.2	574.9
37.5°	2607.8	2414.5	2223.7	1971.8	1719.8	1467.8	1215.8	1054.4	892.9	731.5	570.0
40°	2774.2	2539.3	2306.9	2028.0	1751.6	1472.7	1193.8	1032.4	870.9	707.0	545.5
42.5°	2881.8	2627.4	2373.0	2072.1	1773.6	1472.7	1171.8	1012.8	853.8	692.3	533.3
45°	2943.0	2695.9	2451.2	2125.9	1800.5	1475.1	1149.8	993.2	836.6	677.6	521.1
47.5°	2969.9	2739.9	2509.9	2167.5	1827.4	1484.9	1142.4	983.4	822.0	663.0	501.5
50°	3040.8	2837.8	2634.7	2267.8	1903.3	1536.3	1169.4	998.1	829.3	658.1	486.8
52.5°	3082.4	2908.7	2735.0	2358.3	1981.5	1604.8	1228.1	1037.3	846.4	655.6	464.8
55°	3234.1	3067.7	2901.4	2500.2	2096.5	1695.3	1291.7	1081.3	870.9	658.1	447.7
57.5°	3427.3	3251.2	3077.5	2644.5	2211.5	1778.5	1345.5	1120.4	892.9	667.9	440.3
60°	3561.9	3390.6	3221.8	2761.9	2299.6	1839.7	1377.3	1142.4	907.6	670.3	435.4
62.5°	3576.6	3356.4	3138.7	2691.0	2243.3	1793.2	1345.5	1118.0	890.5	660.5	433.0
65°	3483.6	3226.7	2969.9	2541.8	2113.6	1685.5	1257.4	1049.5	841.5	631.2	423.2
67.5°	3297.7	2996.8	2695.9	2304.5	1913.0	1521.6	1130.2	951.6	775.5	596.9	418.3
70°	2864.7	2600.5	2338.7	1998.7	1661.1	1321.0	981.0	834.2	689.9	543.1	396.3
72.5°	2404.8	2157.7	1913.0	1636.6	1362.6	1086.2	809.7	699.7	589.6	477.0	367.0
75°	1842.1	1656.2	1472.7	1267.2	1061.7	853.8	648.3	567.6	486.8	406.1	325.4
77.5°	1294.1	1193.8	1096.0	941.8	787.7	633.6	479.5	425.7	371.8	318.0	264.2
80°	878.2	822.0	768.2	658.1	548.0	435.4	325.4	291.1	254.4	220.2	183.5
82.5°	545.5	543.1	538.2	462.4	386.5	310.7	234.8	205.5	178.6	149.2	119.9
85°	249.5	291.1	330.3	288.7	247.1	205.5	163.9	144.3	124.8	102.7	83.2
87.5°	78.3	95.4	110.1	105.2	97.9	93.0	85.6	73.4	61.2	48.9	36.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4
2.5°	1712.4	1705.1	1695.3	1685.5	1673.3	1663.5	1651.3	1639.1	1636.6	1631.7	1629.3
5°	1475.1	1460.5	1443.3	1428.7	1414.0	1396.9	1382.2	1365.1	1352.8	1338.2	1325.9
7.5°	1267.2	1242.7	1215.8	1188.9	1164.5	1140.0	1113.1	1088.6	1076.4	1064.2	1051.9
10°	1100.9	1076.4	1054.4	1029.9	1012.8	998.1	981.0	963.9	949.2	934.5	919.8
12.5°	1017.7	1000.6	983.4	966.3	946.7	929.6	910.0	890.5	873.3	858.7	841.5
15°	966.3	941.8	914.9	890.5	863.6	839.1	812.2	785.3	765.7	748.6	729.0
17.5°	905.1	868.5	834.2	797.5	768.2	738.8	707.0	677.6	655.6	631.2	609.1
20°	836.6	795.1	751.0	709.4	675.2	643.4	609.1	574.9	550.4	523.5	499.1
22.5°	777.9	724.1	667.9	611.6	574.9	538.2	499.1	462.4	440.3	415.9	393.9
25°	714.3	655.6	594.5	533.3	496.6	457.5	420.8	381.6	364.5	349.8	332.7
27.5°	680.1	621.4	560.2	501.5	467.3	430.6	396.3	359.6	347.4	332.7	320.5
30°	611.6	555.3	496.6	437.9	413.4	391.4	367.0	342.5	337.6	335.1	330.3
32.5°	550.4	491.7	433.0	374.3	352.3	330.3	308.2	286.2	283.8	278.9	276.4
35°	518.6	462.4	403.6	347.4	327.8	305.8	286.2	264.2	259.3	252.0	247.1
37.5°	511.3	452.6	391.4	332.7	313.1	293.6	271.5	252.0	247.1	242.2	237.3
40°	491.7	435.4	381.6	325.4	305.8	286.2	264.2	244.6	239.7	234.8	230.0
42.5°	477.0	423.2	367.0	310.7	293.6	276.4	256.9	239.7	234.8	230.0	222.6
45°	464.8	408.5	349.8	293.6	281.3	269.1	254.4	242.2	237.3	230.0	225.1
47.5°	445.2	391.4	335.1	278.9	266.7	256.9	244.6	232.4	227.5	222.6	217.7
50°	430.6	374.3	318.0	261.8	252.0	242.2	232.4	222.6	222.6	225.1	225.1
52.5°	411.0	357.2	303.3	249.5	239.7	230.0	220.2	210.4	212.8	215.3	217.7
55°	393.9	342.5	288.7	234.8	225.1	215.3	203.0	193.3	195.7	198.2	200.6
57.5°	386.5	332.7	278.9	225.1	215.3	203.0	193.3	181.0	181.0	181.0	181.0
60°	381.6	325.4	271.5	215.3	203.0	193.3	181.0	168.8	166.4	166.4	163.9
62.5°	379.2	322.9	269.1	212.8	198.2	185.9	171.2	156.6	154.1	151.7	149.2
65°	369.4	318.0	264.2	210.4	193.3	178.6	161.5	144.3	141.9	141.9	139.4
67.5°	367.0	313.1	261.8	207.9	190.8	171.2	154.1	134.5	132.1	129.7	127.2
70°	347.4	300.9	252.0	203.0	183.5	166.4	146.8	127.2	124.8	119.9	117.4
72.5°	322.9	281.3	237.3	193.3	173.7	154.1	134.5	115.0	112.5	110.1	105.2
75°	286.2	247.1	207.9	168.8	151.7	137.0	119.9	102.7	100.3	97.9	93.0
77.5°	234.8	203.0	173.7	141.9	129.7	117.4	105.2	93.0	90.5	88.1	83.2
80°	166.4	146.8	129.7	110.1	102.7	93.0	85.6	75.8	75.8	73.4	73.4
82.5°	110.1	100.3	90.5	80.7	75.8	70.9	66.1	61.2	61.2	58.7	58.7
85°	78.3	73.4	66.1	61.2	58.7	53.8	51.4	46.5	46.5	46.5	46.5
87.5°	36.7	36.7	34.2	34.2	31.8	31.8	29.4	26.9	26.9	26.9	26.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4
2.5°	1624.4	1617.0	1609.7	1599.9	1592.6	1582.8	1570.6	1560.8	1548.5	1548.5	1546.1
5°	1311.2	1303.9	1296.6	1286.8	1279.4	1269.7	1262.3	1252.5	1242.7	1242.7	1240.3
7.5°	1039.7	1025.0	1010.3	993.2	978.5	968.8	959.0	946.7	936.9	929.6	922.3
10°	905.1	890.5	873.3	858.7	841.5	829.3	817.1	802.4	790.2	780.4	770.6
12.5°	824.4	807.3	790.2	773.0	755.9	738.8	724.1	707.0	689.9	677.6	665.4
15°	709.4	692.3	675.2	658.1	640.9	621.4	601.8	579.8	560.2	550.4	543.1
17.5°	584.7	567.6	548.0	530.9	511.3	496.6	481.9	467.3	452.6	442.8	435.4
20°	472.1	452.6	433.0	413.4	393.9	384.1	374.3	364.5	354.7	347.4	342.5
22.5°	369.4	357.2	347.4	335.1	322.9	315.6	310.7	303.3	296.0	296.0	296.0
25°	315.6	308.2	303.3	296.0	288.7	286.2	283.8	278.9	276.4	274.0	274.0
27.5°	305.8	298.5	291.1	283.8	276.4	274.0	271.5	266.7	264.2	264.2	264.2
30°	325.4	322.9	320.5	318.0	315.6	310.7	303.3	298.5	291.1	286.2	281.3
32.5°	271.5	269.1	269.1	266.7	264.2	269.1	271.5	276.4	278.9	281.3	283.8
35°	239.7	234.8	230.0	225.1	220.2	217.7	215.3	212.8	210.4	210.4	207.9
37.5°	232.4	227.5	222.6	217.7	212.8	210.4	207.9	205.5	203.0	203.0	200.6
40°	225.1	220.2	217.7	212.8	207.9	205.5	203.0	198.2	195.7	193.3	193.3
42.5°	217.7	215.3	210.4	207.9	203.0	200.6	198.2	193.3	190.8	188.4	185.9
45°	217.7	212.8	207.9	203.0	198.2	195.7	190.8	188.4	183.5	183.5	181.0
47.5°	212.8	207.9	203.0	198.2	193.3	190.8	185.9	183.5	178.6	176.1	173.7
50°	225.1	217.7	207.9	200.6	190.8	188.4	183.5	181.0	176.1	173.7	171.2
52.5°	220.2	212.8	203.0	195.7	185.9	181.0	178.6	173.7	168.8	166.4	163.9
55°	203.0	195.7	190.8	183.5	176.1	171.2	166.4	161.5	156.6	154.1	154.1
57.5°	181.0	178.6	176.1	173.7	171.2	166.4	161.5	154.1	149.2	146.8	144.3
60°	161.5	163.9	166.4	168.8	171.2	163.9	156.6	149.2	141.9	139.4	137.0
62.5°	146.8	151.7	156.6	159.0	163.9	156.6	149.2	141.9	134.5	132.1	129.7
65°	137.0	139.4	139.4	141.9	141.9	137.0	134.5	129.7	124.8	122.3	122.3
67.5°	124.8	124.8	124.8	122.3	122.3	119.9	119.9	117.4	115.0	112.5	112.5
70°	112.5	112.5	112.5	110.1	110.1	107.6	107.6	105.2	102.7	102.7	100.3
72.5°	102.7	102.7	100.3	100.3	97.9	97.9	97.9	95.4	95.4	93.0	93.0
75°	90.5	90.5	88.1	88.1	85.6	85.6	85.6	83.2	83.2	83.2	80.7
77.5°	80.7	80.7	78.3	78.3	75.8	75.8	75.8	73.4	73.4	70.9	70.9
80°	70.9	70.9	68.5	68.5	66.1	66.1	63.6	63.6	61.2	61.2	58.7
82.5°	56.3	56.3	56.3	56.3	56.3	53.8	53.8	51.4	48.9	48.9	46.5
85°	46.5	46.5	46.5	44.0	44.0	44.0	41.6	41.6	39.1	36.7	36.7
87.5°	26.9	26.9	26.9	24.5	24.5	24.5	24.5	24.5	24.5	24.5	22.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4
2.5°	1546.1	1543.6	1533.9	1524.1	1533.9	1543.6	1543.6	1543.6	1541.2	1541.2	1541.2
5°	1240.3	1237.9	1233.0	1228.1	1228.1	1225.6	1230.5	1235.4	1240.3	1245.2	1250.1
7.5°	912.5	905.1	897.8	890.5	895.4	897.8	905.1	910.0	917.4	922.3	934.5
10°	760.8	751.0	743.7	736.3	731.5	726.6	721.7	719.2	714.3	709.4	714.3
12.5°	650.7	638.5	626.3	611.6	609.1	606.7	601.8	596.9	592.0	587.1	584.7
15°	533.3	523.5	518.6	511.3	501.5	491.7	486.8	484.4	479.5	474.6	472.1
17.5°	425.7	415.9	408.5	401.2	398.8	393.9	393.9	393.9	393.9	393.9	393.9
20°	335.1	327.8	327.8	325.4	325.4	322.9	325.4	327.8	327.8	330.3	332.7
22.5°	293.6	293.6	291.1	288.7	291.1	291.1	293.6	296.0	298.5	300.9	303.3
25°	271.5	269.1	271.5	274.0	274.0	274.0	276.4	276.4	278.9	278.9	278.9
27.5°	261.8	261.8	264.2	264.2	266.7	266.7	266.7	264.2	264.2	261.8	261.8
30°	276.4	271.5	271.5	271.5	269.1	266.7	264.2	264.2	261.8	259.3	256.9
32.5°	286.2	288.7	286.2	281.3	278.9	274.0	271.5	266.7	264.2	259.3	254.4
35°	207.9	205.5	210.4	212.8	215.3	217.7	220.2	222.6	222.6	225.1	225.1
37.5°	200.6	198.2	198.2	195.7	195.7	195.7	195.7	195.7	193.3	193.3	195.7
40°	190.8	188.4	188.4	185.9	185.9	183.5	183.5	183.5	183.5	183.5	183.5
42.5°	183.5	181.0	181.0	181.0	181.0	178.6	178.6	176.1	176.1	173.7	173.7
45°	181.0	178.6	176.1	173.7	173.7	171.2	171.2	171.2	168.8	168.8	168.8
47.5°	171.2	168.8	168.8	166.4	166.4	163.9	163.9	163.9	161.5	161.5	161.5
50°	166.4	163.9	163.9	161.5	161.5	159.0	159.0	159.0	156.6	156.6	156.6
52.5°	159.0	156.6	156.6	156.6	154.1	151.7	151.7	151.7	149.2	149.2	149.2
55°	151.7	149.2	149.2	149.2	146.8	144.3	144.3	144.3	141.9	141.9	141.9
57.5°	141.9	139.4	139.4	137.0	137.0	137.0	137.0	137.0	134.5	134.5	134.5
60°	134.5	132.1	132.1	129.7	129.7	127.2	127.2	127.2	127.2	127.2	127.2
62.5°	127.2	124.8	122.3	119.9	122.3	122.3	122.3	122.3	119.9	119.9	119.9
65°	119.9	117.4	115.0	112.5	112.5	112.5	112.5	112.5	112.5	112.5	112.5
67.5°	110.1	107.6	105.2	102.7	105.2	105.2	105.2	105.2	105.2	105.2	105.2
70°	100.3	97.9	97.9	95.4	95.4	93.0	93.0	95.4	95.4	95.4	95.4
72.5°	90.5	88.1	88.1	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6
75°	80.7	78.3	78.3	75.8	75.8	75.8	75.8	75.8	75.8	75.8	75.8
77.5°	68.5	66.1	66.1	66.1	66.1	66.1	66.1	68.5	68.5	68.5	68.5
80°	58.7	56.3	56.3	56.3	56.3	56.3	56.3	56.3	56.3	56.3	56.3
82.5°	46.5	44.0	44.0	44.0	44.0	44.0	44.0	44.0	44.0	44.0	44.0
85°	34.2	31.8	31.8	31.8	34.2	34.2	34.2	34.2	34.2	34.2	34.2
87.5°	22.0	19.6	19.6	19.6	22.0	22.0	22.0	22.0	19.6	19.6	19.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4
2.5°	1541.2	1541.2	1541.2	1538.8	1536.3	1533.9	1531.4	1538.8	1543.6	1551.0	1555.9
5°	1252.5	1257.4	1259.9	1267.2	1274.5	1281.9	1289.2	1294.1	1299.0	1301.5	1306.3
7.5°	944.3	956.5	966.3	976.1	985.9	993.2	1003.0	1010.3	1017.7	1025.0	1032.4
10°	716.8	721.7	724.1	733.9	741.2	751.0	758.4	765.7	773.0	777.9	785.3
12.5°	582.2	577.3	574.9	574.9	574.9	574.9	574.9	579.8	584.7	589.6	594.5
15°	469.7	467.3	464.8	462.4	459.9	455.0	452.6	457.5	462.4	467.3	472.1
17.5°	393.9	393.9	393.9	391.4	389.0	386.5	384.1	386.5	389.0	389.0	391.4
20°	337.6	340.0	342.5	344.9	344.9	347.4	347.4	349.8	352.3	352.3	354.7
22.5°	303.3	305.8	305.8	305.8	308.2	308.2	308.2	310.7	313.1	315.6	318.0
25°	276.4	276.4	274.0	274.0	276.4	276.4	276.4	276.4	278.9	278.9	278.9
27.5°	261.8	259.3	259.3	259.3	259.3	256.9	256.9	256.9	256.9	256.9	256.9
30°	254.4	252.0	249.5	247.1	247.1	244.6	242.2	242.2	242.2	242.2	242.2
32.5°	252.0	247.1	242.2	239.7	239.7	237.3	234.8	232.4	232.4	230.0	227.5
35°	225.1	222.6	222.6	220.2	217.7	215.3	212.8	212.8	212.8	210.4	210.4
37.5°	195.7	198.2	198.2	198.2	200.6	200.6	200.6	200.6	203.0	203.0	203.0
40°	183.5	183.5	183.5	185.9	188.4	188.4	190.8	190.8	193.3	193.3	193.3
42.5°	173.7	171.2	171.2	173.7	173.7	176.1	176.1	178.6	181.0	181.0	183.5
45°	168.8	166.4	166.4	166.4	166.4	163.9	163.9	166.4	168.8	171.2	173.7
47.5°	159.0	159.0	156.6	156.6	156.6	156.6	156.6	156.6	159.0	159.0	159.0
50°	154.1	154.1	151.7	151.7	151.7	151.7	151.7	151.7	151.7	151.7	151.7
52.5°	149.2	146.8	146.8	146.8	146.8	144.3	144.3	144.3	144.3	144.3	144.3
55°	141.9	139.4	139.4	139.4	139.4	139.4	139.4	139.4	141.9	141.9	141.9
57.5°	134.5	132.1	132.1	132.1	134.5	134.5	134.5	134.5	137.0	137.0	137.0
60°	127.2	127.2	127.2	127.2	127.2	127.2	127.2	129.7	129.7	132.1	132.1
62.5°	119.9	119.9	119.9	119.9	122.3	122.3	122.3	122.3	124.8	124.8	124.8
65°	112.5	112.5	112.5	112.5	115.0	115.0	115.0	115.0	115.0	115.0	115.0
67.5°	105.2	105.2	105.2	105.2	105.2	105.2	105.2	107.6	107.6	110.1	110.1
70°	95.4	93.0	93.0	95.4	95.4	97.9	97.9	100.3	100.3	102.7	102.7
72.5°	85.6	85.6	85.6	85.6	85.6	85.6	85.6	88.1	90.5	90.5	93.0
75°	75.8	75.8	75.8	75.8	78.3	78.3	78.3	80.7	80.7	83.2	83.2
77.5°	68.5	66.1	66.1	66.1	68.5	68.5	68.5	70.9	70.9	73.4	73.4
80°	56.3	56.3	56.3	56.3	58.7	58.7	58.7	58.7	61.2	61.2	61.2
82.5°	46.5	46.5	46.5	46.5	46.5	46.5	46.5	46.5	48.9	48.9	48.9
85°	34.2	34.2	34.2	34.2	36.7	36.7	36.7	36.7	36.7	36.7	36.7
87.5°	22.0	22.0	22.0	22.0	22.0	22.0	22.0	22.0	24.5	24.5	24.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4
2.5°	1555.9	1555.9	1555.9	1555.9	1560.8	1563.2	1568.1	1570.6	1568.1	1565.7	1560.8
5°	1308.8	1311.2	1311.2	1313.7	1313.7	1313.7	1313.7	1313.7	1318.6	1323.5	1328.4
7.5°	1034.8	1037.3	1039.7	1042.1	1042.1	1042.1	1039.7	1039.7	1042.1	1042.1	1044.6
10°	792.6	802.4	809.7	817.1	812.2	804.8	800.0	792.6	792.6	792.6	790.2
12.5°	599.4	601.8	606.7	609.1	606.7	606.7	604.2	601.8	604.2	609.1	611.6
15°	474.6	474.6	477.0	477.0	479.5	481.9	481.9	484.4	489.3	491.7	496.6
17.5°	393.9	396.3	396.3	398.8	398.8	401.2	401.2	401.2	406.1	411.0	418.3
20°	354.7	354.7	354.7	354.7	354.7	352.3	352.3	349.8	352.3	357.2	359.6
22.5°	318.0	320.5	320.5	320.5	318.0	315.6	310.7	308.2	308.2	310.7	310.7
25°	278.9	276.4	276.4	274.0	274.0	276.4	276.4	276.4	278.9	278.9	281.3
27.5°	256.9	254.4	254.4	252.0	252.0	254.4	254.4	254.4	254.4	254.4	254.4
30°	239.7	239.7	237.3	234.8	237.3	237.3	239.7	239.7	242.2	242.2	244.6
32.5°	227.5	225.1	225.1	222.6	225.1	225.1	227.5	227.5	230.0	232.4	232.4
35°	210.4	210.4	210.4	210.4	210.4	210.4	207.9	207.9	207.9	207.9	207.9
37.5°	200.6	200.6	198.2	195.7	195.7	195.7	195.7	195.7	193.3	190.8	188.4
40°	193.3	190.8	190.8	188.4	185.9	185.9	183.5	181.0	181.0	178.6	178.6
42.5°	183.5	181.0	181.0	178.6	176.1	176.1	173.7	171.2	171.2	171.2	168.8
45°	171.2	171.2	168.8	166.4	166.4	166.4	163.9	163.9	163.9	163.9	161.5
47.5°	159.0	159.0	156.6	156.6	156.6	156.6	154.1	154.1	154.1	154.1	154.1
50°	151.7	151.7	151.7	151.7	151.7	151.7	149.2	149.2	149.2	149.2	149.2
52.5°	144.3	144.3	144.3	144.3	144.3	144.3	144.3	144.3	144.3	144.3	144.3
55°	141.9	141.9	141.9	141.9	141.9	141.9	139.4	139.4	139.4	141.9	141.9
57.5°	137.0	137.0	134.5	134.5	134.5	134.5	134.5	134.5	134.5	134.5	134.5
60°	132.1	132.1	132.1	132.1	132.1	132.1	132.1	132.1	132.1	132.1	132.1
62.5°	124.8	124.8	124.8	124.8	124.8	127.2	127.2	127.2	127.2	127.2	124.8
65°	115.0	117.4	117.4	117.4	117.4	117.4	117.4	117.4	117.4	117.4	117.4
67.5°	110.1	110.1	110.1	110.1	110.1	110.1	110.1	110.1	110.1	110.1	110.1
70°	102.7	102.7	100.3	100.3	100.3	102.7	102.7	102.7	102.7	102.7	102.7
72.5°	93.0	93.0	93.0	93.0	93.0	93.0	93.0	93.0	93.0	95.4	95.4
75°	83.2	83.2	83.2	83.2	83.2	83.2	83.2	83.2	83.2	83.2	83.2
77.5°	73.4	73.4	70.9	70.9	70.9	73.4	73.4	73.4	73.4	75.8	75.8
80°	61.2	61.2	61.2	61.2	61.2	61.2	61.2	61.2	61.2	63.6	63.6
82.5°	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	51.4	51.4
85°	36.7	39.1	39.1	39.1	39.1	39.1	39.1	39.1	39.1	41.6	41.6
87.5°	24.5	24.5	24.5	24.5	24.5	24.5	22.0	22.0	22.0	22.0	19.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027
 CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4
2.5°	1558.3	1560.8	1563.2	1563.2	1565.7	1568.1	1568.1	1577.9	1587.7	1592.6	1597.5
5°	1333.3	1330.8	1330.8	1328.4	1325.9	1333.3	1340.6	1355.3	1370.0	1372.4	1377.3
7.5°	1044.6	1047.0	1049.5	1049.5	1051.9	1044.6	1034.8	1037.3	1039.7	1051.9	1061.7
10°	790.2	792.6	795.1	795.1	797.5	795.1	790.2	797.5	804.8	814.6	826.9
12.5°	614.0	621.4	628.7	633.6	640.9	645.8	648.3	658.1	665.4	677.6	689.9
15°	501.5	506.4	511.3	516.2	521.1	526.0	530.9	540.6	550.4	565.1	579.8
17.5°	423.2	423.2	425.7	425.7	425.7	430.6	435.4	440.3	442.8	457.5	472.1
20°	362.1	359.6	357.2	354.7	352.3	357.2	359.6	362.1	364.5	374.3	381.6
22.5°	310.7	310.7	313.1	313.1	313.1	310.7	305.8	308.2	308.2	313.1	320.5
25°	281.3	281.3	281.3	278.9	278.9	281.3	283.8	283.8	281.3	283.8	286.2
27.5°	254.4	256.9	256.9	259.3	259.3	261.8	261.8	261.8	261.8	264.2	266.7
30°	244.6	244.6	247.1	247.1	247.1	249.5	252.0	252.0	252.0	254.4	259.3
32.5°	234.8	237.3	239.7	242.2	244.6	247.1	247.1	249.5	249.5	252.0	254.4
35°	207.9	205.5	205.5	203.0	200.6	200.6	200.6	200.6	198.2	200.6	200.6
37.5°	185.9	185.9	185.9	183.5	183.5	185.9	185.9	185.9	185.9	188.4	188.4
40°	176.1	176.1	176.1	176.1	176.1	176.1	176.1	178.6	178.6	181.0	183.5
42.5°	168.8	168.8	168.8	168.8	168.8	171.2	171.2	171.2	171.2	173.7	173.7
45°	161.5	161.5	161.5	161.5	161.5	161.5	161.5	163.9	163.9	166.4	168.8
47.5°	154.1	154.1	154.1	154.1	154.1	156.6	159.0	159.0	159.0	161.5	161.5
50°	149.2	149.2	149.2	149.2	149.2	151.7	151.7	154.1	154.1	156.6	159.0
52.5°	144.3	144.3	144.3	144.3	144.3	146.8	146.8	149.2	149.2	151.7	154.1
55°	141.9	141.9	141.9	139.4	139.4	141.9	141.9	144.3	144.3	146.8	146.8
57.5°	134.5	134.5	134.5	134.5	134.5	134.5	134.5	137.0	137.0	139.4	141.9
60°	132.1	132.1	129.7	129.7	127.2	129.7	129.7	132.1	132.1	134.5	134.5
62.5°	124.8	124.8	124.8	122.3	122.3	124.8	124.8	124.8	124.8	127.2	129.7
65°	117.4	117.4	117.4	115.0	115.0	117.4	117.4	117.4	117.4	119.9	122.3
67.5°	110.1	110.1	110.1	107.6	107.6	107.6	107.6	110.1	110.1	112.5	115.0
70°	102.7	102.7	102.7	100.3	100.3	100.3	97.9	100.3	102.7	105.2	105.2
72.5°	95.4	95.4	95.4	93.0	93.0	93.0	90.5	93.0	93.0	95.4	95.4
75°	83.2	83.2	83.2	83.2	83.2	83.2	80.7	80.7	80.7	83.2	83.2
77.5°	75.8	75.8	75.8	73.4	73.4	73.4	70.9	70.9	70.9	73.4	73.4
80°	63.6	63.6	63.6	61.2	61.2	61.2	58.7	58.7	58.7	61.2	61.2
82.5°	51.4	51.4	51.4	48.9	48.9	48.9	46.5	46.5	46.5	48.9	48.9
85°	41.6	41.6	41.6	41.6	41.6	41.6	39.1	39.1	39.1	41.6	44.0
87.5°	19.6	19.6	22.0	22.0	22.0	22.0	19.6	19.6	17.1	17.1	19.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4
2.5°	1602.4	1607.2	1619.5	1629.3	1641.5	1651.3	1658.6	1668.4	1675.7	1683.1	1688.0
5°	1379.7	1382.2	1394.4	1406.6	1416.4	1428.7	1445.8	1462.9	1480.0	1497.2	1509.4
7.5°	1073.9	1083.7	1098.4	1115.5	1130.2	1144.9	1162.0	1181.6	1198.7	1215.8	1233.0
10°	836.6	846.4	861.1	875.8	888.0	902.7	922.3	941.8	961.4	981.0	1000.6
12.5°	702.1	714.3	731.5	748.6	763.3	780.4	804.8	826.9	851.3	873.3	897.8
15°	592.0	606.7	628.7	653.2	675.2	697.2	721.7	746.1	768.2	792.6	817.1
17.5°	486.8	501.5	521.1	543.1	562.7	582.2	611.6	638.5	667.9	694.8	721.7
20°	391.4	398.8	418.3	437.9	457.5	477.0	499.1	521.1	543.1	565.1	599.4
22.5°	325.4	330.3	340.0	347.4	357.2	364.5	386.5	408.5	428.1	450.1	481.9
25°	286.2	288.7	296.0	300.9	308.2	313.1	327.8	340.0	354.7	367.0	396.3
27.5°	266.7	269.1	271.5	274.0	276.4	278.9	288.7	298.5	305.8	315.6	342.5
30°	261.8	264.2	271.5	276.4	283.8	288.7	293.6	298.5	303.3	308.2	325.4
32.5°	256.9	259.3	259.3	256.9	256.9	254.4	259.3	261.8	266.7	269.1	283.8
35°	203.0	203.0	205.5	207.9	210.4	212.8	220.2	225.1	232.4	237.3	249.5
37.5°	190.8	190.8	193.3	198.2	200.6	203.0	207.9	212.8	217.7	222.6	234.8
40°	183.5	185.9	188.4	190.8	193.3	195.7	200.6	203.0	207.9	210.4	220.2
42.5°	176.1	176.1	178.6	183.5	185.9	188.4	193.3	195.7	200.6	203.0	212.8
45°	171.2	173.7	176.1	178.6	178.6	181.0	185.9	190.8	193.3	198.2	207.9
47.5°	163.9	163.9	168.8	171.2	176.1	178.6	183.5	185.9	190.8	193.3	203.0
50°	159.0	161.5	166.4	168.8	173.7	176.1	183.5	188.4	195.7	200.6	205.5
52.5°	154.1	156.6	161.5	163.9	168.8	171.2	181.0	190.8	198.2	207.9	207.9
55°	149.2	149.2	154.1	161.5	166.4	171.2	176.1	183.5	188.4	193.3	193.3
57.5°	141.9	144.3	149.2	156.6	161.5	166.4	171.2	176.1	178.6	183.5	181.0
60°	137.0	137.0	144.3	151.7	159.0	166.4	166.4	166.4	163.9	163.9	163.9
62.5°	129.7	132.1	141.9	154.1	163.9	173.7	166.4	159.0	151.7	144.3	146.8
65°	124.8	127.2	132.1	139.4	144.3	149.2	144.3	141.9	137.0	132.1	134.5
67.5°	115.0	117.4	119.9	119.9	122.3	122.3	122.3	122.3	122.3	122.3	124.8
70°	107.6	107.6	107.6	110.1	110.1	110.1	110.1	110.1	110.1	110.1	112.5
72.5°	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	100.3
75°	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6	88.1
77.5°	75.8	75.8	75.8	75.8	75.8	75.8	75.8	75.8	73.4	73.4	75.8
80°	63.6	63.6	63.6	63.6	61.2	61.2	61.2	61.2	61.2	61.2	63.6
82.5°	51.4	51.4	51.4	51.4	48.9	48.9	48.9	48.9	46.5	46.5	48.9
85°	46.5	48.9	48.9	51.4	51.4	51.4	48.9	46.5	44.0	41.6	41.6
87.5°	19.6	19.6	19.6	19.6	17.1	17.1	17.1	17.1	17.1	17.1	17.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4
2.5°	1695.3	1700.2	1705.1	1712.4	1722.2	1729.6	1736.9	1751.6	1768.7	1783.4	1798.1
5°	1521.6	1533.9	1546.1	1560.8	1575.4	1587.7	1602.4	1631.7	1661.1	1688.0	1717.3
7.5°	1247.6	1264.8	1279.4	1303.9	1325.9	1350.4	1372.4	1409.1	1443.3	1480.0	1514.3
10°	1020.1	1039.7	1059.3	1091.1	1125.3	1157.1	1188.9	1218.3	1250.1	1279.4	1308.8
12.5°	922.3	944.3	968.8	988.3	1010.3	1029.9	1049.5	1083.7	1118.0	1152.2	1186.5
15°	841.5	866.0	890.5	914.9	936.9	961.4	983.4	1012.8	1044.6	1073.9	1103.3
17.5°	748.6	773.0	800.0	826.9	853.8	880.7	907.6	949.2	990.8	1029.9	1071.5
20°	631.2	665.4	697.2	733.9	770.6	807.3	844.0	888.0	932.1	973.6	1017.7
22.5°	513.7	545.5	577.3	621.4	665.4	707.0	751.0	809.7	866.0	924.7	981.0
25°	428.1	457.5	486.8	535.7	582.2	631.2	677.6	748.6	817.1	888.0	956.5
27.5°	369.4	396.3	423.2	474.6	526.0	574.9	626.3	704.5	780.4	858.7	934.5
30°	342.5	359.6	376.7	425.7	474.6	521.1	570.0	645.8	721.7	797.5	873.3
32.5°	298.5	313.1	327.8	371.8	415.9	457.5	501.5	579.8	655.6	733.9	809.7
35°	264.2	276.4	288.7	330.3	369.4	411.0	450.1	528.4	606.7	685.0	763.3
37.5°	244.6	256.9	266.7	303.3	342.5	379.2	415.9	494.2	570.0	648.3	724.1
40°	230.0	237.3	247.1	283.8	318.0	354.7	389.0	459.9	533.3	604.2	675.2
42.5°	220.2	230.0	237.3	269.1	303.3	335.1	367.0	435.4	503.9	570.0	638.5
45°	217.7	227.5	237.3	264.2	291.1	315.6	342.5	408.5	474.6	540.6	606.7
47.5°	212.8	220.2	230.0	252.0	271.5	293.6	313.1	379.2	445.2	508.8	574.9
50°	210.4	212.8	217.7	237.3	256.9	276.4	296.0	362.1	428.1	494.2	560.2
52.5°	207.9	207.9	207.9	225.1	242.2	256.9	274.0	340.0	408.5	474.6	540.6
55°	193.3	190.8	190.8	207.9	222.6	239.7	254.4	320.5	386.5	450.1	516.2
57.5°	178.6	176.1	173.7	188.4	203.0	217.7	232.4	298.5	367.0	433.0	499.1
60°	163.9	161.5	161.5	176.1	188.4	203.0	215.3	283.8	349.8	418.3	484.4
62.5°	146.8	149.2	149.2	161.5	176.1	188.4	200.6	269.1	340.0	408.5	477.0
65°	134.5	137.0	137.0	151.7	166.4	181.0	195.7	261.8	330.3	396.3	462.4
67.5°	124.8	127.2	127.2	144.3	159.0	176.1	190.8	249.5	310.7	369.4	428.1
70°	115.0	115.0	117.4	134.5	151.7	168.8	185.9	237.3	288.7	337.6	389.0
72.5°	102.7	105.2	107.6	124.8	139.4	156.6	171.2	217.7	264.2	310.7	357.2
75°	90.5	93.0	95.4	110.1	124.8	139.4	154.1	198.2	239.7	283.8	325.4
77.5°	80.7	83.2	85.6	97.9	110.1	122.3	134.5	166.4	200.6	232.4	264.2
80°	66.1	66.1	68.5	78.3	88.1	95.4	105.2	127.2	149.2	168.8	190.8
82.5°	48.9	51.4	51.4	58.7	63.6	70.9	75.8	88.1	97.9	110.1	119.9
85°	41.6	39.1	39.1	44.0	46.5	51.4	53.8	61.2	66.1	73.4	78.3
87.5°	17.1	14.7	14.7	17.1	22.0	24.5	26.9	26.9	29.4	29.4	29.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4
2.5°	1805.4	1810.3	1817.6	1822.5	1834.8	1844.5	1856.8	1866.6	1873.9	1886.1	1881.2
5°	1739.4	1761.4	1783.4	1805.4	1822.5	1839.7	1854.3	1871.5	1891.0	1927.7	1937.5
7.5°	1543.6	1573.0	1599.9	1629.3	1663.5	1697.8	1732.0	1766.3	1798.1	1844.5	1873.9
10°	1350.4	1392.0	1431.1	1472.7	1504.5	1536.3	1565.7	1597.5	1641.5	1688.0	1741.8
12.5°	1228.1	1269.7	1311.2	1352.8	1399.3	1443.3	1489.8	1533.9	1575.4	1612.1	1673.3
15°	1147.3	1193.8	1237.9	1281.9	1338.2	1392.0	1448.2	1502.1	1563.2	1612.1	1653.7
17.5°	1127.8	1184.0	1237.9	1294.1	1352.8	1411.5	1470.3	1529.0	1590.1	1663.5	1717.3
20°	1093.5	1169.4	1245.2	1321.0	1396.9	1470.3	1546.1	1619.5	1700.2	1788.3	1812.7
22.5°	1073.9	1164.5	1257.4	1347.9	1450.7	1555.9	1658.6	1761.4	1847.0	1913.0	1986.4
25°	1071.5	1184.0	1299.0	1411.5	1541.2	1668.4	1798.1	1925.3	2035.4	2101.4	2160.1
27.5°	1069.1	1206.0	1340.6	1475.1	1634.2	1790.7	1949.7	2106.3	2209.0	2304.5	2353.4
30°	1039.7	1203.6	1370.0	1533.9	1712.4	1891.0	2069.6	2248.2	2353.4	2419.4	2443.9
32.5°	1003.0	1196.3	1389.5	1582.8	1785.8	1988.9	2189.5	2392.5	2475.7	2532.0	2512.4
35°	973.6	1186.5	1396.9	1607.2	1822.5	2040.3	2255.5	2470.8	2590.7	2669.0	2637.2
37.5°	946.7	1169.4	1392.0	1614.6	1866.6	2118.5	2370.5	2622.5	2737.5	2820.6	2783.9
40°	914.9	1152.2	1392.0	1629.3	1917.9	2204.2	2492.8	2779.0	2928.3	2999.2	2943.0
42.5°	888.0	1135.1	1384.6	1631.7	1940.0	2248.2	2556.4	2864.7	3031.0	3131.3	3060.4
45°	853.8	1100.9	1345.5	1592.6	1932.6	2272.7	2610.2	2950.3	3143.6	3221.8	3124.0
47.5°	817.1	1061.7	1303.9	1546.1	1908.1	2270.2	2632.3	2994.3	3172.9	3265.9	3175.4
50°	804.8	1049.5	1291.7	1536.3	1927.7	2321.6	2713.0	3104.4	3234.1	3309.9	3190.0
52.5°	802.4	1061.7	1323.5	1582.8	1976.6	2368.1	2761.9	3153.3	3258.5	3339.3	3231.6
55°	795.1	1076.4	1355.3	1634.2	2045.1	2458.6	2869.6	3280.5	3385.7	3444.5	3363.7
57.5°	802.4	1105.7	1406.6	1710.0	2133.2	2556.4	2979.6	3402.9	3530.1	3571.7	3554.5
60°	807.3	1130.2	1450.7	1773.6	2187.0	2600.5	3013.9	3427.3	3559.4	3662.2	3681.7
62.5°	795.1	1113.1	1428.7	1746.7	2121.0	2495.3	2869.6	3243.9	3461.6	3613.3	3701.3
65°	758.4	1051.9	1347.9	1641.5	1986.4	2333.8	2678.7	3023.7	3253.6	3478.7	3549.6
67.5°	677.6	927.2	1176.7	1426.2	1727.1	2028.0	2326.5	2627.4	2916.0	3133.8	3231.6
70°	587.1	782.8	981.0	1176.7	1450.7	1724.7	1998.7	2272.7	2527.1	2766.8	2859.8
72.5°	511.3	663.0	817.1	968.8	1164.5	1357.7	1553.4	1746.7	2047.6	2287.3	2377.8
75°	435.4	545.5	653.2	763.3	897.8	1032.4	1164.5	1299.0	1511.8	1727.1	1817.6
77.5°	335.1	408.5	479.5	550.4	643.4	733.9	826.9	917.4	1066.6	1228.1	1274.5
80°	232.4	274.0	313.1	354.7	428.1	501.5	574.9	648.3	746.1	836.6	907.6
82.5°	144.3	171.2	195.7	220.2	278.9	337.6	393.9	452.6	491.7	496.6	567.6
85°	93.0	110.1	124.8	139.4	173.7	210.4	244.6	278.9	249.5	232.4	276.4
87.5°	36.7	46.5	53.8	61.2	58.7	56.3	53.8	51.4	44.0	39.1	48.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4
2.5°	1886.1	1893.5	1900.8	1905.7	1913.0	1915.5	1917.9	1917.9	1920.4	1922.8	1927.7
5°	1976.6	1991.3	2006.0	2018.2	2032.9	2045.1	2054.9	2067.2	2076.9	2076.9	2074.5
7.5°	1900.8	1937.5	1974.2	2010.9	2047.6	2074.5	2099.0	2125.9	2150.3	2155.2	2160.1
10°	1800.5	1839.7	1876.3	1915.5	1952.2	1993.8	2032.9	2072.1	2113.6	2121.0	2130.8
12.5°	1707.5	1754.0	1800.5	1844.5	1891.0	1920.4	1949.7	1976.6	2006.0	2025.6	2045.1
15°	1705.1	1744.2	1783.4	1820.1	1859.2	1876.3	1893.5	1908.1	1925.3	1925.3	1927.7
17.5°	1761.4	1785.8	1810.3	1832.3	1856.8	1859.2	1864.1	1866.6	1869.0	1861.7	1854.3
20°	1871.5	1881.2	1891.0	1900.8	1910.6	1893.5	1878.8	1861.7	1844.5	1825.0	1807.8
22.5°	2032.9	2010.9	1988.9	1966.9	1944.8	1915.5	1883.7	1854.3	1822.5	1798.1	1773.6
25°	2184.6	2157.7	2130.8	2103.9	2076.9	2013.3	1949.7	1883.7	1820.1	1793.2	1766.3
27.5°	2387.6	2346.0	2304.5	2262.9	2221.3	2135.7	2050.0	1964.4	1878.8	1832.3	1788.3
30°	2436.6	2390.1	2343.6	2294.7	2248.2	2165.0	2084.3	2001.1	1917.9	1864.1	1812.7
32.5°	2507.5	2453.7	2399.9	2346.0	2292.2	2211.5	2130.8	2047.6	1966.9	1917.9	1866.6
35°	2624.9	2563.8	2502.6	2439.0	2377.8	2294.7	2213.9	2130.8	2047.6	1991.3	1937.5
37.5°	2725.2	2654.3	2583.3	2512.4	2441.5	2368.1	2292.2	2218.8	2143.0	2086.7	2032.9
40°	2837.8	2759.5	2681.2	2605.4	2527.1	2458.6	2390.1	2319.1	2250.6	2206.6	2162.6
42.5°	2935.6	2840.2	2747.2	2654.3	2558.9	2512.4	2468.4	2421.9	2375.4	2353.4	2328.9
45°	3004.1	2916.0	2825.5	2737.5	2649.4	2615.1	2580.9	2546.6	2512.4	2534.4	2556.4
47.5°	3033.5	2962.5	2894.0	2825.5	2754.6	2766.8	2779.0	2788.8	2801.1	2830.4	2862.2
50°	3060.4	3021.2	2979.6	2940.5	2898.9	2945.4	2989.4	3035.9	3082.4	3143.6	3204.7
52.5°	3114.2	3092.2	3072.6	3050.6	3028.6	3109.3	3190.0	3270.8	3351.5	3420.0	3488.5
55°	3275.7	3258.5	3241.4	3221.8	3204.7	3319.7	3432.2	3547.2	3662.2	3733.1	3804.1
57.5°	3498.3	3488.5	3476.3	3466.5	3454.2	3566.8	3676.9	3786.9	3899.5	3968.0	4038.9
60°	3667.1	3669.5	3669.5	3672.0	3672.0	3757.6	3843.2	3931.3	4016.9	4075.6	4136.8
62.5°	3757.6	3752.7	3747.8	3742.9	3738.0	3809.0	3879.9	3950.8	4021.8	4065.8	4109.9
65°	3659.7	3686.6	3713.6	3740.5	3767.4	3777.2	3784.5	3794.3	3801.6	3828.5	3855.4
67.5°	3331.9	3385.7	3437.1	3490.9	3542.3	3505.6	3471.4	3434.7	3398.0	3405.3	3410.2
70°	2967.4	3028.6	3092.2	3153.3	3214.5	3128.9	3043.3	2955.2	2869.6	2840.2	2810.8
72.5°	2502.6	2556.4	2612.7	2666.5	2720.3	2615.1	2512.4	2407.2	2302.0	2250.6	2199.3
75°	1913.0	1976.6	2042.7	2106.3	2169.9	2052.5	1932.6	1815.2	1695.3	1661.1	1629.3
77.5°	1394.4	1470.3	1546.1	1621.9	1697.8	1592.6	1487.4	1379.7	1274.5	1255.0	1235.4
80°	1015.2	1073.9	1130.2	1188.9	1245.2	1184.0	1122.9	1061.7	1000.6	998.1	995.7
82.5°	685.0	736.3	785.3	836.6	885.6	861.1	839.1	814.6	790.2	814.6	841.5
85°	352.3	423.2	496.6	567.6	638.5	631.2	626.3	618.9	611.6	643.4	672.7
87.5°	70.9	132.1	193.3	252.0	313.1	298.5	283.8	266.7	252.0	261.8	269.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4
2.5°	1930.2	1932.6	1932.6	1932.6	1932.6	1932.6	1927.7	1925.3	1920.4	1915.5	1908.1
5°	2074.5	2072.1	2062.3	2052.5	2040.3	2030.5	2023.1	2013.3	2006.0	1996.2	1981.5
7.5°	2165.0	2169.9	2152.8	2138.1	2121.0	2103.9	2086.7	2069.6	2052.5	2035.4	2001.1
10°	2138.1	2145.4	2135.7	2125.9	2113.6	2103.9	2084.3	2062.3	2042.7	2020.7	1979.1
12.5°	2062.3	2081.8	2076.9	2072.1	2067.2	2062.3	2050.0	2035.4	2023.1	2008.4	1962.0
15°	1927.7	1927.7	1930.2	1932.6	1932.6	1935.1	1937.5	1940.0	1942.4	1944.8	1917.9
17.5°	1847.0	1839.7	1839.7	1839.7	1839.7	1839.7	1849.4	1861.7	1871.5	1881.2	1873.9
20°	1788.3	1771.2	1768.7	1768.7	1766.3	1763.8	1780.9	1800.5	1817.6	1834.8	1844.5
22.5°	1749.1	1724.7	1722.2	1719.8	1717.3	1714.9	1736.9	1758.9	1780.9	1803.0	1837.2
25°	1739.4	1712.4	1714.9	1717.3	1717.3	1719.8	1736.9	1754.0	1771.2	1788.3	1847.0
27.5°	1741.8	1697.8	1700.2	1702.7	1702.7	1705.1	1732.0	1756.5	1783.4	1807.8	1881.2
30°	1758.9	1707.5	1702.7	1697.8	1692.9	1688.0	1724.7	1761.4	1798.1	1834.8	1891.0
32.5°	1817.6	1768.7	1756.5	1744.2	1732.0	1719.8	1763.8	1805.4	1849.4	1891.0	1937.5
35°	1881.2	1827.4	1822.5	1817.6	1810.3	1805.4	1844.5	1886.1	1925.3	1964.4	2006.0
37.5°	1976.6	1922.8	1917.9	1910.6	1905.7	1898.4	1942.4	1984.0	2028.0	2069.6	2106.3
40°	2118.5	2074.5	2072.1	2072.1	2069.6	2067.2	2101.4	2138.1	2172.4	2206.6	2231.1
42.5°	2306.9	2284.9	2292.2	2302.0	2309.3	2316.7	2343.6	2373.0	2399.9	2426.8	2419.4
45°	2578.4	2600.5	2602.9	2605.4	2607.8	2610.2	2617.6	2627.4	2634.7	2642.1	2612.7
47.5°	2891.6	2920.9	2935.6	2950.3	2962.5	2977.2	2967.4	2955.2	2945.4	2933.2	2859.8
50°	3263.4	3324.6	3322.1	3319.7	3314.8	3312.4	3292.8	3273.2	3251.2	3231.6	3124.0
52.5°	3557.0	3625.5	3637.7	3649.9	3662.2	3674.4	3637.7	3601.0	3561.9	3525.2	3390.6
55°	3872.6	3943.5	3946.0	3948.4	3948.4	3950.8	3899.5	3848.1	3794.3	3742.9	3603.5
57.5°	4107.4	4175.9	4168.6	4163.7	4156.3	4149.0	4087.8	4026.7	3965.5	3904.4	3764.9
60°	4195.5	4254.2	4239.5	4224.8	4207.7	4193.0	4146.6	4100.1	4051.1	4004.7	3870.1
62.5°	4153.9	4197.9	4175.9	4156.3	4134.3	4112.3	4053.6	3992.4	3933.7	3872.6	3774.7
65°	3879.9	3906.8	3877.5	3850.5	3823.6	3794.3	3745.4	3696.4	3645.1	3596.1	3530.1
67.5°	3417.5	3422.4	3420.0	3417.5	3415.1	3412.7	3341.7	3270.8	3197.4	3126.4	3121.5
70°	2783.9	2754.6	2759.5	2766.8	2771.7	2776.6	2722.8	2671.4	2617.6	2563.8	2588.2
72.5°	2147.9	2096.5	2108.7	2123.4	2135.7	2147.9	2103.9	2062.3	2018.2	1974.2	2008.4
75°	1595.0	1563.2	1575.4	1590.1	1602.4	1614.6	1597.5	1580.3	1560.8	1543.6	1575.4
77.5°	1215.8	1196.3	1198.7	1198.7	1201.2	1201.2	1203.6	1208.5	1210.9	1213.4	1247.6
80°	990.8	988.3	985.9	983.4	978.5	976.1	1000.6	1025.0	1049.5	1073.9	1091.1
82.5°	866.0	890.5	875.8	863.6	848.9	834.2	856.2	878.2	900.3	922.3	914.9
85°	704.5	733.9	707.0	680.1	650.7	623.8	643.4	660.5	680.1	697.2	687.4
87.5°	278.9	286.2	242.2	200.6	156.6	112.5	178.6	242.2	308.2	371.8	381.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4	1761.4
2.5°	1900.8	1891.0	1883.7	1881.2	1876.3	1873.9	1869.0	1864.1	1856.8	1851.9	1844.5
5°	1964.4	1949.7	1932.6	1908.1	1886.1	1861.7	1837.2	1815.2	1793.2	1768.7	1746.7
7.5°	1966.9	1932.6	1898.4	1866.6	1832.3	1800.5	1766.3	1736.9	1705.1	1673.3	1643.9
10°	1940.0	1898.4	1856.8	1815.2	1776.0	1734.5	1692.9	1658.6	1621.9	1585.2	1551.0
12.5°	1917.9	1871.5	1825.0	1776.0	1729.6	1680.6	1631.7	1597.5	1563.2	1529.0	1494.7
15°	1891.0	1861.7	1834.8	1790.7	1746.7	1702.7	1658.6	1612.1	1568.1	1521.6	1475.1
17.5°	1869.0	1861.7	1854.3	1825.0	1795.6	1763.8	1734.5	1688.0	1641.5	1592.6	1546.1
20°	1856.8	1866.6	1876.3	1861.7	1847.0	1829.9	1815.2	1780.9	1746.7	1710.0	1675.7
22.5°	1871.5	1908.1	1942.4	1944.8	1949.7	1952.2	1954.6	1922.8	1891.0	1856.8	1825.0
25°	1905.7	1964.4	2023.1	2054.9	2086.7	2121.0	2152.8	2133.2	2113.6	2094.1	2074.5
27.5°	1952.2	2025.6	2099.0	2145.4	2189.5	2236.0	2282.4	2280.0	2277.5	2272.7	2270.2
30°	1944.8	2001.1	2057.4	2113.6	2169.9	2226.2	2282.4	2311.8	2338.7	2368.1	2397.4
32.5°	1986.4	2032.9	2081.8	2140.6	2199.3	2260.4	2319.1	2380.3	2439.0	2500.2	2561.3
35°	2050.0	2091.6	2135.7	2199.3	2265.3	2328.9	2395.0	2468.4	2544.2	2620.0	2693.4
37.5°	2145.4	2182.1	2221.3	2275.1	2331.4	2385.2	2441.5	2549.1	2656.7	2766.8	2874.5
40°	2255.5	2280.0	2304.5	2355.8	2407.2	2458.6	2509.9	2644.5	2779.0	2913.6	3048.1
42.5°	2414.5	2407.2	2399.9	2441.5	2485.5	2527.1	2571.1	2693.4	2815.7	2938.1	3060.4
45°	2583.3	2554.0	2524.6	2544.2	2566.2	2585.8	2607.8	2732.6	2857.3	2984.5	3109.3
47.5°	2786.4	2713.0	2639.6	2622.5	2605.4	2585.8	2568.7	2703.2	2837.8	2974.8	3109.3
50°	3016.3	2906.3	2798.6	2754.6	2708.1	2664.1	2617.6	2727.7	2840.2	2952.7	3062.8
52.5°	3256.1	3119.1	2984.5	2916.0	2847.5	2776.6	2708.1	2801.1	2896.5	2991.9	3084.8
55°	3461.6	3322.1	3180.2	3099.5	3018.8	2938.1	2857.3	2950.3	3043.3	3136.2	3229.2
57.5°	3625.5	3486.0	3346.6	3270.8	3192.5	3116.6	3038.4	3126.4	3216.9	3307.5	3395.5
60°	3738.0	3603.5	3468.9	3395.5	3322.1	3248.7	3175.4	3280.5	3385.7	3493.4	3598.6
62.5°	3679.3	3581.4	3483.6	3451.8	3420.0	3385.7	3353.9	3454.2	3552.1	3652.4	3752.7
65°	3464.0	3398.0	3331.9	3363.7	3398.0	3429.8	3464.0	3530.1	3596.1	3664.6	3730.7
67.5°	3114.2	3109.3	3102.0	3172.9	3243.9	3317.2	3388.2	3432.2	3473.8	3517.8	3561.9
70°	2612.7	2639.6	2664.1	2786.4	2908.7	3031.0	3153.3	3170.5	3187.6	3204.7	3221.8
72.5°	2045.1	2079.4	2116.1	2277.5	2436.6	2598.0	2759.5	2749.7	2739.9	2727.7	2717.9
75°	1609.7	1641.5	1675.7	1825.0	1974.2	2123.4	2272.7	2231.1	2191.9	2150.3	2108.7
77.5°	1284.3	1318.6	1355.3	1494.7	1634.2	1776.0	1915.5	1815.2	1714.9	1614.6	1514.3
80°	1105.7	1122.9	1137.6	1233.0	1325.9	1421.3	1516.7	1414.0	1308.8	1203.6	1100.9
82.5°	907.6	897.8	890.5	946.7	1003.0	1059.3	1115.5	1017.7	919.8	819.5	721.7
85°	677.6	667.9	658.1	687.4	716.8	748.6	777.9	665.4	552.9	437.9	325.4
87.5°	393.9	403.6	413.4	445.2	477.0	511.3	543.1	428.1	313.1	195.7	80.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676027
 CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1761.4	1761.4
2.5°	1829.9	1817.6
5°	1729.6	1712.4
7.5°	1619.5	1597.5
10°	1519.2	1489.8
12.5°	1455.6	1418.9
15°	1431.1	1387.1
17.5°	1504.5	1462.9
20°	1617.0	1560.8
22.5°	1754.0	1685.5
25°	1991.3	1908.1
27.5°	2184.6	2099.0
30°	2304.5	2211.5
32.5°	2436.6	2314.2
35°	2573.6	2456.1
37.5°	2739.9	2607.8
40°	2911.1	2774.2
42.5°	2969.9	2881.8
45°	3026.1	2943.0
47.5°	3038.4	2969.9
50°	3050.6	3040.8
52.5°	3084.8	3082.4
55°	3231.6	3234.1
57.5°	3412.7	3427.3
60°	3579.0	3561.9
62.5°	3664.6	3576.6
65°	3605.9	3483.6
67.5°	3429.8	3297.7
70°	3043.3	2864.7
72.5°	2561.3	2404.8
75°	1974.2	1842.1
77.5°	1404.2	1294.1
80°	988.3	878.2
82.5°	633.6	545.5
85°	286.2	249.5
87.5°	80.7	78.3
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P676027

CATALOG NUMBER: CCW-SA-2C-827-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)