

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P676049

Luminaire Tested: **CCW-SA-2C-835-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P676049
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2C-835-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @615mA w/
SLR distribution lens
Light Source: (32) 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6182.7 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
- - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 8.8 fc
Type IV - Short - N/A

REPORT NUMBER: P676049
CATALOG NUMBER: CCW-SA-2C-835-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1272.1	0.0	1272.1
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	4910.6	0.0	4910.6
	% Fixture	79.4	0.0	79.4
Total	Lumens	6182.7	0.0	6182.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	2.5
10°-20°	323.9	5.2
20°-30°	473.9	7.7
30°-40°	667.6	10.8
40°-50°	917.4	14.8
50°-60°	1250.5	20.2
60°-70°	1368.6	22.1
70°-80°	790.4	12.8
80°-90°	236.9	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6182.7	100.0
0°-180°	6182.7	100.0

Coefficient of Utilization



REPORT NUMBER: P676049


CATALOG NUMBER: CCW-SA-2C-835-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	635.0	10.3			
FM	(30°-60°)	2256.3	36.5			
FH	(60°-80°)	1818.1	29.4			G2/5000
FVH	(80°-90°)	201.2	3.3			G2/225
BL	(0°-30°)	316.3	5.1	B1/500		
BM	(30°-60°)	579.3	9.4	B1/1000		
BH	(60°-80°)	340.9	5.5	B1/500		G1/500
BVH	(80°-90°)	35.7	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	2037.5	2026.5	2018.3	2010.0	1999.1	1990.8	1979.9	1968.9	1955.2	1944.2	1930.5
5°	1919.5	1886.6	1853.7	1834.5	1812.6	1793.4	1771.5	1746.8	1722.1	1694.7	1670.0
7.5°	1790.7	1749.5	1708.4	1675.5	1639.8	1606.9	1571.3	1541.1	1510.9	1480.8	1450.6
10°	1670.0	1631.6	1593.2	1552.1	1508.2	1467.1	1423.2	1382.1	1340.9	1299.8	1258.7
12.5°	1590.5	1543.9	1500.0	1453.4	1409.5	1362.9	1316.3	1277.9	1239.5	1198.3	1159.9
15°	1554.8	1510.9	1469.8	1423.2	1376.6	1330.0	1283.3	1239.5	1198.3	1154.5	1110.6
17.5°	1639.8	1576.8	1513.7	1453.4	1393.0	1332.7	1272.4	1217.5	1162.7	1107.8	1053.0
20°	1749.5	1670.0	1593.2	1519.2	1442.4	1368.4	1291.6	1214.8	1138.0	1061.2	984.4
22.5°	1889.4	1798.9	1711.1	1615.2	1516.4	1420.5	1321.7	1225.8	1129.8	1031.1	935.1
25°	2138.9	2032.0	1925.0	1787.9	1648.1	1510.9	1371.1	1245.0	1121.6	995.4	869.3
27.5°	2352.8	2207.5	2064.9	1900.3	1735.8	1571.3	1406.7	1261.4	1118.8	973.5	828.1
30°	2478.9	2336.4	2193.8	1993.6	1796.1	1596.0	1395.8	1234.0	1074.9	913.2	751.4
32.5°	2594.1	2435.1	2276.0	2056.6	1834.5	1615.2	1393.0	1214.8	1039.3	861.0	682.8
35°	2753.2	2577.7	2404.9	2149.9	1894.9	1639.8	1384.8	1201.1	1014.6	830.9	644.4
37.5°	2923.2	2706.5	2492.7	2210.2	1927.8	1645.3	1362.9	1181.9	1000.9	819.9	638.9
40°	3109.6	2846.4	2585.9	2273.3	1963.4	1650.8	1338.2	1157.2	976.2	792.5	611.5
42.5°	3230.3	2945.1	2659.9	2322.6	1988.1	1650.8	1313.5	1135.3	957.0	776.0	597.8
45°	3298.9	3021.9	2747.7	2383.0	2018.3	1653.5	1288.8	1113.3	937.8	759.6	584.1
47.5°	3329.0	3071.3	2813.5	2429.6	2048.4	1664.5	1280.6	1102.4	921.4	743.1	562.2
50°	3408.5	3180.9	2953.3	2542.0	2133.4	1722.1	1310.8	1118.8	929.6	737.7	545.7
52.5°	3455.2	3260.5	3065.8	2643.5	2221.2	1798.9	1376.6	1162.7	948.8	734.9	521.0
55°	3625.2	3438.7	3252.2	2802.5	2350.1	1900.3	1447.9	1212.1	976.2	737.7	501.8
57.5°	3841.8	3644.4	3449.7	2964.3	2478.9	1993.6	1508.2	1255.9	1000.9	748.6	493.6
60°	3992.6	3800.7	3611.5	3095.9	2577.7	2062.1	1543.9	1280.6	1017.4	751.4	488.1
62.5°	4009.1	3762.3	3518.2	3016.4	2514.6	2010.0	1508.2	1253.2	998.2	740.4	485.4
65°	3904.9	3617.0	3329.0	2849.1	2369.3	1889.4	1409.5	1176.4	943.3	707.5	474.4
67.5°	3696.5	3359.2	3021.9	2583.1	2144.4	1705.6	1266.9	1066.7	869.3	669.1	468.9
70°	3211.1	2915.0	2621.5	2240.4	1862.0	1480.8	1099.6	935.1	773.3	608.8	444.2
72.5°	2695.6	2418.6	2144.4	1834.5	1527.4	1217.5	907.7	784.3	660.9	534.7	411.3
75°	2064.9	1856.5	1650.8	1420.5	1190.1	957.0	726.7	636.2	545.7	455.2	364.7
77.5°	1450.6	1338.2	1228.5	1055.7	883.0	710.2	537.5	477.1	416.8	356.5	296.2
80°	984.4	921.4	861.0	737.7	614.3	488.1	364.7	326.3	285.2	246.8	205.7
82.5°	611.5	608.8	603.3	518.3	433.3	348.3	263.3	230.3	200.2	167.3	134.4
85°	279.7	326.3	370.2	323.6	277.0	230.3	183.7	161.8	139.9	115.2	93.2
87.5°	87.8	106.9	123.4	117.9	109.7	104.2	96.0	82.3	68.6	54.8	41.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049
 CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	1919.5	1911.3	1900.3	1889.4	1875.7	1864.7	1851.0	1837.3	1834.5	1829.0	1826.3
5°	1653.5	1637.1	1617.9	1601.4	1585.0	1565.8	1549.3	1530.1	1516.4	1500.0	1486.3
7.5°	1420.5	1393.0	1362.9	1332.7	1305.3	1277.9	1247.7	1220.3	1206.6	1192.9	1179.1
10°	1234.0	1206.6	1181.9	1154.5	1135.3	1118.8	1099.6	1080.4	1064.0	1047.5	1031.1
12.5°	1140.8	1121.6	1102.4	1083.2	1061.2	1042.0	1020.1	998.2	979.0	962.5	943.3
15°	1083.2	1055.7	1025.6	998.2	968.0	940.6	910.4	880.2	858.3	839.1	817.2
17.5°	1014.6	973.5	935.1	894.0	861.0	828.1	792.5	759.6	734.9	707.5	682.8
20°	937.8	891.2	841.9	795.2	756.8	721.2	682.8	644.4	617.0	586.8	559.4
22.5°	872.0	811.7	748.6	685.5	644.4	603.3	559.4	518.3	493.6	466.2	441.5
25°	800.7	734.9	666.4	597.8	556.7	512.8	471.7	427.8	408.6	392.1	372.9
27.5°	762.3	696.5	628.0	562.2	523.8	482.6	444.2	403.1	389.4	372.9	359.2
30°	685.5	622.5	556.7	490.9	463.4	438.8	411.3	383.9	378.4	375.7	370.2
32.5°	617.0	551.2	485.4	419.6	394.9	370.2	345.5	320.8	318.1	312.6	309.9
35°	581.3	518.3	452.5	389.4	367.5	342.8	320.8	296.2	290.7	282.4	277.0
37.5°	573.1	507.3	438.8	372.9	351.0	329.1	304.4	282.4	277.0	271.5	266.0
40°	551.2	488.1	427.8	364.7	342.8	320.8	296.2	274.2	268.7	263.3	257.8
42.5°	534.7	474.4	411.3	348.3	329.1	309.9	287.9	268.7	263.3	257.8	249.5
45°	521.0	457.9	392.1	329.1	315.4	301.6	285.2	271.5	266.0	257.8	252.3
47.5°	499.1	438.8	375.7	312.6	298.9	287.9	274.2	260.5	255.0	249.5	244.1
50°	482.6	419.6	356.5	293.4	282.4	271.5	260.5	249.5	249.5	252.3	252.3
52.5°	460.7	400.4	340.0	279.7	268.7	257.8	246.8	235.8	238.6	241.3	244.1
55°	441.5	383.9	323.6	263.3	252.3	241.3	227.6	216.6	219.4	222.1	224.9
57.5°	433.3	372.9	312.6	252.3	241.3	227.6	216.6	202.9	202.9	202.9	202.9
60°	427.8	364.7	304.4	241.3	227.6	216.6	202.9	189.2	186.5	186.5	183.7
62.5°	425.0	362.0	301.6	238.6	222.1	208.4	192.0	175.5	172.8	170.0	167.3
65°	414.1	356.5	296.2	235.8	216.6	200.2	181.0	161.8	159.0	159.0	156.3
67.5°	411.3	351.0	293.4	233.1	213.9	192.0	172.8	150.8	148.1	145.3	142.6
70°	389.4	337.3	282.4	227.6	205.7	186.5	164.5	142.6	139.9	134.4	131.6
72.5°	362.0	315.4	266.0	216.6	194.7	172.8	150.8	128.9	126.1	123.4	117.9
75°	320.8	277.0	233.1	189.2	170.0	153.6	134.4	115.2	112.4	109.7	104.2
77.5°	263.3	227.6	194.7	159.0	145.3	131.6	117.9	104.2	101.5	98.7	93.2
80°	186.5	164.5	145.3	123.4	115.2	104.2	96.0	85.0	85.0	82.3	82.3
82.5°	123.4	112.4	101.5	90.5	85.0	79.5	74.0	68.6	68.6	65.8	65.8
85°	87.8	82.3	74.0	68.6	65.8	60.3	57.6	52.1	52.1	52.1	52.1
87.5°	41.1	41.1	38.4	38.4	35.6	35.6	32.9	30.2	30.2	30.2	30.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	1820.8	1812.6	1804.4	1793.4	1785.2	1774.2	1760.5	1749.5	1735.8	1735.8	1733.1
5°	1469.8	1461.6	1453.4	1442.4	1434.2	1423.2	1415.0	1404.0	1393.0	1393.0	1390.3
7.5°	1165.4	1149.0	1132.5	1113.3	1096.9	1085.9	1074.9	1061.2	1050.3	1042.0	1033.8
10°	1014.6	998.2	979.0	962.5	943.3	929.6	915.9	899.4	885.7	874.8	863.8
12.5°	924.1	904.9	885.7	866.5	847.3	828.1	811.7	792.5	773.3	759.6	745.9
15°	795.2	776.0	756.8	737.7	718.5	696.5	674.6	649.9	628.0	617.0	608.8
17.5°	655.4	636.2	614.3	595.1	573.1	556.7	540.2	523.8	507.3	496.3	488.1
20°	529.2	507.3	485.4	463.4	441.5	430.5	419.6	408.6	397.6	389.4	383.9
22.5°	414.1	400.4	389.4	375.7	362.0	353.7	348.3	340.0	331.8	331.8	331.8
25°	353.7	345.5	340.0	331.8	323.6	320.8	318.1	312.6	309.9	307.1	307.1
27.5°	342.8	334.5	326.3	318.1	309.9	307.1	304.4	298.9	296.2	296.2	296.2
30°	364.7	362.0	359.2	356.5	353.7	348.3	340.0	334.5	326.3	320.8	315.4
32.5°	304.4	301.6	301.6	298.9	296.2	301.6	304.4	309.9	312.6	315.4	318.1
35°	268.7	263.3	257.8	252.3	246.8	244.1	241.3	238.6	235.8	235.8	233.1
37.5°	260.5	255.0	249.5	244.1	238.6	235.8	233.1	230.3	227.6	227.6	224.9
40°	252.3	246.8	244.1	238.6	233.1	230.3	227.6	222.1	219.4	216.6	216.6
42.5°	244.1	241.3	235.8	233.1	227.6	224.9	222.1	216.6	213.9	211.1	208.4
45°	244.1	238.6	233.1	227.6	222.1	219.4	213.9	211.1	205.7	205.7	202.9
47.5°	238.6	233.1	227.6	222.1	216.6	213.9	208.4	205.7	200.2	197.4	194.7
50°	252.3	244.1	233.1	224.9	213.9	211.1	205.7	202.9	197.4	194.7	192.0
52.5°	246.8	238.6	227.6	219.4	208.4	202.9	200.2	194.7	189.2	186.5	183.7
55°	227.6	219.4	213.9	205.7	197.4	192.0	186.5	181.0	175.5	172.8	172.8
57.5°	202.9	200.2	197.4	194.7	192.0	186.5	181.0	172.8	167.3	164.5	161.8
60°	181.0	183.7	186.5	189.2	192.0	183.7	175.5	167.3	159.0	156.3	153.6
62.5°	164.5	170.0	175.5	178.2	183.7	175.5	167.3	159.0	150.8	148.1	145.3
65°	153.6	156.3	156.3	159.0	159.0	153.6	150.8	145.3	139.9	137.1	137.1
67.5°	139.9	139.9	139.9	137.1	137.1	134.4	134.4	131.6	128.9	126.1	126.1
70°	126.1	126.1	126.1	123.4	123.4	120.7	120.7	117.9	115.2	115.2	112.4
72.5°	115.2	115.2	112.4	112.4	109.7	109.7	109.7	106.9	106.9	104.2	104.2
75°	101.5	101.5	98.7	98.7	96.0	96.0	96.0	93.2	93.2	93.2	90.5
77.5°	90.5	90.5	87.8	87.8	85.0	85.0	85.0	82.3	82.3	79.5	79.5
80°	79.5	79.5	76.8	76.8	74.0	74.0	71.3	71.3	68.6	68.6	65.8
82.5°	63.1	63.1	63.1	63.1	63.1	60.3	60.3	57.6	54.8	54.8	52.1
85°	52.1	52.1	52.1	49.4	49.4	49.4	46.6	46.6	43.9	41.1	41.1
87.5°	30.2	30.2	30.2	27.4	27.4	27.4	27.4	27.4	27.4	27.4	24.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	1733.1	1730.3	1719.4	1708.4	1719.4	1730.3	1730.3	1730.3	1727.6	1727.6	1727.6
5°	1390.3	1387.6	1382.1	1376.6	1376.6	1373.8	1379.3	1384.8	1390.3	1395.8	1401.3
7.5°	1022.8	1014.6	1006.4	998.2	1003.6	1006.4	1014.6	1020.1	1028.3	1033.8	1047.5
10°	852.8	841.9	833.6	825.4	819.9	814.4	808.9	806.2	800.7	795.2	800.7
12.5°	729.4	715.7	702.0	685.5	682.8	680.1	674.6	669.1	663.6	658.1	655.4
15°	597.8	586.8	581.3	573.1	562.2	551.2	545.7	543.0	537.5	532.0	529.2
17.5°	477.1	466.2	457.9	449.7	447.0	441.5	441.5	441.5	441.5	441.5	441.5
20°	375.7	367.5	367.5	364.7	364.7	362.0	364.7	367.5	367.5	370.2	372.9
22.5°	329.1	329.1	326.3	323.6	326.3	326.3	329.1	331.8	334.5	337.3	340.0
25°	304.4	301.6	304.4	307.1	307.1	307.1	309.9	309.9	312.6	312.6	312.6
27.5°	293.4	293.4	296.2	296.2	298.9	298.9	298.9	296.2	296.2	293.4	293.4
30°	309.9	304.4	304.4	304.4	301.6	298.9	296.2	296.2	293.4	290.7	287.9
32.5°	320.8	323.6	320.8	315.4	312.6	307.1	304.4	298.9	296.2	290.7	285.2
35°	233.1	230.3	235.8	238.6	241.3	244.1	246.8	249.5	249.5	252.3	252.3
37.5°	224.9	222.1	222.1	219.4	219.4	219.4	219.4	219.4	216.6	216.6	219.4
40°	213.9	211.1	211.1	208.4	208.4	205.7	205.7	205.7	205.7	205.7	205.7
42.5°	205.7	202.9	202.9	202.9	202.9	200.2	200.2	197.4	197.4	194.7	194.7
45°	202.9	200.2	197.4	194.7	194.7	192.0	192.0	192.0	189.2	189.2	189.2
47.5°	192.0	189.2	189.2	186.5	186.5	183.7	183.7	183.7	181.0	181.0	181.0
50°	186.5	183.7	183.7	181.0	181.0	178.2	178.2	178.2	175.5	175.5	175.5
52.5°	178.2	175.5	175.5	175.5	172.8	170.0	170.0	170.0	167.3	167.3	167.3
55°	170.0	167.3	167.3	167.3	164.5	161.8	161.8	161.8	159.0	159.0	159.0
57.5°	159.0	156.3	156.3	153.6	153.6	153.6	153.6	153.6	150.8	150.8	150.8
60°	150.8	148.1	148.1	145.3	145.3	142.6	142.6	142.6	142.6	142.6	142.6
62.5°	142.6	139.9	137.1	134.4	137.1	137.1	137.1	137.1	134.4	134.4	134.4
65°	134.4	131.6	128.9	126.1	126.1	126.1	126.1	126.1	126.1	126.1	126.1
67.5°	123.4	120.7	117.9	115.2	117.9	117.9	117.9	117.9	117.9	117.9	117.9
70°	112.4	109.7	109.7	106.9	106.9	104.2	104.2	106.9	106.9	106.9	106.9
72.5°	101.5	98.7	98.7	96.0	96.0	96.0	96.0	96.0	96.0	96.0	96.0
75°	90.5	87.8	87.8	85.0	85.0	85.0	85.0	85.0	85.0	85.0	85.0
77.5°	76.8	74.0	74.0	74.0	74.0	74.0	74.0	76.8	76.8	76.8	76.8
80°	65.8	63.1	63.1	63.1	63.1	63.1	63.1	63.1	63.1	63.1	63.1
82.5°	52.1	49.4	49.4	49.4	49.4	49.4	49.4	49.4	49.4	49.4	49.4
85°	38.4	35.6	35.6	35.6	38.4	38.4	38.4	38.4	38.4	38.4	38.4
87.5°	24.7	21.9	21.9	21.9	24.7	24.7	24.7	24.7	21.9	21.9	21.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	1727.6	1727.6	1727.6	1724.8	1722.1	1719.4	1716.6	1724.8	1730.3	1738.6	1744.0
5°	1404.0	1409.5	1412.2	1420.5	1428.7	1436.9	1445.1	1450.6	1456.1	1458.8	1464.3
7.5°	1058.5	1072.2	1083.2	1094.1	1105.1	1113.3	1124.3	1132.5	1140.8	1149.0	1157.2
10°	803.5	808.9	811.7	822.7	830.9	841.9	850.1	858.3	866.5	872.0	880.2
12.5°	652.6	647.2	644.4	644.4	644.4	644.4	644.4	649.9	655.4	660.9	666.4
15°	526.5	523.8	521.0	518.3	515.5	510.0	507.3	512.8	518.3	523.8	529.2
17.5°	441.5	441.5	441.5	438.8	436.0	433.3	430.5	433.3	436.0	436.0	438.8
20°	378.4	381.2	383.9	386.6	386.6	389.4	389.4	392.1	394.9	394.9	397.6
22.5°	340.0	342.8	342.8	342.8	345.5	345.5	345.5	348.3	351.0	353.7	356.5
25°	309.9	309.9	307.1	307.1	309.9	309.9	309.9	309.9	312.6	312.6	312.6
27.5°	293.4	290.7	290.7	290.7	290.7	287.9	287.9	287.9	287.9	287.9	287.9
30°	285.2	282.4	279.7	277.0	277.0	274.2	271.5	271.5	271.5	271.5	271.5
32.5°	282.4	277.0	271.5	268.7	268.7	266.0	263.3	260.5	260.5	257.8	255.0
35°	252.3	249.5	249.5	246.8	244.1	241.3	238.6	238.6	238.6	235.8	235.8
37.5°	219.4	222.1	222.1	222.1	224.9	224.9	224.9	224.9	227.6	227.6	227.6
40°	205.7	205.7	205.7	208.4	211.1	211.1	213.9	213.9	216.6	216.6	216.6
42.5°	194.7	192.0	192.0	194.7	194.7	197.4	197.4	200.2	202.9	202.9	205.7
45°	189.2	186.5	186.5	186.5	186.5	183.7	183.7	186.5	189.2	192.0	194.7
47.5°	178.2	178.2	175.5	175.5	175.5	175.5	175.5	175.5	178.2	178.2	178.2
50°	172.8	172.8	170.0	170.0	170.0	170.0	170.0	170.0	170.0	170.0	170.0
52.5°	167.3	164.5	164.5	164.5	164.5	161.8	161.8	161.8	161.8	161.8	161.8
55°	159.0	156.3	156.3	156.3	156.3	156.3	156.3	156.3	159.0	159.0	159.0
57.5°	150.8	148.1	148.1	148.1	150.8	150.8	150.8	150.8	153.6	153.6	153.6
60°	142.6	142.6	142.6	142.6	142.6	142.6	142.6	145.3	145.3	148.1	148.1
62.5°	134.4	134.4	134.4	134.4	137.1	137.1	137.1	137.1	139.9	139.9	139.9
65°	126.1	126.1	126.1	126.1	128.9	128.9	128.9	128.9	128.9	128.9	128.9
67.5°	117.9	117.9	117.9	117.9	117.9	117.9	117.9	120.7	120.7	123.4	123.4
70°	106.9	104.2	104.2	106.9	106.9	109.7	109.7	112.4	112.4	115.2	115.2
72.5°	96.0	96.0	96.0	96.0	96.0	96.0	96.0	98.7	101.5	101.5	104.2
75°	85.0	85.0	85.0	85.0	87.8	87.8	87.8	90.5	90.5	93.2	93.2
77.5°	76.8	74.0	74.0	74.0	76.8	76.8	76.8	79.5	79.5	82.3	82.3
80°	63.1	63.1	63.1	63.1	65.8	65.8	65.8	65.8	68.6	68.6	68.6
82.5°	52.1	52.1	52.1	52.1	52.1	52.1	52.1	52.1	54.8	54.8	54.8
85°	38.4	38.4	38.4	38.4	41.1	41.1	41.1	41.1	41.1	41.1	41.1
87.5°	24.7	24.7	24.7	24.7	24.7	24.7	24.7	24.7	27.4	27.4	27.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049
 CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	1744.0	1744.0	1744.0	1744.0	1749.5	1752.3	1757.7	1760.5	1757.7	1755.0	1749.5
5°	1467.1	1469.8	1469.8	1472.6	1472.6	1472.6	1472.6	1472.6	1478.0	1483.5	1489.0
7.5°	1159.9	1162.7	1165.4	1168.2	1168.2	1168.2	1165.4	1165.4	1168.2	1168.2	1170.9
10°	888.5	899.4	907.7	915.9	910.4	902.2	896.7	888.5	888.5	888.5	885.7
12.5°	671.8	674.6	680.1	682.8	680.1	680.1	677.3	674.6	677.3	682.8	685.5
15°	532.0	532.0	534.7	534.7	537.5	540.2	540.2	543.0	548.4	551.2	556.7
17.5°	441.5	444.2	444.2	447.0	447.0	449.7	449.7	449.7	455.2	460.7	468.9
20°	397.6	397.6	397.6	397.6	397.6	394.9	394.9	392.1	394.9	400.4	403.1
22.5°	356.5	359.2	359.2	359.2	356.5	353.7	348.3	345.5	345.5	348.3	348.3
25°	312.6	309.9	309.9	307.1	307.1	309.9	309.9	309.9	312.6	312.6	315.4
27.5°	287.9	285.2	285.2	282.4	282.4	285.2	285.2	285.2	285.2	285.2	285.2
30°	268.7	268.7	266.0	263.3	266.0	266.0	268.7	268.7	271.5	271.5	274.2
32.5°	255.0	252.3	252.3	249.5	252.3	252.3	255.0	255.0	257.8	260.5	260.5
35°	235.8	235.8	235.8	235.8	235.8	235.8	233.1	233.1	233.1	233.1	233.1
37.5°	224.9	224.9	222.1	219.4	219.4	219.4	219.4	219.4	216.6	213.9	211.1
40°	216.6	213.9	213.9	211.1	208.4	208.4	205.7	202.9	202.9	200.2	200.2
42.5°	205.7	202.9	202.9	200.2	197.4	197.4	194.7	192.0	192.0	192.0	189.2
45°	192.0	192.0	189.2	186.5	186.5	186.5	183.7	183.7	183.7	183.7	181.0
47.5°	178.2	178.2	175.5	175.5	175.5	175.5	172.8	172.8	172.8	172.8	172.8
50°	170.0	170.0	170.0	170.0	170.0	170.0	167.3	167.3	167.3	167.3	167.3
52.5°	161.8	161.8	161.8	161.8	161.8	161.8	161.8	161.8	161.8	161.8	161.8
55°	159.0	159.0	159.0	159.0	159.0	159.0	156.3	156.3	156.3	159.0	159.0
57.5°	153.6	153.6	150.8	150.8	150.8	150.8	150.8	150.8	150.8	150.8	150.8
60°	148.1	148.1	148.1	148.1	148.1	148.1	148.1	148.1	148.1	148.1	148.1
62.5°	139.9	139.9	139.9	139.9	139.9	142.6	142.6	142.6	142.6	142.6	139.9
65°	128.9	131.6	131.6	131.6	131.6	131.6	131.6	131.6	131.6	131.6	131.6
67.5°	123.4	123.4	123.4	123.4	123.4	123.4	123.4	123.4	123.4	123.4	123.4
70°	115.2	115.2	112.4	112.4	112.4	115.2	115.2	115.2	115.2	115.2	115.2
72.5°	104.2	104.2	104.2	104.2	104.2	104.2	104.2	104.2	104.2	106.9	106.9
75°	93.2	93.2	93.2	93.2	93.2	93.2	93.2	93.2	93.2	93.2	93.2
77.5°	82.3	82.3	79.5	79.5	79.5	82.3	82.3	82.3	82.3	85.0	85.0
80°	68.6	68.6	68.6	68.6	68.6	68.6	68.6	68.6	68.6	71.3	71.3
82.5°	54.8	54.8	54.8	54.8	54.8	54.8	54.8	54.8	54.8	57.6	57.6
85°	41.1	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9	46.6	46.6
87.5°	27.4	27.4	27.4	27.4	27.4	27.4	24.7	24.7	24.7	24.7	21.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	1746.8	1749.5	1752.3	1752.3	1755.0	1757.7	1757.7	1768.7	1779.7	1785.2	1790.7
5°	1494.5	1491.8	1491.8	1489.0	1486.3	1494.5	1502.7	1519.2	1535.6	1538.4	1543.9
7.5°	1170.9	1173.7	1176.4	1176.4	1179.1	1170.9	1159.9	1162.7	1165.4	1179.1	1190.1
10°	885.7	888.5	891.2	891.2	894.0	891.2	885.7	894.0	902.2	913.2	926.9
12.5°	688.3	696.5	704.7	710.2	718.5	723.9	726.7	737.7	745.9	759.6	773.3
15°	562.2	567.6	573.1	578.6	584.1	589.6	595.1	606.0	617.0	633.4	649.9
17.5°	474.4	474.4	477.1	477.1	477.1	482.6	488.1	493.6	496.3	512.8	529.2
20°	405.8	403.1	400.4	397.6	394.9	400.4	403.1	405.8	408.6	419.6	427.8
22.5°	348.3	348.3	351.0	351.0	351.0	348.3	342.8	345.5	345.5	351.0	359.2
25°	315.4	315.4	315.4	312.6	312.6	315.4	318.1	318.1	315.4	318.1	320.8
27.5°	285.2	287.9	287.9	290.7	290.7	293.4	293.4	293.4	293.4	296.2	298.9
30°	274.2	274.2	277.0	277.0	277.0	279.7	282.4	282.4	282.4	285.2	290.7
32.5°	263.3	266.0	268.7	271.5	274.2	277.0	277.0	279.7	279.7	282.4	285.2
35°	233.1	230.3	230.3	227.6	224.9	224.9	224.9	224.9	222.1	224.9	224.9
37.5°	208.4	208.4	208.4	205.7	205.7	208.4	208.4	208.4	208.4	211.1	211.1
40°	197.4	197.4	197.4	197.4	197.4	197.4	197.4	200.2	200.2	202.9	205.7
42.5°	189.2	189.2	189.2	189.2	189.2	192.0	192.0	192.0	192.0	194.7	194.7
45°	181.0	181.0	181.0	181.0	181.0	181.0	181.0	183.7	183.7	186.5	189.2
47.5°	172.8	172.8	172.8	172.8	172.8	175.5	178.2	178.2	178.2	181.0	181.0
50°	167.3	167.3	167.3	167.3	167.3	170.0	170.0	172.8	172.8	175.5	178.2
52.5°	161.8	161.8	161.8	161.8	161.8	164.5	164.5	167.3	167.3	170.0	172.8
55°	159.0	159.0	159.0	156.3	156.3	159.0	159.0	161.8	161.8	164.5	164.5
57.5°	150.8	150.8	150.8	150.8	150.8	150.8	150.8	153.6	153.6	156.3	159.0
60°	148.1	148.1	145.3	145.3	142.6	145.3	145.3	148.1	148.1	150.8	150.8
62.5°	139.9	139.9	139.9	137.1	137.1	139.9	139.9	139.9	139.9	142.6	145.3
65°	131.6	131.6	131.6	128.9	128.9	131.6	131.6	131.6	131.6	134.4	137.1
67.5°	123.4	123.4	123.4	120.7	120.7	120.7	120.7	123.4	123.4	126.1	128.9
70°	115.2	115.2	115.2	112.4	112.4	112.4	109.7	112.4	115.2	117.9	117.9
72.5°	106.9	106.9	106.9	104.2	104.2	104.2	101.5	104.2	104.2	106.9	106.9
75°	93.2	93.2	93.2	93.2	93.2	93.2	90.5	90.5	90.5	93.2	93.2
77.5°	85.0	85.0	85.0	82.3	82.3	82.3	79.5	79.5	79.5	82.3	82.3
80°	71.3	71.3	71.3	68.6	68.6	68.6	65.8	65.8	65.8	68.6	68.6
82.5°	57.6	57.6	57.6	54.8	54.8	54.8	52.1	52.1	52.1	54.8	54.8
85°	46.6	46.6	46.6	46.6	46.6	46.6	43.9	43.9	43.9	46.6	49.4
87.5°	21.9	21.9	24.7	24.7	24.7	24.7	21.9	21.9	19.2	19.2	21.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	1796.1	1801.6	1815.3	1826.3	1840.0	1851.0	1859.2	1870.2	1878.4	1886.6	1892.1
5°	1546.6	1549.3	1563.1	1576.8	1587.7	1601.4	1620.6	1639.8	1659.0	1678.2	1691.9
7.5°	1203.8	1214.8	1231.2	1250.4	1266.9	1283.3	1302.5	1324.5	1343.7	1362.9	1382.1
10°	937.8	948.8	965.3	981.7	995.4	1011.9	1033.8	1055.7	1077.7	1099.6	1121.6
12.5°	787.0	800.7	819.9	839.1	855.6	874.8	902.2	926.9	954.3	979.0	1006.4
15°	663.6	680.1	704.7	732.2	756.8	781.5	808.9	836.4	861.0	888.5	915.9
17.5°	545.7	562.2	584.1	608.8	630.7	652.6	685.5	715.7	748.6	778.8	808.9
20°	438.8	447.0	468.9	490.9	512.8	534.7	559.4	584.1	608.8	633.4	671.8
22.5°	364.7	370.2	381.2	389.4	400.4	408.6	433.3	457.9	479.9	504.6	540.2
25°	320.8	323.6	331.8	337.3	345.5	351.0	367.5	381.2	397.6	411.3	444.2
27.5°	298.9	301.6	304.4	307.1	309.9	312.6	323.6	334.5	342.8	353.7	383.9
30°	293.4	296.2	304.4	309.9	318.1	323.6	329.1	334.5	340.0	345.5	364.7
32.5°	287.9	290.7	290.7	287.9	287.9	285.2	290.7	293.4	298.9	301.6	318.1
35°	227.6	227.6	230.3	233.1	235.8	238.6	246.8	252.3	260.5	266.0	279.7
37.5°	213.9	213.9	216.6	222.1	224.9	227.6	233.1	238.6	244.1	249.5	263.3
40°	205.7	208.4	211.1	213.9	216.6	219.4	224.9	227.6	233.1	235.8	246.8
42.5°	197.4	197.4	200.2	205.7	208.4	211.1	216.6	219.4	224.9	227.6	238.6
45°	192.0	194.7	197.4	200.2	200.2	202.9	208.4	213.9	216.6	222.1	233.1
47.5°	183.7	183.7	189.2	192.0	197.4	200.2	205.7	208.4	213.9	216.6	227.6
50°	178.2	181.0	186.5	189.2	194.7	197.4	205.7	211.1	219.4	224.9	230.3
52.5°	172.8	175.5	181.0	183.7	189.2	192.0	202.9	213.9	222.1	233.1	233.1
55°	167.3	167.3	172.8	181.0	186.5	192.0	197.4	205.7	211.1	216.6	216.6
57.5°	159.0	161.8	167.3	175.5	181.0	186.5	192.0	197.4	200.2	205.7	202.9
60°	153.6	153.6	161.8	170.0	178.2	186.5	186.5	186.5	183.7	183.7	183.7
62.5°	145.3	148.1	159.0	172.8	183.7	194.7	186.5	178.2	170.0	161.8	164.5
65°	139.9	142.6	148.1	156.3	161.8	167.3	161.8	159.0	153.6	148.1	150.8
67.5°	128.9	131.6	134.4	134.4	137.1	137.1	137.1	137.1	137.1	137.1	139.9
70°	120.7	120.7	120.7	123.4	123.4	123.4	123.4	123.4	123.4	123.4	126.1
72.5°	109.7	109.7	109.7	109.7	109.7	109.7	109.7	109.7	109.7	109.7	112.4
75°	96.0	96.0	96.0	96.0	96.0	96.0	96.0	96.0	96.0	96.0	98.7
77.5°	85.0	85.0	85.0	85.0	85.0	85.0	85.0	85.0	82.3	82.3	85.0
80°	71.3	71.3	71.3	71.3	68.6	68.6	68.6	68.6	68.6	68.6	71.3
82.5°	57.6	57.6	57.6	57.6	54.8	54.8	54.8	54.8	52.1	52.1	54.8
85°	52.1	54.8	54.8	57.6	57.6	57.6	54.8	52.1	49.4	46.6	46.6
87.5°	21.9	21.9	21.9	21.9	19.2	19.2	19.2	19.2	19.2	19.2	19.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049
 CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	1900.3	1905.8	1911.3	1919.5	1930.5	1938.7	1947.0	1963.4	1982.6	1999.1	2015.5
5°	1705.6	1719.4	1733.1	1749.5	1766.0	1779.7	1796.1	1829.0	1862.0	1892.1	1925.0
7.5°	1398.5	1417.7	1434.2	1461.6	1486.3	1513.7	1538.4	1579.5	1617.9	1659.0	1697.4
10°	1143.5	1165.4	1187.4	1223.0	1261.4	1297.1	1332.7	1365.6	1401.3	1434.2	1467.1
12.5°	1033.8	1058.5	1085.9	1107.8	1132.5	1154.5	1176.4	1214.8	1253.2	1291.6	1330.0
15°	943.3	970.7	998.2	1025.6	1050.3	1077.7	1102.4	1135.3	1170.9	1203.8	1236.7
17.5°	839.1	866.5	896.7	926.9	957.0	987.2	1017.4	1064.0	1110.6	1154.5	1201.1
20°	707.5	745.9	781.5	822.7	863.8	904.9	946.1	995.4	1044.8	1091.4	1140.8
22.5°	575.9	611.5	647.2	696.5	745.9	792.5	841.9	907.7	970.7	1036.5	1099.6
25°	479.9	512.8	545.7	600.5	652.6	707.5	759.6	839.1	915.9	995.4	1072.2
27.5°	414.1	444.2	474.4	532.0	589.6	644.4	702.0	789.8	874.8	962.5	1047.5
30°	383.9	403.1	422.3	477.1	532.0	584.1	638.9	723.9	808.9	894.0	979.0
32.5°	334.5	351.0	367.5	416.8	466.2	512.8	562.2	649.9	734.9	822.7	907.7
35°	296.2	309.9	323.6	370.2	414.1	460.7	504.6	592.3	680.1	767.8	855.6
37.5°	274.2	287.9	298.9	340.0	383.9	425.0	466.2	553.9	638.9	726.7	811.7
40°	257.8	266.0	277.0	318.1	356.5	397.6	436.0	515.5	597.8	677.3	756.8
42.5°	246.8	257.8	266.0	301.6	340.0	375.7	411.3	488.1	564.9	638.9	715.7
45°	244.1	255.0	266.0	296.2	326.3	353.7	383.9	457.9	532.0	606.0	680.1
47.5°	238.6	246.8	257.8	282.4	304.4	329.1	351.0	425.0	499.1	570.4	644.4
50°	235.8	238.6	244.1	266.0	287.9	309.9	331.8	405.8	479.9	553.9	628.0
52.5°	233.1	233.1	233.1	252.3	271.5	287.9	307.1	381.2	457.9	532.0	606.0
55°	216.6	213.9	213.9	233.1	249.5	268.7	285.2	359.2	433.3	504.6	578.6
57.5°	200.2	197.4	194.7	211.1	227.6	244.1	260.5	334.5	411.3	485.4	559.4
60°	183.7	181.0	181.0	197.4	211.1	227.6	241.3	318.1	392.1	468.9	543.0
62.5°	164.5	167.3	167.3	181.0	197.4	211.1	224.9	301.6	381.2	457.9	534.7
65°	150.8	153.6	153.6	170.0	186.5	202.9	219.4	293.4	370.2	444.2	518.3
67.5°	139.9	142.6	142.6	161.8	178.2	197.4	213.9	279.7	348.3	414.1	479.9
70°	128.9	128.9	131.6	150.8	170.0	189.2	208.4	266.0	323.6	378.4	436.0
72.5°	115.2	117.9	120.7	139.9	156.3	175.5	192.0	244.1	296.2	348.3	400.4
75°	101.5	104.2	106.9	123.4	139.9	156.3	172.8	222.1	268.7	318.1	364.7
77.5°	90.5	93.2	96.0	109.7	123.4	137.1	150.8	186.5	224.9	260.5	296.2
80°	74.0	74.0	76.8	87.8	98.7	106.9	117.9	142.6	167.3	189.2	213.9
82.5°	54.8	57.6	57.6	65.8	71.3	79.5	85.0	98.7	109.7	123.4	134.4
85°	46.6	43.9	43.9	49.4	52.1	57.6	60.3	68.6	74.0	82.3	87.8
87.5°	19.2	16.5	16.5	19.2	24.7	27.4	30.2	30.2	32.9	32.9	32.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	2023.7	2029.2	2037.5	2042.9	2056.6	2067.6	2081.3	2092.3	2100.5	2114.2	2108.7
5°	1949.7	1974.4	1999.1	2023.7	2042.9	2062.1	2078.6	2097.8	2119.7	2160.8	2171.8
7.5°	1730.3	1763.2	1793.4	1826.3	1864.7	1903.1	1941.5	1979.9	2015.5	2067.6	2100.5
10°	1513.7	1560.3	1604.2	1650.8	1686.5	1722.1	1755.0	1790.7	1840.0	1892.1	1952.4
12.5°	1376.6	1423.2	1469.8	1516.4	1568.5	1617.9	1670.0	1719.4	1766.0	1807.1	1875.7
15°	1286.1	1338.2	1387.6	1436.9	1500.0	1560.3	1623.4	1683.7	1752.3	1807.1	1853.7
17.5°	1264.2	1327.2	1387.6	1450.6	1516.4	1582.2	1648.1	1713.9	1782.4	1864.7	1925.0
20°	1225.8	1310.8	1395.8	1480.8	1565.8	1648.1	1733.1	1815.3	1905.8	2004.5	2032.0
22.5°	1203.8	1305.3	1409.5	1510.9	1626.1	1744.0	1859.2	1974.4	2070.4	2144.4	2226.7
25°	1201.1	1327.2	1456.1	1582.2	1727.6	1870.2	2015.5	2158.1	2281.5	2355.5	2421.4
27.5°	1198.3	1351.9	1502.7	1653.5	1831.8	2007.3	2185.5	2361.0	2476.2	2583.1	2638.0
30°	1165.4	1349.2	1535.6	1719.4	1919.5	2119.7	2319.9	2520.1	2638.0	2712.0	2739.5
32.5°	1124.3	1340.9	1557.6	1774.2	2001.8	2229.4	2454.3	2681.9	2775.1	2838.2	2816.2
35°	1091.4	1330.0	1565.8	1801.6	2042.9	2287.0	2528.3	2769.6	2904.0	2991.7	2956.1
37.5°	1061.2	1310.8	1560.3	1809.8	2092.3	2374.7	2657.2	2939.6	3068.5	3161.8	3120.6
40°	1025.6	1291.6	1560.3	1826.3	2149.9	2470.7	2794.3	3115.1	3282.4	3361.9	3298.9
42.5°	995.4	1272.4	1552.1	1829.0	2174.6	2520.1	2865.6	3211.1	3397.6	3510.0	3430.5
45°	957.0	1234.0	1508.2	1785.2	2166.3	2547.5	2925.9	3307.1	3523.7	3611.5	3501.8
47.5°	915.9	1190.1	1461.6	1733.1	2138.9	2544.8	2950.6	3356.4	3556.6	3660.8	3559.4
50°	902.2	1176.4	1447.9	1722.1	2160.8	2602.3	3041.1	3479.8	3625.2	3710.2	3575.8
52.5°	899.4	1190.1	1483.5	1774.2	2215.7	2654.4	3095.9	3534.7	3652.6	3743.1	3622.4
55°	891.2	1206.6	1519.2	1831.8	2292.5	2755.9	3216.6	3677.3	3795.2	3861.0	3770.5
57.5°	899.4	1239.5	1576.8	1916.8	2391.2	2865.6	3340.0	3814.4	3957.0	4003.6	3984.4
60°	904.9	1266.9	1626.1	1988.1	2451.5	2915.0	3378.4	3841.8	3989.9	4105.1	4127.0
62.5°	891.2	1247.7	1601.4	1957.9	2377.5	2797.0	3216.6	3636.2	3880.2	4050.2	4148.9
65°	850.1	1179.1	1510.9	1840.0	2226.7	2616.1	3002.7	3389.4	3647.1	3899.4	3978.9
67.5°	759.6	1039.3	1319.0	1598.7	1936.0	2273.3	2607.8	2945.1	3268.7	3512.8	3622.4
70°	658.1	877.5	1099.6	1319.0	1626.1	1933.2	2240.4	2547.5	2832.7	3101.4	3205.6
72.5°	573.1	743.1	915.9	1085.9	1305.3	1521.9	1741.3	1957.9	2295.2	2564.0	2665.4
75°	488.1	611.5	732.2	855.6	1006.4	1157.2	1305.3	1456.1	1694.7	1936.0	2037.5
77.5°	375.7	457.9	537.5	617.0	721.2	822.7	926.9	1028.3	1195.6	1376.6	1428.7
80°	260.5	307.1	351.0	397.6	479.9	562.2	644.4	726.7	836.4	937.8	1017.4
82.5°	161.8	192.0	219.4	246.8	312.6	378.4	441.5	507.3	551.2	556.7	636.2
85°	104.2	123.4	139.9	156.3	194.7	235.8	274.2	312.6	279.7	260.5	309.9
87.5°	41.1	52.1	60.3	68.6	65.8	63.1	60.3	57.6	49.4	43.9	54.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049
 CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	2114.2	2122.5	2130.7	2136.2	2144.4	2147.1	2149.9	2149.9	2152.6	2155.4	2160.8
5°	2215.7	2232.1	2248.6	2262.3	2278.8	2292.5	2303.4	2317.2	2328.1	2328.1	2325.4
7.5°	2130.7	2171.8	2213.0	2254.1	2295.2	2325.4	2352.8	2383.0	2410.4	2415.9	2421.4
10°	2018.3	2062.1	2103.3	2147.1	2188.3	2234.9	2278.8	2322.6	2369.3	2377.5	2388.5
12.5°	1914.1	1966.2	2018.3	2067.6	2119.7	2152.6	2185.5	2215.7	2248.6	2270.5	2292.5
15°	1911.3	1955.2	1999.1	2040.2	2084.1	2103.3	2122.5	2138.9	2158.1	2158.1	2160.8
17.5°	1974.4	2001.8	2029.2	2053.9	2081.3	2084.1	2089.6	2092.3	2095.0	2086.8	2078.6
20°	2097.8	2108.7	2119.7	2130.7	2141.7	2122.5	2106.0	2086.8	2067.6	2045.7	2026.5
22.5°	2278.8	2254.1	2229.4	2204.7	2180.0	2147.1	2111.5	2078.6	2042.9	2015.5	1988.1
25°	2448.8	2418.6	2388.5	2358.3	2328.1	2256.8	2185.5	2111.5	2040.2	2010.0	1979.9
27.5°	2676.4	2629.8	2583.1	2536.5	2489.9	2393.9	2298.0	2202.0	2106.0	2053.9	2004.5
30°	2731.2	2679.1	2627.0	2572.2	2520.1	2426.8	2336.4	2243.1	2149.9	2089.6	2032.0
32.5°	2810.8	2750.4	2690.1	2629.8	2569.4	2478.9	2388.5	2295.2	2204.7	2149.9	2092.3
35°	2942.4	2873.8	2805.3	2734.0	2665.4	2572.2	2481.7	2388.5	2295.2	2232.1	2171.8
37.5°	3054.8	2975.3	2895.8	2816.2	2736.7	2654.4	2569.4	2487.2	2402.2	2339.1	2278.8
40°	3180.9	3093.2	3005.4	2920.4	2832.7	2755.9	2679.1	2599.6	2522.8	2473.5	2424.1
42.5°	3290.6	3183.7	3079.5	2975.3	2868.3	2816.2	2766.9	2714.8	2662.7	2638.0	2610.6
45°	3367.4	3268.7	3167.2	3068.5	2969.8	2931.4	2893.0	2854.6	2816.2	2840.9	2865.6
47.5°	3400.3	3320.8	3244.0	3167.2	3087.7	3101.4	3115.1	3126.1	3139.8	3172.7	3208.4
50°	3430.5	3386.6	3340.0	3296.1	3249.5	3301.6	3351.0	3403.1	3455.2	3523.7	3592.3
52.5°	3490.8	3466.1	3444.2	3419.5	3394.8	3485.3	3575.8	3666.3	3756.8	3833.6	3910.4
55°	3671.8	3652.6	3633.4	3611.5	3592.3	3721.2	3847.3	3976.2	4105.1	4184.6	4264.1
57.5°	3921.3	3910.4	3896.7	3885.7	3872.0	3998.1	4121.5	4244.9	4371.1	4447.8	4527.4
60°	4110.6	4113.3	4113.3	4116.0	4116.0	4212.0	4308.0	4406.7	4502.7	4568.5	4637.1
62.5°	4212.0	4206.5	4201.0	4195.6	4190.1	4269.6	4349.1	4428.6	4508.2	4557.5	4606.9
65°	4102.3	4132.5	4162.7	4192.8	4223.0	4233.9	4242.2	4253.1	4261.4	4291.5	4321.7
67.5°	3734.9	3795.2	3852.8	3913.1	3970.7	3929.6	3891.2	3850.0	3808.9	3817.1	3822.6
70°	3326.3	3394.8	3466.1	3534.7	3603.2	3507.3	3411.3	3312.6	3216.6	3183.7	3150.8
72.5°	2805.3	2865.6	2928.7	2989.0	3049.3	2931.4	2816.2	2698.3	2580.4	2522.8	2465.2
75°	2144.4	2215.7	2289.7	2361.0	2432.3	2300.7	2166.3	2034.7	1900.3	1862.0	1826.3
77.5°	1563.1	1648.1	1733.1	1818.1	1903.1	1785.2	1667.3	1546.6	1428.7	1406.7	1384.8
80°	1138.0	1203.8	1266.9	1332.7	1395.8	1327.2	1258.7	1190.1	1121.6	1118.8	1116.1
82.5°	767.8	825.4	880.2	937.8	992.7	965.3	940.6	913.2	885.7	913.2	943.3
85°	394.9	474.4	556.7	636.2	715.7	707.5	702.0	693.8	685.5	721.2	754.1
87.5°	79.5	148.1	216.6	282.4	351.0	334.5	318.1	298.9	282.4	293.4	301.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049
 CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	2163.6	2166.3	2166.3	2166.3	2166.3	2166.3	2160.8	2158.1	2152.6	2147.1	2138.9
5°	2325.4	2322.6	2311.7	2300.7	2287.0	2276.0	2267.8	2256.8	2248.6	2237.6	2221.2
7.5°	2426.8	2432.3	2413.1	2396.7	2377.5	2358.3	2339.1	2319.9	2300.7	2281.5	2243.1
10°	2396.7	2404.9	2393.9	2383.0	2369.3	2358.3	2336.4	2311.7	2289.7	2265.1	2218.4
12.5°	2311.7	2333.6	2328.1	2322.6	2317.2	2311.7	2298.0	2281.5	2267.8	2251.3	2199.2
15°	2160.8	2160.8	2163.6	2166.3	2166.3	2169.1	2171.8	2174.6	2177.3	2180.0	2149.9
17.5°	2070.4	2062.1	2062.1	2062.1	2062.1	2062.1	2073.1	2086.8	2097.8	2108.7	2100.5
20°	2004.5	1985.3	1982.6	1982.6	1979.9	1977.1	1996.3	2018.3	2037.5	2056.6	2067.6
22.5°	1960.7	1933.2	1930.5	1927.8	1925.0	1922.3	1947.0	1971.6	1996.3	2021.0	2059.4
25°	1949.7	1919.5	1922.3	1925.0	1925.0	1927.8	1947.0	1966.2	1985.3	2004.5	2070.4
27.5°	1952.4	1903.1	1905.8	1908.6	1908.6	1911.3	1941.5	1968.9	1999.1	2026.5	2108.7
30°	1971.6	1914.1	1908.6	1903.1	1897.6	1892.1	1933.2	1974.4	2015.5	2056.6	2119.7
32.5°	2037.5	1982.6	1968.9	1955.2	1941.5	1927.8	1977.1	2023.7	2073.1	2119.7	2171.8
35°	2108.7	2048.4	2042.9	2037.5	2029.2	2023.7	2067.6	2114.2	2158.1	2202.0	2248.6
37.5°	2215.7	2155.4	2149.9	2141.7	2136.2	2127.9	2177.3	2223.9	2273.3	2319.9	2361.0
40°	2374.7	2325.4	2322.6	2322.6	2319.9	2317.2	2355.5	2396.7	2435.1	2473.5	2500.9
42.5°	2585.9	2561.2	2569.4	2580.4	2588.6	2596.9	2627.0	2659.9	2690.1	2720.3	2712.0
45°	2890.3	2915.0	2917.7	2920.4	2923.2	2925.9	2934.1	2945.1	2953.3	2961.6	2928.7
47.5°	3241.3	3274.2	3290.6	3307.1	3320.8	3337.3	3326.3	3312.6	3301.6	3287.9	3205.6
50°	3658.1	3726.6	3723.9	3721.2	3715.7	3712.9	3691.0	3669.1	3644.4	3622.4	3501.8
52.5°	3987.2	4063.9	4077.6	4091.4	4105.1	4118.8	4077.6	4036.5	3992.6	3951.5	3800.7
55°	4340.9	4420.4	4423.2	4425.9	4425.9	4428.6	4371.1	4313.5	4253.1	4195.6	4039.3
57.5°	4604.1	4680.9	4672.7	4667.2	4659.0	4650.8	4582.2	4513.7	4445.1	4376.5	4220.2
60°	4702.9	4768.7	4752.2	4735.8	4716.6	4700.1	4648.0	4595.9	4541.1	4489.0	4338.2
62.5°	4656.2	4705.6	4680.9	4659.0	4634.3	4609.6	4543.8	4475.3	4409.5	4340.9	4231.2
65°	4349.1	4379.3	4346.4	4316.2	4286.1	4253.1	4198.3	4143.5	4085.9	4031.0	3957.0
67.5°	3830.8	3836.3	3833.6	3830.8	3828.1	3825.4	3745.8	3666.3	3584.0	3504.5	3499.0
70°	3120.6	3087.7	3093.2	3101.4	3106.9	3112.4	3052.1	2994.5	2934.1	2873.8	2901.2
72.5°	2407.6	2350.1	2363.8	2380.2	2393.9	2407.6	2358.3	2311.7	2262.3	2213.0	2251.3
75°	1787.9	1752.3	1766.0	1782.4	1796.1	1809.8	1790.7	1771.5	1749.5	1730.3	1766.0
77.5°	1362.9	1340.9	1343.7	1343.7	1346.4	1346.4	1349.2	1354.6	1357.4	1360.1	1398.5
80°	1110.6	1107.8	1105.1	1102.4	1096.9	1094.1	1121.6	1149.0	1176.4	1203.8	1223.0
82.5°	970.7	998.2	981.7	968.0	951.5	935.1	959.8	984.4	1009.1	1033.8	1025.6
85°	789.8	822.7	792.5	762.3	729.4	699.3	721.2	740.4	762.3	781.5	770.6
87.5°	312.6	320.8	271.5	224.9	175.5	126.1	200.2	271.5	345.5	416.8	427.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049
 CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	2130.7	2119.7	2111.5	2108.7	2103.3	2100.5	2095.0	2089.6	2081.3	2075.8	2067.6
5°	2202.0	2185.5	2166.3	2138.9	2114.2	2086.8	2059.4	2034.7	2010.0	1982.6	1957.9
7.5°	2204.7	2166.3	2127.9	2092.3	2053.9	2018.3	1979.9	1947.0	1911.3	1875.7	1842.8
10°	2174.6	2127.9	2081.3	2034.7	1990.8	1944.2	1897.6	1859.2	1818.1	1776.9	1738.6
12.5°	2149.9	2097.8	2045.7	1990.8	1938.7	1883.9	1829.0	1790.7	1752.3	1713.9	1675.5
15°	2119.7	2086.8	2056.6	2007.3	1957.9	1908.6	1859.2	1807.1	1757.7	1705.6	1653.5
17.5°	2095.0	2086.8	2078.6	2045.7	2012.8	1977.1	1944.2	1892.1	1840.0	1785.2	1733.1
20°	2081.3	2092.3	2103.3	2086.8	2070.4	2051.2	2034.7	1996.3	1957.9	1916.8	1878.4
22.5°	2097.8	2138.9	2177.3	2180.0	2185.5	2188.3	2191.0	2155.4	2119.7	2081.3	2045.7
25°	2136.2	2202.0	2267.8	2303.4	2339.1	2377.5	2413.1	2391.2	2369.3	2347.3	2325.4
27.5°	2188.3	2270.5	2352.8	2404.9	2454.3	2506.4	2558.5	2555.7	2553.0	2547.5	2544.8
30°	2180.0	2243.1	2306.2	2369.3	2432.3	2495.4	2558.5	2591.4	2621.5	2654.4	2687.4
32.5°	2226.7	2278.8	2333.6	2399.4	2465.2	2533.8	2599.6	2668.2	2734.0	2802.5	2871.1
35°	2298.0	2344.6	2393.9	2465.2	2539.3	2610.6	2684.6	2766.9	2851.9	2936.9	3019.2
37.5°	2404.9	2446.0	2489.9	2550.2	2613.3	2673.6	2736.7	2857.4	2978.0	3101.4	3222.1
40°	2528.3	2555.7	2583.1	2640.7	2698.3	2755.9	2813.5	2964.3	3115.1	3266.0	3416.8
42.5°	2706.5	2698.3	2690.1	2736.7	2786.1	2832.7	2882.0	3019.2	3156.3	3293.4	3430.5
45°	2895.8	2862.9	2829.9	2851.9	2876.6	2898.5	2923.2	3063.0	3202.9	3345.5	3485.3
47.5°	3123.4	3041.1	2958.8	2939.6	2920.4	2898.5	2879.3	3030.1	3180.9	3334.5	3485.3
50°	3381.1	3257.7	3137.1	3087.7	3035.6	2986.3	2934.1	3057.5	3183.7	3309.8	3433.2
52.5°	3649.9	3496.3	3345.5	3268.7	3191.9	3112.4	3035.6	3139.8	3246.8	3353.7	3457.9
55°	3880.2	3723.9	3564.9	3474.4	3383.9	3293.4	3202.9	3307.1	3411.3	3515.5	3619.7
57.5°	4063.9	3907.6	3751.3	3666.3	3578.6	3493.6	3405.8	3504.5	3606.0	3707.4	3806.2
60°	4190.1	4039.3	3888.4	3806.2	3723.9	3641.6	3559.4	3677.3	3795.2	3915.9	4033.8
62.5°	4124.3	4014.6	3904.9	3869.2	3833.6	3795.2	3759.5	3872.0	3981.7	4094.1	4206.5
65°	3882.9	3808.9	3734.9	3770.5	3808.9	3844.6	3882.9	3957.0	4031.0	4107.8	4181.8
67.5°	3490.8	3485.3	3477.1	3556.6	3636.2	3718.4	3797.9	3847.3	3893.9	3943.3	3992.6
70°	2928.7	2958.8	2986.3	3123.4	3260.5	3397.6	3534.7	3553.9	3573.1	3592.3	3611.5
72.5°	2292.5	2330.9	2372.0	2553.0	2731.2	2912.2	3093.2	3082.2	3071.3	3057.5	3046.6
75°	1804.4	1840.0	1878.4	2045.7	2213.0	2380.2	2547.5	2500.9	2457.0	2410.4	2363.8
77.5°	1439.7	1478.0	1519.2	1675.5	1831.8	1990.8	2147.1	2034.7	1922.3	1809.8	1697.4
80°	1239.5	1258.7	1275.1	1382.1	1486.3	1593.2	1700.2	1585.0	1467.1	1349.2	1234.0
82.5°	1017.4	1006.4	998.2	1061.2	1124.3	1187.4	1250.4	1140.8	1031.1	918.6	808.9
85°	759.6	748.6	737.7	770.6	803.5	839.1	872.0	745.9	619.7	490.9	364.7
87.5°	441.5	452.5	463.4	499.1	534.7	573.1	608.8	479.9	351.0	219.4	90.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049

CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676049
 CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1974.4	1974.4
2.5°	2051.2	2037.5
5°	1938.7	1919.5
7.5°	1815.3	1790.7
10°	1702.9	1670.0
12.5°	1631.6	1590.5
15°	1604.2	1554.8
17.5°	1686.5	1639.8
20°	1812.6	1749.5
22.5°	1966.2	1889.4
25°	2232.1	2138.9
27.5°	2448.8	2352.8
30°	2583.1	2478.9
32.5°	2731.2	2594.1
35°	2884.8	2753.2
37.5°	3071.3	2923.2
40°	3263.2	3109.6
42.5°	3329.0	3230.3
45°	3392.1	3298.9
47.5°	3405.8	3329.0
50°	3419.5	3408.5
52.5°	3457.9	3455.2
55°	3622.4	3625.2
57.5°	3825.4	3841.8
60°	4011.8	3992.6
62.5°	4107.8	4009.1
65°	4042.0	3904.9
67.5°	3844.6	3696.5
70°	3411.3	3211.1
72.5°	2871.1	2695.6
75°	2213.0	2064.9
77.5°	1574.0	1450.6
80°	1107.8	984.4
82.5°	710.2	611.5
85°	320.8	279.7
87.5°	90.5	87.8
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P676049
CATALOG NUMBER: CCW-SA-2C-835-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)