

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P676054

Luminaire Tested: **CCW-SA-1C-840-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P676054
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-1C-840-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @615mA w/
SLR distribution lens
Light Source: (16) 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3199 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 32
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 4.5 fc
 Type IV - Short - N/A

REPORT NUMBER: P676054
CATALOG NUMBER: CCW-SA-1C-840-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	658.2	0.0	658.2
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	2540.8	0.0	2540.8
	% Fixture	79.4	0.0	79.4
Total	Lumens	3199.0	0.0	3199.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.4	2.5
10°-20°	167.6	5.2
20°-30°	245.2	7.7
30°-40°	345.4	10.8
40°-50°	474.7	14.8
50°-60°	647.0	20.2
60°-70°	708.1	22.1
70°-80°	409.0	12.8
80°-90°	122.6	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3199.0	100.0
0°-180°	3199.0	100.0

Coefficient of Utilization



REPORT NUMBER: P676054


CATALOG NUMBER: CCW-SA-1C-840-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	328.5	10.3			
FM	(30°-60°)	1167.4	36.5			
FH	(60°-80°)	940.7	29.4			G1/1800
FVH	(80°-90°)	104.1	3.3			G2/225
BL	(0°-30°)	163.6	5.1	B1/500		
BM	(30°-60°)	299.7	9.4	B1/1000		
BH	(60°-80°)	176.4	5.5	B1/500		G1/500
BVH	(80°-90°)	18.5	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6
2.5°	1054.2	1048.5	1044.3	1040.0	1034.3	1030.1	1024.4	1018.7	1011.6	1006.0	998.9
5°	993.2	976.2	959.1	949.2	937.9	927.9	916.6	903.8	891.0	876.8	864.1
7.5°	926.5	905.2	883.9	866.9	848.5	831.4	813.0	797.4	781.8	766.2	750.6
10°	864.1	844.2	824.3	803.1	780.4	759.1	736.4	715.1	693.8	672.5	651.2
12.5°	822.9	798.8	776.1	752.0	729.3	705.2	681.0	661.2	641.3	620.0	600.2
15°	804.5	781.8	760.5	736.4	712.3	688.1	664.0	641.3	620.0	597.3	574.6
17.5°	848.5	815.8	783.2	752.0	720.8	689.6	658.3	630.0	601.6	573.2	544.8
20°	905.2	864.1	824.3	786.0	746.3	708.0	668.3	628.5	588.8	549.1	509.4
22.5°	977.6	930.8	885.4	835.7	784.6	735.0	683.9	634.2	584.6	533.5	483.8
25°	1106.7	1051.4	996.0	925.1	852.7	781.8	709.4	644.2	580.3	515.0	449.8
27.5°	1217.4	1142.2	1068.4	983.3	898.1	813.0	727.9	652.7	578.9	503.7	428.5
30°	1282.6	1208.9	1135.1	1031.5	929.3	825.8	722.2	638.5	556.2	472.5	388.8
32.5°	1342.2	1259.9	1177.6	1064.1	949.2	835.7	720.8	628.5	537.7	445.5	353.3
35°	1424.5	1333.7	1244.3	1112.4	980.4	848.5	716.5	621.5	525.0	429.9	333.4
37.5°	1512.5	1400.4	1289.7	1143.6	997.4	851.3	705.2	611.5	517.9	424.2	330.6
40°	1609.0	1472.8	1338.0	1176.2	1015.9	854.1	692.4	598.8	505.1	410.0	316.4
42.5°	1671.4	1523.8	1376.3	1201.8	1028.7	854.1	679.6	587.4	495.2	401.5	309.3
45°	1706.9	1563.6	1421.7	1233.0	1044.3	855.6	666.9	576.1	485.2	393.0	302.2
47.5°	1722.5	1589.1	1455.7	1257.1	1059.9	861.2	662.6	570.4	476.7	384.5	290.9
50°	1763.6	1645.9	1528.1	1315.3	1103.9	891.0	678.2	578.9	481.0	381.7	282.3
52.5°	1787.7	1687.0	1586.3	1367.8	1149.3	930.8	712.3	601.6	490.9	380.3	269.6
55°	1875.7	1779.2	1682.7	1450.1	1215.9	983.3	749.1	627.1	505.1	381.7	259.6
57.5°	1987.8	1885.6	1784.9	1533.8	1282.6	1031.5	780.4	649.8	517.9	387.3	255.4
60°	2065.8	1966.5	1868.6	1601.9	1333.7	1067.0	798.8	662.6	526.4	388.8	252.6
62.5°	2074.3	1946.7	1820.4	1560.7	1301.1	1040.0	780.4	648.4	516.5	383.1	251.1
65°	2020.4	1871.5	1722.5	1474.2	1225.9	977.6	729.3	608.7	488.1	366.1	245.5
67.5°	1912.6	1738.1	1563.6	1336.6	1109.5	882.5	655.5	551.9	449.8	346.2	242.6
70°	1661.5	1508.2	1356.4	1159.2	963.4	766.2	569.0	483.8	400.1	315.0	229.9
72.5°	1394.7	1251.4	1109.5	949.2	790.3	630.0	469.6	405.8	341.9	276.7	212.8
75°	1068.4	960.6	854.1	735.0	615.8	495.2	376.0	329.2	282.3	235.5	188.7
77.5°	750.6	692.4	635.6	546.3	456.9	367.5	278.1	246.9	215.7	184.4	153.2
80°	509.4	476.7	445.5	381.7	317.8	252.6	188.7	168.8	147.6	127.7	106.4
82.5°	316.4	315.0	312.1	268.2	224.2	180.2	136.2	119.2	103.6	86.5	69.5
85°	144.7	168.8	191.5	167.4	143.3	119.2	95.1	83.7	72.4	59.6	48.2
87.5°	45.4	55.3	63.8	61.0	56.8	53.9	49.7	42.6	35.5	28.4	21.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6
2.5°	993.2	988.9	983.3	977.6	970.5	964.8	957.7	950.6	949.2	946.4	945.0
5°	855.6	847.0	837.1	828.6	820.1	810.2	801.6	791.7	784.6	776.1	769.0
7.5°	735.0	720.8	705.2	689.6	675.4	661.2	645.6	631.4	624.3	617.2	610.1
10°	638.5	624.3	611.5	597.3	587.4	578.9	569.0	559.0	550.5	542.0	533.5
12.5°	590.2	580.3	570.4	560.4	549.1	539.2	527.8	516.5	506.5	498.0	488.1
15°	560.4	546.3	530.6	516.5	500.9	486.7	471.1	455.4	444.1	434.2	422.8
17.5°	525.0	503.7	483.8	462.5	445.5	428.5	410.0	393.0	380.3	366.1	353.3
20°	485.2	461.1	435.6	411.5	391.6	373.2	353.3	333.4	319.2	303.6	289.4
22.5°	451.2	420.0	387.3	354.7	333.4	312.1	289.4	268.2	255.4	241.2	228.4
25°	414.3	380.3	344.8	309.3	288.0	265.3	244.0	221.3	211.4	202.9	193.0
27.5°	394.4	360.4	324.9	290.9	271.0	249.7	229.9	208.6	201.5	193.0	185.9
30°	354.7	322.1	288.0	254.0	239.8	227.0	212.8	198.6	195.8	194.4	191.5
32.5°	319.2	285.2	251.1	217.1	204.3	191.5	178.8	166.0	164.6	161.7	160.3
35°	300.8	268.2	234.1	201.5	190.1	177.4	166.0	153.2	150.4	146.1	143.3
37.5°	296.5	262.5	227.0	193.0	181.6	170.3	157.5	146.1	143.3	140.5	137.6
40°	285.2	252.6	221.3	188.7	177.4	166.0	153.2	141.9	139.0	136.2	133.4
42.5°	276.7	245.5	212.8	180.2	170.3	160.3	149.0	139.0	136.2	133.4	129.1
45°	269.6	236.9	202.9	170.3	163.2	156.1	147.6	140.5	137.6	133.4	130.5
47.5°	258.2	227.0	194.4	161.7	154.7	149.0	141.9	134.8	132.0	129.1	126.3
50°	249.7	217.1	184.4	151.8	146.1	140.5	134.8	129.1	129.1	130.5	130.5
52.5°	238.4	207.2	175.9	144.7	139.0	133.4	127.7	122.0	123.4	124.9	126.3
55°	228.4	198.6	167.4	136.2	130.5	124.9	117.8	112.1	113.5	114.9	116.3
57.5°	224.2	193.0	161.7	130.5	124.9	117.8	112.1	105.0	105.0	105.0	105.0
60°	221.3	188.7	157.5	124.9	117.8	112.1	105.0	97.9	96.5	96.5	95.1
62.5°	219.9	187.3	156.1	123.4	114.9	107.8	99.3	90.8	89.4	88.0	86.5
65°	214.2	184.4	153.2	122.0	112.1	103.6	93.6	83.7	82.3	82.3	80.9
67.5°	212.8	181.6	151.8	120.6	110.7	99.3	89.4	78.0	76.6	75.2	73.8
70°	201.5	174.5	146.1	117.8	106.4	96.5	85.1	73.8	72.4	69.5	68.1
72.5°	187.3	163.2	137.6	112.1	100.7	89.4	78.0	66.7	65.3	63.8	61.0
75°	166.0	143.3	120.6	97.9	88.0	79.5	69.5	59.6	58.2	56.8	53.9
77.5°	136.2	117.8	100.7	82.3	75.2	68.1	61.0	53.9	52.5	51.1	48.2
80°	96.5	85.1	75.2	63.8	59.6	53.9	49.7	44.0	44.0	42.6	42.6
82.5°	63.8	58.2	52.5	46.8	44.0	41.1	38.3	35.5	35.5	34.1	34.1
85°	45.4	42.6	38.3	35.5	34.1	31.2	29.8	27.0	27.0	27.0	27.0
87.5°	21.3	21.3	19.9	19.9	18.4	18.4	17.0	15.6	15.6	15.6	15.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6
2.5°	942.1	937.9	933.6	927.9	923.7	918.0	910.9	905.2	898.1	898.1	896.7
5°	760.5	756.2	752.0	746.3	742.1	736.4	732.1	726.4	720.8	720.8	719.4
7.5°	603.0	594.5	586.0	576.1	567.5	561.9	556.2	549.1	543.4	539.2	534.9
10°	525.0	516.5	506.5	498.0	488.1	481.0	473.9	465.4	458.3	452.6	446.9
12.5°	478.2	468.2	458.3	448.4	438.4	428.5	420.0	410.0	400.1	393.0	385.9
15°	411.5	401.5	391.6	381.7	371.7	360.4	349.0	336.3	324.9	319.2	315.0
17.5°	339.1	329.2	317.8	307.9	296.5	288.0	279.5	271.0	262.5	256.8	252.6
20°	273.8	262.5	251.1	239.8	228.4	222.8	217.1	211.4	205.7	201.5	198.6
22.5°	214.2	207.2	201.5	194.4	187.3	183.0	180.2	175.9	171.7	171.7	171.7
25°	183.0	178.8	175.9	171.7	167.4	166.0	164.6	161.7	160.3	158.9	158.9
27.5°	177.4	173.1	168.8	164.6	160.3	158.9	157.5	154.7	153.2	153.2	153.2
30°	188.7	187.3	185.9	184.4	183.0	180.2	175.9	173.1	168.8	166.0	163.2
32.5°	157.5	156.1	156.1	154.7	153.2	156.1	157.5	160.3	161.7	163.2	164.6
35°	139.0	136.2	133.4	130.5	127.7	126.3	124.9	123.4	122.0	122.0	120.6
37.5°	134.8	132.0	129.1	126.3	123.4	122.0	120.6	119.2	117.8	117.8	116.3
40°	130.5	127.7	126.3	123.4	120.6	119.2	117.8	114.9	113.5	112.1	112.1
42.5°	126.3	124.9	122.0	120.6	117.8	116.3	114.9	112.1	110.7	109.3	107.8
45°	126.3	123.4	120.6	117.8	114.9	113.5	110.7	109.3	106.4	106.4	105.0
47.5°	123.4	120.6	117.8	114.9	112.1	110.7	107.8	106.4	103.6	102.2	100.7
50°	130.5	126.3	120.6	116.3	110.7	109.3	106.4	105.0	102.2	100.7	99.3
52.5°	127.7	123.4	117.8	113.5	107.8	105.0	103.6	100.7	97.9	96.5	95.1
55°	117.8	113.5	110.7	106.4	102.2	99.3	96.5	93.6	90.8	89.4	89.4
57.5°	105.0	103.6	102.2	100.7	99.3	96.5	93.6	89.4	86.5	85.1	83.7
60°	93.6	95.1	96.5	97.9	99.3	95.1	90.8	86.5	82.3	80.9	79.5
62.5°	85.1	88.0	90.8	92.2	95.1	90.8	86.5	82.3	78.0	76.6	75.2
65°	79.5	80.9	80.9	82.3	82.3	79.5	78.0	75.2	72.4	70.9	70.9
67.5°	72.4	72.4	72.4	70.9	70.9	69.5	69.5	68.1	66.7	65.3	65.3
70°	65.3	65.3	65.3	63.8	63.8	62.4	62.4	61.0	59.6	59.6	58.2
72.5°	59.6	59.6	58.2	58.2	56.8	56.8	56.8	55.3	55.3	53.9	53.9
75°	52.5	52.5	51.1	51.1	49.7	49.7	49.7	48.2	48.2	48.2	46.8
77.5°	46.8	46.8	45.4	45.4	44.0	44.0	44.0	42.6	42.6	41.1	41.1
80°	41.1	41.1	39.7	39.7	38.3	38.3	36.9	36.9	35.5	35.5	34.1
82.5°	32.6	32.6	32.6	32.6	32.6	31.2	31.2	29.8	28.4	28.4	27.0
85°	27.0	27.0	27.0	25.5	25.5	25.5	24.1	24.1	22.7	21.3	21.3
87.5°	15.6	15.6	15.6	14.2	14.2	14.2	14.2	14.2	14.2	14.2	12.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6
2.5°	896.7	895.3	889.6	883.9	889.6	895.3	895.3	895.3	893.9	893.9	893.9
5°	719.4	717.9	715.1	712.3	712.3	710.8	713.7	716.5	719.4	722.2	725.0
7.5°	529.2	525.0	520.7	516.5	519.3	520.7	525.0	527.8	532.1	534.9	542.0
10°	441.3	435.6	431.3	427.1	424.2	421.4	418.6	417.1	414.3	411.5	414.3
12.5°	377.4	370.3	363.2	354.7	353.3	351.9	349.0	346.2	343.4	340.5	339.1
15°	309.3	303.6	300.8	296.5	290.9	285.2	282.3	280.9	278.1	275.3	273.8
17.5°	246.9	241.2	236.9	232.7	231.3	228.4	228.4	228.4	228.4	228.4	228.4
20°	194.4	190.1	190.1	188.7	188.7	187.3	188.7	190.1	190.1	191.5	193.0
22.5°	170.3	170.3	168.8	167.4	168.8	168.8	170.3	171.7	173.1	174.5	175.9
25°	157.5	156.1	157.5	158.9	158.9	158.9	160.3	160.3	161.7	161.7	161.7
27.5°	151.8	151.8	153.2	153.2	154.7	154.7	154.7	153.2	153.2	151.8	151.8
30°	160.3	157.5	157.5	157.5	156.1	154.7	153.2	153.2	151.8	150.4	149.0
32.5°	166.0	167.4	166.0	163.2	161.7	158.9	157.5	154.7	153.2	150.4	147.6
35°	120.6	119.2	122.0	123.4	124.9	126.3	127.7	129.1	129.1	130.5	130.5
37.5°	116.3	114.9	114.9	113.5	113.5	113.5	113.5	113.5	112.1	112.1	113.5
40°	110.7	109.3	109.3	107.8	107.8	106.4	106.4	106.4	106.4	106.4	106.4
42.5°	106.4	105.0	105.0	105.0	105.0	103.6	103.6	102.2	102.2	100.7	100.7
45°	105.0	103.6	102.2	100.7	100.7	99.3	99.3	99.3	97.9	97.9	97.9
47.5°	99.3	97.9	97.9	96.5	96.5	95.1	95.1	95.1	93.6	93.6	93.6
50°	96.5	95.1	95.1	93.6	93.6	92.2	92.2	92.2	90.8	90.8	90.8
52.5°	92.2	90.8	90.8	90.8	89.4	88.0	88.0	88.0	86.5	86.5	86.5
55°	88.0	86.5	86.5	86.5	85.1	83.7	83.7	83.7	82.3	82.3	82.3
57.5°	82.3	80.9	80.9	79.5	79.5	79.5	79.5	79.5	78.0	78.0	78.0
60°	78.0	76.6	76.6	75.2	75.2	73.8	73.8	73.8	73.8	73.8	73.8
62.5°	73.8	72.4	70.9	69.5	70.9	70.9	70.9	70.9	69.5	69.5	69.5
65°	69.5	68.1	66.7	65.3	65.3	65.3	65.3	65.3	65.3	65.3	65.3
67.5°	63.8	62.4	61.0	59.6	61.0	61.0	61.0	61.0	61.0	61.0	61.0
70°	58.2	56.8	56.8	55.3	55.3	53.9	53.9	55.3	55.3	55.3	55.3
72.5°	52.5	51.1	51.1	49.7	49.7	49.7	49.7	49.7	49.7	49.7	49.7
75°	46.8	45.4	45.4	44.0	44.0	44.0	44.0	44.0	44.0	44.0	44.0
77.5°	39.7	38.3	38.3	38.3	38.3	38.3	38.3	39.7	39.7	39.7	39.7
80°	34.1	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.6
82.5°	27.0	25.5	25.5	25.5	25.5	25.5	25.5	25.5	25.5	25.5	25.5
85°	19.9	18.4	18.4	18.4	19.9	19.9	19.9	19.9	19.9	19.9	19.9
87.5°	12.8	11.4	11.4	11.4	12.8	12.8	12.8	12.8	11.4	11.4	11.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6
2.5°	893.9	893.9	893.9	892.5	891.0	889.6	888.2	892.5	895.3	899.5	902.4
5°	726.4	729.3	730.7	735.0	739.2	743.5	747.7	750.6	753.4	754.8	757.7
7.5°	547.7	554.8	560.4	566.1	571.8	576.1	581.7	586.0	590.2	594.5	598.8
10°	415.7	418.6	420.0	425.7	429.9	435.6	439.8	444.1	448.4	451.2	455.4
12.5°	337.7	334.8	333.4	333.4	333.4	333.4	333.4	336.3	339.1	341.9	344.8
15°	272.4	271.0	269.6	268.2	266.7	263.9	262.5	265.3	268.2	271.0	273.8
17.5°	228.4	228.4	228.4	227.0	225.6	224.2	222.8	224.2	225.6	225.6	227.0
20°	195.8	197.2	198.6	200.1	200.1	201.5	201.5	202.9	204.3	204.3	205.7
22.5°	175.9	177.4	177.4	177.4	178.8	178.8	178.8	180.2	181.6	183.0	184.4
25°	160.3	160.3	158.9	158.9	160.3	160.3	160.3	160.3	161.7	161.7	161.7
27.5°	151.8	150.4	150.4	150.4	150.4	149.0	149.0	149.0	149.0	149.0	149.0
30°	147.6	146.1	144.7	143.3	143.3	141.9	140.5	140.5	140.5	140.5	140.5
32.5°	146.1	143.3	140.5	139.0	139.0	137.6	136.2	134.8	134.8	133.4	132.0
35°	130.5	129.1	129.1	127.7	126.3	124.9	123.4	123.4	123.4	122.0	122.0
37.5°	113.5	114.9	114.9	114.9	116.3	116.3	116.3	116.3	117.8	117.8	117.8
40°	106.4	106.4	106.4	107.8	109.3	109.3	110.7	110.7	112.1	112.1	112.1
42.5°	100.7	99.3	99.3	100.7	100.7	102.2	102.2	103.6	105.0	105.0	106.4
45°	97.9	96.5	96.5	96.5	96.5	95.1	95.1	96.5	97.9	99.3	100.7
47.5°	92.2	92.2	90.8	90.8	90.8	90.8	90.8	90.8	92.2	92.2	92.2
50°	89.4	89.4	88.0	88.0	88.0	88.0	88.0	88.0	88.0	88.0	88.0
52.5°	86.5	85.1	85.1	85.1	85.1	83.7	83.7	83.7	83.7	83.7	83.7
55°	82.3	80.9	80.9	80.9	80.9	80.9	80.9	80.9	82.3	82.3	82.3
57.5°	78.0	76.6	76.6	76.6	78.0	78.0	78.0	78.0	79.5	79.5	79.5
60°	73.8	73.8	73.8	73.8	73.8	73.8	73.8	75.2	75.2	76.6	76.6
62.5°	69.5	69.5	69.5	69.5	70.9	70.9	70.9	70.9	72.4	72.4	72.4
65°	65.3	65.3	65.3	65.3	66.7	66.7	66.7	66.7	66.7	66.7	66.7
67.5°	61.0	61.0	61.0	61.0	61.0	61.0	61.0	62.4	62.4	63.8	63.8
70°	55.3	53.9	53.9	55.3	55.3	56.8	56.8	58.2	58.2	59.6	59.6
72.5°	49.7	49.7	49.7	49.7	49.7	49.7	49.7	51.1	52.5	52.5	53.9
75°	44.0	44.0	44.0	44.0	45.4	45.4	45.4	46.8	46.8	48.2	48.2
77.5°	39.7	38.3	38.3	38.3	39.7	39.7	39.7	41.1	41.1	42.6	42.6
80°	32.6	32.6	32.6	32.6	34.1	34.1	34.1	34.1	35.5	35.5	35.5
82.5°	27.0	27.0	27.0	27.0	27.0	27.0	27.0	27.0	28.4	28.4	28.4
85°	19.9	19.9	19.9	19.9	21.3	21.3	21.3	21.3	21.3	21.3	21.3
87.5°	12.8	12.8	12.8	12.8	12.8	12.8	12.8	12.8	14.2	14.2	14.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054
 CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6
2.5°	902.4	902.4	902.4	902.4	905.2	906.6	909.5	910.9	909.5	908.1	905.2
5°	759.1	760.5	760.5	761.9	761.9	761.9	761.9	761.9	764.8	767.6	770.4
7.5°	600.2	601.6	603.0	604.4	604.4	604.4	603.0	603.0	604.4	604.4	605.8
10°	459.7	465.4	469.6	473.9	471.1	466.8	464.0	459.7	459.7	459.7	458.3
12.5°	347.6	349.0	351.9	353.3	351.9	351.9	350.5	349.0	350.5	353.3	354.7
15°	275.3	275.3	276.7	276.7	278.1	279.5	279.5	280.9	283.8	285.2	288.0
17.5°	228.4	229.9	229.9	231.3	231.3	232.7	232.7	232.7	235.5	238.4	242.6
20°	205.7	205.7	205.7	205.7	205.7	204.3	204.3	202.9	204.3	207.2	208.6
22.5°	184.4	185.9	185.9	185.9	184.4	183.0	180.2	178.8	178.8	180.2	180.2
25°	161.7	160.3	160.3	158.9	158.9	160.3	160.3	160.3	161.7	161.7	163.2
27.5°	149.0	147.6	147.6	146.1	146.1	147.6	147.6	147.6	147.6	147.6	147.6
30°	139.0	139.0	137.6	136.2	137.6	137.6	139.0	139.0	140.5	140.5	141.9
32.5°	132.0	130.5	130.5	129.1	130.5	130.5	132.0	132.0	133.4	134.8	134.8
35°	122.0	122.0	122.0	122.0	122.0	122.0	120.6	120.6	120.6	120.6	120.6
37.5°	116.3	116.3	114.9	113.5	113.5	113.5	113.5	113.5	112.1	110.7	109.3
40°	112.1	110.7	110.7	109.3	107.8	107.8	106.4	105.0	105.0	103.6	103.6
42.5°	106.4	105.0	105.0	103.6	102.2	102.2	100.7	99.3	99.3	99.3	97.9
45°	99.3	99.3	97.9	96.5	96.5	96.5	95.1	95.1	95.1	95.1	93.6
47.5°	92.2	92.2	90.8	90.8	90.8	90.8	89.4	89.4	89.4	89.4	89.4
50°	88.0	88.0	88.0	88.0	88.0	88.0	86.5	86.5	86.5	86.5	86.5
52.5°	83.7	83.7	83.7	83.7	83.7	83.7	83.7	83.7	83.7	83.7	83.7
55°	82.3	82.3	82.3	82.3	82.3	82.3	80.9	80.9	80.9	82.3	82.3
57.5°	79.5	79.5	78.0	78.0	78.0	78.0	78.0	78.0	78.0	78.0	78.0
60°	76.6	76.6	76.6	76.6	76.6	76.6	76.6	76.6	76.6	76.6	76.6
62.5°	72.4	72.4	72.4	72.4	72.4	73.8	73.8	73.8	73.8	73.8	72.4
65°	66.7	68.1	68.1	68.1	68.1	68.1	68.1	68.1	68.1	68.1	68.1
67.5°	63.8	63.8	63.8	63.8	63.8	63.8	63.8	63.8	63.8	63.8	63.8
70°	59.6	59.6	58.2	58.2	58.2	59.6	59.6	59.6	59.6	59.6	59.6
72.5°	53.9	53.9	53.9	53.9	53.9	53.9	53.9	53.9	53.9	55.3	55.3
75°	48.2	48.2	48.2	48.2	48.2	48.2	48.2	48.2	48.2	48.2	48.2
77.5°	42.6	42.6	41.1	41.1	41.1	42.6	42.6	42.6	42.6	44.0	44.0
80°	35.5	35.5	35.5	35.5	35.5	35.5	35.5	35.5	35.5	36.9	36.9
82.5°	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4	29.8	29.8
85°	21.3	22.7	22.7	22.7	22.7	22.7	22.7	22.7	22.7	24.1	24.1
87.5°	14.2	14.2	14.2	14.2	14.2	14.2	12.8	12.8	12.8	12.8	11.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6
2.5°	903.8	905.2	906.6	906.6	908.1	909.5	909.5	915.2	920.8	923.7	926.5
5°	773.3	771.9	771.9	770.4	769.0	773.3	777.5	786.0	794.6	796.0	798.8
7.5°	605.8	607.3	608.7	608.7	610.1	605.8	600.2	601.6	603.0	610.1	615.8
10°	458.3	459.7	461.1	461.1	462.5	461.1	458.3	462.5	466.8	472.5	479.6
12.5°	356.1	360.4	364.6	367.5	371.7	374.6	376.0	381.7	385.9	393.0	400.1
15°	290.9	293.7	296.5	299.4	302.2	305.1	307.9	313.6	319.2	327.8	336.3
17.5°	245.5	245.5	246.9	246.9	246.9	249.7	252.6	255.4	256.8	265.3	273.8
20°	210.0	208.6	207.2	205.7	204.3	207.2	208.6	210.0	211.4	217.1	221.3
22.5°	180.2	180.2	181.6	181.6	181.6	180.2	177.4	178.8	178.8	181.6	185.9
25°	163.2	163.2	163.2	161.7	161.7	163.2	164.6	164.6	163.2	164.6	166.0
27.5°	147.6	149.0	149.0	150.4	150.4	151.8	151.8	151.8	151.8	153.2	154.7
30°	141.9	141.9	143.3	143.3	143.3	144.7	146.1	146.1	146.1	147.6	150.4
32.5°	136.2	137.6	139.0	140.5	141.9	143.3	143.3	144.7	144.7	146.1	147.6
35°	120.6	119.2	119.2	117.8	116.3	116.3	116.3	116.3	114.9	116.3	116.3
37.5°	107.8	107.8	107.8	106.4	106.4	107.8	107.8	107.8	107.8	109.3	109.3
40°	102.2	102.2	102.2	102.2	102.2	102.2	102.2	103.6	103.6	105.0	106.4
42.5°	97.9	97.9	97.9	97.9	97.9	99.3	99.3	99.3	99.3	100.7	100.7
45°	93.6	93.6	93.6	93.6	93.6	93.6	93.6	95.1	95.1	96.5	97.9
47.5°	89.4	89.4	89.4	89.4	89.4	90.8	92.2	92.2	92.2	93.6	93.6
50°	86.5	86.5	86.5	86.5	86.5	88.0	88.0	89.4	89.4	90.8	92.2
52.5°	83.7	83.7	83.7	83.7	83.7	85.1	85.1	86.5	86.5	88.0	89.4
55°	82.3	82.3	82.3	80.9	80.9	82.3	82.3	83.7	83.7	85.1	85.1
57.5°	78.0	78.0	78.0	78.0	78.0	78.0	78.0	79.5	79.5	80.9	82.3
60°	76.6	76.6	75.2	75.2	73.8	75.2	75.2	76.6	76.6	78.0	78.0
62.5°	72.4	72.4	72.4	70.9	70.9	72.4	72.4	72.4	72.4	73.8	75.2
65°	68.1	68.1	68.1	66.7	66.7	68.1	68.1	68.1	68.1	69.5	70.9
67.5°	63.8	63.8	63.8	62.4	62.4	62.4	62.4	63.8	63.8	65.3	66.7
70°	59.6	59.6	59.6	58.2	58.2	58.2	56.8	58.2	59.6	61.0	61.0
72.5°	55.3	55.3	55.3	53.9	53.9	53.9	52.5	53.9	53.9	55.3	55.3
75°	48.2	48.2	48.2	48.2	48.2	48.2	46.8	46.8	46.8	48.2	48.2
77.5°	44.0	44.0	44.0	42.6	42.6	42.6	41.1	41.1	41.1	42.6	42.6
80°	36.9	36.9	36.9	35.5	35.5	35.5	34.1	34.1	34.1	35.5	35.5
82.5°	29.8	29.8	29.8	28.4	28.4	28.4	27.0	27.0	27.0	28.4	28.4
85°	24.1	24.1	24.1	24.1	24.1	24.1	22.7	22.7	22.7	24.1	25.5
87.5°	11.4	11.4	12.8	12.8	12.8	12.8	11.4	11.4	9.9	9.9	11.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6
2.5°	929.3	932.2	939.3	945.0	952.0	957.7	962.0	967.7	971.9	976.2	979.0
5°	800.2	801.6	808.7	815.8	821.5	828.6	838.5	848.5	858.4	868.3	875.4
7.5°	622.9	628.5	637.1	647.0	655.5	664.0	674.0	685.3	695.2	705.2	715.1
10°	485.2	490.9	499.4	507.9	515.0	523.6	534.9	546.3	557.6	569.0	580.3
12.5°	407.2	414.3	424.2	434.2	442.7	452.6	466.8	479.6	493.8	506.5	520.7
15°	343.4	351.9	364.6	378.8	391.6	404.4	418.6	432.7	445.5	459.7	473.9
17.5°	282.3	290.9	302.2	315.0	326.3	337.7	354.7	370.3	387.3	403.0	418.6
20°	227.0	231.3	242.6	254.0	265.3	276.7	289.4	302.2	315.0	327.8	347.6
22.5°	188.7	191.5	197.2	201.5	207.2	211.4	224.2	236.9	248.3	261.1	279.5
25°	166.0	167.4	171.7	174.5	178.8	181.6	190.1	197.2	205.7	212.8	229.9
27.5°	154.7	156.1	157.5	158.9	160.3	161.7	167.4	173.1	177.4	183.0	198.6
30°	151.8	153.2	157.5	160.3	164.6	167.4	170.3	173.1	175.9	178.8	188.7
32.5°	149.0	150.4	150.4	149.0	149.0	147.6	150.4	151.8	154.7	156.1	164.6
35°	117.8	117.8	119.2	120.6	122.0	123.4	127.7	130.5	134.8	137.6	144.7
37.5°	110.7	110.7	112.1	114.9	116.3	117.8	120.6	123.4	126.3	129.1	136.2
40°	106.4	107.8	109.3	110.7	112.1	113.5	116.3	117.8	120.6	122.0	127.7
42.5°	102.2	102.2	103.6	106.4	107.8	109.3	112.1	113.5	116.3	117.8	123.4
45°	99.3	100.7	102.2	103.6	103.6	105.0	107.8	110.7	112.1	114.9	120.6
47.5°	95.1	95.1	97.9	99.3	102.2	103.6	106.4	107.8	110.7	112.1	117.8
50°	92.2	93.6	96.5	97.9	100.7	102.2	106.4	109.3	113.5	116.3	119.2
52.5°	89.4	90.8	93.6	95.1	97.9	99.3	105.0	110.7	114.9	120.6	120.6
55°	86.5	86.5	89.4	93.6	96.5	99.3	102.2	106.4	109.3	112.1	112.1
57.5°	82.3	83.7	86.5	90.8	93.6	96.5	99.3	102.2	103.6	106.4	105.0
60°	79.5	79.5	83.7	88.0	92.2	96.5	96.5	96.5	95.1	95.1	95.1
62.5°	75.2	76.6	82.3	89.4	95.1	100.7	96.5	92.2	88.0	83.7	85.1
65°	72.4	73.8	76.6	80.9	83.7	86.5	83.7	82.3	79.5	76.6	78.0
67.5°	66.7	68.1	69.5	69.5	70.9	70.9	70.9	70.9	70.9	70.9	72.4
70°	62.4	62.4	62.4	63.8	63.8	63.8	63.8	63.8	63.8	63.8	65.3
72.5°	56.8	56.8	56.8	56.8	56.8	56.8	56.8	56.8	56.8	56.8	58.2
75°	49.7	49.7	49.7	49.7	49.7	49.7	49.7	49.7	49.7	49.7	51.1
77.5°	44.0	44.0	44.0	44.0	44.0	44.0	44.0	44.0	42.6	42.6	44.0
80°	36.9	36.9	36.9	36.9	35.5	35.5	35.5	35.5	35.5	35.5	36.9
82.5°	29.8	29.8	29.8	29.8	28.4	28.4	28.4	28.4	27.0	27.0	28.4
85°	27.0	28.4	28.4	29.8	29.8	29.8	28.4	27.0	25.5	24.1	24.1
87.5°	11.4	11.4	11.4	11.4	9.9	9.9	9.9	9.9	9.9	9.9	9.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6
2.5°	983.3	986.1	988.9	993.2	998.9	1003.1	1007.4	1015.9	1025.8	1034.3	1042.9
5°	882.5	889.6	896.7	905.2	913.7	920.8	929.3	946.4	963.4	979.0	996.0
7.5°	723.6	733.5	742.1	756.2	769.0	783.2	796.0	817.3	837.1	858.4	878.3
10°	591.7	603.0	614.4	632.8	652.7	671.1	689.6	706.6	725.0	742.1	759.1
12.5°	534.9	547.7	561.9	573.2	586.0	597.3	608.7	628.5	648.4	668.3	688.1
15°	488.1	502.3	516.5	530.6	543.4	557.6	570.4	587.4	605.8	622.9	639.9
17.5°	434.2	448.4	464.0	479.6	495.2	510.8	526.4	550.5	574.6	597.3	621.5
20°	366.1	385.9	404.4	425.7	446.9	468.2	489.5	515.0	540.6	564.7	590.2
22.5°	298.0	316.4	334.8	360.4	385.9	410.0	435.6	469.6	502.3	536.3	569.0
25°	248.3	265.3	282.3	310.7	337.7	366.1	393.0	434.2	473.9	515.0	554.8
27.5°	214.2	229.9	245.5	275.3	305.1	333.4	363.2	408.6	452.6	498.0	542.0
30°	198.6	208.6	218.5	246.9	275.3	302.2	330.6	374.6	418.6	462.5	506.5
32.5°	173.1	181.6	190.1	215.7	241.2	265.3	290.9	336.3	380.3	425.7	469.6
35°	153.2	160.3	167.4	191.5	214.2	238.4	261.1	306.5	351.9	397.3	442.7
37.5°	141.9	149.0	154.7	175.9	198.6	219.9	241.2	286.6	330.6	376.0	420.0
40°	133.4	137.6	143.3	164.6	184.4	205.7	225.6	266.7	309.3	350.5	391.6
42.5°	127.7	133.4	137.6	156.1	175.9	194.4	212.8	252.6	292.3	330.6	370.3
45°	126.3	132.0	137.6	153.2	168.8	183.0	198.6	236.9	275.3	313.6	351.9
47.5°	123.4	127.7	133.4	146.1	157.5	170.3	181.6	219.9	258.2	295.1	333.4
50°	122.0	123.4	126.3	137.6	149.0	160.3	171.7	210.0	248.3	286.6	324.9
52.5°	120.6	120.6	120.6	130.5	140.5	149.0	158.9	197.2	236.9	275.3	313.6
55°	112.1	110.7	110.7	120.6	129.1	139.0	147.6	185.9	224.2	261.1	299.4
57.5°	103.6	102.2	100.7	109.3	117.8	126.3	134.8	173.1	212.8	251.1	289.4
60°	95.1	93.6	93.6	102.2	109.3	117.8	124.9	164.6	202.9	242.6	280.9
62.5°	85.1	86.5	86.5	93.6	102.2	109.3	116.3	156.1	197.2	236.9	276.7
65°	78.0	79.5	79.5	88.0	96.5	105.0	113.5	151.8	191.5	229.9	268.2
67.5°	72.4	73.8	73.8	83.7	92.2	102.2	110.7	144.7	180.2	214.2	248.3
70°	66.7	66.7	68.1	78.0	88.0	97.9	107.8	137.6	167.4	195.8	225.6
72.5°	59.6	61.0	62.4	72.4	80.9	90.8	99.3	126.3	153.2	180.2	207.2
75°	52.5	53.9	55.3	63.8	72.4	80.9	89.4	114.9	139.0	164.6	188.7
77.5°	46.8	48.2	49.7	56.8	63.8	70.9	78.0	96.5	116.3	134.8	153.2
80°	38.3	38.3	39.7	45.4	51.1	55.3	61.0	73.8	86.5	97.9	110.7
82.5°	28.4	29.8	29.8	34.1	36.9	41.1	44.0	51.1	56.8	63.8	69.5
85°	24.1	22.7	22.7	25.5	27.0	29.8	31.2	35.5	38.3	42.6	45.4
87.5°	9.9	8.5	8.5	9.9	12.8	14.2	15.6	15.6	17.0	17.0	17.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6
2.5°	1047.1	1049.9	1054.2	1057.0	1064.1	1069.8	1076.9	1082.6	1086.8	1093.9	1091.1
5°	1008.8	1021.6	1034.3	1047.1	1057.0	1067.0	1075.5	1085.4	1096.8	1118.0	1123.7
7.5°	895.3	912.3	927.9	945.0	964.8	984.7	1004.5	1024.4	1042.9	1069.8	1086.8
10°	783.2	807.3	830.0	854.1	872.6	891.0	908.1	926.5	952.0	979.0	1010.2
12.5°	712.3	736.4	760.5	784.6	811.6	837.1	864.1	889.6	913.7	935.0	970.5
15°	665.4	692.4	717.9	743.5	776.1	807.3	840.0	871.2	906.6	935.0	959.1
17.5°	654.1	686.7	717.9	750.6	784.6	818.7	852.7	886.8	922.2	964.8	996.0
20°	634.2	678.2	722.2	766.2	810.2	852.7	896.7	939.3	986.1	1037.2	1051.4
22.5°	622.9	675.4	729.3	781.8	841.4	902.4	962.0	1021.6	1071.2	1109.5	1152.1
25°	621.5	686.7	753.4	818.7	893.9	967.7	1042.9	1116.6	1180.5	1218.8	1252.8
27.5°	620.0	699.5	777.5	855.6	947.8	1038.6	1130.8	1221.6	1281.2	1336.6	1364.9
30°	603.0	698.1	794.6	889.6	993.2	1096.8	1200.3	1303.9	1364.9	1403.2	1417.4
32.5°	581.7	693.8	805.9	918.0	1035.8	1153.5	1269.9	1387.6	1435.9	1468.5	1457.2
35°	564.7	688.1	810.2	932.2	1057.0	1183.3	1308.2	1433.0	1502.6	1548.0	1529.5
37.5°	549.1	678.2	807.3	936.4	1082.6	1228.7	1374.9	1521.0	1587.7	1635.9	1614.6
40°	530.6	668.3	807.3	945.0	1112.4	1278.4	1445.8	1611.8	1698.4	1739.5	1706.9
42.5°	515.0	658.3	803.1	946.4	1125.1	1303.9	1482.7	1661.5	1757.9	1816.1	1775.0
45°	495.2	638.5	780.4	923.7	1120.9	1318.1	1513.9	1711.1	1823.2	1868.6	1811.9
47.5°	473.9	615.8	756.2	896.7	1106.7	1316.7	1526.7	1736.7	1840.2	1894.2	1841.7
50°	466.8	608.7	749.1	891.0	1118.0	1346.5	1573.5	1800.5	1875.7	1919.7	1850.2
52.5°	465.4	615.8	767.6	918.0	1146.4	1373.4	1601.9	1828.9	1889.9	1936.7	1874.3
55°	461.1	624.3	786.0	947.8	1186.2	1425.9	1664.3	1902.7	1963.7	1997.7	1950.9
57.5°	465.4	641.3	815.8	991.8	1237.2	1482.7	1728.2	1973.6	2047.4	2071.5	2061.6
60°	468.2	655.5	841.4	1028.7	1268.4	1508.2	1748.0	1987.8	2064.4	2124.0	2135.4
62.5°	461.1	645.6	828.6	1013.1	1230.1	1447.2	1664.3	1881.4	2007.7	2095.6	2146.7
65°	439.8	610.1	781.8	952.0	1152.1	1353.6	1553.6	1753.7	1887.1	2017.6	2058.7
67.5°	393.0	537.7	682.5	827.2	1001.7	1176.2	1349.3	1523.8	1691.3	1817.5	1874.3
70°	340.5	454.0	569.0	682.5	841.4	1000.3	1159.2	1318.1	1465.7	1604.7	1658.6
72.5°	296.5	384.5	473.9	561.9	675.4	787.5	901.0	1013.1	1187.6	1326.6	1379.1
75°	252.6	316.4	378.8	442.7	520.7	598.8	675.4	753.4	876.8	1001.7	1054.2
77.5°	194.4	236.9	278.1	319.2	373.2	425.7	479.6	532.1	618.6	712.3	739.2
80°	134.8	158.9	181.6	205.7	248.3	290.9	333.4	376.0	432.7	485.2	526.4
82.5°	83.7	99.3	113.5	127.7	161.7	195.8	228.4	262.5	285.2	288.0	329.2
85°	53.9	63.8	72.4	80.9	100.7	122.0	141.9	161.7	144.7	134.8	160.3
87.5°	21.3	27.0	31.2	35.5	34.1	32.6	31.2	29.8	25.5	22.7	28.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054
 CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6
2.5°	1093.9	1098.2	1102.4	1105.3	1109.5	1111.0	1112.4	1112.4	1113.8	1115.2	1118.0
5°	1146.4	1154.9	1163.5	1170.5	1179.1	1186.2	1191.8	1198.9	1204.6	1204.6	1203.2
7.5°	1102.4	1123.7	1145.0	1166.3	1187.6	1203.2	1217.4	1233.0	1247.2	1250.0	1252.8
10°	1044.3	1067.0	1088.3	1111.0	1132.2	1156.4	1179.1	1201.8	1225.9	1230.1	1235.8
12.5°	990.4	1017.3	1044.3	1069.8	1096.8	1113.8	1130.8	1146.4	1163.5	1174.8	1186.2
15°	988.9	1011.6	1034.3	1055.6	1078.3	1088.3	1098.2	1106.7	1116.6	1116.6	1118.0
17.5°	1021.6	1035.8	1049.9	1062.7	1076.9	1078.3	1081.2	1082.6	1084.0	1079.7	1075.5
20°	1085.4	1091.1	1096.8	1102.4	1108.1	1098.2	1089.7	1079.7	1069.8	1058.5	1048.5
22.5°	1179.1	1166.3	1153.5	1140.8	1128.0	1111.0	1092.5	1075.5	1057.0	1042.9	1028.7
25°	1267.0	1251.4	1235.8	1220.2	1204.6	1167.7	1130.8	1092.5	1055.6	1040.0	1024.4
27.5°	1384.8	1360.7	1336.6	1312.4	1288.3	1238.7	1189.0	1139.3	1089.7	1062.7	1037.2
30°	1413.2	1386.2	1359.3	1330.9	1303.9	1255.7	1208.9	1160.6	1112.4	1081.2	1051.4
32.5°	1454.3	1423.1	1391.9	1360.7	1329.5	1282.6	1235.8	1187.6	1140.8	1112.4	1082.6
35°	1522.4	1486.9	1451.5	1414.6	1379.1	1330.9	1284.1	1235.8	1187.6	1154.9	1123.7
37.5°	1580.6	1539.4	1498.3	1457.2	1416.0	1373.4	1329.5	1286.9	1242.9	1210.3	1179.1
40°	1645.9	1600.5	1555.1	1511.1	1465.7	1425.9	1386.2	1345.1	1305.3	1279.8	1254.3
42.5°	1702.6	1647.3	1593.4	1539.4	1484.1	1457.2	1431.6	1404.7	1377.7	1364.9	1350.7
45°	1742.3	1691.3	1638.8	1587.7	1536.6	1516.7	1496.9	1477.0	1457.2	1469.9	1482.7
47.5°	1759.4	1718.2	1678.5	1638.8	1597.6	1604.7	1611.8	1617.5	1624.6	1641.6	1660.0
50°	1775.0	1752.3	1728.2	1705.5	1681.3	1708.3	1733.8	1760.8	1787.7	1823.2	1858.7
52.5°	1806.2	1793.4	1782.1	1769.3	1756.5	1803.4	1850.2	1897.0	1943.8	1983.5	2023.3
55°	1899.8	1889.9	1880.0	1868.6	1858.7	1925.4	1990.6	2057.3	2124.0	2165.2	2206.3
57.5°	2028.9	2023.3	2016.2	2010.5	2003.4	2068.7	2132.5	2196.4	2261.6	2301.4	2342.5
60°	2126.8	2128.3	2128.3	2129.7	2129.7	2179.3	2229.0	2280.1	2329.7	2363.8	2399.3
62.5°	2179.3	2176.5	2173.7	2170.8	2168.0	2209.1	2250.3	2291.4	2332.6	2358.1	2383.7
65°	2122.6	2138.2	2153.8	2169.4	2185.0	2190.7	2195.0	2200.6	2204.9	2220.5	2236.1
67.5°	1932.5	1963.7	1993.5	2024.7	2054.5	2033.2	2013.3	1992.1	1970.8	1975.0	1977.9
70°	1721.1	1756.5	1793.4	1828.9	1864.4	1814.7	1765.0	1714.0	1664.3	1647.3	1630.3
72.5°	1451.5	1482.7	1515.3	1546.5	1577.8	1516.7	1457.2	1396.1	1335.1	1305.3	1275.5
75°	1109.5	1146.4	1184.7	1221.6	1258.5	1190.4	1120.9	1052.8	983.3	963.4	945.0
77.5°	808.7	852.7	896.7	940.7	984.7	923.7	862.7	800.2	739.2	727.9	716.5
80°	588.8	622.9	655.5	689.6	722.2	686.7	651.2	615.8	580.3	578.9	577.5
82.5°	397.3	427.1	455.4	485.2	513.6	499.4	486.7	472.5	458.3	472.5	488.1
85°	204.3	245.5	288.0	329.2	370.3	366.1	363.2	359.0	354.7	373.2	390.2
87.5°	41.1	76.6	112.1	146.1	181.6	173.1	164.6	154.7	146.1	151.8	156.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6
2.5°	1119.5	1120.9	1120.9	1120.9	1120.9	1120.9	1118.0	1116.6	1113.8	1111.0	1106.7
5°	1203.2	1201.8	1196.1	1190.4	1183.3	1177.6	1173.4	1167.7	1163.5	1157.8	1149.3
7.5°	1255.7	1258.5	1248.6	1240.1	1230.1	1220.2	1210.3	1200.3	1190.4	1180.5	1160.6
10°	1240.1	1244.3	1238.7	1233.0	1225.9	1220.2	1208.9	1196.1	1184.7	1172.0	1147.8
12.5°	1196.1	1207.4	1204.6	1201.8	1198.9	1196.1	1189.0	1180.5	1173.4	1164.9	1137.9
15°	1118.0	1118.0	1119.5	1120.9	1120.9	1122.3	1123.7	1125.1	1126.6	1128.0	1112.4
17.5°	1071.2	1067.0	1067.0	1067.0	1067.0	1067.0	1072.6	1079.7	1085.4	1091.1	1086.8
20°	1037.2	1027.2	1025.8	1025.8	1024.4	1023.0	1032.9	1044.3	1054.2	1064.1	1069.8
22.5°	1014.5	1000.3	998.9	997.4	996.0	994.6	1007.4	1020.1	1032.9	1045.7	1065.6
25°	1008.8	993.2	994.6	996.0	996.0	997.4	1007.4	1017.3	1027.2	1037.2	1071.2
27.5°	1010.2	984.7	986.1	987.5	987.5	988.9	1004.5	1018.7	1034.3	1048.5	1091.1
30°	1020.1	990.4	987.5	984.7	981.8	979.0	1000.3	1021.6	1042.9	1064.1	1096.8
32.5°	1054.2	1025.8	1018.7	1011.6	1004.5	997.4	1023.0	1047.1	1072.6	1096.8	1123.7
35°	1091.1	1059.9	1057.0	1054.2	1049.9	1047.1	1069.8	1093.9	1116.6	1139.3	1163.5
37.5°	1146.4	1115.2	1112.4	1108.1	1105.3	1101.0	1126.6	1150.7	1176.2	1200.3	1221.6
40°	1228.7	1203.2	1201.8	1201.8	1200.3	1198.9	1218.8	1240.1	1259.9	1279.8	1294.0
42.5°	1338.0	1325.2	1329.5	1335.1	1339.4	1343.6	1359.3	1376.3	1391.9	1407.5	1403.2
45°	1495.5	1508.2	1509.7	1511.1	1512.5	1513.9	1518.2	1523.8	1528.1	1532.4	1515.3
47.5°	1677.1	1694.1	1702.6	1711.1	1718.2	1726.7	1721.1	1714.0	1708.3	1701.2	1658.6
50°	1892.7	1928.2	1926.8	1925.4	1922.5	1921.1	1909.8	1898.4	1885.6	1874.3	1811.9
52.5°	2063.0	2102.7	2109.8	2116.9	2124.0	2131.1	2109.8	2088.5	2065.8	2044.6	1966.5
55°	2246.0	2287.2	2288.6	2290.0	2290.0	2291.4	2261.6	2231.8	2200.6	2170.8	2090.0
57.5°	2382.2	2422.0	2417.7	2414.9	2410.6	2406.4	2370.9	2335.4	2299.9	2264.5	2183.6
60°	2433.3	2467.4	2458.9	2450.3	2440.4	2431.9	2404.9	2378.0	2349.6	2322.6	2244.6
62.5°	2409.2	2434.7	2422.0	2410.6	2397.8	2385.1	2351.0	2315.6	2281.5	2246.0	2189.3
65°	2250.3	2265.9	2248.9	2233.3	2217.7	2200.6	2172.3	2143.9	2114.1	2085.7	2047.4
67.5°	1982.1	1985.0	1983.5	1982.1	1980.7	1979.3	1938.1	1897.0	1854.4	1813.3	1810.4
70°	1614.6	1597.6	1600.5	1604.7	1607.6	1610.4	1579.2	1549.4	1518.2	1486.9	1501.1
72.5°	1245.7	1215.9	1223.0	1231.6	1238.7	1245.7	1220.2	1196.1	1170.5	1145.0	1164.9
75°	925.1	906.6	913.7	922.2	929.3	936.4	926.5	916.6	905.2	895.3	913.7
77.5°	705.2	693.8	695.2	695.2	696.7	696.7	698.1	700.9	702.3	703.7	723.6
80°	574.6	573.2	571.8	570.4	567.5	566.1	580.3	594.5	608.7	622.9	632.8
82.5°	502.3	516.5	507.9	500.9	492.3	483.8	496.6	509.4	522.1	534.9	530.6
85°	408.6	425.7	410.0	394.4	377.4	361.8	373.2	383.1	394.4	404.4	398.7
87.5°	161.7	166.0	140.5	116.3	90.8	65.3	103.6	140.5	178.8	215.7	221.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6	1021.6
2.5°	1102.4	1096.8	1092.5	1091.1	1088.3	1086.8	1084.0	1081.2	1076.9	1074.1	1069.8
5°	1139.3	1130.8	1120.9	1106.7	1093.9	1079.7	1065.6	1052.8	1040.0	1025.8	1013.1
7.5°	1140.8	1120.9	1101.0	1082.6	1062.7	1044.3	1024.4	1007.4	988.9	970.5	953.5
10°	1125.1	1101.0	1076.9	1052.8	1030.1	1006.0	981.8	962.0	940.7	919.4	899.5
12.5°	1112.4	1085.4	1058.5	1030.1	1003.1	974.7	946.4	926.5	906.6	886.8	866.9
15°	1096.8	1079.7	1064.1	1038.6	1013.1	987.5	962.0	935.0	909.5	882.5	855.6
17.5°	1084.0	1079.7	1075.5	1058.5	1041.4	1023.0	1006.0	979.0	952.0	923.7	896.7
20°	1076.9	1082.6	1088.3	1079.7	1071.2	1061.3	1052.8	1032.9	1013.1	991.8	971.9
22.5°	1085.4	1106.7	1126.6	1128.0	1130.8	1132.2	1133.7	1115.2	1096.8	1076.9	1058.5
25°	1105.3	1139.3	1173.4	1191.8	1210.3	1230.1	1248.6	1237.2	1225.9	1214.5	1203.2
27.5°	1132.2	1174.8	1217.4	1244.3	1269.9	1296.8	1323.8	1322.4	1320.9	1318.1	1316.7
30°	1128.0	1160.6	1193.2	1225.9	1258.5	1291.1	1323.8	1340.8	1356.4	1373.4	1390.5
32.5°	1152.1	1179.1	1207.4	1241.5	1275.5	1311.0	1345.1	1380.5	1414.6	1450.1	1485.5
35°	1189.0	1213.1	1238.7	1275.5	1313.8	1350.7	1389.0	1431.6	1475.6	1519.6	1562.1
37.5°	1244.3	1265.6	1288.3	1319.5	1352.2	1383.4	1416.0	1478.4	1540.9	1604.7	1667.1
40°	1308.2	1322.4	1336.6	1366.3	1396.1	1425.9	1455.7	1533.8	1611.8	1689.8	1767.9
42.5°	1400.4	1396.1	1391.9	1416.0	1441.5	1465.7	1491.2	1562.1	1633.1	1704.0	1775.0
45°	1498.3	1481.3	1464.2	1475.6	1488.4	1499.7	1512.5	1584.8	1657.2	1731.0	1803.4
47.5°	1616.1	1573.5	1530.9	1521.0	1511.1	1499.7	1489.8	1567.8	1645.9	1725.3	1803.4
50°	1749.4	1685.6	1623.2	1597.6	1570.7	1545.1	1518.2	1582.0	1647.3	1712.5	1776.4
52.5°	1888.5	1809.0	1731.0	1691.3	1651.5	1610.4	1570.7	1624.6	1679.9	1735.2	1789.2
55°	2007.7	1926.8	1844.5	1797.7	1750.9	1704.0	1657.2	1711.1	1765.0	1819.0	1872.9
57.5°	2102.7	2021.9	1941.0	1897.0	1851.6	1807.6	1762.2	1813.3	1865.8	1918.3	1969.4
60°	2168.0	2090.0	2011.9	1969.4	1926.8	1884.2	1841.7	1902.7	1963.7	2026.1	2087.1
62.5°	2133.9	2077.2	2020.4	2002.0	1983.5	1963.7	1945.2	2003.4	2060.2	2118.3	2176.5
65°	2009.1	1970.8	1932.5	1950.9	1970.8	1989.2	2009.1	2047.4	2085.7	2125.4	2163.7
67.5°	1806.2	1803.4	1799.1	1840.2	1881.4	1924.0	1965.1	1990.6	2014.8	2040.3	2065.8
70°	1515.3	1530.9	1545.1	1616.1	1687.0	1757.9	1828.9	1838.8	1848.8	1858.7	1868.6
72.5°	1186.2	1206.0	1227.3	1320.9	1413.2	1506.8	1600.5	1594.8	1589.1	1582.0	1576.3
75°	933.6	952.0	971.9	1058.5	1145.0	1231.6	1318.1	1294.0	1271.3	1247.2	1223.0
77.5°	744.9	764.8	786.0	866.9	947.8	1030.1	1111.0	1052.8	994.6	936.4	878.3
80°	641.3	651.2	659.8	715.1	769.0	824.3	879.7	820.1	759.1	698.1	638.5
82.5°	526.4	520.7	516.5	549.1	581.7	614.4	647.0	590.2	533.5	475.3	418.6
85°	393.0	387.3	381.7	398.7	415.7	434.2	451.2	385.9	320.7	254.0	188.7
87.5°	228.4	234.1	239.8	258.2	276.7	296.5	315.0	248.3	181.6	113.5	46.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054

CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676054
 CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1021.6	1021.6
2.5°	1061.3	1054.2
5°	1003.1	993.2
7.5°	939.3	926.5
10°	881.1	864.1
12.5°	844.2	822.9
15°	830.0	804.5
17.5°	872.6	848.5
20°	937.9	905.2
22.5°	1017.3	977.6
25°	1154.9	1106.7
27.5°	1267.0	1217.4
30°	1336.6	1282.6
32.5°	1413.2	1342.2
35°	1492.6	1424.5
37.5°	1589.1	1512.5
40°	1688.4	1609.0
42.5°	1722.5	1671.4
45°	1755.1	1706.9
47.5°	1762.2	1722.5
50°	1769.3	1763.6
52.5°	1789.2	1787.7
55°	1874.3	1875.7
57.5°	1979.3	1987.8
60°	2075.8	2065.8
62.5°	2125.4	2074.3
65°	2091.4	2020.4
67.5°	1989.2	1912.6
70°	1765.0	1661.5
72.5°	1485.5	1394.7
75°	1145.0	1068.4
77.5°	814.4	750.6
80°	573.2	509.4
82.5°	367.5	316.4
85°	166.0	144.7
87.5°	46.8	45.4
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P676054
CATALOG NUMBER: CCW-SA-1C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)