

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P676060

Luminaire Tested: **CCW-SA-2C-840-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P676060
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2C-840-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @615mA w/
SLR distribution lens
Light Source: (32) 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6397.3 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 9.1 fc

Type IV - Short - N/A

REPORT NUMBER: P676060
CATALOG NUMBER: CCW-SA-2C-840-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1316.3	0.0	1316.3
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	5081.0	0.0	5081.0
	% Fixture	79.4	0.0	79.4
Total	Lumens	6397.3	0.0	6397.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.7	2.5
10°-20°	335.2	5.2
20°-30°	490.4	7.7
30°-40°	690.8	10.8
40°-50°	949.3	14.8
50°-60°	1293.9	20.2
60°-70°	1416.1	22.1
70°-80°	817.8	12.8
80°-90°	245.1	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6397.3	100.0
0°-180°	6397.3	100.0

Coefficient of Utilization



REPORT NUMBER: P676060


CATALOG NUMBER: CCW-SA-2C-840-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	657.0	10.3			
FM	(30°-60°)	2334.6	36.5			
FH	(60°-80°)	1881.2	29.4			G2/5000
FVH	(80°-90°)	208.2	3.3			G2/225
BL	(0°-30°)	327.2	5.1	B1/500		
BM	(30°-60°)	599.4	9.4	B1/1000		
BH	(60°-80°)	352.8	5.5	B1/500		G1/500
BVH	(80°-90°)	36.9	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9
2.5°	2108.2	2096.8	2088.3	2079.8	2068.4	2059.9	2048.6	2037.2	2023.0	2011.7	1997.5
5°	1986.2	1952.1	1918.1	1898.2	1875.5	1855.6	1832.9	1807.4	1781.9	1753.5	1728.0
7.5°	1852.8	1810.2	1767.7	1733.6	1696.7	1662.7	1625.8	1594.6	1563.4	1532.2	1501.0
10°	1728.0	1688.2	1648.5	1606.0	1560.6	1518.0	1472.6	1430.0	1387.5	1344.9	1302.4
12.5°	1645.7	1597.4	1552.0	1503.8	1458.4	1410.2	1361.9	1322.2	1282.5	1239.9	1200.2
15°	1608.8	1563.4	1520.8	1472.6	1424.4	1376.1	1327.9	1282.5	1239.9	1194.5	1149.1
17.5°	1696.7	1631.5	1566.2	1503.8	1441.4	1379.0	1316.5	1259.8	1203.0	1146.3	1089.6
20°	1810.2	1728.0	1648.5	1571.9	1492.5	1415.8	1336.4	1257.0	1177.5	1098.1	1018.6
22.5°	1955.0	1861.3	1770.5	1671.2	1569.1	1469.8	1367.6	1268.3	1169.0	1066.9	967.5
25°	2213.2	2102.5	1991.8	1850.0	1705.3	1563.4	1418.7	1288.2	1160.5	1030.0	899.4
27.5°	2434.5	2284.1	2136.5	1966.3	1796.1	1625.8	1455.6	1305.2	1157.6	1007.3	856.9
30°	2565.0	2417.4	2269.9	2062.8	1858.5	1651.4	1444.2	1276.8	1112.3	944.8	777.4
32.5°	2684.2	2519.6	2355.0	2128.0	1898.2	1671.2	1441.4	1257.0	1075.4	890.9	706.5
35°	2848.7	2667.1	2488.4	2224.5	1960.6	1696.7	1432.9	1242.8	1049.8	859.7	666.8
37.5°	3024.6	2800.5	2579.2	2286.9	1994.7	1702.4	1410.2	1222.9	1035.6	848.4	661.1
40°	3217.6	2945.2	2675.6	2352.2	2031.6	1708.1	1384.6	1197.4	1010.1	820.0	632.7
42.5°	3342.4	3047.3	2752.3	2403.3	2057.1	1708.1	1359.1	1174.7	990.2	803.0	618.5
45°	3413.4	3126.8	2843.0	2465.7	2088.3	1710.9	1333.6	1152.0	970.4	786.0	604.4
47.5°	3444.6	3177.9	2911.1	2513.9	2119.5	1722.3	1325.1	1140.6	953.4	768.9	581.7
50°	3526.9	3291.4	3055.9	2630.2	2207.5	1781.9	1356.3	1157.6	961.9	763.3	564.6
52.5°	3575.1	3373.6	3172.2	2735.2	2298.3	1861.3	1424.4	1203.0	981.7	760.4	539.1
55°	3751.0	3558.1	3365.1	2899.8	2431.6	1966.3	1498.1	1254.1	1010.1	763.3	519.2
57.5°	3975.2	3770.9	3569.4	3067.2	2565.0	2062.8	1560.6	1299.5	1035.6	774.6	510.7
60°	4131.2	3932.6	3736.8	3203.4	2667.1	2133.7	1597.4	1325.1	1052.7	777.4	505.1
62.5°	4148.2	3892.9	3640.4	3121.1	2601.9	2079.8	1560.6	1296.7	1032.8	766.1	502.2
65°	4040.4	3742.5	3444.6	2948.0	2451.5	1955.0	1458.4	1217.2	976.1	732.0	490.9
67.5°	3824.8	3475.8	3126.8	2672.8	2218.8	1764.8	1310.9	1103.7	899.4	692.3	485.2
70°	3322.6	3016.1	2712.5	2318.1	1926.6	1532.2	1137.8	967.5	800.1	629.9	459.7
72.5°	2789.1	2502.6	2218.8	1898.2	1580.4	1259.8	939.2	811.5	683.8	553.3	425.6
75°	2136.5	1920.9	1708.1	1469.8	1231.4	990.2	751.9	658.3	564.6	471.0	377.4
77.5°	1501.0	1384.6	1271.1	1092.4	913.6	734.9	556.1	493.7	431.3	368.9	306.4
80°	1018.6	953.4	890.9	763.3	635.6	505.1	377.4	337.6	295.1	255.4	212.8
82.5°	632.7	629.9	624.2	536.3	448.3	360.3	272.4	238.3	207.1	173.1	139.0
85°	289.4	337.6	383.0	334.8	286.6	238.3	190.1	167.4	144.7	119.2	96.5
87.5°	90.8	110.7	127.7	122.0	113.5	107.8	99.3	85.1	70.9	56.7	42.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060
 CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9
2.5°	1986.2	1977.6	1966.3	1955.0	1940.8	1929.4	1915.2	1901.0	1898.2	1892.5	1889.7
5°	1710.9	1693.9	1674.1	1657.0	1640.0	1620.1	1603.1	1583.3	1569.1	1552.0	1537.9
7.5°	1469.8	1441.4	1410.2	1379.0	1350.6	1322.2	1291.0	1262.6	1248.4	1234.3	1220.1
10°	1276.8	1248.4	1222.9	1194.5	1174.7	1157.6	1137.8	1117.9	1100.9	1083.9	1066.9
12.5°	1180.3	1160.5	1140.6	1120.8	1098.1	1078.2	1055.5	1032.8	1012.9	995.9	976.1
15°	1120.8	1092.4	1061.2	1032.8	1001.6	973.2	942.0	910.8	888.1	868.2	845.5
17.5°	1049.8	1007.3	967.5	925.0	890.9	856.9	820.0	786.0	760.4	732.0	706.5
20°	970.4	922.1	871.1	822.8	783.1	746.2	706.5	666.8	638.4	607.2	578.8
22.5°	902.3	839.9	774.6	709.3	666.8	624.2	578.8	536.3	510.7	482.4	456.8
25°	828.5	760.4	689.5	618.5	576.0	530.6	488.0	442.6	422.8	405.7	385.9
27.5°	788.8	720.7	649.8	581.7	541.9	499.4	459.7	417.1	402.9	385.9	371.7
30°	709.3	644.1	576.0	507.9	479.5	454.0	425.6	397.2	391.6	388.7	383.0
32.5°	638.4	570.3	502.2	434.1	408.6	383.0	357.5	332.0	329.1	323.5	320.6
35°	601.5	536.3	468.2	402.9	380.2	354.7	332.0	306.4	300.8	292.2	286.6
37.5°	593.0	524.9	454.0	385.9	363.2	340.5	314.9	292.2	286.6	280.9	275.2
40°	570.3	505.1	442.6	377.4	354.7	332.0	306.4	283.7	278.1	272.4	266.7
42.5°	553.3	490.9	425.6	360.3	340.5	320.6	297.9	278.1	272.4	266.7	258.2
45°	539.1	473.8	405.7	340.5	326.3	312.1	295.1	280.9	275.2	266.7	261.0
47.5°	516.4	454.0	388.7	323.5	309.3	297.9	283.7	269.6	263.9	258.2	252.5
50°	499.4	434.1	368.9	303.6	292.2	280.9	269.6	258.2	258.2	261.0	261.0
52.5°	476.7	414.3	351.8	289.4	278.1	266.7	255.4	244.0	246.9	249.7	252.5
55°	456.8	397.2	334.8	272.4	261.0	249.7	235.5	224.2	227.0	229.8	232.7
57.5°	448.3	385.9	323.5	261.0	249.7	235.5	224.2	210.0	210.0	210.0	210.0
60°	442.6	377.4	314.9	249.7	235.5	224.2	210.0	195.8	192.9	192.9	190.1
62.5°	439.8	374.5	312.1	246.9	229.8	215.6	198.6	181.6	178.8	175.9	173.1
65°	428.4	368.9	306.4	244.0	224.2	207.1	187.3	167.4	164.6	164.6	161.7
67.5°	425.6	363.2	303.6	241.2	221.3	198.6	178.8	156.1	153.2	150.4	147.5
70°	402.9	349.0	292.2	235.5	212.8	192.9	170.2	147.5	144.7	139.0	136.2
72.5°	374.5	326.3	275.2	224.2	201.5	178.8	156.1	133.4	130.5	127.7	122.0
75°	332.0	286.6	241.2	195.8	175.9	158.9	139.0	119.2	116.3	113.5	107.8
77.5°	272.4	235.5	201.5	164.6	150.4	136.2	122.0	107.8	105.0	102.1	96.5
80°	192.9	170.2	150.4	127.7	119.2	107.8	99.3	88.0	88.0	85.1	85.1
82.5°	127.7	116.3	105.0	93.6	88.0	82.3	76.6	70.9	70.9	68.1	68.1
85°	90.8	85.1	76.6	70.9	68.1	62.4	59.6	53.9	53.9	53.9	53.9
87.5°	42.6	42.6	39.7	39.7	36.9	36.9	34.0	31.2	31.2	31.2	31.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9
2.5°	1884.0	1875.5	1867.0	1855.6	1847.1	1835.8	1821.6	1810.2	1796.1	1796.1	1793.2
5°	1520.8	1512.3	1503.8	1492.5	1483.9	1472.6	1464.1	1452.7	1441.4	1441.4	1438.5
7.5°	1205.9	1188.9	1171.8	1152.0	1134.9	1123.6	1112.3	1098.1	1086.7	1078.2	1069.7
10°	1049.8	1032.8	1012.9	995.9	976.1	961.9	947.7	930.7	916.5	905.1	893.8
12.5°	956.2	936.3	916.5	896.6	876.7	856.9	839.9	820.0	800.1	786.0	771.8
15°	822.8	803.0	783.1	763.3	743.4	720.7	698.0	672.5	649.8	638.4	629.9
17.5°	678.1	658.3	635.6	615.7	593.0	576.0	559.0	541.9	524.9	513.6	505.1
20°	547.6	524.9	502.2	479.5	456.8	445.5	434.1	422.8	411.4	402.9	397.2
22.5°	428.4	414.3	402.9	388.7	374.5	366.0	360.3	351.8	343.3	343.3	343.3
25°	366.0	357.5	351.8	343.3	334.8	332.0	329.1	323.5	320.6	317.8	317.8
27.5°	354.7	346.2	337.6	329.1	320.6	317.8	314.9	309.3	306.4	306.4	306.4
30°	377.4	374.5	371.7	368.9	366.0	360.3	351.8	346.2	337.6	332.0	326.3
32.5°	314.9	312.1	312.1	309.3	306.4	312.1	314.9	320.6	323.5	326.3	329.1
35°	278.1	272.4	266.7	261.0	255.4	252.5	249.7	246.9	244.0	244.0	241.2
37.5°	269.6	263.9	258.2	252.5	246.9	244.0	241.2	238.3	235.5	235.5	232.7
40°	261.0	255.4	252.5	246.9	241.2	238.3	235.5	229.8	227.0	224.2	224.2
42.5°	252.5	249.7	244.0	241.2	235.5	232.7	229.8	224.2	221.3	218.5	215.6
45°	252.5	246.9	241.2	235.5	229.8	227.0	221.3	218.5	212.8	212.8	210.0
47.5°	246.9	241.2	235.5	229.8	224.2	221.3	215.6	212.8	207.1	204.3	201.5
50°	261.0	252.5	241.2	232.7	221.3	218.5	212.8	210.0	204.3	201.5	198.6
52.5°	255.4	246.9	235.5	227.0	215.6	210.0	207.1	201.5	195.8	192.9	190.1
55°	235.5	227.0	221.3	212.8	204.3	198.6	192.9	187.3	181.6	178.8	178.8
57.5°	210.0	207.1	204.3	201.5	198.6	192.9	187.3	178.8	173.1	170.2	167.4
60°	187.3	190.1	192.9	195.8	198.6	190.1	181.6	173.1	164.6	161.7	158.9
62.5°	170.2	175.9	181.6	184.4	190.1	181.6	173.1	164.6	156.1	153.2	150.4
65°	158.9	161.7	161.7	164.6	164.6	158.9	156.1	150.4	144.7	141.9	141.9
67.5°	144.7	144.7	144.7	141.9	141.9	139.0	139.0	136.2	133.4	130.5	130.5
70°	130.5	130.5	130.5	127.7	127.7	124.8	124.8	122.0	119.2	119.2	116.3
72.5°	119.2	119.2	116.3	116.3	113.5	113.5	113.5	110.7	110.7	107.8	107.8
75°	105.0	105.0	102.1	102.1	99.3	99.3	99.3	96.5	96.5	96.5	93.6
77.5°	93.6	93.6	90.8	90.8	88.0	88.0	88.0	85.1	85.1	82.3	82.3
80°	82.3	82.3	79.4	79.4	76.6	76.6	73.8	73.8	70.9	70.9	68.1
82.5°	65.3	65.3	65.3	65.3	65.3	62.4	62.4	59.6	56.7	56.7	53.9
85°	53.9	53.9	53.9	51.1	51.1	51.1	48.2	48.2	45.4	42.6	42.6
87.5°	31.2	31.2	31.2	28.4	28.4	28.4	28.4	28.4	28.4	28.4	25.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060
 CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9
2.5°	1793.2	1790.4	1779.0	1767.7	1779.0	1790.4	1790.4	1790.4	1787.5	1787.5	1787.5
5°	1438.5	1435.7	1430.0	1424.4	1424.4	1421.5	1427.2	1432.9	1438.5	1444.2	1449.9
7.5°	1058.3	1049.8	1041.3	1032.8	1038.5	1041.3	1049.8	1055.5	1064.0	1069.7	1083.9
10°	882.4	871.1	862.6	854.0	848.4	842.7	837.0	834.2	828.5	822.8	828.5
12.5°	754.7	740.6	726.4	709.3	706.5	703.7	698.0	692.3	686.6	681.0	678.1
15°	618.5	607.2	601.5	593.0	581.7	570.3	564.6	561.8	556.1	550.5	547.6
17.5°	493.7	482.4	473.8	465.3	462.5	456.8	456.8	456.8	456.8	456.8	456.8
20°	388.7	380.2	380.2	377.4	377.4	374.5	377.4	380.2	380.2	383.0	385.9
22.5°	340.5	340.5	337.6	334.8	337.6	337.6	340.5	343.3	346.2	349.0	351.8
25°	314.9	312.1	314.9	317.8	317.8	317.8	320.6	320.6	323.5	323.5	323.5
27.5°	303.6	303.6	306.4	306.4	309.3	309.3	309.3	306.4	306.4	303.6	303.6
30°	320.6	314.9	314.9	314.9	312.1	309.3	306.4	306.4	303.6	300.8	297.9
32.5°	332.0	334.8	332.0	326.3	323.5	317.8	314.9	309.3	306.4	300.8	295.1
35°	241.2	238.3	244.0	246.9	249.7	252.5	255.4	258.2	258.2	261.0	261.0
37.5°	232.7	229.8	229.8	227.0	227.0	227.0	227.0	227.0	224.2	224.2	227.0
40°	221.3	218.5	218.5	215.6	215.6	212.8	212.8	212.8	212.8	212.8	212.8
42.5°	212.8	210.0	210.0	210.0	210.0	207.1	207.1	204.3	204.3	201.5	201.5
45°	210.0	207.1	204.3	201.5	201.5	198.6	198.6	198.6	195.8	195.8	195.8
47.5°	198.6	195.8	195.8	192.9	192.9	190.1	190.1	190.1	187.3	187.3	187.3
50°	192.9	190.1	190.1	187.3	187.3	184.4	184.4	184.4	181.6	181.6	181.6
52.5°	184.4	181.6	181.6	181.6	178.8	175.9	175.9	175.9	173.1	173.1	173.1
55°	175.9	173.1	173.1	173.1	170.2	167.4	167.4	167.4	164.6	164.6	164.6
57.5°	164.6	161.7	161.7	158.9	158.9	158.9	158.9	158.9	156.1	156.1	156.1
60°	156.1	153.2	153.2	150.4	150.4	147.5	147.5	147.5	147.5	147.5	147.5
62.5°	147.5	144.7	141.9	139.0	141.9	141.9	141.9	141.9	139.0	139.0	139.0
65°	139.0	136.2	133.4	130.5	130.5	130.5	130.5	130.5	130.5	130.5	130.5
67.5°	127.7	124.8	122.0	119.2	122.0	122.0	122.0	122.0	122.0	122.0	122.0
70°	116.3	113.5	113.5	110.7	110.7	107.8	107.8	110.7	110.7	110.7	110.7
72.5°	105.0	102.1	102.1	99.3	99.3	99.3	99.3	99.3	99.3	99.3	99.3
75°	93.6	90.8	90.8	88.0	88.0	88.0	88.0	88.0	88.0	88.0	88.0
77.5°	79.4	76.6	76.6	76.6	76.6	76.6	76.6	79.4	79.4	79.4	79.4
80°	68.1	65.3	65.3	65.3	65.3	65.3	65.3	65.3	65.3	65.3	65.3
82.5°	53.9	51.1	51.1	51.1	51.1	51.1	51.1	51.1	51.1	51.1	51.1
85°	39.7	36.9	36.9	36.9	39.7	39.7	39.7	39.7	39.7	39.7	39.7
87.5°	25.5	22.7	22.7	22.7	25.5	25.5	25.5	25.5	22.7	22.7	22.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9
2.5°	1787.5	1787.5	1787.5	1784.7	1781.9	1779.0	1776.2	1784.7	1790.4	1798.9	1804.6
5°	1452.7	1458.4	1461.2	1469.8	1478.3	1486.8	1495.3	1501.0	1506.6	1509.5	1515.2
7.5°	1095.2	1109.4	1120.8	1132.1	1143.5	1152.0	1163.3	1171.8	1180.3	1188.9	1197.4
10°	831.4	837.0	839.9	851.2	859.7	871.1	879.6	888.1	896.6	902.3	910.8
12.5°	675.3	669.6	666.8	666.8	666.8	666.8	666.8	672.5	678.1	683.8	689.5
15°	544.8	541.9	539.1	536.3	533.4	527.8	524.9	530.6	536.3	541.9	547.6
17.5°	456.8	456.8	456.8	454.0	451.1	448.3	445.5	448.3	451.1	451.1	454.0
20°	391.6	394.4	397.2	400.1	400.1	402.9	402.9	405.7	408.6	408.6	411.4
22.5°	351.8	354.7	354.7	354.7	357.5	357.5	357.5	360.3	363.2	366.0	368.9
25°	320.6	320.6	317.8	317.8	320.6	320.6	320.6	320.6	323.5	323.5	323.5
27.5°	303.6	300.8	300.8	300.8	300.8	297.9	297.9	297.9	297.9	297.9	297.9
30°	295.1	292.2	289.4	286.6	286.6	283.7	280.9	280.9	280.9	280.9	280.9
32.5°	292.2	286.6	280.9	278.1	278.1	275.2	272.4	269.6	269.6	266.7	263.9
35°	261.0	258.2	258.2	255.4	252.5	249.7	246.9	246.9	246.9	244.0	244.0
37.5°	227.0	229.8	229.8	229.8	232.7	232.7	232.7	232.7	235.5	235.5	235.5
40°	212.8	212.8	212.8	215.6	218.5	218.5	221.3	221.3	224.2	224.2	224.2
42.5°	201.5	198.6	198.6	201.5	201.5	204.3	204.3	207.1	210.0	210.0	212.8
45°	195.8	192.9	192.9	192.9	192.9	190.1	190.1	192.9	195.8	198.6	201.5
47.5°	184.4	184.4	181.6	181.6	181.6	181.6	181.6	181.6	184.4	184.4	184.4
50°	178.8	178.8	175.9	175.9	175.9	175.9	175.9	175.9	175.9	175.9	175.9
52.5°	173.1	170.2	170.2	170.2	170.2	167.4	167.4	167.4	167.4	167.4	167.4
55°	164.6	161.7	161.7	161.7	161.7	161.7	161.7	161.7	164.6	164.6	164.6
57.5°	156.1	153.2	153.2	153.2	156.1	156.1	156.1	156.1	158.9	158.9	158.9
60°	147.5	147.5	147.5	147.5	147.5	147.5	147.5	150.4	150.4	153.2	153.2
62.5°	139.0	139.0	139.0	139.0	141.9	141.9	141.9	141.9	144.7	144.7	144.7
65°	130.5	130.5	130.5	130.5	133.4	133.4	133.4	133.4	133.4	133.4	133.4
67.5°	122.0	122.0	122.0	122.0	122.0	122.0	122.0	124.8	124.8	127.7	127.7
70°	110.7	107.8	107.8	110.7	110.7	113.5	113.5	116.3	116.3	119.2	119.2
72.5°	99.3	99.3	99.3	99.3	99.3	99.3	99.3	102.1	105.0	105.0	107.8
75°	88.0	88.0	88.0	88.0	90.8	90.8	90.8	93.6	93.6	96.5	96.5
77.5°	79.4	76.6	76.6	76.6	79.4	79.4	79.4	82.3	82.3	85.1	85.1
80°	65.3	65.3	65.3	65.3	68.1	68.1	68.1	68.1	70.9	70.9	70.9
82.5°	53.9	53.9	53.9	53.9	53.9	53.9	53.9	53.9	56.7	56.7	56.7
85°	39.7	39.7	39.7	39.7	42.6	42.6	42.6	42.6	42.6	42.6	42.6
87.5°	25.5	25.5	25.5	25.5	25.5	25.5	25.5	25.5	28.4	28.4	28.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060
 CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9
2.5°	1804.6	1804.6	1804.6	1804.6	1810.2	1813.1	1818.8	1821.6	1818.8	1815.9	1810.2
5°	1518.0	1520.8	1520.8	1523.7	1523.7	1523.7	1523.7	1523.7	1529.3	1535.0	1540.7
7.5°	1200.2	1203.0	1205.9	1208.7	1208.7	1208.7	1205.9	1205.9	1208.7	1208.7	1211.6
10°	919.3	930.7	939.2	947.7	942.0	933.5	927.8	919.3	919.3	919.3	916.5
12.5°	695.2	698.0	703.7	706.5	703.7	703.7	700.8	698.0	700.8	706.5	709.3
15°	550.5	550.5	553.3	553.3	556.1	559.0	559.0	561.8	567.5	570.3	576.0
17.5°	456.8	459.7	459.7	462.5	462.5	465.3	465.3	465.3	471.0	476.7	485.2
20°	411.4	411.4	411.4	411.4	411.4	408.6	408.6	405.7	408.6	414.3	417.1
22.5°	368.9	371.7	371.7	371.7	368.9	366.0	360.3	357.5	357.5	360.3	360.3
25°	323.5	320.6	320.6	317.8	317.8	320.6	320.6	320.6	323.5	323.5	326.3
27.5°	297.9	295.1	295.1	292.2	292.2	295.1	295.1	295.1	295.1	295.1	295.1
30°	278.1	278.1	275.2	272.4	275.2	275.2	278.1	278.1	280.9	280.9	283.7
32.5°	263.9	261.0	261.0	258.2	261.0	261.0	263.9	263.9	266.7	269.6	269.6
35°	244.0	244.0	244.0	244.0	244.0	244.0	241.2	241.2	241.2	241.2	241.2
37.5°	232.7	232.7	229.8	227.0	227.0	227.0	227.0	227.0	224.2	221.3	218.5
40°	224.2	221.3	221.3	218.5	215.6	215.6	212.8	210.0	210.0	207.1	207.1
42.5°	212.8	210.0	210.0	207.1	204.3	204.3	201.5	198.6	198.6	198.6	195.8
45°	198.6	198.6	195.8	192.9	192.9	192.9	190.1	190.1	190.1	190.1	187.3
47.5°	184.4	184.4	181.6	181.6	181.6	181.6	178.8	178.8	178.8	178.8	178.8
50°	175.9	175.9	175.9	175.9	175.9	175.9	173.1	173.1	173.1	173.1	173.1
52.5°	167.4	167.4	167.4	167.4	167.4	167.4	167.4	167.4	167.4	167.4	167.4
55°	164.6	164.6	164.6	164.6	164.6	164.6	161.7	161.7	161.7	164.6	164.6
57.5°	158.9	158.9	156.1	156.1	156.1	156.1	156.1	156.1	156.1	156.1	156.1
60°	153.2	153.2	153.2	153.2	153.2	153.2	153.2	153.2	153.2	153.2	153.2
62.5°	144.7	144.7	144.7	144.7	144.7	147.5	147.5	147.5	147.5	147.5	144.7
65°	133.4	136.2	136.2	136.2	136.2	136.2	136.2	136.2	136.2	136.2	136.2
67.5°	127.7	127.7	127.7	127.7	127.7	127.7	127.7	127.7	127.7	127.7	127.7
70°	119.2	119.2	116.3	116.3	116.3	119.2	119.2	119.2	119.2	119.2	119.2
72.5°	107.8	107.8	107.8	107.8	107.8	107.8	107.8	107.8	107.8	110.7	110.7
75°	96.5	96.5	96.5	96.5	96.5	96.5	96.5	96.5	96.5	96.5	96.5
77.5°	85.1	85.1	82.3	82.3	82.3	85.1	85.1	85.1	85.1	88.0	88.0
80°	70.9	70.9	70.9	70.9	70.9	70.9	70.9	70.9	70.9	73.8	73.8
82.5°	56.7	56.7	56.7	56.7	56.7	56.7	56.7	56.7	56.7	59.6	59.6
85°	42.6	45.4	45.4	45.4	45.4	45.4	45.4	45.4	45.4	48.2	48.2
87.5°	28.4	28.4	28.4	28.4	28.4	28.4	25.5	25.5	25.5	25.5	22.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060
 CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9
2.5°	1807.4	1810.2	1813.1	1813.1	1815.9	1818.8	1818.8	1830.1	1841.5	1847.1	1852.8
5°	1546.4	1543.5	1543.5	1540.7	1537.9	1546.4	1554.9	1571.9	1588.9	1591.8	1597.4
7.5°	1211.6	1214.4	1217.2	1217.2	1220.1	1211.6	1200.2	1203.0	1205.9	1220.1	1231.4
10°	916.5	919.3	922.1	922.1	925.0	922.1	916.5	925.0	933.5	944.8	959.0
12.5°	712.2	720.7	729.2	734.9	743.4	749.1	751.9	763.3	771.8	786.0	800.1
15°	581.7	587.3	593.0	598.7	604.4	610.0	615.7	627.1	638.4	655.4	672.5
17.5°	490.9	490.9	493.7	493.7	493.7	499.4	505.1	510.7	513.6	530.6	547.6
20°	419.9	417.1	414.3	411.4	408.6	414.3	417.1	419.9	422.8	434.1	442.6
22.5°	360.3	360.3	363.2	363.2	363.2	360.3	354.7	357.5	357.5	363.2	371.7
25°	326.3	326.3	326.3	323.5	323.5	326.3	329.1	329.1	326.3	329.1	332.0
27.5°	295.1	297.9	297.9	300.8	300.8	303.6	303.6	303.6	303.6	306.4	309.3
30°	283.7	283.7	286.6	286.6	286.6	289.4	292.2	292.2	292.2	295.1	300.8
32.5°	272.4	275.2	278.1	280.9	283.7	286.6	286.6	289.4	289.4	292.2	295.1
35°	241.2	238.3	238.3	235.5	232.7	232.7	232.7	232.7	229.8	232.7	232.7
37.5°	215.6	215.6	215.6	212.8	212.8	215.6	215.6	215.6	215.6	218.5	218.5
40°	204.3	204.3	204.3	204.3	204.3	204.3	204.3	207.1	207.1	210.0	212.8
42.5°	195.8	195.8	195.8	195.8	195.8	198.6	198.6	198.6	198.6	201.5	201.5
45°	187.3	187.3	187.3	187.3	187.3	187.3	187.3	190.1	190.1	192.9	195.8
47.5°	178.8	178.8	178.8	178.8	178.8	181.6	184.4	184.4	184.4	187.3	187.3
50°	173.1	173.1	173.1	173.1	173.1	175.9	175.9	178.8	178.8	181.6	184.4
52.5°	167.4	167.4	167.4	167.4	167.4	170.2	170.2	173.1	173.1	175.9	178.8
55°	164.6	164.6	164.6	161.7	161.7	164.6	164.6	167.4	167.4	170.2	170.2
57.5°	156.1	156.1	156.1	156.1	156.1	156.1	156.1	158.9	158.9	161.7	164.6
60°	153.2	153.2	150.4	150.4	147.5	150.4	150.4	153.2	153.2	156.1	156.1
62.5°	144.7	144.7	144.7	141.9	141.9	144.7	144.7	144.7	144.7	147.5	150.4
65°	136.2	136.2	136.2	133.4	133.4	136.2	136.2	136.2	136.2	139.0	141.9
67.5°	127.7	127.7	127.7	124.8	124.8	124.8	124.8	127.7	127.7	130.5	133.4
70°	119.2	119.2	119.2	116.3	116.3	116.3	113.5	116.3	119.2	122.0	122.0
72.5°	110.7	110.7	110.7	107.8	107.8	107.8	105.0	107.8	107.8	110.7	110.7
75°	96.5	96.5	96.5	96.5	96.5	96.5	93.6	93.6	93.6	96.5	96.5
77.5°	88.0	88.0	88.0	85.1	85.1	85.1	82.3	82.3	82.3	85.1	85.1
80°	73.8	73.8	73.8	70.9	70.9	70.9	68.1	68.1	68.1	70.9	70.9
82.5°	59.6	59.6	59.6	56.7	56.7	56.7	53.9	53.9	53.9	56.7	56.7
85°	48.2	48.2	48.2	48.2	48.2	48.2	45.4	45.4	45.4	48.2	51.1
87.5°	22.7	22.7	25.5	25.5	25.5	25.5	22.7	22.7	19.9	19.9	22.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060
 CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9
2.5°	1858.5	1864.2	1878.3	1889.7	1903.9	1915.2	1923.7	1935.1	1943.6	1952.1	1957.8
5°	1600.3	1603.1	1617.3	1631.5	1642.8	1657.0	1676.9	1696.7	1716.6	1736.5	1750.7
7.5°	1245.6	1257.0	1274.0	1293.8	1310.9	1327.9	1347.8	1370.5	1390.3	1410.2	1430.0
10°	970.4	981.7	998.8	1015.8	1030.0	1047.0	1069.7	1092.4	1115.1	1137.8	1160.5
12.5°	814.3	828.5	848.4	868.2	885.3	905.1	933.5	959.0	987.4	1012.9	1041.3
15°	686.6	703.7	729.2	757.6	783.1	808.7	837.0	865.4	890.9	919.3	947.7
17.5°	564.6	581.7	604.4	629.9	652.6	675.3	709.3	740.6	774.6	805.8	837.0
20°	454.0	462.5	485.2	507.9	530.6	553.3	578.8	604.4	629.9	655.4	695.2
22.5°	377.4	383.0	394.4	402.9	414.3	422.8	448.3	473.8	496.5	522.1	559.0
25°	332.0	334.8	343.3	349.0	357.5	363.2	380.2	394.4	411.4	425.6	459.7
27.5°	309.3	312.1	314.9	317.8	320.6	323.5	334.8	346.2	354.7	366.0	397.2
30°	303.6	306.4	314.9	320.6	329.1	334.8	340.5	346.2	351.8	357.5	377.4
32.5°	297.9	300.8	300.8	297.9	297.9	295.1	300.8	303.6	309.3	312.1	329.1
35°	235.5	235.5	238.3	241.2	244.0	246.9	255.4	261.0	269.6	275.2	289.4
37.5°	221.3	221.3	224.2	229.8	232.7	235.5	241.2	246.9	252.5	258.2	272.4
40°	212.8	215.6	218.5	221.3	224.2	227.0	232.7	235.5	241.2	244.0	255.4
42.5°	204.3	204.3	207.1	212.8	215.6	218.5	224.2	227.0	232.7	235.5	246.9
45°	198.6	201.5	204.3	207.1	207.1	210.0	215.6	221.3	224.2	229.8	241.2
47.5°	190.1	190.1	195.8	198.6	204.3	207.1	212.8	215.6	221.3	224.2	235.5
50°	184.4	187.3	192.9	195.8	201.5	204.3	212.8	218.5	227.0	232.7	238.3
52.5°	178.8	181.6	187.3	190.1	195.8	198.6	210.0	221.3	229.8	241.2	241.2
55°	173.1	173.1	178.8	187.3	192.9	198.6	204.3	212.8	218.5	224.2	224.2
57.5°	164.6	167.4	173.1	181.6	187.3	192.9	198.6	204.3	207.1	212.8	210.0
60°	158.9	158.9	167.4	175.9	184.4	192.9	192.9	192.9	190.1	190.1	190.1
62.5°	150.4	153.2	164.6	178.8	190.1	201.5	192.9	184.4	175.9	167.4	170.2
65°	144.7	147.5	153.2	161.7	167.4	173.1	167.4	164.6	158.9	153.2	156.1
67.5°	133.4	136.2	139.0	139.0	141.9	141.9	141.9	141.9	141.9	141.9	144.7
70°	124.8	124.8	124.8	127.7	127.7	127.7	127.7	127.7	127.7	127.7	130.5
72.5°	113.5	113.5	113.5	113.5	113.5	113.5	113.5	113.5	113.5	113.5	116.3
75°	99.3	99.3	99.3	99.3	99.3	99.3	99.3	99.3	99.3	99.3	102.1
77.5°	88.0	88.0	88.0	88.0	88.0	88.0	88.0	88.0	85.1	85.1	88.0
80°	73.8	73.8	73.8	73.8	70.9	70.9	70.9	70.9	70.9	70.9	73.8
82.5°	59.6	59.6	59.6	59.6	56.7	56.7	56.7	56.7	53.9	53.9	56.7
85°	53.9	56.7	56.7	59.6	59.6	59.6	56.7	53.9	51.1	48.2	48.2
87.5°	22.7	22.7	22.7	22.7	19.9	19.9	19.9	19.9	19.9	19.9	19.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9
2.5°	1966.3	1972.0	1977.6	1986.2	1997.5	2006.0	2014.5	2031.6	2051.4	2068.4	2085.5
5°	1764.8	1779.0	1793.2	1810.2	1827.3	1841.5	1858.5	1892.5	1926.6	1957.8	1991.8
7.5°	1447.1	1466.9	1483.9	1512.3	1537.9	1566.2	1591.8	1634.3	1674.1	1716.6	1756.3
10°	1183.2	1205.9	1228.6	1265.5	1305.2	1342.1	1379.0	1413.0	1449.9	1483.9	1518.0
12.5°	1069.7	1095.2	1123.6	1146.3	1171.8	1194.5	1217.2	1257.0	1296.7	1336.4	1376.1
15°	976.1	1004.4	1032.8	1061.2	1086.7	1115.1	1140.6	1174.7	1211.6	1245.6	1279.7
17.5°	868.2	896.6	927.8	959.0	990.2	1021.5	1052.7	1100.9	1149.1	1194.5	1242.8
20°	732.0	771.8	808.7	851.2	893.8	936.3	978.9	1030.0	1081.0	1129.3	1180.3
22.5°	595.8	632.7	669.6	720.7	771.8	820.0	871.1	939.2	1004.4	1072.5	1137.8
25°	496.5	530.6	564.6	621.4	675.3	732.0	786.0	868.2	947.7	1030.0	1109.4
27.5°	428.4	459.7	490.9	550.5	610.0	666.8	726.4	817.2	905.1	995.9	1083.9
30°	397.2	417.1	437.0	493.7	550.5	604.4	661.1	749.1	837.0	925.0	1012.9
32.5°	346.2	363.2	380.2	431.3	482.4	530.6	581.7	672.5	760.4	851.2	939.2
35°	306.4	320.6	334.8	383.0	428.4	476.7	522.1	612.9	703.7	794.5	885.3
37.5°	283.7	297.9	309.3	351.8	397.2	439.8	482.4	573.1	661.1	751.9	839.9
40°	266.7	275.2	286.6	329.1	368.9	411.4	451.1	533.4	618.5	700.8	783.1
42.5°	255.4	266.7	275.2	312.1	351.8	388.7	425.6	505.1	584.5	661.1	740.6
45°	252.5	263.9	275.2	306.4	337.6	366.0	397.2	473.8	550.5	627.1	703.7
47.5°	246.9	255.4	266.7	292.2	314.9	340.5	363.2	439.8	516.4	590.2	666.8
50°	244.0	246.9	252.5	275.2	297.9	320.6	343.3	419.9	496.5	573.1	649.8
52.5°	241.2	241.2	241.2	261.0	280.9	297.9	317.8	394.4	473.8	550.5	627.1
55°	224.2	221.3	221.3	241.2	258.2	278.1	295.1	371.7	448.3	522.1	598.7
57.5°	207.1	204.3	201.5	218.5	235.5	252.5	269.6	346.2	425.6	502.2	578.8
60°	190.1	187.3	187.3	204.3	218.5	235.5	249.7	329.1	405.7	485.2	561.8
62.5°	170.2	173.1	173.1	187.3	204.3	218.5	232.7	312.1	394.4	473.8	553.3
65°	156.1	158.9	158.9	175.9	192.9	210.0	227.0	303.6	383.0	459.7	536.3
67.5°	144.7	147.5	147.5	167.4	184.4	204.3	221.3	289.4	360.3	428.4	496.5
70°	133.4	133.4	136.2	156.1	175.9	195.8	215.6	275.2	334.8	391.6	451.1
72.5°	119.2	122.0	124.8	144.7	161.7	181.6	198.6	252.5	306.4	360.3	414.3
75°	105.0	107.8	110.7	127.7	144.7	161.7	178.8	229.8	278.1	329.1	377.4
77.5°	93.6	96.5	99.3	113.5	127.7	141.9	156.1	192.9	232.7	269.6	306.4
80°	76.6	76.6	79.4	90.8	102.1	110.7	122.0	147.5	173.1	195.8	221.3
82.5°	56.7	59.6	59.6	68.1	73.8	82.3	88.0	102.1	113.5	127.7	139.0
85°	48.2	45.4	45.4	51.1	53.9	59.6	62.4	70.9	76.6	85.1	90.8
87.5°	19.9	17.0	17.0	19.9	25.5	28.4	31.2	31.2	34.0	34.0	34.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060
 CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9
2.5°	2094.0	2099.7	2108.2	2113.8	2128.0	2139.4	2153.6	2164.9	2173.4	2187.6	2181.9
5°	2017.4	2042.9	2068.4	2094.0	2113.8	2133.7	2150.7	2170.6	2193.3	2235.9	2247.2
7.5°	1790.4	1824.4	1855.6	1889.7	1929.4	1969.1	2008.9	2048.6	2085.5	2139.4	2173.4
10°	1566.2	1614.5	1659.9	1708.1	1745.0	1781.9	1815.9	1852.8	1903.9	1957.8	2020.2
12.5°	1424.4	1472.6	1520.8	1569.1	1623.0	1674.1	1728.0	1779.0	1827.3	1869.8	1940.8
15°	1330.7	1384.6	1435.7	1486.8	1552.0	1614.5	1679.7	1742.1	1813.1	1869.8	1918.1
17.5°	1308.0	1373.3	1435.7	1501.0	1569.1	1637.2	1705.3	1773.4	1844.3	1929.4	1991.8
20°	1268.3	1356.3	1444.2	1532.2	1620.1	1705.3	1793.2	1878.3	1972.0	2074.1	2102.5
22.5°	1245.6	1350.6	1458.4	1563.4	1682.6	1804.6	1923.7	2042.9	2142.2	2218.8	2303.9
25°	1242.8	1373.3	1506.6	1637.2	1787.5	1935.1	2085.5	2233.0	2360.7	2437.3	2505.4
27.5°	1239.9	1398.8	1554.9	1710.9	1895.4	2077.0	2261.4	2443.0	2562.1	2672.8	2729.6
30°	1205.9	1396.0	1588.9	1779.0	1986.2	2193.3	2400.4	2607.5	2729.6	2806.2	2834.5
32.5°	1163.3	1387.5	1611.6	1835.8	2071.3	2306.8	2539.4	2775.0	2871.4	2936.7	2914.0
35°	1129.3	1376.1	1620.1	1864.2	2113.8	2366.4	2616.1	2865.7	3004.8	3095.6	3058.7
37.5°	1098.1	1356.3	1614.5	1872.7	2164.9	2457.2	2749.4	3041.7	3175.0	3271.5	3228.9
40°	1061.2	1336.4	1614.5	1889.7	2224.5	2556.5	2891.3	3223.3	3396.3	3478.6	3413.4
42.5°	1030.0	1316.5	1606.0	1892.5	2250.0	2607.5	2965.1	3322.6	3515.5	3631.8	3549.6
45°	990.2	1276.8	1560.6	1847.1	2241.5	2635.9	3027.5	3421.9	3646.0	3736.8	3623.3
47.5°	947.7	1231.4	1512.3	1793.2	2213.2	2633.1	3053.0	3472.9	3680.1	3787.9	3682.9
50°	933.5	1217.2	1498.1	1781.9	2235.9	2692.7	3146.6	3600.6	3751.0	3839.0	3699.9
52.5°	930.7	1231.4	1535.0	1835.8	2292.6	2746.6	3203.4	3657.4	3779.4	3873.0	3748.2
55°	922.1	1248.4	1571.9	1895.4	2372.0	2851.6	3328.2	3804.9	3926.9	3995.0	3901.4
57.5°	930.7	1282.5	1631.5	1983.3	2474.2	2965.1	3455.9	3946.8	4094.3	4142.6	4122.7
60°	936.3	1310.9	1682.6	2057.1	2536.6	3016.1	3495.6	3975.2	4128.4	4247.5	4270.2
62.5°	922.1	1291.0	1657.0	2025.9	2460.0	2894.1	3328.2	3762.4	4014.9	4190.8	4292.9
65°	879.6	1220.1	1563.4	1903.9	2303.9	2706.9	3106.9	3507.0	3773.7	4034.7	4117.0
67.5°	786.0	1075.4	1364.8	1654.2	2003.2	2352.2	2698.3	3047.3	3382.1	3634.7	3748.2
70°	681.0	908.0	1137.8	1364.8	1682.6	2000.3	2318.1	2635.9	2931.0	3209.1	3316.9
72.5°	593.0	768.9	947.7	1123.6	1350.6	1574.7	1801.7	2025.9	2374.9	2652.9	2757.9
75°	505.1	632.7	757.6	885.3	1041.3	1197.4	1350.6	1506.6	1753.5	2003.2	2108.2
77.5°	388.7	473.8	556.1	638.4	746.2	851.2	959.0	1064.0	1237.1	1424.4	1478.3
80°	269.6	317.8	363.2	411.4	496.5	581.7	666.8	751.9	865.4	970.4	1052.7
82.5°	167.4	198.6	227.0	255.4	323.5	391.6	456.8	524.9	570.3	576.0	658.3
85°	107.8	127.7	144.7	161.7	201.5	244.0	283.7	323.5	289.4	269.6	320.6
87.5°	42.6	53.9	62.4	70.9	68.1	65.3	62.4	59.6	51.1	45.4	56.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060
 CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9
2.5°	2187.6	2196.1	2204.6	2210.3	2218.8	2221.7	2224.5	2224.5	2227.3	2230.2	2235.9
5°	2292.6	2309.6	2326.6	2340.8	2357.9	2372.0	2383.4	2397.6	2408.9	2408.9	2406.1
7.5°	2204.6	2247.2	2289.8	2332.3	2374.9	2406.1	2434.5	2465.7	2494.1	2499.7	2505.4
10°	2088.3	2133.7	2176.3	2221.7	2264.2	2312.5	2357.9	2403.3	2451.5	2460.0	2471.4
12.5°	1980.5	2034.4	2088.3	2139.4	2193.3	2227.3	2261.4	2292.6	2326.6	2349.3	2372.0
15°	1977.6	2023.0	2068.4	2111.0	2156.4	2176.3	2196.1	2213.2	2233.0	2233.0	2235.9
17.5°	2042.9	2071.3	2099.7	2125.2	2153.6	2156.4	2162.1	2164.9	2167.8	2159.2	2150.7
20°	2170.6	2181.9	2193.3	2204.6	2216.0	2196.1	2179.1	2159.2	2139.4	2116.7	2096.8
22.5°	2357.9	2332.3	2306.8	2281.2	2255.7	2221.7	2184.8	2150.7	2113.8	2085.5	2057.1
25°	2533.8	2502.6	2471.4	2440.1	2408.9	2335.2	2261.4	2184.8	2111.0	2079.8	2048.6
27.5°	2769.3	2721.0	2672.8	2624.6	2576.3	2477.0	2377.7	2278.4	2179.1	2125.2	2074.1
30°	2826.0	2772.1	2718.2	2661.5	2607.5	2511.1	2417.4	2321.0	2224.5	2162.1	2102.5
32.5°	2908.3	2845.9	2783.5	2721.0	2658.6	2565.0	2471.4	2374.9	2281.2	2224.5	2164.9
35°	3044.5	2973.6	2902.6	2828.9	2757.9	2661.5	2567.8	2471.4	2374.9	2309.6	2247.2
37.5°	3160.8	3078.6	2996.3	2914.0	2831.7	2746.6	2658.6	2573.5	2485.5	2420.3	2357.9
40°	3291.4	3200.6	3109.8	3021.8	2931.0	2851.6	2772.1	2689.8	2610.4	2559.3	2508.2
42.5°	3404.8	3294.2	3186.4	3078.6	2967.9	2914.0	2862.9	2809.0	2755.1	2729.6	2701.2
45°	3484.3	3382.1	3277.2	3175.0	3072.9	3033.2	2993.4	2953.7	2914.0	2939.5	2965.1
47.5°	3518.3	3436.1	3356.6	3277.2	3194.9	3209.1	3223.3	3234.6	3248.8	3282.8	3319.7
50°	3549.6	3504.2	3455.9	3410.5	3362.3	3416.2	3467.3	3521.2	3575.1	3646.0	3717.0
52.5°	3612.0	3586.4	3563.7	3538.2	3512.7	3606.3	3699.9	3793.6	3887.2	3966.6	4046.1
55°	3799.2	3779.4	3759.5	3736.8	3717.0	3850.3	3980.8	4114.2	4247.5	4329.8	4412.1
57.5°	4057.4	4046.1	4031.9	4020.6	4006.4	4136.9	4264.6	4392.3	4522.8	4602.2	4684.5
60°	4253.2	4256.1	4256.1	4258.9	4258.9	4358.2	4457.5	4559.7	4659.0	4727.1	4798.0
62.5°	4358.2	4352.5	4346.9	4341.2	4335.5	4417.8	4500.1	4582.4	4664.6	4715.7	4766.8
65°	4244.7	4275.9	4307.1	4338.3	4369.6	4380.9	4389.4	4400.8	4409.3	4440.5	4471.7
67.5°	3864.5	3926.9	3986.5	4048.9	4108.5	4066.0	4026.2	3983.7	3941.1	3949.6	3955.3
70°	3441.7	3512.7	3586.4	3657.4	3728.3	3629.0	3529.7	3427.5	3328.2	3294.2	3260.1
72.5°	2902.6	2965.1	3030.3	3092.7	3155.2	3033.2	2914.0	2792.0	2670.0	2610.4	2550.8
75°	2218.8	2292.6	2369.2	2443.0	2516.8	2380.6	2241.5	2105.3	1966.3	1926.6	1889.7
77.5°	1617.3	1705.3	1793.2	1881.2	1969.1	1847.1	1725.1	1600.3	1478.3	1455.6	1432.9
80°	1177.5	1245.6	1310.9	1379.0	1444.2	1373.3	1302.4	1231.4	1160.5	1157.6	1154.8
82.5°	794.5	854.0	910.8	970.4	1027.1	998.8	973.2	944.8	916.5	944.8	976.1
85°	408.6	490.9	576.0	658.3	740.6	732.0	726.4	717.9	709.3	746.2	780.3
87.5°	82.3	153.2	224.2	292.2	363.2	346.2	329.1	309.3	292.2	303.6	312.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060
 CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9
2.5°	2238.7	2241.5	2241.5	2241.5	2241.5	2241.5	2235.9	2233.0	2227.3	2221.7	2213.2
5°	2406.1	2403.3	2391.9	2380.6	2366.4	2355.0	2346.5	2335.2	2326.6	2315.3	2298.3
7.5°	2511.1	2516.8	2496.9	2479.9	2460.0	2440.1	2420.3	2400.4	2380.6	2360.7	2321.0
10°	2479.9	2488.4	2477.0	2465.7	2451.5	2440.1	2417.4	2391.9	2369.2	2343.7	2295.4
12.5°	2391.9	2414.6	2408.9	2403.3	2397.6	2391.9	2377.7	2360.7	2346.5	2329.5	2275.6
15°	2235.9	2235.9	2238.7	2241.5	2241.5	2244.4	2247.2	2250.0	2252.9	2255.7	2224.5
17.5°	2142.2	2133.7	2133.7	2133.7	2133.7	2133.7	2145.1	2159.2	2170.6	2181.9	2173.4
20°	2074.1	2054.3	2051.4	2051.4	2048.6	2045.7	2065.6	2088.3	2108.2	2128.0	2139.4
22.5°	2028.7	2000.3	1997.5	1994.7	1991.8	1989.0	2014.5	2040.1	2065.6	2091.1	2130.9
25°	2017.4	1986.2	1989.0	1991.8	1991.8	1994.7	2014.5	2034.4	2054.3	2074.1	2142.2
27.5°	2020.2	1969.1	1972.0	1974.8	1974.8	1977.6	2008.9	2037.2	2068.4	2096.8	2181.9
30°	2040.1	1980.5	1974.8	1969.1	1963.5	1957.8	2000.3	2042.9	2085.5	2128.0	2193.3
32.5°	2108.2	2051.4	2037.2	2023.0	2008.9	1994.7	2045.7	2094.0	2145.1	2193.3	2247.2
35°	2181.9	2119.5	2113.8	2108.2	2099.7	2094.0	2139.4	2187.6	2233.0	2278.4	2326.6
37.5°	2292.6	2230.2	2224.5	2216.0	2210.3	2201.8	2252.9	2301.1	2352.2	2400.4	2443.0
40°	2457.2	2406.1	2403.3	2403.3	2400.4	2397.6	2437.3	2479.9	2519.6	2559.3	2587.7
42.5°	2675.6	2650.1	2658.6	2670.0	2678.5	2687.0	2718.2	2752.3	2783.5	2814.7	2806.2
45°	2990.6	3016.1	3019.0	3021.8	3024.6	3027.5	3036.0	3047.3	3055.9	3064.4	3030.3
47.5°	3353.8	3387.8	3404.8	3421.9	3436.1	3453.1	3441.7	3427.5	3416.2	3402.0	3316.9
50°	3785.1	3856.0	3853.2	3850.3	3844.6	3841.8	3819.1	3796.4	3770.9	3748.2	3623.3
52.5°	4125.5	4205.0	4219.2	4233.4	4247.5	4261.7	4219.2	4176.6	4131.2	4088.7	3932.6
55°	4491.6	4573.8	4576.7	4579.5	4579.5	4582.4	4522.8	4463.2	4400.8	4341.2	4179.5
57.5°	4764.0	4843.4	4834.9	4829.2	4820.7	4812.2	4741.3	4670.3	4599.4	4528.4	4366.7
60°	4866.1	4934.2	4917.2	4900.1	4880.3	4863.3	4809.3	4755.4	4698.7	4644.8	4488.7
62.5°	4817.9	4868.9	4843.4	4820.7	4795.2	4769.6	4701.5	4630.6	4562.5	4491.6	4378.1
65°	4500.1	4531.3	4497.2	4466.0	4434.8	4400.8	4344.0	4287.3	4227.7	4170.9	4094.3
67.5°	3963.8	3969.5	3966.6	3963.8	3961.0	3958.1	3875.9	3793.6	3708.4	3626.2	3620.5
70°	3228.9	3194.9	3200.6	3209.1	3214.7	3220.4	3158.0	3098.4	3036.0	2973.6	3001.9
72.5°	2491.2	2431.6	2445.8	2462.8	2477.0	2491.2	2440.1	2391.9	2340.8	2289.8	2329.5
75°	1850.0	1813.1	1827.3	1844.3	1858.5	1872.7	1852.8	1832.9	1810.2	1790.4	1827.3
77.5°	1410.2	1387.5	1390.3	1390.3	1393.2	1393.2	1396.0	1401.7	1404.5	1407.3	1447.1
80°	1149.1	1146.3	1143.5	1140.6	1134.9	1132.1	1160.5	1188.9	1217.2	1245.6	1265.5
82.5°	1004.4	1032.8	1015.8	1001.6	984.6	967.5	993.1	1018.6	1044.2	1069.7	1061.2
85°	817.2	851.2	820.0	788.8	754.7	723.5	746.2	766.1	788.8	808.7	797.3
87.5°	323.5	332.0	280.9	232.7	181.6	130.5	207.1	280.9	357.5	431.3	442.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060

CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9	2042.9
2.5°	2204.6	2193.3	2184.8	2181.9	2176.3	2173.4	2167.8	2162.1	2153.6	2147.9	2139.4
5°	2278.4	2261.4	2241.5	2213.2	2187.6	2159.2	2130.9	2105.3	2079.8	2051.4	2025.9
7.5°	2281.2	2241.5	2201.8	2164.9	2125.2	2088.3	2048.6	2014.5	1977.6	1940.8	1906.7
10°	2250.0	2201.8	2153.6	2105.3	2059.9	2011.7	1963.5	1923.7	1881.2	1838.6	1798.9
12.5°	2224.5	2170.6	2116.7	2059.9	2006.0	1949.3	1892.5	1852.8	1813.1	1773.4	1733.6
15°	2193.3	2159.2	2128.0	2077.0	2025.9	1974.8	1923.7	1869.8	1818.8	1764.8	1710.9
17.5°	2167.8	2159.2	2150.7	2116.7	2082.6	2045.7	2011.7	1957.8	1903.9	1847.1	1793.2
20°	2153.6	2164.9	2176.3	2159.2	2142.2	2122.4	2105.3	2065.6	2025.9	1983.3	1943.6
22.5°	2170.6	2213.2	2252.9	2255.7	2261.4	2264.2	2267.1	2230.2	2193.3	2153.6	2116.7
25°	2210.3	2278.4	2346.5	2383.4	2420.3	2460.0	2496.9	2474.2	2451.5	2428.8	2406.1
27.5°	2264.2	2349.3	2434.5	2488.4	2539.4	2593.4	2647.3	2644.4	2641.6	2635.9	2633.1
30°	2255.7	2321.0	2386.2	2451.5	2516.8	2582.0	2647.3	2681.3	2712.5	2746.6	2780.6
32.5°	2303.9	2357.9	2414.6	2482.7	2550.8	2621.7	2689.8	2760.8	2828.9	2899.8	2970.7
35°	2377.7	2426.0	2477.0	2550.8	2627.4	2701.2	2777.8	2862.9	2950.9	3038.8	3123.9
37.5°	2488.4	2530.9	2576.3	2638.8	2704.0	2766.4	2831.7	2956.5	3081.4	3209.1	3333.9
40°	2616.1	2644.4	2672.8	2732.4	2792.0	2851.6	2911.1	3067.2	3223.3	3379.3	3535.4
42.5°	2800.5	2792.0	2783.5	2831.7	2882.8	2931.0	2982.1	3123.9	3265.8	3407.7	3549.6
45°	2996.3	2962.2	2928.2	2950.9	2976.4	2999.1	3024.6	3169.3	3314.1	3461.6	3606.3
47.5°	3231.8	3146.6	3061.5	3041.7	3021.8	2999.1	2979.2	3135.3	3291.4	3450.2	3606.3
50°	3498.5	3370.8	3246.0	3194.9	3141.0	3089.9	3036.0	3163.7	3294.2	3424.7	3552.4
52.5°	3776.5	3617.7	3461.6	3382.1	3302.7	3220.4	3141.0	3248.8	3359.5	3470.1	3577.9
55°	4014.9	3853.2	3688.6	3595.0	3501.3	3407.7	3314.1	3421.9	3529.7	3637.5	3745.3
57.5°	4205.0	4043.3	3881.5	3793.6	3702.8	3614.8	3524.0	3626.2	3731.1	3836.1	3938.3
60°	4335.5	4179.5	4023.4	3938.3	3853.2	3768.0	3682.9	3804.9	3926.9	4051.8	4173.8
62.5°	4267.4	4153.9	4040.4	4003.5	3966.6	3926.9	3890.0	4006.4	4119.9	4236.2	4352.5
65°	4017.7	3941.1	3864.5	3901.4	3941.1	3978.0	4017.7	4094.3	4170.9	4250.4	4327.0
67.5°	3612.0	3606.3	3597.8	3680.1	3762.4	3847.5	3929.8	3980.8	4029.1	4080.1	4131.2
70°	3030.3	3061.5	3089.9	3231.8	3373.6	3515.5	3657.4	3677.2	3697.1	3717.0	3736.8
72.5°	2372.0	2411.8	2454.3	2641.6	2826.0	3013.3	3200.6	3189.2	3177.9	3163.7	3152.3
75°	1867.0	1903.9	1943.6	2116.7	2289.8	2462.8	2635.9	2587.7	2542.3	2494.1	2445.8
77.5°	1489.6	1529.3	1571.9	1733.6	1895.4	2059.9	2221.7	2105.3	1989.0	1872.7	1756.3
80°	1282.5	1302.4	1319.4	1430.0	1537.9	1648.5	1759.2	1640.0	1518.0	1396.0	1276.8
82.5°	1052.7	1041.3	1032.8	1098.1	1163.3	1228.6	1293.8	1180.3	1066.9	950.5	837.0
85°	786.0	774.6	763.3	797.3	831.4	868.2	902.3	771.8	641.2	507.9	377.4
87.5°	456.8	468.2	479.5	516.4	553.3	593.0	629.9	496.5	363.2	227.0	93.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060
 CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676060
 CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	2042.9	2042.9
2.5°	2122.4	2108.2
5°	2006.0	1986.2
7.5°	1878.3	1852.8
10°	1762.0	1728.0
12.5°	1688.2	1645.7
15°	1659.9	1608.8
17.5°	1745.0	1696.7
20°	1875.5	1810.2
22.5°	2034.4	1955.0
25°	2309.6	2213.2
27.5°	2533.8	2434.5
30°	2672.8	2565.0
32.5°	2826.0	2684.2
35°	2984.9	2848.7
37.5°	3177.9	3024.6
40°	3376.5	3217.6
42.5°	3444.6	3342.4
45°	3509.8	3413.4
47.5°	3524.0	3444.6
50°	3538.2	3526.9
52.5°	3577.9	3575.1
55°	3748.2	3751.0
57.5°	3958.1	3975.2
60°	4151.1	4131.2
62.5°	4250.4	4148.2
65°	4182.3	4040.4
67.5°	3978.0	3824.8
70°	3529.7	3322.6
72.5°	2970.7	2789.1
75°	2289.8	2136.5
77.5°	1628.7	1501.0
80°	1146.3	1018.6
82.5°	734.9	632.7
85°	332.0	289.4
87.5°	93.6	90.8
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P676060
CATALOG NUMBER: CCW-SA-2C-840-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)