

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P676065

Luminaire Tested: **CCW-SA-1C-850-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P676065
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-1C-850-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @615mA w/
SLR distribution lens
Light Source: (16) 5000K CCT, 80 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3274.1 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 32
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P676065

CATALOG NUMBER: CCW-SA-1C-850-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 4.6 fc

Type IV - Short - N/A

REPORT NUMBER: P676065
CATALOG NUMBER: CCW-SA-1C-850-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P676065

CATALOG NUMBER: CCW-SA-1C-850-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	673.7	0.0	673.7
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	2600.4	0.0	2600.4
	% Fixture	79.4	0.0	79.4
Total	Lumens	3274.1	0.0	3274.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	2.5
10°-20°	171.5	5.2
20°-30°	251.0	7.7
30°-40°	353.6	10.8
40°-50°	485.8	14.8
50°-60°	662.2	20.2
60°-70°	724.8	22.1
70°-80°	418.5	12.8
80°-90°	125.5	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3274.1	100.0
0°-180°	3274.1	100.0

Coefficient of Utilization



REPORT NUMBER: P676065


CATALOG NUMBER: CCW-SA-1C-850-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	336.3	10.3			
FM	(30°-60°)	1194.8	36.5			
FH	(60°-80°)	962.8	29.4			G1/1800
FVH	(80°-90°)	106.6	3.3			G2/225
BL	(0°-30°)	167.5	5.1	B1/500		
BM	(30°-60°)	306.8	9.4	B1/1000		
BH	(60°-80°)	180.5	5.5	B1/500		G1/500
BVH	(80°-90°)	18.9	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P676065

CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5
2.5°	1078.9	1073.1	1068.8	1064.4	1058.6	1054.2	1048.4	1042.6	1035.4	1029.6	1022.3
5°	1016.5	999.1	981.6	971.5	959.9	949.7	938.1	925.0	911.9	897.4	884.3
7.5°	948.2	926.5	904.7	887.2	868.4	850.9	832.1	816.1	800.1	784.1	768.2
10°	884.3	864.0	843.7	821.9	798.7	776.9	753.7	731.9	710.1	688.3	666.5
12.5°	842.2	817.5	794.3	769.6	746.4	721.7	697.0	676.7	656.4	634.6	614.2
15°	823.4	800.1	778.3	753.7	729.0	704.3	679.6	656.4	634.6	611.3	588.1
17.5°	868.4	835.0	801.6	769.6	737.7	705.7	673.8	644.7	615.7	586.7	557.6
20°	926.5	884.3	843.7	804.5	763.8	724.6	684.0	643.3	602.6	562.0	521.3
22.5°	1000.5	952.6	906.1	855.3	803.0	752.2	699.9	649.1	598.3	546.0	495.2
25°	1132.7	1076.0	1019.4	946.8	872.7	800.1	726.1	659.3	593.9	527.1	460.3
27.5°	1245.9	1169.0	1093.5	1006.3	919.2	832.1	744.9	668.0	592.5	515.5	438.5
30°	1312.7	1237.2	1161.7	1055.7	951.1	845.1	739.1	653.5	569.2	483.6	397.9
32.5°	1373.7	1289.5	1205.3	1089.1	971.5	855.3	737.7	643.3	550.4	456.0	361.6
35°	1457.9	1365.0	1273.5	1138.5	1003.4	868.4	733.3	636.0	537.3	440.0	341.2
37.5°	1548.0	1433.2	1320.0	1170.4	1020.8	871.3	721.7	625.9	530.0	434.2	338.3
40°	1646.7	1507.3	1369.4	1203.8	1039.7	874.2	708.6	612.8	517.0	419.7	323.8
42.5°	1710.6	1559.6	1408.6	1230.0	1052.8	874.2	695.6	601.2	506.8	411.0	316.6
45°	1746.9	1600.2	1455.0	1261.9	1068.8	875.6	682.5	589.6	496.6	402.2	309.3
47.5°	1762.9	1626.4	1489.9	1286.6	1084.7	881.4	678.1	583.8	487.9	393.5	297.7
50°	1805.0	1684.5	1563.9	1346.1	1129.8	911.9	694.1	592.5	492.3	390.6	289.0
52.5°	1829.7	1726.6	1623.5	1399.9	1176.2	952.6	729.0	615.7	502.4	389.2	275.9
55°	1919.7	1821.0	1722.2	1484.1	1244.5	1006.3	766.7	641.8	517.0	390.6	265.7
57.5°	2034.4	1929.9	1826.8	1569.7	1312.7	1055.7	798.7	665.1	530.0	396.4	261.4
60°	2114.3	2012.6	1912.5	1639.5	1365.0	1092.0	817.5	678.1	538.7	397.9	258.5
62.5°	2123.0	1992.3	1863.1	1597.3	1331.6	1064.4	798.7	663.6	528.6	392.1	257.0
65°	2067.8	1915.4	1762.9	1508.8	1254.6	1000.5	746.4	623.0	499.5	374.6	251.2
67.5°	1957.5	1778.9	1600.2	1367.9	1135.6	903.2	670.9	564.9	460.3	354.3	248.3
70°	1700.4	1543.6	1388.2	1186.4	986.0	784.1	582.3	495.2	409.5	322.4	235.2
72.5°	1427.4	1280.8	1135.6	971.5	808.8	644.7	480.7	415.3	350.0	283.2	217.8
75°	1093.5	983.1	874.2	752.2	630.2	506.8	384.8	336.9	289.0	241.1	193.1
77.5°	768.2	708.6	650.6	559.1	467.6	376.1	284.6	252.7	220.7	188.8	156.8
80°	521.3	487.9	456.0	390.6	325.3	258.5	193.1	172.8	151.0	130.7	108.9
82.5°	323.8	322.4	319.5	274.5	229.4	184.4	139.4	122.0	106.0	88.6	71.2
85°	148.1	172.8	196.0	171.4	146.7	122.0	97.3	85.7	74.1	61.0	49.4
87.5°	46.5	56.6	65.3	62.4	58.1	55.2	50.8	43.6	36.3	29.0	21.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065
 CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676065

CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5
2.5°	1016.5	1012.1	1006.3	1000.5	993.3	987.4	980.2	972.9	971.5	968.6	967.1
5°	875.6	866.9	856.8	848.0	839.3	829.2	820.5	810.3	803.0	794.3	787.1
7.5°	752.2	737.7	721.7	705.7	691.2	676.7	660.7	646.2	638.9	631.7	624.4
10°	653.5	638.9	625.9	611.3	601.2	592.5	582.3	572.1	563.4	554.7	546.0
12.5°	604.1	593.9	583.8	573.6	562.0	551.8	540.2	528.6	518.4	509.7	499.5
15°	573.6	559.1	543.1	528.6	512.6	498.1	482.1	466.1	454.5	444.4	432.7
17.5°	537.3	515.5	495.2	473.4	456.0	438.5	419.7	402.2	389.2	374.6	361.6
20°	496.6	471.9	445.8	421.1	400.8	381.9	361.6	341.2	326.7	310.8	296.2
22.5°	461.8	429.8	396.4	363.0	341.2	319.5	296.2	274.5	261.4	246.9	233.8
25°	424.0	389.2	352.9	316.6	294.8	271.5	249.8	226.5	216.4	207.7	197.5
27.5°	403.7	368.8	332.5	297.7	277.4	255.6	235.2	213.5	206.2	197.5	190.2
30°	363.0	329.6	294.8	259.9	245.4	232.3	217.8	203.3	200.4	198.9	196.0
32.5°	326.7	291.9	257.0	222.2	209.1	196.0	183.0	169.9	168.4	165.5	164.1
35°	307.9	274.5	239.6	206.2	194.6	181.5	169.9	156.8	153.9	149.6	146.7
37.5°	303.5	268.6	232.3	197.5	185.9	174.3	161.2	149.6	146.7	143.8	140.9
40°	291.9	258.5	226.5	193.1	181.5	169.9	156.8	145.2	142.3	139.4	136.5
42.5°	283.2	251.2	217.8	184.4	174.3	164.1	152.5	142.3	139.4	136.5	132.1
45°	275.9	242.5	207.7	174.3	167.0	159.7	151.0	143.8	140.9	136.5	133.6
47.5°	264.3	232.3	198.9	165.5	158.3	152.5	145.2	138.0	135.0	132.1	129.2
50°	255.6	222.2	188.8	155.4	149.6	143.8	138.0	132.1	132.1	133.6	133.6
52.5°	244.0	212.0	180.1	148.1	142.3	136.5	130.7	124.9	126.3	127.8	129.2
55°	233.8	203.3	171.4	139.4	133.6	127.8	120.5	114.7	116.2	117.6	119.1
57.5°	229.4	197.5	165.5	133.6	127.8	120.5	114.7	107.5	107.5	107.5	107.5
60°	226.5	193.1	161.2	127.8	120.5	114.7	107.5	100.2	98.7	98.7	97.3
62.5°	225.1	191.7	159.7	126.3	117.6	110.4	101.6	92.9	91.5	90.0	88.6
65°	219.3	188.8	156.8	124.9	114.7	106.0	95.8	85.7	84.2	84.2	82.8
67.5°	217.8	185.9	155.4	123.4	113.3	101.6	91.5	79.9	78.4	77.0	75.5
70°	206.2	178.6	149.6	120.5	108.9	98.7	87.1	75.5	74.1	71.2	69.7
72.5°	191.7	167.0	140.9	114.7	103.1	91.5	79.9	68.2	66.8	65.3	62.4
75°	169.9	146.7	123.4	100.2	90.0	81.3	71.2	61.0	59.5	58.1	55.2
77.5°	139.4	120.5	103.1	84.2	77.0	69.7	62.4	55.2	53.7	52.3	49.4
80°	98.7	87.1	77.0	65.3	61.0	55.2	50.8	45.0	45.0	43.6	43.6
82.5°	65.3	59.5	53.7	47.9	45.0	42.1	39.2	36.3	36.3	34.9	34.9
85°	46.5	43.6	39.2	36.3	34.9	31.9	30.5	27.6	27.6	27.6	27.6
87.5°	21.8	21.8	20.3	20.3	18.9	18.9	17.4	16.0	16.0	16.0	16.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065
 CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676065

CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5
2.5°	964.2	959.9	955.5	949.7	945.3	939.5	932.3	926.5	919.2	919.2	917.7
5°	778.3	774.0	769.6	763.8	759.5	753.7	749.3	743.5	737.7	737.7	736.2
7.5°	617.2	608.4	599.7	589.6	580.9	575.0	569.2	562.0	556.2	551.8	547.5
10°	537.3	528.6	518.4	509.7	499.5	492.3	485.0	476.3	469.0	463.2	457.4
12.5°	489.4	479.2	469.0	458.9	448.7	438.5	429.8	419.7	409.5	402.2	395.0
15°	421.1	411.0	400.8	390.6	380.5	368.8	357.2	344.2	332.5	326.7	322.4
17.5°	347.1	336.9	325.3	315.1	303.5	294.8	286.1	277.4	268.6	262.8	258.5
20°	280.3	268.6	257.0	245.4	233.8	228.0	222.2	216.4	210.6	206.2	203.3
22.5°	219.3	212.0	206.2	198.9	191.7	187.3	184.4	180.1	175.7	175.7	175.7
25°	187.3	183.0	180.1	175.7	171.4	169.9	168.4	165.5	164.1	162.6	162.6
27.5°	181.5	177.2	172.8	168.4	164.1	162.6	161.2	158.3	156.8	156.8	156.8
30°	193.1	191.7	190.2	188.8	187.3	184.4	180.1	177.2	172.8	169.9	167.0
32.5°	161.2	159.7	159.7	158.3	156.8	159.7	161.2	164.1	165.5	167.0	168.4
35°	142.3	139.4	136.5	133.6	130.7	129.2	127.8	126.3	124.9	124.9	123.4
37.5°	138.0	135.0	132.1	129.2	126.3	124.9	123.4	122.0	120.5	120.5	119.1
40°	133.6	130.7	129.2	126.3	123.4	122.0	120.5	117.6	116.2	114.7	114.7
42.5°	129.2	127.8	124.9	123.4	120.5	119.1	117.6	114.7	113.3	111.8	110.4
45°	129.2	126.3	123.4	120.5	117.6	116.2	113.3	111.8	108.9	108.9	107.5
47.5°	126.3	123.4	120.5	117.6	114.7	113.3	110.4	108.9	106.0	104.6	103.1
50°	133.6	129.2	123.4	119.1	113.3	111.8	108.9	107.5	104.6	103.1	101.6
52.5°	130.7	126.3	120.5	116.2	110.4	107.5	106.0	103.1	100.2	98.7	97.3
55°	120.5	116.2	113.3	108.9	104.6	101.6	98.7	95.8	92.9	91.5	91.5
57.5°	107.5	106.0	104.6	103.1	101.6	98.7	95.8	91.5	88.6	87.1	85.7
60°	95.8	97.3	98.7	100.2	101.6	97.3	92.9	88.6	84.2	82.8	81.3
62.5°	87.1	90.0	92.9	94.4	97.3	92.9	88.6	84.2	79.9	78.4	77.0
65°	81.3	82.8	82.8	84.2	84.2	81.3	79.9	77.0	74.1	72.6	72.6
67.5°	74.1	74.1	74.1	72.6	72.6	71.2	71.2	69.7	68.2	66.8	66.8
70°	66.8	66.8	66.8	65.3	65.3	63.9	63.9	62.4	61.0	61.0	59.5
72.5°	61.0	61.0	59.5	59.5	58.1	58.1	58.1	56.6	56.6	55.2	55.2
75°	53.7	53.7	52.3	52.3	50.8	50.8	50.8	49.4	49.4	49.4	47.9
77.5°	47.9	47.9	46.5	46.5	45.0	45.0	45.0	43.6	43.6	42.1	42.1
80°	42.1	42.1	40.7	40.7	39.2	39.2	37.8	37.8	36.3	36.3	34.9
82.5°	33.4	33.4	33.4	33.4	33.4	31.9	31.9	30.5	29.0	29.0	27.6
85°	27.6	27.6	27.6	26.1	26.1	26.1	24.7	24.7	23.2	21.8	21.8
87.5°	16.0	16.0	16.0	14.5	14.5	14.5	14.5	14.5	14.5	14.5	13.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065
 CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065

CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5
2.5°	917.7	916.3	910.5	904.7	910.5	916.3	916.3	916.3	914.8	914.8	914.8
5°	736.2	734.8	731.9	729.0	729.0	727.5	730.4	733.3	736.2	739.1	742.0
7.5°	541.6	537.3	532.9	528.6	531.5	532.9	537.3	540.2	544.5	547.5	554.7
10°	451.6	445.8	441.4	437.1	434.2	431.3	428.4	426.9	424.0	421.1	424.0
12.5°	386.3	379.0	371.7	363.0	361.6	360.1	357.2	354.3	351.4	348.5	347.1
15°	316.6	310.8	307.9	303.5	297.7	291.9	289.0	287.5	284.6	281.7	280.3
17.5°	252.7	246.9	242.5	238.1	236.7	233.8	233.8	233.8	233.8	233.8	233.8
20°	198.9	194.6	194.6	193.1	193.1	191.7	193.1	194.6	194.6	196.0	197.5
22.5°	174.3	174.3	172.8	171.4	172.8	172.8	174.3	175.7	177.2	178.6	180.1
25°	161.2	159.7	161.2	162.6	162.6	162.6	164.1	164.1	165.5	165.5	165.5
27.5°	155.4	155.4	156.8	156.8	158.3	158.3	158.3	156.8	156.8	155.4	155.4
30°	164.1	161.2	161.2	161.2	159.7	158.3	156.8	156.8	155.4	153.9	152.5
32.5°	169.9	171.4	169.9	167.0	165.5	162.6	161.2	158.3	156.8	153.9	151.0
35°	123.4	122.0	124.9	126.3	127.8	129.2	130.7	132.1	132.1	133.6	133.6
37.5°	119.1	117.6	117.6	116.2	116.2	116.2	116.2	116.2	114.7	114.7	116.2
40°	113.3	111.8	111.8	110.4	110.4	108.9	108.9	108.9	108.9	108.9	108.9
42.5°	108.9	107.5	107.5	107.5	107.5	106.0	106.0	104.6	104.6	103.1	103.1
45°	107.5	106.0	104.6	103.1	103.1	101.6	101.6	101.6	100.2	100.2	100.2
47.5°	101.6	100.2	100.2	98.7	98.7	97.3	97.3	97.3	95.8	95.8	95.8
50°	98.7	97.3	97.3	95.8	95.8	94.4	94.4	94.4	92.9	92.9	92.9
52.5°	94.4	92.9	92.9	92.9	91.5	90.0	90.0	90.0	88.6	88.6	88.6
55°	90.0	88.6	88.6	88.6	87.1	85.7	85.7	85.7	84.2	84.2	84.2
57.5°	84.2	82.8	82.8	81.3	81.3	81.3	81.3	81.3	79.9	79.9	79.9
60°	79.9	78.4	78.4	77.0	77.0	75.5	75.5	75.5	75.5	75.5	75.5
62.5°	75.5	74.1	72.6	71.2	72.6	72.6	72.6	72.6	71.2	71.2	71.2
65°	71.2	69.7	68.2	66.8	66.8	66.8	66.8	66.8	66.8	66.8	66.8
67.5°	65.3	63.9	62.4	61.0	62.4	62.4	62.4	62.4	62.4	62.4	62.4
70°	59.5	58.1	58.1	56.6	56.6	55.2	55.2	56.6	56.6	56.6	56.6
72.5°	53.7	52.3	52.3	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8
75°	47.9	46.5	46.5	45.0	45.0	45.0	45.0	45.0	45.0	45.0	45.0
77.5°	40.7	39.2	39.2	39.2	39.2	39.2	39.2	40.7	40.7	40.7	40.7
80°	34.9	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4
82.5°	27.6	26.1	26.1	26.1	26.1	26.1	26.1	26.1	26.1	26.1	26.1
85°	20.3	18.9	18.9	18.9	20.3	20.3	20.3	20.3	20.3	20.3	20.3
87.5°	13.1	11.6	11.6	11.6	13.1	13.1	13.1	13.1	11.6	11.6	11.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065
 CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065

CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5
2.5°	914.8	914.8	914.8	913.4	911.9	910.5	909.0	913.4	916.3	920.6	923.6
5°	743.5	746.4	747.8	752.2	756.6	760.9	765.3	768.2	771.1	772.5	775.4
7.5°	560.5	567.8	573.6	579.4	585.2	589.6	595.4	599.7	604.1	608.4	612.8
10°	425.5	428.4	429.8	435.6	440.0	445.8	450.2	454.5	458.9	461.8	466.1
12.5°	345.6	342.7	341.2	341.2	341.2	341.2	341.2	344.2	347.1	350.0	352.9
15°	278.8	277.4	275.9	274.5	273.0	270.1	268.6	271.5	274.5	277.4	280.3
17.5°	233.8	233.8	233.8	232.3	230.9	229.4	228.0	229.4	230.9	230.9	232.3
20°	200.4	201.8	203.3	204.7	204.7	206.2	206.2	207.7	209.1	209.1	210.6
22.5°	180.1	181.5	181.5	181.5	183.0	183.0	183.0	184.4	185.9	187.3	188.8
25°	164.1	164.1	162.6	162.6	164.1	164.1	164.1	164.1	165.5	165.5	165.5
27.5°	155.4	153.9	153.9	153.9	153.9	152.5	152.5	152.5	152.5	152.5	152.5
30°	151.0	149.6	148.1	146.7	146.7	145.2	143.8	143.8	143.8	143.8	143.8
32.5°	149.6	146.7	143.8	142.3	142.3	140.9	139.4	138.0	138.0	136.5	135.0
35°	133.6	132.1	132.1	130.7	129.2	127.8	126.3	126.3	126.3	124.9	124.9
37.5°	116.2	117.6	117.6	117.6	119.1	119.1	119.1	119.1	120.5	120.5	120.5
40°	108.9	108.9	108.9	110.4	111.8	111.8	113.3	113.3	114.7	114.7	114.7
42.5°	103.1	101.6	101.6	103.1	103.1	104.6	104.6	106.0	107.5	107.5	108.9
45°	100.2	98.7	98.7	98.7	98.7	97.3	97.3	98.7	100.2	101.6	103.1
47.5°	94.4	94.4	92.9	92.9	92.9	92.9	92.9	92.9	94.4	94.4	94.4
50°	91.5	91.5	90.0	90.0	90.0	90.0	90.0	90.0	90.0	90.0	90.0
52.5°	88.6	87.1	87.1	87.1	87.1	85.7	85.7	85.7	85.7	85.7	85.7
55°	84.2	82.8	82.8	82.8	82.8	82.8	82.8	82.8	84.2	84.2	84.2
57.5°	79.9	78.4	78.4	78.4	79.9	79.9	79.9	79.9	81.3	81.3	81.3
60°	75.5	75.5	75.5	75.5	75.5	75.5	75.5	77.0	77.0	78.4	78.4
62.5°	71.2	71.2	71.2	71.2	72.6	72.6	72.6	72.6	74.1	74.1	74.1
65°	66.8	66.8	66.8	66.8	68.2	68.2	68.2	68.2	68.2	68.2	68.2
67.5°	62.4	62.4	62.4	62.4	62.4	62.4	62.4	63.9	63.9	65.3	65.3
70°	56.6	55.2	55.2	56.6	56.6	58.1	58.1	59.5	59.5	61.0	61.0
72.5°	50.8	50.8	50.8	50.8	50.8	50.8	50.8	52.3	53.7	53.7	55.2
75°	45.0	45.0	45.0	45.0	46.5	46.5	46.5	47.9	47.9	49.4	49.4
77.5°	40.7	39.2	39.2	39.2	40.7	40.7	40.7	42.1	42.1	43.6	43.6
80°	33.4	33.4	33.4	33.4	34.9	34.9	34.9	34.9	36.3	36.3	36.3
82.5°	27.6	27.6	27.6	27.6	27.6	27.6	27.6	27.6	29.0	29.0	29.0
85°	20.3	20.3	20.3	20.3	21.8	21.8	21.8	21.8	21.8	21.8	21.8
87.5°	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1	14.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065
 CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676065

CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5
2.5°	923.6	923.6	923.6	923.6	926.5	927.9	930.8	932.3	930.8	929.4	926.5
5°	776.9	778.3	778.3	779.8	779.8	779.8	779.8	779.8	782.7	785.6	788.5
7.5°	614.2	615.7	617.2	618.6	618.6	618.6	617.2	617.2	618.6	618.6	620.1
10°	470.5	476.3	480.7	485.0	482.1	477.7	474.8	470.5	470.5	470.5	469.0
12.5°	355.8	357.2	360.1	361.6	360.1	360.1	358.7	357.2	358.7	361.6	363.0
15°	281.7	281.7	283.2	283.2	284.6	286.1	286.1	287.5	290.4	291.9	294.8
17.5°	233.8	235.2	235.2	236.7	236.7	238.1	238.1	238.1	241.1	244.0	248.3
20°	210.6	210.6	210.6	210.6	210.6	209.1	209.1	207.7	209.1	212.0	213.5
22.5°	188.8	190.2	190.2	190.2	188.8	187.3	184.4	183.0	183.0	184.4	184.4
25°	165.5	164.1	164.1	162.6	162.6	164.1	164.1	164.1	165.5	165.5	167.0
27.5°	152.5	151.0	151.0	149.6	149.6	151.0	151.0	151.0	151.0	151.0	151.0
30°	142.3	142.3	140.9	139.4	140.9	140.9	142.3	142.3	143.8	143.8	145.2
32.5°	135.0	133.6	133.6	132.1	133.6	133.6	135.0	135.0	136.5	138.0	138.0
35°	124.9	124.9	124.9	124.9	124.9	124.9	123.4	123.4	123.4	123.4	123.4
37.5°	119.1	119.1	117.6	116.2	116.2	116.2	116.2	116.2	114.7	113.3	111.8
40°	114.7	113.3	113.3	111.8	110.4	110.4	108.9	107.5	107.5	106.0	106.0
42.5°	108.9	107.5	107.5	106.0	104.6	104.6	103.1	101.6	101.6	101.6	100.2
45°	101.6	101.6	100.2	98.7	98.7	98.7	97.3	97.3	97.3	97.3	95.8
47.5°	94.4	94.4	92.9	92.9	92.9	92.9	91.5	91.5	91.5	91.5	91.5
50°	90.0	90.0	90.0	90.0	90.0	90.0	88.6	88.6	88.6	88.6	88.6
52.5°	85.7	85.7	85.7	85.7	85.7	85.7	85.7	85.7	85.7	85.7	85.7
55°	84.2	84.2	84.2	84.2	84.2	84.2	82.8	82.8	82.8	84.2	84.2
57.5°	81.3	81.3	79.9	79.9	79.9	79.9	79.9	79.9	79.9	79.9	79.9
60°	78.4	78.4	78.4	78.4	78.4	78.4	78.4	78.4	78.4	78.4	78.4
62.5°	74.1	74.1	74.1	74.1	74.1	75.5	75.5	75.5	75.5	75.5	74.1
65°	68.2	69.7	69.7	69.7	69.7	69.7	69.7	69.7	69.7	69.7	69.7
67.5°	65.3	65.3	65.3	65.3	65.3	65.3	65.3	65.3	65.3	65.3	65.3
70°	61.0	61.0	59.5	59.5	59.5	61.0	61.0	61.0	61.0	61.0	61.0
72.5°	55.2	55.2	55.2	55.2	55.2	55.2	55.2	55.2	55.2	56.6	56.6
75°	49.4	49.4	49.4	49.4	49.4	49.4	49.4	49.4	49.4	49.4	49.4
77.5°	43.6	43.6	42.1	42.1	42.1	43.6	43.6	43.6	43.6	45.0	45.0
80°	36.3	36.3	36.3	36.3	36.3	36.3	36.3	36.3	36.3	37.8	37.8
82.5°	29.0	29.0	29.0	29.0	29.0	29.0	29.0	29.0	29.0	30.5	30.5
85°	21.8	23.2	23.2	23.2	23.2	23.2	23.2	23.2	23.2	24.7	24.7
87.5°	14.5	14.5	14.5	14.5	14.5	14.5	13.1	13.1	13.1	13.1	11.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065
 CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065

CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5
2.5°	925.0	926.5	927.9	927.9	929.4	930.8	930.8	936.6	942.4	945.3	948.2
5°	791.4	790.0	790.0	788.5	787.1	791.4	795.8	804.5	813.2	814.6	817.5
7.5°	620.1	621.5	623.0	623.0	624.4	620.1	614.2	615.7	617.2	624.4	630.2
10°	469.0	470.5	471.9	471.9	473.4	471.9	469.0	473.4	477.7	483.6	490.8
12.5°	364.5	368.8	373.2	376.1	380.5	383.4	384.8	390.6	395.0	402.2	409.5
15°	297.7	300.6	303.5	306.4	309.3	312.2	315.1	320.9	326.7	335.4	344.2
17.5°	251.2	251.2	252.7	252.7	252.7	255.6	258.5	261.4	262.8	271.5	280.3
20°	214.9	213.5	212.0	210.6	209.1	212.0	213.5	214.9	216.4	222.2	226.5
22.5°	184.4	184.4	185.9	185.9	185.9	184.4	181.5	183.0	183.0	185.9	190.2
25°	167.0	167.0	167.0	165.5	165.5	167.0	168.4	168.4	167.0	168.4	169.9
27.5°	151.0	152.5	152.5	153.9	153.9	155.4	155.4	155.4	155.4	156.8	158.3
30°	145.2	145.2	146.7	146.7	146.7	148.1	149.6	149.6	149.6	151.0	153.9
32.5°	139.4	140.9	142.3	143.8	145.2	146.7	146.7	148.1	148.1	149.6	151.0
35°	123.4	122.0	122.0	120.5	119.1	119.1	119.1	119.1	117.6	119.1	119.1
37.5°	110.4	110.4	110.4	108.9	108.9	110.4	110.4	110.4	110.4	111.8	111.8
40°	104.6	104.6	104.6	104.6	104.6	104.6	104.6	106.0	106.0	107.5	108.9
42.5°	100.2	100.2	100.2	100.2	100.2	101.6	101.6	101.6	101.6	103.1	103.1
45°	95.8	95.8	95.8	95.8	95.8	95.8	95.8	97.3	97.3	98.7	100.2
47.5°	91.5	91.5	91.5	91.5	91.5	92.9	94.4	94.4	94.4	95.8	95.8
50°	88.6	88.6	88.6	88.6	88.6	90.0	90.0	91.5	91.5	92.9	94.4
52.5°	85.7	85.7	85.7	85.7	85.7	87.1	87.1	88.6	88.6	90.0	91.5
55°	84.2	84.2	84.2	82.8	82.8	84.2	84.2	85.7	85.7	87.1	87.1
57.5°	79.9	79.9	79.9	79.9	79.9	79.9	79.9	81.3	81.3	82.8	84.2
60°	78.4	78.4	77.0	77.0	75.5	77.0	77.0	78.4	78.4	79.9	79.9
62.5°	74.1	74.1	74.1	72.6	72.6	74.1	74.1	74.1	74.1	75.5	77.0
65°	69.7	69.7	69.7	68.2	68.2	69.7	69.7	69.7	69.7	71.2	72.6
67.5°	65.3	65.3	65.3	63.9	63.9	63.9	63.9	65.3	65.3	66.8	68.2
70°	61.0	61.0	61.0	59.5	59.5	59.5	58.1	59.5	61.0	62.4	62.4
72.5°	56.6	56.6	56.6	55.2	55.2	55.2	53.7	55.2	55.2	56.6	56.6
75°	49.4	49.4	49.4	49.4	49.4	49.4	47.9	47.9	47.9	49.4	49.4
77.5°	45.0	45.0	45.0	43.6	43.6	43.6	42.1	42.1	42.1	43.6	43.6
80°	37.8	37.8	37.8	36.3	36.3	36.3	34.9	34.9	34.9	36.3	36.3
82.5°	30.5	30.5	30.5	29.0	29.0	29.0	27.6	27.6	27.6	29.0	29.0
85°	24.7	24.7	24.7	24.7	24.7	24.7	23.2	23.2	23.2	24.7	26.1
87.5°	11.6	11.6	13.1	13.1	13.1	13.1	11.6	11.6	10.2	10.2	11.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065
 CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676065

CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5
2.5°	951.1	954.0	961.3	967.1	974.4	980.2	984.5	990.4	994.7	999.1	1002.0
5°	819.0	820.5	827.7	835.0	840.8	848.0	858.2	868.4	878.5	888.7	896.0
7.5°	637.5	643.3	652.0	662.2	670.9	679.6	689.8	701.4	711.5	721.7	731.9
10°	496.6	502.4	511.1	519.9	527.1	535.8	547.5	559.1	570.7	582.3	593.9
12.5°	416.8	424.0	434.2	444.4	453.1	463.2	477.7	490.8	505.3	518.4	532.9
15°	351.4	360.1	373.2	387.7	400.8	413.9	428.4	442.9	456.0	470.5	485.0
17.5°	289.0	297.7	309.3	322.4	334.0	345.6	363.0	379.0	396.4	412.4	428.4
20°	232.3	236.7	248.3	259.9	271.5	283.2	296.2	309.3	322.4	335.4	355.8
22.5°	193.1	196.0	201.8	206.2	212.0	216.4	229.4	242.5	254.1	267.2	286.1
25°	169.9	171.4	175.7	178.6	183.0	185.9	194.6	201.8	210.6	217.8	235.2
27.5°	158.3	159.7	161.2	162.6	164.1	165.5	171.4	177.2	181.5	187.3	203.3
30°	155.4	156.8	161.2	164.1	168.4	171.4	174.3	177.2	180.1	183.0	193.1
32.5°	152.5	153.9	153.9	152.5	152.5	151.0	153.9	155.4	158.3	159.7	168.4
35°	120.5	120.5	122.0	123.4	124.9	126.3	130.7	133.6	138.0	140.9	148.1
37.5°	113.3	113.3	114.7	117.6	119.1	120.5	123.4	126.3	129.2	132.1	139.4
40°	108.9	110.4	111.8	113.3	114.7	116.2	119.1	120.5	123.4	124.9	130.7
42.5°	104.6	104.6	106.0	108.9	110.4	111.8	114.7	116.2	119.1	120.5	126.3
45°	101.6	103.1	104.6	106.0	106.0	107.5	110.4	113.3	114.7	117.6	123.4
47.5°	97.3	97.3	100.2	101.6	104.6	106.0	108.9	110.4	113.3	114.7	120.5
50°	94.4	95.8	98.7	100.2	103.1	104.6	108.9	111.8	116.2	119.1	122.0
52.5°	91.5	92.9	95.8	97.3	100.2	101.6	107.5	113.3	117.6	123.4	123.4
55°	88.6	88.6	91.5	95.8	98.7	101.6	104.6	108.9	111.8	114.7	114.7
57.5°	84.2	85.7	88.6	92.9	95.8	98.7	101.6	104.6	106.0	108.9	107.5
60°	81.3	81.3	85.7	90.0	94.4	98.7	98.7	98.7	97.3	97.3	97.3
62.5°	77.0	78.4	84.2	91.5	97.3	103.1	98.7	94.4	90.0	85.7	87.1
65°	74.1	75.5	78.4	82.8	85.7	88.6	85.7	84.2	81.3	78.4	79.9
67.5°	68.2	69.7	71.2	71.2	72.6	72.6	72.6	72.6	72.6	72.6	74.1
70°	63.9	63.9	63.9	65.3	65.3	65.3	65.3	65.3	65.3	65.3	66.8
72.5°	58.1	58.1	58.1	58.1	58.1	58.1	58.1	58.1	58.1	58.1	59.5
75°	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8	52.3
77.5°	45.0	45.0	45.0	45.0	45.0	45.0	45.0	45.0	43.6	43.6	45.0
80°	37.8	37.8	37.8	37.8	36.3	36.3	36.3	36.3	36.3	36.3	37.8
82.5°	30.5	30.5	30.5	30.5	29.0	29.0	29.0	29.0	27.6	27.6	29.0
85°	27.6	29.0	29.0	30.5	30.5	30.5	29.0	27.6	26.1	24.7	24.7
87.5°	11.6	11.6	11.6	11.6	10.2	10.2	10.2	10.2	10.2	10.2	10.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065
 CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065

CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5
2.5°	1006.3	1009.2	1012.1	1016.5	1022.3	1026.7	1031.0	1039.7	1049.9	1058.6	1067.3
5°	903.2	910.5	917.7	926.5	935.2	942.4	951.1	968.6	986.0	1002.0	1019.4
7.5°	740.6	750.7	759.5	774.0	787.1	801.6	814.6	836.4	856.8	878.5	898.9
10°	605.5	617.2	628.8	647.6	668.0	686.9	705.7	723.2	742.0	759.5	776.9
12.5°	547.5	560.5	575.0	586.7	599.7	611.3	623.0	643.3	663.6	684.0	704.3
15°	499.5	514.1	528.6	543.1	556.2	570.7	583.8	601.2	620.1	637.5	654.9
17.5°	444.4	458.9	474.8	490.8	506.8	522.8	538.7	563.4	588.1	611.3	636.0
20°	374.6	395.0	413.9	435.6	457.4	479.2	501.0	527.1	553.3	577.9	604.1
22.5°	304.9	323.8	342.7	368.8	395.0	419.7	445.8	480.7	514.1	548.9	582.3
25°	254.1	271.5	289.0	318.0	345.6	374.6	402.2	444.4	485.0	527.1	567.8
27.5°	219.3	235.2	251.2	281.7	312.2	341.2	371.7	418.2	463.2	509.7	554.7
30°	203.3	213.5	223.6	252.7	281.7	309.3	338.3	383.4	428.4	473.4	518.4
32.5°	177.2	185.9	194.6	220.7	246.9	271.5	297.7	344.2	389.2	435.6	480.7
35°	156.8	164.1	171.4	196.0	219.3	244.0	267.2	313.7	360.1	406.6	453.1
37.5°	145.2	152.5	158.3	180.1	203.3	225.1	246.9	293.3	338.3	384.8	429.8
40°	136.5	140.9	146.7	168.4	188.8	210.6	230.9	273.0	316.6	358.7	400.8
42.5°	130.7	136.5	140.9	159.7	180.1	198.9	217.8	258.5	299.1	338.3	379.0
45°	129.2	135.0	140.9	156.8	172.8	187.3	203.3	242.5	281.7	320.9	360.1
47.5°	126.3	130.7	136.5	149.6	161.2	174.3	185.9	225.1	264.3	302.0	341.2
50°	124.9	126.3	129.2	140.9	152.5	164.1	175.7	214.9	254.1	293.3	332.5
52.5°	123.4	123.4	123.4	133.6	143.8	152.5	162.6	201.8	242.5	281.7	320.9
55°	114.7	113.3	113.3	123.4	132.1	142.3	151.0	190.2	229.4	267.2	306.4
57.5°	106.0	104.6	103.1	111.8	120.5	129.2	138.0	177.2	217.8	257.0	296.2
60°	97.3	95.8	95.8	104.6	111.8	120.5	127.8	168.4	207.7	248.3	287.5
62.5°	87.1	88.6	88.6	95.8	104.6	111.8	119.1	159.7	201.8	242.5	283.2
65°	79.9	81.3	81.3	90.0	98.7	107.5	116.2	155.4	196.0	235.2	274.5
67.5°	74.1	75.5	75.5	85.7	94.4	104.6	113.3	148.1	184.4	219.3	254.1
70°	68.2	68.2	69.7	79.9	90.0	100.2	110.4	140.9	171.4	200.4	230.9
72.5°	61.0	62.4	63.9	74.1	82.8	92.9	101.6	129.2	156.8	184.4	212.0
75°	53.7	55.2	56.6	65.3	74.1	82.8	91.5	117.6	142.3	168.4	193.1
77.5°	47.9	49.4	50.8	58.1	65.3	72.6	79.9	98.7	119.1	138.0	156.8
80°	39.2	39.2	40.7	46.5	52.3	56.6	62.4	75.5	88.6	100.2	113.3
82.5°	29.0	30.5	30.5	34.9	37.8	42.1	45.0	52.3	58.1	65.3	71.2
85°	24.7	23.2	23.2	26.1	27.6	30.5	31.9	36.3	39.2	43.6	46.5
87.5°	10.2	8.7	8.7	10.2	13.1	14.5	16.0	16.0	17.4	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065
 CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065

CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5
2.5°	1071.7	1074.6	1078.9	1081.8	1089.1	1094.9	1102.2	1108.0	1112.3	1119.6	1116.7
5°	1032.5	1045.5	1058.6	1071.7	1081.8	1092.0	1100.7	1110.9	1122.5	1144.3	1150.1
7.5°	916.3	933.7	949.7	967.1	987.4	1007.8	1028.1	1048.4	1067.3	1094.9	1112.3
10°	801.6	826.3	849.5	874.2	893.1	911.9	929.4	948.2	974.4	1002.0	1033.9
12.5°	729.0	753.7	778.3	803.0	830.6	856.8	884.3	910.5	935.2	957.0	993.3
15°	681.0	708.6	734.8	760.9	794.3	826.3	859.7	891.6	927.9	957.0	981.6
17.5°	669.4	702.8	734.8	768.2	803.0	837.9	872.7	907.6	943.9	987.4	1019.4
20°	649.1	694.1	739.1	784.1	829.2	872.7	917.7	961.3	1009.2	1061.5	1076.0
22.5°	637.5	691.2	746.4	800.1	861.1	923.6	984.5	1045.5	1096.4	1135.6	1179.1
25°	636.0	702.8	771.1	837.9	914.8	990.4	1067.3	1142.8	1208.2	1247.4	1282.2
27.5°	634.6	715.9	795.8	875.6	970.0	1063.0	1157.3	1250.3	1311.3	1367.9	1396.9
30°	617.2	714.4	813.2	910.5	1016.5	1122.5	1228.5	1334.5	1396.9	1436.2	1450.7
32.5°	595.4	710.1	824.8	939.5	1060.1	1180.6	1299.7	1420.2	1469.6	1503.0	1491.3
35°	577.9	704.3	829.2	954.0	1081.8	1211.1	1338.9	1466.6	1537.8	1584.3	1565.4
37.5°	562.0	694.1	826.3	958.4	1108.0	1257.5	1407.1	1556.7	1624.9	1674.3	1652.5
40°	543.1	684.0	826.3	967.1	1138.5	1308.4	1479.7	1649.6	1738.2	1780.3	1746.9
42.5°	527.1	673.8	821.9	968.6	1151.5	1334.5	1517.5	1700.4	1799.2	1858.7	1816.6
45°	506.8	653.5	798.7	945.3	1147.2	1349.0	1549.4	1751.3	1866.0	1912.5	1854.4
47.5°	485.0	630.2	774.0	917.7	1132.7	1347.6	1562.5	1777.4	1883.4	1938.6	1884.9
50°	477.7	623.0	766.7	911.9	1144.3	1378.1	1610.4	1842.7	1919.7	1964.7	1893.6
52.5°	476.3	630.2	785.6	939.5	1173.3	1405.7	1639.5	1871.8	1934.2	1982.2	1918.3
55°	471.9	638.9	804.5	970.0	1214.0	1459.4	1703.3	1947.3	2009.7	2044.6	1996.7
57.5°	476.3	656.4	835.0	1015.0	1266.3	1517.5	1768.7	2019.9	2095.4	2120.1	2109.9
60°	479.2	670.9	861.1	1052.8	1298.2	1543.6	1789.0	2034.4	2112.8	2173.8	2185.5
62.5°	471.9	660.7	848.0	1036.8	1259.0	1481.2	1703.3	1925.5	2054.8	2144.8	2197.1
65°	450.2	624.4	800.1	974.4	1179.1	1385.3	1590.1	1794.8	1931.3	2064.9	2107.0
67.5°	402.2	550.4	698.5	846.6	1025.2	1203.8	1381.0	1559.6	1730.9	1860.2	1918.3
70°	348.5	464.7	582.3	698.5	861.1	1023.7	1186.4	1349.0	1500.0	1642.4	1697.5
72.5°	303.5	393.5	485.0	575.0	691.2	805.9	922.1	1036.8	1215.4	1357.7	1411.5
75°	258.5	323.8	387.7	453.1	532.9	612.8	691.2	771.1	897.4	1025.2	1078.9
77.5°	198.9	242.5	284.6	326.7	381.9	435.6	490.8	544.5	633.1	729.0	756.6
80°	138.0	162.6	185.9	210.6	254.1	297.7	341.2	384.8	442.9	496.6	538.7
82.5°	85.7	101.6	116.2	130.7	165.5	200.4	233.8	268.6	291.9	294.8	336.9
85°	55.2	65.3	74.1	82.8	103.1	124.9	145.2	165.5	148.1	138.0	164.1
87.5°	21.8	27.6	31.9	36.3	34.9	33.4	31.9	30.5	26.1	23.2	29.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065
 CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676065

CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5
2.5°	1119.6	1123.9	1128.3	1131.2	1135.6	1137.0	1138.5	1138.5	1139.9	1141.4	1144.3
5°	1173.3	1182.0	1190.7	1198.0	1206.7	1214.0	1219.8	1227.0	1232.9	1232.9	1231.4
7.5°	1128.3	1150.1	1171.9	1193.6	1215.4	1231.4	1245.9	1261.9	1276.4	1279.3	1282.2
10°	1068.8	1092.0	1113.8	1137.0	1158.8	1183.5	1206.7	1230.0	1254.6	1259.0	1264.8
12.5°	1013.6	1041.2	1068.8	1094.9	1122.5	1139.9	1157.3	1173.3	1190.7	1202.4	1214.0
15°	1012.1	1035.4	1058.6	1080.4	1103.6	1113.8	1123.9	1132.7	1142.8	1142.8	1144.3
17.5°	1045.5	1060.1	1074.6	1087.6	1102.2	1103.6	1106.5	1108.0	1109.4	1105.1	1100.7
20°	1110.9	1116.7	1122.5	1128.3	1134.1	1123.9	1115.2	1105.1	1094.9	1083.3	1073.1
22.5°	1206.7	1193.6	1180.6	1167.5	1154.4	1137.0	1118.1	1100.7	1081.8	1067.3	1052.8
25°	1296.7	1280.8	1264.8	1248.8	1232.9	1195.1	1157.3	1118.1	1080.4	1064.4	1048.4
27.5°	1417.3	1392.6	1367.9	1343.2	1318.5	1267.7	1216.9	1166.1	1115.2	1087.6	1061.5
30°	1446.3	1418.7	1391.1	1362.1	1334.5	1285.1	1237.2	1187.8	1138.5	1106.5	1076.0
32.5°	1488.4	1456.5	1424.5	1392.6	1360.6	1312.7	1264.8	1215.4	1167.5	1138.5	1108.0
35°	1558.1	1521.8	1485.5	1447.8	1411.5	1362.1	1314.2	1264.8	1215.4	1182.0	1150.1
37.5°	1617.7	1575.6	1533.4	1491.3	1449.2	1405.7	1360.6	1317.1	1272.1	1238.7	1206.7
40°	1684.5	1638.0	1591.5	1546.5	1500.0	1459.4	1418.7	1376.6	1336.0	1309.8	1283.7
42.5°	1742.6	1685.9	1630.7	1575.6	1518.9	1491.3	1465.2	1437.6	1410.0	1396.9	1382.4
45°	1783.2	1730.9	1677.2	1624.9	1572.7	1552.3	1532.0	1511.7	1491.3	1504.4	1517.5
47.5°	1800.6	1758.5	1717.9	1677.2	1635.1	1642.4	1649.6	1655.4	1662.7	1680.1	1699.0
50°	1816.6	1793.4	1768.7	1745.5	1720.8	1748.4	1774.5	1802.1	1829.7	1866.0	1902.3
52.5°	1848.6	1835.5	1823.9	1810.8	1797.7	1845.7	1893.6	1941.5	1989.4	2030.1	2070.7
55°	1944.4	1934.2	1924.1	1912.5	1902.3	1970.5	2037.3	2105.6	2173.8	2215.9	2258.1
57.5°	2076.5	2070.7	2063.5	2057.7	2050.4	2117.2	2182.5	2247.9	2314.7	2355.3	2397.5
60°	2176.7	2178.2	2178.2	2179.6	2179.6	2230.5	2281.3	2333.6	2384.4	2419.2	2455.5
62.5°	2230.5	2227.6	2224.7	2221.8	2218.8	2261.0	2303.1	2345.2	2387.3	2413.4	2439.6
65°	2172.4	2188.4	2204.3	2220.3	2236.3	2242.1	2246.4	2252.2	2256.6	2272.6	2288.6
67.5°	1977.8	2009.7	2040.2	2072.2	2102.7	2080.9	2060.6	2038.8	2017.0	2021.4	2024.3
70°	1761.4	1797.7	1835.5	1871.8	1908.1	1857.3	1806.4	1754.2	1703.3	1685.9	1668.5
72.5°	1485.5	1517.5	1550.9	1582.8	1614.8	1552.3	1491.3	1428.9	1366.5	1336.0	1305.5
75°	1135.6	1173.3	1212.5	1250.3	1288.0	1218.3	1147.2	1077.5	1006.3	986.0	967.1
77.5°	827.7	872.7	917.7	962.8	1007.8	945.3	882.9	819.0	756.6	744.9	733.3
80°	602.6	637.5	670.9	705.7	739.1	702.8	666.5	630.2	593.9	592.5	591.0
82.5°	406.6	437.1	466.1	496.6	525.7	511.1	498.1	483.6	469.0	483.6	499.5
85°	209.1	251.2	294.8	336.9	379.0	374.6	371.7	367.4	363.0	381.9	399.3
87.5°	42.1	78.4	114.7	149.6	185.9	177.2	168.4	158.3	149.6	155.4	159.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065
 CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065

CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5
2.5°	1145.7	1147.2	1147.2	1147.2	1147.2	1147.2	1144.3	1142.8	1139.9	1137.0	1132.7
5°	1231.4	1230.0	1224.1	1218.3	1211.1	1205.3	1200.9	1195.1	1190.7	1184.9	1176.2
7.5°	1285.1	1288.0	1277.9	1269.2	1259.0	1248.8	1238.7	1228.5	1218.3	1208.2	1187.8
10°	1269.2	1273.5	1267.7	1261.9	1254.6	1248.8	1237.2	1224.1	1212.5	1199.5	1174.8
12.5°	1224.1	1235.8	1232.9	1230.0	1227.0	1224.1	1216.9	1208.2	1200.9	1192.2	1164.6
15°	1144.3	1144.3	1145.7	1147.2	1147.2	1148.6	1150.1	1151.5	1153.0	1154.4	1138.5
17.5°	1096.4	1092.0	1092.0	1092.0	1092.0	1092.0	1097.8	1105.1	1110.9	1116.7	1112.3
20°	1061.5	1051.3	1049.9	1049.9	1048.4	1047.0	1057.1	1068.8	1078.9	1089.1	1094.9
22.5°	1038.3	1023.7	1022.3	1020.8	1019.4	1017.9	1031.0	1044.1	1057.1	1070.2	1090.5
25°	1032.5	1016.5	1017.9	1019.4	1019.4	1020.8	1031.0	1041.2	1051.3	1061.5	1096.4
27.5°	1033.9	1007.8	1009.2	1010.7	1010.7	1012.1	1028.1	1042.6	1058.6	1073.1	1116.7
30°	1044.1	1013.6	1010.7	1007.8	1004.9	1002.0	1023.7	1045.5	1067.3	1089.1	1122.5
32.5°	1078.9	1049.9	1042.6	1035.4	1028.1	1020.8	1047.0	1071.7	1097.8	1122.5	1150.1
35°	1116.7	1084.7	1081.8	1078.9	1074.6	1071.7	1094.9	1119.6	1142.8	1166.1	1190.7
37.5°	1173.3	1141.4	1138.5	1134.1	1131.2	1126.9	1153.0	1177.7	1203.8	1228.5	1250.3
40°	1257.5	1231.4	1230.0	1230.0	1228.5	1227.0	1247.4	1269.2	1289.5	1309.8	1324.3
42.5°	1369.4	1356.3	1360.6	1366.5	1370.8	1375.2	1391.1	1408.6	1424.5	1440.5	1436.2
45°	1530.5	1543.6	1545.1	1546.5	1548.0	1549.4	1553.8	1559.6	1563.9	1568.3	1550.9
47.5°	1716.4	1733.8	1742.6	1751.3	1758.5	1767.2	1761.4	1754.2	1748.4	1741.1	1697.5
50°	1937.1	1973.4	1972.0	1970.5	1967.6	1966.2	1954.6	1942.9	1929.9	1918.3	1854.4
52.5°	2111.4	2152.1	2159.3	2166.6	2173.8	2181.1	2159.3	2137.5	2114.3	2092.5	2012.6
55°	2298.7	2340.8	2342.3	2343.7	2343.7	2345.2	2314.7	2284.2	2252.2	2221.8	2139.0
57.5°	2438.1	2478.8	2474.4	2471.5	2467.2	2462.8	2426.5	2390.2	2353.9	2317.6	2234.8
60°	2490.4	2525.2	2516.5	2507.8	2497.7	2488.9	2461.4	2433.8	2404.7	2377.1	2297.3
62.5°	2465.7	2491.8	2478.8	2467.2	2454.1	2441.0	2406.2	2369.9	2335.0	2298.7	2240.6
65°	2303.1	2319.0	2301.6	2285.6	2269.7	2252.2	2223.2	2194.2	2163.7	2134.6	2095.4
67.5°	2028.6	2031.5	2030.1	2028.6	2027.2	2025.7	1983.6	1941.5	1897.9	1855.8	1852.9
70°	1652.5	1635.1	1638.0	1642.4	1645.3	1648.2	1616.2	1585.7	1553.8	1521.8	1536.4
72.5°	1275.0	1244.5	1251.7	1260.4	1267.7	1275.0	1248.8	1224.1	1198.0	1171.9	1192.2
75°	946.8	927.9	935.2	943.9	951.1	958.4	948.2	938.1	926.5	916.3	935.2
77.5°	721.7	710.1	711.5	711.5	713.0	713.0	714.4	717.4	718.8	720.3	740.6
80°	588.1	586.7	585.2	583.8	580.9	579.4	593.9	608.4	623.0	637.5	647.6
82.5°	514.1	528.6	519.9	512.6	503.9	495.2	508.2	521.3	534.4	547.5	543.1
85°	418.2	435.6	419.7	403.7	386.3	370.3	381.9	392.1	403.7	413.9	408.0
87.5°	165.5	169.9	143.8	119.1	92.9	66.8	106.0	143.8	183.0	220.7	226.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065
 CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065

CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5	1045.5
2.5°	1128.3	1122.5	1118.1	1116.7	1113.8	1112.3	1109.4	1106.5	1102.2	1099.3	1094.9
5°	1166.1	1157.3	1147.2	1132.7	1119.6	1105.1	1090.5	1077.5	1064.4	1049.9	1036.8
7.5°	1167.5	1147.2	1126.9	1108.0	1087.6	1068.8	1048.4	1031.0	1012.1	993.3	975.8
10°	1151.5	1126.9	1102.2	1077.5	1054.2	1029.6	1004.9	984.5	962.8	941.0	920.6
12.5°	1138.5	1110.9	1083.3	1054.2	1026.7	997.6	968.6	948.2	927.9	907.6	887.2
15°	1122.5	1105.1	1089.1	1063.0	1036.8	1010.7	984.5	957.0	930.8	903.2	875.6
17.5°	1109.4	1105.1	1100.7	1083.3	1065.9	1047.0	1029.6	1002.0	974.4	945.3	917.7
20°	1102.2	1108.0	1113.8	1105.1	1096.4	1086.2	1077.5	1057.1	1036.8	1015.0	994.7
22.5°	1110.9	1132.7	1153.0	1154.4	1157.3	1158.8	1160.2	1141.4	1122.5	1102.2	1083.3
25°	1131.2	1166.1	1200.9	1219.8	1238.7	1259.0	1277.9	1266.3	1254.6	1243.0	1231.4
27.5°	1158.8	1202.4	1245.9	1273.5	1299.7	1327.2	1354.8	1353.4	1351.9	1349.0	1347.6
30°	1154.4	1187.8	1221.2	1254.6	1288.0	1321.4	1354.8	1372.3	1388.2	1405.7	1423.1
32.5°	1179.1	1206.7	1235.8	1270.6	1305.5	1341.8	1376.6	1412.9	1447.8	1484.1	1520.4
35°	1216.9	1241.6	1267.7	1305.5	1344.7	1382.4	1421.6	1465.2	1510.2	1555.2	1598.8
37.5°	1273.5	1295.3	1318.5	1350.5	1383.9	1415.8	1449.2	1513.1	1577.0	1642.4	1706.2
40°	1338.9	1353.4	1367.9	1398.4	1428.9	1459.4	1489.9	1569.7	1649.6	1729.5	1809.3
42.5°	1433.2	1428.9	1424.5	1449.2	1475.4	1500.0	1526.2	1598.8	1671.4	1744.0	1816.6
45°	1533.4	1516.0	1498.6	1510.2	1523.3	1534.9	1548.0	1622.0	1696.1	1771.6	1845.7
47.5°	1654.0	1610.4	1566.8	1556.7	1546.5	1534.9	1524.7	1604.6	1684.5	1765.8	1845.7
50°	1790.5	1725.1	1661.2	1635.1	1607.5	1581.4	1553.8	1619.1	1685.9	1752.7	1818.1
52.5°	1932.8	1851.5	1771.6	1730.9	1690.3	1648.2	1607.5	1662.7	1719.3	1776.0	1831.1
55°	2054.8	1972.0	1887.8	1839.8	1791.9	1744.0	1696.1	1751.3	1806.4	1861.6	1916.8
57.5°	2152.1	2069.3	1986.5	1941.5	1895.0	1850.0	1803.5	1855.8	1909.5	1963.3	2015.6
60°	2218.8	2139.0	2059.1	2015.6	1972.0	1928.4	1884.9	1947.3	2009.7	2073.6	2136.1
62.5°	2184.0	2125.9	2067.8	2049.0	2030.1	2009.7	1990.9	2050.4	2108.5	2168.0	2227.6
65°	2056.2	2017.0	1977.8	1996.7	2017.0	2035.9	2056.2	2095.4	2134.6	2175.3	2214.5
67.5°	1848.6	1845.7	1841.3	1883.4	1925.5	1969.1	2011.2	2037.3	2062.0	2088.2	2114.3
70°	1550.9	1566.8	1581.4	1654.0	1726.6	1799.2	1871.8	1882.0	1892.1	1902.3	1912.5
72.5°	1214.0	1234.3	1256.1	1351.9	1446.3	1542.2	1638.0	1632.2	1626.4	1619.1	1613.3
75°	955.5	974.4	994.7	1083.3	1171.9	1260.4	1349.0	1324.3	1301.1	1276.4	1251.7
77.5°	762.4	782.7	804.5	887.2	970.0	1054.2	1137.0	1077.5	1017.9	958.4	898.9
80°	656.4	666.5	675.2	731.9	787.1	843.7	900.3	839.3	776.9	714.4	653.5
82.5°	538.7	532.9	528.6	562.0	595.4	628.8	662.2	604.1	546.0	486.5	428.4
85°	402.2	396.4	390.6	408.0	425.5	444.4	461.8	395.0	328.2	259.9	193.1
87.5°	233.8	239.6	245.4	264.3	283.2	303.5	322.4	254.1	185.9	116.2	47.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065
 CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676065
 CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1045.5	1045.5
2.5°	1086.2	1078.9
5°	1026.7	1016.5
7.5°	961.3	948.2
10°	901.8	884.3
12.5°	864.0	842.2
15°	849.5	823.4
17.5°	893.1	868.4
20°	959.9	926.5
22.5°	1041.2	1000.5
25°	1182.0	1132.7
27.5°	1296.7	1245.9
30°	1367.9	1312.7
32.5°	1446.3	1373.7
35°	1527.6	1457.9
37.5°	1626.4	1548.0
40°	1728.0	1646.7
42.5°	1762.9	1710.6
45°	1796.3	1746.9
47.5°	1803.5	1762.9
50°	1810.8	1805.0
52.5°	1831.1	1829.7
55°	1918.3	1919.7
57.5°	2025.7	2034.4
60°	2124.5	2114.3
62.5°	2175.3	2123.0
65°	2140.4	2067.8
67.5°	2035.9	1957.5
70°	1806.4	1700.4
72.5°	1520.4	1427.4
75°	1171.9	1093.5
77.5°	833.5	768.2
80°	586.7	521.3
82.5°	376.1	323.8
85°	169.9	148.1
87.5°	47.9	46.5
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P676065
CATALOG NUMBER: CCW-SA-1C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)