

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P676067

Luminaire Tested: **CCW-SA-1E-850-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P676067
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-1E-850-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/
SLR distribution lens
Light Source: (16) 5000K CCT, 80 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4951 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 56.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 7 fc

Type IV - Short - N/A

REPORT NUMBER: P676067
CATALOG NUMBER: CCW-SA-1E-850-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1018.7	0.0	1018.7
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3932.3	0.0	3932.3
	% Fixture	79.4	0.0	79.4
Total	Lumens	4951.0	0.0	4951.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.9	2.5
10°-20°	259.4	5.2
20°-30°	379.5	7.7
30°-40°	534.6	10.8
40°-50°	734.7	14.8
50°-60°	1001.4	20.2
60°-70°	1096.0	22.1
70°-80°	632.9	12.8
80°-90°	189.7	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4951.0	100.0
0°-180°	4951.0	100.0

Coefficient of Utilization



REPORT NUMBER: P676067


CATALOG NUMBER: CCW-SA-1E-850-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	508.5	10.3			
FM	(30°-60°)	1806.8	36.5			
FH	(60°-80°)	1455.9	29.4			G1/1800
FVH	(80°-90°)	161.2	3.3			G2/225
BL	(0°-30°)	253.3	5.1	B1/500		
BM	(30°-60°)	463.9	9.4	B1/1000		
BH	(60°-80°)	273.0	5.5	B1/500		G1/500
BVH	(80°-90°)	28.6	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0
2.5°	1631.6	1622.8	1616.2	1609.6	1600.8	1594.2	1585.4	1576.7	1565.7	1556.9	1545.9
5°	1537.1	1510.8	1484.4	1469.1	1451.5	1436.1	1418.6	1398.8	1379.0	1357.1	1337.3
7.5°	1433.9	1401.0	1368.0	1341.7	1313.1	1286.8	1258.3	1234.1	1209.9	1185.8	1161.6
10°	1337.3	1306.6	1275.8	1242.9	1207.7	1174.8	1139.7	1106.7	1073.8	1040.9	1007.9
12.5°	1273.6	1236.3	1201.2	1163.8	1128.7	1091.4	1054.0	1023.3	992.5	959.6	928.9
15°	1245.1	1209.9	1177.0	1139.7	1102.3	1065.0	1027.7	992.5	959.6	924.5	889.3
17.5°	1313.1	1262.6	1212.1	1163.8	1115.5	1067.2	1018.9	975.0	931.1	887.1	843.2
20°	1401.0	1337.3	1275.8	1216.5	1155.0	1095.8	1034.3	972.8	911.3	849.8	788.3
22.5°	1513.0	1440.5	1370.2	1293.4	1214.3	1137.5	1058.4	981.6	904.7	825.7	748.8
25°	1712.8	1627.2	1541.5	1431.7	1319.7	1209.9	1097.9	996.9	898.1	797.1	696.1
27.5°	1884.1	1767.7	1653.5	1521.8	1390.0	1258.3	1126.5	1010.1	895.9	779.5	663.2
30°	1985.1	1870.9	1756.7	1596.4	1438.3	1278.0	1117.7	988.2	860.8	731.2	601.7
32.5°	2077.3	1950.0	1822.6	1646.9	1469.1	1293.4	1115.5	972.8	832.2	689.5	546.8
35°	2204.7	2064.1	1925.8	1721.6	1517.4	1313.1	1108.9	961.8	812.5	665.4	516.0
37.5°	2340.8	2167.4	1996.1	1769.9	1543.7	1317.5	1091.4	946.4	801.5	656.6	511.6
40°	2490.1	2279.3	2070.7	1820.4	1572.3	1321.9	1071.6	926.7	781.7	634.6	489.7
42.5°	2586.8	2358.4	2130.0	1859.9	1592.0	1321.9	1051.8	909.1	766.4	621.4	478.7
45°	2641.7	2419.9	2200.3	1908.2	1616.2	1324.1	1032.1	891.5	751.0	608.3	467.7
47.5°	2665.8	2459.4	2253.0	1945.6	1640.3	1332.9	1025.5	882.8	737.8	595.1	450.2
50°	2729.5	2547.2	2365.0	2035.6	1708.4	1379.0	1049.6	895.9	744.4	590.7	437.0
52.5°	2766.8	2610.9	2455.0	2116.8	1778.7	1440.5	1102.3	931.1	759.8	588.5	417.2
55°	2903.0	2753.7	2604.3	2244.2	1881.9	1521.8	1159.4	970.6	781.7	590.7	401.8
57.5°	3076.5	2918.3	2762.4	2373.8	1985.1	1596.4	1207.7	1005.7	801.5	599.5	395.3
60°	3197.2	3043.5	2892.0	2479.2	2064.1	1651.3	1236.3	1025.5	814.7	601.7	390.9
62.5°	3210.4	3012.8	2817.3	2415.5	2013.6	1609.6	1207.7	1003.5	799.3	592.9	388.7
65°	3127.0	2896.4	2665.8	2281.5	1897.3	1513.0	1128.7	942.0	755.4	566.5	379.9
67.5°	2960.1	2690.0	2419.9	2068.5	1717.2	1365.8	1014.5	854.2	696.1	535.8	375.5
70°	2571.4	2334.2	2099.3	1794.0	1491.0	1185.8	880.6	748.8	619.2	487.5	355.7
72.5°	2158.6	1936.8	1717.2	1469.1	1223.1	975.0	726.8	628.0	529.2	428.2	329.4
75°	1653.5	1486.6	1321.9	1137.5	953.0	766.4	581.9	509.4	437.0	364.5	292.1
77.5°	1161.6	1071.6	983.8	845.4	707.1	568.7	430.4	382.1	333.8	285.5	237.2
80°	788.3	737.8	689.5	590.7	491.9	390.9	292.1	261.3	228.4	197.6	164.7
82.5°	489.7	487.5	483.1	415.0	347.0	278.9	210.8	184.5	160.3	133.9	107.6
85°	224.0	261.3	296.4	259.1	221.8	184.5	147.1	129.6	112.0	92.2	74.7
87.5°	70.3	85.6	98.8	94.4	87.8	83.4	76.9	65.9	54.9	43.9	32.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0
2.5°	1537.1	1530.5	1521.8	1513.0	1502.0	1493.2	1482.2	1471.3	1469.1	1464.7	1462.5
5°	1324.1	1311.0	1295.6	1282.4	1269.2	1253.9	1240.7	1225.3	1214.3	1201.2	1190.2
7.5°	1137.5	1115.5	1091.4	1067.2	1045.2	1023.3	999.1	977.2	966.2	955.2	944.2
10°	988.2	966.2	946.4	924.5	909.1	895.9	880.6	865.2	852.0	838.8	825.7
12.5°	913.5	898.1	882.8	867.4	849.8	834.4	816.9	799.3	783.9	770.8	755.4
15°	867.4	845.4	821.3	799.3	775.2	753.2	729.0	704.9	687.3	671.9	654.4
17.5°	812.5	779.5	748.8	715.9	689.5	663.2	634.6	608.3	588.5	566.5	546.8
20°	751.0	713.7	674.1	636.8	606.1	577.5	546.8	516.0	494.1	469.9	448.0
22.5°	698.3	650.0	599.5	549.0	516.0	483.1	448.0	415.0	395.3	373.3	353.5
25°	641.2	588.5	533.6	478.7	445.8	410.6	377.7	342.6	327.2	314.0	298.6
27.5°	610.5	557.8	502.9	450.2	419.4	386.5	355.7	322.8	311.8	298.6	287.7
30°	549.0	498.5	445.8	393.1	371.1	351.3	329.4	307.4	303.0	300.8	296.4
32.5°	494.1	441.4	388.7	336.0	316.2	296.4	276.7	256.9	254.7	250.3	248.1
35°	465.5	415.0	362.3	311.8	294.3	274.5	256.9	237.2	232.8	226.2	221.8
37.5°	458.9	406.2	351.3	298.6	281.1	263.5	243.7	226.2	221.8	217.4	213.0
40°	441.4	390.9	342.6	292.1	274.5	256.9	237.2	219.6	215.2	210.8	206.4
42.5°	428.2	379.9	329.4	278.9	263.5	248.1	230.6	215.2	210.8	206.4	199.8
45°	417.2	366.7	314.0	263.5	252.5	241.5	228.4	217.4	213.0	206.4	202.0
47.5°	399.7	351.3	300.8	250.3	239.4	230.6	219.6	208.6	204.2	199.8	195.4
50°	386.5	336.0	285.5	235.0	226.2	217.4	208.6	199.8	199.8	202.0	202.0
52.5°	368.9	320.6	272.3	224.0	215.2	206.4	197.6	188.8	191.0	193.2	195.4
55°	353.5	307.4	259.1	210.8	202.0	193.2	182.3	173.5	175.7	177.9	180.1
57.5°	347.0	298.6	250.3	202.0	193.2	182.3	173.5	162.5	162.5	162.5	162.5
60°	342.6	292.1	243.7	193.2	182.3	173.5	162.5	151.5	149.3	149.3	147.1
62.5°	340.4	289.9	241.5	191.0	177.9	166.9	153.7	140.5	138.3	136.1	133.9
65°	331.6	285.5	237.2	188.8	173.5	160.3	144.9	129.6	127.4	127.4	125.2
67.5°	329.4	281.1	235.0	186.7	171.3	153.7	138.3	120.8	118.6	116.4	114.2
70°	311.8	270.1	226.2	182.3	164.7	149.3	131.8	114.2	112.0	107.6	105.4
72.5°	289.9	252.5	213.0	173.5	155.9	138.3	120.8	103.2	101.0	98.8	94.4
75°	256.9	221.8	186.7	151.5	136.1	123.0	107.6	92.2	90.0	87.8	83.4
77.5°	210.8	182.3	155.9	127.4	116.4	105.4	94.4	83.4	81.2	79.1	74.7
80°	149.3	131.8	116.4	98.8	92.2	83.4	76.9	68.1	68.1	65.9	65.9
82.5°	98.8	90.0	81.2	72.5	68.1	63.7	59.3	54.9	54.9	52.7	52.7
85°	70.3	65.9	59.3	54.9	52.7	48.3	46.1	41.7	41.7	41.7	41.7
87.5°	32.9	32.9	30.7	30.7	28.5	28.5	26.4	24.2	24.2	24.2	24.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0
2.5°	1458.1	1451.5	1444.9	1436.1	1429.5	1420.7	1409.8	1401.0	1390.0	1390.0	1387.8
5°	1177.0	1170.4	1163.8	1155.0	1148.5	1139.7	1133.1	1124.3	1115.5	1115.5	1113.3
7.5°	933.3	920.1	906.9	891.5	878.4	869.6	860.8	849.8	841.0	834.4	827.9
10°	812.5	799.3	783.9	770.8	755.4	744.4	733.4	720.3	709.3	700.5	691.7
12.5°	740.0	724.6	709.3	693.9	678.5	663.2	650.0	634.6	619.2	608.3	597.3
15°	636.8	621.4	606.1	590.7	575.3	557.8	540.2	520.4	502.9	494.1	487.5
17.5°	524.8	509.4	491.9	476.5	458.9	445.8	432.6	419.4	406.2	397.5	390.9
20°	423.8	406.2	388.7	371.1	353.5	344.8	336.0	327.2	318.4	311.8	307.4
22.5°	331.6	320.6	311.8	300.8	289.9	283.3	278.9	272.3	265.7	265.7	265.7
25°	283.3	276.7	272.3	265.7	259.1	256.9	254.7	250.3	248.1	245.9	245.9
27.5°	274.5	267.9	261.3	254.7	248.1	245.9	243.7	239.4	237.2	237.2	237.2
30°	292.1	289.9	287.7	285.5	283.3	278.9	272.3	267.9	261.3	256.9	252.5
32.5°	243.7	241.5	241.5	239.4	237.2	241.5	243.7	248.1	250.3	252.5	254.7
35°	215.2	210.8	206.4	202.0	197.6	195.4	193.2	191.0	188.8	188.8	186.7
37.5°	208.6	204.2	199.8	195.4	191.0	188.8	186.7	184.5	182.3	182.3	180.1
40°	202.0	197.6	195.4	191.0	186.7	184.5	182.3	177.9	175.7	173.5	173.5
42.5°	195.4	193.2	188.8	186.7	182.3	180.1	177.9	173.5	171.3	169.1	166.9
45°	195.4	191.0	186.7	182.3	177.9	175.7	171.3	169.1	164.7	164.7	162.5
47.5°	191.0	186.7	182.3	177.9	173.5	171.3	166.9	164.7	160.3	158.1	155.9
50°	202.0	195.4	186.7	180.1	171.3	169.1	164.7	162.5	158.1	155.9	153.7
52.5°	197.6	191.0	182.3	175.7	166.9	162.5	160.3	155.9	151.5	149.3	147.1
55°	182.3	175.7	171.3	164.7	158.1	153.7	149.3	144.9	140.5	138.3	138.3
57.5°	162.5	160.3	158.1	155.9	153.7	149.3	144.9	138.3	133.9	131.8	129.6
60°	144.9	147.1	149.3	151.5	153.7	147.1	140.5	133.9	127.4	125.2	123.0
62.5°	131.8	136.1	140.5	142.7	147.1	140.5	133.9	127.4	120.8	118.6	116.4
65°	123.0	125.2	125.2	127.4	127.4	123.0	120.8	116.4	112.0	109.8	109.8
67.5°	112.0	112.0	112.0	109.8	109.8	107.6	107.6	105.4	103.2	101.0	101.0
70°	101.0	101.0	101.0	98.8	98.8	96.6	96.6	94.4	92.2	92.2	90.0
72.5°	92.2	92.2	90.0	90.0	87.8	87.8	87.8	85.6	85.6	83.4	83.4
75°	81.2	81.2	79.1	79.1	76.9	76.9	76.9	74.7	74.7	74.7	72.5
77.5°	72.5	72.5	70.3	70.3	68.1	68.1	68.1	65.9	65.9	63.7	63.7
80°	63.7	63.7	61.5	61.5	59.3	59.3	57.1	57.1	54.9	54.9	52.7
82.5°	50.5	50.5	50.5	50.5	50.5	48.3	48.3	46.1	43.9	43.9	41.7
85°	41.7	41.7	41.7	39.5	39.5	39.5	37.3	37.3	35.1	32.9	32.9
87.5°	24.2	24.2	24.2	22.0	22.0	22.0	22.0	22.0	22.0	22.0	19.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067
 CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0
2.5°	1387.8	1385.6	1376.8	1368.0	1376.8	1385.6	1385.6	1385.6	1383.4	1383.4	1383.4
5°	1113.3	1111.1	1106.7	1102.3	1102.3	1100.1	1104.5	1108.9	1113.3	1117.7	1122.1
7.5°	819.1	812.5	805.9	799.3	803.7	805.9	812.5	816.9	823.5	827.9	838.8
10°	682.9	674.1	667.6	661.0	656.6	652.2	647.8	645.6	641.2	636.8	641.2
12.5°	584.1	573.1	562.2	549.0	546.8	544.6	540.2	535.8	531.4	527.0	524.8
15°	478.7	469.9	465.5	458.9	450.2	441.4	437.0	434.8	430.4	426.0	423.8
17.5°	382.1	373.3	366.7	360.1	357.9	353.5	353.5	353.5	353.5	353.5	353.5
20°	300.8	294.3	294.3	292.1	292.1	289.9	292.1	294.3	294.3	296.4	298.6
22.5°	263.5	263.5	261.3	259.1	261.3	261.3	263.5	265.7	267.9	270.1	272.3
25°	243.7	241.5	243.7	245.9	245.9	245.9	248.1	248.1	250.3	250.3	250.3
27.5°	235.0	235.0	237.2	237.2	239.4	239.4	239.4	237.2	237.2	235.0	235.0
30°	248.1	243.7	243.7	243.7	241.5	239.4	237.2	237.2	235.0	232.8	230.6
32.5°	256.9	259.1	256.9	252.5	250.3	245.9	243.7	239.4	237.2	232.8	228.4
35°	186.7	184.5	188.8	191.0	193.2	195.4	197.6	199.8	199.8	202.0	202.0
37.5°	180.1	177.9	177.9	175.7	175.7	175.7	175.7	175.7	173.5	173.5	175.7
40°	171.3	169.1	169.1	166.9	166.9	164.7	164.7	164.7	164.7	164.7	164.7
42.5°	164.7	162.5	162.5	162.5	162.5	160.3	160.3	158.1	158.1	155.9	155.9
45°	162.5	160.3	158.1	155.9	155.9	153.7	153.7	153.7	151.5	151.5	151.5
47.5°	153.7	151.5	151.5	149.3	149.3	147.1	147.1	147.1	144.9	144.9	144.9
50°	149.3	147.1	147.1	144.9	144.9	142.7	142.7	142.7	140.5	140.5	140.5
52.5°	142.7	140.5	140.5	140.5	138.3	136.1	136.1	136.1	133.9	133.9	133.9
55°	136.1	133.9	133.9	133.9	131.8	129.6	129.6	129.6	127.4	127.4	127.4
57.5°	127.4	125.2	125.2	123.0	123.0	123.0	123.0	123.0	120.8	120.8	120.8
60°	120.8	118.6	118.6	116.4	116.4	114.2	114.2	114.2	114.2	114.2	114.2
62.5°	114.2	112.0	109.8	107.6	109.8	109.8	109.8	109.8	107.6	107.6	107.6
65°	107.6	105.4	103.2	101.0	101.0	101.0	101.0	101.0	101.0	101.0	101.0
67.5°	98.8	96.6	94.4	92.2	94.4	94.4	94.4	94.4	94.4	94.4	94.4
70°	90.0	87.8	87.8	85.6	85.6	83.4	83.4	85.6	85.6	85.6	85.6
72.5°	81.2	79.1	79.1	76.9	76.9	76.9	76.9	76.9	76.9	76.9	76.9
75°	72.5	70.3	70.3	68.1	68.1	68.1	68.1	68.1	68.1	68.1	68.1
77.5°	61.5	59.3	59.3	59.3	59.3	59.3	59.3	61.5	61.5	61.5	61.5
80°	52.7	50.5	50.5	50.5	50.5	50.5	50.5	50.5	50.5	50.5	50.5
82.5°	41.7	39.5	39.5	39.5	39.5	39.5	39.5	39.5	39.5	39.5	39.5
85°	30.7	28.5	28.5	28.5	30.7	30.7	30.7	30.7	30.7	30.7	30.7
87.5°	19.8	17.6	17.6	17.6	19.8	19.8	19.8	19.8	17.6	17.6	17.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067
 CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0
2.5°	1383.4	1383.4	1383.4	1381.2	1379.0	1376.8	1374.6	1381.2	1385.6	1392.2	1396.6
5°	1124.3	1128.7	1130.9	1137.5	1144.1	1150.7	1157.2	1161.6	1166.0	1168.2	1172.6
7.5°	847.6	858.6	867.4	876.2	884.9	891.5	900.3	906.9	913.5	920.1	926.7
10°	643.4	647.8	650.0	658.8	665.4	674.1	680.7	687.3	693.9	698.3	704.9
12.5°	522.6	518.2	516.0	516.0	516.0	516.0	516.0	520.4	524.8	529.2	533.6
15°	421.6	419.4	417.2	415.0	412.8	408.4	406.2	410.6	415.0	419.4	423.8
17.5°	353.5	353.5	353.5	351.3	349.1	347.0	344.8	347.0	349.1	349.1	351.3
20°	303.0	305.2	307.4	309.6	309.6	311.8	311.8	314.0	316.2	316.2	318.4
22.5°	272.3	274.5	274.5	274.5	276.7	276.7	276.7	278.9	281.1	283.3	285.5
25°	248.1	248.1	245.9	245.9	248.1	248.1	248.1	248.1	250.3	250.3	250.3
27.5°	235.0	232.8	232.8	232.8	232.8	230.6	230.6	230.6	230.6	230.6	230.6
30°	228.4	226.2	224.0	221.8	221.8	219.6	217.4	217.4	217.4	217.4	217.4
32.5°	226.2	221.8	217.4	215.2	215.2	213.0	210.8	208.6	208.6	206.4	204.2
35°	202.0	199.8	199.8	197.6	195.4	193.2	191.0	191.0	191.0	188.8	188.8
37.5°	175.7	177.9	177.9	177.9	180.1	180.1	180.1	180.1	182.3	182.3	182.3
40°	164.7	164.7	164.7	166.9	169.1	169.1	171.3	171.3	173.5	173.5	173.5
42.5°	155.9	153.7	153.7	155.9	155.9	158.1	158.1	160.3	162.5	162.5	164.7
45°	151.5	149.3	149.3	149.3	149.3	147.1	147.1	149.3	151.5	153.7	155.9
47.5°	142.7	142.7	140.5	140.5	140.5	140.5	140.5	140.5	142.7	142.7	142.7
50°	138.3	138.3	136.1	136.1	136.1	136.1	136.1	136.1	136.1	136.1	136.1
52.5°	133.9	131.8	131.8	131.8	131.8	129.6	129.6	129.6	129.6	129.6	129.6
55°	127.4	125.2	125.2	125.2	125.2	125.2	125.2	125.2	127.4	127.4	127.4
57.5°	120.8	118.6	118.6	118.6	120.8	120.8	120.8	120.8	123.0	123.0	123.0
60°	114.2	114.2	114.2	114.2	114.2	114.2	114.2	116.4	116.4	118.6	118.6
62.5°	107.6	107.6	107.6	107.6	109.8	109.8	109.8	109.8	112.0	112.0	112.0
65°	101.0	101.0	101.0	101.0	103.2	103.2	103.2	103.2	103.2	103.2	103.2
67.5°	94.4	94.4	94.4	94.4	94.4	94.4	94.4	96.6	96.6	98.8	98.8
70°	85.6	83.4	83.4	85.6	85.6	87.8	87.8	90.0	90.0	92.2	92.2
72.5°	76.9	76.9	76.9	76.9	76.9	76.9	76.9	79.1	81.2	81.2	83.4
75°	68.1	68.1	68.1	68.1	70.3	70.3	70.3	72.5	72.5	74.7	74.7
77.5°	61.5	59.3	59.3	59.3	61.5	61.5	61.5	63.7	63.7	65.9	65.9
80°	50.5	50.5	50.5	50.5	52.7	52.7	52.7	52.7	54.9	54.9	54.9
82.5°	41.7	41.7	41.7	41.7	41.7	41.7	41.7	41.7	43.9	43.9	43.9
85°	30.7	30.7	30.7	30.7	32.9	32.9	32.9	32.9	32.9	32.9	32.9
87.5°	19.8	19.8	19.8	19.8	19.8	19.8	19.8	19.8	22.0	22.0	22.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067
 CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0
2.5°	1396.6	1396.6	1396.6	1396.6	1401.0	1403.2	1407.6	1409.8	1407.6	1405.4	1401.0
5°	1174.8	1177.0	1177.0	1179.2	1179.2	1179.2	1179.2	1179.2	1183.6	1188.0	1192.4
7.5°	928.9	931.1	933.3	935.5	935.5	935.5	933.3	933.3	935.5	935.5	937.6
10°	711.5	720.3	726.8	733.4	729.0	722.5	718.1	711.5	711.5	711.5	709.3
12.5°	538.0	540.2	544.6	546.8	544.6	544.6	542.4	540.2	542.4	546.8	549.0
15°	426.0	426.0	428.2	428.2	430.4	432.6	432.6	434.8	439.2	441.4	445.8
17.5°	353.5	355.7	355.7	357.9	357.9	360.1	360.1	360.1	364.5	368.9	375.5
20°	318.4	318.4	318.4	318.4	318.4	316.2	316.2	314.0	316.2	320.6	322.8
22.5°	285.5	287.7	287.7	287.7	285.5	283.3	278.9	276.7	276.7	278.9	278.9
25°	250.3	248.1	248.1	245.9	245.9	248.1	248.1	248.1	250.3	250.3	252.5
27.5°	230.6	228.4	228.4	226.2	226.2	228.4	228.4	228.4	228.4	228.4	228.4
30°	215.2	215.2	213.0	210.8	213.0	213.0	215.2	215.2	217.4	217.4	219.6
32.5°	204.2	202.0	202.0	199.8	202.0	202.0	204.2	204.2	206.4	208.6	208.6
35°	188.8	188.8	188.8	188.8	188.8	188.8	186.7	186.7	186.7	186.7	186.7
37.5°	180.1	180.1	177.9	175.7	175.7	175.7	175.7	175.7	173.5	171.3	169.1
40°	173.5	171.3	171.3	169.1	166.9	166.9	164.7	162.5	162.5	160.3	160.3
42.5°	164.7	162.5	162.5	160.3	158.1	158.1	155.9	153.7	153.7	153.7	151.5
45°	153.7	153.7	151.5	149.3	149.3	149.3	147.1	147.1	147.1	147.1	144.9
47.5°	142.7	142.7	140.5	140.5	140.5	140.5	138.3	138.3	138.3	138.3	138.3
50°	136.1	136.1	136.1	136.1	136.1	136.1	133.9	133.9	133.9	133.9	133.9
52.5°	129.6	129.6	129.6	129.6	129.6	129.6	129.6	129.6	129.6	129.6	129.6
55°	127.4	127.4	127.4	127.4	127.4	127.4	125.2	125.2	125.2	127.4	127.4
57.5°	123.0	123.0	120.8	120.8	120.8	120.8	120.8	120.8	120.8	120.8	120.8
60°	118.6	118.6	118.6	118.6	118.6	118.6	118.6	118.6	118.6	118.6	118.6
62.5°	112.0	112.0	112.0	112.0	112.0	114.2	114.2	114.2	114.2	114.2	112.0
65°	103.2	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4
67.5°	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8	98.8
70°	92.2	92.2	90.0	90.0	90.0	92.2	92.2	92.2	92.2	92.2	92.2
72.5°	83.4	83.4	83.4	83.4	83.4	83.4	83.4	83.4	83.4	85.6	85.6
75°	74.7	74.7	74.7	74.7	74.7	74.7	74.7	74.7	74.7	74.7	74.7
77.5°	65.9	65.9	63.7	63.7	63.7	65.9	65.9	65.9	65.9	68.1	68.1
80°	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	54.9	57.1	57.1
82.5°	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9	46.1	46.1
85°	32.9	35.1	35.1	35.1	35.1	35.1	35.1	35.1	35.1	37.3	37.3
87.5°	22.0	22.0	22.0	22.0	22.0	22.0	19.8	19.8	19.8	19.8	17.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067
 CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0
2.5°	1398.8	1401.0	1403.2	1403.2	1405.4	1407.6	1407.6	1416.4	1425.1	1429.5	1433.9
5°	1196.8	1194.6	1194.6	1192.4	1190.2	1196.8	1203.4	1216.5	1229.7	1231.9	1236.3
7.5°	937.6	939.8	942.0	942.0	944.2	937.6	928.9	931.1	933.3	944.2	953.0
10°	709.3	711.5	713.7	713.7	715.9	713.7	709.3	715.9	722.5	731.2	742.2
12.5°	551.2	557.8	564.3	568.7	575.3	579.7	581.9	590.7	597.3	608.3	619.2
15°	450.2	454.6	458.9	463.3	467.7	472.1	476.5	485.3	494.1	507.3	520.4
17.5°	379.9	379.9	382.1	382.1	382.1	386.5	390.9	395.3	397.5	410.6	423.8
20°	325.0	322.8	320.6	318.4	316.2	320.6	322.8	325.0	327.2	336.0	342.6
22.5°	278.9	278.9	281.1	281.1	281.1	278.9	274.5	276.7	276.7	281.1	287.7
25°	252.5	252.5	252.5	250.3	250.3	252.5	254.7	254.7	252.5	254.7	256.9
27.5°	228.4	230.6	230.6	232.8	232.8	235.0	235.0	235.0	235.0	237.2	239.4
30°	219.6	219.6	221.8	221.8	221.8	224.0	226.2	226.2	226.2	228.4	232.8
32.5°	210.8	213.0	215.2	217.4	219.6	221.8	221.8	224.0	224.0	226.2	228.4
35°	186.7	184.5	184.5	182.3	180.1	180.1	180.1	180.1	177.9	180.1	180.1
37.5°	166.9	166.9	166.9	164.7	164.7	166.9	166.9	166.9	166.9	169.1	169.1
40°	158.1	158.1	158.1	158.1	158.1	158.1	158.1	160.3	160.3	162.5	164.7
42.5°	151.5	151.5	151.5	151.5	151.5	153.7	153.7	153.7	153.7	155.9	155.9
45°	144.9	144.9	144.9	144.9	144.9	144.9	144.9	147.1	147.1	149.3	151.5
47.5°	138.3	138.3	138.3	138.3	138.3	140.5	142.7	142.7	142.7	144.9	144.9
50°	133.9	133.9	133.9	133.9	133.9	136.1	136.1	138.3	138.3	140.5	142.7
52.5°	129.6	129.6	129.6	129.6	129.6	131.8	131.8	133.9	133.9	136.1	138.3
55°	127.4	127.4	127.4	125.2	125.2	127.4	127.4	129.6	129.6	131.8	131.8
57.5°	120.8	120.8	120.8	120.8	120.8	120.8	120.8	123.0	123.0	125.2	127.4
60°	118.6	118.6	116.4	116.4	114.2	116.4	116.4	118.6	118.6	120.8	120.8
62.5°	112.0	112.0	112.0	109.8	109.8	112.0	112.0	112.0	112.0	114.2	116.4
65°	105.4	105.4	105.4	103.2	103.2	105.4	105.4	105.4	105.4	107.6	109.8
67.5°	98.8	98.8	98.8	96.6	96.6	96.6	96.6	98.8	98.8	101.0	103.2
70°	92.2	92.2	92.2	90.0	90.0	90.0	87.8	90.0	92.2	94.4	94.4
72.5°	85.6	85.6	85.6	83.4	83.4	83.4	81.2	83.4	83.4	85.6	85.6
75°	74.7	74.7	74.7	74.7	74.7	74.7	72.5	72.5	72.5	74.7	74.7
77.5°	68.1	68.1	68.1	65.9	65.9	65.9	63.7	63.7	63.7	65.9	65.9
80°	57.1	57.1	57.1	54.9	54.9	54.9	52.7	52.7	52.7	54.9	54.9
82.5°	46.1	46.1	46.1	43.9	43.9	43.9	41.7	41.7	41.7	43.9	43.9
85°	37.3	37.3	37.3	37.3	37.3	37.3	35.1	35.1	35.1	37.3	39.5
87.5°	17.6	17.6	19.8	19.8	19.8	19.8	17.6	17.6	15.4	15.4	17.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0
2.5°	1438.3	1442.7	1453.7	1462.5	1473.4	1482.2	1488.8	1497.6	1504.2	1510.8	1515.2
5°	1238.5	1240.7	1251.7	1262.6	1271.4	1282.4	1297.8	1313.1	1328.5	1343.9	1354.9
7.5°	964.0	972.8	986.0	1001.3	1014.5	1027.7	1043.1	1060.6	1076.0	1091.4	1106.7
10°	751.0	759.8	773.0	786.1	797.1	810.3	827.9	845.4	863.0	880.6	898.1
12.5°	630.2	641.2	656.6	671.9	685.1	700.5	722.5	742.2	764.2	783.9	805.9
15°	531.4	544.6	564.3	586.3	606.1	625.8	647.8	669.7	689.5	711.5	733.4
17.5°	437.0	450.2	467.7	487.5	505.1	522.6	549.0	573.1	599.5	623.6	647.8
20°	351.3	357.9	375.5	393.1	410.6	428.2	448.0	467.7	487.5	507.3	538.0
22.5°	292.1	296.4	305.2	311.8	320.6	327.2	347.0	366.7	384.3	404.0	432.6
25°	256.9	259.1	265.7	270.1	276.7	281.1	294.3	305.2	318.4	329.4	355.7
27.5°	239.4	241.5	243.7	245.9	248.1	250.3	259.1	267.9	274.5	283.3	307.4
30°	235.0	237.2	243.7	248.1	254.7	259.1	263.5	267.9	272.3	276.7	292.1
32.5°	230.6	232.8	232.8	230.6	230.6	228.4	232.8	235.0	239.4	241.5	254.7
35°	182.3	182.3	184.5	186.7	188.8	191.0	197.6	202.0	208.6	213.0	224.0
37.5°	171.3	171.3	173.5	177.9	180.1	182.3	186.7	191.0	195.4	199.8	210.8
40°	164.7	166.9	169.1	171.3	173.5	175.7	180.1	182.3	186.7	188.8	197.6
42.5°	158.1	158.1	160.3	164.7	166.9	169.1	173.5	175.7	180.1	182.3	191.0
45°	153.7	155.9	158.1	160.3	160.3	162.5	166.9	171.3	173.5	177.9	186.7
47.5°	147.1	147.1	151.5	153.7	158.1	160.3	164.7	166.9	171.3	173.5	182.3
50°	142.7	144.9	149.3	151.5	155.9	158.1	164.7	169.1	175.7	180.1	184.5
52.5°	138.3	140.5	144.9	147.1	151.5	153.7	162.5	171.3	177.9	186.7	186.7
55°	133.9	133.9	138.3	144.9	149.3	153.7	158.1	164.7	169.1	173.5	173.5
57.5°	127.4	129.6	133.9	140.5	144.9	149.3	153.7	158.1	160.3	164.7	162.5
60°	123.0	123.0	129.6	136.1	142.7	149.3	149.3	149.3	147.1	147.1	147.1
62.5°	116.4	118.6	127.4	138.3	147.1	155.9	149.3	142.7	136.1	129.6	131.8
65°	112.0	114.2	118.6	125.2	129.6	133.9	129.6	127.4	123.0	118.6	120.8
67.5°	103.2	105.4	107.6	107.6	109.8	109.8	109.8	109.8	109.8	109.8	112.0
70°	96.6	96.6	96.6	98.8	98.8	98.8	98.8	98.8	98.8	98.8	101.0
72.5°	87.8	87.8	87.8	87.8	87.8	87.8	87.8	87.8	87.8	87.8	90.0
75°	76.9	76.9	76.9	76.9	76.9	76.9	76.9	76.9	76.9	76.9	79.1
77.5°	68.1	68.1	68.1	68.1	68.1	68.1	68.1	68.1	65.9	65.9	68.1
80°	57.1	57.1	57.1	57.1	54.9	54.9	54.9	54.9	54.9	54.9	57.1
82.5°	46.1	46.1	46.1	46.1	43.9	43.9	43.9	43.9	41.7	41.7	43.9
85°	41.7	43.9	43.9	46.1	46.1	46.1	43.9	41.7	39.5	37.3	37.3
87.5°	17.6	17.6	17.6	17.6	15.4	15.4	15.4	15.4	15.4	15.4	15.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067
 CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0
2.5°	1521.8	1526.1	1530.5	1537.1	1545.9	1552.5	1559.1	1572.3	1587.6	1600.8	1614.0
5°	1365.8	1376.8	1387.8	1401.0	1414.2	1425.1	1438.3	1464.7	1491.0	1515.2	1541.5
7.5°	1119.9	1135.3	1148.5	1170.4	1190.2	1212.1	1231.9	1264.8	1295.6	1328.5	1359.3
10°	915.7	933.3	950.8	979.4	1010.1	1038.7	1067.2	1093.6	1122.1	1148.5	1174.8
12.5°	827.9	847.6	869.6	887.1	906.9	924.5	942.0	972.8	1003.5	1034.3	1065.0
15°	755.4	777.3	799.3	821.3	841.0	863.0	882.8	909.1	937.6	964.0	990.4
17.5°	671.9	693.9	718.1	742.2	766.4	790.5	814.7	852.0	889.3	924.5	961.8
20°	566.5	597.3	625.8	658.8	691.7	724.6	757.6	797.1	836.6	874.0	913.5
22.5°	461.1	489.7	518.2	557.8	597.3	634.6	674.1	726.8	777.3	830.0	880.6
25°	384.3	410.6	437.0	480.9	522.6	566.5	608.3	671.9	733.4	797.1	858.6
27.5°	331.6	355.7	379.9	426.0	472.1	516.0	562.2	632.4	700.5	770.8	838.8
30°	307.4	322.8	338.2	382.1	426.0	467.7	511.6	579.7	647.8	715.9	783.9
32.5°	267.9	281.1	294.3	333.8	373.3	410.6	450.2	520.4	588.5	658.8	726.8
35°	237.2	248.1	259.1	296.4	331.6	368.9	404.0	474.3	544.6	614.9	685.1
37.5°	219.6	230.6	239.4	272.3	307.4	340.4	373.3	443.6	511.6	581.9	650.0
40°	206.4	213.0	221.8	254.7	285.5	318.4	349.1	412.8	478.7	542.4	606.1
42.5°	197.6	206.4	213.0	241.5	272.3	300.8	329.4	390.9	452.4	511.6	573.1
45°	195.4	204.2	213.0	237.2	261.3	283.3	307.4	366.7	426.0	485.3	544.6
47.5°	191.0	197.6	206.4	226.2	243.7	263.5	281.1	340.4	399.7	456.7	516.0
50°	188.8	191.0	195.4	213.0	230.6	248.1	265.7	325.0	384.3	443.6	502.9
52.5°	186.7	186.7	186.7	202.0	217.4	230.6	245.9	305.2	366.7	426.0	485.3
55°	173.5	171.3	171.3	186.7	199.8	215.2	228.4	287.7	347.0	404.0	463.3
57.5°	160.3	158.1	155.9	169.1	182.3	195.4	208.6	267.9	329.4	388.7	448.0
60°	147.1	144.9	144.9	158.1	169.1	182.3	193.2	254.7	314.0	375.5	434.8
62.5°	131.8	133.9	133.9	144.9	158.1	169.1	180.1	241.5	305.2	366.7	428.2
65°	120.8	123.0	123.0	136.1	149.3	162.5	175.7	235.0	296.4	355.7	415.0
67.5°	112.0	114.2	114.2	129.6	142.7	158.1	171.3	224.0	278.9	331.6	384.3
70°	103.2	103.2	105.4	120.8	136.1	151.5	166.9	213.0	259.1	303.0	349.1
72.5°	92.2	94.4	96.6	112.0	125.2	140.5	153.7	195.4	237.2	278.9	320.6
75°	81.2	83.4	85.6	98.8	112.0	125.2	138.3	177.9	215.2	254.7	292.1
77.5°	72.5	74.7	76.9	87.8	98.8	109.8	120.8	149.3	180.1	208.6	237.2
80°	59.3	59.3	61.5	70.3	79.1	85.6	94.4	114.2	133.9	151.5	171.3
82.5°	43.9	46.1	46.1	52.7	57.1	63.7	68.1	79.1	87.8	98.8	107.6
85°	37.3	35.1	35.1	39.5	41.7	46.1	48.3	54.9	59.3	65.9	70.3
87.5°	15.4	13.2	13.2	15.4	19.8	22.0	24.2	24.2	26.4	26.4	26.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067
 CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0
2.5°	1620.6	1625.0	1631.6	1635.9	1646.9	1655.7	1666.7	1675.5	1682.1	1693.0	1688.6
5°	1561.3	1581.0	1600.8	1620.6	1635.9	1651.3	1664.5	1679.9	1697.4	1730.4	1739.2
7.5°	1385.6	1412.0	1436.1	1462.5	1493.2	1524.0	1554.7	1585.4	1614.0	1655.7	1682.1
10°	1212.1	1249.5	1284.6	1321.9	1350.5	1379.0	1405.4	1433.9	1473.4	1515.2	1563.5
12.5°	1102.3	1139.7	1177.0	1214.3	1256.1	1295.6	1337.3	1376.8	1414.2	1447.1	1502.0
15°	1029.9	1071.6	1111.1	1150.7	1201.2	1249.5	1300.0	1348.3	1403.2	1447.1	1484.4
17.5°	1012.3	1062.8	1111.1	1161.6	1214.3	1267.0	1319.7	1372.4	1427.3	1493.2	1541.5
20°	981.6	1049.6	1117.7	1185.8	1253.9	1319.7	1387.8	1453.7	1526.1	1605.2	1627.2
22.5°	964.0	1045.2	1128.7	1209.9	1302.2	1396.6	1488.8	1581.0	1657.9	1717.2	1783.1
25°	961.8	1062.8	1166.0	1267.0	1383.4	1497.6	1614.0	1728.2	1827.0	1886.3	1939.0
27.5°	959.6	1082.6	1203.4	1324.1	1466.9	1607.4	1750.1	1890.7	1982.9	2068.5	2112.5
30°	933.3	1080.4	1229.7	1376.8	1537.1	1697.4	1857.7	2018.0	2112.5	2171.7	2193.7
32.5°	900.3	1073.8	1247.3	1420.7	1603.0	1785.3	1965.3	2147.6	2222.2	2272.8	2255.2
35°	874.0	1065.0	1253.9	1442.7	1635.9	1831.4	2024.6	2217.9	2325.5	2395.7	2367.2
37.5°	849.8	1049.6	1249.5	1449.3	1675.5	1901.6	2127.8	2354.0	2457.2	2531.9	2498.9
40°	821.3	1034.3	1249.5	1462.5	1721.6	1978.5	2237.6	2494.5	2628.5	2692.2	2641.7
42.5°	797.1	1018.9	1242.9	1464.7	1741.3	2018.0	2294.7	2571.4	2720.7	2810.8	2747.1
45°	766.4	988.2	1207.7	1429.5	1734.8	2040.0	2343.0	2648.3	2821.7	2892.0	2804.2
47.5°	733.4	953.0	1170.4	1387.8	1712.8	2037.8	2362.8	2687.8	2848.1	2931.5	2850.3
50°	722.5	942.0	1159.4	1379.0	1730.4	2083.9	2435.3	2786.6	2903.0	2971.1	2863.5
52.5°	720.3	953.0	1188.0	1420.7	1774.3	2125.6	2479.2	2830.5	2924.9	2997.4	2900.8
55°	713.7	966.2	1216.5	1466.9	1835.8	2206.9	2575.8	2944.7	3039.1	3091.8	3019.4
57.5°	720.3	992.5	1262.6	1534.9	1914.8	2294.7	2674.6	3054.5	3168.7	3206.0	3190.6
60°	724.6	1014.5	1302.2	1592.0	1963.1	2334.2	2705.3	3076.5	3195.0	3287.3	3304.8
62.5°	713.7	999.1	1282.4	1567.9	1903.8	2239.8	2575.8	2911.8	3107.2	3243.3	3322.4
65°	680.7	944.2	1209.9	1473.4	1783.1	2094.9	2404.5	2714.1	2920.5	3122.6	3186.2
67.5°	608.3	832.2	1056.2	1280.2	1550.3	1820.4	2088.3	2358.4	2617.5	2812.9	2900.8
70°	527.0	702.7	880.6	1056.2	1302.2	1548.1	1794.0	2040.0	2268.4	2483.6	2567.0
72.5°	458.9	595.1	733.4	869.6	1045.2	1218.7	1394.4	1567.9	1838.0	2053.2	2134.4
75°	390.9	489.7	586.3	685.1	805.9	926.7	1045.2	1166.0	1357.1	1550.3	1631.6
77.5°	300.8	366.7	430.4	494.1	577.5	658.8	742.2	823.5	957.4	1102.3	1144.1
80°	208.6	245.9	281.1	318.4	384.3	450.2	516.0	581.9	669.7	751.0	814.7
82.5°	129.6	153.7	175.7	197.6	250.3	303.0	353.5	406.2	441.4	445.8	509.4
85°	83.4	98.8	112.0	125.2	155.9	188.8	219.6	250.3	224.0	208.6	248.1
87.5°	32.9	41.7	48.3	54.9	52.7	50.5	48.3	46.1	39.5	35.1	43.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067
 CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0
2.5°	1693.0	1699.6	1706.2	1710.6	1717.2	1719.4	1721.6	1721.6	1723.8	1726.0	1730.4
5°	1774.3	1787.5	1800.6	1811.6	1824.8	1835.8	1844.6	1855.5	1864.3	1864.3	1862.1
7.5°	1706.2	1739.2	1772.1	1805.0	1838.0	1862.1	1884.1	1908.2	1930.2	1934.6	1939.0
10°	1616.2	1651.3	1684.3	1719.4	1752.3	1789.7	1824.8	1859.9	1897.3	1903.8	1912.6
12.5°	1532.7	1574.5	1616.2	1655.7	1697.4	1723.8	1750.1	1774.3	1800.6	1818.2	1835.8
15°	1530.5	1565.7	1600.8	1633.7	1668.9	1684.3	1699.6	1712.8	1728.2	1728.2	1730.4
17.5°	1581.0	1603.0	1625.0	1644.7	1666.7	1668.9	1673.3	1675.5	1677.7	1671.1	1664.5
20°	1679.9	1688.6	1697.4	1706.2	1715.0	1699.6	1686.5	1671.1	1655.7	1638.1	1622.8
22.5°	1824.8	1805.0	1785.3	1765.5	1745.7	1719.4	1690.8	1664.5	1635.9	1614.0	1592.0
25°	1960.9	1936.8	1912.6	1888.5	1864.3	1807.2	1750.1	1690.8	1633.7	1609.6	1585.4
27.5°	2143.2	2105.9	2068.5	2031.2	1993.9	1917.0	1840.2	1763.3	1686.5	1644.7	1605.2
30°	2187.1	2145.4	2103.7	2059.8	2018.0	1943.4	1870.9	1796.2	1721.6	1673.3	1627.2
32.5°	2250.8	2202.5	2154.2	2105.9	2057.6	1985.1	1912.6	1838.0	1765.5	1721.6	1675.5
35°	2356.2	2301.3	2246.4	2189.3	2134.4	2059.8	1987.3	1912.6	1838.0	1787.5	1739.2
37.5°	2446.2	2382.6	2318.9	2255.2	2191.5	2125.6	2057.6	1991.7	1923.6	1873.1	1824.8
40°	2547.2	2477.0	2406.7	2338.6	2268.4	2206.9	2145.4	2081.7	2020.2	1980.7	1941.2
42.5°	2635.1	2549.4	2466.0	2382.6	2296.9	2255.2	2215.7	2173.9	2132.2	2112.5	2090.5
45°	2696.6	2617.5	2536.3	2457.2	2378.2	2347.4	2316.7	2285.9	2255.2	2275.0	2294.7
47.5°	2722.9	2659.2	2597.7	2536.3	2472.6	2483.6	2494.5	2503.3	2514.3	2540.7	2569.2
50°	2747.1	2711.9	2674.6	2639.5	2602.1	2643.9	2683.4	2725.1	2766.8	2821.7	2876.6
52.5°	2795.4	2775.6	2758.0	2738.3	2718.5	2791.0	2863.5	2935.9	3008.4	3069.9	3131.4
55°	2940.3	2924.9	2909.6	2892.0	2876.6	2979.8	3080.8	3184.1	3287.3	3350.9	3414.6
57.5°	3140.1	3131.4	3120.4	3111.6	3100.6	3201.6	3300.4	3399.3	3500.3	3561.7	3625.4
60°	3291.7	3293.8	3293.8	3296.0	3296.0	3372.9	3449.8	3528.8	3605.7	3658.4	3713.3
62.5°	3372.9	3368.5	3364.1	3359.7	3355.3	3419.0	3482.7	3546.4	3610.1	3649.6	3689.1
65°	3285.1	3309.2	3333.4	3357.5	3381.7	3390.5	3397.1	3405.8	3412.4	3436.6	3460.7
67.5°	2990.8	3039.1	3085.2	3133.5	3179.7	3146.7	3116.0	3083.0	3050.1	3056.7	3061.1
70°	2663.6	2718.5	2775.6	2830.5	2885.4	2808.6	2731.7	2652.6	2575.8	2549.4	2523.1
72.5°	2246.4	2294.7	2345.2	2393.5	2441.8	2347.4	2255.2	2160.8	2066.3	2020.2	1974.1
75°	1717.2	1774.3	1833.6	1890.7	1947.8	1842.4	1734.8	1629.4	1521.8	1491.0	1462.5
77.5°	1251.7	1319.7	1387.8	1455.9	1524.0	1429.5	1335.1	1238.5	1144.1	1126.5	1108.9
80°	911.3	964.0	1014.5	1067.2	1117.7	1062.8	1007.9	953.0	898.1	895.9	893.7
82.5°	614.9	661.0	704.9	751.0	794.9	773.0	753.2	731.2	709.3	731.2	755.4
85°	316.2	379.9	445.8	509.4	573.1	566.5	562.2	555.6	549.0	577.5	603.9
87.5°	63.7	118.6	173.5	226.2	281.1	267.9	254.7	239.4	226.2	235.0	241.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0
2.5°	1732.6	1734.8	1734.8	1734.8	1734.8	1734.8	1730.4	1728.2	1723.8	1719.4	1712.8
5°	1862.1	1859.9	1851.1	1842.4	1831.4	1822.6	1816.0	1807.2	1800.6	1791.9	1778.7
7.5°	1943.4	1947.8	1932.4	1919.2	1903.8	1888.5	1873.1	1857.7	1842.4	1827.0	1796.2
10°	1919.2	1925.8	1917.0	1908.2	1897.3	1888.5	1870.9	1851.1	1833.6	1813.8	1776.5
12.5°	1851.1	1868.7	1864.3	1859.9	1855.5	1851.1	1840.2	1827.0	1816.0	1802.8	1761.1
15°	1730.4	1730.4	1732.6	1734.8	1734.8	1737.0	1739.2	1741.3	1743.5	1745.7	1721.6
17.5°	1657.9	1651.3	1651.3	1651.3	1651.3	1651.3	1660.1	1671.1	1679.9	1688.6	1682.1
20°	1605.2	1589.8	1587.6	1587.6	1585.4	1583.2	1598.6	1616.2	1631.6	1646.9	1655.7
22.5°	1570.1	1548.1	1545.9	1543.7	1541.5	1539.3	1559.1	1578.9	1598.6	1618.4	1649.1
25°	1561.3	1537.1	1539.3	1541.5	1541.5	1543.7	1559.1	1574.5	1589.8	1605.2	1657.9
27.5°	1563.5	1524.0	1526.1	1528.3	1528.3	1530.5	1554.7	1576.7	1600.8	1622.8	1688.6
30°	1578.9	1532.7	1528.3	1524.0	1519.6	1515.2	1548.1	1581.0	1614.0	1646.9	1697.4
32.5°	1631.6	1587.6	1576.7	1565.7	1554.7	1543.7	1583.2	1620.6	1660.1	1697.4	1739.2
35°	1688.6	1640.3	1635.9	1631.6	1625.0	1620.6	1655.7	1693.0	1728.2	1763.3	1800.6
37.5°	1774.3	1726.0	1721.6	1715.0	1710.6	1704.0	1743.5	1780.9	1820.4	1857.7	1890.7
40°	1901.6	1862.1	1859.9	1859.9	1857.7	1855.5	1886.3	1919.2	1950.0	1980.7	2002.7
42.5°	2070.7	2051.0	2057.6	2066.3	2072.9	2079.5	2103.7	2130.0	2154.2	2178.3	2171.7
45°	2314.5	2334.2	2336.4	2338.6	2340.8	2343.0	2349.6	2358.4	2365.0	2371.6	2345.2
47.5°	2595.6	2621.9	2635.1	2648.3	2659.2	2672.4	2663.6	2652.6	2643.9	2632.9	2567.0
50°	2929.3	2984.2	2982.0	2979.8	2975.4	2973.2	2955.7	2938.1	2918.3	2900.8	2804.2
52.5°	3192.8	3254.3	3265.3	3276.3	3287.3	3298.2	3265.3	3232.4	3197.2	3164.3	3043.5
55°	3476.1	3539.8	3542.0	3544.2	3544.2	3546.4	3500.3	3454.1	3405.8	3359.7	3234.6
57.5°	3686.9	3748.4	3741.8	3737.4	3730.8	3724.2	3669.3	3614.4	3559.6	3504.7	3379.5
60°	3766.0	3818.7	3805.5	3792.3	3776.9	3763.8	3722.0	3680.3	3636.4	3594.7	3473.9
62.5°	3728.6	3768.2	3748.4	3730.8	3711.1	3691.3	3638.6	3583.7	3531.0	3476.1	3388.3
65°	3482.7	3506.9	3480.5	3456.3	3432.2	3405.8	3361.9	3318.0	3271.9	3228.0	3168.7
67.5°	3067.7	3072.1	3069.9	3067.7	3065.5	3063.3	2999.6	2935.9	2870.0	2806.4	2802.0
70°	2498.9	2472.6	2477.0	2483.6	2488.0	2492.3	2444.0	2397.9	2349.6	2301.3	2323.3
72.5°	1928.0	1881.9	1892.9	1906.0	1917.0	1928.0	1888.5	1851.1	1811.6	1772.1	1802.8
75°	1431.7	1403.2	1414.2	1427.3	1438.3	1449.3	1433.9	1418.6	1401.0	1385.6	1414.2
77.5°	1091.4	1073.8	1076.0	1076.0	1078.2	1078.2	1080.4	1084.8	1087.0	1089.2	1119.9
80°	889.3	887.1	884.9	882.8	878.4	876.2	898.1	920.1	942.0	964.0	979.4
82.5°	777.3	799.3	786.1	775.2	762.0	748.8	768.6	788.3	808.1	827.9	821.3
85°	632.4	658.8	634.6	610.5	584.1	560.0	577.5	592.9	610.5	625.8	617.0
87.5°	250.3	256.9	217.4	180.1	140.5	101.0	160.3	217.4	276.7	333.8	342.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067
 CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0	1581.0
2.5°	1706.2	1697.4	1690.8	1688.6	1684.3	1682.1	1677.7	1673.3	1666.7	1662.3	1655.7
5°	1763.3	1750.1	1734.8	1712.8	1693.0	1671.1	1649.1	1629.4	1609.6	1587.6	1567.9
7.5°	1765.5	1734.8	1704.0	1675.5	1644.7	1616.2	1585.4	1559.1	1530.5	1502.0	1475.6
10°	1741.3	1704.0	1666.7	1629.4	1594.2	1556.9	1519.6	1488.8	1455.9	1422.9	1392.2
12.5°	1721.6	1679.9	1638.1	1594.2	1552.5	1508.6	1464.7	1433.9	1403.2	1372.4	1341.7
15°	1697.4	1671.1	1646.9	1607.4	1567.9	1528.3	1488.8	1447.1	1407.6	1365.8	1324.1
17.5°	1677.7	1671.1	1664.5	1638.1	1611.8	1583.2	1556.9	1515.2	1473.4	1429.5	1387.8
20°	1666.7	1675.5	1684.3	1671.1	1657.9	1642.5	1629.4	1598.6	1567.9	1534.9	1504.2
22.5°	1679.9	1712.8	1743.5	1745.7	1750.1	1752.3	1754.5	1726.0	1697.4	1666.7	1638.1
25°	1710.6	1763.3	1816.0	1844.6	1873.1	1903.8	1932.4	1914.8	1897.3	1879.7	1862.1
27.5°	1752.3	1818.2	1884.1	1925.8	1965.3	2007.1	2048.8	2046.6	2044.4	2040.0	2037.8
30°	1745.7	1796.2	1846.8	1897.3	1947.8	1998.3	2048.8	2075.1	2099.3	2125.6	2152.0
32.5°	1783.1	1824.8	1868.7	1921.4	1974.1	2029.0	2081.7	2136.6	2189.3	2244.2	2299.1
35°	1840.2	1877.5	1917.0	1974.1	2033.4	2090.5	2149.8	2215.7	2283.7	2351.8	2417.7
37.5°	1925.8	1958.7	1993.9	2042.2	2092.7	2141.0	2191.5	2288.1	2384.7	2483.6	2580.2
40°	2024.6	2046.6	2068.5	2114.7	2160.8	2206.9	2253.0	2373.8	2494.5	2615.3	2736.1
42.5°	2167.4	2160.8	2154.2	2191.5	2231.0	2268.4	2307.9	2417.7	2527.5	2637.3	2747.1
45°	2318.9	2292.5	2266.2	2283.7	2303.5	2321.1	2340.8	2452.8	2564.8	2679.0	2791.0
47.5°	2501.1	2435.3	2369.4	2354.0	2338.6	2321.1	2305.7	2426.5	2547.2	2670.2	2791.0
50°	2707.5	2608.7	2512.1	2472.6	2430.9	2391.3	2349.6	2448.4	2549.4	2650.5	2749.3
52.5°	2922.7	2799.8	2679.0	2617.5	2556.0	2492.3	2430.9	2514.3	2599.9	2685.6	2769.0
55°	3107.2	2982.0	2854.7	2782.2	2709.7	2637.3	2564.8	2648.3	2731.7	2815.1	2898.6
57.5°	3254.3	3129.2	3004.0	2935.9	2865.6	2797.6	2727.3	2806.4	2887.6	2968.9	3047.9
60°	3355.3	3234.6	3113.8	3047.9	2982.0	2916.2	2850.3	2944.7	3039.1	3135.7	3230.2
62.5°	3302.6	3214.8	3127.0	3098.4	3069.9	3039.1	3010.6	3100.6	3188.4	3278.5	3368.5
65°	3109.4	3050.1	2990.8	3019.4	3050.1	3078.7	3109.4	3168.7	3228.0	3289.5	3348.7
67.5°	2795.4	2791.0	2784.4	2848.1	2911.8	2977.6	3041.3	3080.8	3118.2	3157.7	3197.2
70°	2345.2	2369.4	2391.3	2501.1	2610.9	2720.7	2830.5	2845.9	2861.3	2876.6	2892.0
72.5°	1835.8	1866.5	1899.5	2044.4	2187.1	2332.0	2477.0	2468.2	2459.4	2448.4	2439.6
75°	1444.9	1473.4	1504.2	1638.1	1772.1	1906.0	2040.0	2002.7	1967.5	1930.2	1892.9
77.5°	1152.8	1183.6	1216.5	1341.7	1466.9	1594.2	1719.4	1629.4	1539.3	1449.3	1359.3
80°	992.5	1007.9	1021.1	1106.7	1190.2	1275.8	1361.5	1269.2	1174.8	1080.4	988.2
82.5°	814.7	805.9	799.3	849.8	900.3	950.8	1001.3	913.5	825.7	735.6	647.8
85°	608.3	599.5	590.7	617.0	643.4	671.9	698.3	597.3	496.3	393.1	292.1
87.5°	353.5	362.3	371.1	399.7	428.2	458.9	487.5	384.3	281.1	175.7	72.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676067
 CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676067

CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1581.0	1581.0
2.5°	1642.5	1631.6
5°	1552.5	1537.1
7.5°	1453.7	1433.9
10°	1363.7	1337.3
12.5°	1306.6	1273.6
15°	1284.6	1245.1
17.5°	1350.5	1313.1
20°	1451.5	1401.0
22.5°	1574.5	1513.0
25°	1787.5	1712.8
27.5°	1960.9	1884.1
30°	2068.5	1985.1
32.5°	2187.1	2077.3
35°	2310.1	2204.7
37.5°	2459.4	2340.8
40°	2613.1	2490.1
42.5°	2665.8	2586.8
45°	2716.3	2641.7
47.5°	2727.3	2665.8
50°	2738.3	2729.5
52.5°	2769.0	2766.8
55°	2900.8	2903.0
57.5°	3063.3	3076.5
60°	3212.6	3197.2
62.5°	3289.5	3210.4
65°	3236.8	3127.0
67.5°	3078.7	2960.1
70°	2731.7	2571.4
72.5°	2299.1	2158.6
75°	1772.1	1653.5
77.5°	1260.4	1161.6
80°	887.1	788.3
82.5°	568.7	489.7
85°	256.9	224.0
87.5°	72.5	70.3
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P676067
CATALOG NUMBER: CCW-SA-1E-850-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)