

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P676069

Luminaire Tested: **CCW-SA-2A-850-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P676069
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2A-850-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @350mA w/
SLR distribution lens
Light Source: (32) 5000K CCT, 80 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3962.3 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 36.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 5.6 fc
 Type IV - Short - N/A

REPORT NUMBER: P676069
CATALOG NUMBER: CCW-SA-2A-850-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	815.3	0.0	815.3
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3147.0	0.0	3147.0
	% Fixture	79.4	0.0	79.4
Total	Lumens	3962.3	0.0	3962.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.3	2.5
10°-20°	207.6	5.2
20°-30°	303.7	7.7
30°-40°	427.9	10.8
40°-50°	587.9	14.8
50°-60°	801.4	20.2
60°-70°	877.1	22.1
70°-80°	506.5	12.8
80°-90°	151.8	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3962.3	100.0
0°-180°	3962.3	100.0

Coefficient of Utilization



REPORT NUMBER: P676069


CATALOG NUMBER: CCW-SA-2A-850-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	406.9	10.3			
FM	(30°-60°)	1445.9	36.5			
FH	(60°-80°)	1165.1	29.4			G1/1800
FVH	(80°-90°)	129.0	3.3			G2/225
BL	(0°-30°)	202.7	5.1	B1/500		
BM	(30°-60°)	371.2	9.4	B1/1000		
BH	(60°-80°)	218.5	5.5	B1/500		G1/500
BVH	(80°-90°)	22.9	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3
2.5°	1305.7	1298.7	1293.4	1288.1	1281.1	1275.8	1268.8	1261.8	1253.0	1246.0	1237.2
5°	1230.2	1209.1	1188.0	1175.7	1161.6	1149.3	1135.3	1119.4	1103.6	1086.1	1070.2
7.5°	1147.6	1121.2	1094.8	1073.7	1050.9	1029.8	1007.0	987.6	968.3	949.0	929.6
10°	1070.2	1045.6	1021.0	994.7	966.5	940.2	912.1	885.7	859.4	833.0	806.6
12.5°	1019.3	989.4	961.3	931.4	903.3	873.4	843.5	818.9	794.3	768.0	743.4
15°	996.4	968.3	941.9	912.1	882.2	852.3	822.4	794.3	768.0	739.8	711.7
17.5°	1050.9	1010.5	970.1	931.4	892.7	854.1	815.4	780.3	745.1	710.0	674.8
20°	1121.2	1070.2	1021.0	973.6	924.4	876.9	827.7	778.5	729.3	680.1	630.9
22.5°	1210.8	1152.8	1096.6	1035.1	971.8	910.3	847.0	785.5	724.0	660.8	599.3
25°	1370.7	1302.2	1233.7	1145.8	1056.2	968.3	878.7	797.8	718.8	637.9	557.1
27.5°	1507.8	1414.7	1323.3	1217.9	1112.4	1007.0	901.5	808.4	717.0	623.9	530.7
30°	1588.7	1497.3	1405.9	1277.6	1151.1	1022.8	894.5	790.8	688.9	585.2	481.5
32.5°	1662.5	1560.5	1458.6	1318.0	1175.7	1035.1	892.7	778.5	666.0	551.8	437.6
35°	1764.4	1651.9	1541.2	1377.8	1214.3	1050.9	887.5	769.7	650.2	532.5	413.0
37.5°	1873.3	1734.5	1597.4	1416.4	1235.4	1054.4	873.4	757.4	641.4	525.5	409.5
40°	1992.8	1824.1	1657.2	1456.9	1258.3	1057.9	857.6	741.6	625.6	507.9	391.9
42.5°	2070.2	1887.4	1704.6	1488.5	1274.1	1057.9	841.8	727.5	613.3	497.3	383.1
45°	2114.1	1936.6	1760.9	1527.1	1293.4	1059.7	826.0	713.5	601.0	486.8	374.3
47.5°	2133.4	1968.2	1803.1	1557.0	1312.8	1066.7	820.7	706.5	590.5	476.2	360.3
50°	2184.4	2038.5	1892.7	1629.1	1367.2	1103.6	840.0	717.0	595.7	472.7	349.7
52.5°	2214.3	2089.5	1964.7	1694.1	1423.5	1152.8	882.2	745.1	608.0	471.0	333.9
55°	2323.2	2203.7	2084.2	1796.0	1506.1	1217.9	927.9	776.8	625.6	472.7	321.6
57.5°	2462.1	2335.5	2210.8	1899.7	1588.7	1277.6	966.5	804.9	641.4	479.8	316.3
60°	2558.7	2435.7	2314.4	1984.1	1651.9	1321.5	989.4	820.7	652.0	481.5	312.8
62.5°	2569.3	2411.1	2254.7	1933.1	1611.5	1288.1	966.5	803.1	639.7	474.5	311.1
65°	2502.5	2318.0	2133.4	1825.9	1518.4	1210.8	903.3	753.9	604.5	453.4	304.0
67.5°	2368.9	2152.8	1936.6	1655.4	1374.3	1093.1	811.9	683.6	557.1	428.8	300.5
70°	2057.9	1868.1	1680.0	1435.8	1193.2	949.0	704.7	599.3	495.6	390.1	284.7
72.5°	1727.5	1550.0	1374.3	1175.7	978.9	780.3	581.7	502.6	423.5	342.7	263.6
75°	1323.3	1189.7	1057.9	910.3	762.7	613.3	465.7	407.7	349.7	291.7	233.7
77.5°	929.6	857.6	787.3	676.6	565.9	455.2	344.4	305.8	267.1	228.5	189.8
80°	630.9	590.5	551.8	472.7	393.6	312.8	233.7	209.1	182.8	158.2	131.8
82.5°	391.9	390.1	386.6	332.1	277.7	223.2	168.7	147.6	128.3	107.2	86.1
85°	179.3	209.1	237.2	207.4	177.5	147.6	117.7	103.7	89.6	73.8	59.8
87.5°	56.2	68.5	79.1	75.6	70.3	66.8	61.5	52.7	43.9	35.1	26.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069
 CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3
2.5°	1230.2	1224.9	1217.9	1210.8	1202.0	1195.0	1186.2	1177.4	1175.7	1172.2	1170.4
5°	1059.7	1049.1	1036.8	1026.3	1015.8	1003.5	992.9	980.6	971.8	961.3	952.5
7.5°	910.3	892.7	873.4	854.1	836.5	818.9	799.6	782.0	773.2	764.5	755.7
10°	790.8	773.2	757.4	739.8	727.5	717.0	704.7	692.4	681.9	671.3	660.8
12.5°	731.1	718.8	706.5	694.2	680.1	667.8	653.7	639.7	627.4	616.8	604.5
15°	694.2	676.6	657.3	639.7	620.3	602.8	583.4	564.1	550.1	537.8	523.7
17.5°	650.2	623.9	599.3	572.9	551.8	530.7	507.9	486.8	471.0	453.4	437.6
20°	601.0	571.1	539.5	509.6	485.0	462.2	437.6	413.0	395.4	376.1	358.5
22.5°	558.8	520.2	479.8	439.3	413.0	386.6	358.5	332.1	316.3	298.8	282.9
25°	513.2	471.0	427.0	383.1	356.7	328.6	302.3	274.1	261.8	251.3	239.0
27.5°	488.5	446.4	402.4	360.3	335.7	309.3	284.7	258.3	249.5	239.0	230.2
30°	439.3	398.9	356.7	314.6	297.0	281.2	263.6	246.0	242.5	240.8	237.2
32.5°	395.4	353.2	311.1	268.9	253.1	237.2	221.4	205.6	203.9	200.3	198.6
35°	372.6	332.1	290.0	249.5	235.5	219.7	205.6	189.8	186.3	181.0	177.5
37.5°	367.3	325.1	281.2	239.0	224.9	210.9	195.1	181.0	177.5	174.0	170.5
40°	353.2	312.8	274.1	233.7	219.7	205.6	189.8	175.7	172.2	168.7	165.2
42.5°	342.7	304.0	263.6	223.2	210.9	198.6	184.5	172.2	168.7	165.2	159.9
45°	333.9	293.5	251.3	210.9	202.1	193.3	182.8	174.0	170.5	165.2	161.7
47.5°	319.8	281.2	240.8	200.3	191.6	184.5	175.7	166.9	163.4	159.9	156.4
50°	309.3	268.9	228.5	188.0	181.0	174.0	166.9	159.9	159.9	161.7	161.7
52.5°	295.2	256.6	217.9	179.3	172.2	165.2	158.2	151.1	152.9	154.6	156.4
55°	282.9	246.0	207.4	168.7	161.7	154.6	145.9	138.8	140.6	142.3	144.1
57.5°	277.7	239.0	200.3	161.7	154.6	145.9	138.8	130.0	130.0	130.0	130.0
60°	274.1	233.7	195.1	154.6	145.9	138.8	130.0	121.3	119.5	119.5	117.7
62.5°	272.4	232.0	193.3	152.9	142.3	133.6	123.0	112.5	110.7	109.0	107.2
65°	265.4	228.5	189.8	151.1	138.8	128.3	116.0	103.7	101.9	101.9	100.2
67.5°	263.6	224.9	188.0	149.4	137.1	123.0	110.7	96.7	94.9	93.1	91.4
70°	249.5	216.2	181.0	145.9	131.8	119.5	105.4	91.4	89.6	86.1	84.4
72.5°	232.0	202.1	170.5	138.8	124.8	110.7	96.7	82.6	80.8	79.1	75.6
75°	205.6	177.5	149.4	121.3	109.0	98.4	86.1	73.8	72.1	70.3	66.8
77.5°	168.7	145.9	124.8	101.9	93.1	84.4	75.6	66.8	65.0	63.3	59.8
80°	119.5	105.4	93.1	79.1	73.8	66.8	61.5	54.5	54.5	52.7	52.7
82.5°	79.1	72.1	65.0	58.0	54.5	51.0	47.4	43.9	43.9	42.2	42.2
85°	56.2	52.7	47.4	43.9	42.2	38.7	36.9	33.4	33.4	33.4	33.4
87.5°	26.4	26.4	24.6	24.6	22.8	22.8	21.1	19.3	19.3	19.3	19.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3
2.5°	1166.9	1161.6	1156.3	1149.3	1144.0	1137.0	1128.2	1121.2	1112.4	1112.4	1110.7
5°	941.9	936.7	931.4	924.4	919.1	912.1	906.8	899.8	892.7	892.7	891.0
7.5°	746.9	736.3	725.8	713.5	702.9	695.9	688.9	680.1	673.1	667.8	662.5
10°	650.2	639.7	627.4	616.8	604.5	595.7	587.0	576.4	567.6	560.6	553.6
12.5°	592.2	579.9	567.6	555.3	543.0	530.7	520.2	507.9	495.6	486.8	478.0
15°	509.6	497.3	485.0	472.7	460.4	446.4	432.3	416.5	402.4	395.4	390.1
17.5°	420.0	407.7	393.6	381.3	367.3	356.7	346.2	335.7	325.1	318.1	312.8
20°	339.2	325.1	311.1	297.0	282.9	275.9	268.9	261.8	254.8	249.5	246.0
22.5°	265.4	256.6	249.5	240.8	232.0	226.7	223.2	217.9	212.6	212.6	212.6
25°	226.7	221.4	217.9	212.6	207.4	205.6	203.9	200.3	198.6	196.8	196.8
27.5°	219.7	214.4	209.1	203.9	198.6	196.8	195.1	191.6	189.8	189.8	189.8
30°	233.7	232.0	230.2	228.5	226.7	223.2	217.9	214.4	209.1	205.6	202.1
32.5°	195.1	193.3	193.3	191.6	189.8	193.3	195.1	198.6	200.3	202.1	203.9
35°	172.2	168.7	165.2	161.7	158.2	156.4	154.6	152.9	151.1	151.1	149.4
37.5°	166.9	163.4	159.9	156.4	152.9	151.1	149.4	147.6	145.9	145.9	144.1
40°	161.7	158.2	156.4	152.9	149.4	147.6	145.9	142.3	140.6	138.8	138.8
42.5°	156.4	154.6	151.1	149.4	145.9	144.1	142.3	138.8	137.1	135.3	133.6
45°	156.4	152.9	149.4	145.9	142.3	140.6	137.1	135.3	131.8	131.8	130.0
47.5°	152.9	149.4	145.9	142.3	138.8	137.1	133.6	131.8	128.3	126.5	124.8
50°	161.7	156.4	149.4	144.1	137.1	135.3	131.8	130.0	126.5	124.8	123.0
52.5°	158.2	152.9	145.9	140.6	133.6	130.0	128.3	124.8	121.3	119.5	117.7
55°	145.9	140.6	137.1	131.8	126.5	123.0	119.5	116.0	112.5	110.7	110.7
57.5°	130.0	128.3	126.5	124.8	123.0	119.5	116.0	110.7	107.2	105.4	103.7
60°	116.0	117.7	119.5	121.3	123.0	117.7	112.5	107.2	101.9	100.2	98.4
62.5°	105.4	109.0	112.5	114.2	117.7	112.5	107.2	101.9	96.7	94.9	93.1
65°	98.4	100.2	100.2	101.9	101.9	98.4	96.7	93.1	89.6	87.9	87.9
67.5°	89.6	89.6	89.6	87.9	87.9	86.1	86.1	84.4	82.6	80.8	80.8
70°	80.8	80.8	80.8	79.1	79.1	77.3	77.3	75.6	73.8	73.8	72.1
72.5°	73.8	73.8	72.1	72.1	70.3	70.3	70.3	68.5	68.5	66.8	66.8
75°	65.0	65.0	63.3	63.3	61.5	61.5	61.5	59.8	59.8	59.8	58.0
77.5°	58.0	58.0	56.2	56.2	54.5	54.5	54.5	52.7	52.7	51.0	51.0
80°	51.0	51.0	49.2	49.2	47.4	47.4	45.7	45.7	43.9	43.9	42.2
82.5°	40.4	40.4	40.4	40.4	40.4	38.7	38.7	36.9	35.1	35.1	33.4
85°	33.4	33.4	33.4	31.6	31.6	31.6	29.9	29.9	28.1	26.4	26.4
87.5°	19.3	19.3	19.3	17.6	17.6	17.6	17.6	17.6	17.6	17.6	15.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3
2.5°	1110.7	1108.9	1101.9	1094.8	1101.9	1108.9	1108.9	1108.9	1107.1	1107.1	1107.1
5°	891.0	889.2	885.7	882.2	882.2	880.4	884.0	887.5	891.0	894.5	898.0
7.5°	655.5	650.2	645.0	639.7	643.2	645.0	650.2	653.7	659.0	662.5	671.3
10°	546.5	539.5	534.2	529.0	525.5	521.9	518.4	516.7	513.2	509.6	513.2
12.5°	467.5	458.7	449.9	439.3	437.6	435.8	432.3	428.8	425.3	421.8	420.0
15°	383.1	376.1	372.6	367.3	360.3	353.2	349.7	348.0	344.4	340.9	339.2
17.5°	305.8	298.8	293.5	288.2	286.5	282.9	282.9	282.9	282.9	282.9	282.9
20°	240.8	235.5	235.5	233.7	233.7	232.0	233.7	235.5	235.5	237.2	239.0
22.5°	210.9	210.9	209.1	207.4	209.1	209.1	210.9	212.6	214.4	216.2	217.9
25°	195.1	193.3	195.1	196.8	196.8	196.8	198.6	198.6	200.3	200.3	200.3
27.5°	188.0	188.0	189.8	189.8	191.6	191.6	191.6	189.8	189.8	188.0	188.0
30°	198.6	195.1	195.1	195.1	193.3	191.6	189.8	189.8	188.0	186.3	184.5
32.5°	205.6	207.4	205.6	202.1	200.3	196.8	195.1	191.6	189.8	186.3	182.8
35°	149.4	147.6	151.1	152.9	154.6	156.4	158.2	159.9	159.9	161.7	161.7
37.5°	144.1	142.3	142.3	140.6	140.6	140.6	140.6	140.6	138.8	138.8	140.6
40°	137.1	135.3	135.3	133.6	133.6	131.8	131.8	131.8	131.8	131.8	131.8
42.5°	131.8	130.0	130.0	130.0	130.0	128.3	128.3	126.5	126.5	124.8	124.8
45°	130.0	128.3	126.5	124.8	124.8	123.0	123.0	123.0	121.3	121.3	121.3
47.5°	123.0	121.3	121.3	119.5	119.5	117.7	117.7	117.7	116.0	116.0	116.0
50°	119.5	117.7	117.7	116.0	116.0	114.2	114.2	114.2	112.5	112.5	112.5
52.5°	114.2	112.5	112.5	112.5	110.7	109.0	109.0	109.0	107.2	107.2	107.2
55°	109.0	107.2	107.2	107.2	105.4	103.7	103.7	103.7	101.9	101.9	101.9
57.5°	101.9	100.2	100.2	98.4	98.4	98.4	98.4	98.4	96.7	96.7	96.7
60°	96.7	94.9	94.9	93.1	93.1	91.4	91.4	91.4	91.4	91.4	91.4
62.5°	91.4	89.6	87.9	86.1	87.9	87.9	87.9	87.9	86.1	86.1	86.1
65°	86.1	84.4	82.6	80.8	80.8	80.8	80.8	80.8	80.8	80.8	80.8
67.5°	79.1	77.3	75.6	73.8	75.6	75.6	75.6	75.6	75.6	75.6	75.6
70°	72.1	70.3	70.3	68.5	68.5	66.8	66.8	68.5	68.5	68.5	68.5
72.5°	65.0	63.3	63.3	61.5	61.5	61.5	61.5	61.5	61.5	61.5	61.5
75°	58.0	56.2	56.2	54.5	54.5	54.5	54.5	54.5	54.5	54.5	54.5
77.5°	49.2	47.4	47.4	47.4	47.4	47.4	47.4	49.2	49.2	49.2	49.2
80°	42.2	40.4	40.4	40.4	40.4	40.4	40.4	40.4	40.4	40.4	40.4
82.5°	33.4	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6
85°	24.6	22.8	22.8	22.8	24.6	24.6	24.6	24.6	24.6	24.6	24.6
87.5°	15.8	14.1	14.1	14.1	15.8	15.8	15.8	15.8	14.1	14.1	14.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3
2.5°	1107.1	1107.1	1107.1	1105.4	1103.6	1101.9	1100.1	1105.4	1108.9	1114.2	1117.7
5°	899.8	903.3	905.0	910.3	915.6	920.9	926.1	929.6	933.2	934.9	938.4
7.5°	678.3	687.1	694.2	701.2	708.2	713.5	720.5	725.8	731.1	736.3	741.6
10°	514.9	518.4	520.2	527.2	532.5	539.5	544.8	550.1	555.3	558.8	564.1
12.5°	418.3	414.7	413.0	413.0	413.0	413.0	413.0	416.5	420.0	423.5	427.0
15°	337.4	335.7	333.9	332.1	330.4	326.9	325.1	328.6	332.1	335.7	339.2
17.5°	282.9	282.9	282.9	281.2	279.4	277.7	275.9	277.7	279.4	279.4	281.2
20°	242.5	244.3	246.0	247.8	247.8	249.5	249.5	251.3	253.1	253.1	254.8
22.5°	217.9	219.7	219.7	219.7	221.4	221.4	221.4	223.2	224.9	226.7	228.5
25°	198.6	198.6	196.8	196.8	198.6	198.6	198.6	198.6	200.3	200.3	200.3
27.5°	188.0	186.3	186.3	186.3	186.3	184.5	184.5	184.5	184.5	184.5	184.5
30°	182.8	181.0	179.3	177.5	177.5	175.7	174.0	174.0	174.0	174.0	174.0
32.5°	181.0	177.5	174.0	172.2	172.2	170.5	168.7	166.9	166.9	165.2	163.4
35°	161.7	159.9	159.9	158.2	156.4	154.6	152.9	152.9	152.9	151.1	151.1
37.5°	140.6	142.3	142.3	142.3	144.1	144.1	144.1	144.1	145.9	145.9	145.9
40°	131.8	131.8	131.8	133.6	135.3	135.3	137.1	137.1	138.8	138.8	138.8
42.5°	124.8	123.0	123.0	124.8	124.8	126.5	126.5	128.3	130.0	130.0	131.8
45°	121.3	119.5	119.5	119.5	119.5	117.7	117.7	119.5	121.3	123.0	124.8
47.5°	114.2	114.2	112.5	112.5	112.5	112.5	112.5	112.5	114.2	114.2	114.2
50°	110.7	110.7	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0
52.5°	107.2	105.4	105.4	105.4	105.4	103.7	103.7	103.7	103.7	103.7	103.7
55°	101.9	100.2	100.2	100.2	100.2	100.2	100.2	100.2	101.9	101.9	101.9
57.5°	96.7	94.9	94.9	94.9	96.7	96.7	96.7	96.7	98.4	98.4	98.4
60°	91.4	91.4	91.4	91.4	91.4	91.4	91.4	93.1	93.1	94.9	94.9
62.5°	86.1	86.1	86.1	86.1	87.9	87.9	87.9	87.9	89.6	89.6	89.6
65°	80.8	80.8	80.8	80.8	82.6	82.6	82.6	82.6	82.6	82.6	82.6
67.5°	75.6	75.6	75.6	75.6	75.6	75.6	75.6	77.3	77.3	79.1	79.1
70°	68.5	66.8	66.8	68.5	68.5	70.3	70.3	72.1	72.1	73.8	73.8
72.5°	61.5	61.5	61.5	61.5	61.5	61.5	61.5	63.3	65.0	65.0	66.8
75°	54.5	54.5	54.5	54.5	56.2	56.2	56.2	58.0	58.0	59.8	59.8
77.5°	49.2	47.4	47.4	47.4	49.2	49.2	49.2	51.0	51.0	52.7	52.7
80°	40.4	40.4	40.4	40.4	42.2	42.2	42.2	42.2	43.9	43.9	43.9
82.5°	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4	35.1	35.1	35.1
85°	24.6	24.6	24.6	24.6	26.4	26.4	26.4	26.4	26.4	26.4	26.4
87.5°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8	17.6	17.6	17.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069
 CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3
2.5°	1117.7	1117.7	1117.7	1117.7	1121.2	1123.0	1126.5	1128.2	1126.5	1124.7	1121.2
5°	940.2	941.9	941.9	943.7	943.7	943.7	943.7	943.7	947.2	950.7	954.2
7.5°	743.4	745.1	746.9	748.6	748.6	748.6	746.9	746.9	748.6	748.6	750.4
10°	569.4	576.4	581.7	587.0	583.4	578.2	574.7	569.4	569.4	569.4	567.6
12.5°	430.6	432.3	435.8	437.6	435.8	435.8	434.1	432.3	434.1	437.6	439.3
15°	340.9	340.9	342.7	342.7	344.4	346.2	346.2	348.0	351.5	353.2	356.7
17.5°	282.9	284.7	284.7	286.5	286.5	288.2	288.2	288.2	291.7	295.2	300.5
20°	254.8	254.8	254.8	254.8	254.8	253.1	253.1	251.3	253.1	256.6	258.3
22.5°	228.5	230.2	230.2	230.2	228.5	226.7	223.2	221.4	221.4	223.2	223.2
25°	200.3	198.6	198.6	196.8	196.8	198.6	198.6	198.6	200.3	200.3	202.1
27.5°	184.5	182.8	182.8	181.0	181.0	182.8	182.8	182.8	182.8	182.8	182.8
30°	172.2	172.2	170.5	168.7	170.5	170.5	172.2	172.2	174.0	174.0	175.7
32.5°	163.4	161.7	161.7	159.9	161.7	161.7	163.4	163.4	165.2	166.9	166.9
35°	151.1	151.1	151.1	151.1	151.1	151.1	149.4	149.4	149.4	149.4	149.4
37.5°	144.1	144.1	142.3	140.6	140.6	140.6	140.6	140.6	138.8	137.1	135.3
40°	138.8	137.1	137.1	135.3	133.6	133.6	131.8	130.0	130.0	128.3	128.3
42.5°	131.8	130.0	130.0	128.3	126.5	126.5	124.8	123.0	123.0	123.0	121.3
45°	123.0	123.0	121.3	119.5	119.5	119.5	117.7	117.7	117.7	117.7	116.0
47.5°	114.2	114.2	112.5	112.5	112.5	112.5	110.7	110.7	110.7	110.7	110.7
50°	109.0	109.0	109.0	109.0	109.0	109.0	107.2	107.2	107.2	107.2	107.2
52.5°	103.7	103.7	103.7	103.7	103.7	103.7	103.7	103.7	103.7	103.7	103.7
55°	101.9	101.9	101.9	101.9	101.9	101.9	100.2	100.2	100.2	101.9	101.9
57.5°	98.4	98.4	96.7	96.7	96.7	96.7	96.7	96.7	96.7	96.7	96.7
60°	94.9	94.9	94.9	94.9	94.9	94.9	94.9	94.9	94.9	94.9	94.9
62.5°	89.6	89.6	89.6	89.6	89.6	91.4	91.4	91.4	91.4	91.4	89.6
65°	82.6	84.4	84.4	84.4	84.4	84.4	84.4	84.4	84.4	84.4	84.4
67.5°	79.1	79.1	79.1	79.1	79.1	79.1	79.1	79.1	79.1	79.1	79.1
70°	73.8	73.8	72.1	72.1	72.1	73.8	73.8	73.8	73.8	73.8	73.8
72.5°	66.8	66.8	66.8	66.8	66.8	66.8	66.8	66.8	66.8	68.5	68.5
75°	59.8	59.8	59.8	59.8	59.8	59.8	59.8	59.8	59.8	59.8	59.8
77.5°	52.7	52.7	51.0	51.0	51.0	52.7	52.7	52.7	52.7	54.5	54.5
80°	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9	45.7	45.7
82.5°	35.1	35.1	35.1	35.1	35.1	35.1	35.1	35.1	35.1	36.9	36.9
85°	26.4	28.1	28.1	28.1	28.1	28.1	28.1	28.1	28.1	29.9	29.9
87.5°	17.6	17.6	17.6	17.6	17.6	17.6	15.8	15.8	15.8	15.8	14.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3
2.5°	1119.4	1121.2	1123.0	1123.0	1124.7	1126.5	1126.5	1133.5	1140.5	1144.0	1147.6
5°	957.8	956.0	956.0	954.2	952.5	957.8	963.0	973.6	984.1	985.9	989.4
7.5°	750.4	752.2	753.9	753.9	755.7	750.4	743.4	745.1	746.9	755.7	762.7
10°	567.6	569.4	571.1	571.1	572.9	571.1	567.6	572.9	578.2	585.2	594.0
12.5°	441.1	446.4	451.6	455.2	460.4	463.9	465.7	472.7	478.0	486.8	495.6
15°	360.3	363.8	367.3	370.8	374.3	377.8	381.3	388.4	395.4	406.0	416.5
17.5°	304.0	304.0	305.8	305.8	305.8	309.3	312.8	316.3	318.1	328.6	339.2
20°	260.1	258.3	256.6	254.8	253.1	256.6	258.3	260.1	261.8	268.9	274.1
22.5°	223.2	223.2	224.9	224.9	224.9	223.2	219.7	221.4	221.4	224.9	230.2
25°	202.1	202.1	202.1	200.3	200.3	202.1	203.9	203.9	202.1	203.9	205.6
27.5°	182.8	184.5	184.5	186.3	186.3	188.0	188.0	188.0	188.0	189.8	191.6
30°	175.7	175.7	177.5	177.5	177.5	179.3	181.0	181.0	181.0	182.8	186.3
32.5°	168.7	170.5	172.2	174.0	175.7	177.5	177.5	179.3	179.3	181.0	182.8
35°	149.4	147.6	147.6	145.9	144.1	144.1	144.1	144.1	142.3	144.1	144.1
37.5°	133.6	133.6	133.6	131.8	131.8	133.6	133.6	133.6	133.6	135.3	135.3
40°	126.5	126.5	126.5	126.5	126.5	126.5	126.5	128.3	128.3	130.0	131.8
42.5°	121.3	121.3	121.3	121.3	121.3	123.0	123.0	123.0	123.0	124.8	124.8
45°	116.0	116.0	116.0	116.0	116.0	116.0	116.0	117.7	117.7	119.5	121.3
47.5°	110.7	110.7	110.7	110.7	110.7	112.5	114.2	114.2	114.2	116.0	116.0
50°	107.2	107.2	107.2	107.2	107.2	109.0	109.0	110.7	110.7	112.5	114.2
52.5°	103.7	103.7	103.7	103.7	103.7	105.4	105.4	107.2	107.2	109.0	110.7
55°	101.9	101.9	101.9	100.2	100.2	101.9	101.9	103.7	103.7	105.4	105.4
57.5°	96.7	96.7	96.7	96.7	96.7	96.7	96.7	98.4	98.4	100.2	101.9
60°	94.9	94.9	93.1	93.1	91.4	93.1	93.1	94.9	94.9	96.7	96.7
62.5°	89.6	89.6	89.6	87.9	87.9	89.6	89.6	89.6	89.6	91.4	93.1
65°	84.4	84.4	84.4	82.6	82.6	84.4	84.4	84.4	84.4	86.1	87.9
67.5°	79.1	79.1	79.1	77.3	77.3	77.3	77.3	79.1	79.1	80.8	82.6
70°	73.8	73.8	73.8	72.1	72.1	72.1	70.3	72.1	73.8	75.6	75.6
72.5°	68.5	68.5	68.5	66.8	66.8	66.8	65.0	66.8	66.8	68.5	68.5
75°	59.8	59.8	59.8	59.8	59.8	59.8	58.0	58.0	58.0	59.8	59.8
77.5°	54.5	54.5	54.5	52.7	52.7	52.7	51.0	51.0	51.0	52.7	52.7
80°	45.7	45.7	45.7	43.9	43.9	43.9	42.2	42.2	42.2	43.9	43.9
82.5°	36.9	36.9	36.9	35.1	35.1	35.1	33.4	33.4	33.4	35.1	35.1
85°	29.9	29.9	29.9	29.9	29.9	29.9	28.1	28.1	28.1	29.9	31.6
87.5°	14.1	14.1	15.8	15.8	15.8	15.8	14.1	14.1	12.3	12.3	14.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069
 CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3
2.5°	1151.1	1154.6	1163.4	1170.4	1179.2	1186.2	1191.5	1198.5	1203.8	1209.1	1212.6
5°	991.2	992.9	1001.7	1010.5	1017.5	1026.3	1038.6	1050.9	1063.2	1075.5	1084.3
7.5°	771.5	778.5	789.1	801.4	811.9	822.4	834.7	848.8	861.1	873.4	885.7
10°	601.0	608.0	618.6	629.1	637.9	648.5	662.5	676.6	690.6	704.7	718.8
12.5°	504.4	513.2	525.5	537.8	548.3	560.6	578.2	594.0	611.6	627.4	645.0
15°	425.3	435.8	451.6	469.2	485.0	500.8	518.4	536.0	551.8	569.4	587.0
17.5°	349.7	360.3	374.3	390.1	404.2	418.3	439.3	458.7	479.8	499.1	518.4
20°	281.2	286.5	300.5	314.6	328.6	342.7	358.5	374.3	390.1	406.0	430.6
22.5°	233.7	237.2	244.3	249.5	256.6	261.8	277.7	293.5	307.5	323.4	346.2
25°	205.6	207.4	212.6	216.2	221.4	224.9	235.5	244.3	254.8	263.6	284.7
27.5°	191.6	193.3	195.1	196.8	198.6	200.3	207.4	214.4	219.7	226.7	246.0
30°	188.0	189.8	195.1	198.6	203.9	207.4	210.9	214.4	217.9	221.4	233.7
32.5°	184.5	186.3	186.3	184.5	184.5	182.8	186.3	188.0	191.6	193.3	203.9
35°	145.9	145.9	147.6	149.4	151.1	152.9	158.2	161.7	166.9	170.5	179.3
37.5°	137.1	137.1	138.8	142.3	144.1	145.9	149.4	152.9	156.4	159.9	168.7
40°	131.8	133.6	135.3	137.1	138.8	140.6	144.1	145.9	149.4	151.1	158.2
42.5°	126.5	126.5	128.3	131.8	133.6	135.3	138.8	140.6	144.1	145.9	152.9
45°	123.0	124.8	126.5	128.3	128.3	130.0	133.6	137.1	138.8	142.3	149.4
47.5°	117.7	117.7	121.3	123.0	126.5	128.3	131.8	133.6	137.1	138.8	145.9
50°	114.2	116.0	119.5	121.3	124.8	126.5	131.8	135.3	140.6	144.1	147.6
52.5°	110.7	112.5	116.0	117.7	121.3	123.0	130.0	137.1	142.3	149.4	149.4
55°	107.2	107.2	110.7	116.0	119.5	123.0	126.5	131.8	135.3	138.8	138.8
57.5°	101.9	103.7	107.2	112.5	116.0	119.5	123.0	126.5	128.3	131.8	130.0
60°	98.4	98.4	103.7	109.0	114.2	119.5	119.5	119.5	117.7	117.7	117.7
62.5°	93.1	94.9	101.9	110.7	117.7	124.8	119.5	114.2	109.0	103.7	105.4
65°	89.6	91.4	94.9	100.2	103.7	107.2	103.7	101.9	98.4	94.9	96.7
67.5°	82.6	84.4	86.1	86.1	87.9	87.9	87.9	87.9	87.9	87.9	89.6
70°	77.3	77.3	77.3	79.1	79.1	79.1	79.1	79.1	79.1	79.1	80.8
72.5°	70.3	70.3	70.3	70.3	70.3	70.3	70.3	70.3	70.3	70.3	72.1
75°	61.5	61.5	61.5	61.5	61.5	61.5	61.5	61.5	61.5	61.5	63.3
77.5°	54.5	54.5	54.5	54.5	54.5	54.5	54.5	54.5	52.7	52.7	54.5
80°	45.7	45.7	45.7	45.7	43.9	43.9	43.9	43.9	43.9	43.9	45.7
82.5°	36.9	36.9	36.9	36.9	35.1	35.1	35.1	35.1	33.4	33.4	35.1
85°	33.4	35.1	35.1	36.9	36.9	36.9	35.1	33.4	31.6	29.9	29.9
87.5°	14.1	14.1	14.1	14.1	12.3	12.3	12.3	12.3	12.3	12.3	12.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069
 CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3
2.5°	1217.9	1221.4	1224.9	1230.2	1237.2	1242.5	1247.7	1258.3	1270.6	1281.1	1291.7
5°	1093.1	1101.9	1110.7	1121.2	1131.7	1140.5	1151.1	1172.2	1193.2	1212.6	1233.7
7.5°	896.3	908.6	919.1	936.7	952.5	970.1	985.9	1012.2	1036.8	1063.2	1087.8
10°	732.8	746.9	760.9	783.8	808.4	831.2	854.1	875.2	898.0	919.1	940.2
12.5°	662.5	678.3	695.9	710.0	725.8	739.8	753.9	778.5	803.1	827.7	852.3
15°	604.5	622.1	639.7	657.3	673.1	690.6	706.5	727.5	750.4	771.5	792.6
17.5°	537.8	555.3	574.7	594.0	613.3	632.7	652.0	681.9	711.7	739.8	769.7
20°	453.4	478.0	500.8	527.2	553.6	579.9	606.3	637.9	669.6	699.4	731.1
22.5°	369.0	391.9	414.7	446.4	478.0	507.9	539.5	581.7	622.1	664.3	704.7
25°	307.5	328.6	349.7	384.9	418.3	453.4	486.8	537.8	587.0	637.9	687.1
27.5°	265.4	284.7	304.0	340.9	377.8	413.0	449.9	506.1	560.6	616.8	671.3
30°	246.0	258.3	270.6	305.8	340.9	374.3	409.5	463.9	518.4	572.9	627.4
32.5°	214.4	224.9	235.5	267.1	298.8	328.6	360.3	416.5	471.0	527.2	581.7
35°	189.8	198.6	207.4	237.2	265.4	295.2	323.4	379.6	435.8	492.1	548.3
37.5°	175.7	184.5	191.6	217.9	246.0	272.4	298.8	355.0	409.5	465.7	520.2
40°	165.2	170.5	177.5	203.9	228.5	254.8	279.4	330.4	383.1	434.1	485.0
42.5°	158.2	165.2	170.5	193.3	217.9	240.8	263.6	312.8	362.0	409.5	458.7
45°	156.4	163.4	170.5	189.8	209.1	226.7	246.0	293.5	340.9	388.4	435.8
47.5°	152.9	158.2	165.2	181.0	195.1	210.9	224.9	272.4	319.8	365.5	413.0
50°	151.1	152.9	156.4	170.5	184.5	198.6	212.6	260.1	307.5	355.0	402.4
52.5°	149.4	149.4	149.4	161.7	174.0	184.5	196.8	244.3	293.5	340.9	388.4
55°	138.8	137.1	137.1	149.4	159.9	172.2	182.8	230.2	277.7	323.4	370.8
57.5°	128.3	126.5	124.8	135.3	145.9	156.4	166.9	214.4	263.6	311.1	358.5
60°	117.7	116.0	116.0	126.5	135.3	145.9	154.6	203.9	251.3	300.5	348.0
62.5°	105.4	107.2	107.2	116.0	126.5	135.3	144.1	193.3	244.3	293.5	342.7
65°	96.7	98.4	98.4	109.0	119.5	130.0	140.6	188.0	237.2	284.7	332.1
67.5°	89.6	91.4	91.4	103.7	114.2	126.5	137.1	179.3	223.2	265.4	307.5
70°	82.6	82.6	84.4	96.7	109.0	121.3	133.6	170.5	207.4	242.5	279.4
72.5°	73.8	75.6	77.3	89.6	100.2	112.5	123.0	156.4	189.8	223.2	256.6
75°	65.0	66.8	68.5	79.1	89.6	100.2	110.7	142.3	172.2	203.9	233.7
77.5°	58.0	59.8	61.5	70.3	79.1	87.9	96.7	119.5	144.1	166.9	189.8
80°	47.4	47.4	49.2	56.2	63.3	68.5	75.6	91.4	107.2	121.3	137.1
82.5°	35.1	36.9	36.9	42.2	45.7	51.0	54.5	63.3	70.3	79.1	86.1
85°	29.9	28.1	28.1	31.6	33.4	36.9	38.7	43.9	47.4	52.7	56.2
87.5°	12.3	10.5	10.5	12.3	15.8	17.6	19.3	19.3	21.1	21.1	21.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069
 CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3
2.5°	1296.9	1300.4	1305.7	1309.2	1318.0	1325.1	1333.8	1340.9	1346.1	1354.9	1351.4
5°	1249.5	1265.3	1281.1	1296.9	1309.2	1321.5	1332.1	1344.4	1358.4	1384.8	1391.8
7.5°	1108.9	1130.0	1149.3	1170.4	1195.0	1219.6	1244.2	1268.8	1291.7	1325.1	1346.1
10°	970.1	999.9	1028.1	1057.9	1080.8	1103.6	1124.7	1147.6	1179.2	1212.6	1251.2
12.5°	882.2	912.1	941.9	971.8	1005.2	1036.8	1070.2	1101.9	1131.7	1158.1	1202.0
15°	824.2	857.6	889.2	920.9	961.3	999.9	1040.4	1079.0	1123.0	1158.1	1188.0
17.5°	810.1	850.6	889.2	929.6	971.8	1014.0	1056.2	1098.4	1142.3	1195.0	1233.7
20°	785.5	840.0	894.5	949.0	1003.5	1056.2	1110.7	1163.4	1221.4	1284.6	1302.2
22.5°	771.5	836.5	903.3	968.3	1042.1	1117.7	1191.5	1265.3	1326.8	1374.3	1427.0
25°	769.7	850.6	933.2	1014.0	1107.1	1198.5	1291.7	1383.0	1462.1	1509.6	1551.8
27.5°	768.0	866.4	963.0	1059.7	1173.9	1286.4	1400.6	1513.1	1586.9	1655.4	1690.6
30°	746.9	864.6	984.1	1101.9	1230.2	1358.4	1486.7	1615.0	1690.6	1738.0	1755.6
32.5°	720.5	859.4	998.2	1137.0	1282.9	1428.7	1572.8	1718.7	1778.5	1818.9	1804.8
35°	699.4	852.3	1003.5	1154.6	1309.2	1465.6	1620.3	1774.9	1861.0	1917.3	1894.4
37.5°	680.1	840.0	999.9	1159.9	1340.9	1521.9	1702.9	1883.9	1966.5	2026.2	1999.9
40°	657.3	827.7	999.9	1170.4	1377.8	1583.4	1790.8	1996.4	2103.6	2154.5	2114.1
42.5°	637.9	815.4	994.7	1172.2	1393.6	1615.0	1836.4	2057.9	2177.4	2249.4	2198.5
45°	613.3	790.8	966.5	1144.0	1388.3	1632.6	1875.1	2119.4	2258.2	2314.4	2244.2
47.5°	587.0	762.7	936.7	1110.7	1370.7	1630.8	1890.9	2151.0	2279.3	2346.1	2281.1
50°	578.2	753.9	927.9	1103.6	1384.8	1667.7	1948.9	2230.1	2323.2	2377.7	2291.6
52.5°	576.4	762.7	950.7	1137.0	1419.9	1701.1	1984.1	2265.2	2340.8	2398.8	2321.5
55°	571.1	773.2	973.6	1173.9	1469.2	1766.2	2061.4	2356.6	2432.2	2474.4	2416.4
57.5°	576.4	794.3	1010.5	1228.4	1532.4	1836.4	2140.5	2444.5	2535.9	2565.8	2553.4
60°	579.9	811.9	1042.1	1274.1	1571.1	1868.1	2165.1	2462.1	2557.0	2630.8	2644.8
62.5°	571.1	799.6	1026.3	1254.8	1523.6	1792.5	2061.4	2330.3	2486.7	2595.6	2658.9
65°	544.8	755.7	968.3	1179.2	1427.0	1676.5	1924.3	2172.1	2337.3	2499.0	2549.9
67.5°	486.8	666.0	845.3	1024.5	1240.7	1456.9	1671.3	1887.4	2094.8	2251.2	2321.5
70°	421.8	562.4	704.7	845.3	1042.1	1238.9	1435.8	1632.6	1815.4	1987.6	2054.4
72.5°	367.3	476.2	587.0	695.9	836.5	975.3	1115.9	1254.8	1470.9	1643.1	1708.2
75°	312.8	391.9	469.2	548.3	645.0	741.6	836.5	933.2	1086.1	1240.7	1305.7
77.5°	240.8	293.5	344.4	395.4	462.2	527.2	594.0	659.0	766.2	882.2	915.6
80°	166.9	196.8	224.9	254.8	307.5	360.3	413.0	465.7	536.0	601.0	652.0
82.5°	103.7	123.0	140.6	158.2	200.3	242.5	282.9	325.1	353.2	356.7	407.7
85°	66.8	79.1	89.6	100.2	124.8	151.1	175.7	200.3	179.3	166.9	198.6
87.5°	26.4	33.4	38.7	43.9	42.2	40.4	38.7	36.9	31.6	28.1	35.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3
2.5°	1354.9	1360.2	1365.5	1369.0	1374.3	1376.0	1377.8	1377.8	1379.5	1381.3	1384.8
5°	1419.9	1430.5	1441.0	1449.8	1460.4	1469.2	1476.2	1485.0	1492.0	1492.0	1490.2
7.5°	1365.5	1391.8	1418.2	1444.6	1470.9	1490.2	1507.8	1527.1	1544.7	1548.2	1551.8
10°	1293.4	1321.5	1347.9	1376.0	1402.4	1432.3	1460.4	1488.5	1518.4	1523.6	1530.7
12.5°	1226.6	1260.0	1293.4	1325.1	1358.4	1379.5	1400.6	1419.9	1441.0	1455.1	1469.2
15°	1224.9	1253.0	1281.1	1307.5	1335.6	1347.9	1360.2	1370.7	1383.0	1383.0	1384.8
17.5°	1265.3	1282.9	1300.4	1316.3	1333.8	1335.6	1339.1	1340.9	1342.6	1337.4	1332.1
20°	1344.4	1351.4	1358.4	1365.5	1372.5	1360.2	1349.7	1337.4	1325.1	1311.0	1298.7
22.5°	1460.4	1444.6	1428.7	1412.9	1397.1	1376.0	1353.2	1332.1	1309.2	1291.7	1274.1
25°	1569.3	1550.0	1530.7	1511.3	1492.0	1446.3	1400.6	1353.2	1307.5	1288.1	1268.8
27.5°	1715.2	1685.3	1655.4	1625.6	1595.7	1534.2	1472.7	1411.2	1349.7	1316.3	1284.6
30°	1750.3	1716.9	1683.6	1648.4	1615.0	1555.3	1497.3	1437.5	1377.8	1339.1	1302.2
32.5°	1801.3	1762.6	1724.0	1685.3	1646.6	1588.7	1530.7	1470.9	1412.9	1377.8	1340.9
35°	1885.7	1841.7	1797.8	1752.1	1708.2	1648.4	1590.4	1530.7	1470.9	1430.5	1391.8
37.5°	1957.7	1906.7	1855.8	1804.8	1753.8	1701.1	1646.6	1593.9	1539.5	1499.0	1460.4
40°	2038.5	1982.3	1926.1	1871.6	1815.4	1766.2	1716.9	1666.0	1616.8	1585.1	1553.5
42.5°	2108.8	2040.3	1973.5	1906.7	1838.2	1804.8	1773.2	1739.8	1706.4	1690.6	1673.0
45°	2158.0	2094.8	2029.8	1966.5	1903.2	1878.6	1854.0	1829.4	1804.8	1820.6	1836.4
47.5°	2179.1	2128.2	2079.0	2029.8	1978.8	1987.6	1996.4	2003.4	2012.2	2033.3	2056.1
50°	2198.5	2170.3	2140.5	2112.4	2082.5	2115.9	2147.5	2180.9	2214.3	2258.2	2302.1
52.5°	2237.1	2221.3	2207.2	2191.4	2175.6	2233.6	2291.6	2349.6	2407.6	2456.8	2506.0
55°	2353.1	2340.8	2328.5	2314.4	2302.1	2384.7	2465.6	2548.2	2630.8	2681.7	2732.7
57.5°	2513.0	2506.0	2497.2	2490.2	2481.4	2562.2	2641.3	2720.4	2801.2	2850.4	2901.4
60°	2634.3	2636.0	2636.0	2637.8	2637.8	2699.3	2760.8	2824.1	2885.6	2927.8	2971.7
62.5°	2699.3	2695.8	2692.3	2688.8	2685.3	2736.2	2787.2	2838.1	2889.1	2920.7	2952.4
65°	2629.0	2648.3	2667.7	2687.0	2706.3	2713.4	2718.6	2725.7	2730.9	2750.3	2769.6
67.5°	2393.5	2432.2	2469.1	2507.8	2544.7	2518.3	2493.7	2467.3	2441.0	2446.2	2449.8
70°	2131.7	2175.6	2221.3	2265.2	2309.2	2247.7	2186.2	2122.9	2061.4	2040.3	2019.2
72.5°	1797.8	1836.4	1876.9	1915.5	1954.2	1878.6	1804.8	1729.2	1653.7	1616.8	1579.9
75°	1374.3	1419.9	1467.4	1513.1	1558.8	1474.4	1388.3	1304.0	1217.9	1193.2	1170.4
77.5°	1001.7	1056.2	1110.7	1165.1	1219.6	1144.0	1068.5	991.2	915.6	901.5	887.5
80°	729.3	771.5	811.9	854.1	894.5	850.6	806.6	762.7	718.8	717.0	715.2
82.5°	492.1	529.0	564.1	601.0	636.2	618.6	602.8	585.2	567.6	585.2	604.5
85°	253.1	304.0	356.7	407.7	458.7	453.4	449.9	444.6	439.3	462.2	483.3
87.5°	51.0	94.9	138.8	181.0	224.9	214.4	203.9	191.6	181.0	188.0	193.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069
 CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3
2.5°	1386.6	1388.3	1388.3	1388.3	1388.3	1388.3	1384.8	1383.0	1379.5	1376.0	1370.7
5°	1490.2	1488.5	1481.5	1474.4	1465.6	1458.6	1453.3	1446.3	1441.0	1434.0	1423.5
7.5°	1555.3	1558.8	1546.5	1535.9	1523.6	1511.3	1499.0	1486.7	1474.4	1462.1	1437.5
10°	1535.9	1541.2	1534.2	1527.1	1518.4	1511.3	1497.3	1481.5	1467.4	1451.6	1421.7
12.5°	1481.5	1495.5	1492.0	1488.5	1485.0	1481.5	1472.7	1462.1	1453.3	1442.8	1409.4
15°	1384.8	1384.8	1386.6	1388.3	1388.3	1390.1	1391.8	1393.6	1395.3	1397.1	1377.8
17.5°	1326.8	1321.5	1321.5	1321.5	1321.5	1321.5	1328.6	1337.4	1344.4	1351.4	1346.1
20°	1284.6	1272.3	1270.6	1270.6	1268.8	1267.1	1279.4	1293.4	1305.7	1318.0	1325.1
22.5°	1256.5	1238.9	1237.2	1235.4	1233.7	1231.9	1247.7	1263.5	1279.4	1295.2	1319.8
25°	1249.5	1230.2	1231.9	1233.7	1233.7	1235.4	1247.7	1260.0	1272.3	1284.6	1326.8
27.5°	1251.2	1219.6	1221.4	1223.1	1223.1	1224.9	1244.2	1261.8	1281.1	1298.7	1351.4
30°	1263.5	1226.6	1223.1	1219.6	1216.1	1212.6	1238.9	1265.3	1291.7	1318.0	1358.4
32.5°	1305.7	1270.6	1261.8	1253.0	1244.2	1235.4	1267.1	1296.9	1328.6	1358.4	1391.8
35°	1351.4	1312.8	1309.2	1305.7	1300.4	1296.9	1325.1	1354.9	1383.0	1411.2	1441.0
37.5°	1419.9	1381.3	1377.8	1372.5	1369.0	1363.7	1395.3	1425.2	1456.9	1486.7	1513.1
40°	1521.9	1490.2	1488.5	1488.5	1486.7	1485.0	1509.6	1535.9	1560.5	1585.1	1602.7
42.5°	1657.2	1641.4	1646.6	1653.7	1659.0	1664.2	1683.6	1704.6	1724.0	1743.3	1738.0
45°	1852.3	1868.1	1869.8	1871.6	1873.3	1875.1	1880.4	1887.4	1892.7	1898.0	1876.9
47.5°	2077.2	2098.3	2108.8	2119.4	2128.2	2138.7	2131.7	2122.9	2115.9	2107.1	2054.4
50°	2344.3	2388.3	2386.5	2384.7	2381.2	2379.5	2365.4	2351.4	2335.5	2321.5	2244.2
52.5°	2555.2	2604.4	2613.2	2622.0	2630.8	2639.6	2613.2	2586.8	2558.7	2532.4	2435.7
55°	2781.9	2832.9	2834.6	2836.4	2836.4	2838.1	2801.2	2764.3	2725.7	2688.8	2588.6
57.5°	2950.6	2999.8	2994.5	2991.0	2985.8	2980.5	2936.6	2892.6	2848.7	2804.8	2704.6
60°	3013.9	3056.1	3045.5	3035.0	3022.7	3012.1	2978.7	2945.3	2910.2	2876.8	2780.1
62.5°	2984.0	3015.6	2999.8	2985.8	2969.9	2954.1	2912.0	2868.0	2825.8	2781.9	2711.6
65°	2787.2	2806.5	2785.4	2766.1	2746.8	2725.7	2690.5	2655.4	2618.5	2583.3	2535.9
67.5°	2455.0	2458.6	2456.8	2455.0	2453.3	2451.5	2400.6	2349.6	2296.9	2245.9	2242.4
70°	1999.9	1978.8	1982.3	1987.6	1991.1	1994.6	1955.9	1919.0	1880.4	1841.7	1859.3
72.5°	1543.0	1506.1	1514.8	1525.4	1534.2	1543.0	1511.3	1481.5	1449.8	1418.2	1442.8
75°	1145.8	1123.0	1131.7	1142.3	1151.1	1159.9	1147.6	1135.3	1121.2	1108.9	1131.7
77.5°	873.4	859.4	861.1	861.1	862.9	862.9	864.6	868.1	869.9	871.7	896.3
80°	711.7	710.0	708.2	706.5	702.9	701.2	718.8	736.3	753.9	771.5	783.8
82.5°	622.1	639.7	629.1	620.3	609.8	599.3	615.1	630.9	646.7	662.5	657.3
85°	506.1	527.2	507.9	488.5	467.5	448.1	462.2	474.5	488.5	500.8	493.8
87.5°	200.3	205.6	174.0	144.1	112.5	80.8	128.3	174.0	221.4	267.1	274.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069

CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3	1265.3
2.5°	1365.5	1358.4	1353.2	1351.4	1347.9	1346.1	1342.6	1339.1	1333.8	1330.3	1325.1
5°	1411.2	1400.6	1388.3	1370.7	1354.9	1337.4	1319.8	1304.0	1288.1	1270.6	1254.8
7.5°	1412.9	1388.3	1363.7	1340.9	1316.3	1293.4	1268.8	1247.7	1224.9	1202.0	1180.9
10°	1393.6	1363.7	1333.8	1304.0	1275.8	1246.0	1216.1	1191.5	1165.1	1138.8	1114.2
12.5°	1377.8	1344.4	1311.0	1275.8	1242.5	1207.3	1172.2	1147.6	1123.0	1098.4	1073.7
15°	1358.4	1337.4	1318.0	1286.4	1254.8	1223.1	1191.5	1158.1	1126.5	1093.1	1059.7
17.5°	1342.6	1337.4	1332.1	1311.0	1289.9	1267.1	1246.0	1212.6	1179.2	1144.0	1110.7
20°	1333.8	1340.9	1347.9	1337.4	1326.8	1314.5	1304.0	1279.4	1254.8	1228.4	1203.8
22.5°	1344.4	1370.7	1395.3	1397.1	1400.6	1402.4	1404.1	1381.3	1358.4	1333.8	1311.0
25°	1369.0	1411.2	1453.3	1476.2	1499.0	1523.6	1546.5	1532.4	1518.4	1504.3	1490.2
27.5°	1402.4	1455.1	1507.8	1541.2	1572.8	1606.2	1639.6	1637.9	1636.1	1632.6	1630.8
30°	1397.1	1437.5	1477.9	1518.4	1558.8	1599.2	1639.6	1660.7	1680.0	1701.1	1722.2
32.5°	1427.0	1460.4	1495.5	1537.7	1579.9	1623.8	1666.0	1709.9	1752.1	1796.0	1840.0
35°	1472.7	1502.5	1534.2	1579.9	1627.3	1673.0	1720.5	1773.2	1827.7	1882.1	1934.9
37.5°	1541.2	1567.6	1595.7	1634.3	1674.8	1713.4	1753.8	1831.2	1908.5	1987.6	2064.9
40°	1620.3	1637.9	1655.4	1692.3	1729.2	1766.2	1803.1	1899.7	1996.4	2093.0	2189.7
42.5°	1734.5	1729.2	1724.0	1753.8	1785.5	1815.4	1847.0	1934.9	2022.7	2110.6	2198.5
45°	1855.8	1834.7	1813.6	1827.7	1843.5	1857.5	1873.3	1963.0	2052.6	2144.0	2233.6
47.5°	2001.6	1948.9	1896.2	1883.9	1871.6	1857.5	1845.2	1941.9	2038.5	2137.0	2233.6
50°	2166.8	2087.7	2010.4	1978.8	1945.4	1913.8	1880.4	1959.5	2040.3	2121.1	2200.2
52.5°	2339.1	2240.6	2144.0	2094.8	2045.6	1994.6	1945.4	2012.2	2080.7	2149.3	2216.0
55°	2486.7	2386.5	2284.6	2226.6	2168.6	2110.6	2052.6	2119.4	2186.2	2252.9	2319.7
57.5°	2604.4	2504.2	2404.1	2349.6	2293.4	2238.9	2182.6	2245.9	2310.9	2376.0	2439.2
60°	2685.3	2588.6	2491.9	2439.2	2386.5	2333.8	2281.1	2356.6	2432.2	2509.5	2585.1
62.5°	2643.1	2572.8	2502.5	2479.6	2456.8	2432.2	2409.3	2481.4	2551.7	2623.7	2695.8
65°	2488.4	2441.0	2393.5	2416.4	2441.0	2463.8	2488.4	2535.9	2583.3	2632.5	2680.0
67.5°	2237.1	2233.6	2228.3	2279.3	2330.3	2383.0	2433.9	2465.6	2495.5	2527.1	2558.7
70°	1876.9	1896.2	1913.8	2001.6	2089.5	2177.4	2265.2	2277.5	2289.8	2302.1	2314.4
72.5°	1469.2	1493.8	1520.1	1636.1	1750.3	1866.3	1982.3	1975.3	1968.2	1959.5	1952.4
75°	1156.3	1179.2	1203.8	1311.0	1418.2	1525.4	1632.6	1602.7	1574.6	1544.7	1514.8
77.5°	922.6	947.2	973.6	1073.7	1173.9	1275.8	1376.0	1304.0	1231.9	1159.9	1087.8
80°	794.3	806.6	817.2	885.7	952.5	1021.0	1089.6	1015.8	940.2	864.6	790.8
82.5°	652.0	645.0	639.7	680.1	720.5	760.9	801.4	731.1	660.8	588.7	518.4
85°	486.8	479.8	472.7	493.8	514.9	537.8	558.8	478.0	397.2	314.6	233.7
87.5°	282.9	290.0	297.0	319.8	342.7	367.3	390.1	307.5	224.9	140.6	58.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676069
 CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676069
 CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1265.3	1265.3
2.5°	1314.5	1305.7
5°	1242.5	1230.2
7.5°	1163.4	1147.6
10°	1091.3	1070.2
12.5°	1045.6	1019.3
15°	1028.1	996.4
17.5°	1080.8	1050.9
20°	1161.6	1121.2
22.5°	1260.0	1210.8
25°	1430.5	1370.7
27.5°	1569.3	1507.8
30°	1655.4	1588.7
32.5°	1750.3	1662.5
35°	1848.7	1764.4
37.5°	1968.2	1873.3
40°	2091.3	1992.8
42.5°	2133.4	2070.2
45°	2173.9	2114.1
47.5°	2182.6	2133.4
50°	2191.4	2184.4
52.5°	2216.0	2214.3
55°	2321.5	2323.2
57.5°	2451.5	2462.1
60°	2571.0	2558.7
62.5°	2632.5	2569.3
65°	2590.4	2502.5
67.5°	2463.8	2368.9
70°	2186.2	2057.9
72.5°	1840.0	1727.5
75°	1418.2	1323.3
77.5°	1008.7	929.6
80°	710.0	630.9
82.5°	455.2	391.9
85°	205.6	179.3
87.5°	58.0	56.2
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P676069
CATALOG NUMBER: CCW-SA-2A-850-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)