

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P676071

Luminaire Tested: **CCW-SA-2C-850-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P676071
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2C-850-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @615mA w/
SLR distribution lens
Light Source: (32) 5000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6547.4 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 9.3 fc

Type IV - Short - N/A

REPORT NUMBER: P676071
CATALOG NUMBER: CCW-SA-2C-850-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1347.2	0.0	1347.2
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	5200.2	0.0	5200.2
	% Fixture	79.4	0.0	79.4
Total	Lumens	6547.4	0.0	6547.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.5
10°-20°	343.0	5.2
20°-30°	501.9	7.7
30°-40°	707.0	10.8
40°-50°	971.5	14.8
50°-60°	1324.2	20.2
60°-70°	1449.4	22.1
70°-80°	837.0	12.8
80°-90°	250.9	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6547.4	100.0
0°-180°	6547.4	100.0

Coefficient of Utilization



REPORT NUMBER: P676071


CATALOG NUMBER: CCW-SA-2C-850-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	672.4	10.3			
FM	(30°-60°)	2389.3	36.5			
FH	(60°-80°)	1925.3	29.4			G2/5000
FVH	(80°-90°)	213.1	3.3			G2/225
BL	(0°-30°)	334.9	5.1	B1/500		
BM	(30°-60°)	613.4	9.4	B1/1000		
BH	(60°-80°)	361.0	5.5	B1/500		G1/500
BVH	(80°-90°)	37.8	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8
2.5°	2157.6	2146.0	2137.3	2128.6	2117.0	2108.3	2096.6	2085.0	2070.5	2058.9	2044.4
5°	2032.8	1997.9	1963.1	1942.7	1919.5	1899.2	1875.9	1849.8	1823.7	1794.6	1768.5
7.5°	1896.3	1852.7	1809.1	1774.3	1736.6	1701.7	1664.0	1632.0	1600.1	1568.1	1536.2
10°	1768.5	1727.8	1687.2	1643.6	1597.2	1553.6	1507.1	1463.6	1420.0	1376.5	1332.9
12.5°	1684.3	1634.9	1588.5	1539.1	1492.6	1443.3	1393.9	1353.2	1312.6	1269.0	1228.4
15°	1646.5	1600.1	1556.5	1507.1	1457.8	1408.4	1359.0	1312.6	1269.0	1222.6	1176.1
17.5°	1736.6	1669.8	1603.0	1539.1	1475.2	1411.3	1347.4	1289.3	1231.3	1173.2	1115.1
20°	1852.7	1768.5	1687.2	1608.8	1527.5	1449.1	1367.8	1286.4	1205.1	1123.8	1042.5
22.5°	2000.8	1905.0	1812.1	1710.4	1605.9	1504.2	1399.7	1298.1	1196.4	1091.9	990.2
25°	2265.1	2151.8	2038.6	1893.4	1745.3	1600.1	1452.0	1318.4	1187.7	1054.1	920.5
27.5°	2491.6	2337.7	2186.7	2012.4	1838.2	1664.0	1489.7	1335.8	1184.8	1030.9	877.0
30°	2625.2	2474.1	2323.1	2111.2	1902.1	1690.1	1478.1	1306.8	1138.3	967.0	795.7
32.5°	2747.1	2578.7	2410.3	2177.9	1942.7	1710.4	1475.2	1286.4	1100.6	911.8	723.1
35°	2915.5	2729.7	2546.7	2276.7	2006.6	1736.6	1466.5	1271.9	1074.5	879.9	682.4
37.5°	3095.6	2866.2	2639.7	2340.6	2041.5	1742.4	1443.3	1251.6	1059.9	868.3	676.6
40°	3293.1	3014.3	2738.4	2407.4	2079.2	1748.2	1417.1	1225.5	1033.8	839.2	647.6
42.5°	3420.8	3118.8	2816.8	2459.6	2105.4	1748.2	1391.0	1202.2	1013.5	821.8	633.1
45°	3493.4	3200.1	2909.7	2523.5	2137.3	1751.1	1364.8	1179.0	993.1	804.4	618.5
47.5°	3525.4	3252.4	2979.4	2572.9	2169.2	1762.7	1356.1	1167.4	975.7	787.0	595.3
50°	3609.6	3368.6	3127.5	2691.9	2259.3	1823.7	1388.1	1184.8	984.4	781.2	577.9
52.5°	3659.0	3452.8	3246.6	2799.4	2352.2	1905.0	1457.8	1231.3	1004.8	778.3	551.7
55°	3839.0	3641.5	3444.1	2967.8	2488.7	2012.4	1533.3	1283.5	1033.8	781.2	531.4
57.5°	4068.4	3859.3	3653.1	3139.2	2625.2	2111.2	1597.2	1330.0	1059.9	792.8	522.7
60°	4228.1	4024.8	3824.5	3278.5	2729.7	2183.8	1634.9	1356.1	1077.4	795.7	516.9
62.5°	4245.5	3984.2	3725.7	3194.3	2662.9	2128.6	1597.2	1327.1	1057.0	784.1	514.0
65°	4135.2	3830.3	3525.4	3017.2	2509.0	2000.8	1492.6	1245.8	999.0	749.2	502.4
67.5°	3914.5	3557.3	3200.1	2735.5	2270.9	1806.2	1341.6	1129.6	920.5	708.6	496.6
70°	3400.5	3086.9	2776.2	2372.5	1971.8	1568.1	1164.5	990.2	818.9	644.7	470.4
72.5°	2854.6	2561.3	2270.9	1942.7	1617.5	1289.3	961.2	830.5	699.8	566.3	435.6
75°	2186.7	1966.0	1748.2	1504.2	1260.3	1013.5	769.5	673.7	577.9	482.1	386.2
77.5°	1536.2	1417.1	1301.0	1118.0	935.1	752.1	569.2	505.3	441.4	377.5	313.6
80°	1042.5	975.7	911.8	781.2	650.5	516.9	386.2	345.6	302.0	261.4	217.8
82.5°	647.6	644.7	638.9	548.8	458.8	368.8	278.8	243.9	212.0	177.1	142.3
85°	296.2	345.6	392.0	342.7	293.3	243.9	194.6	171.3	148.1	122.0	98.7
87.5°	92.9	113.3	130.7	124.9	116.2	110.3	101.6	87.1	72.6	58.1	43.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676071
 CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8
2.5°	2032.8	2024.0	2012.4	2000.8	1986.3	1974.7	1960.2	1945.6	1942.7	1936.9	1934.0
5°	1751.1	1733.6	1713.3	1695.9	1678.5	1658.1	1640.7	1620.4	1605.9	1588.5	1573.9
7.5°	1504.2	1475.2	1443.3	1411.3	1382.3	1353.2	1321.3	1292.2	1277.7	1263.2	1248.7
10°	1306.8	1277.7	1251.6	1222.6	1202.2	1184.8	1164.5	1144.1	1126.7	1109.3	1091.9
12.5°	1208.0	1187.7	1167.4	1147.1	1123.8	1103.5	1080.3	1057.0	1036.7	1019.3	999.0
15°	1147.1	1118.0	1086.1	1057.0	1025.1	996.0	964.1	932.2	908.9	888.6	865.4
17.5°	1074.5	1030.9	990.2	946.7	911.8	877.0	839.2	804.4	778.3	749.2	723.1
20°	993.1	943.8	891.5	842.1	801.5	763.7	723.1	682.4	653.4	621.4	592.4
22.5°	923.5	859.6	792.8	726.0	682.4	638.9	592.4	548.8	522.7	493.7	467.5
25°	847.9	778.3	705.7	633.1	589.5	543.0	499.5	453.0	432.7	415.3	394.9
27.5°	807.3	737.6	665.0	595.3	554.7	511.1	470.4	426.9	412.4	394.9	380.4
30°	726.0	659.2	589.5	519.8	490.8	464.6	435.6	406.6	400.7	397.8	392.0
32.5°	653.4	583.7	514.0	444.3	418.2	392.0	365.9	339.8	336.9	331.0	328.1
35°	615.6	548.8	479.1	412.4	389.1	363.0	339.8	313.6	307.8	299.1	293.3
37.5°	606.9	537.2	464.6	394.9	371.7	348.5	322.3	299.1	293.3	287.5	281.7
40°	583.7	516.9	453.0	386.2	363.0	339.8	313.6	290.4	284.6	278.8	273.0
42.5°	566.3	502.4	435.6	368.8	348.5	328.1	304.9	284.6	278.8	273.0	264.3
45°	551.7	485.0	415.3	348.5	334.0	319.4	302.0	287.5	281.7	273.0	267.2
47.5°	528.5	464.6	397.8	331.0	316.5	304.9	290.4	275.9	270.1	264.3	258.4
50°	511.1	444.3	377.5	310.7	299.1	287.5	275.9	264.3	264.3	267.2	267.2
52.5°	487.9	424.0	360.1	296.2	284.6	273.0	261.4	249.7	252.6	255.5	258.4
55°	467.5	406.6	342.7	278.8	267.2	255.5	241.0	229.4	232.3	235.2	238.1
57.5°	458.8	394.9	331.0	267.2	255.5	241.0	229.4	214.9	214.9	214.9	214.9
60°	453.0	386.2	322.3	255.5	241.0	229.4	214.9	200.4	197.5	197.5	194.6
62.5°	450.1	383.3	319.4	252.6	235.2	220.7	203.3	185.9	182.9	180.0	177.1
65°	438.5	377.5	313.6	249.7	229.4	212.0	191.7	171.3	168.4	168.4	165.5
67.5°	435.6	371.7	310.7	246.8	226.5	203.3	182.9	159.7	156.8	153.9	151.0
70°	412.4	357.2	299.1	241.0	217.8	197.5	174.2	151.0	148.1	142.3	139.4
72.5°	383.3	334.0	281.7	229.4	206.2	182.9	159.7	136.5	133.6	130.7	124.9
75°	339.8	293.3	246.8	200.4	180.0	162.6	142.3	122.0	119.1	116.2	110.3
77.5°	278.8	241.0	206.2	168.4	153.9	139.4	124.9	110.3	107.4	104.5	98.7
80°	197.5	174.2	153.9	130.7	122.0	110.3	101.6	90.0	90.0	87.1	87.1
82.5°	130.7	119.1	107.4	95.8	90.0	84.2	78.4	72.6	72.6	69.7	69.7
85°	92.9	87.1	78.4	72.6	69.7	63.9	61.0	55.2	55.2	55.2	55.2
87.5°	43.6	43.6	40.7	40.7	37.8	37.8	34.8	31.9	31.9	31.9	31.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8
2.5°	1928.2	1919.5	1910.8	1899.2	1890.5	1878.8	1864.3	1852.7	1838.2	1838.2	1835.3
5°	1556.5	1547.8	1539.1	1527.5	1518.8	1507.1	1498.4	1486.8	1475.2	1475.2	1472.3
7.5°	1234.2	1216.7	1199.3	1179.0	1161.6	1150.0	1138.3	1123.8	1112.2	1103.5	1094.8
10°	1074.5	1057.0	1036.7	1019.3	999.0	984.4	969.9	952.5	938.0	926.4	914.7
12.5°	978.6	958.3	938.0	917.6	897.3	877.0	859.6	839.2	818.9	804.4	789.9
15°	842.1	821.8	801.5	781.2	760.8	737.6	714.4	688.2	665.0	653.4	644.7
17.5°	694.0	673.7	650.5	630.2	606.9	589.5	572.1	554.7	537.2	525.6	516.9
20°	560.5	537.2	514.0	490.8	467.5	455.9	444.3	432.7	421.1	412.4	406.6
22.5°	438.5	424.0	412.4	397.8	383.3	374.6	368.8	360.1	351.4	351.4	351.4
25°	374.6	365.9	360.1	351.4	342.7	339.8	336.9	331.0	328.1	325.2	325.2
27.5°	363.0	354.3	345.6	336.9	328.1	325.2	322.3	316.5	313.6	313.6	313.6
30°	386.2	383.3	380.4	377.5	374.6	368.8	360.1	354.3	345.6	339.8	334.0
32.5°	322.3	319.4	319.4	316.5	313.6	319.4	322.3	328.1	331.0	334.0	336.9
35°	284.6	278.8	273.0	267.2	261.4	258.4	255.5	252.6	249.7	249.7	246.8
37.5°	275.9	270.1	264.3	258.4	252.6	249.7	246.8	243.9	241.0	241.0	238.1
40°	267.2	261.4	258.4	252.6	246.8	243.9	241.0	235.2	232.3	229.4	229.4
42.5°	258.4	255.5	249.7	246.8	241.0	238.1	235.2	229.4	226.5	223.6	220.7
45°	258.4	252.6	246.8	241.0	235.2	232.3	226.5	223.6	217.8	217.8	214.9
47.5°	252.6	246.8	241.0	235.2	229.4	226.5	220.7	217.8	212.0	209.1	206.2
50°	267.2	258.4	246.8	238.1	226.5	223.6	217.8	214.9	209.1	206.2	203.3
52.5°	261.4	252.6	241.0	232.3	220.7	214.9	212.0	206.2	200.4	197.5	194.6
55°	241.0	232.3	226.5	217.8	209.1	203.3	197.5	191.7	185.9	182.9	182.9
57.5°	214.9	212.0	209.1	206.2	203.3	197.5	191.7	182.9	177.1	174.2	171.3
60°	191.7	194.6	197.5	200.4	203.3	194.6	185.9	177.1	168.4	165.5	162.6
62.5°	174.2	180.0	185.9	188.8	194.6	185.9	177.1	168.4	159.7	156.8	153.9
65°	162.6	165.5	165.5	168.4	168.4	162.6	159.7	153.9	148.1	145.2	145.2
67.5°	148.1	148.1	148.1	145.2	145.2	142.3	142.3	139.4	136.5	133.6	133.6
70°	133.6	133.6	133.6	130.7	130.7	127.8	127.8	124.9	122.0	122.0	119.1
72.5°	122.0	122.0	119.1	119.1	116.2	116.2	116.2	113.3	113.3	110.3	110.3
75°	107.4	107.4	104.5	104.5	101.6	101.6	101.6	98.7	98.7	98.7	95.8
77.5°	95.8	95.8	92.9	92.9	90.0	90.0	90.0	87.1	87.1	84.2	84.2
80°	84.2	84.2	81.3	81.3	78.4	78.4	75.5	75.5	72.6	72.6	69.7
82.5°	66.8	66.8	66.8	66.8	66.8	63.9	63.9	61.0	58.1	58.1	55.2
85°	55.2	55.2	55.2	52.3	52.3	52.3	49.4	49.4	46.5	43.6	43.6
87.5°	31.9	31.9	31.9	29.0	29.0	29.0	29.0	29.0	29.0	29.0	26.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676071
 CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8
2.5°	1835.3	1832.4	1820.8	1809.1	1820.8	1832.4	1832.4	1832.4	1829.5	1829.5	1829.5
5°	1472.3	1469.4	1463.6	1457.8	1457.8	1454.9	1460.7	1466.5	1472.3	1478.1	1483.9
7.5°	1083.2	1074.5	1065.7	1057.0	1062.8	1065.7	1074.5	1080.3	1089.0	1094.8	1109.3
10°	903.1	891.5	882.8	874.1	868.3	862.5	856.7	853.8	847.9	842.1	847.9
12.5°	772.4	757.9	743.4	726.0	723.1	720.2	714.4	708.6	702.8	696.9	694.0
15°	633.1	621.4	615.6	606.9	595.3	583.7	577.9	575.0	569.2	563.4	560.5
17.5°	505.3	493.7	485.0	476.2	473.3	467.5	467.5	467.5	467.5	467.5	467.5
20°	397.8	389.1	389.1	386.2	386.2	383.3	386.2	389.1	389.1	392.0	394.9
22.5°	348.5	348.5	345.6	342.7	345.6	345.6	348.5	351.4	354.3	357.2	360.1
25°	322.3	319.4	322.3	325.2	325.2	325.2	328.1	328.1	331.0	331.0	331.0
27.5°	310.7	310.7	313.6	313.6	316.5	316.5	316.5	313.6	313.6	310.7	310.7
30°	328.1	322.3	322.3	322.3	319.4	316.5	313.6	313.6	310.7	307.8	304.9
32.5°	339.8	342.7	339.8	334.0	331.0	325.2	322.3	316.5	313.6	307.8	302.0
35°	246.8	243.9	249.7	252.6	255.5	258.4	261.4	264.3	264.3	267.2	267.2
37.5°	238.1	235.2	235.2	232.3	232.3	232.3	232.3	232.3	229.4	229.4	232.3
40°	226.5	223.6	223.6	220.7	220.7	217.8	217.8	217.8	217.8	217.8	217.8
42.5°	217.8	214.9	214.9	214.9	214.9	212.0	212.0	209.1	209.1	206.2	206.2
45°	214.9	212.0	209.1	206.2	206.2	203.3	203.3	203.3	200.4	200.4	200.4
47.5°	203.3	200.4	200.4	197.5	197.5	194.6	194.6	194.6	191.7	191.7	191.7
50°	197.5	194.6	194.6	191.7	191.7	188.8	188.8	188.8	185.9	185.9	185.9
52.5°	188.8	185.9	185.9	185.9	182.9	180.0	180.0	180.0	177.1	177.1	177.1
55°	180.0	177.1	177.1	177.1	174.2	171.3	171.3	171.3	168.4	168.4	168.4
57.5°	168.4	165.5	165.5	162.6	162.6	162.6	162.6	162.6	159.7	159.7	159.7
60°	159.7	156.8	156.8	153.9	153.9	151.0	151.0	151.0	151.0	151.0	151.0
62.5°	151.0	148.1	145.2	142.3	145.2	145.2	145.2	145.2	142.3	142.3	142.3
65°	142.3	139.4	136.5	133.6	133.6	133.6	133.6	133.6	133.6	133.6	133.6
67.5°	130.7	127.8	124.9	122.0	124.9	124.9	124.9	124.9	124.9	124.9	124.9
70°	119.1	116.2	116.2	113.3	113.3	110.3	110.3	113.3	113.3	113.3	113.3
72.5°	107.4	104.5	104.5	101.6	101.6	101.6	101.6	101.6	101.6	101.6	101.6
75°	95.8	92.9	92.9	90.0	90.0	90.0	90.0	90.0	90.0	90.0	90.0
77.5°	81.3	78.4	78.4	78.4	78.4	78.4	78.4	81.3	81.3	81.3	81.3
80°	69.7	66.8	66.8	66.8	66.8	66.8	66.8	66.8	66.8	66.8	66.8
82.5°	55.2	52.3	52.3	52.3	52.3	52.3	52.3	52.3	52.3	52.3	52.3
85°	40.7	37.8	37.8	37.8	40.7	40.7	40.7	40.7	40.7	40.7	40.7
87.5°	26.1	23.2	23.2	23.2	26.1	26.1	26.1	26.1	23.2	23.2	23.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8
2.5°	1829.5	1829.5	1829.5	1826.6	1823.7	1820.8	1817.9	1826.6	1832.4	1841.1	1846.9
5°	1486.8	1492.6	1495.5	1504.2	1512.9	1521.7	1530.4	1536.2	1542.0	1544.9	1550.7
7.5°	1120.9	1135.4	1147.1	1158.7	1170.3	1179.0	1190.6	1199.3	1208.0	1216.7	1225.5
10°	850.9	856.7	859.6	871.2	879.9	891.5	900.2	908.9	917.6	923.5	932.2
12.5°	691.1	685.3	682.4	682.4	682.4	682.4	682.4	688.2	694.0	699.8	705.7
15°	557.6	554.7	551.7	548.8	545.9	540.1	537.2	543.0	548.8	554.7	560.5
17.5°	467.5	467.5	467.5	464.6	461.7	458.8	455.9	458.8	461.7	461.7	464.6
20°	400.7	403.6	406.6	409.5	409.5	412.4	412.4	415.3	418.2	418.2	421.1
22.5°	360.1	363.0	363.0	363.0	365.9	365.9	365.9	368.8	371.7	374.6	377.5
25°	328.1	328.1	325.2	325.2	328.1	328.1	328.1	328.1	331.0	331.0	331.0
27.5°	310.7	307.8	307.8	307.8	307.8	304.9	304.9	304.9	304.9	304.9	304.9
30°	302.0	299.1	296.2	293.3	293.3	290.4	287.5	287.5	287.5	287.5	287.5
32.5°	299.1	293.3	287.5	284.6	284.6	281.7	278.8	275.9	275.9	273.0	270.1
35°	267.2	264.3	264.3	261.4	258.4	255.5	252.6	252.6	252.6	249.7	249.7
37.5°	232.3	235.2	235.2	235.2	238.1	238.1	238.1	238.1	241.0	241.0	241.0
40°	217.8	217.8	217.8	220.7	223.6	223.6	226.5	226.5	229.4	229.4	229.4
42.5°	206.2	203.3	203.3	206.2	206.2	209.1	209.1	212.0	214.9	214.9	217.8
45°	200.4	197.5	197.5	197.5	197.5	194.6	194.6	197.5	200.4	203.3	206.2
47.5°	188.8	188.8	185.9	185.9	185.9	185.9	185.9	185.9	188.8	188.8	188.8
50°	182.9	182.9	180.0	180.0	180.0	180.0	180.0	180.0	180.0	180.0	180.0
52.5°	177.1	174.2	174.2	174.2	174.2	171.3	171.3	171.3	171.3	171.3	171.3
55°	168.4	165.5	165.5	165.5	165.5	165.5	165.5	165.5	168.4	168.4	168.4
57.5°	159.7	156.8	156.8	156.8	159.7	159.7	159.7	159.7	162.6	162.6	162.6
60°	151.0	151.0	151.0	151.0	151.0	151.0	151.0	153.9	153.9	156.8	156.8
62.5°	142.3	142.3	142.3	142.3	145.2	145.2	145.2	145.2	148.1	148.1	148.1
65°	133.6	133.6	133.6	133.6	136.5	136.5	136.5	136.5	136.5	136.5	136.5
67.5°	124.9	124.9	124.9	124.9	124.9	124.9	124.9	127.8	127.8	130.7	130.7
70°	113.3	110.3	110.3	113.3	113.3	116.2	116.2	119.1	119.1	122.0	122.0
72.5°	101.6	101.6	101.6	101.6	101.6	101.6	101.6	104.5	107.4	107.4	110.3
75°	90.0	90.0	90.0	90.0	92.9	92.9	92.9	95.8	95.8	98.7	98.7
77.5°	81.3	78.4	78.4	78.4	81.3	81.3	81.3	84.2	84.2	87.1	87.1
80°	66.8	66.8	66.8	66.8	69.7	69.7	69.7	69.7	72.6	72.6	72.6
82.5°	55.2	55.2	55.2	55.2	55.2	55.2	55.2	55.2	58.1	58.1	58.1
85°	40.7	40.7	40.7	40.7	43.6	43.6	43.6	43.6	43.6	43.6	43.6
87.5°	26.1	26.1	26.1	26.1	26.1	26.1	26.1	26.1	29.0	29.0	29.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676071
 CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8
2.5°	1846.9	1846.9	1846.9	1846.9	1852.7	1855.6	1861.4	1864.3	1861.4	1858.5	1852.7
5°	1553.6	1556.5	1556.5	1559.4	1559.4	1559.4	1559.4	1559.4	1565.2	1571.0	1576.8
7.5°	1228.4	1231.3	1234.2	1237.1	1237.1	1237.1	1234.2	1234.2	1237.1	1237.1	1240.0
10°	940.9	952.5	961.2	969.9	964.1	955.4	949.6	940.9	940.9	940.9	938.0
12.5°	711.5	714.4	720.2	723.1	720.2	720.2	717.3	714.4	717.3	723.1	726.0
15°	563.4	563.4	566.3	566.3	569.2	572.1	572.1	575.0	580.8	583.7	589.5
17.5°	467.5	470.4	470.4	473.3	473.3	476.2	476.2	476.2	482.1	487.9	496.6
20°	421.1	421.1	421.1	421.1	421.1	418.2	418.2	415.3	418.2	424.0	426.9
22.5°	377.5	380.4	380.4	380.4	377.5	374.6	368.8	365.9	365.9	368.8	368.8
25°	331.0	328.1	328.1	325.2	325.2	328.1	328.1	328.1	331.0	331.0	334.0
27.5°	304.9	302.0	302.0	299.1	299.1	302.0	302.0	302.0	302.0	302.0	302.0
30°	284.6	284.6	281.7	278.8	281.7	281.7	284.6	284.6	287.5	287.5	290.4
32.5°	270.1	267.2	267.2	264.3	267.2	267.2	270.1	270.1	273.0	275.9	275.9
35°	249.7	249.7	249.7	249.7	249.7	249.7	246.8	246.8	246.8	246.8	246.8
37.5°	238.1	238.1	235.2	232.3	232.3	232.3	232.3	232.3	229.4	226.5	223.6
40°	229.4	226.5	226.5	223.6	220.7	220.7	217.8	214.9	214.9	212.0	212.0
42.5°	217.8	214.9	214.9	212.0	209.1	209.1	206.2	203.3	203.3	203.3	200.4
45°	203.3	203.3	200.4	197.5	197.5	197.5	194.6	194.6	194.6	194.6	191.7
47.5°	188.8	188.8	185.9	185.9	185.9	185.9	182.9	182.9	182.9	182.9	182.9
50°	180.0	180.0	180.0	180.0	180.0	180.0	177.1	177.1	177.1	177.1	177.1
52.5°	171.3	171.3	171.3	171.3	171.3	171.3	171.3	171.3	171.3	171.3	171.3
55°	168.4	168.4	168.4	168.4	168.4	168.4	165.5	165.5	165.5	168.4	168.4
57.5°	162.6	162.6	159.7	159.7	159.7	159.7	159.7	159.7	159.7	159.7	159.7
60°	156.8	156.8	156.8	156.8	156.8	156.8	156.8	156.8	156.8	156.8	156.8
62.5°	148.1	148.1	148.1	148.1	148.1	151.0	151.0	151.0	151.0	151.0	148.1
65°	136.5	139.4	139.4	139.4	139.4	139.4	139.4	139.4	139.4	139.4	139.4
67.5°	130.7	130.7	130.7	130.7	130.7	130.7	130.7	130.7	130.7	130.7	130.7
70°	122.0	122.0	119.1	119.1	119.1	122.0	122.0	122.0	122.0	122.0	122.0
72.5°	110.3	110.3	110.3	110.3	110.3	110.3	110.3	110.3	110.3	113.3	113.3
75°	98.7	98.7	98.7	98.7	98.7	98.7	98.7	98.7	98.7	98.7	98.7
77.5°	87.1	87.1	84.2	84.2	84.2	87.1	87.1	87.1	87.1	90.0	90.0
80°	72.6	72.6	72.6	72.6	72.6	72.6	72.6	72.6	72.6	75.5	75.5
82.5°	58.1	58.1	58.1	58.1	58.1	58.1	58.1	58.1	58.1	61.0	61.0
85°	43.6	46.5	46.5	46.5	46.5	46.5	46.5	46.5	46.5	49.4	49.4
87.5°	29.0	29.0	29.0	29.0	29.0	29.0	26.1	26.1	26.1	26.1	23.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676071
 CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8
2.5°	1849.8	1852.7	1855.6	1855.6	1858.5	1861.4	1861.4	1873.0	1884.7	1890.5	1896.3
5°	1582.6	1579.7	1579.7	1576.8	1573.9	1582.6	1591.4	1608.8	1626.2	1629.1	1634.9
7.5°	1240.0	1242.9	1245.8	1245.8	1248.7	1240.0	1228.4	1231.3	1234.2	1248.7	1260.3
10°	938.0	940.9	943.8	943.8	946.7	943.8	938.0	946.7	955.4	967.0	981.5
12.5°	728.9	737.6	746.3	752.1	760.8	766.6	769.5	781.2	789.9	804.4	818.9
15°	595.3	601.1	606.9	612.7	618.5	624.3	630.2	641.8	653.4	670.8	688.2
17.5°	502.4	502.4	505.3	505.3	505.3	511.1	516.9	522.7	525.6	543.0	560.5
20°	429.8	426.9	424.0	421.1	418.2	424.0	426.9	429.8	432.7	444.3	453.0
22.5°	368.8	368.8	371.7	371.7	371.7	368.8	363.0	365.9	365.9	371.7	380.4
25°	334.0	334.0	334.0	331.0	331.0	334.0	336.9	336.9	334.0	336.9	339.8
27.5°	302.0	304.9	304.9	307.8	307.8	310.7	310.7	310.7	310.7	313.6	316.5
30°	290.4	290.4	293.3	293.3	293.3	296.2	299.1	299.1	299.1	302.0	307.8
32.5°	278.8	281.7	284.6	287.5	290.4	293.3	293.3	296.2	296.2	299.1	302.0
35°	246.8	243.9	243.9	241.0	238.1	238.1	238.1	238.1	235.2	238.1	238.1
37.5°	220.7	220.7	220.7	217.8	217.8	220.7	220.7	220.7	220.7	223.6	223.6
40°	209.1	209.1	209.1	209.1	209.1	209.1	209.1	212.0	212.0	214.9	217.8
42.5°	200.4	200.4	200.4	200.4	200.4	203.3	203.3	203.3	203.3	206.2	206.2
45°	191.7	191.7	191.7	191.7	191.7	191.7	191.7	194.6	194.6	197.5	200.4
47.5°	182.9	182.9	182.9	182.9	182.9	185.9	188.8	188.8	188.8	191.7	191.7
50°	177.1	177.1	177.1	177.1	177.1	180.0	180.0	182.9	182.9	185.9	188.8
52.5°	171.3	171.3	171.3	171.3	171.3	174.2	174.2	177.1	177.1	180.0	182.9
55°	168.4	168.4	168.4	165.5	165.5	168.4	168.4	171.3	171.3	174.2	174.2
57.5°	159.7	159.7	159.7	159.7	159.7	159.7	159.7	162.6	162.6	165.5	168.4
60°	156.8	156.8	153.9	153.9	151.0	153.9	153.9	156.8	156.8	159.7	159.7
62.5°	148.1	148.1	148.1	145.2	145.2	148.1	148.1	148.1	148.1	151.0	153.9
65°	139.4	139.4	139.4	136.5	136.5	139.4	139.4	139.4	139.4	142.3	145.2
67.5°	130.7	130.7	130.7	127.8	127.8	127.8	127.8	130.7	130.7	133.6	136.5
70°	122.0	122.0	122.0	119.1	119.1	119.1	116.2	119.1	122.0	124.9	124.9
72.5°	113.3	113.3	113.3	110.3	110.3	110.3	107.4	110.3	110.3	113.3	113.3
75°	98.7	98.7	98.7	98.7	98.7	98.7	95.8	95.8	95.8	98.7	98.7
77.5°	90.0	90.0	90.0	87.1	87.1	87.1	84.2	84.2	84.2	87.1	87.1
80°	75.5	75.5	75.5	72.6	72.6	72.6	69.7	69.7	69.7	72.6	72.6
82.5°	61.0	61.0	61.0	58.1	58.1	58.1	55.2	55.2	55.2	58.1	58.1
85°	49.4	49.4	49.4	49.4	49.4	49.4	46.5	46.5	46.5	49.4	52.3
87.5°	23.2	23.2	26.1	26.1	26.1	26.1	23.2	23.2	20.3	20.3	23.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676071
 CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8
2.5°	1902.1	1907.9	1922.4	1934.0	1948.5	1960.2	1968.9	1980.5	1989.2	1997.9	2003.7
5°	1637.8	1640.7	1655.2	1669.8	1681.4	1695.9	1716.2	1736.6	1756.9	1777.2	1791.7
7.5°	1274.8	1286.4	1303.9	1324.2	1341.6	1359.0	1379.4	1402.6	1422.9	1443.3	1463.6
10°	993.1	1004.8	1022.2	1039.6	1054.1	1071.6	1094.8	1118.0	1141.2	1164.5	1187.7
12.5°	833.4	847.9	868.3	888.6	906.0	926.4	955.4	981.5	1010.6	1036.7	1065.7
15°	702.8	720.2	746.3	775.3	801.5	827.6	856.7	885.7	911.8	940.9	969.9
17.5°	577.9	595.3	618.5	644.7	667.9	691.1	726.0	757.9	792.8	824.7	856.7
20°	464.6	473.3	496.6	519.8	543.0	566.3	592.4	618.5	644.7	670.8	711.5
22.5°	386.2	392.0	403.6	412.4	424.0	432.7	458.8	485.0	508.2	534.3	572.1
25°	339.8	342.7	351.4	357.2	365.9	371.7	389.1	403.6	421.1	435.6	470.4
27.5°	316.5	319.4	322.3	325.2	328.1	331.0	342.7	354.3	363.0	374.6	406.6
30°	310.7	313.6	322.3	328.1	336.9	342.7	348.5	354.3	360.1	365.9	386.2
32.5°	304.9	307.8	307.8	304.9	304.9	302.0	307.8	310.7	316.5	319.4	336.9
35°	241.0	241.0	243.9	246.8	249.7	252.6	261.4	267.2	275.9	281.7	296.2
37.5°	226.5	226.5	229.4	235.2	238.1	241.0	246.8	252.6	258.4	264.3	278.8
40°	217.8	220.7	223.6	226.5	229.4	232.3	238.1	241.0	246.8	249.7	261.4
42.5°	209.1	209.1	212.0	217.8	220.7	223.6	229.4	232.3	238.1	241.0	252.6
45°	203.3	206.2	209.1	212.0	212.0	214.9	220.7	226.5	229.4	235.2	246.8
47.5°	194.6	194.6	200.4	203.3	209.1	212.0	217.8	220.7	226.5	229.4	241.0
50°	188.8	191.7	197.5	200.4	206.2	209.1	217.8	223.6	232.3	238.1	243.9
52.5°	182.9	185.9	191.7	194.6	200.4	203.3	214.9	226.5	235.2	246.8	246.8
55°	177.1	177.1	182.9	191.7	197.5	203.3	209.1	217.8	223.6	229.4	229.4
57.5°	168.4	171.3	177.1	185.9	191.7	197.5	203.3	209.1	212.0	217.8	214.9
60°	162.6	162.6	171.3	180.0	188.8	197.5	197.5	197.5	194.6	194.6	194.6
62.5°	153.9	156.8	168.4	182.9	194.6	206.2	197.5	188.8	180.0	171.3	174.2
65°	148.1	151.0	156.8	165.5	171.3	177.1	171.3	168.4	162.6	156.8	159.7
67.5°	136.5	139.4	142.3	142.3	145.2	145.2	145.2	145.2	145.2	145.2	148.1
70°	127.8	127.8	127.8	130.7	130.7	130.7	130.7	130.7	130.7	130.7	133.6
72.5°	116.2	116.2	116.2	116.2	116.2	116.2	116.2	116.2	116.2	116.2	119.1
75°	101.6	101.6	101.6	101.6	101.6	101.6	101.6	101.6	101.6	101.6	104.5
77.5°	90.0	90.0	90.0	90.0	90.0	90.0	90.0	90.0	87.1	87.1	90.0
80°	75.5	75.5	75.5	75.5	72.6	72.6	72.6	72.6	72.6	72.6	75.5
82.5°	61.0	61.0	61.0	61.0	58.1	58.1	58.1	58.1	55.2	55.2	58.1
85°	55.2	58.1	58.1	61.0	61.0	61.0	58.1	55.2	52.3	49.4	49.4
87.5°	23.2	23.2	23.2	23.2	20.3	20.3	20.3	20.3	20.3	20.3	20.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676071
 CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8
2.5°	2012.4	2018.2	2024.0	2032.8	2044.4	2053.1	2061.8	2079.2	2099.5	2117.0	2134.4
5°	1806.2	1820.8	1835.3	1852.7	1870.1	1884.7	1902.1	1936.9	1971.8	2003.7	2038.6
7.5°	1481.0	1501.3	1518.8	1547.8	1573.9	1603.0	1629.1	1672.7	1713.3	1756.9	1797.5
10°	1210.9	1234.2	1257.4	1295.2	1335.8	1373.6	1411.3	1446.2	1483.9	1518.8	1553.6
12.5°	1094.8	1120.9	1150.0	1173.2	1199.3	1222.6	1245.8	1286.4	1327.1	1367.8	1408.4
15°	999.0	1028.0	1057.0	1086.1	1112.2	1141.2	1167.4	1202.2	1240.0	1274.8	1309.7
17.5°	888.6	917.6	949.6	981.5	1013.5	1045.4	1077.4	1126.7	1176.1	1222.6	1271.9
20°	749.2	789.9	827.6	871.2	914.7	958.3	1001.9	1054.1	1106.4	1155.8	1208.0
22.5°	609.8	647.6	685.3	737.6	789.9	839.2	891.5	961.2	1028.0	1097.7	1164.5
25°	508.2	543.0	577.9	636.0	691.1	749.2	804.4	888.6	969.9	1054.1	1135.4
27.5°	438.5	470.4	502.4	563.4	624.3	682.4	743.4	836.3	926.4	1019.3	1109.3
30°	406.6	426.9	447.2	505.3	563.4	618.5	676.6	766.6	856.7	946.7	1036.7
32.5°	354.3	371.7	389.1	441.4	493.7	543.0	595.3	688.2	778.3	871.2	961.2
35°	313.6	328.1	342.7	392.0	438.5	487.9	534.3	627.2	720.2	813.1	906.0
37.5°	290.4	304.9	316.5	360.1	406.6	450.1	493.7	586.6	676.6	769.5	859.6
40°	273.0	281.7	293.3	336.9	377.5	421.1	461.7	545.9	633.1	717.3	801.5
42.5°	261.4	273.0	281.7	319.4	360.1	397.8	435.6	516.9	598.2	676.6	757.9
45°	258.4	270.1	281.7	313.6	345.6	374.6	406.6	485.0	563.4	641.8	720.2
47.5°	252.6	261.4	273.0	299.1	322.3	348.5	371.7	450.1	528.5	604.0	682.4
50°	249.7	252.6	258.4	281.7	304.9	328.1	351.4	429.8	508.2	586.6	665.0
52.5°	246.8	246.8	246.8	267.2	287.5	304.9	325.2	403.6	485.0	563.4	641.8
55°	229.4	226.5	226.5	246.8	264.3	284.6	302.0	380.4	458.8	534.3	612.7
57.5°	212.0	209.1	206.2	223.6	241.0	258.4	275.9	354.3	435.6	514.0	592.4
60°	194.6	191.7	191.7	209.1	223.6	241.0	255.5	336.9	415.3	496.6	575.0
62.5°	174.2	177.1	177.1	191.7	209.1	223.6	238.1	319.4	403.6	485.0	566.3
65°	159.7	162.6	162.6	180.0	197.5	214.9	232.3	310.7	392.0	470.4	548.8
67.5°	148.1	151.0	151.0	171.3	188.8	209.1	226.5	296.2	368.8	438.5	508.2
70°	136.5	136.5	139.4	159.7	180.0	200.4	220.7	281.7	342.7	400.7	461.7
72.5°	122.0	124.9	127.8	148.1	165.5	185.9	203.3	258.4	313.6	368.8	424.0
75°	107.4	110.3	113.3	130.7	148.1	165.5	182.9	235.2	284.6	336.9	386.2
77.5°	95.8	98.7	101.6	116.2	130.7	145.2	159.7	197.5	238.1	275.9	313.6
80°	78.4	78.4	81.3	92.9	104.5	113.3	124.9	151.0	177.1	200.4	226.5
82.5°	58.1	61.0	61.0	69.7	75.5	84.2	90.0	104.5	116.2	130.7	142.3
85°	49.4	46.5	46.5	52.3	55.2	61.0	63.9	72.6	78.4	87.1	92.9
87.5°	20.3	17.4	17.4	20.3	26.1	29.0	31.9	31.9	34.8	34.8	34.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8
2.5°	2143.1	2148.9	2157.6	2163.4	2177.9	2189.6	2204.1	2215.7	2224.4	2238.9	2233.1
5°	2064.7	2090.8	2117.0	2143.1	2163.4	2183.8	2201.2	2221.5	2244.7	2288.3	2299.9
7.5°	1832.4	1867.2	1899.2	1934.0	1974.7	2015.3	2056.0	2096.6	2134.4	2189.6	2224.4
10°	1603.0	1652.3	1698.8	1748.2	1785.9	1823.7	1858.5	1896.3	1948.5	2003.7	2067.6
12.5°	1457.8	1507.1	1556.5	1605.9	1661.0	1713.3	1768.5	1820.8	1870.1	1913.7	1986.3
15°	1361.9	1417.1	1469.4	1521.7	1588.5	1652.3	1719.1	1783.0	1855.6	1913.7	1963.1
17.5°	1338.7	1405.5	1469.4	1536.2	1605.9	1675.6	1745.3	1815.0	1887.6	1974.7	2038.6
20°	1298.1	1388.1	1478.1	1568.1	1658.1	1745.3	1835.3	1922.4	2018.2	2122.8	2151.8
22.5°	1274.8	1382.3	1492.6	1600.1	1722.0	1846.9	1968.9	2090.8	2192.5	2270.9	2358.0
25°	1271.9	1405.5	1542.0	1675.6	1829.5	1980.5	2134.4	2285.4	2416.1	2494.5	2564.2
27.5°	1269.0	1431.6	1591.4	1751.1	1939.8	2125.7	2314.4	2500.3	2622.3	2735.5	2793.6
30°	1234.2	1428.7	1626.2	1820.8	2032.8	2244.7	2456.7	2668.7	2793.6	2872.0	2901.0
32.5°	1190.6	1420.0	1649.4	1878.8	2119.9	2360.9	2599.0	2840.0	2938.8	3005.6	2982.3
35°	1155.8	1408.4	1658.1	1907.9	2163.4	2421.9	2677.4	2933.0	3075.3	3168.2	3130.4
37.5°	1123.8	1388.1	1652.3	1916.6	2215.7	2514.8	2813.9	3113.0	3249.5	3348.2	3304.7
40°	1086.1	1367.8	1652.3	1934.0	2276.7	2616.4	2959.1	3298.9	3476.0	3560.2	3493.4
42.5°	1054.1	1347.4	1643.6	1936.9	2302.8	2668.7	3034.6	3400.5	3598.0	3717.0	3632.8
45°	1013.5	1306.8	1597.2	1890.5	2294.1	2697.8	3098.5	3502.1	3731.6	3824.5	3708.3
47.5°	969.9	1260.3	1547.8	1835.3	2265.1	2694.8	3124.6	3554.4	3766.4	3876.7	3769.3
50°	955.4	1245.8	1533.3	1823.7	2288.3	2755.8	3220.5	3685.1	3839.0	3929.0	3786.7
52.5°	952.5	1260.3	1571.0	1878.8	2346.4	2811.0	3278.5	3743.2	3868.0	3963.9	3836.1
55°	943.8	1277.7	1608.8	1939.8	2427.7	2918.5	3406.3	3894.2	4019.0	4088.7	3992.9
57.5°	952.5	1312.6	1669.8	2029.8	2532.2	3034.6	3537.0	4039.4	4190.4	4239.7	4219.4
60°	958.3	1341.6	1722.0	2105.4	2596.1	3086.9	3577.6	4068.4	4225.2	4347.2	4370.4
62.5°	943.8	1321.3	1695.9	2073.4	2517.7	2962.0	3406.3	3850.6	4109.1	4289.1	4393.6
65°	900.2	1248.7	1600.1	1948.5	2358.0	2770.4	3179.8	3589.3	3862.2	4129.4	4213.6
67.5°	804.4	1100.6	1396.8	1693.0	2050.2	2407.4	2761.6	3118.8	3461.5	3719.9	3836.1
70°	696.9	929.3	1164.5	1396.8	1722.0	2047.3	2372.5	2697.8	2999.8	3284.3	3394.7
72.5°	606.9	787.0	969.9	1150.0	1382.3	1611.7	1844.0	2073.4	2430.6	2715.2	2822.6
75°	516.9	647.6	775.3	906.0	1065.7	1225.5	1382.3	1542.0	1794.6	2050.2	2157.6
77.5°	397.8	485.0	569.2	653.4	763.7	871.2	981.5	1089.0	1266.1	1457.8	1512.9
80°	275.9	325.2	371.7	421.1	508.2	595.3	682.4	769.5	885.7	993.1	1077.4
82.5°	171.3	203.3	232.3	261.4	331.0	400.7	467.5	537.2	583.7	589.5	673.7
85°	110.3	130.7	148.1	165.5	206.2	249.7	290.4	331.0	296.2	275.9	328.1
87.5°	43.6	55.2	63.9	72.6	69.7	66.8	63.9	61.0	52.3	46.5	58.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676071
 CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8
2.5°	2238.9	2247.6	2256.4	2262.2	2270.9	2273.8	2276.7	2276.7	2279.6	2282.5	2288.3
5°	2346.4	2363.8	2381.2	2395.7	2413.2	2427.7	2439.3	2453.8	2465.4	2465.4	2462.5
7.5°	2256.4	2299.9	2343.5	2387.0	2430.6	2462.5	2491.6	2523.5	2552.6	2558.4	2564.2
10°	2137.3	2183.8	2227.3	2273.8	2317.3	2366.7	2413.2	2459.6	2509.0	2517.7	2529.3
12.5°	2026.9	2082.1	2137.3	2189.6	2244.7	2279.6	2314.4	2346.4	2381.2	2404.5	2427.7
15°	2024.0	2070.5	2117.0	2160.5	2207.0	2227.3	2247.6	2265.1	2285.4	2285.4	2288.3
17.5°	2090.8	2119.9	2148.9	2175.0	2204.1	2207.0	2212.8	2215.7	2218.6	2209.9	2201.2
20°	2221.5	2233.1	2244.7	2256.4	2268.0	2247.6	2230.2	2209.9	2189.6	2166.3	2146.0
22.5°	2413.2	2387.0	2360.9	2334.8	2308.6	2273.8	2236.0	2201.2	2163.4	2134.4	2105.4
25°	2593.2	2561.3	2529.3	2497.4	2465.4	2389.9	2314.4	2236.0	2160.5	2128.6	2096.6
27.5°	2834.2	2784.9	2735.5	2686.1	2636.8	2535.1	2433.5	2331.9	2230.2	2175.0	2122.8
30°	2892.3	2837.1	2782.0	2723.9	2668.7	2570.0	2474.1	2375.4	2276.7	2212.8	2151.8
32.5°	2976.5	2912.6	2848.8	2784.9	2721.0	2625.2	2529.3	2430.6	2334.8	2276.7	2215.7
35°	3115.9	3043.3	2970.7	2895.2	2822.6	2723.9	2628.1	2529.3	2430.6	2363.8	2299.9
37.5°	3235.0	3150.8	3066.6	2982.3	2898.1	2811.0	2721.0	2633.9	2543.8	2477.1	2413.2
40°	3368.6	3275.6	3182.7	3092.7	2999.8	2918.5	2837.1	2752.9	2671.6	2619.3	2567.1
42.5°	3484.7	3371.5	3261.1	3150.8	3037.5	2982.3	2930.1	2874.9	2819.7	2793.6	2764.5
45°	3566.0	3461.5	3354.0	3249.5	3145.0	3104.3	3063.6	3023.0	2982.3	3008.5	3034.6
47.5°	3600.9	3516.7	3435.4	3354.0	3269.8	3284.3	3298.9	3310.5	3325.0	3359.8	3397.6
50°	3632.8	3586.4	3537.0	3490.5	3441.2	3496.3	3548.6	3603.8	3659.0	3731.6	3804.2
52.5°	3696.7	3670.6	3647.3	3621.2	3595.1	3690.9	3786.7	3882.6	3978.4	4059.7	4141.0
55°	3888.4	3868.0	3847.7	3824.5	3804.2	3940.6	4074.2	4210.7	4347.2	4431.4	4515.6
57.5°	4152.6	4141.0	4126.5	4114.9	4100.4	4233.9	4364.6	4495.3	4628.9	4710.2	4794.4
60°	4353.0	4355.9	4355.9	4358.8	4358.8	4460.4	4562.1	4666.6	4768.3	4838.0	4910.5
62.5°	4460.4	4454.6	4448.8	4443.0	4437.2	4521.4	4605.6	4689.8	4774.1	4826.3	4878.6
65°	4344.3	4376.2	4408.2	4440.1	4472.1	4483.7	4492.4	4504.0	4512.7	4544.7	4576.6
67.5°	3955.2	4019.0	4080.0	4143.9	4204.9	4161.3	4120.7	4077.1	4033.6	4042.3	4048.1
70°	3522.5	3595.1	3670.6	3743.2	3815.8	3714.1	3612.5	3507.9	3406.3	3371.5	3336.6
72.5°	2970.7	3034.6	3101.4	3165.3	3229.2	3104.3	2982.3	2857.5	2732.6	2671.6	2610.6
75°	2270.9	2346.4	2424.8	2500.3	2575.8	2436.4	2294.1	2154.7	2012.4	1971.8	1934.0
77.5°	1655.2	1745.3	1835.3	1925.3	2015.3	1890.5	1765.6	1637.8	1512.9	1489.7	1466.5
80°	1205.1	1274.8	1341.6	1411.3	1478.1	1405.5	1332.9	1260.3	1187.7	1184.8	1181.9
82.5°	813.1	874.1	932.2	993.1	1051.2	1022.2	996.0	967.0	938.0	967.0	999.0
85°	418.2	502.4	589.5	673.7	757.9	749.2	743.4	734.7	726.0	763.7	798.6
87.5°	84.2	156.8	229.4	299.1	371.7	354.3	336.9	316.5	299.1	310.7	319.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8
2.5°	2291.2	2294.1	2294.1	2294.1	2294.1	2294.1	2288.3	2285.4	2279.6	2273.8	2265.1
5°	2462.5	2459.6	2448.0	2436.4	2421.9	2410.3	2401.6	2389.9	2381.2	2369.6	2352.2
7.5°	2570.0	2575.8	2555.5	2538.0	2517.7	2497.4	2477.1	2456.7	2436.4	2416.1	2375.4
10°	2538.0	2546.7	2535.1	2523.5	2509.0	2497.4	2474.1	2448.0	2424.8	2398.6	2349.3
12.5°	2448.0	2471.2	2465.4	2459.6	2453.8	2448.0	2433.5	2416.1	2401.6	2384.1	2329.0
15°	2288.3	2288.3	2291.2	2294.1	2294.1	2297.0	2299.9	2302.8	2305.7	2308.6	2276.7
17.5°	2192.5	2183.8	2183.8	2183.8	2183.8	2183.8	2195.4	2209.9	2221.5	2233.1	2224.4
20°	2122.8	2102.4	2099.5	2099.5	2096.6	2093.7	2114.1	2137.3	2157.6	2177.9	2189.6
22.5°	2076.3	2047.3	2044.4	2041.5	2038.6	2035.7	2061.8	2087.9	2114.1	2140.2	2180.9
25°	2064.7	2032.8	2035.7	2038.6	2038.6	2041.5	2061.8	2082.1	2102.4	2122.8	2192.5
27.5°	2067.6	2015.3	2018.2	2021.1	2021.1	2024.0	2056.0	2085.0	2117.0	2146.0	2233.1
30°	2087.9	2026.9	2021.1	2015.3	2009.5	2003.7	2047.3	2090.8	2134.4	2177.9	2244.7
32.5°	2157.6	2099.5	2085.0	2070.5	2056.0	2041.5	2093.7	2143.1	2195.4	2244.7	2299.9
35°	2233.1	2169.2	2163.4	2157.6	2148.9	2143.1	2189.6	2238.9	2285.4	2331.9	2381.2
37.5°	2346.4	2282.5	2276.7	2268.0	2262.2	2253.5	2305.7	2355.1	2407.4	2456.7	2500.3
40°	2514.8	2462.5	2459.6	2459.6	2456.7	2453.8	2494.5	2538.0	2578.7	2619.3	2648.4
42.5°	2738.4	2712.3	2721.0	2732.6	2741.3	2750.0	2782.0	2816.8	2848.8	2880.7	2872.0
45°	3060.7	3086.9	3089.8	3092.7	3095.6	3098.5	3107.2	3118.8	3127.5	3136.2	3101.4
47.5°	3432.4	3467.3	3484.7	3502.1	3516.7	3534.1	3522.5	3507.9	3496.3	3481.8	3394.7
50°	3873.8	3946.4	3943.5	3940.6	3934.8	3931.9	3908.7	3885.5	3859.3	3836.1	3708.3
52.5°	4222.3	4303.6	4318.1	4332.7	4347.2	4361.7	4318.1	4274.6	4228.1	4184.6	4024.8
55°	4596.9	4681.1	4684.0	4686.9	4686.9	4689.8	4628.9	4567.9	4504.0	4443.0	4277.5
57.5°	4875.7	4957.0	4948.3	4942.5	4933.8	4925.1	4852.5	4779.9	4707.3	4634.7	4469.2
60°	4980.2	5049.9	5032.5	5015.1	4994.8	4977.3	4922.2	4867.0	4808.9	4753.7	4594.0
62.5°	4930.9	4983.1	4957.0	4933.8	4907.6	4881.5	4811.8	4739.2	4669.5	4596.9	4480.8
65°	4605.6	4637.6	4602.7	4570.8	4538.8	4504.0	4445.9	4387.8	4326.9	4268.8	4190.4
67.5°	4056.8	4062.6	4059.7	4056.8	4053.9	4051.0	3966.8	3882.6	3795.4	3711.2	3705.4
70°	3304.7	3269.8	3275.6	3284.3	3290.2	3296.0	3232.1	3171.1	3107.2	3043.3	3072.4
72.5°	2549.7	2488.7	2503.2	2520.6	2535.1	2549.7	2497.4	2448.0	2395.7	2343.5	2384.1
75°	1893.4	1855.6	1870.1	1887.6	1902.1	1916.6	1896.3	1875.9	1852.7	1832.4	1870.1
77.5°	1443.3	1420.0	1422.9	1422.9	1425.8	1425.8	1428.7	1434.5	1437.4	1440.4	1481.0
80°	1176.1	1173.2	1170.3	1167.4	1161.6	1158.7	1187.7	1216.7	1245.8	1274.8	1295.2
82.5°	1028.0	1057.0	1039.6	1025.1	1007.7	990.2	1016.4	1042.5	1068.6	1094.8	1086.1
85°	836.3	871.2	839.2	807.3	772.4	740.5	763.7	784.1	807.3	827.6	816.0
87.5°	331.0	339.8	287.5	238.1	185.9	133.6	212.0	287.5	365.9	441.4	453.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676071

CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8	2090.8
2.5°	2256.4	2244.7	2236.0	2233.1	2227.3	2224.4	2218.6	2212.8	2204.1	2198.3	2189.6
5°	2331.9	2314.4	2294.1	2265.1	2238.9	2209.9	2180.9	2154.7	2128.6	2099.5	2073.4
7.5°	2334.8	2294.1	2253.5	2215.7	2175.0	2137.3	2096.6	2061.8	2024.0	1986.3	1951.4
10°	2302.8	2253.5	2204.1	2154.7	2108.3	2058.9	2009.5	1968.9	1925.3	1881.7	1841.1
12.5°	2276.7	2221.5	2166.3	2108.3	2053.1	1995.0	1936.9	1896.3	1855.6	1815.0	1774.3
15°	2244.7	2209.9	2177.9	2125.7	2073.4	2021.1	1968.9	1913.7	1861.4	1806.2	1751.1
17.5°	2218.6	2209.9	2201.2	2166.3	2131.5	2093.7	2058.9	2003.7	1948.5	1890.5	1835.3
20°	2204.1	2215.7	2227.3	2209.9	2192.5	2172.1	2154.7	2114.1	2073.4	2029.8	1989.2
22.5°	2221.5	2265.1	2305.7	2308.6	2314.4	2317.3	2320.2	2282.5	2244.7	2204.1	2166.3
25°	2262.2	2331.9	2401.6	2439.3	2477.1	2517.7	2555.5	2532.2	2509.0	2485.8	2462.5
27.5°	2317.3	2404.5	2491.6	2546.7	2599.0	2654.2	2709.4	2706.5	2703.6	2697.8	2694.8
30°	2308.6	2375.4	2442.2	2509.0	2575.8	2642.6	2709.4	2744.2	2776.2	2811.0	2845.9
32.5°	2358.0	2413.2	2471.2	2540.9	2610.6	2683.2	2752.9	2825.5	2895.2	2967.8	3040.4
35°	2433.5	2482.9	2535.1	2610.6	2689.0	2764.5	2842.9	2930.1	3020.1	3110.1	3197.2
37.5°	2546.7	2590.3	2636.8	2700.7	2767.4	2831.3	2898.1	3025.9	3153.7	3284.3	3412.1
40°	2677.4	2706.5	2735.5	2796.5	2857.5	2918.5	2979.4	3139.2	3298.9	3458.6	3618.3
42.5°	2866.2	2857.5	2848.8	2898.1	2950.4	2999.8	3052.0	3197.2	3342.4	3487.6	3632.8
45°	3066.6	3031.7	2996.9	3020.1	3046.2	3069.5	3095.6	3243.7	3391.8	3542.8	3690.9
47.5°	3307.6	3220.5	3133.3	3113.0	3092.7	3069.5	3049.1	3208.8	3368.6	3531.2	3690.9
50°	3580.5	3449.9	3322.1	3269.8	3214.7	3162.4	3107.2	3237.9	3371.5	3505.0	3635.7
52.5°	3865.1	3702.5	3542.8	3461.5	3380.2	3296.0	3214.7	3325.0	3438.3	3551.5	3661.9
55°	4109.1	3943.5	3775.1	3679.3	3583.5	3487.6	3391.8	3502.1	3612.5	3722.8	3833.2
57.5°	4303.6	4138.1	3972.6	3882.6	3789.6	3699.6	3606.7	3711.2	3818.7	3926.1	4030.7
60°	4437.2	4277.5	4117.8	4030.7	3943.5	3856.4	3769.3	3894.2	4019.0	4146.8	4271.7
62.5°	4367.5	4251.4	4135.2	4097.4	4059.7	4019.0	3981.3	4100.4	4216.5	4335.6	4454.6
65°	4112.0	4033.6	3955.2	3992.9	4033.6	4071.3	4112.0	4190.4	4268.8	4350.1	4428.5
67.5°	3696.7	3690.9	3682.2	3766.4	3850.6	3937.7	4021.9	4074.2	4123.6	4175.9	4228.1
70°	3101.4	3133.3	3162.4	3307.6	3452.8	3598.0	3743.2	3763.5	3783.8	3804.2	3824.5
72.5°	2427.7	2468.3	2511.9	2703.6	2892.3	3084.0	3275.6	3264.0	3252.4	3237.9	3226.3
75°	1910.8	1948.5	1989.2	2166.3	2343.5	2520.6	2697.8	2648.4	2601.9	2552.6	2503.2
77.5°	1524.6	1565.2	1608.8	1774.3	1939.8	2108.3	2273.8	2154.7	2035.7	1916.6	1797.5
80°	1312.6	1332.9	1350.3	1463.6	1573.9	1687.2	1800.4	1678.5	1553.6	1428.7	1306.8
82.5°	1077.4	1065.7	1057.0	1123.8	1190.6	1257.4	1324.2	1208.0	1091.9	972.8	856.7
85°	804.4	792.8	781.2	816.0	850.9	888.6	923.5	789.9	656.3	519.8	386.2
87.5°	467.5	479.1	490.8	528.5	566.3	606.9	644.7	508.2	371.7	232.3	95.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676071
 CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676071
 CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	2090.8	2090.8
2.5°	2172.1	2157.6
5°	2053.1	2032.8
7.5°	1922.4	1896.3
10°	1803.3	1768.5
12.5°	1727.8	1684.3
15°	1698.8	1646.5
17.5°	1785.9	1736.6
20°	1919.5	1852.7
22.5°	2082.1	2000.8
25°	2363.8	2265.1
27.5°	2593.2	2491.6
30°	2735.5	2625.2
32.5°	2892.3	2747.1
35°	3054.9	2915.5
37.5°	3252.4	3095.6
40°	3455.7	3293.1
42.5°	3525.4	3420.8
45°	3592.2	3493.4
47.5°	3606.7	3525.4
50°	3621.2	3609.6
52.5°	3661.9	3659.0
55°	3836.1	3839.0
57.5°	4051.0	4068.4
60°	4248.5	4228.1
62.5°	4350.1	4245.5
65°	4280.4	4135.2
67.5°	4071.3	3914.5
70°	3612.5	3400.5
72.5°	3040.4	2854.6
75°	2343.5	2186.7
77.5°	1666.9	1536.2
80°	1173.2	1042.5
82.5°	752.1	647.6
85°	339.8	296.2
87.5°	95.8	92.9
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P676071
CATALOG NUMBER: CCW-SA-2C-850-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)